

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332296-840

Luminaire Tested: **S123RDIP-S560D1195U840-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332296-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S560D1195U840-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1195 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6614.9 lumens
Efficiency: N/A
Efficacy: 133.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 49.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332296-840

CATALOG NUMBER: S123RDIP-S560D1195U840-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332296-840

CATALOG NUMBER: S123RDIP-S560D1195U840-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	34
1	95	91	87	84	85	82	79	76	66	64	62	51	50	48	37	36	36	29
2	86	79	74	69	78	72	67	63	58	55	52	45	43	41	33	32	31	25
3	79	70	63	58	71	64	58	53	52	47	44	40	37	35	30	28	27	22
4	72	62	55	49	65	57	50	45	46	41	38	36	33	30	27	25	23	19
5	67	56	48	42	60	51	44	39	41	36	33	32	29	26	24	22	20	17
6	61	50	42	37	55	45	39	34	37	32	29	29	26	23	22	20	18	15
7	57	45	37	32	51	41	34	30	34	29	25	27	23	21	20	18	16	13
8	53	41	33	28	47	37	31	26	31	26	22	25	21	18	19	16	15	12
9	49	37	30	25	44	34	28	23	28	23	20	23	19	17	17	15	13	11
10	46	34	27	23	41	31	25	21	26	21	18	21	17	15	16	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9725	9725	9725	9725
5°	11594	9767	8602	9767
10°	14476	9711	7770	9711
15°	16992	9611	7086	9611
20°	18963	9464	6504	9464
25°	18659	9308	6147	9308
30°	13412	9163	5778	9163
35°	8956	8976	5540	8976
40°	6598	8751	5295	8751
45°	5535	8356	5051	8356
50°	4883	7839	4716	7839
55°	4282	7246	4252	7246
60°	3813	6678	3899	6678
65°	3349	6067	3627	6067
70°	2628	5526	3311	5526
75°	2316	4824	3023	4824
80°	2015	4097	2975	4097
85°	1618	3298	3149	3298



TEST NUMBER: P332296-840

CATALOG NUMBER: S123RDIP-S560D1195U840-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.9	1.3
10°-20°	277.6	4.2
20°-30°	436.1	6.6
30°-40°	455.0	6.9
40°-50°	389.4	5.9
50°-60°	296.8	4.5
60°-70°	190.2	2.9
70°-80°	91.5	1.4
80°-90°	28.7	0.4
90°-100°	322.6	4.9
100°-110°	913.4	13.8
110°-120°	898.5	13.6
120°-130°	716.7	10.8
130°-140°	565.1	8.5
140°-150°	421.7	6.4
150°-160°	294.0	4.4
160°-170°	172.7	2.6
170°-180°	56.2	0.8
0°-30°	802.6	12.1
0°-40°	1257.6	19.0
0°-60°	1943.7	29.4
0°-90°	2254.2	34.1
90°-120°	2134.4	32.3
90°-150°	3837.9	58.0
90°-180°	4361.0	65.9
0°-180°	6614.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	904	904	904	904	904	
5°	1073	904	796	904	1073	111
15°	1525	862	636	862	1525	432
25°	1571	784	518	784	1571	675
35°	682	683	422	683	682	447
45°	364	549	332	549	364	286
55°	228	386	227	386	228	206
65°	132	238	142	238	132	129
75°	56	116	73	116	56	60
85°	13	27	26	27	13	16
90°	34	2	34	2	34	18
95°	136	40	136	40	136	245
105°	1492	136	1492	136	1492	1472
115°	1815	240	1815	240	1815	1764
125°	1432	334	1432	334	1432	1297
135°	1160	392	1160	392	1160	900
145°	907	447	907	447	907	577
155°	752	508	752	508	752	351
165°	656	555	656	555	656	187
175°	590	578	590	578	590	57
180°	580	580	580	580	580	



TEST NUMBER: P332296-840

CATALOG NUMBER: S123RDIP-S560D1195U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5
2.5°	962.3	963.6	959.6	959.0	954.3	953.1	953.1	946.5	942.5	937.3	934.2
5°	1073.0	1079.1	1076.1	1069.1	1057.5	1054.8	1047.4	1035.8	1022.7	1006.4	998.8
7.5°	1211.1	1219.6	1216.3	1205.6	1193.5	1183.6	1162.9	1143.6	1116.6	1093.0	1072.7
10°	1324.4	1315.5	1308.6	1298.1	1286.9	1268.7	1247.1	1217.3	1182.9	1155.8	1125.6
12.5°	1409.2	1407.8	1398.9	1388.2	1372.3	1355.0	1328.4	1292.1	1252.1	1212.9	1178.5
15°	1524.8	1527.1	1521.3	1510.1	1487.6	1457.0	1416.8	1401.8	1344.5	1301.9	1259.4
17.5°	1604.8	1604.3	1603.5	1587.9	1565.1	1543.3	1506.0	1466.3	1414.5	1354.5	1297.3
20°	1655.5	1651.6	1652.4	1635.0	1618.0	1592.9	1556.5	1498.8	1456.3	1387.0	1327.9
22.5°	1654.3	1653.5	1656.4	1650.4	1638.1	1618.8	1590.2	1541.6	1487.2	1417.3	1350.8
25°	1571.1	1568.1	1586.3	1591.2	1611.0	1614.5	1606.0	1579.3	1527.8	1455.9	1373.5
27.5°	1314.9	1313.2	1347.0	1389.2	1442.8	1484.4	1524.6	1544.0	1527.8	1476.3	1393.8
30°	1079.1	1115.5	1132.6	1193.7	1261.7	1342.9	1414.1	1481.8	1498.4	1476.0	1408.4
32.5°	896.0	927.7	941.9	994.4	1057.8	1153.0	1259.7	1355.5	1423.3	1440.5	1399.7
35°	681.6	682.0	714.4	737.6	796.4	894.2	997.9	1126.3	1253.9	1350.7	1360.8
37.5°	543.8	545.7	565.4	588.5	632.7	684.4	775.7	882.4	1029.9	1178.3	1265.4
40°	469.6	473.0	487.8	510.6	542.3	581.4	652.6	753.1	876.1	1041.3	1176.3
42.5°	421.9	427.6	435.2	452.7	472.3	509.0	566.5	644.2	756.0	912.2	1067.9
45°	363.6	366.7	372.4	380.6	398.4	423.9	462.6	514.8	607.6	733.4	889.3
47.5°	320.7	319.1	325.2	331.8	343.7	361.0	387.0	429.6	495.8	596.6	728.9
50°	291.6	291.2	295.5	300.5	311.7	324.6	345.8	377.9	430.5	514.0	635.1
52.5°	264.4	265.9	268.9	275.2	283.3	293.6	312.7	335.8	381.0	453.1	554.0
55°	228.2	229.3	233.6	237.1	242.9	253.4	265.4	284.7	315.6	365.9	449.1
57.5°	197.5	197.0	201.2	202.0	208.5	217.0	226.3	241.4	263.8	301.1	357.2
60°	177.1	176.0	179.5	182.2	185.6	192.6	200.4	215.1	232.9	260.3	308.3
62.5°	158.5	158.0	160.6	163.3	166.1	172.5	179.0	190.3	204.4	227.5	265.6
65°	131.5	132.7	133.8	135.0	136.5	140.4	146.6	154.3	164.0	180.3	207.7
67.5°	103.3	104.5	104.9	107.2	110.6	113.0	116.8	123.7	130.5	144.1	159.8
70°	83.5	83.1	83.5	84.7	89.0	93.2	98.3	103.3	107.6	117.2	130.4
72.5°	71.8	71.1	72.1	72.3	74.4	75.5	78.8	83.5	89.0	95.5	105.0
75°	55.7	55.7	55.7	55.7	57.3	58.1	59.2	60.4	62.3	65.3	72.3
77.5°	41.2	41.2	41.8	42.1	42.5	42.9	43.6	44.8	45.4	47.2	50.1
80°	32.5	32.9	32.5	32.9	32.9	33.6	34.0	35.2	35.5	37.6	38.7
82.5°	24.4	24.2	24.4	24.8	24.8	25.7	25.7	26.6	26.7	27.6	28.8
85°	13.1	12.4	13.1	12.7	13.5	12.7	13.1	13.9	13.9	14.3	15.9
87.5°	9.9	10.7	9.9	10.0	10.2	10.1	9.8	9.6	10.0	9.9	9.5
90°	34.0	35.2	34.0	32.8	34.0	31.7	30.5	29.3	28.2	29.3	25.9
92.5°	56.6	58.7	57.5	61.0	63.1	69.2	78.4	98.8	136.1	180.5	198.5
95°	136.1	140.8	149.1	159.6	181.9	224.1	286.3	422.4	564.3	695.8	619.6
97.5°	370.5	380.6	412.3	465.1	551.7	692.1	843.3	1052.9	1153.6	1078.2	789.4
100°	735.7	734.5	780.2	865.9	984.4	1151.0	1288.3	1383.3	1342.3	1111.2	750.9
102.5°	1079.2	1106.2	1144.5	1212.2	1304.4	1410.1	1490.1	1493.2	1351.6	1050.2	694.6
105°	1492.5	1498.3	1535.9	1580.4	1634.5	1665.0	1642.6	1525.3	1280.1	943.3	625.4
107.5°	1730.4	1741.2	1753.8	1768.9	1768.0	1726.2	1623.4	1432.8	1154.8	849.0	581.3
110°	1828.1	1830.4	1832.7	1823.3	1790.5	1708.4	1560.5	1344.6	1075.9	795.5	564.3



TEST NUMBER: P332296-840

CATALOG NUMBER: S123RDIP-S560D1195U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1847.8	1847.2	1838.4	1809.3	1749.2	1643.6	1477.9	1257.3	1007.4	759.8	555.0
115°	1815.1	1809.3	1785.7	1734.1	1646.2	1518.2	1345.7	1141.7	924.5	721.5	551.5
117.5°	1711.4	1703.4	1669.6	1610.5	1518.7	1389.0	1234.1	1057.8	874.5	699.0	553.6
120°	1625.1	1618.0	1589.8	1524.1	1431.5	1312.9	1172.2	1013.7	848.3	688.7	557.3
122.5°	1544.3	1535.4	1504.4	1445.3	1362.9	1252.8	1122.4	979.0	826.7	682.2	563.9
125°	1431.5	1423.2	1393.9	1342.3	1267.2	1173.3	1060.7	932.8	799.0	673.5	573.7
127.5°	1338.5	1331.0	1304.4	1260.4	1193.5	1108.0	1006.4	892.4	774.7	669.2	585.0
130°	1286.0	1276.6	1251.9	1209.7	1147.5	1067.7	972.7	867.1	761.4	666.4	592.5
132.5°	1234.4	1227.8	1205.9	1163.7	1105.3	1029.3	940.8	843.6	749.3	665.5	598.1
135°	1160.4	1152.2	1131.0	1095.9	1038.3	971.5	895.2	811.9	733.4	664.1	606.6
137.5°	1082.3	1076.8	1059.0	1023.4	975.0	917.1	851.3	783.0	719.4	661.5	612.3
140°	1027.8	1029.0	1010.3	977.3	932.8	882.3	826.0	766.2	711.0	660.6	616.0
142.5°	977.1	978.3	961.4	932.3	894.3	850.4	801.6	750.2	703.5	658.7	618.8
145°	907.0	904.6	895.2	870.6	841.2	807.3	769.7	730.9	693.5	655.9	620.7
147.5°	849.2	848.3	839.4	822.7	800.4	776.3	746.0	715.3	683.6	651.5	620.7
150°	815.5	815.5	808.4	795.5	777.9	755.6	730.9	704.0	677.0	647.6	620.7
152.5°	787.3	787.3	783.0	771.1	757.3	738.7	716.9	693.7	669.5	643.0	617.8
155°	752.0	750.9	748.6	739.2	728.6	714.6	696.9	678.1	658.2	634.8	614.8
157.5°	719.9	720.1	718.3	711.2	702.1	691.1	677.5	661.8	645.5	627.5	610.9
160°	699.3	700.4	700.4	693.5	685.2	677.0	665.3	652.4	637.1	621.9	608.9
162.5°	680.5	681.7	681.7	675.6	670.1	662.9	652.2	641.1	628.6	616.2	605.2
165°	655.9	655.9	657.0	652.4	647.6	641.8	633.6	626.5	617.1	607.7	599.6
167.5°	632.4	632.4	633.6	630.3	628.2	624.0	619.2	613.9	606.1	599.4	593.9
170°	618.3	618.3	619.6	617.1	616.0	613.6	608.9	605.4	599.6	593.7	590.2
172.5°	605.2	606.1	608.2	605.9	605.6	604.3	600.5	597.9	593.0	589.0	587.3
175°	590.2	591.4	592.5	591.4	591.4	591.4	589.0	587.8	585.5	583.1	583.1
177.5°	581.5	581.5	583.4	582.4	583.4	583.4	582.4	581.5	580.6	579.7	580.6
180°	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7



TEST NUMBER: P332296-840

CATALOG NUMBER: S123RDIP-S560D1195U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5
2.5°	932.9	932.0	927.7	922.7	916.3	911.9	908.5	906.7	901.1	894.2	889.6
5°	990.6	979.0	966.6	951.5	937.6	923.3	914.4	903.9	891.2	876.9	866.8
7.5°	1052.3	1029.6	1005.0	979.8	954.7	932.3	912.5	895.5	875.3	854.7	840.3
10°	1099.6	1066.4	1032.0	996.7	964.6	934.5	911.3	888.5	864.1	840.5	822.7
12.5°	1142.7	1098.9	1059.2	1015.9	974.9	938.9	905.4	878.6	849.3	824.2	803.9
15°	1197.1	1152.3	1104.3	1038.5	984.0	938.4	897.8	862.5	827.0	796.1	776.3
17.5°	1248.0	1180.5	1116.1	1061.2	990.4	933.3	883.7	841.6	802.6	769.8	745.5
20°	1269.1	1203.8	1133.7	1063.7	994.1	930.3	872.6	826.2	785.6	748.4	726.0
22.5°	1281.7	1207.7	1134.0	1058.7	984.8	918.5	861.5	810.4	766.4	731.1	703.5
25°	1296.6	1208.3	1127.1	1052.9	977.4	905.4	837.8	783.7	736.1	698.5	669.1
27.5°	1306.3	1202.5	1106.5	1024.0	947.5	875.9	813.9	756.4	708.1	668.4	636.9
30°	1308.2	1197.9	1090.8	1001.4	923.6	857.9	792.1	737.2	686.2	644.0	614.6
32.5°	1310.6	1186.5	1069.4	974.5	894.9	829.8	770.2	717.7	665.4	623.9	593.9
35°	1300.4	1180.1	1037.0	928.0	848.3	785.2	731.4	683.1	631.7	591.4	560.9
37.5°	1256.5	1155.0	1003.4	875.5	792.1	733.8	689.9	647.8	600.7	557.2	528.5
40°	1212.2	1130.2	977.4	843.6	756.6	696.6	657.1	622.8	577.1	536.4	505.5
42.5°	1146.3	1096.5	952.7	810.2	716.3	658.5	625.3	593.0	553.0	511.7	482.6
45°	1025.4	1032.0	902.0	757.0	660.7	602.6	571.3	548.9	513.3	479.3	449.5
47.5°	873.7	935.2	842.5	700.2	602.0	547.4	520.1	500.5	476.6	443.1	416.0
50°	774.8	862.5	794.9	662.2	565.1	511.0	483.9	468.1	447.2	420.8	395.0
52.5°	683.5	777.8	737.3	619.8	525.2	475.6	449.2	436.2	419.6	394.9	371.4
55°	557.3	652.9	643.6	555.8	465.3	420.8	400.7	386.1	374.8	356.3	337.7
57.5°	450.8	541.4	546.2	484.6	412.5	368.6	351.3	340.2	332.9	318.9	301.7
60°	383.7	466.9	483.1	436.7	374.8	336.1	319.1	310.2	304.4	293.2	280.0
62.5°	328.0	398.8	417.2	383.7	338.6	302.4	289.1	280.5	276.6	266.9	255.3
65°	251.1	309.8	327.6	309.0	285.5	256.4	245.6	238.2	234.8	229.3	220.9
67.5°	188.7	231.7	251.2	238.0	229.5	211.2	204.3	200.4	197.2	193.6	186.4
70°	151.6	183.4	203.5	200.0	193.0	183.4	178.3	175.6	172.5	169.5	163.2
72.5°	121.9	143.7	162.6	164.4	158.6	156.7	152.3	151.2	149.3	145.6	142.2
75°	80.9	95.9	109.1	114.1	116.4	118.4	116.4	116.0	115.6	112.6	110.6
77.5°	53.0	61.1	69.4	78.0	81.6	84.2	84.8	86.2	85.2	83.6	82.7
80°	40.6	42.5	48.4	55.7	61.5	63.8	65.3	66.1	65.7	65.3	63.8
82.5°	29.5	31.1	33.8	39.0	43.8	47.8	48.7	48.5	49.4	49.6	48.4
85°	15.9	16.3	17.1	17.8	20.5	24.7	26.0	26.7	27.5	27.5	25.1
87.5°	9.4	8.4	8.3	7.9	8.3	7.9	9.3	10.4	11.1	10.4	11.1
90°	22.3	18.8	15.2	12.9	10.6	7.1	4.6	2.3	4.6	7.1	10.6
92.5°	149.1	98.6	67.9	50.5	40.6	31.4	21.6	14.5	21.6	31.4	40.6
95°	427.1	252.3	152.5	106.7	76.2	56.4	43.4	39.9	43.4	56.4	76.2
97.5°	468.6	271.6	176.2	126.7	96.6	79.3	69.2	68.1	69.2	79.3	96.6
100°	442.3	268.7	186.5	140.8	112.6	96.2	88.0	86.8	88.0	96.2	112.6
102.5°	419.8	272.5	198.7	156.7	131.4	115.9	108.7	106.5	108.7	115.9	131.4
105°	403.6	282.8	219.4	183.0	160.8	146.6	139.7	136.1	139.7	146.6	160.8
107.5°	402.4	302.1	246.4	212.6	191.7	177.8	171.1	167.5	171.1	177.8	191.7
110°	407.2	318.0	265.2	232.3	212.4	199.4	193.6	190.1	193.6	199.4	212.4



TEST NUMBER: P332296-840

CATALOG NUMBER: S123RDIP-S560D1195U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	416.6	334.0	284.9	253.0	233.0	220.2	214.3	210.8	214.3	220.2	233.0
115°	431.8	360.2	315.6	284.0	264.0	252.3	245.2	240.5	245.2	252.3	264.0
117.5°	451.9	388.1	344.1	314.7	292.4	281.6	275.7	270.3	275.7	281.6	292.4
120°	467.0	406.0	363.8	334.4	312.1	300.3	294.5	290.9	294.5	300.3	312.1
122.5°	481.1	424.7	383.4	352.2	330.8	318.2	312.4	308.8	312.4	318.2	330.8
125°	503.3	451.7	410.6	379.0	356.7	343.8	336.8	334.4	336.8	343.8	356.7
127.5°	521.7	475.1	435.6	403.8	379.2	366.1	357.4	353.9	357.4	366.1	379.2
130°	533.8	489.3	450.5	418.9	394.3	380.1	369.6	366.1	369.6	380.1	394.3
132.5°	545.1	501.5	463.7	432.9	408.3	391.4	379.9	375.5	379.9	391.4	408.3
135°	559.7	519.8	483.4	451.7	427.1	409.5	396.6	391.9	396.6	409.5	427.1
137.5°	570.5	532.4	497.5	468.2	443.7	425.0	412.3	407.4	412.3	425.0	443.7
140°	576.1	540.9	506.9	477.6	454.0	435.3	423.5	417.7	423.5	435.3	454.0
142.5°	581.7	547.4	514.4	487.0	463.4	446.6	433.9	429.0	433.9	446.6	463.4
145°	587.8	556.1	525.6	498.7	478.7	461.1	450.5	447.1	450.5	461.1	478.7
147.5°	591.6	563.2	535.2	512.3	493.0	477.8	467.5	465.3	467.5	477.8	493.0
150°	592.5	567.8	540.9	519.8	503.3	488.1	478.7	477.6	478.7	488.1	503.3
152.5°	594.4	570.7	547.4	527.3	512.7	499.4	490.0	489.8	490.0	499.4	512.7
155°	594.9	576.1	556.1	539.7	526.8	515.1	508.1	508.1	508.1	515.1	526.8
157.5°	596.0	579.2	563.2	550.5	539.5	529.2	523.5	522.6	523.5	529.2	539.5
160°	596.0	582.0	567.8	556.1	548.0	538.6	533.8	533.8	533.8	538.6	548.0
162.5°	595.1	582.9	570.7	560.9	553.6	546.0	542.3	542.3	542.3	546.0	553.6
165°	592.5	584.3	574.9	566.7	562.0	556.1	553.8	555.0	553.8	556.1	562.0
167.5°	590.7	584.1	577.2	572.1	568.9	564.3	563.2	564.6	563.2	564.3	568.9
170°	587.8	583.1	577.2	574.9	572.6	569.1	567.8	570.3	567.8	569.1	572.6
172.5°	586.9	583.1	578.2	576.8	575.4	572.8	572.6	574.0	572.6	572.8	575.4
175°	584.3	582.0	579.7	578.5	578.5	576.1	577.2	578.5	577.2	576.1	578.5
177.5°	582.4	580.6	579.7	579.7	579.7	578.7	579.7	580.6	579.7	578.7	579.7
180°	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7



TEST NUMBER: P332296-840

CATALOG NUMBER: S123RDIP-S560D1195U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5
2.5°	888.1	884.0	881.3	875.0	871.1	866.8	862.4	865.2	864.8	864.5	864.5
5°	858.3	849.4	841.3	830.8	824.3	816.2	809.9	809.2	810.7	805.3	802.2
7.5°	828.8	816.6	805.1	793.6	781.3	771.5	765.5	762.7	758.7	755.4	751.8
10°	808.0	793.8	782.4	768.2	755.1	743.5	736.1	731.0	728.3	725.6	720.6
12.5°	786.7	772.6	758.3	742.1	729.6	716.2	710.7	705.1	699.8	696.8	689.9
15°	755.4	737.2	722.2	705.1	691.3	678.0	670.3	659.1	657.5	653.7	646.7
17.5°	724.1	704.4	683.6	671.0	655.2	641.6	629.8	626.0	614.9	610.8	604.7
20°	699.3	681.2	665.3	648.6	625.8	613.1	603.8	598.7	589.9	584.4	580.6
22.5°	678.0	659.4	641.2	621.8	602.9	588.7	581.8	574.0	569.2	561.6	557.3
25°	647.5	627.4	605.3	584.4	570.9	560.1	549.3	542.3	535.3	531.8	524.1
27.5°	612.1	591.1	570.5	554.6	538.0	527.3	517.5	511.3	502.9	497.1	492.8
30°	592.6	567.8	550.1	535.7	514.4	504.4	497.1	489.3	483.1	477.0	472.6
32.5°	570.0	547.3	530.5	512.8	496.4	485.5	475.9	469.2	463.9	458.1	453.8
35°	534.5	515.6	498.2	480.4	468.4	457.2	446.0	440.2	435.2	429.7	425.9
37.5°	502.5	484.8	468.3	451.4	436.6	427.4	418.4	413.9	407.2	403.5	399.6
40°	482.7	465.3	447.6	431.3	415.8	408.9	400.7	394.2	388.0	385.3	381.0
42.5°	461.1	443.6	428.7	411.1	398.5	389.0	381.5	374.4	369.7	365.8	363.3
45°	429.0	413.4	398.8	381.4	369.4	361.2	352.7	346.2	341.9	339.2	335.0
47.5°	397.8	382.3	367.4	352.2	340.6	331.3	322.9	318.2	312.7	309.3	306.4
50°	375.2	361.2	345.4	331.4	319.9	310.6	303.7	297.8	292.8	288.5	286.6
52.5°	354.5	339.6	325.9	313.0	300.7	290.1	283.9	277.7	274.0	269.0	266.8
55°	320.2	306.0	294.4	281.6	269.6	260.7	253.0	247.5	243.7	238.2	235.2
57.5°	288.1	275.3	261.5	250.4	238.0	230.6	224.1	216.7	212.1	207.8	204.8
60°	266.5	251.8	239.8	229.3	218.5	208.8	203.1	197.2	192.3	187.9	185.3
62.5°	243.9	231.1	219.7	208.3	198.4	190.0	183.3	178.3	174.0	171.3	168.5
65°	209.2	199.2	187.6	178.3	169.1	162.9	157.4	153.2	150.1	148.1	145.8
67.5°	177.4	167.6	157.5	148.3	142.2	137.4	133.9	130.3	128.8	126.2	124.7
70°	156.6	146.6	137.7	130.8	124.5	121.1	118.8	116.0	114.5	111.4	109.9
72.5°	134.1	126.8	120.4	114.6	109.7	106.5	103.6	100.3	97.8	94.4	92.8
75°	105.6	99.1	94.0	90.1	87.1	82.8	78.6	75.0	73.9	72.7	72.3
77.5°	78.2	74.0	70.4	67.2	63.3	60.2	59.3	58.5	58.3	57.7	57.7
80°	61.5	57.7	54.9	51.1	48.8	48.8	48.8	48.0	48.4	48.4	48.4
82.5°	45.7	42.1	40.7	39.3	38.9	39.2	39.2	39.3	39.1	39.7	39.4
85°	23.6	23.9	24.7	24.3	24.7	24.7	25.5	25.1	25.5	24.7	25.5
87.5°	11.2	12.6	13.6	14.6	15.7	16.1	16.2	16.4	17.0	17.2	17.7
90°	12.9	15.2	18.8	22.3	25.9	29.3	28.2	29.3	30.5	31.7	34.0
92.5°	50.5	67.9	98.6	149.1	198.5	180.5	136.1	98.8	78.4	69.2	63.1
95°	106.7	152.5	252.3	427.1	619.6	695.8	564.3	422.4	286.3	224.1	181.9
97.5°	126.7	176.2	271.6	468.6	789.4	1078.2	1153.6	1052.9	843.3	692.1	551.7
100°	140.8	186.5	268.7	442.3	750.9	1111.2	1342.3	1383.3	1288.3	1151.0	984.4
102.5°	156.7	198.7	272.5	419.8	694.6	1050.2	1351.6	1493.2	1490.1	1410.1	1304.4
105°	183.0	219.4	282.8	403.6	625.4	943.3	1280.1	1525.3	1642.6	1665.0	1634.5
107.5°	212.6	246.4	302.1	402.4	581.3	849.0	1154.8	1432.8	1623.4	1726.2	1768.0
110°	232.3	265.2	318.0	407.2	564.3	795.5	1075.9	1344.6	1560.5	1708.4	1790.5



TEST NUMBER: P332296-840

CATALOG NUMBER: S123RDIP-S560D1195U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	253.0	284.9	334.0	416.6	555.0	759.8	1007.4	1257.3	1477.9	1643.6	1749.2
115°	284.0	315.6	360.2	431.8	551.5	721.5	924.5	1141.7	1345.7	1518.2	1646.2
117.5°	314.7	344.1	388.1	451.9	553.6	699.0	874.5	1057.8	1234.1	1389.0	1518.7
120°	334.4	363.8	406.0	467.0	557.3	688.7	848.3	1013.7	1172.2	1312.9	1431.5
122.5°	352.2	383.4	424.7	481.1	563.9	682.2	826.7	979.0	1122.4	1252.8	1362.9
125°	379.0	410.6	451.7	503.3	573.7	673.5	799.0	932.8	1060.7	1173.3	1267.2
127.5°	403.8	435.6	475.1	521.7	585.0	669.2	774.7	892.4	1006.4	1108.0	1193.5
130°	418.9	450.5	489.3	533.8	592.5	666.4	761.4	867.1	972.7	1067.7	1147.5
132.5°	432.9	463.7	501.5	545.1	598.1	665.5	749.3	843.6	940.8	1029.3	1105.3
135°	451.7	483.4	519.8	559.7	606.6	664.1	733.4	811.9	895.2	971.5	1038.3
137.5°	468.2	497.5	532.4	570.5	612.3	661.5	719.4	783.0	851.3	917.1	975.0
140°	477.6	506.9	540.9	576.1	616.0	660.6	711.0	766.2	826.0	882.3	932.8
142.5°	487.0	514.4	547.4	581.7	618.8	658.7	703.5	750.2	801.6	850.4	894.3
145°	498.7	525.6	556.1	587.8	620.7	655.9	693.5	730.9	769.7	807.3	841.2
147.5°	512.3	535.2	563.2	591.6	620.7	651.5	683.6	715.3	746.0	776.3	800.4
150°	519.8	540.9	567.8	592.5	620.7	647.6	677.0	704.0	730.9	755.6	777.9
152.5°	527.3	547.4	570.7	594.4	617.8	643.0	669.5	693.7	716.9	738.7	757.3
155°	539.7	556.1	576.1	594.9	614.8	634.8	658.2	678.1	696.9	714.6	728.6
157.5°	550.5	563.2	579.2	596.0	610.9	627.5	645.5	661.8	677.5	691.1	702.1
160°	556.1	567.8	582.0	596.0	608.9	621.9	637.1	652.4	665.3	677.0	685.2
162.5°	560.9	570.7	582.9	595.1	605.2	616.2	628.6	641.1	652.2	662.9	670.1
165°	566.7	574.9	584.3	592.5	599.6	607.7	617.1	626.5	633.6	641.8	647.6
167.5°	572.1	577.2	584.1	590.7	593.9	599.4	606.1	613.9	619.2	624.0	628.2
170°	574.9	577.2	583.1	587.8	590.2	593.7	599.6	605.4	608.9	613.6	616.0
172.5°	576.8	578.2	583.1	586.9	587.3	589.0	593.0	597.9	600.5	604.3	605.6
175°	578.5	579.7	582.0	584.3	583.1	583.1	585.5	587.8	589.0	591.4	591.4
177.5°	579.7	579.7	580.6	582.4	580.6	579.7	580.6	581.5	582.4	583.4	583.4
180°	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7



TEST NUMBER: P332296-840

CATALOG NUMBER: S123RDIP-S560D1195U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5
2.5°	860.8	860.5	860.8	859.6	860.8	860.5	860.8	864.5	864.5	864.8	865.2
5°	801.0	800.6	799.5	796.1	799.5	800.6	801.0	802.2	805.3	810.7	809.2
7.5°	748.8	748.3	744.9	745.0	744.9	748.3	748.8	751.8	755.4	758.7	762.7
10°	717.9	718.3	713.7	710.9	713.7	718.3	717.9	720.6	725.6	728.3	731.0
12.5°	687.9	686.1	682.4	679.3	682.4	686.1	687.9	689.9	696.8	699.8	705.1
15°	648.2	644.4	635.1	635.9	635.1	644.4	648.2	646.7	653.7	657.5	659.1
17.5°	601.6	598.7	598.6	593.2	598.6	598.7	601.6	604.7	610.8	614.9	626.0
20°	574.4	572.5	573.2	567.8	573.2	572.5	574.4	580.6	584.4	589.9	598.7
22.5°	553.0	551.1	547.9	546.1	547.9	551.1	553.0	557.3	561.6	569.2	574.0
25°	521.8	518.7	515.6	517.6	515.6	518.7	521.8	524.1	531.8	535.3	542.3
27.5°	490.5	488.2	485.1	484.7	485.1	488.2	490.5	492.8	497.1	502.9	511.3
30°	470.7	468.4	466.9	464.9	466.9	468.4	470.7	472.6	477.0	483.1	489.3
32.5°	450.6	450.2	447.4	447.0	447.4	450.2	450.6	453.8	458.1	463.9	469.2
35°	424.3	422.0	421.2	421.6	421.2	422.0	424.3	425.9	429.7	435.2	440.2
37.5°	399.3	396.3	394.9	393.4	394.9	396.3	399.3	399.6	403.5	407.2	413.9
40°	381.4	378.3	377.5	376.8	377.5	378.3	381.4	381.0	385.3	388.0	394.2
42.5°	361.2	360.0	359.6	358.2	359.6	360.0	361.2	363.3	365.8	369.7	374.4
45°	333.8	333.5	331.1	331.8	331.1	333.5	333.8	335.0	339.2	341.9	346.2
47.5°	304.9	303.2	301.5	302.7	301.5	303.2	304.9	306.4	309.3	312.7	318.2
50°	285.1	284.3	280.8	281.6	280.8	284.3	285.1	286.6	288.5	292.8	297.8
52.5°	265.3	262.4	261.1	260.5	261.1	262.4	265.3	266.8	269.0	274.0	277.7
55°	232.5	228.9	227.4	226.6	227.4	228.9	232.5	235.2	238.2	243.7	247.5
57.5°	200.3	199.3	198.1	198.9	198.1	199.3	200.3	204.8	207.8	212.1	216.7
60°	181.4	181.4	181.4	181.1	181.4	181.4	181.4	185.3	187.9	192.3	197.2
62.5°	166.8	165.9	165.6	166.1	165.6	165.9	166.8	168.5	171.3	174.0	178.3
65°	144.6	144.3	142.7	142.4	142.7	144.3	144.6	145.8	148.1	150.1	153.2
67.5°	123.7	122.3	121.9	121.3	121.9	122.3	123.7	124.7	126.2	128.8	130.3
70°	108.0	107.1	104.8	105.2	104.8	107.1	108.0	109.9	111.4	114.5	116.0
72.5°	90.9	90.1	89.7	89.1	89.7	90.1	90.9	92.8	94.4	97.8	100.3
75°	71.9	71.6	71.2	72.7	71.2	71.6	71.9	72.3	72.7	73.9	75.0
77.5°	57.7	57.7	57.9	57.3	57.9	57.7	57.7	57.7	57.7	58.3	58.5
80°	48.4	48.4	48.0	48.0	48.0	48.4	48.4	48.4	48.4	48.4	48.0
82.5°	38.8	39.1	39.3	38.7	39.3	39.1	38.8	39.4	39.7	39.1	39.3
85°	25.5	25.1	26.0	25.5	26.0	25.1	25.5	25.5	24.7	25.5	25.1
87.5°	18.0	17.7	17.9	18.0	17.9	17.7	18.0	17.7	17.2	17.0	16.4
90°	32.8	34.0	35.2	34.0	35.2	34.0	32.8	34.0	31.7	30.5	29.3
92.5°	61.0	57.5	58.7	56.6	58.7	57.5	61.0	63.1	69.2	78.4	98.8
95°	159.6	149.1	140.8	136.1	140.8	149.1	159.6	181.9	224.1	286.3	422.4
97.5°	465.1	412.3	380.6	370.5	380.6	412.3	465.1	551.7	692.1	843.3	1052.9
100°	865.9	780.2	734.5	735.7	734.5	780.2	865.9	984.4	1151.0	1288.3	1383.3
102.5°	1212.2	1144.5	1106.2	1079.2	1106.2	1144.5	1212.2	1304.4	1410.1	1490.1	1493.2
105°	1580.4	1535.9	1498.3	1492.5	1498.3	1535.9	1580.4	1634.5	1665.0	1642.6	1525.3
107.5°	1768.9	1753.8	1741.2	1730.4	1741.2	1753.8	1768.9	1768.0	1726.2	1623.4	1432.8
110°	1823.3	1832.7	1830.4	1828.1	1830.4	1832.7	1823.3	1790.5	1708.4	1560.5	1344.6



TEST NUMBER: P332296-840

CATALOG NUMBER: S123RDIP-S560D1195U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1809.3	1838.4	1847.2	1847.8	1847.2	1838.4	1809.3	1749.2	1643.6	1477.9	1257.3
115°	1734.1	1785.7	1809.3	1815.1	1809.3	1785.7	1734.1	1646.2	1518.2	1345.7	1141.7
117.5°	1610.5	1669.6	1703.4	1711.4	1703.4	1669.6	1610.5	1518.7	1389.0	1234.1	1057.8
120°	1524.1	1589.8	1618.0	1625.1	1618.0	1589.8	1524.1	1431.5	1312.9	1172.2	1013.7
122.5°	1445.3	1504.4	1535.4	1544.3	1535.4	1504.4	1445.3	1362.9	1252.8	1122.4	979.0
125°	1342.3	1393.9	1423.2	1431.5	1423.2	1393.9	1342.3	1267.2	1173.3	1060.7	932.8
127.5°	1260.4	1304.4	1331.0	1338.5	1331.0	1304.4	1260.4	1193.5	1108.0	1006.4	892.4
130°	1209.7	1251.9	1276.6	1286.0	1276.6	1251.9	1209.7	1147.5	1067.7	972.7	867.1
132.5°	1163.7	1205.9	1227.8	1234.4	1227.8	1205.9	1163.7	1105.3	1029.3	940.8	843.6
135°	1095.9	1131.0	1152.2	1160.4	1152.2	1131.0	1095.9	1038.3	971.5	895.2	811.9
137.5°	1023.4	1059.0	1076.8	1082.3	1076.8	1059.0	1023.4	975.0	917.1	851.3	783.0
140°	977.3	1010.3	1029.0	1027.8	1029.0	1010.3	977.3	932.8	882.3	826.0	766.2
142.5°	932.3	961.4	978.3	977.1	978.3	961.4	932.3	894.3	850.4	801.6	750.2
145°	870.6	895.2	904.6	907.0	904.6	895.2	870.6	841.2	807.3	769.7	730.9
147.5°	822.7	839.4	848.3	849.2	848.3	839.4	822.7	800.4	776.3	746.0	715.3
150°	795.5	808.4	815.5	815.5	815.5	808.4	795.5	777.9	755.6	730.9	704.0
152.5°	771.1	783.0	787.3	787.3	787.3	783.0	771.1	757.3	738.7	716.9	693.7
155°	739.2	748.6	750.9	752.0	750.9	748.6	739.2	728.6	714.6	696.9	678.1
157.5°	711.2	718.3	720.1	719.9	720.1	718.3	711.2	702.1	691.1	677.5	661.8
160°	693.5	700.4	700.4	699.3	700.4	700.4	693.5	685.2	677.0	665.3	652.4
162.5°	675.6	681.7	681.7	680.5	681.7	681.7	675.6	670.1	662.9	652.2	641.1
165°	652.4	657.0	655.9	655.9	655.9	657.0	652.4	647.6	641.8	633.6	626.5
167.5°	630.3	633.6	632.4	632.4	632.4	633.6	630.3	628.2	624.0	619.2	613.9
170°	617.1	619.6	618.3	618.3	618.3	619.6	617.1	616.0	613.6	608.9	605.4
172.5°	605.9	608.2	606.1	605.2	606.1	608.2	605.9	605.6	604.3	600.5	597.9
175°	591.4	592.5	591.4	590.2	591.4	592.5	591.4	591.4	591.4	589.0	587.8
177.5°	582.4	583.4	581.5	581.5	581.5	583.4	582.4	583.4	583.4	582.4	581.5
180°	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7



TEST NUMBER: P332296-840

CATALOG NUMBER: S123RDIP-S560D1195U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5
2.5°	862.4	866.8	871.1	875.0	881.3	884.0	888.1	889.6	894.2	901.1	906.7
5°	809.9	816.2	824.3	830.8	841.3	849.4	858.3	866.8	876.9	891.2	903.9
7.5°	765.5	771.5	781.3	793.6	805.1	816.6	828.8	840.3	854.7	875.3	895.5
10°	736.1	743.5	755.1	768.2	782.4	793.8	808.0	822.7	840.5	864.1	888.5
12.5°	710.7	716.2	729.6	742.1	758.3	772.6	786.7	803.9	824.2	849.3	878.6
15°	670.3	678.0	691.3	705.1	722.2	737.2	755.4	776.3	796.1	827.0	862.5
17.5°	629.8	641.6	655.2	671.0	683.6	704.4	724.1	745.5	769.8	802.6	841.6
20°	603.8	613.1	625.8	648.6	665.3	681.2	699.3	726.0	748.4	785.6	826.2
22.5°	581.8	588.7	602.9	621.8	641.2	659.4	678.0	703.5	731.1	766.4	810.4
25°	549.3	560.1	570.9	584.4	605.3	627.4	647.5	669.1	698.5	736.1	783.7
27.5°	517.5	527.3	538.0	554.6	570.5	591.1	612.1	636.9	668.4	708.1	756.4
30°	497.1	504.4	514.4	535.7	550.1	567.8	592.6	614.6	644.0	686.2	737.2
32.5°	475.9	485.5	496.4	512.8	530.5	547.3	570.0	593.9	623.9	665.4	717.7
35°	446.0	457.2	468.4	480.4	498.2	515.6	534.5	560.9	591.4	631.7	683.1
37.5°	418.4	427.4	436.6	451.4	468.3	484.8	502.5	528.5	557.2	600.7	647.8
40°	400.7	408.9	415.8	431.3	447.6	465.3	482.7	505.5	536.4	577.1	622.8
42.5°	381.5	389.0	398.5	411.1	428.7	443.6	461.1	482.6	511.7	553.0	593.0
45°	352.7	361.2	369.4	381.4	398.8	413.4	429.0	449.5	479.3	513.3	548.9
47.5°	322.9	331.3	340.6	352.2	367.4	382.3	397.8	416.0	443.1	476.6	500.5
50°	303.7	310.6	319.9	331.4	345.4	361.2	375.2	395.0	420.8	447.2	468.1
52.5°	283.9	290.1	300.7	313.0	325.9	339.6	354.5	371.4	394.9	419.6	436.2
55°	253.0	260.7	269.6	281.6	294.4	306.0	320.2	337.7	356.3	374.8	386.1
57.5°	224.1	230.6	238.0	250.4	261.5	275.3	288.1	301.7	318.9	332.9	340.2
60°	203.1	208.8	218.5	229.3	239.8	251.8	266.5	280.0	293.2	304.4	310.2
62.5°	183.3	190.0	198.4	208.3	219.7	231.1	243.9	255.3	266.9	276.6	280.5
65°	157.4	162.9	169.1	178.3	187.6	199.2	209.2	220.9	229.3	234.8	238.2
67.5°	133.9	137.4	142.2	148.3	157.5	167.6	177.4	186.4	193.6	197.2	200.4
70°	118.8	121.1	124.5	130.8	137.7	146.6	156.6	163.2	169.5	172.5	175.6
72.5°	103.6	106.5	109.7	114.6	120.4	126.8	134.1	142.2	145.6	149.3	151.2
75°	78.6	82.8	87.1	90.1	94.0	99.1	105.6	110.6	112.6	115.6	116.0
77.5°	59.3	60.2	63.3	67.2	70.4	74.0	78.2	82.7	83.6	85.2	86.2
80°	48.8	48.8	48.8	51.1	54.9	57.7	61.5	63.8	65.3	65.7	66.1
82.5°	39.2	39.2	38.9	39.3	40.7	42.1	45.7	48.4	49.6	49.4	48.5
85°	25.5	24.7	24.7	24.3	24.7	23.9	23.6	25.1	27.5	27.5	26.7
87.5°	16.2	16.1	15.7	14.6	13.6	12.6	11.2	11.1	10.4	11.1	10.4
90°	28.2	29.3	25.9	22.3	18.8	15.2	12.9	10.6	7.1	4.6	2.3
92.5°	136.1	180.5	198.5	149.1	98.6	67.9	50.5	40.6	31.4	21.6	14.5
95°	564.3	695.8	619.6	427.1	252.3	152.5	106.7	76.2	56.4	43.4	39.9
97.5°	1153.6	1078.2	789.4	468.6	271.6	176.2	126.7	96.6	79.3	69.2	68.1
100°	1342.3	1111.2	750.9	442.3	268.7	186.5	140.8	112.6	96.2	88.0	86.8
102.5°	1351.6	1050.2	694.6	419.8	272.5	198.7	156.7	131.4	115.9	108.7	106.5
105°	1280.1	943.3	625.4	403.6	282.8	219.4	183.0	160.8	146.6	139.7	136.1
107.5°	1154.8	849.0	581.3	402.4	302.1	246.4	212.6	191.7	177.8	171.1	167.5
110°	1075.9	795.5	564.3	407.2	318.0	265.2	232.3	212.4	199.4	193.6	190.1



TEST NUMBER: P332296-840

CATALOG NUMBER: S123RDIP-S560D1195U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	1007.4	759.8	555.0	416.6	334.0	284.9	253.0	233.0	220.2	214.3	210.8
115°	924.5	721.5	551.5	431.8	360.2	315.6	284.0	264.0	252.3	245.2	240.5
117.5°	874.5	699.0	553.6	451.9	388.1	344.1	314.7	292.4	281.6	275.7	270.3
120°	848.3	688.7	557.3	467.0	406.0	363.8	334.4	312.1	300.3	294.5	290.9
122.5°	826.7	682.2	563.9	481.1	424.7	383.4	352.2	330.8	318.2	312.4	308.8
125°	799.0	673.5	573.7	503.3	451.7	410.6	379.0	356.7	343.8	336.8	334.4
127.5°	774.7	669.2	585.0	521.7	475.1	435.6	403.8	379.2	366.1	357.4	353.9
130°	761.4	666.4	592.5	533.8	489.3	450.5	418.9	394.3	380.1	369.6	366.1
132.5°	749.3	665.5	598.1	545.1	501.5	463.7	432.9	408.3	391.4	379.9	375.5
135°	733.4	664.1	606.6	559.7	519.8	483.4	451.7	427.1	409.5	396.6	391.9
137.5°	719.4	661.5	612.3	570.5	532.4	497.5	468.2	443.7	425.0	412.3	407.4
140°	711.0	660.6	616.0	576.1	540.9	506.9	477.6	454.0	435.3	423.5	417.7
142.5°	703.5	658.7	618.8	581.7	547.4	514.4	487.0	463.4	446.6	433.9	429.0
145°	693.5	655.9	620.7	587.8	556.1	525.6	498.7	478.7	461.1	450.5	447.1
147.5°	683.6	651.5	620.7	591.6	563.2	535.2	512.3	493.0	477.8	467.5	465.3
150°	677.0	647.6	620.7	592.5	567.8	540.9	519.8	503.3	488.1	478.7	477.6
152.5°	669.5	643.0	617.8	594.4	570.7	547.4	527.3	512.7	499.4	490.0	489.8
155°	658.2	634.8	614.8	594.9	576.1	556.1	539.7	526.8	515.1	508.1	508.1
157.5°	645.5	627.5	610.9	596.0	579.2	563.2	550.5	539.5	529.2	523.5	522.6
160°	637.1	621.9	608.9	596.0	582.0	567.8	556.1	548.0	538.6	533.8	533.8
162.5°	628.6	616.2	605.2	595.1	582.9	570.7	560.9	553.6	546.0	542.3	542.3
165°	617.1	607.7	599.6	592.5	584.3	574.9	566.7	562.0	556.1	553.8	555.0
167.5°	606.1	599.4	593.9	590.7	584.1	577.2	572.1	568.9	564.3	563.2	564.6
170°	599.6	593.7	590.2	587.8	583.1	577.2	574.9	572.6	569.1	567.8	570.3
172.5°	593.0	589.0	587.3	586.9	583.1	578.2	576.8	575.4	572.8	572.6	574.0
175°	585.5	583.1	583.1	584.3	582.0	579.7	578.5	578.5	576.1	577.2	578.5
177.5°	580.6	579.7	580.6	582.4	580.6	579.7	579.7	579.7	578.7	579.7	580.6
180°	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7



TEST NUMBER: P332296-840

CATALOG NUMBER: S123RDIP-S560D1195U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5
2.5°	908.5	911.9	916.3	922.7	927.7	932.0	932.9	934.2	937.3	942.5	946.5
5°	914.4	923.3	937.6	951.5	966.6	979.0	990.6	998.8	1006.4	1022.7	1035.8
7.5°	912.5	932.3	954.7	979.8	1005.0	1029.6	1052.3	1072.7	1093.0	1116.6	1143.6
10°	911.3	934.5	964.6	996.7	1032.0	1066.4	1099.6	1125.6	1155.8	1182.9	1217.3
12.5°	905.4	938.9	974.9	1015.9	1059.2	1098.9	1142.7	1178.5	1212.9	1252.1	1292.1
15°	897.8	938.4	984.0	1038.5	1104.3	1152.3	1197.1	1259.4	1301.9	1344.5	1401.8
17.5°	883.7	933.3	990.4	1061.2	1116.1	1180.5	1248.0	1297.3	1354.5	1414.5	1466.3
20°	872.6	930.3	994.1	1063.7	1133.7	1203.8	1269.1	1327.9	1387.0	1456.3	1498.8
22.5°	861.5	918.5	984.8	1058.7	1134.0	1207.7	1281.7	1350.8	1417.3	1487.2	1541.6
25°	837.8	905.4	977.4	1052.9	1127.1	1208.3	1296.6	1373.5	1455.9	1527.8	1579.3
27.5°	813.9	875.9	947.5	1024.0	1106.5	1202.5	1306.3	1393.8	1476.3	1527.8	1544.0
30°	792.1	857.9	923.6	1001.4	1090.8	1197.9	1308.2	1408.4	1476.0	1498.4	1481.8
32.5°	770.2	829.8	894.9	974.5	1069.4	1186.5	1310.6	1399.7	1440.5	1423.3	1355.5
35°	731.4	785.2	848.3	928.0	1037.0	1180.1	1300.4	1360.8	1350.7	1253.9	1126.3
37.5°	689.9	733.8	792.1	875.5	1003.4	1155.0	1256.5	1265.4	1178.3	1029.9	882.4
40°	657.1	696.6	756.6	843.6	977.4	1130.2	1212.2	1176.3	1041.3	876.1	753.1
42.5°	625.3	658.5	716.3	810.2	952.7	1096.5	1146.3	1067.9	912.2	756.0	644.2
45°	571.3	602.6	660.7	757.0	902.0	1032.0	1025.4	889.3	733.4	607.6	514.8
47.5°	520.1	547.4	602.0	700.2	842.5	935.2	873.7	728.9	596.6	495.8	429.6
50°	483.9	511.0	565.1	662.2	794.9	862.5	774.8	635.1	514.0	430.5	377.9
52.5°	449.2	475.6	525.2	619.8	737.3	777.8	683.5	554.0	453.1	381.0	335.8
55°	400.7	420.8	465.3	555.8	643.6	652.9	557.3	449.1	365.9	315.6	284.7
57.5°	351.3	368.6	412.5	484.6	546.2	541.4	450.8	357.2	301.1	263.8	241.4
60°	319.1	336.1	374.8	436.7	483.1	466.9	383.7	308.3	260.3	232.9	215.1
62.5°	289.1	302.4	338.6	383.7	417.2	398.8	328.0	265.6	227.5	204.4	190.3
65°	245.6	256.4	285.5	309.0	327.6	309.8	251.1	207.7	180.3	164.0	154.3
67.5°	204.3	211.2	229.5	238.0	251.2	231.7	188.7	159.8	144.1	130.5	123.7
70°	178.3	183.4	193.0	200.0	203.5	183.4	151.6	130.4	117.2	107.6	103.3
72.5°	152.3	156.7	158.6	164.4	162.6	143.7	121.9	105.0	95.5	89.0	83.5
75°	116.4	118.4	116.4	114.1	109.1	95.9	80.9	72.3	65.3	62.3	60.4
77.5°	84.8	84.2	81.6	78.0	69.4	61.1	53.0	50.1	47.2	45.4	44.8
80°	65.3	63.8	61.5	55.7	48.4	42.5	40.6	38.7	37.6	35.5	35.2
82.5°	48.7	47.8	43.8	39.0	33.8	31.1	29.5	28.8	27.6	26.7	26.6
85°	26.0	24.7	20.5	17.8	17.1	16.3	15.9	15.9	14.3	13.9	13.9
87.5°	9.3	7.9	8.3	7.9	8.3	8.4	9.4	9.5	9.9	10.0	9.6
90°	4.6	7.1	10.6	12.9	15.2	18.8	22.3	25.9	29.3	28.2	29.3
92.5°	21.6	31.4	40.6	50.5	67.9	98.6	149.1	198.5	180.5	136.1	98.8
95°	43.4	56.4	76.2	106.7	152.5	252.3	427.1	619.6	695.8	564.3	422.4
97.5°	69.2	79.3	96.6	126.7	176.2	271.6	468.6	789.4	1078.2	1153.6	1052.9
100°	88.0	96.2	112.6	140.8	186.5	268.7	442.3	750.9	1111.2	1342.3	1383.3
102.5°	108.7	115.9	131.4	156.7	198.7	272.5	419.8	694.6	1050.2	1351.6	1493.2
105°	139.7	146.6	160.8	183.0	219.4	282.8	403.6	625.4	943.3	1280.1	1525.3
107.5°	171.1	177.8	191.7	212.6	246.4	302.1	402.4	581.3	849.0	1154.8	1432.8
110°	193.6	199.4	212.4	232.3	265.2	318.0	407.2	564.3	795.5	1075.9	1344.6



TEST NUMBER: P332296-840

CATALOG NUMBER: S123RDIP-S560D1195U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	214.3	220.2	233.0	253.0	284.9	334.0	416.6	555.0	759.8	1007.4	1257.3
115°	245.2	252.3	264.0	284.0	315.6	360.2	431.8	551.5	721.5	924.5	1141.7
117.5°	275.7	281.6	292.4	314.7	344.1	388.1	451.9	553.6	699.0	874.5	1057.8
120°	294.5	300.3	312.1	334.4	363.8	406.0	467.0	557.3	688.7	848.3	1013.7
122.5°	312.4	318.2	330.8	352.2	383.4	424.7	481.1	563.9	682.2	826.7	979.0
125°	336.8	343.8	356.7	379.0	410.6	451.7	503.3	573.7	673.5	799.0	932.8
127.5°	357.4	366.1	379.2	403.8	435.6	475.1	521.7	585.0	669.2	774.7	892.4
130°	369.6	380.1	394.3	418.9	450.5	489.3	533.8	592.5	666.4	761.4	867.1
132.5°	379.9	391.4	408.3	432.9	463.7	501.5	545.1	598.1	665.5	749.3	843.6
135°	396.6	409.5	427.1	451.7	483.4	519.8	559.7	606.6	664.1	733.4	811.9
137.5°	412.3	425.0	443.7	468.2	497.5	532.4	570.5	612.3	661.5	719.4	783.0
140°	423.5	435.3	454.0	477.6	506.9	540.9	576.1	616.0	660.6	711.0	766.2
142.5°	433.9	446.6	463.4	487.0	514.4	547.4	581.7	618.8	658.7	703.5	750.2
145°	450.5	461.1	478.7	498.7	525.6	556.1	587.8	620.7	655.9	693.5	730.9
147.5°	467.5	477.8	493.0	512.3	535.2	563.2	591.6	620.7	651.5	683.6	715.3
150°	478.7	488.1	503.3	519.8	540.9	567.8	592.5	620.7	647.6	677.0	704.0
152.5°	490.0	499.4	512.7	527.3	547.4	570.7	594.4	617.8	643.0	669.5	693.7
155°	508.1	515.1	526.8	539.7	556.1	576.1	594.9	614.8	634.8	658.2	678.1
157.5°	523.5	529.2	539.5	550.5	563.2	579.2	596.0	610.9	627.5	645.5	661.8
160°	533.8	538.6	548.0	556.1	567.8	582.0	596.0	608.9	621.9	637.1	652.4
162.5°	542.3	546.0	553.6	560.9	570.7	582.9	595.1	605.2	616.2	628.6	641.1
165°	553.8	556.1	562.0	566.7	574.9	584.3	592.5	599.6	607.7	617.1	626.5
167.5°	563.2	564.3	568.9	572.1	577.2	584.1	590.7	593.9	599.4	606.1	613.9
170°	567.8	569.1	572.6	574.9	577.2	583.1	587.8	590.2	593.7	599.6	605.4
172.5°	572.6	572.8	575.4	576.8	578.2	583.1	586.9	587.3	589.0	593.0	597.9
175°	577.2	576.1	578.5	578.5	579.7	582.0	584.3	583.1	583.1	585.5	587.8
177.5°	579.7	578.7	579.7	579.7	579.7	580.6	582.4	580.6	579.7	580.6	581.5
180°	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7



TEST NUMBER: P332296-840

CATALOG NUMBER: S123RDIP-S560D1195U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	903.5	903.5	903.5	903.5	903.5	903.5	903.5
2.5°	953.1	953.1	954.3	959.0	959.6	963.6	962.3
5°	1047.4	1054.8	1057.5	1069.1	1076.1	1079.1	1073.0
7.5°	1162.9	1183.6	1193.5	1205.6	1216.3	1219.6	1211.1
10°	1247.1	1268.7	1286.9	1298.1	1308.6	1315.5	1324.4
12.5°	1328.4	1355.0	1372.3	1388.2	1398.9	1407.8	1409.2
15°	1416.8	1457.0	1487.6	1510.1	1521.3	1527.1	1524.8
17.5°	1506.0	1543.3	1565.1	1587.9	1603.5	1604.3	1604.8
20°	1556.5	1592.9	1618.0	1635.0	1652.4	1651.6	1655.5
22.5°	1590.2	1618.8	1638.1	1650.4	1656.4	1653.5	1654.3
25°	1606.0	1614.5	1611.0	1591.2	1586.3	1568.1	1571.1
27.5°	1524.6	1484.4	1442.8	1389.2	1347.0	1313.2	1314.9
30°	1414.1	1342.9	1261.7	1193.7	1132.6	1115.5	1079.1
32.5°	1259.7	1153.0	1057.8	994.4	941.9	927.7	896.0
35°	997.9	894.2	796.4	737.6	714.4	682.0	681.6
37.5°	775.7	684.4	632.7	588.5	565.4	545.7	543.8
40°	652.6	581.4	542.3	510.6	487.8	473.0	469.6
42.5°	566.5	509.0	472.3	452.7	435.2	427.6	421.9
45°	462.6	423.9	398.4	380.6	372.4	366.7	363.6
47.5°	387.0	361.0	343.7	331.8	325.2	319.1	320.7
50°	345.8	324.6	311.7	300.5	295.5	291.2	291.6
52.5°	312.7	293.6	283.3	275.2	268.9	265.9	264.4
55°	265.4	253.4	242.9	237.1	233.6	229.3	228.2
57.5°	226.3	217.0	208.5	202.0	201.2	197.0	197.5
60°	200.4	192.6	185.6	182.2	179.5	176.0	177.1
62.5°	179.0	172.5	166.1	163.3	160.6	158.0	158.5
65°	146.6	140.4	136.5	135.0	133.8	132.7	131.5
67.5°	116.8	113.0	110.6	107.2	104.9	104.5	103.3
70°	98.3	93.2	89.0	84.7	83.5	83.1	83.5
72.5°	78.8	75.5	74.4	72.3	72.1	71.1	71.8
75°	59.2	58.1	57.3	55.7	55.7	55.7	55.7
77.5°	43.6	42.9	42.5	42.1	41.8	41.2	41.2
80°	34.0	33.6	32.9	32.9	32.5	32.9	32.5
82.5°	25.7	25.7	24.8	24.8	24.4	24.2	24.4
85°	13.1	12.7	13.5	12.7	13.1	12.4	13.1
87.5°	9.8	10.1	10.2	10.0	9.9	10.7	9.9
90°	30.5	31.7	34.0	32.8	34.0	35.2	34.0
92.5°	78.4	69.2	63.1	61.0	57.5	58.7	56.6
95°	286.3	224.1	181.9	159.6	149.1	140.8	136.1
97.5°	843.3	692.1	551.7	465.1	412.3	380.6	370.5
100°	1288.3	1151.0	984.4	865.9	780.2	734.5	735.7
102.5°	1490.1	1410.1	1304.4	1212.2	1144.5	1106.2	1079.2
105°	1642.6	1665.0	1634.5	1580.4	1535.9	1498.3	1492.5
107.5°	1623.4	1726.2	1768.0	1768.9	1753.8	1741.2	1730.4
110°	1560.5	1708.4	1790.5	1823.3	1832.7	1830.4	1828.1



TEST NUMBER: P332296-840

CATALOG NUMBER: S123RDIP-S560D1195U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1477.9	1643.6	1749.2	1809.3	1838.4	1847.2	1847.8
115°	1345.7	1518.2	1646.2	1734.1	1785.7	1809.3	1815.1
117.5°	1234.1	1389.0	1518.7	1610.5	1669.6	1703.4	1711.4
120°	1172.2	1312.9	1431.5	1524.1	1589.8	1618.0	1625.1
122.5°	1122.4	1252.8	1362.9	1445.3	1504.4	1535.4	1544.3
125°	1060.7	1173.3	1267.2	1342.3	1393.9	1423.2	1431.5
127.5°	1006.4	1108.0	1193.5	1260.4	1304.4	1331.0	1338.5
130°	972.7	1067.7	1147.5	1209.7	1251.9	1276.6	1286.0
132.5°	940.8	1029.3	1105.3	1163.7	1205.9	1227.8	1234.4
135°	895.2	971.5	1038.3	1095.9	1131.0	1152.2	1160.4
137.5°	851.3	917.1	975.0	1023.4	1059.0	1076.8	1082.3
140°	826.0	882.3	932.8	977.3	1010.3	1029.0	1027.8
142.5°	801.6	850.4	894.3	932.3	961.4	978.3	977.1
145°	769.7	807.3	841.2	870.6	895.2	904.6	907.0
147.5°	746.0	776.3	800.4	822.7	839.4	848.3	849.2
150°	730.9	755.6	777.9	795.5	808.4	815.5	815.5
152.5°	716.9	738.7	757.3	771.1	783.0	787.3	787.3
155°	696.9	714.6	728.6	739.2	748.6	750.9	752.0
157.5°	677.5	691.1	702.1	711.2	718.3	720.1	719.9
160°	665.3	677.0	685.2	693.5	700.4	700.4	699.3
162.5°	652.2	662.9	670.1	675.6	681.7	681.7	680.5
165°	633.6	641.8	647.6	652.4	657.0	655.9	655.9
167.5°	619.2	624.0	628.2	630.3	633.6	632.4	632.4
170°	608.9	613.6	616.0	617.1	619.6	618.3	618.3
172.5°	600.5	604.3	605.6	605.9	608.2	606.1	605.2
175°	589.0	591.4	591.4	591.4	592.5	591.4	590.2
177.5°	582.4	583.4	583.4	582.4	583.4	581.5	581.5
180°	579.7	579.7	579.7	579.7	579.7	579.7	579.7

(END OF REPORT)