

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332276-840

Luminaire Tested: **S123RDIP-S560D585U840-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332276-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S560D585U840-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 585 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4616.1 lumens
Efficiency: N/A
Efficacy: 140.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332276-840

CATALOG NUMBER: S123RDIP-S560D585U840-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332276-840

CATALOG NUMBER: S123RDIP-S560D585U840-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49
1	98	94	90	87	90	87	84	81	73	71	69	61	59	58	49	48	48	42
2	90	83	77	72	83	77	71	67	65	61	58	54	52	49	44	42	41	36
3	82	73	66	61	76	68	62	57	58	53	49	48	45	42	40	37	35	31
4	75	65	58	52	69	60	54	49	52	47	43	43	40	37	36	33	31	27
5	69	58	50	45	64	54	47	42	46	41	37	39	35	32	33	30	27	24
6	64	52	45	39	59	49	42	37	42	37	33	36	32	28	30	27	24	21
7	59	48	40	34	55	44	37	33	38	33	29	33	28	25	27	24	22	19
8	55	43	36	31	51	40	34	29	35	30	26	30	26	23	25	22	20	17
9	51	40	32	27	48	37	30	26	32	27	23	28	23	21	23	20	18	16
10	48	36	29	25	44	34	28	23	30	25	21	26	21	19	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9725	9725	9725	9725
5°	11594	9767	8602	9767
10°	14476	9711	7770	9711
15°	16992	9611	7086	9611
20°	18963	9464	6504	9464
25°	18659	9308	6147	9308
30°	13412	9163	5778	9163
35°	8956	8976	5540	8976
40°	6598	8751	5295	8751
45°	5535	8356	5051	8356
50°	4883	7839	4716	7839
55°	4282	7246	4252	7246
60°	3813	6678	3899	6678
65°	3349	6067	3627	6067
70°	2628	5526	3311	5526
75°	2316	4824	3023	4824
80°	2015	4097	2975	4097
85°	1618	3298	3149	3298



TEST NUMBER: P332276-840

CATALOG NUMBER: S123RDIP-S560D585U840-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.9	1.9
10°-20°	277.6	6.0
20°-30°	436.1	9.4
30°-40°	455.0	9.9
40°-50°	389.4	8.4
50°-60°	296.8	6.4
60°-70°	190.2	4.1
70°-80°	91.5	2.0
80°-90°	26.4	0.6
90°-100°	28.2	0.6
100°-110°	134.3	2.9
110°-120°	322.7	7.0
120°-130°	410.9	8.9
130°-140°	439.0	9.5
140°-150°	410.5	8.9
150°-160°	331.2	7.2
160°-170°	213.7	4.6
170°-180°	73.7	1.6
0°-30°	802.6	17.4
0°-40°	1257.6	27.2
0°-60°	1943.7	42.1
0°-90°	2251.9	48.8
90°-120°	485.2	10.5
90°-150°	1745.7	37.8
90°-180°	2364.0	51.2
0°-180°	4616.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	904	904	904	904	904	
5°	1073	904	796	904	1073	111
15°	1525	862	636	862	1525	432
25°	1571	784	518	784	1571	675
35°	682	683	422	683	682	447
45°	364	549	332	549	364	286
55°	228	386	227	386	228	206
65°	132	238	142	238	132	129
75°	56	116	73	116	56	60
85°	13	27	26	27	13	16
90°	17	1	17	1	17	8
95°	22	35	22	35	22	18
105°	25	172	25	172	25	58
115°	339	322	339	322	339	313
125°	463	454	463	454	463	414
135°	571	565	571	565	571	440
145°	658	652	658	652	658	411
155°	717	718	717	718	717	331
165°	756	757	756	757	756	213
175°	772	775	772	775	772	74
180°	775	775	775	775	775	



TEST NUMBER: P332276-840

CATALOG NUMBER: S123RDIP-S560D585U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5
2.5°	962.3	963.6	959.6	959.0	954.3	953.1	953.1	946.5	942.5	937.3	934.2
5°	1073.0	1079.1	1076.1	1069.1	1057.5	1054.8	1047.4	1035.8	1022.7	1006.4	998.8
7.5°	1211.1	1219.6	1216.3	1205.6	1193.5	1183.6	1162.9	1143.6	1116.6	1093.0	1072.7
10°	1324.4	1315.5	1308.6	1298.1	1286.9	1268.7	1247.1	1217.3	1182.9	1155.8	1125.6
12.5°	1409.2	1407.8	1398.9	1388.2	1372.3	1355.0	1328.4	1292.1	1252.1	1212.9	1178.5
15°	1524.8	1527.1	1521.3	1510.1	1487.6	1457.0	1416.8	1401.8	1344.5	1301.9	1259.4
17.5°	1604.8	1604.3	1603.5	1587.9	1565.1	1543.3	1506.0	1466.3	1414.5	1354.5	1297.3
20°	1655.5	1651.6	1652.4	1635.0	1618.0	1592.9	1556.5	1498.8	1456.3	1387.0	1327.9
22.5°	1654.3	1653.5	1656.4	1650.4	1638.1	1618.8	1590.2	1541.6	1487.2	1417.3	1350.8
25°	1571.1	1568.1	1586.3	1591.2	1611.0	1614.5	1606.0	1579.3	1527.8	1455.9	1373.5
27.5°	1314.9	1313.2	1347.0	1389.2	1442.8	1484.4	1524.6	1544.0	1527.8	1476.3	1393.8
30°	1079.1	1115.5	1132.6	1193.7	1261.7	1342.9	1414.1	1481.8	1498.4	1476.0	1408.4
32.5°	896.0	927.7	941.9	994.4	1057.8	1153.0	1259.7	1355.5	1423.3	1440.5	1399.7
35°	681.6	682.0	714.4	737.6	796.4	894.2	997.9	1126.3	1253.9	1350.7	1360.8
37.5°	543.8	545.7	565.4	588.5	632.7	684.4	775.7	882.4	1029.9	1178.3	1265.4
40°	469.6	473.0	487.8	510.6	542.3	581.4	652.6	753.1	876.1	1041.3	1176.3
42.5°	421.9	427.6	435.2	452.7	472.3	509.0	566.5	644.2	756.0	912.2	1067.9
45°	363.6	366.7	372.4	380.6	398.4	423.9	462.6	514.8	607.6	733.4	889.3
47.5°	320.7	319.1	325.2	331.8	343.7	361.0	387.0	429.6	495.8	596.6	728.9
50°	291.6	291.2	295.5	300.5	311.7	324.6	345.8	377.9	430.5	514.0	635.1
52.5°	264.4	265.9	268.9	275.2	283.3	293.6	312.7	335.8	381.0	453.1	554.0
55°	228.2	229.3	233.6	237.1	242.9	253.4	265.4	284.7	315.6	365.9	449.1
57.5°	197.5	197.0	201.2	202.0	208.5	217.0	226.3	241.4	263.8	301.1	357.2
60°	177.1	176.0	179.5	182.2	185.6	192.6	200.4	215.1	232.9	260.3	308.3
62.5°	158.5	158.0	160.6	163.3	166.1	172.5	179.0	190.3	204.4	227.5	265.6
65°	131.5	132.7	133.8	135.0	136.5	140.4	146.6	154.3	164.0	180.3	207.7
67.5°	103.3	104.5	104.9	107.2	110.6	113.0	116.8	123.7	130.5	144.1	159.8
70°	83.5	83.1	83.5	84.7	89.0	93.2	98.3	103.3	107.6	117.2	130.4
72.5°	71.8	71.1	72.1	72.3	74.4	75.5	78.8	83.5	89.0	95.5	105.0
75°	55.7	55.7	55.7	55.7	57.3	58.1	59.2	60.4	62.3	65.3	72.3
77.5°	41.2	41.2	41.8	42.1	42.5	42.9	43.6	44.8	45.4	47.2	50.1
80°	32.5	32.9	32.5	32.9	32.9	33.6	34.0	35.2	35.5	37.6	38.7
82.5°	24.4	24.2	24.4	24.8	24.8	25.7	25.7	26.6	26.7	27.6	28.8
85°	13.1	12.4	13.1	12.7	13.5	12.7	13.1	13.9	13.9	14.3	15.9
87.5°	6.6	7.1	6.5	6.7	6.7	6.9	6.8	6.7	7.2	6.8	6.8
90°	17.3	17.1	16.8	16.6	16.3	15.9	15.3	14.8	14.3	13.8	12.1
92.5°	19.1	19.0	18.8	18.7	18.5	18.0	17.2	16.4	15.6	14.7	13.5
95°	21.9	21.9	21.9	21.9	21.9	21.4	20.5	19.7	18.8	17.9	16.5
97.5°	23.7	23.6	23.4	23.3	23.2	22.6	21.6	20.6	19.6	18.6	27.8
100°	24.2	24.0	23.9	23.8	23.6	23.1	22.1	21.0	20.0	19.0	39.0
102.5°	24.6	24.4	24.2	23.9	23.7	25.2	28.4	31.5	34.7	37.9	59.7
105°	25.3	25.0	24.8	24.5	24.3	35.5	58.2	80.8	103.5	126.1	137.6
107.5°	79.6	96.6	113.7	130.8	147.9	164.7	181.4	197.9	214.6	231.2	229.3
110°	158.3	176.7	195.0	213.3	231.6	242.9	247.1	251.4	255.5	259.7	258.3



TEST NUMBER: P332276-840

CATALOG NUMBER: S123RDIP-S560D585U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	271.8	275.6	279.4	283.4	287.2	289.1	289.0	288.9	288.9	288.8	287.4
115°	338.7	338.2	337.7	337.1	336.6	335.8	334.5	333.2	331.9	330.6	329.4
117.5°	376.3	376.2	376.1	376.0	375.9	375.3	374.3	373.2	372.2	371.1	370.6
120°	402.0	402.0	402.0	402.0	402.0	401.5	400.5	399.5	398.5	397.4	397.1
122.5°	427.4	427.3	427.2	427.1	427.0	426.6	425.9	425.2	424.4	423.7	423.2
125°	463.1	462.8	462.6	462.3	462.1	461.8	461.5	461.3	461.0	460.8	460.3
127.5°	497.5	497.7	498.0	498.2	498.5	498.4	498.0	497.6	497.2	496.8	496.1
130°	519.6	519.8	520.1	520.3	520.6	520.4	519.9	519.4	518.9	518.4	517.9
132.5°	539.8	540.2	540.5	540.9	541.3	541.2	540.7	540.2	539.7	539.2	538.7
135°	570.8	571.2	571.6	572.0	572.3	572.3	572.0	571.6	571.2	570.8	570.3
137.5°	600.0	600.2	600.5	600.7	601.0	600.8	600.2	599.6	599.0	598.3	598.0
140°	617.4	617.7	617.9	618.2	618.4	618.3	617.8	617.3	616.8	616.3	615.9
142.5°	633.6	633.9	634.3	634.7	635.0	635.0	634.6	634.2	633.8	633.4	633.0
145°	658.3	658.3	658.3	658.3	658.3	658.2	657.9	657.7	657.4	657.2	656.9
147.5°	676.8	677.4	677.9	678.5	679.1	679.3	679.0	678.8	678.5	678.3	678.0
150°	690.6	690.9	691.4	691.8	692.2	692.2	692.0	691.7	691.5	691.2	690.9
152.5°	701.7	702.3	702.9	703.5	704.0	704.1	703.6	703.2	702.7	702.3	702.1
155°	717.1	717.9	718.6	719.4	720.1	720.2	719.6	718.9	718.3	717.7	717.5
157.5°	730.1	731.1	732.2	733.1	734.1	734.3	733.5	732.7	732.0	731.1	731.2
160°	738.4	739.3	740.2	741.1	741.9	742.0	741.2	740.5	739.7	739.0	739.1
162.5°	746.3	747.0	747.8	748.6	749.4	749.4	748.5	747.6	746.8	745.9	746.0
165°	755.7	756.6	757.5	758.4	759.3	759.2	758.2	757.2	756.2	755.1	755.3
167.5°	762.4	763.6	764.6	765.6	766.6	766.6	765.6	764.6	763.6	762.4	762.4
170°	766.6	767.7	768.7	769.7	770.7	770.7	769.7	768.7	767.7	766.6	766.6
172.5°	768.9	770.0	771.2	772.3	773.5	773.5	772.4	771.4	770.4	769.4	769.3
175°	772.3	773.5	774.5	775.5	776.5	776.6	775.7	774.8	773.9	773.0	772.8
177.5°	773.5	774.5	775.5	776.5	777.5	777.6	776.8	776.0	775.2	774.4	774.3
180°	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3



TEST NUMBER: P332276-840

CATALOG NUMBER: S123RDIP-S560D585U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5
2.5°	932.9	932.0	927.7	922.7	916.3	911.9	908.5	906.7	901.1	894.2	889.6
5°	990.6	979.0	966.6	951.5	937.6	923.3	914.4	903.9	891.2	876.9	866.8
7.5°	1052.3	1029.6	1005.0	979.8	954.7	932.3	912.5	895.5	875.3	854.7	840.3
10°	1099.6	1066.4	1032.0	996.7	964.6	934.5	911.3	888.5	864.1	840.5	822.7
12.5°	1142.7	1098.9	1059.2	1015.9	974.9	938.9	905.4	878.6	849.3	824.2	803.9
15°	1197.1	1152.3	1104.3	1038.5	984.0	938.4	897.8	862.5	827.0	796.1	776.3
17.5°	1248.0	1180.5	1116.1	1061.2	990.4	933.3	883.7	841.6	802.6	769.8	745.5
20°	1269.1	1203.8	1133.7	1063.7	994.1	930.3	872.6	826.2	785.6	748.4	726.0
22.5°	1281.7	1207.7	1134.0	1058.7	984.8	918.5	861.5	810.4	766.4	731.1	703.5
25°	1296.6	1208.3	1127.1	1052.9	977.4	905.4	837.8	783.7	736.1	698.5	669.1
27.5°	1306.3	1202.5	1106.5	1024.0	947.5	875.9	813.9	756.4	708.1	668.4	636.9
30°	1308.2	1197.9	1090.8	1001.4	923.6	857.9	792.1	737.2	686.2	644.0	614.6
32.5°	1310.6	1186.5	1069.4	974.5	894.9	829.8	770.2	717.7	665.4	623.9	593.9
35°	1300.4	1180.1	1037.0	928.0	848.3	785.2	731.4	683.1	631.7	591.4	560.9
37.5°	1256.5	1155.0	1003.4	875.5	792.1	733.8	689.9	647.8	600.7	557.2	528.5
40°	1212.2	1130.2	977.4	843.6	756.6	696.6	657.1	622.8	577.1	536.4	505.5
42.5°	1146.3	1096.5	952.7	810.2	716.3	658.5	625.3	593.0	553.0	511.7	482.6
45°	1025.4	1032.0	902.0	757.0	660.7	602.6	571.3	548.9	513.3	479.3	449.5
47.5°	873.7	935.2	842.5	700.2	602.0	547.4	520.1	500.5	476.6	443.1	416.0
50°	774.8	862.5	794.9	662.2	565.1	511.0	483.9	468.1	447.2	420.8	395.0
52.5°	683.5	777.8	737.3	619.8	525.2	475.6	449.2	436.2	419.6	394.9	371.4
55°	557.3	652.9	643.6	555.8	465.3	420.8	400.7	386.1	374.8	356.3	337.7
57.5°	450.8	541.4	546.2	484.6	412.5	368.6	351.3	340.2	332.9	318.9	301.7
60°	383.7	466.9	483.1	436.7	374.8	336.1	319.1	310.2	304.4	293.2	280.0
62.5°	328.0	398.8	417.2	383.7	338.6	302.4	289.1	280.5	276.6	266.9	255.3
65°	251.1	309.8	327.6	309.0	285.5	256.4	245.6	238.2	234.8	229.3	220.9
67.5°	188.7	231.7	251.2	238.0	229.5	211.2	204.3	200.4	197.2	193.6	186.4
70°	151.6	183.4	203.5	200.0	193.0	183.4	178.3	175.6	172.5	169.5	163.2
72.5°	121.9	143.7	162.6	164.4	158.6	156.7	152.3	151.2	149.3	145.6	142.2
75°	80.9	95.9	109.1	114.1	116.4	118.4	116.4	116.0	115.6	112.6	110.6
77.5°	53.0	61.1	69.4	78.0	81.6	84.2	84.8	86.2	85.2	83.6	82.7
80°	40.6	42.5	48.4	55.7	61.5	63.8	65.3	66.1	65.7	65.3	63.8
82.5°	29.5	31.1	33.8	39.0	43.8	47.8	48.7	48.5	49.4	49.6	48.4
85°	15.9	16.3	17.1	17.8	20.5	24.7	26.0	26.7	27.5	27.5	25.1
87.5°	7.1	6.4	6.7	6.4	7.1	7.2	8.7	10.0	10.6	9.6	9.9
90°	10.5	8.8	7.2	5.7	4.4	3.1	1.8	0.6	1.8	3.1	4.4
92.5°	12.2	11.0	9.7	9.3	9.6	10.0	10.4	10.7	10.4	10.0	9.6
95°	15.0	13.6	12.2	14.1	19.4	24.6	29.9	35.1	29.9	24.6	19.4
97.5°	37.0	46.2	55.4	61.2	63.5	65.9	68.3	70.6	68.3	65.9	63.5
100°	59.0	78.9	98.9	107.6	105.0	102.5	99.9	97.4	99.9	102.5	105.0
102.5°	81.5	103.3	125.1	135.1	133.3	131.5	129.6	127.7	129.6	131.5	133.3
105°	149.2	160.7	172.2	177.2	175.8	174.5	173.1	171.7	173.1	174.5	175.8
107.5°	227.5	225.7	223.9	222.5	221.4	220.3	219.0	217.9	219.0	220.3	221.4
110°	256.9	255.5	254.2	252.9	251.9	250.9	249.8	248.8	249.8	250.9	251.9



TEST NUMBER: P332276-840

CATALOG NUMBER: S123RDIP-S560D585U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	286.0	284.6	283.2	282.0	281.0	280.1	279.2	278.3	279.2	280.1	281.0
115°	328.3	327.2	326.0	325.1	324.3	323.5	322.8	321.9	322.8	323.5	324.3
117.5°	370.0	369.4	368.8	368.0	367.1	366.2	365.2	364.3	365.2	366.2	367.1
120°	396.7	396.3	395.9	395.2	393.9	392.8	391.6	390.5	391.6	392.8	393.9
122.5°	422.7	422.2	421.7	421.0	420.1	419.1	418.2	417.3	418.2	419.1	420.1
125°	459.8	459.3	458.8	458.0	457.0	456.0	454.9	453.8	454.9	456.0	457.0
127.5°	495.5	494.8	494.2	493.4	492.4	491.4	490.4	489.4	490.4	491.4	492.4
130°	517.4	516.8	516.3	515.5	514.5	513.5	512.5	511.5	512.5	513.5	514.5
132.5°	538.3	537.9	537.5	536.7	535.7	534.7	533.7	532.7	533.7	534.7	535.7
135°	569.8	569.3	568.8	568.2	567.3	566.5	565.8	565.0	565.8	566.5	567.3
137.5°	597.7	597.4	597.2	596.5	595.6	594.6	593.7	592.7	593.7	594.6	595.6
140°	615.5	615.1	614.8	614.2	613.4	612.7	611.9	611.1	611.9	612.7	613.4
142.5°	632.6	632.2	631.8	631.3	630.5	629.8	628.9	628.1	628.9	629.8	630.5
145°	656.7	656.4	656.2	655.6	654.7	653.8	652.9	652.0	652.9	653.8	654.7
147.5°	677.7	677.5	677.2	676.8	676.2	675.7	675.1	674.5	675.1	675.7	676.2
150°	690.6	690.4	690.1	689.8	689.4	689.0	688.7	688.3	688.7	689.0	689.4
152.5°	702.0	701.8	701.7	701.5	701.3	701.0	700.9	700.7	700.9	701.0	701.3
155°	717.4	717.3	717.2	717.2	717.5	717.7	718.0	718.2	718.0	717.7	717.5
157.5°	731.4	731.5	731.6	731.7	731.7	731.7	731.8	731.8	731.8	731.7	731.7
160°	739.2	739.3	739.5	739.6	739.7	739.9	740.0	740.1	740.0	739.9	739.7
162.5°	746.2	746.3	746.4	746.6	747.0	747.3	747.6	748.0	747.6	747.3	747.0
165°	755.4	755.5	755.6	755.9	756.3	756.7	757.0	757.4	757.0	756.7	756.3
167.5°	762.4	762.4	762.4	762.8	763.3	763.8	764.3	764.8	764.3	763.8	763.3
170°	766.6	766.6	766.6	766.9	767.4	767.9	768.4	768.9	768.4	767.9	767.4
172.5°	769.2	769.1	769.0	769.2	769.8	770.4	771.1	771.7	771.1	770.4	769.8
175°	772.7	772.5	772.4	772.7	773.4	774.0	774.7	775.3	774.7	774.0	773.4
177.5°	774.2	774.1	774.0	774.2	774.7	775.2	775.7	776.2	775.7	775.2	774.7
180°	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3



TEST NUMBER: P332276-840

CATALOG NUMBER: S123RDIP-S560D585U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5
2.5°	888.1	884.0	881.3	875.0	871.1	866.8	862.4	865.2	864.8	864.5	864.5
5°	858.3	849.4	841.3	830.8	824.3	816.2	809.9	809.2	810.7	805.3	802.2
7.5°	828.8	816.6	805.1	793.6	781.3	771.5	765.5	762.7	758.7	755.4	751.8
10°	808.0	793.8	782.4	768.2	755.1	743.5	736.1	731.0	728.3	725.6	720.6
12.5°	786.7	772.6	758.3	742.1	729.6	716.2	710.7	705.1	699.8	696.8	689.9
15°	755.4	737.2	722.2	705.1	691.3	678.0	670.3	659.1	657.5	653.7	646.7
17.5°	724.1	704.4	683.6	671.0	655.2	641.6	629.8	626.0	614.9	610.8	604.7
20°	699.3	681.2	665.3	648.6	625.8	613.1	603.8	598.7	589.9	584.4	580.6
22.5°	678.0	659.4	641.2	621.8	602.9	588.7	581.8	574.0	569.2	561.6	557.3
25°	647.5	627.4	605.3	584.4	570.9	560.1	549.3	542.3	535.3	531.8	524.1
27.5°	612.1	591.1	570.5	554.6	538.0	527.3	517.5	511.3	502.9	497.1	492.8
30°	592.6	567.8	550.1	535.7	514.4	504.4	497.1	489.3	483.1	477.0	472.6
32.5°	570.0	547.3	530.5	512.8	496.4	485.5	475.9	469.2	463.9	458.1	453.8
35°	534.5	515.6	498.2	480.4	468.4	457.2	446.0	440.2	435.2	429.7	425.9
37.5°	502.5	484.8	468.3	451.4	436.6	427.4	418.4	413.9	407.2	403.5	399.6
40°	482.7	465.3	447.6	431.3	415.8	408.9	400.7	394.2	388.0	385.3	381.0
42.5°	461.1	443.6	428.7	411.1	398.5	389.0	381.5	374.4	369.7	365.8	363.3
45°	429.0	413.4	398.8	381.4	369.4	361.2	352.7	346.2	341.9	339.2	335.0
47.5°	397.8	382.3	367.4	352.2	340.6	331.3	322.9	318.2	312.7	309.3	306.4
50°	375.2	361.2	345.4	331.4	319.9	310.6	303.7	297.8	292.8	288.5	286.6
52.5°	354.5	339.6	325.9	313.0	300.7	290.1	283.9	277.7	274.0	269.0	266.8
55°	320.2	306.0	294.4	281.6	269.6	260.7	253.0	247.5	243.7	238.2	235.2
57.5°	288.1	275.3	261.5	250.4	238.0	230.6	224.1	216.7	212.1	207.8	204.8
60°	266.5	251.8	239.8	229.3	218.5	208.8	203.1	197.2	192.3	187.9	185.3
62.5°	243.9	231.1	219.7	208.3	198.4	190.0	183.3	178.3	174.0	171.3	168.5
65°	209.2	199.2	187.6	178.3	169.1	162.9	157.4	153.2	150.1	148.1	145.8
67.5°	177.4	167.6	157.5	148.3	142.2	137.4	133.9	130.3	128.8	126.2	124.7
70°	156.6	146.6	137.7	130.8	124.5	121.1	118.8	116.0	114.5	111.4	109.9
72.5°	134.1	126.8	120.4	114.6	109.7	106.5	103.6	100.3	97.8	94.4	92.8
75°	105.6	99.1	94.0	90.1	87.1	82.8	78.6	75.0	73.9	72.7	72.3
77.5°	78.2	74.0	70.4	67.2	63.3	60.2	59.3	58.5	58.3	57.7	57.7
80°	61.5	57.7	54.9	51.1	48.8	48.8	48.8	48.0	48.4	48.4	48.4
82.5°	45.7	42.1	40.7	39.3	38.9	39.2	39.2	39.3	39.1	39.7	39.4
85°	23.6	23.9	24.7	24.3	24.7	24.7	25.5	25.1	25.5	24.7	25.5
87.5°	9.8	11.0	11.7	12.3	12.9	12.9	13.4	13.5	13.9	14.0	14.0
90°	5.7	7.2	8.8	10.5	12.1	13.8	14.3	14.8	15.3	15.9	16.3
92.5°	9.3	9.7	11.0	12.2	13.5	14.7	15.6	16.4	17.2	18.0	18.5
95°	14.1	12.2	13.6	15.0	16.5	17.9	18.8	19.7	20.5	21.4	21.9
97.5°	61.2	55.4	46.2	37.0	27.8	18.6	19.6	20.6	21.6	22.6	23.2
100°	107.6	98.9	78.9	59.0	39.0	19.0	20.0	21.0	22.1	23.1	23.6
102.5°	135.1	125.1	103.3	81.5	59.7	37.9	34.7	31.5	28.4	25.2	23.7
105°	177.2	172.2	160.7	149.2	137.6	126.1	103.5	80.8	58.2	35.5	24.3
107.5°	222.5	223.9	225.7	227.5	229.3	231.2	214.6	197.9	181.4	164.7	147.9
110°	252.9	254.2	255.5	256.9	258.3	259.7	255.5	251.4	247.1	242.9	231.6



TEST NUMBER: P332276-840

CATALOG NUMBER: S123RDIP-S560D585U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	282.0	283.2	284.6	286.0	287.4	288.8	288.9	288.9	289.0	289.1	287.2
115°	325.1	326.0	327.2	328.3	329.4	330.6	331.9	333.2	334.5	335.8	336.6
117.5°	368.0	368.8	369.4	370.0	370.6	371.1	372.2	373.2	374.3	375.3	375.9
120°	395.2	395.9	396.3	396.7	397.1	397.4	398.5	399.5	400.5	401.5	402.0
122.5°	421.0	421.7	422.2	422.7	423.2	423.7	424.4	425.2	425.9	426.6	427.0
125°	458.0	458.8	459.3	459.8	460.3	460.8	461.0	461.3	461.5	461.8	462.1
127.5°	493.4	494.2	494.8	495.5	496.1	496.8	497.2	497.6	498.0	498.4	498.5
130°	515.5	516.3	516.8	517.4	517.9	518.4	518.9	519.4	519.9	520.4	520.6
132.5°	536.7	537.5	537.9	538.3	538.7	539.2	539.7	540.2	540.7	541.2	541.3
135°	568.2	568.8	569.3	569.8	570.3	570.8	571.2	571.6	572.0	572.3	572.3
137.5°	596.5	597.2	597.4	597.7	598.0	598.3	599.0	599.6	600.2	600.8	601.0
140°	614.2	614.8	615.1	615.5	615.9	616.3	616.8	617.3	617.8	618.3	618.4
142.5°	631.3	631.8	632.2	632.6	633.0	633.4	633.8	634.2	634.6	635.0	635.0
145°	655.6	656.2	656.4	656.7	656.9	657.2	657.4	657.7	657.9	658.2	658.3
147.5°	676.8	677.2	677.5	677.7	678.0	678.3	678.5	678.8	679.0	679.3	679.1
150°	689.8	690.1	690.4	690.6	690.9	691.2	691.5	691.7	692.0	692.2	692.2
152.5°	701.5	701.7	701.8	702.0	702.1	702.3	702.7	703.2	703.6	704.1	704.0
155°	717.2	717.2	717.3	717.4	717.5	717.7	718.3	718.9	719.6	720.2	720.1
157.5°	731.7	731.6	731.5	731.4	731.2	731.1	732.0	732.7	733.5	734.3	734.1
160°	739.6	739.5	739.3	739.2	739.1	739.0	739.7	740.5	741.2	742.0	741.9
162.5°	746.6	746.4	746.3	746.2	746.0	745.9	746.8	747.6	748.5	749.4	749.4
165°	755.9	755.6	755.5	755.4	755.3	755.1	756.2	757.2	758.2	759.2	759.3
167.5°	762.8	762.4	762.4	762.4	762.4	762.4	763.6	764.6	765.6	766.6	766.6
170°	766.9	766.6	766.6	766.6	766.6	766.6	767.7	768.7	769.7	770.7	770.7
172.5°	769.2	769.0	769.1	769.2	769.3	769.4	770.4	771.4	772.4	773.5	773.5
175°	772.7	772.4	772.5	772.7	772.8	773.0	773.9	774.8	775.7	776.6	776.5
177.5°	774.2	774.0	774.1	774.2	774.3	774.4	775.2	776.0	776.8	777.6	777.5
180°	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3



TEST NUMBER: P332276-840

CATALOG NUMBER: S123RDIP-S560D585U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5
2.5°	860.8	860.5	860.8	859.6	860.8	860.5	860.8	864.5	864.5	864.8	865.2
5°	801.0	800.6	799.5	796.1	799.5	800.6	801.0	802.2	805.3	810.7	809.2
7.5°	748.8	748.3	744.9	745.0	744.9	748.3	748.8	751.8	755.4	758.7	762.7
10°	717.9	718.3	713.7	710.9	713.7	718.3	717.9	720.6	725.6	728.3	731.0
12.5°	687.9	686.1	682.4	679.3	682.4	686.1	687.9	689.9	696.8	699.8	705.1
15°	648.2	644.4	635.1	635.9	635.1	644.4	648.2	646.7	653.7	657.5	659.1
17.5°	601.6	598.7	598.6	593.2	598.6	598.7	601.6	604.7	610.8	614.9	626.0
20°	574.4	572.5	573.2	567.8	573.2	572.5	574.4	580.6	584.4	589.9	598.7
22.5°	553.0	551.1	547.9	546.1	547.9	551.1	553.0	557.3	561.6	569.2	574.0
25°	521.8	518.7	515.6	517.6	515.6	518.7	521.8	524.1	531.8	535.3	542.3
27.5°	490.5	488.2	485.1	484.7	485.1	488.2	490.5	492.8	497.1	502.9	511.3
30°	470.7	468.4	466.9	464.9	466.9	468.4	470.7	472.6	477.0	483.1	489.3
32.5°	450.6	450.2	447.4	447.0	447.4	450.2	450.6	453.8	458.1	463.9	469.2
35°	424.3	422.0	421.2	421.6	421.2	422.0	424.3	425.9	429.7	435.2	440.2
37.5°	399.3	396.3	394.9	393.4	394.9	396.3	399.3	399.6	403.5	407.2	413.9
40°	381.4	378.3	377.5	376.8	377.5	378.3	381.4	381.0	385.3	388.0	394.2
42.5°	361.2	360.0	359.6	358.2	359.6	360.0	361.2	363.3	365.8	369.7	374.4
45°	333.8	333.5	331.1	331.8	331.1	333.5	333.8	335.0	339.2	341.9	346.2
47.5°	304.9	303.2	301.5	302.7	301.5	303.2	304.9	306.4	309.3	312.7	318.2
50°	285.1	284.3	280.8	281.6	280.8	284.3	285.1	286.6	288.5	292.8	297.8
52.5°	265.3	262.4	261.1	260.5	261.1	262.4	265.3	266.8	269.0	274.0	277.7
55°	232.5	228.9	227.4	226.6	227.4	228.9	232.5	235.2	238.2	243.7	247.5
57.5°	200.3	199.3	198.1	198.9	198.1	199.3	200.3	204.8	207.8	212.1	216.7
60°	181.4	181.4	181.4	181.1	181.4	181.4	181.4	185.3	187.9	192.3	197.2
62.5°	166.8	165.9	165.6	166.1	165.6	165.9	166.8	168.5	171.3	174.0	178.3
65°	144.6	144.3	142.7	142.4	142.7	144.3	144.6	145.8	148.1	150.1	153.2
67.5°	123.7	122.3	121.9	121.3	121.9	122.3	123.7	124.7	126.2	128.8	130.3
70°	108.0	107.1	104.8	105.2	104.8	107.1	108.0	109.9	111.4	114.5	116.0
72.5°	90.9	90.1	89.7	89.1	89.7	90.1	90.9	92.8	94.4	97.8	100.3
75°	71.9	71.6	71.2	72.7	71.2	71.6	71.9	72.3	72.7	73.9	75.0
77.5°	57.7	57.7	57.9	57.3	57.9	57.7	57.7	57.7	57.7	58.3	58.5
80°	48.4	48.4	48.0	48.0	48.0	48.4	48.4	48.4	48.4	48.4	48.0
82.5°	38.8	39.1	39.3	38.7	39.3	39.1	38.8	39.4	39.7	39.1	39.3
85°	25.5	25.1	26.0	25.5	26.0	25.1	25.5	25.5	24.7	25.5	25.1
87.5°	14.7	14.1	14.2	14.6	14.2	14.1	14.7	14.0	14.0	13.9	13.5
90°	16.6	16.8	17.1	17.3	17.1	16.8	16.6	16.3	15.9	15.3	14.8
92.5°	18.7	18.8	19.0	19.1	19.0	18.8	18.7	18.5	18.0	17.2	16.4
95°	21.9	21.9	21.9	21.9	21.9	21.9	21.9	21.9	21.4	20.5	19.7
97.5°	23.3	23.4	23.6	23.7	23.6	23.4	23.3	23.2	22.6	21.6	20.6
100°	23.8	23.9	24.0	24.2	24.0	23.9	23.8	23.6	23.1	22.1	21.0
102.5°	23.9	24.2	24.4	24.6	24.4	24.2	23.9	23.7	25.2	28.4	31.5
105°	24.5	24.8	25.0	25.3	25.0	24.8	24.5	24.3	35.5	58.2	80.8
107.5°	130.8	113.7	96.6	79.6	96.6	113.7	130.8	147.9	164.7	181.4	197.9
110°	213.3	195.0	176.7	158.3	176.7	195.0	213.3	231.6	242.9	247.1	251.4



TEST NUMBER: P332276-840

CATALOG NUMBER: S123RDIP-S560D585U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	283.4	279.4	275.6	271.8	275.6	279.4	283.4	287.2	289.1	289.0	288.9
115°	337.1	337.7	338.2	338.7	338.2	337.7	337.1	336.6	335.8	334.5	333.2
117.5°	376.0	376.1	376.2	376.3	376.2	376.1	376.0	375.9	375.3	374.3	373.2
120°	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	401.5	400.5	399.5
122.5°	427.1	427.2	427.3	427.4	427.3	427.2	427.1	427.0	426.6	425.9	425.2
125°	462.3	462.6	462.8	463.1	462.8	462.6	462.3	462.1	461.8	461.5	461.3
127.5°	498.2	498.0	497.7	497.5	497.7	498.0	498.2	498.5	498.4	498.0	497.6
130°	520.3	520.1	519.8	519.6	519.8	520.1	520.3	520.6	520.4	519.9	519.4
132.5°	540.9	540.5	540.2	539.8	540.2	540.5	540.9	541.3	541.2	540.7	540.2
135°	572.0	571.6	571.2	570.8	571.2	571.6	572.0	572.3	572.3	572.0	571.6
137.5°	600.7	600.5	600.2	600.0	600.2	600.5	600.7	601.0	600.8	600.2	599.6
140°	618.2	617.9	617.7	617.4	617.7	617.9	618.2	618.4	618.3	617.8	617.3
142.5°	634.7	634.3	633.9	633.6	633.9	634.3	634.7	635.0	635.0	634.6	634.2
145°	658.3	658.3	658.3	658.3	658.3	658.3	658.3	658.3	658.2	657.9	657.7
147.5°	678.5	677.9	677.4	676.8	677.4	677.9	678.5	679.1	679.3	679.0	678.8
150°	691.8	691.4	690.9	690.6	690.9	691.4	691.8	692.2	692.2	692.0	691.7
152.5°	703.5	702.9	702.3	701.7	702.3	702.9	703.5	704.0	704.1	703.6	703.2
155°	719.4	718.6	717.9	717.1	717.9	718.6	719.4	720.1	720.2	719.6	718.9
157.5°	733.1	732.2	731.1	730.1	731.1	732.2	733.1	734.1	734.3	733.5	732.7
160°	741.1	740.2	739.3	738.4	739.3	740.2	741.1	741.9	742.0	741.2	740.5
162.5°	748.6	747.8	747.0	746.3	747.0	747.8	748.6	749.4	749.4	748.5	747.6
165°	758.4	757.5	756.6	755.7	756.6	757.5	758.4	759.3	759.2	758.2	757.2
167.5°	765.6	764.6	763.6	762.4	763.6	764.6	765.6	766.6	766.6	765.6	764.6
170°	769.7	768.7	767.7	766.6	767.7	768.7	769.7	770.7	770.7	769.7	768.7
172.5°	772.3	771.2	770.0	768.9	770.0	771.2	772.3	773.5	773.5	772.4	771.4
175°	775.5	774.5	773.5	772.3	773.5	774.5	775.5	776.5	776.6	775.7	774.8
177.5°	776.5	775.5	774.5	773.5	774.5	775.5	776.5	777.5	777.6	776.8	776.0
180°	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3



TEST NUMBER: P332276-840

CATALOG NUMBER: S123RDIP-S560D585U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5
2.5°	862.4	866.8	871.1	875.0	881.3	884.0	888.1	889.6	894.2	901.1	906.7
5°	809.9	816.2	824.3	830.8	841.3	849.4	858.3	866.8	876.9	891.2	903.9
7.5°	765.5	771.5	781.3	793.6	805.1	816.6	828.8	840.3	854.7	875.3	895.5
10°	736.1	743.5	755.1	768.2	782.4	793.8	808.0	822.7	840.5	864.1	888.5
12.5°	710.7	716.2	729.6	742.1	758.3	772.6	786.7	803.9	824.2	849.3	878.6
15°	670.3	678.0	691.3	705.1	722.2	737.2	755.4	776.3	796.1	827.0	862.5
17.5°	629.8	641.6	655.2	671.0	683.6	704.4	724.1	745.5	769.8	802.6	841.6
20°	603.8	613.1	625.8	648.6	665.3	681.2	699.3	726.0	748.4	785.6	826.2
22.5°	581.8	588.7	602.9	621.8	641.2	659.4	678.0	703.5	731.1	766.4	810.4
25°	549.3	560.1	570.9	584.4	605.3	627.4	647.5	669.1	698.5	736.1	783.7
27.5°	517.5	527.3	538.0	554.6	570.5	591.1	612.1	636.9	668.4	708.1	756.4
30°	497.1	504.4	514.4	535.7	550.1	567.8	592.6	614.6	644.0	686.2	737.2
32.5°	475.9	485.5	496.4	512.8	530.5	547.3	570.0	593.9	623.9	665.4	717.7
35°	446.0	457.2	468.4	480.4	498.2	515.6	534.5	560.9	591.4	631.7	683.1
37.5°	418.4	427.4	436.6	451.4	468.3	484.8	502.5	528.5	557.2	600.7	647.8
40°	400.7	408.9	415.8	431.3	447.6	465.3	482.7	505.5	536.4	577.1	622.8
42.5°	381.5	389.0	398.5	411.1	428.7	443.6	461.1	482.6	511.7	553.0	593.0
45°	352.7	361.2	369.4	381.4	398.8	413.4	429.0	449.5	479.3	513.3	548.9
47.5°	322.9	331.3	340.6	352.2	367.4	382.3	397.8	416.0	443.1	476.6	500.5
50°	303.7	310.6	319.9	331.4	345.4	361.2	375.2	395.0	420.8	447.2	468.1
52.5°	283.9	290.1	300.7	313.0	325.9	339.6	354.5	371.4	394.9	419.6	436.2
55°	253.0	260.7	269.6	281.6	294.4	306.0	320.2	337.7	356.3	374.8	386.1
57.5°	224.1	230.6	238.0	250.4	261.5	275.3	288.1	301.7	318.9	332.9	340.2
60°	203.1	208.8	218.5	229.3	239.8	251.8	266.5	280.0	293.2	304.4	310.2
62.5°	183.3	190.0	198.4	208.3	219.7	231.1	243.9	255.3	266.9	276.6	280.5
65°	157.4	162.9	169.1	178.3	187.6	199.2	209.2	220.9	229.3	234.8	238.2
67.5°	133.9	137.4	142.2	148.3	157.5	167.6	177.4	186.4	193.6	197.2	200.4
70°	118.8	121.1	124.5	130.8	137.7	146.6	156.6	163.2	169.5	172.5	175.6
72.5°	103.6	106.5	109.7	114.6	120.4	126.8	134.1	142.2	145.6	149.3	151.2
75°	78.6	82.8	87.1	90.1	94.0	99.1	105.6	110.6	112.6	115.6	116.0
77.5°	59.3	60.2	63.3	67.2	70.4	74.0	78.2	82.7	83.6	85.2	86.2
80°	48.8	48.8	48.8	51.1	54.9	57.7	61.5	63.8	65.3	65.7	66.1
82.5°	39.2	39.2	38.9	39.3	40.7	42.1	45.7	48.4	49.6	49.4	48.5
85°	25.5	24.7	24.7	24.3	24.7	23.9	23.6	25.1	27.5	27.5	26.7
87.5°	13.4	12.9	12.9	12.3	11.7	11.0	9.8	9.9	9.6	10.6	10.0
90°	14.3	13.8	12.1	10.5	8.8	7.2	5.7	4.4	3.1	1.8	0.6
92.5°	15.6	14.7	13.5	12.2	11.0	9.7	9.3	9.6	10.0	10.4	10.7
95°	18.8	17.9	16.5	15.0	13.6	12.2	14.1	19.4	24.6	29.9	35.1
97.5°	19.6	18.6	27.8	37.0	46.2	55.4	61.2	63.5	65.9	68.3	70.6
100°	20.0	19.0	39.0	59.0	78.9	98.9	107.6	105.0	102.5	99.9	97.4
102.5°	34.7	37.9	59.7	81.5	103.3	125.1	135.1	133.3	131.5	129.6	127.7
105°	103.5	126.1	137.6	149.2	160.7	172.2	177.2	175.8	174.5	173.1	171.7
107.5°	214.6	231.2	229.3	227.5	225.7	223.9	222.5	221.4	220.3	219.0	217.9
110°	255.5	259.7	258.3	256.9	255.5	254.2	252.9	251.9	250.9	249.8	248.8



TEST NUMBER: P332276-840

CATALOG NUMBER: S123RDIP-S560D585U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	288.9	288.8	287.4	286.0	284.6	283.2	282.0	281.0	280.1	279.2	278.3
115°	331.9	330.6	329.4	328.3	327.2	326.0	325.1	324.3	323.5	322.8	321.9
117.5°	372.2	371.1	370.6	370.0	369.4	368.8	368.0	367.1	366.2	365.2	364.3
120°	398.5	397.4	397.1	396.7	396.3	395.9	395.2	393.9	392.8	391.6	390.5
122.5°	424.4	423.7	423.2	422.7	422.2	421.7	421.0	420.1	419.1	418.2	417.3
125°	461.0	460.8	460.3	459.8	459.3	458.8	458.0	457.0	456.0	454.9	453.8
127.5°	497.2	496.8	496.1	495.5	494.8	494.2	493.4	492.4	491.4	490.4	489.4
130°	518.9	518.4	517.9	517.4	516.8	516.3	515.5	514.5	513.5	512.5	511.5
132.5°	539.7	539.2	538.7	538.3	537.9	537.5	536.7	535.7	534.7	533.7	532.7
135°	571.2	570.8	570.3	569.8	569.3	568.8	568.2	567.3	566.5	565.8	565.0
137.5°	599.0	598.3	598.0	597.7	597.4	597.2	596.5	595.6	594.6	593.7	592.7
140°	616.8	616.3	615.9	615.5	615.1	614.8	614.2	613.4	612.7	611.9	611.1
142.5°	633.8	633.4	633.0	632.6	632.2	631.8	631.3	630.5	629.8	628.9	628.1
145°	657.4	657.2	656.9	656.7	656.4	656.2	655.6	654.7	653.8	652.9	652.0
147.5°	678.5	678.3	678.0	677.7	677.5	677.2	676.8	676.2	675.7	675.1	674.5
150°	691.5	691.2	690.9	690.6	690.4	690.1	689.8	689.4	689.0	688.7	688.3
152.5°	702.7	702.3	702.1	702.0	701.8	701.7	701.5	701.3	701.0	700.9	700.7
155°	718.3	717.7	717.5	717.4	717.3	717.2	717.2	717.5	717.7	718.0	718.2
157.5°	732.0	731.1	731.2	731.4	731.5	731.6	731.7	731.7	731.7	731.8	731.8
160°	739.7	739.0	739.1	739.2	739.3	739.5	739.6	739.7	739.9	740.0	740.1
162.5°	746.8	745.9	746.0	746.2	746.3	746.4	746.6	747.0	747.3	747.6	748.0
165°	756.2	755.1	755.3	755.4	755.5	755.6	755.9	756.3	756.7	757.0	757.4
167.5°	763.6	762.4	762.4	762.4	762.4	762.4	762.8	763.3	763.8	764.3	764.8
170°	767.7	766.6	766.6	766.6	766.6	766.6	766.9	767.4	767.9	768.4	768.9
172.5°	770.4	769.4	769.3	769.2	769.1	769.0	769.2	769.8	770.4	771.1	771.7
175°	773.9	773.0	772.8	772.7	772.5	772.4	772.7	773.4	774.0	774.7	775.3
177.5°	775.2	774.4	774.3	774.2	774.1	774.0	774.2	774.7	775.2	775.7	776.2
180°	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3



TEST NUMBER: P332276-840

CATALOG NUMBER: S123RDIP-S560D585U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5
2.5°	908.5	911.9	916.3	922.7	927.7	932.0	932.9	934.2	937.3	942.5	946.5
5°	914.4	923.3	937.6	951.5	966.6	979.0	990.6	998.8	1006.4	1022.7	1035.8
7.5°	912.5	932.3	954.7	979.8	1005.0	1029.6	1052.3	1072.7	1093.0	1116.6	1143.6
10°	911.3	934.5	964.6	996.7	1032.0	1066.4	1099.6	1125.6	1155.8	1182.9	1217.3
12.5°	905.4	938.9	974.9	1015.9	1059.2	1098.9	1142.7	1178.5	1212.9	1252.1	1292.1
15°	897.8	938.4	984.0	1038.5	1104.3	1152.3	1197.1	1259.4	1301.9	1344.5	1401.8
17.5°	883.7	933.3	990.4	1061.2	1116.1	1180.5	1248.0	1297.3	1354.5	1414.5	1466.3
20°	872.6	930.3	994.1	1063.7	1133.7	1203.8	1269.1	1327.9	1387.0	1456.3	1498.8
22.5°	861.5	918.5	984.8	1058.7	1134.0	1207.7	1281.7	1350.8	1417.3	1487.2	1541.6
25°	837.8	905.4	977.4	1052.9	1127.1	1208.3	1296.6	1373.5	1455.9	1527.8	1579.3
27.5°	813.9	875.9	947.5	1024.0	1106.5	1202.5	1306.3	1393.8	1476.3	1527.8	1544.0
30°	792.1	857.9	923.6	1001.4	1090.8	1197.9	1308.2	1408.4	1476.0	1498.4	1481.8
32.5°	770.2	829.8	894.9	974.5	1069.4	1186.5	1310.6	1399.7	1440.5	1423.3	1355.5
35°	731.4	785.2	848.3	928.0	1037.0	1180.1	1300.4	1360.8	1350.7	1253.9	1126.3
37.5°	689.9	733.8	792.1	875.5	1003.4	1155.0	1256.5	1265.4	1178.3	1029.9	882.4
40°	657.1	696.6	756.6	843.6	977.4	1130.2	1212.2	1176.3	1041.3	876.1	753.1
42.5°	625.3	658.5	716.3	810.2	952.7	1096.5	1146.3	1067.9	912.2	756.0	644.2
45°	571.3	602.6	660.7	757.0	902.0	1032.0	1025.4	889.3	733.4	607.6	514.8
47.5°	520.1	547.4	602.0	700.2	842.5	935.2	873.7	728.9	596.6	495.8	429.6
50°	483.9	511.0	565.1	662.2	794.9	862.5	774.8	635.1	514.0	430.5	377.9
52.5°	449.2	475.6	525.2	619.8	737.3	777.8	683.5	554.0	453.1	381.0	335.8
55°	400.7	420.8	465.3	555.8	643.6	652.9	557.3	449.1	365.9	315.6	284.7
57.5°	351.3	368.6	412.5	484.6	546.2	541.4	450.8	357.2	301.1	263.8	241.4
60°	319.1	336.1	374.8	436.7	483.1	466.9	383.7	308.3	260.3	232.9	215.1
62.5°	289.1	302.4	338.6	383.7	417.2	398.8	328.0	265.6	227.5	204.4	190.3
65°	245.6	256.4	285.5	309.0	327.6	309.8	251.1	207.7	180.3	164.0	154.3
67.5°	204.3	211.2	229.5	238.0	251.2	231.7	188.7	159.8	144.1	130.5	123.7
70°	178.3	183.4	193.0	200.0	203.5	183.4	151.6	130.4	117.2	107.6	103.3
72.5°	152.3	156.7	158.6	164.4	162.6	143.7	121.9	105.0	95.5	89.0	83.5
75°	116.4	118.4	116.4	114.1	109.1	95.9	80.9	72.3	65.3	62.3	60.4
77.5°	84.8	84.2	81.6	78.0	69.4	61.1	53.0	50.1	47.2	45.4	44.8
80°	65.3	63.8	61.5	55.7	48.4	42.5	40.6	38.7	37.6	35.5	35.2
82.5°	48.7	47.8	43.8	39.0	33.8	31.1	29.5	28.8	27.6	26.7	26.6
85°	26.0	24.7	20.5	17.8	17.1	16.3	15.9	15.9	14.3	13.9	13.9
87.5°	8.7	7.2	7.1	6.4	6.7	6.4	7.1	6.8	6.8	7.2	6.7
90°	1.8	3.1	4.4	5.7	7.2	8.8	10.5	12.1	13.8	14.3	14.8
92.5°	10.4	10.0	9.6	9.3	9.7	11.0	12.2	13.5	14.7	15.6	16.4
95°	29.9	24.6	19.4	14.1	12.2	13.6	15.0	16.5	17.9	18.8	19.7
97.5°	68.3	65.9	63.5	61.2	55.4	46.2	37.0	27.8	18.6	19.6	20.6
100°	99.9	102.5	105.0	107.6	98.9	78.9	59.0	39.0	19.0	20.0	21.0
102.5°	129.6	131.5	133.3	135.1	125.1	103.3	81.5	59.7	37.9	34.7	31.5
105°	173.1	174.5	175.8	177.2	172.2	160.7	149.2	137.6	126.1	103.5	80.8
107.5°	219.0	220.3	221.4	222.5	223.9	225.7	227.5	229.3	231.2	214.6	197.9
110°	249.8	250.9	251.9	252.9	254.2	255.5	256.9	258.3	259.7	255.5	251.4



TEST NUMBER: P332276-840

CATALOG NUMBER: S123RDIP-S560D585U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	279.2	280.1	281.0	282.0	283.2	284.6	286.0	287.4	288.8	288.9	288.9
115°	322.8	323.5	324.3	325.1	326.0	327.2	328.3	329.4	330.6	331.9	333.2
117.5°	365.2	366.2	367.1	368.0	368.8	369.4	370.0	370.6	371.1	372.2	373.2
120°	391.6	392.8	393.9	395.2	395.9	396.3	396.7	397.1	397.4	398.5	399.5
122.5°	418.2	419.1	420.1	421.0	421.7	422.2	422.7	423.2	423.7	424.4	425.2
125°	454.9	456.0	457.0	458.0	458.8	459.3	459.8	460.3	460.8	461.0	461.3
127.5°	490.4	491.4	492.4	493.4	494.2	494.8	495.5	496.1	496.8	497.2	497.6
130°	512.5	513.5	514.5	515.5	516.3	516.8	517.4	517.9	518.4	518.9	519.4
132.5°	533.7	534.7	535.7	536.7	537.5	537.9	538.3	538.7	539.2	539.7	540.2
135°	565.8	566.5	567.3	568.2	568.8	569.3	569.8	570.3	570.8	571.2	571.6
137.5°	593.7	594.6	595.6	596.5	597.2	597.4	597.7	598.0	598.3	599.0	599.6
140°	611.9	612.7	613.4	614.2	614.8	615.1	615.5	615.9	616.3	616.8	617.3
142.5°	628.9	629.8	630.5	631.3	631.8	632.2	632.6	633.0	633.4	633.8	634.2
145°	652.9	653.8	654.7	655.6	656.2	656.4	656.7	656.9	657.2	657.4	657.7
147.5°	675.1	675.7	676.2	676.8	677.2	677.5	677.7	678.0	678.3	678.5	678.8
150°	688.7	689.0	689.4	689.8	690.1	690.4	690.6	690.9	691.2	691.5	691.7
152.5°	700.9	701.0	701.3	701.5	701.7	701.8	702.0	702.1	702.3	702.7	703.2
155°	718.0	717.7	717.5	717.2	717.2	717.3	717.4	717.5	717.7	718.3	718.9
157.5°	731.8	731.7	731.7	731.7	731.6	731.5	731.4	731.2	731.1	732.0	732.7
160°	740.0	739.9	739.7	739.6	739.5	739.3	739.2	739.1	739.0	739.7	740.5
162.5°	747.6	747.3	747.0	746.6	746.4	746.3	746.2	746.0	745.9	746.8	747.6
165°	757.0	756.7	756.3	755.9	755.6	755.5	755.4	755.3	755.1	756.2	757.2
167.5°	764.3	763.8	763.3	762.8	762.4	762.4	762.4	762.4	762.4	763.6	764.6
170°	768.4	767.9	767.4	766.9	766.6	766.6	766.6	766.6	766.6	767.7	768.7
172.5°	771.1	770.4	769.8	769.2	769.0	769.1	769.2	769.3	769.4	770.4	771.4
175°	774.7	774.0	773.4	772.7	772.4	772.5	772.7	772.8	773.0	773.9	774.8
177.5°	775.7	775.2	774.7	774.2	774.0	774.1	774.2	774.3	774.4	775.2	776.0
180°	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3



TEST NUMBER: P332276-840

CATALOG NUMBER: S123RDIP-S560D585U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	903.5	903.5	903.5	903.5	903.5	903.5	903.5
2.5°	953.1	953.1	954.3	959.0	959.6	963.6	962.3
5°	1047.4	1054.8	1057.5	1069.1	1076.1	1079.1	1073.0
7.5°	1162.9	1183.6	1193.5	1205.6	1216.3	1219.6	1211.1
10°	1247.1	1268.7	1286.9	1298.1	1308.6	1315.5	1324.4
12.5°	1328.4	1355.0	1372.3	1388.2	1398.9	1407.8	1409.2
15°	1416.8	1457.0	1487.6	1510.1	1521.3	1527.1	1524.8
17.5°	1506.0	1543.3	1565.1	1587.9	1603.5	1604.3	1604.8
20°	1556.5	1592.9	1618.0	1635.0	1652.4	1651.6	1655.5
22.5°	1590.2	1618.8	1638.1	1650.4	1656.4	1653.5	1654.3
25°	1606.0	1614.5	1611.0	1591.2	1586.3	1568.1	1571.1
27.5°	1524.6	1484.4	1442.8	1389.2	1347.0	1313.2	1314.9
30°	1414.1	1342.9	1261.7	1193.7	1132.6	1115.5	1079.1
32.5°	1259.7	1153.0	1057.8	994.4	941.9	927.7	896.0
35°	997.9	894.2	796.4	737.6	714.4	682.0	681.6
37.5°	775.7	684.4	632.7	588.5	565.4	545.7	543.8
40°	652.6	581.4	542.3	510.6	487.8	473.0	469.6
42.5°	566.5	509.0	472.3	452.7	435.2	427.6	421.9
45°	462.6	423.9	398.4	380.6	372.4	366.7	363.6
47.5°	387.0	361.0	343.7	331.8	325.2	319.1	320.7
50°	345.8	324.6	311.7	300.5	295.5	291.2	291.6
52.5°	312.7	293.6	283.3	275.2	268.9	265.9	264.4
55°	265.4	253.4	242.9	237.1	233.6	229.3	228.2
57.5°	226.3	217.0	208.5	202.0	201.2	197.0	197.5
60°	200.4	192.6	185.6	182.2	179.5	176.0	177.1
62.5°	179.0	172.5	166.1	163.3	160.6	158.0	158.5
65°	146.6	140.4	136.5	135.0	133.8	132.7	131.5
67.5°	116.8	113.0	110.6	107.2	104.9	104.5	103.3
70°	98.3	93.2	89.0	84.7	83.5	83.1	83.5
72.5°	78.8	75.5	74.4	72.3	72.1	71.1	71.8
75°	59.2	58.1	57.3	55.7	55.7	55.7	55.7
77.5°	43.6	42.9	42.5	42.1	41.8	41.2	41.2
80°	34.0	33.6	32.9	32.9	32.5	32.9	32.5
82.5°	25.7	25.7	24.8	24.8	24.4	24.2	24.4
85°	13.1	12.7	13.5	12.7	13.1	12.4	13.1
87.5°	6.8	6.9	6.7	6.7	6.5	7.1	6.6
90°	15.3	15.9	16.3	16.6	16.8	17.1	17.3
92.5°	17.2	18.0	18.5	18.7	18.8	19.0	19.1
95°	20.5	21.4	21.9	21.9	21.9	21.9	21.9
97.5°	21.6	22.6	23.2	23.3	23.4	23.6	23.7
100°	22.1	23.1	23.6	23.8	23.9	24.0	24.2
102.5°	28.4	25.2	23.7	23.9	24.2	24.4	24.6
105°	58.2	35.5	24.3	24.5	24.8	25.0	25.3
107.5°	181.4	164.7	147.9	130.8	113.7	96.6	79.6
110°	247.1	242.9	231.6	213.3	195.0	176.7	158.3



TEST NUMBER: P332276-840

CATALOG NUMBER: S123RDIP-S560D585U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	289.0	289.1	287.2	283.4	279.4	275.6	271.8
115°	334.5	335.8	336.6	337.1	337.7	338.2	338.7
117.5°	374.3	375.3	375.9	376.0	376.1	376.2	376.3
120°	400.5	401.5	402.0	402.0	402.0	402.0	402.0
122.5°	425.9	426.6	427.0	427.1	427.2	427.3	427.4
125°	461.5	461.8	462.1	462.3	462.6	462.8	463.1
127.5°	498.0	498.4	498.5	498.2	498.0	497.7	497.5
130°	519.9	520.4	520.6	520.3	520.1	519.8	519.6
132.5°	540.7	541.2	541.3	540.9	540.5	540.2	539.8
135°	572.0	572.3	572.3	572.0	571.6	571.2	570.8
137.5°	600.2	600.8	601.0	600.7	600.5	600.2	600.0
140°	617.8	618.3	618.4	618.2	617.9	617.7	617.4
142.5°	634.6	635.0	635.0	634.7	634.3	633.9	633.6
145°	657.9	658.2	658.3	658.3	658.3	658.3	658.3
147.5°	679.0	679.3	679.1	678.5	677.9	677.4	676.8
150°	692.0	692.2	692.2	691.8	691.4	690.9	690.6
152.5°	703.6	704.1	704.0	703.5	702.9	702.3	701.7
155°	719.6	720.2	720.1	719.4	718.6	717.9	717.1
157.5°	733.5	734.3	734.1	733.1	732.2	731.1	730.1
160°	741.2	742.0	741.9	741.1	740.2	739.3	738.4
162.5°	748.5	749.4	749.4	748.6	747.8	747.0	746.3
165°	758.2	759.2	759.3	758.4	757.5	756.6	755.7
167.5°	765.6	766.6	766.6	765.6	764.6	763.6	762.4
170°	769.7	770.7	770.7	769.7	768.7	767.7	766.6
172.5°	772.4	773.5	773.5	772.3	771.2	770.0	768.9
175°	775.7	776.6	776.5	775.5	774.5	773.5	772.3
177.5°	776.8	777.6	777.5	776.5	775.5	774.5	773.5
180°	775.3	775.3	775.3	775.3	775.3	775.3	775.3

(END OF REPORT)