

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332279-840

Luminaire Tested: **S123RDIP-S560D585U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332279-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S560D585U840-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 585 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4521.1 lumens
Efficiency: N/A
Efficacy: 137.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332279-840

CATALOG NUMBER: S123RDIP-S560D585U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332279-840

CATALOG NUMBER: S123RDIP-S560D585U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	48				48
1	98	93	90	86	90	86	83	80	72	70	68	60	58	57	48	47	46				41	
2	89	82	76	71	82	76	70	66	64	60	57	53	50	48	43	41	39				35	
3	81	72	65	59	75	67	61	56	57	52	48	47	44	41	38	36	34				30	
4	75	64	56	50	68	59	53	47	50	45	41	42	38	35	34	32	29				26	
5	69	57	49	43	63	53	46	41	45	40	36	38	34	31	31	28	26				23	
6	63	51	43	38	58	48	41	36	41	35	31	34	30	27	28	25	23				20	
7	59	46	39	33	54	43	36	31	37	32	28	31	27	24	26	23	20				18	
8	54	42	35	29	50	39	33	28	34	28	25	29	24	21	24	21	18				16	
9	51	39	31	26	47	36	29	25	31	26	22	26	22	19	22	19	17				14	
10	47	35	28	24	44	33	27	22	29	23	20	24	20	18	20	17	15				13	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10267	10267	10267
5°	10306	10164	10222
10°	10248	10037	10002
15°	10137	9802	9698
20°	9986	9507	9286
25°	9830	9178	8884
30°	9625	8797	8316
35°	9412	8418	7796
40°	9218	7967	7152
45°	8961	7524	6570
50°	8679	7021	5921
55°	8392	6446	5315
60°	8127	5828	4646
65°	7784	5163	3978
70°	7352	4334	3213
75°	6725	3410	3023
80°	5994	3025	2777
85°	5064	2668	2482



TEST NUMBER: P332279-840

CATALOG NUMBER: S123RDIP-S560D585U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.6	2.0
10°-20°	249.2	5.5
20°-30°	358.8	7.9
30°-40°	404.2	8.9
40°-50°	386.7	8.6
50°-60°	316.7	7.0
60°-70°	213.7	4.7
70°-80°	107.5	2.4
80°-90°	30.6	0.7
90°-100°	28.2	0.6
100°-110°	134.3	3.0
110°-120°	322.7	7.1
120°-130°	410.9	9.1
130°-140°	439.0	9.7
140°-150°	410.5	9.1
150°-160°	331.2	7.3
160°-170°	213.7	4.7
170°-180°	73.7	1.6
0°-30°	697.6	15.4
0°-40°	1101.8	24.4
0°-60°	1805.2	39.9
0°-90°	2156.9	47.7
90°-120°	485.2	10.7
90°-150°	1745.7	38.6
90°-180°	2364.0	52.3
0°-180°	4521.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	954	954	954	954	954	
5°	954	950	941	947	946	90
15°	910	900	880	876	870	256
25°	828	808	773	757	748	381
35°	716	687	641	608	593	448
45°	589	552	494	452	432	454
55°	447	408	344	300	283	401
65°	306	262	203	166	156	302
75°	162	124	82	75	73	172
85°	41	25	22	20	20	46
90°	1	6	14	16	17	4
95°	35	13	18	22	22	43
105°	172	175	126	30	25	182
115°	322	326	331	336	339	318
125°	454	458	461	462	463	405
135°	565	568	571	572	571	435
145°	652	656	657	658	658	408
155°	718	717	718	720	717	331
165°	757	756	755	759	756	214
175°	775	773	773	777	772	74
180°	775	775	775	775	775	



TEST NUMBER: P332279-840

CATALOG NUMBER: S123RDIP-S560D585U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	953.8	953.8	953.8	953.8	953.8	953.8	953.8	953.8	953.8	953.8	953.8
2.5°	956.9	956.3	955.8	955.2	954.7	953.6	952.0	950.3	948.7	947.1	948.6
5°	953.8	953.0	952.1	951.3	950.4	949.0	946.8	944.8	942.7	940.7	942.2
7.5°	945.0	944.1	943.1	942.2	941.3	939.5	936.9	934.1	931.4	928.8	929.6
10°	937.6	936.3	935.1	933.9	932.8	930.6	927.6	924.4	921.3	918.3	918.4
12.5°	927.1	925.7	924.3	923.0	921.7	919.2	915.3	911.6	907.8	904.0	903.9
15°	909.7	907.9	905.9	904.0	902.2	898.8	894.0	889.2	884.3	879.6	878.7
17.5°	887.9	885.8	883.5	881.3	879.1	874.9	868.8	862.7	856.6	850.5	848.7
20°	871.8	869.1	866.4	863.5	860.8	856.2	849.6	843.1	836.6	830.0	827.8
22.5°	853.8	850.7	847.6	844.3	841.2	836.2	829.2	822.2	815.4	808.4	805.6
25°	827.7	823.4	819.1	814.9	810.5	804.5	796.5	788.6	780.7	772.8	769.2
27.5°	796.0	791.2	786.5	781.7	777.0	770.2	761.4	752.7	743.9	735.1	730.0
30°	774.4	769.2	764.1	758.9	753.8	746.3	736.7	727.1	717.4	707.8	702.0
32.5°	752.7	746.9	741.0	735.2	729.3	721.3	711.1	700.9	690.7	680.5	674.2
35°	716.3	710.1	704.0	697.8	691.6	683.2	672.5	661.9	651.2	640.6	633.1
37.5°	679.5	672.7	665.8	658.8	652.0	642.9	631.5	620.2	608.7	597.3	589.0
40°	656.0	648.4	640.9	633.3	625.7	615.8	603.7	591.5	579.3	567.0	558.1
42.5°	629.3	621.8	614.3	606.7	599.2	589.1	576.4	563.8	551.2	538.6	528.8
45°	588.7	581.0	573.2	565.5	557.7	547.2	534.0	520.8	507.6	494.3	484.5
47.5°	548.0	539.5	531.0	522.5	514.0	503.2	489.9	476.7	463.4	450.2	439.6
50°	518.3	510.2	502.1	494.0	485.9	474.9	461.0	447.2	433.2	419.3	408.6
52.5°	491.7	482.9	474.1	465.3	456.7	445.4	431.5	417.8	403.9	390.2	379.1
55°	447.2	438.7	430.3	421.8	413.4	401.9	387.3	372.7	358.1	343.5	333.5
57.5°	406.0	396.8	387.6	378.4	369.2	357.3	342.6	328.0	313.3	298.6	289.2
60°	377.5	368.1	358.6	349.1	339.7	327.8	313.6	299.3	285.0	270.7	261.5
62.5°	349.0	339.6	330.1	320.6	311.2	299.3	285.1	270.8	256.5	242.3	233.6
65°	305.6	296.1	286.7	277.2	267.7	256.3	242.9	229.5	216.1	202.7	194.3
67.5°	262.1	252.6	243.0	233.4	223.9	212.7	199.8	186.9	174.1	161.2	154.9
70°	233.6	224.3	215.1	205.8	196.5	185.8	173.8	161.8	149.8	137.7	131.7
72.5°	205.1	196.0	186.8	177.7	168.5	158.5	147.6	136.6	125.7	114.8	109.9
75°	161.7	153.4	145.2	136.9	128.7	119.8	110.4	100.9	91.5	82.0	80.3
77.5°	122.1	114.6	107.1	99.7	92.2	85.4	79.4	73.3	67.2	61.1	60.2
80°	96.7	89.7	82.6	75.5	68.5	63.2	59.6	55.9	52.3	48.8	48.2
82.5°	72.6	66.4	60.4	54.3	48.2	44.3	42.6	41.0	39.3	37.6	37.1
85°	41.0	37.3	33.4	29.7	25.9	23.7	23.2	22.7	22.2	21.6	21.3
87.5°	14.9	13.7	12.4	11.2	9.9	9.5	9.8	10.1	10.5	10.8	10.8
90°	0.6	1.8	3.1	4.4	5.7	7.2	8.8	10.5	12.1	13.8	14.3
92.5°	10.7	10.4	10.0	9.6	9.3	9.7	11.0	12.2	13.5	14.7	15.6
95°	35.1	29.9	24.6	19.4	14.1	12.2	13.6	15.0	16.5	17.9	18.8
97.5°	70.6	68.3	65.9	63.5	61.2	55.4	46.2	37.0	27.8	18.6	19.6
100°	97.4	99.9	102.5	105.0	107.6	98.9	78.9	59.0	39.0	19.0	20.0
102.5°	127.7	129.6	131.5	133.3	135.1	125.1	103.3	81.5	59.7	37.9	34.7
105°	171.7	173.1	174.5	175.8	177.2	172.2	160.7	149.2	137.6	126.1	103.5
107.5°	217.9	219.0	220.3	221.4	222.5	223.9	225.7	227.5	229.3	231.2	214.6
110°	248.8	249.8	250.9	251.9	252.9	254.2	255.5	256.9	258.3	259.7	255.5



TEST NUMBER: P332279-840

CATALOG NUMBER: S123RDIP-S560D585U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	278.3	279.2	280.1	281.0	282.0	283.2	284.6	286.0	287.4	288.8	288.9
115°	321.9	322.8	323.5	324.3	325.1	326.0	327.2	328.3	329.4	330.6	331.9
117.5°	364.3	365.2	366.2	367.1	368.0	368.8	369.4	370.0	370.6	371.1	372.2
120°	390.5	391.6	392.8	393.9	395.2	395.9	396.3	396.7	397.1	397.4	398.5
122.5°	417.3	418.2	419.1	420.1	421.0	421.7	422.2	422.7	423.2	423.7	424.4
125°	453.8	454.9	456.0	457.0	458.0	458.8	459.3	459.8	460.3	460.8	461.0
127.5°	489.4	490.4	491.4	492.4	493.4	494.2	494.8	495.5	496.1	496.8	497.2
130°	511.5	512.5	513.5	514.5	515.5	516.3	516.8	517.4	517.9	518.4	518.9
132.5°	532.7	533.7	534.7	535.7	536.7	537.5	537.9	538.3	538.7	539.2	539.7
135°	565.0	565.8	566.5	567.3	568.2	568.8	569.3	569.8	570.3	570.8	571.2
137.5°	592.7	593.7	594.6	595.6	596.5	597.2	597.4	597.7	598.0	598.3	599.0
140°	611.1	611.9	612.7	613.4	614.2	614.8	615.1	615.5	615.9	616.3	616.8
142.5°	628.1	628.9	629.8	630.5	631.3	631.8	632.2	632.6	633.0	633.4	633.8
145°	652.0	652.9	653.8	654.7	655.6	656.2	656.4	656.7	656.9	657.2	657.4
147.5°	674.5	675.1	675.7	676.2	676.8	677.2	677.5	677.7	678.0	678.3	678.5
150°	688.3	688.7	689.0	689.4	689.8	690.1	690.4	690.6	690.9	691.2	691.5
152.5°	700.7	700.9	701.0	701.3	701.5	701.7	701.8	702.0	702.1	702.3	702.7
155°	718.2	718.0	717.7	717.5	717.2	717.2	717.3	717.4	717.5	717.7	718.3
157.5°	731.8	731.8	731.7	731.7	731.7	731.6	731.5	731.4	731.2	731.1	732.0
160°	740.1	740.0	739.9	739.7	739.6	739.5	739.3	739.2	739.1	739.0	739.7
162.5°	748.0	747.6	747.3	747.0	746.6	746.4	746.3	746.2	746.0	745.9	746.8
165°	757.4	757.0	756.7	756.3	755.9	755.6	755.5	755.4	755.3	755.1	756.2
167.5°	764.8	764.3	763.8	763.3	762.8	762.4	762.4	762.4	762.4	762.4	763.6
170°	768.9	768.4	767.9	767.4	766.9	766.6	766.6	766.6	766.6	766.6	767.7
172.5°	771.7	771.1	770.4	769.8	769.2	769.0	769.1	769.2	769.3	769.4	770.4
175°	775.3	774.7	774.0	773.4	772.7	772.4	772.5	772.7	772.8	773.0	773.9
177.5°	776.2	775.7	775.2	774.7	774.2	774.0	774.1	774.2	774.3	774.4	775.2
180°	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3



TEST NUMBER: P332279-840

CATALOG NUMBER: S123RDIP-S560D585U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	953.8	953.8	953.8	953.8	953.8	953.8	953.8	953.8
2.5°	950.1	951.6	953.1	953.7	953.4	953.1	952.9	952.6
5°	943.7	945.3	946.8	947.5	947.2	946.7	946.4	946.0
7.5°	930.5	931.3	932.2	932.3	931.7	931.2	930.6	930.0
10°	918.6	918.8	918.9	918.6	917.8	916.9	916.0	915.1
12.5°	903.8	903.7	903.6	903.0	902.0	901.0	900.1	899.1
15°	877.9	877.0	876.2	875.0	873.8	872.7	871.5	870.3
17.5°	846.9	845.1	843.1	841.4	839.6	837.8	836.0	834.2
20°	825.6	823.3	821.1	819.0	816.9	814.9	812.7	810.7
22.5°	802.8	800.0	797.3	794.9	792.9	791.0	789.1	787.2
25°	765.6	761.9	758.4	755.6	753.8	751.8	749.9	748.0
27.5°	725.0	720.0	715.0	711.0	708.1	705.3	702.4	699.4
30°	696.1	690.2	684.5	680.1	677.4	674.7	671.9	669.1
32.5°	667.8	661.4	655.0	650.4	647.5	644.6	641.7	638.8
35°	625.7	618.3	611.0	605.7	602.6	599.6	596.4	593.3
37.5°	580.6	572.2	563.8	557.7	553.9	550.1	546.2	542.4
40°	549.2	540.2	531.3	524.8	520.9	516.9	513.0	509.0
42.5°	519.1	509.3	499.5	492.8	489.3	485.7	482.2	478.7
45°	474.7	464.9	455.1	448.2	444.0	439.9	435.8	431.6
47.5°	428.9	418.3	407.6	400.4	396.8	393.0	389.4	385.7
50°	398.0	387.3	376.7	369.3	365.4	361.4	357.5	353.6
52.5°	368.1	357.0	345.9	338.6	335.1	331.5	328.0	324.5
55°	323.6	313.6	303.6	296.9	293.5	290.0	286.6	283.2
57.5°	279.7	270.3	260.9	254.8	251.9	248.9	246.0	243.1
60°	252.2	242.9	233.6	227.5	224.6	221.7	218.7	215.8
62.5°	224.8	216.1	207.3	201.5	198.4	195.3	192.3	189.2
65°	185.8	177.4	169.0	163.8	162.0	160.1	158.1	156.2
67.5°	148.7	142.3	136.0	131.9	129.9	127.8	125.8	123.8
70°	125.6	119.7	113.6	109.7	107.8	105.9	104.0	102.1
72.5°	104.9	100.1	95.1	92.3	91.5	90.7	89.9	89.1
75°	78.6	76.9	75.1	74.1	73.7	73.4	73.0	72.7
77.5°	59.3	58.4	57.4	56.8	56.5	56.0	55.7	55.3
80°	47.7	47.2	46.7	46.3	45.9	45.5	45.2	44.8
82.5°	36.6	36.1	35.5	35.2	35.1	35.1	35.0	34.9
85°	21.0	20.6	20.3	20.1	20.1	20.1	20.1	20.1
87.5°	10.7	10.7	10.7	10.6	10.5	10.4	10.3	10.3
90°	14.8	15.3	15.9	16.3	16.6	16.8	17.1	17.3
92.5°	16.4	17.2	18.0	18.5	18.7	18.8	19.0	19.1
95°	19.7	20.5	21.4	21.9	21.9	21.9	21.9	21.9
97.5°	20.6	21.6	22.6	23.2	23.3	23.4	23.6	23.7
100°	21.0	22.1	23.1	23.6	23.8	23.9	24.0	24.2
102.5°	31.5	28.4	25.2	23.7	23.9	24.2	24.4	24.6
105°	80.8	58.2	35.5	24.3	24.5	24.8	25.0	25.3
107.5°	197.9	181.4	164.7	147.9	130.8	113.7	96.6	79.6
110°	251.4	247.1	242.9	231.6	213.3	195.0	176.7	158.3



TEST NUMBER: P332279-840

CATALOG NUMBER: S123RDIP-S560D585U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	288.9	289.0	289.1	287.2	283.4	279.4	275.6	271.8
115°	333.2	334.5	335.8	336.6	337.1	337.7	338.2	338.7
117.5°	373.2	374.3	375.3	375.9	376.0	376.1	376.2	376.3
120°	399.5	400.5	401.5	402.0	402.0	402.0	402.0	402.0
122.5°	425.2	425.9	426.6	427.0	427.1	427.2	427.3	427.4
125°	461.3	461.5	461.8	462.1	462.3	462.6	462.8	463.1
127.5°	497.6	498.0	498.4	498.5	498.2	498.0	497.7	497.5
130°	519.4	519.9	520.4	520.6	520.3	520.1	519.8	519.6
132.5°	540.2	540.7	541.2	541.3	540.9	540.5	540.2	539.8
135°	571.6	572.0	572.3	572.3	572.0	571.6	571.2	570.8
137.5°	599.6	600.2	600.8	601.0	600.7	600.5	600.2	600.0
140°	617.3	617.8	618.3	618.4	618.2	617.9	617.7	617.4
142.5°	634.2	634.6	635.0	635.0	634.7	634.3	633.9	633.6
145°	657.7	657.9	658.2	658.3	658.3	658.3	658.3	658.3
147.5°	678.8	679.0	679.3	679.1	678.5	677.9	677.4	676.8
150°	691.7	692.0	692.2	692.2	691.8	691.4	690.9	690.6
152.5°	703.2	703.6	704.1	704.0	703.5	702.9	702.3	701.7
155°	718.9	719.6	720.2	720.1	719.4	718.6	717.9	717.1
157.5°	732.7	733.5	734.3	734.1	733.1	732.2	731.1	730.1
160°	740.5	741.2	742.0	741.9	741.1	740.2	739.3	738.4
162.5°	747.6	748.5	749.4	749.4	748.6	747.8	747.0	746.3
165°	757.2	758.2	759.2	759.3	758.4	757.5	756.6	755.7
167.5°	764.6	765.6	766.6	766.6	765.6	764.6	763.6	762.4
170°	768.7	769.7	770.7	770.7	769.7	768.7	767.7	766.6
172.5°	771.4	772.4	773.5	773.5	772.3	771.2	770.0	768.9
175°	774.8	775.7	776.6	776.5	775.5	774.5	773.5	772.3
177.5°	776.0	776.8	777.6	777.5	776.5	775.5	774.5	773.5
180°	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3

(END OF REPORT)