

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332320-840

Luminaire Tested: **S123RDIP-S775D1025U840-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332320-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S775D1025U840-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1025 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6825.4 lumens
Efficiency: N/A
Efficacy: 131.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332320-840

CATALOG NUMBER: S123RDIP-S775D1025U840-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332320-840

CATALOG NUMBER: S123RDIP-S775D1025U840-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	45
1	97	93	89	86	89	86	82	80	71	69	67	58	57	56	46	45	45	39
2	89	82	76	71	81	75	70	66	63	60	56	52	49	47	41	40	38	34
3	81	72	65	60	74	67	61	56	56	52	48	46	43	41	37	35	33	29
4	75	64	57	51	68	59	53	48	50	45	41	42	38	35	34	31	29	25
5	69	58	50	44	63	53	46	41	45	40	36	38	34	31	30	28	26	22
6	63	52	44	38	58	48	41	36	41	36	32	34	30	27	28	25	23	20
7	59	47	39	34	54	44	37	32	37	32	28	31	27	24	26	23	20	18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	18	16
9	51	39	32	27	47	36	30	25	31	26	22	26	22	20	22	19	17	15
10	47	36	29	24	44	33	27	23	29	24	20	24	20	18	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13295	13295	13295	13295
5°	15847	13351	11757	13351
10°	19787	13274	10622	13274
15°	23226	13138	9686	13138
20°	25921	12936	8891	12936
25°	25508	12722	8402	12722
30°	18334	12525	7899	12525
35°	12242	12269	7573	12269
40°	9020	11960	7235	11960
45°	7566	11420	6905	11420
50°	6677	10712	6445	10712
55°	5853	9903	5814	9903
60°	5214	9128	5326	9128
65°	4579	8295	4956	8295
70°	3594	7553	4526	7553
75°	3165	6596	4134	6596
80°	2752	5604	4060	5604
85°	2223	4508	4310	4508



TEST NUMBER: P332320-840

CATALOG NUMBER: S123RDIP-S775D1025U840-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.5	1.8
10°-20°	379.5	5.6
20°-30°	596.1	8.7
30°-40°	621.9	9.1
40°-50°	532.3	7.8
50°-60°	405.7	5.9
60°-70°	260.0	3.8
70°-80°	125.1	1.8
80°-90°	37.0	0.5
90°-100°	277.1	4.1
100°-110°	784.7	11.5
110°-120°	771.9	11.3
120°-130°	615.7	9.0
130°-140°	485.5	7.1
140°-150°	362.3	5.3
150°-160°	252.5	3.7
160°-170°	148.4	2.2
170°-180°	48.3	0.7
0°-30°	1097.0	16.1
0°-40°	1719.0	25.2
0°-60°	2656.9	38.9
0°-90°	3079.0	45.1
90°-120°	1833.8	26.9
90°-150°	3297.3	48.3
90°-180°	3746.0	54.9
0°-180°	6825.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1235	1235	1235	1235	1235	
5°	1467	1236	1088	1236	1467	151
15°	2084	1179	869	1179	2084	591
25°	2148	1071	707	1071	2148	923
35°	932	934	576	934	932	611
45°	497	750	454	750	497	391
55°	312	528	310	528	312	282
65°	180	326	195	326	180	177
75°	76	159	99	159	76	82
85°	18	36	35	36	18	21
90°	29	2	29	2	29	16
95°	117	34	117	34	117	211
105°	1282	117	1282	117	1282	1265
115°	1559	207	1559	207	1559	1515
125°	1230	287	1230	287	1230	1115
135°	997	337	997	337	997	773
145°	779	384	779	384	779	496
155°	646	436	646	436	646	301
165°	564	477	564	477	564	161
175°	507	497	507	497	507	49
180°	498	498	498	498	498	



TEST NUMBER: P332320-840

CATALOG NUMBER: S123RDIP-S775D1025U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1
2.5°	1315.5	1317.2	1311.6	1310.8	1304.4	1302.7	1302.7	1293.8	1288.4	1281.2	1277.0
5°	1466.6	1475.1	1470.9	1461.4	1445.5	1441.8	1431.8	1415.9	1398.0	1375.7	1365.1
7.5°	1655.5	1667.1	1662.6	1647.9	1631.3	1617.9	1589.5	1563.2	1526.3	1493.9	1466.2
10°	1810.3	1798.2	1788.7	1774.3	1759.1	1734.1	1704.6	1663.9	1616.8	1579.8	1538.5
12.5°	1926.2	1924.2	1912.2	1897.4	1875.8	1852.2	1815.8	1766.3	1711.5	1658.1	1610.9
15°	2084.2	2087.4	2079.4	2064.1	2033.5	1991.7	1936.7	1916.0	1837.9	1779.7	1721.5
17.5°	2193.5	2192.9	2191.8	2170.6	2139.3	2109.6	2058.6	2004.4	1933.5	1851.6	1773.2
20°	2262.9	2257.7	2258.7	2234.8	2211.6	2177.3	2127.6	2048.8	1990.6	1896.0	1815.0
22.5°	2261.2	2260.2	2264.2	2256.0	2239.1	2212.8	2173.6	2107.2	2033.0	1937.4	1846.3
25°	2147.7	2143.4	2168.3	2175.1	2202.1	2206.9	2195.2	2158.8	2088.4	1990.0	1877.4
27.5°	1797.5	1795.1	1841.2	1899.0	1972.1	2029.0	2084.0	2110.5	2088.4	2018.0	1905.2
30°	1475.1	1524.8	1548.1	1631.6	1724.6	1835.7	1933.0	2025.5	2048.2	2017.6	1925.0
32.5°	1224.8	1268.1	1287.5	1359.2	1445.9	1576.0	1721.9	1852.9	1945.5	1968.9	1913.2
35°	931.6	932.1	976.5	1008.2	1088.6	1222.3	1364.1	1539.6	1714.0	1846.2	1860.0
37.5°	743.4	746.0	772.8	804.5	864.7	935.5	1060.3	1206.2	1407.8	1610.6	1729.6
40°	641.9	646.6	666.7	697.9	741.2	794.7	891.9	1029.5	1197.5	1423.3	1607.8
42.5°	576.7	584.4	594.8	618.8	645.7	695.7	774.4	880.5	1033.4	1246.9	1459.8
45°	497.0	501.2	509.2	520.3	544.6	579.5	632.4	703.7	830.6	1002.5	1215.5
47.5°	438.4	436.2	444.5	453.5	469.7	493.5	529.0	587.2	677.7	815.6	996.3
50°	398.7	398.1	403.9	410.8	426.2	443.6	472.7	516.5	588.4	702.7	868.2
52.5°	361.4	363.5	367.6	376.2	387.2	401.3	427.4	459.0	520.8	619.4	757.3
55°	311.9	313.6	319.3	324.1	332.0	346.3	362.7	389.1	431.4	500.2	613.8
57.5°	270.0	269.3	274.9	276.1	285.1	296.7	309.4	329.9	360.6	411.6	488.2
60°	242.2	240.5	245.3	249.0	253.8	263.3	273.9	294.0	318.3	355.8	421.4
62.5°	216.8	216.0	219.5	223.2	227.1	235.8	244.7	260.1	279.3	311.0	363.0
65°	179.8	181.4	182.9	184.5	186.6	191.9	200.4	211.0	224.2	246.4	283.9
67.5°	141.3	142.9	143.4	146.6	151.2	154.5	159.7	169.1	178.2	197.0	218.3
70°	114.2	113.7	114.2	115.8	121.6	127.4	134.3	141.2	146.9	160.2	178.1
72.5°	98.2	97.1	98.6	98.9	101.7	103.3	107.7	114.1	121.6	130.6	143.5
75°	76.1	76.1	76.1	76.1	78.3	79.3	80.9	82.5	85.1	89.4	98.9
77.5°	56.2	56.4	57.1	57.7	58.1	58.7	59.7	61.2	62.2	64.4	68.6
80°	44.4	44.9	44.4	44.9	44.9	45.9	46.6	48.1	48.7	51.3	52.9
82.5°	33.4	33.1	33.4	33.9	33.9	35.0	35.1	36.3	36.4	37.8	39.4
85°	18.0	17.0	18.0	17.5	18.5	17.5	18.0	19.0	19.0	19.6	21.7
87.5°	10.1	11.1	10.1	10.3	10.5	10.5	10.3	10.1	10.8	10.5	10.4
90°	29.2	30.2	29.2	28.2	29.2	27.3	26.3	25.2	24.2	25.2	22.2
92.5°	48.6	50.4	49.4	52.4	54.2	59.5	67.4	84.8	116.9	155.0	170.6
95°	116.9	121.0	128.1	137.1	156.2	192.6	246.0	362.8	484.8	597.7	532.2
97.5°	318.3	327.0	354.3	399.6	473.9	594.5	724.6	904.6	991.1	926.3	678.2
100°	632.1	631.1	670.3	744.0	845.8	988.9	1106.8	1188.5	1153.2	954.6	645.1
102.5°	927.2	950.4	983.2	1041.5	1120.7	1211.4	1280.2	1282.8	1161.2	902.2	596.7
105°	1282.2	1287.3	1319.5	1357.8	1404.2	1430.4	1411.3	1310.4	1099.7	810.4	537.2
107.5°	1486.6	1495.9	1506.8	1519.7	1518.9	1483.0	1394.7	1231.0	992.1	729.4	499.4
110°	1570.5	1572.6	1574.6	1566.5	1538.2	1467.6	1340.7	1155.2	924.3	683.5	484.8



TEST NUMBER: P332320-840

CATALOG NUMBER: S123RDIP-S775D1025U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1587.4	1587.0	1579.3	1554.4	1502.8	1412.0	1269.7	1080.2	865.5	652.8	476.8
115°	1559.4	1554.4	1534.2	1489.9	1414.2	1304.3	1156.2	980.8	794.4	620.0	473.7
117.5°	1470.3	1463.5	1434.4	1383.6	1304.7	1193.3	1060.3	908.9	751.3	600.6	475.5
120°	1396.1	1390.1	1365.8	1309.4	1229.8	1128.0	1007.0	870.9	728.8	591.7	478.8
122.5°	1326.8	1319.1	1292.5	1241.7	1170.9	1076.4	964.3	841.1	710.2	586.0	484.4
125°	1229.8	1222.7	1197.5	1153.2	1088.6	1008.0	911.3	801.4	686.5	578.7	492.9
127.5°	1149.9	1143.5	1120.7	1082.8	1025.3	952.0	864.6	766.7	665.5	575.0	502.6
130°	1104.8	1096.7	1075.6	1039.3	985.8	917.3	835.7	745.0	654.2	572.6	509.1
132.5°	1060.5	1054.8	1036.0	999.8	949.6	884.2	808.2	724.8	643.7	571.8	513.9
135°	996.9	989.9	971.7	941.5	892.1	834.7	769.1	697.5	630.1	570.6	521.2
137.5°	929.8	925.1	909.9	879.2	837.7	787.9	731.4	672.8	618.1	568.4	525.9
140°	883.0	884.0	867.9	839.7	801.4	758.0	709.6	658.2	610.9	567.5	529.2
142.5°	839.5	840.5	826.0	801.0	768.3	730.6	688.7	644.5	604.4	565.9	531.6
145°	779.2	777.2	769.1	747.9	722.8	693.5	661.3	628.0	595.7	563.5	533.2
147.5°	729.6	728.8	721.1	706.8	687.7	666.9	640.9	614.5	587.2	559.7	533.2
150°	700.5	700.5	694.5	683.5	668.3	649.1	628.0	604.8	581.6	556.4	533.2
152.5°	676.4	676.4	672.8	662.5	650.6	634.7	615.9	595.9	575.2	552.4	530.8
155°	646.1	645.1	643.1	635.1	626.0	613.9	598.7	582.6	565.5	545.3	528.2
157.5°	618.5	618.7	617.1	611.1	603.2	593.7	582.0	568.6	554.6	539.1	524.8
160°	600.8	601.8	601.8	595.7	588.7	581.6	571.6	560.5	547.3	534.2	523.2
162.5°	584.6	585.6	585.6	580.5	575.8	569.6	560.3	550.8	540.1	529.4	520.0
165°	563.5	563.5	564.5	560.5	556.4	551.4	544.3	538.3	530.2	522.2	515.1
167.5°	543.3	543.3	544.3	541.5	539.7	536.0	532.0	527.4	520.8	514.9	510.3
170°	531.2	531.2	532.2	530.2	529.2	527.1	523.2	520.2	515.1	510.1	507.1
172.5°	520.0	520.8	522.6	520.6	520.4	519.2	515.9	513.7	509.5	506.0	504.6
175°	507.1	508.1	509.1	508.1	508.1	508.1	506.0	505.0	503.0	501.0	501.0
177.5°	499.6	499.6	501.2	500.4	501.2	501.2	500.4	499.6	498.8	498.0	498.8
180°	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0



TEST NUMBER: P332320-840

CATALOG NUMBER: S123RDIP-S775D1025U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1
2.5°	1275.3	1273.9	1268.1	1261.3	1252.4	1246.5	1241.8	1239.3	1231.7	1222.3	1216.1
5°	1354.0	1338.2	1321.3	1300.6	1281.6	1262.0	1249.9	1235.6	1218.2	1198.6	1184.9
7.5°	1438.5	1407.3	1373.8	1339.3	1305.0	1274.4	1247.4	1224.2	1196.4	1168.3	1148.7
10°	1503.2	1457.6	1410.6	1362.5	1318.6	1277.4	1245.7	1214.5	1181.1	1148.9	1124.6
12.5°	1562.0	1502.1	1447.8	1388.8	1332.6	1283.3	1237.6	1200.9	1160.8	1126.5	1098.7
15°	1636.4	1575.1	1509.4	1419.6	1345.0	1282.6	1227.2	1179.0	1130.4	1088.1	1061.2
17.5°	1706.0	1613.7	1525.6	1450.6	1353.7	1275.8	1208.0	1150.4	1097.1	1052.3	1019.1
20°	1734.7	1645.4	1549.6	1454.0	1358.8	1271.5	1192.8	1129.3	1073.8	1023.1	992.4
22.5°	1752.0	1650.8	1550.0	1447.2	1346.2	1255.5	1177.6	1107.7	1047.6	999.4	961.5
25°	1772.2	1651.7	1540.7	1439.2	1336.1	1237.7	1145.2	1071.2	1006.1	954.8	914.6
27.5°	1785.5	1643.8	1512.6	1399.7	1295.2	1197.2	1112.4	1034.0	968.0	913.7	870.6
30°	1788.1	1637.4	1491.0	1368.9	1262.5	1172.7	1082.8	1007.7	938.0	880.3	840.1
32.5°	1791.5	1621.7	1461.8	1332.0	1223.2	1134.2	1052.8	981.1	909.6	852.8	811.8
35°	1777.6	1613.2	1417.4	1268.4	1159.4	1073.3	999.8	933.7	863.4	808.4	766.6
37.5°	1717.5	1578.7	1371.6	1196.7	1082.8	1003.0	943.1	885.4	821.0	761.6	722.4
40°	1657.0	1544.9	1336.1	1153.2	1034.2	952.2	898.3	851.2	788.8	733.4	691.1
42.5°	1566.9	1498.8	1302.2	1107.4	979.2	900.2	854.7	810.6	755.9	699.5	659.7
45°	1401.6	1410.6	1232.9	1034.7	903.0	823.7	780.9	750.2	701.7	655.1	614.4
47.5°	1194.4	1278.4	1151.7	957.2	822.7	748.3	710.9	684.2	651.4	605.7	568.6
50°	1059.0	1179.0	1086.5	905.1	772.4	698.4	661.5	639.7	611.2	575.2	539.8
52.5°	934.2	1063.2	1007.8	847.2	717.9	650.3	614.1	596.2	573.5	539.7	507.7
55°	761.8	892.5	879.8	759.7	636.0	575.2	547.8	527.7	512.3	487.0	461.6
57.5°	616.3	740.1	746.7	662.5	563.9	503.8	480.2	465.0	455.0	435.9	412.4
60°	524.5	638.1	660.4	596.9	512.3	459.5	436.2	424.0	416.1	400.8	382.8
62.5°	448.4	545.1	570.3	524.6	462.8	413.3	395.2	383.4	378.0	364.8	348.9
65°	343.2	423.5	447.8	422.4	390.2	350.5	335.8	325.7	320.9	313.6	301.8
67.5°	258.0	316.6	343.3	325.4	313.8	288.7	279.2	273.9	269.6	264.6	254.9
70°	207.2	250.6	278.1	273.4	263.9	250.6	243.8	240.0	235.8	231.6	223.1
72.5°	166.6	196.5	222.3	224.7	216.9	214.2	208.2	206.6	204.1	199.0	194.4
75°	110.5	131.1	149.1	155.9	159.2	161.8	159.2	158.6	158.0	153.9	151.2
77.5°	72.4	83.5	94.8	106.5	111.6	115.1	116.0	118.0	116.5	114.3	113.0
80°	55.5	58.2	66.0	76.1	84.0	87.3	89.4	90.4	89.9	89.4	87.3
82.5°	40.3	42.5	46.3	53.3	60.0	65.2	66.6	66.3	67.5	67.8	66.0
85°	21.7	22.2	23.2	24.3	28.0	33.8	35.4	36.5	37.6	37.6	34.3
87.5°	10.6	9.6	9.8	9.4	10.3	10.1	12.2	13.9	14.7	13.4	14.0
90°	19.2	16.2	13.1	11.1	9.1	6.1	4.0	2.0	4.0	6.1	9.1
92.5°	128.1	84.6	58.3	43.3	34.8	27.1	18.6	12.5	18.6	27.1	34.8
95°	366.9	216.7	131.1	91.7	65.5	48.4	37.3	34.2	37.3	48.4	65.5
97.5°	402.6	233.3	151.4	108.9	83.0	68.2	59.5	58.5	59.5	68.2	83.0
100°	380.0	230.9	160.3	121.0	96.7	82.7	75.6	74.6	75.6	82.7	96.7
102.5°	360.6	234.1	170.8	134.7	112.9	99.6	93.3	91.5	93.3	99.6	112.9
105°	346.8	243.0	188.5	157.2	138.1	126.0	120.0	116.9	120.0	126.0	138.1
107.5°	345.8	259.4	211.7	182.7	164.7	152.8	146.9	143.9	146.9	152.8	164.7
110°	349.8	273.2	227.8	199.5	182.5	171.4	166.3	163.3	166.3	171.4	182.5



TEST NUMBER: P332320-840

CATALOG NUMBER: S123RDIP-S775D1025U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	357.9	286.9	244.8	217.3	200.2	189.1	184.1	181.1	184.1	189.1	200.2
115°	370.9	309.4	271.1	244.0	226.8	216.7	210.7	206.6	210.7	216.7	226.8
117.5°	388.3	333.5	295.6	270.3	251.2	242.0	236.9	232.3	236.9	242.0	251.2
120°	401.2	348.8	312.5	287.3	268.1	258.0	253.0	249.9	253.0	258.0	268.1
122.5°	413.3	364.9	329.4	302.7	284.3	273.4	268.3	265.3	268.3	273.4	284.3
125°	432.4	388.1	352.8	325.6	306.4	295.4	289.3	287.3	289.3	295.4	306.4
127.5°	448.2	408.3	374.2	347.0	325.8	314.5	307.0	304.1	307.0	314.5	325.8
130°	458.7	420.3	387.1	359.8	338.7	326.6	317.5	314.5	317.5	326.6	338.7
132.5°	468.4	430.8	398.4	371.9	350.8	336.3	326.4	322.6	326.4	336.3	350.8
135°	480.8	446.6	415.3	388.1	366.9	351.8	340.7	336.7	340.7	351.8	366.9
137.5°	490.1	457.5	427.4	402.2	381.2	365.1	354.3	350.0	354.3	365.1	381.2
140°	494.9	464.7	435.5	410.3	390.1	374.0	363.9	358.9	363.9	374.0	390.1
142.5°	499.8	470.4	441.9	418.3	398.2	383.6	372.7	368.5	372.7	383.6	398.2
145°	505.0	477.8	451.6	428.4	411.3	396.2	387.1	384.1	387.1	396.2	411.3
147.5°	508.3	483.8	459.9	440.1	423.5	410.5	401.6	399.8	401.6	410.5	423.5
150°	509.1	487.9	464.7	446.6	432.4	419.3	411.3	410.3	411.3	419.3	432.4
152.5°	510.7	490.3	470.4	453.0	440.5	429.0	420.9	420.7	420.9	429.0	440.5
155°	511.1	494.9	477.8	463.7	452.6	442.5	436.5	436.5	436.5	442.5	452.6
157.5°	512.1	497.6	483.8	472.9	463.5	454.6	449.8	449.0	449.8	454.6	463.5
160°	512.1	500.0	487.9	477.8	470.7	462.7	458.7	458.7	458.7	462.7	470.7
162.5°	511.3	500.8	490.3	481.8	475.5	469.2	466.0	466.0	466.0	469.2	475.5
165°	509.1	502.0	493.9	486.9	482.8	477.8	475.7	476.8	475.7	477.8	482.8
167.5°	507.5	501.8	495.9	491.5	488.7	484.8	483.8	485.0	483.8	484.8	488.7
170°	505.0	501.0	495.9	493.9	491.9	488.9	487.9	489.9	487.9	488.9	491.9
172.5°	504.2	501.0	496.8	495.5	494.3	492.1	491.9	493.1	491.9	492.1	494.3
175°	502.0	500.0	498.0	497.0	497.0	494.9	495.9	497.0	495.9	494.9	497.0
177.5°	500.4	498.8	498.0	498.0	498.0	497.2	498.0	498.8	498.0	497.2	498.0
180°	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0



TEST NUMBER: P332320-840

CATALOG NUMBER: S123RDIP-S775D1025U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1
2.5°	1214.0	1208.4	1204.7	1196.2	1190.6	1184.8	1178.8	1182.7	1182.2	1181.7	1181.7
5°	1173.3	1161.0	1149.9	1135.7	1126.7	1115.6	1107.1	1106.1	1108.2	1100.8	1096.5
7.5°	1132.9	1116.2	1100.4	1084.7	1068.0	1054.7	1046.3	1042.4	1037.0	1032.5	1027.7
10°	1104.5	1084.9	1069.5	1050.1	1032.1	1016.2	1006.1	999.3	995.5	991.9	985.0
12.5°	1075.3	1056.1	1036.6	1014.5	997.3	979.0	971.5	963.7	956.6	952.5	943.1
15°	1032.6	1007.7	987.1	963.8	944.8	926.9	916.3	900.9	898.8	893.5	884.0
17.5°	989.8	962.8	934.3	917.2	895.6	877.0	860.8	855.7	840.5	834.9	826.6
20°	955.9	931.1	909.4	886.7	855.5	838.0	825.4	818.5	806.3	798.9	793.6
22.5°	926.8	901.5	876.4	849.9	824.2	804.6	795.3	784.6	778.0	767.6	761.8
25°	885.0	857.6	827.5	798.9	780.4	765.6	750.7	741.2	731.7	727.0	716.4
27.5°	836.7	807.9	779.7	758.1	735.4	720.7	707.3	698.8	687.4	679.4	673.6
30°	810.0	776.2	751.8	732.3	703.2	689.4	679.4	668.8	660.4	651.9	646.1
32.5°	779.1	748.2	725.2	700.9	678.6	663.7	650.7	641.4	634.1	626.1	620.3
35°	730.6	704.8	681.0	656.6	640.3	624.9	609.7	601.7	594.8	587.4	582.1
37.5°	686.9	662.7	640.1	617.0	596.7	584.2	571.9	565.8	556.5	551.6	546.1
40°	659.8	636.0	611.7	589.6	568.4	558.9	547.8	538.8	530.3	526.6	520.8
42.5°	630.3	606.4	585.9	562.0	544.7	531.8	521.5	511.7	505.3	500.0	496.7
45°	586.3	565.2	545.1	521.3	504.9	493.8	482.2	473.2	467.4	463.7	457.9
47.5°	543.7	522.6	502.2	481.4	465.5	452.9	441.3	435.0	427.3	422.7	418.9
50°	512.8	493.8	472.1	453.1	437.3	424.5	415.1	407.1	400.2	394.5	391.8
52.5°	484.5	464.2	445.5	427.8	411.0	396.7	388.0	379.6	374.5	367.8	364.7
55°	437.8	418.2	402.3	384.9	368.5	356.4	345.8	338.4	333.1	325.7	321.4
57.5°	393.8	376.4	357.4	342.2	325.4	315.1	306.3	296.3	289.8	284.1	279.9
60°	364.3	344.2	327.8	313.6	298.7	285.5	277.6	269.6	262.8	256.9	253.3
62.5°	333.5	315.9	300.3	284.8	271.2	259.7	250.5	243.9	237.8	234.1	230.5
65°	286.0	272.3	256.4	243.8	231.1	222.6	215.2	209.3	205.1	202.5	199.3
67.5°	242.5	229.1	215.3	202.8	194.4	187.9	183.1	178.0	175.9	172.6	170.5
70°	214.1	200.4	188.2	178.7	170.3	165.5	162.3	158.6	156.5	152.3	150.2
72.5°	183.3	173.3	164.5	156.7	150.0	145.6	141.6	137.0	133.7	129.0	126.9
75°	144.3	135.3	128.5	123.2	119.0	113.1	107.3	102.6	101.0	99.4	98.9
77.5°	106.9	101.2	96.2	91.8	86.5	82.3	81.0	80.0	79.6	78.8	78.8
80°	84.0	78.8	75.0	69.8	66.7	66.7	66.7	65.5	66.0	66.0	66.0
82.5°	62.5	57.7	55.6	53.7	53.1	53.5	53.5	53.7	53.4	54.2	53.8
85°	32.2	32.8	33.8	33.3	33.8	33.8	34.9	34.3	34.9	33.8	34.9
87.5°	14.0	15.8	16.8	17.8	18.8	19.0	19.2	19.4	20.0	20.2	20.6
90°	11.1	13.1	16.2	19.2	22.2	25.2	24.2	25.2	26.3	27.3	29.2
92.5°	43.3	58.3	84.6	128.1	170.6	155.0	116.9	84.8	67.4	59.5	54.2
95°	91.7	131.1	216.7	366.9	532.2	597.7	484.8	362.8	246.0	192.6	156.2
97.5°	108.9	151.4	233.3	402.6	678.2	926.3	991.1	904.6	724.6	594.5	473.9
100°	121.0	160.3	230.9	380.0	645.1	954.6	1153.2	1188.5	1106.8	988.9	845.8
102.5°	134.7	170.8	234.1	360.6	596.7	902.2	1161.2	1282.8	1280.2	1211.4	1120.7
105°	157.2	188.5	243.0	346.8	537.2	810.4	1099.7	1310.4	1411.3	1430.4	1404.2
107.5°	182.7	211.7	259.4	345.8	499.4	729.4	992.1	1231.0	1394.7	1483.0	1518.9
110°	199.5	227.8	273.2	349.8	484.8	683.5	924.3	1155.2	1340.7	1467.6	1538.2



TEST NUMBER: P332320-840

CATALOG NUMBER: S123RDIP-S775D1025U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	217.3	244.8	286.9	357.9	476.8	652.8	865.5	1080.2	1269.7	1412.0	1502.8
115°	244.0	271.1	309.4	370.9	473.7	620.0	794.4	980.8	1156.2	1304.3	1414.2
117.5°	270.3	295.6	333.5	388.3	475.5	600.6	751.3	908.9	1060.3	1193.3	1304.7
120°	287.3	312.5	348.8	401.2	478.8	591.7	728.8	870.9	1007.0	1128.0	1229.8
122.5°	302.7	329.4	364.9	413.3	484.4	586.0	710.2	841.1	964.3	1076.4	1170.9
125°	325.6	352.8	388.1	432.4	492.9	578.7	686.5	801.4	911.3	1008.0	1088.6
127.5°	347.0	374.2	408.3	448.2	502.6	575.0	665.5	766.7	864.6	952.0	1025.3
130°	359.8	387.1	420.3	458.7	509.1	572.6	654.2	745.0	835.7	917.3	985.8
132.5°	371.9	398.4	430.8	468.4	513.9	571.8	643.7	724.8	808.2	884.2	949.6
135°	388.1	415.3	446.6	480.8	521.2	570.6	630.1	697.5	769.1	834.7	892.1
137.5°	402.2	427.4	457.5	490.1	525.9	568.4	618.1	672.8	731.4	787.9	837.7
140°	410.3	435.5	464.7	494.9	529.2	567.5	610.9	658.2	709.6	758.0	801.4
142.5°	418.3	441.9	470.4	499.8	531.6	565.9	604.4	644.5	688.7	730.6	768.3
145°	428.4	451.6	477.8	505.0	533.2	563.5	595.7	628.0	661.3	693.5	722.8
147.5°	440.1	459.9	483.8	508.3	533.2	559.7	587.2	614.5	640.9	666.9	687.7
150°	446.6	464.7	487.9	509.1	533.2	556.4	581.6	604.8	628.0	649.1	668.3
152.5°	453.0	470.4	490.3	510.7	530.8	552.4	575.2	595.9	615.9	634.7	650.6
155°	463.7	477.8	494.9	511.1	528.2	545.3	565.5	582.6	598.7	613.9	626.0
157.5°	472.9	483.8	497.6	512.1	524.8	539.1	554.6	568.6	582.0	593.7	603.2
160°	477.8	487.9	500.0	512.1	523.2	534.2	547.3	560.5	571.6	581.6	588.7
162.5°	481.8	490.3	500.8	511.3	520.0	529.4	540.1	550.8	560.3	569.6	575.8
165°	486.9	493.9	502.0	509.1	515.1	522.2	530.2	538.3	544.3	551.4	556.4
167.5°	491.5	495.9	501.8	507.5	510.3	514.9	520.8	527.4	532.0	536.0	539.7
170°	493.9	495.9	501.0	505.0	507.1	510.1	515.1	520.2	523.2	527.1	529.2
172.5°	495.5	496.8	501.0	504.2	504.6	506.0	509.5	513.7	515.9	519.2	520.4
175°	497.0	498.0	500.0	502.0	501.0	501.0	503.0	505.0	506.0	508.1	508.1
177.5°	498.0	498.0	498.8	500.4	498.8	498.0	498.8	499.6	500.4	501.2	501.2
180°	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0



TEST NUMBER: P332320-840

CATALOG NUMBER: S123RDIP-S775D1025U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1
2.5°	1176.7	1176.3	1176.7	1175.0	1176.7	1176.3	1176.7	1181.7	1181.7	1182.2	1182.7
5°	1095.0	1094.4	1092.9	1088.1	1092.9	1094.4	1095.0	1096.5	1100.8	1108.2	1106.1
7.5°	1023.6	1022.9	1018.2	1018.3	1018.2	1022.9	1023.6	1027.7	1032.5	1037.0	1042.4
10°	981.3	981.8	975.5	971.8	975.5	981.8	981.3	985.0	991.9	995.5	999.3
12.5°	940.3	937.9	932.7	928.7	932.7	937.9	940.3	943.1	952.5	956.6	963.7
15°	886.2	880.8	868.2	869.2	868.2	880.8	886.2	884.0	893.5	898.8	900.9
17.5°	822.3	818.5	818.2	810.8	818.2	818.5	822.3	826.6	834.9	840.5	855.7
20°	785.2	782.5	783.6	776.2	783.6	782.5	785.2	793.6	798.9	806.3	818.5
22.5°	756.0	753.4	748.9	746.6	748.9	753.4	756.0	761.8	767.6	778.0	784.6
25°	713.3	709.0	704.8	707.4	704.8	709.0	713.3	716.4	727.0	731.7	741.2
27.5°	670.6	667.3	663.1	662.6	663.1	667.3	670.6	673.6	679.4	687.4	698.8
30°	643.5	640.3	638.1	635.5	638.1	640.3	643.5	646.1	651.9	660.4	668.8
32.5°	615.9	615.3	611.5	611.0	611.5	615.3	615.9	620.3	626.1	634.1	641.4
35°	580.0	576.8	575.7	576.3	575.7	576.8	580.0	582.1	587.4	594.8	601.7
37.5°	545.8	541.6	539.7	537.9	539.7	541.6	545.8	546.1	551.6	556.5	565.8
40°	521.3	517.1	516.0	514.9	516.0	517.1	521.3	520.8	526.6	530.3	538.8
42.5°	493.8	492.1	491.5	489.6	491.5	492.1	493.8	496.7	500.0	505.3	511.7
45°	456.3	455.8	452.6	453.6	452.6	455.8	456.3	457.9	463.7	467.4	473.2
47.5°	416.8	414.4	412.2	413.6	412.2	414.4	416.8	418.9	422.7	427.3	435.0
50°	389.7	388.6	383.8	384.9	383.8	388.6	389.7	391.8	394.5	400.2	407.1
52.5°	362.6	358.6	356.8	356.2	356.8	358.6	362.6	364.7	367.8	374.5	379.6
55°	317.8	313.0	310.8	309.8	310.8	313.0	317.8	321.4	325.7	333.1	338.4
57.5°	273.8	272.5	270.8	272.0	270.8	272.5	273.8	279.9	284.1	289.8	296.3
60°	247.9	247.9	247.9	247.4	247.9	247.9	247.9	253.3	256.9	262.8	269.6
62.5°	228.1	226.8	226.4	227.1	226.4	226.8	228.1	230.5	234.1	237.8	243.9
65°	197.7	197.2	195.1	194.6	195.1	197.2	197.7	199.3	202.5	205.1	209.3
67.5°	169.1	167.1	166.5	165.8	166.5	167.1	169.1	170.5	172.6	175.9	178.0
70°	147.5	146.4	143.3	143.8	143.3	146.4	147.5	150.2	152.3	156.5	158.6
72.5°	124.2	123.2	122.6	121.8	122.6	123.2	124.2	126.9	129.0	133.7	137.0
75°	98.4	97.9	97.3	99.4	97.3	97.9	98.4	98.9	99.4	101.0	102.6
77.5°	78.8	78.8	79.1	78.3	79.1	78.8	78.8	78.8	78.8	79.6	80.0
80°	66.0	66.0	65.5	65.5	65.5	66.0	66.0	66.0	66.0	66.0	65.5
82.5°	53.0	53.4	53.7	52.9	53.7	53.4	53.0	53.8	54.2	53.4	53.7
85°	34.9	34.3	35.4	34.9	35.4	34.3	34.9	34.9	33.8	34.9	34.3
87.5°	21.3	20.6	20.8	21.1	20.8	20.6	21.3	20.6	20.2	20.0	19.4
90°	28.2	29.2	30.2	29.2	30.2	29.2	28.2	29.2	27.3	26.3	25.2
92.5°	52.4	49.4	50.4	48.6	50.4	49.4	52.4	54.2	59.5	67.4	84.8
95°	137.1	128.1	121.0	116.9	121.0	128.1	137.1	156.2	192.6	246.0	362.8
97.5°	399.6	354.3	327.0	318.3	327.0	354.3	399.6	473.9	594.5	724.6	904.6
100°	744.0	670.3	631.1	632.1	631.1	670.3	744.0	845.8	988.9	1106.8	1188.5
102.5°	1041.5	983.2	950.4	927.2	950.4	983.2	1041.5	1120.7	1211.4	1280.2	1282.8
105°	1357.8	1319.5	1287.3	1282.2	1287.3	1319.5	1357.8	1404.2	1430.4	1411.3	1310.4
107.5°	1519.7	1506.8	1495.9	1486.6	1495.9	1506.8	1519.7	1518.9	1483.0	1394.7	1231.0
110°	1566.5	1574.6	1572.6	1570.5	1572.6	1574.6	1566.5	1538.2	1467.6	1340.7	1155.2



TEST NUMBER: P332320-840

CATALOG NUMBER: S123RDIP-S775D1025U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1554.4	1579.3	1587.0	1587.4	1587.0	1579.3	1554.4	1502.8	1412.0	1269.7	1080.2
115°	1489.9	1534.2	1554.4	1559.4	1554.4	1534.2	1489.9	1414.2	1304.3	1156.2	980.8
117.5°	1383.6	1434.4	1463.5	1470.3	1463.5	1434.4	1383.6	1304.7	1193.3	1060.3	908.9
120°	1309.4	1365.8	1390.1	1396.1	1390.1	1365.8	1309.4	1229.8	1128.0	1007.0	870.9
122.5°	1241.7	1292.5	1319.1	1326.8	1319.1	1292.5	1241.7	1170.9	1076.4	964.3	841.1
125°	1153.2	1197.5	1222.7	1229.8	1222.7	1197.5	1153.2	1088.6	1008.0	911.3	801.4
127.5°	1082.8	1120.7	1143.5	1149.9	1143.5	1120.7	1082.8	1025.3	952.0	864.6	766.7
130°	1039.3	1075.6	1096.7	1104.8	1096.7	1075.6	1039.3	985.8	917.3	835.7	745.0
132.5°	999.8	1036.0	1054.8	1060.5	1054.8	1036.0	999.8	949.6	884.2	808.2	724.8
135°	941.5	971.7	989.9	996.9	989.9	971.7	941.5	892.1	834.7	769.1	697.5
137.5°	879.2	909.9	925.1	929.8	925.1	909.9	879.2	837.7	787.9	731.4	672.8
140°	839.7	867.9	884.0	883.0	884.0	867.9	839.7	801.4	758.0	709.6	658.2
142.5°	801.0	826.0	840.5	839.5	840.5	826.0	801.0	768.3	730.6	688.7	644.5
145°	747.9	769.1	777.2	779.2	777.2	769.1	747.9	722.8	693.5	661.3	628.0
147.5°	706.8	721.1	728.8	729.6	728.8	721.1	706.8	687.7	666.9	640.9	614.5
150°	683.5	694.5	700.5	700.5	700.5	694.5	683.5	668.3	649.1	628.0	604.8
152.5°	662.5	672.8	676.4	676.4	676.4	672.8	662.5	650.6	634.7	615.9	595.9
155°	635.1	643.1	645.1	646.1	645.1	643.1	635.1	626.0	613.9	598.7	582.6
157.5°	611.1	617.1	618.7	618.5	618.7	617.1	611.1	603.2	593.7	582.0	568.6
160°	595.7	601.8	601.8	600.8	601.8	601.8	595.7	588.7	581.6	571.6	560.5
162.5°	580.5	585.6	585.6	584.6	585.6	585.6	580.5	575.8	569.6	560.3	550.8
165°	560.5	564.5	563.5	563.5	563.5	564.5	560.5	556.4	551.4	544.3	538.3
167.5°	541.5	544.3	543.3	543.3	543.3	544.3	541.5	539.7	536.0	532.0	527.4
170°	530.2	532.2	531.2	531.2	531.2	532.2	530.2	529.2	527.1	523.2	520.2
172.5°	520.6	522.6	520.8	520.0	520.8	522.6	520.6	520.4	519.2	515.9	513.7
175°	508.1	509.1	508.1	507.1	508.1	509.1	508.1	508.1	508.1	506.0	505.0
177.5°	500.4	501.2	499.6	499.6	499.6	501.2	500.4	501.2	501.2	500.4	499.6
180°	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0



TEST NUMBER: P332320-840

CATALOG NUMBER: S123RDIP-S775D1025U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1
2.5°	1178.8	1184.8	1190.6	1196.2	1204.7	1208.4	1214.0	1216.1	1222.3	1231.7	1239.3
5°	1107.1	1115.6	1126.7	1135.7	1149.9	1161.0	1173.3	1184.9	1198.6	1218.2	1235.6
7.5°	1046.3	1054.7	1068.0	1084.7	1100.4	1116.2	1132.9	1148.7	1168.3	1196.4	1224.2
10°	1006.1	1016.2	1032.1	1050.1	1069.5	1084.9	1104.5	1124.6	1148.9	1181.1	1214.5
12.5°	971.5	979.0	997.3	1014.5	1036.6	1056.1	1075.3	1098.7	1126.5	1160.8	1200.9
15°	916.3	926.9	944.8	963.8	987.1	1007.7	1032.6	1061.2	1088.1	1130.4	1179.0
17.5°	860.8	877.0	895.6	917.2	934.3	962.8	989.8	1019.1	1052.3	1097.1	1150.4
20°	825.4	838.0	855.5	886.7	909.4	931.1	955.9	992.4	1023.1	1073.8	1129.3
22.5°	795.3	804.6	824.2	849.9	876.4	901.5	926.8	961.5	999.4	1047.6	1107.7
25°	750.7	765.6	780.4	798.9	827.5	857.6	885.0	914.6	954.8	1006.1	1071.2
27.5°	707.3	720.7	735.4	758.1	779.7	807.9	836.7	870.6	913.7	968.0	1034.0
30°	679.4	689.4	703.2	732.3	751.8	776.2	810.0	840.1	880.3	938.0	1007.7
32.5°	650.7	663.7	678.6	700.9	725.2	748.2	779.1	811.8	852.8	909.6	981.1
35°	609.7	624.9	640.3	656.6	681.0	704.8	730.6	766.6	808.4	863.4	933.7
37.5°	571.9	584.2	596.7	617.0	640.1	662.7	686.9	722.4	761.6	821.0	885.4
40°	547.8	558.9	568.4	589.6	611.7	636.0	659.8	691.1	733.4	788.8	851.2
42.5°	521.5	531.8	544.7	562.0	585.9	606.4	630.3	659.7	699.5	755.9	810.6
45°	482.2	493.8	504.9	521.3	545.1	565.2	586.3	614.4	655.1	701.7	750.2
47.5°	441.3	452.9	465.5	481.4	502.2	522.6	543.7	568.6	605.7	651.4	684.2
50°	415.1	424.5	437.3	453.1	472.1	493.8	512.8	539.8	575.2	611.2	639.7
52.5°	388.0	396.7	411.0	427.8	445.5	464.2	484.5	507.7	539.7	573.5	596.2
55°	345.8	356.4	368.5	384.9	402.3	418.2	437.8	461.6	487.0	512.3	527.7
57.5°	306.3	315.1	325.4	342.2	357.4	376.4	393.8	412.4	435.9	455.0	465.0
60°	277.6	285.5	298.7	313.6	327.8	344.2	364.3	382.8	400.8	416.1	424.0
62.5°	250.5	259.7	271.2	284.8	300.3	315.9	333.5	348.9	364.8	378.0	383.4
65°	215.2	222.6	231.1	243.8	256.4	272.3	286.0	301.8	313.6	320.9	325.7
67.5°	183.1	187.9	194.4	202.8	215.3	229.1	242.5	254.9	264.6	269.6	273.9
70°	162.3	165.5	170.3	178.7	188.2	200.4	214.1	223.1	231.6	235.8	240.0
72.5°	141.6	145.6	150.0	156.7	164.5	173.3	183.3	194.4	199.0	204.1	206.6
75°	107.3	113.1	119.0	123.2	128.5	135.3	144.3	151.2	153.9	158.0	158.6
77.5°	81.0	82.3	86.5	91.8	96.2	101.2	106.9	113.0	114.3	116.5	118.0
80°	66.7	66.7	66.7	69.8	75.0	78.8	84.0	87.3	89.4	89.9	90.4
82.5°	53.5	53.5	53.1	53.7	55.6	57.7	62.5	66.0	67.8	67.5	66.3
85°	34.9	33.8	33.8	33.3	33.8	32.8	32.2	34.3	37.6	37.6	36.5
87.5°	19.2	19.0	18.8	17.8	16.8	15.8	14.0	14.0	13.4	14.7	13.9
90°	24.2	25.2	22.2	19.2	16.2	13.1	11.1	9.1	6.1	4.0	2.0
92.5°	116.9	155.0	170.6	128.1	84.6	58.3	43.3	34.8	27.1	18.6	12.5
95°	484.8	597.7	532.2	366.9	216.7	131.1	91.7	65.5	48.4	37.3	34.2
97.5°	991.1	926.3	678.2	402.6	233.3	151.4	108.9	83.0	68.2	59.5	58.5
100°	1153.2	954.6	645.1	380.0	230.9	160.3	121.0	96.7	82.7	75.6	74.6
102.5°	1161.2	902.2	596.7	360.6	234.1	170.8	134.7	112.9	99.6	93.3	91.5
105°	1099.7	810.4	537.2	346.8	243.0	188.5	157.2	138.1	126.0	120.0	116.9
107.5°	992.1	729.4	499.4	345.8	259.4	211.7	182.7	164.7	152.8	146.9	143.9
110°	924.3	683.5	484.8	349.8	273.2	227.8	199.5	182.5	171.4	166.3	163.3



TEST NUMBER: P332320-840

CATALOG NUMBER: S123RDIP-S775D1025U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	865.5	652.8	476.8	357.9	286.9	244.8	217.3	200.2	189.1	184.1	181.1
115°	794.4	620.0	473.7	370.9	309.4	271.1	244.0	226.8	216.7	210.7	206.6
117.5°	751.3	600.6	475.5	388.3	333.5	295.6	270.3	251.2	242.0	236.9	232.3
120°	728.8	591.7	478.8	401.2	348.8	312.5	287.3	268.1	258.0	253.0	249.9
122.5°	710.2	586.0	484.4	413.3	364.9	329.4	302.7	284.3	273.4	268.3	265.3
125°	686.5	578.7	492.9	432.4	388.1	352.8	325.6	306.4	295.4	289.3	287.3
127.5°	665.5	575.0	502.6	448.2	408.3	374.2	347.0	325.8	314.5	307.0	304.1
130°	654.2	572.6	509.1	458.7	420.3	387.1	359.8	338.7	326.6	317.5	314.5
132.5°	643.7	571.8	513.9	468.4	430.8	398.4	371.9	350.8	336.3	326.4	322.6
135°	630.1	570.6	521.2	480.8	446.6	415.3	388.1	366.9	351.8	340.7	336.7
137.5°	618.1	568.4	525.9	490.1	457.5	427.4	402.2	381.2	365.1	354.3	350.0
140°	610.9	567.5	529.2	494.9	464.7	435.5	410.3	390.1	374.0	363.9	358.9
142.5°	604.4	565.9	531.6	499.8	470.4	441.9	418.3	398.2	383.6	372.7	368.5
145°	595.7	563.5	533.2	505.0	477.8	451.6	428.4	411.3	396.2	387.1	384.1
147.5°	587.2	559.7	533.2	508.3	483.8	459.9	440.1	423.5	410.5	401.6	399.8
150°	581.6	556.4	533.2	509.1	487.9	464.7	446.6	432.4	419.3	411.3	410.3
152.5°	575.2	552.4	530.8	510.7	490.3	470.4	453.0	440.5	429.0	420.9	420.7
155°	565.5	545.3	528.2	511.1	494.9	477.8	463.7	452.6	442.5	436.5	436.5
157.5°	554.6	539.1	524.8	512.1	497.6	483.8	472.9	463.5	454.6	449.8	449.0
160°	547.3	534.2	523.2	512.1	500.0	487.9	477.8	470.7	462.7	458.7	458.7
162.5°	540.1	529.4	520.0	511.3	500.8	490.3	481.8	475.5	469.2	466.0	466.0
165°	530.2	522.2	515.1	509.1	502.0	493.9	486.9	482.8	477.8	475.7	476.8
167.5°	520.8	514.9	510.3	507.5	501.8	495.9	491.5	488.7	484.8	483.8	485.0
170°	515.1	510.1	507.1	505.0	501.0	495.9	493.9	491.9	488.9	487.9	489.9
172.5°	509.5	506.0	504.6	504.2	501.0	496.8	495.5	494.3	492.1	491.9	493.1
175°	503.0	501.0	501.0	502.0	500.0	498.0	497.0	497.0	494.9	495.9	497.0
177.5°	498.8	498.0	498.8	500.4	498.8	498.0	498.0	498.0	497.2	498.0	498.8
180°	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0



TEST NUMBER: P332320-840

CATALOG NUMBER: S123RDIP-S775D1025U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1
2.5°	1241.8	1246.5	1252.4	1261.3	1268.1	1273.9	1275.3	1277.0	1281.2	1288.4	1293.8
5°	1249.9	1262.0	1281.6	1300.6	1321.3	1338.2	1354.0	1365.1	1375.7	1398.0	1415.9
7.5°	1247.4	1274.4	1305.0	1339.3	1373.8	1407.3	1438.5	1466.2	1493.9	1526.3	1563.2
10°	1245.7	1277.4	1318.6	1362.5	1410.6	1457.6	1503.2	1538.5	1579.8	1616.8	1663.9
12.5°	1237.6	1283.3	1332.6	1388.8	1447.8	1502.1	1562.0	1610.9	1658.1	1711.5	1766.3
15°	1227.2	1282.6	1345.0	1419.6	1509.4	1575.1	1636.4	1721.5	1779.7	1837.9	1916.0
17.5°	1208.0	1275.8	1353.7	1450.6	1525.6	1613.7	1706.0	1773.2	1851.6	1933.5	2004.4
20°	1192.8	1271.5	1358.8	1454.0	1549.6	1645.4	1734.7	1815.0	1896.0	1990.6	2048.8
22.5°	1177.6	1255.5	1346.2	1447.2	1550.0	1650.8	1752.0	1846.3	1937.4	2033.0	2107.2
25°	1145.2	1237.7	1336.1	1439.2	1540.7	1651.7	1772.2	1877.4	1990.0	2088.4	2158.8
27.5°	1112.4	1197.2	1295.2	1399.7	1512.6	1643.8	1785.5	1905.2	2018.0	2088.4	2110.5
30°	1082.8	1172.7	1262.5	1368.9	1491.0	1637.4	1788.1	1925.0	2017.6	2048.2	2025.5
32.5°	1052.8	1134.2	1223.2	1332.0	1461.8	1621.7	1791.5	1913.2	1968.9	1945.5	1852.9
35°	999.8	1073.3	1159.4	1268.4	1417.4	1613.2	1777.6	1860.0	1846.2	1714.0	1539.6
37.5°	943.1	1003.0	1082.8	1196.7	1371.6	1578.7	1717.5	1729.6	1610.6	1407.8	1206.2
40°	898.3	952.2	1034.2	1153.2	1336.1	1544.9	1657.0	1607.8	1423.3	1197.5	1029.5
42.5°	854.7	900.2	979.2	1107.4	1302.2	1498.8	1566.9	1459.8	1246.9	1033.4	880.5
45°	780.9	823.7	903.0	1034.7	1232.9	1410.6	1401.6	1215.5	1002.5	830.6	703.7
47.5°	710.9	748.3	822.7	957.2	1151.7	1278.4	1194.4	996.3	815.6	677.7	587.2
50°	661.5	698.4	772.4	905.1	1086.5	1179.0	1059.0	868.2	702.7	588.4	516.5
52.5°	614.1	650.3	717.9	847.2	1007.8	1063.2	934.2	757.3	619.4	520.8	459.0
55°	547.8	575.2	636.0	759.7	879.8	892.5	761.8	613.8	500.2	431.4	389.1
57.5°	480.2	503.8	563.9	662.5	746.7	740.1	616.3	488.2	411.6	360.6	329.9
60°	436.2	459.5	512.3	596.9	660.4	638.1	524.5	421.4	355.8	318.3	294.0
62.5°	395.2	413.3	462.8	524.6	570.3	545.1	448.4	363.0	311.0	279.3	260.1
65°	335.8	350.5	390.2	422.4	447.8	423.5	343.2	283.9	246.4	224.2	211.0
67.5°	279.2	288.7	313.8	325.4	343.3	316.6	258.0	218.3	197.0	178.2	169.1
70°	243.8	250.6	263.9	273.4	278.1	250.6	207.2	178.1	160.2	146.9	141.2
72.5°	208.2	214.2	216.9	224.7	222.3	196.5	166.6	143.5	130.6	121.6	114.1
75°	159.2	161.8	159.2	155.9	149.1	131.1	110.5	98.9	89.4	85.1	82.5
77.5°	116.0	115.1	111.6	106.5	94.8	83.5	72.4	68.6	64.4	62.2	61.2
80°	89.4	87.3	84.0	76.1	66.0	58.2	55.5	52.9	51.3	48.7	48.1
82.5°	66.6	65.2	60.0	53.3	46.3	42.5	40.3	39.4	37.8	36.4	36.3
85°	35.4	33.8	28.0	24.3	23.2	22.2	21.7	21.7	19.6	19.0	19.0
87.5°	12.2	10.1	10.3	9.4	9.8	9.6	10.6	10.4	10.5	10.8	10.1
90°	4.0	6.1	9.1	11.1	13.1	16.2	19.2	22.2	25.2	24.2	25.2
92.5°	18.6	27.1	34.8	43.3	58.3	84.6	128.1	170.6	155.0	116.9	84.8
95°	37.3	48.4	65.5	91.7	131.1	216.7	366.9	532.2	597.7	484.8	362.8
97.5°	59.5	68.2	83.0	108.9	151.4	233.3	402.6	678.2	926.3	991.1	904.6
100°	75.6	82.7	96.7	121.0	160.3	230.9	380.0	645.1	954.6	1153.2	1188.5
102.5°	93.3	99.6	112.9	134.7	170.8	234.1	360.6	596.7	902.2	1161.2	1282.8
105°	120.0	126.0	138.1	157.2	188.5	243.0	346.8	537.2	810.4	1099.7	1310.4
107.5°	146.9	152.8	164.7	182.7	211.7	259.4	345.8	499.4	729.4	992.1	1231.0
110°	166.3	171.4	182.5	199.5	227.8	273.2	349.8	484.8	683.5	924.3	1155.2



TEST NUMBER: P332320-840

CATALOG NUMBER: S123RDIP-S775D1025U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	184.1	189.1	200.2	217.3	244.8	286.9	357.9	476.8	652.8	865.5	1080.2
115°	210.7	216.7	226.8	244.0	271.1	309.4	370.9	473.7	620.0	794.4	980.8
117.5°	236.9	242.0	251.2	270.3	295.6	333.5	388.3	475.5	600.6	751.3	908.9
120°	253.0	258.0	268.1	287.3	312.5	348.8	401.2	478.8	591.7	728.8	870.9
122.5°	268.3	273.4	284.3	302.7	329.4	364.9	413.3	484.4	586.0	710.2	841.1
125°	289.3	295.4	306.4	325.6	352.8	388.1	432.4	492.9	578.7	686.5	801.4
127.5°	307.0	314.5	325.8	347.0	374.2	408.3	448.2	502.6	575.0	665.5	766.7
130°	317.5	326.6	338.7	359.8	387.1	420.3	458.7	509.1	572.6	654.2	745.0
132.5°	326.4	336.3	350.8	371.9	398.4	430.8	468.4	513.9	571.8	643.7	724.8
135°	340.7	351.8	366.9	388.1	415.3	446.6	480.8	521.2	570.6	630.1	697.5
137.5°	354.3	365.1	381.2	402.2	427.4	457.5	490.1	525.9	568.4	618.1	672.8
140°	363.9	374.0	390.1	410.3	435.5	464.7	494.9	529.2	567.5	610.9	658.2
142.5°	372.7	383.6	398.2	418.3	441.9	470.4	499.8	531.6	565.9	604.4	644.5
145°	387.1	396.2	411.3	428.4	451.6	477.8	505.0	533.2	563.5	595.7	628.0
147.5°	401.6	410.5	423.5	440.1	459.9	483.8	508.3	533.2	559.7	587.2	614.5
150°	411.3	419.3	432.4	446.6	464.7	487.9	509.1	533.2	556.4	581.6	604.8
152.5°	420.9	429.0	440.5	453.0	470.4	490.3	510.7	530.8	552.4	575.2	595.9
155°	436.5	442.5	452.6	463.7	477.8	494.9	511.1	528.2	545.3	565.5	582.6
157.5°	449.8	454.6	463.5	472.9	483.8	497.6	512.1	524.8	539.1	554.6	568.6
160°	458.7	462.7	470.7	477.8	487.9	500.0	512.1	523.2	534.2	547.3	560.5
162.5°	466.0	469.2	475.5	481.8	490.3	500.8	511.3	520.0	529.4	540.1	550.8
165°	475.7	477.8	482.8	486.9	493.9	502.0	509.1	515.1	522.2	530.2	538.3
167.5°	483.8	484.8	488.7	491.5	495.9	501.8	507.5	510.3	514.9	520.8	527.4
170°	487.9	488.9	491.9	493.9	495.9	501.0	505.0	507.1	510.1	515.1	520.2
172.5°	491.9	492.1	494.3	495.5	496.8	501.0	504.2	504.6	506.0	509.5	513.7
175°	495.9	494.9	497.0	497.0	498.0	500.0	502.0	501.0	501.0	503.0	505.0
177.5°	498.0	497.2	498.0	498.0	498.0	498.8	500.4	498.8	498.0	498.8	499.6
180°	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0



TEST NUMBER: P332320-840

CATALOG NUMBER: S123RDIP-S775D1025U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1
2.5°	1302.7	1302.7	1304.4	1310.8	1311.6	1317.2	1315.5
5°	1431.8	1441.8	1445.5	1461.4	1470.9	1475.1	1466.6
7.5°	1589.5	1617.9	1631.3	1647.9	1662.6	1667.1	1655.5
10°	1704.6	1734.1	1759.1	1774.3	1788.7	1798.2	1810.3
12.5°	1815.8	1852.2	1875.8	1897.4	1912.2	1924.2	1926.2
15°	1936.7	1991.7	2033.5	2064.1	2079.4	2087.4	2084.2
17.5°	2058.6	2109.6	2139.3	2170.6	2191.8	2192.9	2193.5
20°	2127.6	2177.3	2211.6	2234.8	2258.7	2257.7	2262.9
22.5°	2173.6	2212.8	2239.1	2256.0	2264.2	2260.2	2261.2
25°	2195.2	2206.9	2202.1	2175.1	2168.3	2143.4	2147.7
27.5°	2084.0	2029.0	1972.1	1899.0	1841.2	1795.1	1797.5
30°	1933.0	1835.7	1724.6	1631.6	1548.1	1524.8	1475.1
32.5°	1721.9	1576.0	1445.9	1359.2	1287.5	1268.1	1224.8
35°	1364.1	1222.3	1088.6	1008.2	976.5	932.1	931.6
37.5°	1060.3	935.5	864.7	804.5	772.8	746.0	743.4
40°	891.9	794.7	741.2	697.9	666.7	646.6	641.9
42.5°	774.4	695.7	645.7	618.8	594.8	584.4	576.7
45°	632.4	579.5	544.6	520.3	509.2	501.2	497.0
47.5°	529.0	493.5	469.7	453.5	444.5	436.2	438.4
50°	472.7	443.6	426.2	410.8	403.9	398.1	398.7
52.5°	427.4	401.3	387.2	376.2	367.6	363.5	361.4
55°	362.7	346.3	332.0	324.1	319.3	313.6	311.9
57.5°	309.4	296.7	285.1	276.1	274.9	269.3	270.0
60°	273.9	263.3	253.8	249.0	245.3	240.5	242.2
62.5°	244.7	235.8	227.1	223.2	219.5	216.0	216.8
65°	200.4	191.9	186.6	184.5	182.9	181.4	179.8
67.5°	159.7	154.5	151.2	146.6	143.4	142.9	141.3
70°	134.3	127.4	121.6	115.8	114.2	113.7	114.2
72.5°	107.7	103.3	101.7	98.9	98.6	97.1	98.2
75°	80.9	79.3	78.3	76.1	76.1	76.1	76.1
77.5°	59.7	58.7	58.1	57.7	57.1	56.4	56.2
80°	46.6	45.9	44.9	44.9	44.4	44.9	44.4
82.5°	35.1	35.0	33.9	33.9	33.4	33.1	33.4
85°	18.0	17.5	18.5	17.5	18.0	17.0	18.0
87.5°	10.3	10.5	10.5	10.3	10.1	11.1	10.1
90°	26.3	27.3	29.2	28.2	29.2	30.2	29.2
92.5°	67.4	59.5	54.2	52.4	49.4	50.4	48.6
95°	246.0	192.6	156.2	137.1	128.1	121.0	116.9
97.5°	724.6	594.5	473.9	399.6	354.3	327.0	318.3
100°	1106.8	988.9	845.8	744.0	670.3	631.1	632.1
102.5°	1280.2	1211.4	1120.7	1041.5	983.2	950.4	927.2
105°	1411.3	1430.4	1404.2	1357.8	1319.5	1287.3	1282.2
107.5°	1394.7	1483.0	1518.9	1519.7	1506.8	1495.9	1486.6
110°	1340.7	1467.6	1538.2	1566.5	1574.6	1572.6	1570.5



TEST NUMBER: P332320-840

CATALOG NUMBER: S123RDIP-S775D1025U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1269.7	1412.0	1502.8	1554.4	1579.3	1587.0	1587.4
115°	1156.2	1304.3	1414.2	1489.9	1534.2	1554.4	1559.4
117.5°	1060.3	1193.3	1304.7	1383.6	1434.4	1463.5	1470.3
120°	1007.0	1128.0	1229.8	1309.4	1365.8	1390.1	1396.1
122.5°	964.3	1076.4	1170.9	1241.7	1292.5	1319.1	1326.8
125°	911.3	1008.0	1088.6	1153.2	1197.5	1222.7	1229.8
127.5°	864.6	952.0	1025.3	1082.8	1120.7	1143.5	1149.9
130°	835.7	917.3	985.8	1039.3	1075.6	1096.7	1104.8
132.5°	808.2	884.2	949.6	999.8	1036.0	1054.8	1060.5
135°	769.1	834.7	892.1	941.5	971.7	989.9	996.9
137.5°	731.4	787.9	837.7	879.2	909.9	925.1	929.8
140°	709.6	758.0	801.4	839.7	867.9	884.0	883.0
142.5°	688.7	730.6	768.3	801.0	826.0	840.5	839.5
145°	661.3	693.5	722.8	747.9	769.1	777.2	779.2
147.5°	640.9	666.9	687.7	706.8	721.1	728.8	729.6
150°	628.0	649.1	668.3	683.5	694.5	700.5	700.5
152.5°	615.9	634.7	650.6	662.5	672.8	676.4	676.4
155°	598.7	613.9	626.0	635.1	643.1	645.1	646.1
157.5°	582.0	593.7	603.2	611.1	617.1	618.7	618.5
160°	571.6	581.6	588.7	595.7	601.8	601.8	600.8
162.5°	560.3	569.6	575.8	580.5	585.6	585.6	584.6
165°	544.3	551.4	556.4	560.5	564.5	563.5	563.5
167.5°	532.0	536.0	539.7	541.5	544.3	543.3	543.3
170°	523.2	527.1	529.2	530.2	532.2	531.2	531.2
172.5°	515.9	519.2	520.4	520.6	522.6	520.8	520.0
175°	506.0	508.1	508.1	508.1	509.1	508.1	507.1
177.5°	500.4	501.2	501.2	500.4	501.2	499.6	499.6
180°	498.0	498.0	498.0	498.0	498.0	498.0	498.0

(END OF REPORT)