

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331894-940

Luminaire Tested: **S123DIP-S340D1025U940-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331894-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S340D1025U940-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1025 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4605.6 lumens
Efficiency: N/A
Efficacy: 123.5 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 37.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331894-940

CATALOG NUMBER: S123DIP-S340D1025U940-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331894-940

CATALOG NUMBER: S123DIP-S340D1025U940-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	28				
1	93	89	85	82	83	80	77	74	62	60	59	47	45	44	32	31	31	24				
2	85	78	72	67	76	70	65	61	55	52	49	41	39	37	28	27	26	20				
3	77	68	61	56	69	61	56	51	48	44	41	36	34	31	25	24	22	17				
4	71	60	53	47	63	54	48	43	43	38	35	32	29	27	23	21	19	15				
5	65	54	46	40	58	48	42	37	38	34	30	29	26	23	20	18	17	13				
6	60	48	40	35	53	43	37	32	35	30	26	26	23	20	18	16	15	12				
7	55	43	36	30	49	39	33	28	31	26	23	24	20	18	17	15	13	10				
8	51	39	32	27	46	35	29	24	28	24	20	22	18	16	15	13	12	9				
9	47	36	28	24	42	32	26	22	26	21	18	20	17	14	14	12	11	8				
10	44	33	26	21	40	30	23	19	24	19	16	18	15	13	13	11	10	8				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4614	4614	4614	4614
5°	5503	4635	4107	4635
10°	6889	4612	3711	4612
15°	8449	4574	3455	4574
20°	10065	4517	3289	4517
25°	10688	4445	3252	4445
30°	9161	4395	3269	4395
35°	6370	4322	3303	4322
40°	4799	4235	3292	4235
45°	3984	4107	3252	4107
50°	3569	3848	3220	3848
55°	3337	3567	3181	3567
60°	3130	3272	3147	3272
65°	2942	2985	3049	2985
70°	2760	2656	2902	2656
75°	2470	2325	2662	2325
80°	2163	1909	2294	1909
85°	1692	1383	1544	1383



TEST NUMBER: P331894-940

CATALOG NUMBER: S123DIP-S340D1025U940-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.2	0.9
10°-20°	135.4	2.9
20°-30°	227.3	4.9
30°-40°	257.4	5.6
40°-50°	230.8	5.0
50°-60°	186.3	4.0
60°-70°	129.8	2.8
70°-80°	68.2	1.5
80°-90°	20.1	0.4
90°-100°	244.7	5.3
100°-110°	692.9	15.0
110°-120°	681.6	14.8
120°-130°	543.7	11.8
130°-140°	428.7	9.3
140°-150°	319.9	6.9
150°-160°	223.0	4.8
160°-170°	131.0	2.8
170°-180°	42.6	0.9
0°-30°	405.0	8.8
0°-40°	662.4	14.4
0°-60°	1079.4	23.4
0°-90°	1297.5	28.2
90°-120°	1619.2	35.2
90°-150°	2911.5	63.2
90°-180°	3308.0	71.8
0°-180°	4605.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	429	429	429	429	429	
5°	509	429	380	429	509	53
15°	758	410	310	410	758	219
25°	900	374	274	374	900	395
35°	485	329	251	329	485	315
45°	262	270	214	270	262	207
55°	178	190	170	190	178	160
65°	116	117	120	117	116	115
75°	59	56	64	56	59	64
85°	14	11	12	11	14	17
90°	26	2	26	2	26	14
95°	103	30	103	30	103	186
105°	1132	103	1132	103	1132	1117
115°	1377	182	1377	182	1377	1338
125°	1086	254	1086	254	1086	984
135°	880	297	880	297	880	683
145°	688	339	688	339	688	438
155°	570	385	570	385	570	266
165°	498	421	498	421	498	142
175°	448	439	448	439	448	43
180°	440	440	440	440	440	



TEST NUMBER: P331894-940

CATALOG NUMBER: S123DIP-S340D1025U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7
2.5°	455.0	454.7	453.9	454.5	453.2	451.4	451.2	449.5	444.7	444.4	443.1
5°	509.3	507.7	507.5	507.3	504.4	500.4	492.9	492.3	482.3	477.4	471.4
7.5°	579.8	580.6	577.6	575.0	566.1	560.2	552.1	541.9	529.7	517.2	509.0
10°	630.3	637.1	628.7	622.8	617.4	607.3	595.4	580.6	565.9	548.7	535.6
12.5°	684.5	687.8	686.1	680.6	672.3	656.7	635.8	619.5	605.9	577.2	565.6
15°	758.2	770.9	762.8	744.1	744.5	729.8	702.4	672.3	656.2	631.1	596.8
17.5°	836.9	838.4	835.0	819.4	809.0	788.7	763.4	734.6	702.1	671.7	635.3
20°	878.7	877.4	870.2	862.1	844.3	828.5	800.8	768.7	727.1	697.1	657.5
22.5°	902.0	899.9	896.4	889.7	874.9	857.9	833.0	797.9	758.3	717.1	671.3
25°	899.9	902.6	903.0	901.2	896.0	885.8	866.3	838.2	798.8	745.7	698.0
27.5°	818.5	822.3	833.4	843.3	854.3	865.5	864.0	850.1	820.8	775.1	716.7
30°	737.1	728.7	749.3	775.3	792.9	824.1	841.5	842.6	826.2	786.9	730.0
32.5°	624.0	633.2	642.3	674.2	712.8	747.8	782.6	810.5	813.7	787.6	737.8
35°	484.8	496.3	512.9	529.5	571.1	606.8	667.9	721.0	763.4	769.0	738.5
37.5°	390.7	396.4	406.9	423.6	450.7	493.1	540.3	607.5	669.0	714.6	716.6
40°	341.5	343.2	355.0	367.7	389.7	424.6	467.2	526.6	600.1	664.0	690.5
42.5°	304.6	308.3	313.3	325.5	343.0	369.3	408.8	458.0	525.4	598.8	650.8
45°	261.7	265.9	269.0	277.1	289.6	307.3	334.8	379.8	431.1	506.8	576.8
47.5°	233.4	233.7	236.0	242.2	250.7	263.9	283.5	312.3	359.4	420.9	492.8
50°	213.1	216.4	217.3	222.0	228.7	238.4	254.7	279.2	317.8	371.8	437.9
52.5°	198.9	199.8	202.2	205.6	211.4	219.0	233.1	252.3	282.6	328.7	389.4
55°	177.8	177.8	180.1	182.8	186.1	193.0	202.3	216.4	239.5	275.3	325.6
57.5°	158.4	159.4	161.0	161.8	164.7	169.2	177.0	187.8	204.9	232.5	272.4
60°	145.4	147.3	147.0	148.7	151.2	154.8	161.4	170.1	185.5	207.5	241.2
62.5°	134.1	134.0	133.9	136.0	138.4	141.8	146.2	153.6	166.7	186.3	214.9
65°	115.5	115.1	116.5	117.8	118.6	121.1	124.4	131.1	139.8	154.4	176.6
67.5°	99.0	97.7	98.5	99.0	100.4	102.4	105.5	109.6	116.5	128.1	144.9
70°	87.7	86.6	86.4	86.9	88.1	89.5	91.8	95.8	102.2	111.6	123.8
72.5°	76.1	75.3	75.3	76.2	76.8	77.8	79.4	82.9	88.1	95.1	106.6
75°	59.4	59.4	59.4	59.7	60.3	61.1	62.3	64.2	68.1	73.1	80.8
77.5°	44.5	44.5	44.2	44.2	45.1	45.5	45.7	47.5	49.8	53.1	58.7
80°	34.9	33.9	34.2	34.9	35.3	35.5	36.1	36.6	38.4	40.3	44.2
82.5°	25.9	25.1	25.1	26.1	26.2	26.4	27.0	27.6	28.3	30.0	32.1
85°	13.7	13.7	13.9	13.9	14.1	13.9	14.5	14.7	14.7	15.8	17.0
87.5°	10.2	10.0	10.0	10.0	10.0	9.8	9.8	9.8	9.7	10.1	9.7
90°	25.8	26.7	25.8	24.9	25.8	24.1	23.2	22.3	21.4	22.3	19.6
92.5°	42.9	44.5	43.6	46.3	47.9	52.5	59.5	74.9	103.3	136.9	150.6
95°	103.3	106.8	113.1	121.1	137.9	170.0	217.2	320.4	428.1	527.8	469.9
97.5°	281.1	288.7	312.8	352.8	418.5	525.0	639.8	798.8	875.1	818.0	598.9
100°	558.1	557.2	591.9	656.9	746.8	873.2	977.3	1049.5	1018.2	842.9	569.6
102.5°	818.7	839.2	868.2	919.6	989.6	1069.7	1130.4	1132.7	1025.4	796.7	526.9
105°	1132.2	1136.7	1165.1	1198.9	1239.9	1263.0	1246.2	1157.1	971.1	715.6	474.4
107.5°	1312.7	1320.9	1330.5	1341.9	1341.2	1309.5	1231.5	1087.0	876.0	644.1	441.0
110°	1386.8	1388.6	1390.4	1383.2	1358.3	1295.9	1183.8	1020.0	816.2	603.5	428.1



TEST NUMBER: P331894-940

CATALOG NUMBER: S123DIP-S340D1025U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1401.7	1401.3	1394.5	1372.5	1327.0	1246.8	1121.1	953.8	764.2	576.4	421.0
115°	1377.0	1372.5	1354.7	1315.5	1248.8	1151.7	1020.9	866.0	701.4	547.4	418.3
117.5°	1298.2	1292.3	1266.6	1221.7	1152.1	1053.6	936.2	802.5	663.4	530.3	419.9
120°	1232.8	1227.4	1206.0	1156.2	1085.9	996.0	889.2	769.0	643.5	522.5	422.8
122.5°	1171.5	1164.8	1141.3	1096.4	1033.9	950.5	851.5	742.7	627.1	517.5	427.8
125°	1085.9	1079.7	1057.4	1018.2	961.3	890.1	804.7	707.7	606.2	511.0	435.2
127.5°	1015.4	1009.7	989.6	956.1	905.4	840.6	763.5	677.0	587.6	507.7	443.8
130°	975.5	968.4	949.8	917.7	870.5	809.9	737.9	657.8	577.7	505.6	449.5
132.5°	936.4	931.4	914.8	882.8	838.5	780.8	713.6	640.0	568.4	504.9	453.8
135°	880.3	874.1	858.0	831.3	787.7	737.0	679.1	615.9	556.3	503.8	460.2
137.5°	821.0	816.9	803.4	776.3	739.7	695.7	645.9	594.1	545.8	501.9	464.4
140°	779.7	780.6	766.3	741.5	707.7	669.3	626.6	581.2	539.4	501.1	467.3
142.5°	741.3	742.2	729.3	707.3	678.4	645.2	608.1	569.1	533.7	499.7	469.4
145°	688.0	686.3	679.1	660.4	638.2	612.3	583.9	554.6	526.0	497.6	470.8
147.5°	644.3	643.5	636.8	624.1	607.3	588.9	565.9	542.6	518.5	494.2	470.8
150°	618.6	618.6	613.2	603.5	590.1	573.2	554.6	534.0	513.5	491.3	470.8
152.5°	597.3	597.3	594.1	585.0	574.4	560.4	543.9	526.2	507.9	487.8	468.7
155°	570.5	569.6	567.8	560.8	552.8	542.1	528.7	514.4	499.4	481.5	466.4
157.5°	546.2	546.4	544.9	539.6	532.6	524.2	513.9	502.0	489.7	476.0	463.4
160°	530.5	531.4	531.4	526.0	519.8	513.5	504.7	494.9	483.3	471.7	462.0
162.5°	516.2	517.1	517.1	512.6	508.5	502.9	494.7	486.3	476.9	467.4	459.1
165°	497.6	497.6	498.5	494.9	491.3	486.9	480.6	475.3	468.1	461.1	454.9
167.5°	479.7	479.7	480.6	478.1	476.5	473.3	469.8	465.7	459.9	454.7	450.6
170°	469.0	469.0	469.9	468.1	467.3	465.5	462.0	459.3	454.9	450.4	447.7
172.5°	459.1	459.9	461.5	459.7	459.5	458.4	455.6	453.6	449.9	446.8	445.6
175°	447.7	448.6	449.5	448.6	448.6	448.6	446.8	445.9	444.2	442.4	442.4
177.5°	441.1	441.1	442.6	441.8	442.6	442.6	441.8	441.1	440.4	439.7	440.4
180°	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7



TEST NUMBER: P331894-940

CATALOG NUMBER: S123DIP-S340D1025U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7
2.5°	442.0	440.8	439.4	437.1	435.1	432.3	431.4	430.4	427.4	424.8	422.8
5°	469.0	464.0	456.8	450.1	444.8	437.5	433.4	429.0	422.8	417.1	412.6
7.5°	497.3	487.5	476.2	464.0	452.6	441.7	432.8	424.9	416.2	408.0	401.4
10°	519.8	505.6	489.8	472.8	458.3	444.2	432.3	422.0	410.7	400.9	392.8
12.5°	545.4	524.4	502.7	482.0	464.8	445.1	430.8	417.6	404.8	393.2	384.1
15°	575.6	549.0	523.3	494.8	468.7	444.2	427.1	410.5	395.7	383.7	372.0
17.5°	603.2	573.1	539.1	504.5	473.0	443.9	420.1	401.3	382.8	368.1	356.5
20°	618.8	584.6	546.2	510.2	475.3	442.9	416.7	394.3	374.3	358.7	345.7
22.5°	632.3	592.2	552.4	514.0	475.1	440.2	410.5	387.4	365.9	350.6	336.7
25°	646.3	598.2	558.4	513.4	469.9	433.7	400.6	374.3	352.8	334.8	320.6
27.5°	658.3	597.9	550.5	502.0	461.6	425.4	389.9	361.9	338.9	319.5	305.0
30°	666.2	598.7	542.4	494.5	453.7	416.3	381.8	353.6	329.5	309.8	296.0
32.5°	671.2	598.2	534.9	483.8	441.0	408.0	373.0	343.8	319.0	299.6	286.4
35°	674.1	594.5	522.0	461.8	420.7	388.4	359.2	328.9	302.9	284.8	269.8
37.5°	668.2	586.8	507.1	440.6	395.6	363.9	339.2	313.4	288.6	268.7	255.7
40°	659.2	581.8	495.4	425.6	378.3	347.8	326.8	301.4	276.9	258.0	245.9
42.5°	641.7	571.8	482.7	409.0	360.3	329.8	310.5	289.3	266.1	248.3	236.3
45°	599.1	549.7	463.4	384.1	333.9	302.3	285.3	269.8	248.9	231.7	221.2
47.5°	540.0	516.5	435.7	357.8	306.1	275.8	258.1	245.8	230.4	216.4	206.5
50°	499.0	489.2	417.0	339.8	287.8	258.0	240.9	229.8	218.7	204.8	195.7
52.5°	451.7	457.6	395.0	321.3	268.9	239.7	223.7	214.8	204.8	193.3	185.4
55°	385.0	406.7	357.1	290.0	240.9	213.1	198.0	190.1	184.2	175.8	168.9
57.5°	322.5	350.3	316.1	257.8	213.5	189.5	175.0	166.4	162.6	158.2	152.8
60°	285.4	312.8	286.9	236.2	195.1	172.2	159.3	152.0	148.3	145.2	140.6
62.5°	252.4	280.1	258.3	214.3	176.9	155.8	144.5	137.4	134.6	133.0	129.0
65°	206.9	230.8	216.2	180.1	151.1	132.3	122.2	117.2	114.5	113.9	111.4
67.5°	168.4	186.5	176.0	149.4	126.5	110.4	101.7	97.5	95.4	95.1	93.3
70°	143.1	160.2	152.0	128.0	108.3	95.6	88.1	84.4	83.1	82.9	81.9
72.5°	123.5	135.4	128.9	108.9	93.6	82.1	76.6	72.7	71.3	71.6	70.9
75°	91.4	100.3	96.6	82.7	70.4	63.0	58.4	55.9	54.7	55.3	54.4
77.5°	65.8	71.4	68.0	58.4	50.8	45.5	42.1	40.6	39.4	39.4	39.1
80°	49.7	53.0	51.1	45.3	39.1	34.5	31.7	30.8	30.1	29.9	29.7
82.5°	35.4	38.2	35.9	32.0	27.7	25.0	23.5	22.1	21.7	21.8	21.6
85°	17.8	18.9	18.1	15.6	13.9	12.7	11.9	11.2	10.8	11.0	10.6
87.5°	9.5	9.2	8.1	7.1	6.4	5.4	5.0	4.4	4.4	4.7	5.1
90°	16.9	14.3	11.6	9.8	8.0	5.4	3.6	1.8	3.6	5.4	8.0
92.5°	113.1	74.7	51.5	38.3	30.8	23.9	16.4	11.1	16.4	23.9	30.8
95°	324.0	191.4	115.7	81.0	57.9	42.7	32.9	30.2	32.9	42.7	57.9
97.5°	355.5	206.0	133.7	96.1	73.3	60.2	52.5	51.6	52.5	60.2	73.3
100°	335.6	203.8	141.5	106.8	85.4	73.0	66.8	65.9	66.8	73.0	85.4
102.5°	318.4	206.7	150.8	119.0	99.7	87.9	82.4	80.8	82.4	87.9	99.7
105°	306.2	214.5	166.5	138.8	122.0	111.3	105.9	103.3	105.9	111.3	122.0
107.5°	305.3	229.1	186.9	161.3	145.4	134.9	129.7	127.1	129.7	134.9	145.4
110°	308.9	241.2	201.2	176.2	161.1	151.3	146.9	144.2	146.9	151.3	161.1



TEST NUMBER: P331894-940

CATALOG NUMBER: S123DIP-S340D1025U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	316.0	253.3	216.2	191.9	176.7	167.0	162.6	159.9	162.6	167.0	176.7
115°	327.5	273.2	239.4	215.4	200.3	191.4	186.0	182.4	186.0	191.4	200.3
117.5°	342.9	294.4	261.0	238.7	221.8	213.7	209.2	205.1	209.2	213.7	221.8
120°	354.3	308.0	275.9	253.7	236.7	227.8	223.4	220.7	223.4	227.8	236.7
122.5°	365.0	322.2	290.9	267.2	251.0	241.4	236.9	234.3	236.9	241.4	251.0
125°	381.8	342.7	311.6	287.5	270.5	260.8	255.5	253.7	255.5	260.8	270.5
127.5°	395.7	360.5	330.4	306.4	287.7	277.7	271.1	268.5	271.1	277.7	287.7
130°	405.0	371.1	341.8	317.7	299.1	288.4	280.4	277.7	280.4	288.4	299.1
132.5°	413.6	380.4	351.8	328.4	309.8	296.9	288.2	284.8	288.2	296.9	309.8
135°	424.5	394.3	366.7	342.7	324.0	310.7	300.9	297.3	300.9	310.7	324.0
137.5°	432.7	403.9	377.4	355.2	336.6	322.4	312.8	309.1	312.8	322.4	336.6
140°	437.0	410.4	384.5	362.3	344.5	330.2	321.3	316.9	321.3	330.2	344.5
142.5°	441.3	415.4	390.2	369.3	351.6	338.8	329.1	325.4	329.1	338.8	351.6
145°	445.9	421.9	398.8	378.3	363.2	349.8	341.8	339.1	341.8	349.8	363.2
147.5°	448.8	427.2	406.1	388.6	374.0	362.5	354.6	353.0	354.6	362.5	374.0
150°	449.5	430.8	410.4	394.3	381.8	370.2	363.2	362.3	363.2	370.2	381.8
152.5°	450.9	432.9	415.4	400.0	389.0	378.8	371.7	371.5	371.7	378.8	389.0
155°	451.3	437.0	421.9	409.5	399.7	390.7	385.4	385.4	385.4	390.7	399.7
157.5°	452.2	439.3	427.2	417.6	409.3	401.4	397.2	396.5	397.2	401.4	409.3
160°	452.2	441.5	430.8	421.9	415.6	408.6	405.0	405.0	405.0	408.6	415.6
162.5°	451.5	442.2	432.9	425.4	419.9	414.3	411.4	411.4	411.4	414.3	419.9
165°	449.5	443.3	436.1	429.9	426.3	421.9	420.1	421.0	420.1	421.9	426.3
167.5°	448.1	443.1	437.9	434.0	431.5	428.1	427.2	428.3	427.2	428.1	431.5
170°	445.9	442.4	437.9	436.1	434.4	431.7	430.8	432.6	430.8	431.7	434.4
172.5°	445.2	442.4	438.6	437.6	436.5	434.5	434.4	435.4	434.4	434.5	436.5
175°	443.3	441.5	439.7	438.8	438.8	437.0	437.9	438.8	437.9	437.0	438.8
177.5°	441.8	440.4	439.7	439.7	439.7	439.0	439.7	440.4	439.7	439.0	439.7
180°	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7



TEST NUMBER: P331894-940

CATALOG NUMBER: S123DIP-S340D1025U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7
2.5°	421.6	420.4	418.8	416.3	414.3	411.2	411.2	411.6	411.6	411.5	411.2
5°	408.8	405.7	402.0	397.6	393.1	388.4	387.6	385.9	384.8	383.9	382.9
7.5°	395.3	389.8	384.3	378.3	372.6	368.1	364.9	362.2	360.5	358.6	357.3
10°	386.2	379.3	372.9	366.5	359.4	353.7	350.3	347.8	345.9	344.2	343.4
12.5°	375.4	367.6	360.4	354.3	346.6	340.8	337.4	336.3	334.1	330.6	328.8
15°	359.6	352.3	343.8	334.5	330.7	323.7	319.7	317.8	316.6	313.9	313.1
17.5°	346.1	336.6	327.0	320.0	313.1	307.4	305.1	302.8	301.2	299.0	298.3
20°	335.3	326.8	318.1	310.6	303.3	297.0	295.2	293.6	291.9	290.9	290.0
22.5°	324.3	315.8	308.5	301.6	293.8	289.7	287.8	285.9	284.7	284.0	283.2
25°	308.9	301.4	293.3	287.1	280.9	278.1	276.9	275.9	275.0	274.0	273.8
27.5°	295.2	287.0	280.4	274.6	270.1	267.9	266.6	266.2	266.4	266.7	267.0
30°	284.8	277.3	272.0	267.0	262.8	260.7	260.5	260.5	261.4	261.5	262.0
32.5°	275.4	269.2	263.8	259.0	255.8	254.4	255.2	255.2	255.8	256.4	257.2
35°	261.5	256.1	252.0	247.8	245.1	245.8	246.2	246.6	247.6	248.9	249.7
37.5°	248.3	243.7	239.3	236.1	234.9	235.9	237.0	237.8	239.1	240.0	240.9
40°	238.9	235.3	231.2	228.3	228.7	229.3	230.2	231.2	232.3	232.9	233.7
42.5°	230.1	226.4	223.2	220.8	221.4	222.2	222.7	223.2	224.4	225.6	226.0
45°	216.7	213.7	210.9	209.4	209.8	210.3	210.6	211.2	212.3	213.1	213.4
47.5°	201.6	199.6	197.6	196.2	196.9	196.7	197.2	198.6	198.9	199.4	200.5
50°	192.0	190.1	187.8	187.3	187.3	187.3	187.6	189.2	189.2	190.1	190.9
52.5°	181.3	180.1	178.7	177.9	177.5	177.5	178.4	179.2	179.6	180.7	181.6
55°	165.6	164.3	163.1	162.5	162.0	162.5	164.1	164.5	165.6	166.2	166.8
57.5°	149.2	148.2	147.2	146.9	146.8	147.3	148.2	149.5	149.7	151.7	152.6
60°	138.4	136.9	136.1	136.1	135.6	137.5	137.1	139.2	139.6	140.9	142.3
62.5°	127.2	125.3	124.9	124.9	125.6	126.1	126.6	127.5	128.7	130.2	131.3
65°	109.2	108.3	109.7	109.5	109.1	110.3	110.3	111.4	112.6	114.0	116.4
67.5°	92.3	91.8	91.8	91.8	92.5	93.2	93.8	94.7	96.2	97.7	99.2
70°	80.8	81.4	80.4	81.2	81.9	82.0	82.5	83.7	85.3	86.4	88.1
72.5°	69.6	69.6	69.7	70.1	70.7	71.1	71.5	72.9	74.7	75.6	77.0
75°	53.6	53.4	54.0	54.0	55.0	55.5	55.9	56.5	58.1	59.4	60.5
77.5°	39.1	39.4	39.2	39.9	39.7	39.8	41.0	41.6	41.8	44.3	44.9
80°	29.5	29.9	30.1	30.3	30.5	30.1	31.6	32.2	32.2	33.6	34.7
82.5°	21.2	21.4	21.9	22.2	22.2	22.6	22.7	23.2	23.7	24.3	25.7
85°	10.6	11.2	11.4	11.2	11.4	11.0	11.6	11.9	12.0	12.0	12.0
87.5°	5.3	5.8	6.2	6.9	7.2	7.9	7.8	7.6	7.8	8.5	8.1
90°	9.8	11.6	14.3	16.9	19.6	22.3	21.4	22.3	23.2	24.1	25.8
92.5°	38.3	51.5	74.7	113.1	150.6	136.9	103.3	74.9	59.5	52.5	47.9
95°	81.0	115.7	191.4	324.0	469.9	527.8	428.1	320.4	217.2	170.0	137.9
97.5°	96.1	133.7	206.0	355.5	598.9	818.0	875.1	798.8	639.8	525.0	418.5
100°	106.8	141.5	203.8	335.6	569.6	842.9	1018.2	1049.5	977.3	873.2	746.8
102.5°	119.0	150.8	206.7	318.4	526.9	796.7	1025.4	1132.7	1130.4	1069.7	989.6
105°	138.8	166.5	214.5	306.2	474.4	715.6	971.1	1157.1	1246.2	1263.0	1239.9
107.5°	161.3	186.9	229.1	305.3	441.0	644.1	876.0	1087.0	1231.5	1309.5	1341.2
110°	176.2	201.2	241.2	308.9	428.1	603.5	816.2	1020.0	1183.8	1295.9	1358.3



TEST NUMBER: P331894-940

CATALOG NUMBER: S123DIP-S340D1025U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	191.9	216.2	253.3	316.0	421.0	576.4	764.2	953.8	1121.1	1246.8	1327.0
115°	215.4	239.4	273.2	327.5	418.3	547.4	701.4	866.0	1020.9	1151.7	1248.8
117.5°	238.7	261.0	294.4	342.9	419.9	530.3	663.4	802.5	936.2	1053.6	1152.1
120°	253.7	275.9	308.0	354.3	422.8	522.5	643.5	769.0	889.2	996.0	1085.9
122.5°	267.2	290.9	322.2	365.0	427.8	517.5	627.1	742.7	851.5	950.5	1033.9
125°	287.5	311.6	342.7	381.8	435.2	511.0	606.2	707.7	804.7	890.1	961.3
127.5°	306.4	330.4	360.5	395.7	443.8	507.7	587.6	677.0	763.5	840.6	905.4
130°	317.7	341.8	371.1	405.0	449.5	505.6	577.7	657.8	737.9	809.9	870.5
132.5°	328.4	351.8	380.4	413.6	453.8	504.9	568.4	640.0	713.6	780.8	838.5
135°	342.7	366.7	394.3	424.5	460.2	503.8	556.3	615.9	679.1	737.0	787.7
137.5°	355.2	377.4	403.9	432.7	464.4	501.9	545.8	594.1	645.9	695.7	739.7
140°	362.3	384.5	410.4	437.0	467.3	501.1	539.4	581.2	626.6	669.3	707.7
142.5°	369.3	390.2	415.4	441.3	469.4	499.7	533.7	569.1	608.1	645.2	678.4
145°	378.3	398.8	421.9	445.9	470.8	497.6	526.0	554.6	583.9	612.3	638.2
147.5°	388.6	406.1	427.2	448.8	470.8	494.2	518.5	542.6	565.9	588.9	607.3
150°	394.3	410.4	430.8	449.5	470.8	491.3	513.5	534.0	554.6	573.2	590.1
152.5°	400.0	415.4	432.9	450.9	468.7	487.8	507.9	526.2	543.9	560.4	574.4
155°	409.5	421.9	437.0	451.3	466.4	481.5	499.4	514.4	528.7	542.1	552.8
157.5°	417.6	427.2	439.3	452.2	463.4	476.0	489.7	502.0	513.9	524.2	532.6
160°	421.9	430.8	441.5	452.2	462.0	471.7	483.3	494.9	504.7	513.5	519.8
162.5°	425.4	432.9	442.2	451.5	459.1	467.4	476.9	486.3	494.7	502.9	508.5
165°	429.9	436.1	443.3	449.5	454.9	461.1	468.1	475.3	480.6	486.9	491.3
167.5°	434.0	437.9	443.1	448.1	450.6	454.7	459.9	465.7	469.8	473.3	476.5
170°	436.1	437.9	442.4	445.9	447.7	450.4	454.9	459.3	462.0	465.5	467.3
172.5°	437.6	438.6	442.4	445.2	445.6	446.8	449.9	453.6	455.6	458.4	459.5
175°	438.8	439.7	441.5	443.3	442.4	442.4	444.2	445.9	446.8	448.6	448.6
177.5°	439.7	439.7	440.4	441.8	440.4	439.7	440.4	441.1	441.8	442.6	442.6
180°	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7



TEST NUMBER: P331894-940

CATALOG NUMBER: S123DIP-S340D1025U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7
2.5°	410.0	409.8	411.0	410.2	411.0	409.8	410.0	411.2	411.5	411.6	411.6
5°	381.7	382.3	380.1	380.1	380.1	382.3	381.7	382.9	383.9	384.8	385.9
7.5°	356.3	355.4	355.5	354.4	355.5	355.4	356.3	357.3	358.6	360.5	362.2
10°	340.9	339.7	339.2	339.5	339.2	339.7	340.9	343.4	344.2	345.9	347.8
12.5°	328.1	327.9	325.1	325.1	325.1	327.9	328.1	328.8	330.6	334.1	336.3
15°	313.1	309.2	308.7	310.0	308.7	309.2	313.1	313.1	313.9	316.6	317.8
17.5°	298.0	295.9	296.0	295.4	296.0	295.9	298.0	298.3	299.0	301.2	302.8
20°	290.0	288.7	288.6	287.1	288.6	288.7	290.0	290.0	290.9	291.9	293.6
22.5°	282.7	282.3	282.4	280.8	282.4	282.3	282.7	283.2	284.0	284.7	285.9
25°	273.6	274.6	273.8	273.8	273.8	274.6	273.6	273.8	274.0	275.0	275.9
27.5°	267.4	267.4	267.0	267.0	267.0	267.4	267.4	267.0	266.7	266.4	266.2
30°	262.8	262.6	263.0	263.0	263.0	262.6	262.8	262.0	261.5	261.4	260.5
32.5°	258.2	258.4	258.5	258.7	258.5	258.4	258.2	257.2	256.4	255.8	255.2
35°	250.9	251.2	251.8	251.4	251.8	251.2	250.9	249.7	248.9	247.6	246.6
37.5°	241.2	242.2	242.0	242.3	242.0	242.2	241.2	240.9	240.0	239.1	237.8
40°	233.9	234.5	234.3	234.3	234.3	234.5	233.9	233.7	232.9	232.3	231.2
42.5°	226.4	226.9	226.3	226.0	226.3	226.9	226.4	226.0	225.6	224.4	223.2
45°	214.2	213.7	214.4	213.6	214.4	213.7	214.2	213.4	213.1	212.3	211.2
47.5°	200.5	200.9	201.1	201.7	201.1	200.9	200.5	200.5	199.4	198.9	198.6
50°	191.4	192.6	192.6	192.3	192.6	192.6	191.4	190.9	190.1	189.2	189.2
52.5°	182.4	182.9	183.8	183.7	183.8	182.9	182.4	181.6	180.7	179.6	179.2
55°	168.4	168.9	169.3	169.5	169.3	168.9	168.4	166.8	166.2	165.6	164.5
57.5°	154.1	153.9	154.9	155.2	154.9	153.9	154.1	152.6	151.7	149.7	149.5
60°	143.9	143.9	145.6	146.2	145.6	143.9	143.9	142.3	140.9	139.6	139.2
62.5°	133.1	133.8	135.5	134.6	135.5	133.8	133.1	131.3	130.2	128.7	127.5
65°	117.3	119.0	118.9	119.7	118.9	119.0	117.3	116.4	114.0	112.6	111.4
67.5°	100.9	101.9	103.4	103.5	103.4	101.9	100.9	99.2	97.7	96.2	94.7
70°	89.7	90.8	91.6	92.2	91.6	90.8	89.7	88.1	86.4	85.3	83.7
72.5°	78.9	79.5	81.5	80.6	81.5	79.5	78.9	77.0	75.6	74.7	72.9
75°	61.9	63.4	64.6	64.0	64.6	63.4	61.9	60.5	59.4	58.1	56.5
77.5°	45.7	47.3	47.8	47.3	47.8	47.3	45.7	44.9	44.3	41.8	41.6
80°	36.1	35.9	37.2	37.0	37.2	35.9	36.1	34.7	33.6	32.2	32.2
82.5°	26.5	26.3	26.8	27.0	26.8	26.3	26.5	25.7	24.3	23.7	23.2
85°	12.8	13.5	12.7	12.5	12.7	13.5	12.8	12.0	12.0	12.0	11.9
87.5°	7.9	8.1	8.2	7.8	8.2	8.1	7.9	8.1	8.5	7.8	7.6
90°	24.9	25.8	26.7	25.8	26.7	25.8	24.9	25.8	24.1	23.2	22.3
92.5°	46.3	43.6	44.5	42.9	44.5	43.6	46.3	47.9	52.5	59.5	74.9
95°	121.1	113.1	106.8	103.3	106.8	113.1	121.1	137.9	170.0	217.2	320.4
97.5°	352.8	312.8	288.7	281.1	288.7	312.8	352.8	418.5	525.0	639.8	798.8
100°	656.9	591.9	557.2	558.1	557.2	591.9	656.9	746.8	873.2	977.3	1049.5
102.5°	919.6	868.2	839.2	818.7	839.2	868.2	919.6	989.6	1069.7	1130.4	1132.7
105°	1198.9	1165.1	1136.7	1132.2	1136.7	1165.1	1198.9	1239.9	1263.0	1246.2	1157.1
107.5°	1341.9	1330.5	1320.9	1312.7	1320.9	1330.5	1341.9	1341.2	1309.5	1231.5	1087.0
110°	1383.2	1390.4	1388.6	1386.8	1388.6	1390.4	1383.2	1358.3	1295.9	1183.8	1020.0



TEST NUMBER: P331894-940

CATALOG NUMBER: S123DIP-S340D1025U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1372.5	1394.5	1401.3	1401.7	1401.3	1394.5	1372.5	1327.0	1246.8	1121.1	953.8
115°	1315.5	1354.7	1372.5	1377.0	1372.5	1354.7	1315.5	1248.8	1151.7	1020.9	866.0
117.5°	1221.7	1266.6	1292.3	1298.2	1292.3	1266.6	1221.7	1152.1	1053.6	936.2	802.5
120°	1156.2	1206.0	1227.4	1232.8	1227.4	1206.0	1156.2	1085.9	996.0	889.2	769.0
122.5°	1096.4	1141.3	1164.8	1171.5	1164.8	1141.3	1096.4	1033.9	950.5	851.5	742.7
125°	1018.2	1057.4	1079.7	1085.9	1079.7	1057.4	1018.2	961.3	890.1	804.7	707.7
127.5°	956.1	989.6	1009.7	1015.4	1009.7	989.6	956.1	905.4	840.6	763.5	677.0
130°	917.7	949.8	968.4	975.5	968.4	949.8	917.7	870.5	809.9	737.9	657.8
132.5°	882.8	914.8	931.4	936.4	931.4	914.8	882.8	838.5	780.8	713.6	640.0
135°	831.3	858.0	874.1	880.3	874.1	858.0	831.3	787.7	737.0	679.1	615.9
137.5°	776.3	803.4	816.9	821.0	816.9	803.4	776.3	739.7	695.7	645.9	594.1
140°	741.5	766.3	780.6	779.7	780.6	766.3	741.5	707.7	669.3	626.6	581.2
142.5°	707.3	729.3	742.2	741.3	742.2	729.3	707.3	678.4	645.2	608.1	569.1
145°	660.4	679.1	686.3	688.0	686.3	679.1	660.4	638.2	612.3	583.9	554.6
147.5°	624.1	636.8	643.5	644.3	643.5	636.8	624.1	607.3	588.9	565.9	542.6
150°	603.5	613.2	618.6	618.6	618.6	613.2	603.5	590.1	573.2	554.6	534.0
152.5°	585.0	594.1	597.3	597.3	597.3	594.1	585.0	574.4	560.4	543.9	526.2
155°	560.8	567.8	569.6	570.5	569.6	567.8	560.8	552.8	542.1	528.7	514.4
157.5°	539.6	544.9	546.4	546.2	546.4	544.9	539.6	532.6	524.2	513.9	502.0
160°	526.0	531.4	531.4	530.5	531.4	531.4	526.0	519.8	513.5	504.7	494.9
162.5°	512.6	517.1	517.1	516.2	517.1	517.1	512.6	508.5	502.9	494.7	486.3
165°	494.9	498.5	497.6	497.6	497.6	498.5	494.9	491.3	486.9	480.6	475.3
167.5°	478.1	480.6	479.7	479.7	479.7	480.6	478.1	476.5	473.3	469.8	465.7
170°	468.1	469.9	469.0	469.0	469.0	469.9	468.1	467.3	465.5	462.0	459.3
172.5°	459.7	461.5	459.9	459.1	459.9	461.5	459.7	459.5	458.4	455.6	453.6
175°	448.6	449.5	448.6	447.7	448.6	449.5	448.6	448.6	448.6	446.8	445.9
177.5°	441.8	442.6	441.1	441.1	441.1	442.6	441.8	442.6	442.6	441.8	441.1
180°	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7



TEST NUMBER: P331894-940

CATALOG NUMBER: S123DIP-S340D1025U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7
2.5°	411.2	411.2	414.3	416.3	418.8	420.4	421.6	422.8	424.8	427.4	430.4
5°	387.6	388.4	393.1	397.6	402.0	405.7	408.8	412.6	417.1	422.8	429.0
7.5°	364.9	368.1	372.6	378.3	384.3	389.8	395.3	401.4	408.0	416.2	424.9
10°	350.3	353.7	359.4	366.5	372.9	379.3	386.2	392.8	400.9	410.7	422.0
12.5°	337.4	340.8	346.6	354.3	360.4	367.6	375.4	384.1	393.2	404.8	417.6
15°	319.7	323.7	330.7	334.5	343.8	352.3	359.6	372.0	383.7	395.7	410.5
17.5°	305.1	307.4	313.1	320.0	327.0	336.6	346.1	356.5	368.1	382.8	401.3
20°	295.2	297.0	303.3	310.6	318.1	326.8	335.3	345.7	358.7	374.3	394.3
22.5°	287.8	289.7	293.8	301.6	308.5	315.8	324.3	336.7	350.6	365.9	387.4
25°	276.9	278.1	280.9	287.1	293.3	301.4	308.9	320.6	334.8	352.8	374.3
27.5°	266.6	267.9	270.1	274.6	280.4	287.0	295.2	305.0	319.5	338.9	361.9
30°	260.5	260.7	262.8	267.0	272.0	277.3	284.8	296.0	309.8	329.5	353.6
32.5°	255.2	254.4	255.8	259.0	263.8	269.2	275.4	286.4	299.6	319.0	343.8
35°	246.2	245.8	245.1	247.8	252.0	256.1	261.5	269.8	284.8	302.9	328.9
37.5°	237.0	235.9	234.9	236.1	239.3	243.7	248.3	255.7	268.7	288.6	313.4
40°	230.2	229.3	228.7	228.3	231.2	235.3	238.9	245.9	258.0	276.9	301.4
42.5°	222.7	222.2	221.4	220.8	223.2	226.4	230.1	236.3	248.3	266.1	289.3
45°	210.6	210.3	209.8	209.4	210.9	213.7	216.7	221.2	231.7	248.9	269.8
47.5°	197.2	196.7	196.9	196.2	197.6	199.6	201.6	206.5	216.4	230.4	245.8
50°	187.6	187.3	187.3	187.3	187.8	190.1	192.0	195.7	204.8	218.7	229.8
52.5°	178.4	177.5	177.5	177.9	178.7	180.1	181.3	185.4	193.3	204.8	214.8
55°	164.1	162.5	162.0	162.5	163.1	164.3	165.6	168.9	175.8	184.2	190.1
57.5°	148.2	147.3	146.8	146.9	147.2	148.2	149.2	152.8	158.2	162.6	166.4
60°	137.1	137.5	135.6	136.1	136.1	136.9	138.4	140.6	145.2	148.3	152.0
62.5°	126.6	126.1	125.6	124.9	124.9	125.3	127.2	129.0	133.0	134.6	137.4
65°	110.3	110.3	109.1	109.5	109.7	108.3	109.2	111.4	113.9	114.5	117.2
67.5°	93.8	93.2	92.5	91.8	91.8	91.8	92.3	93.3	95.1	95.4	97.5
70°	82.5	82.0	81.9	81.2	80.4	81.4	80.8	81.9	82.9	83.1	84.4
72.5°	71.5	71.1	70.7	70.1	69.7	69.6	69.6	70.9	71.6	71.3	72.7
75°	55.9	55.5	55.0	54.0	54.0	53.4	53.6	54.4	55.3	54.7	55.9
77.5°	41.0	39.8	39.7	39.9	39.2	39.4	39.1	39.1	39.4	39.4	40.6
80°	31.6	30.1	30.5	30.3	30.1	29.9	29.5	29.7	29.9	30.1	30.8
82.5°	22.7	22.6	22.2	22.2	21.9	21.4	21.2	21.6	21.8	21.7	22.1
85°	11.6	11.0	11.4	11.2	11.4	11.2	10.6	10.6	11.0	10.8	11.2
87.5°	7.8	7.9	7.2	6.9	6.2	5.8	5.3	5.1	4.7	4.4	4.4
90°	21.4	22.3	19.6	16.9	14.3	11.6	9.8	8.0	5.4	3.6	1.8
92.5°	103.3	136.9	150.6	113.1	74.7	51.5	38.3	30.8	23.9	16.4	11.1
95°	428.1	527.8	469.9	324.0	191.4	115.7	81.0	57.9	42.7	32.9	30.2
97.5°	875.1	818.0	598.9	355.5	206.0	133.7	96.1	73.3	60.2	52.5	51.6
100°	1018.2	842.9	569.6	335.6	203.8	141.5	106.8	85.4	73.0	66.8	65.9
102.5°	1025.4	796.7	526.9	318.4	206.7	150.8	119.0	99.7	87.9	82.4	80.8
105°	971.1	715.6	474.4	306.2	214.5	166.5	138.8	122.0	111.3	105.9	103.3
107.5°	876.0	644.1	441.0	305.3	229.1	186.9	161.3	145.4	134.9	129.7	127.1
110°	816.2	603.5	428.1	308.9	241.2	201.2	176.2	161.1	151.3	146.9	144.2



TEST NUMBER: P331894-940

CATALOG NUMBER: S123DIP-S340D1025U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	764.2	576.4	421.0	316.0	253.3	216.2	191.9	176.7	167.0	162.6	159.9
115°	701.4	547.4	418.3	327.5	273.2	239.4	215.4	200.3	191.4	186.0	182.4
117.5°	663.4	530.3	419.9	342.9	294.4	261.0	238.7	221.8	213.7	209.2	205.1
120°	643.5	522.5	422.8	354.3	308.0	275.9	253.7	236.7	227.8	223.4	220.7
122.5°	627.1	517.5	427.8	365.0	322.2	290.9	267.2	251.0	241.4	236.9	234.3
125°	606.2	511.0	435.2	381.8	342.7	311.6	287.5	270.5	260.8	255.5	253.7
127.5°	587.6	507.7	443.8	395.7	360.5	330.4	306.4	287.7	277.7	271.1	268.5
130°	577.7	505.6	449.5	405.0	371.1	341.8	317.7	299.1	288.4	280.4	277.7
132.5°	568.4	504.9	453.8	413.6	380.4	351.8	328.4	309.8	296.9	288.2	284.8
135°	556.3	503.8	460.2	424.5	394.3	366.7	342.7	324.0	310.7	300.9	297.3
137.5°	545.8	501.9	464.4	432.7	403.9	377.4	355.2	336.6	322.4	312.8	309.1
140°	539.4	501.1	467.3	437.0	410.4	384.5	362.3	344.5	330.2	321.3	316.9
142.5°	533.7	499.7	469.4	441.3	415.4	390.2	369.3	351.6	338.8	329.1	325.4
145°	526.0	497.6	470.8	445.9	421.9	398.8	378.3	363.2	349.8	341.8	339.1
147.5°	518.5	494.2	470.8	448.8	427.2	406.1	388.6	374.0	362.5	354.6	353.0
150°	513.5	491.3	470.8	449.5	430.8	410.4	394.3	381.8	370.2	363.2	362.3
152.5°	507.9	487.8	468.7	450.9	432.9	415.4	400.0	389.0	378.8	371.7	371.5
155°	499.4	481.5	466.4	451.3	437.0	421.9	409.5	399.7	390.7	385.4	385.4
157.5°	489.7	476.0	463.4	452.2	439.3	427.2	417.6	409.3	401.4	397.2	396.5
160°	483.3	471.7	462.0	452.2	441.5	430.8	421.9	415.6	408.6	405.0	405.0
162.5°	476.9	467.4	459.1	451.5	442.2	432.9	425.4	419.9	414.3	411.4	411.4
165°	468.1	461.1	454.9	449.5	443.3	436.1	429.9	426.3	421.9	420.1	421.0
167.5°	459.9	454.7	450.6	448.1	443.1	437.9	434.0	431.5	428.1	427.2	428.3
170°	454.9	450.4	447.7	445.9	442.4	437.9	436.1	434.4	431.7	430.8	432.6
172.5°	449.9	446.8	445.6	445.2	442.4	438.6	437.6	436.5	434.5	434.4	435.4
175°	444.2	442.4	442.4	443.3	441.5	439.7	438.8	438.8	437.0	437.9	438.8
177.5°	440.4	439.7	440.4	441.8	440.4	439.7	439.7	439.7	439.0	439.7	440.4
180°	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7



TEST NUMBER: P331894-940

CATALOG NUMBER: S123DIP-S340D1025U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7
2.5°	431.4	432.3	435.1	437.1	439.4	440.8	442.0	443.1	444.4	444.7	449.5
5°	433.4	437.5	444.8	450.1	456.8	464.0	469.0	471.4	477.4	482.3	492.3
7.5°	432.8	441.7	452.6	464.0	476.2	487.5	497.3	509.0	517.2	529.7	541.9
10°	432.3	444.2	458.3	472.8	489.8	505.6	519.8	535.6	548.7	565.9	580.6
12.5°	430.8	445.1	464.8	482.0	502.7	524.4	545.4	565.6	577.2	605.9	619.5
15°	427.1	444.2	468.7	494.8	523.3	549.0	575.6	596.8	631.1	656.2	672.3
17.5°	420.1	443.9	473.0	504.5	539.1	573.1	603.2	635.3	671.7	702.1	734.6
20°	416.7	442.9	475.3	510.2	546.2	584.6	618.8	657.5	697.1	727.1	768.7
22.5°	410.5	440.2	475.1	514.0	552.4	592.2	632.3	671.3	717.1	758.3	797.9
25°	400.6	433.7	469.9	513.4	558.4	598.2	646.3	698.0	745.7	798.8	838.2
27.5°	389.9	425.4	461.6	502.0	550.5	597.9	658.3	716.7	775.1	820.8	850.1
30°	381.8	416.3	453.7	494.5	542.4	598.7	666.2	730.0	786.9	826.2	842.6
32.5°	373.0	408.0	441.0	483.8	534.9	598.2	671.2	737.8	787.6	813.7	810.5
35°	359.2	388.4	420.7	461.8	522.0	594.5	674.1	738.5	769.0	763.4	721.0
37.5°	339.2	363.9	395.6	440.6	507.1	586.8	668.2	716.6	714.6	669.0	607.5
40°	326.8	347.8	378.3	425.6	495.4	581.8	659.2	690.5	664.0	600.1	526.6
42.5°	310.5	329.8	360.3	409.0	482.7	571.8	641.7	650.8	598.8	525.4	458.0
45°	285.3	302.3	333.9	384.1	463.4	549.7	599.1	576.8	506.8	431.1	379.8
47.5°	258.1	275.8	306.1	357.8	435.7	516.5	540.0	492.8	420.9	359.4	312.3
50°	240.9	258.0	287.8	339.8	417.0	489.2	499.0	437.9	371.8	317.8	279.2
52.5°	223.7	239.7	268.9	321.3	395.0	457.6	451.7	389.4	328.7	282.6	252.3
55°	198.0	213.1	240.9	290.0	357.1	406.7	385.0	325.6	275.3	239.5	216.4
57.5°	175.0	189.5	213.5	257.8	316.1	350.3	322.5	272.4	232.5	204.9	187.8
60°	159.3	172.2	195.1	236.2	286.9	312.8	285.4	241.2	207.5	185.5	170.1
62.5°	144.5	155.8	176.9	214.3	258.3	280.1	252.4	214.9	186.3	166.7	153.6
65°	122.2	132.3	151.1	180.1	216.2	230.8	206.9	176.6	154.4	139.8	131.1
67.5°	101.7	110.4	126.5	149.4	176.0	186.5	168.4	144.9	128.1	116.5	109.6
70°	88.1	95.6	108.3	128.0	152.0	160.2	143.1	123.8	111.6	102.2	95.8
72.5°	76.6	82.1	93.6	108.9	128.9	135.4	123.5	106.6	95.1	88.1	82.9
75°	58.4	63.0	70.4	82.7	96.6	100.3	91.4	80.8	73.1	68.1	64.2
77.5°	42.1	45.5	50.8	58.4	68.0	71.4	65.8	58.7	53.1	49.8	47.5
80°	31.7	34.5	39.1	45.3	51.1	53.0	49.7	44.2	40.3	38.4	36.6
82.5°	23.5	25.0	27.7	32.0	35.9	38.2	35.4	32.1	30.0	28.3	27.6
85°	11.9	12.7	13.9	15.6	18.1	18.9	17.8	17.0	15.8	14.7	14.7
87.5°	5.0	5.4	6.4	7.1	8.1	9.2	9.5	9.7	10.1	9.7	9.8
90°	3.6	5.4	8.0	9.8	11.6	14.3	16.9	19.6	22.3	21.4	22.3
92.5°	16.4	23.9	30.8	38.3	51.5	74.7	113.1	150.6	136.9	103.3	74.9
95°	32.9	42.7	57.9	81.0	115.7	191.4	324.0	469.9	527.8	428.1	320.4
97.5°	52.5	60.2	73.3	96.1	133.7	206.0	355.5	598.9	818.0	875.1	798.8
100°	66.8	73.0	85.4	106.8	141.5	203.8	335.6	569.6	842.9	1018.2	1049.5
102.5°	82.4	87.9	99.7	119.0	150.8	206.7	318.4	526.9	796.7	1025.4	1132.7
105°	105.9	111.3	122.0	138.8	166.5	214.5	306.2	474.4	715.6	971.1	1157.1
107.5°	129.7	134.9	145.4	161.3	186.9	229.1	305.3	441.0	644.1	876.0	1087.0
110°	146.9	151.3	161.1	176.2	201.2	241.2	308.9	428.1	603.5	816.2	1020.0



TEST NUMBER: P331894-940

CATALOG NUMBER: S123DIP-S340D1025U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	162.6	167.0	176.7	191.9	216.2	253.3	316.0	421.0	576.4	764.2	953.8
115°	186.0	191.4	200.3	215.4	239.4	273.2	327.5	418.3	547.4	701.4	866.0
117.5°	209.2	213.7	221.8	238.7	261.0	294.4	342.9	419.9	530.3	663.4	802.5
120°	223.4	227.8	236.7	253.7	275.9	308.0	354.3	422.8	522.5	643.5	769.0
122.5°	236.9	241.4	251.0	267.2	290.9	322.2	365.0	427.8	517.5	627.1	742.7
125°	255.5	260.8	270.5	287.5	311.6	342.7	381.8	435.2	511.0	606.2	707.7
127.5°	271.1	277.7	287.7	306.4	330.4	360.5	395.7	443.8	507.7	587.6	677.0
130°	280.4	288.4	299.1	317.7	341.8	371.1	405.0	449.5	505.6	577.7	657.8
132.5°	288.2	296.9	309.8	328.4	351.8	380.4	413.6	453.8	504.9	568.4	640.0
135°	300.9	310.7	324.0	342.7	366.7	394.3	424.5	460.2	503.8	556.3	615.9
137.5°	312.8	322.4	336.6	355.2	377.4	403.9	432.7	464.4	501.9	545.8	594.1
140°	321.3	330.2	344.5	362.3	384.5	410.4	437.0	467.3	501.1	539.4	581.2
142.5°	329.1	338.8	351.6	369.3	390.2	415.4	441.3	469.4	499.7	533.7	569.1
145°	341.8	349.8	363.2	378.3	398.8	421.9	445.9	470.8	497.6	526.0	554.6
147.5°	354.6	362.5	374.0	388.6	406.1	427.2	448.8	470.8	494.2	518.5	542.6
150°	363.2	370.2	381.8	394.3	410.4	430.8	449.5	470.8	491.3	513.5	534.0
152.5°	371.7	378.8	389.0	400.0	415.4	432.9	450.9	468.7	487.8	507.9	526.2
155°	385.4	390.7	399.7	409.5	421.9	437.0	451.3	466.4	481.5	499.4	514.4
157.5°	397.2	401.4	409.3	417.6	427.2	439.3	452.2	463.4	476.0	489.7	502.0
160°	405.0	408.6	415.6	421.9	430.8	441.5	452.2	462.0	471.7	483.3	494.9
162.5°	411.4	414.3	419.9	425.4	432.9	442.2	451.5	459.1	467.4	476.9	486.3
165°	420.1	421.9	426.3	429.9	436.1	443.3	449.5	454.9	461.1	468.1	475.3
167.5°	427.2	428.1	431.5	434.0	437.9	443.1	448.1	450.6	454.7	459.9	465.7
170°	430.8	431.7	434.4	436.1	437.9	442.4	445.9	447.7	450.4	454.9	459.3
172.5°	434.4	434.5	436.5	437.6	438.6	442.4	445.2	445.6	446.8	449.9	453.6
175°	437.9	437.0	438.8	438.8	439.7	441.5	443.3	442.4	442.4	444.2	445.9
177.5°	439.7	439.0	439.7	439.7	439.7	440.4	441.8	440.4	439.7	440.4	441.1
180°	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7



TEST NUMBER: P331894-940

CATALOG NUMBER: S123DIP-S340D1025U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	428.7	428.7	428.7	428.7	428.7	428.7	428.7
2.5°	451.2	451.4	453.2	454.5	453.9	454.7	455.0
5°	492.9	500.4	504.4	507.3	507.5	507.7	509.3
7.5°	552.1	560.2	566.1	575.0	577.6	580.6	579.8
10°	595.4	607.3	617.4	622.8	628.7	637.1	630.3
12.5°	635.8	656.7	672.3	680.6	686.1	687.8	684.5
15°	702.4	729.8	744.5	744.1	762.8	770.9	758.2
17.5°	763.4	788.7	809.0	819.4	835.0	838.4	836.9
20°	800.8	828.5	844.3	862.1	870.2	877.4	878.7
22.5°	833.0	857.9	874.9	889.7	896.4	899.9	902.0
25°	866.3	885.8	896.0	901.2	903.0	902.6	899.9
27.5°	864.0	865.5	854.3	843.3	833.4	822.3	818.5
30°	841.5	824.1	792.9	775.3	749.3	728.7	737.1
32.5°	782.6	747.8	712.8	674.2	642.3	633.2	624.0
35°	667.9	606.8	571.1	529.5	512.9	496.3	484.8
37.5°	540.3	493.1	450.7	423.6	406.9	396.4	390.7
40°	467.2	424.6	389.7	367.7	355.0	343.2	341.5
42.5°	408.8	369.3	343.0	325.5	313.3	308.3	304.6
45°	334.8	307.3	289.6	277.1	269.0	265.9	261.7
47.5°	283.5	263.9	250.7	242.2	236.0	233.7	233.4
50°	254.7	238.4	228.7	222.0	217.3	216.4	213.1
52.5°	233.1	219.0	211.4	205.6	202.2	199.8	198.9
55°	202.3	193.0	186.1	182.8	180.1	177.8	177.8
57.5°	177.0	169.2	164.7	161.8	161.0	159.4	158.4
60°	161.4	154.8	151.2	148.7	147.0	147.3	145.4
62.5°	146.2	141.8	138.4	136.0	133.9	134.0	134.1
65°	124.4	121.1	118.6	117.8	116.5	115.1	115.5
67.5°	105.5	102.4	100.4	99.0	98.5	97.7	99.0
70°	91.8	89.5	88.1	86.9	86.4	86.6	87.7
72.5°	79.4	77.8	76.8	76.2	75.3	75.3	76.1
75°	62.3	61.1	60.3	59.7	59.4	59.4	59.4
77.5°	45.7	45.5	45.1	44.2	44.2	44.5	44.5
80°	36.1	35.5	35.3	34.9	34.2	33.9	34.9
82.5°	27.0	26.4	26.2	26.1	25.1	25.1	25.9
85°	14.5	13.9	14.1	13.9	13.9	13.7	13.7
87.5°	9.8	9.8	10.0	10.0	10.0	10.0	10.2
90°	23.2	24.1	25.8	24.9	25.8	26.7	25.8
92.5°	59.5	52.5	47.9	46.3	43.6	44.5	42.9
95°	217.2	170.0	137.9	121.1	113.1	106.8	103.3
97.5°	639.8	525.0	418.5	352.8	312.8	288.7	281.1
100°	977.3	873.2	746.8	656.9	591.9	557.2	558.1
102.5°	1130.4	1069.7	989.6	919.6	868.2	839.2	818.7
105°	1246.2	1263.0	1239.9	1198.9	1165.1	1136.7	1132.2
107.5°	1231.5	1309.5	1341.2	1341.9	1330.5	1320.9	1312.7
110°	1183.8	1295.9	1358.3	1383.2	1390.4	1388.6	1386.8



TEST NUMBER: P331894-940

CATALOG NUMBER: S123DIP-S340D1025U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	<i>1121.1</i>	<i>1246.8</i>	<i>1327.0</i>	<i>1372.5</i>	<i>1394.5</i>	<i>1401.3</i>	<i>1401.7</i>
115°	1020.9	1151.7	1248.8	1315.5	1354.7	1372.5	1377.0
117.5°	936.2	1053.6	1152.1	1221.7	1266.6	1292.3	1298.2
120°	889.2	996.0	1085.9	1156.2	1206.0	1227.4	1232.8
122.5°	851.5	950.5	1033.9	1096.4	1141.3	1164.8	1171.5
125°	804.7	890.1	961.3	1018.2	1057.4	1079.7	1085.9
127.5°	763.5	840.6	905.4	956.1	989.6	1009.7	1015.4
130°	737.9	809.9	870.5	917.7	949.8	968.4	975.5
132.5°	713.6	780.8	838.5	882.8	914.8	931.4	936.4
135°	679.1	737.0	787.7	831.3	858.0	874.1	880.3
137.5°	645.9	695.7	739.7	776.3	803.4	816.9	821.0
140°	626.6	669.3	707.7	741.5	766.3	780.6	779.7
142.5°	608.1	645.2	678.4	707.3	729.3	742.2	741.3
145°	583.9	612.3	638.2	660.4	679.1	686.3	688.0
147.5°	565.9	588.9	607.3	624.1	636.8	643.5	644.3
150°	554.6	573.2	590.1	603.5	613.2	618.6	618.6
152.5°	543.9	560.4	574.4	585.0	594.1	597.3	597.3
155°	528.7	542.1	552.8	560.8	567.8	569.6	570.5
157.5°	513.9	524.2	532.6	539.6	544.9	546.4	546.2
160°	504.7	513.5	519.8	526.0	531.4	531.4	530.5
162.5°	494.7	502.9	508.5	512.6	517.1	517.1	516.2
165°	480.6	486.9	491.3	494.9	498.5	497.6	497.6
167.5°	469.8	473.3	476.5	478.1	480.6	479.7	479.7
170°	462.0	465.5	467.3	468.1	469.9	469.0	469.0
172.5°	455.6	458.4	459.5	459.7	461.5	459.9	459.1
175°	446.8	448.6	448.6	448.6	449.5	448.6	447.7
177.5°	441.8	442.6	442.6	441.8	442.6	441.1	441.1
180°	439.7	439.7	439.7	439.7	439.7	439.7	439.7

(END OF REPORT)