

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332356-940

Luminaire Tested: **S123RDIP-S1000D1195U940-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332356-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1000D1195U940-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1195 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7384.0 lumens
Efficiency: N/A
Efficacy: 112.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 65.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332356-940

CATALOG NUMBER: S123RDIP-S1000D1195U940-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332356-940

CATALOG NUMBER: S123RDIP-S1000D1195U940-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54	48
1	98	94	90	87	90	86	83	81	73	71	69	60	59	57	49	48	47	41
2	90	83	77	72	82	76	71	67	64	61	58	54	51	49	44	42	40	36
3	82	73	66	60	75	68	61	57	57	53	49	48	45	42	39	37	35	31
4	75	65	57	52	69	60	54	48	51	46	42	43	39	36	35	33	31	27
5	69	58	50	45	64	54	47	42	46	41	37	39	35	32	32	29	27	24
6	64	52	44	39	59	49	42	37	42	36	32	35	31	28	29	26	24	21
7	59	47	40	34	55	44	37	32	38	33	29	32	28	25	27	24	21	19
8	55	43	36	30	51	40	33	29	35	29	26	30	25	22	25	22	19	17
9	51	39	32	27	47	37	30	26	32	27	23	27	23	20	23	20	18	15
10	48	36	29	24	44	34	28	23	29	24	21	25	21	18	21	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15259	15259	15259	15259
5°	18189	15324	13493	15324
10°	22710	15235	12191	15235
15°	26658	15081	11117	15081
20°	29751	14848	10204	14848
25°	29276	14602	9644	14602
30°	21044	14375	9066	14375
35°	14051	14082	8692	14082
40°	10352	13728	8304	13728
45°	8683	13108	7926	13108
50°	7661	12295	7398	12295
55°	6718	11365	6673	11365
60°	5983	10478	6114	10478
65°	5254	9521	5687	9521
70°	4126	8670	5196	8670
75°	3635	7573	4741	7573
80°	3161	6434	4668	6434
85°	2544	5175	4940	5175



TEST NUMBER: P332356-940

CATALOG NUMBER: S123RDIP-S1000D1195U940-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	139.4	1.9
10°-20°	435.5	5.9
20°-30°	684.2	9.3
30°-40°	713.8	9.7
40°-50°	610.9	8.3
50°-60°	465.6	6.3
60°-70°	298.4	4.0
70°-80°	143.6	1.9
80°-90°	42.0	0.6
90°-100°	284.8	3.9
100°-110°	806.5	10.9
110°-120°	793.4	10.7
120°-130°	632.8	8.6
130°-140°	498.9	6.8
140°-150°	372.4	5.0
150°-160°	259.6	3.5
160°-170°	152.5	2.1
170°-180°	49.6	0.7
0°-30°	1259.1	17.1
0°-40°	1973.0	26.7
0°-60°	3049.5	41.3
0°-90°	3533.5	47.9
90°-120°	1884.7	25.5
90°-150°	3388.9	45.9
90°-180°	3851.0	52.2
0°-180°	7384.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1418	1418	1418	1418	1418	
5°	1683	1418	1249	1418	1683	174
15°	2392	1353	998	1353	2392	678
25°	2465	1230	812	1230	2465	1059
35°	1069	1072	662	1072	1069	701
45°	570	861	521	861	570	449
55°	358	606	356	606	358	324
65°	206	374	223	374	206	203
75°	87	182	114	182	87	94
85°	21	42	40	42	21	24
90°	30	2	30	2	30	17
95°	120	35	120	35	120	217
105°	1318	120	1318	120	1318	1300
115°	1603	212	1603	212	1603	1557
125°	1264	295	1264	295	1264	1145
135°	1025	346	1025	346	1025	795
145°	801	395	801	395	801	509
155°	664	449	664	449	664	310
165°	579	490	579	490	579	166
175°	521	511	521	511	521	51
180°	512	512	512	512	512	



TEST NUMBER: P332356-940

CATALOG NUMBER: S123RDIP-S1000D1195U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1509.8	1511.7	1505.5	1504.5	1497.2	1495.2	1495.2	1485.1	1478.7	1470.5	1465.6
5°	1683.4	1693.1	1688.2	1677.3	1659.1	1654.8	1643.3	1625.1	1604.5	1579.0	1566.8
7.5°	1900.1	1913.3	1908.3	1891.4	1872.3	1856.9	1824.4	1794.2	1751.9	1714.7	1682.9
10°	2077.8	2063.9	2052.9	2036.6	2018.9	1990.4	1956.4	1909.7	1855.7	1813.2	1765.9
12.5°	2210.8	2208.5	2194.7	2177.8	2152.9	2125.8	2084.1	2027.2	1964.4	1903.1	1848.9
15°	2392.2	2395.8	2386.7	2369.1	2333.9	2286.0	2222.9	2199.2	2109.3	2042.6	1975.9
17.5°	2517.7	2516.9	2515.7	2491.4	2455.4	2421.3	2362.8	2300.5	2219.2	2125.1	2035.2
20°	2597.3	2591.2	2592.4	2565.1	2538.4	2498.9	2442.0	2351.5	2284.7	2176.1	2083.3
22.5°	2595.3	2594.1	2598.7	2589.3	2570.0	2539.8	2494.8	2418.5	2333.3	2223.7	2119.2
25°	2465.0	2460.1	2488.7	2496.5	2527.5	2532.9	2519.6	2477.7	2397.0	2284.1	2154.9
27.5°	2063.0	2060.3	2113.3	2179.5	2263.5	2328.8	2391.9	2422.4	2397.0	2316.2	2186.7
30°	1693.1	1750.2	1776.8	1872.7	1979.5	2106.9	2218.6	2324.8	2350.9	2315.7	2209.5
32.5°	1405.7	1455.5	1477.7	1560.0	1659.6	1808.8	1976.4	2126.7	2232.9	2259.9	2195.9
35°	1069.3	1069.9	1120.8	1157.3	1249.5	1403.0	1565.7	1767.1	1967.4	2119.1	2134.8
37.5°	853.2	856.2	887.1	923.4	992.6	1073.7	1216.9	1384.5	1615.8	1848.7	1985.2
40°	736.7	742.2	765.3	801.0	850.8	912.0	1023.8	1181.5	1374.5	1633.6	1845.4
42.5°	661.9	670.8	682.7	710.2	741.1	798.4	888.8	1010.7	1186.2	1431.2	1675.5
45°	570.4	575.2	584.4	597.1	625.0	665.1	725.8	807.7	953.3	1150.6	1395.1
47.5°	503.2	500.6	510.2	520.6	539.1	566.4	607.1	674.0	777.8	936.1	1143.5
50°	457.5	456.9	463.6	471.5	489.1	509.2	542.5	592.9	675.4	806.5	996.4
52.5°	414.8	417.1	421.9	431.7	444.4	460.6	490.5	526.8	597.7	710.9	869.2
55°	358.0	359.9	366.5	372.0	381.1	397.4	416.3	446.7	495.2	574.1	704.5
57.5°	310.0	309.2	315.6	316.9	327.2	340.5	355.1	378.7	413.8	472.5	560.4
60°	277.9	276.1	281.6	285.8	291.3	302.2	314.3	337.4	365.3	408.4	483.7
62.5°	248.8	248.0	252.0	256.2	260.7	270.6	280.9	298.5	320.7	357.0	416.7
65°	206.3	208.1	210.0	211.8	214.2	220.3	230.0	242.1	257.3	282.8	325.8
67.5°	162.1	164.0	164.6	168.4	173.5	177.4	183.2	194.0	204.6	226.1	250.7
70°	131.1	130.5	131.1	132.9	139.6	146.2	154.2	162.0	168.7	183.9	204.5
72.5°	112.6	111.6	113.2	113.5	116.7	118.6	123.6	131.0	139.6	149.9	164.7
75°	87.4	87.4	87.4	87.4	89.8	91.0	92.8	94.7	97.7	102.5	113.5
77.5°	64.6	64.6	65.5	66.2	66.6	67.3	68.5	70.3	71.3	73.9	78.6
80°	51.0	51.5	51.0	51.5	51.5	52.8	53.4	55.2	55.8	58.9	60.7
82.5°	38.3	38.0	38.3	39.0	39.0	40.2	40.3	41.6	41.7	43.3	45.1
85°	20.6	19.4	20.6	20.1	21.2	20.1	20.6	21.8	21.8	22.5	24.9
87.5°	10.9	12.0	10.9	11.1	11.3	11.4	11.2	11.0	11.8	11.5	11.3
90°	30.1	31.1	30.1	29.0	30.1	28.0	26.9	25.9	24.9	25.9	22.8
92.5°	49.9	51.8	50.7	53.9	55.7	61.1	69.2	87.2	120.2	159.3	175.3
95°	120.2	124.3	131.6	140.9	160.6	197.9	252.8	373.0	498.3	614.4	547.1
97.5°	327.2	336.1	364.1	410.7	487.1	611.1	744.7	929.7	1018.6	952.1	697.1
100°	649.6	648.5	688.9	764.6	869.2	1016.4	1137.6	1221.5	1185.3	981.1	663.1
102.5°	953.0	976.8	1010.6	1070.4	1151.8	1245.1	1315.7	1318.5	1193.5	927.3	613.3
105°	1317.9	1323.0	1356.2	1395.5	1443.2	1470.2	1450.5	1346.8	1130.3	832.9	552.2
107.5°	1527.9	1537.5	1548.6	1561.9	1561.1	1524.2	1433.4	1265.2	1019.7	749.7	513.3
110°	1614.2	1616.2	1618.3	1610.0	1581.0	1508.5	1378.0	1187.3	950.0	702.4	498.3



TEST NUMBER: P332356-940

CATALOG NUMBER: S123RDIP-S1000D1195U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1631.6	1631.1	1623.3	1597.6	1544.5	1451.3	1305.0	1110.2	889.6	670.9	490.1
115°	1602.8	1597.6	1576.8	1531.2	1453.6	1340.6	1188.3	1008.1	816.4	637.1	487.0
117.5°	1511.2	1504.1	1474.3	1422.1	1341.0	1226.5	1089.7	934.1	772.2	617.2	488.8
120°	1434.9	1428.7	1403.8	1345.8	1264.0	1159.3	1035.0	895.1	749.0	608.1	492.1
122.5°	1363.6	1355.8	1328.4	1276.2	1203.5	1106.3	991.0	864.4	730.0	602.4	497.9
125°	1264.0	1256.7	1230.8	1185.3	1118.9	1036.0	936.6	823.7	705.5	594.7	506.6
127.5°	1181.9	1175.3	1151.8	1112.9	1053.8	978.4	888.7	788.0	684.0	590.9	516.6
130°	1135.5	1127.2	1105.5	1068.2	1013.3	942.8	858.9	765.6	672.3	588.4	523.2
132.5°	1089.9	1084.1	1064.8	1027.5	976.0	908.8	830.7	744.9	661.6	587.6	528.2
135°	1024.7	1017.4	998.7	967.7	916.9	857.8	790.5	716.9	647.6	586.4	535.7
137.5°	955.6	950.8	935.1	903.7	860.9	809.8	751.7	691.4	635.3	584.1	540.6
140°	907.6	908.6	892.1	863.0	823.7	779.1	729.3	676.5	627.9	583.3	543.9
142.5°	862.8	863.8	848.9	823.2	789.7	750.9	707.8	662.5	621.2	581.7	546.4
145°	800.8	798.8	790.5	768.7	742.8	712.8	679.7	645.4	612.3	579.2	548.0
147.5°	749.8	749.0	741.2	726.5	706.8	685.5	658.7	631.6	603.6	575.2	548.0
150°	720.1	720.1	713.8	702.4	686.9	667.2	645.4	621.6	597.8	571.9	548.0
152.5°	695.2	695.2	691.4	680.9	668.7	652.3	633.0	612.5	591.2	567.8	545.5
155°	664.1	663.1	661.0	652.7	643.4	631.0	615.4	598.8	581.2	560.5	542.9
157.5°	635.7	635.9	634.3	628.0	619.9	610.2	598.2	584.3	570.0	554.1	539.4
160°	617.5	618.5	618.5	612.3	605.0	597.8	587.5	576.0	562.6	549.1	537.7
162.5°	600.9	601.9	601.9	596.6	591.7	585.3	575.9	566.1	555.1	544.1	534.4
165°	579.2	579.2	580.1	576.0	571.9	566.7	559.5	553.2	544.9	536.6	529.4
167.5°	558.4	558.4	559.5	556.5	554.7	551.0	546.8	542.1	535.2	529.2	524.4
170°	546.0	546.0	547.1	544.9	543.9	541.8	537.7	534.6	529.4	524.2	521.1
172.5°	534.4	535.2	537.1	535.0	534.8	533.6	530.2	528.0	523.6	520.0	518.6
175°	521.1	522.2	523.2	522.2	522.2	522.2	520.0	519.1	517.0	514.9	514.9
177.5°	513.4	513.4	515.1	514.2	515.1	515.1	514.2	513.4	512.6	511.8	512.6
180°	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8



TEST NUMBER: P332356-940

CATALOG NUMBER: S123RDIP-S1000D1195U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1463.7	1462.2	1455.5	1447.7	1437.4	1430.7	1425.3	1422.5	1413.7	1403.0	1395.7
5°	1554.1	1535.9	1516.5	1492.8	1471.0	1448.5	1434.6	1418.2	1398.1	1375.7	1359.9
7.5°	1651.0	1615.2	1576.8	1537.1	1497.9	1462.8	1431.6	1405.1	1373.1	1341.0	1318.4
10°	1725.3	1673.0	1619.1	1563.8	1513.4	1466.2	1429.7	1393.9	1355.7	1318.7	1290.8
12.5°	1792.7	1724.0	1661.8	1593.9	1529.5	1472.9	1420.5	1378.4	1332.4	1292.9	1261.1
15°	1878.1	1807.8	1732.5	1629.3	1543.8	1472.2	1408.5	1353.3	1297.4	1248.8	1217.9
17.5°	1958.0	1852.1	1751.0	1664.9	1553.7	1464.3	1386.5	1320.4	1259.2	1207.7	1169.7
20°	1991.0	1888.5	1778.6	1668.8	1559.6	1459.5	1369.0	1296.2	1232.5	1174.2	1139.1
22.5°	2010.9	1894.8	1779.1	1661.1	1545.0	1441.0	1351.6	1271.5	1202.4	1147.0	1103.6
25°	2034.1	1895.8	1768.4	1651.8	1533.5	1420.6	1314.4	1229.5	1154.9	1095.9	1049.8
27.5°	2049.4	1886.7	1736.1	1606.5	1486.5	1374.1	1276.8	1186.7	1111.0	1048.7	999.3
30°	2052.4	1879.4	1711.3	1571.1	1449.1	1345.9	1242.8	1156.6	1076.6	1010.4	964.3
32.5°	2056.2	1861.4	1677.8	1528.8	1404.0	1301.8	1208.4	1126.1	1044.0	978.8	931.7
35°	2040.2	1851.5	1626.9	1455.8	1330.8	1231.9	1147.5	1071.7	991.0	927.8	879.9
37.5°	1971.2	1812.0	1574.2	1373.5	1242.8	1151.2	1082.4	1016.4	942.3	874.2	829.0
40°	1901.8	1773.2	1533.5	1323.5	1187.0	1092.9	1031.0	977.0	905.4	841.7	793.2
42.5°	1798.4	1720.3	1494.7	1271.0	1123.8	1033.2	981.0	930.4	867.5	802.8	757.2
45°	1608.7	1619.1	1415.1	1187.6	1036.4	945.5	896.3	861.1	805.3	751.9	705.2
47.5°	1370.8	1467.3	1321.8	1098.6	944.3	858.9	815.9	785.2	747.6	695.2	652.6
50°	1215.5	1353.3	1247.1	1038.9	886.6	801.6	759.1	734.2	701.5	660.2	619.6
52.5°	1072.3	1220.2	1156.7	972.4	823.9	746.3	704.8	684.3	658.3	619.5	582.6
55°	874.4	1024.3	1009.8	872.0	730.0	660.2	628.7	605.6	588.0	558.9	529.8
57.5°	707.3	849.4	856.9	760.4	647.3	578.3	551.2	533.8	522.3	500.2	473.3
60°	602.0	732.5	758.0	685.1	588.0	527.4	500.6	486.7	477.6	459.9	439.3
62.5°	514.6	625.6	654.5	602.1	531.2	474.4	453.5	440.1	433.9	418.7	400.6
65°	393.9	486.1	514.0	484.8	447.8	402.3	385.3	373.8	368.4	359.9	346.5
67.5°	296.1	363.4	394.0	373.4	360.1	331.4	320.6	314.3	309.5	303.6	292.5
70°	237.9	287.7	319.2	313.7	302.8	287.7	279.7	275.5	270.6	265.8	256.1
72.5°	191.3	225.5	255.1	257.9	249.0	245.9	239.0	237.2	234.3	228.5	223.1
75°	126.8	150.5	171.1	179.1	182.6	185.7	182.6	182.1	181.5	176.6	173.5
77.5°	83.1	95.9	108.9	122.3	128.0	132.2	133.1	135.4	133.8	131.2	129.7
80°	63.8	66.8	75.9	87.4	96.5	100.1	102.5	103.8	103.2	102.5	100.1
82.5°	46.3	48.8	53.1	61.2	68.8	74.9	76.3	76.1	77.4	77.8	75.9
85°	24.9	25.5	26.7	27.9	32.2	38.9	40.7	41.9	43.1	43.1	39.4
87.5°	11.7	10.6	11.0	10.5	11.6	11.4	13.9	16.0	16.9	15.3	16.0
90°	19.7	16.6	13.5	11.4	9.4	6.2	4.1	2.1	4.1	6.2	9.4
92.5°	131.6	87.0	59.9	44.6	35.8	27.7	19.1	12.8	19.1	27.7	35.8
95°	377.1	222.7	134.6	94.3	67.3	49.8	38.3	35.2	38.3	49.8	67.3
97.5°	413.8	239.8	155.6	111.9	85.3	70.0	61.1	60.1	61.1	70.0	85.3
100°	390.6	237.3	164.7	124.3	99.4	85.0	77.7	76.7	77.7	85.0	99.4
102.5°	370.7	240.6	175.5	138.4	116.0	102.4	95.9	94.1	95.9	102.4	116.0
105°	356.4	249.7	193.8	161.6	142.0	129.5	123.3	120.2	123.3	129.5	142.0
107.5°	355.3	266.7	217.6	187.7	169.2	157.0	151.1	147.9	151.1	157.0	169.2
110°	359.5	280.8	234.2	205.1	187.5	176.1	170.9	167.8	170.9	176.1	187.5



TEST NUMBER: P332356-940

CATALOG NUMBER: S123RDIP-S1000D1195U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	367.8	294.9	251.6	223.4	205.7	194.4	189.2	186.1	189.2	194.4	205.7
115°	381.3	318.1	278.7	250.7	233.1	222.7	216.5	212.4	216.5	222.7	233.1
117.5°	399.0	342.7	303.8	277.9	258.2	248.6	243.4	238.7	243.4	248.6	258.2
120°	412.3	358.5	321.2	295.2	275.6	265.2	260.0	256.9	260.0	265.2	275.6
122.5°	424.8	375.1	338.6	311.0	292.1	281.0	275.8	272.7	275.8	281.0	292.1
125°	444.4	398.9	362.6	334.7	315.0	303.5	297.4	295.2	297.4	303.5	315.0
127.5°	460.7	419.5	384.6	356.6	334.8	323.2	315.6	312.5	315.6	323.2	334.8
130°	471.4	432.0	397.8	369.9	348.1	335.6	326.4	323.2	326.4	335.6	348.1
132.5°	481.3	442.8	409.5	382.3	360.5	345.6	335.5	331.5	335.5	345.6	360.5
135°	494.2	459.0	426.9	398.9	377.1	361.6	350.2	346.1	350.2	361.6	377.1
137.5°	503.7	470.1	439.3	413.4	391.8	375.2	364.1	359.7	364.1	375.2	391.8
140°	508.7	477.6	447.5	421.7	400.9	384.3	374.0	368.8	374.0	384.3	400.9
142.5°	513.6	483.4	454.2	430.0	409.2	394.3	383.2	378.8	383.2	394.3	409.2
145°	519.1	491.1	464.1	440.3	422.7	407.2	397.8	394.8	397.8	407.2	422.7
147.5°	522.4	497.3	472.6	452.4	435.3	421.9	412.8	410.9	412.8	421.9	435.3
150°	523.2	501.4	477.6	459.0	444.4	431.0	422.7	421.7	422.7	431.0	444.4
152.5°	524.9	503.9	483.4	465.6	452.7	441.0	432.7	432.5	432.7	441.0	452.7
155°	525.3	508.7	491.1	476.5	465.2	454.9	448.6	448.6	448.6	454.9	465.2
157.5°	526.3	511.4	497.3	486.1	476.4	467.3	462.3	461.5	462.3	467.3	476.4
160°	526.3	513.9	501.4	491.1	483.8	475.5	471.4	471.4	471.4	475.5	483.8
162.5°	525.5	514.7	503.9	495.3	488.8	482.1	478.8	478.8	478.8	482.1	488.8
165°	523.2	515.9	507.7	500.4	496.2	491.1	489.0	490.1	489.0	491.1	496.2
167.5°	521.6	515.8	509.7	505.2	502.3	498.3	497.3	498.6	497.3	498.3	502.3
170°	519.1	514.9	509.7	507.7	505.6	502.5	501.4	503.5	501.4	502.5	505.6
172.5°	518.3	514.9	510.6	509.3	508.1	505.8	505.6	506.8	505.6	505.8	508.1
175°	515.9	513.9	511.8	510.8	510.8	508.7	509.7	510.8	509.7	508.7	510.8
177.5°	514.2	512.6	511.8	511.8	511.8	511.0	511.8	512.6	511.8	511.0	511.8
180°	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8



TEST NUMBER: P332356-940

CATALOG NUMBER: S123RDIP-S1000D1195U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1393.3	1387.0	1382.6	1372.9	1366.6	1359.8	1353.0	1357.4	1356.9	1356.4	1356.4
5°	1346.6	1332.6	1319.9	1303.5	1293.2	1280.4	1270.7	1269.5	1271.9	1263.5	1258.6
7.5°	1300.2	1281.1	1263.1	1245.0	1225.8	1210.5	1201.0	1196.4	1190.3	1185.0	1179.6
10°	1267.7	1245.3	1227.6	1205.1	1184.5	1166.4	1154.9	1146.9	1142.6	1138.4	1130.5
12.5°	1234.2	1212.2	1189.8	1164.4	1144.8	1123.6	1115.0	1106.2	1098.1	1093.2	1082.4
15°	1185.2	1156.6	1133.0	1106.3	1084.4	1063.8	1051.7	1034.0	1031.6	1025.6	1014.7
17.5°	1136.0	1105.0	1072.4	1052.7	1028.0	1006.5	988.0	982.1	964.7	958.2	948.7
20°	1097.2	1068.6	1043.7	1017.7	981.9	961.8	947.3	939.4	925.4	916.9	910.9
22.5°	1063.6	1034.7	1005.9	975.4	945.9	923.5	912.8	900.5	892.9	881.0	874.4
25°	1015.8	984.3	949.7	916.9	895.7	878.7	861.7	850.8	839.9	834.4	822.2
27.5°	960.3	927.3	894.9	870.0	844.0	827.2	811.8	802.1	789.0	779.8	773.1
30°	929.7	890.8	862.9	840.4	807.1	791.3	779.8	767.7	758.0	748.2	741.5
32.5°	894.2	858.8	832.3	804.6	778.9	761.7	746.8	736.1	727.8	718.6	711.9
35°	838.7	809.0	781.6	753.7	734.9	717.3	699.7	690.5	682.7	674.2	668.2
37.5°	788.4	760.6	734.7	708.2	684.8	670.6	656.4	649.4	638.7	633.0	626.9
40°	757.3	730.0	702.1	676.6	652.4	641.4	628.7	618.4	608.7	604.4	597.7
42.5°	723.4	696.1	672.5	645.1	625.2	610.4	598.6	587.3	580.1	573.8	570.1
45°	673.0	648.7	625.6	598.3	579.5	566.8	553.4	543.1	536.5	532.2	525.5
47.5°	624.1	599.8	576.4	552.6	534.4	519.8	506.5	499.3	490.4	485.3	480.7
50°	588.6	566.8	541.9	520.0	501.9	487.3	476.4	467.3	459.4	452.7	449.7
52.5°	556.1	532.8	511.3	491.0	471.7	455.2	445.3	435.7	429.8	422.1	418.6
55°	502.5	480.0	461.8	441.8	422.9	409.0	396.9	388.3	382.3	373.8	369.0
57.5°	452.1	431.9	410.2	392.9	373.4	361.7	351.6	340.1	332.7	326.0	321.3
60°	418.1	395.0	376.2	359.9	342.9	327.7	318.6	309.5	301.6	294.9	290.7
62.5°	382.6	362.6	344.6	326.8	311.3	298.1	287.5	279.9	273.0	268.7	264.5
65°	328.3	312.5	294.4	279.7	265.2	255.5	247.0	240.3	235.4	232.4	228.8
67.5°	278.3	263.0	247.1	232.8	223.1	215.7	210.1	204.4	202.0	198.0	195.6
70°	245.8	230.0	216.1	205.1	195.4	189.9	186.3	182.1	179.6	174.8	172.4
72.5°	210.4	198.9	188.9	179.9	172.1	167.1	162.5	157.3	153.4	148.0	145.6
75°	165.7	155.3	147.5	141.4	136.5	129.8	123.1	117.7	115.9	114.0	113.5
77.5°	122.7	116.2	110.5	105.3	99.2	94.4	93.0	91.8	91.4	90.4	90.4
80°	96.5	90.4	86.1	80.1	76.4	76.4	76.4	75.3	75.9	75.9	75.9
82.5°	71.7	66.2	63.8	61.6	60.9	61.4	61.4	61.6	61.3	62.2	61.8
85°	37.0	37.6	38.9	38.3	38.9	38.9	40.0	39.4	40.0	38.9	40.0
87.5°	15.9	17.7	18.8	20.0	21.0	21.2	21.5	21.7	22.4	22.6	23.0
90°	11.4	13.5	16.6	19.7	22.8	25.9	24.9	25.9	26.9	28.0	30.1
92.5°	44.6	59.9	87.0	131.6	175.3	159.3	120.2	87.2	69.2	61.1	55.7
95°	94.3	134.6	222.7	377.1	547.1	614.4	498.3	373.0	252.8	197.9	160.6
97.5°	111.9	155.6	239.8	413.8	697.1	952.1	1018.6	929.7	744.7	611.1	487.1
100°	124.3	164.7	237.3	390.6	663.1	981.1	1185.3	1221.5	1137.6	1016.4	869.2
102.5°	138.4	175.5	240.6	370.7	613.3	927.3	1193.5	1318.5	1315.7	1245.1	1151.8
105°	161.6	193.8	249.7	356.4	552.2	832.9	1130.3	1346.8	1450.5	1470.2	1443.2
107.5°	187.7	217.6	266.7	355.3	513.3	749.7	1019.7	1265.2	1433.4	1524.2	1561.1
110°	205.1	234.2	280.8	359.5	498.3	702.4	950.0	1187.3	1378.0	1508.5	1581.0



TEST NUMBER: P332356-940

CATALOG NUMBER: S123RDIP-S1000D1195U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	223.4	251.6	294.9	367.8	490.1	670.9	889.6	1110.2	1305.0	1451.3	1544.5
115°	250.7	278.7	318.1	381.3	487.0	637.1	816.4	1008.1	1188.3	1340.6	1453.6
117.5°	277.9	303.8	342.7	399.0	488.8	617.2	772.2	934.1	1089.7	1226.5	1341.0
120°	295.2	321.2	358.5	412.3	492.1	608.1	749.0	895.1	1035.0	1159.3	1264.0
122.5°	311.0	338.6	375.1	424.8	497.9	602.4	730.0	864.4	991.0	1106.3	1203.5
125°	334.7	362.6	398.9	444.4	506.6	594.7	705.5	823.7	936.6	1036.0	1118.9
127.5°	356.6	384.6	419.5	460.7	516.6	590.9	684.0	788.0	888.7	978.4	1053.8
130°	369.9	397.8	432.0	471.4	523.2	588.4	672.3	765.6	858.9	942.8	1013.3
132.5°	382.3	409.5	442.8	481.3	528.2	587.6	661.6	744.9	830.7	908.8	976.0
135°	398.9	426.9	459.0	494.2	535.7	586.4	647.6	716.9	790.5	857.8	916.9
137.5°	413.4	439.3	470.1	503.7	540.6	584.1	635.3	691.4	751.7	809.8	860.9
140°	421.7	447.5	477.6	508.7	543.9	583.3	627.9	676.5	729.3	779.1	823.7
142.5°	430.0	454.2	483.4	513.6	546.4	581.7	621.2	662.5	707.8	750.9	789.7
145°	440.3	464.1	491.1	519.1	548.0	579.2	612.3	645.4	679.7	712.8	742.8
147.5°	452.4	472.6	497.3	522.4	548.0	575.2	603.6	631.6	658.7	685.5	706.8
150°	459.0	477.6	501.4	523.2	548.0	571.9	597.8	621.6	645.4	667.2	686.9
152.5°	465.6	483.4	503.9	524.9	545.5	567.8	591.2	612.5	633.0	652.3	668.7
155°	476.5	491.1	508.7	525.3	542.9	560.5	581.2	598.8	615.4	631.0	643.4
157.5°	486.1	497.3	511.4	526.3	539.4	554.1	570.0	584.3	598.2	610.2	619.9
160°	491.1	501.4	513.9	526.3	537.7	549.1	562.6	576.0	587.5	597.8	605.0
162.5°	495.3	503.9	514.7	525.5	534.4	544.1	555.1	566.1	575.9	585.3	591.7
165°	500.4	507.7	515.9	523.2	529.4	536.6	544.9	553.2	559.5	566.7	571.9
167.5°	505.2	509.7	515.8	521.6	524.4	529.2	535.2	542.1	546.8	551.0	554.7
170°	507.7	509.7	514.9	519.1	521.1	524.2	529.4	534.6	537.7	541.8	543.9
172.5°	509.3	510.6	514.9	518.3	518.6	520.0	523.6	528.0	530.2	533.6	534.8
175°	510.8	511.8	513.9	515.9	514.9	514.9	517.0	519.1	520.0	522.2	522.2
177.5°	511.8	511.8	512.6	514.2	512.6	511.8	512.6	513.4	514.2	515.1	515.1
180°	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8



TEST NUMBER: P332356-940

CATALOG NUMBER: S123RDIP-S1000D1195U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1350.6	1350.1	1350.6	1348.6	1350.6	1350.1	1350.6	1356.4	1356.4	1356.9	1357.4
5°	1256.8	1256.2	1254.4	1248.8	1254.4	1256.2	1256.8	1258.6	1263.5	1271.9	1269.5
7.5°	1174.8	1174.0	1168.7	1168.8	1168.7	1174.0	1174.8	1179.6	1185.0	1190.3	1196.4
10°	1126.3	1126.9	1119.6	1115.4	1119.6	1126.9	1126.3	1130.5	1138.4	1142.6	1146.9
12.5°	1079.2	1076.4	1070.6	1065.9	1070.6	1076.4	1079.2	1082.4	1093.2	1098.1	1106.2
15°	1017.1	1011.0	996.4	997.6	996.4	1011.0	1017.1	1014.7	1025.6	1031.6	1034.0
17.5°	943.9	939.4	939.1	930.7	939.1	939.4	943.9	948.7	958.2	964.7	982.1
20°	901.2	898.1	899.3	890.8	899.3	898.1	901.2	910.9	916.9	925.4	939.4
22.5°	867.6	864.6	859.5	856.8	859.5	864.6	867.6	874.4	881.0	892.9	900.5
25°	818.6	813.8	809.0	812.0	809.0	813.8	818.6	822.2	834.4	839.9	850.8
27.5°	769.6	766.0	761.1	760.5	761.1	766.0	769.6	773.1	779.8	789.0	802.1
30°	738.5	734.9	732.5	729.4	732.5	734.9	738.5	741.5	748.2	758.0	767.7
32.5°	706.9	706.2	701.9	701.2	701.9	706.2	706.9	711.9	718.6	727.8	736.1
35°	665.7	662.1	660.8	661.5	660.8	662.1	665.7	668.2	674.2	682.7	690.5
37.5°	626.5	621.6	619.5	617.2	619.5	621.6	626.5	626.9	633.0	638.7	649.4
40°	598.3	593.5	592.3	591.0	592.3	593.5	598.3	597.7	604.4	608.7	618.4
42.5°	566.8	564.8	564.1	562.0	564.1	564.8	566.8	570.1	573.8	580.1	587.3
45°	523.7	523.1	519.4	520.7	519.4	523.1	523.7	525.5	532.2	536.5	543.1
47.5°	478.3	475.6	473.1	474.7	473.1	475.6	478.3	480.7	485.3	490.4	499.3
50°	447.3	446.0	440.6	441.8	440.6	446.0	447.3	449.7	452.7	459.4	467.3
52.5°	416.2	411.5	409.5	408.8	409.5	411.5	416.2	418.6	422.1	429.8	435.7
55°	364.7	359.3	356.9	355.6	356.9	359.3	364.7	369.0	373.8	382.3	388.3
57.5°	314.2	312.7	310.9	312.2	310.9	312.7	314.2	321.3	326.0	332.7	340.1
60°	284.6	284.6	284.6	284.0	284.6	284.6	284.6	290.7	294.9	301.6	309.5
62.5°	261.8	260.3	259.8	260.7	259.8	260.3	261.8	264.5	268.7	273.0	279.9
65°	226.9	226.3	223.9	223.3	223.9	226.3	226.9	228.8	232.4	235.4	240.3
67.5°	194.0	191.9	191.2	190.3	191.2	191.9	194.0	195.6	198.0	202.0	204.4
70°	169.3	168.1	164.4	165.1	164.4	168.1	169.3	172.4	174.8	179.6	182.1
72.5°	142.6	141.4	140.6	139.8	140.6	141.4	142.6	145.6	148.0	153.4	157.3
75°	112.9	112.3	111.6	114.0	111.6	112.3	112.9	113.5	114.0	115.9	117.7
77.5°	90.4	90.4	90.8	89.8	90.8	90.4	90.4	90.4	90.4	91.4	91.8
80°	75.9	75.9	75.3	75.3	75.3	75.9	75.9	75.9	75.9	75.9	75.3
82.5°	60.8	61.3	61.6	60.7	61.6	61.3	60.8	61.8	62.2	61.3	61.6
85°	40.0	39.4	40.7	40.0	40.7	39.4	40.0	40.0	38.9	40.0	39.4
87.5°	23.8	23.0	23.2	23.5	23.2	23.0	23.8	23.0	22.6	22.4	21.7
90°	29.0	30.1	31.1	30.1	31.1	30.1	29.0	30.1	28.0	26.9	25.9
92.5°	53.9	50.7	51.8	49.9	51.8	50.7	53.9	55.7	61.1	69.2	87.2
95°	140.9	131.6	124.3	120.2	124.3	131.6	140.9	160.6	197.9	252.8	373.0
97.5°	410.7	364.1	336.1	327.2	336.1	364.1	410.7	487.1	611.1	744.7	929.7
100°	764.6	688.9	648.5	649.6	648.5	688.9	764.6	869.2	1016.4	1137.6	1221.5
102.5°	1070.4	1010.6	976.8	953.0	976.8	1010.6	1070.4	1151.8	1245.1	1315.7	1318.5
105°	1395.5	1356.2	1323.0	1317.9	1323.0	1356.2	1395.5	1443.2	1470.2	1450.5	1346.8
107.5°	1561.9	1548.6	1537.5	1527.9	1537.5	1548.6	1561.9	1561.1	1524.2	1433.4	1265.2
110°	1610.0	1618.3	1616.2	1614.2	1616.2	1618.3	1610.0	1581.0	1508.5	1378.0	1187.3



TEST NUMBER: P332356-940

CATALOG NUMBER: S123RDIP-S1000D1195U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1597.6	1623.3	1631.1	1631.6	1631.1	1623.3	1597.6	1544.5	1451.3	1305.0	1110.2
115°	1531.2	1576.8	1597.6	1602.8	1597.6	1576.8	1531.2	1453.6	1340.6	1188.3	1008.1
117.5°	1422.1	1474.3	1504.1	1511.2	1504.1	1474.3	1422.1	1341.0	1226.5	1089.7	934.1
120°	1345.8	1403.8	1428.7	1434.9	1428.7	1403.8	1345.8	1264.0	1159.3	1035.0	895.1
122.5°	1276.2	1328.4	1355.8	1363.6	1355.8	1328.4	1276.2	1203.5	1106.3	991.0	864.4
125°	1185.3	1230.8	1256.7	1264.0	1256.7	1230.8	1185.3	1118.9	1036.0	936.6	823.7
127.5°	1112.9	1151.8	1175.3	1181.9	1175.3	1151.8	1112.9	1053.8	978.4	888.7	788.0
130°	1068.2	1105.5	1127.2	1135.5	1127.2	1105.5	1068.2	1013.3	942.8	858.9	765.6
132.5°	1027.5	1064.8	1084.1	1089.9	1084.1	1064.8	1027.5	976.0	908.8	830.7	744.9
135°	967.7	998.7	1017.4	1024.7	1017.4	998.7	967.7	916.9	857.8	790.5	716.9
137.5°	903.7	935.1	950.8	955.6	950.8	935.1	903.7	860.9	809.8	751.7	691.4
140°	863.0	892.1	908.6	907.6	908.6	892.1	863.0	823.7	779.1	729.3	676.5
142.5°	823.2	848.9	863.8	862.8	863.8	848.9	823.2	789.7	750.9	707.8	662.5
145°	768.7	790.5	798.8	800.8	798.8	790.5	768.7	742.8	712.8	679.7	645.4
147.5°	726.5	741.2	749.0	749.8	749.0	741.2	726.5	706.8	685.5	658.7	631.6
150°	702.4	713.8	720.1	720.1	720.1	713.8	702.4	686.9	667.2	645.4	621.6
152.5°	680.9	691.4	695.2	695.2	695.2	691.4	680.9	668.7	652.3	633.0	612.5
155°	652.7	661.0	663.1	664.1	663.1	661.0	652.7	643.4	631.0	615.4	598.8
157.5°	628.0	634.3	635.9	635.7	635.9	634.3	628.0	619.9	610.2	598.2	584.3
160°	612.3	618.5	618.5	617.5	618.5	618.5	612.3	605.0	597.8	587.5	576.0
162.5°	596.6	601.9	601.9	600.9	601.9	601.9	596.6	591.7	585.3	575.9	566.1
165°	576.0	580.1	579.2	579.2	579.2	580.1	576.0	571.9	566.7	559.5	553.2
167.5°	556.5	559.5	558.4	558.4	558.4	559.5	556.5	554.7	551.0	546.8	542.1
170°	544.9	547.1	546.0	546.0	546.0	547.1	544.9	543.9	541.8	537.7	534.6
172.5°	535.0	537.1	535.2	534.4	535.2	537.1	535.0	534.8	533.6	530.2	528.0
175°	522.2	523.2	522.2	521.1	522.2	523.2	522.2	522.2	522.2	520.0	519.1
177.5°	514.2	515.1	513.4	513.4	513.4	515.1	514.2	515.1	515.1	514.2	513.4
180°	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8



TEST NUMBER: P332356-940

CATALOG NUMBER: S123RDIP-S1000D1195U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1353.0	1359.8	1366.6	1372.9	1382.6	1387.0	1393.3	1395.7	1403.0	1413.7	1422.5
5°	1270.7	1280.4	1293.2	1303.5	1319.9	1332.6	1346.6	1359.9	1375.7	1398.1	1418.2
7.5°	1201.0	1210.5	1225.8	1245.0	1263.1	1281.1	1300.2	1318.4	1341.0	1373.1	1405.1
10°	1154.9	1166.4	1184.5	1205.1	1227.6	1245.3	1267.7	1290.8	1318.7	1355.7	1393.9
12.5°	1115.0	1123.6	1144.8	1164.4	1189.8	1212.2	1234.2	1261.1	1292.9	1332.4	1378.4
15°	1051.7	1063.8	1084.4	1106.3	1133.0	1156.6	1185.2	1217.9	1248.8	1297.4	1353.3
17.5°	988.0	1006.5	1028.0	1052.7	1072.4	1105.0	1136.0	1169.7	1207.7	1259.2	1320.4
20°	947.3	961.8	981.9	1017.7	1043.7	1068.6	1097.2	1139.1	1174.2	1232.5	1296.2
22.5°	912.8	923.5	945.9	975.4	1005.9	1034.7	1063.6	1103.6	1147.0	1202.4	1271.5
25°	861.7	878.7	895.7	916.9	949.7	984.3	1015.8	1049.8	1095.9	1154.9	1229.5
27.5°	811.8	827.2	844.0	870.0	894.9	927.3	960.3	999.3	1048.7	1111.0	1186.7
30°	779.8	791.3	807.1	840.4	862.9	890.8	929.7	964.3	1010.4	1076.6	1156.6
32.5°	746.8	761.7	778.9	804.6	832.3	858.8	894.2	931.7	978.8	1044.0	1126.1
35°	699.7	717.3	734.9	753.7	781.6	809.0	838.7	879.9	927.8	991.0	1071.7
37.5°	656.4	670.6	684.8	708.2	734.7	760.6	788.4	829.0	874.2	942.3	1016.4
40°	628.7	641.4	652.4	676.6	702.1	730.0	757.3	793.2	841.7	905.4	977.0
42.5°	598.6	610.4	625.2	645.1	672.5	696.1	723.4	757.2	802.8	867.5	930.4
45°	553.4	566.8	579.5	598.3	625.6	648.7	673.0	705.2	751.9	805.3	861.1
47.5°	506.5	519.8	534.4	552.6	576.4	599.8	624.1	652.6	695.2	747.6	785.2
50°	476.4	487.3	501.9	520.0	541.9	566.8	588.6	619.6	660.2	701.5	734.2
52.5°	445.3	455.2	471.7	491.0	511.3	532.8	556.1	582.6	619.5	658.3	684.3
55°	396.9	409.0	422.9	441.8	461.8	480.0	502.5	529.8	558.9	588.0	605.6
57.5°	351.6	361.7	373.4	392.9	410.2	431.9	452.1	473.3	500.2	522.3	533.8
60°	318.6	327.7	342.9	359.9	376.2	395.0	418.1	439.3	459.9	477.6	486.7
62.5°	287.5	298.1	311.3	326.8	344.6	362.6	382.6	400.6	418.7	433.9	440.1
65°	247.0	255.5	265.2	279.7	294.4	312.5	328.3	346.5	359.9	368.4	373.8
67.5°	210.1	215.7	223.1	232.8	247.1	263.0	278.3	292.5	303.6	309.5	314.3
70°	186.3	189.9	195.4	205.1	216.1	230.0	245.8	256.1	265.8	270.6	275.5
72.5°	162.5	167.1	172.1	179.9	188.9	198.9	210.4	223.1	228.5	234.3	237.2
75°	123.1	129.8	136.5	141.4	147.5	155.3	165.7	173.5	176.6	181.5	182.1
77.5°	93.0	94.4	99.2	105.3	110.5	116.2	122.7	129.7	131.2	133.8	135.4
80°	76.4	76.4	76.4	80.1	86.1	90.4	96.5	100.1	102.5	103.2	103.8
82.5°	61.4	61.4	60.9	61.6	63.8	66.2	71.7	75.9	77.8	77.4	76.1
85°	40.0	38.9	38.9	38.3	38.9	37.6	37.0	39.4	43.1	43.1	41.9
87.5°	21.5	21.2	21.0	20.0	18.8	17.7	15.9	16.0	15.3	16.9	16.0
90°	24.9	25.9	22.8	19.7	16.6	13.5	11.4	9.4	6.2	4.1	2.1
92.5°	120.2	159.3	175.3	131.6	87.0	59.9	44.6	35.8	27.7	19.1	12.8
95°	498.3	614.4	547.1	377.1	222.7	134.6	94.3	67.3	49.8	38.3	35.2
97.5°	1018.6	952.1	697.1	413.8	239.8	155.6	111.9	85.3	70.0	61.1	60.1
100°	1185.3	981.1	663.1	390.6	237.3	164.7	124.3	99.4	85.0	77.7	76.7
102.5°	1193.5	927.3	613.3	370.7	240.6	175.5	138.4	116.0	102.4	95.9	94.1
105°	1130.3	832.9	552.2	356.4	249.7	193.8	161.6	142.0	129.5	123.3	120.2
107.5°	1019.7	749.7	513.3	355.3	266.7	217.6	187.7	169.2	157.0	151.1	147.9
110°	950.0	702.4	498.3	359.5	280.8	234.2	205.1	187.5	176.1	170.9	167.8



TEST NUMBER: P332356-940

CATALOG NUMBER: S123RDIP-S1000D1195U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	889.6	670.9	490.1	367.8	294.9	251.6	223.4	205.7	194.4	189.2	186.1
115°	816.4	637.1	487.0	381.3	318.1	278.7	250.7	233.1	222.7	216.5	212.4
117.5°	772.2	617.2	488.8	399.0	342.7	303.8	277.9	258.2	248.6	243.4	238.7
120°	749.0	608.1	492.1	412.3	358.5	321.2	295.2	275.6	265.2	260.0	256.9
122.5°	730.0	602.4	497.9	424.8	375.1	338.6	311.0	292.1	281.0	275.8	272.7
125°	705.5	594.7	506.6	444.4	398.9	362.6	334.7	315.0	303.5	297.4	295.2
127.5°	684.0	590.9	516.6	460.7	419.5	384.6	356.6	334.8	323.2	315.6	312.5
130°	672.3	588.4	523.2	471.4	432.0	397.8	369.9	348.1	335.6	326.4	323.2
132.5°	661.6	587.6	528.2	481.3	442.8	409.5	382.3	360.5	345.6	335.5	331.5
135°	647.6	586.4	535.7	494.2	459.0	426.9	398.9	377.1	361.6	350.2	346.1
137.5°	635.3	584.1	540.6	503.7	470.1	439.3	413.4	391.8	375.2	364.1	359.7
140°	627.9	583.3	543.9	508.7	477.6	447.5	421.7	400.9	384.3	374.0	368.8
142.5°	621.2	581.7	546.4	513.6	483.4	454.2	430.0	409.2	394.3	383.2	378.8
145°	612.3	579.2	548.0	519.1	491.1	464.1	440.3	422.7	407.2	397.8	394.8
147.5°	603.6	575.2	548.0	522.4	497.3	472.6	452.4	435.3	421.9	412.8	410.9
150°	597.8	571.9	548.0	523.2	501.4	477.6	459.0	444.4	431.0	422.7	421.7
152.5°	591.2	567.8	545.5	524.9	503.9	483.4	465.6	452.7	441.0	432.7	432.5
155°	581.2	560.5	542.9	525.3	508.7	491.1	476.5	465.2	454.9	448.6	448.6
157.5°	570.0	554.1	539.4	526.3	511.4	497.3	486.1	476.4	467.3	462.3	461.5
160°	562.6	549.1	537.7	526.3	513.9	501.4	491.1	483.8	475.5	471.4	471.4
162.5°	555.1	544.1	534.4	525.5	514.7	503.9	495.3	488.8	482.1	478.8	478.8
165°	544.9	536.6	529.4	523.2	515.9	507.7	500.4	496.2	491.1	489.0	490.1
167.5°	535.2	529.2	524.4	521.6	515.8	509.7	505.2	502.3	498.3	497.3	498.6
170°	529.4	524.2	521.1	519.1	514.9	509.7	507.7	505.6	502.5	501.4	503.5
172.5°	523.6	520.0	518.6	518.3	514.9	510.6	509.3	508.1	505.8	505.6	506.8
175°	517.0	514.9	514.9	515.9	513.9	511.8	510.8	510.8	508.7	509.7	510.8
177.5°	512.6	511.8	512.6	514.2	512.6	511.8	511.8	511.8	511.0	511.8	512.6
180°	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8



TEST NUMBER: P332356-940

CATALOG NUMBER: S123RDIP-S1000D1195U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1425.3	1430.7	1437.4	1447.7	1455.5	1462.2	1463.7	1465.6	1470.5	1478.7	1485.1
5°	1434.6	1448.5	1471.0	1492.8	1516.5	1535.9	1554.1	1566.8	1579.0	1604.5	1625.1
7.5°	1431.6	1462.8	1497.9	1537.1	1576.8	1615.2	1651.0	1682.9	1714.7	1751.9	1794.2
10°	1429.7	1466.2	1513.4	1563.8	1619.1	1673.0	1725.3	1765.9	1813.2	1855.7	1909.7
12.5°	1420.5	1472.9	1529.5	1593.9	1661.8	1724.0	1792.7	1848.9	1903.1	1964.4	2027.2
15°	1408.5	1472.2	1543.8	1629.3	1732.5	1807.8	1878.1	1975.9	2042.6	2109.3	2199.2
17.5°	1386.5	1464.3	1553.7	1664.9	1751.0	1852.1	1958.0	2035.2	2125.1	2219.2	2300.5
20°	1369.0	1459.5	1559.6	1668.8	1778.6	1888.5	1991.0	2083.3	2176.1	2284.7	2351.5
22.5°	1351.6	1441.0	1545.0	1661.1	1779.1	1894.8	2010.9	2119.2	2223.7	2333.3	2418.5
25°	1314.4	1420.6	1533.5	1651.8	1768.4	1895.8	2034.1	2154.9	2284.1	2397.0	2477.7
27.5°	1276.8	1374.1	1486.5	1606.5	1736.1	1886.7	2049.4	2186.7	2316.2	2397.0	2422.4
30°	1242.8	1345.9	1449.1	1571.1	1711.3	1879.4	2052.4	2209.5	2315.7	2350.9	2324.8
32.5°	1208.4	1301.8	1404.0	1528.8	1677.8	1861.4	2056.2	2195.9	2259.9	2232.9	2126.7
35°	1147.5	1231.9	1330.8	1455.8	1626.9	1851.5	2040.2	2134.8	2119.1	1967.4	1767.1
37.5°	1082.4	1151.2	1242.8	1373.5	1574.2	1812.0	1971.2	1985.2	1848.7	1615.8	1384.5
40°	1031.0	1092.9	1187.0	1323.5	1533.5	1773.2	1901.8	1845.4	1633.6	1374.5	1181.5
42.5°	981.0	1033.2	1123.8	1271.0	1494.7	1720.3	1798.4	1675.5	1431.2	1186.2	1010.7
45°	896.3	945.5	1036.4	1187.6	1415.1	1619.1	1608.7	1395.1	1150.6	953.3	807.7
47.5°	815.9	858.9	944.3	1098.6	1321.8	1467.3	1370.8	1143.5	936.1	777.8	674.0
50°	759.1	801.6	886.6	1038.9	1247.1	1353.3	1215.5	996.4	806.5	675.4	592.9
52.5°	704.8	746.3	823.9	972.4	1156.7	1220.2	1072.3	869.2	710.9	597.7	526.8
55°	628.7	660.2	730.0	872.0	1009.8	1024.3	874.4	704.5	574.1	495.2	446.7
57.5°	551.2	578.3	647.3	760.4	856.9	849.4	707.3	560.4	472.5	413.8	378.7
60°	500.6	527.4	588.0	685.1	758.0	732.5	602.0	483.7	408.4	365.3	337.4
62.5°	453.5	474.4	531.2	602.1	654.5	625.6	514.6	416.7	357.0	320.7	298.5
65°	385.3	402.3	447.8	484.8	514.0	486.1	393.9	325.8	282.8	257.3	242.1
67.5°	320.6	331.4	360.1	373.4	394.0	363.4	296.1	250.7	226.1	204.6	194.0
70°	279.7	287.7	302.8	313.7	319.2	287.7	237.9	204.5	183.9	168.7	162.0
72.5°	239.0	245.9	249.0	257.9	255.1	225.5	191.3	164.7	149.9	139.6	131.0
75°	182.6	185.7	182.6	179.1	171.1	150.5	126.8	113.5	102.5	97.7	94.7
77.5°	133.1	132.2	128.0	122.3	108.9	95.9	83.1	78.6	73.9	71.3	70.3
80°	102.5	100.1	96.5	87.4	75.9	66.8	63.8	60.7	58.9	55.8	55.2
82.5°	76.3	74.9	68.8	61.2	53.1	48.8	46.3	45.1	43.3	41.7	41.6
85°	40.7	38.9	32.2	27.9	26.7	25.5	24.9	24.9	22.5	21.8	21.8
87.5°	13.9	11.4	11.6	10.5	11.0	10.6	11.7	11.3	11.5	11.8	11.0
90°	4.1	6.2	9.4	11.4	13.5	16.6	19.7	22.8	25.9	24.9	25.9
92.5°	19.1	27.7	35.8	44.6	59.9	87.0	131.6	175.3	159.3	120.2	87.2
95°	38.3	49.8	67.3	94.3	134.6	222.7	377.1	547.1	614.4	498.3	373.0
97.5°	61.1	70.0	85.3	111.9	155.6	239.8	413.8	697.1	952.1	1018.6	929.7
100°	77.7	85.0	99.4	124.3	164.7	237.3	390.6	663.1	981.1	1185.3	1221.5
102.5°	95.9	102.4	116.0	138.4	175.5	240.6	370.7	613.3	927.3	1193.5	1318.5
105°	123.3	129.5	142.0	161.6	193.8	249.7	356.4	552.2	832.9	1130.3	1346.8
107.5°	151.1	157.0	169.2	187.7	217.6	266.7	355.3	513.3	749.7	1019.7	1265.2
110°	170.9	176.1	187.5	205.1	234.2	280.8	359.5	498.3	702.4	950.0	1187.3



TEST NUMBER: P332356-940

CATALOG NUMBER: S123RDIP-S1000D1195U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	189.2	194.4	205.7	223.4	251.6	294.9	367.8	490.1	670.9	889.6	1110.2
115°	216.5	222.7	233.1	250.7	278.7	318.1	381.3	487.0	637.1	816.4	1008.1
117.5°	243.4	248.6	258.2	277.9	303.8	342.7	399.0	488.8	617.2	772.2	934.1
120°	260.0	265.2	275.6	295.2	321.2	358.5	412.3	492.1	608.1	749.0	895.1
122.5°	275.8	281.0	292.1	311.0	338.6	375.1	424.8	497.9	602.4	730.0	864.4
125°	297.4	303.5	315.0	334.7	362.6	398.9	444.4	506.6	594.7	705.5	823.7
127.5°	315.6	323.2	334.8	356.6	384.6	419.5	460.7	516.6	590.9	684.0	788.0
130°	326.4	335.6	348.1	369.9	397.8	432.0	471.4	523.2	588.4	672.3	765.6
132.5°	335.5	345.6	360.5	382.3	409.5	442.8	481.3	528.2	587.6	661.6	744.9
135°	350.2	361.6	377.1	398.9	426.9	459.0	494.2	535.7	586.4	647.6	716.9
137.5°	364.1	375.2	391.8	413.4	439.3	470.1	503.7	540.6	584.1	635.3	691.4
140°	374.0	384.3	400.9	421.7	447.5	477.6	508.7	543.9	583.3	627.9	676.5
142.5°	383.2	394.3	409.2	430.0	454.2	483.4	513.6	546.4	581.7	621.2	662.5
145°	397.8	407.2	422.7	440.3	464.1	491.1	519.1	548.0	579.2	612.3	645.4
147.5°	412.8	421.9	435.3	452.4	472.6	497.3	522.4	548.0	575.2	603.6	631.6
150°	422.7	431.0	444.4	459.0	477.6	501.4	523.2	548.0	571.9	597.8	621.6
152.5°	432.7	441.0	452.7	465.6	483.4	503.9	524.9	545.5	567.8	591.2	612.5
155°	448.6	454.9	465.2	476.5	491.1	508.7	525.3	542.9	560.5	581.2	598.8
157.5°	462.3	467.3	476.4	486.1	497.3	511.4	526.3	539.4	554.1	570.0	584.3
160°	471.4	475.5	483.8	491.1	501.4	513.9	526.3	537.7	549.1	562.6	576.0
162.5°	478.8	482.1	488.8	495.3	503.9	514.7	525.5	534.4	544.1	555.1	566.1
165°	489.0	491.1	496.2	500.4	507.7	515.9	523.2	529.4	536.6	544.9	553.2
167.5°	497.3	498.3	502.3	505.2	509.7	515.8	521.6	524.4	529.2	535.2	542.1
170°	501.4	502.5	505.6	507.7	509.7	514.9	519.1	521.1	524.2	529.4	534.6
172.5°	505.6	505.8	508.1	509.3	510.6	514.9	518.3	518.6	520.0	523.6	528.0
175°	509.7	508.7	510.8	510.8	511.8	513.9	515.9	514.9	514.9	517.0	519.1
177.5°	511.8	511.0	511.8	511.8	511.8	512.6	514.2	512.6	511.8	512.6	513.4
180°	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8



TEST NUMBER: P332356-940

CATALOG NUMBER: S123RDIP-S1000D1195U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1495.2	1495.2	1497.2	1504.5	1505.5	1511.7	1509.8
5°	1643.3	1654.8	1659.1	1677.3	1688.2	1693.1	1683.4
7.5°	1824.4	1856.9	1872.3	1891.4	1908.3	1913.3	1900.1
10°	1956.4	1990.4	2018.9	2036.6	2052.9	2063.9	2077.8
12.5°	2084.1	2125.8	2152.9	2177.8	2194.7	2208.5	2210.8
15°	2222.9	2286.0	2333.9	2369.1	2386.7	2395.8	2392.2
17.5°	2362.8	2421.3	2455.4	2491.4	2515.7	2516.9	2517.7
20°	2442.0	2498.9	2538.4	2565.1	2592.4	2591.2	2597.3
22.5°	2494.8	2539.8	2570.0	2589.3	2598.7	2594.1	2595.3
25°	2519.6	2532.9	2527.5	2496.5	2488.7	2460.1	2465.0
27.5°	2391.9	2328.8	2263.5	2179.5	2113.3	2060.3	2063.0
30°	2218.6	2106.9	1979.5	1872.7	1776.8	1750.2	1693.1
32.5°	1976.4	1808.8	1659.6	1560.0	1477.7	1455.5	1405.7
35°	1565.7	1403.0	1249.5	1157.3	1120.8	1069.9	1069.3
37.5°	1216.9	1073.7	992.6	923.4	887.1	856.2	853.2
40°	1023.8	912.0	850.8	801.0	765.3	742.2	736.7
42.5°	888.8	798.4	741.1	710.2	682.7	670.8	661.9
45°	725.8	665.1	625.0	597.1	584.4	575.2	570.4
47.5°	607.1	566.4	539.1	520.6	510.2	500.6	503.2
50°	542.5	509.2	489.1	471.5	463.6	456.9	457.5
52.5°	490.5	460.6	444.4	431.7	421.9	417.1	414.8
55°	416.3	397.4	381.1	372.0	366.5	359.9	358.0
57.5°	355.1	340.5	327.2	316.9	315.6	309.2	310.0
60°	314.3	302.2	291.3	285.8	281.6	276.1	277.9
62.5°	280.9	270.6	260.7	256.2	252.0	248.0	248.8
65°	230.0	220.3	214.2	211.8	210.0	208.1	206.3
67.5°	183.2	177.4	173.5	168.4	164.6	164.0	162.1
70°	154.2	146.2	139.6	132.9	131.1	130.5	131.1
72.5°	123.6	118.6	116.7	113.5	113.2	111.6	112.6
75°	92.8	91.0	89.8	87.4	87.4	87.4	87.4
77.5°	68.5	67.3	66.6	66.2	65.5	64.6	64.6
80°	53.4	52.8	51.5	51.5	51.0	51.5	51.0
82.5°	40.3	40.2	39.0	39.0	38.3	38.0	38.3
85°	20.6	20.1	21.2	20.1	20.6	19.4	20.6
87.5°	11.2	11.4	11.3	11.1	10.9	12.0	10.9
90°	26.9	28.0	30.1	29.0	30.1	31.1	30.1
92.5°	69.2	61.1	55.7	53.9	50.7	51.8	49.9
95°	252.8	197.9	160.6	140.9	131.6	124.3	120.2
97.5°	744.7	611.1	487.1	410.7	364.1	336.1	327.2
100°	1137.6	1016.4	869.2	764.6	688.9	648.5	649.6
102.5°	1315.7	1245.1	1151.8	1070.4	1010.6	976.8	953.0
105°	1450.5	1470.2	1443.2	1395.5	1356.2	1323.0	1317.9
107.5°	1433.4	1524.2	1561.1	1561.9	1548.6	1537.5	1527.9
110°	1378.0	1508.5	1581.0	1610.0	1618.3	1616.2	1614.2



TEST NUMBER: P332356-940

CATALOG NUMBER: S123RDIP-S1000D1195U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1305.0	1451.3	1544.5	1597.6	1623.3	1631.1	1631.6
115°	1188.3	1340.6	1453.6	1531.2	1576.8	1597.6	1602.8
117.5°	1089.7	1226.5	1341.0	1422.1	1474.3	1504.1	1511.2
120°	1035.0	1159.3	1264.0	1345.8	1403.8	1428.7	1434.9
122.5°	991.0	1106.3	1203.5	1276.2	1328.4	1355.8	1363.6
125°	936.6	1036.0	1118.9	1185.3	1230.8	1256.7	1264.0
127.5°	888.7	978.4	1053.8	1112.9	1151.8	1175.3	1181.9
130°	858.9	942.8	1013.3	1068.2	1105.5	1127.2	1135.5
132.5°	830.7	908.8	976.0	1027.5	1064.8	1084.1	1089.9
135°	790.5	857.8	916.9	967.7	998.7	1017.4	1024.7
137.5°	751.7	809.8	860.9	903.7	935.1	950.8	955.6
140°	729.3	779.1	823.7	863.0	892.1	908.6	907.6
142.5°	707.8	750.9	789.7	823.2	848.9	863.8	862.8
145°	679.7	712.8	742.8	768.7	790.5	798.8	800.8
147.5°	658.7	685.5	706.8	726.5	741.2	749.0	749.8
150°	645.4	667.2	686.9	702.4	713.8	720.1	720.1
152.5°	633.0	652.3	668.7	680.9	691.4	695.2	695.2
155°	615.4	631.0	643.4	652.7	661.0	663.1	664.1
157.5°	598.2	610.2	619.9	628.0	634.3	635.9	635.7
160°	587.5	597.8	605.0	612.3	618.5	618.5	617.5
162.5°	575.9	585.3	591.7	596.6	601.9	601.9	600.9
165°	559.5	566.7	571.9	576.0	580.1	579.2	579.2
167.5°	546.8	551.0	554.7	556.5	559.5	558.4	558.4
170°	537.7	541.8	543.9	544.9	547.1	546.0	546.0
172.5°	530.2	533.6	534.8	535.0	537.1	535.2	534.4
175°	520.0	522.2	522.2	522.2	523.2	522.2	521.1
177.5°	514.2	515.1	515.1	514.2	515.1	513.4	513.4
180°	511.8	511.8	511.8	511.8	511.8	511.8	511.8

(END OF REPORT)