

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332364-940

Luminaire Tested: **S123RDIP-S1165D365U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332364-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1165D365U940-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5017.0 lumens
Efficiency: N/A
Efficacy: 100.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 49.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332364-940

CATALOG NUMBER: S123RDIP-S1165D365U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332364-940

CATALOG NUMBER: S123RDIP-S1165D365U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	109	109	109	109	99	99	99	90	90	90	82	82	82	78
1	105	100	96	93	100	96	92	89	88	85	82	80	78	76	73	72	70	67
2	96	88	82	77	91	84	79	74	77	73	69	71	67	64	65	62	60	57
3	88	78	71	65	83	75	68	63	69	63	59	63	59	55	58	54	51	48
4	80	69	61	55	77	67	59	54	61	55	51	57	52	48	52	48	45	42
5	74	62	54	48	71	60	52	47	55	49	44	51	46	42	47	43	39	37
6	69	56	48	42	65	54	46	41	50	44	39	46	41	37	43	38	35	32
7	64	51	43	37	61	49	42	36	46	39	35	42	37	33	39	35	31	29
8	59	47	39	33	57	45	38	32	42	36	31	39	34	30	36	32	28	26
9	55	43	35	30	53	41	34	29	39	32	28	36	31	27	34	29	26	24
10	52	40	32	27	50	38	31	27	36	30	25	33	28	24	31	27	23	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18603	18603	18603
5°	18674	18416	18522
10°	18569	18185	18124
15°	18369	17761	17572
20°	18095	17228	16827
25°	17813	16631	16098
30°	17439	15940	15070
35°	17056	15251	14127
40°	16703	14436	12960
45°	16238	13633	11905
50°	15726	12722	10727
55°	15204	11678	9627
60°	14725	10562	8420
65°	14103	9352	7210
70°	13322	7852	5822
75°	12181	6180	5481
80°	10860	5473	5040
85°	9176	4841	4508



TEST NUMBER: P332364-940

CATALOG NUMBER: S123RDIP-S1165D365U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.3	3.2
10°-20°	451.6	9.0
20°-30°	650.2	13.0
30°-40°	732.4	14.6
40°-50°	700.7	14.0
50°-60°	573.8	11.4
60°-70°	387.1	7.7
70°-80°	194.8	3.9
80°-90°	52.7	1.1
90°-100°	26.1	0.5
100°-110°	78.2	1.6
110°-120°	133.0	2.7
120°-130°	175.0	3.5
130°-140°	196.7	3.9
140°-150°	193.3	3.9
150°-160°	162.8	3.2
160°-170°	108.3	2.2
170°-180°	37.9	0.8
0°-30°	1264.1	25.2
0°-40°	1996.5	39.8
0°-60°	3270.9	65.2
0°-90°	3905.5	77.8
90°-120°	237.4	4.7
90°-150°	802.4	16.0
90°-180°	1111.0	22.1
0°-180°	5017.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1728	1728	1728	1728	1728	
5°	1728	1721	1704	1716	1714	164
15°	1648	1632	1594	1587	1577	464
25°	1500	1463	1400	1372	1355	689
35°	1298	1246	1161	1102	1075	812
45°	1067	1001	896	818	782	823
55°	810	739	622	544	513	726
65°	554	475	367	302	283	548
75°	293	225	149	135	132	312
85°	74	45	39	37	36	83
90°	0	4	8	9	10	5
95°	19	21	23	24	25	21
105°	71	72	74	74	75	76
115°	134	135	134	135	134	132
125°	196	197	196	195	194	175
135°	254	256	256	255	254	196
145°	308	309	310	310	308	193
155°	353	353	354	355	353	163
165°	385	384	384	386	384	108
175°	400	399	399	401	399	38
180°	401	401	401	401	401	



TEST NUMBER: P332364-940

CATALOG NUMBER: S123RDIP-S1165D365U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3
2.5°	1733.9	1732.9	1731.9	1730.9	1729.9	1727.9	1724.9	1721.9	1719.0	1715.9	1718.7
5°	1728.3	1726.7	1725.2	1723.6	1722.1	1719.4	1715.7	1711.9	1708.2	1704.4	1707.3
7.5°	1712.3	1710.7	1709.0	1707.3	1705.6	1702.3	1697.5	1692.6	1687.7	1682.8	1684.4
10°	1698.9	1696.7	1694.5	1692.3	1690.1	1686.2	1680.6	1675.0	1669.4	1663.8	1664.1
12.5°	1679.8	1677.4	1674.9	1672.5	1670.1	1665.4	1658.6	1651.7	1644.8	1638.0	1637.8
15°	1648.4	1644.9	1641.6	1638.1	1634.7	1628.6	1619.9	1611.1	1602.4	1593.8	1592.1
17.5°	1608.8	1604.9	1600.9	1596.9	1593.0	1585.4	1574.3	1563.2	1552.1	1541.1	1537.8
20°	1579.7	1574.8	1569.8	1564.8	1559.8	1551.4	1539.5	1527.7	1515.8	1504.0	1499.9
22.5°	1547.2	1541.4	1535.7	1530.0	1524.3	1515.1	1502.5	1490.0	1477.4	1464.7	1459.7
25°	1499.8	1492.0	1484.3	1476.4	1468.6	1457.6	1443.2	1429.0	1414.6	1400.3	1393.7
27.5°	1442.3	1433.8	1425.1	1416.6	1407.9	1395.7	1379.7	1363.8	1347.8	1331.9	1322.8
30°	1403.1	1393.7	1384.4	1375.0	1365.7	1352.3	1334.9	1317.4	1300.0	1282.5	1271.9
32.5°	1363.9	1353.3	1342.6	1332.0	1321.5	1307.0	1288.5	1270.1	1251.6	1233.2	1221.6
35°	1298.0	1286.7	1275.5	1264.4	1253.1	1237.9	1218.5	1199.3	1179.9	1160.6	1147.2
37.5°	1231.3	1218.8	1206.3	1193.8	1181.4	1164.8	1144.2	1123.6	1103.0	1082.4	1067.2
40°	1188.7	1174.9	1161.2	1147.5	1133.8	1115.9	1093.8	1071.7	1049.5	1027.4	1011.2
42.5°	1140.4	1126.7	1113.0	1099.3	1085.6	1067.3	1044.5	1021.5	998.7	975.9	958.1
45°	1066.7	1052.7	1038.7	1024.7	1010.6	991.6	967.6	943.6	919.6	895.6	877.9
47.5°	992.9	977.6	962.2	946.8	931.4	911.7	887.7	863.7	839.7	815.8	796.5
50°	939.1	924.5	909.8	895.2	880.6	860.7	835.4	810.2	785.0	759.7	740.4
52.5°	890.9	875.0	859.2	843.3	827.3	806.9	781.9	757.0	732.0	707.0	687.0
55°	810.2	794.9	779.6	764.4	749.1	728.3	701.8	675.3	648.8	622.3	604.3
57.5°	735.6	719.0	702.3	685.7	669.1	647.5	620.9	594.2	567.7	541.1	524.0
60°	684.0	666.9	649.8	632.7	615.5	594.0	568.1	542.3	516.5	490.6	473.8
62.5°	632.4	615.3	598.2	581.0	563.9	542.4	516.6	490.7	464.8	439.0	423.2
65°	553.7	536.5	519.4	502.3	485.2	464.4	440.1	415.8	391.6	367.2	352.0
67.5°	474.9	457.5	440.2	422.9	405.6	385.3	362.0	338.7	315.4	292.1	280.7
70°	423.3	406.5	389.7	372.8	356.1	336.7	315.0	293.1	271.3	249.5	238.6
72.5°	371.8	355.2	338.6	322.0	305.4	287.2	267.4	247.6	227.8	208.0	199.1
75°	292.9	278.0	263.1	248.1	233.2	217.1	200.0	182.8	165.7	148.6	145.4
77.5°	221.1	207.7	194.1	180.7	167.1	154.8	143.8	132.8	121.7	110.8	109.1
80°	175.2	162.5	149.6	136.9	124.1	114.5	107.9	101.4	94.9	88.3	87.4
82.5°	131.4	120.5	109.4	98.4	87.4	80.3	77.3	74.2	71.2	68.1	67.1
85°	74.3	67.4	60.5	53.8	46.9	43.0	42.1	41.1	40.2	39.2	38.6
87.5°	27.0	24.3	21.8	19.2	16.6	15.3	15.5	15.7	15.9	16.1	15.9
90°	0.4	1.0	1.7	2.4	3.1	3.9	4.8	5.7	6.7	7.6	7.8
92.5°	7.7	8.1	8.6	9.1	9.5	10.0	10.5	11.1	11.6	12.1	12.3
95°	18.6	19.1	19.5	20.1	20.5	21.0	21.7	22.2	22.7	23.4	23.6
97.5°	33.0	33.3	33.8	34.2	34.5	34.9	35.3	35.7	36.1	36.5	36.8
100°	42.9	43.2	43.7	44.1	44.5	44.9	45.3	45.7	46.0	46.3	46.5
102.5°	54.2	54.5	54.7	54.9	55.2	55.6	56.0	56.5	57.0	57.4	57.6
105°	70.9	71.1	71.2	71.3	71.4	71.9	72.5	73.1	73.7	74.4	74.4
107.5°	90.3	90.4	90.5	90.6	90.7	90.8	91.0	91.3	91.6	91.8	92.0
110°	102.5	102.5	102.7	102.8	103.0	103.1	103.3	103.4	103.5	103.7	104.0



TEST NUMBER: P332364-940

CATALOG NUMBER: S123RDIP-S1165D365U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	115.0	115.1	115.2	115.3	115.4	115.4	115.5	115.5	115.5	115.6	115.8
115°	133.9	134.1	134.4	134.6	134.7	134.8	134.6	134.6	134.4	134.2	134.3
117.5°	152.9	153.1	153.3	153.4	153.6	153.5	153.3	153.1	152.9	152.8	152.8
120°	164.8	165.2	165.7	166.0	166.5	166.5	166.2	165.9	165.5	165.1	165.1
122.5°	177.2	177.5	177.8	178.1	178.4	178.4	178.3	178.1	177.9	177.7	177.5
125°	196.0	196.2	196.4	196.6	196.9	196.9	196.7	196.6	196.4	196.4	196.0
127.5°	213.4	213.8	214.3	214.7	215.2	215.3	215.2	215.0	214.9	214.7	214.4
130°	225.0	225.5	226.1	226.7	227.2	227.4	227.2	227.0	226.8	226.6	226.3
132.5°	236.6	237.2	237.7	238.3	238.8	239.1	238.9	238.7	238.5	238.4	238.1
135°	254.3	254.8	255.1	255.6	256.0	256.2	256.1	256.0	255.9	255.9	255.6
137.5°	270.7	271.1	271.3	271.7	272.1	272.3	272.5	272.7	272.9	273.0	272.8
140°	282.0	282.4	282.8	283.1	283.5	283.7	283.7	283.7	283.8	283.9	283.8
142.5°	292.4	292.7	293.1	293.5	293.7	294.0	294.2	294.3	294.4	294.5	294.4
145°	308.5	308.6	308.8	308.9	309.1	309.2	309.4	309.7	309.9	310.0	310.0
147.5°	322.6	322.9	323.2	323.4	323.6	323.9	324.0	324.2	324.4	324.7	324.7
150°	332.4	332.6	332.7	332.9	333.1	333.1	333.3	333.4	333.6	333.7	333.7
152.5°	340.5	340.7	340.9	341.1	341.3	341.4	341.5	341.6	341.7	341.8	341.9
155°	353.3	353.3	353.3	353.3	353.3	353.3	353.4	353.4	353.5	353.6	353.8
157.5°	364.1	364.0	363.9	363.8	363.7	363.7	363.8	363.8	363.9	364.0	364.3
160°	370.9	370.8	370.6	370.5	370.3	370.2	370.2	370.2	370.2	370.2	370.6
162.5°	376.9	376.7	376.6	376.4	376.1	376.1	376.1	376.2	376.3	376.3	376.7
165°	384.8	384.6	384.3	384.1	383.9	383.8	383.8	383.8	383.8	383.8	384.2
167.5°	391.0	390.7	390.5	390.1	389.9	389.8	389.9	389.9	389.9	390.0	390.4
170°	394.5	394.2	394.0	393.7	393.4	393.2	393.2	393.2	393.2	393.2	393.8
172.5°	397.3	397.0	396.7	396.5	396.2	396.0	396.0	396.0	396.0	396.0	396.5
175°	400.2	399.9	399.7	399.4	399.1	399.0	399.0	399.0	399.0	399.0	399.4
177.5°	401.4	401.2	400.9	400.7	400.5	400.4	400.4	400.4	400.4	400.4	400.7
180°	401.2	401.2	401.2	401.2	401.2	401.2	401.2	401.2	401.2	401.2	401.2



TEST NUMBER: P332364-940

CATALOG NUMBER: S123RDIP-S1165D365U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3
2.5°	1721.4	1724.2	1726.9	1728.0	1727.5	1727.1	1726.5	1726.0
5°	1710.0	1712.9	1715.7	1716.7	1716.1	1715.5	1714.8	1714.2
7.5°	1686.0	1687.6	1689.1	1689.3	1688.3	1687.2	1686.1	1685.1
10°	1664.5	1664.7	1665.1	1664.5	1662.9	1661.3	1659.7	1658.2
12.5°	1637.6	1637.4	1637.3	1636.3	1634.5	1632.6	1630.8	1629.1
15°	1590.6	1589.0	1587.5	1585.6	1583.4	1581.3	1579.0	1576.9
17.5°	1534.5	1531.1	1527.8	1524.6	1521.3	1518.0	1514.8	1511.5
20°	1495.9	1491.8	1487.8	1483.9	1480.2	1476.4	1472.7	1469.0
22.5°	1454.6	1449.7	1444.6	1440.3	1436.8	1433.3	1429.9	1426.4
25°	1387.2	1380.6	1374.1	1369.1	1365.7	1362.3	1358.9	1355.4
27.5°	1313.7	1304.6	1295.5	1288.3	1283.1	1277.9	1272.6	1267.4
30°	1261.3	1250.8	1240.2	1232.4	1227.4	1222.4	1217.5	1212.5
32.5°	1210.1	1198.5	1186.9	1178.5	1173.2	1168.0	1162.8	1157.5
35°	1133.8	1120.4	1107.1	1097.5	1091.9	1086.3	1080.7	1075.1
37.5°	1052.0	1036.8	1021.5	1010.5	1003.6	996.7	989.8	982.8
40°	995.1	978.8	962.7	951.0	943.8	936.7	929.5	922.3
42.5°	940.5	922.7	905.1	893.0	886.6	880.2	873.8	867.4
45°	860.1	842.4	824.7	812.1	804.6	797.1	789.6	782.1
47.5°	777.1	757.9	738.5	725.6	718.9	712.2	705.5	698.9
50°	721.1	701.8	682.4	669.2	662.1	654.9	647.7	640.6
52.5°	666.9	646.8	626.8	613.5	607.1	600.7	594.3	587.9
55°	586.2	568.1	550.1	538.0	531.7	525.5	519.2	513.0
57.5°	506.9	489.8	472.8	461.5	456.3	451.0	445.7	440.4
60°	456.9	440.1	423.3	412.2	407.0	401.6	396.4	391.1
62.5°	407.3	391.6	375.7	365.1	359.4	353.9	348.4	342.9
65°	336.7	321.5	306.2	296.9	293.5	290.0	286.6	283.1
67.5°	269.3	257.9	246.5	239.0	235.3	231.6	227.9	224.3
70°	227.7	216.8	205.9	198.8	195.3	191.9	188.4	185.0
72.5°	190.2	181.3	172.4	167.2	165.8	164.3	162.9	161.5
75°	142.3	139.2	136.1	134.3	133.7	133.0	132.4	131.8
77.5°	107.4	105.7	104.0	102.8	102.2	101.6	100.9	100.3
80°	86.4	85.5	84.5	83.8	83.2	82.6	81.9	81.3
82.5°	66.3	65.4	64.4	63.8	63.8	63.6	63.5	63.4
85°	38.0	37.4	36.7	36.5	36.5	36.5	36.5	36.5
87.5°	15.7	15.5	15.3	15.1	14.9	14.6	14.4	14.3
90°	8.1	8.4	8.6	8.9	9.0	9.2	9.3	9.5
92.5°	12.6	12.8	13.0	13.1	13.0	12.9	12.8	12.8
95°	23.9	24.2	24.4	24.6	24.6	24.6	24.6	24.6
97.5°	37.1	37.5	37.8	37.9	37.9	37.9	37.8	37.8
100°	46.7	47.0	47.2	47.3	47.4	47.6	47.8	47.9
102.5°	57.9	58.1	58.2	58.3	58.3	58.3	58.2	58.2
105°	74.4	74.4	74.4	74.5	74.5	74.7	74.9	75.0
107.5°	92.3	92.5	92.7	92.8	92.7	92.6	92.6	92.5
110°	104.2	104.5	104.8	104.9	104.7	104.6	104.4	104.3



TEST NUMBER: P332364-940

CATALOG NUMBER: S123RDIP-S1165D365U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	116.2	116.5	116.9	117.0	117.0	117.0	116.9	116.9
115°	134.4	134.5	134.6	134.6	134.5	134.4	134.3	134.2
117.5°	152.8	152.8	152.8	152.6	152.4	152.2	152.0	151.9
120°	165.0	164.9	164.9	164.7	164.6	164.4	164.3	164.2
122.5°	177.4	177.2	177.0	176.8	176.6	176.4	176.2	176.0
125°	195.7	195.5	195.2	194.9	194.7	194.4	194.0	193.8
127.5°	213.9	213.6	213.1	212.8	212.5	212.1	211.9	211.5
130°	226.0	225.7	225.4	225.1	224.6	224.1	223.6	223.1
132.5°	237.7	237.4	237.1	236.7	236.3	235.9	235.6	235.2
135°	255.3	255.0	254.8	254.6	254.4	254.2	254.1	254.0
137.5°	272.5	272.2	271.9	271.6	271.3	271.1	270.8	270.5
140°	283.7	283.7	283.7	283.4	282.9	282.4	281.9	281.4
142.5°	294.4	294.3	294.3	294.0	293.6	293.3	292.8	292.5
145°	310.0	309.9	309.8	309.6	309.3	309.1	308.8	308.5
147.5°	324.7	324.7	324.7	324.4	324.0	323.6	323.2	322.7
150°	333.7	333.7	333.7	333.5	333.1	332.7	332.3	331.8
152.5°	342.0	342.1	342.2	342.1	341.7	341.3	341.0	340.6
155°	354.1	354.4	354.7	354.5	354.1	353.6	353.1	352.6
157.5°	364.5	364.9	365.2	365.1	364.7	364.4	363.9	363.6
160°	371.0	371.3	371.7	371.7	371.4	371.1	370.9	370.6
162.5°	377.0	377.4	377.7	377.6	377.2	376.7	376.3	375.9
165°	384.7	385.0	385.5	385.5	385.0	384.5	384.0	383.5
167.5°	390.8	391.3	391.7	391.7	391.3	390.8	390.4	390.0
170°	394.2	394.8	395.2	395.2	394.8	394.2	393.8	393.2
172.5°	396.9	397.3	397.8	397.8	397.3	396.8	396.3	395.8
175°	399.8	400.2	400.6	400.6	400.1	399.6	399.1	398.6
177.5°	401.1	401.4	401.7	401.7	401.4	400.9	400.6	400.1
180°	401.2	401.2	401.2	401.2	401.2	401.2	401.2	401.2

(END OF REPORT)