

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332260-940

Luminaire Tested: **S123RDIP-S340D1025U940-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332260-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S340D1025U940-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1025 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4519.8 lumens
Efficiency: N/A
Efficacy: 121.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 37.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332260-940

CATALOG NUMBER: S123RDIP-S340D1025U940-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332260-940

CATALOG NUMBER: S123RDIP-S340D1025U940-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	35	35	35	27
1	93	89	85	82	83	79	76	74	62	60	58	46	45	44	31	31	30	23
2	85	78	72	67	76	70	65	61	55	51	49	41	39	37	28	27	26	20
3	77	69	62	56	69	62	56	51	48	44	41	36	34	32	25	23	22	17
4	71	61	53	48	63	55	48	44	43	39	35	32	30	27	22	21	19	15
5	65	54	47	41	58	49	42	37	39	34	30	29	26	24	20	18	17	13
6	60	49	41	35	53	44	37	32	35	30	27	26	23	21	18	17	15	12
7	55	44	36	31	49	40	33	28	32	27	23	24	21	18	17	15	13	11
8	51	40	32	27	46	36	29	25	29	24	21	22	19	16	16	14	12	10
9	48	36	29	24	43	33	27	22	26	22	18	20	17	15	14	12	11	9
10	44	33	26	22	40	30	24	20	24	20	17	19	15	13	13	11	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5224	5224	5224	5224
5°	6227	5246	4620	5246
10°	7774	5216	4173	5216
15°	9126	5162	3806	5162
20°	10186	5082	3494	5082
25°	10023	4999	3301	4999
30°	7204	4922	3104	4922
35°	4809	4820	2975	4820
40°	3544	4700	2843	4700
45°	2973	4488	2714	4488
50°	2624	4210	2532	4210
55°	2301	3890	2284	3890
60°	2047	3587	2093	3587
65°	1798	3260	1946	3260
70°	1413	2968	1778	2968
75°	1243	2591	1626	2591
80°	1085	2201	1599	2201
85°	865	1778	1692	1778



TEST NUMBER: P332260-940

CATALOG NUMBER: S123RDIP-S340D1025U940-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.7	1.1
10°-20°	149.1	3.3
20°-30°	234.2	5.2
30°-40°	244.4	5.4
40°-50°	209.1	4.6
50°-60°	159.4	3.5
60°-70°	102.2	2.3
70°-80°	49.1	1.1
80°-90°	16.4	0.4
90°-100°	244.7	5.4
100°-110°	692.9	15.3
110°-120°	681.6	15.1
120°-130°	543.7	12.0
130°-140°	428.7	9.5
140°-150°	319.9	7.1
150°-160°	223.0	4.9
160°-170°	131.0	2.9
170°-180°	42.6	0.9
0°-30°	431.1	9.5
0°-40°	675.4	14.9
0°-60°	1044.0	23.1
0°-90°	1211.7	26.8
90°-120°	1619.2	35.8
90°-150°	2911.5	64.4
90°-180°	3308.0	73.2
0°-180°	4519.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	485	485	485	485	485	
5°	576	486	428	486	576	59
15°	819	463	342	463	819	232
25°	844	421	278	421	844	363
35°	366	367	226	367	366	240
45°	195	295	178	295	195	154
55°	123	207	122	207	123	111
65°	71	128	76	128	71	69
75°	30	62	39	62	30	32
85°	7	14	14	14	7	9
90°	26	2	26	2	26	14
95°	103	30	103	30	103	186
105°	1132	103	1132	103	1132	1117
115°	1377	182	1377	182	1377	1338
125°	1086	254	1086	254	1086	984
135°	880	297	880	297	880	683
145°	688	339	688	339	688	438
155°	570	385	570	385	570	266
165°	498	421	498	421	498	142
175°	448	439	448	439	448	43
180°	440	440	440	440	440	



TEST NUMBER: P332260-940

CATALOG NUMBER: S123RDIP-S340D1025U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3
2.5°	516.9	517.5	515.4	515.1	512.6	511.9	511.9	508.4	506.2	503.5	501.8
5°	576.3	579.6	577.9	574.3	568.0	566.5	562.6	556.3	549.3	540.6	536.5
7.5°	650.5	655.1	653.3	647.6	641.0	635.7	624.6	614.2	599.8	587.0	576.1
10°	711.3	706.6	702.8	697.2	691.2	681.4	669.8	653.8	635.3	620.7	604.6
12.5°	756.9	756.1	751.4	745.6	737.1	727.8	713.5	694.0	672.5	651.5	632.9
15°	818.9	820.2	817.1	811.1	799.0	782.6	761.0	752.9	722.1	699.3	676.5
17.5°	861.9	861.7	861.2	852.9	840.6	828.9	808.9	787.6	759.7	727.5	696.8
20°	889.2	887.1	887.5	878.2	869.1	855.5	836.0	805.0	782.2	745.0	713.2
22.5°	888.5	888.1	889.7	886.4	879.9	869.5	854.1	828.0	798.8	761.3	725.5
25°	843.9	842.2	851.9	854.7	865.3	867.2	862.6	848.3	820.6	781.9	737.7
27.5°	706.2	705.3	723.4	746.2	774.9	797.3	818.9	829.3	820.6	792.9	748.6
30°	579.6	599.1	608.3	641.1	677.7	721.3	759.6	795.9	804.9	792.7	756.4
32.5°	481.3	498.3	506.0	534.0	568.2	619.3	676.6	728.1	764.5	773.6	751.8
35°	366.0	366.2	383.7	396.2	427.8	480.3	536.0	604.9	673.5	725.5	730.8
37.5°	292.1	293.1	303.7	316.1	339.8	367.6	416.6	473.9	553.1	632.8	679.7
40°	252.2	254.0	262.0	274.2	291.2	312.3	350.4	404.5	470.6	559.3	631.8
42.5°	226.6	229.6	233.7	243.2	253.7	273.4	304.3	346.0	406.1	490.0	573.6
45°	195.3	197.0	200.1	204.5	214.0	227.7	248.4	276.5	326.4	393.9	477.6
47.5°	172.3	171.4	174.7	178.2	184.6	193.9	207.9	230.7	266.3	320.5	391.5
50°	156.7	156.4	158.7	161.4	167.5	174.3	185.7	203.0	231.2	276.1	341.2
52.5°	142.0	142.8	144.5	147.8	152.1	157.7	167.9	180.4	204.6	243.3	297.6
55°	122.6	123.2	125.5	127.3	130.5	136.1	142.5	152.9	169.5	196.5	241.2
57.5°	106.1	105.8	108.0	108.5	112.0	116.5	121.5	129.7	141.7	161.8	191.8
60°	95.1	94.5	96.4	97.8	99.7	103.4	107.6	115.5	125.1	139.8	165.6
62.5°	85.2	84.9	86.2	87.7	89.3	92.6	96.1	102.2	109.8	122.2	142.7
65°	70.6	71.2	71.9	72.5	73.3	75.4	78.7	82.9	88.1	96.8	111.6
67.5°	55.6	56.2	56.4	57.6	59.4	60.7	62.8	66.4	70.1	77.4	85.8
70°	44.9	44.7	44.9	45.5	47.8	50.0	52.8	55.5	57.8	63.0	70.0
72.5°	38.5	38.2	38.7	38.9	39.9	40.6	42.3	44.9	47.8	51.3	56.4
75°	29.9	29.9	29.9	29.9	30.8	31.1	31.7	32.4	33.4	35.1	38.9
77.5°	22.1	22.1	22.5	22.6	22.8	23.1	23.5	24.1	24.4	25.3	26.9
80°	17.5	17.7	17.5	17.7	17.7	18.1	18.3	18.9	19.1	20.2	20.8
82.5°	13.1	13.0	13.1	13.4	13.4	13.7	13.8	14.3	14.3	14.8	15.4
85°	7.0	6.7	7.0	6.9	7.3	6.9	7.0	7.5	7.5	7.7	8.6
87.5°	6.9	7.3	6.9	6.8	7.0	6.8	6.6	6.4	6.6	6.6	6.2
90°	25.8	26.7	25.8	24.9	25.8	24.1	23.2	22.3	21.4	22.3	19.6
92.5°	42.9	44.5	43.6	46.3	47.9	52.5	59.5	74.9	103.3	136.9	150.6
95°	103.3	106.8	113.1	121.1	137.9	170.0	217.2	320.4	428.1	527.8	469.9
97.5°	281.1	288.7	312.8	352.8	418.5	525.0	639.8	798.8	875.1	818.0	598.9
100°	558.1	557.2	591.9	656.9	746.8	873.2	977.3	1049.5	1018.2	842.9	569.6
102.5°	818.7	839.2	868.2	919.6	989.6	1069.7	1130.4	1132.7	1025.4	796.7	526.9
105°	1132.2	1136.7	1165.1	1198.9	1239.9	1263.0	1246.2	1157.1	971.1	715.6	474.4
107.5°	1312.7	1320.9	1330.5	1341.9	1341.2	1309.5	1231.5	1087.0	876.0	644.1	441.0
110°	1386.8	1388.6	1390.4	1383.2	1358.3	1295.9	1183.8	1020.0	816.2	603.5	428.1



TEST NUMBER: P332260-940

CATALOG NUMBER: S123RDIP-S340D1025U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1401.7	1401.3	1394.5	1372.5	1327.0	1246.8	1121.1	953.8	764.2	576.4	421.0
115°	1377.0	1372.5	1354.7	1315.5	1248.8	1151.7	1020.9	866.0	701.4	547.4	418.3
117.5°	1298.2	1292.3	1266.6	1221.7	1152.1	1053.6	936.2	802.5	663.4	530.3	419.9
120°	1232.8	1227.4	1206.0	1156.2	1085.9	996.0	889.2	769.0	643.5	522.5	422.8
122.5°	1171.5	1164.8	1141.3	1096.4	1033.9	950.5	851.5	742.7	627.1	517.5	427.8
125°	1085.9	1079.7	1057.4	1018.2	961.3	890.1	804.7	707.7	606.2	511.0	435.2
127.5°	1015.4	1009.7	989.6	956.1	905.4	840.6	763.5	677.0	587.6	507.7	443.8
130°	975.5	968.4	949.8	917.7	870.5	809.9	737.9	657.8	577.7	505.6	449.5
132.5°	936.4	931.4	914.8	882.8	838.5	780.8	713.6	640.0	568.4	504.9	453.8
135°	880.3	874.1	858.0	831.3	787.7	737.0	679.1	615.9	556.3	503.8	460.2
137.5°	821.0	816.9	803.4	776.3	739.7	695.7	645.9	594.1	545.8	501.9	464.4
140°	779.7	780.6	766.3	741.5	707.7	669.3	626.6	581.2	539.4	501.1	467.3
142.5°	741.3	742.2	729.3	707.3	678.4	645.2	608.1	569.1	533.7	499.7	469.4
145°	688.0	686.3	679.1	660.4	638.2	612.3	583.9	554.6	526.0	497.6	470.8
147.5°	644.3	643.5	636.8	624.1	607.3	588.9	565.9	542.6	518.5	494.2	470.8
150°	618.6	618.6	613.2	603.5	590.1	573.2	554.6	534.0	513.5	491.3	470.8
152.5°	597.3	597.3	594.1	585.0	574.4	560.4	543.9	526.2	507.9	487.8	468.7
155°	570.5	569.6	567.8	560.8	552.8	542.1	528.7	514.4	499.4	481.5	466.4
157.5°	546.2	546.4	544.9	539.6	532.6	524.2	513.9	502.0	489.7	476.0	463.4
160°	530.5	531.4	531.4	526.0	519.8	513.5	504.7	494.9	483.3	471.7	462.0
162.5°	516.2	517.1	517.1	512.6	508.5	502.9	494.7	486.3	476.9	467.4	459.1
165°	497.6	497.6	498.5	494.9	491.3	486.9	480.6	475.3	468.1	461.1	454.9
167.5°	479.7	479.7	480.6	478.1	476.5	473.3	469.8	465.7	459.9	454.7	450.6
170°	469.0	469.0	469.9	468.1	467.3	465.5	462.0	459.3	454.9	450.4	447.7
172.5°	459.1	459.9	461.5	459.7	459.5	458.4	455.6	453.6	449.9	446.8	445.6
175°	447.7	448.6	449.5	448.6	448.6	448.6	446.8	445.9	444.2	442.4	442.4
177.5°	441.1	441.1	442.6	441.8	442.6	442.6	441.8	441.1	440.4	439.7	440.4
180°	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7



TEST NUMBER: P332260-940

CATALOG NUMBER: S123RDIP-S340D1025U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3
2.5°	501.1	500.6	498.3	495.6	492.1	489.8	487.9	487.0	483.9	480.3	477.9
5°	532.1	525.8	519.2	511.0	503.5	495.9	491.2	485.5	478.7	471.0	465.6
7.5°	565.2	552.9	539.8	526.2	512.8	500.8	490.1	481.0	470.1	459.1	451.4
10°	590.7	572.7	554.3	535.4	518.2	501.9	489.5	477.2	464.1	451.5	441.8
12.5°	613.8	590.2	568.9	545.6	523.6	504.3	486.3	471.9	456.1	442.6	431.8
15°	643.0	618.8	593.2	557.8	528.5	504.0	482.1	463.2	444.2	427.6	417.0
17.5°	670.3	634.1	599.4	570.0	531.9	501.3	474.7	452.1	431.1	413.5	400.4
20°	681.6	646.5	608.9	571.3	534.0	499.6	468.7	443.7	422.0	402.0	389.9
22.5°	688.4	648.7	609.0	568.6	529.0	493.3	462.7	435.2	411.6	392.7	377.8
25°	696.3	649.0	605.4	565.5	525.0	486.3	450.0	420.9	395.4	375.2	359.4
27.5°	701.6	645.9	594.3	550.0	508.9	470.5	437.1	406.3	380.3	359.0	342.1
30°	702.6	643.4	585.9	537.9	496.1	460.7	425.4	396.0	368.5	345.9	330.1
32.5°	703.9	637.2	574.4	523.4	480.6	445.7	413.7	385.5	357.4	335.1	319.0
35°	698.5	633.8	557.0	498.4	455.6	421.7	392.9	366.8	339.3	317.6	301.2
37.5°	674.8	620.4	539.0	470.2	425.4	394.1	370.6	347.9	322.6	299.3	283.8
40°	651.1	607.1	525.0	453.1	406.4	374.2	352.9	334.5	310.0	288.1	271.5
42.5°	615.7	588.9	511.7	435.2	384.8	353.7	335.8	318.5	297.0	274.8	259.2
45°	550.7	554.3	484.5	406.5	354.8	323.7	306.8	294.8	275.7	257.4	241.4
47.5°	469.3	502.3	452.5	376.1	323.3	294.1	279.4	268.9	255.9	238.0	223.4
50°	416.2	463.2	427.0	355.7	303.5	274.5	259.9	251.4	240.1	226.0	212.1
52.5°	367.1	417.8	396.0	332.9	282.0	255.5	241.3	234.3	225.3	212.0	199.5
55°	299.3	350.7	345.7	298.5	249.9	226.0	215.3	207.3	201.3	191.4	181.4
57.5°	242.2	290.8	293.4	260.3	221.6	198.0	188.7	182.7	178.8	171.3	162.0
60°	206.1	250.7	259.5	234.5	201.3	180.6	171.4	166.6	163.5	157.5	150.4
62.5°	176.2	214.2	224.1	206.2	181.9	162.4	155.2	150.7	148.6	143.4	137.1
65°	134.8	166.4	175.9	166.0	153.3	137.8	131.9	128.0	126.1	123.2	118.6
67.5°	101.4	124.4	134.9	127.9	123.2	113.4	109.8	107.6	105.9	104.0	100.1
70°	81.4	98.4	109.2	107.5	103.7	98.4	95.8	94.3	92.6	91.0	87.7
72.5°	65.5	77.2	87.3	88.3	85.2	84.2	81.8	81.1	80.2	78.2	76.3
75°	43.4	51.5	58.6	61.3	62.5	63.6	62.5	62.3	62.2	60.5	59.4
77.5°	28.4	32.8	37.3	41.9	43.9	45.2	45.6	46.4	45.7	44.9	44.4
80°	21.8	22.8	25.9	29.9	33.0	34.2	35.1	35.5	35.3	35.1	34.2
82.5°	15.9	16.7	18.2	21.0	23.5	25.6	26.1	26.0	26.5	26.7	25.9
85°	8.6	8.7	9.2	9.5	11.0	13.3	13.9	14.4	14.7	14.7	13.5
87.5°	6.1	5.4	5.2	4.8	4.9	4.5	5.2	5.7	6.2	5.9	6.4
90°	16.9	14.3	11.6	9.8	8.0	5.4	3.6	1.8	3.6	5.4	8.0
92.5°	113.1	74.7	51.5	38.3	30.8	23.9	16.4	11.1	16.4	23.9	30.8
95°	324.0	191.4	115.7	81.0	57.9	42.7	32.9	30.2	32.9	42.7	57.9
97.5°	355.5	206.0	133.7	96.1	73.3	60.2	52.5	51.6	52.5	60.2	73.3
100°	335.6	203.8	141.5	106.8	85.4	73.0	66.8	65.9	66.8	73.0	85.4
102.5°	318.4	206.7	150.8	119.0	99.7	87.9	82.4	80.8	82.4	87.9	99.7
105°	306.2	214.5	166.5	138.8	122.0	111.3	105.9	103.3	105.9	111.3	122.0
107.5°	305.3	229.1	186.9	161.3	145.4	134.9	129.7	127.1	129.7	134.9	145.4
110°	308.9	241.2	201.2	176.2	161.1	151.3	146.9	144.2	146.9	151.3	161.1



TEST NUMBER: P332260-940

CATALOG NUMBER: S123RDIP-S340D1025U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	316.0	253.3	216.2	191.9	176.7	167.0	162.6	159.9	162.6	167.0	176.7
115°	327.5	273.2	239.4	215.4	200.3	191.4	186.0	182.4	186.0	191.4	200.3
117.5°	342.9	294.4	261.0	238.7	221.8	213.7	209.2	205.1	209.2	213.7	221.8
120°	354.3	308.0	275.9	253.7	236.7	227.8	223.4	220.7	223.4	227.8	236.7
122.5°	365.0	322.2	290.9	267.2	251.0	241.4	236.9	234.3	236.9	241.4	251.0
125°	381.8	342.7	311.6	287.5	270.5	260.8	255.5	253.7	255.5	260.8	270.5
127.5°	395.7	360.5	330.4	306.4	287.7	277.7	271.1	268.5	271.1	277.7	287.7
130°	405.0	371.1	341.8	317.7	299.1	288.4	280.4	277.7	280.4	288.4	299.1
132.5°	413.6	380.4	351.8	328.4	309.8	296.9	288.2	284.8	288.2	296.9	309.8
135°	424.5	394.3	366.7	342.7	324.0	310.7	300.9	297.3	300.9	310.7	324.0
137.5°	432.7	403.9	377.4	355.2	336.6	322.4	312.8	309.1	312.8	322.4	336.6
140°	437.0	410.4	384.5	362.3	344.5	330.2	321.3	316.9	321.3	330.2	344.5
142.5°	441.3	415.4	390.2	369.3	351.6	338.8	329.1	325.4	329.1	338.8	351.6
145°	445.9	421.9	398.8	378.3	363.2	349.8	341.8	339.1	341.8	349.8	363.2
147.5°	448.8	427.2	406.1	388.6	374.0	362.5	354.6	353.0	354.6	362.5	374.0
150°	449.5	430.8	410.4	394.3	381.8	370.2	363.2	362.3	363.2	370.2	381.8
152.5°	450.9	432.9	415.4	400.0	389.0	378.8	371.7	371.5	371.7	378.8	389.0
155°	451.3	437.0	421.9	409.5	399.7	390.7	385.4	385.4	385.4	390.7	399.7
157.5°	452.2	439.3	427.2	417.6	409.3	401.4	397.2	396.5	397.2	401.4	409.3
160°	452.2	441.5	430.8	421.9	415.6	408.6	405.0	405.0	405.0	408.6	415.6
162.5°	451.5	442.2	432.9	425.4	419.9	414.3	411.4	411.4	411.4	414.3	419.9
165°	449.5	443.3	436.1	429.9	426.3	421.9	420.1	421.0	420.1	421.9	426.3
167.5°	448.1	443.1	437.9	434.0	431.5	428.1	427.2	428.3	427.2	428.1	431.5
170°	445.9	442.4	437.9	436.1	434.4	431.7	430.8	432.6	430.8	431.7	434.4
172.5°	445.2	442.4	438.6	437.6	436.5	434.5	434.4	435.4	434.4	434.5	436.5
175°	443.3	441.5	439.7	438.8	438.8	437.0	437.9	438.8	437.9	437.0	438.8
177.5°	441.8	440.4	439.7	439.7	439.7	439.0	439.7	440.4	439.7	439.0	439.7
180°	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7



TEST NUMBER: P332260-940

CATALOG NUMBER: S123RDIP-S340D1025U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3
2.5°	477.0	474.8	473.3	470.0	467.9	465.6	463.2	464.7	464.5	464.4	464.4
5°	461.0	456.2	451.8	446.2	442.7	438.4	435.1	434.6	435.4	432.6	430.9
7.5°	445.1	438.6	432.4	426.2	419.6	414.4	411.2	409.6	407.5	405.7	403.9
10°	434.0	426.3	420.3	412.6	405.6	399.3	395.4	392.6	391.2	389.8	387.0
12.5°	422.5	415.0	407.3	398.6	391.9	384.7	381.7	378.7	375.9	374.3	370.6
15°	405.7	396.0	387.9	378.7	371.2	364.2	360.1	354.0	353.2	351.1	347.3
17.5°	388.9	378.4	367.1	360.3	352.0	344.6	338.2	336.3	330.3	328.1	324.8
20°	375.6	365.9	357.3	348.4	336.2	329.3	324.3	321.6	316.8	313.9	311.8
22.5°	364.2	354.2	344.4	333.9	323.9	316.1	312.5	308.3	305.7	301.6	299.3
25°	347.8	337.0	325.1	313.9	306.7	300.9	295.0	291.2	287.5	285.6	281.5
27.5°	328.8	317.4	306.4	297.8	288.9	283.2	277.9	274.6	270.1	267.0	264.7
30°	318.3	305.0	295.4	287.8	276.3	270.9	267.0	262.8	259.5	256.2	253.9
32.5°	306.1	294.0	285.0	275.4	266.7	260.7	255.7	252.0	249.1	246.0	243.7
35°	287.1	277.0	267.6	258.1	251.6	245.6	239.5	236.4	233.7	230.8	228.7
37.5°	269.9	260.4	251.5	242.5	234.4	229.5	224.7	222.3	218.6	216.7	214.6
40°	259.3	249.9	240.4	231.7	223.4	219.6	215.3	211.7	208.4	206.9	204.6
42.5°	247.6	238.3	230.2	220.9	214.0	208.9	204.9	201.1	198.6	196.4	195.2
45°	230.4	222.1	214.2	204.8	198.4	194.0	189.5	185.9	183.7	182.2	179.9
47.5°	213.7	205.4	197.3	189.2	183.0	178.0	173.3	170.9	167.9	166.1	164.6
50°	201.5	194.0	185.6	178.1	171.8	166.8	163.1	160.0	157.3	155.0	153.9
52.5°	190.4	182.4	175.0	168.1	161.5	155.9	152.5	149.2	147.1	144.5	143.3
55°	172.0	164.3	158.1	151.2	144.8	140.0	135.9	133.0	130.9	128.0	126.4
57.5°	154.8	147.8	140.4	134.5	127.9	123.9	120.4	116.5	113.9	111.6	109.9
60°	143.1	135.3	128.8	123.2	117.3	112.2	109.1	105.9	103.3	100.9	99.5
62.5°	131.0	124.1	118.0	111.9	106.6	102.0	98.4	95.9	93.5	92.0	90.5
65°	112.4	107.0	100.8	95.8	90.8	87.5	84.5	82.3	80.6	79.5	78.3
67.5°	95.2	90.1	84.6	79.7	76.3	73.8	72.0	70.0	69.1	67.8	67.0
70°	84.2	78.7	73.9	70.2	66.9	65.0	63.8	62.3	61.5	59.8	59.0
72.5°	72.1	68.1	64.6	61.6	58.9	57.2	55.6	53.9	52.5	50.6	49.8
75°	56.7	53.1	50.5	48.4	46.7	44.5	42.2	40.3	39.7	39.1	38.9
77.5°	42.0	39.8	37.8	36.0	34.0	32.4	31.8	31.4	31.3	30.9	30.9
80°	33.0	30.9	29.5	27.5	26.2	26.2	26.2	25.8	25.9	25.9	25.9
82.5°	24.5	22.6	21.8	21.1	20.9	21.0	21.0	21.1	21.0	21.3	21.1
85°	12.7	12.8	13.3	13.1	13.3	13.3	13.7	13.5	13.7	13.3	13.7
87.5°	6.6	7.5	8.2	8.8	9.5	9.9	9.9	10.1	10.4	10.6	11.0
90°	9.8	11.6	14.3	16.9	19.6	22.3	21.4	22.3	23.2	24.1	25.8
92.5°	38.3	51.5	74.7	113.1	150.6	136.9	103.3	74.9	59.5	52.5	47.9
95°	81.0	115.7	191.4	324.0	469.9	527.8	428.1	320.4	217.2	170.0	137.9
97.5°	96.1	133.7	206.0	355.5	598.9	818.0	875.1	798.8	639.8	525.0	418.5
100°	106.8	141.5	203.8	335.6	569.6	842.9	1018.2	1049.5	977.3	873.2	746.8
102.5°	119.0	150.8	206.7	318.4	526.9	796.7	1025.4	1132.7	1130.4	1069.7	989.6
105°	138.8	166.5	214.5	306.2	474.4	715.6	971.1	1157.1	1246.2	1263.0	1239.9
107.5°	161.3	186.9	229.1	305.3	441.0	644.1	876.0	1087.0	1231.5	1309.5	1341.2
110°	176.2	201.2	241.2	308.9	428.1	603.5	816.2	1020.0	1183.8	1295.9	1358.3



TEST NUMBER: P332260-940

CATALOG NUMBER: S123RDIP-S340D1025U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	191.9	216.2	253.3	316.0	421.0	576.4	764.2	953.8	1121.1	1246.8	1327.0
115°	215.4	239.4	273.2	327.5	418.3	547.4	701.4	866.0	1020.9	1151.7	1248.8
117.5°	238.7	261.0	294.4	342.9	419.9	530.3	663.4	802.5	936.2	1053.6	1152.1
120°	253.7	275.9	308.0	354.3	422.8	522.5	643.5	769.0	889.2	996.0	1085.9
122.5°	267.2	290.9	322.2	365.0	427.8	517.5	627.1	742.7	851.5	950.5	1033.9
125°	287.5	311.6	342.7	381.8	435.2	511.0	606.2	707.7	804.7	890.1	961.3
127.5°	306.4	330.4	360.5	395.7	443.8	507.7	587.6	677.0	763.5	840.6	905.4
130°	317.7	341.8	371.1	405.0	449.5	505.6	577.7	657.8	737.9	809.9	870.5
132.5°	328.4	351.8	380.4	413.6	453.8	504.9	568.4	640.0	713.6	780.8	838.5
135°	342.7	366.7	394.3	424.5	460.2	503.8	556.3	615.9	679.1	737.0	787.7
137.5°	355.2	377.4	403.9	432.7	464.4	501.9	545.8	594.1	645.9	695.7	739.7
140°	362.3	384.5	410.4	437.0	467.3	501.1	539.4	581.2	626.6	669.3	707.7
142.5°	369.3	390.2	415.4	441.3	469.4	499.7	533.7	569.1	608.1	645.2	678.4
145°	378.3	398.8	421.9	445.9	470.8	497.6	526.0	554.6	583.9	612.3	638.2
147.5°	388.6	406.1	427.2	448.8	470.8	494.2	518.5	542.6	565.9	588.9	607.3
150°	394.3	410.4	430.8	449.5	470.8	491.3	513.5	534.0	554.6	573.2	590.1
152.5°	400.0	415.4	432.9	450.9	468.7	487.8	507.9	526.2	543.9	560.4	574.4
155°	409.5	421.9	437.0	451.3	466.4	481.5	499.4	514.4	528.7	542.1	552.8
157.5°	417.6	427.2	439.3	452.2	463.4	476.0	489.7	502.0	513.9	524.2	532.6
160°	421.9	430.8	441.5	452.2	462.0	471.7	483.3	494.9	504.7	513.5	519.8
162.5°	425.4	432.9	442.2	451.5	459.1	467.4	476.9	486.3	494.7	502.9	508.5
165°	429.9	436.1	443.3	449.5	454.9	461.1	468.1	475.3	480.6	486.9	491.3
167.5°	434.0	437.9	443.1	448.1	450.6	454.7	459.9	465.7	469.8	473.3	476.5
170°	436.1	437.9	442.4	445.9	447.7	450.4	454.9	459.3	462.0	465.5	467.3
172.5°	437.6	438.6	442.4	445.2	445.6	446.8	449.9	453.6	455.6	458.4	459.5
175°	438.8	439.7	441.5	443.3	442.4	442.4	444.2	445.9	446.8	448.6	448.6
177.5°	439.7	439.7	440.4	441.8	440.4	439.7	440.4	441.1	441.8	442.6	442.6
180°	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7



TEST NUMBER: P332260-940

CATALOG NUMBER: S123RDIP-S340D1025U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3
2.5°	462.4	462.2	462.4	461.7	462.4	462.2	462.4	464.4	464.4	464.5	464.7
5°	430.3	430.1	429.4	427.6	429.4	430.1	430.3	430.9	432.6	435.4	434.6
7.5°	402.2	401.9	400.1	400.1	400.1	401.9	402.2	403.9	405.7	407.5	409.6
10°	385.6	385.8	383.3	381.8	383.3	385.8	385.6	387.0	389.8	391.2	392.6
12.5°	369.4	368.5	366.5	364.9	366.5	368.5	369.4	370.6	374.3	375.9	378.7
15°	348.2	346.1	341.2	341.5	341.2	346.1	348.2	347.3	351.1	353.2	354.0
17.5°	323.2	321.6	321.6	318.6	321.6	321.6	323.2	324.8	328.1	330.3	336.3
20°	308.5	307.5	307.9	305.0	307.9	307.5	308.5	311.8	313.9	316.8	321.6
22.5°	297.0	296.0	294.3	293.4	294.3	296.0	297.0	299.3	301.6	305.7	308.3
25°	280.3	278.6	277.0	277.9	277.0	278.6	280.3	281.5	285.6	287.5	291.2
27.5°	263.5	262.3	260.6	260.4	260.6	262.3	263.5	264.7	267.0	270.1	274.6
30°	252.8	251.6	250.7	249.7	250.7	251.6	252.8	253.9	256.2	259.5	262.8
32.5°	242.0	241.7	240.3	240.0	240.3	241.7	242.0	243.7	246.0	249.1	252.0
35°	227.9	226.7	226.2	226.4	226.2	226.7	227.9	228.7	230.8	233.7	236.4
37.5°	214.5	212.9	212.0	211.3	212.0	212.9	214.5	214.6	216.7	218.6	222.3
40°	204.8	203.2	202.8	202.3	202.8	203.2	204.8	204.6	206.9	208.4	211.7
42.5°	194.0	193.4	193.1	192.3	193.1	193.4	194.0	195.2	196.4	198.6	201.1
45°	179.3	179.1	177.8	178.3	177.8	179.1	179.3	179.9	182.2	183.7	185.9
47.5°	163.7	162.8	161.9	162.6	161.9	162.8	163.7	164.6	166.1	167.9	170.9
50°	153.1	152.7	150.8	151.2	150.8	152.7	153.1	153.9	155.0	157.3	160.0
52.5°	142.5	140.9	140.2	139.9	140.2	140.9	142.5	143.3	144.5	147.1	149.2
55°	124.8	123.0	122.2	121.7	122.2	123.0	124.8	126.4	128.0	130.9	133.0
57.5°	107.5	107.1	106.4	106.8	106.4	107.1	107.5	109.9	111.6	113.9	116.5
60°	97.5	97.5	97.5	97.2	97.5	97.5	97.5	99.5	100.9	103.3	105.9
62.5°	89.6	89.1	89.0	89.3	89.0	89.1	89.6	90.5	92.0	93.5	95.9
65°	77.7	77.5	76.7	76.4	76.7	77.5	77.7	78.3	79.5	80.6	82.3
67.5°	66.4	65.7	65.5	65.2	65.5	65.7	66.4	67.0	67.8	69.1	70.0
70°	58.0	57.5	56.3	56.5	56.3	57.5	58.0	59.0	59.8	61.5	62.3
72.5°	48.9	48.4	48.2	47.9	48.2	48.4	48.9	49.8	50.6	52.5	53.9
75°	38.6	38.4	38.3	39.1	38.3	38.4	38.6	38.9	39.1	39.7	40.3
77.5°	30.9	30.9	31.1	30.8	31.1	30.9	30.9	30.9	30.9	31.3	31.4
80°	25.9	25.9	25.8	25.8	25.8	25.9	25.9	25.9	25.9	25.9	25.8
82.5°	20.8	21.0	21.1	20.8	21.1	21.0	20.8	21.1	21.3	21.0	21.1
85°	13.7	13.5	13.9	13.7	13.9	13.5	13.7	13.7	13.3	13.7	13.5
87.5°	11.1	11.0	11.1	11.1	11.1	11.0	11.1	11.0	10.6	10.4	10.1
90°	24.9	25.8	26.7	25.8	26.7	25.8	24.9	25.8	24.1	23.2	22.3
92.5°	46.3	43.6	44.5	42.9	44.5	43.6	46.3	47.9	52.5	59.5	74.9
95°	121.1	113.1	106.8	103.3	106.8	113.1	121.1	137.9	170.0	217.2	320.4
97.5°	352.8	312.8	288.7	281.1	288.7	312.8	352.8	418.5	525.0	639.8	798.8
100°	656.9	591.9	557.2	558.1	557.2	591.9	656.9	746.8	873.2	977.3	1049.5
102.5°	919.6	868.2	839.2	818.7	839.2	868.2	919.6	989.6	1069.7	1130.4	1132.7
105°	1198.9	1165.1	1136.7	1132.2	1136.7	1165.1	1198.9	1239.9	1263.0	1246.2	1157.1
107.5°	1341.9	1330.5	1320.9	1312.7	1320.9	1330.5	1341.9	1341.2	1309.5	1231.5	1087.0
110°	1383.2	1390.4	1388.6	1386.8	1388.6	1390.4	1383.2	1358.3	1295.9	1183.8	1020.0



TEST NUMBER: P332260-940

CATALOG NUMBER: S123RDIP-S340D1025U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1372.5	1394.5	1401.3	1401.7	1401.3	1394.5	1372.5	1327.0	1246.8	1121.1	953.8
115°	1315.5	1354.7	1372.5	1377.0	1372.5	1354.7	1315.5	1248.8	1151.7	1020.9	866.0
117.5°	1221.7	1266.6	1292.3	1298.2	1292.3	1266.6	1221.7	1152.1	1053.6	936.2	802.5
120°	1156.2	1206.0	1227.4	1232.8	1227.4	1206.0	1156.2	1085.9	996.0	889.2	769.0
122.5°	1096.4	1141.3	1164.8	1171.5	1164.8	1141.3	1096.4	1033.9	950.5	851.5	742.7
125°	1018.2	1057.4	1079.7	1085.9	1079.7	1057.4	1018.2	961.3	890.1	804.7	707.7
127.5°	956.1	989.6	1009.7	1015.4	1009.7	989.6	956.1	905.4	840.6	763.5	677.0
130°	917.7	949.8	968.4	975.5	968.4	949.8	917.7	870.5	809.9	737.9	657.8
132.5°	882.8	914.8	931.4	936.4	931.4	914.8	882.8	838.5	780.8	713.6	640.0
135°	831.3	858.0	874.1	880.3	874.1	858.0	831.3	787.7	737.0	679.1	615.9
137.5°	776.3	803.4	816.9	821.0	816.9	803.4	776.3	739.7	695.7	645.9	594.1
140°	741.5	766.3	780.6	779.7	780.6	766.3	741.5	707.7	669.3	626.6	581.2
142.5°	707.3	729.3	742.2	741.3	742.2	729.3	707.3	678.4	645.2	608.1	569.1
145°	660.4	679.1	686.3	688.0	686.3	679.1	660.4	638.2	612.3	583.9	554.6
147.5°	624.1	636.8	643.5	644.3	643.5	636.8	624.1	607.3	588.9	565.9	542.6
150°	603.5	613.2	618.6	618.6	618.6	613.2	603.5	590.1	573.2	554.6	534.0
152.5°	585.0	594.1	597.3	597.3	597.3	594.1	585.0	574.4	560.4	543.9	526.2
155°	560.8	567.8	569.6	570.5	569.6	567.8	560.8	552.8	542.1	528.7	514.4
157.5°	539.6	544.9	546.4	546.2	546.4	544.9	539.6	532.6	524.2	513.9	502.0
160°	526.0	531.4	531.4	530.5	531.4	531.4	526.0	519.8	513.5	504.7	494.9
162.5°	512.6	517.1	517.1	516.2	517.1	517.1	512.6	508.5	502.9	494.7	486.3
165°	494.9	498.5	497.6	497.6	497.6	498.5	494.9	491.3	486.9	480.6	475.3
167.5°	478.1	480.6	479.7	479.7	479.7	480.6	478.1	476.5	473.3	469.8	465.7
170°	468.1	469.9	469.0	469.0	469.0	469.9	468.1	467.3	465.5	462.0	459.3
172.5°	459.7	461.5	459.9	459.1	459.9	461.5	459.7	459.5	458.4	455.6	453.6
175°	448.6	449.5	448.6	447.7	448.6	449.5	448.6	448.6	448.6	446.8	445.9
177.5°	441.8	442.6	441.1	441.1	441.1	442.6	441.8	442.6	442.6	441.8	441.1
180°	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7



TEST NUMBER: P332260-940

CATALOG NUMBER: S123RDIP-S340D1025U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3
2.5°	463.2	465.6	467.9	470.0	473.3	474.8	477.0	477.9	480.3	483.9	487.0
5°	435.1	438.4	442.7	446.2	451.8	456.2	461.0	465.6	471.0	478.7	485.5
7.5°	411.2	414.4	419.6	426.2	432.4	438.6	445.1	451.4	459.1	470.1	481.0
10°	395.4	399.3	405.6	412.6	420.3	426.3	434.0	441.8	451.5	464.1	477.2
12.5°	381.7	384.7	391.9	398.6	407.3	415.0	422.5	431.8	442.6	456.1	471.9
15°	360.1	364.2	371.2	378.7	387.9	396.0	405.7	417.0	427.6	444.2	463.2
17.5°	338.2	344.6	352.0	360.3	367.1	378.4	388.9	400.4	413.5	431.1	452.1
20°	324.3	329.3	336.2	348.4	357.3	365.9	375.6	389.9	402.0	422.0	443.7
22.5°	312.5	316.1	323.9	333.9	344.4	354.2	364.2	377.8	392.7	411.6	435.2
25°	295.0	300.9	306.7	313.9	325.1	337.0	347.8	359.4	375.2	395.4	420.9
27.5°	277.9	283.2	288.9	297.8	306.4	317.4	328.8	342.1	359.0	380.3	406.3
30°	267.0	270.9	276.3	287.8	295.4	305.0	318.3	330.1	345.9	368.5	396.0
32.5°	255.7	260.7	266.7	275.4	285.0	294.0	306.1	319.0	335.1	357.4	385.5
35°	239.5	245.6	251.6	258.1	267.6	277.0	287.1	301.2	317.6	339.3	366.8
37.5°	224.7	229.5	234.4	242.5	251.5	260.4	269.9	283.8	299.3	322.6	347.9
40°	215.3	219.6	223.4	231.7	240.4	249.9	259.3	271.5	288.1	310.0	334.5
42.5°	204.9	208.9	214.0	220.9	230.2	238.3	247.6	259.2	274.8	297.0	318.5
45°	189.5	194.0	198.4	204.8	214.2	222.1	230.4	241.4	257.4	275.7	294.8
47.5°	173.3	178.0	183.0	189.2	197.3	205.4	213.7	223.4	238.0	255.9	268.9
50°	163.1	166.8	171.8	178.1	185.6	194.0	201.5	212.1	226.0	240.1	251.4
52.5°	152.5	155.9	161.5	168.1	175.0	182.4	190.4	199.5	212.0	225.3	234.3
55°	135.9	140.0	144.8	151.2	158.1	164.3	172.0	181.4	191.4	201.3	207.3
57.5°	120.4	123.9	127.9	134.5	140.4	147.8	154.8	162.0	171.3	178.8	182.7
60°	109.1	112.2	117.3	123.2	128.8	135.3	143.1	150.4	157.5	163.5	166.6
62.5°	98.4	102.0	106.6	111.9	118.0	124.1	131.0	137.1	143.4	148.6	150.7
65°	84.5	87.5	90.8	95.8	100.8	107.0	112.4	118.6	123.2	126.1	128.0
67.5°	72.0	73.8	76.3	79.7	84.6	90.1	95.2	100.1	104.0	105.9	107.6
70°	63.8	65.0	66.9	70.2	73.9	78.7	84.2	87.7	91.0	92.6	94.3
72.5°	55.6	57.2	58.9	61.6	64.6	68.1	72.1	76.3	78.2	80.2	81.1
75°	42.2	44.5	46.7	48.4	50.5	53.1	56.7	59.4	60.5	62.2	62.3
77.5°	31.8	32.4	34.0	36.0	37.8	39.8	42.0	44.4	44.9	45.7	46.4
80°	26.2	26.2	26.2	27.5	29.5	30.9	33.0	34.2	35.1	35.3	35.5
82.5°	21.0	21.0	20.9	21.1	21.8	22.6	24.5	25.9	26.7	26.5	26.0
85°	13.7	13.3	13.3	13.1	13.3	12.8	12.7	13.5	14.7	14.7	14.4
87.5°	9.9	9.9	9.5	8.8	8.2	7.5	6.6	6.4	5.9	6.2	5.7
90°	21.4	22.3	19.6	16.9	14.3	11.6	9.8	8.0	5.4	3.6	1.8
92.5°	103.3	136.9	150.6	113.1	74.7	51.5	38.3	30.8	23.9	16.4	11.1
95°	428.1	527.8	469.9	324.0	191.4	115.7	81.0	57.9	42.7	32.9	30.2
97.5°	875.1	818.0	598.9	355.5	206.0	133.7	96.1	73.3	60.2	52.5	51.6
100°	1018.2	842.9	569.6	335.6	203.8	141.5	106.8	85.4	73.0	66.8	65.9
102.5°	1025.4	796.7	526.9	318.4	206.7	150.8	119.0	99.7	87.9	82.4	80.8
105°	971.1	715.6	474.4	306.2	214.5	166.5	138.8	122.0	111.3	105.9	103.3
107.5°	876.0	644.1	441.0	305.3	229.1	186.9	161.3	145.4	134.9	129.7	127.1
110°	816.2	603.5	428.1	308.9	241.2	201.2	176.2	161.1	151.3	146.9	144.2



TEST NUMBER: P332260-940

CATALOG NUMBER: S123RDIP-S340D1025U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	764.2	576.4	421.0	316.0	253.3	216.2	191.9	176.7	167.0	162.6	159.9
115°	701.4	547.4	418.3	327.5	273.2	239.4	215.4	200.3	191.4	186.0	182.4
117.5°	663.4	530.3	419.9	342.9	294.4	261.0	238.7	221.8	213.7	209.2	205.1
120°	643.5	522.5	422.8	354.3	308.0	275.9	253.7	236.7	227.8	223.4	220.7
122.5°	627.1	517.5	427.8	365.0	322.2	290.9	267.2	251.0	241.4	236.9	234.3
125°	606.2	511.0	435.2	381.8	342.7	311.6	287.5	270.5	260.8	255.5	253.7
127.5°	587.6	507.7	443.8	395.7	360.5	330.4	306.4	287.7	277.7	271.1	268.5
130°	577.7	505.6	449.5	405.0	371.1	341.8	317.7	299.1	288.4	280.4	277.7
132.5°	568.4	504.9	453.8	413.6	380.4	351.8	328.4	309.8	296.9	288.2	284.8
135°	556.3	503.8	460.2	424.5	394.3	366.7	342.7	324.0	310.7	300.9	297.3
137.5°	545.8	501.9	464.4	432.7	403.9	377.4	355.2	336.6	322.4	312.8	309.1
140°	539.4	501.1	467.3	437.0	410.4	384.5	362.3	344.5	330.2	321.3	316.9
142.5°	533.7	499.7	469.4	441.3	415.4	390.2	369.3	351.6	338.8	329.1	325.4
145°	526.0	497.6	470.8	445.9	421.9	398.8	378.3	363.2	349.8	341.8	339.1
147.5°	518.5	494.2	470.8	448.8	427.2	406.1	388.6	374.0	362.5	354.6	353.0
150°	513.5	491.3	470.8	449.5	430.8	410.4	394.3	381.8	370.2	363.2	362.3
152.5°	507.9	487.8	468.7	450.9	432.9	415.4	400.0	389.0	378.8	371.7	371.5
155°	499.4	481.5	466.4	451.3	437.0	421.9	409.5	399.7	390.7	385.4	385.4
157.5°	489.7	476.0	463.4	452.2	439.3	427.2	417.6	409.3	401.4	397.2	396.5
160°	483.3	471.7	462.0	452.2	441.5	430.8	421.9	415.6	408.6	405.0	405.0
162.5°	476.9	467.4	459.1	451.5	442.2	432.9	425.4	419.9	414.3	411.4	411.4
165°	468.1	461.1	454.9	449.5	443.3	436.1	429.9	426.3	421.9	420.1	421.0
167.5°	459.9	454.7	450.6	448.1	443.1	437.9	434.0	431.5	428.1	427.2	428.3
170°	454.9	450.4	447.7	445.9	442.4	437.9	436.1	434.4	431.7	430.8	432.6
172.5°	449.9	446.8	445.6	445.2	442.4	438.6	437.6	436.5	434.5	434.4	435.4
175°	444.2	442.4	442.4	443.3	441.5	439.7	438.8	438.8	437.0	437.9	438.8
177.5°	440.4	439.7	440.4	441.8	440.4	439.7	439.7	439.7	439.0	439.7	440.4
180°	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7



TEST NUMBER: P332260-940

CATALOG NUMBER: S123RDIP-S340D1025U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3
2.5°	487.9	489.8	492.1	495.6	498.3	500.6	501.1	501.8	503.5	506.2	508.4
5°	491.2	495.9	503.5	511.0	519.2	525.8	532.1	536.5	540.6	549.3	556.3
7.5°	490.1	500.8	512.8	526.2	539.8	552.9	565.2	576.1	587.0	599.8	614.2
10°	489.5	501.9	518.2	535.4	554.3	572.7	590.7	604.6	620.7	635.3	653.8
12.5°	486.3	504.3	523.6	545.6	568.9	590.2	613.8	632.9	651.5	672.5	694.0
15°	482.1	504.0	528.5	557.8	593.2	618.8	643.0	676.5	699.3	722.1	752.9
17.5°	474.7	501.3	531.9	570.0	599.4	634.1	670.3	696.8	727.5	759.7	787.6
20°	468.7	499.6	534.0	571.3	608.9	646.5	681.6	713.2	745.0	782.2	805.0
22.5°	462.7	493.3	529.0	568.6	609.0	648.7	688.4	725.5	761.3	798.8	828.0
25°	450.0	486.3	525.0	565.5	605.4	649.0	696.3	737.7	781.9	820.6	848.3
27.5°	437.1	470.5	508.9	550.0	594.3	645.9	701.6	748.6	792.9	820.6	829.3
30°	425.4	460.7	496.1	537.9	585.9	643.4	702.6	756.4	792.7	804.9	795.9
32.5°	413.7	445.7	480.6	523.4	574.4	637.2	703.9	751.8	773.6	764.5	728.1
35°	392.9	421.7	455.6	498.4	557.0	633.8	698.5	730.8	725.5	673.5	604.9
37.5°	370.6	394.1	425.4	470.2	539.0	620.4	674.8	679.7	632.8	553.1	473.9
40°	352.9	374.2	406.4	453.1	525.0	607.1	651.1	631.8	559.3	470.6	404.5
42.5°	335.8	353.7	384.8	435.2	511.7	588.9	615.7	573.6	490.0	406.1	346.0
45°	306.8	323.7	354.8	406.5	484.5	554.3	550.7	477.6	393.9	326.4	276.5
47.5°	279.4	294.1	323.3	376.1	452.5	502.3	469.3	391.5	320.5	266.3	230.7
50°	259.9	274.5	303.5	355.7	427.0	463.2	416.2	341.2	276.1	231.2	203.0
52.5°	241.3	255.5	282.0	332.9	396.0	417.8	367.1	297.6	243.3	204.6	180.4
55°	215.3	226.0	249.9	298.5	345.7	350.7	299.3	241.2	196.5	169.5	152.9
57.5°	188.7	198.0	221.6	260.3	293.4	290.8	242.2	191.8	161.8	141.7	129.7
60°	171.4	180.6	201.3	234.5	259.5	250.7	206.1	165.6	139.8	125.1	115.5
62.5°	155.2	162.4	181.9	206.2	224.1	214.2	176.2	142.7	122.2	109.8	102.2
65°	131.9	137.8	153.3	166.0	175.9	166.4	134.8	111.6	96.8	88.1	82.9
67.5°	109.8	113.4	123.2	127.9	134.9	124.4	101.4	85.8	77.4	70.1	66.4
70°	95.8	98.4	103.7	107.5	109.2	98.4	81.4	70.0	63.0	57.8	55.5
72.5°	81.8	84.2	85.2	88.3	87.3	77.2	65.5	56.4	51.3	47.8	44.9
75°	62.5	63.6	62.5	61.3	58.6	51.5	43.4	38.9	35.1	33.4	32.4
77.5°	45.6	45.2	43.9	41.9	37.3	32.8	28.4	26.9	25.3	24.4	24.1
80°	35.1	34.2	33.0	29.9	25.9	22.8	21.8	20.8	20.2	19.1	18.9
82.5°	26.1	25.6	23.5	21.0	18.2	16.7	15.9	15.4	14.8	14.3	14.3
85°	13.9	13.3	11.0	9.5	9.2	8.7	8.6	8.6	7.7	7.5	7.5
87.5°	5.2	4.5	4.9	4.8	5.2	5.4	6.1	6.2	6.6	6.6	6.4
90°	3.6	5.4	8.0	9.8	11.6	14.3	16.9	19.6	22.3	21.4	22.3
92.5°	16.4	23.9	30.8	38.3	51.5	74.7	113.1	150.6	136.9	103.3	74.9
95°	32.9	42.7	57.9	81.0	115.7	191.4	324.0	469.9	527.8	428.1	320.4
97.5°	52.5	60.2	73.3	96.1	133.7	206.0	355.5	598.9	818.0	875.1	798.8
100°	66.8	73.0	85.4	106.8	141.5	203.8	335.6	569.6	842.9	1018.2	1049.5
102.5°	82.4	87.9	99.7	119.0	150.8	206.7	318.4	526.9	796.7	1025.4	1132.7
105°	105.9	111.3	122.0	138.8	166.5	214.5	306.2	474.4	715.6	971.1	1157.1
107.5°	129.7	134.9	145.4	161.3	186.9	229.1	305.3	441.0	644.1	876.0	1087.0
110°	146.9	151.3	161.1	176.2	201.2	241.2	308.9	428.1	603.5	816.2	1020.0



TEST NUMBER: P332260-940

CATALOG NUMBER: S123RDIP-S340D1025U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	162.6	167.0	176.7	191.9	216.2	253.3	316.0	421.0	576.4	764.2	953.8
115°	186.0	191.4	200.3	215.4	239.4	273.2	327.5	418.3	547.4	701.4	866.0
117.5°	209.2	213.7	221.8	238.7	261.0	294.4	342.9	419.9	530.3	663.4	802.5
120°	223.4	227.8	236.7	253.7	275.9	308.0	354.3	422.8	522.5	643.5	769.0
122.5°	236.9	241.4	251.0	267.2	290.9	322.2	365.0	427.8	517.5	627.1	742.7
125°	255.5	260.8	270.5	287.5	311.6	342.7	381.8	435.2	511.0	606.2	707.7
127.5°	271.1	277.7	287.7	306.4	330.4	360.5	395.7	443.8	507.7	587.6	677.0
130°	280.4	288.4	299.1	317.7	341.8	371.1	405.0	449.5	505.6	577.7	657.8
132.5°	288.2	296.9	309.8	328.4	351.8	380.4	413.6	453.8	504.9	568.4	640.0
135°	300.9	310.7	324.0	342.7	366.7	394.3	424.5	460.2	503.8	556.3	615.9
137.5°	312.8	322.4	336.6	355.2	377.4	403.9	432.7	464.4	501.9	545.8	594.1
140°	321.3	330.2	344.5	362.3	384.5	410.4	437.0	467.3	501.1	539.4	581.2
142.5°	329.1	338.8	351.6	369.3	390.2	415.4	441.3	469.4	499.7	533.7	569.1
145°	341.8	349.8	363.2	378.3	398.8	421.9	445.9	470.8	497.6	526.0	554.6
147.5°	354.6	362.5	374.0	388.6	406.1	427.2	448.8	470.8	494.2	518.5	542.6
150°	363.2	370.2	381.8	394.3	410.4	430.8	449.5	470.8	491.3	513.5	534.0
152.5°	371.7	378.8	389.0	400.0	415.4	432.9	450.9	468.7	487.8	507.9	526.2
155°	385.4	390.7	399.7	409.5	421.9	437.0	451.3	466.4	481.5	499.4	514.4
157.5°	397.2	401.4	409.3	417.6	427.2	439.3	452.2	463.4	476.0	489.7	502.0
160°	405.0	408.6	415.6	421.9	430.8	441.5	452.2	462.0	471.7	483.3	494.9
162.5°	411.4	414.3	419.9	425.4	432.9	442.2	451.5	459.1	467.4	476.9	486.3
165°	420.1	421.9	426.3	429.9	436.1	443.3	449.5	454.9	461.1	468.1	475.3
167.5°	427.2	428.1	431.5	434.0	437.9	443.1	448.1	450.6	454.7	459.9	465.7
170°	430.8	431.7	434.4	436.1	437.9	442.4	445.9	447.7	450.4	454.9	459.3
172.5°	434.4	434.5	436.5	437.6	438.6	442.4	445.2	445.6	446.8	449.9	453.6
175°	437.9	437.0	438.8	438.8	439.7	441.5	443.3	442.4	442.4	444.2	445.9
177.5°	439.7	439.0	439.7	439.7	439.7	440.4	441.8	440.4	439.7	440.4	441.1
180°	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7



TEST NUMBER: P332260-940

CATALOG NUMBER: S123RDIP-S340D1025U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	485.3	485.3	485.3	485.3	485.3	485.3	485.3
2.5°	511.9	511.9	512.6	515.1	515.4	517.5	516.9
5°	562.6	566.5	568.0	574.3	577.9	579.6	576.3
7.5°	624.6	635.7	641.0	647.6	653.3	655.1	650.5
10°	669.8	681.4	691.2	697.2	702.8	706.6	711.3
12.5°	713.5	727.8	737.1	745.6	751.4	756.1	756.9
15°	761.0	782.6	799.0	811.1	817.1	820.2	818.9
17.5°	808.9	828.9	840.6	852.9	861.2	861.7	861.9
20°	836.0	855.5	869.1	878.2	887.5	887.1	889.2
22.5°	854.1	869.5	879.9	886.4	889.7	888.1	888.5
25°	862.6	867.2	865.3	854.7	851.9	842.2	843.9
27.5°	818.9	797.3	774.9	746.2	723.4	705.3	706.2
30°	759.6	721.3	677.7	641.1	608.3	599.1	579.6
32.5°	676.6	619.3	568.2	534.0	506.0	498.3	481.3
35°	536.0	480.3	427.8	396.2	383.7	366.2	366.0
37.5°	416.6	367.6	339.8	316.1	303.7	293.1	292.1
40°	350.4	312.3	291.2	274.2	262.0	254.0	252.2
42.5°	304.3	273.4	253.7	243.2	233.7	229.6	226.6
45°	248.4	227.7	214.0	204.5	200.1	197.0	195.3
47.5°	207.9	193.9	184.6	178.2	174.7	171.4	172.3
50°	185.7	174.3	167.5	161.4	158.7	156.4	156.7
52.5°	167.9	157.7	152.1	147.8	144.5	142.8	142.0
55°	142.5	136.1	130.5	127.3	125.5	123.2	122.6
57.5°	121.5	116.5	112.0	108.5	108.0	105.8	106.1
60°	107.6	103.4	99.7	97.8	96.4	94.5	95.1
62.5°	96.1	92.6	89.3	87.7	86.2	84.9	85.2
65°	78.7	75.4	73.3	72.5	71.9	71.2	70.6
67.5°	62.8	60.7	59.4	57.6	56.4	56.2	55.6
70°	52.8	50.0	47.8	45.5	44.9	44.7	44.9
72.5°	42.3	40.6	39.9	38.9	38.7	38.2	38.5
75°	31.7	31.1	30.8	29.9	29.9	29.9	29.9
77.5°	23.5	23.1	22.8	22.6	22.5	22.1	22.1
80°	18.3	18.1	17.7	17.7	17.5	17.7	17.5
82.5°	13.8	13.7	13.4	13.4	13.1	13.0	13.1
85°	7.0	6.9	7.3	6.9	7.0	6.7	7.0
87.5°	6.6	6.8	7.0	6.8	6.9	7.3	6.9
90°	23.2	24.1	25.8	24.9	25.8	26.7	25.8
92.5°	59.5	52.5	47.9	46.3	43.6	44.5	42.9
95°	217.2	170.0	137.9	121.1	113.1	106.8	103.3
97.5°	639.8	525.0	418.5	352.8	312.8	288.7	281.1
100°	977.3	873.2	746.8	656.9	591.9	557.2	558.1
102.5°	1130.4	1069.7	989.6	919.6	868.2	839.2	818.7
105°	1246.2	1263.0	1239.9	1198.9	1165.1	1136.7	1132.2
107.5°	1231.5	1309.5	1341.2	1341.9	1330.5	1320.9	1312.7
110°	1183.8	1295.9	1358.3	1383.2	1390.4	1388.6	1386.8



TEST NUMBER: P332260-940

CATALOG NUMBER: S123RDIP-S340D1025U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1121.1	1246.8	1327.0	1372.5	1394.5	1401.3	1401.7
115°	1020.9	1151.7	1248.8	1315.5	1354.7	1372.5	1377.0
117.5°	936.2	1053.6	1152.1	1221.7	1266.6	1292.3	1298.2
120°	889.2	996.0	1085.9	1156.2	1206.0	1227.4	1232.8
122.5°	851.5	950.5	1033.9	1096.4	1141.3	1164.8	1171.5
125°	804.7	890.1	961.3	1018.2	1057.4	1079.7	1085.9
127.5°	763.5	840.6	905.4	956.1	989.6	1009.7	1015.4
130°	737.9	809.9	870.5	917.7	949.8	968.4	975.5
132.5°	713.6	780.8	838.5	882.8	914.8	931.4	936.4
135°	679.1	737.0	787.7	831.3	858.0	874.1	880.3
137.5°	645.9	695.7	739.7	776.3	803.4	816.9	821.0
140°	626.6	669.3	707.7	741.5	766.3	780.6	779.7
142.5°	608.1	645.2	678.4	707.3	729.3	742.2	741.3
145°	583.9	612.3	638.2	660.4	679.1	686.3	688.0
147.5°	565.9	588.9	607.3	624.1	636.8	643.5	644.3
150°	554.6	573.2	590.1	603.5	613.2	618.6	618.6
152.5°	543.9	560.4	574.4	585.0	594.1	597.3	597.3
155°	528.7	542.1	552.8	560.8	567.8	569.6	570.5
157.5°	513.9	524.2	532.6	539.6	544.9	546.4	546.2
160°	504.7	513.5	519.8	526.0	531.4	531.4	530.5
162.5°	494.7	502.9	508.5	512.6	517.1	517.1	516.2
165°	480.6	486.9	491.3	494.9	498.5	497.6	497.6
167.5°	469.8	473.3	476.5	478.1	480.6	479.7	479.7
170°	462.0	465.5	467.3	468.1	469.9	469.0	469.0
172.5°	455.6	458.4	459.5	459.7	461.5	459.9	459.1
175°	446.8	448.6	448.6	448.6	449.5	448.6	447.7
177.5°	441.8	442.6	442.6	441.8	442.6	441.1	441.1
180°	439.7	439.7	439.7	439.7	439.7	439.7	439.7

(END OF REPORT)