

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332266-940

Luminaire Tested: **S123RDIP-S340D1195U940-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332266-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S340D1195U940-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1195 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5062.8 lumens
Efficiency: N/A
Efficacy: 120.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 42.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332266-940

CATALOG NUMBER: S123RDIP-S340D1195U940-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332266-940

CATALOG NUMBER: S123RDIP-S340D1195U940-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	32	32	32	24
1	92	88	85	81	82	79	76	73	61	59	57	44	43	42	29	28	28	21
2	84	77	72	67	75	69	64	60	53	50	47	39	37	35	26	25	24	18
3	77	68	61	56	68	61	55	50	47	43	40	35	32	30	23	22	20	15
4	70	60	53	47	62	54	48	43	42	38	34	31	28	26	21	19	18	13
5	65	54	46	40	57	48	42	37	38	33	30	28	25	23	19	17	16	12
6	59	48	40	35	53	43	37	32	34	29	26	25	22	20	17	15	14	11
7	55	43	36	31	49	39	32	28	31	26	23	23	20	17	16	14	12	9
8	51	39	32	27	45	35	29	25	28	23	20	21	18	16	14	12	11	8
9	47	36	29	24	42	32	26	22	25	21	18	19	16	14	13	11	10	8
10	44	33	26	21	39	29	23	19	23	19	16	18	15	13	12	10	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5224	5224	5224	5224
5°	6227	5246	4620	5246
10°	7774	5216	4173	5216
15°	9126	5162	3806	5162
20°	10186	5082	3494	5082
25°	10023	4999	3301	4999
30°	7204	4922	3104	4922
35°	4809	4820	2975	4820
40°	3544	4700	2843	4700
45°	2973	4488	2714	4488
50°	2624	4210	2532	4210
55°	2301	3890	2284	3890
60°	2047	3587	2093	3587
65°	1798	3260	1946	3260
70°	1413	2968	1778	2968
75°	1243	2591	1626	2591
80°	1085	2201	1599	2201
85°	865	1778	1692	1778



TEST NUMBER: P332266-940

CATALOG NUMBER: S123RDIP-S340D1195U940-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.7	0.9
10°-20°	149.1	2.9
20°-30°	234.2	4.6
30°-40°	244.4	4.8
40°-50°	209.1	4.1
50°-60°	159.4	3.1
60°-70°	102.2	2.0
70°-80°	49.1	1.0
80°-90°	17.0	0.3
90°-100°	284.8	5.6
100°-110°	806.5	15.9
110°-120°	793.4	15.7
120°-130°	632.8	12.5
130°-140°	498.9	9.9
140°-150°	372.4	7.4
150°-160°	259.6	5.1
160°-170°	152.5	3.0
170°-180°	49.6	1.0
0°-30°	431.1	8.5
0°-40°	675.4	13.3
0°-60°	1044.0	20.6
0°-90°	1212.3	23.9
90°-120°	1884.7	37.2
90°-150°	3388.9	66.9
90°-180°	3851.0	76.1
0°-180°	5062.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	485	485	485	485	485	
5°	576	486	428	486	576	59
15°	819	463	342	463	819	232
25°	844	421	278	421	844	363
35°	366	367	226	367	366	240
45°	195	295	178	295	195	154
55°	123	207	122	207	123	111
65°	71	128	76	128	71	69
75°	30	62	39	62	30	32
85°	7	14	14	14	7	9
90°	30	2	30	2	30	16
95°	120	35	120	35	120	217
105°	1318	120	1318	120	1318	1300
115°	1603	212	1603	212	1603	1557
125°	1264	295	1264	295	1264	1145
135°	1025	346	1025	346	1025	795
145°	801	395	801	395	801	509
155°	664	449	664	449	664	310
165°	579	490	579	490	579	166
175°	521	511	521	511	521	51
180°	512	512	512	512	512	



TEST NUMBER: P332266-940

CATALOG NUMBER: S123RDIP-S340D1195U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3
2.5°	516.9	517.5	515.4	515.1	512.6	511.9	511.9	508.4	506.2	503.5	501.8
5°	576.3	579.6	577.9	574.3	568.0	566.5	562.6	556.3	549.3	540.6	536.5
7.5°	650.5	655.1	653.3	647.6	641.0	635.7	624.6	614.2	599.8	587.0	576.1
10°	711.3	706.6	702.8	697.2	691.2	681.4	669.8	653.8	635.3	620.7	604.6
12.5°	756.9	756.1	751.4	745.6	737.1	727.8	713.5	694.0	672.5	651.5	632.9
15°	818.9	820.2	817.1	811.1	799.0	782.6	761.0	752.9	722.1	699.3	676.5
17.5°	861.9	861.7	861.2	852.9	840.6	828.9	808.9	787.6	759.7	727.5	696.8
20°	889.2	887.1	887.5	878.2	869.1	855.5	836.0	805.0	782.2	745.0	713.2
22.5°	888.5	888.1	889.7	886.4	879.9	869.5	854.1	828.0	798.8	761.3	725.5
25°	843.9	842.2	851.9	854.7	865.3	867.2	862.6	848.3	820.6	781.9	737.7
27.5°	706.2	705.3	723.4	746.2	774.9	797.3	818.9	829.3	820.6	792.9	748.6
30°	579.6	599.1	608.3	641.1	677.7	721.3	759.6	795.9	804.9	792.7	756.4
32.5°	481.3	498.3	506.0	534.0	568.2	619.3	676.6	728.1	764.5	773.6	751.8
35°	366.0	366.2	383.7	396.2	427.8	480.3	536.0	604.9	673.5	725.5	730.8
37.5°	292.1	293.1	303.7	316.1	339.8	367.6	416.6	473.9	553.1	632.8	679.7
40°	252.2	254.0	262.0	274.2	291.2	312.3	350.4	404.5	470.6	559.3	631.8
42.5°	226.6	229.6	233.7	243.2	253.7	273.4	304.3	346.0	406.1	490.0	573.6
45°	195.3	197.0	200.1	204.5	214.0	227.7	248.4	276.5	326.4	393.9	477.6
47.5°	172.3	171.4	174.7	178.2	184.6	193.9	207.9	230.7	266.3	320.5	391.5
50°	156.7	156.4	158.7	161.4	167.5	174.3	185.7	203.0	231.2	276.1	341.2
52.5°	142.0	142.8	144.5	147.8	152.1	157.7	167.9	180.4	204.6	243.3	297.6
55°	122.6	123.2	125.5	127.3	130.5	136.1	142.5	152.9	169.5	196.5	241.2
57.5°	106.1	105.8	108.0	108.5	112.0	116.5	121.5	129.7	141.7	161.8	191.8
60°	95.1	94.5	96.4	97.8	99.7	103.4	107.6	115.5	125.1	139.8	165.6
62.5°	85.2	84.9	86.2	87.7	89.3	92.6	96.1	102.2	109.8	122.2	142.7
65°	70.6	71.2	71.9	72.5	73.3	75.4	78.7	82.9	88.1	96.8	111.6
67.5°	55.6	56.2	56.4	57.6	59.4	60.7	62.8	66.4	70.1	77.4	85.8
70°	44.9	44.7	44.9	45.5	47.8	50.0	52.8	55.5	57.8	63.0	70.0
72.5°	38.5	38.2	38.7	38.9	39.9	40.6	42.3	44.9	47.8	51.3	56.4
75°	29.9	29.9	29.9	29.9	30.8	31.1	31.7	32.4	33.4	35.1	38.9
77.5°	22.1	22.1	22.5	22.6	22.8	23.1	23.5	24.1	24.4	25.3	26.9
80°	17.5	17.7	17.5	17.7	17.7	18.1	18.3	18.9	19.1	20.2	20.8
82.5°	13.1	13.0	13.1	13.4	13.4	13.7	13.8	14.3	14.3	14.8	15.4
85°	7.0	6.7	7.0	6.9	7.3	6.9	7.0	7.5	7.5	7.7	8.6
87.5°	7.7	8.2	7.7	7.7	7.8	7.6	7.4	7.1	7.3	7.3	6.9
90°	30.1	31.1	30.1	29.0	30.1	28.0	26.9	25.9	24.9	25.9	22.8
92.5°	49.9	51.8	50.7	53.9	55.7	61.1	69.2	87.2	120.2	159.3	175.3
95°	120.2	124.3	131.6	140.9	160.6	197.9	252.8	373.0	498.3	614.4	547.1
97.5°	327.2	336.1	364.1	410.7	487.1	611.1	744.7	929.7	1018.6	952.1	697.1
100°	649.6	648.5	688.9	764.6	869.2	1016.4	1137.6	1221.5	1185.3	981.1	663.1
102.5°	953.0	976.8	1010.6	1070.4	1151.8	1245.1	1315.7	1318.5	1193.5	927.3	613.3
105°	1317.9	1323.0	1356.2	1395.5	1443.2	1470.2	1450.5	1346.8	1130.3	832.9	552.2
107.5°	1527.9	1537.5	1548.6	1561.9	1561.1	1524.2	1433.4	1265.2	1019.7	749.7	513.3
110°	1614.2	1616.2	1618.3	1610.0	1581.0	1508.5	1378.0	1187.3	950.0	702.4	498.3



TEST NUMBER: P332266-940

CATALOG NUMBER: S123RDIP-S340D1195U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1631.6	1631.1	1623.3	1597.6	1544.5	1451.3	1305.0	1110.2	889.6	670.9	490.1
115°	1602.8	1597.6	1576.8	1531.2	1453.6	1340.6	1188.3	1008.1	816.4	637.1	487.0
117.5°	1511.2	1504.1	1474.3	1422.1	1341.0	1226.5	1089.7	934.1	772.2	617.2	488.8
120°	1434.9	1428.7	1403.8	1345.8	1264.0	1159.3	1035.0	895.1	749.0	608.1	492.1
122.5°	1363.6	1355.8	1328.4	1276.2	1203.5	1106.3	991.0	864.4	730.0	602.4	497.9
125°	1264.0	1256.7	1230.8	1185.3	1118.9	1036.0	936.6	823.7	705.5	594.7	506.6
127.5°	1181.9	1175.3	1151.8	1112.9	1053.8	978.4	888.7	788.0	684.0	590.9	516.6
130°	1135.5	1127.2	1105.5	1068.2	1013.3	942.8	858.9	765.6	672.3	588.4	523.2
132.5°	1089.9	1084.1	1064.8	1027.5	976.0	908.8	830.7	744.9	661.6	587.6	528.2
135°	1024.7	1017.4	998.7	967.7	916.9	857.8	790.5	716.9	647.6	586.4	535.7
137.5°	955.6	950.8	935.1	903.7	860.9	809.8	751.7	691.4	635.3	584.1	540.6
140°	907.6	908.6	892.1	863.0	823.7	779.1	729.3	676.5	627.9	583.3	543.9
142.5°	862.8	863.8	848.9	823.2	789.7	750.9	707.8	662.5	621.2	581.7	546.4
145°	800.8	798.8	790.5	768.7	742.8	712.8	679.7	645.4	612.3	579.2	548.0
147.5°	749.8	749.0	741.2	726.5	706.8	685.5	658.7	631.6	603.6	575.2	548.0
150°	720.1	720.1	713.8	702.4	686.9	667.2	645.4	621.6	597.8	571.9	548.0
152.5°	695.2	695.2	691.4	680.9	668.7	652.3	633.0	612.5	591.2	567.8	545.5
155°	664.1	663.1	661.0	652.7	643.4	631.0	615.4	598.8	581.2	560.5	542.9
157.5°	635.7	635.9	634.3	628.0	619.9	610.2	598.2	584.3	570.0	554.1	539.4
160°	617.5	618.5	618.5	612.3	605.0	597.8	587.5	576.0	562.6	549.1	537.7
162.5°	600.9	601.9	601.9	596.6	591.7	585.3	575.9	566.1	555.1	544.1	534.4
165°	579.2	579.2	580.1	576.0	571.9	566.7	559.5	553.2	544.9	536.6	529.4
167.5°	558.4	558.4	559.5	556.5	554.7	551.0	546.8	542.1	535.2	529.2	524.4
170°	546.0	546.0	547.1	544.9	543.9	541.8	537.7	534.6	529.4	524.2	521.1
172.5°	534.4	535.2	537.1	535.0	534.8	533.6	530.2	528.0	523.6	520.0	518.6
175°	521.1	522.2	523.2	522.2	522.2	522.2	520.0	519.1	517.0	514.9	514.9
177.5°	513.4	513.4	515.1	514.2	515.1	515.1	514.2	513.4	512.6	511.8	512.6
180°	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8



TEST NUMBER: P332266-940

CATALOG NUMBER: S123RDIP-S340D1195U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3
2.5°	501.1	500.6	498.3	495.6	492.1	489.8	487.9	487.0	483.9	480.3	477.9
5°	532.1	525.8	519.2	511.0	503.5	495.9	491.2	485.5	478.7	471.0	465.6
7.5°	565.2	552.9	539.8	526.2	512.8	500.8	490.1	481.0	470.1	459.1	451.4
10°	590.7	572.7	554.3	535.4	518.2	501.9	489.5	477.2	464.1	451.5	441.8
12.5°	613.8	590.2	568.9	545.6	523.6	504.3	486.3	471.9	456.1	442.6	431.8
15°	643.0	618.8	593.2	557.8	528.5	504.0	482.1	463.2	444.2	427.6	417.0
17.5°	670.3	634.1	599.4	570.0	531.9	501.3	474.7	452.1	431.1	413.5	400.4
20°	681.6	646.5	608.9	571.3	534.0	499.6	468.7	443.7	422.0	402.0	389.9
22.5°	688.4	648.7	609.0	568.6	529.0	493.3	462.7	435.2	411.6	392.7	377.8
25°	696.3	649.0	605.4	565.5	525.0	486.3	450.0	420.9	395.4	375.2	359.4
27.5°	701.6	645.9	594.3	550.0	508.9	470.5	437.1	406.3	380.3	359.0	342.1
30°	702.6	643.4	585.9	537.9	496.1	460.7	425.4	396.0	368.5	345.9	330.1
32.5°	703.9	637.2	574.4	523.4	480.6	445.7	413.7	385.5	357.4	335.1	319.0
35°	698.5	633.8	557.0	498.4	455.6	421.7	392.9	366.8	339.3	317.6	301.2
37.5°	674.8	620.4	539.0	470.2	425.4	394.1	370.6	347.9	322.6	299.3	283.8
40°	651.1	607.1	525.0	453.1	406.4	374.2	352.9	334.5	310.0	288.1	271.5
42.5°	615.7	588.9	511.7	435.2	384.8	353.7	335.8	318.5	297.0	274.8	259.2
45°	550.7	554.3	484.5	406.5	354.8	323.7	306.8	294.8	275.7	257.4	241.4
47.5°	469.3	502.3	452.5	376.1	323.3	294.1	279.4	268.9	255.9	238.0	223.4
50°	416.2	463.2	427.0	355.7	303.5	274.5	259.9	251.4	240.1	226.0	212.1
52.5°	367.1	417.8	396.0	332.9	282.0	255.5	241.3	234.3	225.3	212.0	199.5
55°	299.3	350.7	345.7	298.5	249.9	226.0	215.3	207.3	201.3	191.4	181.4
57.5°	242.2	290.8	293.4	260.3	221.6	198.0	188.7	182.7	178.8	171.3	162.0
60°	206.1	250.7	259.5	234.5	201.3	180.6	171.4	166.6	163.5	157.5	150.4
62.5°	176.2	214.2	224.1	206.2	181.9	162.4	155.2	150.7	148.6	143.4	137.1
65°	134.8	166.4	175.9	166.0	153.3	137.8	131.9	128.0	126.1	123.2	118.6
67.5°	101.4	124.4	134.9	127.9	123.2	113.4	109.8	107.6	105.9	104.0	100.1
70°	81.4	98.4	109.2	107.5	103.7	98.4	95.8	94.3	92.6	91.0	87.7
72.5°	65.5	77.2	87.3	88.3	85.2	84.2	81.8	81.1	80.2	78.2	76.3
75°	43.4	51.5	58.6	61.3	62.5	63.6	62.5	62.3	62.2	60.5	59.4
77.5°	28.4	32.8	37.3	41.9	43.9	45.2	45.6	46.4	45.7	44.9	44.4
80°	21.8	22.8	25.9	29.9	33.0	34.2	35.1	35.5	35.3	35.1	34.2
82.5°	15.9	16.7	18.2	21.0	23.5	25.6	26.1	26.0	26.5	26.7	25.9
85°	8.6	8.7	9.2	9.5	11.0	13.3	13.9	14.4	14.7	14.7	13.5
87.5°	6.6	5.8	5.5	5.1	5.2	4.7	5.4	5.7	6.3	6.1	6.7
90°	19.7	16.6	13.5	11.4	9.4	6.2	4.1	2.1	4.1	6.2	9.4
92.5°	131.6	87.0	59.9	44.6	35.8	27.7	19.1	12.8	19.1	27.7	35.8
95°	377.1	222.7	134.6	94.3	67.3	49.8	38.3	35.2	38.3	49.8	67.3
97.5°	413.8	239.8	155.6	111.9	85.3	70.0	61.1	60.1	61.1	70.0	85.3
100°	390.6	237.3	164.7	124.3	99.4	85.0	77.7	76.7	77.7	85.0	99.4
102.5°	370.7	240.6	175.5	138.4	116.0	102.4	95.9	94.1	95.9	102.4	116.0
105°	356.4	249.7	193.8	161.6	142.0	129.5	123.3	120.2	123.3	129.5	142.0
107.5°	355.3	266.7	217.6	187.7	169.2	157.0	151.1	147.9	151.1	157.0	169.2
110°	359.5	280.8	234.2	205.1	187.5	176.1	170.9	167.8	170.9	176.1	187.5



TEST NUMBER: P332266-940

CATALOG NUMBER: S123RDIP-S340D1195U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	367.8	294.9	251.6	223.4	205.7	194.4	189.2	186.1	189.2	194.4	205.7
115°	381.3	318.1	278.7	250.7	233.1	222.7	216.5	212.4	216.5	222.7	233.1
117.5°	399.0	342.7	303.8	277.9	258.2	248.6	243.4	238.7	243.4	248.6	258.2
120°	412.3	358.5	321.2	295.2	275.6	265.2	260.0	256.9	260.0	265.2	275.6
122.5°	424.8	375.1	338.6	311.0	292.1	281.0	275.8	272.7	275.8	281.0	292.1
125°	444.4	398.9	362.6	334.7	315.0	303.5	297.4	295.2	297.4	303.5	315.0
127.5°	460.7	419.5	384.6	356.6	334.8	323.2	315.6	312.5	315.6	323.2	334.8
130°	471.4	432.0	397.8	369.9	348.1	335.6	326.4	323.2	326.4	335.6	348.1
132.5°	481.3	442.8	409.5	382.3	360.5	345.6	335.5	331.5	335.5	345.6	360.5
135°	494.2	459.0	426.9	398.9	377.1	361.6	350.2	346.1	350.2	361.6	377.1
137.5°	503.7	470.1	439.3	413.4	391.8	375.2	364.1	359.7	364.1	375.2	391.8
140°	508.7	477.6	447.5	421.7	400.9	384.3	374.0	368.8	374.0	384.3	400.9
142.5°	513.6	483.4	454.2	430.0	409.2	394.3	383.2	378.8	383.2	394.3	409.2
145°	519.1	491.1	464.1	440.3	422.7	407.2	397.8	394.8	397.8	407.2	422.7
147.5°	522.4	497.3	472.6	452.4	435.3	421.9	412.8	410.9	412.8	421.9	435.3
150°	523.2	501.4	477.6	459.0	444.4	431.0	422.7	421.7	422.7	431.0	444.4
152.5°	524.9	503.9	483.4	465.6	452.7	441.0	432.7	432.5	432.7	441.0	452.7
155°	525.3	508.7	491.1	476.5	465.2	454.9	448.6	448.6	448.6	454.9	465.2
157.5°	526.3	511.4	497.3	486.1	476.4	467.3	462.3	461.5	462.3	467.3	476.4
160°	526.3	513.9	501.4	491.1	483.8	475.5	471.4	471.4	471.4	475.5	483.8
162.5°	525.5	514.7	503.9	495.3	488.8	482.1	478.8	478.8	478.8	482.1	488.8
165°	523.2	515.9	507.7	500.4	496.2	491.1	489.0	490.1	489.0	491.1	496.2
167.5°	521.6	515.8	509.7	505.2	502.3	498.3	497.3	498.6	497.3	498.3	502.3
170°	519.1	514.9	509.7	507.7	505.6	502.5	501.4	503.5	501.4	502.5	505.6
172.5°	518.3	514.9	510.6	509.3	508.1	505.8	505.6	506.8	505.6	505.8	508.1
175°	515.9	513.9	511.8	510.8	510.8	508.7	509.7	510.8	509.7	508.7	510.8
177.5°	514.2	512.6	511.8	511.8	511.8	511.0	511.8	512.6	511.8	511.0	511.8
180°	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8



TEST NUMBER: P332266-940

CATALOG NUMBER: S123RDIP-S340D1195U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3
2.5°	477.0	474.8	473.3	470.0	467.9	465.6	463.2	464.7	464.5	464.4	464.4
5°	461.0	456.2	451.8	446.2	442.7	438.4	435.1	434.6	435.4	432.6	430.9
7.5°	445.1	438.6	432.4	426.2	419.6	414.4	411.2	409.6	407.5	405.7	403.9
10°	434.0	426.3	420.3	412.6	405.6	399.3	395.4	392.6	391.2	389.8	387.0
12.5°	422.5	415.0	407.3	398.6	391.9	384.7	381.7	378.7	375.9	374.3	370.6
15°	405.7	396.0	387.9	378.7	371.2	364.2	360.1	354.0	353.2	351.1	347.3
17.5°	388.9	378.4	367.1	360.3	352.0	344.6	338.2	336.3	330.3	328.1	324.8
20°	375.6	365.9	357.3	348.4	336.2	329.3	324.3	321.6	316.8	313.9	311.8
22.5°	364.2	354.2	344.4	333.9	323.9	316.1	312.5	308.3	305.7	301.6	299.3
25°	347.8	337.0	325.1	313.9	306.7	300.9	295.0	291.2	287.5	285.6	281.5
27.5°	328.8	317.4	306.4	297.8	288.9	283.2	277.9	274.6	270.1	267.0	264.7
30°	318.3	305.0	295.4	287.8	276.3	270.9	267.0	262.8	259.5	256.2	253.9
32.5°	306.1	294.0	285.0	275.4	266.7	260.7	255.7	252.0	249.1	246.0	243.7
35°	287.1	277.0	267.6	258.1	251.6	245.6	239.5	236.4	233.7	230.8	228.7
37.5°	269.9	260.4	251.5	242.5	234.4	229.5	224.7	222.3	218.6	216.7	214.6
40°	259.3	249.9	240.4	231.7	223.4	219.6	215.3	211.7	208.4	206.9	204.6
42.5°	247.6	238.3	230.2	220.9	214.0	208.9	204.9	201.1	198.6	196.4	195.2
45°	230.4	222.1	214.2	204.8	198.4	194.0	189.5	185.9	183.7	182.2	179.9
47.5°	213.7	205.4	197.3	189.2	183.0	178.0	173.3	170.9	167.9	166.1	164.6
50°	201.5	194.0	185.6	178.1	171.8	166.8	163.1	160.0	157.3	155.0	153.9
52.5°	190.4	182.4	175.0	168.1	161.5	155.9	152.5	149.2	147.1	144.5	143.3
55°	172.0	164.3	158.1	151.2	144.8	140.0	135.9	133.0	130.9	128.0	126.4
57.5°	154.8	147.8	140.4	134.5	127.9	123.9	120.4	116.5	113.9	111.6	109.9
60°	143.1	135.3	128.8	123.2	117.3	112.2	109.1	105.9	103.3	100.9	99.5
62.5°	131.0	124.1	118.0	111.9	106.6	102.0	98.4	95.9	93.5	92.0	90.5
65°	112.4	107.0	100.8	95.8	90.8	87.5	84.5	82.3	80.6	79.5	78.3
67.5°	95.2	90.1	84.6	79.7	76.3	73.8	72.0	70.0	69.1	67.8	67.0
70°	84.2	78.7	73.9	70.2	66.9	65.0	63.8	62.3	61.5	59.8	59.0
72.5°	72.1	68.1	64.6	61.6	58.9	57.2	55.6	53.9	52.5	50.6	49.8
75°	56.7	53.1	50.5	48.4	46.7	44.5	42.2	40.3	39.7	39.1	38.9
77.5°	42.0	39.8	37.8	36.0	34.0	32.4	31.8	31.4	31.3	30.9	30.9
80°	33.0	30.9	29.5	27.5	26.2	26.2	26.2	25.8	25.9	25.9	25.9
82.5°	24.5	22.6	21.8	21.1	20.9	21.0	21.0	21.1	21.0	21.3	21.1
85°	12.7	12.8	13.3	13.1	13.3	13.3	13.7	13.5	13.7	13.3	13.7
87.5°	7.0	7.8	8.6	9.5	10.2	10.7	10.6	10.8	11.2	11.4	11.9
90°	11.4	13.5	16.6	19.7	22.8	25.9	24.9	25.9	26.9	28.0	30.1
92.5°	44.6	59.9	87.0	131.6	175.3	159.3	120.2	87.2	69.2	61.1	55.7
95°	94.3	134.6	222.7	377.1	547.1	614.4	498.3	373.0	252.8	197.9	160.6
97.5°	111.9	155.6	239.8	413.8	697.1	952.1	1018.6	929.7	744.7	611.1	487.1
100°	124.3	164.7	237.3	390.6	663.1	981.1	1185.3	1221.5	1137.6	1016.4	869.2
102.5°	138.4	175.5	240.6	370.7	613.3	927.3	1193.5	1318.5	1315.7	1245.1	1151.8
105°	161.6	193.8	249.7	356.4	552.2	832.9	1130.3	1346.8	1450.5	1470.2	1443.2
107.5°	187.7	217.6	266.7	355.3	513.3	749.7	1019.7	1265.2	1433.4	1524.2	1561.1
110°	205.1	234.2	280.8	359.5	498.3	702.4	950.0	1187.3	1378.0	1508.5	1581.0



TEST NUMBER: P332266-940

CATALOG NUMBER: S123RDIP-S340D1195U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	223.4	251.6	294.9	367.8	490.1	670.9	889.6	1110.2	1305.0	1451.3	1544.5
115°	250.7	278.7	318.1	381.3	487.0	637.1	816.4	1008.1	1188.3	1340.6	1453.6
117.5°	277.9	303.8	342.7	399.0	488.8	617.2	772.2	934.1	1089.7	1226.5	1341.0
120°	295.2	321.2	358.5	412.3	492.1	608.1	749.0	895.1	1035.0	1159.3	1264.0
122.5°	311.0	338.6	375.1	424.8	497.9	602.4	730.0	864.4	991.0	1106.3	1203.5
125°	334.7	362.6	398.9	444.4	506.6	594.7	705.5	823.7	936.6	1036.0	1118.9
127.5°	356.6	384.6	419.5	460.7	516.6	590.9	684.0	788.0	888.7	978.4	1053.8
130°	369.9	397.8	432.0	471.4	523.2	588.4	672.3	765.6	858.9	942.8	1013.3
132.5°	382.3	409.5	442.8	481.3	528.2	587.6	661.6	744.9	830.7	908.8	976.0
135°	398.9	426.9	459.0	494.2	535.7	586.4	647.6	716.9	790.5	857.8	916.9
137.5°	413.4	439.3	470.1	503.7	540.6	584.1	635.3	691.4	751.7	809.8	860.9
140°	421.7	447.5	477.6	508.7	543.9	583.3	627.9	676.5	729.3	779.1	823.7
142.5°	430.0	454.2	483.4	513.6	546.4	581.7	621.2	662.5	707.8	750.9	789.7
145°	440.3	464.1	491.1	519.1	548.0	579.2	612.3	645.4	679.7	712.8	742.8
147.5°	452.4	472.6	497.3	522.4	548.0	575.2	603.6	631.6	658.7	685.5	706.8
150°	459.0	477.6	501.4	523.2	548.0	571.9	597.8	621.6	645.4	667.2	686.9
152.5°	465.6	483.4	503.9	524.9	545.5	567.8	591.2	612.5	633.0	652.3	668.7
155°	476.5	491.1	508.7	525.3	542.9	560.5	581.2	598.8	615.4	631.0	643.4
157.5°	486.1	497.3	511.4	526.3	539.4	554.1	570.0	584.3	598.2	610.2	619.9
160°	491.1	501.4	513.9	526.3	537.7	549.1	562.6	576.0	587.5	597.8	605.0
162.5°	495.3	503.9	514.7	525.5	534.4	544.1	555.1	566.1	575.9	585.3	591.7
165°	500.4	507.7	515.9	523.2	529.4	536.6	544.9	553.2	559.5	566.7	571.9
167.5°	505.2	509.7	515.8	521.6	524.4	529.2	535.2	542.1	546.8	551.0	554.7
170°	507.7	509.7	514.9	519.1	521.1	524.2	529.4	534.6	537.7	541.8	543.9
172.5°	509.3	510.6	514.9	518.3	518.6	520.0	523.6	528.0	530.2	533.6	534.8
175°	510.8	511.8	513.9	515.9	514.9	514.9	517.0	519.1	520.0	522.2	522.2
177.5°	511.8	511.8	512.6	514.2	512.6	511.8	512.6	513.4	514.2	515.1	515.1
180°	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8



TEST NUMBER: P332266-940

CATALOG NUMBER: S123RDIP-S340D1195U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3
2.5°	462.4	462.2	462.4	461.7	462.4	462.2	462.4	464.4	464.4	464.5	464.7
5°	430.3	430.1	429.4	427.6	429.4	430.1	430.3	430.9	432.6	435.4	434.6
7.5°	402.2	401.9	400.1	400.1	400.1	401.9	402.2	403.9	405.7	407.5	409.6
10°	385.6	385.8	383.3	381.8	383.3	385.8	385.6	387.0	389.8	391.2	392.6
12.5°	369.4	368.5	366.5	364.9	366.5	368.5	369.4	370.6	374.3	375.9	378.7
15°	348.2	346.1	341.2	341.5	341.2	346.1	348.2	347.3	351.1	353.2	354.0
17.5°	323.2	321.6	321.6	318.6	321.6	321.6	323.2	324.8	328.1	330.3	336.3
20°	308.5	307.5	307.9	305.0	307.9	307.5	308.5	311.8	313.9	316.8	321.6
22.5°	297.0	296.0	294.3	293.4	294.3	296.0	297.0	299.3	301.6	305.7	308.3
25°	280.3	278.6	277.0	277.9	277.0	278.6	280.3	281.5	285.6	287.5	291.2
27.5°	263.5	262.3	260.6	260.4	260.6	262.3	263.5	264.7	267.0	270.1	274.6
30°	252.8	251.6	250.7	249.7	250.7	251.6	252.8	253.9	256.2	259.5	262.8
32.5°	242.0	241.7	240.3	240.0	240.3	241.7	242.0	243.7	246.0	249.1	252.0
35°	227.9	226.7	226.2	226.4	226.2	226.7	227.9	228.7	230.8	233.7	236.4
37.5°	214.5	212.9	212.0	211.3	212.0	212.9	214.5	214.6	216.7	218.6	222.3
40°	204.8	203.2	202.8	202.3	202.8	203.2	204.8	204.6	206.9	208.4	211.7
42.5°	194.0	193.4	193.1	192.3	193.1	193.4	194.0	195.2	196.4	198.6	201.1
45°	179.3	179.1	177.8	178.3	177.8	179.1	179.3	179.9	182.2	183.7	185.9
47.5°	163.7	162.8	161.9	162.6	161.9	162.8	163.7	164.6	166.1	167.9	170.9
50°	153.1	152.7	150.8	151.2	150.8	152.7	153.1	153.9	155.0	157.3	160.0
52.5°	142.5	140.9	140.2	139.9	140.2	140.9	142.5	143.3	144.5	147.1	149.2
55°	124.8	123.0	122.2	121.7	122.2	123.0	124.8	126.4	128.0	130.9	133.0
57.5°	107.5	107.1	106.4	106.8	106.4	107.1	107.5	109.9	111.6	113.9	116.5
60°	97.5	97.5	97.5	97.2	97.5	97.5	97.5	99.5	100.9	103.3	105.9
62.5°	89.6	89.1	89.0	89.3	89.0	89.1	89.6	90.5	92.0	93.5	95.9
65°	77.7	77.5	76.7	76.4	76.7	77.5	77.7	78.3	79.5	80.6	82.3
67.5°	66.4	65.7	65.5	65.2	65.5	65.7	66.4	67.0	67.8	69.1	70.0
70°	58.0	57.5	56.3	56.5	56.3	57.5	58.0	59.0	59.8	61.5	62.3
72.5°	48.9	48.4	48.2	47.9	48.2	48.4	48.9	49.8	50.6	52.5	53.9
75°	38.6	38.4	38.3	39.1	38.3	38.4	38.6	38.9	39.1	39.7	40.3
77.5°	30.9	30.9	31.1	30.8	31.1	30.9	30.9	30.9	30.9	31.3	31.4
80°	25.9	25.9	25.8	25.8	25.8	25.9	25.9	25.9	25.9	25.9	25.8
82.5°	20.8	21.0	21.1	20.8	21.1	21.0	20.8	21.1	21.3	21.0	21.1
85°	13.7	13.5	13.9	13.7	13.9	13.5	13.7	13.7	13.3	13.7	13.5
87.5°	11.9	11.9	12.0	11.9	12.0	11.9	11.9	11.9	11.4	11.2	10.8
90°	29.0	30.1	31.1	30.1	31.1	30.1	29.0	30.1	28.0	26.9	25.9
92.5°	53.9	50.7	51.8	49.9	51.8	50.7	53.9	55.7	61.1	69.2	87.2
95°	140.9	131.6	124.3	120.2	124.3	131.6	140.9	160.6	197.9	252.8	373.0
97.5°	410.7	364.1	336.1	327.2	336.1	364.1	410.7	487.1	611.1	744.7	929.7
100°	764.6	688.9	648.5	649.6	648.5	688.9	764.6	869.2	1016.4	1137.6	1221.5
102.5°	1070.4	1010.6	976.8	953.0	976.8	1010.6	1070.4	1151.8	1245.1	1315.7	1318.5
105°	1395.5	1356.2	1323.0	1317.9	1323.0	1356.2	1395.5	1443.2	1470.2	1450.5	1346.8
107.5°	1561.9	1548.6	1537.5	1527.9	1537.5	1548.6	1561.9	1561.1	1524.2	1433.4	1265.2
110°	1610.0	1618.3	1616.2	1614.2	1616.2	1618.3	1610.0	1581.0	1508.5	1378.0	1187.3



TEST NUMBER: P332266-940

CATALOG NUMBER: S123RDIP-S340D1195U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1597.6	1623.3	1631.1	1631.6	1631.1	1623.3	1597.6	1544.5	1451.3	1305.0	1110.2
115°	1531.2	1576.8	1597.6	1602.8	1597.6	1576.8	1531.2	1453.6	1340.6	1188.3	1008.1
117.5°	1422.1	1474.3	1504.1	1511.2	1504.1	1474.3	1422.1	1341.0	1226.5	1089.7	934.1
120°	1345.8	1403.8	1428.7	1434.9	1428.7	1403.8	1345.8	1264.0	1159.3	1035.0	895.1
122.5°	1276.2	1328.4	1355.8	1363.6	1355.8	1328.4	1276.2	1203.5	1106.3	991.0	864.4
125°	1185.3	1230.8	1256.7	1264.0	1256.7	1230.8	1185.3	1118.9	1036.0	936.6	823.7
127.5°	1112.9	1151.8	1175.3	1181.9	1175.3	1151.8	1112.9	1053.8	978.4	888.7	788.0
130°	1068.2	1105.5	1127.2	1135.5	1127.2	1105.5	1068.2	1013.3	942.8	858.9	765.6
132.5°	1027.5	1064.8	1084.1	1089.9	1084.1	1064.8	1027.5	976.0	908.8	830.7	744.9
135°	967.7	998.7	1017.4	1024.7	1017.4	998.7	967.7	916.9	857.8	790.5	716.9
137.5°	903.7	935.1	950.8	955.6	950.8	935.1	903.7	860.9	809.8	751.7	691.4
140°	863.0	892.1	908.6	907.6	908.6	892.1	863.0	823.7	779.1	729.3	676.5
142.5°	823.2	848.9	863.8	862.8	863.8	848.9	823.2	789.7	750.9	707.8	662.5
145°	768.7	790.5	798.8	800.8	798.8	790.5	768.7	742.8	712.8	679.7	645.4
147.5°	726.5	741.2	749.0	749.8	749.0	741.2	726.5	706.8	685.5	658.7	631.6
150°	702.4	713.8	720.1	720.1	720.1	713.8	702.4	686.9	667.2	645.4	621.6
152.5°	680.9	691.4	695.2	695.2	695.2	691.4	680.9	668.7	652.3	633.0	612.5
155°	652.7	661.0	663.1	664.1	663.1	661.0	652.7	643.4	631.0	615.4	598.8
157.5°	628.0	634.3	635.9	635.7	635.9	634.3	628.0	619.9	610.2	598.2	584.3
160°	612.3	618.5	618.5	617.5	618.5	618.5	612.3	605.0	597.8	587.5	576.0
162.5°	596.6	601.9	601.9	600.9	601.9	601.9	596.6	591.7	585.3	575.9	566.1
165°	576.0	580.1	579.2	579.2	579.2	580.1	576.0	571.9	566.7	559.5	553.2
167.5°	556.5	559.5	558.4	558.4	558.4	559.5	556.5	554.7	551.0	546.8	542.1
170°	544.9	547.1	546.0	546.0	546.0	547.1	544.9	543.9	541.8	537.7	534.6
172.5°	535.0	537.1	535.2	534.4	535.2	537.1	535.0	534.8	533.6	530.2	528.0
175°	522.2	523.2	522.2	521.1	522.2	523.2	522.2	522.2	522.2	520.0	519.1
177.5°	514.2	515.1	513.4	513.4	513.4	515.1	514.2	515.1	515.1	514.2	513.4
180°	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8



TEST NUMBER: P332266-940

CATALOG NUMBER: S123RDIP-S340D1195U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3
2.5°	463.2	465.6	467.9	470.0	473.3	474.8	477.0	477.9	480.3	483.9	487.0
5°	435.1	438.4	442.7	446.2	451.8	456.2	461.0	465.6	471.0	478.7	485.5
7.5°	411.2	414.4	419.6	426.2	432.4	438.6	445.1	451.4	459.1	470.1	481.0
10°	395.4	399.3	405.6	412.6	420.3	426.3	434.0	441.8	451.5	464.1	477.2
12.5°	381.7	384.7	391.9	398.6	407.3	415.0	422.5	431.8	442.6	456.1	471.9
15°	360.1	364.2	371.2	378.7	387.9	396.0	405.7	417.0	427.6	444.2	463.2
17.5°	338.2	344.6	352.0	360.3	367.1	378.4	388.9	400.4	413.5	431.1	452.1
20°	324.3	329.3	336.2	348.4	357.3	365.9	375.6	389.9	402.0	422.0	443.7
22.5°	312.5	316.1	323.9	333.9	344.4	354.2	364.2	377.8	392.7	411.6	435.2
25°	295.0	300.9	306.7	313.9	325.1	337.0	347.8	359.4	375.2	395.4	420.9
27.5°	277.9	283.2	288.9	297.8	306.4	317.4	328.8	342.1	359.0	380.3	406.3
30°	267.0	270.9	276.3	287.8	295.4	305.0	318.3	330.1	345.9	368.5	396.0
32.5°	255.7	260.7	266.7	275.4	285.0	294.0	306.1	319.0	335.1	357.4	385.5
35°	239.5	245.6	251.6	258.1	267.6	277.0	287.1	301.2	317.6	339.3	366.8
37.5°	224.7	229.5	234.4	242.5	251.5	260.4	269.9	283.8	299.3	322.6	347.9
40°	215.3	219.6	223.4	231.7	240.4	249.9	259.3	271.5	288.1	310.0	334.5
42.5°	204.9	208.9	214.0	220.9	230.2	238.3	247.6	259.2	274.8	297.0	318.5
45°	189.5	194.0	198.4	204.8	214.2	222.1	230.4	241.4	257.4	275.7	294.8
47.5°	173.3	178.0	183.0	189.2	197.3	205.4	213.7	223.4	238.0	255.9	268.9
50°	163.1	166.8	171.8	178.1	185.6	194.0	201.5	212.1	226.0	240.1	251.4
52.5°	152.5	155.9	161.5	168.1	175.0	182.4	190.4	199.5	212.0	225.3	234.3
55°	135.9	140.0	144.8	151.2	158.1	164.3	172.0	181.4	191.4	201.3	207.3
57.5°	120.4	123.9	127.9	134.5	140.4	147.8	154.8	162.0	171.3	178.8	182.7
60°	109.1	112.2	117.3	123.2	128.8	135.3	143.1	150.4	157.5	163.5	166.6
62.5°	98.4	102.0	106.6	111.9	118.0	124.1	131.0	137.1	143.4	148.6	150.7
65°	84.5	87.5	90.8	95.8	100.8	107.0	112.4	118.6	123.2	126.1	128.0
67.5°	72.0	73.8	76.3	79.7	84.6	90.1	95.2	100.1	104.0	105.9	107.6
70°	63.8	65.0	66.9	70.2	73.9	78.7	84.2	87.7	91.0	92.6	94.3
72.5°	55.6	57.2	58.9	61.6	64.6	68.1	72.1	76.3	78.2	80.2	81.1
75°	42.2	44.5	46.7	48.4	50.5	53.1	56.7	59.4	60.5	62.2	62.3
77.5°	31.8	32.4	34.0	36.0	37.8	39.8	42.0	44.4	44.9	45.7	46.4
80°	26.2	26.2	26.2	27.5	29.5	30.9	33.0	34.2	35.1	35.3	35.5
82.5°	21.0	21.0	20.9	21.1	21.8	22.6	24.5	25.9	26.7	26.5	26.0
85°	13.7	13.3	13.3	13.1	13.3	12.8	12.7	13.5	14.7	14.7	14.4
87.5°	10.6	10.7	10.2	9.5	8.6	7.8	7.0	6.7	6.1	6.3	5.7
90°	24.9	25.9	22.8	19.7	16.6	13.5	11.4	9.4	6.2	4.1	2.1
92.5°	120.2	159.3	175.3	131.6	87.0	59.9	44.6	35.8	27.7	19.1	12.8
95°	498.3	614.4	547.1	377.1	222.7	134.6	94.3	67.3	49.8	38.3	35.2
97.5°	1018.6	952.1	697.1	413.8	239.8	155.6	111.9	85.3	70.0	61.1	60.1
100°	1185.3	981.1	663.1	390.6	237.3	164.7	124.3	99.4	85.0	77.7	76.7
102.5°	1193.5	927.3	613.3	370.7	240.6	175.5	138.4	116.0	102.4	95.9	94.1
105°	1130.3	832.9	552.2	356.4	249.7	193.8	161.6	142.0	129.5	123.3	120.2
107.5°	1019.7	749.7	513.3	355.3	266.7	217.6	187.7	169.2	157.0	151.1	147.9
110°	950.0	702.4	498.3	359.5	280.8	234.2	205.1	187.5	176.1	170.9	167.8



TEST NUMBER: P332266-940

CATALOG NUMBER: S123RDIP-S340D1195U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	889.6	670.9	490.1	367.8	294.9	251.6	223.4	205.7	194.4	189.2	186.1
115°	816.4	637.1	487.0	381.3	318.1	278.7	250.7	233.1	222.7	216.5	212.4
117.5°	772.2	617.2	488.8	399.0	342.7	303.8	277.9	258.2	248.6	243.4	238.7
120°	749.0	608.1	492.1	412.3	358.5	321.2	295.2	275.6	265.2	260.0	256.9
122.5°	730.0	602.4	497.9	424.8	375.1	338.6	311.0	292.1	281.0	275.8	272.7
125°	705.5	594.7	506.6	444.4	398.9	362.6	334.7	315.0	303.5	297.4	295.2
127.5°	684.0	590.9	516.6	460.7	419.5	384.6	356.6	334.8	323.2	315.6	312.5
130°	672.3	588.4	523.2	471.4	432.0	397.8	369.9	348.1	335.6	326.4	323.2
132.5°	661.6	587.6	528.2	481.3	442.8	409.5	382.3	360.5	345.6	335.5	331.5
135°	647.6	586.4	535.7	494.2	459.0	426.9	398.9	377.1	361.6	350.2	346.1
137.5°	635.3	584.1	540.6	503.7	470.1	439.3	413.4	391.8	375.2	364.1	359.7
140°	627.9	583.3	543.9	508.7	477.6	447.5	421.7	400.9	384.3	374.0	368.8
142.5°	621.2	581.7	546.4	513.6	483.4	454.2	430.0	409.2	394.3	383.2	378.8
145°	612.3	579.2	548.0	519.1	491.1	464.1	440.3	422.7	407.2	397.8	394.8
147.5°	603.6	575.2	548.0	522.4	497.3	472.6	452.4	435.3	421.9	412.8	410.9
150°	597.8	571.9	548.0	523.2	501.4	477.6	459.0	444.4	431.0	422.7	421.7
152.5°	591.2	567.8	545.5	524.9	503.9	483.4	465.6	452.7	441.0	432.7	432.5
155°	581.2	560.5	542.9	525.3	508.7	491.1	476.5	465.2	454.9	448.6	448.6
157.5°	570.0	554.1	539.4	526.3	511.4	497.3	486.1	476.4	467.3	462.3	461.5
160°	562.6	549.1	537.7	526.3	513.9	501.4	491.1	483.8	475.5	471.4	471.4
162.5°	555.1	544.1	534.4	525.5	514.7	503.9	495.3	488.8	482.1	478.8	478.8
165°	544.9	536.6	529.4	523.2	515.9	507.7	500.4	496.2	491.1	489.0	490.1
167.5°	535.2	529.2	524.4	521.6	515.8	509.7	505.2	502.3	498.3	497.3	498.6
170°	529.4	524.2	521.1	519.1	514.9	509.7	507.7	505.6	502.5	501.4	503.5
172.5°	523.6	520.0	518.6	518.3	514.9	510.6	509.3	508.1	505.8	505.6	506.8
175°	517.0	514.9	514.9	515.9	513.9	511.8	510.8	510.8	508.7	509.7	510.8
177.5°	512.6	511.8	512.6	514.2	512.6	511.8	511.8	511.8	511.0	511.8	512.6
180°	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8



TEST NUMBER: P332266-940

CATALOG NUMBER: S123RDIP-S340D1195U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3
2.5°	487.9	489.8	492.1	495.6	498.3	500.6	501.1	501.8	503.5	506.2	508.4
5°	491.2	495.9	503.5	511.0	519.2	525.8	532.1	536.5	540.6	549.3	556.3
7.5°	490.1	500.8	512.8	526.2	539.8	552.9	565.2	576.1	587.0	599.8	614.2
10°	489.5	501.9	518.2	535.4	554.3	572.7	590.7	604.6	620.7	635.3	653.8
12.5°	486.3	504.3	523.6	545.6	568.9	590.2	613.8	632.9	651.5	672.5	694.0
15°	482.1	504.0	528.5	557.8	593.2	618.8	643.0	676.5	699.3	722.1	752.9
17.5°	474.7	501.3	531.9	570.0	599.4	634.1	670.3	696.8	727.5	759.7	787.6
20°	468.7	499.6	534.0	571.3	608.9	646.5	681.6	713.2	745.0	782.2	805.0
22.5°	462.7	493.3	529.0	568.6	609.0	648.7	688.4	725.5	761.3	798.8	828.0
25°	450.0	486.3	525.0	565.5	605.4	649.0	696.3	737.7	781.9	820.6	848.3
27.5°	437.1	470.5	508.9	550.0	594.3	645.9	701.6	748.6	792.9	820.6	829.3
30°	425.4	460.7	496.1	537.9	585.9	643.4	702.6	756.4	792.7	804.9	795.9
32.5°	413.7	445.7	480.6	523.4	574.4	637.2	703.9	751.8	773.6	764.5	728.1
35°	392.9	421.7	455.6	498.4	557.0	633.8	698.5	730.8	725.5	673.5	604.9
37.5°	370.6	394.1	425.4	470.2	539.0	620.4	674.8	679.7	632.8	553.1	473.9
40°	352.9	374.2	406.4	453.1	525.0	607.1	651.1	631.8	559.3	470.6	404.5
42.5°	335.8	353.7	384.8	435.2	511.7	588.9	615.7	573.6	490.0	406.1	346.0
45°	306.8	323.7	354.8	406.5	484.5	554.3	550.7	477.6	393.9	326.4	276.5
47.5°	279.4	294.1	323.3	376.1	452.5	502.3	469.3	391.5	320.5	266.3	230.7
50°	259.9	274.5	303.5	355.7	427.0	463.2	416.2	341.2	276.1	231.2	203.0
52.5°	241.3	255.5	282.0	332.9	396.0	417.8	367.1	297.6	243.3	204.6	180.4
55°	215.3	226.0	249.9	298.5	345.7	350.7	299.3	241.2	196.5	169.5	152.9
57.5°	188.7	198.0	221.6	260.3	293.4	290.8	242.2	191.8	161.8	141.7	129.7
60°	171.4	180.6	201.3	234.5	259.5	250.7	206.1	165.6	139.8	125.1	115.5
62.5°	155.2	162.4	181.9	206.2	224.1	214.2	176.2	142.7	122.2	109.8	102.2
65°	131.9	137.8	153.3	166.0	175.9	166.4	134.8	111.6	96.8	88.1	82.9
67.5°	109.8	113.4	123.2	127.9	134.9	124.4	101.4	85.8	77.4	70.1	66.4
70°	95.8	98.4	103.7	107.5	109.2	98.4	81.4	70.0	63.0	57.8	55.5
72.5°	81.8	84.2	85.2	88.3	87.3	77.2	65.5	56.4	51.3	47.8	44.9
75°	62.5	63.6	62.5	61.3	58.6	51.5	43.4	38.9	35.1	33.4	32.4
77.5°	45.6	45.2	43.9	41.9	37.3	32.8	28.4	26.9	25.3	24.4	24.1
80°	35.1	34.2	33.0	29.9	25.9	22.8	21.8	20.8	20.2	19.1	18.9
82.5°	26.1	25.6	23.5	21.0	18.2	16.7	15.9	15.4	14.8	14.3	14.3
85°	13.9	13.3	11.0	9.5	9.2	8.7	8.6	8.6	7.7	7.5	7.5
87.5°	5.4	4.7	5.2	5.1	5.5	5.8	6.6	6.9	7.3	7.3	7.1
90°	4.1	6.2	9.4	11.4	13.5	16.6	19.7	22.8	25.9	24.9	25.9
92.5°	19.1	27.7	35.8	44.6	59.9	87.0	131.6	175.3	159.3	120.2	87.2
95°	38.3	49.8	67.3	94.3	134.6	222.7	377.1	547.1	614.4	498.3	373.0
97.5°	61.1	70.0	85.3	111.9	155.6	239.8	413.8	697.1	952.1	1018.6	929.7
100°	77.7	85.0	99.4	124.3	164.7	237.3	390.6	663.1	981.1	1185.3	1221.5
102.5°	95.9	102.4	116.0	138.4	175.5	240.6	370.7	613.3	927.3	1193.5	1318.5
105°	123.3	129.5	142.0	161.6	193.8	249.7	356.4	552.2	832.9	1130.3	1346.8
107.5°	151.1	157.0	169.2	187.7	217.6	266.7	355.3	513.3	749.7	1019.7	1265.2
110°	170.9	176.1	187.5	205.1	234.2	280.8	359.5	498.3	702.4	950.0	1187.3



TEST NUMBER: P332266-940

CATALOG NUMBER: S123RDIP-S340D1195U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	189.2	194.4	205.7	223.4	251.6	294.9	367.8	490.1	670.9	889.6	1110.2
115°	216.5	222.7	233.1	250.7	278.7	318.1	381.3	487.0	637.1	816.4	1008.1
117.5°	243.4	248.6	258.2	277.9	303.8	342.7	399.0	488.8	617.2	772.2	934.1
120°	260.0	265.2	275.6	295.2	321.2	358.5	412.3	492.1	608.1	749.0	895.1
122.5°	275.8	281.0	292.1	311.0	338.6	375.1	424.8	497.9	602.4	730.0	864.4
125°	297.4	303.5	315.0	334.7	362.6	398.9	444.4	506.6	594.7	705.5	823.7
127.5°	315.6	323.2	334.8	356.6	384.6	419.5	460.7	516.6	590.9	684.0	788.0
130°	326.4	335.6	348.1	369.9	397.8	432.0	471.4	523.2	588.4	672.3	765.6
132.5°	335.5	345.6	360.5	382.3	409.5	442.8	481.3	528.2	587.6	661.6	744.9
135°	350.2	361.6	377.1	398.9	426.9	459.0	494.2	535.7	586.4	647.6	716.9
137.5°	364.1	375.2	391.8	413.4	439.3	470.1	503.7	540.6	584.1	635.3	691.4
140°	374.0	384.3	400.9	421.7	447.5	477.6	508.7	543.9	583.3	627.9	676.5
142.5°	383.2	394.3	409.2	430.0	454.2	483.4	513.6	546.4	581.7	621.2	662.5
145°	397.8	407.2	422.7	440.3	464.1	491.1	519.1	548.0	579.2	612.3	645.4
147.5°	412.8	421.9	435.3	452.4	472.6	497.3	522.4	548.0	575.2	603.6	631.6
150°	422.7	431.0	444.4	459.0	477.6	501.4	523.2	548.0	571.9	597.8	621.6
152.5°	432.7	441.0	452.7	465.6	483.4	503.9	524.9	545.5	567.8	591.2	612.5
155°	448.6	454.9	465.2	476.5	491.1	508.7	525.3	542.9	560.5	581.2	598.8
157.5°	462.3	467.3	476.4	486.1	497.3	511.4	526.3	539.4	554.1	570.0	584.3
160°	471.4	475.5	483.8	491.1	501.4	513.9	526.3	537.7	549.1	562.6	576.0
162.5°	478.8	482.1	488.8	495.3	503.9	514.7	525.5	534.4	544.1	555.1	566.1
165°	489.0	491.1	496.2	500.4	507.7	515.9	523.2	529.4	536.6	544.9	553.2
167.5°	497.3	498.3	502.3	505.2	509.7	515.8	521.6	524.4	529.2	535.2	542.1
170°	501.4	502.5	505.6	507.7	509.7	514.9	519.1	521.1	524.2	529.4	534.6
172.5°	505.6	505.8	508.1	509.3	510.6	514.9	518.3	518.6	520.0	523.6	528.0
175°	509.7	508.7	510.8	510.8	511.8	513.9	515.9	514.9	514.9	517.0	519.1
177.5°	511.8	511.0	511.8	511.8	511.8	512.6	514.2	512.6	511.8	512.6	513.4
180°	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8



TEST NUMBER: P332266-940

CATALOG NUMBER: S123RDIP-S340D1195U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	485.3	485.3	485.3	485.3	485.3	485.3	485.3
2.5°	511.9	511.9	512.6	515.1	515.4	517.5	516.9
5°	562.6	566.5	568.0	574.3	577.9	579.6	576.3
7.5°	624.6	635.7	641.0	647.6	653.3	655.1	650.5
10°	669.8	681.4	691.2	697.2	702.8	706.6	711.3
12.5°	713.5	727.8	737.1	745.6	751.4	756.1	756.9
15°	761.0	782.6	799.0	811.1	817.1	820.2	818.9
17.5°	808.9	828.9	840.6	852.9	861.2	861.7	861.9
20°	836.0	855.5	869.1	878.2	887.5	887.1	889.2
22.5°	854.1	869.5	879.9	886.4	889.7	888.1	888.5
25°	862.6	867.2	865.3	854.7	851.9	842.2	843.9
27.5°	818.9	797.3	774.9	746.2	723.4	705.3	706.2
30°	759.6	721.3	677.7	641.1	608.3	599.1	579.6
32.5°	676.6	619.3	568.2	534.0	506.0	498.3	481.3
35°	536.0	480.3	427.8	396.2	383.7	366.2	366.0
37.5°	416.6	367.6	339.8	316.1	303.7	293.1	292.1
40°	350.4	312.3	291.2	274.2	262.0	254.0	252.2
42.5°	304.3	273.4	253.7	243.2	233.7	229.6	226.6
45°	248.4	227.7	214.0	204.5	200.1	197.0	195.3
47.5°	207.9	193.9	184.6	178.2	174.7	171.4	172.3
50°	185.7	174.3	167.5	161.4	158.7	156.4	156.7
52.5°	167.9	157.7	152.1	147.8	144.5	142.8	142.0
55°	142.5	136.1	130.5	127.3	125.5	123.2	122.6
57.5°	121.5	116.5	112.0	108.5	108.0	105.8	106.1
60°	107.6	103.4	99.7	97.8	96.4	94.5	95.1
62.5°	96.1	92.6	89.3	87.7	86.2	84.9	85.2
65°	78.7	75.4	73.3	72.5	71.9	71.2	70.6
67.5°	62.8	60.7	59.4	57.6	56.4	56.2	55.6
70°	52.8	50.0	47.8	45.5	44.9	44.7	44.9
72.5°	42.3	40.6	39.9	38.9	38.7	38.2	38.5
75°	31.7	31.1	30.8	29.9	29.9	29.9	29.9
77.5°	23.5	23.1	22.8	22.6	22.5	22.1	22.1
80°	18.3	18.1	17.7	17.7	17.5	17.7	17.5
82.5°	13.8	13.7	13.4	13.4	13.1	13.0	13.1
85°	7.0	6.9	7.3	6.9	7.0	6.7	7.0
87.5°	7.4	7.6	7.8	7.7	7.7	8.2	7.7
90°	26.9	28.0	30.1	29.0	30.1	31.1	30.1
92.5°	69.2	61.1	55.7	53.9	50.7	51.8	49.9
95°	252.8	197.9	160.6	140.9	131.6	124.3	120.2
97.5°	744.7	611.1	487.1	410.7	364.1	336.1	327.2
100°	1137.6	1016.4	869.2	764.6	688.9	648.5	649.6
102.5°	1315.7	1245.1	1151.8	1070.4	1010.6	976.8	953.0
105°	1450.5	1470.2	1443.2	1395.5	1356.2	1323.0	1317.9
107.5°	1433.4	1524.2	1561.1	1561.9	1548.6	1537.5	1527.9
110°	1378.0	1508.5	1581.0	1610.0	1618.3	1616.2	1614.2



TEST NUMBER: P332266-940

CATALOG NUMBER: S123RDIP-S340D1195U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1305.0	1451.3	1544.5	1597.6	1623.3	1631.1	1631.6
115°	1188.3	1340.6	1453.6	1531.2	1576.8	1597.6	1602.8
117.5°	1089.7	1226.5	1341.0	1422.1	1474.3	1504.1	1511.2
120°	1035.0	1159.3	1264.0	1345.8	1403.8	1428.7	1434.9
122.5°	991.0	1106.3	1203.5	1276.2	1328.4	1355.8	1363.6
125°	936.6	1036.0	1118.9	1185.3	1230.8	1256.7	1264.0
127.5°	888.7	978.4	1053.8	1112.9	1151.8	1175.3	1181.9
130°	858.9	942.8	1013.3	1068.2	1105.5	1127.2	1135.5
132.5°	830.7	908.8	976.0	1027.5	1064.8	1084.1	1089.9
135°	790.5	857.8	916.9	967.7	998.7	1017.4	1024.7
137.5°	751.7	809.8	860.9	903.7	935.1	950.8	955.6
140°	729.3	779.1	823.7	863.0	892.1	908.6	907.6
142.5°	707.8	750.9	789.7	823.2	848.9	863.8	862.8
145°	679.7	712.8	742.8	768.7	790.5	798.8	800.8
147.5°	658.7	685.5	706.8	726.5	741.2	749.0	749.8
150°	645.4	667.2	686.9	702.4	713.8	720.1	720.1
152.5°	633.0	652.3	668.7	680.9	691.4	695.2	695.2
155°	615.4	631.0	643.4	652.7	661.0	663.1	664.1
157.5°	598.2	610.2	619.9	628.0	634.3	635.9	635.7
160°	587.5	597.8	605.0	612.3	618.5	618.5	617.5
162.5°	575.9	585.3	591.7	596.6	601.9	601.9	600.9
165°	559.5	566.7	571.9	576.0	580.1	579.2	579.2
167.5°	546.8	551.0	554.7	556.5	559.5	558.4	558.4
170°	537.7	541.8	543.9	544.9	547.1	546.0	546.0
172.5°	530.2	533.6	534.8	535.0	537.1	535.2	534.4
175°	520.0	522.2	522.2	522.2	523.2	522.2	521.1
177.5°	514.2	515.1	515.1	514.2	515.1	513.4	513.4
180°	511.8	511.8	511.8	511.8	511.8	511.8	511.8

(END OF REPORT)