

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332242-940

Luminaire Tested: **S123RDIP-S340D365U940-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332242-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S340D365U940-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2380.7 lumens
Efficiency: N/A
Efficacy: 117.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 20.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332242-940

CATALOG NUMBER: S123RDIP-S340D365U940-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332242-940

CATALOG NUMBER: S123RDIP-S340D365U940-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	99	94	91	87	91	87	84	81	74	72	70	62	61	59	51	50	49	44
2	90	83	77	72	83	77	72	68	66	62	59	55	53	50	46	44	42	38
3	83	74	67	61	76	68	62	57	59	54	50	49	46	43	41	39	37	33
4	76	66	58	52	70	61	54	49	52	47	43	44	41	38	37	34	32	29
5	70	59	51	45	64	55	48	43	47	42	38	40	36	33	34	31	28	25
6	65	53	45	39	60	49	42	37	43	37	33	37	32	29	31	28	25	22
7	60	48	40	35	55	45	38	33	39	33	29	33	29	26	28	25	23	20
8	56	44	36	31	51	41	34	29	36	30	26	31	26	23	26	23	20	18
9	52	40	33	28	48	37	31	26	33	27	24	28	24	21	24	21	18	16
10	48	37	30	25	45	34	28	24	30	25	21	26	22	19	22	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5224	5224	5224	5224
5°	6227	5246	4620	5246
10°	7774	5216	4173	5216
15°	9126	5162	3806	5162
20°	10186	5082	3494	5082
25°	10023	4999	3301	4999
30°	7204	4922	3104	4922
35°	4809	4820	2975	4820
40°	3544	4700	2843	4700
45°	2973	4488	2714	4488
50°	2624	4210	2532	4210
55°	2301	3890	2284	3890
60°	2047	3587	2093	3587
65°	1798	3260	1946	3260
70°	1413	2968	1778	2968
75°	1243	2591	1626	2591
80°	1085	2201	1599	2201
85°	865	1778	1692	1778



TEST NUMBER: P332242-940

CATALOG NUMBER: S123RDIP-S340D365U940-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.7	2.0
10°-20°	149.1	6.3
20°-30°	234.2	9.8
30°-40°	244.4	10.3
40°-50°	209.1	8.8
50°-60°	159.4	6.7
60°-70°	102.2	4.3
70°-80°	49.1	2.1
80°-90°	14.2	0.6
90°-100°	86.6	3.6
100°-110°	245.3	10.3
110°-120°	241.3	10.1
120°-130°	192.5	8.1
130°-140°	151.8	6.4
140°-150°	113.3	4.8
150°-160°	78.9	3.3
160°-170°	46.4	1.9
170°-180°	15.1	0.6
0°-30°	431.1	18.1
0°-40°	675.4	28.4
0°-60°	1044.0	43.9
0°-90°	1209.5	50.8
90°-120°	573.2	24.1
90°-150°	1030.7	43.3
90°-180°	1171.0	49.2
0°-180°	2380.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	485	485	485	485	485	
5°	576	486	428	486	576	59
15°	819	463	342	463	819	232
25°	844	421	278	421	844	363
35°	366	367	226	367	366	240
45°	195	295	178	295	195	154
55°	123	207	122	207	123	111
65°	71	128	76	128	71	69
75°	30	62	39	62	30	32
85°	7	14	14	14	7	8
90°	9	1	9	1	9	5
95°	37	11	37	11	37	66
105°	401	37	401	37	401	395
115°	488	65	488	65	488	474
125°	384	90	384	90	384	348
135°	312	105	312	105	312	242
145°	244	120	244	120	244	155
155°	202	136	202	136	202	94
165°	176	149	176	149	176	50
175°	158	155	158	155	158	15
180°	156	156	156	156	156	



TEST NUMBER: P332242-940

CATALOG NUMBER: S123RDIP-S340D365U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3
2.5°	516.9	517.5	515.4	515.1	512.6	511.9	511.9	508.4	506.2	503.5	501.8
5°	576.3	579.6	577.9	574.3	568.0	566.5	562.6	556.3	549.3	540.6	536.5
7.5°	650.5	655.1	653.3	647.6	641.0	635.7	624.6	614.2	599.8	587.0	576.1
10°	711.3	706.6	702.8	697.2	691.2	681.4	669.8	653.8	635.3	620.7	604.6
12.5°	756.9	756.1	751.4	745.6	737.1	727.8	713.5	694.0	672.5	651.5	632.9
15°	818.9	820.2	817.1	811.1	799.0	782.6	761.0	752.9	722.1	699.3	676.5
17.5°	861.9	861.7	861.2	852.9	840.6	828.9	808.9	787.6	759.7	727.5	696.8
20°	889.2	887.1	887.5	878.2	869.1	855.5	836.0	805.0	782.2	745.0	713.2
22.5°	888.5	888.1	889.7	886.4	879.9	869.5	854.1	828.0	798.8	761.3	725.5
25°	843.9	842.2	851.9	854.7	865.3	867.2	862.6	848.3	820.6	781.9	737.7
27.5°	706.2	705.3	723.4	746.2	774.9	797.3	818.9	829.3	820.6	792.9	748.6
30°	579.6	599.1	608.3	641.1	677.7	721.3	759.6	795.9	804.9	792.7	756.4
32.5°	481.3	498.3	506.0	534.0	568.2	619.3	676.6	728.1	764.5	773.6	751.8
35°	366.0	366.2	383.7	396.2	427.8	480.3	536.0	604.9	673.5	725.5	730.8
37.5°	292.1	293.1	303.7	316.1	339.8	367.6	416.6	473.9	553.1	632.8	679.7
40°	252.2	254.0	262.0	274.2	291.2	312.3	350.4	404.5	470.6	559.3	631.8
42.5°	226.6	229.6	233.7	243.2	253.7	273.4	304.3	346.0	406.1	490.0	573.6
45°	195.3	197.0	200.1	204.5	214.0	227.7	248.4	276.5	326.4	393.9	477.6
47.5°	172.3	171.4	174.7	178.2	184.6	193.9	207.9	230.7	266.3	320.5	391.5
50°	156.7	156.4	158.7	161.4	167.5	174.3	185.7	203.0	231.2	276.1	341.2
52.5°	142.0	142.8	144.5	147.8	152.1	157.7	167.9	180.4	204.6	243.3	297.6
55°	122.6	123.2	125.5	127.3	130.5	136.1	142.5	152.9	169.5	196.5	241.2
57.5°	106.1	105.8	108.0	108.5	112.0	116.5	121.5	129.7	141.7	161.8	191.8
60°	95.1	94.5	96.4	97.8	99.7	103.4	107.6	115.5	125.1	139.8	165.6
62.5°	85.2	84.9	86.2	87.7	89.3	92.6	96.1	102.2	109.8	122.2	142.7
65°	70.6	71.2	71.9	72.5	73.3	75.4	78.7	82.9	88.1	96.8	111.6
67.5°	55.6	56.2	56.4	57.6	59.4	60.7	62.8	66.4	70.1	77.4	85.8
70°	44.9	44.7	44.9	45.5	47.8	50.0	52.8	55.5	57.8	63.0	70.0
72.5°	38.5	38.2	38.7	38.9	39.9	40.6	42.3	44.9	47.8	51.3	56.4
75°	29.9	29.9	29.9	29.9	30.8	31.1	31.7	32.4	33.4	35.1	38.9
77.5°	22.1	22.1	22.5	22.6	22.8	23.1	23.5	24.1	24.4	25.3	26.9
80°	17.5	17.7	17.5	17.7	17.7	18.1	18.3	18.9	19.1	20.2	20.8
82.5°	13.1	13.0	13.1	13.4	13.4	13.7	13.8	14.3	14.3	14.8	15.4
85°	7.0	6.7	7.0	6.9	7.3	6.9	7.0	7.5	7.5	7.7	8.6
87.5°	3.5	3.9	3.5	3.6	3.7	3.7	3.7	3.6	3.8	3.7	3.7
90°	9.1	9.5	9.1	8.8	9.1	8.5	8.2	7.8	7.6	7.8	7.0
92.5°	15.2	15.8	15.4	16.4	16.9	18.5	21.0	26.6	36.6	48.4	53.3
95°	36.6	37.8	40.0	42.9	48.9	60.2	76.9	113.4	151.6	186.9	166.4
97.5°	99.5	102.2	110.8	124.9	148.2	185.8	226.5	282.8	309.8	289.6	212.0
100°	197.6	197.2	209.6	232.6	264.4	309.2	346.0	371.5	360.5	298.5	201.7
102.5°	289.8	297.1	307.4	325.6	350.4	378.7	400.2	401.0	363.0	282.0	186.5
105°	400.8	402.4	412.5	424.5	439.0	447.1	441.1	409.7	343.8	253.3	168.0
107.5°	464.8	467.6	471.0	475.1	474.8	463.6	436.0	384.8	310.1	228.0	156.1
110°	491.0	491.6	492.2	489.7	480.9	458.8	419.1	361.1	289.0	213.7	151.6



TEST NUMBER: P332242-940

CATALOG NUMBER: S123RDIP-S340D365U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	496.2	496.1	493.7	485.9	469.8	441.4	396.9	337.7	270.5	204.0	149.0
115°	487.5	485.9	479.6	465.7	442.1	407.8	361.4	306.6	248.3	193.8	148.1
117.5°	459.6	457.4	448.4	432.6	407.9	373.0	331.4	284.1	234.9	187.7	148.6
120°	436.4	434.5	427.0	409.3	384.4	352.6	314.8	272.2	227.8	184.9	149.7
122.5°	414.7	412.3	404.0	388.2	366.0	336.4	301.4	263.0	222.0	183.2	151.4
125°	384.4	382.3	374.3	360.5	340.4	315.1	284.9	250.5	214.6	180.8	154.1
127.5°	359.4	357.5	350.4	338.5	320.6	297.6	270.3	239.7	208.0	179.8	157.1
130°	345.4	342.9	336.3	324.9	308.2	286.8	261.3	232.8	204.5	179.0	159.2
132.5°	331.5	329.8	323.9	312.5	296.9	276.4	252.6	226.6	201.3	178.7	160.7
135°	311.7	309.4	303.8	294.4	278.8	260.9	240.4	218.0	197.0	178.3	162.9
137.5°	290.7	289.2	284.5	274.8	261.9	246.3	228.6	210.3	193.2	177.6	164.4
140°	276.1	276.3	271.3	262.5	250.5	236.9	221.9	205.8	190.9	177.5	165.4
142.5°	262.4	262.7	258.2	250.4	240.1	228.4	215.3	201.5	189.0	176.9	166.2
145°	243.6	243.0	240.4	233.8	226.0	216.8	206.7	196.4	186.2	176.1	166.7
147.5°	228.1	227.8	225.4	221.0	215.0	208.5	200.4	192.1	183.6	175.0	166.7
150°	219.0	219.0	217.1	213.7	208.9	203.0	196.4	189.0	181.8	174.0	166.7
152.5°	211.4	211.4	210.3	207.1	203.4	198.4	192.5	186.3	179.8	172.7	165.9
155°	202.0	201.7	201.1	198.5	195.6	191.9	187.2	182.2	176.7	170.5	165.1
157.5°	193.3	193.4	192.9	191.0	188.6	185.6	181.9	177.7	173.3	168.5	164.1
160°	187.8	188.2	188.2	186.2	184.0	181.8	178.7	175.2	171.1	167.0	163.5
162.5°	182.8	183.1	183.1	181.5	180.0	178.1	175.1	172.2	168.8	165.5	162.6
165°	176.1	176.1	176.5	175.2	174.0	172.4	170.1	168.3	165.8	163.3	161.0
167.5°	169.9	169.9	170.1	169.2	168.7	167.6	166.3	164.9	162.8	161.0	159.5
170°	166.0	166.0	166.4	165.8	165.4	164.8	163.5	162.6	161.0	159.4	158.5
172.5°	162.6	162.8	163.4	162.7	162.6	162.3	161.3	160.6	159.3	158.2	157.7
175°	158.5	158.8	159.2	158.8	158.8	158.8	158.2	157.8	157.2	156.6	156.6
177.5°	156.1	156.1	156.7	156.4	156.7	156.7	156.4	156.1	156.0	155.7	156.0
180°	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7



TEST NUMBER: P332242-940

CATALOG NUMBER: S123RDIP-S340D365U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3
2.5°	501.1	500.6	498.3	495.6	492.1	489.8	487.9	487.0	483.9	480.3	477.9
5°	532.1	525.8	519.2	511.0	503.5	495.9	491.2	485.5	478.7	471.0	465.6
7.5°	565.2	552.9	539.8	526.2	512.8	500.8	490.1	481.0	470.1	459.1	451.4
10°	590.7	572.7	554.3	535.4	518.2	501.9	489.5	477.2	464.1	451.5	441.8
12.5°	613.8	590.2	568.9	545.6	523.6	504.3	486.3	471.9	456.1	442.6	431.8
15°	643.0	618.8	593.2	557.8	528.5	504.0	482.1	463.2	444.2	427.6	417.0
17.5°	670.3	634.1	599.4	570.0	531.9	501.3	474.7	452.1	431.1	413.5	400.4
20°	681.6	646.5	608.9	571.3	534.0	499.6	468.7	443.7	422.0	402.0	389.9
22.5°	688.4	648.7	609.0	568.6	529.0	493.3	462.7	435.2	411.6	392.7	377.8
25°	696.3	649.0	605.4	565.5	525.0	486.3	450.0	420.9	395.4	375.2	359.4
27.5°	701.6	645.9	594.3	550.0	508.9	470.5	437.1	406.3	380.3	359.0	342.1
30°	702.6	643.4	585.9	537.9	496.1	460.7	425.4	396.0	368.5	345.9	330.1
32.5°	703.9	637.2	574.4	523.4	480.6	445.7	413.7	385.5	357.4	335.1	319.0
35°	698.5	633.8	557.0	498.4	455.6	421.7	392.9	366.8	339.3	317.6	301.2
37.5°	674.8	620.4	539.0	470.2	425.4	394.1	370.6	347.9	322.6	299.3	283.8
40°	651.1	607.1	525.0	453.1	406.4	374.2	352.9	334.5	310.0	288.1	271.5
42.5°	615.7	588.9	511.7	435.2	384.8	353.7	335.8	318.5	297.0	274.8	259.2
45°	550.7	554.3	484.5	406.5	354.8	323.7	306.8	294.8	275.7	257.4	241.4
47.5°	469.3	502.3	452.5	376.1	323.3	294.1	279.4	268.9	255.9	238.0	223.4
50°	416.2	463.2	427.0	355.7	303.5	274.5	259.9	251.4	240.1	226.0	212.1
52.5°	367.1	417.8	396.0	332.9	282.0	255.5	241.3	234.3	225.3	212.0	199.5
55°	299.3	350.7	345.7	298.5	249.9	226.0	215.3	207.3	201.3	191.4	181.4
57.5°	242.2	290.8	293.4	260.3	221.6	198.0	188.7	182.7	178.8	171.3	162.0
60°	206.1	250.7	259.5	234.5	201.3	180.6	171.4	166.6	163.5	157.5	150.4
62.5°	176.2	214.2	224.1	206.2	181.9	162.4	155.2	150.7	148.6	143.4	137.1
65°	134.8	166.4	175.9	166.0	153.3	137.8	131.9	128.0	126.1	123.2	118.6
67.5°	101.4	124.4	134.9	127.9	123.2	113.4	109.8	107.6	105.9	104.0	100.1
70°	81.4	98.4	109.2	107.5	103.7	98.4	95.8	94.3	92.6	91.0	87.7
72.5°	65.5	77.2	87.3	88.3	85.2	84.2	81.8	81.1	80.2	78.2	76.3
75°	43.4	51.5	58.6	61.3	62.5	63.6	62.5	62.3	62.2	60.5	59.4
77.5°	28.4	32.8	37.3	41.9	43.9	45.2	45.6	46.4	45.7	44.9	44.4
80°	21.8	22.8	25.9	29.9	33.0	34.2	35.1	35.5	35.3	35.1	34.2
82.5°	15.9	16.7	18.2	21.0	23.5	25.6	26.1	26.0	26.5	26.7	25.9
85°	8.6	8.7	9.2	9.5	11.0	13.3	13.9	14.4	14.7	14.7	13.5
87.5°	3.8	3.5	3.7	3.5	3.9	3.8	4.7	5.4	5.7	5.2	5.4
90°	6.0	5.1	4.1	3.5	2.9	1.9	1.2	0.6	1.2	1.9	2.9
92.5°	40.0	26.5	18.2	13.6	10.9	8.5	5.8	3.9	5.8	8.5	10.9
95°	114.7	67.8	40.9	28.7	20.5	15.2	11.7	10.7	11.7	15.2	20.5
97.5°	125.8	72.9	47.3	34.1	25.9	21.3	18.5	18.3	18.5	21.3	25.9
100°	118.8	72.1	50.1	37.8	30.2	25.9	23.6	23.4	23.6	25.9	30.2
102.5°	112.7	73.2	53.4	42.1	35.3	31.1	29.2	28.6	29.2	31.1	35.3
105°	108.4	76.0	58.9	49.1	43.2	39.4	37.5	36.6	37.5	39.4	43.2
107.5°	108.1	81.1	66.2	57.1	51.5	47.8	45.9	45.0	45.9	47.8	51.5
110°	109.3	85.4	71.2	62.4	57.1	53.6	52.0	51.0	52.0	53.6	57.1



TEST NUMBER: P332242-940

CATALOG NUMBER: S123RDIP-S340D365U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	111.9	89.7	76.5	67.9	62.6	59.1	57.5	56.6	57.5	59.1	62.6
115°	115.9	96.8	84.8	76.2	70.9	67.8	65.9	64.6	65.9	67.8	70.9
117.5°	121.4	104.2	92.4	84.5	78.6	75.6	74.0	72.6	74.0	75.6	78.6
120°	125.4	109.1	97.6	89.8	83.8	80.7	79.1	78.1	79.1	80.7	83.8
122.5°	129.2	114.0	103.0	94.6	88.9	85.4	83.9	82.9	83.9	85.4	88.9
125°	135.2	121.4	110.3	101.7	95.8	92.3	90.4	89.8	90.4	92.3	95.8
127.5°	140.1	127.6	117.0	108.4	101.8	98.4	95.9	95.1	95.9	98.4	101.8
130°	143.4	131.4	121.0	112.5	105.8	102.1	99.2	98.4	99.2	102.1	105.8
132.5°	146.4	134.6	124.6	116.3	109.7	105.1	102.0	100.9	102.0	105.1	109.7
135°	150.3	139.6	129.8	121.4	114.7	109.9	106.5	105.2	106.5	109.9	114.7
137.5°	153.2	143.0	133.6	125.7	119.1	114.1	110.8	109.4	110.8	114.1	119.1
140°	154.7	145.3	136.2	128.2	122.0	116.9	113.8	112.2	113.8	116.9	122.0
142.5°	156.2	147.0	138.1	130.8	124.5	119.9	116.5	115.2	116.5	119.9	124.5
145°	157.8	149.4	141.2	133.9	128.6	123.9	121.0	120.0	121.0	123.9	128.6
147.5°	158.9	151.2	143.7	137.6	132.4	128.3	125.6	125.0	125.6	128.3	132.4
150°	159.2	152.5	145.3	139.6	135.2	131.1	128.6	128.2	128.6	131.1	135.2
152.5°	159.6	153.3	147.0	141.6	137.7	134.1	131.6	131.5	131.6	134.1	137.7
155°	159.8	154.7	149.4	145.0	141.5	138.3	136.4	136.4	136.4	138.3	141.5
157.5°	160.1	155.5	151.2	147.8	144.9	142.1	140.6	140.4	140.6	142.1	144.9
160°	160.1	156.3	152.5	149.4	147.1	144.6	143.4	143.4	143.4	144.6	147.1
162.5°	159.8	156.6	153.3	150.6	148.6	146.7	145.6	145.6	145.6	146.7	148.6
165°	159.2	156.9	154.4	152.2	151.0	149.4	148.7	149.0	148.7	149.4	151.0
167.5°	158.6	156.9	155.1	153.6	152.8	151.6	151.2	151.6	151.2	151.6	152.8
170°	157.8	156.6	155.1	154.4	153.7	152.8	152.5	153.1	152.5	152.8	153.7
172.5°	157.7	156.6	155.2	154.9	154.5	153.8	153.7	154.2	153.7	153.8	154.5
175°	156.9	156.3	155.7	155.3	155.3	154.7	155.1	155.3	155.1	154.7	155.3
177.5°	156.4	156.0	155.7	155.7	155.7	155.4	155.7	156.0	155.7	155.4	155.7
180°	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7



TEST NUMBER: P332242-940

CATALOG NUMBER: S123RDIP-S340D365U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3
2.5°	477.0	474.8	473.3	470.0	467.9	465.6	463.2	464.7	464.5	464.4	464.4
5°	461.0	456.2	451.8	446.2	442.7	438.4	435.1	434.6	435.4	432.6	430.9
7.5°	445.1	438.6	432.4	426.2	419.6	414.4	411.2	409.6	407.5	405.7	403.9
10°	434.0	426.3	420.3	412.6	405.6	399.3	395.4	392.6	391.2	389.8	387.0
12.5°	422.5	415.0	407.3	398.6	391.9	384.7	381.7	378.7	375.9	374.3	370.6
15°	405.7	396.0	387.9	378.7	371.2	364.2	360.1	354.0	353.2	351.1	347.3
17.5°	388.9	378.4	367.1	360.3	352.0	344.6	338.2	336.3	330.3	328.1	324.8
20°	375.6	365.9	357.3	348.4	336.2	329.3	324.3	321.6	316.8	313.9	311.8
22.5°	364.2	354.2	344.4	333.9	323.9	316.1	312.5	308.3	305.7	301.6	299.3
25°	347.8	337.0	325.1	313.9	306.7	300.9	295.0	291.2	287.5	285.6	281.5
27.5°	328.8	317.4	306.4	297.8	288.9	283.2	277.9	274.6	270.1	267.0	264.7
30°	318.3	305.0	295.4	287.8	276.3	270.9	267.0	262.8	259.5	256.2	253.9
32.5°	306.1	294.0	285.0	275.4	266.7	260.7	255.7	252.0	249.1	246.0	243.7
35°	287.1	277.0	267.6	258.1	251.6	245.6	239.5	236.4	233.7	230.8	228.7
37.5°	269.9	260.4	251.5	242.5	234.4	229.5	224.7	222.3	218.6	216.7	214.6
40°	259.3	249.9	240.4	231.7	223.4	219.6	215.3	211.7	208.4	206.9	204.6
42.5°	247.6	238.3	230.2	220.9	214.0	208.9	204.9	201.1	198.6	196.4	195.2
45°	230.4	222.1	214.2	204.8	198.4	194.0	189.5	185.9	183.7	182.2	179.9
47.5°	213.7	205.4	197.3	189.2	183.0	178.0	173.3	170.9	167.9	166.1	164.6
50°	201.5	194.0	185.6	178.1	171.8	166.8	163.1	160.0	157.3	155.0	153.9
52.5°	190.4	182.4	175.0	168.1	161.5	155.9	152.5	149.2	147.1	144.5	143.3
55°	172.0	164.3	158.1	151.2	144.8	140.0	135.9	133.0	130.9	128.0	126.4
57.5°	154.8	147.8	140.4	134.5	127.9	123.9	120.4	116.5	113.9	111.6	109.9
60°	143.1	135.3	128.8	123.2	117.3	112.2	109.1	105.9	103.3	100.9	99.5
62.5°	131.0	124.1	118.0	111.9	106.6	102.0	98.4	95.9	93.5	92.0	90.5
65°	112.4	107.0	100.8	95.8	90.8	87.5	84.5	82.3	80.6	79.5	78.3
67.5°	95.2	90.1	84.6	79.7	76.3	73.8	72.0	70.0	69.1	67.8	67.0
70°	84.2	78.7	73.9	70.2	66.9	65.0	63.8	62.3	61.5	59.8	59.0
72.5°	72.1	68.1	64.6	61.6	58.9	57.2	55.6	53.9	52.5	50.6	49.8
75°	56.7	53.1	50.5	48.4	46.7	44.5	42.2	40.3	39.7	39.1	38.9
77.5°	42.0	39.8	37.8	36.0	34.0	32.4	31.8	31.4	31.3	30.9	30.9
80°	33.0	30.9	29.5	27.5	26.2	26.2	26.2	25.8	25.9	25.9	25.9
82.5°	24.5	22.6	21.8	21.1	20.9	21.0	21.0	21.1	21.0	21.3	21.1
85°	12.7	12.8	13.3	13.1	13.3	13.3	13.7	13.5	13.7	13.3	13.7
87.5°	5.4	6.0	6.3	6.7	7.0	7.0	7.1	7.2	7.5	7.5	7.7
90°	3.5	4.1	5.1	6.0	7.0	7.8	7.6	7.8	8.2	8.5	9.1
92.5°	13.6	18.2	26.5	40.0	53.3	48.4	36.6	26.6	21.0	18.5	16.9
95°	28.7	40.9	67.8	114.7	166.4	186.9	151.6	113.4	76.9	60.2	48.9
97.5°	34.1	47.3	72.9	125.8	212.0	289.6	309.8	282.8	226.5	185.8	148.2
100°	37.8	50.1	72.1	118.8	201.7	298.5	360.5	371.5	346.0	309.2	264.4
102.5°	42.1	53.4	73.2	112.7	186.5	282.0	363.0	401.0	400.2	378.7	350.4
105°	49.1	58.9	76.0	108.4	168.0	253.3	343.8	409.7	441.1	447.1	439.0
107.5°	57.1	66.2	81.1	108.1	156.1	228.0	310.1	384.8	436.0	463.6	474.8
110°	62.4	71.2	85.4	109.3	151.6	213.7	289.0	361.1	419.1	458.8	480.9



TEST NUMBER: P332242-940

CATALOG NUMBER: S123RDIP-S340D365U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	67.9	76.5	89.7	111.9	149.0	204.0	270.5	337.7	396.9	441.4	469.8
115°	76.2	84.8	96.8	115.9	148.1	193.8	248.3	306.6	361.4	407.8	442.1
117.5°	84.5	92.4	104.2	121.4	148.6	187.7	234.9	284.1	331.4	373.0	407.9
120°	89.8	97.6	109.1	125.4	149.7	184.9	227.8	272.2	314.8	352.6	384.4
122.5°	94.6	103.0	114.0	129.2	151.4	183.2	222.0	263.0	301.4	336.4	366.0
125°	101.7	110.3	121.4	135.2	154.1	180.8	214.6	250.5	284.9	315.1	340.4
127.5°	108.4	117.0	127.6	140.1	157.1	179.8	208.0	239.7	270.3	297.6	320.6
130°	112.5	121.0	131.4	143.4	159.2	179.0	204.5	232.8	261.3	286.8	308.2
132.5°	116.3	124.6	134.6	146.4	160.7	178.7	201.3	226.6	252.6	276.4	296.9
135°	121.4	129.8	139.6	150.3	162.9	178.3	197.0	218.0	240.4	260.9	278.8
137.5°	125.7	133.6	143.0	153.2	164.4	177.6	193.2	210.3	228.6	246.3	261.9
140°	128.2	136.2	145.3	154.7	165.4	177.5	190.9	205.8	221.9	236.9	250.5
142.5°	130.8	138.1	147.0	156.2	166.2	176.9	189.0	201.5	215.3	228.4	240.1
145°	133.9	141.2	149.4	157.8	166.7	176.1	186.2	196.4	206.7	216.8	226.0
147.5°	137.6	143.7	151.2	158.9	166.7	175.0	183.6	192.1	200.4	208.5	215.0
150°	139.6	145.3	152.5	159.2	166.7	174.0	181.8	189.0	196.4	203.0	208.9
152.5°	141.6	147.0	153.3	159.6	165.9	172.7	179.8	186.3	192.5	198.4	203.4
155°	145.0	149.4	154.7	159.8	165.1	170.5	176.7	182.2	187.2	191.9	195.6
157.5°	147.8	151.2	155.5	160.1	164.1	168.5	173.3	177.7	181.9	185.6	188.6
160°	149.4	152.5	156.3	160.1	163.5	167.0	171.1	175.2	178.7	181.8	184.0
162.5°	150.6	153.3	156.6	159.8	162.6	165.5	168.8	172.2	175.1	178.1	180.0
165°	152.2	154.4	156.9	159.2	161.0	163.3	165.8	168.3	170.1	172.4	174.0
167.5°	153.6	155.1	156.9	158.6	159.5	161.0	162.8	164.9	166.3	167.6	168.7
170°	154.4	155.1	156.6	157.8	158.5	159.4	161.0	162.6	163.5	164.8	165.4
172.5°	154.9	155.2	156.6	157.7	157.7	158.2	159.3	160.6	161.3	162.3	162.6
175°	155.3	155.7	156.3	156.9	156.6	156.6	157.2	157.8	158.2	158.8	158.8
177.5°	155.7	155.7	156.0	156.4	156.0	155.7	156.0	156.1	156.4	156.7	156.7
180°	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7



TEST NUMBER: P332242-940

CATALOG NUMBER: S123RDIP-S340D365U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3
2.5°	462.4	462.2	462.4	461.7	462.4	462.2	462.4	464.4	464.4	464.5	464.7
5°	430.3	430.1	429.4	427.6	429.4	430.1	430.3	430.9	432.6	435.4	434.6
7.5°	402.2	401.9	400.1	400.1	400.1	401.9	402.2	403.9	405.7	407.5	409.6
10°	385.6	385.8	383.3	381.8	383.3	385.8	385.6	387.0	389.8	391.2	392.6
12.5°	369.4	368.5	366.5	364.9	366.5	368.5	369.4	370.6	374.3	375.9	378.7
15°	348.2	346.1	341.2	341.5	341.2	346.1	348.2	347.3	351.1	353.2	354.0
17.5°	323.2	321.6	321.6	318.6	321.6	321.6	323.2	324.8	328.1	330.3	336.3
20°	308.5	307.5	307.9	305.0	307.9	307.5	308.5	311.8	313.9	316.8	321.6
22.5°	297.0	296.0	294.3	293.4	294.3	296.0	297.0	299.3	301.6	305.7	308.3
25°	280.3	278.6	277.0	277.9	277.0	278.6	280.3	281.5	285.6	287.5	291.2
27.5°	263.5	262.3	260.6	260.4	260.6	262.3	263.5	264.7	267.0	270.1	274.6
30°	252.8	251.6	250.7	249.7	250.7	251.6	252.8	253.9	256.2	259.5	262.8
32.5°	242.0	241.7	240.3	240.0	240.3	241.7	242.0	243.7	246.0	249.1	252.0
35°	227.9	226.7	226.2	226.4	226.2	226.7	227.9	228.7	230.8	233.7	236.4
37.5°	214.5	212.9	212.0	211.3	212.0	212.9	214.5	214.6	216.7	218.6	222.3
40°	204.8	203.2	202.8	202.3	202.8	203.2	204.8	204.6	206.9	208.4	211.7
42.5°	194.0	193.4	193.1	192.3	193.1	193.4	194.0	195.2	196.4	198.6	201.1
45°	179.3	179.1	177.8	178.3	177.8	179.1	179.3	179.9	182.2	183.7	185.9
47.5°	163.7	162.8	161.9	162.6	161.9	162.8	163.7	164.6	166.1	167.9	170.9
50°	153.1	152.7	150.8	151.2	150.8	152.7	153.1	153.9	155.0	157.3	160.0
52.5°	142.5	140.9	140.2	139.9	140.2	140.9	142.5	143.3	144.5	147.1	149.2
55°	124.8	123.0	122.2	121.7	122.2	123.0	124.8	126.4	128.0	130.9	133.0
57.5°	107.5	107.1	106.4	106.8	106.4	107.1	107.5	109.9	111.6	113.9	116.5
60°	97.5	97.5	97.5	97.2	97.5	97.5	97.5	99.5	100.9	103.3	105.9
62.5°	89.6	89.1	89.0	89.3	89.0	89.1	89.6	90.5	92.0	93.5	95.9
65°	77.7	77.5	76.7	76.4	76.7	77.5	77.7	78.3	79.5	80.6	82.3
67.5°	66.4	65.7	65.5	65.2	65.5	65.7	66.4	67.0	67.8	69.1	70.0
70°	58.0	57.5	56.3	56.5	56.3	57.5	58.0	59.0	59.8	61.5	62.3
72.5°	48.9	48.4	48.2	47.9	48.2	48.4	48.9	49.8	50.6	52.5	53.9
75°	38.6	38.4	38.3	39.1	38.3	38.4	38.6	38.9	39.1	39.7	40.3
77.5°	30.9	30.9	31.1	30.8	31.1	30.9	30.9	30.9	30.9	31.3	31.4
80°	25.9	25.9	25.8	25.8	25.8	25.9	25.9	25.9	25.9	25.9	25.8
82.5°	20.8	21.0	21.1	20.8	21.1	21.0	20.8	21.1	21.3	21.0	21.1
85°	13.7	13.5	13.9	13.7	13.9	13.5	13.7	13.7	13.3	13.7	13.5
87.5°	7.9	7.7	7.7	7.8	7.7	7.7	7.9	7.7	7.5	7.5	7.2
90°	8.8	9.1	9.5	9.1	9.5	9.1	8.8	9.1	8.5	8.2	7.8
92.5°	16.4	15.4	15.8	15.2	15.8	15.4	16.4	16.9	18.5	21.0	26.6
95°	42.9	40.0	37.8	36.6	37.8	40.0	42.9	48.9	60.2	76.9	113.4
97.5°	124.9	110.8	102.2	99.5	102.2	110.8	124.9	148.2	185.8	226.5	282.8
100°	232.6	209.6	197.2	197.6	197.2	209.6	232.6	264.4	309.2	346.0	371.5
102.5°	325.6	307.4	297.1	289.8	297.1	307.4	325.6	350.4	378.7	400.2	401.0
105°	424.5	412.5	402.4	400.8	402.4	412.5	424.5	439.0	447.1	441.1	409.7
107.5°	475.1	471.0	467.6	464.8	467.6	471.0	475.1	474.8	463.6	436.0	384.8
110°	489.7	492.2	491.6	491.0	491.6	492.2	489.7	480.9	458.8	419.1	361.1



TEST NUMBER: P332242-940

CATALOG NUMBER: S123RDIP-S340D365U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	485.9	493.7	496.1	496.2	496.1	493.7	485.9	469.8	441.4	396.9	337.7
115°	465.7	479.6	485.9	487.5	485.9	479.6	465.7	442.1	407.8	361.4	306.6
117.5°	432.6	448.4	457.4	459.6	457.4	448.4	432.6	407.9	373.0	331.4	284.1
120°	409.3	427.0	434.5	436.4	434.5	427.0	409.3	384.4	352.6	314.8	272.2
122.5°	388.2	404.0	412.3	414.7	412.3	404.0	388.2	366.0	336.4	301.4	263.0
125°	360.5	374.3	382.3	384.4	382.3	374.3	360.5	340.4	315.1	284.9	250.5
127.5°	338.5	350.4	357.5	359.4	357.5	350.4	338.5	320.6	297.6	270.3	239.7
130°	324.9	336.3	342.9	345.4	342.9	336.3	324.9	308.2	286.8	261.3	232.8
132.5°	312.5	323.9	329.8	331.5	329.8	323.9	312.5	296.9	276.4	252.6	226.6
135°	294.4	303.8	309.4	311.7	309.4	303.8	294.4	278.8	260.9	240.4	218.0
137.5°	274.8	284.5	289.2	290.7	289.2	284.5	274.8	261.9	246.3	228.6	210.3
140°	262.5	271.3	276.3	276.1	276.3	271.3	262.5	250.5	236.9	221.9	205.8
142.5°	250.4	258.2	262.7	262.4	262.7	258.2	250.4	240.1	228.4	215.3	201.5
145°	233.8	240.4	243.0	243.6	243.0	240.4	233.8	226.0	216.8	206.7	196.4
147.5°	221.0	225.4	227.8	228.1	227.8	225.4	221.0	215.0	208.5	200.4	192.1
150°	213.7	217.1	219.0	219.0	219.0	217.1	213.7	208.9	203.0	196.4	189.0
152.5°	207.1	210.3	211.4	211.4	211.4	210.3	207.1	203.4	198.4	192.5	186.3
155°	198.5	201.1	201.7	202.0	201.7	201.1	198.5	195.6	191.9	187.2	182.2
157.5°	191.0	192.9	193.4	193.3	193.4	192.9	191.0	188.6	185.6	181.9	177.7
160°	186.2	188.2	188.2	187.8	188.2	188.2	186.2	184.0	181.8	178.7	175.2
162.5°	181.5	183.1	183.1	182.8	183.1	183.1	181.5	180.0	178.1	175.1	172.2
165°	175.2	176.5	176.1	176.1	176.1	176.5	175.2	174.0	172.4	170.1	168.3
167.5°	169.2	170.1	169.9	169.9	169.9	170.1	169.2	168.7	167.6	166.3	164.9
170°	165.8	166.4	166.0	166.0	166.0	166.4	165.8	165.4	164.8	163.5	162.6
172.5°	162.7	163.4	162.8	162.6	162.8	163.4	162.7	162.6	162.3	161.3	160.6
175°	158.8	159.2	158.8	158.5	158.8	159.2	158.8	158.8	158.8	158.2	157.8
177.5°	156.4	156.7	156.1	156.1	156.1	156.7	156.4	156.7	156.7	156.4	156.1
180°	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7



TEST NUMBER: P332242-940

CATALOG NUMBER: S123RDIP-S340D365U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3
2.5°	463.2	465.6	467.9	470.0	473.3	474.8	477.0	477.9	480.3	483.9	487.0
5°	435.1	438.4	442.7	446.2	451.8	456.2	461.0	465.6	471.0	478.7	485.5
7.5°	411.2	414.4	419.6	426.2	432.4	438.6	445.1	451.4	459.1	470.1	481.0
10°	395.4	399.3	405.6	412.6	420.3	426.3	434.0	441.8	451.5	464.1	477.2
12.5°	381.7	384.7	391.9	398.6	407.3	415.0	422.5	431.8	442.6	456.1	471.9
15°	360.1	364.2	371.2	378.7	387.9	396.0	405.7	417.0	427.6	444.2	463.2
17.5°	338.2	344.6	352.0	360.3	367.1	378.4	388.9	400.4	413.5	431.1	452.1
20°	324.3	329.3	336.2	348.4	357.3	365.9	375.6	389.9	402.0	422.0	443.7
22.5°	312.5	316.1	323.9	333.9	344.4	354.2	364.2	377.8	392.7	411.6	435.2
25°	295.0	300.9	306.7	313.9	325.1	337.0	347.8	359.4	375.2	395.4	420.9
27.5°	277.9	283.2	288.9	297.8	306.4	317.4	328.8	342.1	359.0	380.3	406.3
30°	267.0	270.9	276.3	287.8	295.4	305.0	318.3	330.1	345.9	368.5	396.0
32.5°	255.7	260.7	266.7	275.4	285.0	294.0	306.1	319.0	335.1	357.4	385.5
35°	239.5	245.6	251.6	258.1	267.6	277.0	287.1	301.2	317.6	339.3	366.8
37.5°	224.7	229.5	234.4	242.5	251.5	260.4	269.9	283.8	299.3	322.6	347.9
40°	215.3	219.6	223.4	231.7	240.4	249.9	259.3	271.5	288.1	310.0	334.5
42.5°	204.9	208.9	214.0	220.9	230.2	238.3	247.6	259.2	274.8	297.0	318.5
45°	189.5	194.0	198.4	204.8	214.2	222.1	230.4	241.4	257.4	275.7	294.8
47.5°	173.3	178.0	183.0	189.2	197.3	205.4	213.7	223.4	238.0	255.9	268.9
50°	163.1	166.8	171.8	178.1	185.6	194.0	201.5	212.1	226.0	240.1	251.4
52.5°	152.5	155.9	161.5	168.1	175.0	182.4	190.4	199.5	212.0	225.3	234.3
55°	135.9	140.0	144.8	151.2	158.1	164.3	172.0	181.4	191.4	201.3	207.3
57.5°	120.4	123.9	127.9	134.5	140.4	147.8	154.8	162.0	171.3	178.8	182.7
60°	109.1	112.2	117.3	123.2	128.8	135.3	143.1	150.4	157.5	163.5	166.6
62.5°	98.4	102.0	106.6	111.9	118.0	124.1	131.0	137.1	143.4	148.6	150.7
65°	84.5	87.5	90.8	95.8	100.8	107.0	112.4	118.6	123.2	126.1	128.0
67.5°	72.0	73.8	76.3	79.7	84.6	90.1	95.2	100.1	104.0	105.9	107.6
70°	63.8	65.0	66.9	70.2	73.9	78.7	84.2	87.7	91.0	92.6	94.3
72.5°	55.6	57.2	58.9	61.6	64.6	68.1	72.1	76.3	78.2	80.2	81.1
75°	42.2	44.5	46.7	48.4	50.5	53.1	56.7	59.4	60.5	62.2	62.3
77.5°	31.8	32.4	34.0	36.0	37.8	39.8	42.0	44.4	44.9	45.7	46.4
80°	26.2	26.2	26.2	27.5	29.5	30.9	33.0	34.2	35.1	35.3	35.5
82.5°	21.0	21.0	20.9	21.1	21.8	22.6	24.5	25.9	26.7	26.5	26.0
85°	13.7	13.3	13.3	13.1	13.3	12.8	12.7	13.5	14.7	14.7	14.4
87.5°	7.1	7.0	7.0	6.7	6.3	6.0	5.4	5.4	5.2	5.7	5.4
90°	7.6	7.8	7.0	6.0	5.1	4.1	3.5	2.9	1.9	1.2	0.6
92.5°	36.6	48.4	53.3	40.0	26.5	18.2	13.6	10.9	8.5	5.8	3.9
95°	151.6	186.9	166.4	114.7	67.8	40.9	28.7	20.5	15.2	11.7	10.7
97.5°	309.8	289.6	212.0	125.8	72.9	47.3	34.1	25.9	21.3	18.5	18.3
100°	360.5	298.5	201.7	118.8	72.1	50.1	37.8	30.2	25.9	23.6	23.4
102.5°	363.0	282.0	186.5	112.7	73.2	53.4	42.1	35.3	31.1	29.2	28.6
105°	343.8	253.3	168.0	108.4	76.0	58.9	49.1	43.2	39.4	37.5	36.6
107.5°	310.1	228.0	156.1	108.1	81.1	66.2	57.1	51.5	47.8	45.9	45.0
110°	289.0	213.7	151.6	109.3	85.4	71.2	62.4	57.1	53.6	52.0	51.0



TEST NUMBER: P332242-940

CATALOG NUMBER: S123RDIP-S340D365U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	270.5	204.0	149.0	111.9	89.7	76.5	67.9	62.6	59.1	57.5	56.6
115°	248.3	193.8	148.1	115.9	96.8	84.8	76.2	70.9	67.8	65.9	64.6
117.5°	234.9	187.7	148.6	121.4	104.2	92.4	84.5	78.6	75.6	74.0	72.6
120°	227.8	184.9	149.7	125.4	109.1	97.6	89.8	83.8	80.7	79.1	78.1
122.5°	222.0	183.2	151.4	129.2	114.0	103.0	94.6	88.9	85.4	83.9	82.9
125°	214.6	180.8	154.1	135.2	121.4	110.3	101.7	95.8	92.3	90.4	89.8
127.5°	208.0	179.8	157.1	140.1	127.6	117.0	108.4	101.8	98.4	95.9	95.1
130°	204.5	179.0	159.2	143.4	131.4	121.0	112.5	105.8	102.1	99.2	98.4
132.5°	201.3	178.7	160.7	146.4	134.6	124.6	116.3	109.7	105.1	102.0	100.9
135°	197.0	178.3	162.9	150.3	139.6	129.8	121.4	114.7	109.9	106.5	105.2
137.5°	193.2	177.6	164.4	153.2	143.0	133.6	125.7	119.1	114.1	110.8	109.4
140°	190.9	177.5	165.4	154.7	145.3	136.2	128.2	122.0	116.9	113.8	112.2
142.5°	189.0	176.9	166.2	156.2	147.0	138.1	130.8	124.5	119.9	116.5	115.2
145°	186.2	176.1	166.7	157.8	149.4	141.2	133.9	128.6	123.9	121.0	120.0
147.5°	183.6	175.0	166.7	158.9	151.2	143.7	137.6	132.4	128.3	125.6	125.0
150°	181.8	174.0	166.7	159.2	152.5	145.3	139.6	135.2	131.1	128.6	128.2
152.5°	179.8	172.7	165.9	159.6	153.3	147.0	141.6	137.7	134.1	131.6	131.5
155°	176.7	170.5	165.1	159.8	154.7	149.4	145.0	141.5	138.3	136.4	136.4
157.5°	173.3	168.5	164.1	160.1	155.5	151.2	147.8	144.9	142.1	140.6	140.4
160°	171.1	167.0	163.5	160.1	156.3	152.5	149.4	147.1	144.6	143.4	143.4
162.5°	168.8	165.5	162.6	159.8	156.6	153.3	150.6	148.6	146.7	145.6	145.6
165°	165.8	163.3	161.0	159.2	156.9	154.4	152.2	151.0	149.4	148.7	149.0
167.5°	162.8	161.0	159.5	158.6	156.9	155.1	153.6	152.8	151.6	151.2	151.6
170°	161.0	159.4	158.5	157.8	156.6	155.1	154.4	153.7	152.8	152.5	153.1
172.5°	159.3	158.2	157.7	157.7	156.6	155.2	154.9	154.5	153.8	153.7	154.2
175°	157.2	156.6	156.6	156.9	156.3	155.7	155.3	155.3	154.7	155.1	155.3
177.5°	156.0	155.7	156.0	156.4	156.0	155.7	155.7	155.7	155.4	155.7	156.0
180°	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7



TEST NUMBER: P332242-940

CATALOG NUMBER: S123RDIP-S340D365U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3
2.5°	487.9	489.8	492.1	495.6	498.3	500.6	501.1	501.8	503.5	506.2	508.4
5°	491.2	495.9	503.5	511.0	519.2	525.8	532.1	536.5	540.6	549.3	556.3
7.5°	490.1	500.8	512.8	526.2	539.8	552.9	565.2	576.1	587.0	599.8	614.2
10°	489.5	501.9	518.2	535.4	554.3	572.7	590.7	604.6	620.7	635.3	653.8
12.5°	486.3	504.3	523.6	545.6	568.9	590.2	613.8	632.9	651.5	672.5	694.0
15°	482.1	504.0	528.5	557.8	593.2	618.8	643.0	676.5	699.3	722.1	752.9
17.5°	474.7	501.3	531.9	570.0	599.4	634.1	670.3	696.8	727.5	759.7	787.6
20°	468.7	499.6	534.0	571.3	608.9	646.5	681.6	713.2	745.0	782.2	805.0
22.5°	462.7	493.3	529.0	568.6	609.0	648.7	688.4	725.5	761.3	798.8	828.0
25°	450.0	486.3	525.0	565.5	605.4	649.0	696.3	737.7	781.9	820.6	848.3
27.5°	437.1	470.5	508.9	550.0	594.3	645.9	701.6	748.6	792.9	820.6	829.3
30°	425.4	460.7	496.1	537.9	585.9	643.4	702.6	756.4	792.7	804.9	795.9
32.5°	413.7	445.7	480.6	523.4	574.4	637.2	703.9	751.8	773.6	764.5	728.1
35°	392.9	421.7	455.6	498.4	557.0	633.8	698.5	730.8	725.5	673.5	604.9
37.5°	370.6	394.1	425.4	470.2	539.0	620.4	674.8	679.7	632.8	553.1	473.9
40°	352.9	374.2	406.4	453.1	525.0	607.1	651.1	631.8	559.3	470.6	404.5
42.5°	335.8	353.7	384.8	435.2	511.7	588.9	615.7	573.6	490.0	406.1	346.0
45°	306.8	323.7	354.8	406.5	484.5	554.3	550.7	477.6	393.9	326.4	276.5
47.5°	279.4	294.1	323.3	376.1	452.5	502.3	469.3	391.5	320.5	266.3	230.7
50°	259.9	274.5	303.5	355.7	427.0	463.2	416.2	341.2	276.1	231.2	203.0
52.5°	241.3	255.5	282.0	332.9	396.0	417.8	367.1	297.6	243.3	204.6	180.4
55°	215.3	226.0	249.9	298.5	345.7	350.7	299.3	241.2	196.5	169.5	152.9
57.5°	188.7	198.0	221.6	260.3	293.4	290.8	242.2	191.8	161.8	141.7	129.7
60°	171.4	180.6	201.3	234.5	259.5	250.7	206.1	165.6	139.8	125.1	115.5
62.5°	155.2	162.4	181.9	206.2	224.1	214.2	176.2	142.7	122.2	109.8	102.2
65°	131.9	137.8	153.3	166.0	175.9	166.4	134.8	111.6	96.8	88.1	82.9
67.5°	109.8	113.4	123.2	127.9	134.9	124.4	101.4	85.8	77.4	70.1	66.4
70°	95.8	98.4	103.7	107.5	109.2	98.4	81.4	70.0	63.0	57.8	55.5
72.5°	81.8	84.2	85.2	88.3	87.3	77.2	65.5	56.4	51.3	47.8	44.9
75°	62.5	63.6	62.5	61.3	58.6	51.5	43.4	38.9	35.1	33.4	32.4
77.5°	45.6	45.2	43.9	41.9	37.3	32.8	28.4	26.9	25.3	24.4	24.1
80°	35.1	34.2	33.0	29.9	25.9	22.8	21.8	20.8	20.2	19.1	18.9
82.5°	26.1	25.6	23.5	21.0	18.2	16.7	15.9	15.4	14.8	14.3	14.3
85°	13.9	13.3	11.0	9.5	9.2	8.7	8.6	8.6	7.7	7.5	7.5
87.5°	4.7	3.8	3.9	3.5	3.7	3.5	3.8	3.7	3.7	3.8	3.6
90°	1.2	1.9	2.9	3.5	4.1	5.1	6.0	7.0	7.8	7.6	7.8
92.5°	5.8	8.5	10.9	13.6	18.2	26.5	40.0	53.3	48.4	36.6	26.6
95°	11.7	15.2	20.5	28.7	40.9	67.8	114.7	166.4	186.9	151.6	113.4
97.5°	18.5	21.3	25.9	34.1	47.3	72.9	125.8	212.0	289.6	309.8	282.8
100°	23.6	25.9	30.2	37.8	50.1	72.1	118.8	201.7	298.5	360.5	371.5
102.5°	29.2	31.1	35.3	42.1	53.4	73.2	112.7	186.5	282.0	363.0	401.0
105°	37.5	39.4	43.2	49.1	58.9	76.0	108.4	168.0	253.3	343.8	409.7
107.5°	45.9	47.8	51.5	57.1	66.2	81.1	108.1	156.1	228.0	310.1	384.8
110°	52.0	53.6	57.1	62.4	71.2	85.4	109.3	151.6	213.7	289.0	361.1



TEST NUMBER: P332242-940

CATALOG NUMBER: S123RDIP-S340D365U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	57.5	59.1	62.6	67.9	76.5	89.7	111.9	149.0	204.0	270.5	337.7
115°	65.9	67.8	70.9	76.2	84.8	96.8	115.9	148.1	193.8	248.3	306.6
117.5°	74.0	75.6	78.6	84.5	92.4	104.2	121.4	148.6	187.7	234.9	284.1
120°	79.1	80.7	83.8	89.8	97.6	109.1	125.4	149.7	184.9	227.8	272.2
122.5°	83.9	85.4	88.9	94.6	103.0	114.0	129.2	151.4	183.2	222.0	263.0
125°	90.4	92.3	95.8	101.7	110.3	121.4	135.2	154.1	180.8	214.6	250.5
127.5°	95.9	98.4	101.8	108.4	117.0	127.6	140.1	157.1	179.8	208.0	239.7
130°	99.2	102.1	105.8	112.5	121.0	131.4	143.4	159.2	179.0	204.5	232.8
132.5°	102.0	105.1	109.7	116.3	124.6	134.6	146.4	160.7	178.7	201.3	226.6
135°	106.5	109.9	114.7	121.4	129.8	139.6	150.3	162.9	178.3	197.0	218.0
137.5°	110.8	114.1	119.1	125.7	133.6	143.0	153.2	164.4	177.6	193.2	210.3
140°	113.8	116.9	122.0	128.2	136.2	145.3	154.7	165.4	177.5	190.9	205.8
142.5°	116.5	119.9	124.5	130.8	138.1	147.0	156.2	166.2	176.9	189.0	201.5
145°	121.0	123.9	128.6	133.9	141.2	149.4	157.8	166.7	176.1	186.2	196.4
147.5°	125.6	128.3	132.4	137.6	143.7	151.2	158.9	166.7	175.0	183.6	192.1
150°	128.6	131.1	135.2	139.6	145.3	152.5	159.2	166.7	174.0	181.8	189.0
152.5°	131.6	134.1	137.7	141.6	147.0	153.3	159.6	165.9	172.7	179.8	186.3
155°	136.4	138.3	141.5	145.0	149.4	154.7	159.8	165.1	170.5	176.7	182.2
157.5°	140.6	142.1	144.9	147.8	151.2	155.5	160.1	164.1	168.5	173.3	177.7
160°	143.4	144.6	147.1	149.4	152.5	156.3	160.1	163.5	167.0	171.1	175.2
162.5°	145.6	146.7	148.6	150.6	153.3	156.6	159.8	162.6	165.5	168.8	172.2
165°	148.7	149.4	151.0	152.2	154.4	156.9	159.2	161.0	163.3	165.8	168.3
167.5°	151.2	151.6	152.8	153.6	155.1	156.9	158.6	159.5	161.0	162.8	164.9
170°	152.5	152.8	153.7	154.4	155.1	156.6	157.8	158.5	159.4	161.0	162.6
172.5°	153.7	153.8	154.5	154.9	155.2	156.6	157.7	157.7	158.2	159.3	160.6
175°	155.1	154.7	155.3	155.3	155.7	156.3	156.9	156.6	156.6	157.2	157.8
177.5°	155.7	155.4	155.7	155.7	155.7	156.0	156.4	156.0	155.7	156.0	156.1
180°	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7



TEST NUMBER: P332242-940

CATALOG NUMBER: S123RDIP-S340D365U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	485.3	485.3	485.3	485.3	485.3	485.3	485.3
2.5°	511.9	511.9	512.6	515.1	515.4	517.5	516.9
5°	562.6	566.5	568.0	574.3	577.9	579.6	576.3
7.5°	624.6	635.7	641.0	647.6	653.3	655.1	650.5
10°	669.8	681.4	691.2	697.2	702.8	706.6	711.3
12.5°	713.5	727.8	737.1	745.6	751.4	756.1	756.9
15°	761.0	782.6	799.0	811.1	817.1	820.2	818.9
17.5°	808.9	828.9	840.6	852.9	861.2	861.7	861.9
20°	836.0	855.5	869.1	878.2	887.5	887.1	889.2
22.5°	854.1	869.5	879.9	886.4	889.7	888.1	888.5
25°	862.6	867.2	865.3	854.7	851.9	842.2	843.9
27.5°	818.9	797.3	774.9	746.2	723.4	705.3	706.2
30°	759.6	721.3	677.7	641.1	608.3	599.1	579.6
32.5°	676.6	619.3	568.2	534.0	506.0	498.3	481.3
35°	536.0	480.3	427.8	396.2	383.7	366.2	366.0
37.5°	416.6	367.6	339.8	316.1	303.7	293.1	292.1
40°	350.4	312.3	291.2	274.2	262.0	254.0	252.2
42.5°	304.3	273.4	253.7	243.2	233.7	229.6	226.6
45°	248.4	227.7	214.0	204.5	200.1	197.0	195.3
47.5°	207.9	193.9	184.6	178.2	174.7	171.4	172.3
50°	185.7	174.3	167.5	161.4	158.7	156.4	156.7
52.5°	167.9	157.7	152.1	147.8	144.5	142.8	142.0
55°	142.5	136.1	130.5	127.3	125.5	123.2	122.6
57.5°	121.5	116.5	112.0	108.5	108.0	105.8	106.1
60°	107.6	103.4	99.7	97.8	96.4	94.5	95.1
62.5°	96.1	92.6	89.3	87.7	86.2	84.9	85.2
65°	78.7	75.4	73.3	72.5	71.9	71.2	70.6
67.5°	62.8	60.7	59.4	57.6	56.4	56.2	55.6
70°	52.8	50.0	47.8	45.5	44.9	44.7	44.9
72.5°	42.3	40.6	39.9	38.9	38.7	38.2	38.5
75°	31.7	31.1	30.8	29.9	29.9	29.9	29.9
77.5°	23.5	23.1	22.8	22.6	22.5	22.1	22.1
80°	18.3	18.1	17.7	17.7	17.5	17.7	17.5
82.5°	13.8	13.7	13.4	13.4	13.1	13.0	13.1
85°	7.0	6.9	7.3	6.9	7.0	6.7	7.0
87.5°	3.7	3.7	3.7	3.6	3.5	3.9	3.5
90°	8.2	8.5	9.1	8.8	9.1	9.5	9.1
92.5°	21.0	18.5	16.9	16.4	15.4	15.8	15.2
95°	76.9	60.2	48.9	42.9	40.0	37.8	36.6
97.5°	226.5	185.8	148.2	124.9	110.8	102.2	99.5
100°	346.0	309.2	264.4	232.6	209.6	197.2	197.6
102.5°	400.2	378.7	350.4	325.6	307.4	297.1	289.8
105°	441.1	447.1	439.0	424.5	412.5	402.4	400.8
107.5°	436.0	463.6	474.8	475.1	471.0	467.6	464.8
110°	419.1	458.8	480.9	489.7	492.2	491.6	491.0



TEST NUMBER: P332242-940

CATALOG NUMBER: S123RDIP-S340D365U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	396.9	441.4	469.8	485.9	493.7	496.1	496.2
115°	361.4	407.8	442.1	465.7	479.6	485.9	487.5
117.5°	331.4	373.0	407.9	432.6	448.4	457.4	459.6
120°	314.8	352.6	384.4	409.3	427.0	434.5	436.4
122.5°	301.4	336.4	366.0	388.2	404.0	412.3	414.7
125°	284.9	315.1	340.4	360.5	374.3	382.3	384.4
127.5°	270.3	297.6	320.6	338.5	350.4	357.5	359.4
130°	261.3	286.8	308.2	324.9	336.3	342.9	345.4
132.5°	252.6	276.4	296.9	312.5	323.9	329.8	331.5
135°	240.4	260.9	278.8	294.4	303.8	309.4	311.7
137.5°	228.6	246.3	261.9	274.8	284.5	289.2	290.7
140°	221.9	236.9	250.5	262.5	271.3	276.3	276.1
142.5°	215.3	228.4	240.1	250.4	258.2	262.7	262.4
145°	206.7	216.8	226.0	233.8	240.4	243.0	243.6
147.5°	200.4	208.5	215.0	221.0	225.4	227.8	228.1
150°	196.4	203.0	208.9	213.7	217.1	219.0	219.0
152.5°	192.5	198.4	203.4	207.1	210.3	211.4	211.4
155°	187.2	191.9	195.6	198.5	201.1	201.7	202.0
157.5°	181.9	185.6	188.6	191.0	192.9	193.4	193.3
160°	178.7	181.8	184.0	186.2	188.2	188.2	187.8
162.5°	175.1	178.1	180.0	181.5	183.1	183.1	182.8
165°	170.1	172.4	174.0	175.2	176.5	176.1	176.1
167.5°	166.3	167.6	168.7	169.2	170.1	169.9	169.9
170°	163.5	164.8	165.4	165.8	166.4	166.0	166.0
172.5°	161.3	162.3	162.6	162.7	163.4	162.8	162.6
175°	158.2	158.8	158.8	158.8	159.2	158.8	158.5
177.5°	156.4	156.7	156.7	156.4	156.7	156.1	156.1
180°	155.7	155.7	155.7	155.7	155.7	155.7	155.7

(END OF REPORT)