

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332246-940

Luminaire Tested: **S123RDIP-S340D585U940-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332246-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S340D585U940-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 585 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3297.8 lumens
Efficiency: N/A
Efficacy: 128.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332246-940

CATALOG NUMBER: S123RDIP-S340D585U940-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332246-940

CATALOG NUMBER: S123RDIP-S340D585U940-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	37
1	95	91	87	84	86	83	80	77	67	65	63	53	51	50	39	39	38	32
2	87	80	74	69	79	73	68	64	59	56	53	47	44	42	35	34	33	27
3	80	71	64	58	72	64	59	54	53	48	45	42	39	36	32	30	28	24
4	73	63	55	50	66	57	51	46	47	42	39	37	34	31	28	26	25	21
5	67	56	48	43	61	51	45	40	42	37	33	34	30	27	26	24	22	18
6	62	50	43	37	56	46	39	34	38	33	29	31	27	24	24	21	19	16
7	57	45	38	33	52	42	35	30	35	30	26	28	24	21	22	19	17	14
8	53	41	34	29	48	38	31	27	32	27	23	26	22	19	20	17	15	13
9	49	38	30	26	45	35	28	24	29	24	21	23	20	17	18	16	14	12
10	46	34	28	23	42	32	26	21	27	22	19	22	18	16	17	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5224	5224	5224	5224
5°	6227	5246	4620	5246
10°	7774	5216	4173	5216
15°	9126	5162	3806	5162
20°	10186	5082	3494	5082
25°	10023	4999	3301	4999
30°	7204	4922	3104	4922
35°	4809	4820	2975	4820
40°	3544	4700	2843	4700
45°	2973	4488	2714	4488
50°	2624	4210	2532	4210
55°	2301	3890	2284	3890
60°	2047	3587	2093	3587
65°	1798	3260	1946	3260
70°	1413	2968	1778	2968
75°	1243	2591	1626	2591
80°	1085	2201	1599	2201
85°	865	1778	1692	1778



TEST NUMBER: P332246-940

CATALOG NUMBER: S123RDIP-S340D585U940-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.7	1.4
10°-20°	149.1	4.5
20°-30°	234.2	7.1
30°-40°	244.4	7.4
40°-50°	209.1	6.3
50°-60°	159.4	4.8
60°-70°	102.2	3.1
70°-80°	49.1	1.5
80°-90°	14.9	0.5
90°-100°	24.9	0.8
100°-110°	118.6	3.6
110°-120°	284.9	8.6
120°-130°	362.8	11.0
130°-140°	387.7	11.8
140°-150°	362.5	11.0
150°-160°	292.4	8.9
160°-170°	188.7	5.7
170°-180°	65.0	2.0
0°-30°	431.1	13.1
0°-40°	675.4	20.5
0°-60°	1044.0	31.7
0°-90°	1210.2	36.7
90°-120°	428.4	13.0
90°-150°	1541.4	46.7
90°-180°	2088.0	63.3
0°-180°	3297.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	485	485	485	485	485	
5°	576	486	428	486	576	59
15°	819	463	342	463	819	232
25°	844	421	278	421	844	363
35°	366	367	226	367	366	240
45°	195	295	178	295	195	154
55°	123	207	122	207	123	111
65°	71	128	76	128	71	69
75°	30	62	39	62	30	32
85°	7	14	14	14	7	8
90°	15	0	15	0	15	7
95°	19	31	19	31	19	16
105°	22	152	22	152	22	51
115°	299	284	299	284	299	276
125°	409	401	409	401	409	365
135°	504	499	504	499	504	389
145°	581	576	581	576	581	363
155°	633	634	633	634	633	292
165°	667	669	667	669	667	188
175°	682	685	682	685	682	65
180°	685	685	685	685	685	



TEST NUMBER: P332246-940

CATALOG NUMBER: S123RDIP-S340D585U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3
2.5°	516.9	517.5	515.4	515.1	512.6	511.9	511.9	508.4	506.2	503.5	501.8
5°	576.3	579.6	577.9	574.3	568.0	566.5	562.6	556.3	549.3	540.6	536.5
7.5°	650.5	655.1	653.3	647.6	641.0	635.7	624.6	614.2	599.8	587.0	576.1
10°	711.3	706.6	702.8	697.2	691.2	681.4	669.8	653.8	635.3	620.7	604.6
12.5°	756.9	756.1	751.4	745.6	737.1	727.8	713.5	694.0	672.5	651.5	632.9
15°	818.9	820.2	817.1	811.1	799.0	782.6	761.0	752.9	722.1	699.3	676.5
17.5°	861.9	861.7	861.2	852.9	840.6	828.9	808.9	787.6	759.7	727.5	696.8
20°	889.2	887.1	887.5	878.2	869.1	855.5	836.0	805.0	782.2	745.0	713.2
22.5°	888.5	888.1	889.7	886.4	879.9	869.5	854.1	828.0	798.8	761.3	725.5
25°	843.9	842.2	851.9	854.7	865.3	867.2	862.6	848.3	820.6	781.9	737.7
27.5°	706.2	705.3	723.4	746.2	774.9	797.3	818.9	829.3	820.6	792.9	748.6
30°	579.6	599.1	608.3	641.1	677.7	721.3	759.6	795.9	804.9	792.7	756.4
32.5°	481.3	498.3	506.0	534.0	568.2	619.3	676.6	728.1	764.5	773.6	751.8
35°	366.0	366.2	383.7	396.2	427.8	480.3	536.0	604.9	673.5	725.5	730.8
37.5°	292.1	293.1	303.7	316.1	339.8	367.6	416.6	473.9	553.1	632.8	679.7
40°	252.2	254.0	262.0	274.2	291.2	312.3	350.4	404.5	470.6	559.3	631.8
42.5°	226.6	229.6	233.7	243.2	253.7	273.4	304.3	346.0	406.1	490.0	573.6
45°	195.3	197.0	200.1	204.5	214.0	227.7	248.4	276.5	326.4	393.9	477.6
47.5°	172.3	171.4	174.7	178.2	184.6	193.9	207.9	230.7	266.3	320.5	391.5
50°	156.7	156.4	158.7	161.4	167.5	174.3	185.7	203.0	231.2	276.1	341.2
52.5°	142.0	142.8	144.5	147.8	152.1	157.7	167.9	180.4	204.6	243.3	297.6
55°	122.6	123.2	125.5	127.3	130.5	136.1	142.5	152.9	169.5	196.5	241.2
57.5°	106.1	105.8	108.0	108.5	112.0	116.5	121.5	129.7	141.7	161.8	191.8
60°	95.1	94.5	96.4	97.8	99.7	103.4	107.6	115.5	125.1	139.8	165.6
62.5°	85.2	84.9	86.2	87.7	89.3	92.6	96.1	102.2	109.8	122.2	142.7
65°	70.6	71.2	71.9	72.5	73.3	75.4	78.7	82.9	88.1	96.8	111.6
67.5°	55.6	56.2	56.4	57.6	59.4	60.7	62.8	66.4	70.1	77.4	85.8
70°	44.9	44.7	44.9	45.5	47.8	50.0	52.8	55.5	57.8	63.0	70.0
72.5°	38.5	38.2	38.7	38.9	39.9	40.6	42.3	44.9	47.8	51.3	56.4
75°	29.9	29.9	29.9	29.9	30.8	31.1	31.7	32.4	33.4	35.1	38.9
77.5°	22.1	22.1	22.5	22.6	22.8	23.1	23.5	24.1	24.4	25.3	26.9
80°	17.5	17.7	17.5	17.7	17.7	18.1	18.3	18.9	19.1	20.2	20.8
82.5°	13.1	13.0	13.1	13.4	13.4	13.7	13.8	14.3	14.3	14.8	15.4
85°	7.0	6.7	7.0	6.9	7.3	6.9	7.0	7.5	7.5	7.7	8.6
87.5°	4.7	5.0	4.6	4.7	4.7	4.8	4.7	4.6	4.8	4.6	4.5
90°	15.2	15.1	14.8	14.6	14.4	14.0	13.6	13.1	12.7	12.2	10.7
92.5°	16.9	16.8	16.6	16.5	16.3	15.9	15.2	14.4	13.7	13.0	11.9
95°	19.4	19.4	19.4	19.4	19.4	18.9	18.1	17.4	16.6	15.8	14.5
97.5°	21.0	20.9	20.7	20.6	20.5	20.0	19.1	18.2	17.3	16.4	24.5
100°	21.4	21.2	21.1	21.0	20.9	20.4	19.5	18.5	17.7	16.8	34.4
102.5°	21.8	21.6	21.4	21.1	21.0	22.3	25.1	27.8	30.7	33.4	52.7
105°	22.4	22.1	21.9	21.7	21.5	31.4	51.4	71.3	91.4	111.4	121.5
107.5°	70.3	85.3	100.4	115.5	130.6	145.4	160.2	174.8	189.5	204.1	202.5
110°	139.8	156.0	172.2	188.3	204.5	214.5	218.2	221.9	225.6	229.3	228.1



TEST NUMBER: P332246-940

CATALOG NUMBER: S123RDIP-S340D585U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	240.0	243.3	246.7	250.2	253.6	255.3	255.2	255.1	255.1	255.0	253.8
115°	299.1	298.6	298.2	297.7	297.2	296.5	295.3	294.2	293.1	291.9	290.9
117.5°	332.3	332.2	332.1	332.0	331.9	331.4	330.5	329.6	328.7	327.7	327.3
120°	355.0	355.0	355.0	355.0	355.0	354.5	353.7	352.8	351.9	350.9	350.6
122.5°	377.4	377.3	377.2	377.1	377.0	376.7	376.0	375.4	374.8	374.2	373.7
125°	408.9	408.7	408.5	408.2	408.0	407.8	407.5	407.3	407.1	406.9	406.4
127.5°	439.3	439.4	439.7	439.9	440.1	440.1	439.7	439.3	439.0	438.6	438.1
130°	458.8	459.0	459.2	459.4	459.7	459.5	459.1	458.6	458.2	457.7	457.3
132.5°	476.6	477.0	477.2	477.6	478.0	477.9	477.4	477.0	476.5	476.1	475.6
135°	504.0	504.4	504.7	505.1	505.3	505.3	505.1	504.7	504.4	504.0	503.5
137.5°	529.8	529.9	530.2	530.4	530.7	530.5	529.9	529.4	528.9	528.3	528.1
140°	545.2	545.5	545.6	545.9	546.1	546.0	545.5	545.1	544.7	544.2	543.9
142.5°	559.5	559.7	560.1	560.4	560.7	560.7	560.4	560.0	559.6	559.3	558.9
145°	581.3	581.3	581.3	581.3	581.3	581.2	580.9	580.8	580.5	580.3	580.1
147.5°	597.6	598.2	598.6	599.1	599.7	599.9	599.6	599.4	599.1	599.0	598.7
150°	609.8	610.1	610.5	610.8	611.2	611.2	611.0	610.7	610.6	610.3	610.1
152.5°	619.6	620.1	620.6	621.2	621.6	621.7	621.3	620.9	620.5	620.1	619.9
155°	633.2	633.9	634.5	635.3	635.9	636.0	635.4	634.8	634.3	633.7	633.6
157.5°	644.7	645.6	646.5	647.3	648.2	648.4	647.6	646.9	646.3	645.6	645.7
160°	652.0	652.8	653.6	654.4	655.1	655.2	654.5	653.9	653.2	652.6	652.6
162.5°	659.0	659.6	660.3	661.0	661.7	661.7	660.9	660.1	659.4	658.6	658.7
165°	667.3	668.1	668.9	669.7	670.5	670.4	669.5	668.6	667.7	666.7	666.9
167.5°	673.2	674.2	675.1	676.0	676.9	676.9	676.0	675.1	674.2	673.2	673.2
170°	676.9	677.9	678.8	679.7	680.6	680.6	679.7	678.8	677.9	676.9	676.9
172.5°	678.9	679.9	681.0	682.0	683.0	683.0	682.1	681.2	680.3	679.4	679.3
175°	682.0	683.0	683.9	684.7	685.6	685.7	684.9	684.1	683.3	682.5	682.4
177.5°	683.0	683.9	684.7	685.6	686.5	686.6	685.9	685.2	684.5	683.8	683.7
180°	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6



TEST NUMBER: P332246-940

CATALOG NUMBER: S123RDIP-S340D585U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3
2.5°	501.1	500.6	498.3	495.6	492.1	489.8	487.9	487.0	483.9	480.3	477.9
5°	532.1	525.8	519.2	511.0	503.5	495.9	491.2	485.5	478.7	471.0	465.6
7.5°	565.2	552.9	539.8	526.2	512.8	500.8	490.1	481.0	470.1	459.1	451.4
10°	590.7	572.7	554.3	535.4	518.2	501.9	489.5	477.2	464.1	451.5	441.8
12.5°	613.8	590.2	568.9	545.6	523.6	504.3	486.3	471.9	456.1	442.6	431.8
15°	643.0	618.8	593.2	557.8	528.5	504.0	482.1	463.2	444.2	427.6	417.0
17.5°	670.3	634.1	599.4	570.0	531.9	501.3	474.7	452.1	431.1	413.5	400.4
20°	681.6	646.5	608.9	571.3	534.0	499.6	468.7	443.7	422.0	402.0	389.9
22.5°	688.4	648.7	609.0	568.6	529.0	493.3	462.7	435.2	411.6	392.7	377.8
25°	696.3	649.0	605.4	565.5	525.0	486.3	450.0	420.9	395.4	375.2	359.4
27.5°	701.6	645.9	594.3	550.0	508.9	470.5	437.1	406.3	380.3	359.0	342.1
30°	702.6	643.4	585.9	537.9	496.1	460.7	425.4	396.0	368.5	345.9	330.1
32.5°	703.9	637.2	574.4	523.4	480.6	445.7	413.7	385.5	357.4	335.1	319.0
35°	698.5	633.8	557.0	498.4	455.6	421.7	392.9	366.8	339.3	317.6	301.2
37.5°	674.8	620.4	539.0	470.2	425.4	394.1	370.6	347.9	322.6	299.3	283.8
40°	651.1	607.1	525.0	453.1	406.4	374.2	352.9	334.5	310.0	288.1	271.5
42.5°	615.7	588.9	511.7	435.2	384.8	353.7	335.8	318.5	297.0	274.8	259.2
45°	550.7	554.3	484.5	406.5	354.8	323.7	306.8	294.8	275.7	257.4	241.4
47.5°	469.3	502.3	452.5	376.1	323.3	294.1	279.4	268.9	255.9	238.0	223.4
50°	416.2	463.2	427.0	355.7	303.5	274.5	259.9	251.4	240.1	226.0	212.1
52.5°	367.1	417.8	396.0	332.9	282.0	255.5	241.3	234.3	225.3	212.0	199.5
55°	299.3	350.7	345.7	298.5	249.9	226.0	215.3	207.3	201.3	191.4	181.4
57.5°	242.2	290.8	293.4	260.3	221.6	198.0	188.7	182.7	178.8	171.3	162.0
60°	206.1	250.7	259.5	234.5	201.3	180.6	171.4	166.6	163.5	157.5	150.4
62.5°	176.2	214.2	224.1	206.2	181.9	162.4	155.2	150.7	148.6	143.4	137.1
65°	134.8	166.4	175.9	166.0	153.3	137.8	131.9	128.0	126.1	123.2	118.6
67.5°	101.4	124.4	134.9	127.9	123.2	113.4	109.8	107.6	105.9	104.0	100.1
70°	81.4	98.4	109.2	107.5	103.7	98.4	95.8	94.3	92.6	91.0	87.7
72.5°	65.5	77.2	87.3	88.3	85.2	84.2	81.8	81.1	80.2	78.2	76.3
75°	43.4	51.5	58.6	61.3	62.5	63.6	62.5	62.3	62.2	60.5	59.4
77.5°	28.4	32.8	37.3	41.9	43.9	45.2	45.6	46.4	45.7	44.9	44.4
80°	21.8	22.8	25.9	29.9	33.0	34.2	35.1	35.5	35.3	35.1	34.2
82.5°	15.9	16.7	18.2	21.0	23.5	25.6	26.1	26.0	26.5	26.7	25.9
85°	8.6	8.7	9.2	9.5	11.0	13.3	13.9	14.4	14.7	14.7	13.5
87.5°	4.5	4.0	4.1	3.8	4.1	4.0	4.8	5.4	5.8	5.4	5.6
90°	9.3	7.8	6.3	5.0	3.9	2.8	1.6	0.5	1.6	2.8	3.9
92.5°	10.8	9.7	8.6	8.2	8.5	8.8	9.2	9.5	9.2	8.8	8.5
95°	13.3	12.0	10.8	12.5	17.1	21.8	26.4	31.0	26.4	21.8	17.1
97.5°	32.6	40.8	49.0	54.0	56.1	58.2	60.3	62.3	60.3	58.2	56.1
100°	52.1	69.6	87.3	95.0	92.7	90.5	88.2	86.0	88.2	90.5	92.7
102.5°	72.0	91.2	110.5	119.3	117.7	116.1	114.4	112.8	114.4	116.1	117.7
105°	131.7	141.9	152.0	156.5	155.2	154.1	152.8	151.6	152.8	154.1	155.2
107.5°	200.9	199.3	197.7	196.4	195.5	194.5	193.4	192.4	193.4	194.5	195.5
110°	226.9	225.6	224.4	223.3	222.4	221.5	220.6	219.7	220.6	221.5	222.4



TEST NUMBER: P332246-940

CATALOG NUMBER: S123RDIP-S340D585U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	252.5	251.3	250.0	249.0	248.2	247.4	246.6	245.8	246.6	247.4	248.2
115°	289.9	288.9	287.8	287.0	286.3	285.6	285.0	284.3	285.0	285.6	286.3
117.5°	326.7	326.2	325.7	324.9	324.1	323.3	322.4	321.6	322.4	323.3	324.1
120°	350.3	349.9	349.6	348.9	347.9	346.9	345.8	344.8	345.8	346.9	347.9
122.5°	373.3	372.8	372.4	371.8	371.0	370.1	369.3	368.5	369.3	370.1	371.0
125°	406.0	405.6	405.1	404.4	403.5	402.6	401.7	400.7	401.7	402.6	403.5
127.5°	437.6	436.9	436.4	435.7	434.8	433.9	433.0	432.1	433.0	433.9	434.8
130°	456.8	456.4	455.9	455.2	454.3	453.4	452.5	451.7	452.5	453.4	454.3
132.5°	475.3	474.9	474.6	473.9	473.1	472.2	471.3	470.4	471.3	472.2	473.1
135°	503.1	502.7	502.2	501.7	501.0	500.2	499.6	498.9	499.6	500.2	501.0
137.5°	527.8	527.5	527.4	526.7	525.9	525.0	524.2	523.3	524.2	525.0	525.9
140°	543.5	543.1	542.9	542.3	541.6	541.0	540.3	539.6	540.3	541.0	541.6
142.5°	558.6	558.2	557.9	557.4	556.7	556.1	555.4	554.6	555.4	556.1	556.7
145°	579.9	579.6	579.4	578.9	578.1	577.3	576.5	575.7	576.5	577.3	578.1
147.5°	598.4	598.2	598.0	597.6	597.1	596.6	596.1	595.6	596.1	596.6	597.1
150°	609.8	609.7	609.4	609.1	608.8	608.4	608.1	607.8	608.1	608.4	608.8
152.5°	619.8	619.6	619.6	619.4	619.2	619.0	618.9	618.8	618.9	619.0	619.2
155°	633.5	633.4	633.3	633.3	633.6	633.7	634.0	634.2	634.0	633.7	633.6
157.5°	645.9	646.0	646.0	646.1	646.1	646.1	646.2	646.2	646.2	646.1	646.1
160°	652.7	652.8	653.0	653.1	653.2	653.4	653.4	653.5	653.4	653.4	653.2
162.5°	658.9	659.0	659.1	659.2	659.6	659.9	660.1	660.5	660.1	659.9	659.6
165°	667.0	667.1	667.2	667.4	667.8	668.2	668.4	668.8	668.4	668.2	667.8
167.5°	673.2	673.2	673.2	673.5	674.0	674.4	674.8	675.3	674.8	674.4	674.0
170°	676.9	676.9	676.9	677.2	677.6	678.1	678.5	678.9	678.5	678.1	677.6
172.5°	679.2	679.1	679.0	679.2	679.8	680.3	680.9	681.4	680.9	680.3	679.8
175°	682.3	682.2	682.1	682.3	682.9	683.4	684.0	684.6	684.0	683.4	682.9
177.5°	683.6	683.5	683.4	683.6	684.0	684.5	684.9	685.4	684.9	684.5	684.0
180°	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6



TEST NUMBER: P332246-940

CATALOG NUMBER: S123RDIP-S340D585U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3
2.5°	477.0	474.8	473.3	470.0	467.9	465.6	463.2	464.7	464.5	464.4	464.4
5°	461.0	456.2	451.8	446.2	442.7	438.4	435.1	434.6	435.4	432.6	430.9
7.5°	445.1	438.6	432.4	426.2	419.6	414.4	411.2	409.6	407.5	405.7	403.9
10°	434.0	426.3	420.3	412.6	405.6	399.3	395.4	392.6	391.2	389.8	387.0
12.5°	422.5	415.0	407.3	398.6	391.9	384.7	381.7	378.7	375.9	374.3	370.6
15°	405.7	396.0	387.9	378.7	371.2	364.2	360.1	354.0	353.2	351.1	347.3
17.5°	388.9	378.4	367.1	360.3	352.0	344.6	338.2	336.3	330.3	328.1	324.8
20°	375.6	365.9	357.3	348.4	336.2	329.3	324.3	321.6	316.8	313.9	311.8
22.5°	364.2	354.2	344.4	333.9	323.9	316.1	312.5	308.3	305.7	301.6	299.3
25°	347.8	337.0	325.1	313.9	306.7	300.9	295.0	291.2	287.5	285.6	281.5
27.5°	328.8	317.4	306.4	297.8	288.9	283.2	277.9	274.6	270.1	267.0	264.7
30°	318.3	305.0	295.4	287.8	276.3	270.9	267.0	262.8	259.5	256.2	253.9
32.5°	306.1	294.0	285.0	275.4	266.7	260.7	255.7	252.0	249.1	246.0	243.7
35°	287.1	277.0	267.6	258.1	251.6	245.6	239.5	236.4	233.7	230.8	228.7
37.5°	269.9	260.4	251.5	242.5	234.4	229.5	224.7	222.3	218.6	216.7	214.6
40°	259.3	249.9	240.4	231.7	223.4	219.6	215.3	211.7	208.4	206.9	204.6
42.5°	247.6	238.3	230.2	220.9	214.0	208.9	204.9	201.1	198.6	196.4	195.2
45°	230.4	222.1	214.2	204.8	198.4	194.0	189.5	185.9	183.7	182.2	179.9
47.5°	213.7	205.4	197.3	189.2	183.0	178.0	173.3	170.9	167.9	166.1	164.6
50°	201.5	194.0	185.6	178.1	171.8	166.8	163.1	160.0	157.3	155.0	153.9
52.5°	190.4	182.4	175.0	168.1	161.5	155.9	152.5	149.2	147.1	144.5	143.3
55°	172.0	164.3	158.1	151.2	144.8	140.0	135.9	133.0	130.9	128.0	126.4
57.5°	154.8	147.8	140.4	134.5	127.9	123.9	120.4	116.5	113.9	111.6	109.9
60°	143.1	135.3	128.8	123.2	117.3	112.2	109.1	105.9	103.3	100.9	99.5
62.5°	131.0	124.1	118.0	111.9	106.6	102.0	98.4	95.9	93.5	92.0	90.5
65°	112.4	107.0	100.8	95.8	90.8	87.5	84.5	82.3	80.6	79.5	78.3
67.5°	95.2	90.1	84.6	79.7	76.3	73.8	72.0	70.0	69.1	67.8	67.0
70°	84.2	78.7	73.9	70.2	66.9	65.0	63.8	62.3	61.5	59.8	59.0
72.5°	72.1	68.1	64.6	61.6	58.9	57.2	55.6	53.9	52.5	50.6	49.8
75°	56.7	53.1	50.5	48.4	46.7	44.5	42.2	40.3	39.7	39.1	38.9
77.5°	42.0	39.8	37.8	36.0	34.0	32.4	31.8	31.4	31.3	30.9	30.9
80°	33.0	30.9	29.5	27.5	26.2	26.2	26.2	25.8	25.9	25.9	25.9
82.5°	24.5	22.6	21.8	21.1	20.9	21.0	21.0	21.1	21.0	21.3	21.1
85°	12.7	12.8	13.3	13.1	13.3	13.3	13.7	13.5	13.7	13.3	13.7
87.5°	5.6	6.4	6.9	7.3	7.8	7.9	8.2	8.3	8.6	8.6	8.6
90°	5.0	6.3	7.8	9.3	10.7	12.2	12.7	13.1	13.6	14.0	14.4
92.5°	8.2	8.6	9.7	10.8	11.9	13.0	13.7	14.4	15.2	15.9	16.3
95°	12.5	10.8	12.0	13.3	14.5	15.8	16.6	17.4	18.1	18.9	19.4
97.5°	54.0	49.0	40.8	32.6	24.5	16.4	17.3	18.2	19.1	20.0	20.5
100°	95.0	87.3	69.6	52.1	34.4	16.8	17.7	18.5	19.5	20.4	20.9
102.5°	119.3	110.5	91.2	72.0	52.7	33.4	30.7	27.8	25.1	22.3	21.0
105°	156.5	152.0	141.9	131.7	121.5	111.4	91.4	71.3	51.4	31.4	21.5
107.5°	196.4	197.7	199.3	200.9	202.5	204.1	189.5	174.8	160.2	145.4	130.6
110°	223.3	224.4	225.6	226.9	228.1	229.3	225.6	221.9	218.2	214.5	204.5



TEST NUMBER: P332246-940

CATALOG NUMBER: S123RDIP-S340D585U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	249.0	250.0	251.3	252.5	253.8	255.0	255.1	255.1	255.2	255.3	253.6
115°	287.0	287.8	288.9	289.9	290.9	291.9	293.1	294.2	295.3	296.5	297.2
117.5°	324.9	325.7	326.2	326.7	327.3	327.7	328.7	329.6	330.5	331.4	331.9
120°	348.9	349.6	349.9	350.3	350.6	350.9	351.9	352.8	353.7	354.5	355.0
122.5°	371.8	372.4	372.8	373.3	373.7	374.2	374.8	375.4	376.0	376.7	377.0
125°	404.4	405.1	405.6	406.0	406.4	406.9	407.1	407.3	407.5	407.8	408.0
127.5°	435.7	436.4	436.9	437.6	438.1	438.6	439.0	439.3	439.7	440.1	440.1
130°	455.2	455.9	456.4	456.8	457.3	457.7	458.2	458.6	459.1	459.5	459.7
132.5°	473.9	474.6	474.9	475.3	475.6	476.1	476.5	477.0	477.4	477.9	478.0
135°	501.7	502.2	502.7	503.1	503.5	504.0	504.4	504.7	505.1	505.3	505.3
137.5°	526.7	527.4	527.5	527.8	528.1	528.3	528.9	529.4	529.9	530.5	530.7
140°	542.3	542.9	543.1	543.5	543.9	544.2	544.7	545.1	545.5	546.0	546.1
142.5°	557.4	557.9	558.2	558.6	558.9	559.3	559.6	560.0	560.4	560.7	560.7
145°	578.9	579.4	579.6	579.9	580.1	580.3	580.5	580.8	580.9	581.2	581.3
147.5°	597.6	598.0	598.2	598.4	598.7	599.0	599.1	599.4	599.6	599.9	599.7
150°	609.1	609.4	609.7	609.8	610.1	610.3	610.6	610.7	611.0	611.2	611.2
152.5°	619.4	619.6	619.6	619.8	619.9	620.1	620.5	620.9	621.3	621.7	621.6
155°	633.3	633.3	633.4	633.5	633.6	633.7	634.3	634.8	635.4	636.0	635.9
157.5°	646.1	646.0	646.0	645.9	645.7	645.6	646.3	646.9	647.6	648.4	648.2
160°	653.1	653.0	652.8	652.7	652.6	652.6	653.2	653.9	654.5	655.2	655.1
162.5°	659.2	659.1	659.0	658.9	658.7	658.6	659.4	660.1	660.9	661.7	661.7
165°	667.4	667.2	667.1	667.0	666.9	666.7	667.7	668.6	669.5	670.4	670.5
167.5°	673.5	673.2	673.2	673.2	673.2	673.2	674.2	675.1	676.0	676.9	676.9
170°	677.2	676.9	676.9	676.9	676.9	676.9	677.9	678.8	679.7	680.6	680.6
172.5°	679.2	679.0	679.1	679.2	679.3	679.4	680.3	681.2	682.1	683.0	683.0
175°	682.3	682.1	682.2	682.3	682.4	682.5	683.3	684.1	684.9	685.7	685.6
177.5°	683.6	683.4	683.5	683.6	683.7	683.8	684.5	685.2	685.9	686.6	686.5
180°	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6



TEST NUMBER: P332246-940

CATALOG NUMBER: S123RDIP-S340D585U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3
2.5°	462.4	462.2	462.4	461.7	462.4	462.2	462.4	464.4	464.4	464.5	464.7
5°	430.3	430.1	429.4	427.6	429.4	430.1	430.3	430.9	432.6	435.4	434.6
7.5°	402.2	401.9	400.1	400.1	400.1	401.9	402.2	403.9	405.7	407.5	409.6
10°	385.6	385.8	383.3	381.8	383.3	385.8	385.6	387.0	389.8	391.2	392.6
12.5°	369.4	368.5	366.5	364.9	366.5	368.5	369.4	370.6	374.3	375.9	378.7
15°	348.2	346.1	341.2	341.5	341.2	346.1	348.2	347.3	351.1	353.2	354.0
17.5°	323.2	321.6	321.6	318.6	321.6	321.6	323.2	324.8	328.1	330.3	336.3
20°	308.5	307.5	307.9	305.0	307.9	307.5	308.5	311.8	313.9	316.8	321.6
22.5°	297.0	296.0	294.3	293.4	294.3	296.0	297.0	299.3	301.6	305.7	308.3
25°	280.3	278.6	277.0	277.9	277.0	278.6	280.3	281.5	285.6	287.5	291.2
27.5°	263.5	262.3	260.6	260.4	260.6	262.3	263.5	264.7	267.0	270.1	274.6
30°	252.8	251.6	250.7	249.7	250.7	251.6	252.8	253.9	256.2	259.5	262.8
32.5°	242.0	241.7	240.3	240.0	240.3	241.7	242.0	243.7	246.0	249.1	252.0
35°	227.9	226.7	226.2	226.4	226.2	226.7	227.9	228.7	230.8	233.7	236.4
37.5°	214.5	212.9	212.0	211.3	212.0	212.9	214.5	214.6	216.7	218.6	222.3
40°	204.8	203.2	202.8	202.3	202.8	203.2	204.8	204.6	206.9	208.4	211.7
42.5°	194.0	193.4	193.1	192.3	193.1	193.4	194.0	195.2	196.4	198.6	201.1
45°	179.3	179.1	177.8	178.3	177.8	179.1	179.3	179.9	182.2	183.7	185.9
47.5°	163.7	162.8	161.9	162.6	161.9	162.8	163.7	164.6	166.1	167.9	170.9
50°	153.1	152.7	150.8	151.2	150.8	152.7	153.1	153.9	155.0	157.3	160.0
52.5°	142.5	140.9	140.2	139.9	140.2	140.9	142.5	143.3	144.5	147.1	149.2
55°	124.8	123.0	122.2	121.7	122.2	123.0	124.8	126.4	128.0	130.9	133.0
57.5°	107.5	107.1	106.4	106.8	106.4	107.1	107.5	109.9	111.6	113.9	116.5
60°	97.5	97.5	97.5	97.2	97.5	97.5	97.5	99.5	100.9	103.3	105.9
62.5°	89.6	89.1	89.0	89.3	89.0	89.1	89.6	90.5	92.0	93.5	95.9
65°	77.7	77.5	76.7	76.4	76.7	77.5	77.7	78.3	79.5	80.6	82.3
67.5°	66.4	65.7	65.5	65.2	65.5	65.7	66.4	67.0	67.8	69.1	70.0
70°	58.0	57.5	56.3	56.5	56.3	57.5	58.0	59.0	59.8	61.5	62.3
72.5°	48.9	48.4	48.2	47.9	48.2	48.4	48.9	49.8	50.6	52.5	53.9
75°	38.6	38.4	38.3	39.1	38.3	38.4	38.6	38.9	39.1	39.7	40.3
77.5°	30.9	30.9	31.1	30.8	31.1	30.9	30.9	30.9	30.9	31.3	31.4
80°	25.9	25.9	25.8	25.8	25.8	25.9	25.9	25.9	25.9	25.9	25.8
82.5°	20.8	21.0	21.1	20.8	21.1	21.0	20.8	21.1	21.3	21.0	21.1
85°	13.7	13.5	13.9	13.7	13.9	13.5	13.7	13.7	13.3	13.7	13.5
87.5°	9.1	8.7	8.8	9.0	8.8	8.7	9.1	8.6	8.6	8.6	8.3
90°	14.6	14.8	15.1	15.2	15.1	14.8	14.6	14.4	14.0	13.6	13.1
92.5°	16.5	16.6	16.8	16.9	16.8	16.6	16.5	16.3	15.9	15.2	14.4
95°	19.4	19.4	19.4	19.4	19.4	19.4	19.4	19.4	18.9	18.1	17.4
97.5°	20.6	20.7	20.9	21.0	20.9	20.7	20.6	20.5	20.0	19.1	18.2
100°	21.0	21.1	21.2	21.4	21.2	21.1	21.0	20.9	20.4	19.5	18.5
102.5°	21.1	21.4	21.6	21.8	21.6	21.4	21.1	21.0	22.3	25.1	27.8
105°	21.7	21.9	22.1	22.4	22.1	21.9	21.7	21.5	31.4	51.4	71.3
107.5°	115.5	100.4	85.3	70.3	85.3	100.4	115.5	130.6	145.4	160.2	174.8
110°	188.3	172.2	156.0	139.8	156.0	172.2	188.3	204.5	214.5	218.2	221.9



TEST NUMBER: P332246-940

CATALOG NUMBER: S123RDIP-S340D585U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	250.2	246.7	243.3	240.0	243.3	246.7	250.2	253.6	255.3	255.2	255.1
115°	297.7	298.2	298.6	299.1	298.6	298.2	297.7	297.2	296.5	295.3	294.2
117.5°	332.0	332.1	332.2	332.3	332.2	332.1	332.0	331.9	331.4	330.5	329.6
120°	355.0	355.0	355.0	355.0	355.0	355.0	355.0	355.0	354.5	353.7	352.8
122.5°	377.1	377.2	377.3	377.4	377.3	377.2	377.1	377.0	376.7	376.0	375.4
125°	408.2	408.5	408.7	408.9	408.7	408.5	408.2	408.0	407.8	407.5	407.3
127.5°	439.9	439.7	439.4	439.3	439.4	439.7	439.9	440.1	440.1	439.7	439.3
130°	459.4	459.2	459.0	458.8	459.0	459.2	459.4	459.7	459.5	459.1	458.6
132.5°	477.6	477.2	477.0	476.6	477.0	477.2	477.6	478.0	477.9	477.4	477.0
135°	505.1	504.7	504.4	504.0	504.4	504.7	505.1	505.3	505.3	505.1	504.7
137.5°	530.4	530.2	529.9	529.8	529.9	530.2	530.4	530.7	530.5	529.9	529.4
140°	545.9	545.6	545.5	545.2	545.5	545.6	545.9	546.1	546.0	545.5	545.1
142.5°	560.4	560.1	559.7	559.5	559.7	560.1	560.4	560.7	560.7	560.4	560.0
145°	581.3	581.3	581.3	581.3	581.3	581.3	581.3	581.3	581.2	580.9	580.8
147.5°	599.1	598.6	598.2	597.6	598.2	598.6	599.1	599.7	599.9	599.6	599.4
150°	610.8	610.5	610.1	609.8	610.1	610.5	610.8	611.2	611.2	611.0	610.7
152.5°	621.2	620.6	620.1	619.6	620.1	620.6	621.2	621.6	621.7	621.3	620.9
155°	635.3	634.5	633.9	633.2	633.9	634.5	635.3	635.9	636.0	635.4	634.8
157.5°	647.3	646.5	645.6	644.7	645.6	646.5	647.3	648.2	648.4	647.6	646.9
160°	654.4	653.6	652.8	652.0	652.8	653.6	654.4	655.1	655.2	654.5	653.9
162.5°	661.0	660.3	659.6	659.0	659.6	660.3	661.0	661.7	661.7	660.9	660.1
165°	669.7	668.9	668.1	667.3	668.1	668.9	669.7	670.5	670.4	669.5	668.6
167.5°	676.0	675.1	674.2	673.2	674.2	675.1	676.0	676.9	676.9	676.0	675.1
170°	679.7	678.8	677.9	676.9	677.9	678.8	679.7	680.6	680.6	679.7	678.8
172.5°	682.0	681.0	679.9	678.9	679.9	681.0	682.0	683.0	683.0	682.1	681.2
175°	684.7	683.9	683.0	682.0	683.0	683.9	684.7	685.6	685.7	684.9	684.1
177.5°	685.6	684.7	683.9	683.0	683.9	684.7	685.6	686.5	686.6	685.9	685.2
180°	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6



TEST NUMBER: P332246-940

CATALOG NUMBER: S123RDIP-S340D585U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3
2.5°	463.2	465.6	467.9	470.0	473.3	474.8	477.0	477.9	480.3	483.9	487.0
5°	435.1	438.4	442.7	446.2	451.8	456.2	461.0	465.6	471.0	478.7	485.5
7.5°	411.2	414.4	419.6	426.2	432.4	438.6	445.1	451.4	459.1	470.1	481.0
10°	395.4	399.3	405.6	412.6	420.3	426.3	434.0	441.8	451.5	464.1	477.2
12.5°	381.7	384.7	391.9	398.6	407.3	415.0	422.5	431.8	442.6	456.1	471.9
15°	360.1	364.2	371.2	378.7	387.9	396.0	405.7	417.0	427.6	444.2	463.2
17.5°	338.2	344.6	352.0	360.3	367.1	378.4	388.9	400.4	413.5	431.1	452.1
20°	324.3	329.3	336.2	348.4	357.3	365.9	375.6	389.9	402.0	422.0	443.7
22.5°	312.5	316.1	323.9	333.9	344.4	354.2	364.2	377.8	392.7	411.6	435.2
25°	295.0	300.9	306.7	313.9	325.1	337.0	347.8	359.4	375.2	395.4	420.9
27.5°	277.9	283.2	288.9	297.8	306.4	317.4	328.8	342.1	359.0	380.3	406.3
30°	267.0	270.9	276.3	287.8	295.4	305.0	318.3	330.1	345.9	368.5	396.0
32.5°	255.7	260.7	266.7	275.4	285.0	294.0	306.1	319.0	335.1	357.4	385.5
35°	239.5	245.6	251.6	258.1	267.6	277.0	287.1	301.2	317.6	339.3	366.8
37.5°	224.7	229.5	234.4	242.5	251.5	260.4	269.9	283.8	299.3	322.6	347.9
40°	215.3	219.6	223.4	231.7	240.4	249.9	259.3	271.5	288.1	310.0	334.5
42.5°	204.9	208.9	214.0	220.9	230.2	238.3	247.6	259.2	274.8	297.0	318.5
45°	189.5	194.0	198.4	204.8	214.2	222.1	230.4	241.4	257.4	275.7	294.8
47.5°	173.3	178.0	183.0	189.2	197.3	205.4	213.7	223.4	238.0	255.9	268.9
50°	163.1	166.8	171.8	178.1	185.6	194.0	201.5	212.1	226.0	240.1	251.4
52.5°	152.5	155.9	161.5	168.1	175.0	182.4	190.4	199.5	212.0	225.3	234.3
55°	135.9	140.0	144.8	151.2	158.1	164.3	172.0	181.4	191.4	201.3	207.3
57.5°	120.4	123.9	127.9	134.5	140.4	147.8	154.8	162.0	171.3	178.8	182.7
60°	109.1	112.2	117.3	123.2	128.8	135.3	143.1	150.4	157.5	163.5	166.6
62.5°	98.4	102.0	106.6	111.9	118.0	124.1	131.0	137.1	143.4	148.6	150.7
65°	84.5	87.5	90.8	95.8	100.8	107.0	112.4	118.6	123.2	126.1	128.0
67.5°	72.0	73.8	76.3	79.7	84.6	90.1	95.2	100.1	104.0	105.9	107.6
70°	63.8	65.0	66.9	70.2	73.9	78.7	84.2	87.7	91.0	92.6	94.3
72.5°	55.6	57.2	58.9	61.6	64.6	68.1	72.1	76.3	78.2	80.2	81.1
75°	42.2	44.5	46.7	48.4	50.5	53.1	56.7	59.4	60.5	62.2	62.3
77.5°	31.8	32.4	34.0	36.0	37.8	39.8	42.0	44.4	44.9	45.7	46.4
80°	26.2	26.2	26.2	27.5	29.5	30.9	33.0	34.2	35.1	35.3	35.5
82.5°	21.0	21.0	20.9	21.1	21.8	22.6	24.5	25.9	26.7	26.5	26.0
85°	13.7	13.3	13.3	13.1	13.3	12.8	12.7	13.5	14.7	14.7	14.4
87.5°	8.2	7.9	7.8	7.3	6.9	6.4	5.6	5.6	5.4	5.8	5.4
90°	12.7	12.2	10.7	9.3	7.8	6.3	5.0	3.9	2.8	1.6	0.5
92.5°	13.7	13.0	11.9	10.8	9.7	8.6	8.2	8.5	8.8	9.2	9.5
95°	16.6	15.8	14.5	13.3	12.0	10.8	12.5	17.1	21.8	26.4	31.0
97.5°	17.3	16.4	24.5	32.6	40.8	49.0	54.0	56.1	58.2	60.3	62.3
100°	17.7	16.8	34.4	52.1	69.6	87.3	95.0	92.7	90.5	88.2	86.0
102.5°	30.7	33.4	52.7	72.0	91.2	110.5	119.3	117.7	116.1	114.4	112.8
105°	91.4	111.4	121.5	131.7	141.9	152.0	156.5	155.2	154.1	152.8	151.6
107.5°	189.5	204.1	202.5	200.9	199.3	197.7	196.4	195.5	194.5	193.4	192.4
110°	225.6	229.3	228.1	226.9	225.6	224.4	223.3	222.4	221.5	220.6	219.7



TEST NUMBER: P332246-940

CATALOG NUMBER: S123RDIP-S340D585U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	255.1	255.0	253.8	252.5	251.3	250.0	249.0	248.2	247.4	246.6	245.8
115°	293.1	291.9	290.9	289.9	288.9	287.8	287.0	286.3	285.6	285.0	284.3
117.5°	328.7	327.7	327.3	326.7	326.2	325.7	324.9	324.1	323.3	322.4	321.6
120°	351.9	350.9	350.6	350.3	349.9	349.6	348.9	347.9	346.9	345.8	344.8
122.5°	374.8	374.2	373.7	373.3	372.8	372.4	371.8	371.0	370.1	369.3	368.5
125°	407.1	406.9	406.4	406.0	405.6	405.1	404.4	403.5	402.6	401.7	400.7
127.5°	439.0	438.6	438.1	437.6	436.9	436.4	435.7	434.8	433.9	433.0	432.1
130°	458.2	457.7	457.3	456.8	456.4	455.9	455.2	454.3	453.4	452.5	451.7
132.5°	476.5	476.1	475.6	475.3	474.9	474.6	473.9	473.1	472.2	471.3	470.4
135°	504.4	504.0	503.5	503.1	502.7	502.2	501.7	501.0	500.2	499.6	498.9
137.5°	528.9	528.3	528.1	527.8	527.5	527.4	526.7	525.9	525.0	524.2	523.3
140°	544.7	544.2	543.9	543.5	543.1	542.9	542.3	541.6	541.0	540.3	539.6
142.5°	559.6	559.3	558.9	558.6	558.2	557.9	557.4	556.7	556.1	555.4	554.6
145°	580.5	580.3	580.1	579.9	579.6	579.4	578.9	578.1	577.3	576.5	575.7
147.5°	599.1	599.0	598.7	598.4	598.2	598.0	597.6	597.1	596.6	596.1	595.6
150°	610.6	610.3	610.1	609.8	609.7	609.4	609.1	608.8	608.4	608.1	607.8
152.5°	620.5	620.1	619.9	619.8	619.6	619.6	619.4	619.2	619.0	618.9	618.8
155°	634.3	633.7	633.6	633.5	633.4	633.3	633.3	633.6	633.7	634.0	634.2
157.5°	646.3	645.6	645.7	645.9	646.0	646.0	646.1	646.1	646.1	646.2	646.2
160°	653.2	652.6	652.6	652.7	652.8	653.0	653.1	653.2	653.4	653.4	653.5
162.5°	659.4	658.6	658.7	658.9	659.0	659.1	659.2	659.6	659.9	660.1	660.5
165°	667.7	666.7	666.9	667.0	667.1	667.2	667.4	667.8	668.2	668.4	668.8
167.5°	674.2	673.2	673.2	673.2	673.2	673.2	673.5	674.0	674.4	674.8	675.3
170°	677.9	676.9	676.9	676.9	676.9	676.9	677.2	677.6	678.1	678.5	678.9
172.5°	680.3	679.4	679.3	679.2	679.1	679.0	679.2	679.8	680.3	680.9	681.4
175°	683.3	682.5	682.4	682.3	682.2	682.1	682.3	682.9	683.4	684.0	684.6
177.5°	684.5	683.8	683.7	683.6	683.5	683.4	683.6	684.0	684.5	684.9	685.4
180°	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6



TEST NUMBER: P332246-940

CATALOG NUMBER: S123RDIP-S340D585U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3
2.5°	487.9	489.8	492.1	495.6	498.3	500.6	501.1	501.8	503.5	506.2	508.4
5°	491.2	495.9	503.5	511.0	519.2	525.8	532.1	536.5	540.6	549.3	556.3
7.5°	490.1	500.8	512.8	526.2	539.8	552.9	565.2	576.1	587.0	599.8	614.2
10°	489.5	501.9	518.2	535.4	554.3	572.7	590.7	604.6	620.7	635.3	653.8
12.5°	486.3	504.3	523.6	545.6	568.9	590.2	613.8	632.9	651.5	672.5	694.0
15°	482.1	504.0	528.5	557.8	593.2	618.8	643.0	676.5	699.3	722.1	752.9
17.5°	474.7	501.3	531.9	570.0	599.4	634.1	670.3	696.8	727.5	759.7	787.6
20°	468.7	499.6	534.0	571.3	608.9	646.5	681.6	713.2	745.0	782.2	805.0
22.5°	462.7	493.3	529.0	568.6	609.0	648.7	688.4	725.5	761.3	798.8	828.0
25°	450.0	486.3	525.0	565.5	605.4	649.0	696.3	737.7	781.9	820.6	848.3
27.5°	437.1	470.5	508.9	550.0	594.3	645.9	701.6	748.6	792.9	820.6	829.3
30°	425.4	460.7	496.1	537.9	585.9	643.4	702.6	756.4	792.7	804.9	795.9
32.5°	413.7	445.7	480.6	523.4	574.4	637.2	703.9	751.8	773.6	764.5	728.1
35°	392.9	421.7	455.6	498.4	557.0	633.8	698.5	730.8	725.5	673.5	604.9
37.5°	370.6	394.1	425.4	470.2	539.0	620.4	674.8	679.7	632.8	553.1	473.9
40°	352.9	374.2	406.4	453.1	525.0	607.1	651.1	631.8	559.3	470.6	404.5
42.5°	335.8	353.7	384.8	435.2	511.7	588.9	615.7	573.6	490.0	406.1	346.0
45°	306.8	323.7	354.8	406.5	484.5	554.3	550.7	477.6	393.9	326.4	276.5
47.5°	279.4	294.1	323.3	376.1	452.5	502.3	469.3	391.5	320.5	266.3	230.7
50°	259.9	274.5	303.5	355.7	427.0	463.2	416.2	341.2	276.1	231.2	203.0
52.5°	241.3	255.5	282.0	332.9	396.0	417.8	367.1	297.6	243.3	204.6	180.4
55°	215.3	226.0	249.9	298.5	345.7	350.7	299.3	241.2	196.5	169.5	152.9
57.5°	188.7	198.0	221.6	260.3	293.4	290.8	242.2	191.8	161.8	141.7	129.7
60°	171.4	180.6	201.3	234.5	259.5	250.7	206.1	165.6	139.8	125.1	115.5
62.5°	155.2	162.4	181.9	206.2	224.1	214.2	176.2	142.7	122.2	109.8	102.2
65°	131.9	137.8	153.3	166.0	175.9	166.4	134.8	111.6	96.8	88.1	82.9
67.5°	109.8	113.4	123.2	127.9	134.9	124.4	101.4	85.8	77.4	70.1	66.4
70°	95.8	98.4	103.7	107.5	109.2	98.4	81.4	70.0	63.0	57.8	55.5
72.5°	81.8	84.2	85.2	88.3	87.3	77.2	65.5	56.4	51.3	47.8	44.9
75°	62.5	63.6	62.5	61.3	58.6	51.5	43.4	38.9	35.1	33.4	32.4
77.5°	45.6	45.2	43.9	41.9	37.3	32.8	28.4	26.9	25.3	24.4	24.1
80°	35.1	34.2	33.0	29.9	25.9	22.8	21.8	20.8	20.2	19.1	18.9
82.5°	26.1	25.6	23.5	21.0	18.2	16.7	15.9	15.4	14.8	14.3	14.3
85°	13.9	13.3	11.0	9.5	9.2	8.7	8.6	8.6	7.7	7.5	7.5
87.5°	4.8	4.0	4.1	3.8	4.1	4.0	4.5	4.5	4.6	4.8	4.6
90°	1.6	2.8	3.9	5.0	6.3	7.8	9.3	10.7	12.2	12.7	13.1
92.5°	9.2	8.8	8.5	8.2	8.6	9.7	10.8	11.9	13.0	13.7	14.4
95°	26.4	21.8	17.1	12.5	10.8	12.0	13.3	14.5	15.8	16.6	17.4
97.5°	60.3	58.2	56.1	54.0	49.0	40.8	32.6	24.5	16.4	17.3	18.2
100°	88.2	90.5	92.7	95.0	87.3	69.6	52.1	34.4	16.8	17.7	18.5
102.5°	114.4	116.1	117.7	119.3	110.5	91.2	72.0	52.7	33.4	30.7	27.8
105°	152.8	154.1	155.2	156.5	152.0	141.9	131.7	121.5	111.4	91.4	71.3
107.5°	193.4	194.5	195.5	196.4	197.7	199.3	200.9	202.5	204.1	189.5	174.8
110°	220.6	221.5	222.4	223.3	224.4	225.6	226.9	228.1	229.3	225.6	221.9



TEST NUMBER: P332246-940

CATALOG NUMBER: S123RDIP-S340D585U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	246.6	247.4	248.2	249.0	250.0	251.3	252.5	253.8	255.0	255.1	255.1
115°	285.0	285.6	286.3	287.0	287.8	288.9	289.9	290.9	291.9	293.1	294.2
117.5°	322.4	323.3	324.1	324.9	325.7	326.2	326.7	327.3	327.7	328.7	329.6
120°	345.8	346.9	347.9	348.9	349.6	349.9	350.3	350.6	350.9	351.9	352.8
122.5°	369.3	370.1	371.0	371.8	372.4	372.8	373.3	373.7	374.2	374.8	375.4
125°	401.7	402.6	403.5	404.4	405.1	405.6	406.0	406.4	406.9	407.1	407.3
127.5°	433.0	433.9	434.8	435.7	436.4	436.9	437.6	438.1	438.6	439.0	439.3
130°	452.5	453.4	454.3	455.2	455.9	456.4	456.8	457.3	457.7	458.2	458.6
132.5°	471.3	472.2	473.1	473.9	474.6	474.9	475.3	475.6	476.1	476.5	477.0
135°	499.6	500.2	501.0	501.7	502.2	502.7	503.1	503.5	504.0	504.4	504.7
137.5°	524.2	525.0	525.9	526.7	527.4	527.5	527.8	528.1	528.3	528.9	529.4
140°	540.3	541.0	541.6	542.3	542.9	543.1	543.5	543.9	544.2	544.7	545.1
142.5°	555.4	556.1	556.7	557.4	557.9	558.2	558.6	558.9	559.3	559.6	560.0
145°	576.5	577.3	578.1	578.9	579.4	579.6	579.9	580.1	580.3	580.5	580.8
147.5°	596.1	596.6	597.1	597.6	598.0	598.2	598.4	598.7	599.0	599.1	599.4
150°	608.1	608.4	608.8	609.1	609.4	609.7	609.8	610.1	610.3	610.6	610.7
152.5°	618.9	619.0	619.2	619.4	619.6	619.6	619.8	619.9	620.1	620.5	620.9
155°	634.0	633.7	633.6	633.3	633.3	633.4	633.5	633.6	633.7	634.3	634.8
157.5°	646.2	646.1	646.1	646.1	646.0	646.0	645.9	645.7	645.6	646.3	646.9
160°	653.4	653.4	653.2	653.1	653.0	652.8	652.7	652.6	652.6	653.2	653.9
162.5°	660.1	659.9	659.6	659.2	659.1	659.0	658.9	658.7	658.6	659.4	660.1
165°	668.4	668.2	667.8	667.4	667.2	667.1	667.0	666.9	666.7	667.7	668.6
167.5°	674.8	674.4	674.0	673.5	673.2	673.2	673.2	673.2	673.2	674.2	675.1
170°	678.5	678.1	677.6	677.2	676.9	676.9	676.9	676.9	676.9	677.9	678.8
172.5°	680.9	680.3	679.8	679.2	679.0	679.1	679.2	679.3	679.4	680.3	681.2
175°	684.0	683.4	682.9	682.3	682.1	682.2	682.3	682.4	682.5	683.3	684.1
177.5°	684.9	684.5	684.0	683.6	683.4	683.5	683.6	683.7	683.8	684.5	685.2
180°	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6



TEST NUMBER: P332246-940

CATALOG NUMBER: S123RDIP-S340D585U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	485.3	485.3	485.3	485.3	485.3	485.3	485.3
2.5°	511.9	511.9	512.6	515.1	515.4	517.5	516.9
5°	562.6	566.5	568.0	574.3	577.9	579.6	576.3
7.5°	624.6	635.7	641.0	647.6	653.3	655.1	650.5
10°	669.8	681.4	691.2	697.2	702.8	706.6	711.3
12.5°	713.5	727.8	737.1	745.6	751.4	756.1	756.9
15°	761.0	782.6	799.0	811.1	817.1	820.2	818.9
17.5°	808.9	828.9	840.6	852.9	861.2	861.7	861.9
20°	836.0	855.5	869.1	878.2	887.5	887.1	889.2
22.5°	854.1	869.5	879.9	886.4	889.7	888.1	888.5
25°	862.6	867.2	865.3	854.7	851.9	842.2	843.9
27.5°	818.9	797.3	774.9	746.2	723.4	705.3	706.2
30°	759.6	721.3	677.7	641.1	608.3	599.1	579.6
32.5°	676.6	619.3	568.2	534.0	506.0	498.3	481.3
35°	536.0	480.3	427.8	396.2	383.7	366.2	366.0
37.5°	416.6	367.6	339.8	316.1	303.7	293.1	292.1
40°	350.4	312.3	291.2	274.2	262.0	254.0	252.2
42.5°	304.3	273.4	253.7	243.2	233.7	229.6	226.6
45°	248.4	227.7	214.0	204.5	200.1	197.0	195.3
47.5°	207.9	193.9	184.6	178.2	174.7	171.4	172.3
50°	185.7	174.3	167.5	161.4	158.7	156.4	156.7
52.5°	167.9	157.7	152.1	147.8	144.5	142.8	142.0
55°	142.5	136.1	130.5	127.3	125.5	123.2	122.6
57.5°	121.5	116.5	112.0	108.5	108.0	105.8	106.1
60°	107.6	103.4	99.7	97.8	96.4	94.5	95.1
62.5°	96.1	92.6	89.3	87.7	86.2	84.9	85.2
65°	78.7	75.4	73.3	72.5	71.9	71.2	70.6
67.5°	62.8	60.7	59.4	57.6	56.4	56.2	55.6
70°	52.8	50.0	47.8	45.5	44.9	44.7	44.9
72.5°	42.3	40.6	39.9	38.9	38.7	38.2	38.5
75°	31.7	31.1	30.8	29.9	29.9	29.9	29.9
77.5°	23.5	23.1	22.8	22.6	22.5	22.1	22.1
80°	18.3	18.1	17.7	17.7	17.5	17.7	17.5
82.5°	13.8	13.7	13.4	13.4	13.1	13.0	13.1
85°	7.0	6.9	7.3	6.9	7.0	6.7	7.0
87.5°	4.7	4.8	4.7	4.7	4.6	5.0	4.7
90°	13.6	14.0	14.4	14.6	14.8	15.1	15.2
92.5°	15.2	15.9	16.3	16.5	16.6	16.8	16.9
95°	18.1	18.9	19.4	19.4	19.4	19.4	19.4
97.5°	19.1	20.0	20.5	20.6	20.7	20.9	21.0
100°	19.5	20.4	20.9	21.0	21.1	21.2	21.4
102.5°	25.1	22.3	21.0	21.1	21.4	21.6	21.8
105°	51.4	31.4	21.5	21.7	21.9	22.1	22.4
107.5°	160.2	145.4	130.6	115.5	100.4	85.3	70.3
110°	218.2	214.5	204.5	188.3	172.2	156.0	139.8



TEST NUMBER: P332246-940

CATALOG NUMBER: S123RDIP-S340D585U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	255.2	255.3	253.6	250.2	246.7	243.3	240.0
115°	295.3	296.5	297.2	297.7	298.2	298.6	299.1
117.5°	330.5	331.4	331.9	332.0	332.1	332.2	332.3
120°	353.7	354.5	355.0	355.0	355.0	355.0	355.0
122.5°	376.0	376.7	377.0	377.1	377.2	377.3	377.4
125°	407.5	407.8	408.0	408.2	408.5	408.7	408.9
127.5°	439.7	440.1	440.1	439.9	439.7	439.4	439.3
130°	459.1	459.5	459.7	459.4	459.2	459.0	458.8
132.5°	477.4	477.9	478.0	477.6	477.2	477.0	476.6
135°	505.1	505.3	505.3	505.1	504.7	504.4	504.0
137.5°	529.9	530.5	530.7	530.4	530.2	529.9	529.8
140°	545.5	546.0	546.1	545.9	545.6	545.5	545.2
142.5°	560.4	560.7	560.7	560.4	560.1	559.7	559.5
145°	580.9	581.2	581.3	581.3	581.3	581.3	581.3
147.5°	599.6	599.9	599.7	599.1	598.6	598.2	597.6
150°	611.0	611.2	611.2	610.8	610.5	610.1	609.8
152.5°	621.3	621.7	621.6	621.2	620.6	620.1	619.6
155°	635.4	636.0	635.9	635.3	634.5	633.9	633.2
157.5°	647.6	648.4	648.2	647.3	646.5	645.6	644.7
160°	654.5	655.2	655.1	654.4	653.6	652.8	652.0
162.5°	660.9	661.7	661.7	661.0	660.3	659.6	659.0
165°	669.5	670.4	670.5	669.7	668.9	668.1	667.3
167.5°	676.0	676.9	676.9	676.0	675.1	674.2	673.2
170°	679.7	680.6	680.6	679.7	678.8	677.9	676.9
172.5°	682.1	683.0	683.0	682.0	681.0	679.9	678.9
175°	684.9	685.7	685.6	684.7	683.9	683.0	682.0
177.5°	685.9	686.6	686.5	685.6	684.7	683.9	683.0
180°	684.6	684.6	684.6	684.6	684.6	684.6	684.6

(END OF REPORT)