

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332248-940

Luminaire Tested: **S123RDIP-S340D585U940-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332248-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S340D585U940-4F0-1E-UDD-A4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 585 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3100.5 lumens  
Efficiency: N/A  
Efficacy: 121.1 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 25.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332248-940

CATALOG NUMBER: S123RDIP-S340D585U940-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P332248-940

CATALOG NUMBER: S123RDIP-S340D585U940-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	96	92	88	85	87	84	80	78	68	66	64	54	53	52	41	41	40	34
2	88	81	75	70	79	74	69	64	60	57	54	48	46	44	37	35	34	29
3	80	71	64	59	73	65	59	54	54	49	46	43	40	38	33	31	30	25
4	73	63	56	50	67	58	51	46	48	43	39	39	35	32	30	28	26	22
5	68	56	49	43	61	52	45	40	43	38	34	35	31	28	27	25	23	19
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	25	22	20	17
7	58	46	38	33	52	42	35	31	35	30	26	29	25	22	23	20	18	15
8	53	42	34	29	49	38	32	27	32	27	24	26	23	20	21	18	16	14
9	50	38	31	26	45	35	29	24	30	25	21	24	21	18	19	17	15	13
10	46	35	28	23	42	32	26	22	27	22	19	22	19	16	18	15	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	5224	5224	5224	5224
5°	6227	5246	4620	5246
10°	7774	5216	4173	5216
15°	9126	5162	3806	5162
20°	10186	5082	3494	5082
25°	10023	4999	3301	4999
30°	7204	4922	3104	4922
35°	4809	4820	2975	4820
40°	3544	4700	2843	4700
45°	2973	4488	2714	4488
50°	2624	4210	2532	4210
55°	2301	3890	2284	3890
60°	2047	3587	2093	3587
65°	1798	3260	1946	3260
70°	1413	2968	1778	2968
75°	1243	2591	1626	2591
80°	1085	2201	1599	2201
85°	865	1778	1692	1778



TEST NUMBER: P332248-940

CATALOG NUMBER: S123RDIP-S340D585U940-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	47.7	1.5
10°-20°	149.1	4.8
20°-30°	234.2	7.6
30°-40°	244.4	7.9
40°-50°	209.1	6.7
50°-60°	159.4	5.1
60°-70°	102.2	3.3
70°-80°	49.1	1.6
80°-90°	14.9	0.5
90°-100°	139.8	4.5
100°-110°	395.9	12.8
110°-120°	389.5	12.6
120°-130°	310.7	10.0
130°-140°	244.9	7.9
140°-150°	182.8	5.9
150°-160°	127.4	4.1
160°-170°	74.9	2.4
170°-180°	24.4	0.8
0°-30°	431.1	13.9
0°-40°	675.4	21.8
0°-60°	1044.0	33.7
0°-90°	1210.3	39.0
90°-120°	925.2	29.8
90°-150°	1663.7	53.7
90°-180°	1890.0	61.0
0°-180°	3100.5	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	485	485	485	485	485	
5°	576	486	428	486	576	59
15°	819	463	342	463	819	232
25°	844	421	278	421	844	363
35°	366	367	226	367	366	240
45°	195	295	178	295	195	154
55°	123	207	122	207	123	111
65°	71	128	76	128	71	69
75°	30	62	39	62	30	32
85°	7	14	14	14	7	8
90°	15	1	15	1	15	8
95°	59	17	59	17	59	106
105°	647	59	647	59	647	638
115°	787	104	787	104	787	764
125°	620	145	620	145	620	562
135°	503	170	503	170	503	390
145°	393	194	393	194	393	250
155°	326	220	326	220	326	152
165°	284	241	284	241	284	81
175°	256	251	256	251	256	25
180°	251	251	251	251	251	



TEST NUMBER: P332248-940

CATALOG NUMBER: S123RDIP-S340D585U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3
2.5°	516.9	517.5	515.4	515.1	512.6	511.9	511.9	508.4	506.2	503.5	501.8
5°	576.3	579.6	577.9	574.3	568.0	566.5	562.6	556.3	549.3	540.6	536.5
7.5°	650.5	655.1	653.3	647.6	641.0	635.7	624.6	614.2	599.8	587.0	576.1
10°	711.3	706.6	702.8	697.2	691.2	681.4	669.8	653.8	635.3	620.7	604.6
12.5°	756.9	756.1	751.4	745.6	737.1	727.8	713.5	694.0	672.5	651.5	632.9
15°	818.9	820.2	817.1	811.1	799.0	782.6	761.0	752.9	722.1	699.3	676.5
17.5°	861.9	861.7	861.2	852.9	840.6	828.9	808.9	787.6	759.7	727.5	696.8
20°	889.2	887.1	887.5	878.2	869.1	855.5	836.0	805.0	782.2	745.0	713.2
22.5°	888.5	888.1	889.7	886.4	879.9	869.5	854.1	828.0	798.8	761.3	725.5
25°	843.9	842.2	851.9	854.7	865.3	867.2	862.6	848.3	820.6	781.9	737.7
27.5°	706.2	705.3	723.4	746.2	774.9	797.3	818.9	829.3	820.6	792.9	748.6
30°	579.6	599.1	608.3	641.1	677.7	721.3	759.6	795.9	804.9	792.7	756.4
32.5°	481.3	498.3	506.0	534.0	568.2	619.3	676.6	728.1	764.5	773.6	751.8
35°	366.0	366.2	383.7	396.2	427.8	480.3	536.0	604.9	673.5	725.5	730.8
37.5°	292.1	293.1	303.7	316.1	339.8	367.6	416.6	473.9	553.1	632.8	679.7
40°	252.2	254.0	262.0	274.2	291.2	312.3	350.4	404.5	470.6	559.3	631.8
42.5°	226.6	229.6	233.7	243.2	253.7	273.4	304.3	346.0	406.1	490.0	573.6
45°	195.3	197.0	200.1	204.5	214.0	227.7	248.4	276.5	326.4	393.9	477.6
47.5°	172.3	171.4	174.7	178.2	184.6	193.9	207.9	230.7	266.3	320.5	391.5
50°	156.7	156.4	158.7	161.4	167.5	174.3	185.7	203.0	231.2	276.1	341.2
52.5°	142.0	142.8	144.5	147.8	152.1	157.7	167.9	180.4	204.6	243.3	297.6
55°	122.6	123.2	125.5	127.3	130.5	136.1	142.5	152.9	169.5	196.5	241.2
57.5°	106.1	105.8	108.0	108.5	112.0	116.5	121.5	129.7	141.7	161.8	191.8
60°	95.1	94.5	96.4	97.8	99.7	103.4	107.6	115.5	125.1	139.8	165.6
62.5°	85.2	84.9	86.2	87.7	89.3	92.6	96.1	102.2	109.8	122.2	142.7
65°	70.6	71.2	71.9	72.5	73.3	75.4	78.7	82.9	88.1	96.8	111.6
67.5°	55.6	56.2	56.4	57.6	59.4	60.7	62.8	66.4	70.1	77.4	85.8
70°	44.9	44.7	44.9	45.5	47.8	50.0	52.8	55.5	57.8	63.0	70.0
72.5°	38.5	38.2	38.7	38.9	39.9	40.6	42.3	44.9	47.8	51.3	56.4
75°	29.9	29.9	29.9	29.9	30.8	31.1	31.7	32.4	33.4	35.1	38.9
77.5°	22.1	22.1	22.5	22.6	22.8	23.1	23.5	24.1	24.4	25.3	26.9
80°	17.5	17.7	17.5	17.7	17.7	18.1	18.3	18.9	19.1	20.2	20.8
82.5°	13.1	13.0	13.1	13.4	13.4	13.7	13.8	14.3	14.3	14.8	15.4
85°	7.0	6.7	7.0	6.9	7.3	6.9	7.0	7.5	7.5	7.7	8.6
87.5°	4.6	5.1	4.6	4.6	4.8	4.7	4.6	4.5	4.7	4.7	4.5
90°	14.7	15.2	14.7	14.3	14.7	13.7	13.2	12.8	12.2	12.8	11.1
92.5°	24.5	25.4	24.9	26.5	27.4	30.1	34.0	42.8	59.0	78.2	86.1
95°	59.0	61.0	64.6	69.2	78.8	97.1	124.1	183.1	244.6	301.6	268.6
97.5°	160.6	165.0	178.7	201.6	239.2	300.0	365.6	456.5	500.1	467.4	342.1
100°	318.9	318.4	338.2	375.3	426.7	498.9	558.5	599.7	581.8	481.6	325.5
102.5°	467.8	479.5	496.1	525.5	565.4	611.3	646.0	647.3	585.9	455.2	301.1
105°	646.9	649.5	665.8	685.1	708.5	721.8	712.0	661.2	554.9	408.9	271.1
107.5°	750.1	754.7	760.3	766.8	766.3	748.2	703.7	621.1	500.6	368.0	252.0
110°	792.4	793.4	794.4	790.4	776.1	740.6	676.5	582.8	466.4	344.8	244.6



TEST NUMBER: P332248-940

CATALOG NUMBER: S123RDIP-S340D585U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	800.9	800.8	796.9	784.3	758.2	712.5	640.6	545.0	436.7	329.4	240.6
115°	786.8	784.3	774.1	751.7	713.5	658.2	583.4	494.9	400.8	312.8	239.1
117.5°	741.8	738.4	723.7	698.1	658.4	602.1	534.9	458.5	379.2	303.0	240.0
120°	704.5	701.3	689.2	660.7	620.5	569.1	508.1	439.4	367.7	298.5	241.6
122.5°	669.4	665.6	652.1	626.5	590.8	543.1	486.5	424.4	358.4	295.7	244.4
125°	620.5	617.0	604.2	581.8	549.3	508.6	459.8	404.3	346.3	291.9	248.7
127.5°	580.2	576.9	565.4	546.4	517.4	480.4	436.3	386.8	335.8	290.1	253.6
130°	557.4	553.4	542.7	524.4	497.4	462.8	421.6	375.9	330.1	288.9	256.8
132.5°	535.0	532.2	522.7	504.4	479.1	446.1	407.8	365.7	324.8	288.5	259.3
135°	503.0	499.4	490.3	475.0	450.1	421.2	388.1	352.0	317.9	287.8	263.0
137.5°	469.1	466.8	459.1	443.6	422.7	397.5	369.1	339.5	311.9	286.8	265.4
140°	445.5	446.0	437.9	423.7	404.3	382.5	358.0	332.2	308.2	286.3	267.0
142.5°	423.6	424.1	416.8	404.1	387.6	368.6	347.5	325.2	305.0	285.5	268.2
145°	393.2	392.2	388.1	377.4	364.7	349.9	333.7	316.8	300.6	284.3	269.0
147.5°	368.1	367.7	363.8	356.6	347.0	336.5	323.3	310.0	296.3	282.4	269.0
150°	353.5	353.5	350.4	344.8	337.2	327.5	316.8	305.1	293.5	280.7	269.0
152.5°	341.3	341.3	339.5	334.2	328.2	320.2	310.8	300.7	290.3	278.7	267.9
155°	326.0	325.5	324.5	320.4	315.8	309.8	302.1	294.0	285.3	275.2	266.5
157.5°	312.1	312.2	311.4	308.4	304.3	299.6	293.6	286.9	279.8	272.0	264.7
160°	303.1	303.6	303.6	300.6	297.0	293.5	288.4	282.8	276.2	269.6	263.9
162.5°	295.0	295.5	295.5	292.8	290.5	287.4	282.7	277.9	272.5	267.2	262.3
165°	284.3	284.3	284.8	282.8	280.7	278.2	274.6	271.6	267.5	263.5	259.9
167.5°	274.1	274.1	274.6	273.2	272.3	270.5	268.4	266.1	262.8	259.8	257.4
170°	268.0	268.0	268.6	267.5	267.0	266.0	263.9	262.4	259.9	257.3	255.8
172.5°	262.3	262.8	263.7	262.6	262.5	261.9	260.3	259.2	257.1	255.3	254.6
175°	255.8	256.4	256.8	256.4	256.4	256.4	255.3	254.9	253.8	252.8	252.8
177.5°	252.1	252.1	252.9	252.4	252.9	252.9	252.4	252.1	251.6	251.3	251.6
180°	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3



TEST NUMBER: P332248-940

CATALOG NUMBER: S123RDIP-S340D585U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3
2.5°	501.1	500.6	498.3	495.6	492.1	489.8	487.9	487.0	483.9	480.3	477.9
5°	532.1	525.8	519.2	511.0	503.5	495.9	491.2	485.5	478.7	471.0	465.6
7.5°	565.2	552.9	539.8	526.2	512.8	500.8	490.1	481.0	470.1	459.1	451.4
10°	590.7	572.7	554.3	535.4	518.2	501.9	489.5	477.2	464.1	451.5	441.8
12.5°	613.8	590.2	568.9	545.6	523.6	504.3	486.3	471.9	456.1	442.6	431.8
15°	643.0	618.8	593.2	557.8	528.5	504.0	482.1	463.2	444.2	427.6	417.0
17.5°	670.3	634.1	599.4	570.0	531.9	501.3	474.7	452.1	431.1	413.5	400.4
20°	681.6	646.5	608.9	571.3	534.0	499.6	468.7	443.7	422.0	402.0	389.9
22.5°	688.4	648.7	609.0	568.6	529.0	493.3	462.7	435.2	411.6	392.7	377.8
25°	696.3	649.0	605.4	565.5	525.0	486.3	450.0	420.9	395.4	375.2	359.4
27.5°	701.6	645.9	594.3	550.0	508.9	470.5	437.1	406.3	380.3	359.0	342.1
30°	702.6	643.4	585.9	537.9	496.1	460.7	425.4	396.0	368.5	345.9	330.1
32.5°	703.9	637.2	574.4	523.4	480.6	445.7	413.7	385.5	357.4	335.1	319.0
35°	698.5	633.8	557.0	498.4	455.6	421.7	392.9	366.8	339.3	317.6	301.2
37.5°	674.8	620.4	539.0	470.2	425.4	394.1	370.6	347.9	322.6	299.3	283.8
40°	651.1	607.1	525.0	453.1	406.4	374.2	352.9	334.5	310.0	288.1	271.5
42.5°	615.7	588.9	511.7	435.2	384.8	353.7	335.8	318.5	297.0	274.8	259.2
45°	550.7	554.3	484.5	406.5	354.8	323.7	306.8	294.8	275.7	257.4	241.4
47.5°	469.3	502.3	452.5	376.1	323.3	294.1	279.4	268.9	255.9	238.0	223.4
50°	416.2	463.2	427.0	355.7	303.5	274.5	259.9	251.4	240.1	226.0	212.1
52.5°	367.1	417.8	396.0	332.9	282.0	255.5	241.3	234.3	225.3	212.0	199.5
55°	299.3	350.7	345.7	298.5	249.9	226.0	215.3	207.3	201.3	191.4	181.4
57.5°	242.2	290.8	293.4	260.3	221.6	198.0	188.7	182.7	178.8	171.3	162.0
60°	206.1	250.7	259.5	234.5	201.3	180.6	171.4	166.6	163.5	157.5	150.4
62.5°	176.2	214.2	224.1	206.2	181.9	162.4	155.2	150.7	148.6	143.4	137.1
65°	134.8	166.4	175.9	166.0	153.3	137.8	131.9	128.0	126.1	123.2	118.6
67.5°	101.4	124.4	134.9	127.9	123.2	113.4	109.8	107.6	105.9	104.0	100.1
70°	81.4	98.4	109.2	107.5	103.7	98.4	95.8	94.3	92.6	91.0	87.7
72.5°	65.5	77.2	87.3	88.3	85.2	84.2	81.8	81.1	80.2	78.2	76.3
75°	43.4	51.5	58.6	61.3	62.5	63.6	62.5	62.3	62.2	60.5	59.4
77.5°	28.4	32.8	37.3	41.9	43.9	45.2	45.6	46.4	45.7	44.9	44.4
80°	21.8	22.8	25.9	29.9	33.0	34.2	35.1	35.5	35.3	35.1	34.2
82.5°	15.9	16.7	18.2	21.0	23.5	25.6	26.1	26.0	26.5	26.7	25.9
85°	8.6	8.7	9.2	9.5	11.0	13.3	13.9	14.4	14.7	14.7	13.5
87.5°	4.5	4.1	4.2	3.9	4.3	4.1	4.9	5.5	5.9	5.4	5.7
90°	9.6	8.1	6.6	5.6	4.5	3.0	2.1	1.0	2.1	3.0	4.5
92.5°	64.6	42.7	29.4	21.8	17.6	13.6	9.4	6.3	9.4	13.6	17.6
95°	185.1	109.3	66.1	46.3	33.1	24.4	18.8	17.3	18.8	24.4	33.1
97.5°	203.1	117.7	76.4	54.9	41.9	34.4	30.1	29.5	30.1	34.4	41.9
100°	191.7	116.5	80.9	61.0	48.9	41.7	38.2	37.6	38.2	41.7	48.9
102.5°	182.0	118.1	86.1	67.9	57.0	50.3	47.1	46.2	47.1	50.3	57.0
105°	175.0	122.6	95.1	79.4	69.6	63.6	60.5	59.0	60.5	63.6	69.6
107.5°	174.4	130.9	106.8	92.2	83.1	77.1	74.2	72.6	74.2	77.1	83.1
110°	176.5	137.9	114.9	100.7	92.0	86.5	83.9	82.4	83.9	86.5	92.0





TEST NUMBER: P332248-940

CATALOG NUMBER: S123RDIP-S340D585U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	180.6	144.7	123.5	109.7	101.0	95.4	92.9	91.3	92.9	95.4	101.0
115°	187.2	156.1	136.8	123.1	114.4	109.3	106.3	104.2	106.3	109.3	114.4
117.5°	195.9	168.3	149.1	136.4	126.7	122.1	119.5	117.2	119.5	122.1	126.7
120°	202.4	175.9	157.7	145.0	135.3	130.2	127.7	126.2	127.7	130.2	135.3
122.5°	208.6	184.1	166.2	152.7	143.4	137.9	135.4	133.8	135.4	137.9	143.4
125°	218.2	195.8	178.0	164.3	154.6	149.0	146.0	145.0	146.0	149.0	154.6
127.5°	226.1	206.0	188.8	175.0	164.3	158.7	154.9	153.4	154.9	158.7	164.3
130°	231.4	212.0	195.3	181.6	170.9	164.8	160.2	158.7	160.2	164.8	170.9
132.5°	236.3	217.4	201.0	187.7	177.0	169.7	164.7	162.7	164.7	169.7	177.0
135°	242.6	225.3	209.6	195.8	185.1	177.5	171.9	169.9	171.9	177.5	185.1
137.5°	247.3	230.8	215.6	203.0	192.3	184.2	178.7	176.6	178.7	184.2	192.3
140°	249.8	234.4	219.7	207.0	196.8	188.7	183.6	181.1	183.6	188.7	196.8
142.5°	252.2	237.3	223.0	211.1	200.9	193.6	188.1	185.9	188.1	193.6	200.9
145°	254.9	241.1	227.8	216.2	207.5	199.9	195.3	193.8	195.3	199.9	207.5
147.5°	256.5	244.2	232.0	222.0	213.7	207.1	202.6	201.7	202.6	207.1	213.7
150°	256.8	246.2	234.4	225.3	218.2	211.6	207.5	207.0	207.5	211.6	218.2
152.5°	257.7	247.4	237.3	228.5	222.3	216.5	212.4	212.3	212.4	216.5	222.3
155°	257.9	249.8	241.1	234.0	228.4	223.3	220.3	220.3	220.3	223.3	228.4
157.5°	258.4	251.0	244.2	238.6	233.9	229.3	226.9	226.5	226.9	229.3	233.9
160°	258.4	252.3	246.2	241.1	237.6	233.4	231.4	231.4	231.4	233.4	237.6
162.5°	258.0	252.7	247.4	243.1	240.0	236.7	235.1	235.1	235.1	236.7	240.0
165°	256.8	253.2	249.2	245.7	243.6	241.1	240.0	240.6	240.0	241.1	243.6
167.5°	256.0	253.2	250.2	248.0	246.6	244.6	244.2	244.8	244.2	244.6	246.6
170°	254.9	252.8	250.2	249.2	248.2	246.6	246.2	247.2	246.2	246.6	248.2
172.5°	254.4	252.8	250.7	250.0	249.4	248.3	248.2	248.8	248.2	248.3	249.4
175°	253.2	252.3	251.3	250.7	250.7	249.8	250.2	250.7	250.2	249.8	250.7
177.5°	252.4	251.6	251.3	251.3	251.3	250.8	251.3	251.6	251.3	250.8	251.3
180°	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3



TEST NUMBER: P332248-940

CATALOG NUMBER: S123RDIP-S340D585U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3
2.5°	477.0	474.8	473.3	470.0	467.9	465.6	463.2	464.7	464.5	464.4	464.4
5°	461.0	456.2	451.8	446.2	442.7	438.4	435.1	434.6	435.4	432.6	430.9
7.5°	445.1	438.6	432.4	426.2	419.6	414.4	411.2	409.6	407.5	405.7	403.9
10°	434.0	426.3	420.3	412.6	405.6	399.3	395.4	392.6	391.2	389.8	387.0
12.5°	422.5	415.0	407.3	398.6	391.9	384.7	381.7	378.7	375.9	374.3	370.6
15°	405.7	396.0	387.9	378.7	371.2	364.2	360.1	354.0	353.2	351.1	347.3
17.5°	388.9	378.4	367.1	360.3	352.0	344.6	338.2	336.3	330.3	328.1	324.8
20°	375.6	365.9	357.3	348.4	336.2	329.3	324.3	321.6	316.8	313.9	311.8
22.5°	364.2	354.2	344.4	333.9	323.9	316.1	312.5	308.3	305.7	301.6	299.3
25°	347.8	337.0	325.1	313.9	306.7	300.9	295.0	291.2	287.5	285.6	281.5
27.5°	328.8	317.4	306.4	297.8	288.9	283.2	277.9	274.6	270.1	267.0	264.7
30°	318.3	305.0	295.4	287.8	276.3	270.9	267.0	262.8	259.5	256.2	253.9
32.5°	306.1	294.0	285.0	275.4	266.7	260.7	255.7	252.0	249.1	246.0	243.7
35°	287.1	277.0	267.6	258.1	251.6	245.6	239.5	236.4	233.7	230.8	228.7
37.5°	269.9	260.4	251.5	242.5	234.4	229.5	224.7	222.3	218.6	216.7	214.6
40°	259.3	249.9	240.4	231.7	223.4	219.6	215.3	211.7	208.4	206.9	204.6
42.5°	247.6	238.3	230.2	220.9	214.0	208.9	204.9	201.1	198.6	196.4	195.2
45°	230.4	222.1	214.2	204.8	198.4	194.0	189.5	185.9	183.7	182.2	179.9
47.5°	213.7	205.4	197.3	189.2	183.0	178.0	173.3	170.9	167.9	166.1	164.6
50°	201.5	194.0	185.6	178.1	171.8	166.8	163.1	160.0	157.3	155.0	153.9
52.5°	190.4	182.4	175.0	168.1	161.5	155.9	152.5	149.2	147.1	144.5	143.3
55°	172.0	164.3	158.1	151.2	144.8	140.0	135.9	133.0	130.9	128.0	126.4
57.5°	154.8	147.8	140.4	134.5	127.9	123.9	120.4	116.5	113.9	111.6	109.9
60°	143.1	135.3	128.8	123.2	117.3	112.2	109.1	105.9	103.3	100.9	99.5
62.5°	131.0	124.1	118.0	111.9	106.6	102.0	98.4	95.9	93.5	92.0	90.5
65°	112.4	107.0	100.8	95.8	90.8	87.5	84.5	82.3	80.6	79.5	78.3
67.5°	95.2	90.1	84.6	79.7	76.3	73.8	72.0	70.0	69.1	67.8	67.0
70°	84.2	78.7	73.9	70.2	66.9	65.0	63.8	62.3	61.5	59.8	59.0
72.5°	72.1	68.1	64.6	61.6	58.9	57.2	55.6	53.9	52.5	50.6	49.8
75°	56.7	53.1	50.5	48.4	46.7	44.5	42.2	40.3	39.7	39.1	38.9
77.5°	42.0	39.8	37.8	36.0	34.0	32.4	31.8	31.4	31.3	30.9	30.9
80°	33.0	30.9	29.5	27.5	26.2	26.2	26.2	25.8	25.9	25.9	25.9
82.5°	24.5	22.6	21.8	21.1	20.9	21.0	21.0	21.1	21.0	21.3	21.1
85°	12.7	12.8	13.3	13.1	13.3	13.3	13.7	13.5	13.7	13.3	13.7
87.5°	5.8	6.5	7.0	7.4	7.8	8.0	8.1	8.2	8.5	8.6	8.7
90°	5.6	6.6	8.1	9.6	11.1	12.8	12.2	12.8	13.2	13.7	14.7
92.5°	21.8	29.4	42.7	64.6	86.1	78.2	59.0	42.8	34.0	30.1	27.4
95°	46.3	66.1	109.3	185.1	268.6	301.6	244.6	183.1	124.1	97.1	78.8
97.5°	54.9	76.4	117.7	203.1	342.1	467.4	500.1	456.5	365.6	300.0	239.2
100°	61.0	80.9	116.5	191.7	325.5	481.6	581.8	599.7	558.5	498.9	426.7
102.5°	67.9	86.1	118.1	182.0	301.1	455.2	585.9	647.3	646.0	611.3	565.4
105°	79.4	95.1	122.6	175.0	271.1	408.9	554.9	661.2	712.0	721.8	708.5
107.5°	92.2	106.8	130.9	174.4	252.0	368.0	500.6	621.1	703.7	748.2	766.3
110°	100.7	114.9	137.9	176.5	244.6	344.8	466.4	582.8	676.5	740.6	776.1



TEST NUMBER: P332248-940

CATALOG NUMBER: S123RDIP-S340D585U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	109.7	123.5	144.7	180.6	240.6	329.4	436.7	545.0	640.6	712.5	758.2
115°	123.1	136.8	156.1	187.2	239.1	312.8	400.8	494.9	583.4	658.2	713.5
117.5°	136.4	149.1	168.3	195.9	240.0	303.0	379.2	458.5	534.9	602.1	658.4
120°	145.0	157.7	175.9	202.4	241.6	298.5	367.7	439.4	508.1	569.1	620.5
122.5°	152.7	166.2	184.1	208.6	244.4	295.7	358.4	424.4	486.5	543.1	590.8
125°	164.3	178.0	195.8	218.2	248.7	291.9	346.3	404.3	459.8	508.6	549.3
127.5°	175.0	188.8	206.0	226.1	253.6	290.1	335.8	386.8	436.3	480.4	517.4
130°	181.6	195.3	212.0	231.4	256.8	288.9	330.1	375.9	421.6	462.8	497.4
132.5°	187.7	201.0	217.4	236.3	259.3	288.5	324.8	365.7	407.8	446.1	479.1
135°	195.8	209.6	225.3	242.6	263.0	287.8	317.9	352.0	388.1	421.2	450.1
137.5°	203.0	215.6	230.8	247.3	265.4	286.8	311.9	339.5	369.1	397.5	422.7
140°	207.0	219.7	234.4	249.8	267.0	286.3	308.2	332.2	358.0	382.5	404.3
142.5°	211.1	223.0	237.3	252.2	268.2	285.5	305.0	325.2	347.5	368.6	387.6
145°	216.2	227.8	241.1	254.9	269.0	284.3	300.6	316.8	333.7	349.9	364.7
147.5°	222.0	232.0	244.2	256.5	269.0	282.4	296.3	310.0	323.3	336.5	347.0
150°	225.3	234.4	246.2	256.8	269.0	280.7	293.5	305.1	316.8	327.5	337.2
152.5°	228.5	237.3	247.4	257.7	267.9	278.7	290.3	300.7	310.8	320.2	328.2
155°	234.0	241.1	249.8	257.9	266.5	275.2	285.3	294.0	302.1	309.8	315.8
157.5°	238.6	244.2	251.0	258.4	264.7	272.0	279.8	286.9	293.6	299.6	304.3
160°	241.1	246.2	252.3	258.4	263.9	269.6	276.2	282.8	288.4	293.5	297.0
162.5°	243.1	247.4	252.7	258.0	262.3	267.2	272.5	277.9	282.7	287.4	290.5
165°	245.7	249.2	253.2	256.8	259.9	263.5	267.5	271.6	274.6	278.2	280.7
167.5°	248.0	250.2	253.2	256.0	257.4	259.8	262.8	266.1	268.4	270.5	272.3
170°	249.2	250.2	252.8	254.9	255.8	257.3	259.9	262.4	263.9	266.0	267.0
172.5°	250.0	250.7	252.8	254.4	254.6	255.3	257.1	259.2	260.3	261.9	262.5
175°	250.7	251.3	252.3	253.2	252.8	252.8	253.8	254.9	255.3	256.4	256.4
177.5°	251.3	251.3	251.6	252.4	251.6	251.3	251.6	252.1	252.4	252.9	252.9
180°	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3



TEST NUMBER: P332248-940

CATALOG NUMBER: S123RDIP-S340D585U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3
2.5°	462.4	462.2	462.4	461.7	462.4	462.2	462.4	464.4	464.4	464.5	464.7
5°	430.3	430.1	429.4	427.6	429.4	430.1	430.3	430.9	432.6	435.4	434.6
7.5°	402.2	401.9	400.1	400.1	400.1	401.9	402.2	403.9	405.7	407.5	409.6
10°	385.6	385.8	383.3	381.8	383.3	385.8	385.6	387.0	389.8	391.2	392.6
12.5°	369.4	368.5	366.5	364.9	366.5	368.5	369.4	370.6	374.3	375.9	378.7
15°	348.2	346.1	341.2	341.5	341.2	346.1	348.2	347.3	351.1	353.2	354.0
17.5°	323.2	321.6	321.6	318.6	321.6	321.6	323.2	324.8	328.1	330.3	336.3
20°	308.5	307.5	307.9	305.0	307.9	307.5	308.5	311.8	313.9	316.8	321.6
22.5°	297.0	296.0	294.3	293.4	294.3	296.0	297.0	299.3	301.6	305.7	308.3
25°	280.3	278.6	277.0	277.9	277.0	278.6	280.3	281.5	285.6	287.5	291.2
27.5°	263.5	262.3	260.6	260.4	260.6	262.3	263.5	264.7	267.0	270.1	274.6
30°	252.8	251.6	250.7	249.7	250.7	251.6	252.8	253.9	256.2	259.5	262.8
32.5°	242.0	241.7	240.3	240.0	240.3	241.7	242.0	243.7	246.0	249.1	252.0
35°	227.9	226.7	226.2	226.4	226.2	226.7	227.9	228.7	230.8	233.7	236.4
37.5°	214.5	212.9	212.0	211.3	212.0	212.9	214.5	214.6	216.7	218.6	222.3
40°	204.8	203.2	202.8	202.3	202.8	203.2	204.8	204.6	206.9	208.4	211.7
42.5°	194.0	193.4	193.1	192.3	193.1	193.4	194.0	195.2	196.4	198.6	201.1
45°	179.3	179.1	177.8	178.3	177.8	179.1	179.3	179.9	182.2	183.7	185.9
47.5°	163.7	162.8	161.9	162.6	161.9	162.8	163.7	164.6	166.1	167.9	170.9
50°	153.1	152.7	150.8	151.2	150.8	152.7	153.1	153.9	155.0	157.3	160.0
52.5°	142.5	140.9	140.2	139.9	140.2	140.9	142.5	143.3	144.5	147.1	149.2
55°	124.8	123.0	122.2	121.7	122.2	123.0	124.8	126.4	128.0	130.9	133.0
57.5°	107.5	107.1	106.4	106.8	106.4	107.1	107.5	109.9	111.6	113.9	116.5
60°	97.5	97.5	97.5	97.2	97.5	97.5	97.5	99.5	100.9	103.3	105.9
62.5°	89.6	89.1	89.0	89.3	89.0	89.1	89.6	90.5	92.0	93.5	95.9
65°	77.7	77.5	76.7	76.4	76.7	77.5	77.7	78.3	79.5	80.6	82.3
67.5°	66.4	65.7	65.5	65.2	65.5	65.7	66.4	67.0	67.8	69.1	70.0
70°	58.0	57.5	56.3	56.5	56.3	57.5	58.0	59.0	59.8	61.5	62.3
72.5°	48.9	48.4	48.2	47.9	48.2	48.4	48.9	49.8	50.6	52.5	53.9
75°	38.6	38.4	38.3	39.1	38.3	38.4	38.6	38.9	39.1	39.7	40.3
77.5°	30.9	30.9	31.1	30.8	31.1	30.9	30.9	30.9	30.9	31.3	31.4
80°	25.9	25.9	25.8	25.8	25.8	25.9	25.9	25.9	25.9	25.9	25.8
82.5°	20.8	21.0	21.1	20.8	21.1	21.0	20.8	21.1	21.3	21.0	21.1
85°	13.7	13.5	13.9	13.7	13.9	13.5	13.7	13.7	13.3	13.7	13.5
87.5°	9.0	8.7	8.8	8.9	8.8	8.7	9.0	8.7	8.6	8.5	8.2
90°	14.3	14.7	15.2	14.7	15.2	14.7	14.3	14.7	13.7	13.2	12.8
92.5°	26.5	24.9	25.4	24.5	25.4	24.9	26.5	27.4	30.1	34.0	42.8
95°	69.2	64.6	61.0	59.0	61.0	64.6	69.2	78.8	97.1	124.1	183.1
97.5°	201.6	178.7	165.0	160.6	165.0	178.7	201.6	239.2	300.0	365.6	456.5
100°	375.3	338.2	318.4	318.9	318.4	338.2	375.3	426.7	498.9	558.5	599.7
102.5°	525.5	496.1	479.5	467.8	479.5	496.1	525.5	565.4	611.3	646.0	647.3
105°	685.1	665.8	649.5	646.9	649.5	665.8	685.1	708.5	721.8	712.0	661.2
107.5°	766.8	760.3	754.7	750.1	754.7	760.3	766.8	766.3	748.2	703.7	621.1
110°	790.4	794.4	793.4	792.4	793.4	794.4	790.4	776.1	740.6	676.5	582.8



TEST NUMBER: P332248-940

CATALOG NUMBER: S123RDIP-S340D585U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	784.3	796.9	800.8	800.9	800.8	796.9	784.3	758.2	712.5	640.6	545.0
115°	751.7	774.1	784.3	786.8	784.3	774.1	751.7	713.5	658.2	583.4	494.9
117.5°	698.1	723.7	738.4	741.8	738.4	723.7	698.1	658.4	602.1	534.9	458.5
120°	660.7	689.2	701.3	704.5	701.3	689.2	660.7	620.5	569.1	508.1	439.4
122.5°	626.5	652.1	665.6	669.4	665.6	652.1	626.5	590.8	543.1	486.5	424.4
125°	581.8	604.2	617.0	620.5	617.0	604.2	581.8	549.3	508.6	459.8	404.3
127.5°	546.4	565.4	576.9	580.2	576.9	565.4	546.4	517.4	480.4	436.3	386.8
130°	524.4	542.7	553.4	557.4	553.4	542.7	524.4	497.4	462.8	421.6	375.9
132.5°	504.4	522.7	532.2	535.0	532.2	522.7	504.4	479.1	446.1	407.8	365.7
135°	475.0	490.3	499.4	503.0	499.4	490.3	475.0	450.1	421.2	388.1	352.0
137.5°	443.6	459.1	466.8	469.1	466.8	459.1	443.6	422.7	397.5	369.1	339.5
140°	423.7	437.9	446.0	445.5	446.0	437.9	423.7	404.3	382.5	358.0	332.2
142.5°	404.1	416.8	424.1	423.6	424.1	416.8	404.1	387.6	368.6	347.5	325.2
145°	377.4	388.1	392.2	393.2	392.2	388.1	377.4	364.7	349.9	333.7	316.8
147.5°	356.6	363.8	367.7	368.1	367.7	363.8	356.6	347.0	336.5	323.3	310.0
150°	344.8	350.4	353.5	353.5	353.5	350.4	344.8	337.2	327.5	316.8	305.1
152.5°	334.2	339.5	341.3	341.3	341.3	339.5	334.2	328.2	320.2	310.8	300.7
155°	320.4	324.5	325.5	326.0	325.5	324.5	320.4	315.8	309.8	302.1	294.0
157.5°	308.4	311.4	312.2	312.1	312.2	311.4	308.4	304.3	299.6	293.6	286.9
160°	300.6	303.6	303.6	303.1	303.6	303.6	300.6	297.0	293.5	288.4	282.8
162.5°	292.8	295.5	295.5	295.0	295.5	295.5	292.8	290.5	287.4	282.7	277.9
165°	282.8	284.8	284.3	284.3	284.3	284.8	282.8	280.7	278.2	274.6	271.6
167.5°	273.2	274.6	274.1	274.1	274.1	274.6	273.2	272.3	270.5	268.4	266.1
170°	267.5	268.6	268.0	268.0	268.0	268.6	267.5	267.0	266.0	263.9	262.4
172.5°	262.6	263.7	262.8	262.3	262.8	263.7	262.6	262.5	261.9	260.3	259.2
175°	256.4	256.8	256.4	255.8	256.4	256.8	256.4	256.4	256.4	255.3	254.9
177.5°	252.4	252.9	252.1	252.1	252.1	252.9	252.4	252.9	252.9	252.4	252.1
180°	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3



TEST NUMBER: P332248-940

CATALOG NUMBER: S123RDIP-S340D585U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3
2.5°	463.2	465.6	467.9	470.0	473.3	474.8	477.0	477.9	480.3	483.9	487.0
5°	435.1	438.4	442.7	446.2	451.8	456.2	461.0	465.6	471.0	478.7	485.5
7.5°	411.2	414.4	419.6	426.2	432.4	438.6	445.1	451.4	459.1	470.1	481.0
10°	395.4	399.3	405.6	412.6	420.3	426.3	434.0	441.8	451.5	464.1	477.2
12.5°	381.7	384.7	391.9	398.6	407.3	415.0	422.5	431.8	442.6	456.1	471.9
15°	360.1	364.2	371.2	378.7	387.9	396.0	405.7	417.0	427.6	444.2	463.2
17.5°	338.2	344.6	352.0	360.3	367.1	378.4	388.9	400.4	413.5	431.1	452.1
20°	324.3	329.3	336.2	348.4	357.3	365.9	375.6	389.9	402.0	422.0	443.7
22.5°	312.5	316.1	323.9	333.9	344.4	354.2	364.2	377.8	392.7	411.6	435.2
25°	295.0	300.9	306.7	313.9	325.1	337.0	347.8	359.4	375.2	395.4	420.9
27.5°	277.9	283.2	288.9	297.8	306.4	317.4	328.8	342.1	359.0	380.3	406.3
30°	267.0	270.9	276.3	287.8	295.4	305.0	318.3	330.1	345.9	368.5	396.0
32.5°	255.7	260.7	266.7	275.4	285.0	294.0	306.1	319.0	335.1	357.4	385.5
35°	239.5	245.6	251.6	258.1	267.6	277.0	287.1	301.2	317.6	339.3	366.8
37.5°	224.7	229.5	234.4	242.5	251.5	260.4	269.9	283.8	299.3	322.6	347.9
40°	215.3	219.6	223.4	231.7	240.4	249.9	259.3	271.5	288.1	310.0	334.5
42.5°	204.9	208.9	214.0	220.9	230.2	238.3	247.6	259.2	274.8	297.0	318.5
45°	189.5	194.0	198.4	204.8	214.2	222.1	230.4	241.4	257.4	275.7	294.8
47.5°	173.3	178.0	183.0	189.2	197.3	205.4	213.7	223.4	238.0	255.9	268.9
50°	163.1	166.8	171.8	178.1	185.6	194.0	201.5	212.1	226.0	240.1	251.4
52.5°	152.5	155.9	161.5	168.1	175.0	182.4	190.4	199.5	212.0	225.3	234.3
55°	135.9	140.0	144.8	151.2	158.1	164.3	172.0	181.4	191.4	201.3	207.3
57.5°	120.4	123.9	127.9	134.5	140.4	147.8	154.8	162.0	171.3	178.8	182.7
60°	109.1	112.2	117.3	123.2	128.8	135.3	143.1	150.4	157.5	163.5	166.6
62.5°	98.4	102.0	106.6	111.9	118.0	124.1	131.0	137.1	143.4	148.6	150.7
65°	84.5	87.5	90.8	95.8	100.8	107.0	112.4	118.6	123.2	126.1	128.0
67.5°	72.0	73.8	76.3	79.7	84.6	90.1	95.2	100.1	104.0	105.9	107.6
70°	63.8	65.0	66.9	70.2	73.9	78.7	84.2	87.7	91.0	92.6	94.3
72.5°	55.6	57.2	58.9	61.6	64.6	68.1	72.1	76.3	78.2	80.2	81.1
75°	42.2	44.5	46.7	48.4	50.5	53.1	56.7	59.4	60.5	62.2	62.3
77.5°	31.8	32.4	34.0	36.0	37.8	39.8	42.0	44.4	44.9	45.7	46.4
80°	26.2	26.2	26.2	27.5	29.5	30.9	33.0	34.2	35.1	35.3	35.5
82.5°	21.0	21.0	20.9	21.1	21.8	22.6	24.5	25.9	26.7	26.5	26.0
85°	13.7	13.3	13.3	13.1	13.3	12.8	12.7	13.5	14.7	14.7	14.4
87.5°	8.1	8.0	7.8	7.4	7.0	6.5	5.8	5.7	5.4	5.9	5.5
90°	12.2	12.8	11.1	9.6	8.1	6.6	5.6	4.5	3.0	2.1	1.0
92.5°	59.0	78.2	86.1	64.6	42.7	29.4	21.8	17.6	13.6	9.4	6.3
95°	244.6	301.6	268.6	185.1	109.3	66.1	46.3	33.1	24.4	18.8	17.3
97.5°	500.1	467.4	342.1	203.1	117.7	76.4	54.9	41.9	34.4	30.1	29.5
100°	581.8	481.6	325.5	191.7	116.5	80.9	61.0	48.9	41.7	38.2	37.6
102.5°	585.9	455.2	301.1	182.0	118.1	86.1	67.9	57.0	50.3	47.1	46.2
105°	554.9	408.9	271.1	175.0	122.6	95.1	79.4	69.6	63.6	60.5	59.0
107.5°	500.6	368.0	252.0	174.4	130.9	106.8	92.2	83.1	77.1	74.2	72.6
110°	466.4	344.8	244.6	176.5	137.9	114.9	100.7	92.0	86.5	83.9	82.4



TEST NUMBER: P332248-940

CATALOG NUMBER: S123RDIP-S340D585U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	436.7	329.4	240.6	180.6	144.7	123.5	109.7	101.0	95.4	92.9	91.3
115°	400.8	312.8	239.1	187.2	156.1	136.8	123.1	114.4	109.3	106.3	104.2
117.5°	379.2	303.0	240.0	195.9	168.3	149.1	136.4	126.7	122.1	119.5	117.2
120°	367.7	298.5	241.6	202.4	175.9	157.7	145.0	135.3	130.2	127.7	126.2
122.5°	358.4	295.7	244.4	208.6	184.1	166.2	152.7	143.4	137.9	135.4	133.8
125°	346.3	291.9	248.7	218.2	195.8	178.0	164.3	154.6	149.0	146.0	145.0
127.5°	335.8	290.1	253.6	226.1	206.0	188.8	175.0	164.3	158.7	154.9	153.4
130°	330.1	288.9	256.8	231.4	212.0	195.3	181.6	170.9	164.8	160.2	158.7
132.5°	324.8	288.5	259.3	236.3	217.4	201.0	187.7	177.0	169.7	164.7	162.7
135°	317.9	287.8	263.0	242.6	225.3	209.6	195.8	185.1	177.5	171.9	169.9
137.5°	311.9	286.8	265.4	247.3	230.8	215.6	203.0	192.3	184.2	178.7	176.6
140°	308.2	286.3	267.0	249.8	234.4	219.7	207.0	196.8	188.7	183.6	181.1
142.5°	305.0	285.5	268.2	252.2	237.3	223.0	211.1	200.9	193.6	188.1	185.9
145°	300.6	284.3	269.0	254.9	241.1	227.8	216.2	207.5	199.9	195.3	193.8
147.5°	296.3	282.4	269.0	256.5	244.2	232.0	222.0	213.7	207.1	202.6	201.7
150°	293.5	280.7	269.0	256.8	246.2	234.4	225.3	218.2	211.6	207.5	207.0
152.5°	290.3	278.7	267.9	257.7	247.4	237.3	228.5	222.3	216.5	212.4	212.3
155°	285.3	275.2	266.5	257.9	249.8	241.1	234.0	228.4	223.3	220.3	220.3
157.5°	279.8	272.0	264.7	258.4	251.0	244.2	238.6	233.9	229.3	226.9	226.5
160°	276.2	269.6	263.9	258.4	252.3	246.2	241.1	237.6	233.4	231.4	231.4
162.5°	272.5	267.2	262.3	258.0	252.7	247.4	243.1	240.0	236.7	235.1	235.1
165°	267.5	263.5	259.9	256.8	253.2	249.2	245.7	243.6	241.1	240.0	240.6
167.5°	262.8	259.8	257.4	256.0	253.2	250.2	248.0	246.6	244.6	244.2	244.8
170°	259.9	257.3	255.8	254.9	252.8	250.2	249.2	248.2	246.6	246.2	247.2
172.5°	257.1	255.3	254.6	254.4	252.8	250.7	250.0	249.4	248.3	248.2	248.8
175°	253.8	252.8	252.8	253.2	252.3	251.3	250.7	250.7	249.8	250.2	250.7
177.5°	251.6	251.3	251.6	252.4	251.6	251.3	251.3	251.3	250.8	251.3	251.6
180°	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3



TEST NUMBER: P332248-940

CATALOG NUMBER: S123RDIP-S340D585U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3
2.5°	487.9	489.8	492.1	495.6	498.3	500.6	501.1	501.8	503.5	506.2	508.4
5°	491.2	495.9	503.5	511.0	519.2	525.8	532.1	536.5	540.6	549.3	556.3
7.5°	490.1	500.8	512.8	526.2	539.8	552.9	565.2	576.1	587.0	599.8	614.2
10°	489.5	501.9	518.2	535.4	554.3	572.7	590.7	604.6	620.7	635.3	653.8
12.5°	486.3	504.3	523.6	545.6	568.9	590.2	613.8	632.9	651.5	672.5	694.0
15°	482.1	504.0	528.5	557.8	593.2	618.8	643.0	676.5	699.3	722.1	752.9
17.5°	474.7	501.3	531.9	570.0	599.4	634.1	670.3	696.8	727.5	759.7	787.6
20°	468.7	499.6	534.0	571.3	608.9	646.5	681.6	713.2	745.0	782.2	805.0
22.5°	462.7	493.3	529.0	568.6	609.0	648.7	688.4	725.5	761.3	798.8	828.0
25°	450.0	486.3	525.0	565.5	605.4	649.0	696.3	737.7	781.9	820.6	848.3
27.5°	437.1	470.5	508.9	550.0	594.3	645.9	701.6	748.6	792.9	820.6	829.3
30°	425.4	460.7	496.1	537.9	585.9	643.4	702.6	756.4	792.7	804.9	795.9
32.5°	413.7	445.7	480.6	523.4	574.4	637.2	703.9	751.8	773.6	764.5	728.1
35°	392.9	421.7	455.6	498.4	557.0	633.8	698.5	730.8	725.5	673.5	604.9
37.5°	370.6	394.1	425.4	470.2	539.0	620.4	674.8	679.7	632.8	553.1	473.9
40°	352.9	374.2	406.4	453.1	525.0	607.1	651.1	631.8	559.3	470.6	404.5
42.5°	335.8	353.7	384.8	435.2	511.7	588.9	615.7	573.6	490.0	406.1	346.0
45°	306.8	323.7	354.8	406.5	484.5	554.3	550.7	477.6	393.9	326.4	276.5
47.5°	279.4	294.1	323.3	376.1	452.5	502.3	469.3	391.5	320.5	266.3	230.7
50°	259.9	274.5	303.5	355.7	427.0	463.2	416.2	341.2	276.1	231.2	203.0
52.5°	241.3	255.5	282.0	332.9	396.0	417.8	367.1	297.6	243.3	204.6	180.4
55°	215.3	226.0	249.9	298.5	345.7	350.7	299.3	241.2	196.5	169.5	152.9
57.5°	188.7	198.0	221.6	260.3	293.4	290.8	242.2	191.8	161.8	141.7	129.7
60°	171.4	180.6	201.3	234.5	259.5	250.7	206.1	165.6	139.8	125.1	115.5
62.5°	155.2	162.4	181.9	206.2	224.1	214.2	176.2	142.7	122.2	109.8	102.2
65°	131.9	137.8	153.3	166.0	175.9	166.4	134.8	111.6	96.8	88.1	82.9
67.5°	109.8	113.4	123.2	127.9	134.9	124.4	101.4	85.8	77.4	70.1	66.4
70°	95.8	98.4	103.7	107.5	109.2	98.4	81.4	70.0	63.0	57.8	55.5
72.5°	81.8	84.2	85.2	88.3	87.3	77.2	65.5	56.4	51.3	47.8	44.9
75°	62.5	63.6	62.5	61.3	58.6	51.5	43.4	38.9	35.1	33.4	32.4
77.5°	45.6	45.2	43.9	41.9	37.3	32.8	28.4	26.9	25.3	24.4	24.1
80°	35.1	34.2	33.0	29.9	25.9	22.8	21.8	20.8	20.2	19.1	18.9
82.5°	26.1	25.6	23.5	21.0	18.2	16.7	15.9	15.4	14.8	14.3	14.3
85°	13.9	13.3	11.0	9.5	9.2	8.7	8.6	8.6	7.7	7.5	7.5
87.5°	4.9	4.1	4.3	3.9	4.2	4.1	4.5	4.5	4.7	4.7	4.5
90°	2.1	3.0	4.5	5.6	6.6	8.1	9.6	11.1	12.8	12.2	12.8
92.5°	9.4	13.6	17.6	21.8	29.4	42.7	64.6	86.1	78.2	59.0	42.8
95°	18.8	24.4	33.1	46.3	66.1	109.3	185.1	268.6	301.6	244.6	183.1
97.5°	30.1	34.4	41.9	54.9	76.4	117.7	203.1	342.1	467.4	500.1	456.5
100°	38.2	41.7	48.9	61.0	80.9	116.5	191.7	325.5	481.6	581.8	599.7
102.5°	47.1	50.3	57.0	67.9	86.1	118.1	182.0	301.1	455.2	585.9	647.3
105°	60.5	63.6	69.6	79.4	95.1	122.6	175.0	271.1	408.9	554.9	661.2
107.5°	74.2	77.1	83.1	92.2	106.8	130.9	174.4	252.0	368.0	500.6	621.1
110°	83.9	86.5	92.0	100.7	114.9	137.9	176.5	244.6	344.8	466.4	582.8





TEST NUMBER: P332248-940

CATALOG NUMBER: S123RDIP-S340D585U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	92.9	95.4	101.0	109.7	123.5	144.7	180.6	240.6	329.4	436.7	545.0
115°	106.3	109.3	114.4	123.1	136.8	156.1	187.2	239.1	312.8	400.8	494.9
117.5°	119.5	122.1	126.7	136.4	149.1	168.3	195.9	240.0	303.0	379.2	458.5
120°	127.7	130.2	135.3	145.0	157.7	175.9	202.4	241.6	298.5	367.7	439.4
122.5°	135.4	137.9	143.4	152.7	166.2	184.1	208.6	244.4	295.7	358.4	424.4
125°	146.0	149.0	154.6	164.3	178.0	195.8	218.2	248.7	291.9	346.3	404.3
127.5°	154.9	158.7	164.3	175.0	188.8	206.0	226.1	253.6	290.1	335.8	386.8
130°	160.2	164.8	170.9	181.6	195.3	212.0	231.4	256.8	288.9	330.1	375.9
132.5°	164.7	169.7	177.0	187.7	201.0	217.4	236.3	259.3	288.5	324.8	365.7
135°	171.9	177.5	185.1	195.8	209.6	225.3	242.6	263.0	287.8	317.9	352.0
137.5°	178.7	184.2	192.3	203.0	215.6	230.8	247.3	265.4	286.8	311.9	339.5
140°	183.6	188.7	196.8	207.0	219.7	234.4	249.8	267.0	286.3	308.2	332.2
142.5°	188.1	193.6	200.9	211.1	223.0	237.3	252.2	268.2	285.5	305.0	325.2
145°	195.3	199.9	207.5	216.2	227.8	241.1	254.9	269.0	284.3	300.6	316.8
147.5°	202.6	207.1	213.7	222.0	232.0	244.2	256.5	269.0	282.4	296.3	310.0
150°	207.5	211.6	218.2	225.3	234.4	246.2	256.8	269.0	280.7	293.5	305.1
152.5°	212.4	216.5	222.3	228.5	237.3	247.4	257.7	267.9	278.7	290.3	300.7
155°	220.3	223.3	228.4	234.0	241.1	249.8	257.9	266.5	275.2	285.3	294.0
157.5°	226.9	229.3	233.9	238.6	244.2	251.0	258.4	264.7	272.0	279.8	286.9
160°	231.4	233.4	237.6	241.1	246.2	252.3	258.4	263.9	269.6	276.2	282.8
162.5°	235.1	236.7	240.0	243.1	247.4	252.7	258.0	262.3	267.2	272.5	277.9
165°	240.0	241.1	243.6	245.7	249.2	253.2	256.8	259.9	263.5	267.5	271.6
167.5°	244.2	244.6	246.6	248.0	250.2	253.2	256.0	257.4	259.8	262.8	266.1
170°	246.2	246.6	248.2	249.2	250.2	252.8	254.9	255.8	257.3	259.9	262.4
172.5°	248.2	248.3	249.4	250.0	250.7	252.8	254.4	254.6	255.3	257.1	259.2
175°	250.2	249.8	250.7	250.7	251.3	252.3	253.2	252.8	252.8	253.8	254.9
177.5°	251.3	250.8	251.3	251.3	251.3	251.6	252.4	251.6	251.3	251.6	252.1
180°	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3



TEST NUMBER: P332248-940

CATALOG NUMBER: S123RDIP-S340D585U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	485.3	485.3	485.3	485.3	485.3	485.3	485.3
2.5°	511.9	511.9	512.6	515.1	515.4	517.5	516.9
5°	562.6	566.5	568.0	574.3	577.9	579.6	576.3
7.5°	624.6	635.7	641.0	647.6	653.3	655.1	650.5
10°	669.8	681.4	691.2	697.2	702.8	706.6	711.3
12.5°	713.5	727.8	737.1	745.6	751.4	756.1	756.9
15°	761.0	782.6	799.0	811.1	817.1	820.2	818.9
17.5°	808.9	828.9	840.6	852.9	861.2	861.7	861.9
20°	836.0	855.5	869.1	878.2	887.5	887.1	889.2
22.5°	854.1	869.5	879.9	886.4	889.7	888.1	888.5
25°	862.6	867.2	865.3	854.7	851.9	842.2	843.9
27.5°	818.9	797.3	774.9	746.2	723.4	705.3	706.2
30°	759.6	721.3	677.7	641.1	608.3	599.1	579.6
32.5°	676.6	619.3	568.2	534.0	506.0	498.3	481.3
35°	536.0	480.3	427.8	396.2	383.7	366.2	366.0
37.5°	416.6	367.6	339.8	316.1	303.7	293.1	292.1
40°	350.4	312.3	291.2	274.2	262.0	254.0	252.2
42.5°	304.3	273.4	253.7	243.2	233.7	229.6	226.6
45°	248.4	227.7	214.0	204.5	200.1	197.0	195.3
47.5°	207.9	193.9	184.6	178.2	174.7	171.4	172.3
50°	185.7	174.3	167.5	161.4	158.7	156.4	156.7
52.5°	167.9	157.7	152.1	147.8	144.5	142.8	142.0
55°	142.5	136.1	130.5	127.3	125.5	123.2	122.6
57.5°	121.5	116.5	112.0	108.5	108.0	105.8	106.1
60°	107.6	103.4	99.7	97.8	96.4	94.5	95.1
62.5°	96.1	92.6	89.3	87.7	86.2	84.9	85.2
65°	78.7	75.4	73.3	72.5	71.9	71.2	70.6
67.5°	62.8	60.7	59.4	57.6	56.4	56.2	55.6
70°	52.8	50.0	47.8	45.5	44.9	44.7	44.9
72.5°	42.3	40.6	39.9	38.9	38.7	38.2	38.5
75°	31.7	31.1	30.8	29.9	29.9	29.9	29.9
77.5°	23.5	23.1	22.8	22.6	22.5	22.1	22.1
80°	18.3	18.1	17.7	17.7	17.5	17.7	17.5
82.5°	13.8	13.7	13.4	13.4	13.1	13.0	13.1
85°	7.0	6.9	7.3	6.9	7.0	6.7	7.0
87.5°	4.6	4.7	4.8	4.6	4.6	5.1	4.6
90°	13.2	13.7	14.7	14.3	14.7	15.2	14.7
92.5°	34.0	30.1	27.4	26.5	24.9	25.4	24.5
95°	124.1	97.1	78.8	69.2	64.6	61.0	59.0
97.5°	365.6	300.0	239.2	201.6	178.7	165.0	160.6
100°	558.5	498.9	426.7	375.3	338.2	318.4	318.9
102.5°	646.0	611.3	565.4	525.5	496.1	479.5	467.8
105°	712.0	721.8	708.5	685.1	665.8	649.5	646.9
107.5°	703.7	748.2	766.3	766.8	760.3	754.7	750.1
110°	676.5	740.6	776.1	790.4	794.4	793.4	792.4



TEST NUMBER: P332248-940

CATALOG NUMBER: S123RDIP-S340D585U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	640.6	712.5	758.2	784.3	796.9	800.8	800.9
115°	583.4	658.2	713.5	751.7	774.1	784.3	786.8
117.5°	534.9	602.1	658.4	698.1	723.7	738.4	741.8
120°	508.1	569.1	620.5	660.7	689.2	701.3	704.5
122.5°	486.5	543.1	590.8	626.5	652.1	665.6	669.4
125°	459.8	508.6	549.3	581.8	604.2	617.0	620.5
127.5°	436.3	480.4	517.4	546.4	565.4	576.9	580.2
130°	421.6	462.8	497.4	524.4	542.7	553.4	557.4
132.5°	407.8	446.1	479.1	504.4	522.7	532.2	535.0
135°	388.1	421.2	450.1	475.0	490.3	499.4	503.0
137.5°	369.1	397.5	422.7	443.6	459.1	466.8	469.1
140°	358.0	382.5	404.3	423.7	437.9	446.0	445.5
142.5°	347.5	368.6	387.6	404.1	416.8	424.1	423.6
145°	333.7	349.9	364.7	377.4	388.1	392.2	393.2
147.5°	323.3	336.5	347.0	356.6	363.8	367.7	368.1
150°	316.8	327.5	337.2	344.8	350.4	353.5	353.5
152.5°	310.8	320.2	328.2	334.2	339.5	341.3	341.3
155°	302.1	309.8	315.8	320.4	324.5	325.5	326.0
157.5°	293.6	299.6	304.3	308.4	311.4	312.2	312.1
160°	288.4	293.5	297.0	300.6	303.6	303.6	303.1
162.5°	282.7	287.4	290.5	292.8	295.5	295.5	295.0
165°	274.6	278.2	280.7	282.8	284.8	284.3	284.3
167.5°	268.4	270.5	272.3	273.2	274.6	274.1	274.1
170°	263.9	266.0	267.0	267.5	268.6	268.0	268.0
172.5°	260.3	261.9	262.5	262.6	263.7	262.8	262.3
175°	255.3	256.4	256.4	256.4	256.8	256.4	255.8
177.5°	252.4	252.9	252.9	252.4	252.9	252.1	252.1
180°	251.3	251.3	251.3	251.3	251.3	251.3	251.3

(END OF REPORT)