

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332290-940

Luminaire Tested: **S123RDIP-S560D1025U940-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332290-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S560D1025U940-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1025 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5298.0 lumens
Efficiency: N/A
Efficacy: 119.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 44.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332290-940

CATALOG NUMBER: S123RDIP-S560D1025U940-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332290-940

CATALOG NUMBER: S123RDIP-S560D1025U940-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	45	45	45	38				
1	95	91	88	84	86	83	80	77	68	65	63	53	52	51	40	39	39	32				
2	87	80	74	70	79	73	68	64	60	56	53	47	45	43	36	34	33	28				
3	80	71	64	58	72	65	59	54	53	49	45	42	39	37	32	30	29	24				
4	73	63	55	50	66	58	51	46	47	43	39	38	35	32	29	27	25	21				
5	67	56	48	43	61	51	45	40	42	37	34	34	31	28	26	24	22	19				
6	62	50	43	37	56	46	40	35	38	33	29	31	27	24	24	22	20	17				
7	57	46	38	33	52	42	35	30	35	30	26	28	25	22	22	19	18	15				
8	53	41	34	29	48	38	32	27	32	27	23	26	22	19	20	18	16	13				
9	50	38	31	26	45	35	28	24	29	24	21	24	20	18	19	16	14	12				
10	46	35	28	23	42	32	26	22	27	22	19	22	18	16	17	15	13	11				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8587	8587	8587	8587
5°	10237	8625	7595	8625
10°	12783	8575	6862	8575
15°	15004	8487	6257	8487
20°	16745	8356	5743	8356
25°	16476	8219	5428	8219
30°	11844	8090	5102	8090
35°	7908	7926	4892	7926
40°	5826	7727	4675	7727
45°	4886	7377	4460	7377
50°	4312	6921	4163	6921
55°	3781	6397	3755	6397
60°	3367	5896	3442	5896
65°	2957	5359	3202	5359
70°	2319	4881	2924	4881
75°	2046	4263	2670	4263
80°	1779	3620	2628	3620
85°	1433	2902	2791	2902



TEST NUMBER: P332290-940

CATALOG NUMBER: S123RDIP-S560D1025U940-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.5	1.5
10°-20°	245.1	4.6
20°-30°	385.1	7.3
30°-40°	401.8	7.6
40°-50°	343.8	6.5
50°-60°	262.1	4.9
60°-70°	168.0	3.2
70°-80°	80.8	1.5
80°-90°	24.8	0.5
90°-100°	244.7	4.6
100°-110°	692.9	13.1
110°-120°	681.6	12.9
120°-130°	543.7	10.3
130°-140°	428.7	8.1
140°-150°	319.9	6.0
150°-160°	223.0	4.2
160°-170°	131.0	2.5
170°-180°	42.6	0.8
0°-30°	708.7	13.4
0°-40°	1110.4	21.0
0°-60°	1716.3	32.4
0°-90°	1989.9	37.6
90°-120°	1619.2	30.6
90°-150°	2911.5	55.0
90°-180°	3308.0	62.4
0°-180°	5298.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	798	798	798	798	798	
5°	947	798	703	798	947	98
15°	1346	762	562	762	1346	382
25°	1387	692	457	692	1387	596
35°	602	603	372	603	602	395
45°	321	485	293	485	321	252
55°	202	341	200	341	202	182
65°	116	210	126	210	116	114
75°	49	102	64	102	49	53
85°	12	24	23	24	12	14
90°	26	2	26	2	26	14
95°	103	30	103	30	103	186
105°	1132	103	1132	103	1132	1117
115°	1377	182	1377	182	1377	1338
125°	1086	254	1086	254	1086	984
135°	880	297	880	297	880	683
145°	688	339	688	339	688	438
155°	570	385	570	385	570	266
165°	498	421	498	421	498	142
175°	448	439	448	439	448	43
180°	440	440	440	440	440	



TEST NUMBER: P332290-940

CATALOG NUMBER: S123RDIP-S560D1025U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8
2.5°	849.7	850.9	847.3	846.8	842.7	841.6	841.6	835.8	832.2	827.6	824.9
5°	947.4	952.9	950.2	944.1	933.8	931.4	924.9	914.6	903.0	888.7	881.9
7.5°	1069.4	1076.9	1074.0	1064.5	1053.8	1045.1	1026.8	1009.8	986.0	965.1	947.2
10°	1169.5	1161.5	1155.5	1146.2	1136.3	1120.3	1101.2	1074.9	1044.5	1020.6	993.9
12.5°	1244.3	1243.0	1235.2	1225.7	1211.7	1196.5	1173.0	1140.9	1105.6	1071.0	1040.6
15°	1346.4	1348.4	1343.3	1333.4	1313.6	1286.6	1251.1	1237.8	1187.2	1149.6	1112.1
17.5°	1417.0	1416.6	1415.9	1402.1	1382.0	1362.7	1329.8	1294.8	1249.0	1196.1	1145.5
20°	1461.8	1458.4	1459.1	1443.7	1428.7	1406.5	1374.4	1323.5	1285.9	1224.8	1172.5
22.5°	1460.7	1460.0	1462.6	1457.3	1446.4	1429.4	1404.2	1361.2	1313.2	1251.5	1192.8
25°	1387.3	1384.6	1400.7	1405.1	1422.5	1425.6	1418.1	1394.5	1349.1	1285.6	1212.8
27.5°	1161.1	1159.6	1189.4	1226.6	1274.0	1310.7	1346.2	1363.3	1349.1	1303.6	1230.7
30°	952.9	985.0	1000.1	1054.0	1114.1	1185.8	1248.7	1308.4	1323.1	1303.3	1243.6
32.5°	791.1	819.1	831.7	878.1	934.1	1018.1	1112.3	1196.9	1256.8	1271.9	1235.9
35°	601.8	602.2	630.8	651.3	703.2	789.6	881.2	994.5	1107.2	1192.7	1201.6
37.5°	480.2	481.9	499.3	519.7	558.7	604.3	684.9	779.2	909.4	1040.4	1117.3
40°	414.6	417.7	430.7	450.8	478.8	513.4	576.2	664.9	773.6	919.4	1038.7
42.5°	372.6	377.6	384.2	399.8	417.1	449.4	500.2	568.8	667.5	805.5	943.0
45°	321.0	323.8	328.9	336.1	351.8	374.3	408.5	454.6	536.5	647.6	785.2
47.5°	283.2	281.8	287.1	293.0	303.4	318.8	341.7	379.3	437.8	526.8	643.6
50°	257.5	257.2	260.9	265.4	275.3	286.6	305.3	333.7	380.1	453.9	560.8
52.5°	233.4	234.8	237.5	243.0	250.1	259.2	276.1	296.5	336.4	400.1	489.2
55°	201.5	202.5	206.3	209.4	214.5	223.7	234.3	251.4	278.7	323.1	396.5
57.5°	174.4	174.0	177.6	178.3	184.1	191.6	199.8	213.1	232.9	265.9	315.4
60°	156.4	155.4	158.5	160.9	163.9	170.0	176.9	189.9	205.6	229.9	272.2
62.5°	140.0	139.6	141.8	144.2	146.7	152.3	158.1	168.0	180.5	200.9	234.5
65°	116.1	117.2	118.2	119.2	120.6	123.9	129.5	136.3	144.8	159.2	183.4
67.5°	91.2	92.3	92.6	94.7	97.6	99.8	103.2	109.2	115.2	127.2	141.1
70°	73.7	73.4	73.7	74.8	78.6	82.3	86.8	91.2	95.0	103.5	115.1
72.5°	63.4	62.8	63.7	63.8	65.7	66.7	69.6	73.7	78.6	84.4	92.7
75°	49.2	49.2	49.2	49.2	50.6	51.3	52.3	53.3	55.0	57.7	63.8
77.5°	36.4	36.4	36.9	37.2	37.5	37.9	38.5	39.6	40.1	41.6	44.2
80°	28.7	29.1	28.7	29.1	29.1	29.7	30.1	31.1	31.4	33.2	34.2
82.5°	21.6	21.4	21.6	21.9	21.9	22.6	22.6	23.5	23.5	24.3	25.4
85°	11.6	11.0	11.6	11.2	11.9	11.2	11.6	12.3	12.3	12.7	14.0
87.5°	7.9	8.6	7.9	8.0	8.2	8.1	7.9	7.8	8.1	8.0	7.8
90°	25.8	26.7	25.8	24.9	25.8	24.1	23.2	22.3	21.4	22.3	19.6
92.5°	42.9	44.5	43.6	46.3	47.9	52.5	59.5	74.9	103.3	136.9	150.6
95°	103.3	106.8	113.1	121.1	137.9	170.0	217.2	320.4	428.1	527.8	469.9
97.5°	281.1	288.7	312.8	352.8	418.5	525.0	639.8	798.8	875.1	818.0	598.9
100°	558.1	557.2	591.9	656.9	746.8	873.2	977.3	1049.5	1018.2	842.9	569.6
102.5°	818.7	839.2	868.2	919.6	989.6	1069.7	1130.4	1132.7	1025.4	796.7	526.9
105°	1132.2	1136.7	1165.1	1198.9	1239.9	1263.0	1246.2	1157.1	971.1	715.6	474.4
107.5°	1312.7	1320.9	1330.5	1341.9	1341.2	1309.5	1231.5	1087.0	876.0	644.1	441.0
110°	1386.8	1388.6	1390.4	1383.2	1358.3	1295.9	1183.8	1020.0	816.2	603.5	428.1



TEST NUMBER: P332290-940

CATALOG NUMBER: S123RDIP-S560D1025U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1401.7	1401.3	1394.5	1372.5	1327.0	1246.8	1121.1	953.8	764.2	576.4	421.0
115°	1377.0	1372.5	1354.7	1315.5	1248.8	1151.7	1020.9	866.0	701.4	547.4	418.3
117.5°	1298.2	1292.3	1266.6	1221.7	1152.1	1053.6	936.2	802.5	663.4	530.3	419.9
120°	1232.8	1227.4	1206.0	1156.2	1085.9	996.0	889.2	769.0	643.5	522.5	422.8
122.5°	1171.5	1164.8	1141.3	1096.4	1033.9	950.5	851.5	742.7	627.1	517.5	427.8
125°	1085.9	1079.7	1057.4	1018.2	961.3	890.1	804.7	707.7	606.2	511.0	435.2
127.5°	1015.4	1009.7	989.6	956.1	905.4	840.6	763.5	677.0	587.6	507.7	443.8
130°	975.5	968.4	949.8	917.7	870.5	809.9	737.9	657.8	577.7	505.6	449.5
132.5°	936.4	931.4	914.8	882.8	838.5	780.8	713.6	640.0	568.4	504.9	453.8
135°	880.3	874.1	858.0	831.3	787.7	737.0	679.1	615.9	556.3	503.8	460.2
137.5°	821.0	816.9	803.4	776.3	739.7	695.7	645.9	594.1	545.8	501.9	464.4
140°	779.7	780.6	766.3	741.5	707.7	669.3	626.6	581.2	539.4	501.1	467.3
142.5°	741.3	742.2	729.3	707.3	678.4	645.2	608.1	569.1	533.7	499.7	469.4
145°	688.0	686.3	679.1	660.4	638.2	612.3	583.9	554.6	526.0	497.6	470.8
147.5°	644.3	643.5	636.8	624.1	607.3	588.9	565.9	542.6	518.5	494.2	470.8
150°	618.6	618.6	613.2	603.5	590.1	573.2	554.6	534.0	513.5	491.3	470.8
152.5°	597.3	597.3	594.1	585.0	574.4	560.4	543.9	526.2	507.9	487.8	468.7
155°	570.5	569.6	567.8	560.8	552.8	542.1	528.7	514.4	499.4	481.5	466.4
157.5°	546.2	546.4	544.9	539.6	532.6	524.2	513.9	502.0	489.7	476.0	463.4
160°	530.5	531.4	531.4	526.0	519.8	513.5	504.7	494.9	483.3	471.7	462.0
162.5°	516.2	517.1	517.1	512.6	508.5	502.9	494.7	486.3	476.9	467.4	459.1
165°	497.6	497.6	498.5	494.9	491.3	486.9	480.6	475.3	468.1	461.1	454.9
167.5°	479.7	479.7	480.6	478.1	476.5	473.3	469.8	465.7	459.9	454.7	450.6
170°	469.0	469.0	469.9	468.1	467.3	465.5	462.0	459.3	454.9	450.4	447.7
172.5°	459.1	459.9	461.5	459.7	459.5	458.4	455.6	453.6	449.9	446.8	445.6
175°	447.7	448.6	449.5	448.6	448.6	448.6	446.8	445.9	444.2	442.4	442.4
177.5°	441.1	441.1	442.6	441.8	442.6	442.6	441.8	441.1	440.4	439.7	440.4
180°	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7



TEST NUMBER: P332290-940

CATALOG NUMBER: S123RDIP-S560D1025U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8
2.5°	823.8	823.0	819.1	814.8	809.0	805.2	802.2	800.6	795.7	789.6	785.5
5°	874.7	864.4	853.5	840.2	827.9	815.3	807.4	798.2	786.9	774.3	765.4
7.5°	929.2	909.1	887.4	865.1	843.0	823.2	805.7	790.8	772.8	754.7	742.0
10°	971.0	941.6	911.2	880.1	851.8	825.2	804.7	784.5	763.0	742.2	726.5
12.5°	1009.0	970.4	935.3	897.1	860.9	829.0	799.5	775.8	749.9	727.7	709.8
15°	1057.0	1017.4	975.1	917.0	868.9	828.6	792.7	761.6	730.2	702.9	685.5
17.5°	1102.0	1042.4	985.5	937.0	874.5	824.1	780.3	743.2	708.7	679.8	658.3
20°	1120.6	1062.9	1001.0	939.2	877.8	821.4	770.5	729.5	693.7	660.8	641.1
22.5°	1131.8	1066.4	1001.3	934.9	869.6	811.0	760.7	715.6	676.7	645.6	621.2
25°	1144.9	1066.9	995.2	929.7	863.1	799.5	739.8	692.0	650.0	616.8	590.8
27.5°	1153.4	1061.8	977.0	904.2	836.6	773.4	718.6	667.9	625.3	590.2	562.4
30°	1155.1	1057.7	963.1	884.2	815.6	757.5	699.5	650.9	605.9	568.6	542.7
32.5°	1157.3	1047.7	944.3	860.5	790.2	732.7	680.1	633.7	587.5	550.9	524.4
35°	1148.3	1042.1	915.7	819.4	749.0	693.3	645.9	603.2	557.8	522.2	495.3
37.5°	1109.5	1019.8	886.0	773.0	699.5	647.9	609.2	572.0	530.4	492.0	466.6
40°	1070.4	998.0	863.1	744.9	668.1	615.1	580.2	549.9	509.6	473.7	446.4
42.5°	1012.2	968.2	841.2	715.4	632.5	581.5	552.1	523.6	488.3	451.8	426.1
45°	905.4	911.2	796.5	668.4	583.4	532.1	504.4	484.6	453.3	423.2	396.9
47.5°	771.5	825.8	744.0	618.3	531.5	483.4	459.2	441.9	420.8	391.3	367.3
50°	684.1	761.6	701.9	584.7	499.0	451.2	427.3	413.3	394.8	371.6	348.7
52.5°	603.5	686.8	651.0	547.2	463.8	420.0	396.6	385.1	370.5	348.7	328.0
55°	492.1	576.5	568.3	490.8	410.9	371.6	353.8	340.9	330.9	314.6	298.2
57.5°	398.1	478.0	482.3	427.9	364.3	325.5	310.2	300.4	293.9	281.6	266.4
60°	338.9	412.2	426.6	385.6	330.9	296.8	281.8	273.9	268.8	258.9	247.3
62.5°	289.6	352.1	368.4	338.9	299.0	267.0	255.3	247.7	244.2	235.7	225.4
65°	221.7	273.6	289.3	272.9	252.1	226.4	216.9	210.4	207.3	202.5	195.0
67.5°	166.7	204.6	221.8	210.2	202.7	186.5	180.4	176.9	174.2	170.9	164.6
70°	133.8	161.9	179.7	176.6	170.4	161.9	157.5	155.1	152.3	149.6	144.1
72.5°	107.6	126.9	143.6	145.2	140.1	138.4	134.5	133.5	131.8	128.6	125.6
75°	71.4	84.7	96.3	100.8	102.8	104.5	102.8	102.5	102.1	99.4	97.6
77.5°	46.8	53.9	61.3	68.8	72.1	74.4	74.9	76.2	75.3	73.8	73.0
80°	35.8	37.5	42.7	49.2	54.3	56.4	57.7	58.4	58.1	57.7	56.4
82.5°	26.0	27.5	29.9	34.4	38.7	42.2	43.0	42.8	43.6	43.8	42.7
85°	14.0	14.4	15.1	15.7	18.1	21.8	22.9	23.5	24.3	24.3	22.2
87.5°	7.8	7.0	7.0	6.6	7.0	6.8	8.1	9.1	9.7	9.0	9.5
90°	16.9	14.3	11.6	9.8	8.0	5.4	3.6	1.8	3.6	5.4	8.0
92.5°	113.1	74.7	51.5	38.3	30.8	23.9	16.4	11.1	16.4	23.9	30.8
95°	324.0	191.4	115.7	81.0	57.9	42.7	32.9	30.2	32.9	42.7	57.9
97.5°	355.5	206.0	133.7	96.1	73.3	60.2	52.5	51.6	52.5	60.2	73.3
100°	335.6	203.8	141.5	106.8	85.4	73.0	66.8	65.9	66.8	73.0	85.4
102.5°	318.4	206.7	150.8	119.0	99.7	87.9	82.4	80.8	82.4	87.9	99.7
105°	306.2	214.5	166.5	138.8	122.0	111.3	105.9	103.3	105.9	111.3	122.0
107.5°	305.3	229.1	186.9	161.3	145.4	134.9	129.7	127.1	129.7	134.9	145.4
110°	308.9	241.2	201.2	176.2	161.1	151.3	146.9	144.2	146.9	151.3	161.1



TEST NUMBER: P332290-940

CATALOG NUMBER: S123RDIP-S560D1025U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	316.0	253.3	216.2	191.9	176.7	167.0	162.6	159.9	162.6	167.0	176.7
115°	327.5	273.2	239.4	215.4	200.3	191.4	186.0	182.4	186.0	191.4	200.3
117.5°	342.9	294.4	261.0	238.7	221.8	213.7	209.2	205.1	209.2	213.7	221.8
120°	354.3	308.0	275.9	253.7	236.7	227.8	223.4	220.7	223.4	227.8	236.7
122.5°	365.0	322.2	290.9	267.2	251.0	241.4	236.9	234.3	236.9	241.4	251.0
125°	381.8	342.7	311.6	287.5	270.5	260.8	255.5	253.7	255.5	260.8	270.5
127.5°	395.7	360.5	330.4	306.4	287.7	277.7	271.1	268.5	271.1	277.7	287.7
130°	405.0	371.1	341.8	317.7	299.1	288.4	280.4	277.7	280.4	288.4	299.1
132.5°	413.6	380.4	351.8	328.4	309.8	296.9	288.2	284.8	288.2	296.9	309.8
135°	424.5	394.3	366.7	342.7	324.0	310.7	300.9	297.3	300.9	310.7	324.0
137.5°	432.7	403.9	377.4	355.2	336.6	322.4	312.8	309.1	312.8	322.4	336.6
140°	437.0	410.4	384.5	362.3	344.5	330.2	321.3	316.9	321.3	330.2	344.5
142.5°	441.3	415.4	390.2	369.3	351.6	338.8	329.1	325.4	329.1	338.8	351.6
145°	445.9	421.9	398.8	378.3	363.2	349.8	341.8	339.1	341.8	349.8	363.2
147.5°	448.8	427.2	406.1	388.6	374.0	362.5	354.6	353.0	354.6	362.5	374.0
150°	449.5	430.8	410.4	394.3	381.8	370.2	363.2	362.3	363.2	370.2	381.8
152.5°	450.9	432.9	415.4	400.0	389.0	378.8	371.7	371.5	371.7	378.8	389.0
155°	451.3	437.0	421.9	409.5	399.7	390.7	385.4	385.4	385.4	390.7	399.7
157.5°	452.2	439.3	427.2	417.6	409.3	401.4	397.2	396.5	397.2	401.4	409.3
160°	452.2	441.5	430.8	421.9	415.6	408.6	405.0	405.0	405.0	408.6	415.6
162.5°	451.5	442.2	432.9	425.4	419.9	414.3	411.4	411.4	411.4	414.3	419.9
165°	449.5	443.3	436.1	429.9	426.3	421.9	420.1	421.0	420.1	421.9	426.3
167.5°	448.1	443.1	437.9	434.0	431.5	428.1	427.2	428.3	427.2	428.1	431.5
170°	445.9	442.4	437.9	436.1	434.4	431.7	430.8	432.6	430.8	431.7	434.4
172.5°	445.2	442.4	438.6	437.6	436.5	434.5	434.4	435.4	434.4	434.5	436.5
175°	443.3	441.5	439.7	438.8	438.8	437.0	437.9	438.8	437.9	437.0	438.8
177.5°	441.8	440.4	439.7	439.7	439.7	439.0	439.7	440.4	439.7	439.0	439.7
180°	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7



TEST NUMBER: P332290-940

CATALOG NUMBER: S123RDIP-S560D1025U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8
2.5°	784.2	780.6	778.2	772.7	769.2	765.4	761.5	763.9	763.7	763.4	763.4
5°	757.9	750.0	742.9	733.6	727.8	720.7	715.2	714.5	715.9	711.1	708.4
7.5°	731.8	721.0	710.9	700.7	689.9	681.3	675.9	673.4	669.9	667.0	663.9
10°	713.5	700.9	690.9	678.3	666.7	656.5	650.0	645.5	643.1	640.7	636.3
12.5°	694.6	682.2	669.6	655.3	644.3	632.4	627.6	622.6	618.0	615.3	609.2
15°	667.0	650.9	637.7	622.6	610.4	598.7	591.9	582.0	580.6	577.2	571.1
17.5°	639.4	622.0	603.6	592.5	578.5	566.5	556.1	552.8	543.0	539.3	534.0
20°	617.5	601.5	587.5	572.7	552.6	541.4	533.2	528.7	520.8	516.0	512.6
22.5°	598.7	582.3	566.1	549.0	532.4	519.8	513.7	506.8	502.6	495.9	492.1
25°	571.8	554.0	534.5	516.0	504.1	494.5	485.0	478.8	472.7	469.6	462.8
27.5°	540.5	521.9	503.7	489.7	475.0	465.6	456.9	451.5	444.1	438.9	435.2
30°	523.3	501.4	485.7	473.1	454.2	445.4	438.9	432.0	426.6	421.2	417.3
32.5°	503.3	483.3	468.4	452.8	438.4	428.7	420.3	414.3	409.7	404.5	400.7
35°	472.0	455.3	439.9	424.2	413.6	403.7	393.8	388.7	384.2	379.4	376.0
37.5°	443.7	428.1	413.5	398.6	385.5	377.4	369.4	365.5	359.5	356.3	352.8
40°	426.2	410.9	395.2	380.8	367.1	361.1	353.8	348.0	342.6	340.2	336.4
42.5°	407.2	391.7	378.5	363.0	351.9	343.5	336.9	330.6	326.5	323.0	320.8
45°	378.8	365.1	352.1	336.8	326.2	319.0	311.5	305.7	301.9	299.5	295.8
47.5°	351.2	337.6	324.4	311.0	300.8	292.6	285.1	281.0	276.1	273.1	270.5
50°	331.3	319.0	305.0	292.7	282.5	274.3	268.1	263.0	258.5	254.8	253.1
52.5°	313.0	299.9	287.8	276.3	265.6	256.2	250.7	245.2	241.9	237.6	235.6
55°	282.8	270.2	259.9	248.6	238.1	230.2	223.4	218.6	215.2	210.4	207.7
57.5°	254.4	243.1	230.9	221.1	210.2	203.6	197.9	191.4	187.3	183.5	180.8
60°	235.3	222.3	211.8	202.5	193.0	184.4	179.3	174.2	169.8	165.9	163.6
62.5°	215.3	204.0	194.0	184.0	175.2	167.7	161.8	157.5	153.6	151.2	148.8
65°	184.8	175.9	165.7	157.5	149.3	143.8	139.0	135.3	132.5	130.8	128.8
67.5°	156.7	148.0	139.1	131.0	125.6	121.4	118.2	115.0	113.7	111.5	110.1
70°	138.3	129.5	121.6	115.5	109.9	106.9	104.9	102.5	101.1	98.4	97.0
72.5°	118.4	112.0	106.3	101.2	96.8	94.1	91.5	88.5	86.3	83.4	81.9
75°	93.3	87.5	83.0	79.5	76.9	73.1	69.4	66.3	65.3	64.2	63.8
77.5°	69.0	65.4	62.2	59.3	55.9	53.1	52.3	51.6	51.5	50.9	50.9
80°	54.3	50.9	48.5	45.1	43.1	43.1	43.1	42.4	42.7	42.7	42.7
82.5°	40.4	37.2	35.9	34.7	34.3	34.6	34.6	34.7	34.5	35.0	34.8
85°	20.9	21.1	21.8	21.5	21.8	21.8	22.6	22.2	22.6	21.8	22.6
87.5°	9.6	10.8	11.6	12.4	13.2	13.5	13.6	13.7	14.2	14.4	14.7
90°	9.8	11.6	14.3	16.9	19.6	22.3	21.4	22.3	23.2	24.1	25.8
92.5°	38.3	51.5	74.7	113.1	150.6	136.9	103.3	74.9	59.5	52.5	47.9
95°	81.0	115.7	191.4	324.0	469.9	527.8	428.1	320.4	217.2	170.0	137.9
97.5°	96.1	133.7	206.0	355.5	598.9	818.0	875.1	798.8	639.8	525.0	418.5
100°	106.8	141.5	203.8	335.6	569.6	842.9	1018.2	1049.5	977.3	873.2	746.8
102.5°	119.0	150.8	206.7	318.4	526.9	796.7	1025.4	1132.7	1130.4	1069.7	989.6
105°	138.8	166.5	214.5	306.2	474.4	715.6	971.1	1157.1	1246.2	1263.0	1239.9
107.5°	161.3	186.9	229.1	305.3	441.0	644.1	876.0	1087.0	1231.5	1309.5	1341.2
110°	176.2	201.2	241.2	308.9	428.1	603.5	816.2	1020.0	1183.8	1295.9	1358.3



TEST NUMBER: P332290-940

CATALOG NUMBER: S123RDIP-S560D1025U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	191.9	216.2	253.3	316.0	421.0	576.4	764.2	953.8	1121.1	1246.8	1327.0
115°	215.4	239.4	273.2	327.5	418.3	547.4	701.4	866.0	1020.9	1151.7	1248.8
117.5°	238.7	261.0	294.4	342.9	419.9	530.3	663.4	802.5	936.2	1053.6	1152.1
120°	253.7	275.9	308.0	354.3	422.8	522.5	643.5	769.0	889.2	996.0	1085.9
122.5°	267.2	290.9	322.2	365.0	427.8	517.5	627.1	742.7	851.5	950.5	1033.9
125°	287.5	311.6	342.7	381.8	435.2	511.0	606.2	707.7	804.7	890.1	961.3
127.5°	306.4	330.4	360.5	395.7	443.8	507.7	587.6	677.0	763.5	840.6	905.4
130°	317.7	341.8	371.1	405.0	449.5	505.6	577.7	657.8	737.9	809.9	870.5
132.5°	328.4	351.8	380.4	413.6	453.8	504.9	568.4	640.0	713.6	780.8	838.5
135°	342.7	366.7	394.3	424.5	460.2	503.8	556.3	615.9	679.1	737.0	787.7
137.5°	355.2	377.4	403.9	432.7	464.4	501.9	545.8	594.1	645.9	695.7	739.7
140°	362.3	384.5	410.4	437.0	467.3	501.1	539.4	581.2	626.6	669.3	707.7
142.5°	369.3	390.2	415.4	441.3	469.4	499.7	533.7	569.1	608.1	645.2	678.4
145°	378.3	398.8	421.9	445.9	470.8	497.6	526.0	554.6	583.9	612.3	638.2
147.5°	388.6	406.1	427.2	448.8	470.8	494.2	518.5	542.6	565.9	588.9	607.3
150°	394.3	410.4	430.8	449.5	470.8	491.3	513.5	534.0	554.6	573.2	590.1
152.5°	400.0	415.4	432.9	450.9	468.7	487.8	507.9	526.2	543.9	560.4	574.4
155°	409.5	421.9	437.0	451.3	466.4	481.5	499.4	514.4	528.7	542.1	552.8
157.5°	417.6	427.2	439.3	452.2	463.4	476.0	489.7	502.0	513.9	524.2	532.6
160°	421.9	430.8	441.5	452.2	462.0	471.7	483.3	494.9	504.7	513.5	519.8
162.5°	425.4	432.9	442.2	451.5	459.1	467.4	476.9	486.3	494.7	502.9	508.5
165°	429.9	436.1	443.3	449.5	454.9	461.1	468.1	475.3	480.6	486.9	491.3
167.5°	434.0	437.9	443.1	448.1	450.6	454.7	459.9	465.7	469.8	473.3	476.5
170°	436.1	437.9	442.4	445.9	447.7	450.4	454.9	459.3	462.0	465.5	467.3
172.5°	437.6	438.6	442.4	445.2	445.6	446.8	449.9	453.6	455.6	458.4	459.5
175°	438.8	439.7	441.5	443.3	442.4	442.4	444.2	445.9	446.8	448.6	448.6
177.5°	439.7	439.7	440.4	441.8	440.4	439.7	440.4	441.1	441.8	442.6	442.6
180°	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7



TEST NUMBER: P332290-940

CATALOG NUMBER: S123RDIP-S560D1025U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8
2.5°	760.1	759.8	760.1	759.0	760.1	759.8	760.1	763.4	763.4	763.7	763.9
5°	707.3	706.9	706.0	702.9	706.0	706.9	707.3	708.4	711.1	715.9	714.5
7.5°	661.2	660.8	657.7	657.8	657.7	660.8	661.2	663.9	667.0	669.9	673.4
10°	633.9	634.3	630.2	627.8	630.2	634.3	633.9	636.3	640.7	643.1	645.5
12.5°	607.4	605.8	602.5	599.9	602.5	605.8	607.4	609.2	615.3	618.0	622.6
15°	572.4	569.0	560.8	561.5	560.8	569.0	572.4	571.1	577.2	580.6	582.0
17.5°	531.2	528.7	528.6	523.8	528.6	528.7	531.2	534.0	539.3	543.0	552.8
20°	507.2	505.5	506.1	501.4	506.1	505.5	507.2	512.6	516.0	520.8	528.7
22.5°	488.3	486.6	483.8	482.2	483.8	486.6	488.3	492.1	495.9	502.6	506.8
25°	460.7	458.0	455.3	457.0	455.3	458.0	460.7	462.8	469.6	472.7	478.8
27.5°	433.1	431.1	428.4	428.0	428.4	431.1	433.1	435.2	438.9	444.1	451.5
30°	415.6	413.6	412.2	410.5	412.2	413.6	415.6	417.3	421.2	426.6	432.0
32.5°	397.9	397.5	395.0	394.7	395.0	397.5	397.9	400.7	404.5	409.7	414.3
35°	374.7	372.6	371.9	372.3	371.9	372.6	374.7	376.0	379.4	384.2	388.7
37.5°	352.6	349.9	348.7	347.4	348.7	349.9	352.6	352.8	356.3	359.5	365.5
40°	336.8	334.0	333.3	332.7	333.3	334.0	336.8	336.4	340.2	342.6	348.0
42.5°	319.0	317.9	317.5	316.3	317.5	317.9	319.0	320.8	323.0	326.5	330.6
45°	294.7	294.4	292.4	293.0	292.4	294.4	294.7	295.8	299.5	301.9	305.7
47.5°	269.2	267.7	266.3	267.2	266.3	267.7	269.2	270.5	273.1	276.1	281.0
50°	251.7	251.0	248.0	248.6	248.0	251.0	251.7	253.1	254.8	258.5	263.0
52.5°	234.3	231.7	230.5	230.1	230.5	231.7	234.3	235.6	237.6	241.9	245.2
55°	205.3	202.2	200.8	200.1	200.8	202.2	205.3	207.7	210.4	215.2	218.6
57.5°	176.8	176.0	175.0	175.7	175.0	176.0	176.8	180.8	183.5	187.3	191.4
60°	160.2	160.2	160.2	159.9	160.2	160.2	160.2	163.6	165.9	169.8	174.2
62.5°	147.3	146.5	146.2	146.7	146.2	146.5	147.3	148.8	151.2	153.6	157.5
65°	127.7	127.4	126.0	125.7	126.0	127.4	127.7	128.8	130.8	132.5	135.3
67.5°	109.2	108.0	107.6	107.1	107.6	108.0	109.2	110.1	111.5	113.7	115.0
70°	95.3	94.6	92.6	92.9	92.6	94.6	95.3	97.0	98.4	101.1	102.5
72.5°	80.3	79.5	79.2	78.6	79.2	79.5	80.3	81.9	83.4	86.3	88.5
75°	63.5	63.2	62.9	64.2	62.9	63.2	63.5	63.8	64.2	65.3	66.3
77.5°	50.9	50.9	51.1	50.6	51.1	50.9	50.9	50.9	50.9	51.5	51.6
80°	42.7	42.7	42.4	42.4	42.4	42.7	42.7	42.7	42.7	42.7	42.4
82.5°	34.2	34.5	34.7	34.2	34.7	34.5	34.2	34.8	35.0	34.5	34.7
85°	22.6	22.2	22.9	22.6	22.9	22.2	22.6	22.6	21.8	22.6	22.2
87.5°	15.1	14.7	14.9	15.0	14.9	14.7	15.1	14.7	14.4	14.2	13.7
90°	24.9	25.8	26.7	25.8	26.7	25.8	24.9	25.8	24.1	23.2	22.3
92.5°	46.3	43.6	44.5	42.9	44.5	43.6	46.3	47.9	52.5	59.5	74.9
95°	121.1	113.1	106.8	103.3	106.8	113.1	121.1	137.9	170.0	217.2	320.4
97.5°	352.8	312.8	288.7	281.1	288.7	312.8	352.8	418.5	525.0	639.8	798.8
100°	656.9	591.9	557.2	558.1	557.2	591.9	656.9	746.8	873.2	977.3	1049.5
102.5°	919.6	868.2	839.2	818.7	839.2	868.2	919.6	989.6	1069.7	1130.4	1132.7
105°	1198.9	1165.1	1136.7	1132.2	1136.7	1165.1	1198.9	1239.9	1263.0	1246.2	1157.1
107.5°	1341.9	1330.5	1320.9	1312.7	1320.9	1330.5	1341.9	1341.2	1309.5	1231.5	1087.0
110°	1383.2	1390.4	1388.6	1386.8	1388.6	1390.4	1383.2	1358.3	1295.9	1183.8	1020.0



TEST NUMBER: P332290-940

CATALOG NUMBER: S123RDIP-S560D1025U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1372.5	1394.5	1401.3	1401.7	1401.3	1394.5	1372.5	1327.0	1246.8	1121.1	953.8
115°	1315.5	1354.7	1372.5	1377.0	1372.5	1354.7	1315.5	1248.8	1151.7	1020.9	866.0
117.5°	1221.7	1266.6	1292.3	1298.2	1292.3	1266.6	1221.7	1152.1	1053.6	936.2	802.5
120°	1156.2	1206.0	1227.4	1232.8	1227.4	1206.0	1156.2	1085.9	996.0	889.2	769.0
122.5°	1096.4	1141.3	1164.8	1171.5	1164.8	1141.3	1096.4	1033.9	950.5	851.5	742.7
125°	1018.2	1057.4	1079.7	1085.9	1079.7	1057.4	1018.2	961.3	890.1	804.7	707.7
127.5°	956.1	989.6	1009.7	1015.4	1009.7	989.6	956.1	905.4	840.6	763.5	677.0
130°	917.7	949.8	968.4	975.5	968.4	949.8	917.7	870.5	809.9	737.9	657.8
132.5°	882.8	914.8	931.4	936.4	931.4	914.8	882.8	838.5	780.8	713.6	640.0
135°	831.3	858.0	874.1	880.3	874.1	858.0	831.3	787.7	737.0	679.1	615.9
137.5°	776.3	803.4	816.9	821.0	816.9	803.4	776.3	739.7	695.7	645.9	594.1
140°	741.5	766.3	780.6	779.7	780.6	766.3	741.5	707.7	669.3	626.6	581.2
142.5°	707.3	729.3	742.2	741.3	742.2	729.3	707.3	678.4	645.2	608.1	569.1
145°	660.4	679.1	686.3	688.0	686.3	679.1	660.4	638.2	612.3	583.9	554.6
147.5°	624.1	636.8	643.5	644.3	643.5	636.8	624.1	607.3	588.9	565.9	542.6
150°	603.5	613.2	618.6	618.6	618.6	613.2	603.5	590.1	573.2	554.6	534.0
152.5°	585.0	594.1	597.3	597.3	597.3	594.1	585.0	574.4	560.4	543.9	526.2
155°	560.8	567.8	569.6	570.5	569.6	567.8	560.8	552.8	542.1	528.7	514.4
157.5°	539.6	544.9	546.4	546.2	546.4	544.9	539.6	532.6	524.2	513.9	502.0
160°	526.0	531.4	531.4	530.5	531.4	531.4	526.0	519.8	513.5	504.7	494.9
162.5°	512.6	517.1	517.1	516.2	517.1	517.1	512.6	508.5	502.9	494.7	486.3
165°	494.9	498.5	497.6	497.6	497.6	498.5	494.9	491.3	486.9	480.6	475.3
167.5°	478.1	480.6	479.7	479.7	479.7	480.6	478.1	476.5	473.3	469.8	465.7
170°	468.1	469.9	469.0	469.0	469.0	469.9	468.1	467.3	465.5	462.0	459.3
172.5°	459.7	461.5	459.9	459.1	459.9	461.5	459.7	459.5	458.4	455.6	453.6
175°	448.6	449.5	448.6	447.7	448.6	449.5	448.6	448.6	448.6	446.8	445.9
177.5°	441.8	442.6	441.1	441.1	441.1	442.6	441.8	442.6	442.6	441.8	441.1
180°	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7



TEST NUMBER: P332290-940

CATALOG NUMBER: S123RDIP-S560D1025U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8
2.5°	761.5	765.4	769.2	772.7	778.2	780.6	784.2	785.5	789.6	795.7	800.6
5°	715.2	720.7	727.8	733.6	742.9	750.0	757.9	765.4	774.3	786.9	798.2
7.5°	675.9	681.3	689.9	700.7	710.9	721.0	731.8	742.0	754.7	772.8	790.8
10°	650.0	656.5	666.7	678.3	690.9	700.9	713.5	726.5	742.2	763.0	784.5
12.5°	627.6	632.4	644.3	655.3	669.6	682.2	694.6	709.8	727.7	749.9	775.8
15°	591.9	598.7	610.4	622.6	637.7	650.9	667.0	685.5	702.9	730.2	761.6
17.5°	556.1	566.5	578.5	592.5	603.6	622.0	639.4	658.3	679.8	708.7	743.2
20°	533.2	541.4	552.6	572.7	587.5	601.5	617.5	641.1	660.8	693.7	729.5
22.5°	513.7	519.8	532.4	549.0	566.1	582.3	598.7	621.2	645.6	676.7	715.6
25°	485.0	494.5	504.1	516.0	534.5	554.0	571.8	590.8	616.8	650.0	692.0
27.5°	456.9	465.6	475.0	489.7	503.7	521.9	540.5	562.4	590.2	625.3	667.9
30°	438.9	445.4	454.2	473.1	485.7	501.4	523.3	542.7	568.6	605.9	650.9
32.5°	420.3	428.7	438.4	452.8	468.4	483.3	503.3	524.4	550.9	587.5	633.7
35°	393.8	403.7	413.6	424.2	439.9	455.3	472.0	495.3	522.2	557.8	603.2
37.5°	369.4	377.4	385.5	398.6	413.5	428.1	443.7	466.6	492.0	530.4	572.0
40°	353.8	361.1	367.1	380.8	395.2	410.9	426.2	446.4	473.7	509.6	549.9
42.5°	336.9	343.5	351.9	363.0	378.5	391.7	407.2	426.1	451.8	488.3	523.6
45°	311.5	319.0	326.2	336.8	352.1	365.1	378.8	396.9	423.2	453.3	484.6
47.5°	285.1	292.6	300.8	311.0	324.4	337.6	351.2	367.3	391.3	420.8	441.9
50°	268.1	274.3	282.5	292.7	305.0	319.0	331.3	348.7	371.6	394.8	413.3
52.5°	250.7	256.2	265.6	276.3	287.8	299.9	313.0	328.0	348.7	370.5	385.1
55°	223.4	230.2	238.1	248.6	259.9	270.2	282.8	298.2	314.6	330.9	340.9
57.5°	197.9	203.6	210.2	221.1	230.9	243.1	254.4	266.4	281.6	293.9	300.4
60°	179.3	184.4	193.0	202.5	211.8	222.3	235.3	247.3	258.9	268.8	273.9
62.5°	161.8	167.7	175.2	184.0	194.0	204.0	215.3	225.4	235.7	244.2	247.7
65°	139.0	143.8	149.3	157.5	165.7	175.9	184.8	195.0	202.5	207.3	210.4
67.5°	118.2	121.4	125.6	131.0	139.1	148.0	156.7	164.6	170.9	174.2	176.9
70°	104.9	106.9	109.9	115.5	121.6	129.5	138.3	144.1	149.6	152.3	155.1
72.5°	91.5	94.1	96.8	101.2	106.3	112.0	118.4	125.6	128.6	131.8	133.5
75°	69.4	73.1	76.9	79.5	83.0	87.5	93.3	97.6	99.4	102.1	102.5
77.5°	52.3	53.1	55.9	59.3	62.2	65.4	69.0	73.0	73.8	75.3	76.2
80°	43.1	43.1	43.1	45.1	48.5	50.9	54.3	56.4	57.7	58.1	58.4
82.5°	34.6	34.6	34.3	34.7	35.9	37.2	40.4	42.7	43.8	43.6	42.8
85°	22.6	21.8	21.8	21.5	21.8	21.1	20.9	22.2	24.3	24.3	23.5
87.5°	13.6	13.5	13.2	12.4	11.6	10.8	9.6	9.5	9.0	9.7	9.1
90°	21.4	22.3	19.6	16.9	14.3	11.6	9.8	8.0	5.4	3.6	1.8
92.5°	103.3	136.9	150.6	113.1	74.7	51.5	38.3	30.8	23.9	16.4	11.1
95°	428.1	527.8	469.9	324.0	191.4	115.7	81.0	57.9	42.7	32.9	30.2
97.5°	875.1	818.0	598.9	355.5	206.0	133.7	96.1	73.3	60.2	52.5	51.6
100°	1018.2	842.9	569.6	335.6	203.8	141.5	106.8	85.4	73.0	66.8	65.9
102.5°	1025.4	796.7	526.9	318.4	206.7	150.8	119.0	99.7	87.9	82.4	80.8
105°	971.1	715.6	474.4	306.2	214.5	166.5	138.8	122.0	111.3	105.9	103.3
107.5°	876.0	644.1	441.0	305.3	229.1	186.9	161.3	145.4	134.9	129.7	127.1
110°	816.2	603.5	428.1	308.9	241.2	201.2	176.2	161.1	151.3	146.9	144.2



TEST NUMBER: P332290-940

CATALOG NUMBER: S123RDIP-S560D1025U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	764.2	576.4	421.0	316.0	253.3	216.2	191.9	176.7	167.0	162.6	159.9
115°	701.4	547.4	418.3	327.5	273.2	239.4	215.4	200.3	191.4	186.0	182.4
117.5°	663.4	530.3	419.9	342.9	294.4	261.0	238.7	221.8	213.7	209.2	205.1
120°	643.5	522.5	422.8	354.3	308.0	275.9	253.7	236.7	227.8	223.4	220.7
122.5°	627.1	517.5	427.8	365.0	322.2	290.9	267.2	251.0	241.4	236.9	234.3
125°	606.2	511.0	435.2	381.8	342.7	311.6	287.5	270.5	260.8	255.5	253.7
127.5°	587.6	507.7	443.8	395.7	360.5	330.4	306.4	287.7	277.7	271.1	268.5
130°	577.7	505.6	449.5	405.0	371.1	341.8	317.7	299.1	288.4	280.4	277.7
132.5°	568.4	504.9	453.8	413.6	380.4	351.8	328.4	309.8	296.9	288.2	284.8
135°	556.3	503.8	460.2	424.5	394.3	366.7	342.7	324.0	310.7	300.9	297.3
137.5°	545.8	501.9	464.4	432.7	403.9	377.4	355.2	336.6	322.4	312.8	309.1
140°	539.4	501.1	467.3	437.0	410.4	384.5	362.3	344.5	330.2	321.3	316.9
142.5°	533.7	499.7	469.4	441.3	415.4	390.2	369.3	351.6	338.8	329.1	325.4
145°	526.0	497.6	470.8	445.9	421.9	398.8	378.3	363.2	349.8	341.8	339.1
147.5°	518.5	494.2	470.8	448.8	427.2	406.1	388.6	374.0	362.5	354.6	353.0
150°	513.5	491.3	470.8	449.5	430.8	410.4	394.3	381.8	370.2	363.2	362.3
152.5°	507.9	487.8	468.7	450.9	432.9	415.4	400.0	389.0	378.8	371.7	371.5
155°	499.4	481.5	466.4	451.3	437.0	421.9	409.5	399.7	390.7	385.4	385.4
157.5°	489.7	476.0	463.4	452.2	439.3	427.2	417.6	409.3	401.4	397.2	396.5
160°	483.3	471.7	462.0	452.2	441.5	430.8	421.9	415.6	408.6	405.0	405.0
162.5°	476.9	467.4	459.1	451.5	442.2	432.9	425.4	419.9	414.3	411.4	411.4
165°	468.1	461.1	454.9	449.5	443.3	436.1	429.9	426.3	421.9	420.1	421.0
167.5°	459.9	454.7	450.6	448.1	443.1	437.9	434.0	431.5	428.1	427.2	428.3
170°	454.9	450.4	447.7	445.9	442.4	437.9	436.1	434.4	431.7	430.8	432.6
172.5°	449.9	446.8	445.6	445.2	442.4	438.6	437.6	436.5	434.5	434.4	435.4
175°	444.2	442.4	442.4	443.3	441.5	439.7	438.8	438.8	437.0	437.9	438.8
177.5°	440.4	439.7	440.4	441.8	440.4	439.7	439.7	439.7	439.0	439.7	440.4
180°	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7



TEST NUMBER: P332290-940

CATALOG NUMBER: S123RDIP-S560D1025U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8
2.5°	802.2	805.2	809.0	814.8	819.1	823.0	823.8	824.9	827.6	832.2	835.8
5°	807.4	815.3	827.9	840.2	853.5	864.4	874.7	881.9	888.7	903.0	914.6
7.5°	805.7	823.2	843.0	865.1	887.4	909.1	929.2	947.2	965.1	986.0	1009.8
10°	804.7	825.2	851.8	880.1	911.2	941.6	971.0	993.9	1020.6	1044.5	1074.9
12.5°	799.5	829.0	860.9	897.1	935.3	970.4	1009.0	1040.6	1071.0	1105.6	1140.9
15°	792.7	828.6	868.9	917.0	975.1	1017.4	1057.0	1112.1	1149.6	1187.2	1237.8
17.5°	780.3	824.1	874.5	937.0	985.5	1042.4	1102.0	1145.5	1196.1	1249.0	1294.8
20°	770.5	821.4	877.8	939.2	1001.0	1062.9	1120.6	1172.5	1224.8	1285.9	1323.5
22.5°	760.7	811.0	869.6	934.9	1001.3	1066.4	1131.8	1192.8	1251.5	1313.2	1361.2
25°	739.8	799.5	863.1	929.7	995.2	1066.9	1144.9	1212.8	1285.6	1349.1	1394.5
27.5°	718.6	773.4	836.6	904.2	977.0	1061.8	1153.4	1230.7	1303.6	1349.1	1363.3
30°	699.5	757.5	815.6	884.2	963.1	1057.7	1155.1	1243.6	1303.3	1323.1	1308.4
32.5°	680.1	732.7	790.2	860.5	944.3	1047.7	1157.3	1235.9	1271.9	1256.8	1196.9
35°	645.9	693.3	749.0	819.4	915.7	1042.1	1148.3	1201.6	1192.7	1107.2	994.5
37.5°	609.2	647.9	699.5	773.0	886.0	1019.8	1109.5	1117.3	1040.4	909.4	779.2
40°	580.2	615.1	668.1	744.9	863.1	998.0	1070.4	1038.7	919.4	773.6	664.9
42.5°	552.1	581.5	632.5	715.4	841.2	968.2	1012.2	943.0	805.5	667.5	568.8
45°	504.4	532.1	583.4	668.4	796.5	911.2	905.4	785.2	647.6	536.5	454.6
47.5°	459.2	483.4	531.5	618.3	744.0	825.8	771.5	643.6	526.8	437.8	379.3
50°	427.3	451.2	499.0	584.7	701.9	761.6	684.1	560.8	453.9	380.1	333.7
52.5°	396.6	420.0	463.8	547.2	651.0	686.8	603.5	489.2	400.1	336.4	296.5
55°	353.8	371.6	410.9	490.8	568.3	576.5	492.1	396.5	323.1	278.7	251.4
57.5°	310.2	325.5	364.3	427.9	482.3	478.0	398.1	315.4	265.9	232.9	213.1
60°	281.8	296.8	330.9	385.6	426.6	412.2	338.9	272.2	229.9	205.6	189.9
62.5°	255.3	267.0	299.0	338.9	368.4	352.1	289.6	234.5	200.9	180.5	168.0
65°	216.9	226.4	252.1	272.9	289.3	273.6	221.7	183.4	159.2	144.8	136.3
67.5°	180.4	186.5	202.7	210.2	221.8	204.6	166.7	141.1	127.2	115.2	109.2
70°	157.5	161.9	170.4	176.6	179.7	161.9	133.8	115.1	103.5	95.0	91.2
72.5°	134.5	138.4	140.1	145.2	143.6	126.9	107.6	92.7	84.4	78.6	73.7
75°	102.8	104.5	102.8	100.8	96.3	84.7	71.4	63.8	57.7	55.0	53.3
77.5°	74.9	74.4	72.1	68.8	61.3	53.9	46.8	44.2	41.6	40.1	39.6
80°	57.7	56.4	54.3	49.2	42.7	37.5	35.8	34.2	33.2	31.4	31.1
82.5°	43.0	42.2	38.7	34.4	29.9	27.5	26.0	25.4	24.3	23.5	23.5
85°	22.9	21.8	18.1	15.7	15.1	14.4	14.0	14.0	12.7	12.3	12.3
87.5°	8.1	6.8	7.0	6.6	7.0	7.0	7.8	7.8	8.0	8.1	7.8
90°	3.6	5.4	8.0	9.8	11.6	14.3	16.9	19.6	22.3	21.4	22.3
92.5°	16.4	23.9	30.8	38.3	51.5	74.7	113.1	150.6	136.9	103.3	74.9
95°	32.9	42.7	57.9	81.0	115.7	191.4	324.0	469.9	527.8	428.1	320.4
97.5°	52.5	60.2	73.3	96.1	133.7	206.0	355.5	598.9	818.0	875.1	798.8
100°	66.8	73.0	85.4	106.8	141.5	203.8	335.6	569.6	842.9	1018.2	1049.5
102.5°	82.4	87.9	99.7	119.0	150.8	206.7	318.4	526.9	796.7	1025.4	1132.7
105°	105.9	111.3	122.0	138.8	166.5	214.5	306.2	474.4	715.6	971.1	1157.1
107.5°	129.7	134.9	145.4	161.3	186.9	229.1	305.3	441.0	644.1	876.0	1087.0
110°	146.9	151.3	161.1	176.2	201.2	241.2	308.9	428.1	603.5	816.2	1020.0



TEST NUMBER: P332290-940

CATALOG NUMBER: S123RDIP-S560D1025U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	162.6	167.0	176.7	191.9	216.2	253.3	316.0	421.0	576.4	764.2	953.8
115°	186.0	191.4	200.3	215.4	239.4	273.2	327.5	418.3	547.4	701.4	866.0
117.5°	209.2	213.7	221.8	238.7	261.0	294.4	342.9	419.9	530.3	663.4	802.5
120°	223.4	227.8	236.7	253.7	275.9	308.0	354.3	422.8	522.5	643.5	769.0
122.5°	236.9	241.4	251.0	267.2	290.9	322.2	365.0	427.8	517.5	627.1	742.7
125°	255.5	260.8	270.5	287.5	311.6	342.7	381.8	435.2	511.0	606.2	707.7
127.5°	271.1	277.7	287.7	306.4	330.4	360.5	395.7	443.8	507.7	587.6	677.0
130°	280.4	288.4	299.1	317.7	341.8	371.1	405.0	449.5	505.6	577.7	657.8
132.5°	288.2	296.9	309.8	328.4	351.8	380.4	413.6	453.8	504.9	568.4	640.0
135°	300.9	310.7	324.0	342.7	366.7	394.3	424.5	460.2	503.8	556.3	615.9
137.5°	312.8	322.4	336.6	355.2	377.4	403.9	432.7	464.4	501.9	545.8	594.1
140°	321.3	330.2	344.5	362.3	384.5	410.4	437.0	467.3	501.1	539.4	581.2
142.5°	329.1	338.8	351.6	369.3	390.2	415.4	441.3	469.4	499.7	533.7	569.1
145°	341.8	349.8	363.2	378.3	398.8	421.9	445.9	470.8	497.6	526.0	554.6
147.5°	354.6	362.5	374.0	388.6	406.1	427.2	448.8	470.8	494.2	518.5	542.6
150°	363.2	370.2	381.8	394.3	410.4	430.8	449.5	470.8	491.3	513.5	534.0
152.5°	371.7	378.8	389.0	400.0	415.4	432.9	450.9	468.7	487.8	507.9	526.2
155°	385.4	390.7	399.7	409.5	421.9	437.0	451.3	466.4	481.5	499.4	514.4
157.5°	397.2	401.4	409.3	417.6	427.2	439.3	452.2	463.4	476.0	489.7	502.0
160°	405.0	408.6	415.6	421.9	430.8	441.5	452.2	462.0	471.7	483.3	494.9
162.5°	411.4	414.3	419.9	425.4	432.9	442.2	451.5	459.1	467.4	476.9	486.3
165°	420.1	421.9	426.3	429.9	436.1	443.3	449.5	454.9	461.1	468.1	475.3
167.5°	427.2	428.1	431.5	434.0	437.9	443.1	448.1	450.6	454.7	459.9	465.7
170°	430.8	431.7	434.4	436.1	437.9	442.4	445.9	447.7	450.4	454.9	459.3
172.5°	434.4	434.5	436.5	437.6	438.6	442.4	445.2	445.6	446.8	449.9	453.6
175°	437.9	437.0	438.8	438.8	439.7	441.5	443.3	442.4	442.4	444.2	445.9
177.5°	439.7	439.0	439.7	439.7	439.7	440.4	441.8	440.4	439.7	440.4	441.1
180°	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7



TEST NUMBER: P332290-940

CATALOG NUMBER: S123RDIP-S560D1025U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	797.8	797.8	797.8	797.8	797.8	797.8	797.8
2.5°	841.6	841.6	842.7	846.8	847.3	850.9	849.7
5°	924.9	931.4	933.8	944.1	950.2	952.9	947.4
7.5°	1026.8	1045.1	1053.8	1064.5	1074.0	1076.9	1069.4
10°	1101.2	1120.3	1136.3	1146.2	1155.5	1161.5	1169.5
12.5°	1173.0	1196.5	1211.7	1225.7	1235.2	1243.0	1244.3
15°	1251.1	1286.6	1313.6	1333.4	1343.3	1348.4	1346.4
17.5°	1329.8	1362.7	1382.0	1402.1	1415.9	1416.6	1417.0
20°	1374.4	1406.5	1428.7	1443.7	1459.1	1458.4	1461.8
22.5°	1404.2	1429.4	1446.4	1457.3	1462.6	1460.0	1460.7
25°	1418.1	1425.6	1422.5	1405.1	1400.7	1384.6	1387.3
27.5°	1346.2	1310.7	1274.0	1226.6	1189.4	1159.6	1161.1
30°	1248.7	1185.8	1114.1	1054.0	1000.1	985.0	952.9
32.5°	1112.3	1018.1	934.1	878.1	831.7	819.1	791.1
35°	881.2	789.6	703.2	651.3	630.8	602.2	601.8
37.5°	684.9	604.3	558.7	519.7	499.3	481.9	480.2
40°	576.2	513.4	478.8	450.8	430.7	417.7	414.6
42.5°	500.2	449.4	417.1	399.8	384.2	377.6	372.6
45°	408.5	374.3	351.8	336.1	328.9	323.8	321.0
47.5°	341.7	318.8	303.4	293.0	287.1	281.8	283.2
50°	305.3	286.6	275.3	265.4	260.9	257.2	257.5
52.5°	276.1	259.2	250.1	243.0	237.5	234.8	233.4
55°	234.3	223.7	214.5	209.4	206.3	202.5	201.5
57.5°	199.8	191.6	184.1	178.3	177.6	174.0	174.4
60°	176.9	170.0	163.9	160.9	158.5	155.4	156.4
62.5°	158.1	152.3	146.7	144.2	141.8	139.6	140.0
65°	129.5	123.9	120.6	119.2	118.2	117.2	116.1
67.5°	103.2	99.8	97.6	94.7	92.6	92.3	91.2
70°	86.8	82.3	78.6	74.8	73.7	73.4	73.7
72.5°	69.6	66.7	65.7	63.8	63.7	62.8	63.4
75°	52.3	51.3	50.6	49.2	49.2	49.2	49.2
77.5°	38.5	37.9	37.5	37.2	36.9	36.4	36.4
80°	30.1	29.7	29.1	29.1	28.7	29.1	28.7
82.5°	22.6	22.6	21.9	21.9	21.6	21.4	21.6
85°	11.6	11.2	11.9	11.2	11.6	11.0	11.6
87.5°	7.9	8.1	8.2	8.0	7.9	8.6	7.9
90°	23.2	24.1	25.8	24.9	25.8	26.7	25.8
92.5°	59.5	52.5	47.9	46.3	43.6	44.5	42.9
95°	217.2	170.0	137.9	121.1	113.1	106.8	103.3
97.5°	639.8	525.0	418.5	352.8	312.8	288.7	281.1
100°	977.3	873.2	746.8	656.9	591.9	557.2	558.1
102.5°	1130.4	1069.7	989.6	919.6	868.2	839.2	818.7
105°	1246.2	1263.0	1239.9	1198.9	1165.1	1136.7	1132.2
107.5°	1231.5	1309.5	1341.2	1341.9	1330.5	1320.9	1312.7
110°	1183.8	1295.9	1358.3	1383.2	1390.4	1388.6	1386.8



TEST NUMBER: P332290-940

CATALOG NUMBER: S123RDIP-S560D1025U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1121.1	1246.8	1327.0	1372.5	1394.5	1401.3	1401.7
115°	1020.9	1151.7	1248.8	1315.5	1354.7	1372.5	1377.0
117.5°	936.2	1053.6	1152.1	1221.7	1266.6	1292.3	1298.2
120°	889.2	996.0	1085.9	1156.2	1206.0	1227.4	1232.8
122.5°	851.5	950.5	1033.9	1096.4	1141.3	1164.8	1171.5
125°	804.7	890.1	961.3	1018.2	1057.4	1079.7	1085.9
127.5°	763.5	840.6	905.4	956.1	989.6	1009.7	1015.4
130°	737.9	809.9	870.5	917.7	949.8	968.4	975.5
132.5°	713.6	780.8	838.5	882.8	914.8	931.4	936.4
135°	679.1	737.0	787.7	831.3	858.0	874.1	880.3
137.5°	645.9	695.7	739.7	776.3	803.4	816.9	821.0
140°	626.6	669.3	707.7	741.5	766.3	780.6	779.7
142.5°	608.1	645.2	678.4	707.3	729.3	742.2	741.3
145°	583.9	612.3	638.2	660.4	679.1	686.3	688.0
147.5°	565.9	588.9	607.3	624.1	636.8	643.5	644.3
150°	554.6	573.2	590.1	603.5	613.2	618.6	618.6
152.5°	543.9	560.4	574.4	585.0	594.1	597.3	597.3
155°	528.7	542.1	552.8	560.8	567.8	569.6	570.5
157.5°	513.9	524.2	532.6	539.6	544.9	546.4	546.2
160°	504.7	513.5	519.8	526.0	531.4	531.4	530.5
162.5°	494.7	502.9	508.5	512.6	517.1	517.1	516.2
165°	480.6	486.9	491.3	494.9	498.5	497.6	497.6
167.5°	469.8	473.3	476.5	478.1	480.6	479.7	479.7
170°	462.0	465.5	467.3	468.1	469.9	469.0	469.0
172.5°	455.6	458.4	459.5	459.7	461.5	459.9	459.1
175°	446.8	448.6	448.6	448.6	449.5	448.6	447.7
177.5°	441.8	442.6	442.6	441.8	442.6	441.1	441.1
180°	439.7	439.7	439.7	439.7	439.7	439.7	439.7

(END OF REPORT)