

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332284-940

Luminaire Tested: **S123RDIP-S560D805U940-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332284-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S560D805U940-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 805 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4580.2 lumens
Efficiency: N/A
Efficacy: 119.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332284-940

CATALOG NUMBER: S123RDIP-S560D805U940-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332284-940

CATALOG NUMBER: S123RDIP-S560D805U940-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	43
1	97	93	89	86	88	85	82	79	71	68	66	57	56	54	45	44	43	38
2	89	82	76	71	81	75	70	66	62	59	56	51	48	46	40	39	37	32
3	81	72	65	60	74	66	60	55	55	51	47	45	42	40	36	34	32	28
4	74	64	57	51	68	59	52	47	50	45	41	41	37	34	33	30	28	24
5	68	57	50	44	62	53	46	41	45	39	35	37	33	30	30	27	25	21
6	63	52	44	38	58	48	41	36	40	35	31	33	30	27	27	24	22	19
7	58	47	39	34	53	43	36	32	37	31	28	30	27	24	25	22	20	17
8	54	42	35	30	50	39	33	28	33	28	25	28	24	21	23	20	18	15
9	51	39	31	27	46	36	29	25	31	26	22	26	22	19	21	18	16	14
10	47	36	29	24	43	33	27	23	28	23	20	24	20	17	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8587	8587	8587	8587
5°	10237	8625	7595	8625
10°	12783	8575	6862	8575
15°	15004	8487	6257	8487
20°	16745	8356	5743	8356
25°	16476	8219	5428	8219
30°	11844	8090	5102	8090
35°	7908	7926	4892	7926
40°	5826	7727	4675	7727
45°	4886	7377	4460	7377
50°	4312	6921	4163	6921
55°	3781	6397	3755	6397
60°	3367	5896	3442	5896
65°	2957	5359	3202	5359
70°	2319	4881	2924	4881
75°	2046	4263	2670	4263
80°	1779	3620	2628	3620
85°	1433	2902	2791	2902



TEST NUMBER: P332284-940

CATALOG NUMBER: S123RDIP-S560D805U940-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.5	1.7
10°-20°	245.1	5.4
20°-30°	385.1	8.4
30°-40°	401.8	8.8
40°-50°	343.8	7.5
50°-60°	262.1	5.7
60°-70°	168.0	3.7
70°-80°	80.8	1.8
80°-90°	24.0	0.5
90°-100°	191.7	4.2
100°-110°	542.7	11.8
110°-120°	533.9	11.7
120°-130°	425.8	9.3
130°-140°	335.7	7.3
140°-150°	250.6	5.5
150°-160°	174.7	3.8
160°-170°	102.6	2.2
170°-180°	33.4	0.7
0°-30°	708.7	15.5
0°-40°	1110.4	24.2
0°-60°	1716.3	37.5
0°-90°	1989.2	43.4
90°-120°	1268.2	27.7
90°-150°	2280.4	49.8
90°-180°	2591.0	56.6
0°-180°	4580.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	798	798	798	798	798	
5°	947	798	703	798	947	98
15°	1346	762	562	762	1346	382
25°	1387	692	457	692	1387	596
35°	602	603	372	603	602	395
45°	321	485	293	485	321	252
55°	202	341	200	341	202	182
65°	116	210	126	210	116	114
75°	49	102	64	102	49	53
85°	12	24	23	24	12	14
90°	20	1	20	1	20	11
95°	81	24	81	24	81	146
105°	887	81	887	81	887	875
115°	1078	143	1078	143	1078	1048
125°	850	199	850	199	850	771
135°	690	233	690	233	690	535
145°	539	266	539	266	539	343
155°	447	302	447	302	447	208
165°	390	330	390	330	390	111
175°	351	344	351	344	351	34
180°	344	344	344	344	344	



TEST NUMBER: P332284-940

CATALOG NUMBER: S123RDIP-S560D805U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8
2.5°	849.7	850.9	847.3	846.8	842.7	841.6	841.6	835.8	832.2	827.6	824.9
5°	947.4	952.9	950.2	944.1	933.8	931.4	924.9	914.6	903.0	888.7	881.9
7.5°	1069.4	1076.9	1074.0	1064.5	1053.8	1045.1	1026.8	1009.8	986.0	965.1	947.2
10°	1169.5	1161.5	1155.5	1146.2	1136.3	1120.3	1101.2	1074.9	1044.5	1020.6	993.9
12.5°	1244.3	1243.0	1235.2	1225.7	1211.7	1196.5	1173.0	1140.9	1105.6	1071.0	1040.6
15°	1346.4	1348.4	1343.3	1333.4	1313.6	1286.6	1251.1	1237.8	1187.2	1149.6	1112.1
17.5°	1417.0	1416.6	1415.9	1402.1	1382.0	1362.7	1329.8	1294.8	1249.0	1196.1	1145.5
20°	1461.8	1458.4	1459.1	1443.7	1428.7	1406.5	1374.4	1323.5	1285.9	1224.8	1172.5
22.5°	1460.7	1460.0	1462.6	1457.3	1446.4	1429.4	1404.2	1361.2	1313.2	1251.5	1192.8
25°	1387.3	1384.6	1400.7	1405.1	1422.5	1425.6	1418.1	1394.5	1349.1	1285.6	1212.8
27.5°	1161.1	1159.6	1189.4	1226.6	1274.0	1310.7	1346.2	1363.3	1349.1	1303.6	1230.7
30°	952.9	985.0	1000.1	1054.0	1114.1	1185.8	1248.7	1308.4	1323.1	1303.3	1243.6
32.5°	791.1	819.1	831.7	878.1	934.1	1018.1	1112.3	1196.9	1256.8	1271.9	1235.9
35°	601.8	602.2	630.8	651.3	703.2	789.6	881.2	994.5	1107.2	1192.7	1201.6
37.5°	480.2	481.9	499.3	519.7	558.7	604.3	684.9	779.2	909.4	1040.4	1117.3
40°	414.6	417.7	430.7	450.8	478.8	513.4	576.2	664.9	773.6	919.4	1038.7
42.5°	372.6	377.6	384.2	399.8	417.1	449.4	500.2	568.8	667.5	805.5	943.0
45°	321.0	323.8	328.9	336.1	351.8	374.3	408.5	454.6	536.5	647.6	785.2
47.5°	283.2	281.8	287.1	293.0	303.4	318.8	341.7	379.3	437.8	526.8	643.6
50°	257.5	257.2	260.9	265.4	275.3	286.6	305.3	333.7	380.1	453.9	560.8
52.5°	233.4	234.8	237.5	243.0	250.1	259.2	276.1	296.5	336.4	400.1	489.2
55°	201.5	202.5	206.3	209.4	214.5	223.7	234.3	251.4	278.7	323.1	396.5
57.5°	174.4	174.0	177.6	178.3	184.1	191.6	199.8	213.1	232.9	265.9	315.4
60°	156.4	155.4	158.5	160.9	163.9	170.0	176.9	189.9	205.6	229.9	272.2
62.5°	140.0	139.6	141.8	144.2	146.7	152.3	158.1	168.0	180.5	200.9	234.5
65°	116.1	117.2	118.2	119.2	120.6	123.9	129.5	136.3	144.8	159.2	183.4
67.5°	91.2	92.3	92.6	94.7	97.6	99.8	103.2	109.2	115.2	127.2	141.1
70°	73.7	73.4	73.7	74.8	78.6	82.3	86.8	91.2	95.0	103.5	115.1
72.5°	63.4	62.8	63.7	63.8	65.7	66.7	69.6	73.7	78.6	84.4	92.7
75°	49.2	49.2	49.2	49.2	50.6	51.3	52.3	53.3	55.0	57.7	63.8
77.5°	36.4	36.4	36.9	37.2	37.5	37.9	38.5	39.6	40.1	41.6	44.2
80°	28.7	29.1	28.7	29.1	29.1	29.7	30.1	31.1	31.4	33.2	34.2
82.5°	21.6	21.4	21.6	21.9	21.9	22.6	22.6	23.5	23.5	24.3	25.4
85°	11.6	11.0	11.6	11.2	11.9	11.2	11.6	12.3	12.3	12.7	14.0
87.5°	6.8	7.5	6.8	6.9	7.0	7.0	6.9	6.8	7.1	7.0	6.9
90°	20.2	21.0	20.2	19.5	20.2	18.8	18.1	17.4	16.8	17.4	15.3
92.5°	33.6	34.9	34.2	36.3	37.5	41.1	46.5	58.7	80.9	107.2	118.0
95°	80.9	83.6	88.5	94.8	108.1	133.1	170.1	251.0	335.4	413.4	368.1
97.5°	220.2	226.1	245.0	276.3	327.8	411.2	501.1	625.6	685.5	640.7	469.0
100°	437.1	436.4	463.6	514.5	584.9	683.9	765.4	822.0	797.5	660.2	446.2
102.5°	641.2	657.3	680.0	720.3	775.1	837.9	885.4	887.2	803.2	623.9	412.7
105°	886.8	890.3	912.6	939.1	971.2	989.3	976.0	906.3	760.6	560.5	371.6
107.5°	1028.1	1034.6	1042.1	1051.1	1050.4	1025.6	964.6	851.4	686.2	504.4	345.4
110°	1086.2	1087.5	1089.0	1083.3	1063.9	1015.0	927.2	799.0	639.3	472.7	335.4



TEST NUMBER: P332284-940

CATALOG NUMBER: S123RDIP-S560D805U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1097.9	1097.6	1092.3	1075.0	1039.3	976.6	878.2	747.1	598.6	451.5	329.8
115°	1078.5	1075.0	1061.0	1030.4	978.1	902.1	799.6	678.3	549.4	428.7	327.7
117.5°	1016.9	1012.1	992.0	956.9	902.4	825.3	733.3	628.6	519.7	415.4	329.0
120°	965.5	961.4	944.7	905.6	850.5	780.2	696.4	602.4	504.1	409.2	331.2
122.5°	917.6	912.3	893.9	858.7	809.9	744.4	666.9	581.8	491.2	405.4	335.0
125°	850.5	845.6	828.2	797.5	753.0	697.1	630.3	554.2	474.7	400.2	340.9
127.5°	795.3	790.9	775.1	748.9	709.2	658.4	598.0	530.3	460.3	397.7	347.6
130°	764.1	758.5	743.9	718.8	681.8	634.5	577.9	515.2	452.5	396.0	352.0
132.5°	733.4	729.5	716.6	691.4	656.7	611.5	559.0	501.2	445.2	395.4	355.4
135°	689.5	684.6	672.1	651.1	617.0	577.2	531.9	482.4	435.7	394.6	360.4
137.5°	643.1	639.9	629.3	608.1	579.3	544.9	505.9	465.3	427.5	393.1	363.8
140°	610.7	611.4	600.2	580.8	554.2	524.2	490.8	455.2	422.5	392.5	366.0
142.5°	580.6	581.3	571.2	553.9	531.4	505.3	476.3	445.8	418.0	391.4	367.7
145°	538.9	537.5	531.9	517.3	499.9	479.7	457.4	434.4	412.1	389.7	368.8
147.5°	504.6	504.1	498.7	488.8	475.6	461.3	443.3	425.0	406.2	387.1	368.8
150°	484.6	484.6	480.4	472.7	462.2	449.0	434.4	418.3	402.3	384.9	368.8
152.5°	467.8	467.8	465.3	458.2	450.0	438.9	426.0	412.1	397.8	382.0	367.1
155°	446.8	446.2	444.8	439.2	432.9	424.5	414.1	403.0	391.1	377.2	365.3
157.5°	427.8	427.9	426.8	422.6	417.1	410.6	402.5	393.2	383.6	372.8	362.9
160°	415.5	416.2	416.2	412.1	407.2	402.3	395.3	387.6	378.5	369.5	361.9
162.5°	404.4	405.0	405.0	401.4	398.2	393.9	387.4	380.9	373.5	366.1	359.6
165°	389.7	389.7	390.4	387.6	384.9	381.4	376.5	372.3	366.7	361.1	356.2
167.5°	375.8	375.8	376.5	374.5	373.3	370.8	367.9	364.7	360.2	356.1	352.9
170°	367.4	367.4	368.1	366.7	366.0	364.6	361.9	359.7	356.2	352.8	350.7
172.5°	359.6	360.2	361.4	360.0	359.9	359.0	356.8	355.3	352.3	350.0	349.0
175°	350.7	351.3	352.0	351.3	351.3	351.3	350.0	349.3	347.9	346.5	346.5
177.5°	345.5	345.5	346.6	346.1	346.6	346.6	346.1	345.5	344.9	344.4	344.9
180°	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4



TEST NUMBER: P332284-940

CATALOG NUMBER: S123RDIP-S560D805U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8
2.5°	823.8	823.0	819.1	814.8	809.0	805.2	802.2	800.6	795.7	789.6	785.5
5°	874.7	864.4	853.5	840.2	827.9	815.3	807.4	798.2	786.9	774.3	765.4
7.5°	929.2	909.1	887.4	865.1	843.0	823.2	805.7	790.8	772.8	754.7	742.0
10°	971.0	941.6	911.2	880.1	851.8	825.2	804.7	784.5	763.0	742.2	726.5
12.5°	1009.0	970.4	935.3	897.1	860.9	829.0	799.5	775.8	749.9	727.7	709.8
15°	1057.0	1017.4	975.1	917.0	868.9	828.6	792.7	761.6	730.2	702.9	685.5
17.5°	1102.0	1042.4	985.5	937.0	874.5	824.1	780.3	743.2	708.7	679.8	658.3
20°	1120.6	1062.9	1001.0	939.2	877.8	821.4	770.5	729.5	693.7	660.8	641.1
22.5°	1131.8	1066.4	1001.3	934.9	869.6	811.0	760.7	715.6	676.7	645.6	621.2
25°	1144.9	1066.9	995.2	929.7	863.1	799.5	739.8	692.0	650.0	616.8	590.8
27.5°	1153.4	1061.8	977.0	904.2	836.6	773.4	718.6	667.9	625.3	590.2	562.4
30°	1155.1	1057.7	963.1	884.2	815.6	757.5	699.5	650.9	605.9	568.6	542.7
32.5°	1157.3	1047.7	944.3	860.5	790.2	732.7	680.1	633.7	587.5	550.9	524.4
35°	1148.3	1042.1	915.7	819.4	749.0	693.3	645.9	603.2	557.8	522.2	495.3
37.5°	1109.5	1019.8	886.0	773.0	699.5	647.9	609.2	572.0	530.4	492.0	466.6
40°	1070.4	998.0	863.1	744.9	668.1	615.1	580.2	549.9	509.6	473.7	446.4
42.5°	1012.2	968.2	841.2	715.4	632.5	581.5	552.1	523.6	488.3	451.8	426.1
45°	905.4	911.2	796.5	668.4	583.4	532.1	504.4	484.6	453.3	423.2	396.9
47.5°	771.5	825.8	744.0	618.3	531.5	483.4	459.2	441.9	420.8	391.3	367.3
50°	684.1	761.6	701.9	584.7	499.0	451.2	427.3	413.3	394.8	371.6	348.7
52.5°	603.5	686.8	651.0	547.2	463.8	420.0	396.6	385.1	370.5	348.7	328.0
55°	492.1	576.5	568.3	490.8	410.9	371.6	353.8	340.9	330.9	314.6	298.2
57.5°	398.1	478.0	482.3	427.9	364.3	325.5	310.2	300.4	293.9	281.6	266.4
60°	338.9	412.2	426.6	385.6	330.9	296.8	281.8	273.9	268.8	258.9	247.3
62.5°	289.6	352.1	368.4	338.9	299.0	267.0	255.3	247.7	244.2	235.7	225.4
65°	221.7	273.6	289.3	272.9	252.1	226.4	216.9	210.4	207.3	202.5	195.0
67.5°	166.7	204.6	221.8	210.2	202.7	186.5	180.4	176.9	174.2	170.9	164.6
70°	133.8	161.9	179.7	176.6	170.4	161.9	157.5	155.1	152.3	149.6	144.1
72.5°	107.6	126.9	143.6	145.2	140.1	138.4	134.5	133.5	131.8	128.6	125.6
75°	71.4	84.7	96.3	100.8	102.8	104.5	102.8	102.5	102.1	99.4	97.6
77.5°	46.8	53.9	61.3	68.8	72.1	74.4	74.9	76.2	75.3	73.8	73.0
80°	35.8	37.5	42.7	49.2	54.3	56.4	57.7	58.4	58.1	57.7	56.4
82.5°	26.0	27.5	29.9	34.4	38.7	42.2	43.0	42.8	43.6	43.8	42.7
85°	14.0	14.4	15.1	15.7	18.1	21.8	22.9	23.5	24.3	24.3	22.2
87.5°	7.0	6.3	6.4	6.2	6.7	6.6	7.9	9.0	9.5	8.7	9.2
90°	13.3	11.1	9.1	7.7	6.2	4.2	2.8	1.4	2.8	4.2	6.2
92.5°	88.5	58.6	40.3	30.0	24.2	18.7	12.8	8.6	12.8	18.7	24.2
95°	253.8	149.9	90.6	63.4	45.3	33.4	25.8	23.7	25.8	33.4	45.3
97.5°	278.5	161.3	104.7	75.3	57.4	47.2	41.1	40.4	41.1	47.2	57.4
100°	262.8	159.6	110.8	83.6	67.0	57.2	52.3	51.6	52.3	57.2	67.0
102.5°	249.4	161.8	118.1	93.2	78.1	68.8	64.6	63.3	64.6	68.8	78.1
105°	239.8	168.0	130.4	108.8	95.5	87.1	82.9	80.9	82.9	87.1	95.5
107.5°	239.2	179.4	146.4	126.4	113.9	105.7	101.7	99.5	101.7	105.7	113.9
110°	241.9	189.0	157.6	138.0	126.2	118.5	115.0	113.0	115.0	118.5	126.2



TEST NUMBER: P332284-940

CATALOG NUMBER: S123RDIP-S560D805U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	247.4	198.4	169.2	150.3	138.5	130.8	127.3	125.2	127.3	130.8	138.5
115°	256.5	214.0	187.5	168.7	156.9	149.9	145.7	142.9	145.7	149.9	156.9
117.5°	268.6	230.6	204.4	187.0	173.7	167.3	163.8	160.6	163.8	167.3	173.7
120°	277.5	241.2	216.2	198.7	185.5	178.4	175.0	172.9	175.0	178.4	185.5
122.5°	285.8	252.4	227.8	209.3	196.6	189.0	185.6	183.5	185.6	189.0	196.6
125°	299.1	268.4	244.0	225.2	212.0	204.3	200.1	198.7	200.1	204.3	212.0
127.5°	310.0	282.3	258.8	240.0	225.3	217.5	212.3	210.3	212.3	217.5	225.3
130°	317.2	290.7	267.7	248.9	234.3	225.9	219.6	217.5	219.6	225.9	234.3
132.5°	323.9	297.9	275.5	257.3	242.6	232.6	225.8	223.1	225.8	232.6	242.6
135°	332.5	308.8	287.2	268.4	253.8	243.3	235.7	232.8	235.7	243.3	253.8
137.5°	338.9	316.4	295.6	278.1	263.7	252.5	245.0	242.0	245.0	252.5	263.7
140°	342.3	321.4	301.1	283.7	269.8	258.7	251.6	248.2	251.6	258.7	269.8
142.5°	345.6	325.3	305.6	289.4	275.4	265.4	257.8	254.9	257.8	265.4	275.4
145°	349.3	330.5	312.4	296.3	284.5	274.0	267.7	265.6	267.7	274.0	284.5
147.5°	351.5	334.7	318.1	304.3	292.9	283.9	277.8	276.5	277.8	283.9	292.9
150°	352.0	337.4	321.4	308.8	299.1	290.0	284.5	283.7	284.5	290.0	299.1
152.5°	353.2	339.1	325.3	313.3	304.7	296.7	291.1	291.0	291.1	296.7	304.7
155°	353.5	342.3	330.5	320.7	313.0	306.0	301.8	301.8	301.8	306.0	313.0
157.5°	354.2	344.1	334.7	327.1	320.6	314.4	311.0	310.5	311.0	314.4	320.6
160°	354.2	345.8	337.4	330.5	325.6	320.0	317.2	317.2	317.2	320.0	325.6
162.5°	353.6	346.3	339.1	333.2	329.0	324.5	322.3	322.3	322.3	324.5	329.0
165°	352.0	347.1	341.6	336.7	333.9	330.5	329.0	329.8	329.0	330.5	333.9
167.5°	351.0	347.1	343.0	339.9	338.0	335.4	334.7	335.5	334.7	335.4	338.0
170°	349.3	346.5	343.0	341.6	340.2	338.1	337.4	338.9	337.4	338.1	340.2
172.5°	348.7	346.5	343.6	342.7	341.9	340.4	340.2	341.1	340.2	340.4	341.9
175°	347.1	345.8	344.4	343.7	343.7	342.3	343.0	343.7	343.0	342.3	343.7
177.5°	346.1	344.9	344.4	344.4	344.4	343.8	344.4	344.9	344.4	343.8	344.4
180°	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4



TEST NUMBER: P332284-940

CATALOG NUMBER: S123RDIP-S560D805U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8
2.5°	784.2	780.6	778.2	772.7	769.2	765.4	761.5	763.9	763.7	763.4	763.4
5°	757.9	750.0	742.9	733.6	727.8	720.7	715.2	714.5	715.9	711.1	708.4
7.5°	731.8	721.0	710.9	700.7	689.9	681.3	675.9	673.4	669.9	667.0	663.9
10°	713.5	700.9	690.9	678.3	666.7	656.5	650.0	645.5	643.1	640.7	636.3
12.5°	694.6	682.2	669.6	655.3	644.3	632.4	627.6	622.6	618.0	615.3	609.2
15°	667.0	650.9	637.7	622.6	610.4	598.7	591.9	582.0	580.6	577.2	571.1
17.5°	639.4	622.0	603.6	592.5	578.5	566.5	556.1	552.8	543.0	539.3	534.0
20°	617.5	601.5	587.5	572.7	552.6	541.4	533.2	528.7	520.8	516.0	512.6
22.5°	598.7	582.3	566.1	549.0	532.4	519.8	513.7	506.8	502.6	495.9	492.1
25°	571.8	554.0	534.5	516.0	504.1	494.5	485.0	478.8	472.7	469.6	462.8
27.5°	540.5	521.9	503.7	489.7	475.0	465.6	456.9	451.5	444.1	438.9	435.2
30°	523.3	501.4	485.7	473.1	454.2	445.4	438.9	432.0	426.6	421.2	417.3
32.5°	503.3	483.3	468.4	452.8	438.4	428.7	420.3	414.3	409.7	404.5	400.7
35°	472.0	455.3	439.9	424.2	413.6	403.7	393.8	388.7	384.2	379.4	376.0
37.5°	443.7	428.1	413.5	398.6	385.5	377.4	369.4	365.5	359.5	356.3	352.8
40°	426.2	410.9	395.2	380.8	367.1	361.1	353.8	348.0	342.6	340.2	336.4
42.5°	407.2	391.7	378.5	363.0	351.9	343.5	336.9	330.6	326.5	323.0	320.8
45°	378.8	365.1	352.1	336.8	326.2	319.0	311.5	305.7	301.9	299.5	295.8
47.5°	351.2	337.6	324.4	311.0	300.8	292.6	285.1	281.0	276.1	273.1	270.5
50°	331.3	319.0	305.0	292.7	282.5	274.3	268.1	263.0	258.5	254.8	253.1
52.5°	313.0	299.9	287.8	276.3	265.6	256.2	250.7	245.2	241.9	237.6	235.6
55°	282.8	270.2	259.9	248.6	238.1	230.2	223.4	218.6	215.2	210.4	207.7
57.5°	254.4	243.1	230.9	221.1	210.2	203.6	197.9	191.4	187.3	183.5	180.8
60°	235.3	222.3	211.8	202.5	193.0	184.4	179.3	174.2	169.8	165.9	163.6
62.5°	215.3	204.0	194.0	184.0	175.2	167.7	161.8	157.5	153.6	151.2	148.8
65°	184.8	175.9	165.7	157.5	149.3	143.8	139.0	135.3	132.5	130.8	128.8
67.5°	156.7	148.0	139.1	131.0	125.6	121.4	118.2	115.0	113.7	111.5	110.1
70°	138.3	129.5	121.6	115.5	109.9	106.9	104.9	102.5	101.1	98.4	97.0
72.5°	118.4	112.0	106.3	101.2	96.8	94.1	91.5	88.5	86.3	83.4	81.9
75°	93.3	87.5	83.0	79.5	76.9	73.1	69.4	66.3	65.3	64.2	63.8
77.5°	69.0	65.4	62.2	59.3	55.9	53.1	52.3	51.6	51.5	50.9	50.9
80°	54.3	50.9	48.5	45.1	43.1	43.1	43.1	42.4	42.7	42.7	42.7
82.5°	40.4	37.2	35.9	34.7	34.3	34.6	34.6	34.7	34.5	35.0	34.8
85°	20.9	21.1	21.8	21.5	21.8	21.8	22.6	22.2	22.6	21.8	22.6
87.5°	9.2	10.3	11.0	11.7	12.4	12.5	12.7	12.8	13.2	13.3	13.6
90°	7.7	9.1	11.1	13.3	15.3	17.4	16.8	17.4	18.1	18.8	20.2
92.5°	30.0	40.3	58.6	88.5	118.0	107.2	80.9	58.7	46.5	41.1	37.5
95°	63.4	90.6	149.9	253.8	368.1	413.4	335.4	251.0	170.1	133.1	108.1
97.5°	75.3	104.7	161.3	278.5	469.0	640.7	685.5	625.6	501.1	411.2	327.8
100°	83.6	110.8	159.6	262.8	446.2	660.2	797.5	822.0	765.4	683.9	584.9
102.5°	93.2	118.1	161.8	249.4	412.7	623.9	803.2	887.2	885.4	837.9	775.1
105°	108.8	130.4	168.0	239.8	371.6	560.5	760.6	906.3	976.0	989.3	971.2
107.5°	126.4	146.4	179.4	239.2	345.4	504.4	686.2	851.4	964.6	1025.6	1050.4
110°	138.0	157.6	189.0	241.9	335.4	472.7	639.3	799.0	927.2	1015.0	1063.9



TEST NUMBER: P332284-940

CATALOG NUMBER: S123RDIP-S560D805U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	150.3	169.2	198.4	247.4	329.8	451.5	598.6	747.1	878.2	976.6	1039.3
115°	168.7	187.5	214.0	256.5	327.7	428.7	549.4	678.3	799.6	902.1	978.1
117.5°	187.0	204.4	230.6	268.6	329.0	415.4	519.7	628.6	733.3	825.3	902.4
120°	198.7	216.2	241.2	277.5	331.2	409.2	504.1	602.4	696.4	780.2	850.5
122.5°	209.3	227.8	252.4	285.8	335.0	405.4	491.2	581.8	666.9	744.4	809.9
125°	225.2	244.0	268.4	299.1	340.9	400.2	474.7	554.2	630.3	697.1	753.0
127.5°	240.0	258.8	282.3	310.0	347.6	397.7	460.3	530.3	598.0	658.4	709.2
130°	248.9	267.7	290.7	317.2	352.0	396.0	452.5	515.2	577.9	634.5	681.8
132.5°	257.3	275.5	297.9	323.9	355.4	395.4	445.2	501.2	559.0	611.5	656.7
135°	268.4	287.2	308.8	332.5	360.4	394.6	435.7	482.4	531.9	577.2	617.0
137.5°	278.1	295.6	316.4	338.9	363.8	393.1	427.5	465.3	505.9	544.9	579.3
140°	283.7	301.1	321.4	342.3	366.0	392.5	422.5	455.2	490.8	524.2	554.2
142.5°	289.4	305.6	325.3	345.6	367.7	391.4	418.0	445.8	476.3	505.3	531.4
145°	296.3	312.4	330.5	349.3	368.8	389.7	412.1	434.4	457.4	479.7	499.9
147.5°	304.3	318.1	334.7	351.5	368.8	387.1	406.2	425.0	443.3	461.3	475.6
150°	308.8	321.4	337.4	352.0	368.8	384.9	402.3	418.3	434.4	449.0	462.2
152.5°	313.3	325.3	339.1	353.2	367.1	382.0	397.8	412.1	426.0	438.9	450.0
155°	320.7	330.5	342.3	353.5	365.3	377.2	391.1	403.0	414.1	424.5	432.9
157.5°	327.1	334.7	344.1	354.2	362.9	372.8	383.6	393.2	402.5	410.6	417.1
160°	330.5	337.4	345.8	354.2	361.9	369.5	378.5	387.6	395.3	402.3	407.2
162.5°	333.2	339.1	346.3	353.6	359.6	366.1	373.5	380.9	387.4	393.9	398.2
165°	336.7	341.6	347.1	352.0	356.2	361.1	366.7	372.3	376.5	381.4	384.9
167.5°	339.9	343.0	347.1	351.0	352.9	356.1	360.2	364.7	367.9	370.8	373.3
170°	341.6	343.0	346.5	349.3	350.7	352.8	356.2	359.7	361.9	364.6	366.0
172.5°	342.7	343.6	346.5	348.7	349.0	350.0	352.3	355.3	356.8	359.0	359.9
175°	343.7	344.4	345.8	347.1	346.5	346.5	347.9	349.3	350.0	351.3	351.3
177.5°	344.4	344.4	344.9	346.1	344.9	344.4	344.9	345.5	346.1	346.6	346.6
180°	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4



TEST NUMBER: P332284-940

CATALOG NUMBER: S123RDIP-S560D805U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8
2.5°	760.1	759.8	760.1	759.0	760.1	759.8	760.1	763.4	763.4	763.7	763.9
5°	707.3	706.9	706.0	702.9	706.0	706.9	707.3	708.4	711.1	715.9	714.5
7.5°	661.2	660.8	657.7	657.8	657.7	660.8	661.2	663.9	667.0	669.9	673.4
10°	633.9	634.3	630.2	627.8	630.2	634.3	633.9	636.3	640.7	643.1	645.5
12.5°	607.4	605.8	602.5	599.9	602.5	605.8	607.4	609.2	615.3	618.0	622.6
15°	572.4	569.0	560.8	561.5	560.8	569.0	572.4	571.1	577.2	580.6	582.0
17.5°	531.2	528.7	528.6	523.8	528.6	528.7	531.2	534.0	539.3	543.0	552.8
20°	507.2	505.5	506.1	501.4	506.1	505.5	507.2	512.6	516.0	520.8	528.7
22.5°	488.3	486.6	483.8	482.2	483.8	486.6	488.3	492.1	495.9	502.6	506.8
25°	460.7	458.0	455.3	457.0	455.3	458.0	460.7	462.8	469.6	472.7	478.8
27.5°	433.1	431.1	428.4	428.0	428.4	431.1	433.1	435.2	438.9	444.1	451.5
30°	415.6	413.6	412.2	410.5	412.2	413.6	415.6	417.3	421.2	426.6	432.0
32.5°	397.9	397.5	395.0	394.7	395.0	397.5	397.9	400.7	404.5	409.7	414.3
35°	374.7	372.6	371.9	372.3	371.9	372.6	374.7	376.0	379.4	384.2	388.7
37.5°	352.6	349.9	348.7	347.4	348.7	349.9	352.6	352.8	356.3	359.5	365.5
40°	336.8	334.0	333.3	332.7	333.3	334.0	336.8	336.4	340.2	342.6	348.0
42.5°	319.0	317.9	317.5	316.3	317.5	317.9	319.0	320.8	323.0	326.5	330.6
45°	294.7	294.4	292.4	293.0	292.4	294.4	294.7	295.8	299.5	301.9	305.7
47.5°	269.2	267.7	266.3	267.2	266.3	267.7	269.2	270.5	273.1	276.1	281.0
50°	251.7	251.0	248.0	248.6	248.0	251.0	251.7	253.1	254.8	258.5	263.0
52.5°	234.3	231.7	230.5	230.1	230.5	231.7	234.3	235.6	237.6	241.9	245.2
55°	205.3	202.2	200.8	200.1	200.8	202.2	205.3	207.7	210.4	215.2	218.6
57.5°	176.8	176.0	175.0	175.7	175.0	176.0	176.8	180.8	183.5	187.3	191.4
60°	160.2	160.2	160.2	159.9	160.2	160.2	160.2	163.6	165.9	169.8	174.2
62.5°	147.3	146.5	146.2	146.7	146.2	146.5	147.3	148.8	151.2	153.6	157.5
65°	127.7	127.4	126.0	125.7	126.0	127.4	127.7	128.8	130.8	132.5	135.3
67.5°	109.2	108.0	107.6	107.1	107.6	108.0	109.2	110.1	111.5	113.7	115.0
70°	95.3	94.6	92.6	92.9	92.6	94.6	95.3	97.0	98.4	101.1	102.5
72.5°	80.3	79.5	79.2	78.6	79.2	79.5	80.3	81.9	83.4	86.3	88.5
75°	63.5	63.2	62.9	64.2	62.9	63.2	63.5	63.8	64.2	65.3	66.3
77.5°	50.9	50.9	51.1	50.6	51.1	50.9	50.9	50.9	50.9	51.5	51.6
80°	42.7	42.7	42.4	42.4	42.4	42.7	42.7	42.7	42.7	42.7	42.4
82.5°	34.2	34.5	34.7	34.2	34.7	34.5	34.2	34.8	35.0	34.5	34.7
85°	22.6	22.2	22.9	22.6	22.9	22.2	22.6	22.6	21.8	22.6	22.2
87.5°	14.0	13.6	13.7	13.9	13.7	13.6	14.0	13.6	13.3	13.2	12.8
90°	19.5	20.2	21.0	20.2	21.0	20.2	19.5	20.2	18.8	18.1	17.4
92.5°	36.3	34.2	34.9	33.6	34.9	34.2	36.3	37.5	41.1	46.5	58.7
95°	94.8	88.5	83.6	80.9	83.6	88.5	94.8	108.1	133.1	170.1	251.0
97.5°	276.3	245.0	226.1	220.2	226.1	245.0	276.3	327.8	411.2	501.1	625.6
100°	514.5	463.6	436.4	437.1	436.4	463.6	514.5	584.9	683.9	765.4	822.0
102.5°	720.3	680.0	657.3	641.2	657.3	680.0	720.3	775.1	837.9	885.4	887.2
105°	939.1	912.6	890.3	886.8	890.3	912.6	939.1	971.2	989.3	976.0	906.3
107.5°	1051.1	1042.1	1034.6	1028.1	1034.6	1042.1	1051.1	1050.4	1025.6	964.6	851.4
110°	1083.3	1089.0	1087.5	1086.2	1087.5	1089.0	1083.3	1063.9	1015.0	927.2	799.0



TEST NUMBER: P332284-940

CATALOG NUMBER: S123RDIP-S560D805U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1075.0	1092.3	1097.6	1097.9	1097.6	1092.3	1075.0	1039.3	976.6	878.2	747.1
115°	1030.4	1061.0	1075.0	1078.5	1075.0	1061.0	1030.4	978.1	902.1	799.6	678.3
117.5°	956.9	992.0	1012.1	1016.9	1012.1	992.0	956.9	902.4	825.3	733.3	628.6
120°	905.6	944.7	961.4	965.5	961.4	944.7	905.6	850.5	780.2	696.4	602.4
122.5°	858.7	893.9	912.3	917.6	912.3	893.9	858.7	809.9	744.4	666.9	581.8
125°	797.5	828.2	845.6	850.5	845.6	828.2	797.5	753.0	697.1	630.3	554.2
127.5°	748.9	775.1	790.9	795.3	790.9	775.1	748.9	709.2	658.4	598.0	530.3
130°	718.8	743.9	758.5	764.1	758.5	743.9	718.8	681.8	634.5	577.9	515.2
132.5°	691.4	716.6	729.5	733.4	729.5	716.6	691.4	656.7	611.5	559.0	501.2
135°	651.1	672.1	684.6	689.5	684.6	672.1	651.1	617.0	577.2	531.9	482.4
137.5°	608.1	629.3	639.9	643.1	639.9	629.3	608.1	579.3	544.9	505.9	465.3
140°	580.8	600.2	611.4	610.7	611.4	600.2	580.8	554.2	524.2	490.8	455.2
142.5°	553.9	571.2	581.3	580.6	581.3	571.2	553.9	531.4	505.3	476.3	445.8
145°	517.3	531.9	537.5	538.9	537.5	531.9	517.3	499.9	479.7	457.4	434.4
147.5°	488.8	498.7	504.1	504.6	504.1	498.7	488.8	475.6	461.3	443.3	425.0
150°	472.7	480.4	484.6	484.6	484.6	480.4	472.7	462.2	449.0	434.4	418.3
152.5°	458.2	465.3	467.8	467.8	467.8	465.3	458.2	450.0	438.9	426.0	412.1
155°	439.2	444.8	446.2	446.8	446.2	444.8	439.2	432.9	424.5	414.1	403.0
157.5°	422.6	426.8	427.9	427.8	427.9	426.8	422.6	417.1	410.6	402.5	393.2
160°	412.1	416.2	416.2	415.5	416.2	416.2	412.1	407.2	402.3	395.3	387.6
162.5°	401.4	405.0	405.0	404.4	405.0	405.0	401.4	398.2	393.9	387.4	380.9
165°	387.6	390.4	389.7	389.7	389.7	390.4	387.6	384.9	381.4	376.5	372.3
167.5°	374.5	376.5	375.8	375.8	375.8	376.5	374.5	373.3	370.8	367.9	364.7
170°	366.7	368.1	367.4	367.4	367.4	368.1	366.7	366.0	364.6	361.9	359.7
172.5°	360.0	361.4	360.2	359.6	360.2	361.4	360.0	359.9	359.0	356.8	355.3
175°	351.3	352.0	351.3	350.7	351.3	352.0	351.3	351.3	351.3	350.0	349.3
177.5°	346.1	346.6	345.5	345.5	345.5	346.6	346.1	346.6	346.6	346.1	345.5
180°	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4



TEST NUMBER: P332284-940

CATALOG NUMBER: S123RDIP-S560D805U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8
2.5°	761.5	765.4	769.2	772.7	778.2	780.6	784.2	785.5	789.6	795.7	800.6
5°	715.2	720.7	727.8	733.6	742.9	750.0	757.9	765.4	774.3	786.9	798.2
7.5°	675.9	681.3	689.9	700.7	710.9	721.0	731.8	742.0	754.7	772.8	790.8
10°	650.0	656.5	666.7	678.3	690.9	700.9	713.5	726.5	742.2	763.0	784.5
12.5°	627.6	632.4	644.3	655.3	669.6	682.2	694.6	709.8	727.7	749.9	775.8
15°	591.9	598.7	610.4	622.6	637.7	650.9	667.0	685.5	702.9	730.2	761.6
17.5°	556.1	566.5	578.5	592.5	603.6	622.0	639.4	658.3	679.8	708.7	743.2
20°	533.2	541.4	552.6	572.7	587.5	601.5	617.5	641.1	660.8	693.7	729.5
22.5°	513.7	519.8	532.4	549.0	566.1	582.3	598.7	621.2	645.6	676.7	715.6
25°	485.0	494.5	504.1	516.0	534.5	554.0	571.8	590.8	616.8	650.0	692.0
27.5°	456.9	465.6	475.0	489.7	503.7	521.9	540.5	562.4	590.2	625.3	667.9
30°	438.9	445.4	454.2	473.1	485.7	501.4	523.3	542.7	568.6	605.9	650.9
32.5°	420.3	428.7	438.4	452.8	468.4	483.3	503.3	524.4	550.9	587.5	633.7
35°	393.8	403.7	413.6	424.2	439.9	455.3	472.0	495.3	522.2	557.8	603.2
37.5°	369.4	377.4	385.5	398.6	413.5	428.1	443.7	466.6	492.0	530.4	572.0
40°	353.8	361.1	367.1	380.8	395.2	410.9	426.2	446.4	473.7	509.6	549.9
42.5°	336.9	343.5	351.9	363.0	378.5	391.7	407.2	426.1	451.8	488.3	523.6
45°	311.5	319.0	326.2	336.8	352.1	365.1	378.8	396.9	423.2	453.3	484.6
47.5°	285.1	292.6	300.8	311.0	324.4	337.6	351.2	367.3	391.3	420.8	441.9
50°	268.1	274.3	282.5	292.7	305.0	319.0	331.3	348.7	371.6	394.8	413.3
52.5°	250.7	256.2	265.6	276.3	287.8	299.9	313.0	328.0	348.7	370.5	385.1
55°	223.4	230.2	238.1	248.6	259.9	270.2	282.8	298.2	314.6	330.9	340.9
57.5°	197.9	203.6	210.2	221.1	230.9	243.1	254.4	266.4	281.6	293.9	300.4
60°	179.3	184.4	193.0	202.5	211.8	222.3	235.3	247.3	258.9	268.8	273.9
62.5°	161.8	167.7	175.2	184.0	194.0	204.0	215.3	225.4	235.7	244.2	247.7
65°	139.0	143.8	149.3	157.5	165.7	175.9	184.8	195.0	202.5	207.3	210.4
67.5°	118.2	121.4	125.6	131.0	139.1	148.0	156.7	164.6	170.9	174.2	176.9
70°	104.9	106.9	109.9	115.5	121.6	129.5	138.3	144.1	149.6	152.3	155.1
72.5°	91.5	94.1	96.8	101.2	106.3	112.0	118.4	125.6	128.6	131.8	133.5
75°	69.4	73.1	76.9	79.5	83.0	87.5	93.3	97.6	99.4	102.1	102.5
77.5°	52.3	53.1	55.9	59.3	62.2	65.4	69.0	73.0	73.8	75.3	76.2
80°	43.1	43.1	43.1	45.1	48.5	50.9	54.3	56.4	57.7	58.1	58.4
82.5°	34.6	34.6	34.3	34.7	35.9	37.2	40.4	42.7	43.8	43.6	42.8
85°	22.6	21.8	21.8	21.5	21.8	21.1	20.9	22.2	24.3	24.3	23.5
87.5°	12.7	12.5	12.4	11.7	11.0	10.3	9.2	9.2	8.7	9.5	9.0
90°	16.8	17.4	15.3	13.3	11.1	9.1	7.7	6.2	4.2	2.8	1.4
92.5°	80.9	107.2	118.0	88.5	58.6	40.3	30.0	24.2	18.7	12.8	8.6
95°	335.4	413.4	368.1	253.8	149.9	90.6	63.4	45.3	33.4	25.8	23.7
97.5°	685.5	640.7	469.0	278.5	161.3	104.7	75.3	57.4	47.2	41.1	40.4
100°	797.5	660.2	446.2	262.8	159.6	110.8	83.6	67.0	57.2	52.3	51.6
102.5°	803.2	623.9	412.7	249.4	161.8	118.1	93.2	78.1	68.8	64.6	63.3
105°	760.6	560.5	371.6	239.8	168.0	130.4	108.8	95.5	87.1	82.9	80.9
107.5°	686.2	504.4	345.4	239.2	179.4	146.4	126.4	113.9	105.7	101.7	99.5
110°	639.3	472.7	335.4	241.9	189.0	157.6	138.0	126.2	118.5	115.0	113.0



TEST NUMBER: P332284-940

CATALOG NUMBER: S123RDIP-S560D805U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	598.6	451.5	329.8	247.4	198.4	169.2	150.3	138.5	130.8	127.3	125.2
115°	549.4	428.7	327.7	256.5	214.0	187.5	168.7	156.9	149.9	145.7	142.9
117.5°	519.7	415.4	329.0	268.6	230.6	204.4	187.0	173.7	167.3	163.8	160.6
120°	504.1	409.2	331.2	277.5	241.2	216.2	198.7	185.5	178.4	175.0	172.9
122.5°	491.2	405.4	335.0	285.8	252.4	227.8	209.3	196.6	189.0	185.6	183.5
125°	474.7	400.2	340.9	299.1	268.4	244.0	225.2	212.0	204.3	200.1	198.7
127.5°	460.3	397.7	347.6	310.0	282.3	258.8	240.0	225.3	217.5	212.3	210.3
130°	452.5	396.0	352.0	317.2	290.7	267.7	248.9	234.3	225.9	219.6	217.5
132.5°	445.2	395.4	355.4	323.9	297.9	275.5	257.3	242.6	232.6	225.8	223.1
135°	435.7	394.6	360.4	332.5	308.8	287.2	268.4	253.8	243.3	235.7	232.8
137.5°	427.5	393.1	363.8	338.9	316.4	295.6	278.1	263.7	252.5	245.0	242.0
140°	422.5	392.5	366.0	342.3	321.4	301.1	283.7	269.8	258.7	251.6	248.2
142.5°	418.0	391.4	367.7	345.6	325.3	305.6	289.4	275.4	265.4	257.8	254.9
145°	412.1	389.7	368.8	349.3	330.5	312.4	296.3	284.5	274.0	267.7	265.6
147.5°	406.2	387.1	368.8	351.5	334.7	318.1	304.3	292.9	283.9	277.8	276.5
150°	402.3	384.9	368.8	352.0	337.4	321.4	308.8	299.1	290.0	284.5	283.7
152.5°	397.8	382.0	367.1	353.2	339.1	325.3	313.3	304.7	296.7	291.1	291.0
155°	391.1	377.2	365.3	353.5	342.3	330.5	320.7	313.0	306.0	301.8	301.8
157.5°	383.6	372.8	362.9	354.2	344.1	334.7	327.1	320.6	314.4	311.0	310.5
160°	378.5	369.5	361.9	354.2	345.8	337.4	330.5	325.6	320.0	317.2	317.2
162.5°	373.5	366.1	359.6	353.6	346.3	339.1	333.2	329.0	324.5	322.3	322.3
165°	366.7	361.1	356.2	352.0	347.1	341.6	336.7	333.9	330.5	329.0	329.8
167.5°	360.2	356.1	352.9	351.0	347.1	343.0	339.9	338.0	335.4	334.7	335.5
170°	356.2	352.8	350.7	349.3	346.5	343.0	341.6	340.2	338.1	337.4	338.9
172.5°	352.3	350.0	349.0	348.7	346.5	343.6	342.7	341.9	340.4	340.2	341.1
175°	347.9	346.5	346.5	347.1	345.8	344.4	343.7	343.7	342.3	343.0	343.7
177.5°	344.9	344.4	344.9	346.1	344.9	344.4	344.4	344.4	343.8	344.4	344.9
180°	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4



TEST NUMBER: P332284-940

CATALOG NUMBER: S123RDIP-S560D805U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8
2.5°	802.2	805.2	809.0	814.8	819.1	823.0	823.8	824.9	827.6	832.2	835.8
5°	807.4	815.3	827.9	840.2	853.5	864.4	874.7	881.9	888.7	903.0	914.6
7.5°	805.7	823.2	843.0	865.1	887.4	909.1	929.2	947.2	965.1	986.0	1009.8
10°	804.7	825.2	851.8	880.1	911.2	941.6	971.0	993.9	1020.6	1044.5	1074.9
12.5°	799.5	829.0	860.9	897.1	935.3	970.4	1009.0	1040.6	1071.0	1105.6	1140.9
15°	792.7	828.6	868.9	917.0	975.1	1017.4	1057.0	1112.1	1149.6	1187.2	1237.8
17.5°	780.3	824.1	874.5	937.0	985.5	1042.4	1102.0	1145.5	1196.1	1249.0	1294.8
20°	770.5	821.4	877.8	939.2	1001.0	1062.9	1120.6	1172.5	1224.8	1285.9	1323.5
22.5°	760.7	811.0	869.6	934.9	1001.3	1066.4	1131.8	1192.8	1251.5	1313.2	1361.2
25°	739.8	799.5	863.1	929.7	995.2	1066.9	1144.9	1212.8	1285.6	1349.1	1394.5
27.5°	718.6	773.4	836.6	904.2	977.0	1061.8	1153.4	1230.7	1303.6	1349.1	1363.3
30°	699.5	757.5	815.6	884.2	963.1	1057.7	1155.1	1243.6	1303.3	1323.1	1308.4
32.5°	680.1	732.7	790.2	860.5	944.3	1047.7	1157.3	1235.9	1271.9	1256.8	1196.9
35°	645.9	693.3	749.0	819.4	915.7	1042.1	1148.3	1201.6	1192.7	1107.2	994.5
37.5°	609.2	647.9	699.5	773.0	886.0	1019.8	1109.5	1117.3	1040.4	909.4	779.2
40°	580.2	615.1	668.1	744.9	863.1	998.0	1070.4	1038.7	919.4	773.6	664.9
42.5°	552.1	581.5	632.5	715.4	841.2	968.2	1012.2	943.0	805.5	667.5	568.8
45°	504.4	532.1	583.4	668.4	796.5	911.2	905.4	785.2	647.6	536.5	454.6
47.5°	459.2	483.4	531.5	618.3	744.0	825.8	771.5	643.6	526.8	437.8	379.3
50°	427.3	451.2	499.0	584.7	701.9	761.6	684.1	560.8	453.9	380.1	333.7
52.5°	396.6	420.0	463.8	547.2	651.0	686.8	603.5	489.2	400.1	336.4	296.5
55°	353.8	371.6	410.9	490.8	568.3	576.5	492.1	396.5	323.1	278.7	251.4
57.5°	310.2	325.5	364.3	427.9	482.3	478.0	398.1	315.4	265.9	232.9	213.1
60°	281.8	296.8	330.9	385.6	426.6	412.2	338.9	272.2	229.9	205.6	189.9
62.5°	255.3	267.0	299.0	338.9	368.4	352.1	289.6	234.5	200.9	180.5	168.0
65°	216.9	226.4	252.1	272.9	289.3	273.6	221.7	183.4	159.2	144.8	136.3
67.5°	180.4	186.5	202.7	210.2	221.8	204.6	166.7	141.1	127.2	115.2	109.2
70°	157.5	161.9	170.4	176.6	179.7	161.9	133.8	115.1	103.5	95.0	91.2
72.5°	134.5	138.4	140.1	145.2	143.6	126.9	107.6	92.7	84.4	78.6	73.7
75°	102.8	104.5	102.8	100.8	96.3	84.7	71.4	63.8	57.7	55.0	53.3
77.5°	74.9	74.4	72.1	68.8	61.3	53.9	46.8	44.2	41.6	40.1	39.6
80°	57.7	56.4	54.3	49.2	42.7	37.5	35.8	34.2	33.2	31.4	31.1
82.5°	43.0	42.2	38.7	34.4	29.9	27.5	26.0	25.4	24.3	23.5	23.5
85°	22.9	21.8	18.1	15.7	15.1	14.4	14.0	14.0	12.7	12.3	12.3
87.5°	7.9	6.6	6.7	6.2	6.4	6.3	7.0	6.9	7.0	7.1	6.8
90°	2.8	4.2	6.2	7.7	9.1	11.1	13.3	15.3	17.4	16.8	17.4
92.5°	12.8	18.7	24.2	30.0	40.3	58.6	88.5	118.0	107.2	80.9	58.7
95°	25.8	33.4	45.3	63.4	90.6	149.9	253.8	368.1	413.4	335.4	251.0
97.5°	41.1	47.2	57.4	75.3	104.7	161.3	278.5	469.0	640.7	685.5	625.6
100°	52.3	57.2	67.0	83.6	110.8	159.6	262.8	446.2	660.2	797.5	822.0
102.5°	64.6	68.8	78.1	93.2	118.1	161.8	249.4	412.7	623.9	803.2	887.2
105°	82.9	87.1	95.5	108.8	130.4	168.0	239.8	371.6	560.5	760.6	906.3
107.5°	101.7	105.7	113.9	126.4	146.4	179.4	239.2	345.4	504.4	686.2	851.4
110°	115.0	118.5	126.2	138.0	157.6	189.0	241.9	335.4	472.7	639.3	799.0



TEST NUMBER: P332284-940

CATALOG NUMBER: S123RDIP-S560D805U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	127.3	130.8	138.5	150.3	169.2	198.4	247.4	329.8	451.5	598.6	747.1
115°	145.7	149.9	156.9	168.7	187.5	214.0	256.5	327.7	428.7	549.4	678.3
117.5°	163.8	167.3	173.7	187.0	204.4	230.6	268.6	329.0	415.4	519.7	628.6
120°	175.0	178.4	185.5	198.7	216.2	241.2	277.5	331.2	409.2	504.1	602.4
122.5°	185.6	189.0	196.6	209.3	227.8	252.4	285.8	335.0	405.4	491.2	581.8
125°	200.1	204.3	212.0	225.2	244.0	268.4	299.1	340.9	400.2	474.7	554.2
127.5°	212.3	217.5	225.3	240.0	258.8	282.3	310.0	347.6	397.7	460.3	530.3
130°	219.6	225.9	234.3	248.9	267.7	290.7	317.2	352.0	396.0	452.5	515.2
132.5°	225.8	232.6	242.6	257.3	275.5	297.9	323.9	355.4	395.4	445.2	501.2
135°	235.7	243.3	253.8	268.4	287.2	308.8	332.5	360.4	394.6	435.7	482.4
137.5°	245.0	252.5	263.7	278.1	295.6	316.4	338.9	363.8	393.1	427.5	465.3
140°	251.6	258.7	269.8	283.7	301.1	321.4	342.3	366.0	392.5	422.5	455.2
142.5°	257.8	265.4	275.4	289.4	305.6	325.3	345.6	367.7	391.4	418.0	445.8
145°	267.7	274.0	284.5	296.3	312.4	330.5	349.3	368.8	389.7	412.1	434.4
147.5°	277.8	283.9	292.9	304.3	318.1	334.7	351.5	368.8	387.1	406.2	425.0
150°	284.5	290.0	299.1	308.8	321.4	337.4	352.0	368.8	384.9	402.3	418.3
152.5°	291.1	296.7	304.7	313.3	325.3	339.1	353.2	367.1	382.0	397.8	412.1
155°	301.8	306.0	313.0	320.7	330.5	342.3	353.5	365.3	377.2	391.1	403.0
157.5°	311.0	314.4	320.6	327.1	334.7	344.1	354.2	362.9	372.8	383.6	393.2
160°	317.2	320.0	325.6	330.5	337.4	345.8	354.2	361.9	369.5	378.5	387.6
162.5°	322.3	324.5	329.0	333.2	339.1	346.3	353.6	359.6	366.1	373.5	380.9
165°	329.0	330.5	333.9	336.7	341.6	347.1	352.0	356.2	361.1	366.7	372.3
167.5°	334.7	335.4	338.0	339.9	343.0	347.1	351.0	352.9	356.1	360.2	364.7
170°	337.4	338.1	340.2	341.6	343.0	346.5	349.3	350.7	352.8	356.2	359.7
172.5°	340.2	340.4	341.9	342.7	343.6	346.5	348.7	349.0	350.0	352.3	355.3
175°	343.0	342.3	343.7	343.7	344.4	345.8	347.1	346.5	346.5	347.9	349.3
177.5°	344.4	343.8	344.4	344.4	344.4	344.9	346.1	344.9	344.4	344.9	345.5
180°	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4



TEST NUMBER: P332284-940

CATALOG NUMBER: S123RDIP-S560D805U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	797.8	797.8	797.8	797.8	797.8	797.8	797.8
2.5°	841.6	841.6	842.7	846.8	847.3	850.9	849.7
5°	924.9	931.4	933.8	944.1	950.2	952.9	947.4
7.5°	1026.8	1045.1	1053.8	1064.5	1074.0	1076.9	1069.4
10°	1101.2	1120.3	1136.3	1146.2	1155.5	1161.5	1169.5
12.5°	1173.0	1196.5	1211.7	1225.7	1235.2	1243.0	1244.3
15°	1251.1	1286.6	1313.6	1333.4	1343.3	1348.4	1346.4
17.5°	1329.8	1362.7	1382.0	1402.1	1415.9	1416.6	1417.0
20°	1374.4	1406.5	1428.7	1443.7	1459.1	1458.4	1461.8
22.5°	1404.2	1429.4	1446.4	1457.3	1462.6	1460.0	1460.7
25°	1418.1	1425.6	1422.5	1405.1	1400.7	1384.6	1387.3
27.5°	1346.2	1310.7	1274.0	1226.6	1189.4	1159.6	1161.1
30°	1248.7	1185.8	1114.1	1054.0	1000.1	985.0	952.9
32.5°	1112.3	1018.1	934.1	878.1	831.7	819.1	791.1
35°	881.2	789.6	703.2	651.3	630.8	602.2	601.8
37.5°	684.9	604.3	558.7	519.7	499.3	481.9	480.2
40°	576.2	513.4	478.8	450.8	430.7	417.7	414.6
42.5°	500.2	449.4	417.1	399.8	384.2	377.6	372.6
45°	408.5	374.3	351.8	336.1	328.9	323.8	321.0
47.5°	341.7	318.8	303.4	293.0	287.1	281.8	283.2
50°	305.3	286.6	275.3	265.4	260.9	257.2	257.5
52.5°	276.1	259.2	250.1	243.0	237.5	234.8	233.4
55°	234.3	223.7	214.5	209.4	206.3	202.5	201.5
57.5°	199.8	191.6	184.1	178.3	177.6	174.0	174.4
60°	176.9	170.0	163.9	160.9	158.5	155.4	156.4
62.5°	158.1	152.3	146.7	144.2	141.8	139.6	140.0
65°	129.5	123.9	120.6	119.2	118.2	117.2	116.1
67.5°	103.2	99.8	97.6	94.7	92.6	92.3	91.2
70°	86.8	82.3	78.6	74.8	73.7	73.4	73.7
72.5°	69.6	66.7	65.7	63.8	63.7	62.8	63.4
75°	52.3	51.3	50.6	49.2	49.2	49.2	49.2
77.5°	38.5	37.9	37.5	37.2	36.9	36.4	36.4
80°	30.1	29.7	29.1	29.1	28.7	29.1	28.7
82.5°	22.6	22.6	21.9	21.9	21.6	21.4	21.6
85°	11.6	11.2	11.9	11.2	11.6	11.0	11.6
87.5°	6.9	7.0	7.0	6.9	6.8	7.5	6.8
90°	18.1	18.8	20.2	19.5	20.2	21.0	20.2
92.5°	46.5	41.1	37.5	36.3	34.2	34.9	33.6
95°	170.1	133.1	108.1	94.8	88.5	83.6	80.9
97.5°	501.1	411.2	327.8	276.3	245.0	226.1	220.2
100°	765.4	683.9	584.9	514.5	463.6	436.4	437.1
102.5°	885.4	837.9	775.1	720.3	680.0	657.3	641.2
105°	976.0	989.3	971.2	939.1	912.6	890.3	886.8
107.5°	964.6	1025.6	1050.4	1051.1	1042.1	1034.6	1028.1
110°	927.2	1015.0	1063.9	1083.3	1089.0	1087.5	1086.2



TEST NUMBER: P332284-940

CATALOG NUMBER: S123RDIP-S560D805U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	878.2	976.6	1039.3	1075.0	1092.3	1097.6	1097.9
115°	799.6	902.1	978.1	1030.4	1061.0	1075.0	1078.5
117.5°	733.3	825.3	902.4	956.9	992.0	1012.1	1016.9
120°	696.4	780.2	850.5	905.6	944.7	961.4	965.5
122.5°	666.9	744.4	809.9	858.7	893.9	912.3	917.6
125°	630.3	697.1	753.0	797.5	828.2	845.6	850.5
127.5°	598.0	658.4	709.2	748.9	775.1	790.9	795.3
130°	577.9	634.5	681.8	718.8	743.9	758.5	764.1
132.5°	559.0	611.5	656.7	691.4	716.6	729.5	733.4
135°	531.9	577.2	617.0	651.1	672.1	684.6	689.5
137.5°	505.9	544.9	579.3	608.1	629.3	639.9	643.1
140°	490.8	524.2	554.2	580.8	600.2	611.4	610.7
142.5°	476.3	505.3	531.4	553.9	571.2	581.3	580.6
145°	457.4	479.7	499.9	517.3	531.9	537.5	538.9
147.5°	443.3	461.3	475.6	488.8	498.7	504.1	504.6
150°	434.4	449.0	462.2	472.7	480.4	484.6	484.6
152.5°	426.0	438.9	450.0	458.2	465.3	467.8	467.8
155°	414.1	424.5	432.9	439.2	444.8	446.2	446.8
157.5°	402.5	410.6	417.1	422.6	426.8	427.9	427.8
160°	395.3	402.3	407.2	412.1	416.2	416.2	415.5
162.5°	387.4	393.9	398.2	401.4	405.0	405.0	404.4
165°	376.5	381.4	384.9	387.6	390.4	389.7	389.7
167.5°	367.9	370.8	373.3	374.5	376.5	375.8	375.8
170°	361.9	364.6	366.0	366.7	368.1	367.4	367.4
172.5°	356.8	359.0	359.9	360.0	361.4	360.2	359.6
175°	350.0	351.3	351.3	351.3	352.0	351.3	350.7
177.5°	346.1	346.6	346.6	346.1	346.6	345.5	345.5
180°	344.4	344.4	344.4	344.4	344.4	344.4	344.4

(END OF REPORT)