

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332321-940

Luminaire Tested: **S123RDIP-S775D1025U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332321-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S775D1025U940-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1025 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6257.5 lumens
Efficiency: N/A
Efficacy: 120.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332321-940

CATALOG NUMBER: S123RDIP-S775D1025U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332321-940

CATALOG NUMBER: S123RDIP-S775D1025U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48	42
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	41	36
2	88	81	75	70	80	74	69	64	61	57	54	49	47	45	38	37	35	30
3	80	71	64	58	73	65	59	54	54	50	46	44	41	38	34	32	30	26
4	73	63	55	50	67	58	51	46	48	43	39	39	36	33	31	28	26	22
5	67	56	48	42	61	52	45	40	43	38	34	35	31	28	28	25	23	20
6	62	50	43	37	57	46	40	34	39	34	30	32	28	25	25	23	20	17
7	57	46	38	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15
8	53	41	34	29	49	38	31	27	32	27	23	27	23	20	21	18	16	14
9	50	38	30	26	45	35	28	24	30	24	21	24	21	18	20	17	15	13
10	46	35	28	23	42	32	26	21	27	22	19	23	19	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12392	12392	12392
5°	12440	12268	12338
10°	12369	12114	12073
15°	12237	11830	11705
20°	12054	11475	11208
25°	11866	11077	10723
30°	11616	10618	10038
35°	11361	10159	9410
40°	11126	9617	8633
45°	10816	9082	7931
50°	10474	8473	7145
55°	10128	7781	6412
60°	9810	7035	5608
65°	9393	6230	4804
70°	8875	5231	3877
75°	8114	4117	3647
80°	7234	3651	3353
85°	6113	3223	3001



TEST NUMBER: P332321-940

CATALOG NUMBER: S123RDIP-S775D1025U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	108.1	1.7
10°-20°	300.8	4.8
20°-30°	433.1	6.9
30°-40°	487.9	7.8
40°-50°	466.7	7.5
50°-60°	382.2	6.1
60°-70°	257.9	4.1
70°-80°	129.7	2.1
80°-90°	37.7	0.6
90°-100°	43.6	0.7
100°-110°	207.6	3.3
110°-120°	498.6	8.0
120°-130°	634.9	10.1
130°-140°	678.4	10.8
140°-150°	634.4	10.1
150°-160°	511.7	8.2
160°-170°	330.3	5.3
170°-180°	113.8	1.8
0°-30°	842.0	13.5
0°-40°	1329.9	21.3
0°-60°	2178.8	34.8
0°-90°	2604.1	41.6
90°-120°	749.8	12.0
90°-150°	2697.6	43.1
90°-180°	3653.0	58.4
0°-180°	6257.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1151	1151	1151	1151	1151	
5°	1151	1146	1135	1143	1142	109
15°	1098	1087	1062	1057	1050	309
25°	999	975	933	914	903	459
35°	865	830	773	734	716	541
45°	710	667	597	545	521	548
55°	540	492	415	362	342	484
65°	369	316	245	201	189	365
75°	195	150	99	90	88	208
85°	50	30	26	24	24	56
90°	1	10	21	25	27	5
95°	54	20	28	34	34	67
105°	265	270	195	46	39	281
115°	498	503	511	520	523	491
125°	701	708	712	714	716	626
135°	873	878	882	884	882	672
145°	1008	1014	1016	1017	1017	630
155°	1110	1108	1109	1113	1108	511
165°	1170	1168	1167	1173	1168	331
175°	1198	1194	1194	1200	1194	114
180°	1198	1198	1198	1198	1198	



TEST NUMBER: P332321-940

CATALOG NUMBER: S123RDIP-S775D1025U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1151.3	1151.3	1151.3	1151.3	1151.3	1151.3	1151.3	1151.3	1151.3	1151.3	1151.3
2.5°	1154.9	1154.3	1153.6	1153.0	1152.4	1151.0	1149.0	1147.0	1145.0	1143.0	1144.9
5°	1151.3	1150.2	1149.1	1148.2	1147.1	1145.3	1142.8	1140.3	1137.8	1135.4	1137.2
7.5°	1140.6	1139.5	1138.4	1137.2	1136.1	1133.9	1130.7	1127.5	1124.3	1121.0	1122.0
10°	1131.7	1130.2	1128.7	1127.3	1125.8	1123.2	1119.5	1115.8	1112.1	1108.3	1108.5
12.5°	1118.9	1117.3	1115.7	1114.1	1112.5	1109.4	1104.8	1100.3	1095.6	1091.1	1091.0
15°	1098.1	1095.7	1093.4	1091.2	1088.9	1084.9	1079.1	1073.3	1067.4	1061.6	1060.6
17.5°	1071.7	1069.1	1066.4	1063.7	1061.0	1056.1	1048.7	1041.3	1033.8	1026.5	1024.3
20°	1052.3	1048.9	1045.6	1042.3	1039.0	1033.4	1025.5	1017.6	1009.8	1001.8	999.2
22.5°	1030.6	1026.8	1023.0	1019.1	1015.3	1009.2	1000.9	992.5	984.1	975.7	972.3
25°	999.1	993.9	988.6	983.5	978.3	970.9	961.4	951.8	942.3	932.7	928.4
27.5°	960.7	955.0	949.3	943.6	937.9	929.7	919.1	908.5	897.8	887.2	881.1
30°	934.6	928.4	922.2	916.0	909.7	900.8	889.2	877.5	865.9	854.3	847.3
32.5°	908.5	901.4	894.4	887.3	880.3	870.6	858.3	846.1	833.7	821.4	813.8
35°	864.6	857.1	849.6	842.2	834.7	824.6	811.7	798.8	786.0	773.1	764.2
37.5°	820.2	811.8	803.5	795.2	786.9	776.0	762.2	748.5	734.8	721.0	710.9
40°	791.8	782.7	773.5	764.4	755.3	743.3	728.6	713.9	699.1	684.4	673.6
42.5°	759.6	750.6	741.4	732.3	723.2	711.0	695.7	680.5	665.3	650.1	638.3
45°	710.5	701.2	691.9	682.5	673.2	660.6	644.5	628.6	612.6	596.6	584.8
47.5°	661.5	651.2	641.0	630.7	620.5	607.3	591.4	575.3	559.4	543.4	530.6
50°	625.5	615.8	606.1	596.3	586.6	573.3	556.5	539.7	522.9	506.0	493.2
52.5°	593.4	582.9	572.3	561.7	551.2	537.5	520.8	504.3	487.6	470.9	457.6
55°	539.7	529.5	519.3	509.2	499.0	485.1	467.4	449.9	432.2	414.6	402.5
57.5°	490.0	478.9	467.9	456.7	445.7	431.3	413.6	395.8	378.1	360.4	349.0
60°	455.7	444.3	432.8	421.4	410.0	395.7	378.4	361.2	344.0	326.8	315.6
62.5°	421.2	409.8	398.4	387.0	375.7	361.3	344.1	326.9	309.7	292.4	281.9
65°	368.8	357.4	346.0	334.6	323.2	309.3	293.2	277.0	260.8	244.6	234.4
67.5°	316.4	304.8	293.3	281.7	270.2	256.6	241.1	225.6	210.1	194.6	187.0
70°	282.0	270.8	259.6	248.3	237.2	224.3	209.7	195.3	180.7	166.2	158.9
72.5°	247.6	236.6	225.5	214.5	203.5	191.4	178.2	165.0	151.8	138.6	132.6
75°	195.1	185.2	175.2	165.2	155.3	144.6	133.2	121.8	110.4	99.0	96.9
77.5°	147.3	138.3	129.3	120.3	111.3	103.2	95.8	88.5	81.1	73.7	72.7
80°	116.7	108.2	99.7	91.2	82.7	76.2	71.9	67.5	63.2	58.9	58.2
82.5°	87.6	80.3	72.9	65.5	58.2	53.5	51.5	49.4	47.4	45.4	44.8
85°	49.5	44.9	40.4	35.8	31.2	28.6	28.0	27.4	26.8	26.1	25.8
87.5°	18.1	16.7	15.2	13.8	12.4	11.9	12.5	12.9	13.5	14.0	14.0
90°	0.9	2.9	4.8	6.9	8.8	11.1	13.6	16.2	18.8	21.4	22.1
92.5°	16.6	16.0	15.4	14.9	14.4	15.1	16.9	18.9	20.9	22.8	24.1
95°	54.3	46.2	38.1	30.0	21.8	18.9	21.0	23.3	25.4	27.6	29.0
97.5°	109.1	105.5	101.8	98.2	94.5	85.6	71.4	57.2	42.9	28.6	30.2
100°	150.4	154.4	158.4	162.3	166.2	152.8	121.9	91.0	60.2	29.3	30.9
102.5°	197.4	200.3	203.1	206.0	208.8	193.4	159.7	126.0	92.3	58.6	53.7
105°	265.2	267.4	269.6	271.8	273.9	266.1	248.3	230.5	212.8	194.9	159.9
107.5°	336.8	338.6	340.3	342.1	343.8	346.1	348.8	351.7	354.5	357.3	331.6
110°	384.5	386.1	387.6	389.2	390.8	392.7	394.8	397.1	399.2	401.4	394.8



TEST NUMBER: P332321-940

CATALOG NUMBER: S123RDIP-S775D1025U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	430.1	431.5	432.9	434.4	435.8	437.6	439.8	441.9	444.1	446.3	446.4
115°	497.6	498.7	499.9	501.1	502.3	503.8	505.5	507.3	509.1	510.9	512.9
117.5°	562.8	564.4	565.8	567.3	568.7	569.9	570.8	571.8	572.7	573.5	575.2
120°	603.4	605.2	607.0	608.8	610.6	611.8	612.3	613.0	613.6	614.1	615.7
122.5°	644.8	646.2	647.6	649.2	650.6	651.8	652.5	653.3	654.0	654.7	655.9
125°	701.3	702.9	704.5	706.1	707.7	708.9	709.7	710.4	711.2	712.0	712.5
127.5°	756.2	757.8	759.4	760.9	762.5	763.8	764.7	765.7	766.6	767.6	768.2
130°	790.4	791.9	793.5	795.1	796.7	797.9	798.7	799.5	800.2	801.0	801.8
132.5°	823.1	824.7	826.3	827.9	829.5	830.5	831.2	831.8	832.5	833.1	833.9
135°	873.2	874.3	875.5	876.7	877.9	878.9	879.7	880.5	881.3	882.1	882.6
137.5°	915.9	917.4	918.9	920.4	921.9	922.8	923.3	923.7	924.2	924.6	925.5
140°	944.3	945.6	946.7	947.9	949.1	950.0	950.6	951.2	951.8	952.3	953.1
142.5°	970.7	971.9	973.0	974.3	975.4	976.3	977.0	977.5	978.1	978.7	979.4
145°	1007.5	1009.0	1010.3	1011.7	1013.1	1014.0	1014.4	1014.8	1015.1	1015.6	1015.9
147.5°	1042.2	1043.2	1044.1	1045.0	1045.9	1046.5	1047.0	1047.3	1047.8	1048.1	1048.6
150°	1063.6	1064.3	1064.8	1065.4	1066.0	1066.5	1066.8	1067.3	1067.6	1068.1	1068.4
152.5°	1082.8	1083.2	1083.4	1083.7	1084.0	1084.2	1084.4	1084.7	1084.9	1085.1	1085.8
155°	1109.9	1109.5	1109.1	1108.8	1108.3	1108.2	1108.4	1108.6	1108.8	1109.0	1110.0
157.5°	1130.9	1130.9	1130.9	1130.8	1130.8	1130.6	1130.4	1130.2	1130.1	1129.8	1131.0
160°	1143.7	1143.5	1143.4	1143.2	1142.9	1142.7	1142.5	1142.4	1142.1	1141.9	1143.2
162.5°	1155.8	1155.3	1154.8	1154.3	1153.8	1153.4	1153.2	1153.0	1152.8	1152.6	1154.0
165°	1170.5	1169.8	1169.2	1168.7	1168.1	1167.7	1167.4	1167.2	1167.1	1166.9	1168.4
167.5°	1181.8	1181.1	1180.3	1179.5	1178.7	1178.2	1178.2	1178.2	1178.2	1178.2	1179.8
170°	1188.2	1187.4	1186.7	1185.9	1185.1	1184.6	1184.6	1184.6	1184.6	1184.6	1186.2
172.5°	1192.5	1191.6	1190.6	1189.6	1188.7	1188.3	1188.5	1188.7	1188.7	1188.9	1190.5
175°	1198.0	1197.0	1196.1	1195.1	1194.1	1193.6	1193.8	1194.1	1194.3	1194.4	1195.9
177.5°	1199.4	1198.6	1197.8	1197.0	1196.3	1196.0	1196.1	1196.3	1196.4	1196.6	1197.8
180°	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0



TEST NUMBER: P332321-940

CATALOG NUMBER: S123RDIP-S775D1025U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1151.3	1151.3	1151.3	1151.3	1151.3	1151.3	1151.3	1151.3
2.5°	1146.7	1148.5	1150.3	1151.1	1150.8	1150.4	1150.0	1149.8
5°	1139.1	1140.9	1142.8	1143.5	1143.2	1142.7	1142.3	1141.9
7.5°	1123.1	1124.1	1125.2	1125.3	1124.6	1123.9	1123.2	1122.5
10°	1108.8	1108.9	1109.1	1108.8	1107.7	1106.6	1105.6	1104.6
12.5°	1090.8	1090.7	1090.7	1089.9	1088.8	1087.5	1086.4	1085.1
15°	1059.5	1058.5	1057.5	1056.2	1054.8	1053.3	1051.9	1050.4
17.5°	1022.1	1019.9	1017.7	1015.6	1013.3	1011.2	1009.1	1006.9
20°	996.5	993.7	991.0	988.5	986.0	983.5	981.0	978.5
22.5°	969.0	965.6	962.2	959.4	957.1	954.8	952.4	950.1
25°	924.1	919.7	915.3	912.0	909.7	907.4	905.2	902.9
27.5°	875.0	869.1	863.0	858.2	854.7	851.2	847.7	844.3
30°	840.3	833.1	826.1	820.9	817.6	814.3	810.9	807.6
32.5°	806.0	798.3	790.6	785.0	781.5	778.0	774.5	771.1
35°	755.3	746.4	737.4	731.1	727.4	723.6	719.9	716.1
37.5°	700.7	690.6	680.5	673.2	668.5	663.9	659.3	654.7
40°	662.8	652.0	641.2	633.5	628.7	623.9	619.1	614.4
42.5°	626.4	614.7	602.9	594.9	590.6	586.3	582.0	577.7
45°	573.0	561.2	549.3	540.9	535.9	530.9	526.0	521.0
47.5°	517.6	504.8	492.0	483.3	478.8	474.4	470.0	465.6
50°	480.4	467.4	454.6	445.8	441.0	436.2	431.5	426.7
52.5°	444.3	430.9	417.5	408.7	404.4	400.1	395.8	391.6
55°	390.5	378.4	366.4	358.3	354.2	350.0	345.9	341.7
57.5°	337.7	326.3	315.0	307.5	304.0	300.4	296.9	293.4
60°	304.3	293.2	282.0	274.6	271.1	267.5	264.0	260.5
62.5°	271.3	260.8	250.3	243.2	239.4	235.8	232.1	228.4
65°	224.3	214.1	203.9	197.7	195.5	193.1	190.9	188.6
67.5°	179.4	171.8	164.2	159.2	156.8	154.3	151.9	149.4
70°	151.7	144.4	137.1	132.4	130.1	127.8	125.6	123.2
72.5°	126.7	120.7	114.9	111.4	110.4	109.5	108.5	107.5
75°	94.8	92.7	90.7	89.4	89.0	88.6	88.2	87.7
77.5°	71.5	70.4	69.3	68.5	68.1	67.7	67.2	66.9
80°	57.6	57.0	56.4	55.8	55.4	55.0	54.6	54.1
82.5°	44.1	43.5	42.9	42.5	42.4	42.4	42.3	42.2
85°	25.3	24.9	24.5	24.3	24.3	24.3	24.3	24.3
87.5°	14.0	14.0	13.9	13.9	13.8	13.7	13.6	13.6
90°	22.9	23.7	24.5	25.1	25.5	25.9	26.3	26.7
92.5°	25.3	26.6	27.8	28.6	28.8	29.1	29.3	29.5
95°	30.3	31.7	33.2	33.8	33.8	33.8	33.8	33.8
97.5°	31.8	33.4	35.0	35.8	36.1	36.3	36.5	36.6
100°	32.5	34.2	35.7	36.6	36.8	37.0	37.2	37.4
102.5°	48.8	43.9	39.0	36.6	37.0	37.4	37.7	38.1
105°	124.9	89.9	54.9	37.5	38.0	38.3	38.8	39.1
107.5°	305.9	280.3	254.6	228.5	202.2	175.8	149.4	123.0
110°	388.3	381.8	375.3	357.9	329.6	301.3	273.0	244.8



TEST NUMBER: P332321-940

CATALOG NUMBER: S123RDIP-S775D1025U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	446.5	446.7	446.7	443.8	437.8	431.9	425.9	419.9
115°	514.9	516.8	518.8	520.2	520.9	521.7	522.5	523.3
117.5°	576.8	578.3	579.9	580.8	580.9	581.0	581.2	581.4
120°	617.3	618.8	620.5	621.3	621.3	621.3	621.3	621.3
122.5°	656.9	658.1	659.2	659.8	660.0	660.1	660.2	660.4
125°	712.8	713.2	713.6	714.0	714.4	714.8	715.2	715.6
127.5°	768.8	769.5	770.1	770.3	769.8	769.5	769.0	768.7
130°	802.6	803.4	804.2	804.4	804.1	803.6	803.3	802.8
132.5°	834.6	835.4	836.2	836.3	835.8	835.3	834.7	834.2
135°	883.2	883.9	884.4	884.4	883.9	883.2	882.6	882.1
137.5°	926.5	927.5	928.4	928.6	928.3	927.9	927.5	927.1
140°	954.0	954.8	955.6	955.7	955.3	954.9	954.6	954.1
142.5°	980.0	980.6	981.2	981.2	980.7	980.2	979.6	979.1
145°	1016.4	1016.7	1017.2	1017.4	1017.4	1017.4	1017.4	1017.4
147.5°	1048.9	1049.3	1049.7	1049.5	1048.6	1047.7	1046.7	1045.8
150°	1068.9	1069.3	1069.7	1069.5	1069.0	1068.4	1067.7	1067.2
152.5°	1086.5	1087.3	1088.0	1087.9	1087.0	1086.1	1085.2	1084.2
155°	1111.0	1112.0	1112.9	1112.9	1111.7	1110.5	1109.3	1108.1
157.5°	1132.2	1133.4	1134.6	1134.4	1132.8	1131.3	1129.8	1128.3
160°	1144.3	1145.5	1146.7	1146.6	1145.2	1143.8	1142.5	1141.0
162.5°	1155.3	1156.6	1158.0	1158.1	1156.8	1155.6	1154.4	1153.2
165°	1170.0	1171.6	1173.2	1173.3	1171.9	1170.5	1169.1	1167.8
167.5°	1181.4	1183.0	1184.5	1184.5	1183.0	1181.4	1179.8	1178.2
170°	1187.8	1189.5	1191.0	1191.0	1189.5	1187.8	1186.2	1184.6
172.5°	1192.1	1193.6	1195.2	1195.2	1193.5	1191.7	1190.0	1188.2
175°	1197.2	1198.6	1200.0	1199.9	1198.3	1196.8	1195.2	1193.6
177.5°	1199.1	1200.4	1201.7	1201.5	1199.9	1198.4	1196.8	1195.2
180°	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0

(END OF REPORT)