

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332324-940

Luminaire Tested: **S123RDIP-S775D1195U940-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332324-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S775D1195U940-4F0-1E-UDD-A  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1195 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6971.7 lumens  
Efficiency: N/A  
Efficacy: 122.5 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 56.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332324-940

CATALOG NUMBER: S123RDIP-S775D1195U940-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P332324-940

CATALOG NUMBER: S123RDIP-S775D1195U940-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	96	92	88	85	87	84	80	78	68	66	64	54	53	52	41	40	40	34
2	88	81	75	70	79	74	69	64	60	57	54	48	46	44	37	35	34	29
3	80	71	64	59	73	65	59	54	54	49	46	43	40	38	33	31	30	25
4	73	63	56	50	67	58	51	46	48	43	39	39	35	32	30	28	26	22
5	68	56	49	43	61	52	45	40	43	38	34	35	31	28	27	25	23	19
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	25	22	20	17
7	58	46	38	33	52	42	35	31	35	30	26	29	25	22	23	20	18	15
8	53	42	34	29	49	38	32	27	32	27	24	26	23	20	21	18	16	14
9	50	38	31	26	45	35	29	24	30	25	21	24	21	18	19	17	15	13
10	46	35	28	23	42	32	26	22	27	22	19	22	19	16	18	15	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	11739	11739	11739	11739
5°	13993	11788	10381	11788
10°	17472	11721	9379	11721
15°	20508	11602	8553	11602
20°	22888	11423	7851	11423
25°	22523	11233	7418	11233
30°	16189	11059	6975	11059
35°	10809	10834	6687	10834
40°	7964	10561	6389	10561
45°	6680	10085	6098	10085
50°	5894	9460	5690	9460
55°	5168	8743	5134	8743
60°	4603	8060	4704	8060
65°	4042	7325	4376	7325
70°	3175	6672	3997	6672
75°	2795	5827	3647	5827
80°	2430	4947	3589	4947
85°	1964	3977	3816	3977



TEST NUMBER: P332324-940

CATALOG NUMBER: S123RDIP-S775D1195U940-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	107.2	1.5
10°-20°	335.1	4.8
20°-30°	526.4	7.6
30°-40°	549.2	7.9
40°-50°	470.0	6.7
50°-60°	358.2	5.1
60°-70°	229.6	3.3
70°-80°	110.5	1.6
80°-90°	33.1	0.5
90°-100°	50.7	0.7
100°-110°	241.6	3.5
110°-120°	580.4	8.3
120°-130°	739.1	10.6
130°-140°	789.7	11.3
140°-150°	738.4	10.6
150°-160°	595.6	8.5
160°-170°	384.4	5.5
170°-180°	132.5	1.9
0°-30°	968.7	13.9
0°-40°	1517.9	21.8
0°-60°	2346.1	33.7
0°-90°	2719.3	39.0
90°-120°	872.7	12.5
90°-150°	3139.9	45.0
90°-180°	4252.0	61.0
0°-180°	6971.7	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1091	1091	1091	1091	1091	
5°	1295	1091	961	1091	1295	134
15°	1840	1041	768	1041	1840	522
25°	1896	946	625	946	1896	815
35°	823	824	509	824	823	539
45°	439	662	401	662	439	345
55°	275	466	274	466	275	249
65°	159	288	172	288	159	156
75°	67	140	88	140	67	72
85°	16	32	31	32	16	19
90°	31	1	31	1	31	15
95°	39	63	39	63	39	33
105°	46	309	46	309	46	104
115°	609	579	609	579	609	563
125°	833	816	833	816	833	744
135°	1027	1016	1027	1016	1027	792
145°	1184	1173	1184	1173	1184	739
155°	1290	1292	1290	1292	1290	595
165°	1359	1362	1359	1362	1359	384
175°	1389	1394	1389	1394	1389	132
180°	1394	1394	1394	1394	1394	



TEST NUMBER: P332324-940

CATALOG NUMBER: S123RDIP-S775D1195U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6
2.5°	1161.5	1163.1	1158.2	1157.4	1151.8	1150.3	1150.3	1142.5	1137.6	1131.3	1127.6
5°	1295.0	1302.5	1298.8	1290.4	1276.4	1273.1	1264.3	1250.3	1234.4	1214.8	1205.4
7.5°	1461.8	1472.0	1468.1	1455.1	1440.5	1428.6	1403.6	1380.3	1347.7	1319.1	1294.7
10°	1598.5	1587.8	1579.4	1566.7	1553.3	1531.2	1505.1	1469.2	1427.6	1395.0	1358.5
12.5°	1700.8	1699.1	1688.5	1675.4	1656.4	1635.5	1603.4	1559.6	1511.3	1464.1	1422.5
15°	1840.3	1843.2	1836.1	1822.6	1795.5	1758.6	1710.1	1691.8	1622.8	1571.5	1520.1
17.5°	1936.9	1936.4	1935.4	1916.6	1889.0	1862.8	1817.8	1769.9	1707.3	1635.0	1565.8
20°	1998.1	1993.5	1994.4	1973.4	1952.8	1922.5	1878.7	1809.1	1757.7	1674.2	1602.7
22.5°	1996.6	1995.7	1999.3	1992.1	1977.1	1953.9	1919.3	1860.6	1795.1	1710.7	1630.3
25°	1896.4	1892.7	1914.6	1920.7	1944.5	1948.7	1938.4	1906.2	1844.1	1757.2	1657.8
27.5°	1587.2	1585.1	1625.8	1676.8	1741.3	1791.6	1840.1	1863.6	1844.1	1781.9	1682.3
30°	1302.5	1346.4	1367.0	1440.7	1522.9	1621.0	1706.8	1788.5	1808.6	1781.5	1699.8
32.5°	1081.5	1119.7	1136.8	1200.2	1276.8	1391.6	1520.5	1636.1	1717.9	1738.6	1689.3
35°	822.6	823.0	862.3	890.3	961.3	1079.3	1204.5	1359.5	1513.5	1630.2	1642.4
37.5°	656.4	658.7	682.4	710.3	763.6	826.1	936.2	1065.1	1243.0	1422.2	1527.2
40°	566.8	571.0	588.7	616.3	654.5	701.7	787.6	909.0	1057.4	1256.8	1419.7
42.5°	509.3	516.0	525.2	546.4	570.2	614.3	683.8	777.5	912.5	1101.0	1289.0
45°	438.8	442.6	449.6	459.4	480.9	511.7	558.4	621.3	733.4	885.2	1073.3
47.5°	387.1	385.1	392.5	400.5	414.7	435.8	467.1	518.5	598.4	720.1	879.8
50°	352.0	351.5	356.7	362.7	376.3	391.7	417.4	456.1	519.6	620.5	766.6
52.5°	319.1	320.9	324.6	332.2	341.9	354.4	377.4	405.3	459.9	546.9	668.7
55°	275.4	276.9	282.0	286.1	293.2	305.8	320.3	343.6	380.9	441.7	542.0
57.5°	238.4	237.8	242.7	243.8	251.7	262.0	273.2	291.3	318.4	363.5	431.1
60°	213.8	212.4	216.6	219.9	224.1	232.5	241.8	259.6	281.1	314.1	372.1
62.5°	191.5	190.7	193.9	197.1	200.5	208.2	216.1	229.7	246.6	274.6	320.6
65°	158.7	160.2	161.5	162.9	164.8	169.4	176.9	186.3	198.0	217.6	250.7
67.5°	124.8	126.2	126.6	129.5	133.5	136.4	141.0	149.3	157.4	174.0	192.8
70°	100.9	100.4	100.9	102.3	107.4	112.5	118.6	124.7	129.7	141.4	157.3
72.5°	86.7	85.8	87.0	87.3	89.8	91.2	95.1	100.8	107.4	115.3	126.7
75°	67.2	67.2	67.2	67.2	69.1	70.0	71.4	72.9	75.2	78.9	87.3
77.5°	49.7	49.8	50.4	50.9	51.3	51.8	52.7	54.0	54.9	56.9	60.5
80°	39.2	39.7	39.2	39.7	39.7	40.6	41.1	42.4	43.0	45.3	46.7
82.5°	29.5	29.2	29.5	30.0	30.0	30.9	31.0	32.0	32.1	33.3	34.8
85°	15.9	15.0	15.9	15.4	16.3	15.4	15.9	16.8	16.8	17.3	19.2
87.5°	10.0	10.6	9.8	10.1	10.0	10.2	10.0	9.8	10.3	9.8	9.6
90°	31.1	30.6	30.1	29.7	29.2	28.5	27.6	26.7	25.8	24.9	21.8
92.5°	34.4	34.2	33.9	33.5	33.3	32.5	30.9	29.4	28.0	26.5	24.3
95°	39.3	39.3	39.3	39.3	39.3	38.5	36.9	35.3	33.7	32.1	29.6
97.5°	42.7	42.4	42.3	42.0	41.7	40.8	38.9	37.0	35.2	33.3	49.9
100°	43.5	43.2	43.1	42.8	42.6	41.6	39.7	37.9	36.0	34.2	70.1
102.5°	44.3	44.0	43.5	43.1	42.7	45.3	51.0	56.7	62.4	68.1	107.4
105°	45.6	45.1	44.7	44.2	43.8	63.8	104.6	145.3	186.1	226.9	247.6
107.5°	143.2	173.9	204.6	235.3	266.0	296.3	326.2	356.1	385.9	415.9	412.6
110°	284.9	317.8	350.7	383.7	416.6	436.8	444.4	452.0	459.7	467.3	464.7



TEST NUMBER: P332324-940

CATALOG NUMBER: S123RDIP-S775D1195U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	488.7	495.7	502.7	509.6	516.6	520.0	519.9	519.7	519.6	519.4	516.9
115°	609.1	608.2	607.3	606.4	605.5	603.9	601.5	599.2	597.0	594.7	592.6
117.5°	676.7	676.5	676.4	676.2	676.0	674.9	673.2	671.3	669.4	667.6	666.6
120°	723.1	723.1	723.1	723.1	723.1	722.2	720.3	718.5	716.7	714.8	714.2
122.5°	768.7	768.6	768.3	768.1	767.9	767.2	766.0	764.6	763.4	762.1	761.2
125°	832.9	832.5	832.1	831.5	831.1	830.6	830.2	829.7	829.3	828.8	827.9
127.5°	894.7	895.2	895.6	896.1	896.5	896.3	895.6	894.9	894.2	893.4	892.3
130°	934.5	935.0	935.4	935.9	936.3	936.1	935.1	934.2	933.4	932.4	931.5
132.5°	970.9	971.6	972.2	972.9	973.5	973.4	972.5	971.5	970.6	969.7	968.9
135°	1026.7	1027.3	1028.1	1028.8	1029.5	1029.5	1028.8	1028.1	1027.3	1026.7	1025.7
137.5°	1079.1	1079.6	1080.0	1080.5	1080.9	1080.6	1079.5	1078.4	1077.3	1076.2	1075.7
140°	1110.6	1111.1	1111.5	1112.0	1112.4	1112.2	1111.3	1110.4	1109.5	1108.5	1107.9
142.5°	1139.6	1140.2	1140.9	1141.6	1142.2	1142.1	1141.4	1140.7	1140.0	1139.2	1138.5
145°	1184.1	1184.1	1184.1	1184.1	1184.1	1183.9	1183.5	1183.0	1182.5	1182.1	1181.6
147.5°	1217.3	1218.3	1219.4	1220.5	1221.6	1221.8	1221.4	1220.9	1220.5	1219.9	1219.5
150°	1242.2	1242.9	1243.6	1244.2	1244.9	1245.0	1244.6	1244.1	1243.7	1243.2	1242.8
152.5°	1262.0	1263.1	1264.2	1265.2	1266.3	1266.4	1265.6	1264.7	1263.9	1263.1	1262.8
155°	1289.9	1291.2	1292.6	1294.0	1295.3	1295.5	1294.3	1293.2	1292.0	1290.8	1290.7
157.5°	1313.2	1315.0	1316.8	1318.7	1320.4	1320.6	1319.2	1317.9	1316.5	1315.1	1315.4
160°	1328.1	1329.7	1331.4	1333.0	1334.6	1334.7	1333.3	1331.9	1330.6	1329.2	1329.5
162.5°	1342.2	1343.6	1345.1	1346.5	1347.9	1347.9	1346.3	1344.8	1343.2	1341.6	1341.8
165°	1359.2	1360.8	1362.4	1364.1	1365.7	1365.6	1363.7	1361.9	1360.0	1358.2	1358.4
167.5°	1371.5	1373.3	1375.1	1377.0	1378.9	1378.9	1377.0	1375.1	1373.3	1371.5	1371.5
170°	1378.9	1380.7	1382.6	1384.5	1386.3	1386.3	1384.5	1382.6	1380.7	1378.9	1378.9
172.5°	1383.0	1385.1	1387.1	1389.1	1391.2	1391.2	1389.4	1387.6	1385.7	1383.8	1383.7
175°	1389.3	1391.2	1392.9	1394.8	1396.6	1396.8	1395.2	1393.6	1392.0	1390.3	1390.1
177.5°	1391.2	1392.9	1394.8	1396.7	1398.5	1398.6	1397.2	1395.7	1394.3	1392.8	1392.6
180°	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5



TEST NUMBER: P332324-940

CATALOG NUMBER: S123RDIP-S775D1195U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6
2.5°	1126.1	1124.9	1119.7	1113.7	1105.9	1100.6	1096.5	1094.3	1087.6	1079.3	1073.8
5°	1195.6	1181.6	1166.7	1148.4	1131.7	1114.4	1103.7	1091.0	1075.7	1058.4	1046.2
7.5°	1270.2	1242.7	1213.1	1182.6	1152.4	1125.3	1101.4	1080.9	1056.4	1031.6	1014.3
10°	1327.3	1287.1	1245.5	1203.1	1164.3	1127.9	1099.9	1072.4	1042.9	1014.5	993.0
12.5°	1379.2	1326.3	1278.4	1226.3	1176.7	1133.2	1092.8	1060.4	1025.0	994.7	970.2
15°	1444.9	1390.8	1332.8	1253.5	1187.7	1132.6	1083.6	1041.1	998.2	960.8	937.0
17.5°	1506.4	1424.9	1347.1	1280.9	1195.3	1126.5	1066.7	1015.8	968.8	929.2	899.8
20°	1531.8	1452.9	1368.3	1283.9	1199.8	1122.8	1053.2	997.2	948.2	903.4	876.3
22.5°	1547.0	1457.7	1368.7	1277.9	1188.7	1108.6	1039.8	978.1	925.1	882.4	849.0
25°	1564.9	1458.5	1360.4	1270.8	1179.7	1092.9	1011.2	945.8	888.4	843.1	807.6
27.5°	1576.6	1451.4	1335.6	1235.9	1143.6	1057.1	982.2	913.0	854.7	806.8	768.7
30°	1578.9	1445.8	1316.5	1208.7	1114.8	1035.5	956.1	889.8	828.2	777.3	741.8
32.5°	1581.9	1432.0	1290.8	1176.2	1080.1	1001.5	929.6	866.3	803.2	753.0	716.8
35°	1569.6	1424.4	1251.6	1120.0	1023.8	947.7	882.8	824.5	762.4	713.8	676.9
37.5°	1516.5	1394.0	1211.1	1056.7	956.1	885.6	832.8	781.9	725.0	672.5	637.8
40°	1463.1	1364.1	1179.7	1018.2	913.2	840.8	793.2	751.6	696.5	647.6	610.2
42.5°	1383.6	1323.5	1149.9	977.9	864.6	794.9	754.7	715.8	667.4	617.7	582.6
45°	1237.6	1245.5	1088.7	913.6	797.4	727.4	689.6	662.5	619.6	578.5	542.5
47.5°	1054.6	1128.8	1016.9	845.2	726.5	660.8	627.8	604.1	575.2	534.8	502.0
50°	935.1	1041.1	959.4	799.2	682.1	616.7	584.1	564.9	539.7	507.9	476.6
52.5°	824.9	938.8	889.9	748.1	633.9	574.2	542.2	526.5	506.4	476.5	448.3
55°	672.7	788.1	776.9	670.8	561.6	507.9	483.7	465.9	452.4	430.0	407.6
57.5°	544.2	653.5	659.3	585.0	497.9	444.9	424.0	410.6	401.8	384.9	364.2
60°	463.2	563.5	583.1	527.1	452.4	405.7	385.1	374.4	367.4	353.9	338.0
62.5°	395.9	481.3	503.5	463.2	408.7	365.0	348.9	338.6	333.8	322.1	308.1
65°	303.0	374.0	395.4	373.0	344.6	309.5	296.5	287.6	283.4	276.9	266.5
67.5°	227.8	279.6	303.1	287.3	277.1	254.9	246.6	241.8	238.1	233.6	225.1
70°	183.0	221.3	245.6	241.4	233.0	221.3	215.3	212.0	208.2	204.5	197.0
72.5°	147.1	173.5	196.3	198.4	191.5	189.1	183.9	182.4	180.2	175.8	171.7
75°	97.6	115.7	131.6	137.7	140.5	142.9	140.5	140.1	139.6	135.9	133.5
77.5°	63.9	73.7	83.7	94.1	98.5	101.7	102.5	104.2	102.9	100.9	99.8
80°	49.0	51.4	58.3	67.2	74.2	77.0	78.9	79.8	79.4	78.9	77.0
82.5°	35.6	37.5	40.8	47.1	53.0	57.6	58.8	58.6	59.6	59.8	58.3
85°	19.2	19.6	20.5	21.5	24.7	29.9	31.3	32.2	33.2	33.2	30.3
87.5°	9.7	8.7	8.9	8.4	9.1	9.0	10.8	12.1	13.0	11.9	12.4
90°	18.9	15.9	12.9	10.3	7.9	5.6	3.3	1.1	3.3	5.6	7.9
92.5°	22.0	19.8	17.5	16.7	17.3	18.0	18.6	19.3	18.6	18.0	17.3
95°	27.0	24.5	22.0	25.4	34.9	44.3	53.8	63.2	53.8	44.3	34.9
97.5°	66.5	83.1	99.7	110.0	114.3	118.5	122.8	127.0	122.8	118.5	114.3
100°	106.0	142.0	177.8	193.5	188.9	184.3	179.7	175.0	179.7	184.3	188.9
102.5°	146.6	185.8	225.1	243.1	239.7	236.4	233.1	229.8	233.1	236.4	239.7
105°	268.3	289.0	309.8	318.9	316.3	313.8	311.3	308.7	311.3	313.8	316.3
107.5°	409.3	406.1	402.8	400.1	398.1	396.1	394.0	392.0	394.0	396.1	398.1
110°	462.2	459.7	457.1	455.0	453.1	451.2	449.4	447.5	449.4	451.2	453.1





TEST NUMBER: P332324-940

CATALOG NUMBER: S123RDIP-S775D1195U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	514.4	511.8	509.3	507.2	505.6	503.9	502.2	500.6	502.2	503.9	505.6
115°	590.5	588.4	586.4	584.6	583.3	581.8	580.5	579.2	580.5	581.8	583.3
117.5°	665.5	664.4	663.3	662.0	660.3	658.5	656.8	655.1	656.8	658.5	660.3
120°	713.5	712.7	712.1	710.7	708.6	706.6	704.5	702.4	704.5	706.6	708.6
122.5°	760.4	759.5	758.6	757.3	755.5	753.9	752.2	750.5	752.2	753.9	755.5
125°	827.0	826.0	825.1	823.8	821.9	820.0	818.2	816.4	818.2	820.0	821.9
127.5°	891.3	890.1	889.0	887.5	885.7	883.9	882.0	880.2	882.0	883.9	885.7
130°	930.6	929.6	928.7	927.3	925.5	923.6	921.9	920.0	921.9	923.6	925.5
132.5°	968.2	967.5	966.7	965.5	963.6	961.8	959.9	958.1	959.9	961.8	963.6
135°	1024.8	1024.0	1023.0	1021.8	1020.5	1019.0	1017.7	1016.3	1017.7	1019.0	1020.5
137.5°	1075.2	1074.7	1074.2	1073.1	1071.3	1069.5	1067.8	1066.0	1067.8	1069.5	1071.3
140°	1107.1	1106.4	1105.7	1104.7	1103.3	1102.0	1100.5	1099.2	1100.5	1102.0	1103.3
142.5°	1137.8	1137.1	1136.4	1135.4	1134.0	1132.7	1131.2	1129.9	1131.2	1132.7	1134.0
145°	1181.2	1180.7	1180.3	1179.2	1177.6	1176.0	1174.4	1172.8	1174.4	1176.0	1177.6
147.5°	1219.1	1218.6	1218.2	1217.4	1216.3	1215.3	1214.2	1213.2	1214.2	1215.3	1216.3
150°	1242.2	1241.8	1241.4	1240.8	1240.1	1239.4	1238.7	1238.1	1238.7	1239.4	1240.1
152.5°	1262.6	1262.2	1261.9	1261.7	1261.3	1261.1	1260.7	1260.4	1260.7	1261.1	1261.3
155°	1290.4	1290.1	1289.9	1290.0	1290.5	1290.9	1291.5	1291.9	1291.5	1290.9	1290.5
157.5°	1315.5	1315.8	1316.0	1316.2	1316.2	1316.3	1316.3	1316.3	1316.3	1316.3	1316.2
160°	1329.6	1329.9	1330.1	1330.3	1330.6	1330.8	1331.1	1331.2	1331.1	1330.8	1330.6
162.5°	1342.1	1342.3	1342.6	1342.9	1343.5	1344.2	1344.8	1345.3	1344.8	1344.2	1343.5
165°	1358.6	1358.9	1359.1	1359.6	1360.3	1360.9	1361.6	1362.4	1361.6	1360.9	1360.3
167.5°	1371.5	1371.5	1371.5	1371.9	1372.9	1373.8	1374.7	1375.6	1374.7	1373.8	1372.9
170°	1378.9	1378.9	1378.9	1379.4	1380.3	1381.3	1382.2	1383.0	1382.2	1381.3	1380.3
172.5°	1383.5	1383.3	1383.1	1383.6	1384.7	1385.8	1387.0	1388.0	1387.0	1385.8	1384.7
175°	1389.8	1389.6	1389.4	1389.8	1391.0	1392.1	1393.3	1394.5	1393.3	1392.1	1391.0
177.5°	1392.4	1392.2	1392.0	1392.4	1393.4	1394.3	1395.2	1396.2	1395.2	1394.3	1393.4
180°	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5



TEST NUMBER: P332324-940

CATALOG NUMBER: S123RDIP-S775D1195U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6
2.5°	1071.9	1067.0	1063.7	1056.2	1051.3	1046.2	1040.9	1044.3	1043.9	1043.5	1043.5
5°	1036.0	1025.2	1015.4	1002.8	994.9	985.1	977.6	976.7	978.6	972.0	968.2
7.5°	1000.3	985.6	971.7	957.8	943.1	931.3	923.9	920.4	915.7	911.7	907.5
10°	975.3	958.0	944.4	927.2	911.3	897.3	888.4	882.3	879.0	875.8	869.8
12.5°	949.5	932.6	915.3	895.8	880.7	864.4	857.8	851.0	844.7	841.1	832.8
15°	911.8	889.8	871.6	851.0	834.3	818.4	809.0	795.5	793.6	789.0	780.6
17.5°	874.0	850.2	825.0	809.9	790.9	774.4	760.1	755.5	742.2	737.2	729.9
20°	844.1	822.2	803.0	782.9	755.4	739.9	728.8	722.7	711.9	705.4	700.7
22.5°	818.3	796.0	773.8	750.5	727.7	710.4	702.2	692.8	687.0	677.8	672.7
25°	781.5	757.2	730.7	705.4	689.1	676.0	662.9	654.5	646.1	641.9	632.6
27.5°	738.8	713.4	688.5	669.4	649.3	636.4	624.6	617.1	607.0	599.9	594.8
30°	715.2	685.4	663.9	646.6	620.9	608.8	599.9	590.6	583.1	575.6	570.5
32.5°	688.0	660.7	640.3	618.9	599.2	586.0	574.5	566.3	559.9	552.9	547.7
35°	645.2	622.3	601.3	579.8	565.3	551.8	538.3	531.3	525.2	518.7	514.0
37.5°	606.5	585.1	565.2	544.8	526.9	515.9	505.0	499.6	491.4	487.1	482.2
40°	582.6	561.6	540.1	520.6	501.9	493.5	483.7	475.7	468.2	465.0	459.9
42.5°	556.5	535.5	517.4	496.2	481.0	469.6	460.5	451.8	446.2	441.5	438.5
45°	517.7	499.1	481.3	460.3	445.9	436.0	425.8	417.9	412.7	409.5	404.3
47.5°	480.1	461.5	443.4	425.1	411.1	399.9	389.7	384.1	377.3	373.3	369.9
50°	452.8	436.0	416.9	400.1	386.1	374.9	366.5	359.4	353.4	348.3	346.0
52.5°	427.8	409.9	393.3	377.7	362.9	350.3	342.6	335.2	330.6	324.8	322.0
55°	386.6	369.3	355.3	339.8	325.4	314.7	305.3	298.8	294.1	287.6	283.8
57.5°	347.8	332.3	315.6	302.2	287.3	278.2	270.5	261.6	255.9	250.8	247.2
60°	321.6	303.9	289.4	276.9	263.8	252.1	245.1	238.1	232.0	226.9	223.6
62.5°	294.4	278.9	265.2	251.5	239.5	229.3	221.2	215.3	210.0	206.7	203.5
65°	252.5	240.4	226.4	215.3	204.0	196.5	190.0	184.9	181.1	178.8	176.0
67.5°	214.1	202.3	190.1	179.1	171.7	165.9	161.7	157.2	155.3	152.4	150.5
70°	189.0	176.9	166.2	157.8	150.3	146.2	143.3	140.1	138.2	134.5	132.6
72.5°	161.8	153.0	145.3	138.4	132.4	128.6	125.0	121.0	118.1	113.9	112.1
75°	127.4	119.5	113.4	108.8	105.0	99.9	94.8	90.6	89.2	87.7	87.3
77.5°	94.4	89.3	85.0	81.1	76.4	72.7	71.5	70.6	70.3	69.6	69.6
80°	74.2	69.6	66.3	61.6	58.9	58.9	58.9	57.9	58.3	58.3	58.3
82.5°	55.2	50.9	49.1	47.4	46.9	47.3	47.3	47.4	47.2	47.9	47.5
85°	28.4	29.0	29.9	29.4	29.9	29.9	30.9	30.3	30.9	29.9	30.9
87.5°	12.5	14.2	15.2	16.1	17.0	17.3	17.8	18.0	18.6	18.8	18.9
90°	10.3	12.9	15.9	18.9	21.8	24.9	25.8	26.7	27.6	28.5	29.2
92.5°	16.7	17.5	19.8	22.0	24.3	26.5	28.0	29.4	30.9	32.5	33.3
95°	25.4	22.0	24.5	27.0	29.6	32.1	33.7	35.3	36.9	38.5	39.3
97.5°	110.0	99.7	83.1	66.5	49.9	33.3	35.2	37.0	38.9	40.8	41.7
100°	193.5	177.8	142.0	106.0	70.1	34.2	36.0	37.9	39.7	41.6	42.6
102.5°	243.1	225.1	185.8	146.6	107.4	68.1	62.4	56.7	51.0	45.3	42.7
105°	318.9	309.8	289.0	268.3	247.6	226.9	186.1	145.3	104.6	63.8	43.8
107.5°	400.1	402.8	406.1	409.3	412.6	415.9	385.9	356.1	326.2	296.3	266.0
110°	455.0	457.1	459.7	462.2	464.7	467.3	459.7	452.0	444.4	436.8	416.6



TEST NUMBER: P332324-940

CATALOG NUMBER: S123RDIP-S775D1195U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	507.2	509.3	511.8	514.4	516.9	519.4	519.6	519.7	519.9	520.0	516.6
115°	584.6	586.4	588.4	590.5	592.6	594.7	597.0	599.2	601.5	603.9	605.5
117.5°	662.0	663.3	664.4	665.5	666.6	667.6	669.4	671.3	673.2	674.9	676.0
120°	710.7	712.1	712.7	713.5	714.2	714.8	716.7	718.5	720.3	722.2	723.1
122.5°	757.3	758.6	759.5	760.4	761.2	762.1	763.4	764.6	766.0	767.2	767.9
125°	823.8	825.1	826.0	827.0	827.9	828.8	829.3	829.7	830.2	830.6	831.1
127.5°	887.5	889.0	890.1	891.3	892.3	893.4	894.2	894.9	895.6	896.3	896.5
130°	927.3	928.7	929.6	930.6	931.5	932.4	933.4	934.2	935.1	936.1	936.3
132.5°	965.5	966.7	967.5	968.2	968.9	969.7	970.6	971.5	972.5	973.4	973.5
135°	1021.8	1023.0	1024.0	1024.8	1025.7	1026.7	1027.3	1028.1	1028.8	1029.5	1029.5
137.5°	1073.1	1074.2	1074.7	1075.2	1075.7	1076.2	1077.3	1078.4	1079.5	1080.6	1080.9
140°	1104.7	1105.7	1106.4	1107.1	1107.9	1108.5	1109.5	1110.4	1111.3	1112.2	1112.4
142.5°	1135.4	1136.4	1137.1	1137.8	1138.5	1139.2	1140.0	1140.7	1141.4	1142.1	1142.2
145°	1179.2	1180.3	1180.7	1181.2	1181.6	1182.1	1182.5	1183.0	1183.5	1183.9	1184.1
147.5°	1217.4	1218.2	1218.6	1219.1	1219.5	1219.9	1220.5	1220.9	1221.4	1221.8	1221.6
150°	1240.8	1241.4	1241.8	1242.2	1242.8	1243.2	1243.7	1244.1	1244.6	1245.0	1244.9
152.5°	1261.7	1261.9	1262.2	1262.6	1262.8	1263.1	1263.9	1264.7	1265.6	1266.4	1266.3
155°	1290.0	1289.9	1290.1	1290.4	1290.7	1290.8	1292.0	1293.2	1294.3	1295.5	1295.3
157.5°	1316.2	1316.0	1315.8	1315.5	1315.4	1315.1	1316.5	1317.9	1319.2	1320.6	1320.4
160°	1330.3	1330.1	1329.9	1329.6	1329.5	1329.2	1330.6	1331.9	1333.3	1334.7	1334.6
162.5°	1342.9	1342.6	1342.3	1342.1	1341.8	1341.6	1343.2	1344.8	1346.3	1347.9	1347.9
165°	1359.6	1359.1	1358.9	1358.6	1358.4	1358.2	1360.0	1361.9	1363.7	1365.6	1365.7
167.5°	1371.9	1371.5	1371.5	1371.5	1371.5	1371.5	1373.3	1375.1	1377.0	1378.9	1378.9
170°	1379.4	1378.9	1378.9	1378.9	1378.9	1378.9	1380.7	1382.6	1384.5	1386.3	1386.3
172.5°	1383.6	1383.1	1383.3	1383.5	1383.7	1383.8	1385.7	1387.6	1389.4	1391.2	1391.2
175°	1389.8	1389.4	1389.6	1389.8	1390.1	1390.3	1392.0	1393.6	1395.2	1396.8	1396.6
177.5°	1392.4	1392.0	1392.2	1392.4	1392.6	1392.8	1394.3	1395.7	1397.2	1398.6	1398.5
180°	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5



TEST NUMBER: P332324-940

CATALOG NUMBER: S123RDIP-S775D1195U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6
2.5°	1039.0	1038.7	1039.0	1037.5	1039.0	1038.7	1039.0	1043.5	1043.5	1043.9	1044.3
5°	966.9	966.3	965.0	960.8	965.0	966.3	966.9	968.2	972.0	978.6	976.7
7.5°	903.8	903.2	899.1	899.2	899.1	903.2	903.8	907.5	911.7	915.7	920.4
10°	866.5	866.9	861.4	858.1	861.4	866.9	866.5	869.8	875.8	879.0	882.3
12.5°	830.3	828.1	823.6	820.0	823.6	828.1	830.3	832.8	841.1	844.7	851.0
15°	782.5	777.8	766.6	767.5	766.6	777.8	782.5	780.6	789.0	793.6	795.5
17.5°	726.1	722.7	722.5	716.0	722.5	722.7	726.1	729.9	737.2	742.2	755.5
20°	693.3	691.0	691.9	685.4	691.9	691.0	693.3	700.7	705.4	711.9	722.7
22.5°	667.5	665.2	661.3	659.2	661.3	665.2	667.5	672.7	677.8	687.0	692.8
25°	629.8	626.1	622.3	624.6	622.3	626.1	629.8	632.6	641.9	646.1	654.5
27.5°	592.1	589.2	585.5	585.1	585.5	589.2	592.1	594.8	599.9	607.0	617.1
30°	568.2	565.3	563.5	561.2	563.5	565.3	568.2	570.5	575.6	583.1	590.6
32.5°	543.9	543.3	539.9	539.5	539.9	543.3	543.9	547.7	552.9	559.9	566.3
35°	512.1	509.3	508.4	508.9	508.4	509.3	512.1	514.0	518.7	525.2	531.3
37.5°	482.0	478.2	476.5	474.9	476.5	478.2	482.0	482.2	487.1	491.4	499.6
40°	460.3	456.6	455.7	454.7	455.7	456.6	460.3	459.9	465.0	468.2	475.7
42.5°	436.0	434.5	434.0	432.3	434.0	434.5	436.0	438.5	441.5	446.2	451.8
45°	402.9	402.4	399.7	400.6	399.7	402.4	402.9	404.3	409.5	412.7	417.9
47.5°	368.0	366.0	364.0	365.2	364.0	366.0	368.0	369.9	373.3	377.3	384.1
50°	344.1	343.1	338.9	339.8	338.9	343.1	344.1	346.0	348.3	353.4	359.4
52.5°	320.2	316.6	315.0	314.5	315.0	316.6	320.2	322.0	324.8	330.6	335.2
55°	280.6	276.3	274.5	273.6	274.5	276.3	280.6	283.8	287.6	294.1	298.8
57.5°	241.7	240.6	239.2	240.1	239.2	240.6	241.7	247.2	250.8	255.9	261.6
60°	218.9	218.9	218.9	218.5	218.9	218.9	218.9	223.6	226.9	232.0	238.1
62.5°	201.4	200.3	199.9	200.5	199.9	200.3	201.4	203.5	206.7	210.0	215.3
65°	174.6	174.2	172.3	171.8	172.3	174.2	174.6	176.0	178.8	181.1	184.9
67.5°	149.3	147.6	147.0	146.4	147.0	147.6	149.3	150.5	152.4	155.3	157.2
70°	130.3	129.3	126.5	127.0	126.5	129.3	130.3	132.6	134.5	138.2	140.1
72.5°	109.7	108.8	108.3	107.5	108.3	108.8	109.7	112.1	113.9	118.1	121.0
75°	86.9	86.4	85.9	87.7	85.9	86.4	86.9	87.3	87.7	89.2	90.6
77.5°	69.6	69.6	69.8	69.1	69.8	69.6	69.6	69.6	69.6	70.3	70.6
80°	58.3	58.3	57.9	57.9	57.9	58.3	58.3	58.3	58.3	58.3	57.9
82.5°	46.8	47.2	47.4	46.7	47.4	47.2	46.8	47.5	47.9	47.2	47.4
85°	30.9	30.3	31.3	30.9	31.3	30.3	30.9	30.9	29.9	30.9	30.3
87.5°	19.8	19.1	19.2	19.6	19.2	19.1	19.8	18.9	18.8	18.6	18.0
90°	29.7	30.1	30.6	31.1	30.6	30.1	29.7	29.2	28.5	27.6	26.7
92.5°	33.5	33.9	34.2	34.4	34.2	33.9	33.5	33.3	32.5	30.9	29.4
95°	39.3	39.3	39.3	39.3	39.3	39.3	39.3	39.3	38.5	36.9	35.3
97.5°	42.0	42.3	42.4	42.7	42.4	42.3	42.0	41.7	40.8	38.9	37.0
100°	42.8	43.1	43.2	43.5	43.2	43.1	42.8	42.6	41.6	39.7	37.9
102.5°	43.1	43.5	44.0	44.3	44.0	43.5	43.1	42.7	45.3	51.0	56.7
105°	44.2	44.7	45.1	45.6	45.1	44.7	44.2	43.8	63.8	104.6	145.3
107.5°	235.3	204.6	173.9	143.2	173.9	204.6	235.3	266.0	296.3	326.2	356.1
110°	383.7	350.7	317.8	284.9	317.8	350.7	383.7	416.6	436.8	444.4	452.0



TEST NUMBER: P332324-940

CATALOG NUMBER: S123RDIP-S775D1195U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	509.6	502.7	495.7	488.7	495.7	502.7	509.6	516.6	520.0	519.9	519.7
115°	606.4	607.3	608.2	609.1	608.2	607.3	606.4	605.5	603.9	601.5	599.2
117.5°	676.2	676.4	676.5	676.7	676.5	676.4	676.2	676.0	674.9	673.2	671.3
120°	723.1	723.1	723.1	723.1	723.1	723.1	723.1	723.1	722.2	720.3	718.5
122.5°	768.1	768.3	768.6	768.7	768.6	768.3	768.1	767.9	767.2	766.0	764.6
125°	831.5	832.1	832.5	832.9	832.5	832.1	831.5	831.1	830.6	830.2	829.7
127.5°	896.1	895.6	895.2	894.7	895.2	895.6	896.1	896.5	896.3	895.6	894.9
130°	935.9	935.4	935.0	934.5	935.0	935.4	935.9	936.3	936.1	935.1	934.2
132.5°	972.9	972.2	971.6	970.9	971.6	972.2	972.9	973.5	973.4	972.5	971.5
135°	1028.8	1028.1	1027.3	1026.7	1027.3	1028.1	1028.8	1029.5	1029.5	1028.8	1028.1
137.5°	1080.5	1080.0	1079.6	1079.1	1079.6	1080.0	1080.5	1080.9	1080.6	1079.5	1078.4
140°	1112.0	1111.5	1111.1	1110.6	1111.1	1111.5	1112.0	1112.4	1112.2	1111.3	1110.4
142.5°	1141.6	1140.9	1140.2	1139.6	1140.2	1140.9	1141.6	1142.2	1142.1	1141.4	1140.7
145°	1184.1	1184.1	1184.1	1184.1	1184.1	1184.1	1184.1	1184.1	1183.9	1183.5	1183.0
147.5°	1220.5	1219.4	1218.3	1217.3	1218.3	1219.4	1220.5	1221.6	1221.8	1221.4	1220.9
150°	1244.2	1243.6	1242.9	1242.2	1242.9	1243.6	1244.2	1244.9	1245.0	1244.6	1244.1
152.5°	1265.2	1264.2	1263.1	1262.0	1263.1	1264.2	1265.2	1266.3	1266.4	1265.6	1264.7
155°	1294.0	1292.6	1291.2	1289.9	1291.2	1292.6	1294.0	1295.3	1295.5	1294.3	1293.2
157.5°	1318.7	1316.8	1315.0	1313.2	1315.0	1316.8	1318.7	1320.4	1320.6	1319.2	1317.9
160°	1333.0	1331.4	1329.7	1328.1	1329.7	1331.4	1333.0	1334.6	1334.7	1333.3	1331.9
162.5°	1346.5	1345.1	1343.6	1342.2	1343.6	1345.1	1346.5	1347.9	1347.9	1346.3	1344.8
165°	1364.1	1362.4	1360.8	1359.2	1360.8	1362.4	1364.1	1365.7	1365.6	1363.7	1361.9
167.5°	1377.0	1375.1	1373.3	1371.5	1373.3	1375.1	1377.0	1378.9	1378.9	1377.0	1375.1
170°	1384.5	1382.6	1380.7	1378.9	1380.7	1382.6	1384.5	1386.3	1386.3	1384.5	1382.6
172.5°	1389.1	1387.1	1385.1	1383.0	1385.1	1387.1	1389.1	1391.2	1391.2	1389.4	1387.6
175°	1394.8	1392.9	1391.2	1389.3	1391.2	1392.9	1394.8	1396.6	1396.8	1395.2	1393.6
177.5°	1396.7	1394.8	1392.9	1391.2	1392.9	1394.8	1396.7	1398.5	1398.6	1397.2	1395.7
180°	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5



TEST NUMBER: P332324-940

CATALOG NUMBER: S123RDIP-S775D1195U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6
2.5°	1040.9	1046.2	1051.3	1056.2	1063.7	1067.0	1071.9	1073.8	1079.3	1087.6	1094.3
5°	977.6	985.1	994.9	1002.8	1015.4	1025.2	1036.0	1046.2	1058.4	1075.7	1091.0
7.5°	923.9	931.3	943.1	957.8	971.7	985.6	1000.3	1014.3	1031.6	1056.4	1080.9
10°	888.4	897.3	911.3	927.2	944.4	958.0	975.3	993.0	1014.5	1042.9	1072.4
12.5°	857.8	864.4	880.7	895.8	915.3	932.6	949.5	970.2	994.7	1025.0	1060.4
15°	809.0	818.4	834.3	851.0	871.6	889.8	911.8	937.0	960.8	998.2	1041.1
17.5°	760.1	774.4	790.9	809.9	825.0	850.2	874.0	899.8	929.2	968.8	1015.8
20°	728.8	739.9	755.4	782.9	803.0	822.2	844.1	876.3	903.4	948.2	997.2
22.5°	702.2	710.4	727.7	750.5	773.8	796.0	818.3	849.0	882.4	925.1	978.1
25°	662.9	676.0	689.1	705.4	730.7	757.2	781.5	807.6	843.1	888.4	945.8
27.5°	624.6	636.4	649.3	669.4	688.5	713.4	738.8	768.7	806.8	854.7	913.0
30°	599.9	608.8	620.9	646.6	663.9	685.4	715.2	741.8	777.3	828.2	889.8
32.5°	574.5	586.0	599.2	618.9	640.3	660.7	688.0	716.8	753.0	803.2	866.3
35°	538.3	551.8	565.3	579.8	601.3	622.3	645.2	676.9	713.8	762.4	824.5
37.5°	505.0	515.9	526.9	544.8	565.2	585.1	606.5	637.8	672.5	725.0	781.9
40°	483.7	493.5	501.9	520.6	540.1	561.6	582.6	610.2	647.6	696.5	751.6
42.5°	460.5	469.6	481.0	496.2	517.4	535.5	556.5	582.6	617.7	667.4	715.8
45°	425.8	436.0	445.9	460.3	481.3	499.1	517.7	542.5	578.5	619.6	662.5
47.5°	389.7	399.9	411.1	425.1	443.4	461.5	480.1	502.0	534.8	575.2	604.1
50°	366.5	374.9	386.1	400.1	416.9	436.0	452.8	476.6	507.9	539.7	564.9
52.5°	342.6	350.3	362.9	377.7	393.3	409.9	427.8	448.3	476.5	506.4	526.5
55°	305.3	314.7	325.4	339.8	355.3	369.3	386.6	407.6	430.0	452.4	465.9
57.5°	270.5	278.2	287.3	302.2	315.6	332.3	347.8	364.2	384.9	401.8	410.6
60°	245.1	252.1	263.8	276.9	289.4	303.9	321.6	338.0	353.9	367.4	374.4
62.5°	221.2	229.3	239.5	251.5	265.2	278.9	294.4	308.1	322.1	333.8	338.6
65°	190.0	196.5	204.0	215.3	226.4	240.4	252.5	266.5	276.9	283.4	287.6
67.5°	161.7	165.9	171.7	179.1	190.1	202.3	214.1	225.1	233.6	238.1	241.8
70°	143.3	146.2	150.3	157.8	166.2	176.9	189.0	197.0	204.5	208.2	212.0
72.5°	125.0	128.6	132.4	138.4	145.3	153.0	161.8	171.7	175.8	180.2	182.4
75°	94.8	99.9	105.0	108.8	113.4	119.5	127.4	133.5	135.9	139.6	140.1
77.5°	71.5	72.7	76.4	81.1	85.0	89.3	94.4	99.8	100.9	102.9	104.2
80°	58.9	58.9	58.9	61.6	66.3	69.6	74.2	77.0	78.9	79.4	79.8
82.5°	47.3	47.3	46.9	47.4	49.1	50.9	55.2	58.3	59.8	59.6	58.6
85°	30.9	29.9	29.9	29.4	29.9	29.0	28.4	30.3	33.2	33.2	32.2
87.5°	17.8	17.3	17.0	16.1	15.2	14.2	12.5	12.4	11.9	13.0	12.1
90°	25.8	24.9	21.8	18.9	15.9	12.9	10.3	7.9	5.6	3.3	1.1
92.5°	28.0	26.5	24.3	22.0	19.8	17.5	16.7	17.3	18.0	18.6	19.3
95°	33.7	32.1	29.6	27.0	24.5	22.0	25.4	34.9	44.3	53.8	63.2
97.5°	35.2	33.3	49.9	66.5	83.1	99.7	110.0	114.3	118.5	122.8	127.0
100°	36.0	34.2	70.1	106.0	142.0	177.8	193.5	188.9	184.3	179.7	175.0
102.5°	62.4	68.1	107.4	146.6	185.8	225.1	243.1	239.7	236.4	233.1	229.8
105°	186.1	226.9	247.6	268.3	289.0	309.8	318.9	316.3	313.8	311.3	308.7
107.5°	385.9	415.9	412.6	409.3	406.1	402.8	400.1	398.1	396.1	394.0	392.0
110°	459.7	467.3	464.7	462.2	459.7	457.1	455.0	453.1	451.2	449.4	447.5



TEST NUMBER: P332324-940

CATALOG NUMBER: S123RDIP-S775D1195U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	519.6	519.4	516.9	514.4	511.8	509.3	507.2	505.6	503.9	502.2	500.6
115°	597.0	594.7	592.6	590.5	588.4	586.4	584.6	583.3	581.8	580.5	579.2
117.5°	669.4	667.6	666.6	665.5	664.4	663.3	662.0	660.3	658.5	656.8	655.1
120°	716.7	714.8	714.2	713.5	712.7	712.1	710.7	708.6	706.6	704.5	702.4
122.5°	763.4	762.1	761.2	760.4	759.5	758.6	757.3	755.5	753.9	752.2	750.5
125°	829.3	828.8	827.9	827.0	826.0	825.1	823.8	821.9	820.0	818.2	816.4
127.5°	894.2	893.4	892.3	891.3	890.1	889.0	887.5	885.7	883.9	882.0	880.2
130°	933.4	932.4	931.5	930.6	929.6	928.7	927.3	925.5	923.6	921.9	920.0
132.5°	970.6	969.7	968.9	968.2	967.5	966.7	965.5	963.6	961.8	959.9	958.1
135°	1027.3	1026.7	1025.7	1024.8	1024.0	1023.0	1021.8	1020.5	1019.0	1017.7	1016.3
137.5°	1077.3	1076.2	1075.7	1075.2	1074.7	1074.2	1073.1	1071.3	1069.5	1067.8	1066.0
140°	1109.5	1108.5	1107.9	1107.1	1106.4	1105.7	1104.7	1103.3	1102.0	1100.5	1099.2
142.5°	1140.0	1139.2	1138.5	1137.8	1137.1	1136.4	1135.4	1134.0	1132.7	1131.2	1129.9
145°	1182.5	1182.1	1181.6	1181.2	1180.7	1180.3	1179.2	1177.6	1176.0	1174.4	1172.8
147.5°	1220.5	1219.9	1219.5	1219.1	1218.6	1218.2	1217.4	1216.3	1215.3	1214.2	1213.2
150°	1243.7	1243.2	1242.8	1242.2	1241.8	1241.4	1240.8	1240.1	1239.4	1238.7	1238.1
152.5°	1263.9	1263.1	1262.8	1262.6	1262.2	1261.9	1261.7	1261.3	1261.1	1260.7	1260.4
155°	1292.0	1290.8	1290.7	1290.4	1290.1	1289.9	1290.0	1290.5	1290.9	1291.5	1291.9
157.5°	1316.5	1315.1	1315.4	1315.5	1315.8	1316.0	1316.2	1316.2	1316.3	1316.3	1316.3
160°	1330.6	1329.2	1329.5	1329.6	1329.9	1330.1	1330.3	1330.6	1330.8	1331.1	1331.2
162.5°	1343.2	1341.6	1341.8	1342.1	1342.3	1342.6	1342.9	1343.5	1344.2	1344.8	1345.3
165°	1360.0	1358.2	1358.4	1358.6	1358.9	1359.1	1359.6	1360.3	1360.9	1361.6	1362.4
167.5°	1373.3	1371.5	1371.5	1371.5	1371.5	1371.5	1371.9	1372.9	1373.8	1374.7	1375.6
170°	1380.7	1378.9	1378.9	1378.9	1378.9	1378.9	1379.4	1380.3	1381.3	1382.2	1383.0
172.5°	1385.7	1383.8	1383.7	1383.5	1383.3	1383.1	1383.6	1384.7	1385.8	1387.0	1388.0
175°	1392.0	1390.3	1390.1	1389.8	1389.6	1389.4	1389.8	1391.0	1392.1	1393.3	1394.5
177.5°	1394.3	1392.8	1392.6	1392.4	1392.2	1392.0	1392.4	1393.4	1394.3	1395.2	1396.2
180°	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5



TEST NUMBER: P332324-940

CATALOG NUMBER: S123RDIP-S775D1195U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6
2.5°	1096.5	1100.6	1105.9	1113.7	1119.7	1124.9	1126.1	1127.6	1131.3	1137.6	1142.5
5°	1103.7	1114.4	1131.7	1148.4	1166.7	1181.6	1195.6	1205.4	1214.8	1234.4	1250.3
7.5°	1101.4	1125.3	1152.4	1182.6	1213.1	1242.7	1270.2	1294.7	1319.1	1347.7	1380.3
10°	1099.9	1127.9	1164.3	1203.1	1245.5	1287.1	1327.3	1358.5	1395.0	1427.6	1469.2
12.5°	1092.8	1133.2	1176.7	1226.3	1278.4	1326.3	1379.2	1422.5	1464.1	1511.3	1559.6
15°	1083.6	1132.6	1187.7	1253.5	1332.8	1390.8	1444.9	1520.1	1571.5	1622.8	1691.8
17.5°	1066.7	1126.5	1195.3	1280.9	1347.1	1424.9	1506.4	1565.8	1635.0	1707.3	1769.9
20°	1053.2	1122.8	1199.8	1283.9	1368.3	1452.9	1531.8	1602.7	1674.2	1757.7	1809.1
22.5°	1039.8	1108.6	1188.7	1277.9	1368.7	1457.7	1547.0	1630.3	1710.7	1795.1	1860.6
25°	1011.2	1092.9	1179.7	1270.8	1360.4	1458.5	1564.9	1657.8	1757.2	1844.1	1906.2
27.5°	982.2	1057.1	1143.6	1235.9	1335.6	1451.4	1576.6	1682.3	1781.9	1844.1	1863.6
30°	956.1	1035.5	1114.8	1208.7	1316.5	1445.8	1578.9	1699.8	1781.5	1808.6	1788.5
32.5°	929.6	1001.5	1080.1	1176.2	1290.8	1432.0	1581.9	1689.3	1738.6	1717.9	1636.1
35°	882.8	947.7	1023.8	1120.0	1251.6	1424.4	1569.6	1642.4	1630.2	1513.5	1359.5
37.5°	832.8	885.6	956.1	1056.7	1211.1	1394.0	1516.5	1527.2	1422.2	1243.0	1065.1
40°	793.2	840.8	913.2	1018.2	1179.7	1364.1	1463.1	1419.7	1256.8	1057.4	909.0
42.5°	754.7	794.9	864.6	977.9	1149.9	1323.5	1383.6	1289.0	1101.0	912.5	777.5
45°	689.6	727.4	797.4	913.6	1088.7	1245.5	1237.6	1073.3	885.2	733.4	621.3
47.5°	627.8	660.8	726.5	845.2	1016.9	1128.8	1054.6	879.8	720.1	598.4	518.5
50°	584.1	616.7	682.1	799.2	959.4	1041.1	935.1	766.6	620.5	519.6	456.1
52.5°	542.2	574.2	633.9	748.1	889.9	938.8	824.9	668.7	546.9	459.9	405.3
55°	483.7	507.9	561.6	670.8	776.9	788.1	672.7	542.0	441.7	380.9	343.6
57.5°	424.0	444.9	497.9	585.0	659.3	653.5	544.2	431.1	363.5	318.4	291.3
60°	385.1	405.7	452.4	527.1	583.1	563.5	463.2	372.1	314.1	281.1	259.6
62.5°	348.9	365.0	408.7	463.2	503.5	481.3	395.9	320.6	274.6	246.6	229.7
65°	296.5	309.5	344.6	373.0	395.4	374.0	303.0	250.7	217.6	198.0	186.3
67.5°	246.6	254.9	277.1	287.3	303.1	279.6	227.8	192.8	174.0	157.4	149.3
70°	215.3	221.3	233.0	241.4	245.6	221.3	183.0	157.3	141.4	129.7	124.7
72.5°	183.9	189.1	191.5	198.4	196.3	173.5	147.1	126.7	115.3	107.4	100.8
75°	140.5	142.9	140.5	137.7	131.6	115.7	97.6	87.3	78.9	75.2	72.9
77.5°	102.5	101.7	98.5	94.1	83.7	73.7	63.9	60.5	56.9	54.9	54.0
80°	78.9	77.0	74.2	67.2	58.3	51.4	49.0	46.7	45.3	43.0	42.4
82.5°	58.8	57.6	53.0	47.1	40.8	37.5	35.6	34.8	33.3	32.1	32.0
85°	31.3	29.9	24.7	21.5	20.5	19.6	19.2	19.2	17.3	16.8	16.8
87.5°	10.8	9.0	9.1	8.4	8.9	8.7	9.7	9.6	9.8	10.3	9.8
90°	3.3	5.6	7.9	10.3	12.9	15.9	18.9	21.8	24.9	25.8	26.7
92.5°	18.6	18.0	17.3	16.7	17.5	19.8	22.0	24.3	26.5	28.0	29.4
95°	53.8	44.3	34.9	25.4	22.0	24.5	27.0	29.6	32.1	33.7	35.3
97.5°	122.8	118.5	114.3	110.0	99.7	83.1	66.5	49.9	33.3	35.2	37.0
100°	179.7	184.3	188.9	193.5	177.8	142.0	106.0	70.1	34.2	36.0	37.9
102.5°	233.1	236.4	239.7	243.1	225.1	185.8	146.6	107.4	68.1	62.4	56.7
105°	311.3	313.8	316.3	318.9	309.8	289.0	268.3	247.6	226.9	186.1	145.3
107.5°	394.0	396.1	398.1	400.1	402.8	406.1	409.3	412.6	415.9	385.9	356.1
110°	449.4	451.2	453.1	455.0	457.1	459.7	462.2	464.7	467.3	459.7	452.0





TEST NUMBER: P332324-940

CATALOG NUMBER: S123RDIP-S775D1195U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	502.2	503.9	505.6	507.2	509.3	511.8	514.4	516.9	519.4	519.6	519.7
115°	580.5	581.8	583.3	584.6	586.4	588.4	590.5	592.6	594.7	597.0	599.2
117.5°	656.8	658.5	660.3	662.0	663.3	664.4	665.5	666.6	667.6	669.4	671.3
120°	704.5	706.6	708.6	710.7	712.1	712.7	713.5	714.2	714.8	716.7	718.5
122.5°	752.2	753.9	755.5	757.3	758.6	759.5	760.4	761.2	762.1	763.4	764.6
125°	818.2	820.0	821.9	823.8	825.1	826.0	827.0	827.9	828.8	829.3	829.7
127.5°	882.0	883.9	885.7	887.5	889.0	890.1	891.3	892.3	893.4	894.2	894.9
130°	921.9	923.6	925.5	927.3	928.7	929.6	930.6	931.5	932.4	933.4	934.2
132.5°	959.9	961.8	963.6	965.5	966.7	967.5	968.2	968.9	969.7	970.6	971.5
135°	1017.7	1019.0	1020.5	1021.8	1023.0	1024.0	1024.8	1025.7	1026.7	1027.3	1028.1
137.5°	1067.8	1069.5	1071.3	1073.1	1074.2	1074.7	1075.2	1075.7	1076.2	1077.3	1078.4
140°	1100.5	1102.0	1103.3	1104.7	1105.7	1106.4	1107.1	1107.9	1108.5	1109.5	1110.4
142.5°	1131.2	1132.7	1134.0	1135.4	1136.4	1137.1	1137.8	1138.5	1139.2	1140.0	1140.7
145°	1174.4	1176.0	1177.6	1179.2	1180.3	1180.7	1181.2	1181.6	1182.1	1182.5	1183.0
147.5°	1214.2	1215.3	1216.3	1217.4	1218.2	1218.6	1219.1	1219.5	1219.9	1220.5	1220.9
150°	1238.7	1239.4	1240.1	1240.8	1241.4	1241.8	1242.2	1242.8	1243.2	1243.7	1244.1
152.5°	1260.7	1261.1	1261.3	1261.7	1261.9	1262.2	1262.6	1262.8	1263.1	1263.9	1264.7
155°	1291.5	1290.9	1290.5	1290.0	1289.9	1290.1	1290.4	1290.7	1290.8	1292.0	1293.2
157.5°	1316.3	1316.3	1316.2	1316.2	1316.0	1315.8	1315.5	1315.4	1315.1	1316.5	1317.9
160°	1331.1	1330.8	1330.6	1330.3	1330.1	1329.9	1329.6	1329.5	1329.2	1330.6	1331.9
162.5°	1344.8	1344.2	1343.5	1342.9	1342.6	1342.3	1342.1	1341.8	1341.6	1343.2	1344.8
165°	1361.6	1360.9	1360.3	1359.6	1359.1	1358.9	1358.6	1358.4	1358.2	1360.0	1361.9
167.5°	1374.7	1373.8	1372.9	1371.9	1371.5	1371.5	1371.5	1371.5	1371.5	1373.3	1375.1
170°	1382.2	1381.3	1380.3	1379.4	1378.9	1378.9	1378.9	1378.9	1378.9	1380.7	1382.6
172.5°	1387.0	1385.8	1384.7	1383.6	1383.1	1383.3	1383.5	1383.7	1383.8	1385.7	1387.6
175°	1393.3	1392.1	1391.0	1389.8	1389.4	1389.6	1389.8	1390.1	1390.3	1392.0	1393.6
177.5°	1395.2	1394.3	1393.4	1392.4	1392.0	1392.2	1392.4	1392.6	1392.8	1394.3	1395.7
180°	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5



TEST NUMBER: P332324-940

CATALOG NUMBER: S123RDIP-S775D1195U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6
2.5°	1150.3	1150.3	1151.8	1157.4	1158.2	1163.1	1161.5
5°	1264.3	1273.1	1276.4	1290.4	1298.8	1302.5	1295.0
7.5°	1403.6	1428.6	1440.5	1455.1	1468.1	1472.0	1461.8
10°	1505.1	1531.2	1553.3	1566.7	1579.4	1587.8	1598.5
12.5°	1603.4	1635.5	1656.4	1675.4	1688.5	1699.1	1700.8
15°	1710.1	1758.6	1795.5	1822.6	1836.1	1843.2	1840.3
17.5°	1817.8	1862.8	1889.0	1916.6	1935.4	1936.4	1936.9
20°	1878.7	1922.5	1952.8	1973.4	1994.4	1993.5	1998.1
22.5°	1919.3	1953.9	1977.1	1992.1	1999.3	1995.7	1996.6
25°	1938.4	1948.7	1944.5	1920.7	1914.6	1892.7	1896.4
27.5°	1840.1	1791.6	1741.3	1676.8	1625.8	1585.1	1587.2
30°	1706.8	1621.0	1522.9	1440.7	1367.0	1346.4	1302.5
32.5°	1520.5	1391.6	1276.8	1200.2	1136.8	1119.7	1081.5
35°	1204.5	1079.3	961.3	890.3	862.3	823.0	822.6
37.5°	936.2	826.1	763.6	710.3	682.4	658.7	656.4
40°	787.6	701.7	654.5	616.3	588.7	571.0	566.8
42.5°	683.8	614.3	570.2	546.4	525.2	516.0	509.3
45°	558.4	511.7	480.9	459.4	449.6	442.6	438.8
47.5°	467.1	435.8	414.7	400.5	392.5	385.1	387.1
50°	417.4	391.7	376.3	362.7	356.7	351.5	352.0
52.5°	377.4	354.4	341.9	332.2	324.6	320.9	319.1
55°	320.3	305.8	293.2	286.1	282.0	276.9	275.4
57.5°	273.2	262.0	251.7	243.8	242.7	237.8	238.4
60°	241.8	232.5	224.1	219.9	216.6	212.4	213.8
62.5°	216.1	208.2	200.5	197.1	193.9	190.7	191.5
65°	176.9	169.4	164.8	162.9	161.5	160.2	158.7
67.5°	141.0	136.4	133.5	129.5	126.6	126.2	124.8
70°	118.6	112.5	107.4	102.3	100.9	100.4	100.9
72.5°	95.1	91.2	89.8	87.3	87.0	85.8	86.7
75°	71.4	70.0	69.1	67.2	67.2	67.2	67.2
77.5°	52.7	51.8	51.3	50.9	50.4	49.8	49.7
80°	41.1	40.6	39.7	39.7	39.2	39.7	39.2
82.5°	31.0	30.9	30.0	30.0	29.5	29.2	29.5
85°	15.9	15.4	16.3	15.4	15.9	15.0	15.9
87.5°	10.0	10.2	10.0	10.1	9.8	10.6	10.0
90°	27.6	28.5	29.2	29.7	30.1	30.6	31.1
92.5°	30.9	32.5	33.3	33.5	33.9	34.2	34.4
95°	36.9	38.5	39.3	39.3	39.3	39.3	39.3
97.5°	38.9	40.8	41.7	42.0	42.3	42.4	42.7
100°	39.7	41.6	42.6	42.8	43.1	43.2	43.5
102.5°	51.0	45.3	42.7	43.1	43.5	44.0	44.3
105°	104.6	63.8	43.8	44.2	44.7	45.1	45.6
107.5°	326.2	296.3	266.0	235.3	204.6	173.9	143.2
110°	444.4	436.8	416.6	383.7	350.7	317.8	284.9



TEST NUMBER: P332324-940

CATALOG NUMBER: S123RDIP-S775D1195U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	519.9	520.0	516.6	509.6	502.7	495.7	488.7
115°	601.5	603.9	605.5	606.4	607.3	608.2	609.1
117.5°	673.2	674.9	676.0	676.2	676.4	676.5	676.7
120°	720.3	722.2	723.1	723.1	723.1	723.1	723.1
122.5°	766.0	767.2	767.9	768.1	768.3	768.6	768.7
125°	830.2	830.6	831.1	831.5	832.1	832.5	832.9
127.5°	895.6	896.3	896.5	896.1	895.6	895.2	894.7
130°	935.1	936.1	936.3	935.9	935.4	935.0	934.5
132.5°	972.5	973.4	973.5	972.9	972.2	971.6	970.9
135°	1028.8	1029.5	1029.5	1028.8	1028.1	1027.3	1026.7
137.5°	1079.5	1080.6	1080.9	1080.5	1080.0	1079.6	1079.1
140°	1111.3	1112.2	1112.4	1112.0	1111.5	1111.1	1110.6
142.5°	1141.4	1142.1	1142.2	1141.6	1140.9	1140.2	1139.6
145°	1183.5	1183.9	1184.1	1184.1	1184.1	1184.1	1184.1
147.5°	1221.4	1221.8	1221.6	1220.5	1219.4	1218.3	1217.3
150°	1244.6	1245.0	1244.9	1244.2	1243.6	1242.9	1242.2
152.5°	1265.6	1266.4	1266.3	1265.2	1264.2	1263.1	1262.0
155°	1294.3	1295.5	1295.3	1294.0	1292.6	1291.2	1289.9
157.5°	1319.2	1320.6	1320.4	1318.7	1316.8	1315.0	1313.2
160°	1333.3	1334.7	1334.6	1333.0	1331.4	1329.7	1328.1
162.5°	1346.3	1347.9	1347.9	1346.5	1345.1	1343.6	1342.2
165°	1363.7	1365.6	1365.7	1364.1	1362.4	1360.8	1359.2
167.5°	1377.0	1378.9	1378.9	1377.0	1375.1	1373.3	1371.5
170°	1384.5	1386.3	1386.3	1384.5	1382.6	1380.7	1378.9
172.5°	1389.4	1391.2	1391.2	1389.1	1387.1	1385.1	1383.0
175°	1395.2	1396.8	1396.6	1394.8	1392.9	1391.2	1389.3
177.5°	1397.2	1398.6	1398.5	1396.7	1394.8	1392.9	1391.2
180°	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5

(END OF REPORT)