

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332329-940

Luminaire Tested: **S123RDIP-S775D1195U940-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332329-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S775D1195U940-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1195 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6455.3 lumens
Efficiency: N/A
Efficacy: 113.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332329-940

CATALOG NUMBER: S123RDIP-S775D1195U940-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332329-940

CATALOG NUMBER: S123RDIP-S775D1195U940-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	40				
1	96	92	88	85	87	84	81	78	69	66	64	55	53	52	42	41	40	34				
2	87	80	74	69	79	73	68	64	60	57	54	48	46	44	37	36	34	29				
3	80	71	64	58	73	65	59	54	54	49	45	43	40	37	33	31	30	25				
4	73	63	55	49	66	58	51	46	48	43	39	38	35	32	30	28	26	22				
5	67	56	48	42	61	51	45	39	43	38	34	35	31	28	27	25	22	19				
6	62	50	42	37	56	46	39	34	39	33	29	31	27	25	25	22	20	17				
7	57	45	38	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15				
8	53	41	34	28	48	38	31	27	32	27	23	26	22	19	21	18	16	13				
9	49	38	30	25	45	35	28	24	29	24	21	24	20	17	19	16	14	12				
10	46	34	27	23	42	32	26	21	27	22	19	22	18	16	18	15	13	11				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12392	12392	12392
5°	12440	12268	12338
10°	12369	12114	12073
15°	12237	11830	11705
20°	12054	11475	11208
25°	11866	11077	10723
30°	11616	10618	10038
35°	11361	10159	9410
40°	11126	9617	8633
45°	10816	9082	7931
50°	10474	8473	7145
55°	10128	7781	6412
60°	9810	7035	5608
65°	9393	6230	4804
70°	8875	5231	3877
75°	8114	4117	3647
80°	7234	3651	3353
85°	6113	3223	3001



TEST NUMBER: P332329-940

CATALOG NUMBER: S123RDIP-S775D1195U940-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	108.1	1.7
10°-20°	300.8	4.7
20°-30°	433.1	6.7
30°-40°	487.9	7.6
40°-50°	466.7	7.2
50°-60°	382.2	5.9
60°-70°	257.9	4.0
70°-80°	129.7	2.0
80°-90°	38.3	0.6
90°-100°	284.8	4.4
100°-110°	806.5	12.5
110°-120°	793.4	12.3
120°-130°	632.8	9.8
130°-140°	498.9	7.7
140°-150°	372.4	5.8
150°-160°	259.6	4.0
160°-170°	152.5	2.4
170°-180°	49.6	0.8
0°-30°	842.0	13.0
0°-40°	1329.9	20.6
0°-60°	2178.8	33.8
0°-90°	2604.7	40.4
90°-120°	1884.7	29.2
90°-150°	3388.9	52.5
90°-180°	3851.0	59.7
0°-180°	6455.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1151	1151	1151	1151	1151	
5°	1151	1146	1135	1143	1142	109
15°	1098	1087	1062	1057	1050	309
25°	999	975	933	914	903	459
35°	865	830	773	734	716	541
45°	710	667	597	545	521	548
55°	540	492	415	362	342	484
65°	369	316	245	201	189	365
75°	195	150	99	90	88	208
85°	50	30	26	24	24	56
90°	2	12	26	29	30	5
95°	35	114	614	179	120	38
105°	120	178	833	1457	1318	128
115°	212	265	637	1397	1603	210
125°	295	349	595	1077	1264	262
135°	346	413	586	887	1025	267
145°	395	452	579	728	801	247
155°	449	484	560	637	664	206
165°	490	504	537	569	579	138
175°	511	511	515	522	521	48
180°	512	512	512	512	512	



TEST NUMBER: P332329-940

CATALOG NUMBER: S123RDIP-S775D1195U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1151.3	1151.3	1151.3	1151.3	1151.3	1151.3	1151.3	1151.3	1151.3	1151.3	1151.3
2.5°	1154.9	1154.3	1153.6	1153.0	1152.4	1151.0	1149.0	1147.0	1145.0	1143.0	1144.9
5°	1151.3	1150.2	1149.1	1148.2	1147.1	1145.3	1142.8	1140.3	1137.8	1135.4	1137.2
7.5°	1140.6	1139.5	1138.4	1137.2	1136.1	1133.9	1130.7	1127.5	1124.3	1121.0	1122.0
10°	1131.7	1130.2	1128.7	1127.3	1125.8	1123.2	1119.5	1115.8	1112.1	1108.3	1108.5
12.5°	1118.9	1117.3	1115.7	1114.1	1112.5	1109.4	1104.8	1100.3	1095.6	1091.1	1091.0
15°	1098.1	1095.7	1093.4	1091.2	1088.9	1084.9	1079.1	1073.3	1067.4	1061.6	1060.6
17.5°	1071.7	1069.1	1066.4	1063.7	1061.0	1056.1	1048.7	1041.3	1033.8	1026.5	1024.3
20°	1052.3	1048.9	1045.6	1042.3	1039.0	1033.4	1025.5	1017.6	1009.8	1001.8	999.2
22.5°	1030.6	1026.8	1023.0	1019.1	1015.3	1009.2	1000.9	992.5	984.1	975.7	972.3
25°	999.1	993.9	988.6	983.5	978.3	970.9	961.4	951.8	942.3	932.7	928.4
27.5°	960.7	955.0	949.3	943.6	937.9	929.7	919.1	908.5	897.8	887.2	881.1
30°	934.6	928.4	922.2	916.0	909.7	900.8	889.2	877.5	865.9	854.3	847.3
32.5°	908.5	901.4	894.4	887.3	880.3	870.6	858.3	846.1	833.7	821.4	813.8
35°	864.6	857.1	849.6	842.2	834.7	824.6	811.7	798.8	786.0	773.1	764.2
37.5°	820.2	811.8	803.5	795.2	786.9	776.0	762.2	748.5	734.8	721.0	710.9
40°	791.8	782.7	773.5	764.4	755.3	743.3	728.6	713.9	699.1	684.4	673.6
42.5°	759.6	750.6	741.4	732.3	723.2	711.0	695.7	680.5	665.3	650.1	638.3
45°	710.5	701.2	691.9	682.5	673.2	660.6	644.5	628.6	612.6	596.6	584.8
47.5°	661.5	651.2	641.0	630.7	620.5	607.3	591.4	575.3	559.4	543.4	530.6
50°	625.5	615.8	606.1	596.3	586.6	573.3	556.5	539.7	522.9	506.0	493.2
52.5°	593.4	582.9	572.3	561.7	551.2	537.5	520.8	504.3	487.6	470.9	457.6
55°	539.7	529.5	519.3	509.2	499.0	485.1	467.4	449.9	432.2	414.6	402.5
57.5°	490.0	478.9	467.9	456.7	445.7	431.3	413.6	395.8	378.1	360.4	349.0
60°	455.7	444.3	432.8	421.4	410.0	395.7	378.4	361.2	344.0	326.8	315.6
62.5°	421.2	409.8	398.4	387.0	375.7	361.3	344.1	326.9	309.7	292.4	281.9
65°	368.8	357.4	346.0	334.6	323.2	309.3	293.2	277.0	260.8	244.6	234.4
67.5°	316.4	304.8	293.3	281.7	270.2	256.6	241.1	225.6	210.1	194.6	187.0
70°	282.0	270.8	259.6	248.3	237.2	224.3	209.7	195.3	180.7	166.2	158.9
72.5°	247.6	236.6	225.5	214.5	203.5	191.4	178.2	165.0	151.8	138.6	132.6
75°	195.1	185.2	175.2	165.2	155.3	144.6	133.2	121.8	110.4	99.0	96.9
77.5°	147.3	138.3	129.3	120.3	111.3	103.2	95.8	88.5	81.1	73.7	72.7
80°	116.7	108.2	99.7	91.2	82.7	76.2	71.9	67.5	63.2	58.9	58.2
82.5°	87.6	80.3	72.9	65.5	58.2	53.5	51.5	49.4	47.4	45.4	44.8
85°	49.5	44.9	40.4	35.8	31.2	28.6	28.0	27.4	26.8	26.1	25.8
87.5°	18.4	16.9	15.5	14.4	12.9	12.4	13.0	13.6	14.3	14.9	14.5
90°	2.1	4.1	6.2	9.4	11.4	13.5	16.6	19.7	22.8	25.9	24.9
92.5°	12.8	19.1	27.7	35.8	44.6	59.9	87.0	131.6	175.3	159.3	120.2
95°	35.2	38.3	49.8	67.3	94.3	134.6	222.7	377.1	547.1	614.4	498.3
97.5°	60.1	61.1	70.0	85.3	111.9	155.6	239.8	413.8	697.1	952.1	1018.6
100°	76.7	77.7	85.0	99.4	124.3	164.7	237.3	390.6	663.1	981.1	1185.3
102.5°	94.1	95.9	102.4	116.0	138.4	175.5	240.6	370.7	613.3	927.3	1193.5
105°	120.2	123.3	129.5	142.0	161.6	193.8	249.7	356.4	552.2	832.9	1130.3
107.5°	147.9	151.1	157.0	169.2	187.7	217.6	266.7	355.3	513.3	749.7	1019.7
110°	167.8	170.9	176.1	187.5	205.1	234.2	280.8	359.5	498.3	702.4	950.0



TEST NUMBER: P332329-940

CATALOG NUMBER: S123RDIP-S775D1195U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	186.1	189.2	194.4	205.7	223.4	251.6	294.9	367.8	490.1	670.9	889.6
115°	212.4	216.5	222.7	233.1	250.7	278.7	318.1	381.3	487.0	637.1	816.4
117.5°	238.7	243.4	248.6	258.2	277.9	303.8	342.7	399.0	488.8	617.2	772.2
120°	256.9	260.0	265.2	275.6	295.2	321.2	358.5	412.3	492.1	608.1	749.0
122.5°	272.7	275.8	281.0	292.1	311.0	338.6	375.1	424.8	497.9	602.4	730.0
125°	295.2	297.4	303.5	315.0	334.7	362.6	398.9	444.4	506.6	594.7	705.5
127.5°	312.5	315.6	323.2	334.8	356.6	384.6	419.5	460.7	516.6	590.9	684.0
130°	323.2	326.4	335.6	348.1	369.9	397.8	432.0	471.4	523.2	588.4	672.3
132.5°	331.5	335.5	345.6	360.5	382.3	409.5	442.8	481.3	528.2	587.6	661.6
135°	346.1	350.2	361.6	377.1	398.9	426.9	459.0	494.2	535.7	586.4	647.6
137.5°	359.7	364.1	375.2	391.8	413.4	439.3	470.1	503.7	540.6	584.1	635.3
140°	368.8	374.0	384.3	400.9	421.7	447.5	477.6	508.7	543.9	583.3	627.9
142.5°	378.8	383.2	394.3	409.2	430.0	454.2	483.4	513.6	546.4	581.7	621.2
145°	394.8	397.8	407.2	422.7	440.3	464.1	491.1	519.1	548.0	579.2	612.3
147.5°	410.9	412.8	421.9	435.3	452.4	472.6	497.3	522.4	548.0	575.2	603.6
150°	421.7	422.7	431.0	444.4	459.0	477.6	501.4	523.2	548.0	571.9	597.8
152.5°	432.5	432.7	441.0	452.7	465.6	483.4	503.9	524.9	545.5	567.8	591.2
155°	448.6	448.6	454.9	465.2	476.5	491.1	508.7	525.3	542.9	560.5	581.2
157.5°	461.5	462.3	467.3	476.4	486.1	497.3	511.4	526.3	539.4	554.1	570.0
160°	471.4	471.4	475.5	483.8	491.1	501.4	513.9	526.3	537.7	549.1	562.6
162.5°	478.8	478.8	482.1	488.8	495.3	503.9	514.7	525.5	534.4	544.1	555.1
165°	490.1	489.0	491.1	496.2	500.4	507.7	515.9	523.2	529.4	536.6	544.9
167.5°	498.6	497.3	498.3	502.3	505.2	509.7	515.8	521.6	524.4	529.2	535.2
170°	503.5	501.4	502.5	505.6	507.7	509.7	514.9	519.1	521.1	524.2	529.4
172.5°	506.8	505.6	505.8	508.1	509.3	510.6	514.9	518.3	518.6	520.0	523.6
175°	510.8	509.7	508.7	510.8	510.8	511.8	513.9	515.9	514.9	514.9	517.0
177.5°	512.6	511.8	511.0	511.8	511.8	511.8	512.6	514.2	512.6	511.8	512.6
180°	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8



TEST NUMBER: P332329-940

CATALOG NUMBER: S123RDIP-S775D1195U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1151.3	1151.3	1151.3	1151.3	1151.3	1151.3	1151.3	1151.3
2.5°	1146.7	1148.5	1150.3	1151.1	1150.8	1150.4	1150.0	1149.8
5°	1139.1	1140.9	1142.8	1143.5	1143.2	1142.7	1142.3	1141.9
7.5°	1123.1	1124.1	1125.2	1125.3	1124.6	1123.9	1123.2	1122.5
10°	1108.8	1108.9	1109.1	1108.8	1107.7	1106.6	1105.6	1104.6
12.5°	1090.8	1090.7	1090.7	1089.9	1088.8	1087.5	1086.4	1085.1
15°	1059.5	1058.5	1057.5	1056.2	1054.8	1053.3	1051.9	1050.4
17.5°	1022.1	1019.9	1017.7	1015.6	1013.3	1011.2	1009.1	1006.9
20°	996.5	993.7	991.0	988.5	986.0	983.5	981.0	978.5
22.5°	969.0	965.6	962.2	959.4	957.1	954.8	952.4	950.1
25°	924.1	919.7	915.3	912.0	909.7	907.4	905.2	902.9
27.5°	875.0	869.1	863.0	858.2	854.7	851.2	847.7	844.3
30°	840.3	833.1	826.1	820.9	817.6	814.3	810.9	807.6
32.5°	806.0	798.3	790.6	785.0	781.5	778.0	774.5	771.1
35°	755.3	746.4	737.4	731.1	727.4	723.6	719.9	716.1
37.5°	700.7	690.6	680.5	673.2	668.5	663.9	659.3	654.7
40°	662.8	652.0	641.2	633.5	628.7	623.9	619.1	614.4
42.5°	626.4	614.7	602.9	594.9	590.6	586.3	582.0	577.7
45°	573.0	561.2	549.3	540.9	535.9	530.9	526.0	521.0
47.5°	517.6	504.8	492.0	483.3	478.8	474.4	470.0	465.6
50°	480.4	467.4	454.6	445.8	441.0	436.2	431.5	426.7
52.5°	444.3	430.9	417.5	408.7	404.4	400.1	395.8	391.6
55°	390.5	378.4	366.4	358.3	354.2	350.0	345.9	341.7
57.5°	337.7	326.3	315.0	307.5	304.0	300.4	296.9	293.4
60°	304.3	293.2	282.0	274.6	271.1	267.5	264.0	260.5
62.5°	271.3	260.8	250.3	243.2	239.4	235.8	232.1	228.4
65°	224.3	214.1	203.9	197.7	195.5	193.1	190.9	188.6
67.5°	179.4	171.8	164.2	159.2	156.8	154.3	151.9	149.4
70°	151.7	144.4	137.1	132.4	130.1	127.8	125.6	123.2
72.5°	126.7	120.7	114.9	111.4	110.4	109.5	108.5	107.5
75°	94.8	92.7	90.7	89.4	89.0	88.6	88.2	87.7
77.5°	71.5	70.4	69.3	68.5	68.1	67.7	67.2	66.9
80°	57.6	57.0	56.4	55.8	55.4	55.0	54.6	54.1
82.5°	44.1	43.5	42.9	42.5	42.4	42.4	42.3	42.2
85°	25.3	24.9	24.5	24.3	24.3	24.3	24.3	24.3
87.5°	14.5	14.6	14.6	14.9	14.5	14.5	14.6	14.3
90°	25.9	26.9	28.0	30.1	29.0	30.1	31.1	30.1
92.5°	87.2	69.2	61.1	55.7	53.9	50.7	51.8	49.9
95°	373.0	252.8	197.9	160.6	140.9	131.6	124.3	120.2
97.5°	929.7	744.7	611.1	487.1	410.7	364.1	336.1	327.2
100°	1221.5	1137.6	1016.4	869.2	764.6	688.9	648.5	649.6
102.5°	1318.5	1315.7	1245.1	1151.8	1070.4	1010.6	976.8	953.0
105°	1346.8	1450.5	1470.2	1443.2	1395.5	1356.2	1323.0	1317.9
107.5°	1265.2	1433.4	1524.2	1561.1	1561.9	1548.6	1537.5	1527.9
110°	1187.3	1378.0	1508.5	1581.0	1610.0	1618.3	1616.2	1614.2



TEST NUMBER: P332329-940

CATALOG NUMBER: S123RDIP-S775D1195U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	1110.2	1305.0	1451.3	1544.5	1597.6	1623.3	1631.1	1631.6
115°	1008.1	1188.3	1340.6	1453.6	1531.2	1576.8	1597.6	1602.8
117.5°	934.1	1089.7	1226.5	1341.0	1422.1	1474.3	1504.1	1511.2
120°	895.1	1035.0	1159.3	1264.0	1345.8	1403.8	1428.7	1434.9
122.5°	864.4	991.0	1106.3	1203.5	1276.2	1328.4	1355.8	1363.6
125°	823.7	936.6	1036.0	1118.9	1185.3	1230.8	1256.7	1264.0
127.5°	788.0	888.7	978.4	1053.8	1112.9	1151.8	1175.3	1181.9
130°	765.6	858.9	942.8	1013.3	1068.2	1105.5	1127.2	1135.5
132.5°	744.9	830.7	908.8	976.0	1027.5	1064.8	1084.1	1089.9
135°	716.9	790.5	857.8	916.9	967.7	998.7	1017.4	1024.7
137.5°	691.4	751.7	809.8	860.9	903.7	935.1	950.8	955.6
140°	676.5	729.3	779.1	823.7	863.0	892.1	908.6	907.6
142.5°	662.5	707.8	750.9	789.7	823.2	848.9	863.8	862.8
145°	645.4	679.7	712.8	742.8	768.7	790.5	798.8	800.8
147.5°	631.6	658.7	685.5	706.8	726.5	741.2	749.0	749.8
150°	621.6	645.4	667.2	686.9	702.4	713.8	720.1	720.1
152.5°	612.5	633.0	652.3	668.7	680.9	691.4	695.2	695.2
155°	598.8	615.4	631.0	643.4	652.7	661.0	663.1	664.1
157.5°	584.3	598.2	610.2	619.9	628.0	634.3	635.9	635.7
160°	576.0	587.5	597.8	605.0	612.3	618.5	618.5	617.5
162.5°	566.1	575.9	585.3	591.7	596.6	601.9	601.9	600.9
165°	553.2	559.5	566.7	571.9	576.0	580.1	579.2	579.2
167.5°	542.1	546.8	551.0	554.7	556.5	559.5	558.4	558.4
170°	534.6	537.7	541.8	543.9	544.9	547.1	546.0	546.0
172.5°	528.0	530.2	533.6	534.8	535.0	537.1	535.2	534.4
175°	519.1	520.0	522.2	522.2	522.2	523.2	522.2	521.1
177.5°	513.4	514.2	515.1	515.1	514.2	515.1	513.4	513.4
180°	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8

(END OF REPORT)