

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332301-940

Luminaire Tested: **S123RDIP-S775D365U940-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332301-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S775D365U940-4F0-1E-UDD-A1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3828.0 lumens
Efficiency: N/A
Efficacy: 109.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 35
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332301-940

CATALOG NUMBER: S123RDIP-S775D365U940-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332301-940

CATALOG NUMBER: S123RDIP-S775D365U940-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	75	75	75	71
1	103	99	95	92	98	94	91	88	85	82	80	76	74	72	68	67	65	61
2	95	88	82	77	90	83	78	74	75	71	68	68	65	62	61	58	56	53
3	87	78	71	65	82	74	68	63	67	62	58	61	57	53	55	52	49	46
4	80	69	62	56	76	66	59	54	60	55	50	55	50	46	49	46	43	40
5	74	62	54	48	70	60	52	47	54	48	44	49	45	41	45	41	38	35
6	68	56	48	43	65	54	47	41	49	43	39	45	40	36	41	37	34	31
7	64	51	43	38	60	49	42	37	45	39	35	41	36	32	38	33	30	28
8	59	47	39	34	56	45	38	33	41	35	31	38	33	29	35	30	27	25
9	55	43	36	30	52	41	34	30	38	32	28	35	30	26	32	28	25	23
10	52	40	32	28	49	38	31	27	35	29	25	33	28	24	30	26	23	21

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11739	11739	11739	11739
5°	13993	11788	10381	11788
10°	17472	11721	9379	11721
15°	20508	11602	8553	11602
20°	22888	11423	7851	11423
25°	22523	11233	7418	11233
30°	16189	11059	6975	11059
35°	10809	10834	6687	10834
40°	7964	10561	6389	10561
45°	6680	10085	6098	10085
50°	5894	9460	5690	9460
55°	5168	8743	5134	8743
60°	4603	8060	4704	8060
65°	4042	7325	4376	7325
70°	3175	6672	3997	6672
75°	2795	5827	3647	5827
80°	2430	4947	3589	4947
85°	1964	3977	3816	3977



TEST NUMBER: P332301-940

CATALOG NUMBER: S123RDIP-S775D365U940-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	107.2	2.8
10°-20°	335.1	8.8
20°-30°	526.4	13.8
30°-40°	549.2	14.3
40°-50°	470.0	12.3
50°-60°	358.2	9.4
60°-70°	229.6	6.0
70°-80°	110.5	2.9
80°-90°	30.4	0.8
90°-100°	26.1	0.7
100°-110°	78.2	2.0
110°-120°	133.0	3.5
120°-130°	175.0	4.6
130°-140°	196.7	5.1
140°-150°	193.3	5.1
150°-160°	162.8	4.3
160°-170°	108.3	2.8
170°-180°	37.9	1.0
0°-30°	968.7	25.3
0°-40°	1517.9	39.7
0°-60°	2346.1	61.3
0°-90°	2716.5	71.0
90°-120°	237.4	6.2
90°-150°	802.4	21.0
90°-180°	1111.0	29.0
0°-180°	3828.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1091	1091	1091	1091	1091	
5°	1295	1091	961	1091	1295	134
15°	1840	1041	768	1041	1840	522
25°	1896	946	625	946	1896	815
35°	823	824	509	824	823	539
45°	439	662	401	662	439	345
55°	275	466	274	466	275	249
65°	159	288	172	288	159	156
75°	67	140	88	140	67	72
85°	16	32	31	32	16	18
90°	10	0	10	0	10	5
95°	25	19	25	19	25	25
105°	75	71	75	71	75	80
115°	134	134	134	134	134	133
125°	194	196	194	196	194	173
135°	254	254	254	254	254	195
145°	308	308	308	308	308	193
155°	353	353	353	353	353	162
165°	384	385	384	385	384	108
175°	399	400	399	400	399	38
180°	401	401	401	401	401	



TEST NUMBER: P332301-940

CATALOG NUMBER: S123RDIP-S775D365U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6
2.5°	1161.5	1163.1	1158.2	1157.4	1151.8	1150.3	1150.3	1142.5	1137.6	1131.3	1127.6
5°	1295.0	1302.5	1298.8	1290.4	1276.4	1273.1	1264.3	1250.3	1234.4	1214.8	1205.4
7.5°	1461.8	1472.0	1468.1	1455.1	1440.5	1428.6	1403.6	1380.3	1347.7	1319.1	1294.7
10°	1598.5	1587.8	1579.4	1566.7	1553.3	1531.2	1505.1	1469.2	1427.6	1395.0	1358.5
12.5°	1700.8	1699.1	1688.5	1675.4	1656.4	1635.5	1603.4	1559.6	1511.3	1464.1	1422.5
15°	1840.3	1843.2	1836.1	1822.6	1795.5	1758.6	1710.1	1691.8	1622.8	1571.5	1520.1
17.5°	1936.9	1936.4	1935.4	1916.6	1889.0	1862.8	1817.8	1769.9	1707.3	1635.0	1565.8
20°	1998.1	1993.5	1994.4	1973.4	1952.8	1922.5	1878.7	1809.1	1757.7	1674.2	1602.7
22.5°	1996.6	1995.7	1999.3	1992.1	1977.1	1953.9	1919.3	1860.6	1795.1	1710.7	1630.3
25°	1896.4	1892.7	1914.6	1920.7	1944.5	1948.7	1938.4	1906.2	1844.1	1757.2	1657.8
27.5°	1587.2	1585.1	1625.8	1676.8	1741.3	1791.6	1840.1	1863.6	1844.1	1781.9	1682.3
30°	1302.5	1346.4	1367.0	1440.7	1522.9	1621.0	1706.8	1788.5	1808.6	1781.5	1699.8
32.5°	1081.5	1119.7	1136.8	1200.2	1276.8	1391.6	1520.5	1636.1	1717.9	1738.6	1689.3
35°	822.6	823.0	862.3	890.3	961.3	1079.3	1204.5	1359.5	1513.5	1630.2	1642.4
37.5°	656.4	658.7	682.4	710.3	763.6	826.1	936.2	1065.1	1243.0	1422.2	1527.2
40°	566.8	571.0	588.7	616.3	654.5	701.7	787.6	909.0	1057.4	1256.8	1419.7
42.5°	509.3	516.0	525.2	546.4	570.2	614.3	683.8	777.5	912.5	1101.0	1289.0
45°	438.8	442.6	449.6	459.4	480.9	511.7	558.4	621.3	733.4	885.2	1073.3
47.5°	387.1	385.1	392.5	400.5	414.7	435.8	467.1	518.5	598.4	720.1	879.8
50°	352.0	351.5	356.7	362.7	376.3	391.7	417.4	456.1	519.6	620.5	766.6
52.5°	319.1	320.9	324.6	332.2	341.9	354.4	377.4	405.3	459.9	546.9	668.7
55°	275.4	276.9	282.0	286.1	293.2	305.8	320.3	343.6	380.9	441.7	542.0
57.5°	238.4	237.8	242.7	243.8	251.7	262.0	273.2	291.3	318.4	363.5	431.1
60°	213.8	212.4	216.6	219.9	224.1	232.5	241.8	259.6	281.1	314.1	372.1
62.5°	191.5	190.7	193.9	197.1	200.5	208.2	216.1	229.7	246.6	274.6	320.6
65°	158.7	160.2	161.5	162.9	164.8	169.4	176.9	186.3	198.0	217.6	250.7
67.5°	124.8	126.2	126.6	129.5	133.5	136.4	141.0	149.3	157.4	174.0	192.8
70°	100.9	100.4	100.9	102.3	107.4	112.5	118.6	124.7	129.7	141.4	157.3
72.5°	86.7	85.8	87.0	87.3	89.8	91.2	95.1	100.8	107.4	115.3	126.7
75°	67.2	67.2	67.2	67.2	69.1	70.0	71.4	72.9	75.2	78.9	87.3
77.5°	49.7	49.8	50.4	50.9	51.3	51.8	52.7	54.0	54.9	56.9	60.5
80°	39.2	39.7	39.2	39.7	39.7	40.6	41.1	42.4	43.0	45.3	46.7
82.5°	29.5	29.2	29.5	30.0	30.0	30.9	31.0	32.0	32.1	33.3	34.8
85°	15.9	15.0	15.9	15.4	16.3	15.4	15.9	16.8	16.8	17.3	19.2
87.5°	5.6	6.3	5.5	5.9	5.9	6.2	6.2	6.1	6.8	6.3	6.6
90°	9.5	9.3	9.2	9.0	8.9	8.6	8.4	8.1	7.8	7.6	6.7
92.5°	12.8	12.8	12.9	13.0	13.1	13.0	12.8	12.6	12.3	12.1	11.6
95°	24.6	24.6	24.6	24.6	24.6	24.4	24.2	23.9	23.6	23.4	22.7
97.5°	37.8	37.8	37.9	37.9	37.9	37.8	37.5	37.1	36.8	36.5	36.1
100°	47.9	47.8	47.6	47.4	47.3	47.2	47.0	46.7	46.5	46.3	46.0
102.5°	58.2	58.2	58.3	58.3	58.3	58.2	58.1	57.9	57.6	57.4	57.0
105°	75.0	74.9	74.7	74.5	74.5	74.4	74.4	74.4	74.4	74.4	73.7
107.5°	92.5	92.6	92.6	92.7	92.8	92.7	92.5	92.3	92.0	91.8	91.6
110°	104.3	104.4	104.6	104.7	104.9	104.8	104.5	104.2	104.0	103.7	103.5



TEST NUMBER: P332301-940

CATALOG NUMBER: S123RDIP-S775D365U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	116.9	116.9	117.0	117.0	117.0	116.9	116.5	116.2	115.8	115.6	115.5
115°	134.2	134.3	134.4	134.5	134.6	134.6	134.5	134.4	134.3	134.2	134.4
117.5°	151.9	152.0	152.2	152.4	152.6	152.8	152.8	152.8	152.8	152.8	152.9
120°	164.2	164.3	164.4	164.6	164.7	164.9	164.9	165.0	165.1	165.1	165.5
122.5°	176.0	176.2	176.4	176.6	176.8	177.0	177.2	177.4	177.5	177.7	177.9
125°	193.8	194.0	194.4	194.7	194.9	195.2	195.5	195.7	196.0	196.4	196.4
127.5°	211.5	211.9	212.1	212.5	212.8	213.1	213.6	213.9	214.4	214.7	214.9
130°	223.1	223.6	224.1	224.6	225.1	225.4	225.7	226.0	226.3	226.6	226.8
132.5°	235.2	235.6	235.9	236.3	236.7	237.1	237.4	237.7	238.1	238.4	238.5
135°	254.0	254.1	254.2	254.4	254.6	254.8	255.0	255.3	255.6	255.9	255.9
137.5°	270.5	270.8	271.1	271.3	271.6	271.9	272.2	272.5	272.8	273.0	272.9
140°	281.4	281.9	282.4	282.9	283.4	283.7	283.7	283.7	283.8	283.9	283.8
142.5°	292.5	292.8	293.3	293.6	294.0	294.3	294.3	294.4	294.4	294.5	294.4
145°	308.5	308.8	309.1	309.3	309.6	309.8	309.9	310.0	310.0	310.0	309.9
147.5°	322.7	323.2	323.6	324.0	324.4	324.7	324.7	324.7	324.7	324.7	324.4
150°	331.8	332.3	332.7	333.1	333.5	333.7	333.7	333.7	333.7	333.7	333.6
152.5°	340.6	341.0	341.3	341.7	342.1	342.2	342.1	342.0	341.9	341.8	341.7
155°	352.6	353.1	353.6	354.1	354.5	354.7	354.4	354.1	353.8	353.6	353.5
157.5°	363.6	363.9	364.4	364.7	365.1	365.2	364.9	364.5	364.3	364.0	363.9
160°	370.6	370.9	371.1	371.4	371.7	371.7	371.3	371.0	370.6	370.2	370.2
162.5°	375.9	376.3	376.7	377.2	377.6	377.7	377.4	377.0	376.7	376.3	376.3
165°	383.5	384.0	384.5	385.0	385.5	385.5	385.0	384.7	384.2	383.8	383.8
167.5°	390.0	390.4	390.8	391.3	391.7	391.7	391.3	390.8	390.4	390.0	389.9
170°	393.2	393.8	394.2	394.8	395.2	395.2	394.8	394.2	393.8	393.2	393.2
172.5°	395.8	396.3	396.8	397.3	397.8	397.8	397.3	396.9	396.5	396.0	396.0
175°	398.6	399.1	399.6	400.1	400.6	400.6	400.2	399.8	399.4	399.0	399.0
177.5°	400.1	400.6	400.9	401.4	401.7	401.7	401.4	401.1	400.7	400.4	400.4
180°	401.2	401.2	401.2	401.2	401.2	401.2	401.2	401.2	401.2	401.2	401.2



TEST NUMBER: P332301-940

CATALOG NUMBER: S123RDIP-S775D365U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6
2.5°	1126.1	1124.9	1119.7	1113.7	1105.9	1100.6	1096.5	1094.3	1087.6	1079.3	1073.8
5°	1195.6	1181.6	1166.7	1148.4	1131.7	1114.4	1103.7	1091.0	1075.7	1058.4	1046.2
7.5°	1270.2	1242.7	1213.1	1182.6	1152.4	1125.3	1101.4	1080.9	1056.4	1031.6	1014.3
10°	1327.3	1287.1	1245.5	1203.1	1164.3	1127.9	1099.9	1072.4	1042.9	1014.5	993.0
12.5°	1379.2	1326.3	1278.4	1226.3	1176.7	1133.2	1092.8	1060.4	1025.0	994.7	970.2
15°	1444.9	1390.8	1332.8	1253.5	1187.7	1132.6	1083.6	1041.1	998.2	960.8	937.0
17.5°	1506.4	1424.9	1347.1	1280.9	1195.3	1126.5	1066.7	1015.8	968.8	929.2	899.8
20°	1531.8	1452.9	1368.3	1283.9	1199.8	1122.8	1053.2	997.2	948.2	903.4	876.3
22.5°	1547.0	1457.7	1368.7	1277.9	1188.7	1108.6	1039.8	978.1	925.1	882.4	849.0
25°	1564.9	1458.5	1360.4	1270.8	1179.7	1092.9	1011.2	945.8	888.4	843.1	807.6
27.5°	1576.6	1451.4	1335.6	1235.9	1143.6	1057.1	982.2	913.0	854.7	806.8	768.7
30°	1578.9	1445.8	1316.5	1208.7	1114.8	1035.5	956.1	889.8	828.2	777.3	741.8
32.5°	1581.9	1432.0	1290.8	1176.2	1080.1	1001.5	929.6	866.3	803.2	753.0	716.8
35°	1569.6	1424.4	1251.6	1120.0	1023.8	947.7	882.8	824.5	762.4	713.8	676.9
37.5°	1516.5	1394.0	1211.1	1056.7	956.1	885.6	832.8	781.9	725.0	672.5	637.8
40°	1463.1	1364.1	1179.7	1018.2	913.2	840.8	793.2	751.6	696.5	647.6	610.2
42.5°	1383.6	1323.5	1149.9	977.9	864.6	794.9	754.7	715.8	667.4	617.7	582.6
45°	1237.6	1245.5	1088.7	913.6	797.4	727.4	689.6	662.5	619.6	578.5	542.5
47.5°	1054.6	1128.8	1016.9	845.2	726.5	660.8	627.8	604.1	575.2	534.8	502.0
50°	935.1	1041.1	959.4	799.2	682.1	616.7	584.1	564.9	539.7	507.9	476.6
52.5°	824.9	938.8	889.9	748.1	633.9	574.2	542.2	526.5	506.4	476.5	448.3
55°	672.7	788.1	776.9	670.8	561.6	507.9	483.7	465.9	452.4	430.0	407.6
57.5°	544.2	653.5	659.3	585.0	497.9	444.9	424.0	410.6	401.8	384.9	364.2
60°	463.2	563.5	583.1	527.1	452.4	405.7	385.1	374.4	367.4	353.9	338.0
62.5°	395.9	481.3	503.5	463.2	408.7	365.0	348.9	338.6	333.8	322.1	308.1
65°	303.0	374.0	395.4	373.0	344.6	309.5	296.5	287.6	283.4	276.9	266.5
67.5°	227.8	279.6	303.1	287.3	277.1	254.9	246.6	241.8	238.1	233.6	225.1
70°	183.0	221.3	245.6	241.4	233.0	221.3	215.3	212.0	208.2	204.5	197.0
72.5°	147.1	173.5	196.3	198.4	191.5	189.1	183.9	182.4	180.2	175.8	171.7
75°	97.6	115.7	131.6	137.7	140.5	142.9	140.5	140.1	139.6	135.9	133.5
77.5°	63.9	73.7	83.7	94.1	98.5	101.7	102.5	104.2	102.9	100.9	99.8
80°	49.0	51.4	58.3	67.2	74.2	77.0	78.9	79.8	79.4	78.9	77.0
82.5°	35.6	37.5	40.8	47.1	53.0	57.6	58.8	58.6	59.6	59.8	58.3
85°	19.2	19.6	20.5	21.5	24.7	29.9	31.3	32.2	33.2	33.2	30.3
87.5°	7.1	6.6	7.1	7.0	7.9	8.2	10.3	12.0	12.5	11.1	11.3
90°	5.7	4.8	3.9	3.1	2.4	1.7	1.0	0.4	1.0	1.7	2.4
92.5°	11.1	10.5	10.0	9.5	9.1	8.6	8.1	7.7	8.1	8.6	9.1
95°	22.2	21.7	21.0	20.5	20.1	19.5	19.1	18.6	19.1	19.5	20.1
97.5°	35.7	35.3	34.9	34.5	34.2	33.8	33.3	33.0	33.3	33.8	34.2
100°	45.7	45.3	44.9	44.5	44.1	43.7	43.2	42.9	43.2	43.7	44.1
102.5°	56.5	56.0	55.6	55.2	54.9	54.7	54.5	54.2	54.5	54.7	54.9
105°	73.1	72.5	71.9	71.4	71.3	71.2	71.1	70.9	71.1	71.2	71.3
107.5°	91.3	91.0	90.8	90.7	90.6	90.5	90.4	90.3	90.4	90.5	90.6
110°	103.4	103.3	103.1	103.0	102.8	102.7	102.5	102.5	102.5	102.7	102.8



TEST NUMBER: P332301-940

CATALOG NUMBER: S123RDIP-S775D365U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	115.5	115.5	115.4	115.4	115.3	115.2	115.1	115.0	115.1	115.2	115.3
115°	134.6	134.6	134.8	134.7	134.6	134.4	134.1	133.9	134.1	134.4	134.6
117.5°	153.1	153.3	153.5	153.6	153.4	153.3	153.1	152.9	153.1	153.3	153.4
120°	165.9	166.2	166.5	166.5	166.0	165.7	165.2	164.8	165.2	165.7	166.0
122.5°	178.1	178.3	178.4	178.4	178.1	177.8	177.5	177.2	177.5	177.8	178.1
125°	196.6	196.7	196.9	196.9	196.6	196.4	196.2	196.0	196.2	196.4	196.6
127.5°	215.0	215.2	215.3	215.2	214.7	214.3	213.8	213.4	213.8	214.3	214.7
130°	227.0	227.2	227.4	227.2	226.7	226.1	225.5	225.0	225.5	226.1	226.7
132.5°	238.7	238.9	239.1	238.8	238.3	237.7	237.2	236.6	237.2	237.7	238.3
135°	256.0	256.1	256.2	256.0	255.6	255.1	254.8	254.3	254.8	255.1	255.6
137.5°	272.7	272.5	272.3	272.1	271.7	271.3	271.1	270.7	271.1	271.3	271.7
140°	283.7	283.7	283.7	283.5	283.1	282.8	282.4	282.0	282.4	282.8	283.1
142.5°	294.3	294.2	294.0	293.7	293.5	293.1	292.7	292.4	292.7	293.1	293.5
145°	309.7	309.4	309.2	309.1	308.9	308.8	308.6	308.5	308.6	308.8	308.9
147.5°	324.2	324.0	323.9	323.6	323.4	323.2	322.9	322.6	322.9	323.2	323.4
150°	333.4	333.3	333.1	333.1	332.9	332.7	332.6	332.4	332.6	332.7	332.9
152.5°	341.6	341.5	341.4	341.3	341.1	340.9	340.7	340.5	340.7	340.9	341.1
155°	353.4	353.4	353.3	353.3	353.3	353.3	353.3	353.3	353.3	353.3	353.3
157.5°	363.8	363.8	363.7	363.7	363.8	363.9	364.0	364.1	364.0	363.9	363.8
160°	370.2	370.2	370.2	370.3	370.5	370.6	370.8	370.9	370.8	370.6	370.5
162.5°	376.2	376.1	376.1	376.1	376.4	376.6	376.7	376.9	376.7	376.6	376.4
165°	383.8	383.8	383.8	383.9	384.1	384.3	384.6	384.8	384.6	384.3	384.1
167.5°	389.9	389.9	389.8	389.9	390.1	390.5	390.7	391.0	390.7	390.5	390.1
170°	393.2	393.2	393.2	393.4	393.7	394.0	394.2	394.5	394.2	394.0	393.7
172.5°	396.0	396.0	396.0	396.2	396.5	396.7	397.0	397.3	397.0	396.7	396.5
175°	399.0	399.0	399.0	399.1	399.4	399.7	399.9	400.2	399.9	399.7	399.4
177.5°	400.4	400.4	400.4	400.5	400.7	400.9	401.2	401.4	401.2	400.9	400.7
180°	401.2	401.2	401.2	401.2	401.2	401.2	401.2	401.2	401.2	401.2	401.2



TEST NUMBER: P332301-940

CATALOG NUMBER: S123RDIP-S775D365U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6
2.5°	1071.9	1067.0	1063.7	1056.2	1051.3	1046.2	1040.9	1044.3	1043.9	1043.5	1043.5
5°	1036.0	1025.2	1015.4	1002.8	994.9	985.1	977.6	976.7	978.6	972.0	968.2
7.5°	1000.3	985.6	971.7	957.8	943.1	931.3	923.9	920.4	915.7	911.7	907.5
10°	975.3	958.0	944.4	927.2	911.3	897.3	888.4	882.3	879.0	875.8	869.8
12.5°	949.5	932.6	915.3	895.8	880.7	864.4	857.8	851.0	844.7	841.1	832.8
15°	911.8	889.8	871.6	851.0	834.3	818.4	809.0	795.5	793.6	789.0	780.6
17.5°	874.0	850.2	825.0	809.9	790.9	774.4	760.1	755.5	742.2	737.2	729.9
20°	844.1	822.2	803.0	782.9	755.4	739.9	728.8	722.7	711.9	705.4	700.7
22.5°	818.3	796.0	773.8	750.5	727.7	710.4	702.2	692.8	687.0	677.8	672.7
25°	781.5	757.2	730.7	705.4	689.1	676.0	662.9	654.5	646.1	641.9	632.6
27.5°	738.8	713.4	688.5	669.4	649.3	636.4	624.6	617.1	607.0	599.9	594.8
30°	715.2	685.4	663.9	646.6	620.9	608.8	599.9	590.6	583.1	575.6	570.5
32.5°	688.0	660.7	640.3	618.9	599.2	586.0	574.5	566.3	559.9	552.9	547.7
35°	645.2	622.3	601.3	579.8	565.3	551.8	538.3	531.3	525.2	518.7	514.0
37.5°	606.5	585.1	565.2	544.8	526.9	515.9	505.0	499.6	491.4	487.1	482.2
40°	582.6	561.6	540.1	520.6	501.9	493.5	483.7	475.7	468.2	465.0	459.9
42.5°	556.5	535.5	517.4	496.2	481.0	469.6	460.5	451.8	446.2	441.5	438.5
45°	517.7	499.1	481.3	460.3	445.9	436.0	425.8	417.9	412.7	409.5	404.3
47.5°	480.1	461.5	443.4	425.1	411.1	399.9	389.7	384.1	377.3	373.3	369.9
50°	452.8	436.0	416.9	400.1	386.1	374.9	366.5	359.4	353.4	348.3	346.0
52.5°	427.8	409.9	393.3	377.7	362.9	350.3	342.6	335.2	330.6	324.8	322.0
55°	386.6	369.3	355.3	339.8	325.4	314.7	305.3	298.8	294.1	287.6	283.8
57.5°	347.8	332.3	315.6	302.2	287.3	278.2	270.5	261.6	255.9	250.8	247.2
60°	321.6	303.9	289.4	276.9	263.8	252.1	245.1	238.1	232.0	226.9	223.6
62.5°	294.4	278.9	265.2	251.5	239.5	229.3	221.2	215.3	210.0	206.7	203.5
65°	252.5	240.4	226.4	215.3	204.0	196.5	190.0	184.9	181.1	178.8	176.0
67.5°	214.1	202.3	190.1	179.1	171.7	165.9	161.7	157.2	155.3	152.4	150.5
70°	189.0	176.9	166.2	157.8	150.3	146.2	143.3	140.1	138.2	134.5	132.6
72.5°	161.8	153.0	145.3	138.4	132.4	128.6	125.0	121.0	118.1	113.9	112.1
75°	127.4	119.5	113.4	108.8	105.0	99.9	94.8	90.6	89.2	87.7	87.3
77.5°	94.4	89.3	85.0	81.1	76.4	72.7	71.5	70.6	70.3	69.6	69.6
80°	74.2	69.6	66.3	61.6	58.9	58.9	58.9	57.9	58.3	58.3	58.3
82.5°	55.2	50.9	49.1	47.4	46.9	47.3	47.3	47.4	47.2	47.9	47.5
85°	28.4	29.0	29.9	29.4	29.9	29.9	30.9	30.3	30.9	29.9	30.9
87.5°	11.1	12.4	12.9	13.5	14.0	13.8	14.3	14.4	14.7	14.8	14.9
90°	3.1	3.9	4.8	5.7	6.7	7.6	7.8	8.1	8.4	8.6	8.9
92.5°	9.5	10.0	10.5	11.1	11.6	12.1	12.3	12.6	12.8	13.0	13.1
95°	20.5	21.0	21.7	22.2	22.7	23.4	23.6	23.9	24.2	24.4	24.6
97.5°	34.5	34.9	35.3	35.7	36.1	36.5	36.8	37.1	37.5	37.8	37.9
100°	44.5	44.9	45.3	45.7	46.0	46.3	46.5	46.7	47.0	47.2	47.3
102.5°	55.2	55.6	56.0	56.5	57.0	57.4	57.6	57.9	58.1	58.2	58.3
105°	71.4	71.9	72.5	73.1	73.7	74.4	74.4	74.4	74.4	74.4	74.5
107.5°	90.7	90.8	91.0	91.3	91.6	91.8	92.0	92.3	92.5	92.7	92.8
110°	103.0	103.1	103.3	103.4	103.5	103.7	104.0	104.2	104.5	104.8	104.9



TEST NUMBER: P332301-940

CATALOG NUMBER: S123RDIP-S775D365U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	115.4	115.4	115.5	115.5	115.5	115.6	115.8	116.2	116.5	116.9	117.0
115°	134.7	134.8	134.6	134.6	134.4	134.2	134.3	134.4	134.5	134.6	134.6
117.5°	153.6	153.5	153.3	153.1	152.9	152.8	152.8	152.8	152.8	152.8	152.6
120°	166.5	166.5	166.2	165.9	165.5	165.1	165.1	165.0	164.9	164.9	164.7
122.5°	178.4	178.4	178.3	178.1	177.9	177.7	177.5	177.4	177.2	177.0	176.8
125°	196.9	196.9	196.7	196.6	196.4	196.4	196.0	195.7	195.5	195.2	194.9
127.5°	215.2	215.3	215.2	215.0	214.9	214.7	214.4	213.9	213.6	213.1	212.8
130°	227.2	227.4	227.2	227.0	226.8	226.6	226.3	226.0	225.7	225.4	225.1
132.5°	238.8	239.1	238.9	238.7	238.5	238.4	238.1	237.7	237.4	237.1	236.7
135°	256.0	256.2	256.1	256.0	255.9	255.9	255.6	255.3	255.0	254.8	254.6
137.5°	272.1	272.3	272.5	272.7	272.9	273.0	272.8	272.5	272.2	271.9	271.6
140°	283.5	283.7	283.7	283.7	283.8	283.9	283.8	283.7	283.7	283.7	283.4
142.5°	293.7	294.0	294.2	294.3	294.4	294.5	294.4	294.4	294.3	294.3	294.0
145°	309.1	309.2	309.4	309.7	309.9	310.0	310.0	310.0	309.9	309.8	309.6
147.5°	323.6	323.9	324.0	324.2	324.4	324.7	324.7	324.7	324.7	324.7	324.4
150°	333.1	333.1	333.3	333.4	333.6	333.7	333.7	333.7	333.7	333.7	333.5
152.5°	341.3	341.4	341.5	341.6	341.7	341.8	341.9	342.0	342.1	342.2	342.1
155°	353.3	353.3	353.4	353.4	353.5	353.6	353.8	354.1	354.4	354.7	354.5
157.5°	363.7	363.7	363.8	363.8	363.9	364.0	364.3	364.5	364.9	365.2	365.1
160°	370.3	370.2	370.2	370.2	370.2	370.2	370.6	371.0	371.3	371.7	371.7
162.5°	376.1	376.1	376.1	376.2	376.3	376.3	376.7	377.0	377.4	377.7	377.6
165°	383.9	383.8	383.8	383.8	383.8	383.8	384.2	384.7	385.0	385.5	385.5
167.5°	389.9	389.8	389.9	389.9	389.9	390.0	390.4	390.8	391.3	391.7	391.7
170°	393.4	393.2	393.2	393.2	393.2	393.2	393.8	394.2	394.8	395.2	395.2
172.5°	396.2	396.0	396.0	396.0	396.0	396.0	396.5	396.9	397.3	397.8	397.8
175°	399.1	399.0	399.0	399.0	399.0	399.0	399.4	399.8	400.2	400.6	400.6
177.5°	400.5	400.4	400.4	400.4	400.4	400.4	400.7	401.1	401.4	401.7	401.7
180°	401.2	401.2	401.2	401.2	401.2	401.2	401.2	401.2	401.2	401.2	401.2



TEST NUMBER: P332301-940

CATALOG NUMBER: S123RDIP-S775D365U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6
2.5°	1039.0	1038.7	1039.0	1037.5	1039.0	1038.7	1039.0	1043.5	1043.5	1043.9	1044.3
5°	966.9	966.3	965.0	960.8	965.0	966.3	966.9	968.2	972.0	978.6	976.7
7.5°	903.8	903.2	899.1	899.2	899.1	903.2	903.8	907.5	911.7	915.7	920.4
10°	866.5	866.9	861.4	858.1	861.4	866.9	866.5	869.8	875.8	879.0	882.3
12.5°	830.3	828.1	823.6	820.0	823.6	828.1	830.3	832.8	841.1	844.7	851.0
15°	782.5	777.8	766.6	767.5	766.6	777.8	782.5	780.6	789.0	793.6	795.5
17.5°	726.1	722.7	722.5	716.0	722.5	722.7	726.1	729.9	737.2	742.2	755.5
20°	693.3	691.0	691.9	685.4	691.9	691.0	693.3	700.7	705.4	711.9	722.7
22.5°	667.5	665.2	661.3	659.2	661.3	665.2	667.5	672.7	677.8	687.0	692.8
25°	629.8	626.1	622.3	624.6	622.3	626.1	629.8	632.6	641.9	646.1	654.5
27.5°	592.1	589.2	585.5	585.1	585.5	589.2	592.1	594.8	599.9	607.0	617.1
30°	568.2	565.3	563.5	561.2	563.5	565.3	568.2	570.5	575.6	583.1	590.6
32.5°	543.9	543.3	539.9	539.5	539.9	543.3	543.9	547.7	552.9	559.9	566.3
35°	512.1	509.3	508.4	508.9	508.4	509.3	512.1	514.0	518.7	525.2	531.3
37.5°	482.0	478.2	476.5	474.9	476.5	478.2	482.0	482.2	487.1	491.4	499.6
40°	460.3	456.6	455.7	454.7	455.7	456.6	460.3	459.9	465.0	468.2	475.7
42.5°	436.0	434.5	434.0	432.3	434.0	434.5	436.0	438.5	441.5	446.2	451.8
45°	402.9	402.4	399.7	400.6	399.7	402.4	402.9	404.3	409.5	412.7	417.9
47.5°	368.0	366.0	364.0	365.2	364.0	366.0	368.0	369.9	373.3	377.3	384.1
50°	344.1	343.1	338.9	339.8	338.9	343.1	344.1	346.0	348.3	353.4	359.4
52.5°	320.2	316.6	315.0	314.5	315.0	316.6	320.2	322.0	324.8	330.6	335.2
55°	280.6	276.3	274.5	273.6	274.5	276.3	280.6	283.8	287.6	294.1	298.8
57.5°	241.7	240.6	239.2	240.1	239.2	240.6	241.7	247.2	250.8	255.9	261.6
60°	218.9	218.9	218.9	218.5	218.9	218.9	218.9	223.6	226.9	232.0	238.1
62.5°	201.4	200.3	199.9	200.5	199.9	200.3	201.4	203.5	206.7	210.0	215.3
65°	174.6	174.2	172.3	171.8	172.3	174.2	174.6	176.0	178.8	181.1	184.9
67.5°	149.3	147.6	147.0	146.4	147.0	147.6	149.3	150.5	152.4	155.3	157.2
70°	130.3	129.3	126.5	127.0	126.5	129.3	130.3	132.6	134.5	138.2	140.1
72.5°	109.7	108.8	108.3	107.5	108.3	108.8	109.7	112.1	113.9	118.1	121.0
75°	86.9	86.4	85.9	87.7	85.9	86.4	86.9	87.3	87.7	89.2	90.6
77.5°	69.6	69.6	69.8	69.1	69.8	69.6	69.6	69.6	69.6	70.3	70.6
80°	58.3	58.3	57.9	57.9	57.9	58.3	58.3	58.3	58.3	58.3	57.9
82.5°	46.8	47.2	47.4	46.7	47.4	47.2	46.8	47.5	47.9	47.2	47.4
85°	30.9	30.3	31.3	30.9	31.3	30.3	30.9	30.9	29.9	30.9	30.3
87.5°	15.6	14.9	14.9	15.3	14.9	14.9	15.6	14.9	14.8	14.7	14.4
90°	9.0	9.2	9.3	9.5	9.3	9.2	9.0	8.9	8.6	8.4	8.1
92.5°	13.0	12.9	12.8	12.8	12.8	12.9	13.0	13.1	13.0	12.8	12.6
95°	24.6	24.6	24.6	24.6	24.6	24.6	24.6	24.6	24.4	24.2	23.9
97.5°	37.9	37.9	37.8	37.8	37.8	37.9	37.9	37.9	37.8	37.5	37.1
100°	47.4	47.6	47.8	47.9	47.8	47.6	47.4	47.3	47.2	47.0	46.7
102.5°	58.3	58.3	58.2	58.2	58.2	58.3	58.3	58.3	58.2	58.1	57.9
105°	74.5	74.7	74.9	75.0	74.9	74.7	74.5	74.5	74.4	74.4	74.4
107.5°	92.7	92.6	92.6	92.5	92.6	92.6	92.7	92.8	92.7	92.5	92.3
110°	104.7	104.6	104.4	104.3	104.4	104.6	104.7	104.9	104.8	104.5	104.2



TEST NUMBER: P332301-940

CATALOG NUMBER: S123RDIP-S775D365U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	117.0	117.0	116.9	116.9	116.9	117.0	117.0	117.0	116.9	116.5	116.2
115°	134.5	134.4	134.3	134.2	134.3	134.4	134.5	134.6	134.6	134.5	134.4
117.5°	152.4	152.2	152.0	151.9	152.0	152.2	152.4	152.6	152.8	152.8	152.8
120°	164.6	164.4	164.3	164.2	164.3	164.4	164.6	164.7	164.9	164.9	165.0
122.5°	176.6	176.4	176.2	176.0	176.2	176.4	176.6	176.8	177.0	177.2	177.4
125°	194.7	194.4	194.0	193.8	194.0	194.4	194.7	194.9	195.2	195.5	195.7
127.5°	212.5	212.1	211.9	211.5	211.9	212.1	212.5	212.8	213.1	213.6	213.9
130°	224.6	224.1	223.6	223.1	223.6	224.1	224.6	225.1	225.4	225.7	226.0
132.5°	236.3	235.9	235.6	235.2	235.6	235.9	236.3	236.7	237.1	237.4	237.7
135°	254.4	254.2	254.1	254.0	254.1	254.2	254.4	254.6	254.8	255.0	255.3
137.5°	271.3	271.1	270.8	270.5	270.8	271.1	271.3	271.6	271.9	272.2	272.5
140°	282.9	282.4	281.9	281.4	281.9	282.4	282.9	283.4	283.7	283.7	283.7
142.5°	293.6	293.3	292.8	292.5	292.8	293.3	293.6	294.0	294.3	294.3	294.4
145°	309.3	309.1	308.8	308.5	308.8	309.1	309.3	309.6	309.8	309.9	310.0
147.5°	324.0	323.6	323.2	322.7	323.2	323.6	324.0	324.4	324.7	324.7	324.7
150°	333.1	332.7	332.3	331.8	332.3	332.7	333.1	333.5	333.7	333.7	333.7
152.5°	341.7	341.3	341.0	340.6	341.0	341.3	341.7	342.1	342.2	342.1	342.0
155°	354.1	353.6	353.1	352.6	353.1	353.6	354.1	354.5	354.7	354.4	354.1
157.5°	364.7	364.4	363.9	363.6	363.9	364.4	364.7	365.1	365.2	364.9	364.5
160°	371.4	371.1	370.9	370.6	370.9	371.1	371.4	371.7	371.7	371.3	371.0
162.5°	377.2	376.7	376.3	375.9	376.3	376.7	377.2	377.6	377.7	377.4	377.0
165°	385.0	384.5	384.0	383.5	384.0	384.5	385.0	385.5	385.5	385.0	384.7
167.5°	391.3	390.8	390.4	390.0	390.4	390.8	391.3	391.7	391.7	391.3	390.8
170°	394.8	394.2	393.8	393.2	393.8	394.2	394.8	395.2	395.2	394.8	394.2
172.5°	397.3	396.8	396.3	395.8	396.3	396.8	397.3	397.8	397.8	397.3	396.9
175°	400.1	399.6	399.1	398.6	399.1	399.6	400.1	400.6	400.6	400.2	399.8
177.5°	401.4	400.9	400.6	400.1	400.6	400.9	401.4	401.7	401.7	401.4	401.1
180°	401.2	401.2	401.2	401.2	401.2	401.2	401.2	401.2	401.2	401.2	401.2



TEST NUMBER: P332301-940

CATALOG NUMBER: S123RDIP-S775D365U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6
2.5°	1040.9	1046.2	1051.3	1056.2	1063.7	1067.0	1071.9	1073.8	1079.3	1087.6	1094.3
5°	977.6	985.1	994.9	1002.8	1015.4	1025.2	1036.0	1046.2	1058.4	1075.7	1091.0
7.5°	923.9	931.3	943.1	957.8	971.7	985.6	1000.3	1014.3	1031.6	1056.4	1080.9
10°	888.4	897.3	911.3	927.2	944.4	958.0	975.3	993.0	1014.5	1042.9	1072.4
12.5°	857.8	864.4	880.7	895.8	915.3	932.6	949.5	970.2	994.7	1025.0	1060.4
15°	809.0	818.4	834.3	851.0	871.6	889.8	911.8	937.0	960.8	998.2	1041.1
17.5°	760.1	774.4	790.9	809.9	825.0	850.2	874.0	899.8	929.2	968.8	1015.8
20°	728.8	739.9	755.4	782.9	803.0	822.2	844.1	876.3	903.4	948.2	997.2
22.5°	702.2	710.4	727.7	750.5	773.8	796.0	818.3	849.0	882.4	925.1	978.1
25°	662.9	676.0	689.1	705.4	730.7	757.2	781.5	807.6	843.1	888.4	945.8
27.5°	624.6	636.4	649.3	669.4	688.5	713.4	738.8	768.7	806.8	854.7	913.0
30°	599.9	608.8	620.9	646.6	663.9	685.4	715.2	741.8	777.3	828.2	889.8
32.5°	574.5	586.0	599.2	618.9	640.3	660.7	688.0	716.8	753.0	803.2	866.3
35°	538.3	551.8	565.3	579.8	601.3	622.3	645.2	676.9	713.8	762.4	824.5
37.5°	505.0	515.9	526.9	544.8	565.2	585.1	606.5	637.8	672.5	725.0	781.9
40°	483.7	493.5	501.9	520.6	540.1	561.6	582.6	610.2	647.6	696.5	751.6
42.5°	460.5	469.6	481.0	496.2	517.4	535.5	556.5	582.6	617.7	667.4	715.8
45°	425.8	436.0	445.9	460.3	481.3	499.1	517.7	542.5	578.5	619.6	662.5
47.5°	389.7	399.9	411.1	425.1	443.4	461.5	480.1	502.0	534.8	575.2	604.1
50°	366.5	374.9	386.1	400.1	416.9	436.0	452.8	476.6	507.9	539.7	564.9
52.5°	342.6	350.3	362.9	377.7	393.3	409.9	427.8	448.3	476.5	506.4	526.5
55°	305.3	314.7	325.4	339.8	355.3	369.3	386.6	407.6	430.0	452.4	465.9
57.5°	270.5	278.2	287.3	302.2	315.6	332.3	347.8	364.2	384.9	401.8	410.6
60°	245.1	252.1	263.8	276.9	289.4	303.9	321.6	338.0	353.9	367.4	374.4
62.5°	221.2	229.3	239.5	251.5	265.2	278.9	294.4	308.1	322.1	333.8	338.6
65°	190.0	196.5	204.0	215.3	226.4	240.4	252.5	266.5	276.9	283.4	287.6
67.5°	161.7	165.9	171.7	179.1	190.1	202.3	214.1	225.1	233.6	238.1	241.8
70°	143.3	146.2	150.3	157.8	166.2	176.9	189.0	197.0	204.5	208.2	212.0
72.5°	125.0	128.6	132.4	138.4	145.3	153.0	161.8	171.7	175.8	180.2	182.4
75°	94.8	99.9	105.0	108.8	113.4	119.5	127.4	133.5	135.9	139.6	140.1
77.5°	71.5	72.7	76.4	81.1	85.0	89.3	94.4	99.8	100.9	102.9	104.2
80°	58.9	58.9	58.9	61.6	66.3	69.6	74.2	77.0	78.9	79.4	79.8
82.5°	47.3	47.3	46.9	47.4	49.1	50.9	55.2	58.3	59.8	59.6	58.6
85°	30.9	29.9	29.9	29.4	29.9	29.0	28.4	30.3	33.2	33.2	32.2
87.5°	14.3	13.8	14.0	13.5	12.9	12.4	11.1	11.3	11.1	12.5	12.0
90°	7.8	7.6	6.7	5.7	4.8	3.9	3.1	2.4	1.7	1.0	0.4
92.5°	12.3	12.1	11.6	11.1	10.5	10.0	9.5	9.1	8.6	8.1	7.7
95°	23.6	23.4	22.7	22.2	21.7	21.0	20.5	20.1	19.5	19.1	18.6
97.5°	36.8	36.5	36.1	35.7	35.3	34.9	34.5	34.2	33.8	33.3	33.0
100°	46.5	46.3	46.0	45.7	45.3	44.9	44.5	44.1	43.7	43.2	42.9
102.5°	57.6	57.4	57.0	56.5	56.0	55.6	55.2	54.9	54.7	54.5	54.2
105°	74.4	74.4	73.7	73.1	72.5	71.9	71.4	71.3	71.2	71.1	70.9
107.5°	92.0	91.8	91.6	91.3	91.0	90.8	90.7	90.6	90.5	90.4	90.3
110°	104.0	103.7	103.5	103.4	103.3	103.1	103.0	102.8	102.7	102.5	102.5



TEST NUMBER: P332301-940

CATALOG NUMBER: S123RDIP-S775D365U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	115.8	115.6	115.5	115.5	115.5	115.4	115.4	115.3	115.2	115.1	115.0
115°	134.3	134.2	134.4	134.6	134.6	134.8	134.7	134.6	134.4	134.1	133.9
117.5°	152.8	152.8	152.9	153.1	153.3	153.5	153.6	153.4	153.3	153.1	152.9
120°	165.1	165.1	165.5	165.9	166.2	166.5	166.5	166.0	165.7	165.2	164.8
122.5°	177.5	177.7	177.9	178.1	178.3	178.4	178.4	178.1	177.8	177.5	177.2
125°	196.0	196.4	196.4	196.6	196.7	196.9	196.9	196.6	196.4	196.2	196.0
127.5°	214.4	214.7	214.9	215.0	215.2	215.3	215.2	214.7	214.3	213.8	213.4
130°	226.3	226.6	226.8	227.0	227.2	227.4	227.2	226.7	226.1	225.5	225.0
132.5°	238.1	238.4	238.5	238.7	238.9	239.1	238.8	238.3	237.7	237.2	236.6
135°	255.6	255.9	255.9	256.0	256.1	256.2	256.0	255.6	255.1	254.8	254.3
137.5°	272.8	273.0	272.9	272.7	272.5	272.3	272.1	271.7	271.3	271.1	270.7
140°	283.8	283.9	283.8	283.7	283.7	283.7	283.5	283.1	282.8	282.4	282.0
142.5°	294.4	294.5	294.4	294.3	294.2	294.0	293.7	293.5	293.1	292.7	292.4
145°	310.0	310.0	309.9	309.7	309.4	309.2	309.1	308.9	308.8	308.6	308.5
147.5°	324.7	324.7	324.4	324.2	324.0	323.9	323.6	323.4	323.2	322.9	322.6
150°	333.7	333.7	333.6	333.4	333.3	333.1	333.1	332.9	332.7	332.6	332.4
152.5°	341.9	341.8	341.7	341.6	341.5	341.4	341.3	341.1	340.9	340.7	340.5
155°	353.8	353.6	353.5	353.4	353.4	353.3	353.3	353.3	353.3	353.3	353.3
157.5°	364.3	364.0	363.9	363.8	363.8	363.7	363.7	363.8	363.9	364.0	364.1
160°	370.6	370.2	370.2	370.2	370.2	370.2	370.3	370.5	370.6	370.8	370.9
162.5°	376.7	376.3	376.3	376.2	376.1	376.1	376.1	376.4	376.6	376.7	376.9
165°	384.2	383.8	383.8	383.8	383.8	383.8	383.9	384.1	384.3	384.6	384.8
167.5°	390.4	390.0	389.9	389.9	389.9	389.8	389.9	390.1	390.5	390.7	391.0
170°	393.8	393.2	393.2	393.2	393.2	393.2	393.4	393.7	394.0	394.2	394.5
172.5°	396.5	396.0	396.0	396.0	396.0	396.0	396.2	396.5	396.7	397.0	397.3
175°	399.4	399.0	399.0	399.0	399.0	399.0	399.1	399.4	399.7	399.9	400.2
177.5°	400.7	400.4	400.4	400.4	400.4	400.4	400.5	400.7	400.9	401.2	401.4
180°	401.2	401.2	401.2	401.2	401.2	401.2	401.2	401.2	401.2	401.2	401.2



TEST NUMBER: P332301-940

CATALOG NUMBER: S123RDIP-S775D365U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6
2.5°	1096.5	1100.6	1105.9	1113.7	1119.7	1124.9	1126.1	1127.6	1131.3	1137.6	1142.5
5°	1103.7	1114.4	1131.7	1148.4	1166.7	1181.6	1195.6	1205.4	1214.8	1234.4	1250.3
7.5°	1101.4	1125.3	1152.4	1182.6	1213.1	1242.7	1270.2	1294.7	1319.1	1347.7	1380.3
10°	1099.9	1127.9	1164.3	1203.1	1245.5	1287.1	1327.3	1358.5	1395.0	1427.6	1469.2
12.5°	1092.8	1133.2	1176.7	1226.3	1278.4	1326.3	1379.2	1422.5	1464.1	1511.3	1559.6
15°	1083.6	1132.6	1187.7	1253.5	1332.8	1390.8	1444.9	1520.1	1571.5	1622.8	1691.8
17.5°	1066.7	1126.5	1195.3	1280.9	1347.1	1424.9	1506.4	1565.8	1635.0	1707.3	1769.9
20°	1053.2	1122.8	1199.8	1283.9	1368.3	1452.9	1531.8	1602.7	1674.2	1757.7	1809.1
22.5°	1039.8	1108.6	1188.7	1277.9	1368.7	1457.7	1547.0	1630.3	1710.7	1795.1	1860.6
25°	1011.2	1092.9	1179.7	1270.8	1360.4	1458.5	1564.9	1657.8	1757.2	1844.1	1906.2
27.5°	982.2	1057.1	1143.6	1235.9	1335.6	1451.4	1576.6	1682.3	1781.9	1844.1	1863.6
30°	956.1	1035.5	1114.8	1208.7	1316.5	1445.8	1578.9	1699.8	1781.5	1808.6	1788.5
32.5°	929.6	1001.5	1080.1	1176.2	1290.8	1432.0	1581.9	1689.3	1738.6	1717.9	1636.1
35°	882.8	947.7	1023.8	1120.0	1251.6	1424.4	1569.6	1642.4	1630.2	1513.5	1359.5
37.5°	832.8	885.6	956.1	1056.7	1211.1	1394.0	1516.5	1527.2	1422.2	1243.0	1065.1
40°	793.2	840.8	913.2	1018.2	1179.7	1364.1	1463.1	1419.7	1256.8	1057.4	909.0
42.5°	754.7	794.9	864.6	977.9	1149.9	1323.5	1383.6	1289.0	1101.0	912.5	777.5
45°	689.6	727.4	797.4	913.6	1088.7	1245.5	1237.6	1073.3	885.2	733.4	621.3
47.5°	627.8	660.8	726.5	845.2	1016.9	1128.8	1054.6	879.8	720.1	598.4	518.5
50°	584.1	616.7	682.1	799.2	959.4	1041.1	935.1	766.6	620.5	519.6	456.1
52.5°	542.2	574.2	633.9	748.1	889.9	938.8	824.9	668.7	546.9	459.9	405.3
55°	483.7	507.9	561.6	670.8	776.9	788.1	672.7	542.0	441.7	380.9	343.6
57.5°	424.0	444.9	497.9	585.0	659.3	653.5	544.2	431.1	363.5	318.4	291.3
60°	385.1	405.7	452.4	527.1	583.1	563.5	463.2	372.1	314.1	281.1	259.6
62.5°	348.9	365.0	408.7	463.2	503.5	481.3	395.9	320.6	274.6	246.6	229.7
65°	296.5	309.5	344.6	373.0	395.4	374.0	303.0	250.7	217.6	198.0	186.3
67.5°	246.6	254.9	277.1	287.3	303.1	279.6	227.8	192.8	174.0	157.4	149.3
70°	215.3	221.3	233.0	241.4	245.6	221.3	183.0	157.3	141.4	129.7	124.7
72.5°	183.9	189.1	191.5	198.4	196.3	173.5	147.1	126.7	115.3	107.4	100.8
75°	140.5	142.9	140.5	137.7	131.6	115.7	97.6	87.3	78.9	75.2	72.9
77.5°	102.5	101.7	98.5	94.1	83.7	73.7	63.9	60.5	56.9	54.9	54.0
80°	78.9	77.0	74.2	67.2	58.3	51.4	49.0	46.7	45.3	43.0	42.4
82.5°	58.8	57.6	53.0	47.1	40.8	37.5	35.6	34.8	33.3	32.1	32.0
85°	31.3	29.9	24.7	21.5	20.5	19.6	19.2	19.2	17.3	16.8	16.8
87.5°	10.3	8.2	7.9	7.0	7.1	6.6	7.1	6.6	6.3	6.8	6.1
90°	1.0	1.7	2.4	3.1	3.9	4.8	5.7	6.7	7.6	7.8	8.1
92.5°	8.1	8.6	9.1	9.5	10.0	10.5	11.1	11.6	12.1	12.3	12.6
95°	19.1	19.5	20.1	20.5	21.0	21.7	22.2	22.7	23.4	23.6	23.9
97.5°	33.3	33.8	34.2	34.5	34.9	35.3	35.7	36.1	36.5	36.8	37.1
100°	43.2	43.7	44.1	44.5	44.9	45.3	45.7	46.0	46.3	46.5	46.7
102.5°	54.5	54.7	54.9	55.2	55.6	56.0	56.5	57.0	57.4	57.6	57.9
105°	71.1	71.2	71.3	71.4	71.9	72.5	73.1	73.7	74.4	74.4	74.4
107.5°	90.4	90.5	90.6	90.7	90.8	91.0	91.3	91.6	91.8	92.0	92.3
110°	102.5	102.7	102.8	103.0	103.1	103.3	103.4	103.5	103.7	104.0	104.2



TEST NUMBER: P332301-940

CATALOG NUMBER: S123RDIP-S775D365U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	115.1	115.2	115.3	115.4	115.4	115.5	115.5	115.5	115.6	115.8	116.2
115°	134.1	134.4	134.6	134.7	134.8	134.6	134.6	134.4	134.2	134.3	134.4
117.5°	153.1	153.3	153.4	153.6	153.5	153.3	153.1	152.9	152.8	152.8	152.8
120°	165.2	165.7	166.0	166.5	166.5	166.2	165.9	165.5	165.1	165.1	165.0
122.5°	177.5	177.8	178.1	178.4	178.4	178.3	178.1	177.9	177.7	177.5	177.4
125°	196.2	196.4	196.6	196.9	196.9	196.7	196.6	196.4	196.4	196.0	195.7
127.5°	213.8	214.3	214.7	215.2	215.3	215.2	215.0	214.9	214.7	214.4	213.9
130°	225.5	226.1	226.7	227.2	227.4	227.2	227.0	226.8	226.6	226.3	226.0
132.5°	237.2	237.7	238.3	238.8	239.1	238.9	238.7	238.5	238.4	238.1	237.7
135°	254.8	255.1	255.6	256.0	256.2	256.1	256.0	255.9	255.9	255.6	255.3
137.5°	271.1	271.3	271.7	272.1	272.3	272.5	272.7	272.9	273.0	272.8	272.5
140°	282.4	282.8	283.1	283.5	283.7	283.7	283.7	283.8	283.9	283.8	283.7
142.5°	292.7	293.1	293.5	293.7	294.0	294.2	294.3	294.4	294.5	294.4	294.4
145°	308.6	308.8	308.9	309.1	309.2	309.4	309.7	309.9	310.0	310.0	310.0
147.5°	322.9	323.2	323.4	323.6	323.9	324.0	324.2	324.4	324.7	324.7	324.7
150°	332.6	332.7	332.9	333.1	333.1	333.3	333.4	333.6	333.7	333.7	333.7
152.5°	340.7	340.9	341.1	341.3	341.4	341.5	341.6	341.7	341.8	341.9	342.0
155°	353.3	353.3	353.3	353.3	353.3	353.4	353.4	353.5	353.6	353.8	354.1
157.5°	364.0	363.9	363.8	363.7	363.7	363.8	363.8	363.9	364.0	364.3	364.5
160°	370.8	370.6	370.5	370.3	370.2	370.2	370.2	370.2	370.2	370.6	371.0
162.5°	376.7	376.6	376.4	376.1	376.1	376.1	376.2	376.3	376.3	376.7	377.0
165°	384.6	384.3	384.1	383.9	383.8	383.8	383.8	383.8	383.8	384.2	384.7
167.5°	390.7	390.5	390.1	389.9	389.8	389.9	389.9	389.9	390.0	390.4	390.8
170°	394.2	394.0	393.7	393.4	393.2	393.2	393.2	393.2	393.2	393.8	394.2
172.5°	397.0	396.7	396.5	396.2	396.0	396.0	396.0	396.0	396.0	396.5	396.9
175°	399.9	399.7	399.4	399.1	399.0	399.0	399.0	399.0	399.0	399.4	399.8
177.5°	401.2	400.9	400.7	400.5	400.4	400.4	400.4	400.4	400.4	400.7	401.1
180°	401.2	401.2	401.2	401.2	401.2	401.2	401.2	401.2	401.2	401.2	401.2



TEST NUMBER: P332301-940

CATALOG NUMBER: S123RDIP-S775D365U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6
2.5°	1150.3	1150.3	1151.8	1157.4	1158.2	1163.1	1161.5
5°	1264.3	1273.1	1276.4	1290.4	1298.8	1302.5	1295.0
7.5°	1403.6	1428.6	1440.5	1455.1	1468.1	1472.0	1461.8
10°	1505.1	1531.2	1553.3	1566.7	1579.4	1587.8	1598.5
12.5°	1603.4	1635.5	1656.4	1675.4	1688.5	1699.1	1700.8
15°	1710.1	1758.6	1795.5	1822.6	1836.1	1843.2	1840.3
17.5°	1817.8	1862.8	1889.0	1916.6	1935.4	1936.4	1936.9
20°	1878.7	1922.5	1952.8	1973.4	1994.4	1993.5	1998.1
22.5°	1919.3	1953.9	1977.1	1992.1	1999.3	1995.7	1996.6
25°	1938.4	1948.7	1944.5	1920.7	1914.6	1892.7	1896.4
27.5°	1840.1	1791.6	1741.3	1676.8	1625.8	1585.1	1587.2
30°	1706.8	1621.0	1522.9	1440.7	1367.0	1346.4	1302.5
32.5°	1520.5	1391.6	1276.8	1200.2	1136.8	1119.7	1081.5
35°	1204.5	1079.3	961.3	890.3	862.3	823.0	822.6
37.5°	936.2	826.1	763.6	710.3	682.4	658.7	656.4
40°	787.6	701.7	654.5	616.3	588.7	571.0	566.8
42.5°	683.8	614.3	570.2	546.4	525.2	516.0	509.3
45°	558.4	511.7	480.9	459.4	449.6	442.6	438.8
47.5°	467.1	435.8	414.7	400.5	392.5	385.1	387.1
50°	417.4	391.7	376.3	362.7	356.7	351.5	352.0
52.5°	377.4	354.4	341.9	332.2	324.6	320.9	319.1
55°	320.3	305.8	293.2	286.1	282.0	276.9	275.4
57.5°	273.2	262.0	251.7	243.8	242.7	237.8	238.4
60°	241.8	232.5	224.1	219.9	216.6	212.4	213.8
62.5°	216.1	208.2	200.5	197.1	193.9	190.7	191.5
65°	176.9	169.4	164.8	162.9	161.5	160.2	158.7
67.5°	141.0	136.4	133.5	129.5	126.6	126.2	124.8
70°	118.6	112.5	107.4	102.3	100.9	100.4	100.9
72.5°	95.1	91.2	89.8	87.3	87.0	85.8	86.7
75°	71.4	70.0	69.1	67.2	67.2	67.2	67.2
77.5°	52.7	51.8	51.3	50.9	50.4	49.8	49.7
80°	41.1	40.6	39.7	39.7	39.2	39.7	39.2
82.5°	31.0	30.9	30.0	30.0	29.5	29.2	29.5
85°	15.9	15.4	16.3	15.4	15.9	15.0	15.9
87.5°	6.2	6.2	5.9	5.9	5.5	6.3	5.6
90°	8.4	8.6	8.9	9.0	9.2	9.3	9.5
92.5°	12.8	13.0	13.1	13.0	12.9	12.8	12.8
95°	24.2	24.4	24.6	24.6	24.6	24.6	24.6
97.5°	37.5	37.8	37.9	37.9	37.9	37.8	37.8
100°	47.0	47.2	47.3	47.4	47.6	47.8	47.9
102.5°	58.1	58.2	58.3	58.3	58.3	58.2	58.2
105°	74.4	74.4	74.5	74.5	74.7	74.9	75.0
107.5°	92.5	92.7	92.8	92.7	92.6	92.6	92.5
110°	104.5	104.8	104.9	104.7	104.6	104.4	104.3



TEST NUMBER: P332301-940

CATALOG NUMBER: S123RDIP-S775D365U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	116.5	116.9	117.0	117.0	117.0	116.9	116.9
115°	134.5	134.6	134.6	134.5	134.4	134.3	134.2
117.5°	152.8	152.8	152.6	152.4	152.2	152.0	151.9
120°	164.9	164.9	164.7	164.6	164.4	164.3	164.2
122.5°	177.2	177.0	176.8	176.6	176.4	176.2	176.0
125°	195.5	195.2	194.9	194.7	194.4	194.0	193.8
127.5°	213.6	213.1	212.8	212.5	212.1	211.9	211.5
130°	225.7	225.4	225.1	224.6	224.1	223.6	223.1
132.5°	237.4	237.1	236.7	236.3	235.9	235.6	235.2
135°	255.0	254.8	254.6	254.4	254.2	254.1	254.0
137.5°	272.2	271.9	271.6	271.3	271.1	270.8	270.5
140°	283.7	283.7	283.4	282.9	282.4	281.9	281.4
142.5°	294.3	294.3	294.0	293.6	293.3	292.8	292.5
145°	309.9	309.8	309.6	309.3	309.1	308.8	308.5
147.5°	324.7	324.7	324.4	324.0	323.6	323.2	322.7
150°	333.7	333.7	333.5	333.1	332.7	332.3	331.8
152.5°	342.1	342.2	342.1	341.7	341.3	341.0	340.6
155°	354.4	354.7	354.5	354.1	353.6	353.1	352.6
157.5°	364.9	365.2	365.1	364.7	364.4	363.9	363.6
160°	371.3	371.7	371.7	371.4	371.1	370.9	370.6
162.5°	377.4	377.7	377.6	377.2	376.7	376.3	375.9
165°	385.0	385.5	385.5	385.0	384.5	384.0	383.5
167.5°	391.3	391.7	391.7	391.3	390.8	390.4	390.0
170°	394.8	395.2	395.2	394.8	394.2	393.8	393.2
172.5°	397.3	397.8	397.8	397.3	396.8	396.3	395.8
175°	400.2	400.6	400.6	400.1	399.6	399.1	398.6
177.5°	401.4	401.7	401.7	401.4	400.9	400.6	400.1
180°	401.2	401.2	401.2	401.2	401.2	401.2	401.2

(END OF REPORT)