

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332302-940

Luminaire Tested: **S123RDIP-S775D365U940-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332302-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S775D365U940-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3887.7 lumens
Efficiency: N/A
Efficacy: 111.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 35
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332302-940

CATALOG NUMBER: S123RDIP-S775D365U940-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332302-940

CATALOG NUMBER: S123RDIP-S775D365U940-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	74	74	74	70
1	103	99	95	92	97	94	91	88	84	82	79	75	73	72	67	66	64	61
2	95	87	81	76	89	83	78	73	75	71	67	67	64	61	60	58	56	52
3	87	78	70	65	82	74	67	62	67	62	57	60	56	53	54	51	48	45
4	80	69	62	56	75	66	59	54	60	54	50	54	50	46	49	45	42	39
5	74	62	54	48	70	59	52	47	54	48	43	49	44	40	44	40	37	35
6	68	56	48	42	64	54	46	41	49	43	38	45	40	36	40	36	33	31
7	63	51	43	38	60	49	42	37	45	39	34	41	36	32	37	33	30	28
8	59	47	39	34	56	45	38	33	41	35	31	38	33	29	34	30	27	25
9	55	43	35	30	52	41	34	29	38	32	28	35	30	26	32	28	25	23
10	52	40	32	27	49	38	31	27	35	29	25	32	27	24	30	25	22	21

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11739	11739	11739	11739
5°	13993	11788	10381	11788
10°	17472	11721	9379	11721
15°	20508	11602	8553	11602
20°	22888	11423	7851	11423
25°	22523	11233	7418	11233
30°	16189	11059	6975	11059
35°	10809	10834	6687	10834
40°	7964	10561	6389	10561
45°	6680	10085	6098	10085
50°	5894	9460	5690	9460
55°	5168	8743	5134	8743
60°	4603	8060	4704	8060
65°	4042	7325	4376	7325
70°	3175	6672	3997	6672
75°	2795	5827	3647	5827
80°	2430	4947	3589	4947
85°	1964	3977	3816	3977



TEST NUMBER: P332302-940

CATALOG NUMBER: S123RDIP-S775D365U940-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	107.2	2.8
10°-20°	335.1	8.6
20°-30°	526.4	13.5
30°-40°	549.2	14.1
40°-50°	470.0	12.1
50°-60°	358.2	9.2
60°-70°	229.6	5.9
70°-80°	110.5	2.8
80°-90°	30.4	0.8
90°-100°	86.6	2.2
100°-110°	245.3	6.3
110°-120°	241.3	6.2
120°-130°	192.5	5.0
130°-140°	151.8	3.9
140°-150°	113.3	2.9
150°-160°	78.9	2.0
160°-170°	46.4	1.2
170°-180°	15.1	0.4
0°-30°	968.7	24.9
0°-40°	1517.9	39.0
0°-60°	2346.1	60.3
0°-90°	2716.6	69.9
90°-120°	573.2	14.7
90°-150°	1030.7	26.5
90°-180°	1171.0	30.1
0°-180°	3887.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1091	1091	1091	1091	1091	
5°	1295	1091	961	1091	1295	134
15°	1840	1041	768	1041	1840	522
25°	1896	946	625	946	1896	815
35°	823	824	509	824	823	539
45°	439	662	401	662	439	345
55°	275	466	274	466	275	249
65°	159	288	172	288	159	156
75°	67	140	88	140	67	72
85°	16	32	31	32	16	18
90°	9	1	9	1	9	5
95°	37	11	37	11	37	66
105°	401	37	401	37	401	395
115°	488	65	488	65	488	474
125°	384	90	384	90	384	348
135°	312	105	312	105	312	242
145°	244	120	244	120	244	155
155°	202	136	202	136	202	94
165°	176	149	176	149	176	50
175°	158	155	158	155	158	15
180°	156	156	156	156	156	



TEST NUMBER: P332302-940

CATALOG NUMBER: S123RDIP-S775D365U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6
2.5°	1161.5	1163.1	1158.2	1157.4	1151.8	1150.3	1150.3	1142.5	1137.6	1131.3	1127.6
5°	1295.0	1302.5	1298.8	1290.4	1276.4	1273.1	1264.3	1250.3	1234.4	1214.8	1205.4
7.5°	1461.8	1472.0	1468.1	1455.1	1440.5	1428.6	1403.6	1380.3	1347.7	1319.1	1294.7
10°	1598.5	1587.8	1579.4	1566.7	1553.3	1531.2	1505.1	1469.2	1427.6	1395.0	1358.5
12.5°	1700.8	1699.1	1688.5	1675.4	1656.4	1635.5	1603.4	1559.6	1511.3	1464.1	1422.5
15°	1840.3	1843.2	1836.1	1822.6	1795.5	1758.6	1710.1	1691.8	1622.8	1571.5	1520.1
17.5°	1936.9	1936.4	1935.4	1916.6	1889.0	1862.8	1817.8	1769.9	1707.3	1635.0	1565.8
20°	1998.1	1993.5	1994.4	1973.4	1952.8	1922.5	1878.7	1809.1	1757.7	1674.2	1602.7
22.5°	1996.6	1995.7	1999.3	1992.1	1977.1	1953.9	1919.3	1860.6	1795.1	1710.7	1630.3
25°	1896.4	1892.7	1914.6	1920.7	1944.5	1948.7	1938.4	1906.2	1844.1	1757.2	1657.8
27.5°	1587.2	1585.1	1625.8	1676.8	1741.3	1791.6	1840.1	1863.6	1844.1	1781.9	1682.3
30°	1302.5	1346.4	1367.0	1440.7	1522.9	1621.0	1706.8	1788.5	1808.6	1781.5	1699.8
32.5°	1081.5	1119.7	1136.8	1200.2	1276.8	1391.6	1520.5	1636.1	1717.9	1738.6	1689.3
35°	822.6	823.0	862.3	890.3	961.3	1079.3	1204.5	1359.5	1513.5	1630.2	1642.4
37.5°	656.4	658.7	682.4	710.3	763.6	826.1	936.2	1065.1	1243.0	1422.2	1527.2
40°	566.8	571.0	588.7	616.3	654.5	701.7	787.6	909.0	1057.4	1256.8	1419.7
42.5°	509.3	516.0	525.2	546.4	570.2	614.3	683.8	777.5	912.5	1101.0	1289.0
45°	438.8	442.6	449.6	459.4	480.9	511.7	558.4	621.3	733.4	885.2	1073.3
47.5°	387.1	385.1	392.5	400.5	414.7	435.8	467.1	518.5	598.4	720.1	879.8
50°	352.0	351.5	356.7	362.7	376.3	391.7	417.4	456.1	519.6	620.5	766.6
52.5°	319.1	320.9	324.6	332.2	341.9	354.4	377.4	405.3	459.9	546.9	668.7
55°	275.4	276.9	282.0	286.1	293.2	305.8	320.3	343.6	380.9	441.7	542.0
57.5°	238.4	237.8	242.7	243.8	251.7	262.0	273.2	291.3	318.4	363.5	431.1
60°	213.8	212.4	216.6	219.9	224.1	232.5	241.8	259.6	281.1	314.1	372.1
62.5°	191.5	190.7	193.9	197.1	200.5	208.2	216.1	229.7	246.6	274.6	320.6
65°	158.7	160.2	161.5	162.9	164.8	169.4	176.9	186.3	198.0	217.6	250.7
67.5°	124.8	126.2	126.6	129.5	133.5	136.4	141.0	149.3	157.4	174.0	192.8
70°	100.9	100.4	100.9	102.3	107.4	112.5	118.6	124.7	129.7	141.4	157.3
72.5°	86.7	85.8	87.0	87.3	89.8	91.2	95.1	100.8	107.4	115.3	126.7
75°	67.2	67.2	67.2	67.2	69.1	70.0	71.4	72.9	75.2	78.9	87.3
77.5°	49.7	49.8	50.4	50.9	51.3	51.8	52.7	54.0	54.9	56.9	60.5
80°	39.2	39.7	39.2	39.7	39.7	40.6	41.1	42.4	43.0	45.3	46.7
82.5°	29.5	29.2	29.5	30.0	30.0	30.9	31.0	32.0	32.1	33.3	34.8
85°	15.9	15.0	15.9	15.4	16.3	15.4	15.9	16.8	16.8	17.3	19.2
87.5°	5.5	6.3	5.5	5.9	6.0	6.2	6.2	6.1	6.8	6.4	6.6
90°	9.1	9.5	9.1	8.8	9.1	8.5	8.2	7.8	7.6	7.8	7.0
92.5°	15.2	15.8	15.4	16.4	16.9	18.5	21.0	26.6	36.6	48.4	53.3
95°	36.6	37.8	40.0	42.9	48.9	60.2	76.9	113.4	151.6	186.9	166.4
97.5°	99.5	102.2	110.8	124.9	148.2	185.8	226.5	282.8	309.8	289.6	212.0
100°	197.6	197.2	209.6	232.6	264.4	309.2	346.0	371.5	360.5	298.5	201.7
102.5°	289.8	297.1	307.4	325.6	350.4	378.7	400.2	401.0	363.0	282.0	186.5
105°	400.8	402.4	412.5	424.5	439.0	447.1	441.1	409.7	343.8	253.3	168.0
107.5°	464.8	467.6	471.0	475.1	474.8	463.6	436.0	384.8	310.1	228.0	156.1
110°	491.0	491.6	492.2	489.7	480.9	458.8	419.1	361.1	289.0	213.7	151.6



TEST NUMBER: P332302-940

CATALOG NUMBER: S123RDIP-S775D365U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	496.2	496.1	493.7	485.9	469.8	441.4	396.9	337.7	270.5	204.0	149.0
115°	487.5	485.9	479.6	465.7	442.1	407.8	361.4	306.6	248.3	193.8	148.1
117.5°	459.6	457.4	448.4	432.6	407.9	373.0	331.4	284.1	234.9	187.7	148.6
120°	436.4	434.5	427.0	409.3	384.4	352.6	314.8	272.2	227.8	184.9	149.7
122.5°	414.7	412.3	404.0	388.2	366.0	336.4	301.4	263.0	222.0	183.2	151.4
125°	384.4	382.3	374.3	360.5	340.4	315.1	284.9	250.5	214.6	180.8	154.1
127.5°	359.4	357.5	350.4	338.5	320.6	297.6	270.3	239.7	208.0	179.8	157.1
130°	345.4	342.9	336.3	324.9	308.2	286.8	261.3	232.8	204.5	179.0	159.2
132.5°	331.5	329.8	323.9	312.5	296.9	276.4	252.6	226.6	201.3	178.7	160.7
135°	311.7	309.4	303.8	294.4	278.8	260.9	240.4	218.0	197.0	178.3	162.9
137.5°	290.7	289.2	284.5	274.8	261.9	246.3	228.6	210.3	193.2	177.6	164.4
140°	276.1	276.3	271.3	262.5	250.5	236.9	221.9	205.8	190.9	177.5	165.4
142.5°	262.4	262.7	258.2	250.4	240.1	228.4	215.3	201.5	189.0	176.9	166.2
145°	243.6	243.0	240.4	233.8	226.0	216.8	206.7	196.4	186.2	176.1	166.7
147.5°	228.1	227.8	225.4	221.0	215.0	208.5	200.4	192.1	183.6	175.0	166.7
150°	219.0	219.0	217.1	213.7	208.9	203.0	196.4	189.0	181.8	174.0	166.7
152.5°	211.4	211.4	210.3	207.1	203.4	198.4	192.5	186.3	179.8	172.7	165.9
155°	202.0	201.7	201.1	198.5	195.6	191.9	187.2	182.2	176.7	170.5	165.1
157.5°	193.3	193.4	192.9	191.0	188.6	185.6	181.9	177.7	173.3	168.5	164.1
160°	187.8	188.2	188.2	186.2	184.0	181.8	178.7	175.2	171.1	167.0	163.5
162.5°	182.8	183.1	183.1	181.5	180.0	178.1	175.1	172.2	168.8	165.5	162.6
165°	176.1	176.1	176.5	175.2	174.0	172.4	170.1	168.3	165.8	163.3	161.0
167.5°	169.9	169.9	170.1	169.2	168.7	167.6	166.3	164.9	162.8	161.0	159.5
170°	166.0	166.0	166.4	165.8	165.4	164.8	163.5	162.6	161.0	159.4	158.5
172.5°	162.6	162.8	163.4	162.7	162.6	162.3	161.3	160.6	159.3	158.2	157.7
175°	158.5	158.8	159.2	158.8	158.8	158.8	158.2	157.8	157.2	156.6	156.6
177.5°	156.1	156.1	156.7	156.4	156.7	156.7	156.4	156.1	156.0	155.7	156.0
180°	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7



TEST NUMBER: P332302-940

CATALOG NUMBER: S123RDIP-S775D365U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6
2.5°	1126.1	1124.9	1119.7	1113.7	1105.9	1100.6	1096.5	1094.3	1087.6	1079.3	1073.8
5°	1195.6	1181.6	1166.7	1148.4	1131.7	1114.4	1103.7	1091.0	1075.7	1058.4	1046.2
7.5°	1270.2	1242.7	1213.1	1182.6	1152.4	1125.3	1101.4	1080.9	1056.4	1031.6	1014.3
10°	1327.3	1287.1	1245.5	1203.1	1164.3	1127.9	1099.9	1072.4	1042.9	1014.5	993.0
12.5°	1379.2	1326.3	1278.4	1226.3	1176.7	1133.2	1092.8	1060.4	1025.0	994.7	970.2
15°	1444.9	1390.8	1332.8	1253.5	1187.7	1132.6	1083.6	1041.1	998.2	960.8	937.0
17.5°	1506.4	1424.9	1347.1	1280.9	1195.3	1126.5	1066.7	1015.8	968.8	929.2	899.8
20°	1531.8	1452.9	1368.3	1283.9	1199.8	1122.8	1053.2	997.2	948.2	903.4	876.3
22.5°	1547.0	1457.7	1368.7	1277.9	1188.7	1108.6	1039.8	978.1	925.1	882.4	849.0
25°	1564.9	1458.5	1360.4	1270.8	1179.7	1092.9	1011.2	945.8	888.4	843.1	807.6
27.5°	1576.6	1451.4	1335.6	1235.9	1143.6	1057.1	982.2	913.0	854.7	806.8	768.7
30°	1578.9	1445.8	1316.5	1208.7	1114.8	1035.5	956.1	889.8	828.2	777.3	741.8
32.5°	1581.9	1432.0	1290.8	1176.2	1080.1	1001.5	929.6	866.3	803.2	753.0	716.8
35°	1569.6	1424.4	1251.6	1120.0	1023.8	947.7	882.8	824.5	762.4	713.8	676.9
37.5°	1516.5	1394.0	1211.1	1056.7	956.1	885.6	832.8	781.9	725.0	672.5	637.8
40°	1463.1	1364.1	1179.7	1018.2	913.2	840.8	793.2	751.6	696.5	647.6	610.2
42.5°	1383.6	1323.5	1149.9	977.9	864.6	794.9	754.7	715.8	667.4	617.7	582.6
45°	1237.6	1245.5	1088.7	913.6	797.4	727.4	689.6	662.5	619.6	578.5	542.5
47.5°	1054.6	1128.8	1016.9	845.2	726.5	660.8	627.8	604.1	575.2	534.8	502.0
50°	935.1	1041.1	959.4	799.2	682.1	616.7	584.1	564.9	539.7	507.9	476.6
52.5°	824.9	938.8	889.9	748.1	633.9	574.2	542.2	526.5	506.4	476.5	448.3
55°	672.7	788.1	776.9	670.8	561.6	507.9	483.7	465.9	452.4	430.0	407.6
57.5°	544.2	653.5	659.3	585.0	497.9	444.9	424.0	410.6	401.8	384.9	364.2
60°	463.2	563.5	583.1	527.1	452.4	405.7	385.1	374.4	367.4	353.9	338.0
62.5°	395.9	481.3	503.5	463.2	408.7	365.0	348.9	338.6	333.8	322.1	308.1
65°	303.0	374.0	395.4	373.0	344.6	309.5	296.5	287.6	283.4	276.9	266.5
67.5°	227.8	279.6	303.1	287.3	277.1	254.9	246.6	241.8	238.1	233.6	225.1
70°	183.0	221.3	245.6	241.4	233.0	221.3	215.3	212.0	208.2	204.5	197.0
72.5°	147.1	173.5	196.3	198.4	191.5	189.1	183.9	182.4	180.2	175.8	171.7
75°	97.6	115.7	131.6	137.7	140.5	142.9	140.5	140.1	139.6	135.9	133.5
77.5°	63.9	73.7	83.7	94.1	98.5	101.7	102.5	104.2	102.9	100.9	99.8
80°	49.0	51.4	58.3	67.2	74.2	77.0	78.9	79.8	79.4	78.9	77.0
82.5°	35.6	37.5	40.8	47.1	53.0	57.6	58.8	58.6	59.6	59.8	58.3
85°	19.2	19.6	20.5	21.5	24.7	29.9	31.3	32.2	33.2	33.2	30.3
87.5°	7.1	6.6	7.1	7.0	8.0	8.2	10.3	12.0	12.6	11.2	11.4
90°	6.0	5.1	4.1	3.5	2.9	1.9	1.2	0.6	1.2	1.9	2.9
92.5°	40.0	26.5	18.2	13.6	10.9	8.5	5.8	3.9	5.8	8.5	10.9
95°	114.7	67.8	40.9	28.7	20.5	15.2	11.7	10.7	11.7	15.2	20.5
97.5°	125.8	72.9	47.3	34.1	25.9	21.3	18.5	18.3	18.5	21.3	25.9
100°	118.8	72.1	50.1	37.8	30.2	25.9	23.6	23.4	23.6	25.9	30.2
102.5°	112.7	73.2	53.4	42.1	35.3	31.1	29.2	28.6	29.2	31.1	35.3
105°	108.4	76.0	58.9	49.1	43.2	39.4	37.5	36.6	37.5	39.4	43.2
107.5°	108.1	81.1	66.2	57.1	51.5	47.8	45.9	45.0	45.9	47.8	51.5
110°	109.3	85.4	71.2	62.4	57.1	53.6	52.0	51.0	52.0	53.6	57.1



TEST NUMBER: P332302-940

CATALOG NUMBER: S123RDIP-S775D365U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	111.9	89.7	76.5	67.9	62.6	59.1	57.5	56.6	57.5	59.1	62.6
115°	115.9	96.8	84.8	76.2	70.9	67.8	65.9	64.6	65.9	67.8	70.9
117.5°	121.4	104.2	92.4	84.5	78.6	75.6	74.0	72.6	74.0	75.6	78.6
120°	125.4	109.1	97.6	89.8	83.8	80.7	79.1	78.1	79.1	80.7	83.8
122.5°	129.2	114.0	103.0	94.6	88.9	85.4	83.9	82.9	83.9	85.4	88.9
125°	135.2	121.4	110.3	101.7	95.8	92.3	90.4	89.8	90.4	92.3	95.8
127.5°	140.1	127.6	117.0	108.4	101.8	98.4	95.9	95.1	95.9	98.4	101.8
130°	143.4	131.4	121.0	112.5	105.8	102.1	99.2	98.4	99.2	102.1	105.8
132.5°	146.4	134.6	124.6	116.3	109.7	105.1	102.0	100.9	102.0	105.1	109.7
135°	150.3	139.6	129.8	121.4	114.7	109.9	106.5	105.2	106.5	109.9	114.7
137.5°	153.2	143.0	133.6	125.7	119.1	114.1	110.8	109.4	110.8	114.1	119.1
140°	154.7	145.3	136.2	128.2	122.0	116.9	113.8	112.2	113.8	116.9	122.0
142.5°	156.2	147.0	138.1	130.8	124.5	119.9	116.5	115.2	116.5	119.9	124.5
145°	157.8	149.4	141.2	133.9	128.6	123.9	121.0	120.0	121.0	123.9	128.6
147.5°	158.9	151.2	143.7	137.6	132.4	128.3	125.6	125.0	125.6	128.3	132.4
150°	159.2	152.5	145.3	139.6	135.2	131.1	128.6	128.2	128.6	131.1	135.2
152.5°	159.6	153.3	147.0	141.6	137.7	134.1	131.6	131.5	131.6	134.1	137.7
155°	159.8	154.7	149.4	145.0	141.5	138.3	136.4	136.4	136.4	138.3	141.5
157.5°	160.1	155.5	151.2	147.8	144.9	142.1	140.6	140.4	140.6	142.1	144.9
160°	160.1	156.3	152.5	149.4	147.1	144.6	143.4	143.4	143.4	144.6	147.1
162.5°	159.8	156.6	153.3	150.6	148.6	146.7	145.6	145.6	145.6	146.7	148.6
165°	159.2	156.9	154.4	152.2	151.0	149.4	148.7	149.0	148.7	149.4	151.0
167.5°	158.6	156.9	155.1	153.6	152.8	151.6	151.2	151.6	151.2	151.6	152.8
170°	157.8	156.6	155.1	154.4	153.7	152.8	152.5	153.1	152.5	152.8	153.7
172.5°	157.7	156.6	155.2	154.9	154.5	153.8	153.7	154.2	153.7	153.8	154.5
175°	156.9	156.3	155.7	155.3	155.3	154.7	155.1	155.3	155.1	154.7	155.3
177.5°	156.4	156.0	155.7	155.7	155.7	155.4	155.7	156.0	155.7	155.4	155.7
180°	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7



TEST NUMBER: P332302-940

CATALOG NUMBER: S123RDIP-S775D365U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6
2.5°	1071.9	1067.0	1063.7	1056.2	1051.3	1046.2	1040.9	1044.3	1043.9	1043.5	1043.5
5°	1036.0	1025.2	1015.4	1002.8	994.9	985.1	977.6	976.7	978.6	972.0	968.2
7.5°	1000.3	985.6	971.7	957.8	943.1	931.3	923.9	920.4	915.7	911.7	907.5
10°	975.3	958.0	944.4	927.2	911.3	897.3	888.4	882.3	879.0	875.8	869.8
12.5°	949.5	932.6	915.3	895.8	880.7	864.4	857.8	851.0	844.7	841.1	832.8
15°	911.8	889.8	871.6	851.0	834.3	818.4	809.0	795.5	793.6	789.0	780.6
17.5°	874.0	850.2	825.0	809.9	790.9	774.4	760.1	755.5	742.2	737.2	729.9
20°	844.1	822.2	803.0	782.9	755.4	739.9	728.8	722.7	711.9	705.4	700.7
22.5°	818.3	796.0	773.8	750.5	727.7	710.4	702.2	692.8	687.0	677.8	672.7
25°	781.5	757.2	730.7	705.4	689.1	676.0	662.9	654.5	646.1	641.9	632.6
27.5°	738.8	713.4	688.5	669.4	649.3	636.4	624.6	617.1	607.0	599.9	594.8
30°	715.2	685.4	663.9	646.6	620.9	608.8	599.9	590.6	583.1	575.6	570.5
32.5°	688.0	660.7	640.3	618.9	599.2	586.0	574.5	566.3	559.9	552.9	547.7
35°	645.2	622.3	601.3	579.8	565.3	551.8	538.3	531.3	525.2	518.7	514.0
37.5°	606.5	585.1	565.2	544.8	526.9	515.9	505.0	499.6	491.4	487.1	482.2
40°	582.6	561.6	540.1	520.6	501.9	493.5	483.7	475.7	468.2	465.0	459.9
42.5°	556.5	535.5	517.4	496.2	481.0	469.6	460.5	451.8	446.2	441.5	438.5
45°	517.7	499.1	481.3	460.3	445.9	436.0	425.8	417.9	412.7	409.5	404.3
47.5°	480.1	461.5	443.4	425.1	411.1	399.9	389.7	384.1	377.3	373.3	369.9
50°	452.8	436.0	416.9	400.1	386.1	374.9	366.5	359.4	353.4	348.3	346.0
52.5°	427.8	409.9	393.3	377.7	362.9	350.3	342.6	335.2	330.6	324.8	322.0
55°	386.6	369.3	355.3	339.8	325.4	314.7	305.3	298.8	294.1	287.6	283.8
57.5°	347.8	332.3	315.6	302.2	287.3	278.2	270.5	261.6	255.9	250.8	247.2
60°	321.6	303.9	289.4	276.9	263.8	252.1	245.1	238.1	232.0	226.9	223.6
62.5°	294.4	278.9	265.2	251.5	239.5	229.3	221.2	215.3	210.0	206.7	203.5
65°	252.5	240.4	226.4	215.3	204.0	196.5	190.0	184.9	181.1	178.8	176.0
67.5°	214.1	202.3	190.1	179.1	171.7	165.9	161.7	157.2	155.3	152.4	150.5
70°	189.0	176.9	166.2	157.8	150.3	146.2	143.3	140.1	138.2	134.5	132.6
72.5°	161.8	153.0	145.3	138.4	132.4	128.6	125.0	121.0	118.1	113.9	112.1
75°	127.4	119.5	113.4	108.8	105.0	99.9	94.8	90.6	89.2	87.7	87.3
77.5°	94.4	89.3	85.0	81.1	76.4	72.7	71.5	70.6	70.3	69.6	69.6
80°	74.2	69.6	66.3	61.6	58.9	58.9	58.9	57.9	58.3	58.3	58.3
82.5°	55.2	50.9	49.1	47.4	46.9	47.3	47.3	47.4	47.2	47.9	47.5
85°	28.4	29.0	29.9	29.4	29.9	29.9	30.9	30.3	30.9	29.9	30.9
87.5°	11.1	12.4	12.9	13.6	14.1	13.9	14.2	14.3	14.7	14.8	14.9
90°	3.5	4.1	5.1	6.0	7.0	7.8	7.6	7.8	8.2	8.5	9.1
92.5°	13.6	18.2	26.5	40.0	53.3	48.4	36.6	26.6	21.0	18.5	16.9
95°	28.7	40.9	67.8	114.7	166.4	186.9	151.6	113.4	76.9	60.2	48.9
97.5°	34.1	47.3	72.9	125.8	212.0	289.6	309.8	282.8	226.5	185.8	148.2
100°	37.8	50.1	72.1	118.8	201.7	298.5	360.5	371.5	346.0	309.2	264.4
102.5°	42.1	53.4	73.2	112.7	186.5	282.0	363.0	401.0	400.2	378.7	350.4
105°	49.1	58.9	76.0	108.4	168.0	253.3	343.8	409.7	441.1	447.1	439.0
107.5°	57.1	66.2	81.1	108.1	156.1	228.0	310.1	384.8	436.0	463.6	474.8
110°	62.4	71.2	85.4	109.3	151.6	213.7	289.0	361.1	419.1	458.8	480.9



TEST NUMBER: P332302-940

CATALOG NUMBER: S123RDIP-S775D365U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	67.9	76.5	89.7	111.9	149.0	204.0	270.5	337.7	396.9	441.4	469.8
115°	76.2	84.8	96.8	115.9	148.1	193.8	248.3	306.6	361.4	407.8	442.1
117.5°	84.5	92.4	104.2	121.4	148.6	187.7	234.9	284.1	331.4	373.0	407.9
120°	89.8	97.6	109.1	125.4	149.7	184.9	227.8	272.2	314.8	352.6	384.4
122.5°	94.6	103.0	114.0	129.2	151.4	183.2	222.0	263.0	301.4	336.4	366.0
125°	101.7	110.3	121.4	135.2	154.1	180.8	214.6	250.5	284.9	315.1	340.4
127.5°	108.4	117.0	127.6	140.1	157.1	179.8	208.0	239.7	270.3	297.6	320.6
130°	112.5	121.0	131.4	143.4	159.2	179.0	204.5	232.8	261.3	286.8	308.2
132.5°	116.3	124.6	134.6	146.4	160.7	178.7	201.3	226.6	252.6	276.4	296.9
135°	121.4	129.8	139.6	150.3	162.9	178.3	197.0	218.0	240.4	260.9	278.8
137.5°	125.7	133.6	143.0	153.2	164.4	177.6	193.2	210.3	228.6	246.3	261.9
140°	128.2	136.2	145.3	154.7	165.4	177.5	190.9	205.8	221.9	236.9	250.5
142.5°	130.8	138.1	147.0	156.2	166.2	176.9	189.0	201.5	215.3	228.4	240.1
145°	133.9	141.2	149.4	157.8	166.7	176.1	186.2	196.4	206.7	216.8	226.0
147.5°	137.6	143.7	151.2	158.9	166.7	175.0	183.6	192.1	200.4	208.5	215.0
150°	139.6	145.3	152.5	159.2	166.7	174.0	181.8	189.0	196.4	203.0	208.9
152.5°	141.6	147.0	153.3	159.6	165.9	172.7	179.8	186.3	192.5	198.4	203.4
155°	145.0	149.4	154.7	159.8	165.1	170.5	176.7	182.2	187.2	191.9	195.6
157.5°	147.8	151.2	155.5	160.1	164.1	168.5	173.3	177.7	181.9	185.6	188.6
160°	149.4	152.5	156.3	160.1	163.5	167.0	171.1	175.2	178.7	181.8	184.0
162.5°	150.6	153.3	156.6	159.8	162.6	165.5	168.8	172.2	175.1	178.1	180.0
165°	152.2	154.4	156.9	159.2	161.0	163.3	165.8	168.3	170.1	172.4	174.0
167.5°	153.6	155.1	156.9	158.6	159.5	161.0	162.8	164.9	166.3	167.6	168.7
170°	154.4	155.1	156.6	157.8	158.5	159.4	161.0	162.6	163.5	164.8	165.4
172.5°	154.9	155.2	156.6	157.7	157.7	158.2	159.3	160.6	161.3	162.3	162.6
175°	155.3	155.7	156.3	156.9	156.6	156.6	157.2	157.8	158.2	158.8	158.8
177.5°	155.7	155.7	156.0	156.4	156.0	155.7	156.0	156.1	156.4	156.7	156.7
180°	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7



TEST NUMBER: P332302-940

CATALOG NUMBER: S123RDIP-S775D365U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6
2.5°	1039.0	1038.7	1039.0	1037.5	1039.0	1038.7	1039.0	1043.5	1043.5	1043.9	1044.3
5°	966.9	966.3	965.0	960.8	965.0	966.3	966.9	968.2	972.0	978.6	976.7
7.5°	903.8	903.2	899.1	899.2	899.1	903.2	903.8	907.5	911.7	915.7	920.4
10°	866.5	866.9	861.4	858.1	861.4	866.9	866.5	869.8	875.8	879.0	882.3
12.5°	830.3	828.1	823.6	820.0	823.6	828.1	830.3	832.8	841.1	844.7	851.0
15°	782.5	777.8	766.6	767.5	766.6	777.8	782.5	780.6	789.0	793.6	795.5
17.5°	726.1	722.7	722.5	716.0	722.5	722.7	726.1	729.9	737.2	742.2	755.5
20°	693.3	691.0	691.9	685.4	691.9	691.0	693.3	700.7	705.4	711.9	722.7
22.5°	667.5	665.2	661.3	659.2	661.3	665.2	667.5	672.7	677.8	687.0	692.8
25°	629.8	626.1	622.3	624.6	622.3	626.1	629.8	632.6	641.9	646.1	654.5
27.5°	592.1	589.2	585.5	585.1	585.5	589.2	592.1	594.8	599.9	607.0	617.1
30°	568.2	565.3	563.5	561.2	563.5	565.3	568.2	570.5	575.6	583.1	590.6
32.5°	543.9	543.3	539.9	539.5	539.9	543.3	543.9	547.7	552.9	559.9	566.3
35°	512.1	509.3	508.4	508.9	508.4	509.3	512.1	514.0	518.7	525.2	531.3
37.5°	482.0	478.2	476.5	474.9	476.5	478.2	482.0	482.2	487.1	491.4	499.6
40°	460.3	456.6	455.7	454.7	455.7	456.6	460.3	459.9	465.0	468.2	475.7
42.5°	436.0	434.5	434.0	432.3	434.0	434.5	436.0	438.5	441.5	446.2	451.8
45°	402.9	402.4	399.7	400.6	399.7	402.4	402.9	404.3	409.5	412.7	417.9
47.5°	368.0	366.0	364.0	365.2	364.0	366.0	368.0	369.9	373.3	377.3	384.1
50°	344.1	343.1	338.9	339.8	338.9	343.1	344.1	346.0	348.3	353.4	359.4
52.5°	320.2	316.6	315.0	314.5	315.0	316.6	320.2	322.0	324.8	330.6	335.2
55°	280.6	276.3	274.5	273.6	274.5	276.3	280.6	283.8	287.6	294.1	298.8
57.5°	241.7	240.6	239.2	240.1	239.2	240.6	241.7	247.2	250.8	255.9	261.6
60°	218.9	218.9	218.9	218.5	218.9	218.9	218.9	223.6	226.9	232.0	238.1
62.5°	201.4	200.3	199.9	200.5	199.9	200.3	201.4	203.5	206.7	210.0	215.3
65°	174.6	174.2	172.3	171.8	172.3	174.2	174.6	176.0	178.8	181.1	184.9
67.5°	149.3	147.6	147.0	146.4	147.0	147.6	149.3	150.5	152.4	155.3	157.2
70°	130.3	129.3	126.5	127.0	126.5	129.3	130.3	132.6	134.5	138.2	140.1
72.5°	109.7	108.8	108.3	107.5	108.3	108.8	109.7	112.1	113.9	118.1	121.0
75°	86.9	86.4	85.9	87.7	85.9	86.4	86.9	87.3	87.7	89.2	90.6
77.5°	69.6	69.6	69.8	69.1	69.8	69.6	69.6	69.6	69.6	70.3	70.6
80°	58.3	58.3	57.9	57.9	57.9	58.3	58.3	58.3	58.3	58.3	57.9
82.5°	46.8	47.2	47.4	46.7	47.4	47.2	46.8	47.5	47.9	47.2	47.4
85°	30.9	30.3	31.3	30.9	31.3	30.3	30.9	30.9	29.9	30.9	30.3
87.5°	15.6	14.9	15.0	15.2	15.0	14.9	15.6	14.9	14.8	14.7	14.3
90°	8.8	9.1	9.5	9.1	9.5	9.1	8.8	9.1	8.5	8.2	7.8
92.5°	16.4	15.4	15.8	15.2	15.8	15.4	16.4	16.9	18.5	21.0	26.6
95°	42.9	40.0	37.8	36.6	37.8	40.0	42.9	48.9	60.2	76.9	113.4
97.5°	124.9	110.8	102.2	99.5	102.2	110.8	124.9	148.2	185.8	226.5	282.8
100°	232.6	209.6	197.2	197.6	197.2	209.6	232.6	264.4	309.2	346.0	371.5
102.5°	325.6	307.4	297.1	289.8	297.1	307.4	325.6	350.4	378.7	400.2	401.0
105°	424.5	412.5	402.4	400.8	402.4	412.5	424.5	439.0	447.1	441.1	409.7
107.5°	475.1	471.0	467.6	464.8	467.6	471.0	475.1	474.8	463.6	436.0	384.8
110°	489.7	492.2	491.6	491.0	491.6	492.2	489.7	480.9	458.8	419.1	361.1



TEST NUMBER: P332302-940

CATALOG NUMBER: S123RDIP-S775D365U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	485.9	493.7	496.1	496.2	496.1	493.7	485.9	469.8	441.4	396.9	337.7
115°	465.7	479.6	485.9	487.5	485.9	479.6	465.7	442.1	407.8	361.4	306.6
117.5°	432.6	448.4	457.4	459.6	457.4	448.4	432.6	407.9	373.0	331.4	284.1
120°	409.3	427.0	434.5	436.4	434.5	427.0	409.3	384.4	352.6	314.8	272.2
122.5°	388.2	404.0	412.3	414.7	412.3	404.0	388.2	366.0	336.4	301.4	263.0
125°	360.5	374.3	382.3	384.4	382.3	374.3	360.5	340.4	315.1	284.9	250.5
127.5°	338.5	350.4	357.5	359.4	357.5	350.4	338.5	320.6	297.6	270.3	239.7
130°	324.9	336.3	342.9	345.4	342.9	336.3	324.9	308.2	286.8	261.3	232.8
132.5°	312.5	323.9	329.8	331.5	329.8	323.9	312.5	296.9	276.4	252.6	226.6
135°	294.4	303.8	309.4	311.7	309.4	303.8	294.4	278.8	260.9	240.4	218.0
137.5°	274.8	284.5	289.2	290.7	289.2	284.5	274.8	261.9	246.3	228.6	210.3
140°	262.5	271.3	276.3	276.1	276.3	271.3	262.5	250.5	236.9	221.9	205.8
142.5°	250.4	258.2	262.7	262.4	262.7	258.2	250.4	240.1	228.4	215.3	201.5
145°	233.8	240.4	243.0	243.6	243.0	240.4	233.8	226.0	216.8	206.7	196.4
147.5°	221.0	225.4	227.8	228.1	227.8	225.4	221.0	215.0	208.5	200.4	192.1
150°	213.7	217.1	219.0	219.0	219.0	217.1	213.7	208.9	203.0	196.4	189.0
152.5°	207.1	210.3	211.4	211.4	211.4	210.3	207.1	203.4	198.4	192.5	186.3
155°	198.5	201.1	201.7	202.0	201.7	201.1	198.5	195.6	191.9	187.2	182.2
157.5°	191.0	192.9	193.4	193.3	193.4	192.9	191.0	188.6	185.6	181.9	177.7
160°	186.2	188.2	188.2	187.8	188.2	188.2	186.2	184.0	181.8	178.7	175.2
162.5°	181.5	183.1	183.1	182.8	183.1	183.1	181.5	180.0	178.1	175.1	172.2
165°	175.2	176.5	176.1	176.1	176.1	176.5	175.2	174.0	172.4	170.1	168.3
167.5°	169.2	170.1	169.9	169.9	169.9	170.1	169.2	168.7	167.6	166.3	164.9
170°	165.8	166.4	166.0	166.0	166.0	166.4	165.8	165.4	164.8	163.5	162.6
172.5°	162.7	163.4	162.8	162.6	162.8	163.4	162.7	162.6	162.3	161.3	160.6
175°	158.8	159.2	158.8	158.5	158.8	159.2	158.8	158.8	158.8	158.2	157.8
177.5°	156.4	156.7	156.1	156.1	156.1	156.7	156.4	156.7	156.7	156.4	156.1
180°	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7



TEST NUMBER: P332302-940

CATALOG NUMBER: S123RDIP-S775D365U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6
2.5°	1040.9	1046.2	1051.3	1056.2	1063.7	1067.0	1071.9	1073.8	1079.3	1087.6	1094.3
5°	977.6	985.1	994.9	1002.8	1015.4	1025.2	1036.0	1046.2	1058.4	1075.7	1091.0
7.5°	923.9	931.3	943.1	957.8	971.7	985.6	1000.3	1014.3	1031.6	1056.4	1080.9
10°	888.4	897.3	911.3	927.2	944.4	958.0	975.3	993.0	1014.5	1042.9	1072.4
12.5°	857.8	864.4	880.7	895.8	915.3	932.6	949.5	970.2	994.7	1025.0	1060.4
15°	809.0	818.4	834.3	851.0	871.6	889.8	911.8	937.0	960.8	998.2	1041.1
17.5°	760.1	774.4	790.9	809.9	825.0	850.2	874.0	899.8	929.2	968.8	1015.8
20°	728.8	739.9	755.4	782.9	803.0	822.2	844.1	876.3	903.4	948.2	997.2
22.5°	702.2	710.4	727.7	750.5	773.8	796.0	818.3	849.0	882.4	925.1	978.1
25°	662.9	676.0	689.1	705.4	730.7	757.2	781.5	807.6	843.1	888.4	945.8
27.5°	624.6	636.4	649.3	669.4	688.5	713.4	738.8	768.7	806.8	854.7	913.0
30°	599.9	608.8	620.9	646.6	663.9	685.4	715.2	741.8	777.3	828.2	889.8
32.5°	574.5	586.0	599.2	618.9	640.3	660.7	688.0	716.8	753.0	803.2	866.3
35°	538.3	551.8	565.3	579.8	601.3	622.3	645.2	676.9	713.8	762.4	824.5
37.5°	505.0	515.9	526.9	544.8	565.2	585.1	606.5	637.8	672.5	725.0	781.9
40°	483.7	493.5	501.9	520.6	540.1	561.6	582.6	610.2	647.6	696.5	751.6
42.5°	460.5	469.6	481.0	496.2	517.4	535.5	556.5	582.6	617.7	667.4	715.8
45°	425.8	436.0	445.9	460.3	481.3	499.1	517.7	542.5	578.5	619.6	662.5
47.5°	389.7	399.9	411.1	425.1	443.4	461.5	480.1	502.0	534.8	575.2	604.1
50°	366.5	374.9	386.1	400.1	416.9	436.0	452.8	476.6	507.9	539.7	564.9
52.5°	342.6	350.3	362.9	377.7	393.3	409.9	427.8	448.3	476.5	506.4	526.5
55°	305.3	314.7	325.4	339.8	355.3	369.3	386.6	407.6	430.0	452.4	465.9
57.5°	270.5	278.2	287.3	302.2	315.6	332.3	347.8	364.2	384.9	401.8	410.6
60°	245.1	252.1	263.8	276.9	289.4	303.9	321.6	338.0	353.9	367.4	374.4
62.5°	221.2	229.3	239.5	251.5	265.2	278.9	294.4	308.1	322.1	333.8	338.6
65°	190.0	196.5	204.0	215.3	226.4	240.4	252.5	266.5	276.9	283.4	287.6
67.5°	161.7	165.9	171.7	179.1	190.1	202.3	214.1	225.1	233.6	238.1	241.8
70°	143.3	146.2	150.3	157.8	166.2	176.9	189.0	197.0	204.5	208.2	212.0
72.5°	125.0	128.6	132.4	138.4	145.3	153.0	161.8	171.7	175.8	180.2	182.4
75°	94.8	99.9	105.0	108.8	113.4	119.5	127.4	133.5	135.9	139.6	140.1
77.5°	71.5	72.7	76.4	81.1	85.0	89.3	94.4	99.8	100.9	102.9	104.2
80°	58.9	58.9	58.9	61.6	66.3	69.6	74.2	77.0	78.9	79.4	79.8
82.5°	47.3	47.3	46.9	47.4	49.1	50.9	55.2	58.3	59.8	59.6	58.6
85°	30.9	29.9	29.9	29.4	29.9	29.0	28.4	30.3	33.2	33.2	32.2
87.5°	14.2	13.9	14.1	13.6	12.9	12.4	11.1	11.4	11.2	12.6	12.0
90°	7.6	7.8	7.0	6.0	5.1	4.1	3.5	2.9	1.9	1.2	0.6
92.5°	36.6	48.4	53.3	40.0	26.5	18.2	13.6	10.9	8.5	5.8	3.9
95°	151.6	186.9	166.4	114.7	67.8	40.9	28.7	20.5	15.2	11.7	10.7
97.5°	309.8	289.6	212.0	125.8	72.9	47.3	34.1	25.9	21.3	18.5	18.3
100°	360.5	298.5	201.7	118.8	72.1	50.1	37.8	30.2	25.9	23.6	23.4
102.5°	363.0	282.0	186.5	112.7	73.2	53.4	42.1	35.3	31.1	29.2	28.6
105°	343.8	253.3	168.0	108.4	76.0	58.9	49.1	43.2	39.4	37.5	36.6
107.5°	310.1	228.0	156.1	108.1	81.1	66.2	57.1	51.5	47.8	45.9	45.0
110°	289.0	213.7	151.6	109.3	85.4	71.2	62.4	57.1	53.6	52.0	51.0



TEST NUMBER: P332302-940

CATALOG NUMBER: S123RDIP-S775D365U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	270.5	204.0	149.0	111.9	89.7	76.5	67.9	62.6	59.1	57.5	56.6
115°	248.3	193.8	148.1	115.9	96.8	84.8	76.2	70.9	67.8	65.9	64.6
117.5°	234.9	187.7	148.6	121.4	104.2	92.4	84.5	78.6	75.6	74.0	72.6
120°	227.8	184.9	149.7	125.4	109.1	97.6	89.8	83.8	80.7	79.1	78.1
122.5°	222.0	183.2	151.4	129.2	114.0	103.0	94.6	88.9	85.4	83.9	82.9
125°	214.6	180.8	154.1	135.2	121.4	110.3	101.7	95.8	92.3	90.4	89.8
127.5°	208.0	179.8	157.1	140.1	127.6	117.0	108.4	101.8	98.4	95.9	95.1
130°	204.5	179.0	159.2	143.4	131.4	121.0	112.5	105.8	102.1	99.2	98.4
132.5°	201.3	178.7	160.7	146.4	134.6	124.6	116.3	109.7	105.1	102.0	100.9
135°	197.0	178.3	162.9	150.3	139.6	129.8	121.4	114.7	109.9	106.5	105.2
137.5°	193.2	177.6	164.4	153.2	143.0	133.6	125.7	119.1	114.1	110.8	109.4
140°	190.9	177.5	165.4	154.7	145.3	136.2	128.2	122.0	116.9	113.8	112.2
142.5°	189.0	176.9	166.2	156.2	147.0	138.1	130.8	124.5	119.9	116.5	115.2
145°	186.2	176.1	166.7	157.8	149.4	141.2	133.9	128.6	123.9	121.0	120.0
147.5°	183.6	175.0	166.7	158.9	151.2	143.7	137.6	132.4	128.3	125.6	125.0
150°	181.8	174.0	166.7	159.2	152.5	145.3	139.6	135.2	131.1	128.6	128.2
152.5°	179.8	172.7	165.9	159.6	153.3	147.0	141.6	137.7	134.1	131.6	131.5
155°	176.7	170.5	165.1	159.8	154.7	149.4	145.0	141.5	138.3	136.4	136.4
157.5°	173.3	168.5	164.1	160.1	155.5	151.2	147.8	144.9	142.1	140.6	140.4
160°	171.1	167.0	163.5	160.1	156.3	152.5	149.4	147.1	144.6	143.4	143.4
162.5°	168.8	165.5	162.6	159.8	156.6	153.3	150.6	148.6	146.7	145.6	145.6
165°	165.8	163.3	161.0	159.2	156.9	154.4	152.2	151.0	149.4	148.7	149.0
167.5°	162.8	161.0	159.5	158.6	156.9	155.1	153.6	152.8	151.6	151.2	151.6
170°	161.0	159.4	158.5	157.8	156.6	155.1	154.4	153.7	152.8	152.5	153.1
172.5°	159.3	158.2	157.7	157.7	156.6	155.2	154.9	154.5	153.8	153.7	154.2
175°	157.2	156.6	156.6	156.9	156.3	155.7	155.3	155.3	154.7	155.1	155.3
177.5°	156.0	155.7	156.0	156.4	156.0	155.7	155.7	155.7	155.4	155.7	156.0
180°	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7



TEST NUMBER: P332302-940

CATALOG NUMBER: S123RDIP-S775D365U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6
2.5°	1096.5	1100.6	1105.9	1113.7	1119.7	1124.9	1126.1	1127.6	1131.3	1137.6	1142.5
5°	1103.7	1114.4	1131.7	1148.4	1166.7	1181.6	1195.6	1205.4	1214.8	1234.4	1250.3
7.5°	1101.4	1125.3	1152.4	1182.6	1213.1	1242.7	1270.2	1294.7	1319.1	1347.7	1380.3
10°	1099.9	1127.9	1164.3	1203.1	1245.5	1287.1	1327.3	1358.5	1395.0	1427.6	1469.2
12.5°	1092.8	1133.2	1176.7	1226.3	1278.4	1326.3	1379.2	1422.5	1464.1	1511.3	1559.6
15°	1083.6	1132.6	1187.7	1253.5	1332.8	1390.8	1444.9	1520.1	1571.5	1622.8	1691.8
17.5°	1066.7	1126.5	1195.3	1280.9	1347.1	1424.9	1506.4	1565.8	1635.0	1707.3	1769.9
20°	1053.2	1122.8	1199.8	1283.9	1368.3	1452.9	1531.8	1602.7	1674.2	1757.7	1809.1
22.5°	1039.8	1108.6	1188.7	1277.9	1368.7	1457.7	1547.0	1630.3	1710.7	1795.1	1860.6
25°	1011.2	1092.9	1179.7	1270.8	1360.4	1458.5	1564.9	1657.8	1757.2	1844.1	1906.2
27.5°	982.2	1057.1	1143.6	1235.9	1335.6	1451.4	1576.6	1682.3	1781.9	1844.1	1863.6
30°	956.1	1035.5	1114.8	1208.7	1316.5	1445.8	1578.9	1699.8	1781.5	1808.6	1788.5
32.5°	929.6	1001.5	1080.1	1176.2	1290.8	1432.0	1581.9	1689.3	1738.6	1717.9	1636.1
35°	882.8	947.7	1023.8	1120.0	1251.6	1424.4	1569.6	1642.4	1630.2	1513.5	1359.5
37.5°	832.8	885.6	956.1	1056.7	1211.1	1394.0	1516.5	1527.2	1422.2	1243.0	1065.1
40°	793.2	840.8	913.2	1018.2	1179.7	1364.1	1463.1	1419.7	1256.8	1057.4	909.0
42.5°	754.7	794.9	864.6	977.9	1149.9	1323.5	1383.6	1289.0	1101.0	912.5	777.5
45°	689.6	727.4	797.4	913.6	1088.7	1245.5	1237.6	1073.3	885.2	733.4	621.3
47.5°	627.8	660.8	726.5	845.2	1016.9	1128.8	1054.6	879.8	720.1	598.4	518.5
50°	584.1	616.7	682.1	799.2	959.4	1041.1	935.1	766.6	620.5	519.6	456.1
52.5°	542.2	574.2	633.9	748.1	889.9	938.8	824.9	668.7	546.9	459.9	405.3
55°	483.7	507.9	561.6	670.8	776.9	788.1	672.7	542.0	441.7	380.9	343.6
57.5°	424.0	444.9	497.9	585.0	659.3	653.5	544.2	431.1	363.5	318.4	291.3
60°	385.1	405.7	452.4	527.1	583.1	563.5	463.2	372.1	314.1	281.1	259.6
62.5°	348.9	365.0	408.7	463.2	503.5	481.3	395.9	320.6	274.6	246.6	229.7
65°	296.5	309.5	344.6	373.0	395.4	374.0	303.0	250.7	217.6	198.0	186.3
67.5°	246.6	254.9	277.1	287.3	303.1	279.6	227.8	192.8	174.0	157.4	149.3
70°	215.3	221.3	233.0	241.4	245.6	221.3	183.0	157.3	141.4	129.7	124.7
72.5°	183.9	189.1	191.5	198.4	196.3	173.5	147.1	126.7	115.3	107.4	100.8
75°	140.5	142.9	140.5	137.7	131.6	115.7	97.6	87.3	78.9	75.2	72.9
77.5°	102.5	101.7	98.5	94.1	83.7	73.7	63.9	60.5	56.9	54.9	54.0
80°	78.9	77.0	74.2	67.2	58.3	51.4	49.0	46.7	45.3	43.0	42.4
82.5°	58.8	57.6	53.0	47.1	40.8	37.5	35.6	34.8	33.3	32.1	32.0
85°	31.3	29.9	24.7	21.5	20.5	19.6	19.2	19.2	17.3	16.8	16.8
87.5°	10.3	8.2	8.0	7.0	7.1	6.6	7.1	6.6	6.4	6.8	6.1
90°	1.2	1.9	2.9	3.5	4.1	5.1	6.0	7.0	7.8	7.6	7.8
92.5°	5.8	8.5	10.9	13.6	18.2	26.5	40.0	53.3	48.4	36.6	26.6
95°	11.7	15.2	20.5	28.7	40.9	67.8	114.7	166.4	186.9	151.6	113.4
97.5°	18.5	21.3	25.9	34.1	47.3	72.9	125.8	212.0	289.6	309.8	282.8
100°	23.6	25.9	30.2	37.8	50.1	72.1	118.8	201.7	298.5	360.5	371.5
102.5°	29.2	31.1	35.3	42.1	53.4	73.2	112.7	186.5	282.0	363.0	401.0
105°	37.5	39.4	43.2	49.1	58.9	76.0	108.4	168.0	253.3	343.8	409.7
107.5°	45.9	47.8	51.5	57.1	66.2	81.1	108.1	156.1	228.0	310.1	384.8
110°	52.0	53.6	57.1	62.4	71.2	85.4	109.3	151.6	213.7	289.0	361.1



TEST NUMBER: P332302-940

CATALOG NUMBER: S123RDIP-S775D365U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	57.5	59.1	62.6	67.9	76.5	89.7	111.9	149.0	204.0	270.5	337.7
115°	65.9	67.8	70.9	76.2	84.8	96.8	115.9	148.1	193.8	248.3	306.6
117.5°	74.0	75.6	78.6	84.5	92.4	104.2	121.4	148.6	187.7	234.9	284.1
120°	79.1	80.7	83.8	89.8	97.6	109.1	125.4	149.7	184.9	227.8	272.2
122.5°	83.9	85.4	88.9	94.6	103.0	114.0	129.2	151.4	183.2	222.0	263.0
125°	90.4	92.3	95.8	101.7	110.3	121.4	135.2	154.1	180.8	214.6	250.5
127.5°	95.9	98.4	101.8	108.4	117.0	127.6	140.1	157.1	179.8	208.0	239.7
130°	99.2	102.1	105.8	112.5	121.0	131.4	143.4	159.2	179.0	204.5	232.8
132.5°	102.0	105.1	109.7	116.3	124.6	134.6	146.4	160.7	178.7	201.3	226.6
135°	106.5	109.9	114.7	121.4	129.8	139.6	150.3	162.9	178.3	197.0	218.0
137.5°	110.8	114.1	119.1	125.7	133.6	143.0	153.2	164.4	177.6	193.2	210.3
140°	113.8	116.9	122.0	128.2	136.2	145.3	154.7	165.4	177.5	190.9	205.8
142.5°	116.5	119.9	124.5	130.8	138.1	147.0	156.2	166.2	176.9	189.0	201.5
145°	121.0	123.9	128.6	133.9	141.2	149.4	157.8	166.7	176.1	186.2	196.4
147.5°	125.6	128.3	132.4	137.6	143.7	151.2	158.9	166.7	175.0	183.6	192.1
150°	128.6	131.1	135.2	139.6	145.3	152.5	159.2	166.7	174.0	181.8	189.0
152.5°	131.6	134.1	137.7	141.6	147.0	153.3	159.6	165.9	172.7	179.8	186.3
155°	136.4	138.3	141.5	145.0	149.4	154.7	159.8	165.1	170.5	176.7	182.2
157.5°	140.6	142.1	144.9	147.8	151.2	155.5	160.1	164.1	168.5	173.3	177.7
160°	143.4	144.6	147.1	149.4	152.5	156.3	160.1	163.5	167.0	171.1	175.2
162.5°	145.6	146.7	148.6	150.6	153.3	156.6	159.8	162.6	165.5	168.8	172.2
165°	148.7	149.4	151.0	152.2	154.4	156.9	159.2	161.0	163.3	165.8	168.3
167.5°	151.2	151.6	152.8	153.6	155.1	156.9	158.6	159.5	161.0	162.8	164.9
170°	152.5	152.8	153.7	154.4	155.1	156.6	157.8	158.5	159.4	161.0	162.6
172.5°	153.7	153.8	154.5	154.9	155.2	156.6	157.7	157.7	158.2	159.3	160.6
175°	155.1	154.7	155.3	155.3	155.7	156.3	156.9	156.6	156.6	157.2	157.8
177.5°	155.7	155.4	155.7	155.7	155.7	156.0	156.4	156.0	155.7	156.0	156.1
180°	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7



TEST NUMBER: P332302-940

CATALOG NUMBER: S123RDIP-S775D365U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6
2.5°	1150.3	1150.3	1151.8	1157.4	1158.2	1163.1	1161.5
5°	1264.3	1273.1	1276.4	1290.4	1298.8	1302.5	1295.0
7.5°	1403.6	1428.6	1440.5	1455.1	1468.1	1472.0	1461.8
10°	1505.1	1531.2	1553.3	1566.7	1579.4	1587.8	1598.5
12.5°	1603.4	1635.5	1656.4	1675.4	1688.5	1699.1	1700.8
15°	1710.1	1758.6	1795.5	1822.6	1836.1	1843.2	1840.3
17.5°	1817.8	1862.8	1889.0	1916.6	1935.4	1936.4	1936.9
20°	1878.7	1922.5	1952.8	1973.4	1994.4	1993.5	1998.1
22.5°	1919.3	1953.9	1977.1	1992.1	1999.3	1995.7	1996.6
25°	1938.4	1948.7	1944.5	1920.7	1914.6	1892.7	1896.4
27.5°	1840.1	1791.6	1741.3	1676.8	1625.8	1585.1	1587.2
30°	1706.8	1621.0	1522.9	1440.7	1367.0	1346.4	1302.5
32.5°	1520.5	1391.6	1276.8	1200.2	1136.8	1119.7	1081.5
35°	1204.5	1079.3	961.3	890.3	862.3	823.0	822.6
37.5°	936.2	826.1	763.6	710.3	682.4	658.7	656.4
40°	787.6	701.7	654.5	616.3	588.7	571.0	566.8
42.5°	683.8	614.3	570.2	546.4	525.2	516.0	509.3
45°	558.4	511.7	480.9	459.4	449.6	442.6	438.8
47.5°	467.1	435.8	414.7	400.5	392.5	385.1	387.1
50°	417.4	391.7	376.3	362.7	356.7	351.5	352.0
52.5°	377.4	354.4	341.9	332.2	324.6	320.9	319.1
55°	320.3	305.8	293.2	286.1	282.0	276.9	275.4
57.5°	273.2	262.0	251.7	243.8	242.7	237.8	238.4
60°	241.8	232.5	224.1	219.9	216.6	212.4	213.8
62.5°	216.1	208.2	200.5	197.1	193.9	190.7	191.5
65°	176.9	169.4	164.8	162.9	161.5	160.2	158.7
67.5°	141.0	136.4	133.5	129.5	126.6	126.2	124.8
70°	118.6	112.5	107.4	102.3	100.9	100.4	100.9
72.5°	95.1	91.2	89.8	87.3	87.0	85.8	86.7
75°	71.4	70.0	69.1	67.2	67.2	67.2	67.2
77.5°	52.7	51.8	51.3	50.9	50.4	49.8	49.7
80°	41.1	40.6	39.7	39.7	39.2	39.7	39.2
82.5°	31.0	30.9	30.0	30.0	29.5	29.2	29.5
85°	15.9	15.4	16.3	15.4	15.9	15.0	15.9
87.5°	6.2	6.2	6.0	5.9	5.5	6.3	5.5
90°	8.2	8.5	9.1	8.8	9.1	9.5	9.1
92.5°	21.0	18.5	16.9	16.4	15.4	15.8	15.2
95°	76.9	60.2	48.9	42.9	40.0	37.8	36.6
97.5°	226.5	185.8	148.2	124.9	110.8	102.2	99.5
100°	346.0	309.2	264.4	232.6	209.6	197.2	197.6
102.5°	400.2	378.7	350.4	325.6	307.4	297.1	289.8
105°	441.1	447.1	439.0	424.5	412.5	402.4	400.8
107.5°	436.0	463.6	474.8	475.1	471.0	467.6	464.8
110°	419.1	458.8	480.9	489.7	492.2	491.6	491.0



TEST NUMBER: P332302-940

CATALOG NUMBER: S123RDIP-S775D365U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	396.9	441.4	469.8	485.9	493.7	496.1	496.2
115°	361.4	407.8	442.1	465.7	479.6	485.9	487.5
117.5°	331.4	373.0	407.9	432.6	448.4	457.4	459.6
120°	314.8	352.6	384.4	409.3	427.0	434.5	436.4
122.5°	301.4	336.4	366.0	388.2	404.0	412.3	414.7
125°	284.9	315.1	340.4	360.5	374.3	382.3	384.4
127.5°	270.3	297.6	320.6	338.5	350.4	357.5	359.4
130°	261.3	286.8	308.2	324.9	336.3	342.9	345.4
132.5°	252.6	276.4	296.9	312.5	323.9	329.8	331.5
135°	240.4	260.9	278.8	294.4	303.8	309.4	311.7
137.5°	228.6	246.3	261.9	274.8	284.5	289.2	290.7
140°	221.9	236.9	250.5	262.5	271.3	276.3	276.1
142.5°	215.3	228.4	240.1	250.4	258.2	262.7	262.4
145°	206.7	216.8	226.0	233.8	240.4	243.0	243.6
147.5°	200.4	208.5	215.0	221.0	225.4	227.8	228.1
150°	196.4	203.0	208.9	213.7	217.1	219.0	219.0
152.5°	192.5	198.4	203.4	207.1	210.3	211.4	211.4
155°	187.2	191.9	195.6	198.5	201.1	201.7	202.0
157.5°	181.9	185.6	188.6	191.0	192.9	193.4	193.3
160°	178.7	181.8	184.0	186.2	188.2	188.2	187.8
162.5°	175.1	178.1	180.0	181.5	183.1	183.1	182.8
165°	170.1	172.4	174.0	175.2	176.5	176.1	176.1
167.5°	166.3	167.6	168.7	169.2	170.1	169.9	169.9
170°	163.5	164.8	165.4	165.8	166.4	166.0	166.0
172.5°	161.3	162.3	162.6	162.7	163.4	162.8	162.6
175°	158.2	158.8	158.8	158.8	159.2	158.8	158.5
177.5°	156.4	156.7	156.7	156.4	156.7	156.1	156.1
180°	155.7	155.7	155.7	155.7	155.7	155.7	155.7

(END OF REPORT)