

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332528-927

Luminaire Tested: **S124DIP-S350D1205U927-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332528-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIP-S350D1205U927-4F0-1E-UDD-A4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4658.9 lumens
Efficiency: N/A
Efficacy: 110.4 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 42.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332528-927

CATALOG NUMBER: S124DIP-S350D1205U927-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332528-927

CATALOG NUMBER: S124DIP-S350D1205U927-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	35	35	35	27				
1	93	89	85	82	83	79	76	73	62	60	58	46	44	43	31	30	30	23				
2	84	77	72	67	75	69	64	60	54	51	48	40	38	36	27	26	25	19				
3	77	68	61	56	69	61	55	50	48	44	40	36	33	31	24	23	21	16				
4	70	60	53	47	63	54	48	43	43	38	34	32	29	26	22	20	19	14				
5	65	54	46	40	57	48	42	37	38	33	30	28	25	23	20	18	16	12				
6	59	48	40	35	53	43	36	32	34	29	26	26	22	20	18	16	14	11				
7	55	43	36	30	49	39	32	28	31	26	23	23	20	18	16	14	13	10				
8	51	39	32	27	45	35	29	24	28	23	20	21	18	16	15	13	11	9				
9	47	35	28	23	42	32	26	22	26	21	18	20	16	14	14	12	10	8				
10	44	32	26	21	39	29	23	19	24	19	16	18	15	13	13	11	9	7				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	3654	3654	3654	3654
5°	4302	3663	3233	3663
10°	5151	3647	2911	3647
15°	6095	3611	2674	3611
20°	6787	3572	2461	3572
25°	6897	3517	2314	3517
30°	5868	3464	2269	3464
35°	4512	3377	2269	3377
40°	3517	3276	2312	3276
45°	2932	3123	2351	3123
50°	2581	2936	2430	2936
55°	2365	2712	2528	2712
60°	2215	2512	2645	2512
65°	2063	2288	2743	2288
70°	1886	2065	2804	2065
75°	1684	1818	2773	1818
80°	1409	1492	2687	1492
85°	1037	1074	2566	1074



TEST NUMBER: P332528-927

CATALOG NUMBER: S124DIP-S350D1205U927-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.1	0.9
10°-20°	135.9	2.9
20°-30°	215.5	4.6
30°-40°	239.8	5.1
40°-50°	218.3	4.7
50°-60°	178.4	3.8
60°-70°	127.4	2.7
70°-80°	70.1	1.5
80°-90°	21.7	0.5
90°-100°	338.4	7.3
100°-110°	704.3	15.1
110°-120°	630.9	13.5
120°-130°	530.7	11.4
130°-140°	442.5	9.5
140°-150°	338.0	7.3
150°-160°	237.6	5.1
160°-170°	139.8	3.0
170°-180°	45.5	1.0
0°-30°	395.5	8.5
0°-40°	635.3	13.6
0°-60°	1032.1	22.2
0°-90°	1251.3	26.9
90°-120°	1673.6	35.9
90°-150°	2984.8	64.1
90°-180°	3408.0	73.1
0°-180°	4658.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	453	453	453	453	453	
5°	531	452	399	452	531	54
15°	729	432	320	432	729	206
25°	774	395	260	395	774	341
35°	458	343	230	343	458	291
45°	257	274	206	274	257	202
55°	168	193	180	193	168	152
65°	108	120	144	120	108	107
75°	54	58	89	58	54	57
85°	11	12	28	12	11	14
90°	19	1	19	1	19	16
95°	225	30	225	30	225	349
105°	1295	108	1295	108	1295	1280
115°	1244	190	1244	190	1244	1235
125°	992	264	992	264	992	902
135°	887	314	887	314	887	685
145°	724	362	724	362	724	459
155°	607	412	607	412	607	283
165°	529	448	529	448	529	152
175°	477	468	477	468	477	46
180°	469	469	469	469	469	



TEST NUMBER: P332528-927

CATALOG NUMBER: S124DIP-S350D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6
2.5°	481.6	481.6	480.1	479.7	478.7	477.4	477.1	474.6	469.8	467.5	467.0
5°	530.9	534.7	529.8	528.9	528.3	522.1	519.0	515.2	506.6	501.5	497.6
7.5°	589.8	590.2	588.0	586.4	581.5	576.2	568.1	559.4	549.1	538.5	530.4
10°	628.4	629.9	627.5	627.2	617.6	611.6	599.6	589.5	577.8	564.9	553.1
12.5°	669.2	667.2	665.9	657.9	656.1	645.2	631.2	620.8	602.9	588.0	572.3
15°	729.3	725.2	722.5	711.5	706.1	690.9	676.0	664.6	641.2	618.9	602.0
17.5°	764.5	768.7	762.6	758.0	744.0	733.3	718.2	694.2	675.9	648.2	626.9
20°	790.0	790.4	787.0	782.4	771.3	757.8	741.3	715.1	693.2	665.6	636.3
22.5°	796.9	797.0	795.6	791.2	782.8	771.9	755.3	733.3	706.8	676.8	647.5
25°	774.3	773.6	775.2	780.1	777.0	773.6	764.0	747.7	722.9	691.3	659.7
27.5°	690.1	695.4	704.9	716.8	728.4	737.2	739.7	736.3	721.0	695.0	661.9
30°	629.5	636.0	643.1	655.1	678.3	691.7	706.2	717.3	711.1	690.3	659.6
32.5°	563.0	564.6	575.1	588.7	610.1	635.6	658.9	681.4	688.8	677.9	652.2
35°	457.8	460.5	471.9	485.4	511.4	542.8	577.7	608.8	634.5	644.8	631.6
37.5°	373.6	381.1	389.2	403.7	426.7	454.9	491.1	531.4	569.7	595.3	599.7
40°	333.7	338.4	344.2	355.3	374.8	402.5	433.6	479.7	520.5	557.2	569.2
42.5°	302.2	305.0	308.6	318.5	333.4	361.0	389.4	430.0	470.8	514.8	534.9
45°	256.8	259.7	265.7	271.5	282.7	301.8	328.3	361.6	402.7	445.0	482.2
47.5°	224.1	225.9	229.4	235.7	245.3	257.9	279.3	307.2	345.2	386.4	426.0
50°	205.5	207.0	209.8	215.4	222.8	234.0	251.6	277.7	307.4	348.9	387.7
52.5°	190.8	191.4	193.5	197.3	203.1	212.5	227.0	248.6	276.3	313.2	351.9
55°	168.0	168.7	170.6	173.4	178.5	184.5	195.5	211.7	235.8	267.9	301.5
57.5°	149.2	149.8	151.3	152.4	156.6	161.4	170.0	181.5	199.8	227.0	257.0
60°	137.2	136.9	138.7	139.7	142.5	146.6	153.2	164.2	180.1	202.1	229.7
62.5°	125.6	125.0	126.6	127.9	129.4	132.9	138.3	146.9	159.9	179.7	203.6
65°	108.0	107.3	108.2	109.7	111.1	113.0	117.0	124.7	135.0	149.2	167.4
67.5°	90.4	91.2	91.3	92.1	92.9	95.5	98.2	103.6	110.9	122.3	137.7
70°	79.9	80.1	80.8	80.8	81.4	83.7	85.9	89.0	96.2	106.7	119.2
72.5°	69.4	70.2	69.9	70.4	70.9	72.4	74.0	77.1	83.1	90.9	101.6
75°	54.0	54.6	54.6	54.7	55.3	55.8	57.2	59.4	63.8	69.6	76.8
77.5°	39.4	39.5	39.7	40.4	40.4	41.3	42.2	44.0	46.2	50.1	54.7
80°	30.3	30.7	30.6	31.0	31.0	31.7	32.1	34.3	35.3	37.9	41.4
82.5°	22.3	22.7	22.6	23.1	23.4	23.6	24.1	25.0	26.0	28.3	29.7
85°	11.2	11.6	11.2	11.6	12.2	12.4	12.9	13.2	13.9	14.4	15.8
87.5°	7.1	7.6	7.8	7.8	7.8	8.0	8.0	7.7	8.1	8.4	8.6
90°	19.3	19.3	20.3	19.3	18.4	18.4	17.5	16.6	15.7	16.6	14.7
92.5°	70.9	70.9	74.0	79.0	89.8	108.3	136.0	180.8	243.2	292.0	255.6
95°	224.6	236.5	253.2	281.7	326.8	416.1	539.4	682.1	771.4	750.2	566.1
97.5°	600.4	619.5	647.1	702.5	768.7	864.7	954.7	1007.8	969.2	790.2	529.8
100°	844.1	851.5	879.1	935.3	1015.3	1083.5	1128.5	1110.2	975.7	740.1	480.5
102.5°	1056.2	1062.1	1091.2	1131.9	1181.0	1209.3	1196.3	1105.0	920.5	677.5	447.3
105°	1295.1	1300.7	1313.6	1321.0	1319.1	1281.4	1190.3	1030.9	820.1	603.9	418.8
107.5°	1383.9	1381.5	1372.3	1351.3	1305.8	1223.8	1095.4	925.8	739.2	562.6	413.7
110°	1385.4	1377.1	1360.5	1321.8	1256.5	1155.2	1021.8	862.5	698.7	548.7	415.2



TEST NUMBER: P332528-927

CATALOG NUMBER: S124DIP-S350D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1342.0	1328.5	1305.3	1258.5	1184.3	1083.1	957.0	816.1	675.8	542.0	419.5
115°	1243.6	1236.3	1206.8	1151.6	1078.9	990.5	882.8	769.5	654.5	538.5	428.0
117.5°	1144.0	1138.3	1108.5	1062.1	1000.1	925.1	840.4	746.7	644.9	537.6	437.0
120°	1088.1	1077.9	1054.0	1013.5	961.0	895.6	822.0	736.4	639.8	537.6	443.7
122.5°	1043.9	1033.7	1013.5	978.9	934.5	877.3	810.2	727.5	633.9	536.9	450.4
125°	992.3	986.8	969.3	942.6	905.8	855.2	791.6	712.5	624.1	535.8	460.3
127.5°	962.1	956.6	941.9	918.1	881.1	833.1	769.8	694.0	611.0	533.7	468.2
130°	944.4	938.9	924.2	901.2	863.5	814.7	752.1	679.4	602.9	533.0	474.0
132.5°	924.6	919.0	905.1	879.1	842.1	793.3	732.2	663.8	595.6	532.3	479.2
135°	887.4	881.9	867.1	841.4	804.5	758.5	702.3	642.5	584.6	531.2	487.0
137.5°	841.4	834.7	822.6	797.2	762.7	721.1	673.8	623.2	575.0	530.9	491.5
140°	808.2	800.8	788.0	767.7	735.5	696.8	655.4	612.1	569.8	530.2	495.3
142.5°	772.9	767.7	756.3	737.5	709.0	675.5	639.9	601.8	565.4	530.2	498.2
145°	724.5	719.9	710.7	695.0	672.0	646.2	618.6	587.3	557.9	528.4	499.9
147.5°	681.5	679.9	672.9	659.5	642.5	622.3	600.2	575.4	551.0	525.1	500.7
150°	657.3	656.3	650.8	638.8	624.1	607.5	589.1	568.0	545.9	522.8	500.7
152.5°	635.2	634.2	630.9	621.2	608.6	595.0	578.1	559.8	540.0	519.2	499.3
155°	606.7	606.7	603.9	596.5	587.3	576.2	562.4	547.7	531.2	513.7	497.1
157.5°	581.6	581.6	580.0	574.4	567.4	558.6	547.0	534.6	522.1	507.9	494.7
160°	566.1	566.1	565.2	559.7	554.1	546.8	536.6	526.6	515.5	503.5	492.5
162.5°	551.4	552.2	551.2	545.7	541.6	535.0	527.1	518.4	509.6	499.1	490.3
165°	529.3	530.2	531.2	527.4	523.8	519.2	512.7	507.2	499.9	492.5	486.0
167.5°	511.8	512.5	512.7	510.3	508.5	505.7	500.6	496.4	491.0	485.8	481.6
170°	500.7	500.7	501.7	500.7	498.9	496.1	492.5	489.7	485.1	481.4	478.6
172.5°	489.7	491.2	492.1	491.2	490.0	488.1	485.8	483.8	480.0	477.0	475.7
175°	476.8	478.6	480.5	478.6	478.6	478.6	476.8	475.9	474.0	472.2	472.2
177.5°	469.3	470.7	472.2	471.5	472.2	471.5	471.5	470.7	470.0	469.3	469.3
180°	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6



TEST NUMBER: P332528-927

CATALOG NUMBER: S124DIP-S350D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6
2.5°	467.1	465.0	463.5	462.3	459.1	457.1	455.6	453.5	451.1	448.5	445.4
5°	493.6	487.3	482.6	475.5	468.7	463.1	457.2	452.0	445.7	438.7	433.6
7.5°	521.5	512.0	499.9	489.3	477.4	467.1	458.0	448.5	438.7	429.1	420.4
10°	539.2	527.0	513.5	497.6	482.6	469.3	456.9	444.9	433.2	421.7	411.7
12.5°	558.3	543.0	523.1	504.5	487.7	469.8	455.0	440.2	426.2	414.0	402.4
15°	583.8	561.9	538.8	513.9	491.8	471.0	450.5	432.0	416.2	400.1	388.8
17.5°	599.5	572.4	546.1	520.0	493.2	466.9	444.9	423.5	403.8	387.8	373.6
20°	609.9	582.9	550.1	524.0	492.2	465.2	439.7	415.8	395.2	378.2	363.5
22.5°	618.9	587.7	554.8	520.5	488.9	460.2	432.3	408.4	387.3	369.3	355.3
25°	623.8	588.0	552.3	518.2	482.2	448.3	422.9	394.8	372.3	353.4	338.4
27.5°	624.3	586.0	545.7	507.8	470.6	439.0	407.1	381.9	358.6	338.6	324.2
30°	622.7	582.7	539.4	498.4	461.1	426.7	398.9	371.6	347.8	327.9	312.9
32.5°	617.3	575.8	531.3	487.8	449.2	415.6	387.0	360.9	337.7	318.1	302.4
35°	602.2	561.1	513.7	468.5	429.0	395.1	369.2	342.7	319.5	301.0	285.7
37.5°	578.5	541.4	493.1	446.4	407.5	373.4	347.8	323.9	302.9	284.1	268.5
40°	557.8	525.1	476.7	431.2	389.2	356.8	332.8	310.9	290.0	272.2	257.4
42.5°	533.9	505.5	460.9	412.6	372.1	339.5	316.2	296.4	276.9	260.4	245.6
45°	491.4	472.6	430.6	386.0	343.8	313.1	290.8	273.5	257.1	240.9	228.5
47.5°	442.5	433.2	397.8	355.5	315.4	285.1	265.8	249.9	235.4	221.7	210.8
50°	409.6	405.1	374.6	333.7	295.5	267.0	247.5	233.8	221.4	209.5	199.1
52.5°	377.2	377.1	349.5	312.1	276.7	249.3	229.9	217.1	206.4	196.7	187.4
55°	327.7	333.0	311.4	278.1	246.4	221.6	204.1	192.7	185.2	177.2	170.2
57.5°	282.3	291.0	273.1	243.8	217.3	194.6	179.4	170.8	162.8	157.9	152.8
60°	252.5	260.8	246.9	222.2	197.3	177.8	163.3	155.6	148.7	145.3	141.7
62.5°	226.2	233.5	223.2	200.3	178.6	159.9	147.7	140.3	135.6	132.0	129.6
65°	188.5	194.6	185.8	169.1	150.5	135.5	125.6	119.8	115.3	113.8	111.1
67.5°	152.3	158.0	153.2	139.0	124.1	112.7	105.0	99.4	96.7	95.5	93.6
70°	130.9	136.5	131.4	119.1	107.6	98.1	90.7	87.5	84.8	84.2	81.6
72.5°	112.7	116.5	111.5	101.8	92.1	84.0	78.3	74.9	73.5	72.5	71.1
75°	84.5	87.9	84.5	77.1	70.1	64.5	59.7	58.3	56.6	56.1	55.1
77.5°	59.8	62.7	60.2	55.5	50.3	45.9	43.3	41.7	41.3	40.3	40.8
80°	45.7	47.6	45.2	42.0	37.9	34.9	33.0	32.1	31.0	30.6	31.3
82.5°	32.9	33.7	32.4	30.3	27.3	25.3	24.0	22.9	22.7	22.7	22.7
85°	17.0	16.9	16.7	14.8	13.9	12.6	11.8	11.6	11.4	11.8	12.2
87.5°	8.2	8.4	7.2	6.6	5.9	5.3	4.6	4.1	4.6	5.3	5.6
90°	12.9	12.9	7.4	7.4	6.4	5.5	2.8	1.0	2.8	5.5	6.4
92.5°	185.9	114.5	67.7	48.6	35.2	23.9	15.3	10.5	15.3	23.9	35.2
95°	346.1	195.1	115.1	76.4	54.3	42.4	33.1	30.3	33.1	42.4	54.3
97.5°	311.2	186.5	124.8	92.4	73.4	62.4	54.5	54.5	54.5	62.4	73.4
100°	292.7	188.7	134.4	105.0	87.5	76.4	69.9	69.9	69.9	76.4	87.5
102.5°	287.6	196.1	146.9	118.9	102.2	91.9	86.2	84.7	86.2	91.9	102.2
105°	289.9	213.6	169.4	142.7	126.1	115.1	110.4	107.7	110.4	115.1	126.1
107.5°	303.6	234.0	193.5	167.2	151.3	139.6	134.9	133.1	134.9	139.6	151.3
110°	313.9	249.5	209.0	184.1	167.5	156.5	151.9	150.0	151.9	156.5	167.5



TEST NUMBER: P332528-927

CATALOG NUMBER: S124DIP-S350D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	325.0	264.2	225.1	200.3	183.7	173.4	168.1	166.3	168.1	173.4	183.7
115°	342.5	287.2	250.4	225.5	208.0	198.8	192.4	189.6	192.4	198.8	208.0
117.5°	360.3	309.5	274.5	248.7	232.3	222.2	216.5	213.9	216.5	222.2	232.3
120°	372.8	325.0	289.9	264.2	248.5	238.4	232.0	230.1	232.0	238.4	248.5
122.5°	384.6	339.7	304.7	279.6	262.5	253.2	246.7	244.9	246.7	253.2	262.5
125°	402.3	359.9	326.8	301.0	283.5	273.4	267.8	264.2	267.8	273.4	283.5
127.5°	417.6	378.7	346.7	320.7	302.5	290.9	284.2	281.3	284.2	290.9	302.5
130°	427.1	391.3	359.9	333.2	315.8	301.9	294.5	290.9	294.5	301.9	315.8
132.5°	436.7	401.6	370.3	345.0	326.1	313.0	303.4	300.5	303.4	313.0	326.1
135°	449.2	416.1	385.7	361.8	342.5	326.8	317.6	313.9	317.6	326.8	342.5
137.5°	458.0	427.1	398.8	376.0	355.8	341.0	330.8	327.3	330.8	341.0	355.8
140°	463.9	434.5	406.9	384.8	365.4	349.8	339.7	336.9	339.7	349.8	365.4
142.5°	468.3	441.1	414.2	392.8	374.3	359.3	350.0	347.2	350.0	359.3	374.3
145°	473.2	448.3	424.4	404.1	386.6	373.8	364.6	361.8	364.6	373.8	386.6
147.5°	477.4	455.7	433.2	414.9	400.4	387.1	379.1	378.1	379.1	387.1	400.4
150°	479.6	459.3	439.1	421.6	407.8	396.7	389.4	388.5	389.4	396.7	407.8
152.5°	481.1	462.3	444.3	428.3	415.9	405.6	398.2	398.0	398.2	405.6	415.9
155°	482.4	466.7	451.1	437.3	427.1	417.9	412.4	411.5	412.4	417.9	427.1
157.5°	482.4	469.8	456.6	445.7	436.9	429.7	424.5	424.5	424.5	429.7	436.9
160°	482.4	471.3	460.3	450.1	442.8	436.3	432.6	432.6	432.6	436.3	442.8
162.5°	482.4	472.8	462.5	454.6	447.9	442.2	439.3	440.0	439.3	442.2	447.9
165°	480.5	473.2	464.9	459.3	454.7	450.1	448.3	448.3	448.3	450.1	454.7
167.5°	478.3	472.9	466.9	462.6	460.1	456.6	455.7	456.6	455.7	456.6	460.1
170°	476.8	472.2	467.6	464.9	463.0	460.3	459.3	460.3	459.3	460.3	463.0
172.5°	475.4	471.5	468.3	466.4	465.2	463.2	463.0	463.9	463.0	463.2	465.2
175°	473.2	470.4	468.6	468.6	467.6	466.7	466.7	467.6	466.7	466.7	467.6
177.5°	470.7	469.3	468.6	468.6	468.6	467.8	468.6	469.3	468.6	467.8	468.6
180°	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6



TEST NUMBER: P332528-927

CATALOG NUMBER: S124DIP-S350D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6
2.5°	443.9	442.5	440.6	437.9	435.6	433.2	432.6	431.7	433.6	432.1	431.6
5°	429.4	425.4	420.3	414.5	411.1	406.3	405.4	403.5	401.6	401.4	399.5
7.5°	413.9	408.1	401.5	395.6	390.1	384.8	381.3	380.6	377.8	376.1	374.3
10°	404.0	396.9	389.2	383.6	377.2	371.6	367.7	365.4	363.5	361.5	359.6
12.5°	392.4	384.8	378.4	372.3	364.8	360.5	354.0	350.1	349.7	349.7	344.9
15°	378.7	371.2	361.5	352.8	348.7	340.5	336.9	332.4	329.6	326.8	324.6
17.5°	363.1	353.8	346.2	336.3	328.4	321.9	317.2	314.5	310.2	306.3	303.4
20°	353.4	343.5	335.4	324.9	316.3	308.2	304.3	300.6	297.4	294.0	290.8
22.5°	343.5	333.1	323.3	313.1	305.1	296.5	292.7	287.6	284.6	282.7	279.6
25°	327.9	316.6	305.4	295.6	287.4	279.9	274.9	270.9	267.5	266.0	264.0
27.5°	310.9	299.8	288.9	277.8	268.5	263.0	259.0	256.0	254.1	252.1	251.1
30°	300.2	288.5	276.9	266.6	258.0	252.5	248.8	246.8	245.3	244.3	243.4
32.5°	289.2	277.7	265.5	256.1	248.3	243.5	240.7	238.6	237.9	237.6	237.2
35°	271.6	260.1	248.8	240.3	233.1	231.2	228.7	227.6	227.2	228.5	229.1
37.5°	254.7	243.9	233.5	225.4	220.5	217.9	217.0	217.1	218.4	219.5	220.9
40°	243.8	233.2	223.5	216.3	211.8	210.2	209.8	210.7	212.2	213.6	215.1
42.5°	233.1	222.8	213.9	207.2	204.1	202.5	202.7	203.7	205.8	207.4	209.6
45°	216.6	207.9	199.3	193.8	191.2	191.6	191.6	193.3	195.4	197.8	200.3
47.5°	201.0	192.3	185.2	180.6	179.3	179.0	180.0	182.2	185.1	188.1	191.5
50°	190.5	182.2	176.0	171.9	170.4	171.0	172.5	174.5	178.1	181.9	185.4
52.5°	179.8	172.3	166.6	162.8	161.7	162.7	164.2	167.5	170.6	174.7	179.0
55°	163.3	156.9	152.4	149.6	149.2	149.8	151.5	155.0	159.5	164.6	168.7
57.5°	146.9	141.5	137.4	135.5	135.6	136.2	138.9	143.1	148.0	153.4	158.7
60°	135.7	130.9	127.5	126.0	126.2	127.3	130.7	134.6	140.6	145.8	151.5
62.5°	125.2	121.0	117.7	116.4	116.1	118.6	121.8	125.9	131.9	137.8	143.9
65°	108.4	105.0	102.3	101.6	102.2	104.1	108.2	113.6	118.7	124.8	131.3
67.5°	91.9	89.1	87.3	87.6	88.3	91.1	94.5	99.2	105.0	111.4	117.6
70°	81.4	78.7	77.2	77.4	78.6	81.9	84.9	89.6	95.8	102.3	107.6
72.5°	70.6	68.8	67.5	68.3	69.4	71.7	75.5	80.2	85.6	91.7	97.3
75°	54.2	54.2	53.5	54.0	55.7	57.9	60.8	65.6	71.1	76.0	80.4
77.5°	40.2	39.8	40.2	41.0	41.9	44.6	47.8	51.3	55.4	60.3	64.0
80°	30.7	31.0	31.8	33.0	33.4	35.4	38.8	42.0	45.2	49.3	52.8
82.5°	23.1	23.3	23.8	25.2	25.6	27.8	29.9	33.1	36.0	38.8	41.7
85°	12.6	12.6	13.5	14.1	15.0	16.5	17.8	19.7	22.3	24.2	27.0
87.5°	6.3	6.3	8.0	8.2	9.1	10.2	10.3	12.2	12.9	13.9	15.2
90°	7.4	7.4	12.9	12.9	14.7	16.6	15.7	16.6	17.5	18.4	18.4
92.5°	48.6	67.7	114.5	185.9	255.6	292.0	243.2	180.8	136.0	108.3	89.8
95°	76.4	115.1	195.1	346.1	566.1	750.2	771.4	682.1	539.4	416.1	326.8
97.5°	92.4	124.8	186.5	311.2	529.8	790.2	969.2	1007.8	954.7	864.7	768.7
100°	105.0	134.4	188.7	292.7	480.5	740.1	975.7	1110.2	1128.5	1083.5	1015.3
102.5°	118.9	146.9	196.1	287.6	447.3	677.5	920.5	1105.0	1196.3	1209.3	1181.0
105°	142.7	169.4	213.6	289.9	418.8	603.9	820.1	1030.9	1190.3	1281.4	1319.1
107.5°	167.2	193.5	234.0	303.6	413.7	562.6	739.2	925.8	1095.4	1223.8	1305.8
110°	184.1	209.0	249.5	313.9	415.2	548.7	698.7	862.5	1021.8	1155.2	1256.5



TEST NUMBER: P332528-927

CATALOG NUMBER: S124DIP-S350D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	200.3	225.1	264.2	325.0	419.5	542.0	675.8	816.1	957.0	1083.1	1184.3
115°	225.5	250.4	287.2	342.5	428.0	538.5	654.5	769.5	882.8	990.5	1078.9
117.5°	248.7	274.5	309.5	360.3	437.0	537.6	644.9	746.7	840.4	925.1	1000.1
120°	264.2	289.9	325.0	372.8	443.7	537.6	639.8	736.4	822.0	895.6	961.0
122.5°	279.6	304.7	339.7	384.6	450.4	536.9	633.9	727.5	810.2	877.3	934.5
125°	301.0	326.8	359.9	402.3	460.3	535.8	624.1	712.5	791.6	855.2	905.8
127.5°	320.7	346.7	378.7	417.6	468.2	533.7	611.0	694.0	769.8	833.1	881.1
130°	333.2	359.9	391.3	427.1	474.0	533.0	602.9	679.4	752.1	814.7	863.5
132.5°	345.0	370.3	401.6	436.7	479.2	532.3	595.6	663.8	732.2	793.3	842.1
135°	361.8	385.7	416.1	449.2	487.0	531.2	584.6	642.5	702.3	758.5	804.5
137.5°	376.0	398.8	427.1	458.0	491.5	530.9	575.0	623.2	673.8	721.1	762.7
140°	384.8	406.9	434.5	463.9	495.3	530.2	569.8	612.1	655.4	696.8	735.5
142.5°	392.8	414.2	441.1	468.3	498.2	530.2	565.4	601.8	639.9	675.5	709.0
145°	404.1	424.4	448.3	473.2	499.9	528.4	557.9	587.3	618.6	646.2	672.0
147.5°	414.9	433.2	455.7	477.4	500.7	525.1	551.0	575.4	600.2	622.3	642.5
150°	421.6	439.1	459.3	479.6	500.7	522.8	545.9	568.0	589.1	607.5	624.1
152.5°	428.3	444.3	462.3	481.1	499.3	519.2	540.0	559.8	578.1	595.0	608.6
155°	437.3	451.1	466.7	482.4	497.1	513.7	531.2	547.7	562.4	576.2	587.3
157.5°	445.7	456.6	469.8	482.4	494.7	507.9	522.1	534.6	547.0	558.6	567.4
160°	450.1	460.3	471.3	482.4	492.5	503.5	515.5	526.6	536.6	546.8	554.1
162.5°	454.6	462.5	472.8	482.4	490.3	499.1	509.6	518.4	527.1	535.0	541.6
165°	459.3	464.9	473.2	480.5	486.0	492.5	499.9	507.2	512.7	519.2	523.8
167.5°	462.6	466.9	472.9	478.3	481.6	485.8	491.0	496.4	500.6	505.7	508.5
170°	464.9	467.6	472.2	476.8	478.6	481.4	485.1	489.7	492.5	496.1	498.9
172.5°	466.4	468.3	471.5	475.4	475.7	477.0	480.0	483.8	485.8	488.1	490.0
175°	468.6	468.6	470.4	473.2	472.2	472.2	474.0	475.9	476.8	478.6	478.6
177.5°	468.6	468.6	469.3	470.7	469.3	469.3	470.0	470.7	471.5	471.5	472.2
180°	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6



TEST NUMBER: P332528-927

CATALOG NUMBER: S124DIP-S350D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6
2.5°	431.3	431.0	429.9	429.8	429.9	431.0	431.3	431.6	432.1	433.6	431.7
5°	398.4	397.4	396.9	398.9	396.9	397.4	398.4	399.5	401.4	401.6	403.5
7.5°	373.6	372.9	371.2	370.7	371.2	372.9	373.6	374.3	376.1	377.8	380.6
10°	357.7	357.0	355.5	355.1	355.5	357.0	357.7	359.6	361.5	363.5	365.4
12.5°	342.4	341.0	340.6	341.0	340.6	341.0	342.4	344.9	349.7	349.7	350.1
15°	322.1	321.3	319.2	319.9	319.2	321.3	322.1	324.6	326.8	329.6	332.4
17.5°	302.1	301.2	298.7	300.9	298.7	301.2	302.1	303.4	306.3	310.2	314.5
20°	289.5	288.0	286.7	286.5	286.7	288.0	289.5	290.8	294.0	297.4	300.6
22.5°	277.5	276.2	276.0	274.8	276.0	276.2	277.5	279.6	282.7	284.6	287.6
25°	262.4	261.2	260.8	259.8	260.8	261.2	262.4	264.0	266.0	267.5	270.9
27.5°	251.0	250.3	249.6	249.9	249.6	250.3	251.0	251.1	252.1	254.1	256.0
30°	243.9	243.8	243.4	243.4	243.4	243.8	243.9	243.4	244.3	245.3	246.8
32.5°	238.1	238.1	238.3	238.3	238.3	238.1	238.1	237.2	237.6	237.9	238.6
35°	229.9	230.4	230.8	230.2	230.8	230.4	229.9	229.1	228.5	227.2	227.6
37.5°	222.4	223.0	223.6	224.2	223.6	223.0	222.4	220.9	219.5	218.4	217.1
40°	216.7	218.0	218.4	219.4	218.4	218.0	216.7	215.1	213.6	212.2	210.7
42.5°	211.4	212.8	213.7	214.0	213.7	212.8	211.4	209.6	207.4	205.8	203.7
45°	203.0	204.5	205.9	205.9	205.9	204.5	203.0	200.3	197.8	195.4	193.3
47.5°	194.5	196.6	198.0	198.3	198.0	196.6	194.5	191.5	188.1	185.1	182.2
50°	188.6	191.2	192.6	193.5	192.6	191.2	188.6	185.4	181.9	178.1	174.5
52.5°	182.9	185.5	187.3	187.7	187.3	185.5	182.9	179.0	174.7	170.6	167.5
55°	173.0	176.8	178.9	179.6	178.9	176.8	173.0	168.7	164.6	159.5	155.0
57.5°	163.7	167.2	169.6	170.2	169.6	167.2	163.7	158.7	153.4	148.0	143.1
60°	156.5	160.3	163.3	163.8	163.3	160.3	156.5	151.5	145.8	140.6	134.6
62.5°	149.2	153.1	155.8	157.2	155.8	153.1	149.2	143.9	137.8	131.9	125.9
65°	136.5	140.5	143.1	143.6	143.1	140.5	136.5	131.3	124.8	118.7	113.6
67.5°	122.6	126.6	128.3	129.4	128.3	126.6	122.6	117.6	111.4	105.0	99.2
70°	112.9	116.1	118.0	118.8	118.0	116.1	112.9	107.6	102.3	95.8	89.6
72.5°	101.8	105.1	107.3	107.5	107.3	105.1	101.8	97.3	91.7	85.6	80.2
75°	84.8	87.8	88.9	88.9	88.9	87.8	84.8	80.4	76.0	71.1	65.6
77.5°	67.1	68.6	70.0	70.3	70.0	68.6	67.1	64.0	60.3	55.4	51.3
80°	55.7	56.6	57.8	57.8	57.8	56.6	55.7	52.8	49.3	45.2	42.0
82.5°	44.0	44.8	45.9	45.7	45.9	44.8	44.0	41.7	38.8	36.0	33.1
85°	26.6	28.3	28.1	27.7	28.1	28.3	26.6	27.0	24.2	22.3	19.7
87.5°	15.8	16.2	16.5	16.8	16.5	16.2	15.8	15.2	13.9	12.9	12.2
90°	19.3	20.3	19.3	19.3	19.3	20.3	19.3	18.4	18.4	17.5	16.6
92.5°	79.0	74.0	70.9	70.9	70.9	74.0	79.0	89.8	108.3	136.0	180.8
95°	281.7	253.2	236.5	224.6	236.5	253.2	281.7	326.8	416.1	539.4	682.1
97.5°	702.5	647.1	619.5	600.4	619.5	647.1	702.5	768.7	864.7	954.7	1007.8
100°	935.3	879.1	851.5	844.1	851.5	879.1	935.3	1015.3	1083.5	1128.5	1110.2
102.5°	1131.9	1091.2	1062.1	1056.2	1062.1	1091.2	1131.9	1181.0	1209.3	1196.3	1105.0
105°	1321.0	1313.6	1300.7	1295.1	1300.7	1313.6	1321.0	1319.1	1281.4	1190.3	1030.9
107.5°	1351.3	1372.3	1381.5	1383.9	1381.5	1372.3	1351.3	1305.8	1223.8	1095.4	925.8
110°	1321.8	1360.5	1377.1	1385.4	1377.1	1360.5	1321.8	1256.5	1155.2	1021.8	862.5



TEST NUMBER: P332528-927

CATALOG NUMBER: S124DIP-S350D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1258.5	1305.3	1328.5	1342.0	1328.5	1305.3	1258.5	1184.3	1083.1	957.0	816.1
115°	1151.6	1206.8	1236.3	1243.6	1236.3	1206.8	1151.6	1078.9	990.5	882.8	769.5
117.5°	1062.1	1108.5	1138.3	1144.0	1138.3	1108.5	1062.1	1000.1	925.1	840.4	746.7
120°	1013.5	1054.0	1077.9	1088.1	1077.9	1054.0	1013.5	961.0	895.6	822.0	736.4
122.5°	978.9	1013.5	1033.7	1043.9	1033.7	1013.5	978.9	934.5	877.3	810.2	727.5
125°	942.6	969.3	986.8	992.3	986.8	969.3	942.6	905.8	855.2	791.6	712.5
127.5°	918.1	941.9	956.6	962.1	956.6	941.9	918.1	881.1	833.1	769.8	694.0
130°	901.2	924.2	938.9	944.4	938.9	924.2	901.2	863.5	814.7	752.1	679.4
132.5°	879.1	905.1	919.0	924.6	919.0	905.1	879.1	842.1	793.3	732.2	663.8
135°	841.4	867.1	881.9	887.4	881.9	867.1	841.4	804.5	758.5	702.3	642.5
137.5°	797.2	822.6	834.7	841.4	834.7	822.6	797.2	762.7	721.1	673.8	623.2
140°	767.7	788.0	800.8	808.2	800.8	788.0	767.7	735.5	696.8	655.4	612.1
142.5°	737.5	756.3	767.7	772.9	767.7	756.3	737.5	709.0	675.5	639.9	601.8
145°	695.0	710.7	719.9	724.5	719.9	710.7	695.0	672.0	646.2	618.6	587.3
147.5°	659.5	672.9	679.9	681.5	679.9	672.9	659.5	642.5	622.3	600.2	575.4
150°	638.8	650.8	656.3	657.3	656.3	650.8	638.8	624.1	607.5	589.1	568.0
152.5°	621.2	630.9	634.2	635.2	634.2	630.9	621.2	608.6	595.0	578.1	559.8
155°	596.5	603.9	606.7	606.7	606.7	603.9	596.5	587.3	576.2	562.4	547.7
157.5°	574.4	580.0	581.6	581.6	581.6	580.0	574.4	567.4	558.6	547.0	534.6
160°	559.7	565.2	566.1	566.1	566.1	565.2	559.7	554.1	546.8	536.6	526.6
162.5°	545.7	551.2	552.2	551.4	552.2	551.2	545.7	541.6	535.0	527.1	518.4
165°	527.4	531.2	530.2	529.3	530.2	531.2	527.4	523.8	519.2	512.7	507.2
167.5°	510.3	512.7	512.5	511.8	512.5	512.7	510.3	508.5	505.7	500.6	496.4
170°	500.7	501.7	500.7	500.7	500.7	501.7	500.7	498.9	496.1	492.5	489.7
172.5°	491.2	492.1	491.2	489.7	491.2	492.1	491.2	490.0	488.1	485.8	483.8
175°	478.6	480.5	478.6	476.8	478.6	480.5	478.6	478.6	478.6	476.8	475.9
177.5°	471.5	472.2	470.7	469.3	470.7	472.2	471.5	472.2	471.5	471.5	470.7
180°	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6



TEST NUMBER: P332528-927

CATALOG NUMBER: S124DIP-S350D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6
2.5°	432.6	433.2	435.6	437.9	440.6	442.5	443.9	445.4	448.5	451.1	453.5
5°	405.4	406.3	411.1	414.5	420.3	425.4	429.4	433.6	438.7	445.7	452.0
7.5°	381.3	384.8	390.1	395.6	401.5	408.1	413.9	420.4	429.1	438.7	448.5
10°	367.7	371.6	377.2	383.6	389.2	396.9	404.0	411.7	421.7	433.2	444.9
12.5°	354.0	360.5	364.8	372.3	378.4	384.8	392.4	402.4	414.0	426.2	440.2
15°	336.9	340.5	348.7	352.8	361.5	371.2	378.7	388.8	400.1	416.2	432.0
17.5°	317.2	321.9	328.4	336.3	346.2	353.8	363.1	373.6	387.8	403.8	423.5
20°	304.3	308.2	316.3	324.9	335.4	343.5	353.4	363.5	378.2	395.2	415.8
22.5°	292.7	296.5	305.1	313.1	323.3	333.1	343.5	355.3	369.3	387.3	408.4
25°	274.9	279.9	287.4	295.6	305.4	316.6	327.9	338.4	353.4	372.3	394.8
27.5°	259.0	263.0	268.5	277.8	288.9	299.8	310.9	324.2	338.6	358.6	381.9
30°	248.8	252.5	258.0	266.6	276.9	288.5	300.2	312.9	327.9	347.8	371.6
32.5°	240.7	243.5	248.3	256.1	265.5	277.7	289.2	302.4	318.1	337.7	360.9
35°	228.7	231.2	233.1	240.3	248.8	260.1	271.6	285.7	301.0	319.5	342.7
37.5°	217.0	217.9	220.5	225.4	233.5	243.9	254.7	268.5	284.1	302.9	323.9
40°	209.8	210.2	211.8	216.3	223.5	233.2	243.8	257.4	272.2	290.0	310.9
42.5°	202.7	202.5	204.1	207.2	213.9	222.8	233.1	245.6	260.4	276.9	296.4
45°	191.6	191.6	191.2	193.8	199.3	207.9	216.6	228.5	240.9	257.1	273.5
47.5°	180.0	179.0	179.3	180.6	185.2	192.3	201.0	210.8	221.7	235.4	249.9
50°	172.5	171.0	170.4	171.9	176.0	182.2	190.5	199.1	209.5	221.4	233.8
52.5°	164.2	162.7	161.7	162.8	166.6	172.3	179.8	187.4	196.7	206.4	217.1
55°	151.5	149.8	149.2	149.6	152.4	156.9	163.3	170.2	177.2	185.2	192.7
57.5°	138.9	136.2	135.6	135.5	137.4	141.5	146.9	152.8	157.9	162.8	170.8
60°	130.7	127.3	126.2	126.0	127.5	130.9	135.7	141.7	145.3	148.7	155.6
62.5°	121.8	118.6	116.1	116.4	117.7	121.0	125.2	129.6	132.0	135.6	140.3
65°	108.2	104.1	102.2	101.6	102.3	105.0	108.4	111.1	113.8	115.3	119.8
67.5°	94.5	91.1	88.3	87.6	87.3	89.1	91.9	93.6	95.5	96.7	99.4
70°	84.9	81.9	78.6	77.4	77.2	78.7	81.4	81.6	84.2	84.8	87.5
72.5°	75.5	71.7	69.4	68.3	67.5	68.8	70.6	71.1	72.5	73.5	74.9
75°	60.8	57.9	55.7	54.0	53.5	54.2	54.2	55.1	56.1	56.6	58.3
77.5°	47.8	44.6	41.9	41.0	40.2	39.8	40.2	40.8	40.3	41.3	41.7
80°	38.8	35.4	33.4	33.0	31.8	31.0	30.7	31.3	30.6	31.0	32.1
82.5°	29.9	27.8	25.6	25.2	23.8	23.3	23.1	22.7	22.7	22.7	22.9
85°	17.8	16.5	15.0	14.1	13.5	12.6	12.6	12.2	11.8	11.4	11.6
87.5°	10.3	10.2	9.1	8.2	8.0	6.3	6.3	5.6	5.3	4.6	4.1
90°	15.7	16.6	14.7	12.9	12.9	7.4	7.4	6.4	5.5	2.8	1.0
92.5°	243.2	292.0	255.6	185.9	114.5	67.7	48.6	35.2	23.9	15.3	10.5
95°	771.4	750.2	566.1	346.1	195.1	115.1	76.4	54.3	42.4	33.1	30.3
97.5°	969.2	790.2	529.8	311.2	186.5	124.8	92.4	73.4	62.4	54.5	54.5
100°	975.7	740.1	480.5	292.7	188.7	134.4	105.0	87.5	76.4	69.9	69.9
102.5°	920.5	677.5	447.3	287.6	196.1	146.9	118.9	102.2	91.9	86.2	84.7
105°	820.1	603.9	418.8	289.9	213.6	169.4	142.7	126.1	115.1	110.4	107.7
107.5°	739.2	562.6	413.7	303.6	234.0	193.5	167.2	151.3	139.6	134.9	133.1
110°	698.7	548.7	415.2	313.9	249.5	209.0	184.1	167.5	156.5	151.9	150.0



TEST NUMBER: P332528-927

CATALOG NUMBER: S124DIP-S350D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	675.8	542.0	419.5	325.0	264.2	225.1	200.3	183.7	173.4	168.1	166.3
115°	654.5	538.5	428.0	342.5	287.2	250.4	225.5	208.0	198.8	192.4	189.6
117.5°	644.9	537.6	437.0	360.3	309.5	274.5	248.7	232.3	222.2	216.5	213.9
120°	639.8	537.6	443.7	372.8	325.0	289.9	264.2	248.5	238.4	232.0	230.1
122.5°	633.9	536.9	450.4	384.6	339.7	304.7	279.6	262.5	253.2	246.7	244.9
125°	624.1	535.8	460.3	402.3	359.9	326.8	301.0	283.5	273.4	267.8	264.2
127.5°	611.0	533.7	468.2	417.6	378.7	346.7	320.7	302.5	290.9	284.2	281.3
130°	602.9	533.0	474.0	427.1	391.3	359.9	333.2	315.8	301.9	294.5	290.9
132.5°	595.6	532.3	479.2	436.7	401.6	370.3	345.0	326.1	313.0	303.4	300.5
135°	584.6	531.2	487.0	449.2	416.1	385.7	361.8	342.5	326.8	317.6	313.9
137.5°	575.0	530.9	491.5	458.0	427.1	398.8	376.0	355.8	341.0	330.8	327.3
140°	569.8	530.2	495.3	463.9	434.5	406.9	384.8	365.4	349.8	339.7	336.9
142.5°	565.4	530.2	498.2	468.3	441.1	414.2	392.8	374.3	359.3	350.0	347.2
145°	557.9	528.4	499.9	473.2	448.3	424.4	404.1	386.6	373.8	364.6	361.8
147.5°	551.0	525.1	500.7	477.4	455.7	433.2	414.9	400.4	387.1	379.1	378.1
150°	545.9	522.8	500.7	479.6	459.3	439.1	421.6	407.8	396.7	389.4	388.5
152.5°	540.0	519.2	499.3	481.1	462.3	444.3	428.3	415.9	405.6	398.2	398.0
155°	531.2	513.7	497.1	482.4	466.7	451.1	437.3	427.1	417.9	412.4	411.5
157.5°	522.1	507.9	494.7	482.4	469.8	456.6	445.7	436.9	429.7	424.5	424.5
160°	515.5	503.5	492.5	482.4	471.3	460.3	450.1	442.8	436.3	432.6	432.6
162.5°	509.6	499.1	490.3	482.4	472.8	462.5	454.6	447.9	442.2	439.3	440.0
165°	499.9	492.5	486.0	480.5	473.2	464.9	459.3	454.7	450.1	448.3	448.3
167.5°	491.0	485.8	481.6	478.3	472.9	466.9	462.6	460.1	456.6	455.7	456.6
170°	485.1	481.4	478.6	476.8	472.2	467.6	464.9	463.0	460.3	459.3	460.3
172.5°	480.0	477.0	475.7	475.4	471.5	468.3	466.4	465.2	463.2	463.0	463.9
175°	474.0	472.2	472.2	473.2	470.4	468.6	468.6	467.6	466.7	466.7	467.6
177.5°	470.0	469.3	469.3	470.7	469.3	468.6	468.6	468.6	467.8	468.6	469.3
180°	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6



TEST NUMBER: P332528-927

CATALOG NUMBER: S124DIP-S350D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6
2.5°	455.6	457.1	459.1	462.3	463.5	465.0	467.1	467.0	467.5	469.8	474.6
5°	457.2	463.1	468.7	475.5	482.6	487.3	493.6	497.6	501.5	506.6	515.2
7.5°	458.0	467.1	477.4	489.3	499.9	512.0	521.5	530.4	538.5	549.1	559.4
10°	456.9	469.3	482.6	497.6	513.5	527.0	539.2	553.1	564.9	577.8	589.5
12.5°	455.0	469.8	487.7	504.5	523.1	543.0	558.3	572.3	588.0	602.9	620.8
15°	450.5	471.0	491.8	513.9	538.8	561.9	583.8	602.0	618.9	641.2	664.6
17.5°	444.9	466.9	493.2	520.0	546.1	572.4	599.5	626.9	648.2	675.9	694.2
20°	439.7	465.2	492.2	524.0	550.1	582.9	609.9	636.3	665.6	693.2	715.1
22.5°	432.3	460.2	488.9	520.5	554.8	587.7	618.9	647.5	676.8	706.8	733.3
25°	422.9	448.3	482.2	518.2	552.3	588.0	623.8	659.7	691.3	722.9	747.7
27.5°	407.1	439.0	470.6	507.8	545.7	586.0	624.3	661.9	695.0	721.0	736.3
30°	398.9	426.7	461.1	498.4	539.4	582.7	622.7	659.6	690.3	711.1	717.3
32.5°	387.0	415.6	449.2	487.8	531.3	575.8	617.3	652.2	677.9	688.8	681.4
35°	369.2	395.1	429.0	468.5	513.7	561.1	602.2	631.6	644.8	634.5	608.8
37.5°	347.8	373.4	407.5	446.4	493.1	541.4	578.5	599.7	595.3	569.7	531.4
40°	332.8	356.8	389.2	431.2	476.7	525.1	557.8	569.2	557.2	520.5	479.7
42.5°	316.2	339.5	372.1	412.6	460.9	505.5	533.9	534.9	514.8	470.8	430.0
45°	290.8	313.1	343.8	386.0	430.6	472.6	491.4	482.2	445.0	402.7	361.6
47.5°	265.8	285.1	315.4	355.5	397.8	433.2	442.5	426.0	386.4	345.2	307.2
50°	247.5	267.0	295.5	333.7	374.6	405.1	409.6	387.7	348.9	307.4	277.7
52.5°	229.9	249.3	276.7	312.1	349.5	377.1	377.2	351.9	313.2	276.3	248.6
55°	204.1	221.6	246.4	278.1	311.4	333.0	327.7	301.5	267.9	235.8	211.7
57.5°	179.4	194.6	217.3	243.8	273.1	291.0	282.3	257.0	227.0	199.8	181.5
60°	163.3	177.8	197.3	222.2	246.9	260.8	252.5	229.7	202.1	180.1	164.2
62.5°	147.7	159.9	178.6	200.3	223.2	233.5	226.2	203.6	179.7	159.9	146.9
65°	125.6	135.5	150.5	169.1	185.8	194.6	188.5	167.4	149.2	135.0	124.7
67.5°	105.0	112.7	124.1	139.0	153.2	158.0	152.3	137.7	122.3	110.9	103.6
70°	90.7	98.1	107.6	119.1	131.4	136.5	130.9	119.2	106.7	96.2	89.0
72.5°	78.3	84.0	92.1	101.8	111.5	116.5	112.7	101.6	90.9	83.1	77.1
75°	59.7	64.5	70.1	77.1	84.5	87.9	84.5	76.8	69.6	63.8	59.4
77.5°	43.3	45.9	50.3	55.5	60.2	62.7	59.8	54.7	50.1	46.2	44.0
80°	33.0	34.9	37.9	42.0	45.2	47.6	45.7	41.4	37.9	35.3	34.3
82.5°	24.0	25.3	27.3	30.3	32.4	33.7	32.9	29.7	28.3	26.0	25.0
85°	11.8	12.6	13.9	14.8	16.7	16.9	17.0	15.8	14.4	13.9	13.2
87.5°	4.6	5.3	5.9	6.6	7.2	8.4	8.2	8.6	8.4	8.1	7.7
90°	2.8	5.5	6.4	7.4	7.4	12.9	12.9	14.7	16.6	15.7	16.6
92.5°	15.3	23.9	35.2	48.6	67.7	114.5	185.9	255.6	292.0	243.2	180.8
95°	33.1	42.4	54.3	76.4	115.1	195.1	346.1	566.1	750.2	771.4	682.1
97.5°	54.5	62.4	73.4	92.4	124.8	186.5	311.2	529.8	790.2	969.2	1007.8
100°	69.9	76.4	87.5	105.0	134.4	188.7	292.7	480.5	740.1	975.7	1110.2
102.5°	86.2	91.9	102.2	118.9	146.9	196.1	287.6	447.3	677.5	920.5	1105.0
105°	110.4	115.1	126.1	142.7	169.4	213.6	289.9	418.8	603.9	820.1	1030.9
107.5°	134.9	139.6	151.3	167.2	193.5	234.0	303.6	413.7	562.6	739.2	925.8
110°	151.9	156.5	167.5	184.1	209.0	249.5	313.9	415.2	548.7	698.7	862.5



TEST NUMBER: P332528-927

CATALOG NUMBER: S124DIP-S350D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	168.1	173.4	183.7	200.3	225.1	264.2	325.0	419.5	542.0	675.8	816.1
115°	192.4	198.8	208.0	225.5	250.4	287.2	342.5	428.0	538.5	654.5	769.5
117.5°	216.5	222.2	232.3	248.7	274.5	309.5	360.3	437.0	537.6	644.9	746.7
120°	232.0	238.4	248.5	264.2	289.9	325.0	372.8	443.7	537.6	639.8	736.4
122.5°	246.7	253.2	262.5	279.6	304.7	339.7	384.6	450.4	536.9	633.9	727.5
125°	267.8	273.4	283.5	301.0	326.8	359.9	402.3	460.3	535.8	624.1	712.5
127.5°	284.2	290.9	302.5	320.7	346.7	378.7	417.6	468.2	533.7	611.0	694.0
130°	294.5	301.9	315.8	333.2	359.9	391.3	427.1	474.0	533.0	602.9	679.4
132.5°	303.4	313.0	326.1	345.0	370.3	401.6	436.7	479.2	532.3	595.6	663.8
135°	317.6	326.8	342.5	361.8	385.7	416.1	449.2	487.0	531.2	584.6	642.5
137.5°	330.8	341.0	355.8	376.0	398.8	427.1	458.0	491.5	530.9	575.0	623.2
140°	339.7	349.8	365.4	384.8	406.9	434.5	463.9	495.3	530.2	569.8	612.1
142.5°	350.0	359.3	374.3	392.8	414.2	441.1	468.3	498.2	530.2	565.4	601.8
145°	364.6	373.8	386.6	404.1	424.4	448.3	473.2	499.9	528.4	557.9	587.3
147.5°	379.1	387.1	400.4	414.9	433.2	455.7	477.4	500.7	525.1	551.0	575.4
150°	389.4	396.7	407.8	421.6	439.1	459.3	479.6	500.7	522.8	545.9	568.0
152.5°	398.2	405.6	415.9	428.3	444.3	462.3	481.1	499.3	519.2	540.0	559.8
155°	412.4	417.9	427.1	437.3	451.1	466.7	482.4	497.1	513.7	531.2	547.7
157.5°	424.5	429.7	436.9	445.7	456.6	469.8	482.4	494.7	507.9	522.1	534.6
160°	432.6	436.3	442.8	450.1	460.3	471.3	482.4	492.5	503.5	515.5	526.6
162.5°	439.3	442.2	447.9	454.6	462.5	472.8	482.4	490.3	499.1	509.6	518.4
165°	448.3	450.1	454.7	459.3	464.9	473.2	480.5	486.0	492.5	499.9	507.2
167.5°	455.7	456.6	460.1	462.6	466.9	472.9	478.3	481.6	485.8	491.0	496.4
170°	459.3	460.3	463.0	464.9	467.6	472.2	476.8	478.6	481.4	485.1	489.7
172.5°	463.0	463.2	465.2	466.4	468.3	471.5	475.4	475.7	477.0	480.0	483.8
175°	466.7	466.7	467.6	468.6	468.6	470.4	473.2	472.2	472.2	474.0	475.9
177.5°	468.6	467.8	468.6	468.6	468.6	469.3	470.7	469.3	469.3	470.0	470.7
180°	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6



TEST NUMBER: P332528-927

CATALOG NUMBER: S124DIP-S350D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	452.6	452.6	452.6	452.6	452.6	452.6	452.6
2.5°	477.1	477.4	478.7	479.7	480.1	481.6	481.6
5°	519.0	522.1	528.3	528.9	529.8	534.7	530.9
7.5°	568.1	576.2	581.5	586.4	588.0	590.2	589.8
10°	599.6	611.6	617.6	627.2	627.5	629.9	628.4
12.5°	631.2	645.2	656.1	657.9	665.9	667.2	669.2
15°	676.0	690.9	706.1	711.5	722.5	725.2	729.3
17.5°	718.2	733.3	744.0	758.0	762.6	768.7	764.5
20°	741.3	757.8	771.3	782.4	787.0	790.4	790.0
22.5°	755.3	771.9	782.8	791.2	795.6	797.0	796.9
25°	764.0	773.6	777.0	780.1	775.2	773.6	774.3
27.5°	739.7	737.2	728.4	716.8	704.9	695.4	690.1
30°	706.2	691.7	678.3	655.1	643.1	636.0	629.5
32.5°	658.9	635.6	610.1	588.7	575.1	564.6	563.0
35°	577.7	542.8	511.4	485.4	471.9	460.5	457.8
37.5°	491.1	454.9	426.7	403.7	389.2	381.1	373.6
40°	433.6	402.5	374.8	355.3	344.2	338.4	333.7
42.5°	389.4	361.0	333.4	318.5	308.6	305.0	302.2
45°	328.3	301.8	282.7	271.5	265.7	259.7	256.8
47.5°	279.3	257.9	245.3	235.7	229.4	225.9	224.1
50°	251.6	234.0	222.8	215.4	209.8	207.0	205.5
52.5°	227.0	212.5	203.1	197.3	193.5	191.4	190.8
55°	195.5	184.5	178.5	173.4	170.6	168.7	168.0
57.5°	170.0	161.4	156.6	152.4	151.3	149.8	149.2
60°	153.2	146.6	142.5	139.7	138.7	136.9	137.2
62.5°	138.3	132.9	129.4	127.9	126.6	125.0	125.6
65°	117.0	113.0	111.1	109.7	108.2	107.3	108.0
67.5°	98.2	95.5	92.9	92.1	91.3	91.2	90.4
70°	85.9	83.7	81.4	80.8	80.8	80.1	79.9
72.5°	74.0	72.4	70.9	70.4	69.9	70.2	69.4
75°	57.2	55.8	55.3	54.7	54.6	54.6	54.0
77.5°	42.2	41.3	40.4	40.4	39.7	39.5	39.4
80°	32.1	31.7	31.0	31.0	30.6	30.7	30.3
82.5°	24.1	23.6	23.4	23.1	22.6	22.7	22.3
85°	12.9	12.4	12.2	11.6	11.2	11.6	11.2
87.5°	8.0	8.0	7.8	7.8	7.8	7.6	7.1
90°	17.5	18.4	18.4	19.3	20.3	19.3	19.3
92.5°	136.0	108.3	89.8	79.0	74.0	70.9	70.9
95°	539.4	416.1	326.8	281.7	253.2	236.5	224.6
97.5°	954.7	864.7	768.7	702.5	647.1	619.5	600.4
100°	1128.5	1083.5	1015.3	935.3	879.1	851.5	844.1
102.5°	1196.3	1209.3	1181.0	1131.9	1091.2	1062.1	1056.2
105°	1190.3	1281.4	1319.1	1321.0	1313.6	1300.7	1295.1
107.5°	1095.4	1223.8	1305.8	1351.3	1372.3	1381.5	1383.9
110°	1021.8	1155.2	1256.5	1321.8	1360.5	1377.1	1385.4



TEST NUMBER: P332528-927

CATALOG NUMBER: S124DIP-S350D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	957.0	1083.1	1184.3	1258.5	1305.3	1328.5	1342.0
115°	882.8	990.5	1078.9	1151.6	1206.8	1236.3	1243.6
117.5°	840.4	925.1	1000.1	1062.1	1108.5	1138.3	1144.0
120°	822.0	895.6	961.0	1013.5	1054.0	1077.9	1088.1
122.5°	810.2	877.3	934.5	978.9	1013.5	1033.7	1043.9
125°	791.6	855.2	905.8	942.6	969.3	986.8	992.3
127.5°	769.8	833.1	881.1	918.1	941.9	956.6	962.1
130°	752.1	814.7	863.5	901.2	924.2	938.9	944.4
132.5°	732.2	793.3	842.1	879.1	905.1	919.0	924.6
135°	702.3	758.5	804.5	841.4	867.1	881.9	887.4
137.5°	673.8	721.1	762.7	797.2	822.6	834.7	841.4
140°	655.4	696.8	735.5	767.7	788.0	800.8	808.2
142.5°	639.9	675.5	709.0	737.5	756.3	767.7	772.9
145°	618.6	646.2	672.0	695.0	710.7	719.9	724.5
147.5°	600.2	622.3	642.5	659.5	672.9	679.9	681.5
150°	589.1	607.5	624.1	638.8	650.8	656.3	657.3
152.5°	578.1	595.0	608.6	621.2	630.9	634.2	635.2
155°	562.4	576.2	587.3	596.5	603.9	606.7	606.7
157.5°	547.0	558.6	567.4	574.4	580.0	581.6	581.6
160°	536.6	546.8	554.1	559.7	565.2	566.1	566.1
162.5°	527.1	535.0	541.6	545.7	551.2	552.2	551.4
165°	512.7	519.2	523.8	527.4	531.2	530.2	529.3
167.5°	500.6	505.7	508.5	510.3	512.7	512.5	511.8
170°	492.5	496.1	498.9	500.7	501.7	500.7	500.7
172.5°	485.8	488.1	490.0	491.2	492.1	491.2	489.7
175°	476.8	478.6	478.6	478.6	480.5	478.6	476.8
177.5°	471.5	471.5	472.2	471.5	472.2	470.7	469.3
180°	468.6	468.6	468.6	468.6	468.6	468.6	468.6

(END OF REPORT)