

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332964-927

Luminaire Tested: **S124RDIP-S1020D590U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332964-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIP-S1020D590U927-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 590 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5175.5 lumens  
Efficiency: N/A  
Efficacy: 106.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 48.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332964-927

CATALOG NUMBER: S124RDIP-S1020D590U927-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332964-927

CATALOG NUMBER: S124RDIP-S1020D590U927-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	110	110	110	110	104	104	104	104	91	91	91	79	79	79	69	69	69	64					64			
1	101	97	93	90	95	91	88	85	80	78	76	71	69	67	61	60	59	55					55			
2	92	85	79	74	87	80	75	70	71	67	63	62	59	57	54	52	50	46					46			
3	85	75	68	62	79	71	64	59	63	58	54	55	51	48	49	46	43	40					40			
4	78	67	59	53	73	63	56	50	56	50	46	50	45	42	44	40	37	34					34			
5	71	60	52	45	67	56	49	44	50	44	40	45	40	36	39	36	33	30					30			
6	66	54	46	40	62	51	44	38	46	40	35	41	36	32	36	32	29	26					26			
7	61	49	41	35	57	46	39	34	41	35	31	37	32	28	33	29	26	23					23			
8	57	44	37	31	53	42	35	30	38	32	28	34	29	26	30	26	23	21					21			
9	53	41	33	28	50	39	32	27	35	29	25	31	27	23	28	24	21	19					19			
10	50	37	30	25	47	36	29	24	32	27	23	29	24	21	26	22	19	17					17			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11548	11548	11548
5°	11574	11432	11503
10°	11501	11294	11294
15°	11369	11058	10975
20°	11188	10746	10548
25°	10956	10381	10117
30°	10730	9996	9577
35°	10481	9596	9034
40°	10181	9141	8450
45°	9903	8691	7854
50°	9588	8171	7222
55°	9250	7631	6536
60°	8879	7038	5837
65°	8537	6298	5146
70°	8039	5481	4369
75°	7414	4545	3553
80°	6467	3464	3259
85°	5483	3149	2946



TEST NUMBER: P332964-927

CATALOG NUMBER: S124RDIP-S1020D590U927-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	134.4	2.6
10°-20°	374.7	7.2
20°-30°	541.1	10.5
30°-40°	613.3	11.9
40°-50°	592.3	11.4
50°-60°	492.5	9.5
60°-70°	340.1	6.6
70°-80°	172.4	3.3
80°-90°	46.0	0.9
90°-100°	20.7	0.4
100°-110°	131.7	2.5
110°-120°	252.0	4.9
120°-130°	319.9	6.2
130°-140°	342.3	6.6
140°-150°	320.1	6.2
150°-160°	258.1	5.0
160°-170°	166.5	3.2
170°-180°	57.4	1.1
0°-30°	1050.1	20.3
0°-40°	1663.5	32.1
0°-60°	2748.2	53.1
0°-90°	3306.6	63.9
90°-120°	404.5	7.8
90°-150°	1386.8	26.8
90°-180°	1869.0	36.1
0°-180°	5175.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1430	1430	1430	1430	1430	
5°	1428	1423	1411	1421	1420	135
15°	1360	1349	1323	1321	1313	383
25°	1230	1209	1165	1147	1136	566
35°	1064	1027	974	937	917	664
45°	867	826	761	709	688	669
55°	657	612	542	487	464	588
65°	447	398	330	284	269	441
75°	238	197	146	122	114	251
85°	59	38	34	32	32	67
90°	1	6	10	13	14	4
95°	25	10	10	13	13	32
105°	136	139	141	144	129	142
115°	254	255	255	256	256	250
125°	357	359	358	359	360	319
135°	443	442	444	445	446	341
145°	511	512	512	512	513	319
155°	560	560	559	561	559	258
165°	591	588	588	592	588	167
175°	604	602	602	605	601	58
180°	604	604	604	604	604	



TEST NUMBER: P332964-927

CATALOG NUMBER: S124RDIP-S1020D590U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4
2.5°	1433.9	1433.1	1432.3	1431.6	1430.8	1429.3	1427.2	1425.1	1422.9	1420.8	1422.9
5°	1428.2	1427.3	1426.3	1425.3	1424.3	1422.4	1419.5	1416.6	1413.6	1410.7	1413.2
7.5°	1415.3	1414.3	1413.3	1412.2	1411.2	1408.8	1405.0	1401.2	1397.4	1393.6	1395.2
10°	1403.0	1401.8	1400.6	1399.4	1398.2	1395.3	1391.0	1386.6	1382.2	1377.8	1378.8
12.5°	1387.3	1385.8	1384.4	1383.1	1381.6	1378.3	1373.2	1368.0	1362.9	1357.7	1358.3
15°	1360.3	1358.1	1356.0	1353.8	1351.5	1347.4	1341.3	1335.2	1329.2	1323.1	1322.6
17.5°	1327.7	1324.5	1321.4	1318.2	1315.0	1309.8	1302.5	1295.2	1287.9	1280.6	1279.2
20°	1302.3	1299.1	1295.9	1292.8	1289.6	1283.9	1275.7	1267.3	1259.1	1250.8	1248.9
22.5°	1274.2	1270.7	1267.1	1263.6	1260.0	1253.8	1245.0	1236.1	1227.2	1218.4	1215.4
25°	1230.0	1225.6	1221.2	1216.9	1212.4	1205.3	1195.3	1185.3	1175.4	1165.4	1161.3
27.5°	1183.5	1178.1	1172.6	1167.0	1161.6	1153.5	1142.8	1132.2	1121.5	1110.8	1105.7
30°	1151.1	1145.0	1139.0	1132.9	1126.8	1118.0	1106.6	1095.1	1083.7	1072.3	1066.2
32.5°	1117.0	1110.1	1103.2	1096.4	1089.5	1080.1	1068.3	1056.5	1044.7	1032.8	1025.8
35°	1063.5	1055.7	1047.9	1040.1	1032.4	1022.4	1010.2	998.1	985.9	973.7	965.4
37.5°	1006.3	998.3	990.3	982.2	974.2	963.5	950.0	936.5	923.0	909.5	900.2
40°	966.1	958.0	950.0	941.9	933.9	923.0	909.1	895.2	881.3	867.4	857.2
42.5°	927.5	919.1	910.6	902.2	893.8	882.3	867.9	853.4	839.0	824.5	814.1
45°	867.4	858.5	849.5	840.4	831.4	819.6	805.0	790.4	775.8	761.2	749.3
47.5°	805.5	796.1	786.9	777.6	768.3	756.1	740.8	725.6	710.4	695.3	682.9
50°	763.4	753.9	744.4	734.9	725.4	712.9	697.4	681.8	666.1	650.6	638.4
52.5°	720.5	711.1	701.9	692.6	683.3	670.7	654.7	638.7	622.7	606.8	594.5
55°	657.2	647.5	637.7	628.0	618.2	605.5	589.6	573.8	558.0	542.2	529.5
57.5°	594.5	584.4	574.3	564.1	554.1	541.1	525.6	510.0	494.4	478.9	466.0
60°	549.9	540.1	530.4	520.6	510.9	498.2	482.7	467.1	451.5	435.9	423.3
62.5°	509.5	499.4	489.3	479.1	469.1	456.0	440.0	424.1	408.1	392.1	380.4
65°	446.9	436.4	426.0	415.5	405.0	392.0	376.4	360.8	345.2	329.7	319.2
67.5°	381.8	371.8	361.8	351.7	341.7	329.5	315.0	300.6	286.1	271.6	262.6
70°	340.6	330.4	320.2	310.0	299.8	287.7	273.9	259.9	246.1	232.2	224.2
72.5°	296.8	287.6	278.3	269.1	259.8	248.7	235.6	222.4	209.4	196.3	189.4
75°	237.7	228.7	219.7	210.6	201.7	191.4	180.0	168.6	157.1	145.7	140.1
77.5°	177.7	170.0	162.4	154.7	147.1	138.6	129.4	120.2	110.9	101.6	98.4
80°	139.1	132.1	125.0	118.0	110.9	103.7	96.4	89.1	81.8	74.5	73.8
82.5°	105.8	99.3	92.8	86.3	79.9	74.5	70.4	66.2	62.0	57.8	57.3
85°	59.2	54.3	49.4	44.5	39.7	36.8	36.1	35.4	34.7	34.0	33.4
87.5°	20.4	19.1	17.7	16.4	15.1	14.4	14.3	14.3	14.3	14.3	14.2
90°	1.3	2.5	3.6	4.7	5.8	6.7	7.5	8.3	9.1	9.9	10.5
92.5°	5.7	5.8	5.8	5.9	5.9	6.3	7.2	8.0	8.8	9.6	10.2
95°	24.9	21.5	18.1	14.6	11.2	9.5	9.7	9.7	9.8	9.9	10.5
97.5°	52.8	54.9	57.0	59.2	61.3	56.7	45.6	34.4	23.1	12.0	12.0
100°	74.1	75.9	77.7	79.5	81.4	75.3	61.5	47.6	33.7	19.9	18.1
102.5°	98.0	99.3	100.6	102.0	103.3	103.1	101.2	99.4	97.6	95.8	77.4
105°	136.0	136.7	137.2	137.8	138.4	138.9	139.5	140.0	140.5	141.0	141.9
107.5°	171.3	171.7	172.0	172.2	172.5	173.0	173.7	174.4	175.1	175.8	176.3
110°	195.2	195.5	195.8	196.1	196.4	196.9	197.5	198.0	198.7	199.3	199.5



TEST NUMBER: P332964-927

CATALOG NUMBER: S124RDIP-S1020D590U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	218.3	218.9	219.4	220.0	220.5	220.9	221.2	221.5	221.8	222.0	222.0
115°	254.0	254.3	254.5	254.8	255.2	255.2	255.2	255.1	254.9	254.8	255.1
117.5°	286.1	286.5	286.8	287.2	287.6	288.0	288.2	288.4	288.6	288.8	288.8
120°	307.8	308.2	308.6	309.0	309.3	309.5	309.4	309.3	309.2	309.1	309.3
122.5°	328.0	328.2	328.4	328.7	328.9	329.2	329.3	329.4	329.5	329.7	329.8
125°	357.0	357.4	357.8	358.2	358.6	358.7	358.5	358.3	358.1	357.9	358.2
127.5°	384.4	384.5	384.7	384.8	384.8	385.2	385.6	386.0	386.5	387.0	386.9
130°	402.2	402.3	402.3	402.5	402.6	402.7	403.1	403.4	403.7	404.0	404.1
132.5°	418.4	418.6	418.8	419.0	419.1	419.5	419.9	420.2	420.6	421.0	421.0
135°	442.8	442.8	442.7	442.5	442.4	442.6	443.0	443.4	443.8	444.2	444.4
137.5°	464.5	464.5	464.5	464.5	464.6	464.9	465.2	465.7	466.2	466.6	466.8
140°	478.6	478.7	479.0	479.1	479.3	479.5	479.7	480.0	480.1	480.4	480.6
142.5°	491.2	491.5	491.9	492.3	492.7	492.9	493.0	493.1	493.2	493.4	493.6
145°	510.6	511.0	511.2	511.5	511.8	512.0	512.0	512.0	512.0	512.0	512.1
147.5°	526.1	526.6	527.2	527.8	528.3	528.5	528.5	528.4	528.2	528.1	528.2
150°	537.3	537.7	538.1	538.5	538.9	539.1	538.9	538.8	538.8	538.6	538.6
152.5°	546.7	547.0	547.3	547.6	548.0	548.0	547.9	547.7	547.5	547.3	547.5
155°	559.9	560.0	560.1	560.2	560.3	560.2	559.9	559.6	559.3	559.0	559.4
157.5°	571.0	570.9	570.8	570.8	570.8	570.5	570.2	569.9	569.5	569.2	569.7
160°	577.5	577.2	576.9	576.6	576.3	576.1	576.0	575.9	575.8	575.7	576.3
162.5°	583.3	582.9	582.5	582.2	581.8	581.5	581.4	581.3	581.2	581.1	581.7
165°	590.6	590.1	589.6	589.1	588.6	588.4	588.4	588.4	588.4	588.4	589.1
167.5°	596.4	595.9	595.3	594.8	594.3	594.0	594.0	593.9	593.8	593.7	594.7
170°	599.7	599.0	598.4	597.9	597.2	597.0	597.1	597.1	597.3	597.4	598.2
172.5°	601.8	601.2	600.6	600.0	599.4	599.1	599.3	599.4	599.4	599.5	600.4
175°	604.2	603.6	602.9	602.4	601.7	601.5	601.6	601.7	601.8	601.9	602.8
177.5°	605.2	604.7	604.1	603.6	603.0	602.8	602.9	603.1	603.2	603.4	604.1
180°	604.2	604.2	604.2	604.2	604.2	604.2	604.2	604.2	604.2	604.2	604.2



TEST NUMBER: P332964-927

CATALOG NUMBER: S124RDIP-S1020D590U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4
2.5°	1425.1	1427.2	1429.3	1430.4	1430.1	1430.0	1429.7	1429.6
5°	1415.6	1418.0	1420.5	1421.4	1420.9	1420.5	1420.0	1419.5
7.5°	1396.8	1398.3	1399.9	1400.3	1399.5	1398.7	1397.9	1397.1
10°	1379.8	1380.8	1381.7	1381.7	1380.8	1379.8	1378.8	1377.8
12.5°	1358.8	1359.5	1360.0	1359.6	1358.3	1356.9	1355.6	1354.2
15°	1322.2	1321.6	1321.1	1320.0	1318.3	1316.6	1314.9	1313.2
17.5°	1277.9	1276.5	1275.2	1273.2	1270.6	1268.0	1265.4	1262.8
20°	1246.9	1245.0	1243.0	1240.5	1237.3	1234.1	1231.0	1227.8
22.5°	1212.5	1209.6	1206.7	1204.0	1201.3	1198.8	1196.2	1193.7
25°	1157.1	1152.9	1148.8	1145.5	1143.1	1140.7	1138.2	1135.8
27.5°	1100.6	1095.5	1090.4	1086.1	1082.6	1079.0	1075.5	1072.1
30°	1060.1	1054.0	1047.9	1042.9	1039.0	1035.1	1031.3	1027.4
32.5°	1018.7	1011.7	1004.6	999.3	995.5	991.8	988.2	984.4
35°	957.1	948.9	940.6	934.3	929.9	925.5	921.1	916.7
37.5°	891.0	881.8	872.5	865.7	861.3	856.9	852.5	848.2
40°	847.0	836.8	826.6	819.3	814.9	810.5	806.1	801.8
42.5°	803.7	793.3	782.8	775.4	770.8	766.2	761.6	757.1
45°	737.4	725.4	713.5	705.4	701.0	696.6	692.2	687.9
47.5°	670.6	658.2	645.8	637.2	632.4	627.6	622.7	618.0
50°	626.2	614.1	601.9	593.5	588.9	584.2	579.6	575.0
52.5°	582.0	569.7	557.3	548.7	543.9	539.1	534.2	529.5
55°	516.8	504.2	491.5	482.9	478.2	473.6	469.1	464.4
57.5°	453.1	440.3	427.5	419.3	415.7	412.3	408.8	405.3
60°	410.6	397.9	385.3	377.0	373.1	369.2	365.4	361.5
62.5°	368.8	357.0	345.4	337.9	334.9	331.8	328.6	325.5
65°	308.7	298.3	287.8	281.1	278.2	275.3	272.4	269.4
67.5°	253.6	244.6	235.6	229.5	226.2	223.1	219.8	216.7
70°	216.1	208.1	200.1	194.8	192.4	190.0	187.5	185.1
72.5°	182.5	175.7	168.8	164.3	162.0	159.8	157.6	155.3
75°	134.5	128.9	123.3	119.8	118.3	116.8	115.3	113.9
77.5°	95.1	91.9	88.6	86.7	86.3	85.9	85.4	85.0
80°	73.0	72.3	71.5	71.1	70.8	70.6	70.3	70.1
82.5°	56.7	56.2	55.7	55.3	55.1	54.8	54.6	54.3
85°	33.0	32.5	32.0	31.8	31.8	31.8	31.8	31.8
87.5°	14.1	14.0	13.9	14.0	14.3	14.5	14.7	15.0
90°	11.2	11.7	12.4	12.8	13.0	13.2	13.4	13.5
92.5°	10.8	11.4	12.0	12.3	12.4	12.4	12.4	12.4
95°	11.2	11.7	12.4	12.7	12.8	12.9	13.0	13.1
97.5°	12.0	12.1	12.2	12.3	12.4	12.4	12.5	12.7
100°	16.5	14.7	13.1	12.3	12.4	12.4	12.5	12.7
102.5°	58.9	40.6	22.1	12.9	13.0	13.0	13.0	13.0
105°	142.8	143.7	144.6	143.2	139.7	136.0	132.4	128.8
107.5°	176.7	177.1	177.5	177.9	178.3	178.7	179.1	179.5
110°	199.7	199.9	200.1	200.3	200.7	200.9	201.2	201.5





TEST NUMBER: P332964-927

CATALOG NUMBER: S124RDIP-S1020D590U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	222.0	222.0	221.9	222.0	222.4	222.8	223.2	223.6
115°	255.2	255.5	255.6	255.8	255.8	255.8	255.8	255.8
117.5°	288.8	288.8	288.7	288.7	288.6	288.6	288.5	288.5
120°	309.5	309.7	309.9	309.9	309.7	309.5	309.3	309.1
122.5°	329.9	330.0	330.2	330.1	329.9	329.7	329.5	329.3
125°	358.5	358.8	359.1	359.3	359.4	359.5	359.6	359.7
127.5°	386.9	386.8	386.7	386.7	386.6	386.5	386.4	386.3
130°	404.2	404.3	404.4	404.4	404.4	404.4	404.4	404.4
132.5°	421.2	421.3	421.4	421.4	421.3	421.2	421.1	421.0
135°	444.6	444.8	445.0	445.2	445.4	445.6	445.8	446.0
137.5°	467.1	467.3	467.5	467.5	467.5	467.5	467.4	467.3
140°	480.9	481.3	481.6	481.7	481.9	482.0	482.0	482.1
142.5°	493.8	494.0	494.2	494.4	494.4	494.4	494.4	494.5
145°	512.1	512.3	512.4	512.5	512.7	512.9	513.2	513.3
147.5°	528.3	528.4	528.5	528.5	528.7	528.8	528.9	528.9
150°	538.6	538.6	538.6	538.7	538.8	538.9	539.0	539.1
152.5°	547.6	547.8	548.0	548.0	548.0	547.9	547.8	547.8
155°	559.8	560.2	560.5	560.6	560.3	560.0	559.8	559.4
157.5°	570.2	570.8	571.2	571.2	570.8	570.2	569.7	569.2
160°	576.9	577.5	578.1	578.1	577.5	576.9	576.3	575.7
162.5°	582.3	582.9	583.5	583.5	582.8	582.1	581.5	580.7
165°	589.9	590.7	591.6	591.5	590.6	589.7	588.8	587.9
167.5°	595.6	596.4	597.3	597.2	596.3	595.2	594.2	593.3
170°	599.0	599.8	600.6	600.5	599.5	598.5	597.5	596.5
172.5°	601.2	602.0	602.8	602.6	601.6	600.5	599.4	598.3
175°	603.7	604.6	605.5	605.4	604.2	602.9	601.7	600.6
177.5°	604.8	605.4	606.0	605.9	604.9	604.0	602.9	602.0
180°	604.2	604.2	604.2	604.2	604.2	604.2	604.2	604.2

(END OF REPORT)