

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332885-927

Luminaire Tested: **S124RDIP-S350D1035U927-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332885-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIP-S350D1035U927-4F0-1E-UDD-A4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 350 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4106.1 lumens  
Efficiency: N/A  
Efficacy: 110.1 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 37.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332885-927

CATALOG NUMBER: S124RDIP-S350D1035U927-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P332885-927

CATALOG NUMBER: S124RDIP-S350D1035U927-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	72	72	72	53	53	53	37	37	37	29
1	93	89	86	82	83	80	77	74	63	61	59	47	46	45	33	32	31	25
2	85	78	72	68	76	70	65	61	55	52	49	42	40	38	29	28	27	21
3	78	69	62	56	69	62	56	51	49	45	42	37	34	32	26	24	23	18
4	71	61	53	48	64	55	49	44	44	39	36	33	30	28	23	22	20	16
5	65	54	47	41	58	49	42	37	39	34	31	30	27	24	21	19	18	14
6	60	49	41	35	54	44	37	32	35	30	27	27	24	21	19	17	15	12
7	55	44	36	31	50	40	33	28	32	27	23	24	21	19	18	15	14	11
8	51	40	32	27	46	36	30	25	29	24	21	22	19	17	16	14	12	10
9	48	36	29	24	43	33	27	22	26	22	19	20	17	15	15	13	11	9
10	45	33	26	22	40	30	24	20	24	20	17	19	16	13	14	12	10	8

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	3756	3756	3756	3756
5°	4357	3767	3331	3767
10°	5155	3751	2972	3751
15°	5954	3717	2554	3717
20°	6630	3669	2310	3669
25°	6844	3622	2144	3622
30°	5991	3566	2045	3566
35°	4664	3481	1985	3481
40°	3497	3385	1952	3385
45°	2762	3230	1934	3230
50°	2331	3052	1879	3052
55°	2031	2856	1779	2856
60°	1828	2651	1574	2651
65°	1612	2432	1354	2432
70°	1452	2205	1220	2205
75°	1216	1953	1042	1953
80°	1027	1664	976	1664
85°	861	1306	861	1306



TEST NUMBER: P332885-927

CATALOG NUMBER: S124RDIP-S350D1035U927-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	45.1	1.1
10°-20°	136.0	3.3
20°-30°	212.7	5.2
30°-40°	236.5	5.8
40°-50°	209.8	5.1
50°-60°	163.5	4.0
60°-70°	107.0	2.6
70°-80°	52.6	1.3
80°-90°	15.2	0.4
90°-100°	290.8	7.1
100°-110°	605.1	14.7
110°-120°	542.0	13.2
120°-130°	455.9	11.1
130°-140°	380.1	9.3
140°-150°	290.4	7.1
150°-160°	204.1	5.0
160°-170°	120.1	2.9
170°-180°	39.1	1.0
0°-30°	393.8	9.6
0°-40°	630.3	15.4
0°-60°	1003.6	24.4
0°-90°	1178.5	28.7
90°-120°	1437.9	35.0
90°-150°	2564.4	62.5
90°-180°	2928.0	71.3
0°-180°	4106.1	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	465	465	465	465	465	
5°	538	465	411	465	538	54
15°	712	445	306	445	712	203
25°	768	407	241	407	768	341
35°	473	353	201	353	473	297
45°	242	283	169	283	242	192
55°	144	203	126	203	144	131
65°	84	127	71	127	84	85
75°	39	63	33	63	39	43
85°	9	14	9	14	9	11
90°	17	1	17	1	17	14
95°	193	26	193	26	193	299
105°	1113	92	1113	92	1113	1100
115°	1068	163	1068	163	1068	1061
125°	852	227	852	227	852	775
135°	762	270	762	270	762	588
145°	622	311	622	311	622	395
155°	521	354	521	354	521	243
165°	455	385	455	385	455	130
175°	410	402	410	402	410	40
180°	402	402	402	402	402	



TEST NUMBER: P332885-927

CATALOG NUMBER: S124RDIP-S350D1035U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3
2.5°	490.8	492.2	490.8	490.7	489.2	488.7	488.1	486.2	482.6	480.5	480.9
5°	537.7	542.4	539.8	539.4	535.3	531.2	528.5	522.5	516.1	511.8	508.3
7.5°	591.9	594.6	592.9	590.3	583.7	579.9	573.8	565.9	554.4	545.7	537.7
10°	628.8	631.1	630.3	625.4	620.6	610.6	605.0	594.0	579.5	568.1	557.4
12.5°	665.1	667.5	660.9	661.2	651.9	644.0	635.2	621.2	604.6	589.9	576.5
15°	712.4	709.4	709.4	705.7	695.4	684.5	675.3	660.7	639.7	622.1	603.5
17.5°	749.5	750.5	749.0	740.1	732.1	720.8	703.9	686.9	667.4	643.7	624.8
20°	771.7	771.7	770.0	764.0	753.5	741.5	723.3	704.7	680.0	656.2	634.9
22.5°	780.7	781.3	779.3	774.4	764.9	753.2	737.7	718.8	693.3	666.5	640.1
25°	768.3	771.9	772.2	771.0	768.1	761.0	747.7	728.4	705.5	676.4	647.9
27.5°	705.4	709.9	713.8	720.3	729.0	733.4	734.0	724.2	704.3	676.3	647.6
30°	642.7	646.4	658.6	674.5	686.9	698.2	708.0	710.6	699.3	674.2	644.0
32.5°	573.1	578.2	590.4	607.5	628.1	647.2	669.1	680.2	679.9	664.9	637.0
35°	473.2	477.0	488.2	506.2	530.9	559.3	594.0	620.9	639.3	638.0	620.9
37.5°	381.7	385.9	397.2	412.2	436.2	471.2	504.8	542.0	575.9	595.0	589.3
40°	331.8	332.0	343.1	358.5	381.0	411.5	448.1	489.3	527.2	558.2	564.1
42.5°	292.6	292.6	299.9	316.5	332.6	361.4	396.3	437.3	481.6	517.4	533.2
45°	241.9	243.5	249.5	259.4	272.2	296.6	324.6	362.6	412.3	454.6	481.1
47.5°	204.8	207.3	211.1	219.2	229.3	245.6	268.7	302.9	343.3	389.9	427.5
50°	185.6	186.0	190.8	195.4	204.1	217.1	237.3	265.9	303.0	347.8	389.6
52.5°	169.1	169.1	172.0	177.7	184.8	194.9	211.3	237.2	270.1	310.3	353.5
55°	144.3	145.3	147.6	152.0	157.5	164.6	177.5	197.0	222.9	257.2	296.4
57.5°	125.6	126.0	127.8	129.7	134.7	139.9	149.6	163.1	184.9	213.0	249.5
60°	113.2	113.4	114.0	116.8	120.7	125.6	132.2	143.6	162.0	187.7	216.6
62.5°	101.2	101.6	102.4	104.5	107.6	110.9	117.8	127.0	142.2	164.1	190.1
65°	84.4	84.5	85.9	86.6	89.0	92.1	97.1	103.3	113.8	132.2	151.9
67.5°	70.5	70.5	70.6	71.6	73.3	75.3	78.3	83.3	91.2	102.4	119.8
70°	61.5	61.5	61.9	62.4	63.4	65.0	66.8	70.5	76.3	85.5	98.8
72.5°	53.1	53.2	53.6	53.7	54.2	55.6	56.9	59.3	63.5	70.5	81.3
75°	39.0	39.5	40.5	41.3	42.2	42.0	43.3	44.8	46.1	50.2	56.4
77.5°	29.0	28.8	28.8	29.5	29.5	29.8	30.7	31.8	32.9	34.8	37.0
80°	22.1	22.1	22.7	22.9	22.7	22.9	23.8	24.4	24.7	25.5	27.6
82.5°	16.7	17.0	16.9	17.0	17.1	17.3	18.1	18.2	18.6	18.9	19.7
85°	9.3	9.6	9.7	9.3	9.3	9.3	9.7	9.9	10.3	10.1	10.5
87.5°	6.7	6.5	6.8	6.7	6.6	6.5	6.4	6.6	6.1	6.4	6.1
90°	16.6	16.6	17.4	16.6	15.8	15.8	15.1	14.3	13.5	14.3	12.7
92.5°	60.9	60.9	63.6	67.9	77.2	93.0	116.9	155.3	209.0	250.9	219.5
95°	193.0	203.3	217.5	242.0	280.7	357.4	463.4	586.0	662.7	644.5	486.4
97.5°	515.8	532.3	556.0	603.6	660.4	742.9	820.2	865.9	832.6	678.8	455.2
100°	725.2	731.5	755.3	803.5	872.3	930.8	969.6	953.8	838.3	635.8	412.8
102.5°	907.4	912.5	937.5	972.4	1014.6	1039.0	1027.8	949.4	790.8	582.1	384.4
105°	1112.7	1117.5	1128.5	1134.9	1133.3	1100.8	1022.5	885.7	704.6	518.8	359.8
107.5°	1189.0	1186.9	1179.0	1160.9	1121.9	1051.4	941.1	795.4	635.0	483.4	355.4
110°	1190.3	1183.1	1168.9	1135.7	1079.5	992.5	877.8	741.0	600.2	471.3	356.6



TEST NUMBER: P332885-927

CATALOG NUMBER: S124RDIP-S350D1035U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1152.9	1141.4	1121.4	1081.2	1017.5	930.5	822.1	701.2	580.7	465.6	360.4
115°	1068.4	1062.1	1036.8	989.4	926.9	851.0	758.4	661.2	562.3	462.6	367.7
117.5°	982.9	977.9	952.4	912.5	859.2	794.8	722.1	641.5	554.1	461.8	375.5
120°	934.8	926.1	905.5	870.7	825.6	769.5	706.2	632.6	549.6	461.8	381.2
122.5°	896.8	888.1	870.7	841.0	802.9	753.7	696.1	625.1	544.5	461.2	386.9
125°	852.5	847.8	832.7	809.8	778.2	734.7	680.1	612.1	536.2	460.3	395.5
127.5°	826.6	821.8	809.2	788.8	757.0	715.7	661.3	596.3	525.0	458.5	402.2
130°	811.4	806.7	794.0	774.2	741.8	699.9	646.1	583.7	518.0	457.9	407.3
132.5°	794.3	789.6	777.5	755.3	723.5	681.5	629.1	570.4	511.7	457.2	411.7
135°	762.4	757.6	745.0	722.9	691.2	651.6	603.4	552.0	502.2	456.3	418.4
137.5°	722.9	717.2	706.7	684.8	655.3	619.6	578.9	535.4	493.9	456.1	422.3
140°	694.3	688.0	677.0	659.6	631.8	598.7	563.1	525.9	489.6	455.5	425.5
142.5°	664.0	659.6	649.7	633.6	609.1	580.4	549.8	517.1	485.8	455.5	428.0
145°	622.4	618.5	610.5	597.1	577.3	555.2	531.5	504.5	479.3	453.9	429.4
147.5°	585.5	584.2	578.1	566.6	552.0	534.6	515.6	494.2	473.4	451.1	430.2
150°	564.7	563.9	559.1	548.8	536.2	522.0	506.1	488.0	469.0	449.2	430.2
152.5°	545.7	544.9	542.0	533.7	522.9	511.2	496.6	481.0	463.9	446.0	429.0
155°	521.2	521.2	518.8	512.5	504.5	495.0	483.2	470.6	456.3	441.3	427.1
157.5°	499.6	499.6	498.2	493.5	487.5	479.9	469.9	459.3	448.5	436.4	425.0
160°	486.4	486.4	485.6	480.9	476.1	469.8	461.1	452.3	442.9	432.6	423.1
162.5°	473.7	474.4	473.6	468.8	465.3	459.6	452.8	445.4	437.8	428.8	421.2
165°	454.7	455.5	456.3	453.1	450.0	446.0	440.5	435.8	429.4	423.1	417.6
167.5°	439.7	440.4	440.5	438.5	436.9	434.5	430.1	426.4	421.8	417.4	413.8
170°	430.2	430.2	431.0	430.2	428.6	426.3	423.1	420.7	416.8	413.6	411.2
172.5°	420.7	422.0	422.8	422.0	421.0	419.3	417.4	415.7	412.3	409.8	408.7
175°	409.6	411.2	412.8	411.2	411.2	411.2	409.6	408.8	407.3	405.7	405.7
177.5°	403.1	404.4	405.7	405.0	405.7	405.0	405.0	404.4	403.8	403.1	403.1
180°	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5



TEST NUMBER: P332885-927

CATALOG NUMBER: S124RDIP-S350D1035U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3
2.5°	479.4	477.4	476.3	473.9	471.0	469.5	468.2	466.2	463.7	461.0	459.1
5°	503.7	499.2	493.6	486.9	480.9	475.1	470.0	464.9	459.1	453.1	447.2
7.5°	528.7	519.9	510.3	499.2	488.5	478.7	469.7	461.1	451.4	442.6	434.7
10°	546.1	534.2	520.9	506.8	492.7	480.5	468.5	457.6	445.7	435.0	426.0
12.5°	560.2	546.1	530.1	512.6	495.7	480.9	467.1	453.0	439.3	427.8	415.7
15°	583.6	564.4	542.8	521.7	499.9	479.7	461.2	444.7	429.1	412.8	401.4
17.5°	599.8	576.8	550.6	525.4	499.5	475.8	454.4	434.7	416.8	400.1	386.5
20°	609.3	584.0	554.9	526.2	497.2	471.9	448.9	427.1	408.5	390.5	376.4
22.5°	614.7	586.7	554.9	524.9	494.8	467.4	442.1	419.5	399.3	381.2	365.7
25°	616.5	586.5	554.1	519.5	486.6	457.5	431.2	406.6	384.1	366.1	349.7
27.5°	614.0	578.7	545.5	510.1	476.0	445.4	417.9	392.1	369.6	350.2	333.3
30°	610.5	572.6	536.9	500.2	465.7	436.3	407.2	382.5	359.0	339.0	321.9
32.5°	602.6	565.1	526.7	489.1	454.2	423.8	396.2	371.4	348.4	327.9	309.7
35°	587.2	549.1	507.6	468.9	434.6	403.1	377.2	353.2	331.3	309.3	290.3
37.5°	566.8	528.0	486.6	444.3	409.9	380.2	356.5	333.9	312.5	292.5	271.3
40°	547.6	512.2	469.4	427.5	392.2	363.5	341.6	321.2	299.6	279.7	258.6
42.5°	524.4	494.2	451.0	408.8	374.1	346.4	326.0	306.0	286.4	267.1	245.0
45°	485.6	462.7	422.2	381.8	346.7	319.2	300.6	282.9	265.7	247.3	226.5
47.5°	441.1	425.6	390.7	349.2	316.8	292.2	274.0	259.6	245.0	226.6	208.4
50°	410.2	400.3	366.5	328.7	297.7	275.0	256.5	243.0	230.8	213.2	196.9
52.5°	377.2	371.9	343.4	307.2	277.3	255.1	239.2	227.1	214.8	200.1	184.9
55°	326.9	329.8	305.6	274.3	246.1	227.4	213.0	202.9	192.3	180.0	168.2
57.5°	275.6	285.9	269.7	242.2	215.8	198.4	187.6	179.1	170.2	160.0	149.9
60°	244.9	253.5	244.3	220.1	197.0	180.9	170.8	164.2	155.4	146.1	138.4
62.5°	214.8	224.1	218.6	199.1	177.7	163.8	154.9	148.8	142.2	134.0	126.0
65°	177.2	183.2	180.5	167.1	151.9	140.1	131.8	127.3	121.3	115.3	108.2
67.5°	135.7	147.3	145.8	138.6	125.5	116.2	110.8	106.9	101.4	97.0	92.1
70°	111.5	122.2	122.1	116.2	109.1	100.5	96.7	93.4	88.5	84.2	80.2
72.5°	91.3	101.1	102.6	98.1	93.2	86.7	83.1	80.8	76.0	73.1	69.9
75°	63.9	71.1	73.0	73.0	70.7	67.3	64.1	62.6	59.3	56.6	54.7
77.5°	41.9	46.4	49.4	50.0	50.4	49.2	46.6	45.6	42.9	42.1	40.2
80°	29.6	32.6	36.0	37.2	38.0	37.7	36.6	35.8	33.4	32.4	31.7
82.5°	20.4	22.1	24.9	27.4	27.1	28.1	27.1	26.5	24.6	24.3	23.6
85°	10.7	10.9	11.2	12.9	13.9	14.3	14.4	14.1	13.5	13.5	12.2
87.5°	5.8	5.6	5.0	5.0	5.0	5.5	5.4	5.2	5.1	5.1	4.8
90°	11.1	11.1	6.3	6.3	5.5	4.8	2.4	0.8	2.4	4.8	5.5
92.5°	159.8	98.4	58.2	41.7	30.2	20.6	13.2	9.0	13.2	20.6	30.2
95°	297.4	167.6	98.9	65.7	46.7	36.4	28.4	26.1	28.4	36.4	46.7
97.5°	267.3	160.3	107.3	79.4	63.1	53.6	46.8	46.8	46.8	53.6	63.1
100°	251.5	162.2	115.5	90.2	75.1	65.7	60.1	60.1	60.1	65.7	75.1
102.5°	247.1	168.4	126.2	102.2	87.8	78.9	74.0	72.7	74.0	78.9	87.8
105°	249.1	183.5	145.5	122.6	108.4	98.9	94.9	92.5	94.9	98.9	108.4
107.5°	260.8	201.1	166.2	143.6	130.0	119.9	116.0	114.4	116.0	119.9	130.0
110°	269.7	214.3	179.5	158.2	143.9	134.4	130.5	128.9	130.5	134.4	143.9





TEST NUMBER: P332885-927

CATALOG NUMBER: S124RDIP-S350D1035U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	279.2	227.0	193.5	172.1	157.9	149.0	144.4	142.8	144.4	149.0	157.9
115°	294.2	246.8	215.1	193.8	178.7	170.8	165.2	163.0	165.2	170.8	178.7
117.5°	309.5	265.9	235.8	213.7	199.6	190.9	186.0	183.8	186.0	190.9	199.6
120°	320.3	279.2	249.1	227.0	213.5	204.9	199.3	197.7	199.3	204.9	213.5
122.5°	330.4	291.8	261.7	240.3	225.5	217.5	211.9	210.4	211.9	217.5	225.5
125°	345.6	309.2	280.7	258.6	243.6	234.9	230.1	227.0	230.1	234.9	243.6
127.5°	358.7	325.3	297.9	275.5	259.8	249.9	244.2	241.7	244.2	249.9	259.8
130°	366.9	336.1	309.2	286.3	271.2	259.4	253.1	249.9	253.1	259.4	271.2
132.5°	375.2	345.0	318.1	296.4	280.1	268.9	260.6	258.1	260.6	268.9	280.1
135°	386.0	357.4	331.4	310.8	294.2	280.7	272.8	269.7	272.8	280.7	294.2
137.5°	393.6	366.9	342.6	323.0	305.7	292.9	284.2	281.2	284.2	292.9	305.7
140°	398.5	373.3	349.6	330.6	313.9	300.6	291.8	289.5	291.8	300.6	313.9
142.5°	402.3	379.0	355.8	337.5	321.5	308.7	300.7	298.3	300.7	308.7	321.5
145°	406.5	385.2	364.6	347.2	332.2	321.1	313.1	310.8	313.1	321.1	332.2
147.5°	410.1	391.5	372.2	356.5	344.0	332.6	325.7	324.9	325.7	332.6	344.0
150°	412.0	394.7	377.2	362.2	350.4	340.9	334.5	333.7	334.5	340.9	350.4
152.5°	413.3	397.2	381.7	367.9	357.3	348.5	342.1	342.0	342.1	348.5	357.3
155°	414.4	400.9	387.5	375.7	366.9	359.0	354.3	353.5	354.3	359.0	366.9
157.5°	414.4	403.6	392.3	382.9	375.3	369.2	364.7	364.7	364.7	369.2	375.3
160°	414.4	404.9	395.5	386.7	380.4	374.9	371.7	371.7	371.7	374.9	380.4
162.5°	414.4	406.2	397.4	390.5	384.8	379.9	377.4	378.0	377.4	379.9	384.8
165°	412.8	406.5	399.3	394.7	390.7	386.7	385.2	385.2	385.2	386.7	390.7
167.5°	410.9	406.3	401.1	397.5	395.3	392.3	391.5	392.3	391.5	392.3	395.3
170°	409.6	405.7	401.7	399.3	397.8	395.5	394.7	395.5	394.7	395.5	397.8
172.5°	408.4	405.0	402.3	400.6	399.7	397.9	397.8	398.5	397.8	397.9	399.7
175°	406.5	404.1	402.5	402.5	401.7	400.9	400.9	401.7	400.9	400.9	401.7
177.5°	404.4	403.1	402.5	402.5	402.5	401.9	402.5	403.1	402.5	401.9	402.5
180°	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5



TEST NUMBER: P332885-927

CATALOG NUMBER: S124RDIP-S350D1035U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3
2.5°	456.9	455.4	453.5	451.2	448.5	446.2	445.0	446.0	446.5	445.2	445.0
5°	443.0	438.3	434.6	429.0	424.5	420.7	418.1	416.9	417.3	414.3	413.6
7.5°	427.4	421.8	415.7	409.0	402.8	397.3	394.4	392.8	389.6	388.2	386.0
10°	417.3	409.9	403.9	395.9	388.8	382.3	379.1	376.4	373.3	371.8	368.6
12.5°	407.0	398.3	391.7	383.5	376.2	368.4	365.3	360.4	355.5	352.3	348.2
15°	392.4	381.9	373.8	364.1	355.5	346.5	338.4	329.4	326.1	318.9	314.8
17.5°	375.3	364.7	354.7	341.7	328.4	317.1	308.6	299.9	294.8	290.3	288.1
20°	364.1	354.3	340.5	325.3	310.5	298.1	291.1	285.5	279.9	276.7	274.5
22.5°	353.5	341.0	324.9	308.5	293.7	284.0	278.1	272.4	267.8	264.7	261.7
25°	335.6	319.2	302.2	283.4	273.4	264.9	258.6	253.8	251.0	247.1	245.6
27.5°	317.3	297.5	278.7	266.1	255.6	247.8	242.2	238.8	235.2	232.7	230.7
30°	303.2	283.1	266.3	254.2	243.5	237.2	232.7	228.5	225.7	223.6	222.2
32.5°	289.2	269.2	255.0	242.1	233.6	227.4	222.6	219.5	217.3	214.7	213.7
35°	269.0	251.2	238.8	227.2	218.6	213.0	209.2	206.0	204.1	203.4	202.9
37.5°	249.6	235.0	221.7	212.2	204.5	200.1	195.7	194.1	192.8	191.5	192.1
40°	237.3	223.6	211.8	201.8	195.5	190.7	188.1	186.2	185.1	185.1	185.1
42.5°	226.7	213.3	201.8	192.7	186.6	182.4	179.5	177.9	177.5	177.4	178.3
45°	210.2	197.8	186.2	178.6	173.4	169.3	167.6	166.3	166.3	167.1	167.2
47.5°	193.8	182.2	172.9	164.5	159.6	157.1	155.6	155.0	155.0	155.7	156.6
50°	183.7	172.3	163.1	155.6	151.1	148.7	147.3	146.9	147.3	147.3	148.7
52.5°	172.8	162.6	153.5	147.2	142.1	139.8	139.1	138.6	138.8	139.4	140.0
55°	156.8	147.6	138.9	132.9	129.2	127.7	126.0	126.2	125.8	126.2	126.2
57.5°	140.6	132.4	124.4	119.6	116.3	114.2	112.3	112.8	112.3	112.2	111.9
60°	130.3	121.3	114.9	110.6	106.9	105.0	103.3	103.7	103.1	102.7	102.0
62.5°	119.1	111.5	105.4	101.3	98.3	96.2	94.4	94.1	92.8	91.5	89.8
65°	102.7	96.6	91.1	87.2	84.4	82.7	81.4	80.2	77.4	74.5	73.0
67.5°	86.9	82.4	77.3	74.0	71.7	69.6	67.0	65.1	62.5	60.8	59.9
70°	76.7	72.4	68.0	64.9	62.4	60.4	57.6	56.2	54.3	53.6	52.7
72.5°	66.9	62.9	58.9	56.0	53.5	51.8	49.6	48.3	47.5	47.1	46.3
75°	52.1	49.0	45.9	43.3	41.3	40.1	39.2	38.3	37.9	36.2	35.3
77.5°	38.0	35.9	34.1	32.2	30.7	29.9	28.1	27.1	26.5	25.7	25.4
80°	29.6	28.1	26.2	25.1	23.1	22.3	21.5	21.4	21.2	21.0	20.8
82.5°	22.3	20.8	18.9	18.2	17.7	17.2	16.8	16.6	16.4	16.5	16.5
85°	11.2	10.5	10.5	10.3	10.1	9.9	9.7	9.7	9.6	9.7	9.6
87.5°	5.0	4.8	5.8	5.5	5.9	6.3	6.0	6.2	6.4	6.3	6.3
90°	6.3	6.3	11.1	11.1	12.7	14.3	13.5	14.3	15.1	15.8	15.8
92.5°	41.7	58.2	98.4	159.8	219.5	250.9	209.0	155.3	116.9	93.0	77.2
95°	65.7	98.9	167.6	297.4	486.4	644.5	662.7	586.0	463.4	357.4	280.7
97.5°	79.4	107.3	160.3	267.3	455.2	678.8	832.6	865.9	820.2	742.9	660.4
100°	90.2	115.5	162.2	251.5	412.8	635.8	838.3	953.8	969.6	930.8	872.3
102.5°	102.2	126.2	168.4	247.1	384.4	582.1	790.8	949.4	1027.8	1039.0	1014.6
105°	122.6	145.5	183.5	249.1	359.8	518.8	704.6	885.7	1022.5	1100.8	1133.3
107.5°	143.6	166.2	201.1	260.8	355.4	483.4	635.0	795.4	941.1	1051.4	1121.9
110°	158.2	179.5	214.3	269.7	356.6	471.3	600.2	741.0	877.8	992.5	1079.5



TEST NUMBER: P332885-927

CATALOG NUMBER: S124RDIP-S350D1035U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	172.1	193.5	227.0	279.2	360.4	465.6	580.7	701.2	822.1	930.5	1017.5
115°	193.8	215.1	246.8	294.2	367.7	462.6	562.3	661.2	758.4	851.0	926.9
117.5°	213.7	235.8	265.9	309.5	375.5	461.8	554.1	641.5	722.1	794.8	859.2
120°	227.0	249.1	279.2	320.3	381.2	461.8	549.6	632.6	706.2	769.5	825.6
122.5°	240.3	261.7	291.8	330.4	386.9	461.2	544.5	625.1	696.1	753.7	802.9
125°	258.6	280.7	309.2	345.6	395.5	460.3	536.2	612.1	680.1	734.7	778.2
127.5°	275.5	297.9	325.3	358.7	402.2	458.5	525.0	596.3	661.3	715.7	757.0
130°	286.3	309.2	336.1	366.9	407.3	457.9	518.0	583.7	646.1	699.9	741.8
132.5°	296.4	318.1	345.0	375.2	411.7	457.2	511.7	570.4	629.1	681.5	723.5
135°	310.8	331.4	357.4	386.0	418.4	456.3	502.2	552.0	603.4	651.6	691.2
137.5°	323.0	342.6	366.9	393.6	422.3	456.1	493.9	535.4	578.9	619.6	655.3
140°	330.6	349.6	373.3	398.5	425.5	455.5	489.6	525.9	563.1	598.7	631.8
142.5°	337.5	355.8	379.0	402.3	428.0	455.5	485.8	517.1	549.8	580.4	609.1
145°	347.2	364.6	385.2	406.5	429.4	453.9	479.3	504.5	531.5	555.2	577.3
147.5°	356.5	372.2	391.5	410.1	430.2	451.1	473.4	494.2	515.6	534.6	552.0
150°	362.2	377.2	394.7	412.0	430.2	449.2	469.0	488.0	506.1	522.0	536.2
152.5°	367.9	381.7	397.2	413.3	429.0	446.0	463.9	481.0	496.6	511.2	522.9
155°	375.7	387.5	400.9	414.4	427.1	441.3	456.3	470.6	483.2	495.0	504.5
157.5°	382.9	392.3	403.6	414.4	425.0	436.4	448.5	459.3	469.9	479.9	487.5
160°	386.7	395.5	404.9	414.4	423.1	432.6	442.9	452.3	461.1	469.8	476.1
162.5°	390.5	397.4	406.2	414.4	421.2	428.8	437.8	445.4	452.8	459.6	465.3
165°	394.7	399.3	406.5	412.8	417.6	423.1	429.4	435.8	440.5	446.0	450.0
167.5°	397.5	401.1	406.3	410.9	413.8	417.4	421.8	426.4	430.1	434.5	436.9
170°	399.3	401.7	405.7	409.6	411.2	413.6	416.8	420.7	423.1	426.3	428.6
172.5°	400.6	402.3	405.0	408.4	408.7	409.8	412.3	415.7	417.4	419.3	421.0
175°	402.5	402.5	404.1	406.5	405.7	405.7	407.3	408.8	409.6	411.2	411.2
177.5°	402.5	402.5	403.1	404.4	403.1	403.1	403.8	404.4	405.0	405.0	405.7
180°	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5



TEST NUMBER: P332885-927

CATALOG NUMBER: S124RDIP-S350D1035U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3
2.5°	444.2	444.5	443.5	443.1	443.5	444.5	444.2	445.0	445.2	446.5	446.0
5°	412.1	411.7	410.7	411.0	410.7	411.7	412.1	413.6	414.3	417.3	416.9
7.5°	384.6	383.2	383.6	382.1	383.6	383.2	384.6	386.0	388.2	389.6	392.8
10°	367.8	365.8	364.1	362.6	364.1	365.8	367.8	368.6	371.8	373.3	376.4
12.5°	344.9	343.1	340.9	341.3	340.9	343.1	344.9	348.2	352.3	355.5	360.4
15°	312.4	309.5	305.1	305.6	305.1	309.5	312.4	314.8	318.9	326.1	329.4
17.5°	284.8	284.8	282.7	283.3	282.7	284.8	284.8	288.1	290.3	294.8	299.9
20°	270.5	269.3	269.4	268.9	269.4	269.3	270.5	274.5	276.7	279.9	285.5
22.5°	260.6	259.0	257.7	256.6	257.7	259.0	260.6	261.7	264.7	267.8	272.4
25°	243.9	242.8	241.1	240.7	241.1	242.8	243.9	245.6	247.1	251.0	253.8
27.5°	229.2	229.0	228.3	227.4	228.3	229.0	229.2	230.7	232.7	235.2	238.8
30°	220.7	220.3	219.9	219.4	219.9	220.3	220.7	222.2	223.6	225.7	228.5
32.5°	213.0	212.8	212.4	212.5	212.4	212.8	213.0	213.7	214.7	217.3	219.5
35°	202.1	201.9	201.5	201.4	201.5	201.9	202.1	202.9	203.4	204.1	206.0
37.5°	191.9	192.4	192.2	192.1	192.2	192.4	191.9	192.1	191.5	192.8	194.1
40°	184.9	185.1	185.4	185.2	185.4	185.1	184.9	185.1	185.1	185.1	186.2
42.5°	179.0	179.0	179.6	179.0	179.6	179.0	179.0	178.3	177.4	177.5	177.9
45°	168.6	169.7	169.4	169.4	169.4	169.7	168.6	167.2	167.1	166.3	166.3
47.5°	157.1	158.1	158.4	158.3	158.4	158.1	157.1	156.6	155.7	155.0	155.0
50°	149.6	149.2	149.8	149.6	149.8	149.2	149.6	148.7	147.3	147.3	146.9
52.5°	140.5	140.5	140.5	140.3	140.5	140.5	140.5	140.0	139.4	138.8	138.6
55°	126.4	126.6	126.2	126.4	126.2	126.6	126.4	126.2	126.2	125.8	126.2
57.5°	111.1	110.2	110.5	110.1	110.5	110.2	111.1	111.9	112.2	112.3	112.8
60°	100.1	98.6	98.2	97.5	98.2	98.6	100.1	102.0	102.7	103.1	103.7
62.5°	87.9	86.7	85.5	86.1	85.5	86.7	87.9	89.8	91.5	92.8	94.1
65°	71.5	70.7	70.1	70.9	70.1	70.7	71.5	73.0	74.5	77.4	80.2
67.5°	59.1	58.7	58.7	58.4	58.7	58.7	59.1	59.9	60.8	62.5	65.1
70°	52.7	52.1	52.1	51.7	52.1	52.1	52.7	52.7	53.6	54.3	56.2
72.5°	46.1	45.6	45.7	45.5	45.7	45.6	46.1	46.3	47.1	47.5	48.3
75°	34.1	33.2	33.2	33.4	33.2	33.2	34.1	35.3	36.2	37.9	38.3
77.5°	25.4	25.3	25.5	25.2	25.5	25.3	25.4	25.4	25.7	26.5	27.1
80°	20.8	20.6	20.4	21.0	20.4	20.6	20.8	20.8	21.0	21.2	21.4
82.5°	16.2	16.2	16.1	16.8	16.1	16.2	16.2	16.5	16.5	16.4	16.6
85°	9.7	9.3	9.7	9.3	9.7	9.3	9.7	9.6	9.7	9.6	9.7
87.5°	6.7	6.8	6.5	6.7	6.5	6.8	6.7	6.3	6.3	6.4	6.2
90°	16.6	17.4	16.6	16.6	16.6	17.4	16.6	15.8	15.8	15.1	14.3
92.5°	67.9	63.6	60.9	60.9	60.9	63.6	67.9	77.2	93.0	116.9	155.3
95°	242.0	217.5	203.3	193.0	203.3	217.5	242.0	280.7	357.4	463.4	586.0
97.5°	603.6	556.0	532.3	515.8	532.3	556.0	603.6	660.4	742.9	820.2	865.9
100°	803.5	755.3	731.5	725.2	731.5	755.3	803.5	872.3	930.8	969.6	953.8
102.5°	972.4	937.5	912.5	907.4	912.5	937.5	972.4	1014.6	1039.0	1027.8	949.4
105°	1134.9	1128.5	1117.5	1112.7	1117.5	1128.5	1134.9	1133.3	1100.8	1022.5	885.7
107.5°	1160.9	1179.0	1186.9	1189.0	1186.9	1179.0	1160.9	1121.9	1051.4	941.1	795.4
110°	1135.7	1168.9	1183.1	1190.3	1183.1	1168.9	1135.7	1079.5	992.5	877.8	741.0



TEST NUMBER: P332885-927

CATALOG NUMBER: S124RDIP-S350D1035U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1081.2	1121.4	1141.4	1152.9	1141.4	1121.4	1081.2	1017.5	930.5	822.1	701.2
115°	989.4	1036.8	1062.1	1068.4	1062.1	1036.8	989.4	926.9	851.0	758.4	661.2
117.5°	912.5	952.4	977.9	982.9	977.9	952.4	912.5	859.2	794.8	722.1	641.5
120°	870.7	905.5	926.1	934.8	926.1	905.5	870.7	825.6	769.5	706.2	632.6
122.5°	841.0	870.7	888.1	896.8	888.1	870.7	841.0	802.9	753.7	696.1	625.1
125°	809.8	832.7	847.8	852.5	847.8	832.7	809.8	778.2	734.7	680.1	612.1
127.5°	788.8	809.2	821.8	826.6	821.8	809.2	788.8	757.0	715.7	661.3	596.3
130°	774.2	794.0	806.7	811.4	806.7	794.0	774.2	741.8	699.9	646.1	583.7
132.5°	755.3	777.5	789.6	794.3	789.6	777.5	755.3	723.5	681.5	629.1	570.4
135°	722.9	745.0	757.6	762.4	757.6	745.0	722.9	691.2	651.6	603.4	552.0
137.5°	684.8	706.7	717.2	722.9	717.2	706.7	684.8	655.3	619.6	578.9	535.4
140°	659.6	677.0	688.0	694.3	688.0	677.0	659.6	631.8	598.7	563.1	525.9
142.5°	633.6	649.7	659.6	664.0	659.6	649.7	633.6	609.1	580.4	549.8	517.1
145°	597.1	610.5	618.5	622.4	618.5	610.5	597.1	577.3	555.2	531.5	504.5
147.5°	566.6	578.1	584.2	585.5	584.2	578.1	566.6	552.0	534.6	515.6	494.2
150°	548.8	559.1	563.9	564.7	563.9	559.1	548.8	536.2	522.0	506.1	488.0
152.5°	533.7	542.0	544.9	545.7	544.9	542.0	533.7	522.9	511.2	496.6	481.0
155°	512.5	518.8	521.2	521.2	521.2	518.8	512.5	504.5	495.0	483.2	470.6
157.5°	493.5	498.2	499.6	499.6	499.6	498.2	493.5	487.5	479.9	469.9	459.3
160°	480.9	485.6	486.4	486.4	486.4	485.6	480.9	476.1	469.8	461.1	452.3
162.5°	468.8	473.6	474.4	473.7	474.4	473.6	468.8	465.3	459.6	452.8	445.4
165°	453.1	456.3	455.5	454.7	455.5	456.3	453.1	450.0	446.0	440.5	435.8
167.5°	438.5	440.5	440.4	439.7	440.4	440.5	438.5	436.9	434.5	430.1	426.4
170°	430.2	431.0	430.2	430.2	430.2	431.0	430.2	428.6	426.3	423.1	420.7
172.5°	422.0	422.8	422.0	420.7	422.0	422.8	422.0	421.0	419.3	417.4	415.7
175°	411.2	412.8	411.2	409.6	411.2	412.8	411.2	411.2	411.2	409.6	408.8
177.5°	405.0	405.7	404.4	403.1	404.4	405.7	405.0	405.7	405.0	405.0	404.4
180°	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5



TEST NUMBER: P332885-927

CATALOG NUMBER: S124RDIP-S350D1035U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3
2.5°	445.0	446.2	448.5	451.2	453.5	455.4	456.9	459.1	461.0	463.7	466.2
5°	418.1	420.7	424.5	429.0	434.6	438.3	443.0	447.2	453.1	459.1	464.9
7.5°	394.4	397.3	402.8	409.0	415.7	421.8	427.4	434.7	442.6	451.4	461.1
10°	379.1	382.3	388.8	395.9	403.9	409.9	417.3	426.0	435.0	445.7	457.6
12.5°	365.3	368.4	376.2	383.5	391.7	398.3	407.0	415.7	427.8	439.3	453.0
15°	338.4	346.5	355.5	364.1	373.8	381.9	392.4	401.4	412.8	429.1	444.7
17.5°	308.6	317.1	328.4	341.7	354.7	364.7	375.3	386.5	400.1	416.8	434.7
20°	291.1	298.1	310.5	325.3	340.5	354.3	364.1	376.4	390.5	408.5	427.1
22.5°	278.1	284.0	293.7	308.5	324.9	341.0	353.5	365.7	381.2	399.3	419.5
25°	258.6	264.9	273.4	283.4	302.2	319.2	335.6	349.7	366.1	384.1	406.6
27.5°	242.2	247.8	255.6	266.1	278.7	297.5	317.3	333.3	350.2	369.6	392.1
30°	232.7	237.2	243.5	254.2	266.3	283.1	303.2	321.9	339.0	359.0	382.5
32.5°	222.6	227.4	233.6	242.1	255.0	269.2	289.2	309.7	327.9	348.4	371.4
35°	209.2	213.0	218.6	227.2	238.8	251.2	269.0	290.3	309.3	331.3	353.2
37.5°	195.7	200.1	204.5	212.2	221.7	235.0	249.6	271.3	292.5	312.5	333.9
40°	188.1	190.7	195.5	201.8	211.8	223.6	237.3	258.6	279.7	299.6	321.2
42.5°	179.5	182.4	186.6	192.7	201.8	213.3	226.7	245.0	267.1	286.4	306.0
45°	167.6	169.3	173.4	178.6	186.2	197.8	210.2	226.5	247.3	265.7	282.9
47.5°	155.6	157.1	159.6	164.5	172.9	182.2	193.8	208.4	226.6	245.0	259.6
50°	147.3	148.7	151.1	155.6	163.1	172.3	183.7	196.9	213.2	230.8	243.0
52.5°	139.1	139.8	142.1	147.2	153.5	162.6	172.8	184.9	200.1	214.8	227.1
55°	126.0	127.7	129.2	132.9	138.9	147.6	156.8	168.2	180.0	192.3	202.9
57.5°	112.3	114.2	116.3	119.6	124.4	132.4	140.6	149.9	160.0	170.2	179.1
60°	103.3	105.0	106.9	110.6	114.9	121.3	130.3	138.4	146.1	155.4	164.2
62.5°	94.4	96.2	98.3	101.3	105.4	111.5	119.1	126.0	134.0	142.2	148.8
65°	81.4	82.7	84.4	87.2	91.1	96.6	102.7	108.2	115.3	121.3	127.3
67.5°	67.0	69.6	71.7	74.0	77.3	82.4	86.9	92.1	97.0	101.4	106.9
70°	57.6	60.4	62.4	64.9	68.0	72.4	76.7	80.2	84.2	88.5	93.4
72.5°	49.6	51.8	53.5	56.0	58.9	62.9	66.9	69.9	73.1	76.0	80.8
75°	39.2	40.1	41.3	43.3	45.9	49.0	52.1	54.7	56.6	59.3	62.6
77.5°	28.1	29.9	30.7	32.2	34.1	35.9	38.0	40.2	42.1	42.9	45.6
80°	21.5	22.3	23.1	25.1	26.2	28.1	29.6	31.7	32.4	33.4	35.8
82.5°	16.8	17.2	17.7	18.2	18.9	20.8	22.3	23.6	24.3	24.6	26.5
85°	9.7	9.9	10.1	10.3	10.5	10.5	11.2	12.2	13.5	13.5	14.1
87.5°	6.0	6.3	5.9	5.5	5.8	4.8	5.0	4.8	5.1	5.1	5.2
90°	13.5	14.3	12.7	11.1	11.1	6.3	6.3	5.5	4.8	2.4	0.8
92.5°	209.0	250.9	219.5	159.8	98.4	58.2	41.7	30.2	20.6	13.2	9.0
95°	662.7	644.5	486.4	297.4	167.6	98.9	65.7	46.7	36.4	28.4	26.1
97.5°	832.6	678.8	455.2	267.3	160.3	107.3	79.4	63.1	53.6	46.8	46.8
100°	838.3	635.8	412.8	251.5	162.2	115.5	90.2	75.1	65.7	60.1	60.1
102.5°	790.8	582.1	384.4	247.1	168.4	126.2	102.2	87.8	78.9	74.0	72.7
105°	704.6	518.8	359.8	249.1	183.5	145.5	122.6	108.4	98.9	94.9	92.5
107.5°	635.0	483.4	355.4	260.8	201.1	166.2	143.6	130.0	119.9	116.0	114.4
110°	600.2	471.3	356.6	269.7	214.3	179.5	158.2	143.9	134.4	130.5	128.9



TEST NUMBER: P332885-927

CATALOG NUMBER: S124RDIP-S350D1035U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	580.7	465.6	360.4	279.2	227.0	193.5	172.1	157.9	149.0	144.4	142.8
115°	562.3	462.6	367.7	294.2	246.8	215.1	193.8	178.7	170.8	165.2	163.0
117.5°	554.1	461.8	375.5	309.5	265.9	235.8	213.7	199.6	190.9	186.0	183.8
120°	549.6	461.8	381.2	320.3	279.2	249.1	227.0	213.5	204.9	199.3	197.7
122.5°	544.5	461.2	386.9	330.4	291.8	261.7	240.3	225.5	217.5	211.9	210.4
125°	536.2	460.3	395.5	345.6	309.2	280.7	258.6	243.6	234.9	230.1	227.0
127.5°	525.0	458.5	402.2	358.7	325.3	297.9	275.5	259.8	249.9	244.2	241.7
130°	518.0	457.9	407.3	366.9	336.1	309.2	286.3	271.2	259.4	253.1	249.9
132.5°	511.7	457.2	411.7	375.2	345.0	318.1	296.4	280.1	268.9	260.6	258.1
135°	502.2	456.3	418.4	386.0	357.4	331.4	310.8	294.2	280.7	272.8	269.7
137.5°	493.9	456.1	422.3	393.6	366.9	342.6	323.0	305.7	292.9	284.2	281.2
140°	489.6	455.5	425.5	398.5	373.3	349.6	330.6	313.9	300.6	291.8	289.5
142.5°	485.8	455.5	428.0	402.3	379.0	355.8	337.5	321.5	308.7	300.7	298.3
145°	479.3	453.9	429.4	406.5	385.2	364.6	347.2	332.2	321.1	313.1	310.8
147.5°	473.4	451.1	430.2	410.1	391.5	372.2	356.5	344.0	332.6	325.7	324.9
150°	469.0	449.2	430.2	412.0	394.7	377.2	362.2	350.4	340.9	334.5	333.7
152.5°	463.9	446.0	429.0	413.3	397.2	381.7	367.9	357.3	348.5	342.1	342.0
155°	456.3	441.3	427.1	414.4	400.9	387.5	375.7	366.9	359.0	354.3	353.5
157.5°	448.5	436.4	425.0	414.4	403.6	392.3	382.9	375.3	369.2	364.7	364.7
160°	442.9	432.6	423.1	414.4	404.9	395.5	386.7	380.4	374.9	371.7	371.7
162.5°	437.8	428.8	421.2	414.4	406.2	397.4	390.5	384.8	379.9	377.4	378.0
165°	429.4	423.1	417.6	412.8	406.5	399.3	394.7	390.7	386.7	385.2	385.2
167.5°	421.8	417.4	413.8	410.9	406.3	401.1	397.5	395.3	392.3	391.5	392.3
170°	416.8	413.6	411.2	409.6	405.7	401.7	399.3	397.8	395.5	394.7	395.5
172.5°	412.3	409.8	408.7	408.4	405.0	402.3	400.6	399.7	397.9	397.8	398.5
175°	407.3	405.7	405.7	406.5	404.1	402.5	402.5	401.7	400.9	400.9	401.7
177.5°	403.8	403.1	403.1	404.4	403.1	402.5	402.5	402.5	401.9	402.5	403.1
180°	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5



TEST NUMBER: P332885-927

CATALOG NUMBER: S124RDIP-S350D1035U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3
2.5°	468.2	469.5	471.0	473.9	476.3	477.4	479.4	480.9	480.5	482.6	486.2
5°	470.0	475.1	480.9	486.9	493.6	499.2	503.7	508.3	511.8	516.1	522.5
7.5°	469.7	478.7	488.5	499.2	510.3	519.9	528.7	537.7	545.7	554.4	565.9
10°	468.5	480.5	492.7	506.8	520.9	534.2	546.1	557.4	568.1	579.5	594.0
12.5°	467.1	480.9	495.7	512.6	530.1	546.1	560.2	576.5	589.9	604.6	621.2
15°	461.2	479.7	499.9	521.7	542.8	564.4	583.6	603.5	622.1	639.7	660.7
17.5°	454.4	475.8	499.5	525.4	550.6	576.8	599.8	624.8	643.7	667.4	686.9
20°	448.9	471.9	497.2	526.2	554.9	584.0	609.3	634.9	656.2	680.0	704.7
22.5°	442.1	467.4	494.8	524.9	554.9	586.7	614.7	640.1	666.5	693.3	718.8
25°	431.2	457.5	486.6	519.5	554.1	586.5	616.5	647.9	676.4	705.5	728.4
27.5°	417.9	445.4	476.0	510.1	545.5	578.7	614.0	647.6	676.3	704.3	724.2
30°	407.2	436.3	465.7	500.2	536.9	572.6	610.5	644.0	674.2	699.3	710.6
32.5°	396.2	423.8	454.2	489.1	526.7	565.1	602.6	637.0	664.9	679.9	680.2
35°	377.2	403.1	434.6	468.9	507.6	549.1	587.2	620.9	638.0	639.3	620.9
37.5°	356.5	380.2	409.9	444.3	486.6	528.0	566.8	589.3	595.0	575.9	542.0
40°	341.6	363.5	392.2	427.5	469.4	512.2	547.6	564.1	558.2	527.2	489.3
42.5°	326.0	346.4	374.1	408.8	451.0	494.2	524.4	533.2	517.4	481.6	437.3
45°	300.6	319.2	346.7	381.8	422.2	462.7	485.6	481.1	454.6	412.3	362.6
47.5°	274.0	292.2	316.8	349.2	390.7	425.6	441.1	427.5	389.9	343.3	302.9
50°	256.5	275.0	297.7	328.7	366.5	400.3	410.2	389.6	347.8	303.0	265.9
52.5°	239.2	255.1	277.3	307.2	343.4	371.9	377.2	353.5	310.3	270.1	237.2
55°	213.0	227.4	246.1	274.3	305.6	329.8	326.9	296.4	257.2	222.9	197.0
57.5°	187.6	198.4	215.8	242.2	269.7	285.9	275.6	249.5	213.0	184.9	163.1
60°	170.8	180.9	197.0	220.1	244.3	253.5	244.9	216.6	187.7	162.0	143.6
62.5°	154.9	163.8	177.7	199.1	218.6	224.1	214.8	190.1	164.1	142.2	127.0
65°	131.8	140.1	151.9	167.1	180.5	183.2	177.2	151.9	132.2	113.8	103.3
67.5°	110.8	116.2	125.5	138.6	145.8	147.3	135.7	119.8	102.4	91.2	83.3
70°	96.7	100.5	109.1	116.2	122.1	122.2	111.5	98.8	85.5	76.3	70.5
72.5°	83.1	86.7	93.2	98.1	102.6	101.1	91.3	81.3	70.5	63.5	59.3
75°	64.1	67.3	70.7	73.0	73.0	71.1	63.9	56.4	50.2	46.1	44.8
77.5°	46.6	49.2	50.4	50.0	49.4	46.4	41.9	37.0	34.8	32.9	31.8
80°	36.6	37.7	38.0	37.2	36.0	32.6	29.6	27.6	25.5	24.7	24.4
82.5°	27.1	28.1	27.1	27.4	24.9	22.1	20.4	19.7	18.9	18.6	18.2
85°	14.4	14.3	13.9	12.9	11.2	10.9	10.7	10.5	10.1	10.3	9.9
87.5°	5.4	5.5	5.0	5.0	5.0	5.6	5.8	6.1	6.4	6.1	6.6
90°	2.4	4.8	5.5	6.3	6.3	11.1	11.1	12.7	14.3	13.5	14.3
92.5°	13.2	20.6	30.2	41.7	58.2	98.4	159.8	219.5	250.9	209.0	155.3
95°	28.4	36.4	46.7	65.7	98.9	167.6	297.4	486.4	644.5	662.7	586.0
97.5°	46.8	53.6	63.1	79.4	107.3	160.3	267.3	455.2	678.8	832.6	865.9
100°	60.1	65.7	75.1	90.2	115.5	162.2	251.5	412.8	635.8	838.3	953.8
102.5°	74.0	78.9	87.8	102.2	126.2	168.4	247.1	384.4	582.1	790.8	949.4
105°	94.9	98.9	108.4	122.6	145.5	183.5	249.1	359.8	518.8	704.6	885.7
107.5°	116.0	119.9	130.0	143.6	166.2	201.1	260.8	355.4	483.4	635.0	795.4
110°	130.5	134.4	143.9	158.2	179.5	214.3	269.7	356.6	471.3	600.2	741.0





TEST NUMBER: P332885-927

CATALOG NUMBER: S124RDIP-S350D1035U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	144.4	149.0	157.9	172.1	193.5	227.0	279.2	360.4	465.6	580.7	701.2
115°	165.2	170.8	178.7	193.8	215.1	246.8	294.2	367.7	462.6	562.3	661.2
117.5°	186.0	190.9	199.6	213.7	235.8	265.9	309.5	375.5	461.8	554.1	641.5
120°	199.3	204.9	213.5	227.0	249.1	279.2	320.3	381.2	461.8	549.6	632.6
122.5°	211.9	217.5	225.5	240.3	261.7	291.8	330.4	386.9	461.2	544.5	625.1
125°	230.1	234.9	243.6	258.6	280.7	309.2	345.6	395.5	460.3	536.2	612.1
127.5°	244.2	249.9	259.8	275.5	297.9	325.3	358.7	402.2	458.5	525.0	596.3
130°	253.1	259.4	271.2	286.3	309.2	336.1	366.9	407.3	457.9	518.0	583.7
132.5°	260.6	268.9	280.1	296.4	318.1	345.0	375.2	411.7	457.2	511.7	570.4
135°	272.8	280.7	294.2	310.8	331.4	357.4	386.0	418.4	456.3	502.2	552.0
137.5°	284.2	292.9	305.7	323.0	342.6	366.9	393.6	422.3	456.1	493.9	535.4
140°	291.8	300.6	313.9	330.6	349.6	373.3	398.5	425.5	455.5	489.6	525.9
142.5°	300.7	308.7	321.5	337.5	355.8	379.0	402.3	428.0	455.5	485.8	517.1
145°	313.1	321.1	332.2	347.2	364.6	385.2	406.5	429.4	453.9	479.3	504.5
147.5°	325.7	332.6	344.0	356.5	372.2	391.5	410.1	430.2	451.1	473.4	494.2
150°	334.5	340.9	350.4	362.2	377.2	394.7	412.0	430.2	449.2	469.0	488.0
152.5°	342.1	348.5	357.3	367.9	381.7	397.2	413.3	429.0	446.0	463.9	481.0
155°	354.3	359.0	366.9	375.7	387.5	400.9	414.4	427.1	441.3	456.3	470.6
157.5°	364.7	369.2	375.3	382.9	392.3	403.6	414.4	425.0	436.4	448.5	459.3
160°	371.7	374.9	380.4	386.7	395.5	404.9	414.4	423.1	432.6	442.9	452.3
162.5°	377.4	379.9	384.8	390.5	397.4	406.2	414.4	421.2	428.8	437.8	445.4
165°	385.2	386.7	390.7	394.7	399.3	406.5	412.8	417.6	423.1	429.4	435.8
167.5°	391.5	392.3	395.3	397.5	401.1	406.3	410.9	413.8	417.4	421.8	426.4
170°	394.7	395.5	397.8	399.3	401.7	405.7	409.6	411.2	413.6	416.8	420.7
172.5°	397.8	397.9	399.7	400.6	402.3	405.0	408.4	408.7	409.8	412.3	415.7
175°	400.9	400.9	401.7	402.5	402.5	404.1	406.5	405.7	405.7	407.3	408.8
177.5°	402.5	401.9	402.5	402.5	402.5	403.1	404.4	403.1	403.1	403.8	404.4
180°	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5



TEST NUMBER: P332885-927

CATALOG NUMBER: S124RDIP-S350D1035U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	465.3	465.3	465.3	465.3	465.3	465.3	465.3
2.5°	488.1	488.7	489.2	490.7	490.8	492.2	490.8
5°	528.5	531.2	535.3	539.4	539.8	542.4	537.7
7.5°	573.8	579.9	583.7	590.3	592.9	594.6	591.9
10°	605.0	610.6	620.6	625.4	630.3	631.1	628.8
12.5°	635.2	644.0	651.9	661.2	660.9	667.5	665.1
15°	675.3	684.5	695.4	705.7	709.4	709.4	712.4
17.5°	703.9	720.8	732.1	740.1	749.0	750.5	749.5
20°	723.3	741.5	753.5	764.0	770.0	771.7	771.7
22.5°	737.7	753.2	764.9	774.4	779.3	781.3	780.7
25°	747.7	761.0	768.1	771.0	772.2	771.9	768.3
27.5°	734.0	733.4	729.0	720.3	713.8	709.9	705.4
30°	708.0	698.2	686.9	674.5	658.6	646.4	642.7
32.5°	669.1	647.2	628.1	607.5	590.4	578.2	573.1
35°	594.0	559.3	530.9	506.2	488.2	477.0	473.2
37.5°	504.8	471.2	436.2	412.2	397.2	385.9	381.7
40°	448.1	411.5	381.0	358.5	343.1	332.0	331.8
42.5°	396.3	361.4	332.6	316.5	299.9	292.6	292.6
45°	324.6	296.6	272.2	259.4	249.5	243.5	241.9
47.5°	268.7	245.6	229.3	219.2	211.1	207.3	204.8
50°	237.3	217.1	204.1	195.4	190.8	186.0	185.6
52.5°	211.3	194.9	184.8	177.7	172.0	169.1	169.1
55°	177.5	164.6	157.5	152.0	147.6	145.3	144.3
57.5°	149.6	139.9	134.7	129.7	127.8	126.0	125.6
60°	132.2	125.6	120.7	116.8	114.0	113.4	113.2
62.5°	117.8	110.9	107.6	104.5	102.4	101.6	101.2
65°	97.1	92.1	89.0	86.6	85.9	84.5	84.4
67.5°	78.3	75.3	73.3	71.6	70.6	70.5	70.5
70°	66.8	65.0	63.4	62.4	61.9	61.5	61.5
72.5°	56.9	55.6	54.2	53.7	53.6	53.2	53.1
75°	43.3	42.0	42.2	41.3	40.5	39.5	39.0
77.5°	30.7	29.8	29.5	29.5	28.8	28.8	29.0
80°	23.8	22.9	22.7	22.9	22.7	22.1	22.1
82.5°	18.1	17.3	17.1	17.0	16.9	17.0	16.7
85°	9.7	9.3	9.3	9.3	9.7	9.6	9.3
87.5°	6.4	6.5	6.6	6.7	6.8	6.5	6.7
90°	15.1	15.8	15.8	16.6	17.4	16.6	16.6
92.5°	116.9	93.0	77.2	67.9	63.6	60.9	60.9
95°	463.4	357.4	280.7	242.0	217.5	203.3	193.0
97.5°	820.2	742.9	660.4	603.6	556.0	532.3	515.8
100°	969.6	930.8	872.3	803.5	755.3	731.5	725.2
102.5°	1027.8	1039.0	1014.6	972.4	937.5	912.5	907.4
105°	1022.5	1100.8	1133.3	1134.9	1128.5	1117.5	1112.7
107.5°	941.1	1051.4	1121.9	1160.9	1179.0	1186.9	1189.0
110°	877.8	992.5	1079.5	1135.7	1168.9	1183.1	1190.3



TEST NUMBER: P332885-927

CATALOG NUMBER: S124RDIP-S350D1035U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	822.1	930.5	1017.5	1081.2	1121.4	1141.4	1152.9
115°	758.4	851.0	926.9	989.4	1036.8	1062.1	1068.4
117.5°	722.1	794.8	859.2	912.5	952.4	977.9	982.9
120°	706.2	769.5	825.6	870.7	905.5	926.1	934.8
122.5°	696.1	753.7	802.9	841.0	870.7	888.1	896.8
125°	680.1	734.7	778.2	809.8	832.7	847.8	852.5
127.5°	661.3	715.7	757.0	788.8	809.2	821.8	826.6
130°	646.1	699.9	741.8	774.2	794.0	806.7	811.4
132.5°	629.1	681.5	723.5	755.3	777.5	789.6	794.3
135°	603.4	651.6	691.2	722.9	745.0	757.6	762.4
137.5°	578.9	619.6	655.3	684.8	706.7	717.2	722.9
140°	563.1	598.7	631.8	659.6	677.0	688.0	694.3
142.5°	549.8	580.4	609.1	633.6	649.7	659.6	664.0
145°	531.5	555.2	577.3	597.1	610.5	618.5	622.4
147.5°	515.6	534.6	552.0	566.6	578.1	584.2	585.5
150°	506.1	522.0	536.2	548.8	559.1	563.9	564.7
152.5°	496.6	511.2	522.9	533.7	542.0	544.9	545.7
155°	483.2	495.0	504.5	512.5	518.8	521.2	521.2
157.5°	469.9	479.9	487.5	493.5	498.2	499.6	499.6
160°	461.1	469.8	476.1	480.9	485.6	486.4	486.4
162.5°	452.8	459.6	465.3	468.8	473.6	474.4	473.7
165°	440.5	446.0	450.0	453.1	456.3	455.5	454.7
167.5°	430.1	434.5	436.9	438.5	440.5	440.4	439.7
170°	423.1	426.3	428.6	430.2	431.0	430.2	430.2
172.5°	417.4	419.3	421.0	422.0	422.8	422.0	420.7
175°	409.6	411.2	411.2	411.2	412.8	411.2	409.6
177.5°	405.0	405.0	405.7	405.0	405.7	404.4	403.1
180°	402.5	402.5	402.5	402.5	402.5	402.5	402.5

(END OF REPORT)