

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332913-927

Luminaire Tested: **S124RDIP-S575D1035U927-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332913-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIP-S575D1035U927-4F0-1E-UDD-A  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 575 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1035 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5207.4 lumens  
Efficiency: N/A  
Efficacy: 117.0 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 44.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332913-927

CATALOG NUMBER: S124RDIP-S575D1035U927-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P332913-927

CATALOG NUMBER: S124RDIP-S575D1035U927-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	44	44	44	37
1	95	91	87	84	86	83	80	77	67	65	63	53	52	50	40	39	38	32
2	87	80	74	69	79	73	68	64	59	56	53	47	45	42	35	34	33	27
3	80	71	64	58	72	64	58	53	53	48	45	42	39	36	32	30	28	24
4	73	63	55	49	66	57	51	46	47	42	38	37	34	31	28	26	24	20
5	67	56	48	42	60	51	44	39	42	37	33	34	30	27	26	23	21	18
6	62	50	42	37	56	46	39	34	38	33	29	30	27	24	23	21	19	16
7	57	45	37	32	52	41	35	30	34	29	26	28	24	21	21	19	17	14
8	53	41	33	28	48	38	31	26	31	26	23	25	22	19	20	17	15	13
9	49	37	30	25	45	34	28	24	29	24	20	23	20	17	18	16	14	12
10	46	34	27	23	42	32	25	21	26	22	18	21	18	15	17	14	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	6176	6176	6176	6176
5°	7164	6195	5476	6195
10°	8475	6167	4887	6167
15°	9789	6110	4199	6110
20°	10899	6032	3797	6032
25°	11251	5955	3526	5955
30°	9849	5862	3361	5862
35°	7666	5723	3263	5723
40°	5750	5564	3209	5564
45°	4539	5310	3181	5310
50°	3832	5016	3090	5016
55°	3340	4694	2923	4694
60°	3006	4359	2588	4359
65°	2649	3998	2225	3998
70°	2386	3623	2009	3623
75°	1999	3213	1712	3213
80°	1692	2738	1604	2738
85°	1426	2140	1426	2140



TEST NUMBER: P332913-927

CATALOG NUMBER: S124RDIP-S575D1035U927-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	74.1	1.4
10°-20°	223.6	4.3
20°-30°	349.7	6.7
30°-40°	388.8	7.5
40°-50°	344.9	6.6
50°-60°	268.8	5.2
60°-70°	176.0	3.4
70°-80°	86.5	1.7
80°-90°	24.4	0.5
90°-100°	36.2	0.7
100°-110°	230.6	4.4
110°-120°	441.1	8.5
120°-130°	559.9	10.8
130°-140°	599.1	11.5
140°-150°	560.2	10.8
150°-160°	451.8	8.7
160°-170°	291.4	5.6
170°-180°	100.4	1.9
0°-30°	647.4	12.4
0°-40°	1036.2	19.9
0°-60°	1649.9	31.7
0°-90°	1936.8	37.2
90°-120°	707.8	13.6
90°-150°	2427.0	46.6
90°-180°	3271.0	62.8
0°-180°	5207.4	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	765	765	765	765	765	
5°	884	764	676	764	884	89
15°	1171	731	502	731	1171	333
25°	1263	668	396	668	1263	560
35°	778	581	331	581	778	488
45°	398	465	279	465	398	315
55°	237	334	208	334	237	216
65°	139	209	116	209	139	140
75°	64	103	55	103	64	71
85°	15	23	15	23	15	18
90°	24	2	24	2	24	11
95°	23	44	23	44	23	18
105°	225	238	225	238	225	197
115°	448	444	448	444	448	443
125°	630	625	630	625	630	561
135°	780	775	780	775	780	601
145°	898	894	898	894	898	561
155°	979	980	979	980	979	451
165°	1029	1034	1029	1034	1029	291
175°	1051	1057	1051	1057	1051	100
180°	1057	1057	1057	1057	1057	



TEST NUMBER: P332913-927

CATALOG NUMBER: S124RDIP-S575D1035U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0
2.5°	806.9	809.1	806.9	806.7	804.2	803.5	802.5	799.3	793.4	789.9	790.7
5°	884.0	891.7	887.4	886.8	880.0	873.2	868.9	859.0	848.5	841.5	835.6
7.5°	973.1	977.6	974.9	970.5	959.6	953.3	943.3	930.3	911.6	897.1	884.1
10°	1033.8	1037.4	1036.3	1028.3	1020.3	1003.9	994.7	976.4	952.7	933.9	916.3
12.5°	1093.4	1097.4	1086.6	1087.0	1071.7	1058.8	1044.2	1021.4	993.9	969.6	947.7
15°	1171.2	1166.3	1166.3	1160.2	1143.2	1125.3	1110.2	1086.2	1051.6	1022.7	992.2
17.5°	1232.2	1233.9	1231.4	1216.8	1203.5	1185.0	1157.3	1129.3	1097.2	1058.3	1027.1
20°	1268.7	1268.7	1265.9	1256.0	1238.7	1219.0	1189.1	1158.6	1117.9	1078.8	1043.6
22.5°	1283.4	1284.4	1281.2	1273.0	1257.5	1238.3	1212.8	1181.8	1139.9	1095.8	1052.3
25°	1263.1	1268.9	1269.6	1267.4	1262.8	1251.1	1229.2	1197.5	1159.8	1112.1	1065.2
27.5°	1159.7	1167.0	1173.5	1184.2	1198.3	1205.8	1206.7	1190.6	1157.8	1111.8	1064.7
30°	1056.6	1062.7	1082.8	1109.0	1129.3	1147.8	1163.9	1168.2	1149.7	1108.3	1058.8
32.5°	942.1	950.5	970.6	998.8	1032.7	1064.0	1100.0	1118.3	1117.8	1093.1	1047.2
35°	777.9	784.1	802.6	832.2	872.9	919.4	976.4	1020.8	1051.1	1048.8	1020.8
37.5°	627.4	634.4	653.1	677.6	717.1	774.7	829.9	891.0	946.9	978.3	968.8
40°	545.6	545.9	564.0	589.3	626.3	676.5	736.7	804.5	866.7	917.6	927.4
42.5°	480.9	481.0	493.1	520.3	546.9	594.2	651.6	718.9	791.8	850.5	876.6
45°	397.6	400.4	410.3	426.6	447.5	487.6	533.5	596.1	677.8	747.4	790.9
47.5°	336.7	340.8	347.1	360.4	377.1	403.8	441.7	498.0	564.4	641.0	702.9
50°	305.1	305.8	313.8	321.2	335.6	357.0	390.2	437.0	498.1	571.7	640.5
52.5°	278.1	277.9	282.7	292.1	303.9	320.4	347.3	390.0	444.1	510.1	581.1
55°	237.3	238.8	242.6	249.9	258.9	270.6	291.9	323.9	366.5	422.9	487.3
57.5°	206.4	207.2	210.1	213.3	221.4	230.0	245.9	268.2	304.0	350.2	410.3
60°	186.2	186.5	187.4	192.0	198.5	206.5	217.3	236.1	266.3	308.6	356.0
62.5°	166.4	167.0	168.4	171.8	176.8	182.4	193.6	208.7	233.8	269.8	312.6
65°	138.7	139.0	141.2	142.4	146.4	151.3	159.6	169.8	187.1	217.3	249.7
67.5°	115.9	115.9	116.0	117.7	120.5	123.7	128.7	136.9	149.9	168.4	196.9
70°	101.1	101.1	101.7	102.7	104.2	106.9	109.7	115.9	125.5	140.5	162.4
72.5°	87.3	87.5	88.2	88.3	89.1	91.4	93.5	97.4	104.5	115.9	133.6
75°	64.1	65.0	66.5	67.8	69.3	69.1	71.2	73.7	75.8	82.6	92.8
77.5°	47.7	47.2	47.4	48.5	48.6	49.0	50.5	52.4	54.0	57.2	60.8
80°	36.4	36.4	37.3	37.6	37.3	37.6	39.1	40.1	40.7	41.9	45.3
82.5°	27.5	28.0	27.6	28.0	28.2	28.5	29.8	29.9	30.6	31.1	32.5
85°	15.4	15.7	16.0	15.4	15.4	15.4	16.0	16.3	17.0	16.6	17.3
87.5°	10.1	9.8	10.1	10.0	10.1	9.7	9.8	10.1	9.3	9.4	9.1
90°	23.7	23.4	23.1	22.7	22.3	21.6	20.6	19.5	18.5	17.4	16.0
92.5°	21.9	21.8	21.7	21.6	21.5	21.0	20.0	18.9	17.8	16.8	15.4
95°	22.9	22.7	22.6	22.4	22.3	21.6	20.6	19.5	18.5	17.4	17.2
97.5°	22.2	21.9	21.8	21.6	21.5	21.3	21.2	21.1	21.0	20.9	40.5
100°	22.2	21.9	21.8	21.6	21.5	22.8	25.8	28.8	31.8	34.8	59.0
102.5°	22.8	22.7	22.7	22.7	22.7	38.7	71.0	103.2	135.4	167.6	170.8
105°	225.4	231.7	238.1	244.4	250.7	253.0	251.4	249.9	248.3	246.8	245.9
107.5°	314.1	313.5	312.8	312.1	311.4	310.7	310.0	309.2	308.4	307.6	306.4
110°	352.7	352.2	351.6	351.1	350.6	350.1	349.8	349.4	349.1	348.7	347.7



TEST NUMBER: P332913-927

CATALOG NUMBER: S124RDIP-S575D1035U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	391.3	390.6	390.0	389.3	388.6	388.3	388.4	388.5	388.6	388.6	388.1
115°	447.6	447.6	447.6	447.6	447.6	447.4	447.1	446.7	446.4	446.0	446.2
117.5°	504.9	504.9	505.0	505.1	505.2	505.2	505.3	505.3	505.4	505.5	505.1
120°	540.9	541.3	541.6	541.9	542.3	542.3	541.9	541.6	541.3	540.9	541.1
122.5°	576.3	576.7	577.0	577.4	577.7	577.8	577.6	577.4	577.2	576.9	576.7
125°	629.5	629.3	629.2	629.0	628.8	628.4	627.9	627.4	626.9	626.3	626.7
127.5°	676.1	676.3	676.4	676.6	676.7	676.8	676.9	677.1	677.2	677.2	676.4
130°	707.8	707.8	707.8	707.8	707.8	707.7	707.5	707.3	707.2	707.0	706.5
132.5°	736.9	737.0	737.1	737.3	737.4	737.4	737.3	737.0	736.9	736.7	736.0
135°	780.5	780.1	779.8	779.5	779.1	778.8	778.4	778.1	777.7	777.4	776.7
137.5°	817.8	817.9	818.1	818.2	818.2	818.2	817.8	817.4	817.0	816.6	815.8
140°	843.8	843.6	843.4	843.3	843.1	842.7	842.2	841.7	841.1	840.7	840.3
142.5°	865.3	865.3	865.2	865.2	865.1	865.0	864.6	864.2	863.8	863.4	863.2
145°	898.3	898.0	897.6	897.3	897.0	896.7	896.5	896.4	896.2	896.0	896.0
147.5°	925.7	925.6	925.3	925.2	925.0	924.9	924.7	924.6	924.5	924.3	924.5
150°	943.4	943.3	943.1	942.9	942.7	942.6	942.6	942.6	942.6	942.6	942.9
152.5°	958.6	958.7	958.9	958.9	959.0	958.9	958.7	958.4	958.1	957.8	958.1
155°	979.1	979.5	980.1	980.6	981.1	981.0	980.3	979.6	978.9	978.3	978.7
157.5°	996.1	997.0	997.9	998.9	999.7	999.7	998.9	997.9	997.0	996.1	996.7
160°	1007.5	1008.5	1009.6	1010.7	1011.7	1011.7	1010.7	1009.6	1008.5	1007.5	1007.7
162.5°	1016.4	1017.6	1018.7	1019.9	1021.1	1021.2	1020.2	1019.1	1018.0	1017.0	1017.2
165°	1028.8	1030.4	1032.0	1033.6	1035.1	1035.2	1033.9	1032.5	1031.0	1029.6	1029.6
167.5°	1038.2	1039.9	1041.7	1043.5	1045.2	1045.3	1043.8	1042.2	1040.7	1039.1	1039.3
170°	1043.9	1045.6	1047.4	1049.2	1050.9	1051.1	1049.6	1048.3	1046.9	1045.4	1045.3
172.5°	1047.0	1048.9	1050.8	1052.7	1054.6	1054.9	1053.4	1052.1	1050.7	1049.2	1049.1
175°	1051.0	1053.1	1055.2	1057.3	1059.4	1059.7	1058.1	1056.5	1054.9	1053.4	1053.2
177.5°	1053.5	1055.2	1056.9	1058.6	1060.3	1060.6	1059.4	1058.3	1057.2	1056.1	1055.7
180°	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3



TEST NUMBER: P332913-927

CATALOG NUMBER: S124RDIP-S575D1035U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0
2.5°	788.2	784.7	783.0	779.0	774.4	771.9	769.7	766.5	762.3	757.9	754.6
5°	828.2	820.8	811.5	800.4	790.6	781.0	772.7	764.4	754.9	745.0	735.1
7.5°	869.3	854.7	839.0	820.8	803.1	787.0	772.2	758.0	742.0	727.6	714.5
10°	897.9	878.1	856.3	833.1	810.0	790.0	770.2	752.3	732.6	715.1	700.3
12.5°	921.1	897.9	871.6	842.7	814.9	790.7	768.0	744.7	722.3	703.2	683.5
15°	959.5	927.7	892.3	857.8	821.7	788.8	758.2	731.1	705.5	678.7	659.9
17.5°	986.0	948.2	905.2	863.7	821.1	782.2	747.0	714.7	685.2	657.8	635.4
20°	1001.7	960.1	912.4	865.1	817.4	775.8	737.9	702.1	671.6	642.1	618.9
22.5°	1010.6	964.6	912.4	862.9	813.5	768.4	726.8	689.6	656.3	626.8	601.2
25°	1013.4	964.1	910.8	854.1	799.9	752.1	708.9	668.5	631.5	602.0	574.8
27.5°	1009.5	951.4	896.8	838.6	782.7	732.3	687.0	644.5	607.5	575.8	548.0
30°	1003.5	941.4	882.7	822.4	765.6	717.2	669.5	628.8	590.3	557.3	529.3
32.5°	990.8	929.0	866.0	804.1	746.6	696.8	651.5	610.5	572.7	539.0	509.2
35°	965.4	902.8	834.3	770.9	714.5	662.7	620.1	580.7	544.6	508.6	477.1
37.5°	931.8	868.0	799.9	730.4	673.9	625.0	586.0	549.0	513.7	480.9	446.0
40°	900.3	842.1	771.8	702.7	644.8	597.6	561.6	528.0	492.6	459.9	425.0
42.5°	862.1	812.5	741.5	672.2	615.0	569.5	535.9	503.1	470.9	439.2	402.8
45°	798.3	760.7	694.1	627.6	569.9	524.9	494.1	465.1	436.7	406.5	372.3
47.5°	725.2	699.7	642.3	574.1	520.8	480.3	450.5	426.8	402.8	372.6	342.6
50°	674.4	658.1	602.6	540.3	489.5	452.2	421.7	399.4	379.5	350.5	323.6
52.5°	620.1	611.5	564.6	505.0	455.9	419.4	393.3	373.4	353.1	329.0	303.9
55°	537.6	542.2	502.4	450.9	404.7	373.9	350.1	333.5	316.2	295.9	276.5
57.5°	453.0	470.0	443.3	398.1	354.7	326.3	308.4	294.4	280.0	263.0	246.4
60°	402.5	416.7	401.6	361.9	323.9	297.5	280.8	270.0	255.5	240.1	227.4
62.5°	353.2	368.4	359.4	327.3	292.2	269.3	254.7	244.6	233.9	220.4	207.2
65°	291.3	301.1	296.8	274.6	249.7	230.2	216.7	209.3	199.4	189.6	177.8
67.5°	223.1	242.2	239.6	227.8	206.3	191.1	182.2	175.7	166.7	159.4	151.4
70°	183.4	201.0	200.7	191.1	179.4	165.2	159.1	153.5	145.4	138.4	131.9
72.5°	150.1	166.2	168.6	161.3	153.3	142.5	136.6	132.8	125.0	120.2	114.9
75°	105.1	116.8	119.9	119.9	116.2	110.7	105.4	103.0	97.4	93.1	90.0
77.5°	68.9	76.3	81.1	82.2	82.8	81.0	76.6	74.9	70.7	69.1	66.1
80°	48.7	53.6	59.2	61.0	62.6	61.9	60.1	58.9	54.9	53.3	52.1
82.5°	33.7	36.4	41.0	45.0	44.6	46.2	44.6	43.6	40.6	40.0	38.7
85°	17.6	17.9	18.5	21.2	22.8	23.4	23.8	23.1	22.2	22.2	20.0
87.5°	8.9	8.3	8.6	8.2	8.1	8.6	9.0	8.9	8.5	8.2	7.8
90°	14.6	13.2	11.8	10.1	8.2	6.3	4.3	2.4	4.3	6.3	8.2
92.5°	13.9	12.5	11.2	10.4	10.3	10.1	10.1	10.0	10.1	10.1	10.3
95°	17.0	16.9	16.7	19.6	25.6	31.5	37.5	43.5	37.5	31.5	25.6
97.5°	60.1	79.7	99.3	107.3	103.5	99.8	96.1	92.4	96.1	99.8	103.5
100°	83.3	107.6	131.8	142.4	139.2	136.0	132.8	129.7	132.8	136.0	139.2
102.5°	174.0	177.1	180.3	180.7	178.4	176.1	173.8	171.4	173.8	176.1	178.4
105°	244.9	244.1	243.2	242.2	241.2	240.1	239.1	238.1	239.1	240.1	241.2
107.5°	305.2	304.0	302.9	302.0	301.4	301.0	300.4	299.8	300.4	301.0	301.4
110°	346.7	345.5	344.5	343.7	343.2	342.7	342.1	341.7	342.1	342.7	343.2





TEST NUMBER: P332913-927

CATALOG NUMBER: S124RDIP-S575D1035U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	387.6	387.1	386.7	386.0	385.0	384.0	383.1	382.1	383.1	384.0	385.0
115°	446.4	446.6	446.7	446.6	446.0	445.5	445.0	444.4	445.0	445.5	446.0
117.5°	504.7	504.3	503.9	503.4	502.7	502.0	501.3	500.6	501.3	502.0	502.7
120°	541.3	541.5	541.6	541.4	540.7	540.0	539.2	538.5	539.2	540.0	540.7
122.5°	576.5	576.2	576.0	575.7	575.2	574.8	574.4	573.9	574.4	574.8	575.2
125°	627.0	627.4	627.7	627.6	626.9	626.1	625.4	624.7	625.4	626.1	626.9
127.5°	675.7	674.9	674.0	673.5	673.4	673.2	673.0	672.8	673.0	673.2	673.4
130°	705.9	705.4	704.9	704.5	704.3	704.2	704.0	703.9	704.0	704.2	704.3
132.5°	735.4	734.7	734.0	733.6	733.2	732.9	732.6	732.3	732.6	732.9	733.2
135°	775.9	775.2	774.5	774.3	774.4	774.7	774.8	775.0	774.8	774.7	774.4
137.5°	815.1	814.3	813.5	813.1	813.0	812.9	812.9	812.8	812.9	812.9	813.0
140°	840.0	839.6	839.2	838.8	838.5	838.2	837.8	837.5	837.8	838.2	838.5
142.5°	863.0	862.8	862.5	862.1	861.5	860.9	860.2	859.6	860.2	860.9	861.5
145°	896.0	896.0	896.0	895.7	895.2	894.7	894.1	893.6	894.1	894.7	895.2
147.5°	924.6	924.8	925.0	924.6	923.6	922.7	921.6	920.7	921.6	922.7	923.6
150°	943.0	943.2	943.3	943.1	942.4	941.7	941.0	940.2	941.0	941.7	942.4
152.5°	958.5	958.8	959.1	958.9	958.4	957.8	957.3	956.7	957.3	957.8	958.4
155°	979.3	979.9	980.3	980.5	980.3	980.2	980.0	979.9	980.0	980.2	980.3
157.5°	997.3	997.9	998.5	998.9	998.9	999.0	999.2	999.3	999.2	999.0	998.9
160°	1007.8	1008.1	1008.2	1008.5	1009.1	1009.6	1010.1	1010.7	1010.1	1009.6	1009.1
162.5°	1017.3	1017.5	1017.7	1018.1	1018.7	1019.5	1020.1	1020.8	1020.1	1019.5	1018.7
165°	1029.6	1029.6	1029.6	1030.1	1030.9	1031.8	1032.7	1033.6	1032.7	1031.8	1030.9
167.5°	1039.3	1039.4	1039.6	1040.1	1041.0	1041.9	1042.8	1043.7	1042.8	1041.9	1041.0
170°	1045.1	1044.9	1044.7	1045.2	1046.2	1047.3	1048.4	1049.4	1048.4	1047.3	1046.2
172.5°	1048.9	1048.7	1048.5	1049.0	1050.0	1051.1	1052.2	1053.2	1052.2	1051.1	1050.0
175°	1053.0	1052.8	1052.7	1053.1	1054.2	1055.2	1056.3	1057.3	1056.3	1055.2	1054.2
177.5°	1055.5	1055.2	1054.9	1055.3	1056.3	1057.2	1058.2	1059.2	1058.2	1057.2	1056.3
180°	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3



TEST NUMBER: P332913-927

CATALOG NUMBER: S124RDIP-S575D1035U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0
2.5°	751.2	748.8	745.5	741.8	737.4	733.5	731.7	733.2	734.0	732.0	731.7
5°	728.3	720.6	714.5	705.2	697.8	691.7	687.3	685.5	686.1	681.2	679.9
7.5°	702.6	693.5	683.4	672.4	662.2	653.2	648.4	645.8	640.6	638.3	634.5
10°	686.1	673.8	663.9	650.9	639.3	628.4	623.2	618.9	613.7	611.2	605.9
12.5°	669.1	654.8	644.0	630.5	618.5	605.5	600.6	592.6	584.3	579.2	572.4
15°	645.1	627.9	614.6	598.6	584.4	569.6	556.3	541.5	536.0	524.3	517.5
17.5°	617.0	599.5	583.1	561.7	539.8	521.4	507.2	493.1	484.6	477.1	473.6
20°	598.6	582.6	559.8	534.8	510.4	490.0	478.6	469.4	460.2	455.0	451.2
22.5°	581.1	560.6	534.1	507.2	482.8	466.9	457.2	447.7	440.2	435.2	430.3
25°	551.8	524.9	496.9	466.0	449.4	435.5	425.0	417.3	412.7	406.2	403.8
27.5°	521.6	489.1	458.1	437.4	420.1	407.4	398.3	392.5	386.7	382.5	379.3
30°	498.4	465.4	437.7	418.0	400.4	389.9	382.5	375.7	371.1	367.7	365.3
32.5°	475.5	442.5	419.1	398.0	384.1	373.9	366.0	360.9	357.3	352.9	351.4
35°	442.3	413.0	392.7	373.6	359.4	350.1	344.0	338.7	335.6	334.5	333.5
37.5°	410.4	386.4	364.6	348.9	336.3	329.0	321.7	319.2	317.0	314.8	315.8
40°	390.2	367.7	348.3	331.7	321.5	313.5	309.1	306.1	304.2	304.2	304.2
42.5°	372.7	350.7	331.8	316.9	306.7	299.9	295.1	292.5	291.9	291.6	293.1
45°	345.5	325.2	306.1	293.7	285.1	278.3	275.5	273.4	273.4	274.6	275.0
47.5°	318.6	299.5	284.2	270.4	262.4	258.3	255.8	254.7	254.8	256.0	257.5
50°	302.1	283.3	268.2	255.8	248.4	244.4	242.2	241.6	242.2	242.2	244.4
52.5°	284.1	267.2	252.4	242.0	233.6	229.9	228.7	227.8	228.2	229.2	230.1
55°	257.7	242.6	228.4	218.6	212.4	209.9	207.2	207.5	206.8	207.5	207.5
57.5°	231.2	217.7	204.5	196.6	191.2	187.7	184.7	185.4	184.6	184.4	183.9
60°	214.2	199.4	188.9	181.9	175.7	172.6	169.8	170.5	169.5	168.9	167.7
62.5°	195.7	183.4	173.4	166.6	161.6	158.0	155.3	154.6	152.5	150.4	147.7
65°	168.9	158.8	149.8	143.3	138.7	135.9	133.8	131.9	127.3	122.4	119.9
67.5°	142.8	135.5	127.1	121.7	118.0	114.3	110.2	107.0	102.7	100.0	98.5
70°	126.0	119.0	111.9	106.6	102.7	99.3	94.6	92.4	89.4	88.2	86.6
72.5°	110.0	103.5	96.8	92.1	87.9	85.2	81.6	79.4	78.0	77.6	76.0
75°	85.7	80.5	75.5	71.2	67.8	66.0	64.4	62.9	62.3	59.5	57.9
77.5°	62.5	59.0	56.0	52.9	50.5	49.3	46.3	44.5	43.5	42.1	41.8
80°	48.7	46.3	43.2	41.3	37.9	36.7	35.4	35.2	34.9	34.5	34.2
82.5°	36.6	34.1	31.1	29.9	29.1	28.3	27.6	27.3	26.9	27.1	27.1
85°	18.5	17.3	17.3	17.0	16.6	16.3	16.0	16.0	15.7	16.0	15.7
87.5°	8.2	8.2	8.6	8.3	8.9	9.2	9.1	9.3	9.8	9.5	9.7
90°	10.1	11.8	13.2	14.6	16.0	17.4	18.5	19.5	20.6	21.6	22.3
92.5°	10.4	11.2	12.5	13.9	15.4	16.8	17.8	18.9	20.0	21.0	21.5
95°	19.6	16.7	16.9	17.0	17.2	17.4	18.5	19.5	20.6	21.6	22.3
97.5°	107.3	99.3	79.7	60.1	40.5	20.9	21.0	21.1	21.2	21.3	21.5
100°	142.4	131.8	107.6	83.3	59.0	34.8	31.8	28.8	25.8	22.8	21.5
102.5°	180.7	180.3	177.1	174.0	170.8	167.6	135.4	103.2	71.0	38.7	22.7
105°	242.2	243.2	244.1	244.9	245.9	246.8	248.3	249.9	251.4	253.0	250.7
107.5°	302.0	302.9	304.0	305.2	306.4	307.6	308.4	309.2	310.0	310.7	311.4
110°	343.7	344.5	345.5	346.7	347.7	348.7	349.1	349.4	349.8	350.1	350.6



TEST NUMBER: P332913-927

CATALOG NUMBER: S124RDIP-S575D1035U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	386.0	386.7	387.1	387.6	388.1	388.6	388.6	388.5	388.4	388.3	388.6
115°	446.6	446.7	446.6	446.4	446.2	446.0	446.4	446.7	447.1	447.4	447.6
117.5°	503.4	503.9	504.3	504.7	505.1	505.5	505.4	505.3	505.3	505.2	505.2
120°	541.4	541.6	541.5	541.3	541.1	540.9	541.3	541.6	541.9	542.3	542.3
122.5°	575.7	576.0	576.2	576.5	576.7	576.9	577.2	577.4	577.6	577.8	577.7
125°	627.6	627.7	627.4	627.0	626.7	626.3	626.9	627.4	627.9	628.4	628.8
127.5°	673.5	674.0	674.9	675.7	676.4	677.2	677.2	677.1	676.9	676.8	676.7
130°	704.5	704.9	705.4	705.9	706.5	707.0	707.2	707.3	707.5	707.7	707.8
132.5°	733.6	734.0	734.7	735.4	736.0	736.7	736.9	737.0	737.3	737.4	737.4
135°	774.3	774.5	775.2	775.9	776.7	777.4	777.7	778.1	778.4	778.8	779.1
137.5°	813.1	813.5	814.3	815.1	815.8	816.6	817.0	817.4	817.8	818.2	818.2
140°	838.8	839.2	839.6	840.0	840.3	840.7	841.1	841.7	842.2	842.7	843.1
142.5°	862.1	862.5	862.8	863.0	863.2	863.4	863.8	864.2	864.6	865.0	865.1
145°	895.7	896.0	896.0	896.0	896.0	896.0	896.2	896.4	896.5	896.7	897.0
147.5°	924.6	925.0	924.8	924.6	924.5	924.3	924.5	924.6	924.7	924.9	925.0
150°	943.1	943.3	943.2	943.0	942.9	942.6	942.6	942.6	942.6	942.6	942.7
152.5°	958.9	959.1	958.8	958.5	958.1	957.8	958.1	958.4	958.7	958.9	959.0
155°	980.5	980.3	979.9	979.3	978.7	978.3	978.9	979.6	980.3	981.0	981.1
157.5°	998.9	998.5	997.9	997.3	996.7	996.1	997.0	997.9	998.9	999.7	999.7
160°	1008.5	1008.2	1008.1	1007.8	1007.7	1007.5	1008.5	1009.6	1010.7	1011.7	1011.7
162.5°	1018.1	1017.7	1017.5	1017.3	1017.2	1017.0	1018.0	1019.1	1020.2	1021.2	1021.1
165°	1030.1	1029.6	1029.6	1029.6	1029.6	1029.6	1031.0	1032.5	1033.9	1035.2	1035.1
167.5°	1040.1	1039.6	1039.4	1039.3	1039.3	1039.1	1040.7	1042.2	1043.8	1045.3	1045.2
170°	1045.2	1044.7	1044.9	1045.1	1045.3	1045.4	1046.9	1048.3	1049.6	1051.1	1050.9
172.5°	1049.0	1048.5	1048.7	1048.9	1049.1	1049.2	1050.7	1052.1	1053.4	1054.9	1054.6
175°	1053.1	1052.7	1052.8	1053.0	1053.2	1053.4	1054.9	1056.5	1058.1	1059.7	1059.4
177.5°	1055.3	1054.9	1055.2	1055.5	1055.7	1056.1	1057.2	1058.3	1059.4	1060.6	1060.3
180°	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3



TEST NUMBER: P332913-927

CATALOG NUMBER: S124RDIP-S575D1035U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0
2.5°	730.2	730.7	729.0	728.5	729.0	730.7	730.2	731.7	732.0	734.0	733.2
5°	677.5	676.8	675.3	675.7	675.3	676.8	677.5	679.9	681.2	686.1	685.5
7.5°	632.3	629.9	630.7	628.1	630.7	629.9	632.3	634.5	638.3	640.6	645.8
10°	604.8	601.3	598.6	596.1	598.6	601.3	604.8	605.9	611.2	613.7	618.9
12.5°	567.0	564.1	560.3	561.1	560.3	564.1	567.0	572.4	579.2	584.3	592.6
15°	513.5	508.9	501.5	502.4	501.5	508.9	513.5	517.5	524.3	536.0	541.5
17.5°	468.2	468.3	464.9	465.6	464.9	468.3	468.2	473.6	477.1	484.6	493.1
20°	444.7	442.6	442.9	442.0	442.9	442.6	444.7	451.2	455.0	460.2	469.4
22.5°	428.5	425.9	423.7	421.8	423.7	425.9	428.5	430.3	435.2	440.2	447.7
25°	401.0	399.2	396.4	395.8	396.4	399.2	401.0	403.8	406.2	412.7	417.3
27.5°	376.8	376.4	375.3	373.9	375.3	376.4	376.8	379.3	382.5	386.7	392.5
30°	362.7	362.2	361.6	360.6	361.6	362.2	362.7	365.3	367.7	371.1	375.7
32.5°	350.2	349.8	349.2	349.3	349.2	349.8	350.2	351.4	352.9	357.3	360.9
35°	332.2	331.9	331.4	331.1	331.4	331.9	332.2	333.5	334.5	335.6	338.7
37.5°	315.5	316.3	315.9	315.8	315.9	316.3	315.5	315.8	314.8	317.0	319.2
40°	303.9	304.2	304.8	304.5	304.8	304.2	303.9	304.2	304.2	304.2	306.1
42.5°	294.3	294.4	295.2	294.1	295.2	294.4	294.3	293.1	291.6	291.9	292.5
45°	277.1	278.9	278.6	278.6	278.6	278.9	277.1	275.0	274.6	273.4	273.4
47.5°	258.3	259.9	260.3	260.2	260.3	259.9	258.3	257.5	256.0	254.8	254.7
50°	246.0	245.3	246.3	246.0	246.3	245.3	246.0	244.4	242.2	242.2	241.6
52.5°	230.9	231.1	231.0	230.7	231.0	231.1	230.9	230.1	229.2	228.2	227.8
55°	207.7	208.0	207.5	207.7	207.5	208.0	207.7	207.5	207.5	206.8	207.5
57.5°	182.6	181.1	181.7	181.0	181.7	181.1	182.6	183.9	184.4	184.6	185.4
60°	164.6	162.2	161.5	160.3	161.5	162.2	164.6	167.7	168.9	169.5	170.5
62.5°	144.3	142.7	140.5	141.6	140.5	142.7	144.3	147.7	150.4	152.5	154.6
65°	117.4	116.2	115.3	116.5	115.3	116.2	117.4	119.9	122.4	127.3	131.9
67.5°	97.2	96.6	96.6	95.9	96.6	96.6	97.2	98.5	100.0	102.7	107.0
70°	86.6	85.7	85.7	85.1	85.7	85.7	86.6	86.6	88.2	89.4	92.4
72.5°	75.7	74.9	75.1	74.7	75.1	74.9	75.7	76.0	77.6	78.0	79.4
75°	56.1	54.6	54.6	54.9	54.6	54.6	56.1	57.9	59.5	62.3	62.9
77.5°	41.8	41.5	42.0	41.4	42.0	41.5	41.8	41.8	42.1	43.5	44.5
80°	34.2	33.9	33.6	34.5	33.6	33.9	34.2	34.2	34.5	34.9	35.2
82.5°	26.5	26.5	26.5	27.6	26.5	26.5	26.5	27.1	27.1	26.9	27.3
85°	16.0	15.4	16.0	15.4	16.0	15.4	16.0	15.7	16.0	15.7	16.0
87.5°	10.2	10.1	9.8	10.1	9.8	10.1	10.2	9.7	9.5	9.8	9.3
90°	22.7	23.1	23.4	23.7	23.4	23.1	22.7	22.3	21.6	20.6	19.5
92.5°	21.6	21.7	21.8	21.9	21.8	21.7	21.6	21.5	21.0	20.0	18.9
95°	22.4	22.6	22.7	22.9	22.7	22.6	22.4	22.3	21.6	20.6	19.5
97.5°	21.6	21.8	21.9	22.2	21.9	21.8	21.6	21.5	21.3	21.2	21.1
100°	21.6	21.8	21.9	22.2	21.9	21.8	21.6	21.5	22.8	25.8	28.8
102.5°	22.7	22.7	22.7	22.8	22.7	22.7	22.7	22.7	38.7	71.0	103.2
105°	244.4	238.1	231.7	225.4	231.7	238.1	244.4	250.7	253.0	251.4	249.9
107.5°	312.1	312.8	313.5	314.1	313.5	312.8	312.1	311.4	310.7	310.0	309.2
110°	351.1	351.6	352.2	352.7	352.2	351.6	351.1	350.6	350.1	349.8	349.4



TEST NUMBER: P332913-927

CATALOG NUMBER: S124RDIP-S575D1035U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	389.3	390.0	390.6	391.3	390.6	390.0	389.3	388.6	388.3	388.4	388.5
115°	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.4	447.1	446.7
117.5°	505.1	505.0	504.9	504.9	504.9	505.0	505.1	505.2	505.2	505.3	505.3
120°	541.9	541.6	541.3	540.9	541.3	541.6	541.9	542.3	542.3	541.9	541.6
122.5°	577.4	577.0	576.7	576.3	576.7	577.0	577.4	577.7	577.8	577.6	577.4
125°	629.0	629.2	629.3	629.5	629.3	629.2	629.0	628.8	628.4	627.9	627.4
127.5°	676.6	676.4	676.3	676.1	676.3	676.4	676.6	676.7	676.8	676.9	677.1
130°	707.8	707.8	707.8	707.8	707.8	707.8	707.8	707.8	707.7	707.5	707.3
132.5°	737.3	737.1	737.0	736.9	737.0	737.1	737.3	737.4	737.4	737.3	737.0
135°	779.5	779.8	780.1	780.5	780.1	779.8	779.5	779.1	778.8	778.4	778.1
137.5°	818.2	818.1	817.9	817.8	817.9	818.1	818.2	818.2	818.2	817.8	817.4
140°	843.3	843.4	843.6	843.8	843.6	843.4	843.3	843.1	842.7	842.2	841.7
142.5°	865.2	865.2	865.3	865.3	865.3	865.2	865.2	865.1	865.0	864.6	864.2
145°	897.3	897.6	898.0	898.3	898.0	897.6	897.3	897.0	896.7	896.5	896.4
147.5°	925.2	925.3	925.6	925.7	925.6	925.3	925.2	925.0	924.9	924.7	924.6
150°	942.9	943.1	943.3	943.4	943.3	943.1	942.9	942.7	942.6	942.6	942.6
152.5°	958.9	958.9	958.7	958.6	958.7	958.9	958.9	959.0	958.9	958.7	958.4
155°	980.6	980.1	979.5	979.1	979.5	980.1	980.6	981.1	981.0	980.3	979.6
157.5°	998.9	997.9	997.0	996.1	997.0	997.9	998.9	999.7	999.7	998.9	997.9
160°	1010.7	1009.6	1008.5	1007.5	1008.5	1009.6	1010.7	1011.7	1011.7	1010.7	1009.6
162.5°	1019.9	1018.7	1017.6	1016.4	1017.6	1018.7	1019.9	1021.1	1021.2	1020.2	1019.1
165°	1033.6	1032.0	1030.4	1028.8	1030.4	1032.0	1033.6	1035.1	1035.2	1033.9	1032.5
167.5°	1043.5	1041.7	1039.9	1038.2	1039.9	1041.7	1043.5	1045.2	1045.3	1043.8	1042.2
170°	1049.2	1047.4	1045.6	1043.9	1045.6	1047.4	1049.2	1050.9	1051.1	1049.6	1048.3
172.5°	1052.7	1050.8	1048.9	1047.0	1048.9	1050.8	1052.7	1054.6	1054.9	1053.4	1052.1
175°	1057.3	1055.2	1053.1	1051.0	1053.1	1055.2	1057.3	1059.4	1059.7	1058.1	1056.5
177.5°	1058.6	1056.9	1055.2	1053.5	1055.2	1056.9	1058.6	1060.3	1060.6	1059.4	1058.3
180°	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3



TEST NUMBER: P332913-927

CATALOG NUMBER: S124RDIP-S575D1035U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0
2.5°	731.7	733.5	737.4	741.8	745.5	748.8	751.2	754.6	757.9	762.3	766.5
5°	687.3	691.7	697.8	705.2	714.5	720.6	728.3	735.1	745.0	754.9	764.4
7.5°	648.4	653.2	662.2	672.4	683.4	693.5	702.6	714.5	727.6	742.0	758.0
10°	623.2	628.4	639.3	650.9	663.9	673.8	686.1	700.3	715.1	732.6	752.3
12.5°	600.6	605.5	618.5	630.5	644.0	654.8	669.1	683.5	703.2	722.3	744.7
15°	556.3	569.6	584.4	598.6	614.6	627.9	645.1	659.9	678.7	705.5	731.1
17.5°	507.2	521.4	539.8	561.7	583.1	599.5	617.0	635.4	657.8	685.2	714.7
20°	478.6	490.0	510.4	534.8	559.8	582.6	598.6	618.9	642.1	671.6	702.1
22.5°	457.2	466.9	482.8	507.2	534.1	560.6	581.1	601.2	626.8	656.3	689.6
25°	425.0	435.5	449.4	466.0	496.9	524.9	551.8	574.8	602.0	631.5	668.5
27.5°	398.3	407.4	420.1	437.4	458.1	489.1	521.6	548.0	575.8	607.5	644.5
30°	382.5	389.9	400.4	418.0	437.7	465.4	498.4	529.3	557.3	590.3	628.8
32.5°	366.0	373.9	384.1	398.0	419.1	442.5	475.5	509.2	539.0	572.7	610.5
35°	344.0	350.1	359.4	373.6	392.7	413.0	442.3	477.1	508.6	544.6	580.7
37.5°	321.7	329.0	336.3	348.9	364.6	386.4	410.4	446.0	480.9	513.7	549.0
40°	309.1	313.5	321.5	331.7	348.3	367.7	390.2	425.0	459.9	492.6	528.0
42.5°	295.1	299.9	306.7	316.9	331.8	350.7	372.7	402.8	439.2	470.9	503.1
45°	275.5	278.3	285.1	293.7	306.1	325.2	345.5	372.3	406.5	436.7	465.1
47.5°	255.8	258.3	262.4	270.4	284.2	299.5	318.6	342.6	372.6	402.8	426.8
50°	242.2	244.4	248.4	255.8	268.2	283.3	302.1	323.6	350.5	379.5	399.4
52.5°	228.7	229.9	233.6	242.0	252.4	267.2	284.1	303.9	329.0	353.1	373.4
55°	207.2	209.9	212.4	218.6	228.4	242.6	257.7	276.5	295.9	316.2	333.5
57.5°	184.7	187.7	191.2	196.6	204.5	217.7	231.2	246.4	263.0	280.0	294.4
60°	169.8	172.6	175.7	181.9	188.9	199.4	214.2	227.4	240.1	255.5	270.0
62.5°	155.3	158.0	161.6	166.6	173.4	183.4	195.7	207.2	220.4	233.9	244.6
65°	133.8	135.9	138.7	143.3	149.8	158.8	168.9	177.8	189.6	199.4	209.3
67.5°	110.2	114.3	118.0	121.7	127.1	135.5	142.8	151.4	159.4	166.7	175.7
70°	94.6	99.3	102.7	106.6	111.9	119.0	126.0	131.9	138.4	145.4	153.5
72.5°	81.6	85.2	87.9	92.1	96.8	103.5	110.0	114.9	120.2	125.0	132.8
75°	64.4	66.0	67.8	71.2	75.5	80.5	85.7	90.0	93.1	97.4	103.0
77.5°	46.3	49.3	50.5	52.9	56.0	59.0	62.5	66.1	69.1	70.7	74.9
80°	35.4	36.7	37.9	41.3	43.2	46.3	48.7	52.1	53.3	54.9	58.9
82.5°	27.6	28.3	29.1	29.9	31.1	34.1	36.6	38.7	40.0	40.6	43.6
85°	16.0	16.3	16.6	17.0	17.3	17.3	18.5	20.0	22.2	22.2	23.1
87.5°	9.1	9.2	8.9	8.3	8.6	8.2	8.2	7.8	8.2	8.5	8.9
90°	18.5	17.4	16.0	14.6	13.2	11.8	10.1	8.2	6.3	4.3	2.4
92.5°	17.8	16.8	15.4	13.9	12.5	11.2	10.4	10.3	10.1	10.1	10.0
95°	18.5	17.4	17.2	17.0	16.9	16.7	19.6	25.6	31.5	37.5	43.5
97.5°	21.0	20.9	40.5	60.1	79.7	99.3	107.3	103.5	99.8	96.1	92.4
100°	31.8	34.8	59.0	83.3	107.6	131.8	142.4	139.2	136.0	132.8	129.7
102.5°	135.4	167.6	170.8	174.0	177.1	180.3	180.7	178.4	176.1	173.8	171.4
105°	248.3	246.8	245.9	244.9	244.1	243.2	242.2	241.2	240.1	239.1	238.1
107.5°	308.4	307.6	306.4	305.2	304.0	302.9	302.0	301.4	301.0	300.4	299.8
110°	349.1	348.7	347.7	346.7	345.5	344.5	343.7	343.2	342.7	342.1	341.7



TEST NUMBER: P332913-927

CATALOG NUMBER: S124RDIP-S575D1035U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	388.6	388.6	388.1	387.6	387.1	386.7	386.0	385.0	384.0	383.1	382.1
115°	446.4	446.0	446.2	446.4	446.6	446.7	446.6	446.0	445.5	445.0	444.4
117.5°	505.4	505.5	505.1	504.7	504.3	503.9	503.4	502.7	502.0	501.3	500.6
120°	541.3	540.9	541.1	541.3	541.5	541.6	541.4	540.7	540.0	539.2	538.5
122.5°	577.2	576.9	576.7	576.5	576.2	576.0	575.7	575.2	574.8	574.4	573.9
125°	626.9	626.3	626.7	627.0	627.4	627.7	627.6	626.9	626.1	625.4	624.7
127.5°	677.2	677.2	676.4	675.7	674.9	674.0	673.5	673.4	673.2	673.0	672.8
130°	707.2	707.0	706.5	705.9	705.4	704.9	704.5	704.3	704.2	704.0	703.9
132.5°	736.9	736.7	736.0	735.4	734.7	734.0	733.6	733.2	732.9	732.6	732.3
135°	777.7	777.4	776.7	775.9	775.2	774.5	774.3	774.4	774.7	774.8	775.0
137.5°	817.0	816.6	815.8	815.1	814.3	813.5	813.1	813.0	812.9	812.9	812.8
140°	841.1	840.7	840.3	840.0	839.6	839.2	838.8	838.5	838.2	837.8	837.5
142.5°	863.8	863.4	863.2	863.0	862.8	862.5	862.1	861.5	860.9	860.2	859.6
145°	896.2	896.0	896.0	896.0	896.0	896.0	895.7	895.2	894.7	894.1	893.6
147.5°	924.5	924.3	924.5	924.6	924.8	925.0	924.6	923.6	922.7	921.6	920.7
150°	942.6	942.6	942.9	943.0	943.2	943.3	943.1	942.4	941.7	941.0	940.2
152.5°	958.1	957.8	958.1	958.5	958.8	959.1	958.9	958.4	957.8	957.3	956.7
155°	978.9	978.3	978.7	979.3	979.9	980.3	980.5	980.3	980.2	980.0	979.9
157.5°	997.0	996.1	996.7	997.3	997.9	998.5	998.9	998.9	999.0	999.2	999.3
160°	1008.5	1007.5	1007.7	1007.8	1008.1	1008.2	1008.5	1009.1	1009.6	1010.1	1010.7
162.5°	1018.0	1017.0	1017.2	1017.3	1017.5	1017.7	1018.1	1018.7	1019.5	1020.1	1020.8
165°	1031.0	1029.6	1029.6	1029.6	1029.6	1029.6	1030.1	1030.9	1031.8	1032.7	1033.6
167.5°	1040.7	1039.1	1039.3	1039.3	1039.4	1039.6	1040.1	1041.0	1041.9	1042.8	1043.7
170°	1046.9	1045.4	1045.3	1045.1	1044.9	1044.7	1045.2	1046.2	1047.3	1048.4	1049.4
172.5°	1050.7	1049.2	1049.1	1048.9	1048.7	1048.5	1049.0	1050.0	1051.1	1052.2	1053.2
175°	1054.9	1053.4	1053.2	1053.0	1052.8	1052.7	1053.1	1054.2	1055.2	1056.3	1057.3
177.5°	1057.2	1056.1	1055.7	1055.5	1055.2	1054.9	1055.3	1056.3	1057.2	1058.2	1059.2
180°	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3



TEST NUMBER: P332913-927

CATALOG NUMBER: S124RDIP-S575D1035U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0
2.5°	769.7	771.9	774.4	779.0	783.0	784.7	788.2	790.7	789.9	793.4	799.3
5°	772.7	781.0	790.6	800.4	811.5	820.8	828.2	835.6	841.5	848.5	859.0
7.5°	772.2	787.0	803.1	820.8	839.0	854.7	869.3	884.1	897.1	911.6	930.3
10°	770.2	790.0	810.0	833.1	856.3	878.1	897.9	916.3	933.9	952.7	976.4
12.5°	768.0	790.7	814.9	842.7	871.6	897.9	921.1	947.7	969.6	993.9	1021.4
15°	758.2	788.8	821.7	857.8	892.3	927.7	959.5	992.2	1022.7	1051.6	1086.2
17.5°	747.0	782.2	821.1	863.7	905.2	948.2	986.0	1027.1	1058.3	1097.2	1129.3
20°	737.9	775.8	817.4	865.1	912.4	960.1	1001.7	1043.6	1078.8	1117.9	1158.6
22.5°	726.8	768.4	813.5	862.9	912.4	964.6	1010.6	1052.3	1095.8	1139.9	1181.8
25°	708.9	752.1	799.9	854.1	910.8	964.1	1013.4	1065.2	1112.1	1159.8	1197.5
27.5°	687.0	732.3	782.7	838.6	896.8	951.4	1009.5	1064.7	1111.8	1157.8	1190.6
30°	669.5	717.2	765.6	822.4	882.7	941.4	1003.5	1058.8	1108.3	1149.7	1168.2
32.5°	651.5	696.8	746.6	804.1	866.0	929.0	990.8	1047.2	1093.1	1117.8	1118.3
35°	620.1	662.7	714.5	770.9	834.3	902.8	965.4	1020.8	1048.8	1051.1	1020.8
37.5°	586.0	625.0	673.9	730.4	799.9	868.0	931.8	968.8	978.3	946.9	891.0
40°	561.6	597.6	644.8	702.7	771.8	842.1	900.3	927.4	917.6	866.7	804.5
42.5°	535.9	569.5	615.0	672.2	741.5	812.5	862.1	876.6	850.5	791.8	718.9
45°	494.1	524.9	569.9	627.6	694.1	760.7	798.3	790.9	747.4	677.8	596.1
47.5°	450.5	480.3	520.8	574.1	642.3	699.7	725.2	702.9	641.0	564.4	498.0
50°	421.7	452.2	489.5	540.3	602.6	658.1	674.4	640.5	571.7	498.1	437.0
52.5°	393.3	419.4	455.9	505.0	564.6	611.5	620.1	581.1	510.1	444.1	390.0
55°	350.1	373.9	404.7	450.9	502.4	542.2	537.6	487.3	422.9	366.5	323.9
57.5°	308.4	326.3	354.7	398.1	443.3	470.0	453.0	410.3	350.2	304.0	268.2
60°	280.8	297.5	323.9	361.9	401.6	416.7	402.5	356.0	308.6	266.3	236.1
62.5°	254.7	269.3	292.2	327.3	359.4	368.4	353.2	312.6	269.8	233.8	208.7
65°	216.7	230.2	249.7	274.6	296.8	301.1	291.3	249.7	217.3	187.1	169.8
67.5°	182.2	191.1	206.3	227.8	239.6	242.2	223.1	196.9	168.4	149.9	136.9
70°	159.1	165.2	179.4	191.1	200.7	201.0	183.4	162.4	140.5	125.5	115.9
72.5°	136.6	142.5	153.3	161.3	168.6	166.2	150.1	133.6	115.9	104.5	97.4
75°	105.4	110.7	116.2	119.9	119.9	116.8	105.1	92.8	82.6	75.8	73.7
77.5°	76.6	81.0	82.8	82.2	81.1	76.3	68.9	60.8	57.2	54.0	52.4
80°	60.1	61.9	62.6	61.0	59.2	53.6	48.7	45.3	41.9	40.7	40.1
82.5°	44.6	46.2	44.6	45.0	41.0	36.4	33.7	32.5	31.1	30.6	29.9
85°	23.8	23.4	22.8	21.2	18.5	17.9	17.6	17.3	16.6	17.0	16.3
87.5°	9.0	8.6	8.1	8.2	8.6	8.3	8.9	9.1	9.4	9.3	10.1
90°	4.3	6.3	8.2	10.1	11.8	13.2	14.6	16.0	17.4	18.5	19.5
92.5°	10.1	10.1	10.3	10.4	11.2	12.5	13.9	15.4	16.8	17.8	18.9
95°	37.5	31.5	25.6	19.6	16.7	16.9	17.0	17.2	17.4	18.5	19.5
97.5°	96.1	99.8	103.5	107.3	99.3	79.7	60.1	40.5	20.9	21.0	21.1
100°	132.8	136.0	139.2	142.4	131.8	107.6	83.3	59.0	34.8	31.8	28.8
102.5°	173.8	176.1	178.4	180.7	180.3	177.1	174.0	170.8	167.6	135.4	103.2
105°	239.1	240.1	241.2	242.2	243.2	244.1	244.9	245.9	246.8	248.3	249.9
107.5°	300.4	301.0	301.4	302.0	302.9	304.0	305.2	306.4	307.6	308.4	309.2
110°	342.1	342.7	343.2	343.7	344.5	345.5	346.7	347.7	348.7	349.1	349.4





TEST NUMBER: P332913-927

CATALOG NUMBER: S124RDIP-S575D1035U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	383.1	384.0	385.0	386.0	386.7	387.1	387.6	388.1	388.6	388.6	388.5
115°	445.0	445.5	446.0	446.6	446.7	446.6	446.4	446.2	446.0	446.4	446.7
117.5°	501.3	502.0	502.7	503.4	503.9	504.3	504.7	505.1	505.5	505.4	505.3
120°	539.2	540.0	540.7	541.4	541.6	541.5	541.3	541.1	540.9	541.3	541.6
122.5°	574.4	574.8	575.2	575.7	576.0	576.2	576.5	576.7	576.9	577.2	577.4
125°	625.4	626.1	626.9	627.6	627.7	627.4	627.0	626.7	626.3	626.9	627.4
127.5°	673.0	673.2	673.4	673.5	674.0	674.9	675.7	676.4	677.2	677.2	677.1
130°	704.0	704.2	704.3	704.5	704.9	705.4	705.9	706.5	707.0	707.2	707.3
132.5°	732.6	732.9	733.2	733.6	734.0	734.7	735.4	736.0	736.7	736.9	737.0
135°	774.8	774.7	774.4	774.3	774.5	775.2	775.9	776.7	777.4	777.7	778.1
137.5°	812.9	812.9	813.0	813.1	813.5	814.3	815.1	815.8	816.6	817.0	817.4
140°	837.8	838.2	838.5	838.8	839.2	839.6	840.0	840.3	840.7	841.1	841.7
142.5°	860.2	860.9	861.5	862.1	862.5	862.8	863.0	863.2	863.4	863.8	864.2
145°	894.1	894.7	895.2	895.7	896.0	896.0	896.0	896.0	896.0	896.2	896.4
147.5°	921.6	922.7	923.6	924.6	925.0	924.8	924.6	924.5	924.3	924.5	924.6
150°	941.0	941.7	942.4	943.1	943.3	943.2	943.0	942.9	942.6	942.6	942.6
152.5°	957.3	957.8	958.4	958.9	959.1	958.8	958.5	958.1	957.8	958.1	958.4
155°	980.0	980.2	980.3	980.5	980.3	979.9	979.3	978.7	978.3	978.9	979.6
157.5°	999.2	999.0	998.9	998.9	998.5	997.9	997.3	996.7	996.1	997.0	997.9
160°	1010.1	1009.6	1009.1	1008.5	1008.2	1008.1	1007.8	1007.7	1007.5	1008.5	1009.6
162.5°	1020.1	1019.5	1018.7	1018.1	1017.7	1017.5	1017.3	1017.2	1017.0	1018.0	1019.1
165°	1032.7	1031.8	1030.9	1030.1	1029.6	1029.6	1029.6	1029.6	1029.6	1031.0	1032.5
167.5°	1042.8	1041.9	1041.0	1040.1	1039.6	1039.4	1039.3	1039.3	1039.1	1040.7	1042.2
170°	1048.4	1047.3	1046.2	1045.2	1044.7	1044.9	1045.1	1045.3	1045.4	1046.9	1048.3
172.5°	1052.2	1051.1	1050.0	1049.0	1048.5	1048.7	1048.9	1049.1	1049.2	1050.7	1052.1
175°	1056.3	1055.2	1054.2	1053.1	1052.7	1052.8	1053.0	1053.2	1053.4	1054.9	1056.5
177.5°	1058.2	1057.2	1056.3	1055.3	1054.9	1055.2	1055.5	1055.7	1056.1	1057.2	1058.3
180°	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3



TEST NUMBER: P332913-927

CATALOG NUMBER: S124RDIP-S575D1035U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	765.0	765.0	765.0	765.0	765.0	765.0	765.0
2.5°	802.5	803.5	804.2	806.7	806.9	809.1	806.9
5°	868.9	873.2	880.0	886.8	887.4	891.7	884.0
7.5°	943.3	953.3	959.6	970.5	974.9	977.6	973.1
10°	994.7	1003.9	1020.3	1028.3	1036.3	1037.4	1033.8
12.5°	1044.2	1058.8	1071.7	1087.0	1086.6	1097.4	1093.4
15°	1110.2	1125.3	1143.2	1160.2	1166.3	1166.3	1171.2
17.5°	1157.3	1185.0	1203.5	1216.8	1231.4	1233.9	1232.2
20°	1189.1	1219.0	1238.7	1256.0	1265.9	1268.7	1268.7
22.5°	1212.8	1238.3	1257.5	1273.0	1281.2	1284.4	1283.4
25°	1229.2	1251.1	1262.8	1267.4	1269.6	1268.9	1263.1
27.5°	1206.7	1205.8	1198.3	1184.2	1173.5	1167.0	1159.7
30°	1163.9	1147.8	1129.3	1109.0	1082.8	1062.7	1056.6
32.5°	1100.0	1064.0	1032.7	998.8	970.6	950.5	942.1
35°	976.4	919.4	872.9	832.2	802.6	784.1	777.9
37.5°	829.9	774.7	717.1	677.6	653.1	634.4	627.4
40°	736.7	676.5	626.3	589.3	564.0	545.9	545.6
42.5°	651.6	594.2	546.9	520.3	493.1	481.0	480.9
45°	533.5	487.6	447.5	426.6	410.3	400.4	397.6
47.5°	441.7	403.8	377.1	360.4	347.1	340.8	336.7
50°	390.2	357.0	335.6	321.2	313.8	305.8	305.1
52.5°	347.3	320.4	303.9	292.1	282.7	277.9	278.1
55°	291.9	270.6	258.9	249.9	242.6	238.8	237.3
57.5°	245.9	230.0	221.4	213.3	210.1	207.2	206.4
60°	217.3	206.5	198.5	192.0	187.4	186.5	186.2
62.5°	193.6	182.4	176.8	171.8	168.4	167.0	166.4
65°	159.6	151.3	146.4	142.4	141.2	139.0	138.7
67.5°	128.7	123.7	120.5	117.7	116.0	115.9	115.9
70°	109.7	106.9	104.2	102.7	101.7	101.1	101.1
72.5°	93.5	91.4	89.1	88.3	88.2	87.5	87.3
75°	71.2	69.1	69.3	67.8	66.5	65.0	64.1
77.5°	50.5	49.0	48.6	48.5	47.4	47.2	47.7
80°	39.1	37.6	37.3	37.6	37.3	36.4	36.4
82.5°	29.8	28.5	28.2	28.0	27.6	28.0	27.5
85°	16.0	15.4	15.4	15.4	16.0	15.7	15.4
87.5°	9.8	9.7	10.1	10.0	10.1	9.8	10.1
90°	20.6	21.6	22.3	22.7	23.1	23.4	23.7
92.5°	20.0	21.0	21.5	21.6	21.7	21.8	21.9
95°	20.6	21.6	22.3	22.4	22.6	22.7	22.9
97.5°	21.2	21.3	21.5	21.6	21.8	21.9	22.2
100°	25.8	22.8	21.5	21.6	21.8	21.9	22.2
102.5°	71.0	38.7	22.7	22.7	22.7	22.7	22.8
105°	251.4	253.0	250.7	244.4	238.1	231.7	225.4
107.5°	310.0	310.7	311.4	312.1	312.8	313.5	314.1
110°	349.8	350.1	350.6	351.1	351.6	352.2	352.7



TEST NUMBER: P332913-927

CATALOG NUMBER: S124RDIP-S575D1035U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	388.4	388.3	388.6	389.3	390.0	390.6	391.3
115°	447.1	447.4	447.6	447.6	447.6	447.6	447.6
117.5°	505.3	505.2	505.2	505.1	505.0	504.9	504.9
120°	541.9	542.3	542.3	541.9	541.6	541.3	540.9
122.5°	577.6	577.8	577.7	577.4	577.0	576.7	576.3
125°	627.9	628.4	628.8	629.0	629.2	629.3	629.5
127.5°	676.9	676.8	676.7	676.6	676.4	676.3	676.1
130°	707.5	707.7	707.8	707.8	707.8	707.8	707.8
132.5°	737.3	737.4	737.4	737.3	737.1	737.0	736.9
135°	778.4	778.8	779.1	779.5	779.8	780.1	780.5
137.5°	817.8	818.2	818.2	818.2	818.1	817.9	817.8
140°	842.2	842.7	843.1	843.3	843.4	843.6	843.8
142.5°	864.6	865.0	865.1	865.2	865.2	865.3	865.3
145°	896.5	896.7	897.0	897.3	897.6	898.0	898.3
147.5°	924.7	924.9	925.0	925.2	925.3	925.6	925.7
150°	942.6	942.6	942.7	942.9	943.1	943.3	943.4
152.5°	958.7	958.9	959.0	958.9	958.9	958.7	958.6
155°	980.3	981.0	981.1	980.6	980.1	979.5	979.1
157.5°	998.9	999.7	999.7	998.9	997.9	997.0	996.1
160°	1010.7	1011.7	1011.7	1010.7	1009.6	1008.5	1007.5
162.5°	1020.2	1021.2	1021.1	1019.9	1018.7	1017.6	1016.4
165°	1033.9	1035.2	1035.1	1033.6	1032.0	1030.4	1028.8
167.5°	1043.8	1045.3	1045.2	1043.5	1041.7	1039.9	1038.2
170°	1049.6	1051.1	1050.9	1049.2	1047.4	1045.6	1043.9
172.5°	1053.4	1054.9	1054.6	1052.7	1050.8	1048.9	1047.0
175°	1058.1	1059.7	1059.4	1057.3	1055.2	1053.1	1051.0
177.5°	1059.4	1060.6	1060.3	1058.6	1056.9	1055.2	1053.5
180°	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3

(END OF REPORT)