

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332933-927

Luminaire Tested: **S124RDIP-S795D590U927-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332933-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIP-S795D590U927-4F0-1E-UDD-A4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4317.4 lumens
Efficiency: N/A
Efficacy: 107.1 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 40.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332933-927

CATALOG NUMBER: S124RDIP-S795D590U927-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332933-927

CATALOG NUMBER: S124RDIP-S795D590U927-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	66	66	66	61
1	101	97	93	90	94	91	87	85	79	77	75	69	67	66	60	58	57	53
2	92	85	79	74	86	80	75	70	70	66	63	61	58	56	53	51	49	45
3	85	75	68	62	79	71	65	59	63	58	54	55	51	48	48	45	42	39
4	78	67	59	53	72	63	56	51	56	50	46	49	45	41	43	40	37	34
5	71	60	52	46	67	57	49	44	50	45	40	44	40	36	39	35	33	30
6	66	54	46	40	62	51	44	39	46	40	35	40	36	32	35	32	29	26
7	61	49	41	36	57	46	39	34	41	36	31	37	32	29	32	29	26	23
8	57	45	37	32	53	42	35	30	38	32	28	34	29	26	30	26	23	21
9	53	41	33	28	50	39	32	27	35	29	25	31	26	23	28	24	21	19
10	50	38	30	26	47	36	29	25	32	27	23	29	24	21	26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8442	8442	8442	8442
5°	9792	8468	7484	8468
10°	11584	8430	6679	8430
15°	13381	8352	5739	8352
20°	14898	8245	5191	8245
25°	15380	8141	4819	8141
30°	13463	8011	4595	8011
35°	10480	7823	4459	7823
40°	7860	7606	4387	7606
45°	6205	7258	4349	7258
50°	5238	6859	4222	6859
55°	4566	6415	3997	6415
60°	4108	5959	3538	5959
65°	3622	5465	3041	5465
70°	3262	4952	2745	4952
75°	2732	4389	2339	4389
80°	2311	3742	2194	3742
85°	1954	2927	1954	2927



TEST NUMBER: P332933-927

CATALOG NUMBER: S124RDIP-S795D590U927-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	101.3	2.3
10°-20°	305.6	7.1
20°-30°	478.0	11.1
30°-40°	531.4	12.3
40°-50°	471.5	10.9
50°-60°	367.4	8.5
60°-70°	240.5	5.6
70°-80°	118.3	2.7
80°-90°	30.5	0.7
90°-100°	166.1	3.8
100°-110°	345.8	8.0
110°-120°	309.7	7.2
120°-130°	260.5	6.0
130°-140°	217.2	5.0
140°-150°	166.0	3.8
150°-160°	116.6	2.7
160°-170°	68.6	1.6
170°-180°	22.3	0.5
0°-30°	885.0	20.5
0°-40°	1416.4	32.8
0°-60°	2255.3	52.2
0°-90°	2644.5	61.3
90°-120°	821.6	19.0
90°-150°	1465.3	33.9
90°-180°	1673.0	38.7
0°-180°	4317.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1046	1046	1046	1046	1046	
5°	1208	1045	924	1045	1208	122
15°	1601	999	687	999	1601	455
25°	1727	914	541	914	1727	766
35°	1063	794	452	794	1063	667
45°	544	636	381	636	544	430
55°	324	456	284	456	324	295
65°	190	286	159	286	190	191
75°	88	141	75	141	88	96
85°	21	32	21	32	21	24
90°	10	0	10	0	10	9
95°	110	15	110	15	110	171
105°	636	53	636	53	636	629
115°	610	93	610	93	610	606
125°	487	130	487	130	487	443
135°	436	154	436	154	436	336
145°	356	178	356	178	356	225
155°	298	202	298	202	298	139
165°	260	220	260	220	260	74
175°	234	230	234	230	234	23
180°	230	230	230	230	230	



TEST NUMBER: P332933-927

CATALOG NUMBER: S124RDIP-S795D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7
2.5°	1103.0	1106.0	1103.0	1102.6	1099.3	1098.3	1096.9	1092.6	1084.4	1079.7	1080.8
5°	1208.3	1218.9	1213.0	1212.1	1202.8	1193.6	1187.6	1174.2	1159.8	1150.2	1142.2
7.5°	1330.2	1336.3	1332.5	1326.6	1311.6	1303.1	1289.4	1271.7	1246.0	1226.4	1208.4
10°	1413.1	1418.2	1416.4	1405.5	1394.6	1372.2	1359.5	1334.7	1302.3	1276.6	1252.6
12.5°	1494.6	1500.1	1485.2	1485.7	1465.0	1447.4	1427.4	1396.1	1358.6	1325.5	1295.4
15°	1601.0	1594.3	1594.3	1585.8	1562.7	1538.2	1517.6	1484.7	1437.5	1397.9	1356.2
17.5°	1684.3	1686.6	1683.1	1663.3	1645.0	1619.8	1581.9	1543.6	1499.8	1446.6	1404.0
20°	1734.1	1734.1	1730.4	1716.8	1693.3	1666.3	1625.4	1583.7	1528.1	1474.6	1426.6
22.5°	1754.4	1755.7	1751.2	1740.1	1718.9	1692.6	1657.8	1615.4	1558.1	1497.9	1438.4
25°	1726.6	1734.6	1735.4	1732.4	1726.1	1710.1	1680.2	1636.8	1585.4	1520.1	1456.0
27.5°	1585.2	1595.2	1604.1	1618.7	1638.1	1648.1	1649.5	1627.5	1582.6	1519.7	1455.3
30°	1444.2	1452.7	1480.0	1515.8	1543.7	1569.0	1590.9	1596.8	1571.5	1515.0	1447.2
32.5°	1287.9	1299.3	1326.7	1365.2	1411.6	1454.4	1503.6	1528.7	1528.0	1494.1	1431.4
35°	1063.4	1071.8	1097.1	1137.6	1193.2	1256.8	1334.7	1395.3	1436.7	1433.7	1395.3
37.5°	857.6	867.1	892.7	926.2	980.2	1058.9	1134.3	1217.9	1294.3	1337.1	1324.4
40°	745.8	746.2	771.0	805.6	856.1	924.8	1006.9	1099.6	1184.7	1254.3	1267.7
42.5°	657.4	657.5	673.9	711.1	747.6	812.2	890.7	982.7	1082.3	1162.6	1198.3
45°	543.5	547.3	560.8	583.1	611.7	666.5	729.3	814.8	926.5	1021.7	1081.1
47.5°	460.3	465.8	474.4	492.6	515.4	551.9	603.8	680.6	771.5	876.2	960.8
50°	417.1	418.0	428.9	439.0	458.8	487.9	533.4	597.4	680.8	781.6	875.5
52.5°	380.0	379.9	386.4	399.3	415.3	438.0	474.8	533.1	607.0	697.3	794.2
55°	324.4	326.5	331.6	341.7	353.9	369.9	398.9	442.8	501.0	578.1	666.1
57.5°	282.1	283.2	287.2	291.4	302.7	314.3	336.1	366.5	415.6	478.7	560.8
60°	254.4	254.9	256.2	262.4	271.3	282.3	297.0	322.7	364.0	421.8	486.6
62.5°	227.5	228.2	230.2	234.8	241.7	249.2	264.7	285.3	319.5	368.8	427.3
65°	189.6	190.0	193.0	194.6	200.1	206.8	218.2	232.1	255.7	297.0	341.3
67.5°	158.4	158.4	158.6	160.9	164.6	169.1	175.9	187.0	204.9	230.2	269.2
70°	138.2	138.2	139.0	140.3	142.4	146.2	150.0	158.4	171.5	192.1	222.0
72.5°	119.3	119.6	120.5	120.7	121.8	124.9	127.8	133.2	142.8	158.4	182.6
75°	87.6	88.9	91.0	92.7	94.8	94.3	97.4	100.7	103.6	112.9	126.8
77.5°	65.2	64.6	64.8	66.2	66.5	66.9	69.0	71.6	73.8	78.2	83.2
80°	49.7	49.7	51.0	51.4	51.0	51.4	53.5	54.7	55.6	57.3	61.9
82.5°	37.5	38.3	37.9	38.3	38.5	38.9	40.7	41.0	41.8	42.5	44.4
85°	21.1	21.5	21.9	21.1	21.1	21.1	21.9	22.3	23.2	22.7	23.6
87.5°	9.3	9.0	9.4	9.3	9.6	9.2	9.5	10.1	9.3	9.7	9.5
90°	9.5	9.5	9.9	9.5	9.0	9.0	8.6	8.2	7.7	8.2	7.2
92.5°	34.8	34.8	36.4	38.7	44.1	53.2	66.8	88.7	119.4	143.3	125.5
95°	110.3	116.1	124.3	138.3	160.4	204.2	264.8	334.9	378.7	368.3	277.9
97.5°	294.7	304.1	317.7	344.9	377.3	424.5	468.7	494.7	475.8	387.9	260.2
100°	414.4	418.0	431.6	459.1	498.4	531.9	554.1	545.0	479.0	363.3	235.9
102.5°	518.5	521.4	535.7	555.6	579.8	593.7	587.3	542.5	451.9	332.6	219.6
105°	635.8	638.5	644.8	648.5	647.6	629.1	584.3	506.1	402.7	296.4	205.7
107.5°	679.4	678.2	673.7	663.4	641.0	600.8	537.7	454.6	362.9	276.2	203.1
110°	680.1	676.0	667.9	649.0	616.9	567.1	501.6	423.4	343.0	269.3	203.8



TEST NUMBER: P332933-927

CATALOG NUMBER: S124RDIP-S795D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	658.8	652.2	640.8	617.8	581.4	531.7	469.8	400.7	331.8	266.1	206.0
115°	610.5	606.9	592.5	565.3	529.7	486.2	433.4	377.8	321.3	264.4	210.2
117.5°	561.7	558.8	544.2	521.4	490.9	454.2	412.6	366.5	316.6	263.9	214.5
120°	534.2	529.2	517.5	497.6	471.7	439.7	403.5	361.6	314.1	263.9	217.9
122.5°	512.5	507.5	497.6	480.5	458.8	430.6	397.8	357.2	311.2	263.6	221.1
125°	487.1	484.4	475.9	462.7	444.7	419.8	388.6	349.7	306.4	263.0	225.9
127.5°	472.3	469.6	462.4	450.8	432.5	409.0	377.9	340.7	300.0	262.0	229.8
130°	463.7	461.0	453.7	442.4	423.9	399.9	369.2	333.5	296.0	261.7	232.7
132.5°	453.9	451.1	444.3	431.6	413.4	389.4	359.4	325.9	292.4	261.3	235.3
135°	435.6	432.9	425.7	413.0	395.0	372.3	344.8	315.4	286.9	260.7	239.1
137.5°	413.0	409.8	403.9	391.3	374.5	354.0	330.8	305.9	282.3	260.6	241.3
140°	396.8	393.2	386.8	376.9	361.1	342.1	321.8	300.5	279.7	260.3	243.1
142.5°	379.4	376.9	371.3	362.0	348.1	331.6	314.2	295.5	277.6	260.3	244.5
145°	355.6	353.4	348.9	341.2	329.9	317.3	303.6	288.3	273.9	259.4	245.4
147.5°	334.6	333.7	330.3	323.8	315.4	305.5	294.6	282.4	270.5	257.8	245.8
150°	322.7	322.2	319.5	313.6	306.4	298.3	289.2	278.8	268.0	256.7	245.8
152.5°	311.8	311.3	309.7	304.9	298.8	292.1	283.8	274.8	265.1	254.8	245.1
155°	297.8	297.8	296.4	292.9	288.3	282.9	276.1	268.9	260.7	252.2	244.0
157.5°	285.5	285.5	284.7	282.0	278.5	274.2	268.5	262.4	256.4	249.4	242.9
160°	277.9	277.9	277.5	274.7	272.0	268.4	263.5	258.5	253.1	247.2	241.8
162.5°	270.7	271.1	270.6	267.9	265.9	262.6	258.7	254.5	250.2	245.0	240.7
165°	259.8	260.3	260.7	259.0	257.1	254.8	251.7	249.0	245.4	241.8	238.6
167.5°	251.3	251.6	251.7	250.6	249.6	248.3	245.7	243.7	241.1	238.5	236.5
170°	245.8	245.8	246.3	245.8	244.9	243.6	241.8	240.4	238.1	236.3	235.0
172.5°	240.4	241.1	241.6	241.1	240.6	239.6	238.5	237.5	235.6	234.2	233.5
175°	234.1	235.0	235.9	235.0	235.0	235.0	234.1	233.6	232.7	231.8	231.8
177.5°	230.4	231.1	231.8	231.5	231.8	231.5	231.5	231.1	230.8	230.4	230.4
180°	230.0	230.0	230.0	230.0	230.0	230.0	230.0	230.0	230.0	230.0	230.0



TEST NUMBER: P332933-927

CATALOG NUMBER: S124RDIP-S795D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7
2.5°	1077.4	1072.7	1070.3	1064.9	1058.5	1055.1	1052.1	1047.7	1042.0	1035.9	1031.5
5°	1132.0	1122.0	1109.3	1094.2	1080.7	1067.6	1056.2	1044.9	1031.8	1018.3	1004.8
7.5°	1188.2	1168.3	1146.8	1122.0	1097.8	1075.8	1055.6	1036.2	1014.2	994.7	976.8
10°	1227.2	1200.3	1170.4	1138.8	1107.2	1079.8	1052.9	1028.4	1001.5	977.5	957.2
12.5°	1258.9	1227.2	1191.3	1151.9	1114.0	1080.9	1049.8	1018.0	987.3	961.2	934.3
15°	1311.5	1268.1	1219.7	1172.5	1123.2	1078.2	1036.4	999.3	964.4	927.7	902.1
17.5°	1347.7	1296.2	1237.3	1180.6	1122.4	1069.2	1021.1	976.9	936.6	899.1	868.5
20°	1369.3	1312.4	1247.1	1182.6	1117.3	1060.4	1008.6	959.7	918.1	877.6	846.0
22.5°	1381.4	1318.4	1247.1	1179.6	1111.9	1050.4	993.5	942.5	897.1	856.7	821.7
25°	1385.3	1317.9	1245.0	1167.4	1093.3	1028.0	969.0	913.9	863.2	822.8	785.8
27.5°	1379.9	1300.5	1225.8	1146.3	1069.8	1000.9	939.1	881.1	830.4	787.0	749.0
30°	1371.8	1286.7	1206.7	1124.0	1046.6	980.4	915.0	859.4	806.8	761.8	723.4
32.5°	1354.2	1269.9	1183.7	1099.2	1020.6	952.4	890.5	834.6	782.9	736.8	696.1
35°	1319.5	1234.1	1140.5	1053.7	976.6	905.8	847.7	793.8	744.5	695.1	652.2
37.5°	1273.8	1186.5	1093.4	998.3	921.1	854.4	801.0	750.4	702.3	657.3	609.7
40°	1230.7	1151.0	1054.9	960.6	881.4	816.9	767.6	721.7	673.3	628.6	581.0
42.5°	1178.4	1110.6	1013.5	918.8	840.6	778.5	732.6	687.7	643.6	600.3	550.6
45°	1091.2	1039.8	948.8	857.8	779.0	717.5	675.3	635.7	597.0	555.7	509.0
47.5°	991.3	956.5	877.9	784.7	711.9	656.5	615.8	583.4	550.6	509.4	468.3
50°	921.9	899.5	823.6	738.6	669.1	618.1	576.4	546.1	518.6	479.0	442.4
52.5°	847.7	835.8	771.7	690.4	623.2	573.2	537.6	510.3	482.6	449.7	415.4
55°	734.7	741.1	686.7	616.4	553.2	511.0	478.6	455.8	432.3	404.5	378.0
57.5°	619.3	642.4	605.9	544.2	484.9	446.0	421.6	402.4	382.6	359.6	336.9
60°	550.2	569.6	549.0	494.6	442.8	406.5	383.8	369.1	349.3	328.2	310.9
62.5°	482.8	503.6	491.3	447.4	399.3	368.1	348.1	334.4	319.6	301.3	283.3
65°	398.2	411.6	405.8	375.4	341.3	314.7	296.2	286.1	272.6	259.1	243.1
67.5°	304.9	331.0	327.6	311.4	281.9	261.2	249.1	240.1	227.8	217.9	206.9
70°	250.6	274.7	274.3	261.2	245.2	225.9	217.4	209.8	198.8	189.2	180.3
72.5°	205.2	227.2	230.4	220.5	209.5	194.8	186.7	181.5	170.9	164.2	157.1
75°	143.7	159.7	163.9	163.9	158.8	151.2	144.1	140.7	133.2	127.2	123.0
77.5°	94.2	104.3	110.9	112.4	113.2	110.7	104.7	102.3	96.6	94.4	90.4
80°	66.5	73.3	80.9	83.4	85.6	84.7	82.1	80.5	75.0	72.9	71.2
82.5°	46.0	49.7	55.9	61.5	60.9	63.1	60.9	59.6	55.5	54.7	53.0
85°	24.0	24.4	25.3	29.1	31.2	32.0	32.5	31.6	30.3	30.3	27.4
87.5°	9.3	9.0	9.1	9.1	9.4	10.6	11.4	11.6	10.7	10.0	9.0
90°	6.3	6.3	3.6	3.6	3.2	2.7	1.3	0.5	1.3	2.7	3.2
92.5°	91.3	56.2	33.3	23.8	17.3	11.7	7.5	5.1	7.5	11.7	17.3
95°	169.9	95.8	56.5	37.5	26.7	20.8	16.2	14.9	16.2	20.8	26.7
97.5°	152.7	91.6	61.3	45.4	36.0	30.7	26.8	26.8	26.8	30.7	36.0
100°	143.7	92.6	66.0	51.5	42.9	37.5	34.4	34.4	34.4	37.5	42.9
102.5°	141.2	96.3	72.1	58.4	50.1	45.1	42.3	41.6	42.3	45.1	50.1
105°	142.4	104.8	83.2	70.0	61.9	56.5	54.3	52.8	54.3	56.5	61.9
107.5°	149.0	114.9	95.0	82.1	74.3	68.5	66.2	65.4	66.2	68.5	74.3
110°	154.1	122.5	102.6	90.4	82.2	76.8	74.5	73.7	74.5	76.8	82.2



TEST NUMBER: P332933-927

CATALOG NUMBER: S124RDIP-S795D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	159.5	129.7	110.5	98.3	90.2	85.2	82.5	81.6	82.5	85.2	90.2
115°	168.1	141.0	122.9	110.7	102.1	97.6	94.4	93.1	94.4	97.6	102.1
117.5°	176.9	151.9	134.8	122.1	114.1	109.1	106.3	105.0	106.3	109.1	114.1
120°	183.0	159.5	142.4	129.7	122.0	117.0	113.9	113.0	113.9	117.0	122.0
122.5°	188.8	166.8	149.6	137.3	128.9	124.3	121.1	120.2	121.1	124.3	128.9
125°	197.5	176.7	160.4	147.7	139.2	134.2	131.5	129.7	131.5	134.2	139.2
127.5°	205.0	185.9	170.2	157.4	148.5	142.8	139.6	138.1	139.6	142.8	148.5
130°	209.7	192.0	176.7	163.6	155.0	148.2	144.6	142.8	144.6	148.2	155.0
132.5°	214.4	197.1	181.7	169.4	160.1	153.7	148.9	147.5	148.9	153.7	160.1
135°	220.5	204.2	189.3	177.6	168.1	160.4	155.9	154.1	155.9	160.4	168.1
137.5°	224.9	209.7	195.7	184.6	174.7	167.4	162.4	160.7	162.4	167.4	174.7
140°	227.8	213.3	199.7	188.9	179.4	171.7	166.8	165.4	166.8	171.7	179.4
142.5°	229.9	216.6	203.4	192.9	183.7	176.4	171.8	170.5	171.8	176.4	183.7
145°	232.3	220.1	208.3	198.4	189.8	183.5	179.0	177.6	179.0	183.5	189.8
147.5°	234.3	223.7	212.7	203.7	196.5	190.0	186.1	185.6	186.1	190.0	196.5
150°	235.4	225.5	215.6	207.0	200.2	194.8	191.2	190.7	191.2	194.8	200.2
152.5°	236.1	227.0	218.1	210.2	204.1	199.1	195.5	195.4	195.5	199.1	204.1
155°	236.8	229.1	221.4	214.7	209.7	205.2	202.5	202.0	202.5	205.2	209.7
157.5°	236.8	230.7	224.1	218.8	214.4	211.0	208.4	208.4	208.4	211.0	214.4
160°	236.8	231.4	225.9	220.9	217.4	214.2	212.4	212.4	212.4	214.2	217.4
162.5°	236.8	232.1	227.0	223.2	219.9	217.1	215.6	216.0	215.6	217.1	219.9
165°	235.9	232.3	228.2	225.5	223.2	220.9	220.1	220.1	220.1	220.9	223.2
167.5°	234.8	232.2	229.2	227.1	225.9	224.1	223.7	224.1	223.7	224.1	225.9
170°	234.1	231.8	229.6	228.2	227.3	225.9	225.5	225.9	225.5	225.9	227.3
172.5°	233.4	231.5	229.9	228.9	228.4	227.4	227.3	227.8	227.3	227.4	228.4
175°	232.3	230.9	230.0	230.0	229.6	229.1	229.1	229.6	229.1	229.1	229.6
177.5°	231.1	230.4	230.0	230.0	230.0	229.7	230.0	230.4	230.0	229.7	230.0
180°	230.0	230.0	230.0	230.0	230.0	230.0	230.0	230.0	230.0	230.0	230.0



TEST NUMBER: P332933-927

CATALOG NUMBER: S124RDIP-S795D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7
2.5°	1026.8	1023.4	1019.1	1014.0	1008.0	1002.6	1000.2	1002.2	1003.2	1000.5	1000.2
5°	995.5	985.0	976.6	963.9	953.9	945.4	939.5	937.0	937.9	931.1	929.4
7.5°	960.4	947.9	934.1	919.2	905.1	892.8	886.3	882.7	875.6	872.5	867.4
10°	937.9	921.0	907.5	889.8	873.8	859.0	851.9	846.0	838.8	835.4	828.3
12.5°	914.6	895.0	880.2	861.8	845.5	827.7	820.9	809.9	798.8	791.6	782.4
15°	881.8	858.3	840.1	818.2	798.8	778.6	760.5	740.2	732.7	716.7	707.4
17.5°	843.4	819.5	797.1	767.7	737.8	712.7	693.4	674.0	662.4	652.2	647.5
20°	818.2	796.3	765.1	730.9	697.7	669.9	654.3	641.7	629.0	621.9	616.8
22.5°	794.2	766.3	730.1	693.2	660.0	638.2	625.0	612.0	601.7	594.9	588.1
25°	754.2	717.5	679.1	637.0	614.3	595.3	581.0	570.5	564.1	555.3	551.9
27.5°	713.0	668.5	626.2	597.9	574.3	556.9	544.4	536.5	528.5	522.8	518.5
30°	681.3	636.2	598.3	571.3	547.3	533.0	522.8	513.6	507.2	502.6	499.2
32.5°	649.9	604.8	573.0	544.0	525.1	511.0	500.3	493.4	488.4	482.4	480.4
35°	604.6	564.6	536.8	510.6	491.2	478.6	470.2	463.0	458.8	457.1	455.8
37.5°	561.0	528.2	498.4	476.9	459.6	449.7	439.7	436.3	433.3	430.3	431.7
40°	533.4	502.6	476.1	453.4	439.4	428.5	422.6	418.4	415.8	415.8	415.8
42.5°	509.5	479.3	453.5	433.1	419.2	410.0	403.4	399.8	398.9	398.6	400.7
45°	472.3	444.5	418.4	401.5	389.7	380.4	376.7	373.7	373.7	375.4	375.8
47.5°	435.5	409.4	388.5	369.6	358.8	353.0	349.7	348.2	348.3	350.1	352.0
50°	412.9	387.2	366.5	349.7	339.6	334.1	331.1	330.3	331.1	331.1	334.1
52.5°	388.2	365.3	345.0	330.8	319.3	314.2	312.6	311.4	312.0	313.3	314.6
55°	352.2	331.6	312.2	298.7	290.3	286.9	283.1	283.5	282.7	283.5	283.5
57.5°	316.1	297.5	279.5	268.8	261.4	256.5	252.4	253.6	252.3	252.2	251.4
60°	292.8	272.6	258.3	248.6	240.1	235.9	232.1	233.0	231.7	230.8	229.2
62.5°	267.5	250.6	237.0	227.7	220.9	216.0	212.2	211.4	208.5	205.6	201.9
65°	230.8	217.0	204.8	195.9	189.6	185.8	182.8	180.3	174.0	167.2	163.9
67.5°	195.3	185.2	173.8	166.4	161.2	156.2	150.6	146.3	140.4	136.7	134.6
70°	172.3	162.6	153.0	145.8	140.3	135.7	129.4	126.4	122.2	120.5	118.4
72.5°	150.4	141.4	132.4	125.9	120.1	116.5	111.5	108.5	106.7	106.0	103.9
75°	117.2	110.0	103.2	97.4	92.7	90.2	88.1	86.0	85.1	81.3	79.2
77.5°	85.5	80.7	76.5	72.3	69.0	67.3	63.3	60.8	59.4	57.7	57.2
80°	66.5	63.2	59.0	56.5	51.8	50.1	48.5	48.0	47.6	47.2	46.7
82.5°	50.1	46.7	42.5	41.0	39.7	38.7	37.6	37.2	36.8	37.1	37.0
85°	25.3	23.6	23.6	23.2	22.7	22.3	21.9	21.9	21.5	21.9	21.5
87.5°	9.1	8.8	9.3	8.7	9.2	9.3	9.0	9.0	9.5	8.9	8.9
90°	3.6	3.6	6.3	6.3	7.2	8.2	7.7	8.2	8.6	9.0	9.0
92.5°	23.8	33.3	56.2	91.3	125.5	143.3	119.4	88.7	66.8	53.2	44.1
95°	37.5	56.5	95.8	169.9	277.9	368.3	378.7	334.9	264.8	204.2	160.4
97.5°	45.4	61.3	91.6	152.7	260.2	387.9	475.8	494.7	468.7	424.5	377.3
100°	51.5	66.0	92.6	143.7	235.9	363.3	479.0	545.0	554.1	531.9	498.4
102.5°	58.4	72.1	96.3	141.2	219.6	332.6	451.9	542.5	587.3	593.7	579.8
105°	70.0	83.2	104.8	142.4	205.7	296.4	402.7	506.1	584.3	629.1	647.6
107.5°	82.1	95.0	114.9	149.0	203.1	276.2	362.9	454.6	537.7	600.8	641.0
110°	90.4	102.6	122.5	154.1	203.8	269.3	343.0	423.4	501.6	567.1	616.9



TEST NUMBER: P332933-927

CATALOG NUMBER: S124RDIP-S795D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	98.3	110.5	129.7	159.5	206.0	266.1	331.8	400.7	469.8	531.7	581.4
115°	110.7	122.9	141.0	168.1	210.2	264.4	321.3	377.8	433.4	486.2	529.7
117.5°	122.1	134.8	151.9	176.9	214.5	263.9	316.6	366.5	412.6	454.2	490.9
120°	129.7	142.4	159.5	183.0	217.9	263.9	314.1	361.6	403.5	439.7	471.7
122.5°	137.3	149.6	166.8	188.8	221.1	263.6	311.2	357.2	397.8	430.6	458.8
125°	147.7	160.4	176.7	197.5	225.9	263.0	306.4	349.7	388.6	419.8	444.7
127.5°	157.4	170.2	185.9	205.0	229.8	262.0	300.0	340.7	377.9	409.0	432.5
130°	163.6	176.7	192.0	209.7	232.7	261.7	296.0	333.5	369.2	399.9	423.9
132.5°	169.4	181.7	197.1	214.4	235.3	261.3	292.4	325.9	359.4	389.4	413.4
135°	177.6	189.3	204.2	220.5	239.1	260.7	286.9	315.4	344.8	372.3	395.0
137.5°	184.6	195.7	209.7	224.9	241.3	260.6	282.3	305.9	330.8	354.0	374.5
140°	188.9	199.7	213.3	227.8	243.1	260.3	279.7	300.5	321.8	342.1	361.1
142.5°	192.9	203.4	216.6	229.9	244.5	260.3	277.6	295.5	314.2	331.6	348.1
145°	198.4	208.3	220.1	232.3	245.4	259.4	273.9	288.3	303.6	317.3	329.9
147.5°	203.7	212.7	223.7	234.3	245.8	257.8	270.5	282.4	294.6	305.5	315.4
150°	207.0	215.6	225.5	235.4	245.8	256.7	268.0	278.8	289.2	298.3	306.4
152.5°	210.2	218.1	227.0	236.1	245.1	254.8	265.1	274.8	283.8	292.1	298.8
155°	214.7	221.4	229.1	236.8	244.0	252.2	260.7	268.9	276.1	282.9	288.3
157.5°	218.8	224.1	230.7	236.8	242.9	249.4	256.4	262.4	268.5	274.2	278.5
160°	220.9	225.9	231.4	236.8	241.8	247.2	253.1	258.5	263.5	268.4	272.0
162.5°	223.2	227.0	232.1	236.8	240.7	245.0	250.2	254.5	258.7	262.6	265.9
165°	225.5	228.2	232.3	235.9	238.6	241.8	245.4	249.0	251.7	254.8	257.1
167.5°	227.1	229.2	232.2	234.8	236.5	238.5	241.1	243.7	245.7	248.3	249.6
170°	228.2	229.6	231.8	234.1	235.0	236.3	238.1	240.4	241.8	243.6	244.9
172.5°	228.9	229.9	231.5	233.4	233.5	234.2	235.6	237.5	238.5	239.6	240.6
175°	230.0	230.0	230.9	232.3	231.8	231.8	232.7	233.6	234.1	235.0	235.0
177.5°	230.0	230.0	230.4	231.1	230.4	230.4	230.8	231.1	231.5	231.5	231.8
180°	230.0	230.0	230.0	230.0	230.0	230.0	230.0	230.0	230.0	230.0	230.0



TEST NUMBER: P332933-927

CATALOG NUMBER: S124RDIP-S795D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7
2.5°	998.1	998.9	996.5	995.8	996.5	998.9	998.1	1000.2	1000.5	1003.2	1002.2
5°	926.1	925.2	923.1	923.5	923.1	925.2	926.1	929.4	931.1	937.9	937.0
7.5°	864.4	861.1	862.0	858.6	862.0	861.1	864.4	867.4	872.5	875.6	882.7
10°	826.6	822.0	818.2	814.8	818.2	822.0	826.6	828.3	835.4	838.8	846.0
12.5°	775.1	771.1	766.0	767.0	766.0	771.1	775.1	782.4	791.6	798.8	809.9
15°	701.9	695.6	685.5	686.7	685.5	695.6	701.9	707.4	716.7	732.7	740.2
17.5°	640.0	640.1	635.4	636.5	635.4	640.1	640.0	647.5	652.2	662.4	674.0
20°	607.9	605.0	605.4	604.2	605.4	605.0	607.9	616.8	621.9	629.0	641.7
22.5°	585.7	582.1	579.2	576.6	579.2	582.1	585.7	588.1	594.9	601.7	612.0
25°	548.1	545.6	541.8	541.0	541.8	545.6	548.1	551.9	555.3	564.1	570.5
27.5°	515.1	514.6	513.1	511.1	513.1	514.6	515.1	518.5	522.8	528.5	536.5
30°	495.9	495.0	494.2	492.9	494.2	495.0	495.9	499.2	502.6	507.2	513.6
32.5°	478.7	478.2	477.4	477.4	477.4	478.2	478.7	480.4	482.4	488.4	493.4
35°	454.2	453.8	452.9	452.5	452.9	453.8	454.2	455.8	457.1	458.8	463.0
37.5°	431.3	432.4	431.8	431.7	431.8	432.4	431.3	431.7	430.3	433.3	436.3
40°	415.4	415.8	416.7	416.3	416.7	415.8	415.4	415.8	415.8	415.8	418.4
42.5°	402.3	402.3	403.5	402.1	403.5	402.3	402.3	400.7	398.6	398.9	399.8
45°	378.7	381.3	380.9	380.9	380.9	381.3	378.7	375.8	375.4	373.7	373.7
47.5°	353.1	355.2	355.8	355.8	355.8	355.2	353.1	352.0	350.1	348.3	348.2
50°	336.2	335.3	336.6	336.2	336.6	335.3	336.2	334.1	331.1	331.1	330.3
52.5°	315.7	315.8	315.8	315.3	315.8	315.8	315.7	314.6	313.3	312.0	311.4
55°	284.0	284.4	283.5	284.0	283.5	284.4	284.0	283.5	283.5	282.7	283.5
57.5°	249.6	247.6	248.4	247.4	248.4	247.6	249.6	251.4	252.2	252.3	253.6
60°	225.0	221.6	220.8	219.1	220.8	221.6	225.0	229.2	230.8	231.7	233.0
62.5°	197.3	195.0	192.1	193.5	192.1	195.0	197.3	201.9	205.6	208.5	211.4
65°	160.5	158.8	157.6	159.2	157.6	158.8	160.5	163.9	167.2	174.0	180.3
67.5°	132.8	132.0	132.0	131.1	132.0	132.0	132.8	134.6	136.7	140.4	146.3
70°	118.4	117.2	117.2	116.3	117.2	117.2	118.4	118.4	120.5	122.2	126.4
72.5°	103.5	102.3	102.7	102.1	102.7	102.3	103.5	103.9	106.0	106.7	108.5
75°	76.7	74.5	74.5	75.0	74.5	74.5	76.7	79.2	81.3	85.1	86.0
77.5°	57.2	56.8	57.4	56.6	57.4	56.8	57.2	57.2	57.7	59.4	60.8
80°	46.7	46.3	45.9	47.2	45.9	46.3	46.7	46.7	47.2	47.6	48.0
82.5°	36.3	36.2	36.1	37.8	36.1	36.2	36.3	37.0	37.1	36.8	37.2
85°	21.9	21.1	21.9	21.1	21.9	21.1	21.9	21.5	21.9	21.5	21.9
87.5°	9.7	9.4	9.0	9.3	9.0	9.4	9.7	8.9	8.9	9.5	9.0
90°	9.5	9.9	9.5	9.5	9.5	9.9	9.5	9.0	9.0	8.6	8.2
92.5°	38.7	36.4	34.8	34.8	34.8	36.4	38.7	44.1	53.2	66.8	88.7
95°	138.3	124.3	116.1	110.3	116.1	124.3	138.3	160.4	204.2	264.8	334.9
97.5°	344.9	317.7	304.1	294.7	304.1	317.7	344.9	377.3	424.5	468.7	494.7
100°	459.1	431.6	418.0	414.4	418.0	431.6	459.1	498.4	531.9	554.1	545.0
102.5°	555.6	535.7	521.4	518.5	521.4	535.7	555.6	579.8	593.7	587.3	542.5
105°	648.5	644.8	638.5	635.8	638.5	644.8	648.5	647.6	629.1	584.3	506.1
107.5°	663.4	673.7	678.2	679.4	678.2	673.7	663.4	641.0	600.8	537.7	454.6
110°	649.0	667.9	676.0	680.1	676.0	667.9	649.0	616.9	567.1	501.6	423.4



TEST NUMBER: P332933-927

CATALOG NUMBER: S124RDIP-S795D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	617.8	640.8	652.2	658.8	652.2	640.8	617.8	581.4	531.7	469.8	400.7
115°	565.3	592.5	606.9	610.5	606.9	592.5	565.3	529.7	486.2	433.4	377.8
117.5°	521.4	544.2	558.8	561.7	558.8	544.2	521.4	490.9	454.2	412.6	366.5
120°	497.6	517.5	529.2	534.2	529.2	517.5	497.6	471.7	439.7	403.5	361.6
122.5°	480.5	497.6	507.5	512.5	507.5	497.6	480.5	458.8	430.6	397.8	357.2
125°	462.7	475.9	484.4	487.1	484.4	475.9	462.7	444.7	419.8	388.6	349.7
127.5°	450.8	462.4	469.6	472.3	469.6	462.4	450.8	432.5	409.0	377.9	340.7
130°	442.4	453.7	461.0	463.7	461.0	453.7	442.4	423.9	399.9	369.2	333.5
132.5°	431.6	444.3	451.1	453.9	451.1	444.3	431.6	413.4	389.4	359.4	325.9
135°	413.0	425.7	432.9	435.6	432.9	425.7	413.0	395.0	372.3	344.8	315.4
137.5°	391.3	403.9	409.8	413.0	409.8	403.9	391.3	374.5	354.0	330.8	305.9
140°	376.9	386.8	393.2	396.8	393.2	386.8	376.9	361.1	342.1	321.8	300.5
142.5°	362.0	371.3	376.9	379.4	376.9	371.3	362.0	348.1	331.6	314.2	295.5
145°	341.2	348.9	353.4	355.6	353.4	348.9	341.2	329.9	317.3	303.6	288.3
147.5°	323.8	330.3	333.7	334.6	333.7	330.3	323.8	315.4	305.5	294.6	282.4
150°	313.6	319.5	322.2	322.7	322.2	319.5	313.6	306.4	298.3	289.2	278.8
152.5°	304.9	309.7	311.3	311.8	311.3	309.7	304.9	298.8	292.1	283.8	274.8
155°	292.9	296.4	297.8	297.8	297.8	296.4	292.9	288.3	282.9	276.1	268.9
157.5°	282.0	284.7	285.5	285.5	285.5	284.7	282.0	278.5	274.2	268.5	262.4
160°	274.7	277.5	277.9	277.9	277.9	277.5	274.7	272.0	268.4	263.5	258.5
162.5°	267.9	270.6	271.1	270.7	271.1	270.6	267.9	265.9	262.6	258.7	254.5
165°	259.0	260.7	260.3	259.8	260.3	260.7	259.0	257.1	254.8	251.7	249.0
167.5°	250.6	251.7	251.6	251.3	251.6	251.7	250.6	249.6	248.3	245.7	243.7
170°	245.8	246.3	245.8	245.8	245.8	246.3	245.8	244.9	243.6	241.8	240.4
172.5°	241.1	241.6	241.1	240.4	241.1	241.6	241.1	240.6	239.6	238.5	237.5
175°	235.0	235.9	235.0	234.1	235.0	235.9	235.0	235.0	235.0	234.1	233.6
177.5°	231.5	231.8	231.1	230.4	231.1	231.8	231.5	231.8	231.5	231.5	231.1
180°	230.0	230.0	230.0	230.0	230.0	230.0	230.0	230.0	230.0	230.0	230.0



TEST NUMBER: P332933-927

CATALOG NUMBER: S124RDIP-S795D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7
2.5°	1000.2	1002.6	1008.0	1014.0	1019.1	1023.4	1026.8	1031.5	1035.9	1042.0	1047.7
5°	939.5	945.4	953.9	963.9	976.6	985.0	995.5	1004.8	1018.3	1031.8	1044.9
7.5°	886.3	892.8	905.1	919.2	934.1	947.9	960.4	976.8	994.7	1014.2	1036.2
10°	851.9	859.0	873.8	889.8	907.5	921.0	937.9	957.2	977.5	1001.5	1028.4
12.5°	820.9	827.7	845.5	861.8	880.2	895.0	914.6	934.3	961.2	987.3	1018.0
15°	760.5	778.6	798.8	818.2	840.1	858.3	881.8	902.1	927.7	964.4	999.3
17.5°	693.4	712.7	737.8	767.7	797.1	819.5	843.4	868.5	899.1	936.6	976.9
20°	654.3	669.9	697.7	730.9	765.1	796.3	818.2	846.0	877.6	918.1	959.7
22.5°	625.0	638.2	660.0	693.2	730.1	766.3	794.2	821.7	856.7	897.1	942.5
25°	581.0	595.3	614.3	637.0	679.1	717.5	754.2	785.8	822.8	863.2	913.9
27.5°	544.4	556.9	574.3	597.9	626.2	668.5	713.0	749.0	787.0	830.4	881.1
30°	522.8	533.0	547.3	571.3	598.3	636.2	681.3	723.4	761.8	806.8	859.4
32.5°	500.3	511.0	525.1	544.0	573.0	604.8	649.9	696.1	736.8	782.9	834.6
35°	470.2	478.6	491.2	510.6	536.8	564.6	604.6	652.2	695.1	744.5	793.8
37.5°	439.7	449.7	459.6	476.9	498.4	528.2	561.0	609.7	657.3	702.3	750.4
40°	422.6	428.5	439.4	453.4	476.1	502.6	533.4	581.0	628.6	673.3	721.7
42.5°	403.4	410.0	419.2	433.1	453.5	479.3	509.5	550.6	600.3	643.6	687.7
45°	376.7	380.4	389.7	401.5	418.4	444.5	472.3	509.0	555.7	597.0	635.7
47.5°	349.7	353.0	358.8	369.6	388.5	409.4	435.5	468.3	509.4	550.6	583.4
50°	331.1	334.1	339.6	349.7	366.5	387.2	412.9	442.4	479.0	518.6	546.1
52.5°	312.6	314.2	319.3	330.8	345.0	365.3	388.2	415.4	449.7	482.6	510.3
55°	283.1	286.9	290.3	298.7	312.2	331.6	352.2	378.0	404.5	432.3	455.8
57.5°	252.4	256.5	261.4	268.8	279.5	297.5	316.1	336.9	359.6	382.6	402.4
60°	232.1	235.9	240.1	248.6	258.3	272.6	292.8	310.9	328.2	349.3	369.1
62.5°	212.2	216.0	220.9	227.7	237.0	250.6	267.5	283.3	301.3	319.6	334.4
65°	182.8	185.8	189.6	195.9	204.8	217.0	230.8	243.1	259.1	272.6	286.1
67.5°	150.6	156.2	161.2	166.4	173.8	185.2	195.3	206.9	217.9	227.8	240.1
70°	129.4	135.7	140.3	145.8	153.0	162.6	172.3	180.3	189.2	198.8	209.8
72.5°	111.5	116.5	120.1	125.9	132.4	141.4	150.4	157.1	164.2	170.9	181.5
75°	88.1	90.2	92.7	97.4	103.2	110.0	117.2	123.0	127.2	133.2	140.7
77.5°	63.3	67.3	69.0	72.3	76.5	80.7	85.5	90.4	94.4	96.6	102.3
80°	48.5	50.1	51.8	56.5	59.0	63.2	66.5	71.2	72.9	75.0	80.5
82.5°	37.6	38.7	39.7	41.0	42.5	46.7	50.1	53.0	54.7	55.5	59.6
85°	21.9	22.3	22.7	23.2	23.6	23.6	25.3	27.4	30.3	30.3	31.6
87.5°	9.0	9.3	9.2	8.7	9.3	8.8	9.1	9.0	10.0	10.7	11.6
90°	7.7	8.2	7.2	6.3	6.3	3.6	3.6	3.2	2.7	1.3	0.5
92.5°	119.4	143.3	125.5	91.3	56.2	33.3	23.8	17.3	11.7	7.5	5.1
95°	378.7	368.3	277.9	169.9	95.8	56.5	37.5	26.7	20.8	16.2	14.9
97.5°	475.8	387.9	260.2	152.7	91.6	61.3	45.4	36.0	30.7	26.8	26.8
100°	479.0	363.3	235.9	143.7	92.6	66.0	51.5	42.9	37.5	34.4	34.4
102.5°	451.9	332.6	219.6	141.2	96.3	72.1	58.4	50.1	45.1	42.3	41.6
105°	402.7	296.4	205.7	142.4	104.8	83.2	70.0	61.9	56.5	54.3	52.8
107.5°	362.9	276.2	203.1	149.0	114.9	95.0	82.1	74.3	68.5	66.2	65.4
110°	343.0	269.3	203.8	154.1	122.5	102.6	90.4	82.2	76.8	74.5	73.7



TEST NUMBER: P332933-927

CATALOG NUMBER: S124RDIP-S795D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	331.8	266.1	206.0	159.5	129.7	110.5	98.3	90.2	85.2	82.5	81.6
115°	321.3	264.4	210.2	168.1	141.0	122.9	110.7	102.1	97.6	94.4	93.1
117.5°	316.6	263.9	214.5	176.9	151.9	134.8	122.1	114.1	109.1	106.3	105.0
120°	314.1	263.9	217.9	183.0	159.5	142.4	129.7	122.0	117.0	113.9	113.0
122.5°	311.2	263.6	221.1	188.8	166.8	149.6	137.3	128.9	124.3	121.1	120.2
125°	306.4	263.0	225.9	197.5	176.7	160.4	147.7	139.2	134.2	131.5	129.7
127.5°	300.0	262.0	229.8	205.0	185.9	170.2	157.4	148.5	142.8	139.6	138.1
130°	296.0	261.7	232.7	209.7	192.0	176.7	163.6	155.0	148.2	144.6	142.8
132.5°	292.4	261.3	235.3	214.4	197.1	181.7	169.4	160.1	153.7	148.9	147.5
135°	286.9	260.7	239.1	220.5	204.2	189.3	177.6	168.1	160.4	155.9	154.1
137.5°	282.3	260.6	241.3	224.9	209.7	195.7	184.6	174.7	167.4	162.4	160.7
140°	279.7	260.3	243.1	227.8	213.3	199.7	188.9	179.4	171.7	166.8	165.4
142.5°	277.6	260.3	244.5	229.9	216.6	203.4	192.9	183.7	176.4	171.8	170.5
145°	273.9	259.4	245.4	232.3	220.1	208.3	198.4	189.8	183.5	179.0	177.6
147.5°	270.5	257.8	245.8	234.3	223.7	212.7	203.7	196.5	190.0	186.1	185.6
150°	268.0	256.7	245.8	235.4	225.5	215.6	207.0	200.2	194.8	191.2	190.7
152.5°	265.1	254.8	245.1	236.1	227.0	218.1	210.2	204.1	199.1	195.5	195.4
155°	260.7	252.2	244.0	236.8	229.1	221.4	214.7	209.7	205.2	202.5	202.0
157.5°	256.4	249.4	242.9	236.8	230.7	224.1	218.8	214.4	211.0	208.4	208.4
160°	253.1	247.2	241.8	236.8	231.4	225.9	220.9	217.4	214.2	212.4	212.4
162.5°	250.2	245.0	240.7	236.8	232.1	227.0	223.2	219.9	217.1	215.6	216.0
165°	245.4	241.8	238.6	235.9	232.3	228.2	225.5	223.2	220.9	220.1	220.1
167.5°	241.1	238.5	236.5	234.8	232.2	229.2	227.1	225.9	224.1	223.7	224.1
170°	238.1	236.3	235.0	234.1	231.8	229.6	228.2	227.3	225.9	225.5	225.9
172.5°	235.6	234.2	233.5	233.4	231.5	229.9	228.9	228.4	227.4	227.3	227.8
175°	232.7	231.8	231.8	232.3	230.9	230.0	230.0	229.6	229.1	229.1	229.6
177.5°	230.8	230.4	230.4	231.1	230.4	230.0	230.0	230.0	229.7	230.0	230.4
180°	230.0	230.0	230.0	230.0	230.0	230.0	230.0	230.0	230.0	230.0	230.0



TEST NUMBER: P332933-927

CATALOG NUMBER: S124RDIP-S795D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7
2.5°	1052.1	1055.1	1058.5	1064.9	1070.3	1072.7	1077.4	1080.8	1079.7	1084.4	1092.6
5°	1056.2	1067.6	1080.7	1094.2	1109.3	1122.0	1132.0	1142.2	1150.2	1159.8	1174.2
7.5°	1055.6	1075.8	1097.8	1122.0	1146.8	1168.3	1188.2	1208.4	1226.4	1246.0	1271.7
10°	1052.9	1079.8	1107.2	1138.8	1170.4	1200.3	1227.2	1252.6	1276.6	1302.3	1334.7
12.5°	1049.8	1080.9	1114.0	1151.9	1191.3	1227.2	1258.9	1295.4	1325.5	1358.6	1396.1
15°	1036.4	1078.2	1123.2	1172.5	1219.7	1268.1	1311.5	1356.2	1397.9	1437.5	1484.7
17.5°	1021.1	1069.2	1122.4	1180.6	1237.3	1296.2	1347.7	1404.0	1446.6	1499.8	1543.6
20°	1008.6	1060.4	1117.3	1182.6	1247.1	1312.4	1369.3	1426.6	1474.6	1528.1	1583.7
22.5°	993.5	1050.4	1111.9	1179.6	1247.1	1318.4	1381.4	1438.4	1497.9	1558.1	1615.4
25°	969.0	1028.0	1093.3	1167.4	1245.0	1317.9	1385.3	1456.0	1520.1	1585.4	1636.8
27.5°	939.1	1000.9	1069.8	1146.3	1225.8	1300.5	1379.9	1455.3	1519.7	1582.6	1627.5
30°	915.0	980.4	1046.6	1124.0	1206.7	1286.7	1371.8	1447.2	1515.0	1571.5	1596.8
32.5°	890.5	952.4	1020.6	1099.2	1183.7	1269.9	1354.2	1431.4	1494.1	1528.0	1528.7
35°	847.7	905.8	976.6	1053.7	1140.5	1234.1	1319.5	1395.3	1433.7	1436.7	1395.3
37.5°	801.0	854.4	921.1	998.3	1093.4	1186.5	1273.8	1324.4	1337.1	1294.3	1217.9
40°	767.6	816.9	881.4	960.6	1054.9	1151.0	1230.7	1267.7	1254.3	1184.7	1099.6
42.5°	732.6	778.5	840.6	918.8	1013.5	1110.6	1178.4	1198.3	1162.6	1082.3	982.7
45°	675.3	717.5	779.0	857.8	948.8	1039.8	1091.2	1081.1	1021.7	926.5	814.8
47.5°	615.8	656.5	711.9	784.7	877.9	956.5	991.3	960.8	876.2	771.5	680.6
50°	576.4	618.1	669.1	738.6	823.6	899.5	921.9	875.5	781.6	680.8	597.4
52.5°	537.6	573.2	623.2	690.4	771.7	835.8	847.7	794.2	697.3	607.0	533.1
55°	478.6	511.0	553.2	616.4	686.7	741.1	734.7	666.1	578.1	501.0	442.8
57.5°	421.6	446.0	484.9	544.2	605.9	642.4	619.3	560.8	478.7	415.6	366.5
60°	383.8	406.5	442.8	494.6	549.0	569.6	550.2	486.6	421.8	364.0	322.7
62.5°	348.1	368.1	399.3	447.4	491.3	503.6	482.8	427.3	368.8	319.5	285.3
65°	296.2	314.7	341.3	375.4	405.8	411.6	398.2	341.3	297.0	255.7	232.1
67.5°	249.1	261.2	281.9	311.4	327.6	331.0	304.9	269.2	230.2	204.9	187.0
70°	217.4	225.9	245.2	261.2	274.3	274.7	250.6	222.0	192.1	171.5	158.4
72.5°	186.7	194.8	209.5	220.5	230.4	227.2	205.2	182.6	158.4	142.8	133.2
75°	144.1	151.2	158.8	163.9	163.9	159.7	143.7	126.8	112.9	103.6	100.7
77.5°	104.7	110.7	113.2	112.4	110.9	104.3	94.2	83.2	78.2	73.8	71.6
80°	82.1	84.7	85.6	83.4	80.9	73.3	66.5	61.9	57.3	55.6	54.7
82.5°	60.9	63.1	60.9	61.5	55.9	49.7	46.0	44.4	42.5	41.8	41.0
85°	32.5	32.0	31.2	29.1	25.3	24.4	24.0	23.6	22.7	23.2	22.3
87.5°	11.4	10.6	9.4	9.1	9.1	9.0	9.3	9.5	9.7	9.3	10.1
90°	1.3	2.7	3.2	3.6	3.6	6.3	6.3	7.2	8.2	7.7	8.2
92.5°	7.5	11.7	17.3	23.8	33.3	56.2	91.3	125.5	143.3	119.4	88.7
95°	16.2	20.8	26.7	37.5	56.5	95.8	169.9	277.9	368.3	378.7	334.9
97.5°	26.8	30.7	36.0	45.4	61.3	91.6	152.7	260.2	387.9	475.8	494.7
100°	34.4	37.5	42.9	51.5	66.0	92.6	143.7	235.9	363.3	479.0	545.0
102.5°	42.3	45.1	50.1	58.4	72.1	96.3	141.2	219.6	332.6	451.9	542.5
105°	54.3	56.5	61.9	70.0	83.2	104.8	142.4	205.7	296.4	402.7	506.1
107.5°	66.2	68.5	74.3	82.1	95.0	114.9	149.0	203.1	276.2	362.9	454.6
110°	74.5	76.8	82.2	90.4	102.6	122.5	154.1	203.8	269.3	343.0	423.4



TEST NUMBER: P332933-927

CATALOG NUMBER: S124RDIP-S795D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	82.5	85.2	90.2	98.3	110.5	129.7	159.5	206.0	266.1	331.8	400.7
115°	94.4	97.6	102.1	110.7	122.9	141.0	168.1	210.2	264.4	321.3	377.8
117.5°	106.3	109.1	114.1	122.1	134.8	151.9	176.9	214.5	263.9	316.6	366.5
120°	113.9	117.0	122.0	129.7	142.4	159.5	183.0	217.9	263.9	314.1	361.6
122.5°	121.1	124.3	128.9	137.3	149.6	166.8	188.8	221.1	263.6	311.2	357.2
125°	131.5	134.2	139.2	147.7	160.4	176.7	197.5	225.9	263.0	306.4	349.7
127.5°	139.6	142.8	148.5	157.4	170.2	185.9	205.0	229.8	262.0	300.0	340.7
130°	144.6	148.2	155.0	163.6	176.7	192.0	209.7	232.7	261.7	296.0	333.5
132.5°	148.9	153.7	160.1	169.4	181.7	197.1	214.4	235.3	261.3	292.4	325.9
135°	155.9	160.4	168.1	177.6	189.3	204.2	220.5	239.1	260.7	286.9	315.4
137.5°	162.4	167.4	174.7	184.6	195.7	209.7	224.9	241.3	260.6	282.3	305.9
140°	166.8	171.7	179.4	188.9	199.7	213.3	227.8	243.1	260.3	279.7	300.5
142.5°	171.8	176.4	183.7	192.9	203.4	216.6	229.9	244.5	260.3	277.6	295.5
145°	179.0	183.5	189.8	198.4	208.3	220.1	232.3	245.4	259.4	273.9	288.3
147.5°	186.1	190.0	196.5	203.7	212.7	223.7	234.3	245.8	257.8	270.5	282.4
150°	191.2	194.8	200.2	207.0	215.6	225.5	235.4	245.8	256.7	268.0	278.8
152.5°	195.5	199.1	204.1	210.2	218.1	227.0	236.1	245.1	254.8	265.1	274.8
155°	202.5	205.2	209.7	214.7	221.4	229.1	236.8	244.0	252.2	260.7	268.9
157.5°	208.4	211.0	214.4	218.8	224.1	230.7	236.8	242.9	249.4	256.4	262.4
160°	212.4	214.2	217.4	220.9	225.9	231.4	236.8	241.8	247.2	253.1	258.5
162.5°	215.6	217.1	219.9	223.2	227.0	232.1	236.8	240.7	245.0	250.2	254.5
165°	220.1	220.9	223.2	225.5	228.2	232.3	235.9	238.6	241.8	245.4	249.0
167.5°	223.7	224.1	225.9	227.1	229.2	232.2	234.8	236.5	238.5	241.1	243.7
170°	225.5	225.9	227.3	228.2	229.6	231.8	234.1	235.0	236.3	238.1	240.4
172.5°	227.3	227.4	228.4	228.9	229.9	231.5	233.4	233.5	234.2	235.6	237.5
175°	229.1	229.1	229.6	230.0	230.0	230.9	232.3	231.8	231.8	232.7	233.6
177.5°	230.0	229.7	230.0	230.0	230.0	230.4	231.1	230.4	230.4	230.8	231.1
180°	230.0	230.0	230.0	230.0	230.0	230.0	230.0	230.0	230.0	230.0	230.0



TEST NUMBER: P332933-927

CATALOG NUMBER: S124RDIP-S795D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7
2.5°	1096.9	1098.3	1099.3	1102.6	1103.0	1106.0	1103.0
5°	1187.6	1193.6	1202.8	1212.1	1213.0	1218.9	1208.3
7.5°	1289.4	1303.1	1311.6	1326.6	1332.5	1336.3	1330.2
10°	1359.5	1372.2	1394.6	1405.5	1416.4	1418.2	1413.1
12.5°	1427.4	1447.4	1465.0	1485.7	1485.2	1500.1	1494.6
15°	1517.6	1538.2	1562.7	1585.8	1594.3	1594.3	1601.0
17.5°	1581.9	1619.8	1645.0	1663.3	1683.1	1686.6	1684.3
20°	1625.4	1666.3	1693.3	1716.8	1730.4	1734.1	1734.1
22.5°	1657.8	1692.6	1718.9	1740.1	1751.2	1755.7	1754.4
25°	1680.2	1710.1	1726.1	1732.4	1735.4	1734.6	1726.6
27.5°	1649.5	1648.1	1638.1	1618.7	1604.1	1595.2	1585.2
30°	1590.9	1569.0	1543.7	1515.8	1480.0	1452.7	1444.2
32.5°	1503.6	1454.4	1411.6	1365.2	1326.7	1299.3	1287.9
35°	1334.7	1256.8	1193.2	1137.6	1097.1	1071.8	1063.4
37.5°	1134.3	1058.9	980.2	926.2	892.7	867.1	857.6
40°	1006.9	924.8	856.1	805.6	771.0	746.2	745.8
42.5°	890.7	812.2	747.6	711.1	673.9	657.5	657.4
45°	729.3	666.5	611.7	583.1	560.8	547.3	543.5
47.5°	603.8	551.9	515.4	492.6	474.4	465.8	460.3
50°	533.4	487.9	458.8	439.0	428.9	418.0	417.1
52.5°	474.8	438.0	415.3	399.3	386.4	379.9	380.0
55°	398.9	369.9	353.9	341.7	331.6	326.5	324.4
57.5°	336.1	314.3	302.7	291.4	287.2	283.2	282.1
60°	297.0	282.3	271.3	262.4	256.2	254.9	254.4
62.5°	264.7	249.2	241.7	234.8	230.2	228.2	227.5
65°	218.2	206.8	200.1	194.6	193.0	190.0	189.6
67.5°	175.9	169.1	164.6	160.9	158.6	158.4	158.4
70°	150.0	146.2	142.4	140.3	139.0	138.2	138.2
72.5°	127.8	124.9	121.8	120.7	120.5	119.6	119.3
75°	97.4	94.3	94.8	92.7	91.0	88.9	87.6
77.5°	69.0	66.9	66.5	66.2	64.8	64.6	65.2
80°	53.5	51.4	51.0	51.4	51.0	49.7	49.7
82.5°	40.7	38.9	38.5	38.3	37.9	38.3	37.5
85°	21.9	21.1	21.1	21.1	21.9	21.5	21.1
87.5°	9.5	9.2	9.6	9.3	9.4	9.0	9.3
90°	8.6	9.0	9.0	9.5	9.9	9.5	9.5
92.5°	66.8	53.2	44.1	38.7	36.4	34.8	34.8
95°	264.8	204.2	160.4	138.3	124.3	116.1	110.3
97.5°	468.7	424.5	377.3	344.9	317.7	304.1	294.7
100°	554.1	531.9	498.4	459.1	431.6	418.0	414.4
102.5°	587.3	593.7	579.8	555.6	535.7	521.4	518.5
105°	584.3	629.1	647.6	648.5	644.8	638.5	635.8
107.5°	537.7	600.8	641.0	663.4	673.7	678.2	679.4
110°	501.6	567.1	616.9	649.0	667.9	676.0	680.1



TEST NUMBER: P332933-927

CATALOG NUMBER: S124RDIP-S795D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	469.8	531.7	581.4	617.8	640.8	652.2	658.8
115°	433.4	486.2	529.7	565.3	592.5	606.9	610.5
117.5°	412.6	454.2	490.9	521.4	544.2	558.8	561.7
120°	403.5	439.7	471.7	497.6	517.5	529.2	534.2
122.5°	397.8	430.6	458.8	480.5	497.6	507.5	512.5
125°	388.6	419.8	444.7	462.7	475.9	484.4	487.1
127.5°	377.9	409.0	432.5	450.8	462.4	469.6	472.3
130°	369.2	399.9	423.9	442.4	453.7	461.0	463.7
132.5°	359.4	389.4	413.4	431.6	444.3	451.1	453.9
135°	344.8	372.3	395.0	413.0	425.7	432.9	435.6
137.5°	330.8	354.0	374.5	391.3	403.9	409.8	413.0
140°	321.8	342.1	361.1	376.9	386.8	393.2	396.8
142.5°	314.2	331.6	348.1	362.0	371.3	376.9	379.4
145°	303.6	317.3	329.9	341.2	348.9	353.4	355.6
147.5°	294.6	305.5	315.4	323.8	330.3	333.7	334.6
150°	289.2	298.3	306.4	313.6	319.5	322.2	322.7
152.5°	283.8	292.1	298.8	304.9	309.7	311.3	311.8
155°	276.1	282.9	288.3	292.9	296.4	297.8	297.8
157.5°	268.5	274.2	278.5	282.0	284.7	285.5	285.5
160°	263.5	268.4	272.0	274.7	277.5	277.9	277.9
162.5°	258.7	262.6	265.9	267.9	270.6	271.1	270.7
165°	251.7	254.8	257.1	259.0	260.7	260.3	259.8
167.5°	245.7	248.3	249.6	250.6	251.7	251.6	251.3
170°	241.8	243.6	244.9	245.8	246.3	245.8	245.8
172.5°	238.5	239.6	240.6	241.1	241.6	241.1	240.4
175°	234.1	235.0	235.0	235.0	235.9	235.0	234.1
177.5°	231.5	231.5	231.8	231.5	231.8	231.1	230.4
180°	230.0	230.0	230.0	230.0	230.0	230.0	230.0

(END OF REPORT)