

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332699-830

Luminaire Tested: **S124DIP-S1195D1035U830-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332699-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIP-S1195D1035U830-4F0-1E-UDD-A4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1195 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8498.0 lumens  
Efficiency: N/A  
Efficacy: 127.2 lumens/watt  
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 66.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332699-830

CATALOG NUMBER: S124DIP-S1195D1035U830-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P332699-830

CATALOG NUMBER: S124DIP-S1195D1035U830-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59
1	100	96	92	88	93	90	86	83	78	75	73	67	65	64	57	56	55	50
2	91	84	78	73	85	79	73	69	69	65	61	59	56	54	51	49	47	42
3	84	74	67	61	78	69	63	58	61	56	52	53	49	46	45	42	40	36
4	77	66	58	52	71	62	55	49	54	49	44	47	43	39	41	37	35	31
5	70	59	51	45	66	55	48	43	49	43	38	42	38	34	37	33	30	27
6	65	53	45	39	60	50	42	37	44	38	34	38	34	30	33	30	27	24
7	60	48	40	34	56	45	38	33	40	34	30	35	30	27	31	27	24	22
8	56	44	36	30	52	41	34	29	36	31	27	32	27	24	28	24	22	19
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	26	22	20	17
10	49	37	29	24	46	35	28	24	31	25	22	27	23	20	24	20	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	14666	14666	14666	14666
5°	17271	14704	12977	14704
10°	20678	14638	11684	14638
15°	24466	14491	10730	14491
20°	27244	14339	9879	14339
25°	27684	14118	9291	14118
30°	23557	13904	9106	13904
35°	18111	13557	9107	13557
40°	14116	13149	9278	13149
45°	11771	12536	9434	12536
50°	10359	11786	9755	11786
55°	9491	10888	10148	10888
60°	8893	10085	10619	10085
65°	8281	9186	11012	9186
70°	7567	8297	11261	8297
75°	6759	7299	11126	7299
80°	5667	5983	10776	5983
85°	4177	4326	10319	4326



TEST NUMBER: P332699-830

CATALOG NUMBER: S124DIP-S1195D1035U830-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	177.0	2.1
10°-20°	545.5	6.4
20°-30°	865.0	10.2
30°-40°	962.7	11.3
40°-50°	876.3	10.3
50°-60°	716.1	8.4
60°-70°	511.2	6.0
70°-80°	281.5	3.3
80°-90°	79.5	0.9
90°-100°	345.9	4.1
100°-110°	720.0	8.5
110°-120°	644.9	7.6
120°-130°	542.4	6.4
130°-140°	452.3	5.3
140°-150°	345.5	4.1
150°-160°	242.9	2.9
160°-170°	142.9	1.7
170°-180°	46.5	0.5
0°-30°	1587.5	18.7
0°-40°	2550.2	30.0
0°-60°	4142.6	48.7
0°-90°	5014.8	59.0
90°-120°	1710.8	20.1
90°-150°	3051.1	35.9
90°-180°	3483.0	41.0
0°-180°	8498.0	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1817	1817	1817	1817	1817	
5°	2131	1814	1601	1814	2131	217
15°	2927	1734	1284	1734	2927	827
25°	3108	1585	1043	1585	3108	1370
35°	1838	1376	924	1376	1838	1166
45°	1031	1098	826	1098	1031	812
55°	674	774	721	774	674	609
65°	434	481	576	481	434	429
75°	217	234	357	234	217	230
85°	45	47	111	47	45	55
90°	20	1	20	1	20	18
95°	230	31	230	31	230	356
105°	1324	110	1324	110	1324	1309
115°	1271	194	1271	194	1271	1262
125°	1014	270	1014	270	1014	922
135°	907	321	907	321	907	700
145°	741	370	741	370	741	469
155°	620	421	620	421	620	289
165°	541	458	541	458	541	155
175°	487	478	487	478	487	47
180°	479	479	479	479	479	



TEST NUMBER: P332699-830

CATALOG NUMBER: S124DIP-S1195D1035U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7
2.5°	1933.4	1932.8	1926.8	1925.6	1921.4	1916.0	1914.8	1905.2	1885.8	1876.8	1874.4
5°	2131.2	2146.3	2126.7	2122.9	2120.6	2095.8	2083.0	2067.9	2033.3	2013.1	1997.2
7.5°	2367.2	2369.0	2360.4	2353.5	2334.4	2312.7	2280.2	2245.6	2204.3	2161.4	2129.1
10°	2522.5	2528.6	2518.8	2517.2	2478.9	2454.8	2406.6	2366.0	2319.3	2267.4	2220.0
12.5°	2686.2	2677.9	2672.9	2640.6	2633.6	2589.6	2533.6	2491.8	2419.9	2360.1	2297.1
15°	2927.3	2910.9	2900.3	2855.9	2834.0	2773.1	2713.7	2667.8	2573.7	2484.2	2416.4
17.5°	3068.8	3085.4	3061.0	3042.8	2986.4	2943.7	2882.9	2786.5	2712.9	2601.7	2516.2
20°	3171.2	3172.7	3159.1	3140.4	3096.0	3041.8	2975.5	2870.1	2782.1	2671.5	2554.1
22.5°	3198.9	3199.2	3193.4	3175.9	3142.2	3098.3	3031.5	2943.7	2837.0	2716.7	2599.2
25°	3107.9	3104.9	3111.7	3131.3	3118.5	3104.9	3066.6	3001.1	2901.8	2774.6	2648.2
27.5°	2770.2	2791.0	2829.2	2877.4	2923.8	2959.1	2969.1	2955.6	2894.1	2789.5	2657.0
30°	2527.1	2552.6	2581.2	2629.3	2722.7	2776.1	2834.8	2879.2	2854.4	2770.9	2647.4
32.5°	2259.7	2266.1	2308.5	2363.2	2448.7	2551.6	2644.6	2734.7	2764.7	2720.8	2617.9
35°	1837.7	1848.2	1894.1	1948.3	2053.0	2178.6	2318.6	2443.4	2546.6	2587.9	2535.3
37.5°	1499.7	1529.9	1562.3	1620.5	1712.6	1825.8	1971.2	2132.9	2286.5	2389.4	2406.9
40°	1339.5	1358.3	1381.7	1426.1	1504.3	1615.7	1740.6	1925.7	2089.1	2236.6	2284.7
42.5°	1213.1	1224.1	1238.4	1278.6	1338.1	1449.0	1563.0	1725.9	1889.8	2066.1	2146.8
45°	1031.0	1042.3	1066.3	1089.7	1134.8	1211.5	1317.7	1451.6	1616.5	1786.5	1935.5
47.5°	899.5	906.6	921.0	945.9	984.3	1034.9	1121.2	1233.1	1385.9	1551.0	1709.8
50°	824.8	830.8	842.1	864.7	894.0	939.1	1009.9	1114.5	1234.2	1400.4	1556.2
52.5°	765.8	768.2	776.5	791.8	815.1	853.1	911.2	997.7	1108.9	1257.2	1412.4
55°	674.3	677.3	684.9	696.1	716.4	740.5	784.9	849.6	946.7	1075.3	1210.0
57.5°	599.0	601.2	607.5	611.8	628.5	648.1	682.2	728.5	802.0	911.2	1031.4
60°	550.8	549.3	556.9	560.6	571.9	588.5	614.8	659.2	723.2	811.2	921.9
62.5°	503.9	501.8	508.1	513.1	519.5	533.7	555.3	590.0	641.9	721.5	817.1
65°	433.5	430.5	434.2	440.3	446.3	453.7	469.6	500.4	541.9	599.0	672.0
67.5°	362.7	365.9	366.5	369.5	373.0	383.2	394.0	415.8	445.1	490.8	552.7
70°	320.6	321.3	324.3	324.3	326.6	335.6	344.7	357.4	386.1	428.2	478.6
72.5°	278.4	281.6	280.4	282.8	284.5	290.5	297.1	309.2	333.7	365.0	407.6
75°	216.7	219.0	219.0	219.7	222.0	224.2	229.5	238.6	255.9	279.2	308.5
77.5°	158.1	158.3	159.4	162.1	162.1	165.7	169.7	176.8	185.4	201.4	219.3
80°	121.9	123.4	122.6	124.1	124.1	127.1	128.7	137.7	141.5	152.0	166.3
82.5°	89.4	90.9	90.8	92.8	94.1	94.6	96.8	100.4	104.2	113.5	119.3
85°	45.1	46.7	45.1	46.7	48.9	49.7	51.9	52.7	55.7	58.0	63.2
87.5°	17.2	19.0	19.2	19.6	20.6	21.2	21.7	20.8	23.1	23.8	25.9
90°	19.8	19.8	20.7	19.8	18.9	18.9	17.9	17.0	16.0	17.0	15.1
92.5°	72.5	72.5	75.7	80.8	91.8	110.7	139.1	184.8	248.6	298.5	261.2
95°	229.6	241.9	258.7	287.9	334.0	425.3	551.4	697.2	788.5	766.9	578.7
97.5°	613.7	633.3	661.5	718.1	785.7	883.9	975.9	1030.2	990.6	807.7	541.6
100°	862.9	870.3	898.6	956.0	1037.8	1107.5	1153.6	1134.8	997.4	756.5	491.2
102.5°	1079.7	1085.7	1115.4	1157.0	1207.2	1236.2	1222.9	1129.5	940.9	692.6	457.3
105°	1323.9	1329.6	1342.7	1350.3	1348.4	1309.8	1216.6	1053.9	838.4	617.3	428.1
107.5°	1414.7	1412.2	1402.8	1381.3	1334.8	1250.9	1119.7	946.4	755.5	575.1	422.8
110°	1416.2	1407.7	1390.7	1351.2	1284.4	1180.9	1044.4	881.7	714.2	560.8	424.3



TEST NUMBER: P332699-830

CATALOG NUMBER: S124DIP-S1195D1035U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1371.7	1358.0	1334.3	1286.5	1210.6	1107.1	978.2	834.2	690.9	554.0	428.9
115°	1271.2	1263.7	1233.6	1177.1	1102.8	1012.5	902.4	786.6	669.0	550.4	437.5
117.5°	1169.4	1163.6	1133.1	1085.7	1022.3	945.7	859.1	763.3	659.2	549.5	446.8
120°	1112.2	1101.8	1077.4	1035.9	982.3	915.6	840.3	752.7	653.9	549.5	453.6
122.5°	1067.1	1056.7	1035.9	1000.6	955.3	896.7	828.2	743.8	647.9	548.7	460.3
125°	1014.4	1008.7	990.8	963.6	925.9	874.1	809.2	728.3	638.0	547.6	470.5
127.5°	983.4	977.8	962.8	938.5	900.7	851.6	786.8	709.5	624.6	545.5	478.5
130°	965.4	959.8	944.7	921.1	882.6	832.7	768.7	694.5	616.3	544.8	484.6
132.5°	945.1	939.4	925.1	898.6	860.8	810.9	748.5	678.6	608.8	544.0	489.8
135°	907.1	901.4	886.4	860.1	822.4	775.3	717.9	656.8	597.5	542.9	497.8
137.5°	860.1	853.3	840.8	814.8	779.7	737.2	688.8	637.1	587.7	542.7	502.5
140°	826.1	818.6	805.5	784.8	751.8	712.3	670.0	625.8	582.5	542.0	506.2
142.5°	790.0	784.8	773.1	753.8	724.7	690.5	654.1	615.2	578.0	542.0	509.3
145°	740.6	735.8	726.4	710.4	686.9	660.5	632.4	600.3	570.2	540.1	511.0
147.5°	696.6	695.0	687.9	674.1	656.8	636.1	613.5	588.1	563.3	536.7	511.9
150°	671.8	670.9	665.2	653.0	638.0	621.0	602.2	580.6	558.0	534.4	511.9
152.5°	649.2	648.3	644.9	635.0	622.2	608.2	590.9	572.3	552.0	530.7	510.4
155°	620.1	620.1	617.3	609.7	600.3	589.0	575.0	559.9	542.9	525.1	508.1
157.5°	594.5	594.5	592.8	587.1	580.0	571.0	559.1	546.5	533.7	519.2	505.7
160°	578.7	578.7	577.8	572.1	566.5	558.9	548.6	538.2	527.0	514.7	503.4
162.5°	563.6	564.4	563.5	557.8	553.6	546.9	538.8	529.9	520.9	510.2	501.1
165°	541.0	542.0	542.9	539.1	535.4	530.7	524.1	518.5	511.0	503.4	496.8
167.5°	523.2	524.0	524.1	521.7	519.8	517.0	511.7	507.4	501.9	496.6	492.3
170°	511.9	511.9	512.8	511.9	510.0	507.2	503.4	500.6	495.9	492.1	489.3
172.5°	500.6	502.1	503.0	502.1	501.0	498.9	496.6	494.6	490.6	487.6	486.3
175°	487.4	489.3	491.2	489.3	489.3	489.3	487.4	486.4	484.6	482.7	482.7
177.5°	479.7	481.2	482.7	481.9	482.7	481.9	481.9	481.2	480.4	479.7	479.7
180°	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9



TEST NUMBER: P332699-830

CATALOG NUMBER: S124DIP-S1195D1035U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7
2.5°	1875.0	1866.6	1860.6	1855.8	1842.5	1834.7	1828.6	1820.2	1810.6	1800.4	1787.7
5°	1981.4	1955.9	1937.0	1908.5	1881.3	1858.8	1835.4	1814.4	1788.8	1761.0	1740.6
7.5°	2093.3	2055.2	2006.4	1964.2	1916.6	1875.2	1838.1	1800.3	1760.8	1722.6	1687.5
10°	2164.3	2115.3	2061.2	1997.2	1937.0	1883.6	1833.9	1785.7	1739.1	1692.4	1652.6
12.5°	2240.8	2179.8	2099.7	2025.0	1957.5	1886.0	1826.1	1767.1	1710.8	1661.8	1615.2
15°	2343.4	2255.3	2162.8	2062.7	1973.9	1890.4	1808.4	1733.8	1670.7	1605.9	1560.8
17.5°	2406.5	2297.5	2191.7	2087.1	1979.6	1874.2	1785.7	1699.9	1620.7	1556.4	1499.5
20°	2448.0	2339.7	2207.9	2103.4	1975.4	1867.1	1764.7	1669.1	1586.4	1517.9	1459.2
22.5°	2484.2	2358.9	2227.2	2089.5	1962.2	1847.2	1735.2	1639.0	1554.4	1482.3	1426.1
25°	2503.7	2359.9	2217.0	2080.0	1935.5	1799.3	1697.7	1584.9	1494.5	1418.5	1358.3
27.5°	2505.8	2352.1	2190.4	2038.2	1889.0	1762.2	1633.9	1533.0	1439.3	1359.0	1301.2
30°	2499.2	2338.9	2165.0	2000.3	1850.5	1712.8	1601.4	1491.6	1396.0	1316.2	1255.9
32.5°	2478.1	2311.2	2132.5	1958.1	1802.9	1668.2	1553.2	1448.8	1355.7	1277.1	1213.8
35°	2417.2	2252.3	2061.9	1880.6	1721.8	1585.6	1481.8	1375.6	1282.3	1207.9	1146.9
37.5°	2321.9	2172.8	1979.3	1791.7	1635.7	1498.9	1396.0	1300.0	1216.0	1140.3	1077.8
40°	2238.8	2107.9	1913.7	1730.8	1562.3	1432.1	1335.8	1247.7	1164.1	1092.7	1033.2
42.5°	2143.1	2029.0	1849.9	1656.1	1493.6	1362.8	1268.9	1189.9	1111.2	1045.1	985.7
45°	1972.4	1897.1	1728.6	1549.4	1380.2	1256.7	1167.2	1098.0	1031.7	967.0	917.4
47.5°	1776.1	1738.8	1596.9	1426.8	1266.0	1144.4	1066.8	1002.9	944.7	889.9	846.1
50°	1644.3	1626.3	1503.5	1339.5	1186.0	1071.6	993.3	938.4	888.7	840.6	799.2
52.5°	1514.3	1513.6	1403.1	1252.8	1110.8	1000.6	922.9	871.6	828.6	789.4	752.2
55°	1315.4	1336.5	1250.0	1116.0	988.8	889.5	819.5	773.6	743.5	711.1	683.3
57.5°	1132.8	1167.8	1096.5	978.5	872.3	780.8	719.9	685.4	653.4	633.8	613.5
60°	1013.7	1046.8	991.1	891.7	791.6	713.4	655.4	624.6	596.7	583.2	568.9
62.5°	907.7	937.2	896.0	803.9	717.0	641.8	592.9	563.2	544.4	529.6	520.2
65°	756.3	781.2	745.7	678.8	604.3	544.1	504.2	480.9	462.8	456.8	446.3
67.5°	611.3	634.0	614.8	557.9	498.1	452.6	421.4	399.0	388.3	383.0	375.5
70°	525.3	547.8	527.5	477.9	432.0	393.6	364.2	351.5	340.2	337.9	327.3
72.5°	452.4	467.8	447.4	408.6	369.4	337.0	314.2	300.9	295.0	291.0	285.2
75°	339.4	353.0	339.4	309.2	281.4	258.9	239.3	234.0	227.2	225.0	221.2
77.5°	240.3	251.9	241.6	222.7	202.0	184.5	174.0	167.2	165.7	161.8	163.6
80°	183.6	191.1	181.3	168.5	152.0	140.0	132.4	128.7	124.1	122.6	125.6
82.5°	131.9	135.2	130.2	121.6	109.2	101.4	96.3	92.0	91.0	91.3	91.3
85°	68.5	67.8	67.0	59.5	55.7	50.4	47.4	46.7	45.9	47.4	48.9
87.5°	25.5	26.1	24.4	22.0	20.0	18.0	16.8	15.8	16.8	18.0	18.8
90°	13.2	13.2	7.5	7.5	6.6	5.7	2.8	0.9	2.8	5.7	6.6
92.5°	190.1	117.1	69.3	49.7	35.9	24.5	15.6	10.7	15.6	24.5	35.9
95°	353.8	199.4	117.6	78.1	55.5	43.3	33.8	31.0	33.8	43.3	55.5
97.5°	318.0	190.7	127.6	94.4	75.1	63.8	55.7	55.7	55.7	63.8	75.1
100°	299.3	192.9	137.4	107.3	89.4	78.1	71.5	71.5	71.5	78.1	89.4
102.5°	294.0	200.4	150.1	121.6	104.4	93.9	88.0	86.5	88.0	93.9	104.4
105°	296.4	218.3	173.1	145.8	128.9	117.6	112.9	110.1	112.9	117.6	128.9
107.5°	310.3	239.2	197.7	170.9	154.7	142.6	138.0	136.1	138.0	142.6	154.7
110°	320.8	255.0	213.6	188.2	171.3	159.9	155.2	153.4	155.2	159.9	171.3





TEST NUMBER: P332699-830

CATALOG NUMBER: S124DIP-S1195D1035U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	332.2	270.0	230.2	204.7	187.8	177.3	171.8	169.9	171.8	177.3	187.8
115°	350.1	293.6	255.9	230.5	212.6	203.2	196.6	193.9	196.6	203.2	212.6
117.5°	368.3	316.3	280.6	254.2	237.5	227.2	221.3	218.7	221.3	227.2	237.5
120°	381.1	332.2	296.4	270.0	254.0	243.7	237.1	235.3	237.1	243.7	254.0
122.5°	393.1	347.2	311.4	285.9	268.3	258.7	252.1	250.3	252.1	258.7	268.3
125°	411.2	367.9	334.0	307.6	289.8	279.5	273.8	270.0	273.8	279.5	289.8
127.5°	426.8	387.1	354.4	327.8	309.2	297.4	290.6	287.6	290.6	297.4	309.2
130°	436.6	399.9	367.9	340.6	322.7	308.6	301.1	297.4	301.1	308.6	322.7
132.5°	446.4	410.5	378.4	352.7	333.3	319.9	310.1	307.1	310.1	319.9	333.3
135°	459.2	425.3	394.3	369.8	350.1	334.0	324.6	320.8	324.6	334.0	350.1
137.5°	468.3	436.6	407.6	384.3	363.7	348.6	338.2	334.6	338.2	348.6	363.7
140°	474.2	444.1	415.9	393.3	373.5	357.6	347.2	344.4	347.2	357.6	373.5
142.5°	478.7	450.9	423.4	401.6	382.6	367.3	357.8	355.0	357.8	367.3	382.6
145°	483.6	458.3	433.8	413.1	395.2	382.0	372.6	369.8	372.6	382.0	395.2
147.5°	488.0	465.8	442.8	424.1	409.3	395.8	387.5	386.5	387.5	395.8	409.3
150°	490.2	469.6	448.8	430.9	416.9	405.6	398.0	397.1	398.0	405.6	416.9
152.5°	491.7	472.6	454.1	437.7	425.1	414.6	407.1	406.9	407.1	414.6	425.1
155°	493.0	477.0	461.1	447.0	436.6	427.2	421.5	420.6	421.5	427.2	436.6
157.5°	493.0	480.2	466.7	455.6	446.6	439.2	433.9	433.9	433.9	439.2	446.6
160°	493.0	481.7	470.5	460.1	452.6	446.0	442.2	442.2	442.2	446.0	452.6
162.5°	493.0	483.2	472.8	464.7	457.9	452.0	449.0	449.8	449.0	452.0	457.9
165°	491.2	483.6	475.1	469.6	464.9	460.1	458.3	458.3	458.3	460.1	464.9
167.5°	488.9	483.4	477.2	473.0	470.3	466.7	465.8	466.7	465.8	466.7	470.3
170°	487.4	482.7	478.0	475.1	473.3	470.5	469.6	470.5	469.6	470.5	473.3
172.5°	485.9	481.9	478.7	476.6	475.5	473.4	473.3	474.2	473.3	473.4	475.5
175°	483.6	480.8	478.9	478.9	478.0	477.0	477.0	478.0	477.0	477.0	478.0
177.5°	481.2	479.7	478.9	478.9	478.9	478.2	478.9	479.7	478.9	478.2	478.9
180°	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9



TEST NUMBER: P332699-830

CATALOG NUMBER: S124DIP-S1195D1035U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7
2.5°	1781.7	1776.3	1768.5	1757.7	1748.6	1739.0	1736.5	1733.0	1740.1	1734.2	1732.3
5°	1723.3	1707.5	1687.2	1663.9	1650.3	1630.8	1627.0	1619.5	1611.9	1611.2	1603.6
7.5°	1661.4	1638.2	1611.7	1587.8	1565.8	1544.5	1530.5	1527.5	1516.4	1509.9	1502.3
10°	1621.7	1593.1	1562.3	1539.7	1514.1	1491.6	1475.7	1466.7	1459.2	1450.9	1443.4
12.5°	1574.8	1544.4	1518.9	1494.5	1464.1	1447.0	1421.0	1405.3	1403.8	1403.9	1384.4
15°	1520.1	1490.1	1450.9	1416.3	1399.7	1366.6	1352.3	1334.3	1323.0	1311.6	1302.7
17.5°	1457.6	1420.2	1389.6	1349.9	1318.3	1291.9	1273.2	1262.3	1245.3	1229.4	1217.8
20°	1418.5	1378.7	1346.3	1304.1	1269.5	1237.2	1221.3	1206.4	1193.5	1180.0	1167.2
22.5°	1378.8	1337.1	1297.5	1256.6	1224.4	1190.2	1175.0	1154.5	1142.4	1134.8	1122.0
25°	1316.2	1271.0	1225.9	1186.8	1153.7	1123.5	1103.2	1087.4	1073.8	1067.8	1059.6
27.5°	1248.1	1203.3	1159.7	1115.2	1077.6	1055.8	1039.5	1027.7	1019.8	1011.8	1008.1
30°	1204.9	1158.2	1111.5	1070.1	1035.5	1013.7	998.6	990.3	984.3	980.5	976.8
32.5°	1160.8	1114.8	1065.7	1027.9	996.9	977.5	966.1	957.8	954.8	953.5	952.2
35°	1090.4	1043.8	998.6	964.8	935.4	927.8	918.1	913.6	912.1	917.4	919.6
37.5°	1022.3	978.9	937.4	904.6	885.3	874.3	871.0	871.1	876.6	881.2	886.6
40°	978.3	936.1	897.0	868.5	850.4	843.6	842.1	845.8	851.9	857.1	863.2
42.5°	935.6	894.0	858.5	831.7	819.1	812.8	813.8	817.6	826.0	832.5	841.5
45°	869.2	834.5	799.9	778.2	767.6	769.1	769.1	775.9	784.1	793.9	803.7
47.5°	806.7	771.8	743.4	725.0	719.5	718.2	722.5	731.3	743.2	755.3	768.9
50°	764.6	731.5	706.6	690.0	684.1	686.4	692.3	700.6	714.9	730.0	744.2
52.5°	721.8	691.7	668.7	653.4	649.1	653.2	659.2	672.3	684.9	701.1	718.4
55°	655.4	629.9	611.8	600.5	599.0	601.2	608.0	622.4	640.4	660.7	677.3
57.5°	589.4	568.0	551.5	543.7	544.4	546.5	557.6	574.7	593.9	615.6	637.0
60°	544.8	525.3	511.7	505.7	506.4	511.0	524.5	540.4	564.4	585.5	608.0
62.5°	502.7	485.5	472.6	467.2	466.1	476.1	489.0	505.4	529.5	553.0	577.3
65°	435.0	421.4	410.9	407.8	410.1	417.6	434.2	456.0	476.4	501.1	526.8
67.5°	368.7	357.6	350.3	351.8	354.5	365.6	379.5	398.2	421.3	447.0	472.3
70°	326.6	316.0	310.0	310.8	315.3	328.9	340.9	359.7	384.6	410.9	432.0
72.5°	283.2	276.4	270.9	274.1	278.6	287.9	302.9	321.8	343.7	368.2	390.4
75°	217.4	217.4	214.4	216.7	223.5	232.5	243.8	263.3	285.2	304.8	322.8
77.5°	161.4	159.7	161.6	164.4	168.2	179.0	191.9	205.9	222.3	241.9	256.7
80°	123.4	124.1	127.9	132.4	133.9	142.2	155.8	168.5	181.3	197.9	212.3
82.5°	92.7	93.5	95.4	101.1	102.6	111.5	120.3	133.1	144.7	155.8	167.7
85°	50.4	50.4	54.2	56.5	60.2	66.3	71.4	79.0	89.5	97.1	108.4
87.5°	20.7	20.7	24.3	25.5	27.7	31.1	32.1	38.9	41.5	44.7	50.1
90°	7.5	7.5	13.2	13.2	15.1	17.0	16.0	17.0	17.9	18.9	18.9
92.5°	49.7	69.3	117.1	190.1	261.2	298.5	248.6	184.8	139.1	110.7	91.8
95°	78.1	117.6	199.4	353.8	578.7	766.9	788.5	697.2	551.4	425.3	334.0
97.5°	94.4	127.6	190.7	318.0	541.6	807.7	990.6	1030.2	975.9	883.9	785.7
100°	107.3	137.4	192.9	299.3	491.2	756.5	997.4	1134.8	1153.6	1107.5	1037.8
102.5°	121.6	150.1	200.4	294.0	457.3	692.6	940.9	1129.5	1222.9	1236.2	1207.2
105°	145.8	173.1	218.3	296.4	428.1	617.3	838.4	1053.9	1216.6	1309.8	1348.4
107.5°	170.9	197.7	239.2	310.3	422.8	575.1	755.5	946.4	1119.7	1250.9	1334.8
110°	188.2	213.6	255.0	320.8	424.3	560.8	714.2	881.7	1044.4	1180.9	1284.4



TEST NUMBER: P332699-830

CATALOG NUMBER: S124DIP-S1195D1035U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	204.7	230.2	270.0	332.2	428.9	554.0	690.9	834.2	978.2	1107.1	1210.6
115°	230.5	255.9	293.6	350.1	437.5	550.4	669.0	786.6	902.4	1012.5	1102.8
117.5°	254.2	280.6	316.3	368.3	446.8	549.5	659.2	763.3	859.1	945.7	1022.3
120°	270.0	296.4	332.2	381.1	453.6	549.5	653.9	752.7	840.3	915.6	982.3
122.5°	285.9	311.4	347.2	393.1	460.3	548.7	647.9	743.8	828.2	896.7	955.3
125°	307.6	334.0	367.9	411.2	470.5	547.6	638.0	728.3	809.2	874.1	925.9
127.5°	327.8	354.4	387.1	426.8	478.5	545.5	624.6	709.5	786.8	851.6	900.7
130°	340.6	367.9	399.9	436.6	484.6	544.8	616.3	694.5	768.7	832.7	882.6
132.5°	352.7	378.4	410.5	446.4	489.8	544.0	608.8	678.6	748.5	810.9	860.8
135°	369.8	394.3	425.3	459.2	497.8	542.9	597.5	656.8	717.9	775.3	822.4
137.5°	384.3	407.6	436.6	468.3	502.5	542.7	587.7	637.1	688.8	737.2	779.7
140°	393.3	415.9	444.1	474.2	506.2	542.0	582.5	625.8	670.0	712.3	751.8
142.5°	401.6	423.4	450.9	478.7	509.3	542.0	578.0	615.2	654.1	690.5	724.7
145°	413.1	433.8	458.3	483.6	511.0	540.1	570.2	600.3	632.4	660.5	686.9
147.5°	424.1	442.8	465.8	488.0	511.9	536.7	563.3	588.1	613.5	636.1	656.8
150°	430.9	448.8	469.6	490.2	511.9	534.4	558.0	580.6	602.2	621.0	638.0
152.5°	437.7	454.1	472.6	491.7	510.4	530.7	552.0	572.3	590.9	608.2	622.2
155°	447.0	461.1	477.0	493.0	508.1	525.1	542.9	559.9	575.0	589.0	600.3
157.5°	455.6	466.7	480.2	493.0	505.7	519.2	533.7	546.5	559.1	571.0	580.0
160°	460.1	470.5	481.7	493.0	503.4	514.7	527.0	538.2	548.6	558.9	566.5
162.5°	464.7	472.8	483.2	493.0	501.1	510.2	520.9	529.9	538.8	546.9	553.6
165°	469.6	475.1	483.6	491.2	496.8	503.4	511.0	518.5	524.1	530.7	535.4
167.5°	473.0	477.2	483.4	488.9	492.3	496.6	501.9	507.4	511.7	517.0	519.8
170°	475.1	478.0	482.7	487.4	489.3	492.1	495.9	500.6	503.4	507.2	510.0
172.5°	476.6	478.7	481.9	485.9	486.3	487.6	490.6	494.6	496.6	498.9	501.0
175°	478.9	478.9	480.8	483.6	482.7	482.7	484.6	486.4	487.4	489.3	489.3
177.5°	478.9	478.9	479.7	481.2	479.7	479.7	480.4	481.2	481.9	481.9	482.7
180°	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9



TEST NUMBER: P332699-830

CATALOG NUMBER: S124DIP-S1195D1035U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7
2.5°	1731.2	1729.9	1725.7	1725.1	1725.7	1729.9	1731.2	1732.3	1734.2	1740.1	1733.0
5°	1599.1	1595.3	1593.1	1601.4	1593.1	1595.3	1599.1	1603.6	1611.2	1611.9	1619.5
7.5°	1499.7	1496.7	1490.1	1487.9	1490.1	1496.7	1499.7	1502.3	1509.9	1516.4	1527.5
10°	1435.9	1432.9	1426.8	1425.3	1426.8	1432.9	1435.9	1443.4	1450.9	1459.2	1466.7
12.5°	1374.4	1368.4	1367.3	1368.8	1367.3	1368.4	1374.4	1384.4	1403.9	1403.8	1405.3
15°	1292.9	1289.9	1281.6	1283.8	1281.6	1289.9	1292.9	1302.7	1311.6	1323.0	1334.3
17.5°	1212.5	1208.9	1198.8	1207.7	1198.8	1208.9	1212.5	1217.8	1229.4	1245.3	1262.3
20°	1161.9	1155.9	1150.7	1149.9	1150.7	1155.9	1161.9	1167.2	1180.0	1193.5	1206.4
22.5°	1113.7	1108.3	1107.9	1103.0	1107.9	1108.3	1113.7	1122.0	1134.8	1142.4	1154.5
25°	1053.6	1048.3	1046.8	1043.0	1046.8	1048.3	1053.6	1059.6	1067.8	1073.8	1087.4
27.5°	1007.4	1004.8	1002.1	1003.2	1002.1	1004.8	1007.4	1008.1	1011.8	1019.8	1027.7
30°	979.0	978.3	976.8	976.8	976.8	978.3	979.0	976.8	980.5	984.3	990.3
32.5°	955.5	955.5	956.3	956.3	956.3	955.5	955.5	952.2	953.5	954.8	957.8
35°	922.7	924.8	926.3	924.1	926.3	924.8	922.7	919.6	917.4	912.1	913.6
37.5°	892.8	895.0	897.2	899.8	897.2	895.0	892.8	886.6	881.2	876.6	871.1
40°	870.0	875.2	876.7	880.4	876.7	875.2	870.0	863.2	857.1	851.9	845.8
42.5°	848.3	854.1	858.0	858.8	858.0	854.1	848.3	841.5	832.5	826.0	817.6
45°	815.0	821.0	826.3	826.3	826.3	821.0	815.0	803.7	793.9	784.1	775.9
47.5°	780.5	789.3	794.6	795.9	794.6	789.3	780.5	768.9	755.3	743.2	731.3
50°	757.1	767.6	772.9	776.7	772.9	767.6	757.1	744.2	730.0	714.9	700.6
52.5°	734.1	744.7	751.8	753.8	751.8	744.7	734.1	718.4	701.1	684.9	672.3
55°	694.6	709.6	717.9	721.0	717.9	709.6	694.6	677.3	660.7	640.4	622.4
57.5°	657.2	671.1	680.7	683.0	680.7	671.1	657.2	637.0	615.6	593.9	574.7
60°	628.4	643.4	655.4	657.7	655.4	643.4	628.4	608.0	585.5	564.4	540.4
62.5°	598.9	614.5	625.4	631.2	625.4	614.5	598.9	577.3	553.0	529.5	505.4
65°	547.8	563.6	574.2	576.5	574.2	563.6	547.8	526.8	501.1	476.4	456.0
67.5°	492.2	507.9	514.9	519.2	514.9	507.9	492.2	472.3	447.0	421.3	398.2
70°	453.0	465.8	473.3	477.1	473.3	465.8	453.0	432.0	410.9	384.6	359.7
72.5°	408.5	421.9	430.6	431.3	430.6	421.9	408.5	390.4	368.2	343.7	321.8
75°	340.2	352.2	356.7	356.7	356.7	352.2	340.2	322.8	304.8	285.2	263.3
77.5°	269.3	275.4	281.2	282.4	281.2	275.4	269.3	256.7	241.9	222.3	205.9
80°	223.5	227.2	231.8	231.8	231.8	227.2	223.5	212.3	197.9	181.3	168.5
82.5°	176.5	179.7	184.3	183.6	184.3	179.7	176.5	167.7	155.8	144.7	133.1
85°	106.9	113.7	112.9	111.4	112.9	113.7	106.9	108.4	97.1	89.5	79.0
87.5°	52.1	52.9	54.5	55.7	54.5	52.9	52.1	50.1	44.7	41.5	38.9
90°	19.8	20.7	19.8	19.8	19.8	20.7	19.8	18.9	18.9	17.9	17.0
92.5°	80.8	75.7	72.5	72.5	72.5	75.7	80.8	91.8	110.7	139.1	184.8
95°	287.9	258.7	241.9	229.6	241.9	258.7	287.9	334.0	425.3	551.4	697.2
97.5°	718.1	661.5	633.3	613.7	633.3	661.5	718.1	785.7	883.9	975.9	1030.2
100°	956.0	898.6	870.3	862.9	870.3	898.6	956.0	1037.8	1107.5	1153.6	1134.8
102.5°	1157.0	1115.4	1085.7	1079.7	1085.7	1115.4	1157.0	1207.2	1236.2	1222.9	1129.5
105°	1350.3	1342.7	1329.6	1323.9	1329.6	1342.7	1350.3	1348.4	1309.8	1216.6	1053.9
107.5°	1381.3	1402.8	1412.2	1414.7	1412.2	1402.8	1381.3	1334.8	1250.9	1119.7	946.4
110°	1351.2	1390.7	1407.7	1416.2	1407.7	1390.7	1351.2	1284.4	1180.9	1044.4	881.7



TEST NUMBER: P332699-830

CATALOG NUMBER: S124DIP-S1195D1035U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1286.5	1334.3	1358.0	1371.7	1358.0	1334.3	1286.5	1210.6	1107.1	978.2	834.2
115°	1177.1	1233.6	1263.7	1271.2	1263.7	1233.6	1177.1	1102.8	1012.5	902.4	786.6
117.5°	1085.7	1133.1	1163.6	1169.4	1163.6	1133.1	1085.7	1022.3	945.7	859.1	763.3
120°	1035.9	1077.4	1101.8	1112.2	1101.8	1077.4	1035.9	982.3	915.6	840.3	752.7
122.5°	1000.6	1035.9	1056.7	1067.1	1056.7	1035.9	1000.6	955.3	896.7	828.2	743.8
125°	963.6	990.8	1008.7	1014.4	1008.7	990.8	963.6	925.9	874.1	809.2	728.3
127.5°	938.5	962.8	977.8	983.4	977.8	962.8	938.5	900.7	851.6	786.8	709.5
130°	921.1	944.7	959.8	965.4	959.8	944.7	921.1	882.6	832.7	768.7	694.5
132.5°	898.6	925.1	939.4	945.1	939.4	925.1	898.6	860.8	810.9	748.5	678.6
135°	860.1	886.4	901.4	907.1	901.4	886.4	860.1	822.4	775.3	717.9	656.8
137.5°	814.8	840.8	853.3	860.1	853.3	840.8	814.8	779.7	737.2	688.8	637.1
140°	784.8	805.5	818.6	826.1	818.6	805.5	784.8	751.8	712.3	670.0	625.8
142.5°	753.8	773.1	784.8	790.0	784.8	773.1	753.8	724.7	690.5	654.1	615.2
145°	710.4	726.4	735.8	740.6	735.8	726.4	710.4	686.9	660.5	632.4	600.3
147.5°	674.1	687.9	695.0	696.6	695.0	687.9	674.1	656.8	636.1	613.5	588.1
150°	653.0	665.2	670.9	671.8	670.9	665.2	653.0	638.0	621.0	602.2	580.6
152.5°	635.0	644.9	648.3	649.2	648.3	644.9	635.0	622.2	608.2	590.9	572.3
155°	609.7	617.3	620.1	620.1	620.1	617.3	609.7	600.3	589.0	575.0	559.9
157.5°	587.1	592.8	594.5	594.5	594.5	592.8	587.1	580.0	571.0	559.1	546.5
160°	572.1	577.8	578.7	578.7	578.7	577.8	572.1	566.5	558.9	548.6	538.2
162.5°	557.8	563.5	564.4	563.6	564.4	563.5	557.8	553.6	546.9	538.8	529.9
165°	539.1	542.9	542.0	541.0	542.0	542.9	539.1	535.4	530.7	524.1	518.5
167.5°	521.7	524.1	524.0	523.2	524.0	524.1	521.7	519.8	517.0	511.7	507.4
170°	511.9	512.8	511.9	511.9	511.9	512.8	511.9	510.0	507.2	503.4	500.6
172.5°	502.1	503.0	502.1	500.6	502.1	503.0	502.1	501.0	498.9	496.6	494.6
175°	489.3	491.2	489.3	487.4	489.3	491.2	489.3	489.3	489.3	487.4	486.4
177.5°	481.9	482.7	481.2	479.7	481.2	482.7	481.9	482.7	481.9	481.9	481.2
180°	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9



TEST NUMBER: P332699-830

CATALOG NUMBER: S124DIP-S1195D1035U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7
2.5°	1736.5	1739.0	1748.6	1757.7	1768.5	1776.3	1781.7	1787.7	1800.4	1810.6	1820.2
5°	1627.0	1630.8	1650.3	1663.9	1687.2	1707.5	1723.3	1740.6	1761.0	1788.8	1814.4
7.5°	1530.5	1544.5	1565.8	1587.8	1611.7	1638.2	1661.4	1687.5	1722.6	1760.8	1800.3
10°	1475.7	1491.6	1514.1	1539.7	1562.3	1593.1	1621.7	1652.6	1692.4	1739.1	1785.7
12.5°	1421.0	1447.0	1464.1	1494.5	1518.9	1544.4	1574.8	1615.2	1661.8	1710.8	1767.1
15°	1352.3	1366.6	1399.7	1416.3	1450.9	1490.1	1520.1	1560.8	1605.9	1670.7	1733.8
17.5°	1273.2	1291.9	1318.3	1349.9	1389.6	1420.2	1457.6	1499.5	1556.4	1620.7	1699.9
20°	1221.3	1237.2	1269.5	1304.1	1346.3	1378.7	1418.5	1459.2	1517.9	1586.4	1669.1
22.5°	1175.0	1190.2	1224.4	1256.6	1297.5	1337.1	1378.8	1426.1	1482.3	1554.4	1639.0
25°	1103.2	1123.5	1153.7	1186.8	1225.9	1271.0	1316.2	1358.3	1418.5	1494.5	1584.9
27.5°	1039.5	1055.8	1077.6	1115.2	1159.7	1203.3	1248.1	1301.2	1359.0	1439.3	1533.0
30°	998.6	1013.7	1035.5	1070.1	1111.5	1158.2	1204.9	1255.9	1316.2	1396.0	1491.6
32.5°	966.1	977.5	996.9	1027.9	1065.7	1114.8	1160.8	1213.8	1277.1	1355.7	1448.8
35°	918.1	927.8	935.4	964.8	998.6	1043.8	1090.4	1146.9	1207.9	1282.3	1375.6
37.5°	871.0	874.3	885.3	904.6	937.4	978.9	1022.3	1077.8	1140.3	1216.0	1300.0
40°	842.1	843.6	850.4	868.5	897.0	936.1	978.3	1033.2	1092.7	1164.1	1247.7
42.5°	813.8	812.8	819.1	831.7	858.5	894.0	935.6	985.7	1045.1	1111.2	1189.9
45°	769.1	769.1	767.6	778.2	799.9	834.5	869.2	917.4	967.0	1031.7	1098.0
47.5°	722.5	718.2	719.5	725.0	743.4	771.8	806.7	846.1	889.9	944.7	1002.9
50°	692.3	686.4	684.1	690.0	706.6	731.5	764.6	799.2	840.6	888.7	938.4
52.5°	659.2	653.2	649.1	653.4	668.7	691.7	721.8	752.2	789.4	828.6	871.6
55°	608.0	601.2	599.0	600.5	611.8	629.9	655.4	683.3	711.1	743.5	773.6
57.5°	557.6	546.5	544.4	543.7	551.5	568.0	589.4	613.5	633.8	653.4	685.4
60°	524.5	511.0	506.4	505.7	511.7	525.3	544.8	568.9	583.2	596.7	624.6
62.5°	489.0	476.1	466.1	467.2	472.6	485.5	502.7	520.2	529.6	544.4	563.2
65°	434.2	417.6	410.1	407.8	410.9	421.4	435.0	446.3	456.8	462.8	480.9
67.5°	379.5	365.6	354.5	351.8	350.3	357.6	368.7	375.5	383.0	388.3	399.0
70°	340.9	328.9	315.3	310.8	310.0	316.0	326.6	327.3	337.9	340.2	351.5
72.5°	302.9	287.9	278.6	274.1	270.9	276.4	283.2	285.2	291.0	295.0	300.9
75°	243.8	232.5	223.5	216.7	214.4	217.4	217.4	221.2	225.0	227.2	234.0
77.5°	191.9	179.0	168.2	164.4	161.6	159.7	161.4	163.6	161.8	165.7	167.2
80°	155.8	142.2	133.9	132.4	127.9	124.1	123.4	125.6	122.6	124.1	128.7
82.5°	120.3	111.5	102.6	101.1	95.4	93.5	92.7	91.3	91.3	91.0	92.0
85°	71.4	66.3	60.2	56.5	54.2	50.4	50.4	48.9	47.4	45.9	46.7
87.5°	32.1	31.1	27.7	25.5	24.3	20.7	20.7	18.8	18.0	16.8	15.8
90°	16.0	17.0	15.1	13.2	13.2	7.5	7.5	6.6	5.7	2.8	0.9
92.5°	248.6	298.5	261.2	190.1	117.1	69.3	49.7	35.9	24.5	15.6	10.7
95°	788.5	766.9	578.7	353.8	199.4	117.6	78.1	55.5	43.3	33.8	31.0
97.5°	990.6	807.7	541.6	318.0	190.7	127.6	94.4	75.1	63.8	55.7	55.7
100°	997.4	756.5	491.2	299.3	192.9	137.4	107.3	89.4	78.1	71.5	71.5
102.5°	940.9	692.6	457.3	294.0	200.4	150.1	121.6	104.4	93.9	88.0	86.5
105°	838.4	617.3	428.1	296.4	218.3	173.1	145.8	128.9	117.6	112.9	110.1
107.5°	755.5	575.1	422.8	310.3	239.2	197.7	170.9	154.7	142.6	138.0	136.1
110°	714.2	560.8	424.3	320.8	255.0	213.6	188.2	171.3	159.9	155.2	153.4



TEST NUMBER: P332699-830

CATALOG NUMBER: S124DIP-S1195D1035U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	690.9	554.0	428.9	332.2	270.0	230.2	204.7	187.8	177.3	171.8	169.9
115°	669.0	550.4	437.5	350.1	293.6	255.9	230.5	212.6	203.2	196.6	193.9
117.5°	659.2	549.5	446.8	368.3	316.3	280.6	254.2	237.5	227.2	221.3	218.7
120°	653.9	549.5	453.6	381.1	332.2	296.4	270.0	254.0	243.7	237.1	235.3
122.5°	647.9	548.7	460.3	393.1	347.2	311.4	285.9	268.3	258.7	252.1	250.3
125°	638.0	547.6	470.5	411.2	367.9	334.0	307.6	289.8	279.5	273.8	270.0
127.5°	624.6	545.5	478.5	426.8	387.1	354.4	327.8	309.2	297.4	290.6	287.6
130°	616.3	544.8	484.6	436.6	399.9	367.9	340.6	322.7	308.6	301.1	297.4
132.5°	608.8	544.0	489.8	446.4	410.5	378.4	352.7	333.3	319.9	310.1	307.1
135°	597.5	542.9	497.8	459.2	425.3	394.3	369.8	350.1	334.0	324.6	320.8
137.5°	587.7	542.7	502.5	468.3	436.6	407.6	384.3	363.7	348.6	338.2	334.6
140°	582.5	542.0	506.2	474.2	444.1	415.9	393.3	373.5	357.6	347.2	344.4
142.5°	578.0	542.0	509.3	478.7	450.9	423.4	401.6	382.6	367.3	357.8	355.0
145°	570.2	540.1	511.0	483.6	458.3	433.8	413.1	395.2	382.0	372.6	369.8
147.5°	563.3	536.7	511.9	488.0	465.8	442.8	424.1	409.3	395.8	387.5	386.5
150°	558.0	534.4	511.9	490.2	469.6	448.8	430.9	416.9	405.6	398.0	397.1
152.5°	552.0	530.7	510.4	491.7	472.6	454.1	437.7	425.1	414.6	407.1	406.9
155°	542.9	525.1	508.1	493.0	477.0	461.1	447.0	436.6	427.2	421.5	420.6
157.5°	533.7	519.2	505.7	493.0	480.2	466.7	455.6	446.6	439.2	433.9	433.9
160°	527.0	514.7	503.4	493.0	481.7	470.5	460.1	452.6	446.0	442.2	442.2
162.5°	520.9	510.2	501.1	493.0	483.2	472.8	464.7	457.9	452.0	449.0	449.8
165°	511.0	503.4	496.8	491.2	483.6	475.1	469.6	464.9	460.1	458.3	458.3
167.5°	501.9	496.6	492.3	488.9	483.4	477.2	473.0	470.3	466.7	465.8	466.7
170°	495.9	492.1	489.3	487.4	482.7	478.0	475.1	473.3	470.5	469.6	470.5
172.5°	490.6	487.6	486.3	485.9	481.9	478.7	476.6	475.5	473.4	473.3	474.2
175°	484.6	482.7	482.7	483.6	480.8	478.9	478.9	478.0	477.0	477.0	478.0
177.5°	480.4	479.7	479.7	481.2	479.7	478.9	478.9	478.9	478.2	478.9	479.7
180°	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9



TEST NUMBER: P332699-830

CATALOG NUMBER: S124DIP-S1195D1035U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7
2.5°	1828.6	1834.7	1842.5	1855.8	1860.6	1866.6	1875.0	1874.4	1876.8	1885.8	1905.2
5°	1835.4	1858.8	1881.3	1908.5	1937.0	1955.9	1981.4	1997.2	2013.1	2033.3	2067.9
7.5°	1838.1	1875.2	1916.6	1964.2	2006.4	2055.2	2093.3	2129.1	2161.4	2204.3	2245.6
10°	1833.9	1883.6	1937.0	1997.2	2061.2	2115.3	2164.3	2220.0	2267.4	2319.3	2366.0
12.5°	1826.1	1886.0	1957.5	2025.0	2099.7	2179.8	2240.8	2297.1	2360.1	2419.9	2491.8
15°	1808.4	1890.4	1973.9	2062.7	2162.8	2255.3	2343.4	2416.4	2484.2	2573.7	2667.8
17.5°	1785.7	1874.2	1979.6	2087.1	2191.7	2297.5	2406.5	2516.2	2601.7	2712.9	2786.5
20°	1764.7	1867.1	1975.4	2103.4	2207.9	2339.7	2448.0	2554.1	2671.5	2782.1	2870.1
22.5°	1735.2	1847.2	1962.2	2089.5	2227.2	2358.9	2484.2	2599.2	2716.7	2837.0	2943.7
25°	1697.7	1799.3	1935.5	2080.0	2217.0	2359.9	2503.7	2648.2	2774.6	2901.8	3001.1
27.5°	1633.9	1762.2	1889.0	2038.2	2190.4	2352.1	2505.8	2657.0	2789.5	2894.1	2955.6
30°	1601.4	1712.8	1850.5	2000.3	2165.0	2338.9	2499.2	2647.4	2770.9	2854.4	2879.2
32.5°	1553.2	1668.2	1802.9	1958.1	2132.5	2311.2	2478.1	2617.9	2720.8	2764.7	2734.7
35°	1481.8	1585.6	1721.8	1880.6	2061.9	2252.3	2417.2	2535.3	2587.9	2546.6	2443.4
37.5°	1396.0	1498.9	1635.7	1791.7	1979.3	2172.8	2321.9	2406.9	2389.4	2286.5	2132.9
40°	1335.8	1432.1	1562.3	1730.8	1913.7	2107.9	2238.8	2284.7	2236.6	2089.1	1925.7
42.5°	1268.9	1362.8	1493.6	1656.1	1849.9	2029.0	2143.1	2146.8	2066.1	1889.8	1725.9
45°	1167.2	1256.7	1380.2	1549.4	1728.6	1897.1	1972.4	1935.5	1786.5	1616.5	1451.6
47.5°	1066.8	1144.4	1266.0	1426.8	1596.9	1738.8	1776.1	1709.8	1551.0	1385.9	1233.1
50°	993.3	1071.6	1186.0	1339.5	1503.5	1626.3	1644.3	1556.2	1400.4	1234.2	1114.5
52.5°	922.9	1000.6	1110.8	1252.8	1403.1	1513.6	1514.3	1412.4	1257.2	1108.9	997.7
55°	819.5	889.5	988.8	1116.0	1250.0	1336.5	1315.4	1210.0	1075.3	946.7	849.6
57.5°	719.9	780.8	872.3	978.5	1096.5	1167.8	1132.8	1031.4	911.2	802.0	728.5
60°	655.4	713.4	791.6	891.7	991.1	1046.8	1013.7	921.9	811.2	723.2	659.2
62.5°	592.9	641.8	717.0	803.9	896.0	937.2	907.7	817.1	721.5	641.9	590.0
65°	504.2	544.1	604.3	678.8	745.7	781.2	756.3	672.0	599.0	541.9	500.4
67.5°	421.4	452.6	498.1	557.9	614.8	634.0	611.3	552.7	490.8	445.1	415.8
70°	364.2	393.6	432.0	477.9	527.5	547.8	525.3	478.6	428.2	386.1	357.4
72.5°	314.2	337.0	369.4	408.6	447.4	467.8	452.4	407.6	365.0	333.7	309.2
75°	239.3	258.9	281.4	309.2	339.4	353.0	339.4	308.5	279.2	255.9	238.6
77.5°	174.0	184.5	202.0	222.7	241.6	251.9	240.3	219.3	201.4	185.4	176.8
80°	132.4	140.0	152.0	168.5	181.3	191.1	183.6	166.3	152.0	141.5	137.7
82.5°	96.3	101.4	109.2	121.6	130.2	135.2	131.9	119.3	113.5	104.2	100.4
85°	47.4	50.4	55.7	59.5	67.0	67.8	68.5	63.2	58.0	55.7	52.7
87.5°	16.8	18.0	20.0	22.0	24.4	26.1	25.5	25.9	23.8	23.1	20.8
90°	2.8	5.7	6.6	7.5	7.5	13.2	13.2	15.1	17.0	16.0	17.0
92.5°	15.6	24.5	35.9	49.7	69.3	117.1	190.1	261.2	298.5	248.6	184.8
95°	33.8	43.3	55.5	78.1	117.6	199.4	353.8	578.7	766.9	788.5	697.2
97.5°	55.7	63.8	75.1	94.4	127.6	190.7	318.0	541.6	807.7	990.6	1030.2
100°	71.5	78.1	89.4	107.3	137.4	192.9	299.3	491.2	756.5	997.4	1134.8
102.5°	88.0	93.9	104.4	121.6	150.1	200.4	294.0	457.3	692.6	940.9	1129.5
105°	112.9	117.6	128.9	145.8	173.1	218.3	296.4	428.1	617.3	838.4	1053.9
107.5°	138.0	142.6	154.7	170.9	197.7	239.2	310.3	422.8	575.1	755.5	946.4
110°	155.2	159.9	171.3	188.2	213.6	255.0	320.8	424.3	560.8	714.2	881.7





TEST NUMBER: P332699-830

CATALOG NUMBER: S124DIP-S1195D1035U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	171.8	177.3	187.8	204.7	230.2	270.0	332.2	428.9	554.0	690.9	834.2
115°	196.6	203.2	212.6	230.5	255.9	293.6	350.1	437.5	550.4	669.0	786.6
117.5°	221.3	227.2	237.5	254.2	280.6	316.3	368.3	446.8	549.5	659.2	763.3
120°	237.1	243.7	254.0	270.0	296.4	332.2	381.1	453.6	549.5	653.9	752.7
122.5°	252.1	258.7	268.3	285.9	311.4	347.2	393.1	460.3	548.7	647.9	743.8
125°	273.8	279.5	289.8	307.6	334.0	367.9	411.2	470.5	547.6	638.0	728.3
127.5°	290.6	297.4	309.2	327.8	354.4	387.1	426.8	478.5	545.5	624.6	709.5
130°	301.1	308.6	322.7	340.6	367.9	399.9	436.6	484.6	544.8	616.3	694.5
132.5°	310.1	319.9	333.3	352.7	378.4	410.5	446.4	489.8	544.0	608.8	678.6
135°	324.6	334.0	350.1	369.8	394.3	425.3	459.2	497.8	542.9	597.5	656.8
137.5°	338.2	348.6	363.7	384.3	407.6	436.6	468.3	502.5	542.7	587.7	637.1
140°	347.2	357.6	373.5	393.3	415.9	444.1	474.2	506.2	542.0	582.5	625.8
142.5°	357.8	367.3	382.6	401.6	423.4	450.9	478.7	509.3	542.0	578.0	615.2
145°	372.6	382.0	395.2	413.1	433.8	458.3	483.6	511.0	540.1	570.2	600.3
147.5°	387.5	395.8	409.3	424.1	442.8	465.8	488.0	511.9	536.7	563.3	588.1
150°	398.0	405.6	416.9	430.9	448.8	469.6	490.2	511.9	534.4	558.0	580.6
152.5°	407.1	414.6	425.1	437.7	454.1	472.6	491.7	510.4	530.7	552.0	572.3
155°	421.5	427.2	436.6	447.0	461.1	477.0	493.0	508.1	525.1	542.9	559.9
157.5°	433.9	439.2	446.6	455.6	466.7	480.2	493.0	505.7	519.2	533.7	546.5
160°	442.2	446.0	452.6	460.1	470.5	481.7	493.0	503.4	514.7	527.0	538.2
162.5°	449.0	452.0	457.9	464.7	472.8	483.2	493.0	501.1	510.2	520.9	529.9
165°	458.3	460.1	464.9	469.6	475.1	483.6	491.2	496.8	503.4	511.0	518.5
167.5°	465.8	466.7	470.3	473.0	477.2	483.4	488.9	492.3	496.6	501.9	507.4
170°	469.6	470.5	473.3	475.1	478.0	482.7	487.4	489.3	492.1	495.9	500.6
172.5°	473.3	473.4	475.5	476.6	478.7	481.9	485.9	486.3	487.6	490.6	494.6
175°	477.0	477.0	478.0	478.9	478.9	480.8	483.6	482.7	482.7	484.6	486.4
177.5°	478.9	478.2	478.9	478.9	478.9	479.7	481.2	479.7	479.7	480.4	481.2
180°	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9



TEST NUMBER: P332699-830

CATALOG NUMBER: S124DIP-S1195D1035U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7	1816.7
2.5°	1914.8	1916.0	1921.4	1925.6	1926.8	1932.8	1933.4
5°	2083.0	2095.8	2120.6	2122.9	2126.7	2146.3	2131.2
7.5°	2280.2	2312.7	2334.4	2353.5	2360.4	2369.0	2367.2
10°	2406.6	2454.8	2478.9	2517.2	2518.8	2528.6	2522.5
12.5°	2533.6	2589.6	2633.6	2640.6	2672.9	2677.9	2686.2
15°	2713.7	2773.1	2834.0	2855.9	2900.3	2910.9	2927.3
17.5°	2882.9	2943.7	2986.4	3042.8	3061.0	3085.4	3068.8
20°	2975.5	3041.8	3096.0	3140.4	3159.1	3172.7	3171.2
22.5°	3031.5	3098.3	3142.2	3175.9	3193.4	3199.2	3198.9
25°	3066.6	3104.9	3118.5	3131.3	3111.7	3104.9	3107.9
27.5°	2969.1	2959.1	2923.8	2877.4	2829.2	2791.0	2770.2
30°	2834.8	2776.1	2722.7	2629.3	2581.2	2552.6	2527.1
32.5°	2644.6	2551.6	2448.7	2363.2	2308.5	2266.1	2259.7
35°	2318.6	2178.6	2053.0	1948.3	1894.1	1848.2	1837.7
37.5°	1971.2	1825.8	1712.6	1620.5	1562.3	1529.9	1499.7
40°	1740.6	1615.7	1504.3	1426.1	1381.7	1358.3	1339.5
42.5°	1563.0	1449.0	1338.1	1278.6	1238.4	1224.1	1213.1
45°	1317.7	1211.5	1134.8	1089.7	1066.3	1042.3	1031.0
47.5°	1121.2	1034.9	984.3	945.9	921.0	906.6	899.5
50°	1009.9	939.1	894.0	864.7	842.1	830.8	824.8
52.5°	911.2	853.1	815.1	791.8	776.5	768.2	765.8
55°	784.9	740.5	716.4	696.1	684.9	677.3	674.3
57.5°	682.2	648.1	628.5	611.8	607.5	601.2	599.0
60°	614.8	588.5	571.9	560.6	556.9	549.3	550.8
62.5°	555.3	533.7	519.5	513.1	508.1	501.8	503.9
65°	469.6	453.7	446.3	440.3	434.2	430.5	433.5
67.5°	394.0	383.2	373.0	369.5	366.5	365.9	362.7
70°	344.7	335.6	326.6	324.3	324.3	321.3	320.6
72.5°	297.1	290.5	284.5	282.8	280.4	281.6	278.4
75°	229.5	224.2	222.0	219.7	219.0	219.0	216.7
77.5°	169.7	165.7	162.1	162.1	159.4	158.3	158.1
80°	128.7	127.1	124.1	124.1	122.6	123.4	121.9
82.5°	96.8	94.6	94.1	92.8	90.8	90.9	89.4
85°	51.9	49.7	48.9	46.7	45.1	46.7	45.1
87.5°	21.7	21.2	20.6	19.6	19.2	19.0	17.2
90°	17.9	18.9	18.9	19.8	20.7	19.8	19.8
92.5°	139.1	110.7	91.8	80.8	75.7	72.5	72.5
95°	551.4	425.3	334.0	287.9	258.7	241.9	229.6
97.5°	975.9	883.9	785.7	718.1	661.5	633.3	613.7
100°	1153.6	1107.5	1037.8	956.0	898.6	870.3	862.9
102.5°	1222.9	1236.2	1207.2	1157.0	1115.4	1085.7	1079.7
105°	1216.6	1309.8	1348.4	1350.3	1342.7	1329.6	1323.9
107.5°	1119.7	1250.9	1334.8	1381.3	1402.8	1412.2	1414.7
110°	1044.4	1180.9	1284.4	1351.2	1390.7	1407.7	1416.2



TEST NUMBER: P332699-830

CATALOG NUMBER: S124DIP-S1195D1035U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	978.2	1107.1	1210.6	1286.5	1334.3	1358.0	1371.7
115°	902.4	1012.5	1102.8	1177.1	1233.6	1263.7	1271.2
117.5°	859.1	945.7	1022.3	1085.7	1133.1	1163.6	1169.4
120°	840.3	915.6	982.3	1035.9	1077.4	1101.8	1112.2
122.5°	828.2	896.7	955.3	1000.6	1035.9	1056.7	1067.1
125°	809.2	874.1	925.9	963.6	990.8	1008.7	1014.4
127.5°	786.8	851.6	900.7	938.5	962.8	977.8	983.4
130°	768.7	832.7	882.6	921.1	944.7	959.8	965.4
132.5°	748.5	810.9	860.8	898.6	925.1	939.4	945.1
135°	717.9	775.3	822.4	860.1	886.4	901.4	907.1
137.5°	688.8	737.2	779.7	814.8	840.8	853.3	860.1
140°	670.0	712.3	751.8	784.8	805.5	818.6	826.1
142.5°	654.1	690.5	724.7	753.8	773.1	784.8	790.0
145°	632.4	660.5	686.9	710.4	726.4	735.8	740.6
147.5°	613.5	636.1	656.8	674.1	687.9	695.0	696.6
150°	602.2	621.0	638.0	653.0	665.2	670.9	671.8
152.5°	590.9	608.2	622.2	635.0	644.9	648.3	649.2
155°	575.0	589.0	600.3	609.7	617.3	620.1	620.1
157.5°	559.1	571.0	580.0	587.1	592.8	594.5	594.5
160°	548.6	558.9	566.5	572.1	577.8	578.7	578.7
162.5°	538.8	546.9	553.6	557.8	563.5	564.4	563.6
165°	524.1	530.7	535.4	539.1	542.9	542.0	541.0
167.5°	511.7	517.0	519.8	521.7	524.1	524.0	523.2
170°	503.4	507.2	510.0	511.9	512.8	511.9	511.9
172.5°	496.6	498.9	501.0	502.1	503.0	502.1	500.6
175°	487.4	489.3	489.3	489.3	491.2	489.3	487.4
177.5°	481.9	481.9	482.7	481.9	482.7	481.2	479.7
180°	478.9	478.9	478.9	478.9	478.9	478.9	478.9

(END OF REPORT)