

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332964-830

Luminaire Tested: **S124RDIP-S1020D590U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332964-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIP-S1020D590U830-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 590 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6157.8 lumens
Efficiency: N/A
Efficacy: 126.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 48.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332964-830

CATALOG NUMBER: S124RDIP-S1020D590U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332964-830

CATALOG NUMBER: S124RDIP-S1020D590U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	104	104	104	104	91	91	91	79	79	79	69	69	69	64
1	101	97	93	90	95	91	88	85	80	78	76	71	69	67	61	60	59	55
2	92	85	79	74	87	80	75	70	71	67	63	62	59	57	54	52	50	46
3	85	75	68	62	79	71	64	59	63	58	54	55	51	48	49	46	43	40
4	78	67	59	53	73	63	56	50	56	50	46	50	45	42	44	40	37	34
5	71	60	52	45	67	56	49	44	50	44	40	45	40	36	39	36	33	30
6	66	54	46	40	62	51	44	38	46	40	35	41	36	32	36	32	29	26
7	61	49	41	35	57	46	39	34	41	35	31	37	32	28	33	29	26	23
8	57	44	37	31	53	42	35	30	38	32	28	34	29	26	30	26	23	21
9	53	41	33	28	50	39	32	27	35	29	25	31	27	23	28	24	21	19
10	50	37	30	25	47	36	29	24	32	27	23	29	24	21	26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13739	13739	13739
5°	13771	13602	13686
10°	13684	13439	13439
15°	13527	13157	13059
20°	13311	12785	12550
25°	13036	12351	12038
30°	12767	11893	11395
35°	12471	11417	10749
40°	12113	10877	10053
45°	11783	10340	9344
50°	11408	9722	8593
55°	11005	9080	7776
60°	10563	8375	6944
65°	10157	7494	6124
70°	9567	6522	5200
75°	8821	5405	4226
80°	7694	4119	3877
85°	6521	3742	3501



TEST NUMBER: P332964-830

CATALOG NUMBER: S124RDIP-S1020D590U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.9	2.6
10°-20°	445.8	7.2
20°-30°	643.8	10.5
30°-40°	729.7	11.9
40°-50°	704.7	11.4
50°-60°	586.0	9.5
60°-70°	404.6	6.6
70°-80°	205.1	3.3
80°-90°	54.7	0.9
90°-100°	24.6	0.4
100°-110°	156.8	2.5
110°-120°	299.9	4.9
120°-130°	380.7	6.2
130°-140°	407.3	6.6
140°-150°	380.9	6.2
150°-160°	307.1	5.0
160°-170°	198.1	3.2
170°-180°	68.3	1.1
0°-30°	1249.5	20.3
0°-40°	1979.2	32.1
0°-60°	3269.8	53.1
0°-90°	3934.3	63.9
90°-120°	481.2	7.8
90°-150°	1650.1	26.8
90°-180°	2224.0	36.1
0°-180°	6157.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1702	1702	1702	1702	1702	
5°	1699	1694	1678	1691	1689	161
15°	1618	1606	1574	1571	1562	456
25°	1464	1438	1387	1365	1351	674
35°	1265	1222	1158	1115	1091	790
45°	1032	982	906	844	818	795
55°	782	728	645	580	552	699
65°	532	474	392	338	321	525
75°	283	234	173	145	136	299
85°	70	46	40	38	38	79
90°	2	7	12	15	16	5
95°	30	12	12	15	16	38
105°	162	165	168	171	153	169
115°	302	304	303	304	304	297
125°	425	427	426	427	428	379
135°	527	526	528	530	531	406
145°	608	609	609	610	611	380
155°	666	667	665	667	666	307
165°	703	700	700	704	700	198
175°	719	716	716	720	714	68
180°	719	719	719	719	719	



TEST NUMBER: P332964-830

CATALOG NUMBER: S124RDIP-S1020D590U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9
2.5°	1706.1	1705.2	1704.2	1703.4	1702.4	1700.6	1698.1	1695.5	1693.0	1690.5	1693.0
5°	1699.3	1698.2	1697.0	1695.8	1694.7	1692.3	1688.9	1685.5	1682.0	1678.5	1681.4
7.5°	1683.9	1682.7	1681.5	1680.3	1679.0	1676.2	1671.7	1667.2	1662.6	1658.1	1660.0
10°	1669.3	1667.9	1666.4	1665.0	1663.6	1660.2	1655.0	1649.8	1644.5	1639.4	1640.5
12.5°	1650.6	1648.9	1647.2	1645.6	1643.9	1639.9	1633.8	1627.7	1621.6	1615.4	1616.1
15°	1618.5	1615.9	1613.4	1610.7	1608.1	1603.2	1595.9	1588.7	1581.5	1574.2	1573.7
17.5°	1579.7	1575.9	1572.2	1568.4	1564.6	1558.4	1549.7	1541.1	1532.4	1523.6	1522.0
20°	1549.4	1545.7	1541.9	1538.1	1534.4	1527.6	1517.8	1507.9	1498.1	1488.2	1485.9
22.5°	1516.1	1511.8	1507.6	1503.4	1499.2	1491.8	1481.3	1470.7	1460.2	1449.6	1446.1
25°	1463.5	1458.2	1453.0	1447.8	1442.6	1434.1	1422.2	1410.3	1398.5	1386.6	1381.7
27.5°	1408.2	1401.7	1395.2	1388.6	1382.1	1372.4	1359.7	1347.1	1334.4	1321.6	1315.6
30°	1369.6	1362.4	1355.2	1347.9	1340.7	1330.2	1316.6	1303.0	1289.4	1275.8	1268.6
32.5°	1329.0	1320.8	1312.6	1304.5	1296.3	1285.2	1271.1	1257.1	1242.9	1228.9	1220.5
35°	1265.4	1256.1	1246.8	1237.6	1228.3	1216.4	1201.9	1187.5	1173.0	1158.5	1148.7
37.5°	1197.3	1187.8	1178.3	1168.7	1159.1	1146.3	1130.3	1114.3	1098.2	1082.1	1071.1
40°	1149.4	1139.8	1130.3	1120.7	1111.2	1098.2	1081.7	1065.1	1048.6	1032.1	1019.9
42.5°	1103.5	1093.5	1083.5	1073.5	1063.5	1049.8	1032.6	1015.4	998.2	981.0	968.7
45°	1032.1	1021.4	1010.7	999.9	989.2	975.2	957.8	940.5	923.0	905.7	891.6
47.5°	958.4	947.3	936.2	925.2	914.1	899.6	881.5	863.4	845.3	827.3	812.6
50°	908.3	897.0	885.7	874.4	863.1	848.2	829.7	811.2	792.6	774.1	759.6
52.5°	857.2	846.1	835.1	824.1	812.9	798.0	778.9	760.0	740.9	722.0	707.3
55°	781.9	770.3	758.7	747.2	735.6	720.4	701.5	682.7	663.9	645.1	630.0
57.5°	707.4	695.3	683.2	671.2	659.2	643.9	625.4	606.8	588.2	569.8	554.5
60°	654.2	642.6	631.0	619.4	607.8	592.8	574.3	555.7	537.2	518.7	503.6
62.5°	606.2	594.2	582.1	570.0	558.1	542.5	523.5	504.5	485.5	466.6	452.6
65°	531.7	519.2	506.8	494.4	481.9	466.4	447.9	429.3	410.8	392.3	379.8
67.5°	454.3	442.3	430.5	418.5	406.5	392.0	374.8	357.6	340.4	323.2	312.5
70°	405.3	393.1	381.0	368.8	356.7	342.3	325.8	309.2	292.8	276.3	266.7
72.5°	353.2	342.1	331.1	320.2	309.2	295.9	280.3	264.7	249.1	233.6	225.4
75°	282.8	272.1	261.4	250.6	240.0	227.7	214.1	200.6	186.9	173.3	166.6
77.5°	211.4	202.3	193.2	184.1	175.0	164.9	153.9	143.0	132.0	120.9	117.1
80°	165.5	157.1	148.7	140.3	132.0	123.4	114.7	106.0	97.3	88.6	87.8
82.5°	125.9	118.2	110.5	102.7	95.1	88.7	83.8	78.8	73.8	68.8	68.1
85°	70.4	64.6	58.8	53.0	47.2	43.8	43.0	42.1	41.3	40.4	39.8
87.5°	24.3	22.7	21.1	19.5	17.9	17.2	17.1	17.1	17.0	17.0	16.9
90°	1.6	2.9	4.2	5.6	6.9	8.0	9.0	9.9	10.8	11.8	12.5
92.5°	6.8	6.9	6.9	7.0	7.1	7.5	8.6	9.5	10.5	11.4	12.2
95°	29.6	25.5	21.5	17.3	13.3	11.3	11.5	11.6	11.7	11.8	12.5
97.5°	62.8	65.3	67.9	70.4	73.0	67.5	54.2	40.9	27.5	14.2	14.2
100°	88.1	90.3	92.5	94.6	96.8	89.6	73.1	56.6	40.2	23.7	21.6
102.5°	116.6	118.1	119.7	121.3	122.9	122.6	120.5	118.3	116.1	114.0	92.1
105°	161.8	162.6	163.2	164.0	164.7	165.3	166.0	166.5	167.1	167.8	168.8
107.5°	203.9	204.2	204.6	204.9	205.3	205.9	206.7	207.5	208.3	209.2	209.7
110°	232.2	232.6	233.0	233.4	233.7	234.2	235.0	235.6	236.4	237.1	237.3



TEST NUMBER: P332964-830

CATALOG NUMBER: S124RDIP-S1020D590U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	259.8	260.4	261.1	261.7	262.4	262.9	263.2	263.5	263.9	264.2	264.2
115°	302.2	302.6	302.8	303.2	303.6	303.7	303.6	303.5	303.3	303.2	303.5
117.5°	340.4	340.8	341.3	341.8	342.2	342.6	342.9	343.2	343.4	343.7	343.7
120°	366.2	366.6	367.1	367.6	368.1	368.3	368.2	368.0	367.9	367.8	368.0
122.5°	390.2	390.5	390.8	391.1	391.3	391.6	391.8	391.9	392.1	392.3	392.4
125°	424.7	425.2	425.7	426.2	426.7	426.8	426.5	426.3	426.0	425.8	426.2
127.5°	457.4	457.5	457.7	457.8	457.9	458.3	458.8	459.3	459.9	460.4	460.3
130°	478.5	478.6	478.7	478.9	479.0	479.2	479.6	479.9	480.3	480.7	480.8
132.5°	497.9	498.0	498.3	498.5	498.7	499.1	499.5	499.9	500.4	500.9	501.0
135°	526.9	526.8	526.7	526.5	526.4	526.6	527.1	527.5	528.0	528.5	528.8
137.5°	552.6	552.6	552.7	552.7	552.8	553.1	553.6	554.1	554.7	555.2	555.4
140°	569.4	569.6	569.9	570.0	570.3	570.5	570.8	571.1	571.3	571.6	571.8
142.5°	584.5	584.8	585.3	585.7	586.2	586.4	586.5	586.7	586.8	587.0	587.3
145°	607.6	607.9	608.2	608.6	609.0	609.2	609.2	609.2	609.2	609.2	609.3
147.5°	625.9	626.6	627.3	627.9	628.6	628.9	628.8	628.7	628.5	628.4	628.5
150°	639.2	639.7	640.3	640.7	641.2	641.4	641.2	641.1	641.0	640.8	640.8
152.5°	650.4	650.8	651.2	651.6	652.0	652.1	651.9	651.7	651.4	651.2	651.4
155°	666.2	666.3	666.4	666.5	666.7	666.5	666.2	665.8	665.4	665.1	665.5
157.5°	679.4	679.3	679.2	679.2	679.1	678.8	678.4	678.1	677.6	677.2	677.9
160°	687.1	686.7	686.4	686.1	685.7	685.4	685.3	685.2	685.0	684.9	685.7
162.5°	694.0	693.5	693.1	692.7	692.2	691.9	691.7	691.6	691.5	691.4	692.1
165°	702.7	702.1	701.5	700.9	700.3	700.0	700.0	700.0	700.0	700.0	701.0
167.5°	709.5	709.0	708.3	707.8	707.1	706.7	706.7	706.6	706.5	706.4	707.6
170°	713.5	712.8	712.0	711.3	710.6	710.3	710.4	710.5	710.7	710.8	711.7
172.5°	716.0	715.3	714.6	713.9	713.2	712.8	713.0	713.1	713.2	713.3	714.4
175°	718.9	718.1	717.4	716.7	716.0	715.7	715.8	716.0	716.0	716.1	717.2
177.5°	720.1	719.4	718.8	718.1	717.5	717.2	717.4	717.6	717.7	717.9	718.8
180°	718.9	718.9	718.9	718.9	718.9	718.9	718.9	718.9	718.9	718.9	718.9



TEST NUMBER: P332964-830

CATALOG NUMBER: S124RDIP-S1020D590U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9
2.5°	1695.5	1698.1	1700.6	1701.9	1701.6	1701.4	1701.1	1700.9
5°	1684.2	1687.2	1690.1	1691.2	1690.6	1690.1	1689.5	1688.9
7.5°	1661.9	1663.7	1665.6	1666.0	1665.1	1664.2	1663.2	1662.3
10°	1641.7	1642.9	1644.0	1644.0	1642.9	1641.7	1640.5	1639.4
12.5°	1616.7	1617.5	1618.2	1617.7	1616.1	1614.5	1612.9	1611.3
15°	1573.1	1572.4	1571.9	1570.6	1568.6	1566.5	1564.5	1562.5
17.5°	1520.4	1518.8	1517.2	1514.9	1511.7	1508.7	1505.6	1502.5
20°	1483.6	1481.3	1478.9	1475.9	1472.2	1468.4	1464.6	1460.8
22.5°	1442.7	1439.2	1435.8	1432.5	1429.4	1426.3	1423.2	1420.2
25°	1376.7	1371.8	1366.9	1362.9	1360.1	1357.2	1354.2	1351.4
27.5°	1309.5	1303.4	1297.3	1292.2	1288.1	1283.8	1279.7	1275.5
30°	1261.3	1254.1	1246.8	1240.9	1236.2	1231.6	1227.0	1222.4
32.5°	1212.1	1203.7	1195.3	1188.9	1184.5	1180.1	1175.7	1171.3
35°	1138.8	1129.0	1119.1	1111.6	1106.4	1101.2	1096.0	1090.7
37.5°	1060.2	1049.1	1038.1	1030.0	1024.8	1019.5	1014.4	1009.2
40°	1007.8	995.6	983.4	974.8	969.6	964.3	959.1	953.9
42.5°	956.2	943.9	931.4	922.6	917.1	911.6	906.2	900.8
45°	877.3	863.1	848.9	839.2	834.1	828.8	823.6	818.4
47.5°	797.9	783.2	768.4	758.2	752.4	746.7	740.9	735.3
50°	745.1	730.7	716.1	706.2	700.7	695.1	689.7	684.2
52.5°	692.5	677.8	663.1	652.9	647.1	641.4	635.7	630.0
55°	614.9	599.9	584.8	574.6	569.0	563.5	558.1	552.5
57.5°	539.1	523.9	508.6	498.9	494.6	490.5	486.4	482.2
60°	488.5	473.4	458.5	448.6	443.9	439.3	434.7	430.1
62.5°	438.8	424.8	410.9	402.1	398.4	394.7	391.0	387.3
65°	367.3	354.9	342.4	334.5	331.0	327.5	324.0	320.6
67.5°	301.7	291.1	280.3	273.1	269.2	265.4	261.6	257.8
70°	257.1	247.6	238.1	231.8	228.9	226.0	223.1	220.3
72.5°	217.2	209.1	200.9	195.5	192.7	190.1	187.5	184.8
75°	160.0	153.4	146.7	142.5	140.7	139.0	137.2	135.5
77.5°	113.2	109.3	105.4	103.2	102.6	102.2	101.6	101.1
80°	86.9	86.1	85.1	84.5	84.3	84.0	83.7	83.4
82.5°	67.5	66.9	66.3	65.8	65.5	65.2	64.9	64.7
85°	39.2	38.6	38.1	37.8	37.8	37.8	37.8	37.8
87.5°	16.8	16.7	16.6	16.7	17.0	17.2	17.5	17.8
90°	13.3	13.9	14.7	15.2	15.5	15.6	15.9	16.1
92.5°	12.8	13.6	14.2	14.6	14.7	14.7	14.8	14.8
95°	13.3	13.9	14.7	15.1	15.3	15.4	15.5	15.6
97.5°	14.3	14.4	14.5	14.6	14.7	14.8	14.9	15.1
100°	19.6	17.5	15.6	14.6	14.7	14.8	14.9	15.1
102.5°	70.1	48.3	26.3	15.4	15.5	15.5	15.5	15.5
105°	169.9	171.0	172.0	170.4	166.2	161.8	157.5	153.3
107.5°	210.2	210.8	211.2	211.7	212.2	212.6	213.1	213.6
110°	237.6	237.8	238.1	238.4	238.7	239.0	239.4	239.8



TEST NUMBER: P332964-830

CATALOG NUMBER: S124RDIP-S1020D590U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	264.1	264.1	264.0	264.2	264.7	265.1	265.6	266.0
115°	303.7	304.0	304.2	304.3	304.3	304.3	304.3	304.3
117.5°	343.6	343.6	343.5	343.5	343.4	343.4	343.3	343.3
120°	368.3	368.4	368.7	368.7	368.4	368.3	368.0	367.8
122.5°	392.6	392.7	392.9	392.8	392.6	392.3	392.1	391.8
125°	426.5	426.9	427.3	427.5	427.6	427.7	427.8	428.0
127.5°	460.3	460.2	460.1	460.1	460.0	459.9	459.8	459.7
130°	480.9	481.0	481.2	481.2	481.2	481.2	481.2	481.2
132.5°	501.1	501.2	501.3	501.3	501.2	501.1	501.1	501.0
135°	529.0	529.2	529.4	529.7	529.9	530.2	530.5	530.7
137.5°	555.7	556.0	556.2	556.3	556.3	556.2	556.1	556.0
140°	572.2	572.6	573.0	573.2	573.3	573.4	573.5	573.6
142.5°	587.5	587.8	588.1	588.2	588.2	588.2	588.2	588.3
145°	609.4	609.5	609.6	609.8	610.0	610.3	610.6	610.8
147.5°	628.6	628.7	628.8	628.9	629.1	629.1	629.2	629.3
150°	640.8	640.8	640.8	640.9	641.0	641.2	641.3	641.4
152.5°	651.6	651.8	652.0	652.1	652.0	651.9	651.8	651.8
155°	666.0	666.5	666.9	667.0	666.7	666.3	666.0	665.6
157.5°	678.4	679.1	679.7	679.7	679.1	678.4	677.9	677.2
160°	686.4	687.1	687.9	687.9	687.1	686.4	685.7	684.9
162.5°	692.9	693.5	694.3	694.3	693.4	692.6	691.8	691.0
165°	701.9	702.9	703.9	703.8	702.7	701.6	700.6	699.5
167.5°	708.6	709.6	710.7	710.6	709.5	708.2	707.0	705.9
170°	712.7	713.6	714.6	714.4	713.3	712.1	710.9	709.7
172.5°	715.3	716.2	717.2	717.0	715.8	714.4	713.1	711.8
175°	718.3	719.3	720.5	720.3	718.9	717.4	716.0	714.5
177.5°	719.5	720.3	721.0	720.9	719.7	718.6	717.4	716.2
180°	718.9	718.9	718.9	718.9	718.9	718.9	718.9	718.9

(END OF REPORT)