

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332969-830

Luminaire Tested: **S124RDIP-S1020D810U830-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332969-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIP-S1020D810U830-4F0-1E-UDD-A4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1020 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6818.3 lumens  
Efficiency: N/A  
Efficacy: 125.3 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 54.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332969-830

CATALOG NUMBER: S124RDIP-S1020D810U830-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P332969-830

CATALOG NUMBER: S124RDIP-S1020D810U830-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	65	65	65	60
1	101	96	93	89	94	90	87	84	79	76	74	68	67	65	59	57	56	52
2	92	85	79	74	86	80	74	70	70	66	62	61	58	55	52	50	48	44
3	84	75	68	62	79	71	64	59	62	57	53	54	50	47	47	44	42	38
4	77	67	59	53	72	63	56	51	55	50	46	49	44	41	42	39	36	33
5	71	60	52	46	66	56	49	44	50	44	40	44	39	36	38	35	32	29
6	66	54	46	40	61	51	44	38	45	39	35	40	35	32	35	31	28	26
7	61	49	41	35	57	46	39	34	41	35	31	36	32	28	32	28	25	23
8	57	44	37	31	53	42	35	30	38	32	28	33	29	25	29	26	23	21
9	53	41	33	28	49	39	32	27	35	29	25	31	26	23	27	23	21	19
10	49	37	30	25	46	36	29	24	32	26	23	28	24	21	25	22	19	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	13056	13056	13056	13056
5°	15144	13095	11574	13095
10°	17915	13038	10330	13038
15°	20695	12918	8877	12918
20°	23040	12752	8027	12752
25°	23785	12588	7452	12588
30°	20821	12392	7106	12392
35°	16208	12098	6897	12098
40°	12154	11763	6785	11763
45°	9597	11226	6725	11226
50°	8102	10605	6531	10605
55°	7061	9923	6180	9923
60°	6353	9216	5470	9216
65°	5601	8451	4705	8451
70°	5044	7659	4244	7659
75°	4226	6787	3618	6787
80°	3575	5783	3394	5783
85°	3020	4520	3020	4520



TEST NUMBER: P332969-830

CATALOG NUMBER: S124RDIP-S1020D810U830-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	156.7	2.3
10°-20°	472.7	6.9
20°-30°	739.3	10.8
30°-40°	821.9	12.1
40°-50°	729.2	10.7
50°-60°	568.2	8.3
60°-70°	372.0	5.5
70°-80°	182.9	2.7
80°-90°	47.2	0.7
90°-100°	270.9	4.0
100°-110°	563.9	8.3
110°-120°	505.1	7.4
120°-130°	424.9	6.2
130°-140°	354.3	5.2
140°-150°	270.6	4.0
150°-160°	190.2	2.8
160°-170°	111.9	1.6
170°-180°	36.4	0.5
0°-30°	1368.7	20.1
0°-40°	2190.5	32.1
0°-60°	3487.9	51.2
0°-90°	4090.0	60.0
90°-120°	1340.0	19.7
90°-150°	2389.7	35.0
90°-180°	2728.0	40.0
0°-180°	6818.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1617	1617	1617	1617	1617	
5°	1869	1616	1428	1616	1869	189
15°	2476	1546	1062	1546	2476	704
25°	2670	1413	837	1413	2670	1185
35°	1645	1228	700	1228	1645	1031
45°	841	983	589	983	841	666
55°	502	705	439	705	502	456
65°	293	442	246	442	293	295
75°	136	218	116	218	136	149
85°	33	49	33	49	33	37
90°	16	1	16	1	16	14
95°	180	24	180	24	180	279
105°	1037	86	1037	86	1037	1025
115°	996	152	996	152	996	988
125°	794	212	794	212	794	722
135°	710	251	710	251	710	548
145°	580	290	580	290	580	368
155°	486	329	486	329	486	227
165°	424	359	424	359	424	121
175°	382	374	382	374	382	37
180°	375	375	375	375	375	



TEST NUMBER: P332969-830

CATALOG NUMBER: S124RDIP-S1020D810U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2
2.5°	1705.8	1710.5	1705.8	1705.3	1700.2	1698.6	1696.5	1689.7	1677.2	1669.9	1671.4
5°	1868.8	1885.0	1875.9	1874.6	1860.3	1846.0	1836.8	1816.0	1793.8	1778.9	1766.4
7.5°	2057.2	2066.5	2060.9	2051.7	2028.5	2015.3	1994.2	1966.7	1927.0	1896.6	1868.9
10°	2185.4	2193.2	2190.7	2173.7	2156.7	2122.2	2102.6	2064.3	2014.0	1974.3	1937.1
12.5°	2311.6	2319.9	2297.0	2297.7	2265.7	2238.4	2207.4	2159.1	2101.1	2049.8	2003.4
15°	2476.1	2465.6	2465.6	2452.6	2416.7	2379.0	2347.0	2296.2	2223.2	2161.9	2097.4
17.5°	2604.8	2608.4	2603.1	2572.3	2544.2	2505.1	2446.6	2387.3	2319.5	2237.3	2171.3
20°	2681.9	2681.9	2676.1	2655.2	2618.8	2577.0	2513.9	2449.3	2363.3	2280.6	2206.3
22.5°	2713.2	2715.3	2708.4	2691.1	2658.3	2617.6	2563.8	2498.3	2409.7	2316.5	2224.5
25°	2670.2	2682.6	2683.9	2679.3	2669.6	2644.8	2598.5	2531.4	2451.9	2350.9	2251.8
27.5°	2451.6	2467.2	2480.9	2503.4	2533.4	2549.0	2551.1	2517.0	2447.6	2350.4	2250.7
30°	2233.6	2246.6	2289.1	2344.4	2387.4	2426.5	2460.4	2469.5	2430.4	2343.1	2238.2
32.5°	1991.8	2009.5	2051.8	2111.4	2183.0	2249.3	2325.3	2364.2	2363.1	2310.7	2213.7
35°	1644.6	1657.6	1696.8	1759.3	1845.3	1943.7	2064.3	2158.0	2221.9	2217.3	2158.0
37.5°	1326.3	1341.0	1380.5	1432.5	1515.9	1637.7	1754.4	1883.6	2001.7	2068.0	2048.1
40°	1153.3	1154.0	1192.4	1245.9	1324.0	1430.2	1557.3	1700.6	1832.2	1939.8	1960.6
42.5°	1016.7	1016.8	1042.3	1099.9	1156.2	1256.1	1377.4	1519.8	1673.8	1798.0	1853.2
45°	840.6	846.4	867.2	901.8	946.1	1030.8	1127.8	1260.2	1432.9	1580.1	1672.0
47.5°	711.8	720.4	733.7	761.9	797.1	853.6	933.9	1052.7	1193.2	1355.2	1485.9
50°	645.1	646.4	663.3	678.9	709.5	754.5	824.9	924.0	1052.9	1208.7	1354.0
52.5°	587.8	587.5	597.7	617.5	642.3	677.4	734.2	824.3	938.8	1078.4	1228.3
55°	501.7	505.0	512.8	528.4	547.3	572.1	617.1	684.9	774.8	894.0	1030.2
57.5°	436.3	438.0	444.1	450.7	468.1	486.1	519.8	566.8	642.7	740.4	867.2
60°	393.5	394.2	396.2	406.0	419.6	436.6	459.4	499.1	563.0	652.2	752.6
62.5°	351.9	353.0	356.0	363.2	373.7	385.5	409.3	441.3	494.2	570.4	660.8
65°	293.2	293.9	298.4	301.0	309.5	319.9	337.5	359.0	395.5	459.4	527.8
67.5°	245.0	245.0	245.2	248.7	254.7	261.6	272.1	289.3	316.8	356.0	416.3
70°	213.7	213.7	215.0	217.0	220.3	226.1	232.0	245.0	265.2	297.1	343.4
72.5°	184.5	185.0	186.3	186.7	188.4	193.2	197.6	205.9	220.9	245.0	282.4
75°	135.5	137.5	140.7	143.4	146.6	146.0	150.5	155.7	160.3	174.7	196.1
77.5°	100.9	99.8	100.2	102.5	102.8	103.5	106.7	110.7	114.1	120.9	128.7
80°	76.9	76.9	78.8	79.5	78.8	79.5	82.8	84.7	86.1	88.6	95.8
82.5°	58.2	59.2	58.5	59.2	59.6	60.2	63.0	63.3	64.7	65.7	68.7
85°	32.6	33.3	33.8	32.6	32.6	32.6	33.8	34.5	35.8	35.2	36.5
87.5°	14.6	14.0	14.7	14.6	14.9	14.4	14.8	15.6	14.5	15.2	14.9
90°	15.5	15.5	16.2	15.5	14.7	14.7	14.0	13.3	12.5	13.3	11.8
92.5°	56.7	56.7	59.3	63.2	71.9	86.7	109.0	144.8	194.7	233.8	204.6
95°	179.8	189.5	202.6	225.6	261.6	333.1	431.9	546.1	617.6	600.7	453.3
97.5°	480.7	496.0	518.1	562.5	615.4	692.3	764.4	806.8	775.9	632.6	424.2
100°	675.8	681.7	703.8	748.8	812.9	867.4	903.5	888.8	781.2	592.6	384.7
102.5°	845.6	850.4	873.6	906.3	945.6	968.3	957.8	884.7	737.0	542.4	358.2
105°	1037.0	1041.4	1051.7	1057.6	1056.1	1025.9	952.9	825.5	656.7	483.4	335.4
107.5°	1108.0	1106.1	1098.7	1081.9	1045.5	979.8	877.0	741.3	591.8	450.4	331.2
110°	1109.2	1102.6	1089.3	1058.3	1006.0	924.9	818.0	690.6	559.4	439.2	332.3



TEST NUMBER: P332969-830

CATALOG NUMBER: S124RDIP-S1020D810U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1074.4	1063.7	1045.1	1007.6	948.2	867.1	766.2	653.5	541.1	433.9	335.9
115°	995.7	989.8	966.2	922.0	863.7	793.0	706.8	616.1	524.0	431.1	342.7
117.5°	916.0	911.3	887.5	850.4	800.7	740.6	672.9	597.9	516.3	430.4	350.0
120°	871.1	863.0	843.9	811.4	769.4	717.1	658.2	589.6	512.2	430.4	355.2
122.5°	835.8	827.6	811.4	783.7	748.2	702.4	648.7	582.5	507.5	429.8	360.5
125°	794.5	790.0	776.1	754.7	725.2	684.7	633.9	570.4	499.6	429.0	368.5
127.5°	770.3	765.9	754.1	735.1	705.5	666.9	616.2	555.7	489.2	427.3	374.8
130°	756.2	751.8	740.0	721.5	691.3	652.2	602.1	543.9	482.8	426.7	379.6
132.5°	740.3	735.8	724.6	703.8	674.2	635.2	586.2	531.5	476.8	426.1	383.7
135°	710.5	706.1	694.3	673.6	644.1	607.3	562.3	514.4	468.0	425.3	389.8
137.5°	673.6	668.3	658.6	638.2	610.7	577.4	539.5	499.0	460.3	425.1	393.5
140°	647.1	641.2	630.8	614.6	588.9	557.9	524.7	490.1	456.2	424.5	396.5
142.5°	618.8	614.6	605.5	590.5	567.6	540.8	512.4	481.8	452.7	424.5	398.9
145°	580.0	576.4	568.9	556.5	538.0	517.4	495.3	470.2	446.6	423.0	400.2
147.5°	545.6	544.3	538.8	528.0	514.4	498.2	480.5	460.6	441.2	420.4	401.0
150°	526.2	525.5	521.0	511.5	499.6	486.4	471.6	454.7	437.1	418.6	401.0
152.5°	508.5	507.7	505.1	497.3	487.3	476.4	462.8	448.3	432.3	415.7	399.7
155°	485.7	485.7	483.4	477.6	470.2	461.4	450.3	438.5	425.3	411.2	397.9
157.5°	465.6	465.6	464.3	459.9	454.3	447.2	437.9	428.0	418.0	406.7	396.1
160°	453.3	453.3	452.5	448.1	443.7	437.8	429.7	421.6	412.7	403.1	394.3
162.5°	441.5	442.1	441.3	436.9	433.7	428.4	422.0	415.1	408.0	399.6	392.6
165°	423.8	424.5	425.3	422.3	419.3	415.7	410.5	406.0	400.2	394.3	389.2
167.5°	409.7	410.4	410.5	408.6	407.1	404.9	400.8	397.4	393.1	389.0	385.6
170°	401.0	401.0	401.6	401.0	399.4	397.3	394.3	392.1	388.4	385.4	383.2
172.5°	392.1	393.2	394.0	393.2	392.4	390.8	389.0	387.4	384.3	381.9	380.9
175°	381.7	383.2	384.7	383.2	383.2	383.2	381.7	381.1	379.6	378.1	378.1
177.5°	375.7	376.9	378.1	377.5	378.1	377.5	377.5	376.9	376.3	375.7	375.7
180°	375.1	375.1	375.1	375.1	375.1	375.1	375.1	375.1	375.1	375.1	375.1



TEST NUMBER: P332969-830

CATALOG NUMBER: S124RDIP-S1020D810U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2
2.5°	1666.2	1659.0	1655.3	1646.9	1637.0	1631.8	1627.1	1620.3	1611.5	1602.1	1595.3
5°	1750.8	1735.1	1715.6	1692.1	1671.3	1651.1	1633.5	1615.9	1595.7	1574.9	1554.1
7.5°	1837.6	1806.9	1773.6	1735.1	1697.8	1663.8	1632.5	1602.5	1568.6	1538.2	1510.6
10°	1898.1	1856.3	1810.1	1761.2	1712.3	1670.0	1628.3	1590.5	1548.8	1511.6	1480.4
12.5°	1947.1	1898.1	1842.4	1781.6	1722.8	1671.6	1623.6	1574.3	1526.9	1486.7	1444.9
15°	2028.4	1961.2	1886.3	1813.4	1737.1	1667.4	1602.9	1545.6	1491.5	1434.8	1395.1
17.5°	2084.2	2004.7	1913.5	1825.9	1735.8	1653.6	1579.1	1510.9	1448.5	1390.6	1343.3
20°	2117.6	2029.7	1928.7	1829.0	1728.0	1640.0	1559.9	1484.3	1419.8	1357.3	1308.3
22.5°	2136.4	2039.1	1928.7	1824.3	1719.7	1624.4	1536.4	1457.7	1387.5	1324.9	1270.8
25°	2142.4	2038.2	1925.4	1805.5	1690.8	1589.9	1498.6	1413.2	1335.1	1272.5	1215.2
27.5°	2134.1	2011.3	1895.8	1772.8	1654.5	1548.0	1452.3	1362.6	1284.3	1217.2	1158.4
30°	2121.6	1989.9	1866.1	1738.4	1618.5	1516.3	1415.2	1329.3	1247.7	1178.1	1118.8
32.5°	2094.4	1963.9	1830.7	1699.9	1578.4	1473.0	1377.1	1290.6	1210.8	1139.5	1076.6
35°	2040.8	1908.5	1763.9	1629.7	1510.3	1400.9	1311.0	1227.6	1151.3	1075.2	1008.6
37.5°	1970.0	1834.8	1691.0	1544.0	1424.7	1321.3	1238.8	1160.5	1086.1	1016.4	942.8
40°	1903.3	1780.1	1631.5	1485.6	1363.1	1263.4	1187.2	1116.2	1041.2	972.1	898.5
42.5°	1822.5	1717.6	1567.4	1421.0	1300.0	1204.0	1132.9	1063.5	995.3	928.4	851.6
45°	1687.6	1608.1	1467.4	1326.6	1204.8	1109.7	1044.5	983.3	923.3	859.4	787.1
47.5°	1533.0	1479.2	1357.7	1213.6	1100.9	1015.3	952.3	902.3	851.6	787.8	724.3
50°	1425.7	1391.1	1273.8	1142.3	1034.7	955.8	891.4	844.4	802.1	740.8	684.2
52.5°	1311.0	1292.6	1193.5	1067.7	963.8	886.6	831.4	789.2	746.3	695.5	642.4
55°	1136.3	1146.1	1062.1	953.3	855.5	790.4	740.2	705.0	668.5	625.6	584.5
57.5°	957.8	993.5	937.1	841.6	750.0	689.8	652.0	622.4	591.7	556.1	521.0
60°	850.9	880.9	849.0	765.0	684.9	628.8	593.6	570.8	540.2	507.6	480.9
62.5°	746.7	778.7	759.9	692.0	617.6	569.4	538.4	517.1	494.3	465.9	438.1
65°	615.8	636.6	627.5	580.6	527.8	486.7	458.1	442.4	421.6	400.8	376.0
67.5°	471.6	511.9	506.5	481.6	436.0	404.0	385.2	371.4	352.4	336.9	320.1
70°	387.7	424.8	424.1	404.0	379.2	349.2	336.2	324.5	307.6	292.6	278.9
72.5°	317.4	351.4	356.4	340.9	324.0	301.3	288.8	280.7	264.3	254.0	242.9
75°	222.2	246.9	253.4	253.4	245.6	233.9	222.8	217.6	205.9	196.8	190.3
77.5°	145.7	161.4	171.5	173.8	175.0	171.1	162.0	158.3	149.3	146.1	139.9
80°	102.9	113.4	125.1	129.0	132.2	131.0	127.1	124.4	116.0	112.7	110.1
82.5°	71.2	76.9	86.5	95.1	94.3	97.6	94.3	92.2	85.8	84.5	82.0
85°	37.1	37.8	39.1	45.0	48.3	49.5	50.1	48.8	46.9	46.9	42.3
87.5°	14.6	14.0	14.2	14.2	14.6	16.5	17.6	17.9	16.6	15.5	14.0
90°	10.3	10.3	5.9	5.9	5.2	4.4	2.2	0.8	2.2	4.4	5.2
92.5°	148.8	91.7	54.2	38.9	28.2	19.1	12.3	8.4	12.3	19.1	28.2
95°	277.1	156.3	92.1	61.2	43.5	33.9	26.5	24.3	26.5	33.9	43.5
97.5°	249.1	149.3	99.9	74.0	58.8	50.0	43.6	43.6	43.6	50.0	58.8
100°	234.4	151.1	107.6	84.0	70.0	61.2	56.0	56.0	56.0	61.2	70.0
102.5°	230.3	156.9	117.6	95.2	81.8	73.5	69.0	67.8	69.0	73.5	81.8
105°	232.1	171.0	135.6	114.2	100.9	92.1	88.4	86.2	88.4	92.1	100.9
107.5°	243.1	187.4	155.0	133.8	121.1	111.7	108.0	106.6	108.0	111.7	121.1
110°	251.3	199.7	167.3	147.4	134.1	125.3	121.6	120.2	121.6	125.3	134.1





TEST NUMBER: P332969-830

CATALOG NUMBER: S124RDIP-S1020D810U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	260.1	211.5	180.3	160.3	147.1	138.8	134.6	133.1	134.6	138.8	147.1
115°	274.2	230.0	200.5	180.6	166.5	159.2	154.0	151.8	154.0	159.2	166.5
117.5°	288.4	247.8	219.8	199.2	186.1	178.0	173.3	171.3	173.3	178.0	186.1
120°	298.5	260.1	232.1	211.5	199.0	190.9	185.7	184.3	185.7	190.9	199.0
122.5°	307.9	271.9	243.9	223.9	210.2	202.6	197.6	196.0	197.6	202.6	210.2
125°	322.1	288.1	261.6	241.0	227.0	218.9	214.4	211.5	214.4	218.9	227.0
127.5°	334.3	303.2	277.6	256.7	242.1	232.9	227.6	225.3	227.6	232.9	242.1
130°	342.0	313.2	288.1	266.8	252.8	241.8	235.8	232.9	235.8	241.8	252.8
132.5°	349.6	321.5	296.4	276.3	261.1	250.6	242.9	240.5	242.9	250.6	261.1
135°	359.7	333.1	308.8	289.6	274.2	261.6	254.3	251.3	254.3	261.6	274.2
137.5°	366.7	342.0	319.2	301.0	284.9	273.0	264.9	262.1	264.9	273.0	284.9
140°	371.5	347.9	325.7	308.0	292.6	280.0	271.9	269.8	271.9	280.0	292.6
142.5°	374.9	353.2	331.7	314.5	299.6	287.8	280.2	278.0	280.2	287.8	299.6
145°	378.8	358.9	339.8	323.6	309.5	299.3	291.8	289.6	291.8	299.3	309.5
147.5°	382.2	364.9	346.9	332.2	320.6	310.0	303.5	302.7	303.5	310.0	320.6
150°	384.0	367.8	351.6	337.5	326.5	317.6	311.8	311.0	311.8	317.6	326.5
152.5°	385.1	370.1	355.7	342.9	333.0	324.7	318.9	318.7	318.9	324.7	333.0
155°	386.2	373.6	361.1	350.1	342.0	334.6	330.2	329.4	330.2	334.6	342.0
157.5°	386.2	376.2	365.5	356.8	349.8	344.0	339.9	339.9	339.9	344.0	349.8
160°	386.2	377.3	368.5	360.4	354.5	349.3	346.4	346.4	346.4	349.3	354.5
162.5°	386.2	378.5	370.2	363.9	358.6	354.0	351.7	352.3	351.7	354.0	358.6
165°	384.7	378.8	372.2	367.8	364.1	360.4	358.9	358.9	358.9	360.4	364.1
167.5°	383.0	378.7	373.8	370.4	368.3	365.5	364.9	365.5	364.9	365.5	368.3
170°	381.7	378.1	374.4	372.2	370.7	368.5	367.8	368.5	367.8	368.5	370.7
172.5°	380.6	377.5	374.9	373.3	372.5	370.9	370.7	371.5	370.7	370.9	372.5
175°	378.8	376.6	375.1	375.1	374.4	373.6	373.6	374.4	373.6	373.6	374.4
177.5°	376.9	375.7	375.1	375.1	375.1	374.6	375.1	375.7	375.1	374.6	375.1
180°	375.1	375.1	375.1	375.1	375.1	375.1	375.1	375.1	375.1	375.1	375.1



TEST NUMBER: P332969-830

CATALOG NUMBER: S124RDIP-S1020D810U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2
2.5°	1588.0	1582.8	1576.0	1568.2	1558.9	1550.5	1546.9	1550.0	1551.5	1547.4	1546.9
5°	1539.7	1523.4	1510.3	1490.8	1475.2	1462.2	1453.0	1449.2	1450.4	1440.0	1437.4
7.5°	1485.4	1466.0	1444.7	1421.4	1399.9	1380.7	1370.6	1365.2	1354.2	1349.4	1341.5
10°	1450.4	1424.4	1403.5	1376.1	1351.4	1328.6	1317.5	1308.3	1297.3	1292.1	1281.0
12.5°	1414.5	1384.2	1361.3	1332.8	1307.6	1280.1	1269.5	1252.6	1235.3	1224.4	1210.1
15°	1363.8	1327.3	1299.3	1265.4	1235.4	1204.1	1176.1	1144.8	1133.1	1108.3	1094.0
17.5°	1304.5	1267.4	1232.8	1187.3	1141.0	1102.2	1072.3	1042.4	1024.4	1008.6	1001.4
20°	1265.4	1231.5	1183.3	1130.5	1079.0	1036.0	1011.9	992.4	972.8	961.8	953.9
22.5°	1228.3	1185.1	1129.1	1072.1	1020.7	987.0	966.6	946.5	930.6	920.0	909.6
25°	1166.3	1109.7	1050.4	985.2	950.0	920.7	898.5	882.2	872.5	858.8	853.6
27.5°	1102.6	1034.0	968.6	924.7	888.1	861.3	842.0	829.7	817.4	808.6	801.8
30°	1053.6	983.9	925.3	883.5	846.4	824.3	808.6	794.3	784.5	777.3	772.1
32.5°	1005.1	935.4	886.2	841.3	812.0	790.4	773.7	763.0	755.4	746.0	742.9
35°	935.0	873.1	830.1	789.8	759.8	740.2	727.2	716.0	709.5	707.0	705.0
37.5°	867.6	817.0	770.7	737.6	710.9	695.5	680.1	674.7	670.2	665.5	667.6
40°	824.9	777.3	736.3	701.1	679.6	662.7	653.6	647.1	643.1	643.1	643.1
42.5°	787.9	741.4	701.3	669.9	648.3	634.0	623.9	618.3	617.1	616.5	619.6
45°	730.5	687.4	647.1	620.9	602.8	588.3	582.5	578.0	578.0	580.6	581.2
47.5°	673.4	633.2	600.8	571.6	554.9	545.9	540.8	538.5	538.8	541.3	544.3
50°	638.6	598.8	566.8	540.8	525.2	516.7	512.2	510.9	512.2	512.2	516.7
52.5°	600.5	565.0	533.5	511.6	493.9	486.0	483.4	481.6	482.4	484.6	486.4
55°	544.7	512.8	482.9	461.9	448.9	443.7	437.9	438.5	437.2	438.5	438.5
57.5°	488.8	460.1	432.3	415.8	404.3	396.7	390.3	392.1	390.2	389.9	388.9
60°	452.9	421.6	399.4	384.5	371.4	364.9	359.0	360.3	358.4	357.0	354.5
62.5°	413.8	387.7	366.6	352.1	341.7	334.1	328.3	327.0	322.4	318.0	312.3
65°	357.0	335.5	316.7	303.0	293.2	287.4	282.8	278.9	269.1	258.6	253.4
67.5°	302.0	286.4	268.8	257.2	249.3	241.6	232.9	226.2	217.1	211.4	208.1
70°	266.5	251.5	236.5	225.5	217.0	209.8	200.0	195.5	189.0	186.3	183.1
72.5°	232.6	218.7	204.7	194.7	185.7	180.1	172.4	167.9	164.9	163.9	160.7
75°	181.2	170.0	159.7	150.5	143.4	139.4	136.2	132.9	131.6	125.7	122.5
77.5°	132.1	124.9	118.3	111.8	106.7	104.2	97.8	94.1	91.9	89.2	88.5
80°	102.9	97.7	91.2	87.3	80.1	77.6	74.9	74.3	73.6	73.0	72.3
82.5°	77.4	72.2	65.7	63.3	61.4	59.9	58.2	57.6	56.9	57.3	57.2
85°	39.1	36.5	36.5	35.8	35.2	34.5	33.8	33.8	33.3	33.8	33.3
87.5°	14.2	13.7	14.6	13.6	14.3	14.6	13.9	14.1	14.8	13.9	13.9
90°	5.9	5.9	10.3	10.3	11.8	13.3	12.5	13.3	14.0	14.7	14.7
92.5°	38.9	54.2	91.7	148.8	204.6	233.8	194.7	144.8	109.0	86.7	71.9
95°	61.2	92.1	156.3	277.1	453.3	600.7	617.6	546.1	431.9	333.1	261.6
97.5°	74.0	99.9	149.3	249.1	424.2	632.6	775.9	806.8	764.4	692.3	615.4
100°	84.0	107.6	151.1	234.4	384.7	592.6	781.2	888.8	903.5	867.4	812.9
102.5°	95.2	117.6	156.9	230.3	358.2	542.4	737.0	884.7	957.8	968.3	945.6
105°	114.2	135.6	171.0	232.1	335.4	483.4	656.7	825.5	952.9	1025.9	1056.1
107.5°	133.8	155.0	187.4	243.1	331.2	450.4	591.8	741.3	877.0	979.8	1045.5
110°	147.4	167.3	199.7	251.3	332.3	439.2	559.4	690.6	818.0	924.9	1006.0



TEST NUMBER: P332969-830

CATALOG NUMBER: S124RDIP-S1020D810U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	160.3	180.3	211.5	260.1	335.9	433.9	541.1	653.5	766.2	867.1	948.2
115°	180.6	200.5	230.0	274.2	342.7	431.1	524.0	616.1	706.8	793.0	863.7
117.5°	199.2	219.8	247.8	288.4	350.0	430.4	516.3	597.9	672.9	740.6	800.7
120°	211.5	232.1	260.1	298.5	355.2	430.4	512.2	589.6	658.2	717.1	769.4
122.5°	223.9	243.9	271.9	307.9	360.5	429.8	507.5	582.5	648.7	702.4	748.2
125°	241.0	261.6	288.1	322.1	368.5	429.0	499.6	570.4	633.9	684.7	725.2
127.5°	256.7	277.6	303.2	334.3	374.8	427.3	489.2	555.7	616.2	666.9	705.5
130°	266.8	288.1	313.2	342.0	379.6	426.7	482.8	543.9	602.1	652.2	691.3
132.5°	276.3	296.4	321.5	349.6	383.7	426.1	476.8	531.5	586.2	635.2	674.2
135°	289.6	308.8	333.1	359.7	389.8	425.3	468.0	514.4	562.3	607.3	644.1
137.5°	301.0	319.2	342.0	366.7	393.5	425.1	460.3	499.0	539.5	577.4	610.7
140°	308.0	325.7	347.9	371.5	396.5	424.5	456.2	490.1	524.7	557.9	588.9
142.5°	314.5	331.7	353.2	374.9	398.9	424.5	452.7	481.8	512.4	540.8	567.6
145°	323.6	339.8	358.9	378.8	400.2	423.0	446.6	470.2	495.3	517.4	538.0
147.5°	332.2	346.9	364.9	382.2	401.0	420.4	441.2	460.6	480.5	498.2	514.4
150°	337.5	351.6	367.8	384.0	401.0	418.6	437.1	454.7	471.6	486.4	499.6
152.5°	342.9	355.7	370.1	385.1	399.7	415.7	432.3	448.3	462.8	476.4	487.3
155°	350.1	361.1	373.6	386.2	397.9	411.2	425.3	438.5	450.3	461.4	470.2
157.5°	356.8	365.5	376.2	386.2	396.1	406.7	418.0	428.0	437.9	447.2	454.3
160°	360.4	368.5	377.3	386.2	394.3	403.1	412.7	421.6	429.7	437.8	443.7
162.5°	363.9	370.2	378.5	386.2	392.6	399.6	408.0	415.1	422.0	428.4	433.7
165°	367.8	372.2	378.8	384.7	389.2	394.3	400.2	406.0	410.5	415.7	419.3
167.5°	370.4	373.8	378.7	383.0	385.6	389.0	393.1	397.4	400.8	404.9	407.1
170°	372.2	374.4	378.1	381.7	383.2	385.4	388.4	392.1	394.3	397.3	399.4
172.5°	373.3	374.9	377.5	380.6	380.9	381.9	384.3	387.4	389.0	390.8	392.4
175°	375.1	375.1	376.6	378.8	378.1	378.1	379.6	381.1	381.7	383.2	383.2
177.5°	375.1	375.1	375.7	376.9	375.7	375.7	376.3	376.9	377.5	377.5	378.1
180°	375.1	375.1	375.1	375.1	375.1	375.1	375.1	375.1	375.1	375.1	375.1



TEST NUMBER: P332969-830

CATALOG NUMBER: S124RDIP-S1020D810U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2
2.5°	1543.7	1544.7	1541.2	1540.1	1541.2	1544.7	1543.7	1546.9	1547.4	1551.5	1550.0
5°	1432.2	1430.9	1427.6	1428.2	1427.6	1430.9	1432.2	1437.4	1440.0	1450.4	1449.2
7.5°	1336.8	1331.7	1333.1	1327.9	1333.1	1331.7	1336.8	1341.5	1349.4	1354.2	1365.2
10°	1278.4	1271.2	1265.4	1260.2	1265.4	1271.2	1278.4	1281.0	1292.1	1297.3	1308.3
12.5°	1198.6	1192.5	1184.6	1186.2	1184.6	1192.5	1198.6	1210.1	1224.4	1235.3	1252.6
15°	1085.5	1075.7	1060.2	1062.1	1060.2	1075.7	1085.5	1094.0	1108.3	1133.1	1144.8
17.5°	989.8	989.9	982.7	984.4	982.7	989.9	989.8	1001.4	1008.6	1024.4	1042.4
20°	940.3	935.7	936.3	934.3	936.3	935.7	940.3	953.9	961.8	972.8	992.4
22.5°	905.9	900.2	895.7	891.6	895.7	900.2	905.9	909.6	920.0	930.6	946.5
25°	847.7	843.8	837.9	836.6	837.9	843.8	847.7	853.6	858.8	872.5	882.2
27.5°	796.6	795.9	793.5	790.5	793.5	795.9	796.6	801.8	808.6	817.4	829.7
30°	766.9	765.6	764.3	762.3	764.3	765.6	766.9	772.1	777.3	784.5	794.3
32.5°	740.4	739.5	738.2	738.4	738.2	739.5	740.4	742.9	746.0	755.4	763.0
35°	702.4	701.7	700.5	699.8	700.5	701.7	702.4	705.0	707.0	709.5	716.0
37.5°	666.9	668.6	667.9	667.7	667.9	668.6	666.9	667.6	665.5	670.2	674.7
40°	642.4	643.1	644.4	643.8	644.4	643.1	642.4	643.1	643.1	643.1	647.1
42.5°	622.2	622.3	624.1	621.9	624.1	622.3	622.2	619.6	616.5	617.1	618.3
45°	585.8	589.7	589.0	589.0	589.0	589.7	585.8	581.2	580.6	578.0	578.0
47.5°	546.0	549.4	550.4	550.2	550.4	549.4	546.0	544.3	541.3	538.8	538.5
50°	520.0	518.7	520.7	520.0	520.7	518.7	520.0	516.7	512.2	512.2	510.9
52.5°	488.1	488.4	488.3	487.7	488.3	488.4	488.1	486.4	484.6	482.4	481.6
55°	439.1	439.8	438.5	439.1	438.5	439.8	439.1	438.5	438.5	437.2	438.5
57.5°	386.0	382.9	384.2	382.6	384.2	382.9	386.0	388.9	389.9	390.2	392.1
60°	348.0	342.7	341.4	338.8	341.4	342.7	348.0	354.5	357.0	358.4	360.3
62.5°	305.2	301.5	297.1	299.2	297.1	301.5	305.2	312.3	318.0	322.4	327.0
65°	248.3	245.6	243.6	246.3	243.6	245.6	248.3	253.4	258.6	269.1	278.9
67.5°	205.5	204.1	204.1	202.7	204.1	204.1	205.5	208.1	211.4	217.1	226.2
70°	183.1	181.2	181.2	179.8	181.2	181.2	183.1	183.1	186.3	189.0	195.5
72.5°	160.1	158.2	158.7	158.0	158.7	158.2	160.1	160.7	163.9	164.9	167.9
75°	118.6	115.4	115.4	116.0	115.4	115.4	118.6	122.5	125.7	131.6	132.9
77.5°	88.5	87.8	88.8	87.6	88.8	87.8	88.5	88.5	89.2	91.9	94.1
80°	72.3	71.6	71.1	73.0	71.1	71.6	72.3	72.3	73.0	73.6	74.3
82.5°	56.2	56.1	55.9	58.3	55.9	56.1	56.2	57.2	57.3	56.9	57.6
85°	33.8	32.6	33.8	32.6	33.8	32.6	33.8	33.3	33.8	33.3	33.8
87.5°	15.1	14.7	14.0	14.6	14.0	14.7	15.1	13.9	13.9	14.8	14.1
90°	15.5	16.2	15.5	15.5	15.5	16.2	15.5	14.7	14.7	14.0	13.3
92.5°	63.2	59.3	56.7	56.7	56.7	59.3	63.2	71.9	86.7	109.0	144.8
95°	225.6	202.6	189.5	179.8	189.5	202.6	225.6	261.6	333.1	431.9	546.1
97.5°	562.5	518.1	496.0	480.7	496.0	518.1	562.5	615.4	692.3	764.4	806.8
100°	748.8	703.8	681.7	675.8	681.7	703.8	748.8	812.9	867.4	903.5	888.8
102.5°	906.3	873.6	850.4	845.6	850.4	873.6	906.3	945.6	968.3	957.8	884.7
105°	1057.6	1051.7	1041.4	1037.0	1041.4	1051.7	1057.6	1056.1	1025.9	952.9	825.5
107.5°	1081.9	1098.7	1106.1	1108.0	1106.1	1098.7	1081.9	1045.5	979.8	877.0	741.3
110°	1058.3	1089.3	1102.6	1109.2	1102.6	1089.3	1058.3	1006.0	924.9	818.0	690.6



TEST NUMBER: P332969-830

CATALOG NUMBER: S124RDIP-S1020D810U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1007.6	1045.1	1063.7	1074.4	1063.7	1045.1	1007.6	948.2	867.1	766.2	653.5
115°	922.0	966.2	989.8	995.7	989.8	966.2	922.0	863.7	793.0	706.8	616.1
117.5°	850.4	887.5	911.3	916.0	911.3	887.5	850.4	800.7	740.6	672.9	597.9
120°	811.4	843.9	863.0	871.1	863.0	843.9	811.4	769.4	717.1	658.2	589.6
122.5°	783.7	811.4	827.6	835.8	827.6	811.4	783.7	748.2	702.4	648.7	582.5
125°	754.7	776.1	790.0	794.5	790.0	776.1	754.7	725.2	684.7	633.9	570.4
127.5°	735.1	754.1	765.9	770.3	765.9	754.1	735.1	705.5	666.9	616.2	555.7
130°	721.5	740.0	751.8	756.2	751.8	740.0	721.5	691.3	652.2	602.1	543.9
132.5°	703.8	724.6	735.8	740.3	735.8	724.6	703.8	674.2	635.2	586.2	531.5
135°	673.6	694.3	706.1	710.5	706.1	694.3	673.6	644.1	607.3	562.3	514.4
137.5°	638.2	658.6	668.3	673.6	668.3	658.6	638.2	610.7	577.4	539.5	499.0
140°	614.6	630.8	641.2	647.1	641.2	630.8	614.6	588.9	557.9	524.7	490.1
142.5°	590.5	605.5	614.6	618.8	614.6	605.5	590.5	567.6	540.8	512.4	481.8
145°	556.5	568.9	576.4	580.0	576.4	568.9	556.5	538.0	517.4	495.3	470.2
147.5°	528.0	538.8	544.3	545.6	544.3	538.8	528.0	514.4	498.2	480.5	460.6
150°	511.5	521.0	525.5	526.2	525.5	521.0	511.5	499.6	486.4	471.6	454.7
152.5°	497.3	505.1	507.7	508.5	507.7	505.1	497.3	487.3	476.4	462.8	448.3
155°	477.6	483.4	485.7	485.7	485.7	483.4	477.6	470.2	461.4	450.3	438.5
157.5°	459.9	464.3	465.6	465.6	465.6	464.3	459.9	454.3	447.2	437.9	428.0
160°	448.1	452.5	453.3	453.3	453.3	452.5	448.1	443.7	437.8	429.7	421.6
162.5°	436.9	441.3	442.1	441.5	442.1	441.3	436.9	433.7	428.4	422.0	415.1
165°	422.3	425.3	424.5	423.8	424.5	425.3	422.3	419.3	415.7	410.5	406.0
167.5°	408.6	410.5	410.4	409.7	410.4	410.5	408.6	407.1	404.9	400.8	397.4
170°	401.0	401.6	401.0	401.0	401.0	401.6	401.0	399.4	397.3	394.3	392.1
172.5°	393.2	394.0	393.2	392.1	393.2	394.0	393.2	392.4	390.8	389.0	387.4
175°	383.2	384.7	383.2	381.7	383.2	384.7	383.2	383.2	383.2	381.7	381.1
177.5°	377.5	378.1	376.9	375.7	376.9	378.1	377.5	378.1	377.5	377.5	376.9
180°	375.1	375.1	375.1	375.1	375.1	375.1	375.1	375.1	375.1	375.1	375.1



TEST NUMBER: P332969-830

CATALOG NUMBER: S124RDIP-S1020D810U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2
2.5°	1546.9	1550.5	1558.9	1568.2	1576.0	1582.8	1588.0	1595.3	1602.1	1611.5	1620.3
5°	1453.0	1462.2	1475.2	1490.8	1510.3	1523.4	1539.7	1554.1	1574.9	1595.7	1615.9
7.5°	1370.6	1380.7	1399.9	1421.4	1444.7	1466.0	1485.4	1510.6	1538.2	1568.6	1602.5
10°	1317.5	1328.6	1351.4	1376.1	1403.5	1424.4	1450.4	1480.4	1511.6	1548.8	1590.5
12.5°	1269.5	1280.1	1307.6	1332.8	1361.3	1384.2	1414.5	1444.9	1486.7	1526.9	1574.3
15°	1176.1	1204.1	1235.4	1265.4	1299.3	1327.3	1363.8	1395.1	1434.8	1491.5	1545.6
17.5°	1072.3	1102.2	1141.0	1187.3	1232.8	1267.4	1304.5	1343.3	1390.6	1448.5	1510.9
20°	1011.9	1036.0	1079.0	1130.5	1183.3	1231.5	1265.4	1308.3	1357.3	1419.8	1484.3
22.5°	966.6	987.0	1020.7	1072.1	1129.1	1185.1	1228.3	1270.8	1324.9	1387.5	1457.7
25°	898.5	920.7	950.0	985.2	1050.4	1109.7	1166.3	1215.2	1272.5	1335.1	1413.2
27.5°	842.0	861.3	888.1	924.7	968.6	1034.0	1102.6	1158.4	1217.2	1284.3	1362.6
30°	808.6	824.3	846.4	883.5	925.3	983.9	1053.6	1118.8	1178.1	1247.7	1329.3
32.5°	773.7	790.4	812.0	841.3	886.2	935.4	1005.1	1076.6	1139.5	1210.8	1290.6
35°	727.2	740.2	759.8	789.8	830.1	873.1	935.0	1008.6	1075.2	1151.3	1227.6
37.5°	680.1	695.5	710.9	737.6	770.7	817.0	867.6	942.8	1016.4	1086.1	1160.5
40°	653.6	662.7	679.6	701.1	736.3	777.3	824.9	898.5	972.1	1041.2	1116.2
42.5°	623.9	634.0	648.3	669.9	701.3	741.4	787.9	851.6	928.4	995.3	1063.5
45°	582.5	588.3	602.8	620.9	647.1	687.4	730.5	787.1	859.4	923.3	983.3
47.5°	540.8	545.9	554.9	571.6	600.8	633.2	673.4	724.3	787.8	851.6	902.3
50°	512.2	516.7	525.2	540.8	566.8	598.8	638.6	684.2	740.8	802.1	844.4
52.5°	483.4	486.0	493.9	511.6	533.5	565.0	600.5	642.4	695.5	746.3	789.2
55°	437.9	443.7	448.9	461.9	482.9	512.8	544.7	584.5	625.6	668.5	705.0
57.5°	390.3	396.7	404.3	415.8	432.3	460.1	488.8	521.0	556.1	591.7	622.4
60°	359.0	364.9	371.4	384.5	399.4	421.6	452.9	480.9	507.6	540.2	570.8
62.5°	328.3	334.1	341.7	352.1	366.6	387.7	413.8	438.1	465.9	494.3	517.1
65°	282.8	287.4	293.2	303.0	316.7	335.5	357.0	376.0	400.8	421.6	442.4
67.5°	232.9	241.6	249.3	257.2	268.8	286.4	302.0	320.1	336.9	352.4	371.4
70°	200.0	209.8	217.0	225.5	236.5	251.5	266.5	278.9	292.6	307.6	324.5
72.5°	172.4	180.1	185.7	194.7	204.7	218.7	232.6	242.9	254.0	264.3	280.7
75°	136.2	139.4	143.4	150.5	159.7	170.0	181.2	190.3	196.8	205.9	217.6
77.5°	97.8	104.2	106.7	111.8	118.3	124.9	132.1	139.9	146.1	149.3	158.3
80°	74.9	77.6	80.1	87.3	91.2	97.7	102.9	110.1	112.7	116.0	124.4
82.5°	58.2	59.9	61.4	63.3	65.7	72.2	77.4	82.0	84.5	85.8	92.2
85°	33.8	34.5	35.2	35.8	36.5	36.5	39.1	42.3	46.9	46.9	48.8
87.5°	13.9	14.6	14.3	13.6	14.6	13.7	14.2	14.0	15.5	16.6	17.9
90°	12.5	13.3	11.8	10.3	10.3	5.9	5.9	5.2	4.4	2.2	0.8
92.5°	194.7	233.8	204.6	148.8	91.7	54.2	38.9	28.2	19.1	12.3	8.4
95°	617.6	600.7	453.3	277.1	156.3	92.1	61.2	43.5	33.9	26.5	24.3
97.5°	775.9	632.6	424.2	249.1	149.3	99.9	74.0	58.8	50.0	43.6	43.6
100°	781.2	592.6	384.7	234.4	151.1	107.6	84.0	70.0	61.2	56.0	56.0
102.5°	737.0	542.4	358.2	230.3	156.9	117.6	95.2	81.8	73.5	69.0	67.8
105°	656.7	483.4	335.4	232.1	171.0	135.6	114.2	100.9	92.1	88.4	86.2
107.5°	591.8	450.4	331.2	243.1	187.4	155.0	133.8	121.1	111.7	108.0	106.6
110°	559.4	439.2	332.3	251.3	199.7	167.3	147.4	134.1	125.3	121.6	120.2



TEST NUMBER: P332969-830

CATALOG NUMBER: S124RDIP-S1020D810U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	541.1	433.9	335.9	260.1	211.5	180.3	160.3	147.1	138.8	134.6	133.1
115°	524.0	431.1	342.7	274.2	230.0	200.5	180.6	166.5	159.2	154.0	151.8
117.5°	516.3	430.4	350.0	288.4	247.8	219.8	199.2	186.1	178.0	173.3	171.3
120°	512.2	430.4	355.2	298.5	260.1	232.1	211.5	199.0	190.9	185.7	184.3
122.5°	507.5	429.8	360.5	307.9	271.9	243.9	223.9	210.2	202.6	197.6	196.0
125°	499.6	429.0	368.5	322.1	288.1	261.6	241.0	227.0	218.9	214.4	211.5
127.5°	489.2	427.3	374.8	334.3	303.2	277.6	256.7	242.1	232.9	227.6	225.3
130°	482.8	426.7	379.6	342.0	313.2	288.1	266.8	252.8	241.8	235.8	232.9
132.5°	476.8	426.1	383.7	349.6	321.5	296.4	276.3	261.1	250.6	242.9	240.5
135°	468.0	425.3	389.8	359.7	333.1	308.8	289.6	274.2	261.6	254.3	251.3
137.5°	460.3	425.1	393.5	366.7	342.0	319.2	301.0	284.9	273.0	264.9	262.1
140°	456.2	424.5	396.5	371.5	347.9	325.7	308.0	292.6	280.0	271.9	269.8
142.5°	452.7	424.5	398.9	374.9	353.2	331.7	314.5	299.6	287.8	280.2	278.0
145°	446.6	423.0	400.2	378.8	358.9	339.8	323.6	309.5	299.3	291.8	289.6
147.5°	441.2	420.4	401.0	382.2	364.9	346.9	332.2	320.6	310.0	303.5	302.7
150°	437.1	418.6	401.0	384.0	367.8	351.6	337.5	326.5	317.6	311.8	311.0
152.5°	432.3	415.7	399.7	385.1	370.1	355.7	342.9	333.0	324.7	318.9	318.7
155°	425.3	411.2	397.9	386.2	373.6	361.1	350.1	342.0	334.6	330.2	329.4
157.5°	418.0	406.7	396.1	386.2	376.2	365.5	356.8	349.8	344.0	339.9	339.9
160°	412.7	403.1	394.3	386.2	377.3	368.5	360.4	354.5	349.3	346.4	346.4
162.5°	408.0	399.6	392.6	386.2	378.5	370.2	363.9	358.6	354.0	351.7	352.3
165°	400.2	394.3	389.2	384.7	378.8	372.2	367.8	364.1	360.4	358.9	358.9
167.5°	393.1	389.0	385.6	383.0	378.7	373.8	370.4	368.3	365.5	364.9	365.5
170°	388.4	385.4	383.2	381.7	378.1	374.4	372.2	370.7	368.5	367.8	368.5
172.5°	384.3	381.9	380.9	380.6	377.5	374.9	373.3	372.5	370.9	370.7	371.5
175°	379.6	378.1	378.1	378.8	376.6	375.1	375.1	374.4	373.6	373.6	374.4
177.5°	376.3	375.7	375.7	376.9	375.7	375.1	375.1	375.1	374.6	375.1	375.7
180°	375.1	375.1	375.1	375.1	375.1	375.1	375.1	375.1	375.1	375.1	375.1



TEST NUMBER: P332969-830

CATALOG NUMBER: S124RDIP-S1020D810U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2
2.5°	1627.1	1631.8	1637.0	1646.9	1655.3	1659.0	1666.2	1671.4	1669.9	1677.2	1689.7
5°	1633.5	1651.1	1671.3	1692.1	1715.6	1735.1	1750.8	1766.4	1778.9	1793.8	1816.0
7.5°	1632.5	1663.8	1697.8	1735.1	1773.6	1806.9	1837.6	1868.9	1896.6	1927.0	1966.7
10°	1628.3	1670.0	1712.3	1761.2	1810.1	1856.3	1898.1	1937.1	1974.3	2014.0	2064.3
12.5°	1623.6	1671.6	1722.8	1781.6	1842.4	1898.1	1947.1	2003.4	2049.8	2101.1	2159.1
15°	1602.9	1667.4	1737.1	1813.4	1886.3	1961.2	2028.4	2097.4	2161.9	2223.2	2296.2
17.5°	1579.1	1653.6	1735.8	1825.9	1913.5	2004.7	2084.2	2171.3	2237.3	2319.5	2387.3
20°	1559.9	1640.0	1728.0	1829.0	1928.7	2029.7	2117.6	2206.3	2280.6	2363.3	2449.3
22.5°	1536.4	1624.4	1719.7	1824.3	1928.7	2039.1	2136.4	2224.5	2316.5	2409.7	2498.3
25°	1498.6	1589.9	1690.8	1805.5	1925.4	2038.2	2142.4	2251.8	2350.9	2451.9	2531.4
27.5°	1452.3	1548.0	1654.5	1772.8	1895.8	2011.3	2134.1	2250.7	2350.4	2447.6	2517.0
30°	1415.2	1516.3	1618.5	1738.4	1866.1	1989.9	2121.6	2238.2	2343.1	2430.4	2469.5
32.5°	1377.1	1473.0	1578.4	1699.9	1830.7	1963.9	2094.4	2213.7	2310.7	2363.1	2364.2
35°	1311.0	1400.9	1510.3	1629.7	1763.9	1908.5	2040.8	2158.0	2217.3	2221.9	2158.0
37.5°	1238.8	1321.3	1424.7	1544.0	1691.0	1834.8	1970.0	2048.1	2068.0	2001.7	1883.6
40°	1187.2	1263.4	1363.1	1485.6	1631.5	1780.1	1903.3	1960.6	1939.8	1832.2	1700.6
42.5°	1132.9	1204.0	1300.0	1421.0	1567.4	1717.6	1822.5	1853.2	1798.0	1673.8	1519.8
45°	1044.5	1109.7	1204.8	1326.6	1467.4	1608.1	1687.6	1672.0	1580.1	1432.9	1260.2
47.5°	952.3	1015.3	1100.9	1213.6	1357.7	1479.2	1533.0	1485.9	1355.2	1193.2	1052.7
50°	891.4	955.8	1034.7	1142.3	1273.8	1391.1	1425.7	1354.0	1208.7	1052.9	924.0
52.5°	831.4	886.6	963.8	1067.7	1193.5	1292.6	1311.0	1228.3	1078.4	938.8	824.3
55°	740.2	790.4	855.5	953.3	1062.1	1146.1	1136.3	1030.2	894.0	774.8	684.9
57.5°	652.0	689.8	750.0	841.6	937.1	993.5	957.8	867.2	740.4	642.7	566.8
60°	593.6	628.8	684.9	765.0	849.0	880.9	850.9	752.6	652.2	563.0	499.1
62.5°	538.4	569.4	617.6	692.0	759.9	778.7	746.7	660.8	570.4	494.2	441.3
65°	458.1	486.7	527.8	580.6	627.5	636.6	615.8	527.8	459.4	395.5	359.0
67.5°	385.2	404.0	436.0	481.6	506.5	511.9	471.6	416.3	356.0	316.8	289.3
70°	336.2	349.2	379.2	404.0	424.1	424.8	387.7	343.4	297.1	265.2	245.0
72.5°	288.8	301.3	324.0	340.9	356.4	351.4	317.4	282.4	245.0	220.9	205.9
75°	222.8	233.9	245.6	253.4	253.4	246.9	222.2	196.1	174.7	160.3	155.7
77.5°	162.0	171.1	175.0	173.8	171.5	161.4	145.7	128.7	120.9	114.1	110.7
80°	127.1	131.0	132.2	129.0	125.1	113.4	102.9	95.8	88.6	86.1	84.7
82.5°	94.3	97.6	94.3	95.1	86.5	76.9	71.2	68.7	65.7	64.7	63.3
85°	50.1	49.5	48.3	45.0	39.1	37.8	37.1	36.5	35.2	35.8	34.5
87.5°	17.6	16.5	14.6	14.2	14.2	14.0	14.6	14.9	15.2	14.5	15.6
90°	2.2	4.4	5.2	5.9	5.9	10.3	10.3	11.8	13.3	12.5	13.3
92.5°	12.3	19.1	28.2	38.9	54.2	91.7	148.8	204.6	233.8	194.7	144.8
95°	26.5	33.9	43.5	61.2	92.1	156.3	277.1	453.3	600.7	617.6	546.1
97.5°	43.6	50.0	58.8	74.0	99.9	149.3	249.1	424.2	632.6	775.9	806.8
100°	56.0	61.2	70.0	84.0	107.6	151.1	234.4	384.7	592.6	781.2	888.8
102.5°	69.0	73.5	81.8	95.2	117.6	156.9	230.3	358.2	542.4	737.0	884.7
105°	88.4	92.1	100.9	114.2	135.6	171.0	232.1	335.4	483.4	656.7	825.5
107.5°	108.0	111.7	121.1	133.8	155.0	187.4	243.1	331.2	450.4	591.8	741.3
110°	121.6	125.3	134.1	147.4	167.3	199.7	251.3	332.3	439.2	559.4	690.6





TEST NUMBER: P332969-830

CATALOG NUMBER: S124RDIP-S1020D810U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	134.6	138.8	147.1	160.3	180.3	211.5	260.1	335.9	433.9	541.1	653.5
115°	154.0	159.2	166.5	180.6	200.5	230.0	274.2	342.7	431.1	524.0	616.1
117.5°	173.3	178.0	186.1	199.2	219.8	247.8	288.4	350.0	430.4	516.3	597.9
120°	185.7	190.9	199.0	211.5	232.1	260.1	298.5	355.2	430.4	512.2	589.6
122.5°	197.6	202.6	210.2	223.9	243.9	271.9	307.9	360.5	429.8	507.5	582.5
125°	214.4	218.9	227.0	241.0	261.6	288.1	322.1	368.5	429.0	499.6	570.4
127.5°	227.6	232.9	242.1	256.7	277.6	303.2	334.3	374.8	427.3	489.2	555.7
130°	235.8	241.8	252.8	266.8	288.1	313.2	342.0	379.6	426.7	482.8	543.9
132.5°	242.9	250.6	261.1	276.3	296.4	321.5	349.6	383.7	426.1	476.8	531.5
135°	254.3	261.6	274.2	289.6	308.8	333.1	359.7	389.8	425.3	468.0	514.4
137.5°	264.9	273.0	284.9	301.0	319.2	342.0	366.7	393.5	425.1	460.3	499.0
140°	271.9	280.0	292.6	308.0	325.7	347.9	371.5	396.5	424.5	456.2	490.1
142.5°	280.2	287.8	299.6	314.5	331.7	353.2	374.9	398.9	424.5	452.7	481.8
145°	291.8	299.3	309.5	323.6	339.8	358.9	378.8	400.2	423.0	446.6	470.2
147.5°	303.5	310.0	320.6	332.2	346.9	364.9	382.2	401.0	420.4	441.2	460.6
150°	311.8	317.6	326.5	337.5	351.6	367.8	384.0	401.0	418.6	437.1	454.7
152.5°	318.9	324.7	333.0	342.9	355.7	370.1	385.1	399.7	415.7	432.3	448.3
155°	330.2	334.6	342.0	350.1	361.1	373.6	386.2	397.9	411.2	425.3	438.5
157.5°	339.9	344.0	349.8	356.8	365.5	376.2	386.2	396.1	406.7	418.0	428.0
160°	346.4	349.3	354.5	360.4	368.5	377.3	386.2	394.3	403.1	412.7	421.6
162.5°	351.7	354.0	358.6	363.9	370.2	378.5	386.2	392.6	399.6	408.0	415.1
165°	358.9	360.4	364.1	367.8	372.2	378.8	384.7	389.2	394.3	400.2	406.0
167.5°	364.9	365.5	368.3	370.4	373.8	378.7	383.0	385.6	389.0	393.1	397.4
170°	367.8	368.5	370.7	372.2	374.4	378.1	381.7	383.2	385.4	388.4	392.1
172.5°	370.7	370.9	372.5	373.3	374.9	377.5	380.6	380.9	381.9	384.3	387.4
175°	373.6	373.6	374.4	375.1	375.1	376.6	378.8	378.1	378.1	379.6	381.1
177.5°	375.1	374.6	375.1	375.1	375.1	375.7	376.9	375.7	375.7	376.3	376.9
180°	375.1	375.1	375.1	375.1	375.1	375.1	375.1	375.1	375.1	375.1	375.1



TEST NUMBER: P332969-830

CATALOG NUMBER: S124RDIP-S1020D810U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2
2.5°	1696.5	1698.6	1700.2	1705.3	1705.8	1710.5	1705.8
5°	1836.8	1846.0	1860.3	1874.6	1875.9	1885.0	1868.8
7.5°	1994.2	2015.3	2028.5	2051.7	2060.9	2066.5	2057.2
10°	2102.6	2122.2	2156.7	2173.7	2190.7	2193.2	2185.4
12.5°	2207.4	2238.4	2265.7	2297.7	2297.0	2319.9	2311.6
15°	2347.0	2379.0	2416.7	2452.6	2465.6	2465.6	2476.1
17.5°	2446.6	2505.1	2544.2	2572.3	2603.1	2608.4	2604.8
20°	2513.9	2577.0	2618.8	2655.2	2676.1	2681.9	2681.9
22.5°	2563.8	2617.6	2658.3	2691.1	2708.4	2715.3	2713.2
25°	2598.5	2644.8	2669.6	2679.3	2683.9	2682.6	2670.2
27.5°	2551.1	2549.0	2533.4	2503.4	2480.9	2467.2	2451.6
30°	2460.4	2426.5	2387.4	2344.4	2289.1	2246.6	2233.6
32.5°	2325.3	2249.3	2183.0	2111.4	2051.8	2009.5	1991.8
35°	2064.3	1943.7	1845.3	1759.3	1696.8	1657.6	1644.6
37.5°	1754.4	1637.7	1515.9	1432.5	1380.5	1341.0	1326.3
40°	1557.3	1430.2	1324.0	1245.9	1192.4	1154.0	1153.3
42.5°	1377.4	1256.1	1156.2	1099.9	1042.3	1016.8	1016.7
45°	1127.8	1030.8	946.1	901.8	867.2	846.4	840.6
47.5°	933.9	853.6	797.1	761.9	733.7	720.4	711.8
50°	824.9	754.5	709.5	678.9	663.3	646.4	645.1
52.5°	734.2	677.4	642.3	617.5	597.7	587.5	587.8
55°	617.1	572.1	547.3	528.4	512.8	505.0	501.7
57.5°	519.8	486.1	468.1	450.7	444.1	438.0	436.3
60°	459.4	436.6	419.6	406.0	396.2	394.2	393.5
62.5°	409.3	385.5	373.7	363.2	356.0	353.0	351.9
65°	337.5	319.9	309.5	301.0	298.4	293.9	293.2
67.5°	272.1	261.6	254.7	248.7	245.2	245.0	245.0
70°	232.0	226.1	220.3	217.0	215.0	213.7	213.7
72.5°	197.6	193.2	188.4	186.7	186.3	185.0	184.5
75°	150.5	146.0	146.6	143.4	140.7	137.5	135.5
77.5°	106.7	103.5	102.8	102.5	100.2	99.8	100.9
80°	82.8	79.5	78.8	79.5	78.8	76.9	76.9
82.5°	63.0	60.2	59.6	59.2	58.5	59.2	58.2
85°	33.8	32.6	32.6	32.6	33.8	33.3	32.6
87.5°	14.8	14.4	14.9	14.6	14.7	14.0	14.6
90°	14.0	14.7	14.7	15.5	16.2	15.5	15.5
92.5°	109.0	86.7	71.9	63.2	59.3	56.7	56.7
95°	431.9	333.1	261.6	225.6	202.6	189.5	179.8
97.5°	764.4	692.3	615.4	562.5	518.1	496.0	480.7
100°	903.5	867.4	812.9	748.8	703.8	681.7	675.8
102.5°	957.8	968.3	945.6	906.3	873.6	850.4	845.6
105°	952.9	1025.9	1056.1	1057.6	1051.7	1041.4	1037.0
107.5°	877.0	979.8	1045.5	1081.9	1098.7	1106.1	1108.0
110°	818.0	924.9	1006.0	1058.3	1089.3	1102.6	1109.2



TEST NUMBER: P332969-830

CATALOG NUMBER: S124RDIP-S1020D810U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	766.2	867.1	948.2	1007.6	1045.1	1063.7	1074.4
115°	706.8	793.0	863.7	922.0	966.2	989.8	995.7
117.5°	672.9	740.6	800.7	850.4	887.5	911.3	916.0
120°	658.2	717.1	769.4	811.4	843.9	863.0	871.1
122.5°	648.7	702.4	748.2	783.7	811.4	827.6	835.8
125°	633.9	684.7	725.2	754.7	776.1	790.0	794.5
127.5°	616.2	666.9	705.5	735.1	754.1	765.9	770.3
130°	602.1	652.2	691.3	721.5	740.0	751.8	756.2
132.5°	586.2	635.2	674.2	703.8	724.6	735.8	740.3
135°	562.3	607.3	644.1	673.6	694.3	706.1	710.5
137.5°	539.5	577.4	610.7	638.2	658.6	668.3	673.6
140°	524.7	557.9	588.9	614.6	630.8	641.2	647.1
142.5°	512.4	540.8	567.6	590.5	605.5	614.6	618.8
145°	495.3	517.4	538.0	556.5	568.9	576.4	580.0
147.5°	480.5	498.2	514.4	528.0	538.8	544.3	545.6
150°	471.6	486.4	499.6	511.5	521.0	525.5	526.2
152.5°	462.8	476.4	487.3	497.3	505.1	507.7	508.5
155°	450.3	461.4	470.2	477.6	483.4	485.7	485.7
157.5°	437.9	447.2	454.3	459.9	464.3	465.6	465.6
160°	429.7	437.8	443.7	448.1	452.5	453.3	453.3
162.5°	422.0	428.4	433.7	436.9	441.3	442.1	441.5
165°	410.5	415.7	419.3	422.3	425.3	424.5	423.8
167.5°	400.8	404.9	407.1	408.6	410.5	410.4	409.7
170°	394.3	397.3	399.4	401.0	401.6	401.0	401.0
172.5°	389.0	390.8	392.4	393.2	394.0	393.2	392.1
175°	381.7	383.2	383.2	383.2	384.7	383.2	381.7
177.5°	377.5	377.5	378.1	377.5	378.1	376.9	375.7
180°	375.1	375.1	375.1	375.1	375.1	375.1	375.1

(END OF REPORT)