

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332891-830

Luminaire Tested: **S124RDIP-S350D1205U830-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332891-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIP-S350D1205U830-4F0-1E-UDD-A4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 350 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5457.0 lumens  
Efficiency: N/A  
Efficacy: 129.3 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 42.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332891-830

CATALOG NUMBER: S124RDIP-S350D1205U830-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P332891-830

CATALOG NUMBER: S124RDIP-S350D1205U830-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34	26
1	93	88	85	82	82	79	76	73	61	59	58	45	44	43	30	30	29	22
2	84	77	72	67	75	69	65	60	54	51	48	40	38	36	27	26	25	19
3	77	68	61	56	69	61	55	51	48	44	41	35	33	31	24	22	21	16
4	71	60	53	47	63	54	48	43	42	38	35	32	29	26	22	20	18	14
5	65	54	46	40	57	48	42	37	38	33	30	28	25	23	19	18	16	12
6	60	48	40	35	53	43	37	32	34	29	26	26	22	20	18	16	14	11
7	55	43	36	30	49	39	33	28	31	26	23	23	20	18	16	14	13	10
8	51	39	32	27	45	35	29	25	28	23	20	21	18	16	15	13	11	9
9	47	36	29	24	42	32	26	22	26	21	18	19	16	14	14	12	10	8
10	44	33	26	21	39	29	23	19	24	19	16	18	15	13	13	11	9	7

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	4469	4469	4469	4469
5°	5185	4483	3963	4483
10°	6133	4464	3536	4464
15°	7084	4422	3039	4422
20°	7887	4365	2748	4365
25°	8143	4309	2551	4309
30°	7128	4242	2433	4242
35°	5549	4142	2361	4142
40°	4161	4027	2323	4027
45°	3286	3843	2302	3843
50°	2773	3631	2236	3631
55°	2417	3398	2115	3398
60°	2175	3155	1873	3155
65°	1918	2894	1612	2894
70°	1725	2622	1452	2622
75°	1447	2324	1238	2324
80°	1223	1980	1162	1980
85°	1028	1556	1028	1556



TEST NUMBER: P332891-830

CATALOG NUMBER: S124RDIP-S350D1205U830-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	53.6	1.0
10°-20°	161.8	3.0
20°-30°	253.1	4.6
30°-40°	281.4	5.2
40°-50°	249.6	4.6
50°-60°	194.5	3.6
60°-70°	127.4	2.3
70°-80°	62.6	1.1
80°-90°	18.5	0.3
90°-100°	402.7	7.4
100°-110°	838.0	15.4
110°-120°	750.6	13.8
120°-130°	631.4	11.6
130°-140°	526.5	9.6
140°-150°	402.2	7.4
150°-160°	282.7	5.2
160°-170°	166.3	3.0
170°-180°	54.1	1.0
0°-30°	468.6	8.6
0°-40°	749.9	13.7
0°-60°	1194.1	21.9
0°-90°	1402.6	25.7
90°-120°	1991.3	36.5
90°-150°	3551.4	65.1
90°-180°	4054.0	74.3
0°-180°	5457.0	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	554	554	554	554	554	
5°	640	553	489	553	640	65
15°	848	529	364	529	848	241
25°	914	484	286	484	914	406
35°	563	420	240	420	563	353
45°	288	337	202	337	288	228
55°	172	241	150	241	172	156
65°	100	152	84	152	100	101
75°	46	74	40	74	46	51
85°	11	17	11	17	11	13
90°	23	1	23	1	23	19
95°	267	36	267	36	267	415
105°	1541	128	1541	128	1541	1524
115°	1480	226	1480	226	1480	1469
125°	1181	314	1181	314	1181	1073
135°	1056	373	1056	373	1056	815
145°	862	430	862	430	862	546
155°	722	490	722	490	722	337
165°	630	533	630	533	630	180
175°	567	556	567	556	567	55
180°	558	558	558	558	558	



TEST NUMBER: P332891-830

CATALOG NUMBER: S124RDIP-S350D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6
2.5°	584.0	585.6	584.0	583.8	582.0	581.5	580.8	578.4	574.2	571.7	572.2
5°	639.8	645.4	642.2	641.8	636.9	632.0	628.9	621.7	614.1	609.0	604.7
7.5°	704.3	707.5	705.5	702.4	694.5	689.9	682.7	673.4	659.7	649.3	639.8
10°	748.2	750.8	750.0	744.1	738.4	726.5	719.8	706.7	689.5	675.9	663.2
12.5°	791.4	794.2	786.4	786.6	775.6	766.3	755.7	739.1	719.3	701.8	685.9
15°	847.6	844.0	844.0	839.6	827.4	814.5	803.5	786.1	761.1	740.2	718.0
17.5°	891.7	893.0	891.2	880.6	871.0	857.6	837.5	817.3	794.1	765.9	743.4
20°	918.1	918.1	916.2	909.0	896.5	882.2	860.6	838.5	809.1	780.7	755.4
22.5°	928.9	929.5	927.2	921.3	910.1	896.2	877.7	855.3	824.9	793.1	761.6
25°	914.2	918.4	918.8	917.3	913.9	905.4	889.6	866.7	839.4	804.8	770.9
27.5°	839.2	844.6	849.3	857.1	867.3	872.6	873.4	861.7	837.9	804.6	770.5
30°	764.7	769.1	783.6	802.6	817.3	830.7	842.4	845.5	832.1	802.2	766.3
32.5°	681.8	688.0	702.5	722.8	747.3	770.1	796.1	809.4	809.0	791.1	757.9
35°	563.0	567.5	580.9	602.3	631.7	665.4	706.7	738.8	760.6	759.1	738.8
37.5°	454.1	459.1	472.6	490.4	519.0	560.6	600.6	644.9	685.2	707.9	701.2
40°	394.8	395.0	408.2	426.5	453.3	489.7	533.1	582.2	627.3	664.1	671.2
42.5°	348.1	348.1	356.8	376.5	395.8	430.0	471.6	520.3	573.1	615.6	634.4
45°	287.8	289.7	296.9	308.7	323.9	352.9	386.2	431.4	490.5	540.9	572.4
47.5°	243.6	246.7	251.2	260.8	272.9	292.2	319.7	360.4	408.5	463.9	508.7
50°	220.8	221.3	227.1	232.4	242.9	258.4	282.4	316.3	360.5	413.8	463.5
52.5°	201.2	201.1	204.6	211.4	219.9	231.9	251.4	282.2	321.4	369.2	420.6
55°	171.7	172.9	175.6	180.9	187.4	195.9	211.2	234.4	265.2	306.0	352.7
57.5°	149.4	150.0	152.0	154.3	160.2	166.5	178.0	194.1	220.0	253.4	296.9
60°	134.7	135.0	135.6	138.9	143.6	149.5	157.3	170.9	192.7	223.3	257.7
62.5°	120.5	120.8	121.9	124.3	128.0	132.0	140.2	151.1	169.2	195.3	226.2
65°	100.4	100.6	102.2	103.0	105.9	109.5	115.6	122.9	135.4	157.3	180.7
67.5°	83.9	83.9	84.0	85.2	87.2	89.5	93.1	99.1	108.5	121.9	142.5
70°	73.1	73.1	73.6	74.3	75.4	77.4	79.5	83.9	90.8	101.7	117.5
72.5°	63.2	63.3	63.8	63.9	64.5	66.2	67.7	70.5	75.6	83.9	96.7
75°	46.4	47.0	48.2	49.1	50.2	50.0	51.6	53.3	54.9	59.8	67.1
77.5°	34.5	34.2	34.3	35.1	35.2	35.4	36.6	37.9	39.1	41.4	44.0
80°	26.3	26.3	27.0	27.2	27.0	27.2	28.4	29.0	29.4	30.3	32.8
82.5°	19.9	20.3	20.1	20.3	20.4	20.6	21.6	21.7	22.1	22.5	23.5
85°	11.1	11.4	11.6	11.1	11.1	11.1	11.6	11.8	12.3	12.1	12.5
87.5°	8.5	8.4	8.8	8.5	8.5	8.3	8.3	8.4	7.8	8.2	7.8
90°	23.0	23.0	24.1	23.0	21.9	21.9	20.8	19.7	18.7	19.7	17.5
92.5°	84.4	84.4	88.0	94.0	106.9	128.8	161.8	215.1	289.4	347.4	304.1
95°	267.2	281.4	301.2	335.2	388.8	495.0	641.8	811.5	917.8	892.6	673.5
97.5°	714.4	737.1	770.0	835.8	914.5	1028.9	1136.0	1199.1	1153.1	940.2	630.4
100°	1004.4	1013.1	1045.9	1112.8	1208.1	1289.1	1342.7	1320.9	1160.9	880.5	571.7
102.5°	1256.7	1263.7	1298.3	1346.7	1405.1	1438.9	1423.3	1314.8	1095.2	806.1	532.3
105°	1541.0	1547.6	1562.9	1571.7	1569.4	1524.6	1416.2	1226.6	975.8	718.5	498.3
107.5°	1646.6	1643.7	1632.8	1607.8	1553.7	1456.0	1303.3	1101.5	879.5	669.4	492.2
110°	1648.3	1638.5	1618.7	1572.7	1495.0	1374.5	1215.7	1026.2	831.3	652.8	494.0



TEST NUMBER: P332891-830

CATALOG NUMBER: S124RDIP-S350D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1596.7	1580.6	1553.0	1497.4	1409.1	1288.6	1138.6	971.0	804.1	644.9	499.2
115°	1479.7	1470.9	1435.9	1370.2	1283.6	1178.5	1050.4	915.6	778.7	640.7	509.3
117.5°	1361.1	1354.3	1318.9	1263.7	1189.9	1100.7	999.9	888.4	767.3	639.6	520.0
120°	1294.6	1282.5	1254.1	1205.9	1143.4	1065.6	978.1	876.2	761.2	639.6	527.9
122.5°	1242.0	1229.9	1205.9	1164.7	1111.9	1043.8	964.0	865.6	754.2	638.8	535.8
125°	1180.6	1174.1	1153.3	1121.5	1077.7	1017.5	941.9	847.7	742.5	637.4	547.6
127.5°	1144.7	1138.2	1120.7	1092.4	1048.4	991.2	915.9	825.8	727.0	635.0	557.0
130°	1123.7	1117.1	1099.6	1072.2	1027.4	969.3	894.8	808.3	717.4	634.1	564.0
132.5°	1100.0	1093.4	1076.9	1045.9	1001.9	943.9	871.2	789.9	708.6	633.3	570.1
135°	1055.8	1049.2	1031.7	1001.1	957.2	902.5	835.7	764.5	695.5	632.0	579.4
137.5°	1001.1	993.2	978.7	948.5	907.5	858.0	801.7	741.5	684.1	631.7	584.8
140°	961.6	952.8	937.5	913.4	875.1	829.1	779.8	728.3	678.0	630.8	589.3
142.5°	919.5	913.4	899.8	877.5	843.6	803.7	761.4	716.0	672.7	630.8	592.8
145°	862.0	856.5	845.6	826.9	799.6	768.8	736.0	698.8	663.7	628.7	594.7
147.5°	810.9	809.0	800.6	784.7	764.5	740.4	714.1	684.6	655.6	624.7	595.8
150°	782.0	780.9	774.3	760.1	742.5	722.8	701.0	675.8	649.5	622.1	595.8
152.5°	755.7	754.6	750.6	739.0	724.2	707.9	687.8	666.1	642.4	617.7	594.1
155°	721.8	721.8	718.5	709.7	698.8	685.6	669.2	651.7	632.0	611.1	591.4
157.5°	692.0	692.0	690.0	683.4	675.1	664.6	650.8	636.1	621.2	604.4	588.6
160°	673.5	673.5	672.5	665.9	659.3	650.5	638.5	626.5	613.3	599.1	586.0
162.5°	656.0	657.0	655.8	649.2	644.4	636.6	627.2	616.8	606.3	593.8	583.3
165°	629.8	630.8	632.0	627.5	623.2	617.7	610.0	603.5	594.7	586.0	578.2
167.5°	609.0	609.8	610.0	607.2	605.0	601.7	595.6	590.6	584.2	578.1	573.1
170°	595.8	595.8	596.9	595.8	593.6	590.3	586.0	582.7	577.2	572.8	569.5
172.5°	582.7	584.4	585.5	584.4	583.1	580.7	578.1	575.6	571.1	567.5	566.0
175°	567.3	569.5	571.7	569.5	569.5	569.5	567.3	566.3	564.0	561.8	561.8
177.5°	558.4	560.1	561.8	561.0	561.8	561.0	561.0	560.1	559.2	558.4	558.4
180°	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5



TEST NUMBER: P332891-830

CATALOG NUMBER: S124RDIP-S350D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6
2.5°	570.4	568.0	566.7	563.8	560.4	558.6	557.0	554.7	551.7	548.5	546.2
5°	599.4	594.0	587.3	579.3	572.2	565.2	559.2	553.2	546.3	539.1	532.1
7.5°	629.1	618.6	607.2	594.0	581.3	569.6	558.8	548.7	537.1	526.6	517.2
10°	649.8	635.6	619.7	602.9	586.3	571.7	557.4	544.5	530.3	517.6	506.8
12.5°	666.6	649.8	630.7	609.9	589.7	572.2	555.8	538.9	522.7	509.0	494.6
15°	694.4	671.5	645.8	620.8	594.7	570.8	548.7	529.1	510.6	491.2	477.6
17.5°	713.6	686.3	655.1	625.1	594.3	566.1	540.6	517.3	495.9	476.1	459.9
20°	725.0	694.8	660.3	626.1	591.5	561.5	534.0	508.1	486.1	464.7	447.9
22.5°	731.4	698.0	660.3	624.5	588.7	556.1	526.0	499.1	475.0	453.6	435.1
25°	733.5	697.8	659.2	618.1	578.9	544.3	513.0	483.8	457.0	435.6	416.0
27.5°	730.6	688.5	649.0	606.9	566.4	530.0	497.2	466.5	439.7	416.7	396.5
30°	726.3	681.3	638.9	595.1	554.1	519.1	484.5	455.1	427.2	403.3	383.0
32.5°	717.0	672.3	626.7	581.9	540.4	504.3	471.5	441.9	414.5	390.1	368.5
35°	698.6	653.4	603.9	557.9	517.1	479.6	448.8	420.3	394.2	368.1	345.3
37.5°	674.4	628.2	578.9	528.6	487.7	452.3	424.1	397.3	371.8	348.0	322.8
40°	651.6	609.4	558.6	508.6	466.7	432.5	406.4	382.1	356.5	332.8	307.6
42.5°	624.0	588.1	536.6	486.4	445.1	412.2	387.9	364.1	340.7	317.8	291.5
45°	577.8	550.5	502.4	454.2	412.5	379.8	357.6	336.6	316.1	294.3	269.5
47.5°	524.8	506.4	464.9	415.5	376.9	347.6	326.0	308.9	291.5	269.7	248.0
50°	488.0	476.3	436.1	391.1	354.2	327.3	305.2	289.1	274.6	253.6	234.2
52.5°	448.8	442.5	408.6	365.5	330.0	303.5	284.6	270.2	255.5	238.1	220.0
55°	389.0	392.4	363.6	326.3	292.8	270.6	253.4	241.4	228.8	214.1	200.1
57.5°	327.9	340.2	320.8	288.1	256.7	236.1	223.2	213.1	202.6	190.4	178.3
60°	291.3	301.6	290.7	261.8	234.4	215.3	203.2	195.4	184.9	173.8	164.7
62.5°	255.6	266.6	260.1	236.9	211.4	194.9	184.3	177.0	169.2	159.5	150.0
65°	210.8	217.9	214.8	198.8	180.7	166.6	156.8	151.5	144.3	137.2	128.8
67.5°	161.5	175.2	173.4	164.9	149.3	138.3	131.9	127.1	120.6	115.4	109.6
70°	132.7	145.4	145.2	138.3	129.8	119.6	115.1	111.1	105.3	100.2	95.5
72.5°	108.7	120.3	122.1	116.7	110.9	103.1	98.9	96.1	90.5	87.0	83.1
75°	76.1	84.5	86.8	86.8	84.1	80.1	76.3	74.5	70.5	67.4	65.1
77.5°	49.9	55.2	58.7	59.5	59.9	58.5	55.4	54.2	51.1	50.0	47.9
80°	35.3	38.8	42.8	44.2	45.2	44.9	43.5	42.6	39.7	38.5	37.7
82.5°	24.3	26.3	29.6	32.6	32.2	33.5	32.2	31.6	29.3	28.9	28.1
85°	12.7	12.9	13.4	15.4	16.5	17.0	17.2	16.8	16.0	16.0	14.5
87.5°	7.4	7.2	6.2	6.2	6.1	6.7	6.5	6.3	6.2	6.3	6.0
90°	15.4	15.4	8.8	8.8	7.6	6.6	3.3	1.1	3.3	6.6	7.6
92.5°	221.2	136.3	80.6	57.9	41.8	28.5	18.2	12.4	18.2	28.5	41.8
95°	411.8	232.1	137.0	90.9	64.7	50.4	39.4	36.1	39.4	50.4	64.7
97.5°	370.2	221.9	148.5	110.0	87.4	74.3	64.8	64.8	64.8	74.3	87.4
100°	348.3	224.5	159.9	124.9	104.1	90.9	83.2	83.2	83.2	90.9	104.1
102.5°	342.1	233.3	174.8	141.5	121.6	109.3	102.5	100.8	102.5	109.3	121.6
105°	345.0	254.1	201.5	169.8	150.1	137.0	131.4	128.2	131.4	137.0	150.1
107.5°	361.2	278.4	230.3	198.9	180.0	166.1	160.5	158.3	160.5	166.1	180.0
110°	373.4	296.8	248.6	219.0	199.3	186.2	180.7	178.5	180.7	186.2	199.3





TEST NUMBER: P332891-830

CATALOG NUMBER: S124RDIP-S350D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	386.6	314.3	267.9	238.4	218.6	206.3	200.0	197.8	200.0	206.3	218.6
115°	407.5	341.7	297.9	268.3	247.5	236.6	228.9	225.6	228.9	236.6	247.5
117.5°	428.7	368.3	326.6	296.0	276.4	264.4	257.6	254.5	257.6	264.4	276.4
120°	443.6	386.6	345.0	314.3	295.7	283.7	276.0	273.8	276.0	283.7	295.7
122.5°	457.6	404.2	362.5	332.7	312.4	301.2	293.5	291.3	293.5	301.2	312.4
125°	478.6	428.2	388.8	358.2	337.3	325.3	318.7	314.3	318.7	325.3	337.3
127.5°	496.8	450.5	412.5	381.5	359.9	346.1	338.2	334.7	338.2	346.1	359.9
130°	508.2	465.5	428.2	396.4	375.7	359.2	350.4	346.1	350.4	359.2	375.7
132.5°	519.6	477.8	440.5	410.5	388.0	372.4	361.0	357.5	361.0	372.4	388.0
135°	534.5	495.0	458.9	430.5	407.5	388.8	377.9	373.4	377.9	388.8	407.5
137.5°	545.0	508.2	474.5	447.3	423.4	405.7	393.6	389.5	393.6	405.7	423.4
140°	552.0	517.0	484.1	457.8	434.8	416.2	404.2	400.9	404.2	416.2	434.8
142.5°	557.2	524.8	492.9	467.4	445.4	427.5	416.4	413.1	416.4	427.5	445.4
145°	563.0	533.4	504.9	480.8	460.0	444.7	433.8	430.5	433.8	444.7	460.0
147.5°	568.0	542.2	515.4	493.7	476.5	460.6	451.0	449.9	451.0	460.6	476.5
150°	570.6	546.5	522.5	501.6	485.2	472.0	463.3	462.2	463.3	472.0	485.2
152.5°	572.4	550.1	528.6	509.5	494.8	482.6	473.8	473.5	473.8	482.6	494.8
155°	573.9	555.3	536.7	520.3	508.2	497.2	490.7	489.6	490.7	497.2	508.2
157.5°	573.9	559.0	543.3	530.3	519.8	511.2	505.1	505.1	505.1	511.2	519.8
160°	573.9	560.7	547.6	535.6	526.8	519.2	514.7	514.7	514.7	519.2	526.8
162.5°	573.9	562.5	550.3	540.8	532.9	526.1	522.6	523.5	522.6	526.1	532.9
165°	571.7	563.0	553.1	546.5	541.0	535.6	533.4	533.4	533.4	535.6	541.0
167.5°	569.1	562.7	555.5	550.4	547.4	543.3	542.2	543.3	542.2	543.3	547.4
170°	567.3	561.8	556.4	553.1	550.9	547.6	546.5	547.6	546.5	547.6	550.9
172.5°	565.6	561.0	557.2	554.9	553.6	551.1	550.9	552.0	550.9	551.1	553.6
175°	563.0	559.7	557.5	557.5	556.4	555.3	555.3	556.4	555.3	555.3	556.4
177.5°	560.1	558.4	557.5	557.5	557.5	556.6	557.5	558.4	557.5	556.6	557.5
180°	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5



TEST NUMBER: P332891-830

CATALOG NUMBER: S124RDIP-S350D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6
2.5°	543.7	541.9	539.6	536.9	533.7	530.8	529.5	530.7	531.2	529.7	529.5
5°	527.1	521.5	517.1	510.4	505.0	500.6	497.5	496.1	496.5	492.9	492.1
7.5°	508.5	501.9	494.6	486.6	479.3	472.7	469.3	467.4	463.5	461.9	459.2
10°	496.5	487.7	480.5	471.1	462.6	454.9	451.0	447.9	444.1	442.3	438.6
12.5°	484.3	473.9	466.0	456.3	447.6	438.3	434.6	428.9	422.9	419.1	414.2
15°	466.8	454.4	444.8	433.2	422.9	412.3	402.7	391.9	388.0	379.5	374.6
17.5°	446.6	433.9	422.1	406.5	390.7	377.3	367.1	356.8	350.7	345.3	342.8
20°	433.2	421.6	405.1	387.0	369.4	354.7	346.4	339.7	333.0	329.2	326.6
22.5°	420.6	405.7	386.5	367.0	349.4	337.9	330.9	324.0	318.6	315.0	311.4
25°	399.3	379.8	359.6	337.2	325.3	315.2	307.6	302.0	298.7	294.0	292.2
27.5°	377.5	353.9	331.6	316.6	304.1	294.8	288.2	284.1	279.8	276.8	274.5
30°	360.7	336.9	316.8	302.5	289.7	282.2	276.8	271.9	268.5	266.1	264.4
32.5°	344.1	320.3	303.4	288.0	278.0	270.6	264.9	261.2	258.5	255.4	254.3
35°	320.1	298.9	284.2	270.3	260.1	253.4	248.9	245.2	242.9	242.0	241.4
37.5°	297.0	279.7	263.8	252.5	243.4	238.1	232.8	230.9	229.4	227.8	228.6
40°	282.4	266.1	252.0	240.1	232.6	226.9	223.8	221.5	220.2	220.2	220.2
42.5°	269.8	253.8	240.1	229.3	222.0	217.1	213.6	211.7	211.2	211.0	212.2
45°	250.1	235.4	221.5	212.5	206.3	201.4	199.4	197.8	197.8	198.8	199.0
47.5°	230.5	216.8	205.7	195.7	189.9	186.9	185.1	184.4	184.5	185.3	186.3
50°	218.6	205.0	194.1	185.1	179.8	176.9	175.3	174.8	175.3	175.3	176.9
52.5°	205.6	193.4	182.7	175.1	169.1	166.4	165.5	164.9	165.1	165.9	166.5
55°	186.5	175.6	165.3	158.2	153.7	151.9	149.9	150.1	149.7	150.1	150.1
57.5°	167.3	157.5	148.0	142.3	138.4	135.8	133.7	134.2	133.6	133.5	133.1
60°	155.0	144.3	136.8	131.6	127.1	124.9	122.9	123.4	122.7	122.2	121.3
62.5°	141.7	132.7	125.5	120.6	117.0	114.4	112.4	112.0	110.4	108.9	106.9
65°	122.2	114.9	108.4	103.8	100.4	98.4	96.8	95.5	92.1	88.6	86.8
67.5°	103.4	98.0	92.0	88.0	85.3	82.8	79.7	77.5	74.4	72.4	71.3
70°	91.2	86.1	81.0	77.2	74.3	71.8	68.5	66.9	64.7	63.8	62.7
72.5°	79.6	74.8	70.1	66.6	63.6	61.6	59.0	57.5	56.5	56.1	55.0
75°	62.0	58.2	54.7	51.6	49.1	47.7	46.7	45.5	45.1	43.1	41.9
77.5°	45.2	42.7	40.5	38.3	36.6	35.6	33.5	32.2	31.5	30.5	30.3
80°	35.3	33.5	31.2	29.9	27.4	26.6	25.6	25.4	25.2	25.0	24.8
82.5°	26.5	24.7	22.5	21.7	21.0	20.5	20.0	19.7	19.5	19.6	19.6
85°	13.4	12.5	12.5	12.3	12.1	11.8	11.6	11.6	11.4	11.6	11.4
87.5°	6.2	6.0	7.4	7.0	7.6	8.0	7.6	7.8	8.3	8.1	8.1
90°	8.8	8.8	15.4	15.4	17.5	19.7	18.7	19.7	20.8	21.9	21.9
92.5°	57.9	80.6	136.3	221.2	304.1	347.4	289.4	215.1	161.8	128.8	106.9
95°	90.9	137.0	232.1	411.8	673.5	892.6	917.8	811.5	641.8	495.0	388.8
97.5°	110.0	148.5	221.9	370.2	630.4	940.2	1153.1	1199.1	1136.0	1028.9	914.5
100°	124.9	159.9	224.5	348.3	571.7	880.5	1160.9	1320.9	1342.7	1289.1	1208.1
102.5°	141.5	174.8	233.3	342.1	532.3	806.1	1095.2	1314.8	1423.3	1438.9	1405.1
105°	169.8	201.5	254.1	345.0	498.3	718.5	975.8	1226.6	1416.2	1524.6	1569.4
107.5°	198.9	230.3	278.4	361.2	492.2	669.4	879.5	1101.5	1303.3	1456.0	1553.7
110°	219.0	248.6	296.8	373.4	494.0	652.8	831.3	1026.2	1215.7	1374.5	1495.0



TEST NUMBER: P332891-830

CATALOG NUMBER: S124RDIP-S350D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	238.4	267.9	314.3	386.6	499.2	644.9	804.1	971.0	1138.6	1288.6	1409.1
115°	268.3	297.9	341.7	407.5	509.3	640.7	778.7	915.6	1050.4	1178.5	1283.6
117.5°	296.0	326.6	368.3	428.7	520.0	639.6	767.3	888.4	999.9	1100.7	1189.9
120°	314.3	345.0	386.6	443.6	527.9	639.6	761.2	876.2	978.1	1065.6	1143.4
122.5°	332.7	362.5	404.2	457.6	535.8	638.8	754.2	865.6	964.0	1043.8	1111.9
125°	358.2	388.8	428.2	478.6	547.6	637.4	742.5	847.7	941.9	1017.5	1077.7
127.5°	381.5	412.5	450.5	496.8	557.0	635.0	727.0	825.8	915.9	991.2	1048.4
130°	396.4	428.2	465.5	508.2	564.0	634.1	717.4	808.3	894.8	969.3	1027.4
132.5°	410.5	440.5	477.8	519.6	570.1	633.3	708.6	789.9	871.2	943.9	1001.9
135°	430.5	458.9	495.0	534.5	579.4	632.0	695.5	764.5	835.7	902.5	957.2
137.5°	447.3	474.5	508.2	545.0	584.8	631.7	684.1	741.5	801.7	858.0	907.5
140°	457.8	484.1	517.0	552.0	589.3	630.8	678.0	728.3	779.8	829.1	875.1
142.5°	467.4	492.9	524.8	557.2	592.8	630.8	672.7	716.0	761.4	803.7	843.6
145°	480.8	504.9	533.4	563.0	594.7	628.7	663.7	698.8	736.0	768.8	799.6
147.5°	493.7	515.4	542.2	568.0	595.8	624.7	655.6	684.6	714.1	740.4	764.5
150°	501.6	522.5	546.5	570.6	595.8	622.1	649.5	675.8	701.0	722.8	742.5
152.5°	509.5	528.6	550.1	572.4	594.1	617.7	642.4	666.1	687.8	707.9	724.2
155°	520.3	536.7	555.3	573.9	591.4	611.1	632.0	651.7	669.2	685.6	698.8
157.5°	530.3	543.3	559.0	573.9	588.6	604.4	621.2	636.1	650.8	664.6	675.1
160°	535.6	547.6	560.7	573.9	586.0	599.1	613.3	626.5	638.5	650.5	659.3
162.5°	540.8	550.3	562.5	573.9	583.3	593.8	606.3	616.8	627.2	636.6	644.4
165°	546.5	553.1	563.0	571.7	578.2	586.0	594.7	603.5	610.0	617.7	623.2
167.5°	550.4	555.5	562.7	569.1	573.1	578.1	584.2	590.6	595.6	601.7	605.0
170°	553.1	556.4	561.8	567.3	569.5	572.8	577.2	582.7	586.0	590.3	593.6
172.5°	554.9	557.2	561.0	565.6	566.0	567.5	571.1	575.6	578.1	580.7	583.1
175°	557.5	557.5	559.7	563.0	561.8	561.8	564.0	566.3	567.3	569.5	569.5
177.5°	557.5	557.5	558.4	560.1	558.4	558.4	559.2	560.1	561.0	561.0	561.8
180°	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5



TEST NUMBER: P332891-830

CATALOG NUMBER: S124RDIP-S350D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6
2.5°	528.5	528.9	527.6	527.3	527.6	528.9	528.5	529.5	529.7	531.2	530.7
5°	490.3	489.8	488.7	489.0	488.7	489.8	490.3	492.1	492.9	496.5	496.1
7.5°	457.6	455.9	456.4	454.6	456.4	455.9	457.6	459.2	461.9	463.5	467.4
10°	437.6	435.2	433.2	431.4	433.2	435.2	437.6	438.6	442.3	444.1	447.9
12.5°	410.4	408.2	405.6	406.0	405.6	408.2	410.4	414.2	419.1	422.9	428.9
15°	371.6	368.3	363.0	363.6	363.0	368.3	371.6	374.6	379.5	388.0	391.9
17.5°	338.8	338.8	336.4	337.1	336.4	338.8	338.8	342.8	345.3	350.7	356.8
20°	321.9	320.4	320.6	319.9	320.6	320.4	321.9	326.6	329.2	333.0	339.7
22.5°	310.1	308.2	306.6	305.3	306.6	308.2	310.1	311.4	315.0	318.6	324.0
25°	290.2	288.9	286.9	286.4	286.9	288.9	290.2	292.2	294.0	298.7	302.0
27.5°	272.7	272.5	271.6	270.6	271.6	272.5	272.7	274.5	276.8	279.8	284.1
30°	262.6	262.1	261.6	261.0	261.6	262.1	262.6	264.4	266.1	268.5	271.9
32.5°	253.4	253.2	252.7	252.8	252.7	253.2	253.4	254.3	255.4	258.5	261.2
35°	240.4	240.3	239.8	239.6	239.8	240.3	240.4	241.4	242.0	242.9	245.2
37.5°	228.4	228.9	228.7	228.6	228.7	228.9	228.4	228.6	227.8	229.4	230.9
40°	220.0	220.2	220.6	220.4	220.6	220.2	220.0	220.2	220.2	220.2	221.5
42.5°	213.0	213.0	213.7	212.9	213.7	213.0	213.0	212.2	211.0	211.2	211.7
45°	200.6	201.9	201.6	201.6	201.6	201.9	200.6	199.0	198.8	197.8	197.8
47.5°	186.9	188.1	188.4	188.3	188.4	188.1	186.9	186.3	185.3	184.5	184.4
50°	178.0	177.6	178.2	178.0	178.2	177.6	178.0	176.9	175.3	175.3	174.8
52.5°	167.1	167.2	167.2	166.9	167.2	167.2	167.1	166.5	165.9	165.1	164.9
55°	150.3	150.6	150.1	150.3	150.1	150.6	150.3	150.1	150.1	149.7	150.1
57.5°	132.1	131.1	131.5	131.0	131.5	131.1	132.1	133.1	133.5	133.6	134.2
60°	119.1	117.3	116.9	116.0	116.9	117.3	119.1	121.3	122.2	122.7	123.4
62.5°	104.5	103.2	101.7	102.5	101.7	103.2	104.5	106.9	108.9	110.4	112.0
65°	85.0	84.1	83.4	84.4	83.4	84.1	85.0	86.8	88.6	92.1	95.5
67.5°	70.3	69.8	69.8	69.5	69.8	69.8	70.3	71.3	72.4	74.4	77.5
70°	62.7	62.0	62.0	61.5	62.0	62.0	62.7	62.7	63.8	64.7	66.9
72.5°	54.9	54.2	54.4	54.1	54.4	54.2	54.9	55.0	56.1	56.5	57.5
75°	40.6	39.5	39.5	39.7	39.5	39.5	40.6	41.9	43.1	45.1	45.5
77.5°	30.3	30.1	30.3	30.0	30.3	30.1	30.3	30.3	30.5	31.5	32.2
80°	24.8	24.5	24.3	25.0	24.3	24.5	24.8	24.8	25.0	25.2	25.4
82.5°	19.2	19.2	19.1	20.0	19.1	19.2	19.2	19.6	19.6	19.5	19.7
85°	11.6	11.1	11.6	11.1	11.6	11.1	11.6	11.4	11.6	11.4	11.6
87.5°	8.7	8.8	8.4	8.5	8.4	8.8	8.7	8.1	8.1	8.3	7.8
90°	23.0	24.1	23.0	23.0	23.0	24.1	23.0	21.9	21.9	20.8	19.7
92.5°	94.0	88.0	84.4	84.4	84.4	88.0	94.0	106.9	128.8	161.8	215.1
95°	335.2	301.2	281.4	267.2	281.4	301.2	335.2	388.8	495.0	641.8	811.5
97.5°	835.8	770.0	737.1	714.4	737.1	770.0	835.8	914.5	1028.9	1136.0	1199.1
100°	1112.8	1045.9	1013.1	1004.4	1013.1	1045.9	1112.8	1208.1	1289.1	1342.7	1320.9
102.5°	1346.7	1298.3	1263.7	1256.7	1263.7	1298.3	1346.7	1405.1	1438.9	1423.3	1314.8
105°	1571.7	1562.9	1547.6	1541.0	1547.6	1562.9	1571.7	1569.4	1524.6	1416.2	1226.6
107.5°	1607.8	1632.8	1643.7	1646.6	1643.7	1632.8	1607.8	1553.7	1456.0	1303.3	1101.5
110°	1572.7	1618.7	1638.5	1648.3	1638.5	1618.7	1572.7	1495.0	1374.5	1215.7	1026.2



TEST NUMBER: P332891-830

CATALOG NUMBER: S124RDIP-S350D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1497.4	1553.0	1580.6	1596.7	1580.6	1553.0	1497.4	1409.1	1288.6	1138.6	971.0
115°	1370.2	1435.9	1470.9	1479.7	1470.9	1435.9	1370.2	1283.6	1178.5	1050.4	915.6
117.5°	1263.7	1318.9	1354.3	1361.1	1354.3	1318.9	1263.7	1189.9	1100.7	999.9	888.4
120°	1205.9	1254.1	1282.5	1294.6	1282.5	1254.1	1205.9	1143.4	1065.6	978.1	876.2
122.5°	1164.7	1205.9	1229.9	1242.0	1229.9	1205.9	1164.7	1111.9	1043.8	964.0	865.6
125°	1121.5	1153.3	1174.1	1180.6	1174.1	1153.3	1121.5	1077.7	1017.5	941.9	847.7
127.5°	1092.4	1120.7	1138.2	1144.7	1138.2	1120.7	1092.4	1048.4	991.2	915.9	825.8
130°	1072.2	1099.6	1117.1	1123.7	1117.1	1099.6	1072.2	1027.4	969.3	894.8	808.3
132.5°	1045.9	1076.9	1093.4	1100.0	1093.4	1076.9	1045.9	1001.9	943.9	871.2	789.9
135°	1001.1	1031.7	1049.2	1055.8	1049.2	1031.7	1001.1	957.2	902.5	835.7	764.5
137.5°	948.5	978.7	993.2	1001.1	993.2	978.7	948.5	907.5	858.0	801.7	741.5
140°	913.4	937.5	952.8	961.6	952.8	937.5	913.4	875.1	829.1	779.8	728.3
142.5°	877.5	899.8	913.4	919.5	913.4	899.8	877.5	843.6	803.7	761.4	716.0
145°	826.9	845.6	856.5	862.0	856.5	845.6	826.9	799.6	768.8	736.0	698.8
147.5°	784.7	800.6	809.0	810.9	809.0	800.6	784.7	764.5	740.4	714.1	684.6
150°	760.1	774.3	780.9	782.0	780.9	774.3	760.1	742.5	722.8	701.0	675.8
152.5°	739.0	750.6	754.6	755.7	754.6	739.0	724.2	707.9	687.8	666.1	646.1
155°	709.7	718.5	721.8	721.8	721.8	718.5	709.7	698.8	685.6	669.2	651.7
157.5°	683.4	690.0	692.0	692.0	692.0	690.0	683.4	675.1	664.6	650.8	636.1
160°	665.9	672.5	673.5	673.5	673.5	672.5	665.9	659.3	650.5	638.5	626.5
162.5°	649.2	655.8	657.0	656.0	657.0	655.8	649.2	644.4	636.6	627.2	616.8
165°	627.5	632.0	630.8	629.8	630.8	632.0	627.5	623.2	617.7	610.0	603.5
167.5°	607.2	610.0	609.8	609.0	609.8	610.0	607.2	605.0	601.7	595.6	590.6
170°	595.8	596.9	595.8	595.8	595.8	596.9	595.8	593.6	590.3	586.0	582.7
172.5°	584.4	585.5	584.4	582.7	584.4	585.5	584.4	583.1	580.7	578.1	575.6
175°	569.5	571.7	569.5	567.3	569.5	571.7	569.5	569.5	569.5	567.3	566.3
177.5°	561.0	561.8	560.1	558.4	560.1	561.8	561.0	561.8	561.0	561.0	560.1
180°	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5



TEST NUMBER: P332891-830

CATALOG NUMBER: S124RDIP-S350D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6
2.5°	529.5	530.8	533.7	536.9	539.6	541.9	543.7	546.2	548.5	551.7	554.7
5°	497.5	500.6	505.0	510.4	517.1	521.5	527.1	532.1	539.1	546.3	553.2
7.5°	469.3	472.7	479.3	486.6	494.6	501.9	508.5	517.2	526.6	537.1	548.7
10°	451.0	454.9	462.6	471.1	480.5	487.7	496.5	506.8	517.6	530.3	544.5
12.5°	434.6	438.3	447.6	456.3	466.0	473.9	484.3	494.6	509.0	522.7	538.9
15°	402.7	412.3	422.9	433.2	444.8	454.4	466.8	477.6	491.2	510.6	529.1
17.5°	367.1	377.3	390.7	406.5	422.1	433.9	446.6	459.9	476.1	495.9	517.3
20°	346.4	354.7	369.4	387.0	405.1	421.6	433.2	447.9	464.7	486.1	508.1
22.5°	330.9	337.9	349.4	367.0	386.5	405.7	420.6	435.1	453.6	475.0	499.1
25°	307.6	315.2	325.3	337.2	359.6	379.8	399.3	416.0	435.6	457.0	483.8
27.5°	288.2	294.8	304.1	316.6	331.6	353.9	377.5	396.5	416.7	439.7	466.5
30°	276.8	282.2	289.7	302.5	316.8	336.9	360.7	383.0	403.3	427.2	455.1
32.5°	264.9	270.6	278.0	288.0	303.4	320.3	344.1	368.5	390.1	414.5	441.9
35°	248.9	253.4	260.1	270.3	284.2	298.9	320.1	345.3	368.1	394.2	420.3
37.5°	232.8	238.1	243.4	252.5	263.8	279.7	297.0	322.8	348.0	371.8	397.3
40°	223.8	226.9	232.6	240.1	252.0	266.1	282.4	307.6	332.8	356.5	382.1
42.5°	213.6	217.1	222.0	229.3	240.1	253.8	269.8	291.5	317.8	340.7	364.1
45°	199.4	201.4	206.3	212.5	221.5	235.4	250.1	269.5	294.3	316.1	336.6
47.5°	185.1	186.9	189.9	195.7	205.7	216.8	230.5	248.0	269.7	291.5	308.9
50°	175.3	176.9	179.8	185.1	194.1	205.0	218.6	234.2	253.6	274.6	289.1
52.5°	165.5	166.4	169.1	175.1	182.7	193.4	205.6	220.0	238.1	255.5	270.2
55°	149.9	151.9	153.7	158.2	165.3	175.6	186.5	200.1	214.1	228.8	241.4
57.5°	133.7	135.8	138.4	142.3	148.0	157.5	167.3	178.3	190.4	202.6	213.1
60°	122.9	124.9	127.1	131.6	136.8	144.3	155.0	164.7	173.8	184.9	195.4
62.5°	112.4	114.4	117.0	120.6	125.5	132.7	141.7	150.0	159.5	169.2	177.0
65°	96.8	98.4	100.4	103.8	108.4	114.9	122.2	128.8	137.2	144.3	151.5
67.5°	79.7	82.8	85.3	88.0	92.0	98.0	103.4	109.6	115.4	120.6	127.1
70°	68.5	71.8	74.3	77.2	81.0	86.1	91.2	95.5	100.2	105.3	111.1
72.5°	59.0	61.6	63.6	66.6	70.1	74.8	79.6	83.1	87.0	90.5	96.1
75°	46.7	47.7	49.1	51.6	54.7	58.2	62.0	65.1	67.4	70.5	74.5
77.5°	33.5	35.6	36.6	38.3	40.5	42.7	45.2	47.9	50.0	51.1	54.2
80°	25.6	26.6	27.4	29.9	31.2	33.5	35.3	37.7	38.5	39.7	42.6
82.5°	20.0	20.5	21.0	21.7	22.5	24.7	26.5	28.1	28.9	29.3	31.6
85°	11.6	11.8	12.1	12.3	12.5	12.5	13.4	14.5	16.0	16.0	16.8
87.5°	7.6	8.0	7.6	7.0	7.4	6.0	6.2	6.0	6.3	6.2	6.3
90°	18.7	19.7	17.5	15.4	15.4	8.8	8.8	7.6	6.6	3.3	1.1
92.5°	289.4	347.4	304.1	221.2	136.3	80.6	57.9	41.8	28.5	18.2	12.4
95°	917.8	892.6	673.5	411.8	232.1	137.0	90.9	64.7	50.4	39.4	36.1
97.5°	1153.1	940.2	630.4	370.2	221.9	148.5	110.0	87.4	74.3	64.8	64.8
100°	1160.9	880.5	571.7	348.3	224.5	159.9	124.9	104.1	90.9	83.2	83.2
102.5°	1095.2	806.1	532.3	342.1	233.3	174.8	141.5	121.6	109.3	102.5	100.8
105°	975.8	718.5	498.3	345.0	254.1	201.5	169.8	150.1	137.0	131.4	128.2
107.5°	879.5	669.4	492.2	361.2	278.4	230.3	198.9	180.0	166.1	160.5	158.3
110°	831.3	652.8	494.0	373.4	296.8	248.6	219.0	199.3	186.2	180.7	178.5



TEST NUMBER: P332891-830

CATALOG NUMBER: S124RDIP-S350D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	804.1	644.9	499.2	386.6	314.3	267.9	238.4	218.6	206.3	200.0	197.8
115°	778.7	640.7	509.3	407.5	341.7	297.9	268.3	247.5	236.6	228.9	225.6
117.5°	767.3	639.6	520.0	428.7	368.3	326.6	296.0	276.4	264.4	257.6	254.5
120°	761.2	639.6	527.9	443.6	386.6	345.0	314.3	295.7	283.7	276.0	273.8
122.5°	754.2	638.8	535.8	457.6	404.2	362.5	332.7	312.4	301.2	293.5	291.3
125°	742.5	637.4	547.6	478.6	428.2	388.8	358.2	337.3	325.3	318.7	314.3
127.5°	727.0	635.0	557.0	496.8	450.5	412.5	381.5	359.9	346.1	338.2	334.7
130°	717.4	634.1	564.0	508.2	465.5	428.2	396.4	375.7	359.2	350.4	346.1
132.5°	708.6	633.3	570.1	519.6	477.8	440.5	410.5	388.0	372.4	361.0	357.5
135°	695.5	632.0	579.4	534.5	495.0	458.9	430.5	407.5	388.8	377.9	373.4
137.5°	684.1	631.7	584.8	545.0	508.2	474.5	447.3	423.4	405.7	393.6	389.5
140°	678.0	630.8	589.3	552.0	517.0	484.1	457.8	434.8	416.2	404.2	400.9
142.5°	672.7	630.8	592.8	557.2	524.8	492.9	467.4	445.4	427.5	416.4	413.1
145°	663.7	628.7	594.7	563.0	533.4	504.9	480.8	460.0	444.7	433.8	430.5
147.5°	655.6	624.7	595.8	568.0	542.2	515.4	493.7	476.5	460.6	451.0	449.9
150°	649.5	622.1	595.8	570.6	546.5	522.5	501.6	485.2	472.0	463.3	462.2
152.5°	642.4	617.7	594.1	572.4	550.1	528.6	509.5	494.8	482.6	473.8	473.5
155°	632.0	611.1	591.4	573.9	555.3	536.7	520.3	508.2	497.2	490.7	489.6
157.5°	621.2	604.4	588.6	573.9	559.0	543.3	530.3	519.8	511.2	505.1	505.1
160°	613.3	599.1	586.0	573.9	560.7	547.6	535.6	526.8	519.2	514.7	514.7
162.5°	606.3	593.8	583.3	573.9	562.5	550.3	540.8	532.9	526.1	522.6	523.5
165°	594.7	586.0	578.2	571.7	563.0	553.1	546.5	541.0	535.6	533.4	533.4
167.5°	584.2	578.1	573.1	569.1	562.7	555.5	550.4	547.4	543.3	542.2	543.3
170°	577.2	572.8	569.5	567.3	561.8	556.4	553.1	550.9	547.6	546.5	547.6
172.5°	571.1	567.5	566.0	565.6	561.0	557.2	554.9	553.6	551.1	550.9	552.0
175°	564.0	561.8	561.8	563.0	559.7	557.5	557.5	556.4	555.3	555.3	556.4
177.5°	559.2	558.4	558.4	560.1	558.4	557.5	557.5	557.5	556.6	557.5	558.4
180°	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5



TEST NUMBER: P332891-830

CATALOG NUMBER: S124RDIP-S350D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6
2.5°	557.0	558.6	560.4	563.8	566.7	568.0	570.4	572.2	571.7	574.2	578.4
5°	559.2	565.2	572.2	579.3	587.3	594.0	599.4	604.7	609.0	614.1	621.7
7.5°	558.8	569.6	581.3	594.0	607.2	618.6	629.1	639.8	649.3	659.7	673.4
10°	557.4	571.7	586.3	602.9	619.7	635.6	649.8	663.2	675.9	689.5	706.7
12.5°	555.8	572.2	589.7	609.9	630.7	649.8	666.6	685.9	701.8	719.3	739.1
15°	548.7	570.8	594.7	620.8	645.8	671.5	694.4	718.0	740.2	761.1	786.1
17.5°	540.6	566.1	594.3	625.1	655.1	686.3	713.6	743.4	765.9	794.1	817.3
20°	534.0	561.5	591.5	626.1	660.3	694.8	725.0	755.4	780.7	809.1	838.5
22.5°	526.0	556.1	588.7	624.5	660.3	698.0	731.4	761.6	793.1	824.9	855.3
25°	513.0	544.3	578.9	618.1	659.2	697.8	733.5	770.9	804.8	839.4	866.7
27.5°	497.2	530.0	566.4	606.9	649.0	688.5	730.6	770.5	804.6	837.9	861.7
30°	484.5	519.1	554.1	595.1	638.9	681.3	726.3	766.3	802.2	832.1	845.5
32.5°	471.5	504.3	540.4	581.9	626.7	672.3	717.0	757.9	791.1	809.0	809.4
35°	448.8	479.6	517.1	557.9	603.9	653.4	698.6	738.8	759.1	760.6	738.8
37.5°	424.1	452.3	487.7	528.6	578.9	628.2	674.4	701.2	707.9	685.2	644.9
40°	406.4	432.5	466.7	508.6	558.6	609.4	651.6	671.2	664.1	627.3	582.2
42.5°	387.9	412.2	445.1	486.4	536.6	588.1	624.0	634.4	615.6	573.1	520.3
45°	357.6	379.8	412.5	454.2	502.4	550.5	577.8	572.4	540.9	490.5	431.4
47.5°	326.0	347.6	376.9	415.5	464.9	506.4	524.8	508.7	463.9	408.5	360.4
50°	305.2	327.3	354.2	391.1	436.1	476.3	488.0	463.5	413.8	360.5	316.3
52.5°	284.6	303.5	330.0	365.5	408.6	442.5	448.8	420.6	369.2	321.4	282.2
55°	253.4	270.6	292.8	326.3	363.6	392.4	389.0	352.7	306.0	265.2	234.4
57.5°	223.2	236.1	256.7	288.1	320.8	340.2	327.9	296.9	253.4	220.0	194.1
60°	203.2	215.3	234.4	261.8	290.7	301.6	291.3	257.7	223.3	192.7	170.9
62.5°	184.3	194.9	211.4	236.9	260.1	266.6	255.6	226.2	195.3	169.2	151.1
65°	156.8	166.6	180.7	198.8	214.8	217.9	210.8	180.7	157.3	135.4	122.9
67.5°	131.9	138.3	149.3	164.9	173.4	175.2	161.5	142.5	121.9	108.5	99.1
70°	115.1	119.6	129.8	138.3	145.2	145.4	132.7	117.5	101.7	90.8	83.9
72.5°	98.9	103.1	110.9	116.7	122.1	120.3	108.7	96.7	83.9	75.6	70.5
75°	76.3	80.1	84.1	86.8	86.8	84.5	76.1	67.1	59.8	54.9	53.3
77.5°	55.4	58.5	59.9	59.5	58.7	55.2	49.9	44.0	41.4	39.1	37.9
80°	43.5	44.9	45.2	44.2	42.8	38.8	35.3	32.8	30.3	29.4	29.0
82.5°	32.2	33.5	32.2	32.6	29.6	26.3	24.3	23.5	22.5	22.1	21.7
85°	17.2	17.0	16.5	15.4	13.4	12.9	12.7	12.5	12.1	12.3	11.8
87.5°	6.5	6.7	6.1	6.2	6.2	7.2	7.4	7.8	8.2	7.8	8.4
90°	3.3	6.6	7.6	8.8	8.8	15.4	15.4	17.5	19.7	18.7	19.7
92.5°	18.2	28.5	41.8	57.9	80.6	136.3	221.2	304.1	347.4	289.4	215.1
95°	39.4	50.4	64.7	90.9	137.0	232.1	411.8	673.5	892.6	917.8	811.5
97.5°	64.8	74.3	87.4	110.0	148.5	221.9	370.2	630.4	940.2	1153.1	1199.1
100°	83.2	90.9	104.1	124.9	159.9	224.5	348.3	571.7	880.5	1160.9	1320.9
102.5°	102.5	109.3	121.6	141.5	174.8	233.3	342.1	532.3	806.1	1095.2	1314.8
105°	131.4	137.0	150.1	169.8	201.5	254.1	345.0	498.3	718.5	975.8	1226.6
107.5°	160.5	166.1	180.0	198.9	230.3	278.4	361.2	492.2	669.4	879.5	1101.5
110°	180.7	186.2	199.3	219.0	248.6	296.8	373.4	494.0	652.8	831.3	1026.2





TEST NUMBER: P332891-830

CATALOG NUMBER: S124RDIP-S350D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	200.0	206.3	218.6	238.4	267.9	314.3	386.6	499.2	644.9	804.1	971.0
115°	228.9	236.6	247.5	268.3	297.9	341.7	407.5	509.3	640.7	778.7	915.6
117.5°	257.6	264.4	276.4	296.0	326.6	368.3	428.7	520.0	639.6	767.3	888.4
120°	276.0	283.7	295.7	314.3	345.0	386.6	443.6	527.9	639.6	761.2	876.2
122.5°	293.5	301.2	312.4	332.7	362.5	404.2	457.6	535.8	638.8	754.2	865.6
125°	318.7	325.3	337.3	358.2	388.8	428.2	478.6	547.6	637.4	742.5	847.7
127.5°	338.2	346.1	359.9	381.5	412.5	450.5	496.8	557.0	635.0	727.0	825.8
130°	350.4	359.2	375.7	396.4	428.2	465.5	508.2	564.0	634.1	717.4	808.3
132.5°	361.0	372.4	388.0	410.5	440.5	477.8	519.6	570.1	633.3	708.6	789.9
135°	377.9	388.8	407.5	430.5	458.9	495.0	534.5	579.4	632.0	695.5	764.5
137.5°	393.6	405.7	423.4	447.3	474.5	508.2	545.0	584.8	631.7	684.1	741.5
140°	404.2	416.2	434.8	457.8	484.1	517.0	552.0	589.3	630.8	678.0	728.3
142.5°	416.4	427.5	445.4	467.4	492.9	524.8	557.2	592.8	630.8	672.7	716.0
145°	433.8	444.7	460.0	480.8	504.9	533.4	563.0	594.7	628.7	663.7	698.8
147.5°	451.0	460.6	476.5	493.7	515.4	542.2	568.0	595.8	624.7	655.6	684.6
150°	463.3	472.0	485.2	501.6	522.5	546.5	570.6	595.8	622.1	649.5	675.8
152.5°	473.8	482.6	494.8	509.5	528.6	550.1	572.4	594.1	617.7	642.4	666.1
155°	490.7	497.2	508.2	520.3	536.7	555.3	573.9	591.4	611.1	632.0	651.7
157.5°	505.1	511.2	519.8	530.3	543.3	559.0	573.9	588.6	604.4	621.2	636.1
160°	514.7	519.2	526.8	535.6	547.6	560.7	573.9	586.0	599.1	613.3	626.5
162.5°	522.6	526.1	532.9	540.8	550.3	562.5	573.9	583.3	593.8	606.3	616.8
165°	533.4	535.6	541.0	546.5	553.1	563.0	571.7	578.2	586.0	594.7	603.5
167.5°	542.2	543.3	547.4	550.4	555.5	562.7	569.1	573.1	578.1	584.2	590.6
170°	546.5	547.6	550.9	553.1	556.4	561.8	567.3	569.5	572.8	577.2	582.7
172.5°	550.9	551.1	553.6	554.9	557.2	561.0	565.6	566.0	567.5	571.1	575.6
175°	555.3	555.3	556.4	557.5	557.5	559.7	563.0	561.8	561.8	564.0	566.3
177.5°	557.5	556.6	557.5	557.5	557.5	558.4	560.1	558.4	558.4	559.2	560.1
180°	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5



TEST NUMBER: P332891-830

CATALOG NUMBER: S124RDIP-S350D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	553.6	553.6	553.6	553.6	553.6	553.6	553.6
2.5°	580.8	581.5	582.0	583.8	584.0	585.6	584.0
5°	628.9	632.0	636.9	641.8	642.2	645.4	639.8
7.5°	682.7	689.9	694.5	702.4	705.5	707.5	704.3
10°	719.8	726.5	738.4	744.1	750.0	750.8	748.2
12.5°	755.7	766.3	775.6	786.6	786.4	794.2	791.4
15°	803.5	814.5	827.4	839.6	844.0	844.0	847.6
17.5°	837.5	857.6	871.0	880.6	891.2	893.0	891.7
20°	860.6	882.2	896.5	909.0	916.2	918.1	918.1
22.5°	877.7	896.2	910.1	921.3	927.2	929.5	928.9
25°	889.6	905.4	913.9	917.3	918.8	918.4	914.2
27.5°	873.4	872.6	867.3	857.1	849.3	844.6	839.2
30°	842.4	830.7	817.3	802.6	783.6	769.1	764.7
32.5°	796.1	770.1	747.3	722.8	702.5	688.0	681.8
35°	706.7	665.4	631.7	602.3	580.9	567.5	563.0
37.5°	600.6	560.6	519.0	490.4	472.6	459.1	454.1
40°	533.1	489.7	453.3	426.5	408.2	395.0	394.8
42.5°	471.6	430.0	395.8	376.5	356.8	348.1	348.1
45°	386.2	352.9	323.9	308.7	296.9	289.7	287.8
47.5°	319.7	292.2	272.9	260.8	251.2	246.7	243.6
50°	282.4	258.4	242.9	232.4	227.1	221.3	220.8
52.5°	251.4	231.9	219.9	211.4	204.6	201.1	201.2
55°	211.2	195.9	187.4	180.9	175.6	172.9	171.7
57.5°	178.0	166.5	160.2	154.3	152.0	150.0	149.4
60°	157.3	149.5	143.6	138.9	135.6	135.0	134.7
62.5°	140.2	132.0	128.0	124.3	121.9	120.8	120.5
65°	115.6	109.5	105.9	103.0	102.2	100.6	100.4
67.5°	93.1	89.5	87.2	85.2	84.0	83.9	83.9
70°	79.5	77.4	75.4	74.3	73.6	73.1	73.1
72.5°	67.7	66.2	64.5	63.9	63.8	63.3	63.2
75°	51.6	50.0	50.2	49.1	48.2	47.0	46.4
77.5°	36.6	35.4	35.2	35.1	34.3	34.2	34.5
80°	28.4	27.2	27.0	27.2	27.0	26.3	26.3
82.5°	21.6	20.6	20.4	20.3	20.1	20.3	19.9
85°	11.6	11.1	11.1	11.1	11.6	11.4	11.1
87.5°	8.3	8.3	8.5	8.5	8.8	8.4	8.5
90°	20.8	21.9	21.9	23.0	24.1	23.0	23.0
92.5°	161.8	128.8	106.9	94.0	88.0	84.4	84.4
95°	641.8	495.0	388.8	335.2	301.2	281.4	267.2
97.5°	1136.0	1028.9	914.5	835.8	770.0	737.1	714.4
100°	1342.7	1289.1	1208.1	1112.8	1045.9	1013.1	1004.4
102.5°	1423.3	1438.9	1405.1	1346.7	1298.3	1263.7	1256.7
105°	1416.2	1524.6	1569.4	1571.7	1562.9	1547.6	1541.0
107.5°	1303.3	1456.0	1553.7	1607.8	1632.8	1643.7	1646.6
110°	1215.7	1374.5	1495.0	1572.7	1618.7	1638.5	1648.3



TEST NUMBER: P332891-830

CATALOG NUMBER: S124RDIP-S350D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	1138.6	1288.6	1409.1	1497.4	1553.0	1580.6	1596.7
115°	1050.4	1178.5	1283.6	1370.2	1435.9	1470.9	1479.7
117.5°	999.9	1100.7	1189.9	1263.7	1318.9	1354.3	1361.1
120°	978.1	1065.6	1143.4	1205.9	1254.1	1282.5	1294.6
122.5°	964.0	1043.8	1111.9	1164.7	1205.9	1229.9	1242.0
125°	941.9	1017.5	1077.7	1121.5	1153.3	1174.1	1180.6
127.5°	915.9	991.2	1048.4	1092.4	1120.7	1138.2	1144.7
130°	894.8	969.3	1027.4	1072.2	1099.6	1117.1	1123.7
132.5°	871.2	943.9	1001.9	1045.9	1076.9	1093.4	1100.0
135°	835.7	902.5	957.2	1001.1	1031.7	1049.2	1055.8
137.5°	801.7	858.0	907.5	948.5	978.7	993.2	1001.1
140°	779.8	829.1	875.1	913.4	937.5	952.8	961.6
142.5°	761.4	803.7	843.6	877.5	899.8	913.4	919.5
145°	736.0	768.8	799.6	826.9	845.6	856.5	862.0
147.5°	714.1	740.4	764.5	784.7	800.6	809.0	810.9
150°	701.0	722.8	742.5	760.1	774.3	780.9	782.0
152.5°	687.8	707.9	724.2	739.0	750.6	754.6	755.7
155°	669.2	685.6	698.8	709.7	718.5	721.8	721.8
157.5°	650.8	664.6	675.1	683.4	690.0	692.0	692.0
160°	638.5	650.5	659.3	665.9	672.5	673.5	673.5
162.5°	627.2	636.6	644.4	649.2	655.8	657.0	656.0
165°	610.0	617.7	623.2	627.5	632.0	630.8	629.8
167.5°	595.6	601.7	605.0	607.2	610.0	609.8	609.0
170°	586.0	590.3	593.6	595.8	596.9	595.8	595.8
172.5°	578.1	580.7	583.1	584.4	585.5	584.4	582.7
175°	567.3	569.5	569.5	569.5	571.7	569.5	567.3
177.5°	561.0	561.0	561.8	561.0	561.8	560.1	558.4
180°	557.5	557.5	557.5	557.5	557.5	557.5	557.5

(END OF REPORT)