

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332920-830

Luminaire Tested: **S124RDIP-S575D1205U830-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332920-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIP-S575D1205U830-4F0-1E-UDD-A1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1205 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6233.3 lumens
Efficiency: N/A
Efficacy: 126.2 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 49.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332920-830

CATALOG NUMBER: S124RDIP-S575D1205U830-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332920-830

CATALOG NUMBER: S124RDIP-S575D1205U830-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	37
1	95	91	87	84	86	83	80	77	67	65	63	53	51	50	40	39	38	32
2	87	80	74	69	79	73	68	64	59	56	53	47	44	42	35	34	32	27
3	79	70	63	58	72	64	58	53	52	48	45	42	39	36	31	30	28	23
4	73	62	55	49	66	57	51	45	47	42	38	37	34	31	28	26	24	20
5	67	56	48	42	60	51	44	39	42	37	33	33	30	27	26	23	21	18
6	62	50	42	37	56	46	39	34	38	33	29	30	27	24	23	21	19	16
7	57	45	37	32	52	41	35	30	34	29	25	28	24	21	21	19	17	14
8	53	41	33	28	48	38	31	26	31	26	23	25	22	19	20	17	15	13
9	49	37	30	25	45	34	28	24	29	24	20	23	20	17	18	16	14	11
10	46	34	27	23	42	31	25	21	26	21	18	21	18	15	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7348	7348	7348	7348
5°	8524	7370	6515	7370
10°	10083	7338	5814	7338
15°	11646	7270	4996	7270
20°	12968	7177	4517	7177
25°	13387	7085	4195	7085
30°	11719	6974	3999	6974
35°	9122	6809	3882	6809
40°	6841	6620	3818	6620
45°	5401	6318	3785	6318
50°	4560	5968	3676	5968
55°	3975	5585	3478	5585
60°	3576	5186	3079	5186
65°	3152	4756	2648	4756
70°	2840	4312	2389	4312
75°	2380	3821	2037	3821
80°	2013	3254	1911	3254
85°	1704	2547	1704	2547



TEST NUMBER: P332920-830

CATALOG NUMBER: S124RDIP-S575D1205U830-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.2	1.4
10°-20°	266.0	4.3
20°-30°	416.1	6.7
30°-40°	462.6	7.4
40°-50°	410.4	6.6
50°-60°	319.8	5.1
60°-70°	209.4	3.4
70°-80°	103.0	1.7
80°-90°	29.6	0.5
90°-100°	93.4	1.5
100°-110°	276.7	4.4
110°-120°	469.6	7.5
120°-130°	619.1	9.9
130°-140°	695.3	11.2
140°-150°	683.3	11.0
150°-160°	574.7	9.2
160°-170°	382.4	6.1
170°-180°	133.9	2.1
0°-30°	770.3	12.4
0°-40°	1232.9	19.8
0°-60°	1963.1	31.5
0°-90°	2305.0	37.0
90°-120°	839.6	13.5
90°-150°	2837.4	45.5
90°-180°	3928.0	63.0
0°-180°	6233.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	910	910	910	910	910	
5°	1052	910	804	910	1052	106
15°	1394	870	598	870	1394	396
25°	1503	795	471	795	1503	667
35°	926	691	394	691	926	580
45°	473	553	332	553	473	375
55°	282	397	247	397	282	257
65°	165	249	139	249	165	166
75°	76	122	65	122	76	84
85°	18	28	18	28	18	22
90°	33	3	33	3	33	17
95°	86	66	86	66	86	90
105°	267	255	267	255	267	282
115°	473	477	473	477	473	468
125°	690	695	690	695	690	615
135°	898	897	898	897	898	693
145°	1091	1090	1091	1090	1091	683
155°	1247	1248	1247	1248	1247	574
165°	1356	1359	1356	1359	1356	382
175°	1407	1414	1407	1414	1407	134
180°	1416	1416	1416	1416	1416	



TEST NUMBER: P332920-830

CATALOG NUMBER: S124RDIP-S575D1205U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	910.2	910.2	910.2	910.2	910.2	910.2	910.2	910.2	910.2	910.2	910.2
2.5°	960.1	962.7	960.1	959.8	956.9	956.0	954.8	951.0	944.0	939.8	940.8
5°	1051.8	1060.9	1055.8	1055.1	1047.0	1039.0	1033.8	1022.1	1009.6	1001.2	994.2
7.5°	1157.8	1163.1	1159.9	1154.7	1141.7	1134.3	1122.4	1106.9	1084.6	1067.4	1051.9
10°	1230.0	1234.4	1232.9	1223.4	1213.9	1194.4	1183.5	1161.8	1133.5	1111.2	1090.2
12.5°	1301.0	1305.7	1292.8	1293.3	1275.2	1259.8	1242.4	1215.2	1182.5	1153.7	1127.6
15°	1393.5	1387.7	1387.7	1380.4	1360.2	1338.9	1321.0	1292.3	1251.2	1216.8	1180.5
17.5°	1466.0	1468.1	1465.1	1447.7	1431.9	1409.9	1377.0	1343.6	1305.4	1259.1	1222.1
20°	1509.5	1509.5	1506.2	1494.4	1473.9	1450.4	1414.9	1378.6	1330.1	1283.6	1241.7
22.5°	1527.0	1528.2	1524.4	1514.7	1496.2	1473.3	1443.0	1406.1	1356.2	1303.8	1252.0
25°	1502.9	1509.8	1510.5	1508.0	1502.5	1488.6	1462.5	1424.7	1380.0	1323.1	1267.4
27.5°	1379.8	1388.6	1396.3	1408.9	1425.8	1434.6	1435.8	1416.5	1377.5	1322.9	1266.8
30°	1257.2	1264.4	1288.3	1319.5	1343.7	1365.6	1384.8	1389.9	1367.9	1318.7	1259.7
32.5°	1121.0	1131.0	1154.8	1188.4	1228.7	1265.9	1308.8	1330.6	1330.0	1300.5	1245.9
35°	925.6	932.9	955.0	990.1	1038.6	1093.9	1161.8	1214.6	1250.6	1247.9	1214.6
37.5°	746.5	754.8	777.0	806.3	853.2	921.7	987.4	1060.2	1126.6	1163.9	1152.7
40°	649.1	649.5	671.1	701.2	745.2	804.9	876.5	957.2	1031.2	1091.7	1103.4
42.5°	572.2	572.3	586.6	619.1	650.7	707.0	775.2	855.4	942.1	1011.9	1043.0
45°	473.1	476.4	488.1	507.6	532.4	580.1	634.8	709.3	806.4	889.3	941.0
47.5°	400.6	405.5	412.9	428.8	448.7	480.4	525.6	592.5	671.6	762.7	836.3
50°	363.1	363.8	373.3	382.1	399.4	424.7	464.3	520.0	592.7	680.2	762.0
52.5°	330.8	330.6	336.4	347.5	361.6	381.3	413.2	464.0	528.4	606.9	691.4
55°	282.4	284.2	288.6	297.4	308.0	322.0	347.3	385.4	436.0	503.1	579.8
57.5°	245.5	246.5	250.0	253.7	263.4	273.6	292.6	319.1	361.7	416.7	488.1
60°	221.5	221.9	223.0	228.5	236.2	245.7	258.5	280.9	316.9	367.1	423.6
62.5°	198.0	198.7	200.4	204.4	210.4	217.0	230.4	248.4	278.1	321.0	371.9
65°	165.0	165.4	168.0	169.5	174.2	180.0	189.9	202.1	222.6	258.5	297.1
67.5°	137.9	137.9	138.0	140.1	143.4	147.2	153.2	162.9	178.3	200.4	234.3
70°	120.3	120.3	121.0	122.2	123.9	127.2	130.5	137.9	149.3	167.2	193.2
72.5°	103.9	104.2	104.9	105.1	106.0	108.8	111.2	115.8	124.3	137.9	158.9
75°	76.3	77.4	79.2	80.7	82.5	82.2	84.7	87.7	90.2	98.3	110.4
77.5°	56.7	56.2	56.4	57.7	57.9	58.2	60.0	62.3	64.3	68.1	72.4
80°	43.3	43.3	44.4	44.8	44.4	44.8	46.6	47.7	48.4	49.9	53.9
82.5°	32.7	33.3	32.9	33.3	33.6	33.9	35.4	35.6	36.4	36.9	38.6
85°	18.4	18.7	19.0	18.4	18.4	18.4	19.0	19.4	20.2	19.8	20.5
87.5°	13.0	12.6	12.8	12.7	12.9	12.4	12.4	12.7	11.9	11.9	11.5
90°	32.9	32.3	31.9	31.4	30.9	30.0	28.5	27.1	25.5	24.1	22.1
92.5°	48.6	48.4	48.1	47.8	47.4	46.8	46.0	45.1	44.2	43.4	42.0
95°	86.5	86.5	86.5	86.5	86.5	86.1	85.4	84.6	84.0	83.2	81.5
97.5°	135.5	135.5	135.5	135.5	135.5	135.2	134.2	133.4	132.5	131.6	129.6
100°	169.8	169.8	169.8	169.8	169.8	169.5	169.0	168.5	168.1	167.6	165.3
102.5°	208.3	208.1	207.9	207.7	207.5	207.1	206.4	205.7	205.0	204.3	202.4
105°	267.2	266.5	265.7	265.0	264.3	263.5	262.8	262.1	261.4	260.6	259.7
107.5°	324.6	324.6	324.7	324.7	324.8	324.4	323.8	323.1	322.4	321.7	321.6
110°	365.7	365.0	364.3	363.5	362.8	362.7	363.2	363.6	364.2	364.7	364.9



TEST NUMBER: P332920-830

CATALOG NUMBER: S124RDIP-S575D1205U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	407.8	407.6	407.5	407.4	407.2	407.2	407.3	407.4	407.5	407.6	408.0
115°	473.1	473.3	473.5	473.8	474.0	474.3	474.5	474.8	475.0	475.2	475.7
117.5°	535.3	535.7	536.2	536.7	537.2	537.8	538.7	539.5	540.4	541.2	541.5
120°	582.6	582.1	581.5	581.1	580.6	581.0	582.2	583.4	584.7	585.9	586.5
122.5°	622.0	622.8	623.8	624.6	625.5	626.3	627.2	628.0	628.9	629.6	630.0
125°	689.8	690.3	690.9	691.4	691.8	692.3	692.8	693.2	693.8	694.3	694.5
127.5°	752.7	753.1	753.5	753.9	754.3	754.7	755.3	755.7	756.2	756.7	757.1
130°	793.9	794.8	795.9	796.8	797.8	798.5	799.0	799.5	800.0	800.5	800.5
132.5°	837.7	838.1	838.5	838.9	839.2	839.7	840.2	840.7	841.1	841.7	841.9
135°	898.0	898.6	899.4	900.1	900.9	901.4	901.9	902.5	903.0	903.4	903.4
137.5°	961.2	961.1	960.9	960.8	960.6	960.9	961.5	962.1	962.8	963.4	963.0
140°	999.8	1000.0	1000.2	1000.5	1000.8	1001.0	1001.3	1001.5	1001.7	1001.9	1001.9
142.5°	1038.3	1038.4	1038.4	1038.5	1038.5	1038.6	1038.6	1038.7	1038.7	1038.8	1039.0
145°	1090.7	1091.4	1092.1	1092.9	1093.5	1094.1	1094.3	1094.6	1094.8	1095.0	1094.8
147.5°	1143.7	1143.9	1144.2	1144.4	1144.6	1144.8	1145.1	1145.3	1145.5	1145.7	1145.8
150°	1176.1	1176.3	1176.6	1176.8	1177.0	1177.1	1177.1	1177.1	1177.1	1177.1	1177.1
152.5°	1205.9	1206.5	1207.1	1207.8	1208.4	1208.4	1207.9	1207.2	1206.6	1206.1	1205.9
155°	1247.3	1248.2	1249.2	1250.2	1251.1	1251.1	1250.2	1249.2	1248.2	1247.3	1247.5
157.5°	1284.3	1285.1	1285.9	1286.8	1287.6	1287.6	1286.9	1286.2	1285.4	1284.7	1284.8
160°	1305.3	1306.6	1307.7	1308.9	1310.1	1310.4	1309.7	1308.9	1308.2	1307.5	1307.7
162.5°	1327.2	1328.4	1329.6	1330.9	1332.1	1332.0	1330.7	1329.4	1328.0	1326.7	1327.0
165°	1355.7	1356.6	1357.6	1358.6	1359.5	1359.3	1357.8	1356.4	1354.9	1353.5	1354.0
167.5°	1376.0	1377.5	1379.0	1380.5	1382.1	1382.1	1380.6	1379.1	1377.7	1376.2	1376.2
170°	1387.4	1389.1	1390.8	1392.5	1394.2	1394.4	1392.9	1391.5	1390.0	1388.6	1388.3
172.5°	1397.0	1398.7	1400.4	1402.1	1403.9	1403.9	1402.2	1400.6	1398.9	1397.3	1397.2
175°	1407.1	1408.8	1410.5	1412.2	1413.9	1413.9	1412.2	1410.5	1408.8	1407.1	1407.4
177.5°	1412.4	1413.9	1415.5	1417.0	1418.6	1418.7	1417.4	1416.0	1414.7	1413.2	1413.2
180°	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9



TEST NUMBER: P332920-830

CATALOG NUMBER: S124RDIP-S575D1205U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	910.2	910.2	910.2	910.2	910.2	910.2	910.2	910.2	910.2	910.2	910.2
2.5°	937.8	933.7	931.6	926.9	921.3	918.4	915.8	912.0	907.0	901.7	897.9
5°	985.4	976.6	965.5	952.3	940.7	929.3	919.4	909.5	898.1	886.4	874.7
7.5°	1034.3	1016.9	998.2	976.6	955.5	936.4	918.8	901.9	882.9	865.7	850.2
10°	1068.3	1044.8	1018.8	991.3	963.7	939.9	916.4	895.1	871.7	850.8	833.2
12.5°	1095.9	1068.3	1037.0	1002.7	969.6	940.8	913.8	886.1	859.4	836.7	813.2
15°	1141.6	1103.8	1061.7	1020.6	977.7	938.5	902.1	869.9	839.4	807.6	785.1
17.5°	1173.1	1128.2	1077.0	1027.7	976.9	930.7	888.8	850.4	815.2	782.7	756.0
20°	1191.8	1142.4	1085.5	1029.4	972.5	923.0	878.0	835.4	799.1	763.9	736.4
22.5°	1202.4	1147.6	1085.5	1026.7	967.9	914.3	864.8	820.5	780.9	745.7	715.3
25°	1205.8	1147.1	1083.6	1016.2	951.7	894.8	843.5	795.4	751.4	716.2	683.9
27.5°	1201.1	1132.0	1067.1	997.8	931.2	871.3	817.4	766.9	722.8	685.0	652.0
30°	1194.0	1120.0	1050.3	978.5	911.0	853.4	796.5	748.1	702.3	663.1	629.7
32.5°	1178.8	1105.3	1030.4	956.7	888.3	829.1	775.1	726.4	681.5	641.3	605.9
35°	1148.6	1074.1	992.7	917.2	850.1	788.4	737.8	690.9	648.0	605.1	567.7
37.5°	1108.7	1032.7	951.7	869.0	801.8	743.7	697.2	653.2	611.2	572.1	530.7
40°	1071.2	1001.9	918.3	836.1	767.2	711.1	668.2	628.2	586.1	547.1	505.7
42.5°	1025.8	966.7	882.2	799.7	731.7	677.6	637.6	598.6	560.2	522.5	479.3
45°	949.8	905.1	825.9	746.7	678.1	624.5	587.9	553.4	519.6	483.7	443.0
47.5°	862.8	832.5	764.2	683.1	619.6	571.5	536.0	507.8	479.3	443.4	407.6
50°	802.4	783.0	717.0	642.9	582.4	538.0	501.7	475.2	451.5	417.0	385.0
52.5°	737.8	727.5	671.8	600.9	542.4	499.0	468.0	444.2	420.1	391.4	361.6
55°	639.6	645.1	597.8	536.5	481.5	444.9	416.6	396.8	376.3	352.0	328.9
57.5°	539.0	559.2	527.4	473.6	422.1	388.2	366.9	350.2	333.1	312.9	293.2
60°	478.9	495.8	477.9	430.6	385.4	353.9	334.1	321.2	304.0	285.7	270.6
62.5°	420.3	438.3	427.6	389.5	347.6	320.5	303.0	291.1	278.2	262.2	246.6
65°	346.6	358.3	353.2	326.8	297.1	273.9	257.8	249.0	237.2	225.6	211.6
67.5°	265.4	288.1	285.1	271.1	245.4	227.3	216.8	209.1	198.3	189.6	180.1
70°	218.2	239.1	238.7	227.3	213.4	196.5	189.3	182.7	173.1	164.7	156.9
72.5°	178.6	197.7	200.6	191.9	182.4	169.6	162.5	158.0	148.7	143.0	136.7
75°	125.1	139.0	142.7	142.7	138.3	131.7	125.5	122.5	115.8	110.7	107.1
77.5°	82.0	90.8	96.5	97.8	98.5	96.3	91.1	89.1	84.1	82.2	78.7
80°	58.0	63.8	70.4	72.6	74.5	73.7	71.5	70.0	65.3	63.4	62.0
82.5°	40.1	43.3	48.7	53.5	53.1	55.0	53.1	51.8	48.3	47.6	46.1
85°	20.9	21.3	22.0	25.3	27.1	27.9	28.3	27.5	26.4	26.4	23.8
87.5°	11.1	10.4	10.6	10.2	9.9	10.6	10.8	10.7	10.3	9.9	9.6
90°	20.2	18.3	16.3	13.9	11.3	8.7	5.9	3.3	5.9	8.7	11.3
92.5°	40.6	39.3	37.9	35.7	32.6	29.6	26.5	23.5	26.5	29.6	32.6
95°	79.8	78.1	76.4	74.5	72.3	70.1	67.9	65.7	67.9	70.1	72.3
97.5°	127.6	125.6	123.7	121.8	120.0	118.3	116.5	114.8	116.5	118.3	120.0
100°	163.2	161.0	158.8	157.2	156.2	155.2	154.3	153.4	154.3	155.2	156.2
102.5°	200.4	198.3	196.3	195.2	194.7	194.4	194.0	193.6	194.0	194.4	194.7
105°	258.6	257.7	256.7	256.1	255.9	255.6	255.4	255.1	255.4	255.6	255.9
107.5°	321.4	321.3	321.1	320.9	320.7	320.4	320.1	319.7	320.1	320.4	320.7
110°	365.1	365.4	365.6	365.5	365.0	364.5	364.0	363.5	364.0	364.5	365.0



TEST NUMBER: P332920-830

CATALOG NUMBER: S124RDIP-S575D1205U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	408.5	408.9	409.3	409.5	409.4	409.3	409.3	409.1	409.3	409.3	409.4
115°	476.3	476.7	477.2	477.4	477.4	477.4	477.4	477.4	477.4	477.4	477.4
117.5°	541.9	542.2	542.5	542.6	542.4	542.2	542.1	541.9	542.1	542.2	542.4
120°	587.3	588.1	588.8	588.6	587.7	586.7	585.7	584.8	585.7	586.7	587.7
122.5°	630.4	630.7	631.0	631.0	630.6	630.2	629.8	629.4	629.8	630.2	630.6
125°	694.7	695.0	695.2	695.3	695.3	695.3	695.3	695.3	695.3	695.3	695.3
127.5°	757.4	757.8	758.3	758.1	757.3	756.6	755.9	755.2	755.9	756.6	757.3
130°	800.5	800.5	800.5	800.1	799.4	798.6	798.0	797.2	798.0	798.6	799.4
132.5°	842.1	842.3	842.4	842.3	841.7	841.2	840.7	840.1	840.7	841.2	841.7
135°	903.4	903.4	903.4	902.7	901.3	899.8	898.3	896.8	898.3	899.8	901.3
137.5°	962.6	962.2	961.9	961.3	960.6	960.0	959.3	958.6	959.3	960.0	960.6
140°	1001.9	1001.9	1001.9	1001.7	1001.3	1000.8	1000.2	999.8	1000.2	1000.8	1001.3
142.5°	1039.2	1039.3	1039.5	1039.4	1038.9	1038.4	1037.9	1037.5	1037.9	1038.4	1038.9
145°	1094.6	1094.3	1094.1	1093.4	1092.5	1091.6	1090.5	1089.6	1090.5	1091.6	1092.5
147.5°	1146.0	1146.2	1146.4	1145.9	1144.7	1143.6	1142.5	1141.2	1142.5	1143.6	1144.7
150°	1177.1	1177.1	1177.1	1176.7	1175.7	1174.8	1173.7	1172.8	1173.7	1174.8	1175.7
152.5°	1205.7	1205.5	1205.3	1204.9	1204.3	1203.7	1203.2	1202.6	1203.2	1203.7	1204.3
155°	1247.7	1248.0	1248.2	1248.3	1248.3	1248.3	1248.3	1248.3	1248.3	1248.3	1248.3
157.5°	1284.8	1284.9	1284.9	1285.2	1285.6	1286.0	1286.5	1286.9	1286.5	1286.0	1285.6
160°	1308.0	1308.2	1308.4	1308.7	1308.9	1309.2	1309.5	1309.7	1309.5	1309.2	1308.9
162.5°	1327.3	1327.5	1327.8	1328.1	1328.8	1329.5	1330.0	1330.7	1330.0	1329.5	1328.8
165°	1354.4	1354.9	1355.4	1356.0	1356.8	1357.4	1358.2	1359.0	1358.2	1357.4	1356.8
167.5°	1376.1	1376.1	1376.0	1376.6	1377.5	1378.6	1379.6	1380.6	1379.6	1378.6	1377.5
170°	1388.0	1387.8	1387.5	1388.0	1389.2	1390.4	1391.7	1392.9	1391.7	1390.4	1389.2
172.5°	1397.2	1397.1	1397.0	1397.6	1398.5	1399.6	1400.6	1401.7	1400.6	1399.6	1398.5
175°	1407.6	1407.9	1408.1	1408.8	1410.0	1411.3	1412.5	1413.7	1412.5	1411.3	1410.0
177.5°	1413.2	1413.2	1413.2	1413.7	1414.8	1415.7	1416.6	1417.7	1416.6	1415.7	1414.8
180°	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9



TEST NUMBER: P332920-830

CATALOG NUMBER: S124RDIP-S575D1205U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	910.2	910.2	910.2	910.2	910.2	910.2	910.2	910.2	910.2	910.2	910.2
2.5°	893.8	890.9	887.0	882.6	877.3	872.7	870.6	872.3	873.3	870.9	870.6
5°	866.6	857.4	850.1	839.1	830.3	822.9	817.7	815.6	816.3	810.5	809.0
7.5°	835.9	825.1	813.1	800.0	787.9	777.1	771.5	768.4	762.1	759.5	755.0
10°	816.3	801.6	789.9	774.5	760.6	747.7	741.5	736.4	730.2	727.2	721.0
12.5°	796.1	779.1	766.2	750.2	735.9	720.5	714.5	705.0	695.2	689.1	681.1
15°	767.5	747.1	731.2	712.2	695.3	677.7	661.9	644.3	637.7	623.8	615.8
17.5°	734.1	713.3	693.8	668.3	642.2	620.4	603.5	586.7	576.6	567.7	563.5
20°	712.2	693.1	666.0	636.3	607.3	583.1	569.5	558.6	547.5	541.3	536.9
22.5°	691.4	667.0	635.5	603.4	574.5	555.5	544.0	532.7	523.8	517.8	512.0
25°	656.5	624.5	591.2	554.5	534.7	518.2	505.7	496.5	491.1	483.3	480.4
27.5°	620.6	581.9	545.1	520.5	499.8	484.7	473.9	467.0	460.1	455.1	451.3
30°	593.0	553.7	520.8	497.3	476.4	463.9	455.1	447.0	441.6	437.5	434.6
32.5°	565.7	526.5	498.7	473.5	457.0	444.9	435.5	429.4	425.1	419.9	418.1
35°	526.2	491.4	467.2	444.5	427.6	416.6	409.3	403.0	399.4	397.9	396.8
37.5°	488.3	459.8	433.8	415.1	400.1	391.4	382.8	379.8	377.2	374.6	375.8
40°	464.3	437.5	414.4	394.6	382.5	373.0	367.8	364.2	361.9	361.9	361.9
42.5°	443.5	417.3	394.7	377.0	364.9	356.8	351.1	348.0	347.3	346.9	348.7
45°	411.1	386.9	364.2	349.5	339.2	331.1	327.8	325.3	325.3	326.8	327.2
47.5°	379.1	356.4	338.1	321.7	312.3	307.3	304.3	303.0	303.2	304.6	306.3
50°	359.4	337.1	319.1	304.3	295.6	290.8	288.2	287.5	288.2	288.2	290.8
52.5°	338.0	317.9	300.3	287.9	278.0	273.5	272.1	271.1	271.5	272.7	273.8
55°	306.6	288.6	271.7	260.0	252.7	249.8	246.5	246.9	246.1	246.9	246.9
57.5°	275.1	259.0	243.3	233.9	227.5	223.3	219.7	220.6	219.6	219.4	218.9
60°	254.9	237.2	224.8	216.4	209.1	205.4	202.1	202.8	201.7	201.0	199.5
62.5°	232.9	218.2	206.3	198.2	192.3	188.0	184.7	184.0	181.4	179.0	175.7
65°	201.0	188.9	178.2	170.5	165.0	161.7	159.2	156.9	151.5	145.6	142.7
67.5°	169.9	161.2	151.3	144.8	140.3	136.0	131.1	127.3	122.2	118.9	117.2
70°	150.0	141.6	133.1	126.9	122.2	118.1	112.5	110.0	106.3	104.9	103.0
72.5°	130.9	123.1	115.2	109.6	104.5	101.3	97.1	94.4	92.8	92.3	90.4
75°	102.0	95.8	89.8	84.7	80.7	78.5	76.6	74.8	74.1	70.8	68.9
77.5°	74.4	70.2	66.6	63.0	60.0	58.6	55.0	53.0	51.7	50.1	49.8
80°	58.0	55.0	51.4	49.1	45.1	43.6	42.1	41.8	41.5	41.1	40.7
82.5°	43.5	40.6	36.9	35.6	34.6	33.6	32.8	32.4	32.0	32.2	32.2
85°	22.0	20.5	20.5	20.2	19.8	19.4	19.0	19.0	18.7	19.0	18.7
87.5°	10.2	10.3	10.7	10.5	11.2	11.6	11.6	11.9	12.4	12.2	12.3
90°	13.9	16.3	18.3	20.2	22.1	24.1	25.5	27.1	28.5	30.0	30.9
92.5°	35.7	37.9	39.3	40.6	42.0	43.4	44.2	45.1	46.0	46.8	47.4
95°	74.5	76.4	78.1	79.8	81.5	83.2	84.0	84.6	85.4	86.1	86.5
97.5°	121.8	123.7	125.6	127.6	129.6	131.6	132.5	133.4	134.2	135.2	135.5
100°	157.2	158.8	161.0	163.2	165.3	167.6	168.1	168.5	169.0	169.5	169.8
102.5°	195.2	196.3	198.3	200.4	202.4	204.3	205.0	205.7	206.4	207.1	207.5
105°	256.1	256.7	257.7	258.6	259.7	260.6	261.4	262.1	262.8	263.5	264.3
107.5°	320.9	321.1	321.3	321.4	321.6	321.7	322.4	323.1	323.8	324.4	324.8
110°	365.5	365.6	365.4	365.1	364.9	364.7	364.2	363.6	363.2	362.7	362.8



TEST NUMBER: P332920-830

CATALOG NUMBER: S124RDIP-S575D1205U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	409.5	409.3	408.9	408.5	408.0	407.6	407.5	407.4	407.3	407.2	407.2
115°	477.4	477.2	476.7	476.3	475.7	475.2	475.0	474.8	474.5	474.3	474.0
117.5°	542.6	542.5	542.2	541.9	541.5	541.2	540.4	539.5	538.7	537.8	537.2
120°	588.6	588.8	588.1	587.3	586.5	585.9	584.7	583.4	582.2	581.0	580.6
122.5°	631.0	631.0	630.7	630.4	630.0	629.6	628.9	628.0	627.2	626.3	625.5
125°	695.3	695.2	695.0	694.7	694.5	694.3	693.8	693.2	692.8	692.3	691.8
127.5°	758.1	758.3	757.8	757.4	757.1	756.7	756.2	755.7	755.3	754.7	754.3
130°	800.1	800.5	800.5	800.5	800.5	800.5	800.0	799.5	799.0	798.5	797.8
132.5°	842.3	842.4	842.3	842.1	841.9	841.7	841.1	840.7	840.2	839.7	839.2
135°	902.7	903.4	903.4	903.4	903.4	903.4	903.0	902.5	901.9	901.4	900.9
137.5°	961.3	961.9	962.2	962.6	963.0	963.4	962.8	962.1	961.5	960.9	960.6
140°	1001.7	1001.9	1001.9	1001.9	1001.9	1001.9	1001.7	1001.5	1001.3	1001.0	1000.8
142.5°	1039.4	1039.5	1039.3	1039.2	1039.0	1038.8	1038.7	1038.7	1038.6	1038.6	1038.5
145°	1093.4	1094.1	1094.3	1094.6	1094.8	1095.0	1094.8	1094.6	1094.3	1094.1	1093.5
147.5°	1145.9	1146.4	1146.2	1146.0	1145.8	1145.7	1145.5	1145.3	1145.1	1144.8	1144.6
150°	1176.7	1177.1	1177.1	1177.1	1177.1	1177.1	1177.1	1177.1	1177.1	1177.1	1177.0
152.5°	1204.9	1205.3	1205.5	1205.7	1205.9	1206.1	1206.6	1207.2	1207.9	1208.4	1208.4
155°	1248.3	1248.2	1248.0	1247.7	1247.5	1247.3	1248.2	1249.2	1250.2	1251.1	1251.1
157.5°	1285.2	1284.9	1284.9	1284.8	1284.8	1284.7	1285.4	1286.2	1286.9	1287.6	1287.6
160°	1308.7	1308.4	1308.2	1308.0	1307.7	1307.5	1308.2	1308.9	1309.7	1310.4	1310.1
162.5°	1328.1	1327.8	1327.5	1327.3	1327.0	1326.7	1328.0	1329.4	1330.7	1332.0	1332.1
165°	1356.0	1355.4	1354.9	1354.4	1354.0	1353.5	1354.9	1356.4	1357.8	1359.3	1359.5
167.5°	1376.6	1376.0	1376.1	1376.1	1376.2	1376.2	1377.7	1379.1	1380.6	1382.1	1382.1
170°	1388.0	1387.5	1387.8	1388.0	1388.3	1388.6	1390.0	1391.5	1392.9	1394.4	1394.2
172.5°	1397.6	1397.0	1397.1	1397.2	1397.2	1397.3	1398.9	1400.6	1402.2	1403.9	1403.9
175°	1408.8	1408.1	1407.9	1407.6	1407.4	1407.1	1408.8	1410.5	1412.2	1413.9	1413.9
177.5°	1413.7	1413.2	1413.2	1413.2	1413.2	1413.2	1414.7	1416.0	1417.4	1418.7	1418.6
180°	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9



TEST NUMBER: P332920-830

CATALOG NUMBER: S124RDIP-S575D1205U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	910.2	910.2	910.2	910.2	910.2	910.2	910.2	910.2	910.2	910.2	910.2
2.5°	868.8	869.4	867.4	866.8	867.4	869.4	868.8	870.6	870.9	873.3	872.3
5°	806.1	805.3	803.5	803.9	803.5	805.3	806.1	809.0	810.5	816.3	815.6
7.5°	752.3	749.5	750.4	747.3	750.4	749.5	752.3	755.0	759.5	762.1	768.4
10°	719.5	715.5	712.2	709.3	712.2	715.5	719.5	721.0	727.2	730.2	736.4
12.5°	674.7	671.2	666.7	667.6	666.7	671.2	674.7	681.1	689.1	695.2	705.0
15°	611.0	605.5	596.6	597.8	596.6	605.5	611.0	615.8	623.8	637.7	644.3
17.5°	557.0	557.1	553.1	554.0	553.1	557.1	557.0	563.5	567.7	576.6	586.7
20°	529.1	526.6	527.0	525.8	527.0	526.6	529.1	536.9	541.3	547.5	558.6
22.5°	509.8	506.7	504.1	501.8	504.1	506.7	509.8	512.0	517.8	523.8	532.7
25°	477.1	474.9	471.6	470.9	471.6	474.9	477.1	480.4	483.3	491.1	496.5
27.5°	448.4	447.9	446.6	444.9	446.6	447.9	448.4	451.3	455.1	460.1	467.0
30°	431.6	430.9	430.2	429.0	430.2	430.9	431.6	434.6	437.5	441.6	447.0
32.5°	416.7	416.2	415.5	415.6	415.5	416.2	416.7	418.1	419.9	425.1	429.4
35°	395.3	394.9	394.3	393.9	394.3	394.9	395.3	396.8	397.9	399.4	403.0
37.5°	375.4	376.4	375.9	375.8	375.9	376.4	375.4	375.8	374.6	377.2	379.8
40°	361.6	361.9	362.7	362.3	362.7	361.9	361.6	361.9	361.9	361.9	364.2
42.5°	350.2	350.2	351.3	350.0	351.3	350.2	350.2	348.7	346.9	347.3	348.0
45°	329.7	331.9	331.5	331.5	331.5	331.9	329.7	327.2	326.8	325.3	325.3
47.5°	307.3	309.2	309.7	309.6	309.7	309.2	307.3	306.3	304.6	303.2	303.0
50°	292.7	291.9	293.0	292.7	293.0	291.9	292.7	290.8	288.2	288.2	287.5
52.5°	274.8	274.9	274.8	274.5	274.8	274.9	274.8	273.8	272.7	271.5	271.1
55°	247.1	247.5	246.9	247.1	246.9	247.5	247.1	246.9	246.9	246.1	246.9
57.5°	217.3	215.5	216.2	215.4	216.2	215.5	217.3	218.9	219.4	219.6	220.6
60°	195.9	192.9	192.2	190.7	192.2	192.9	195.9	199.5	201.0	201.7	202.8
62.5°	171.7	169.8	167.2	168.4	167.2	169.8	171.7	175.7	179.0	181.4	184.0
65°	139.7	138.3	137.1	138.6	137.1	138.3	139.7	142.7	145.6	151.5	156.9
67.5°	115.6	114.9	114.9	114.1	114.9	114.9	115.6	117.2	118.9	122.2	127.3
70°	103.0	102.0	102.0	101.2	102.0	102.0	103.0	103.0	104.9	106.3	110.0
72.5°	90.1	89.1	89.4	88.9	89.4	89.1	90.1	90.4	92.3	92.8	94.4
75°	66.7	64.9	64.9	65.3	64.9	64.9	66.7	68.9	70.8	74.1	74.8
77.5°	49.8	49.4	50.0	49.3	50.0	49.4	49.8	49.8	50.1	51.7	53.0
80°	40.7	40.3	40.0	41.1	40.0	40.3	40.7	40.7	41.1	41.5	41.8
82.5°	31.6	31.6	31.5	32.9	31.5	31.6	31.6	32.2	32.2	32.0	32.4
85°	19.0	18.4	19.0	18.4	19.0	18.4	19.0	18.7	19.0	18.7	19.0
87.5°	13.0	12.8	12.6	13.0	12.6	12.8	13.0	12.3	12.2	12.4	11.9
90°	31.4	31.9	32.3	32.9	32.3	31.9	31.4	30.9	30.0	28.5	27.1
92.5°	47.8	48.1	48.4	48.6	48.4	48.1	47.8	47.4	46.8	46.0	45.1
95°	86.5	86.5	86.5	86.5	86.5	86.5	86.5	86.5	86.1	85.4	84.6
97.5°	135.5	135.5	135.5	135.5	135.5	135.5	135.5	135.5	135.2	134.2	133.4
100°	169.8	169.8	169.8	169.8	169.8	169.8	169.8	169.8	169.5	169.0	168.5
102.5°	207.7	207.9	208.1	208.3	208.1	207.9	207.7	207.5	207.1	206.4	205.7
105°	265.0	265.7	266.5	267.2	266.5	265.7	265.0	264.3	263.5	262.8	262.1
107.5°	324.7	324.7	324.6	324.6	324.6	324.7	324.7	324.8	324.4	323.8	323.1
110°	363.5	364.3	365.0	365.7	365.0	364.3	363.5	362.8	362.7	363.2	363.6



TEST NUMBER: P332920-830

CATALOG NUMBER: S124RDIP-S575D1205U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	407.4	407.5	407.6	407.8	407.6	407.5	407.4	407.2	407.2	407.3	407.4
115°	473.8	473.5	473.3	473.1	473.3	473.5	473.8	474.0	474.3	474.5	474.8
117.5°	536.7	536.2	535.7	535.3	535.7	536.2	536.7	537.2	537.8	538.7	539.5
120°	581.1	581.5	582.1	582.6	582.1	581.5	581.1	580.6	581.0	582.2	583.4
122.5°	624.6	623.8	622.8	622.0	622.8	623.8	624.6	625.5	626.3	627.2	628.0
125°	691.4	690.9	690.3	689.8	690.3	690.9	691.4	691.8	692.3	692.8	693.2
127.5°	753.9	753.5	753.1	752.7	753.1	753.5	753.9	754.3	754.7	755.3	755.7
130°	796.8	795.9	794.8	793.9	794.8	795.9	796.8	797.8	798.5	799.0	799.5
132.5°	838.9	838.5	838.1	837.7	838.1	838.5	838.9	839.2	839.7	840.2	840.7
135°	900.1	899.4	898.6	898.0	898.6	899.4	900.1	900.9	901.4	901.9	902.5
137.5°	960.8	960.9	961.1	961.2	961.1	960.9	960.8	960.6	960.9	961.5	962.1
140°	1000.5	1000.2	1000.0	999.8	1000.0	1000.2	1000.5	1000.8	1001.0	1001.3	1001.5
142.5°	1038.5	1038.4	1038.4	1038.3	1038.4	1038.4	1038.5	1038.5	1038.6	1038.6	1038.7
145°	1092.9	1092.1	1091.4	1090.7	1091.4	1092.1	1092.9	1093.5	1094.1	1094.3	1094.6
147.5°	1144.4	1144.2	1143.9	1143.7	1143.9	1144.2	1144.4	1144.6	1144.8	1145.1	1145.3
150°	1176.8	1176.6	1176.3	1176.1	1176.3	1176.6	1176.8	1177.0	1177.1	1177.1	1177.1
152.5°	1207.8	1207.1	1206.5	1205.9	1206.5	1207.1	1207.8	1208.4	1208.4	1207.9	1207.2
155°	1250.2	1249.2	1248.2	1247.3	1248.2	1249.2	1250.2	1251.1	1251.1	1250.2	1249.2
157.5°	1286.8	1285.9	1285.1	1284.3	1285.1	1285.9	1286.8	1287.6	1287.6	1286.9	1286.2
160°	1308.9	1307.7	1306.6	1305.3	1306.6	1307.7	1308.9	1310.1	1310.4	1309.7	1308.9
162.5°	1330.9	1329.6	1328.4	1327.2	1328.4	1329.6	1330.9	1332.1	1332.0	1330.7	1329.4
165°	1358.6	1357.6	1356.6	1355.7	1356.6	1357.6	1358.6	1359.5	1359.3	1357.8	1356.4
167.5°	1380.5	1379.0	1377.5	1376.0	1377.5	1379.0	1380.5	1382.1	1382.1	1380.6	1379.1
170°	1392.5	1390.8	1389.1	1387.4	1389.1	1390.8	1392.5	1394.2	1394.4	1392.9	1391.5
172.5°	1402.1	1400.4	1398.7	1397.0	1398.7	1400.4	1402.1	1403.9	1403.9	1402.2	1400.6
175°	1412.2	1410.5	1408.8	1407.1	1408.8	1410.5	1412.2	1413.9	1413.9	1412.2	1410.5
177.5°	1417.0	1415.5	1413.9	1412.4	1413.9	1415.5	1417.0	1418.6	1418.7	1417.4	1416.0
180°	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9



TEST NUMBER: P332920-830

CATALOG NUMBER: S124RDIP-S575D1205U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	910.2	910.2	910.2	910.2	910.2	910.2	910.2	910.2	910.2	910.2	910.2
2.5°	870.6	872.7	877.3	882.6	887.0	890.9	893.8	897.9	901.7	907.0	912.0
5°	817.7	822.9	830.3	839.1	850.1	857.4	866.6	874.7	886.4	898.1	909.5
7.5°	771.5	777.1	787.9	800.0	813.1	825.1	835.9	850.2	865.7	882.9	901.9
10°	741.5	747.7	760.6	774.5	789.9	801.6	816.3	833.2	850.8	871.7	895.1
12.5°	714.5	720.5	735.9	750.2	766.2	779.1	796.1	813.2	836.7	859.4	886.1
15°	661.9	677.7	695.3	712.2	731.2	747.1	767.5	785.1	807.6	839.4	869.9
17.5°	603.5	620.4	642.2	668.3	693.8	713.3	734.1	756.0	782.7	815.2	850.4
20°	569.5	583.1	607.3	636.3	666.0	693.1	712.2	736.4	763.9	799.1	835.4
22.5°	544.0	555.5	574.5	603.4	635.5	667.0	691.4	715.3	745.7	780.9	820.5
25°	505.7	518.2	534.7	554.5	591.2	624.5	656.5	683.9	716.2	751.4	795.4
27.5°	473.9	484.7	499.8	520.5	545.1	581.9	620.6	652.0	685.0	722.8	766.9
30°	455.1	463.9	476.4	497.3	520.8	553.7	593.0	629.7	663.1	702.3	748.1
32.5°	435.5	444.9	457.0	473.5	498.7	526.5	565.7	605.9	641.3	681.5	726.4
35°	409.3	416.6	427.6	444.5	467.2	491.4	526.2	567.7	605.1	648.0	690.9
37.5°	382.8	391.4	400.1	415.1	433.8	459.8	488.3	530.7	572.1	611.2	653.2
40°	367.8	373.0	382.5	394.6	414.4	437.5	464.3	505.7	547.1	586.1	628.2
42.5°	351.1	356.8	364.9	377.0	394.7	417.3	443.5	479.3	522.5	560.2	598.6
45°	327.8	331.1	339.2	349.5	364.2	386.9	411.1	443.0	483.7	519.6	553.4
47.5°	304.3	307.3	312.3	321.7	338.1	356.4	379.1	407.6	443.4	479.3	507.8
50°	288.2	290.8	295.6	304.3	319.1	337.1	359.4	385.0	417.0	451.5	475.2
52.5°	272.1	273.5	278.0	287.9	300.3	317.9	338.0	361.6	391.4	420.1	444.2
55°	246.5	249.8	252.7	260.0	271.7	288.6	306.6	328.9	352.0	376.3	396.8
57.5°	219.7	223.3	227.5	233.9	243.3	259.0	275.1	293.2	312.9	333.1	350.2
60°	202.1	205.4	209.1	216.4	224.8	237.2	254.9	270.6	285.7	304.0	321.2
62.5°	184.7	188.0	192.3	198.2	206.3	218.2	232.9	246.6	262.2	278.2	291.1
65°	159.2	161.7	165.0	170.5	178.2	188.9	201.0	211.6	225.6	237.2	249.0
67.5°	131.1	136.0	140.3	144.8	151.3	161.2	169.9	180.1	189.6	198.3	209.1
70°	112.5	118.1	122.2	126.9	133.1	141.6	150.0	156.9	164.7	173.1	182.7
72.5°	97.1	101.3	104.5	109.6	115.2	123.1	130.9	136.7	143.0	148.7	158.0
75°	76.6	78.5	80.7	84.7	89.8	95.8	102.0	107.1	110.7	115.8	122.5
77.5°	55.0	58.6	60.0	63.0	66.6	70.2	74.4	78.7	82.2	84.1	89.1
80°	42.1	43.6	45.1	49.1	51.4	55.0	58.0	62.0	63.4	65.3	70.0
82.5°	32.8	33.6	34.6	35.6	36.9	40.6	43.5	46.1	47.6	48.3	51.8
85°	19.0	19.4	19.8	20.2	20.5	20.5	22.0	23.8	26.4	26.4	27.5
87.5°	11.6	11.6	11.2	10.5	10.7	10.3	10.2	9.6	9.9	10.3	10.7
90°	25.5	24.1	22.1	20.2	18.3	16.3	13.9	11.3	8.7	5.9	3.3
92.5°	44.2	43.4	42.0	40.6	39.3	37.9	35.7	32.6	29.6	26.5	23.5
95°	84.0	83.2	81.5	79.8	78.1	76.4	74.5	72.3	70.1	67.9	65.7
97.5°	132.5	131.6	129.6	127.6	125.6	123.7	121.8	120.0	118.3	116.5	114.8
100°	168.1	167.6	165.3	163.2	161.0	158.8	157.2	156.2	155.2	154.3	153.4
102.5°	205.0	204.3	202.4	200.4	198.3	196.3	195.2	194.7	194.4	194.0	193.6
105°	261.4	260.6	259.7	258.6	257.7	256.7	256.1	255.9	255.6	255.4	255.1
107.5°	322.4	321.7	321.6	321.4	321.3	321.1	320.9	320.7	320.4	320.1	319.7
110°	364.2	364.7	364.9	365.1	365.4	365.6	365.5	365.0	364.5	364.0	363.5



TEST NUMBER: P332920-830

CATALOG NUMBER: S124RDIP-S575D1205U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	407.5	407.6	408.0	408.5	408.9	409.3	409.5	409.4	409.3	409.3	409.1
115°	475.0	475.2	475.7	476.3	476.7	477.2	477.4	477.4	477.4	477.4	477.4
117.5°	540.4	541.2	541.5	541.9	542.2	542.5	542.6	542.4	542.2	542.1	541.9
120°	584.7	585.9	586.5	587.3	588.1	588.8	588.6	587.7	586.7	585.7	584.8
122.5°	628.9	629.6	630.0	630.4	630.7	631.0	631.0	630.6	630.2	629.8	629.4
125°	693.8	694.3	694.5	694.7	695.0	695.2	695.3	695.3	695.3	695.3	695.3
127.5°	756.2	756.7	757.1	757.4	757.8	758.3	758.1	757.3	756.6	755.9	755.2
130°	800.0	800.5	800.5	800.5	800.5	800.5	800.1	799.4	798.6	798.0	797.2
132.5°	841.1	841.7	841.9	842.1	842.3	842.4	842.3	841.7	841.2	840.7	840.1
135°	903.0	903.4	903.4	903.4	903.4	903.4	902.7	901.3	899.8	898.3	896.8
137.5°	962.8	963.4	963.0	962.6	962.2	961.9	961.3	960.6	960.0	959.3	958.6
140°	1001.7	1001.9	1001.9	1001.9	1001.9	1001.9	1001.7	1001.3	1000.8	1000.2	999.8
142.5°	1038.7	1038.8	1039.0	1039.2	1039.3	1039.5	1039.4	1038.9	1038.4	1037.9	1037.5
145°	1094.8	1095.0	1094.8	1094.6	1094.3	1094.1	1093.4	1092.5	1091.6	1090.5	1089.6
147.5°	1145.5	1145.7	1145.8	1146.0	1146.2	1146.4	1145.9	1144.7	1143.6	1142.5	1141.2
150°	1177.1	1177.1	1177.1	1177.1	1177.1	1177.1	1176.7	1175.7	1174.8	1173.7	1172.8
152.5°	1206.6	1206.1	1205.9	1205.7	1205.5	1205.3	1204.9	1204.3	1203.7	1203.2	1202.6
155°	1248.2	1247.3	1247.5	1247.7	1248.0	1248.2	1248.3	1248.3	1248.3	1248.3	1248.3
157.5°	1285.4	1284.7	1284.8	1284.8	1284.9	1284.9	1285.2	1285.6	1286.0	1286.5	1286.9
160°	1308.2	1307.5	1307.7	1308.0	1308.2	1308.4	1308.7	1308.9	1309.2	1309.5	1309.7
162.5°	1328.0	1326.7	1327.0	1327.3	1327.5	1327.8	1328.1	1328.8	1329.5	1330.0	1330.7
165°	1354.9	1353.5	1354.0	1354.4	1354.9	1355.4	1356.0	1356.8	1357.4	1358.2	1359.0
167.5°	1377.7	1376.2	1376.2	1376.1	1376.1	1376.0	1376.6	1377.5	1378.6	1379.6	1380.6
170°	1390.0	1388.6	1388.3	1388.0	1387.8	1387.5	1388.0	1389.2	1390.4	1391.7	1392.9
172.5°	1398.9	1397.3	1397.2	1397.2	1397.1	1397.0	1397.6	1398.5	1399.6	1400.6	1401.7
175°	1408.8	1407.1	1407.4	1407.6	1407.9	1408.1	1408.8	1410.0	1411.3	1412.5	1413.7
177.5°	1414.7	1413.2	1413.2	1413.2	1413.2	1413.2	1413.7	1414.8	1415.7	1416.6	1417.7
180°	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9



TEST NUMBER: P332920-830

CATALOG NUMBER: S124RDIP-S575D1205U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	910.2	910.2	910.2	910.2	910.2	910.2	910.2	910.2	910.2	910.2	910.2
2.5°	915.8	918.4	921.3	926.9	931.6	933.7	937.8	940.8	939.8	944.0	951.0
5°	919.4	929.3	940.7	952.3	965.5	976.6	985.4	994.2	1001.2	1009.6	1022.1
7.5°	918.8	936.4	955.5	976.6	998.2	1016.9	1034.3	1051.9	1067.4	1084.6	1106.9
10°	916.4	939.9	963.7	991.3	1018.8	1044.8	1068.3	1090.2	1111.2	1133.5	1161.8
12.5°	913.8	940.8	969.6	1002.7	1037.0	1068.3	1095.9	1127.6	1153.7	1182.5	1215.2
15°	902.1	938.5	977.7	1020.6	1061.7	1103.8	1141.6	1180.5	1216.8	1251.2	1292.3
17.5°	888.8	930.7	976.9	1027.7	1077.0	1128.2	1173.1	1222.1	1259.1	1305.4	1343.6
20°	878.0	923.0	972.5	1029.4	1085.5	1142.4	1191.8	1241.7	1283.6	1330.1	1378.6
22.5°	864.8	914.3	967.9	1026.7	1085.5	1147.6	1202.4	1252.0	1303.8	1356.2	1406.1
25°	843.5	894.8	951.7	1016.2	1083.6	1147.1	1205.8	1267.4	1323.1	1380.0	1424.7
27.5°	817.4	871.3	931.2	997.8	1067.1	1132.0	1201.1	1266.8	1322.9	1377.5	1416.5
30°	796.5	853.4	911.0	978.5	1050.3	1120.0	1194.0	1259.7	1318.7	1367.9	1389.9
32.5°	775.1	829.1	888.3	956.7	1030.4	1105.3	1178.8	1245.9	1300.5	1330.0	1330.6
35°	737.8	788.4	850.1	917.2	992.7	1074.1	1148.6	1214.6	1247.9	1250.6	1214.6
37.5°	697.2	743.7	801.8	869.0	951.7	1032.7	1108.7	1152.7	1163.9	1126.6	1060.2
40°	668.2	711.1	767.2	836.1	918.3	1001.9	1071.2	1103.4	1091.7	1031.2	957.2
42.5°	637.6	677.6	731.7	799.7	882.2	966.7	1025.8	1043.0	1011.9	942.1	855.4
45°	587.9	624.5	678.1	746.7	825.9	905.1	949.8	941.0	889.3	806.4	709.3
47.5°	536.0	571.5	619.6	683.1	764.2	832.5	862.8	836.3	762.7	671.6	592.5
50°	501.7	538.0	582.4	642.9	717.0	783.0	802.4	762.0	680.2	592.7	520.0
52.5°	468.0	499.0	542.4	600.9	671.8	727.5	737.8	691.4	606.9	528.4	464.0
55°	416.6	444.9	481.5	536.5	597.8	645.1	639.6	579.8	503.1	436.0	385.4
57.5°	366.9	388.2	422.1	473.6	527.4	559.2	539.0	488.1	416.7	361.7	319.1
60°	334.1	353.9	385.4	430.6	477.9	495.8	478.9	423.6	367.1	316.9	280.9
62.5°	303.0	320.5	347.6	389.5	427.6	438.3	420.3	371.9	321.0	278.1	248.4
65°	257.8	273.9	297.1	326.8	353.2	358.3	346.6	297.1	258.5	222.6	202.1
67.5°	216.8	227.3	245.4	271.1	285.1	288.1	265.4	234.3	200.4	178.3	162.9
70°	189.3	196.5	213.4	227.3	238.7	239.1	218.2	193.2	167.2	149.3	137.9
72.5°	162.5	169.6	182.4	191.9	200.6	197.7	178.6	158.9	137.9	124.3	115.8
75°	125.5	131.7	138.3	142.7	142.7	139.0	125.1	110.4	98.3	90.2	87.7
77.5°	91.1	96.3	98.5	97.8	96.5	90.8	82.0	72.4	68.1	64.3	62.3
80°	71.5	73.7	74.5	72.6	70.4	63.8	58.0	53.9	49.9	48.4	47.7
82.5°	53.1	55.0	53.1	53.5	48.7	43.3	40.1	38.6	36.9	36.4	35.6
85°	28.3	27.9	27.1	25.3	22.0	21.3	20.9	20.5	19.8	20.2	19.4
87.5°	10.8	10.6	9.9	10.2	10.6	10.4	11.1	11.5	11.9	11.9	12.7
90°	5.9	8.7	11.3	13.9	16.3	18.3	20.2	22.1	24.1	25.5	27.1
92.5°	26.5	29.6	32.6	35.7	37.9	39.3	40.6	42.0	43.4	44.2	45.1
95°	67.9	70.1	72.3	74.5	76.4	78.1	79.8	81.5	83.2	84.0	84.6
97.5°	116.5	118.3	120.0	121.8	123.7	125.6	127.6	129.6	131.6	132.5	133.4
100°	154.3	155.2	156.2	157.2	158.8	161.0	163.2	165.3	167.6	168.1	168.5
102.5°	194.0	194.4	194.7	195.2	196.3	198.3	200.4	202.4	204.3	205.0	205.7
105°	255.4	255.6	255.9	256.1	256.7	257.7	258.6	259.7	260.6	261.4	262.1
107.5°	320.1	320.4	320.7	320.9	321.1	321.3	321.4	321.6	321.7	322.4	323.1
110°	364.0	364.5	365.0	365.5	365.6	365.4	365.1	364.9	364.7	364.2	363.6



TEST NUMBER: P332920-830

CATALOG NUMBER: S124RDIP-S575D1205U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	409.3	409.3	409.4	409.5	409.3	408.9	408.5	408.0	407.6	407.5	407.4
115°	477.4	477.4	477.4	477.4	477.2	476.7	476.3	475.7	475.2	475.0	474.8
117.5°	542.1	542.2	542.4	542.6	542.5	542.2	541.9	541.5	541.2	540.4	539.5
120°	585.7	586.7	587.7	588.6	588.8	588.1	587.3	586.5	585.9	584.7	583.4
122.5°	629.8	630.2	630.6	631.0	631.0	630.7	630.4	630.0	629.6	628.9	628.0
125°	695.3	695.3	695.3	695.3	695.2	695.0	694.7	694.5	694.3	693.8	693.2
127.5°	755.9	756.6	757.3	758.1	758.3	757.8	757.4	757.1	756.7	756.2	755.7
130°	798.0	798.6	799.4	800.1	800.5	800.5	800.5	800.5	800.5	800.0	799.5
132.5°	840.7	841.2	841.7	842.3	842.4	842.3	842.1	841.9	841.7	841.1	840.7
135°	898.3	899.8	901.3	902.7	903.4	903.4	903.4	903.4	903.4	903.0	902.5
137.5°	959.3	960.0	960.6	961.3	961.9	962.2	962.6	963.0	963.4	962.8	962.1
140°	1000.2	1000.8	1001.3	1001.7	1001.9	1001.9	1001.9	1001.9	1001.9	1001.7	1001.5
142.5°	1037.9	1038.4	1038.9	1039.4	1039.5	1039.3	1039.2	1039.0	1038.8	1038.7	1038.7
145°	1090.5	1091.6	1092.5	1093.4	1094.1	1094.3	1094.6	1094.8	1095.0	1094.8	1094.6
147.5°	1142.5	1143.6	1144.7	1145.9	1146.4	1146.2	1146.0	1145.8	1145.7	1145.5	1145.3
150°	1173.7	1174.8	1175.7	1176.7	1177.1	1177.1	1177.1	1177.1	1177.1	1177.1	1177.1
152.5°	1203.2	1203.7	1204.3	1204.9	1205.3	1205.5	1205.7	1205.9	1206.1	1206.6	1207.2
155°	1248.3	1248.3	1248.3	1248.3	1248.2	1248.0	1247.7	1247.5	1247.3	1248.2	1249.2
157.5°	1286.5	1286.0	1285.6	1285.2	1284.9	1284.9	1284.8	1284.8	1284.7	1285.4	1286.2
160°	1309.5	1309.2	1308.9	1308.7	1308.4	1308.2	1308.0	1307.7	1307.5	1308.2	1308.9
162.5°	1330.0	1329.5	1328.8	1328.1	1327.8	1327.5	1327.3	1327.0	1326.7	1328.0	1329.4
165°	1358.2	1357.4	1356.8	1356.0	1355.4	1354.9	1354.4	1354.0	1353.5	1354.9	1356.4
167.5°	1379.6	1378.6	1377.5	1376.6	1376.0	1376.1	1376.1	1376.2	1376.2	1377.7	1379.1
170°	1391.7	1390.4	1389.2	1388.0	1387.5	1387.8	1388.0	1388.3	1388.6	1390.0	1391.5
172.5°	1400.6	1399.6	1398.5	1397.6	1397.0	1397.1	1397.2	1397.2	1397.3	1398.9	1400.6
175°	1412.5	1411.3	1410.0	1408.8	1408.1	1407.9	1407.6	1407.4	1407.1	1408.8	1410.5
177.5°	1416.6	1415.7	1414.8	1413.7	1413.2	1413.2	1413.2	1413.2	1413.2	1414.7	1416.0
180°	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9



TEST NUMBER: P332920-830

CATALOG NUMBER: S124RDIP-S575D1205U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	910.2	910.2	910.2	910.2	910.2	910.2	910.2
2.5°	954.8	956.0	956.9	959.8	960.1	962.7	960.1
5°	1033.8	1039.0	1047.0	1055.1	1055.8	1060.9	1051.8
7.5°	1122.4	1134.3	1141.7	1154.7	1159.9	1163.1	1157.8
10°	1183.5	1194.4	1213.9	1223.4	1232.9	1234.4	1230.0
12.5°	1242.4	1259.8	1275.2	1293.3	1292.8	1305.7	1301.0
15°	1321.0	1338.9	1360.2	1380.4	1387.7	1387.7	1393.5
17.5°	1377.0	1409.9	1431.9	1447.7	1465.1	1468.1	1466.0
20°	1414.9	1450.4	1473.9	1494.4	1506.2	1509.5	1509.5
22.5°	1443.0	1473.3	1496.2	1514.7	1524.4	1528.2	1527.0
25°	1462.5	1488.6	1502.5	1508.0	1510.5	1509.8	1502.9
27.5°	1435.8	1434.6	1425.8	1408.9	1396.3	1388.6	1379.8
30°	1384.8	1365.6	1343.7	1319.5	1288.3	1264.4	1257.2
32.5°	1308.8	1265.9	1228.7	1188.4	1154.8	1131.0	1121.0
35°	1161.8	1093.9	1038.6	990.1	955.0	932.9	925.6
37.5°	987.4	921.7	853.2	806.3	777.0	754.8	746.5
40°	876.5	804.9	745.2	701.2	671.1	649.5	649.1
42.5°	775.2	707.0	650.7	619.1	586.6	572.3	572.2
45°	634.8	580.1	532.4	507.6	488.1	476.4	473.1
47.5°	525.6	480.4	448.7	428.8	412.9	405.5	400.6
50°	464.3	424.7	399.4	382.1	373.3	363.8	363.1
52.5°	413.2	381.3	361.6	347.5	336.4	330.6	330.8
55°	347.3	322.0	308.0	297.4	288.6	284.2	282.4
57.5°	292.6	273.6	263.4	253.7	250.0	246.5	245.5
60°	258.5	245.7	236.2	228.5	223.0	221.9	221.5
62.5°	230.4	217.0	210.4	204.4	200.4	198.7	198.0
65°	189.9	180.0	174.2	169.5	168.0	165.4	165.0
67.5°	153.2	147.2	143.4	140.1	138.0	137.9	137.9
70°	130.5	127.2	123.9	122.2	121.0	120.3	120.3
72.5°	111.2	108.8	106.0	105.1	104.9	104.2	103.9
75°	84.7	82.2	82.5	80.7	79.2	77.4	76.3
77.5°	60.0	58.2	57.9	57.7	56.4	56.2	56.7
80°	46.6	44.8	44.4	44.8	44.4	43.3	43.3
82.5°	35.4	33.9	33.6	33.3	32.9	33.3	32.7
85°	19.0	18.4	18.4	18.4	19.0	18.7	18.4
87.5°	12.4	12.4	12.9	12.7	12.8	12.6	13.0
90°	28.5	30.0	30.9	31.4	31.9	32.3	32.9
92.5°	46.0	46.8	47.4	47.8	48.1	48.4	48.6
95°	85.4	86.1	86.5	86.5	86.5	86.5	86.5
97.5°	134.2	135.2	135.5	135.5	135.5	135.5	135.5
100°	169.0	169.5	169.8	169.8	169.8	169.8	169.8
102.5°	206.4	207.1	207.5	207.7	207.9	208.1	208.3
105°	262.8	263.5	264.3	265.0	265.7	266.5	267.2
107.5°	323.8	324.4	324.8	324.7	324.7	324.6	324.6
110°	363.2	362.7	362.8	363.5	364.3	365.0	365.7



TEST NUMBER: P332920-830

CATALOG NUMBER: S124RDIP-S575D1205U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	407.3	407.2	407.2	407.4	407.5	407.6	407.8
115°	474.5	474.3	474.0	473.8	473.5	473.3	473.1
117.5°	538.7	537.8	537.2	536.7	536.2	535.7	535.3
120°	582.2	581.0	580.6	581.1	581.5	582.1	582.6
122.5°	627.2	626.3	625.5	624.6	623.8	622.8	622.0
125°	692.8	692.3	691.8	691.4	690.9	690.3	689.8
127.5°	755.3	754.7	754.3	753.9	753.5	753.1	752.7
130°	799.0	798.5	797.8	796.8	795.9	794.8	793.9
132.5°	840.2	839.7	839.2	838.9	838.5	838.1	837.7
135°	901.9	901.4	900.9	900.1	899.4	898.6	898.0
137.5°	961.5	960.9	960.6	960.8	960.9	961.1	961.2
140°	1001.3	1001.0	1000.8	1000.5	1000.2	1000.0	999.8
142.5°	1038.6	1038.6	1038.5	1038.5	1038.4	1038.4	1038.3
145°	1094.3	1094.1	1093.5	1092.9	1092.1	1091.4	1090.7
147.5°	1145.1	1144.8	1144.6	1144.4	1144.2	1143.9	1143.7
150°	1177.1	1177.1	1177.0	1176.8	1176.6	1176.3	1176.1
152.5°	1207.9	1208.4	1208.4	1207.8	1207.1	1206.5	1205.9
155°	1250.2	1251.1	1251.1	1250.2	1249.2	1248.2	1247.3
157.5°	1286.9	1287.6	1287.6	1286.8	1285.9	1285.1	1284.3
160°	1309.7	1310.4	1310.1	1308.9	1307.7	1306.6	1305.3
162.5°	1330.7	1332.0	1332.1	1330.9	1329.6	1328.4	1327.2
165°	1357.8	1359.3	1359.5	1358.6	1357.6	1356.6	1355.7
167.5°	1380.6	1382.1	1382.1	1380.5	1379.0	1377.5	1376.0
170°	1392.9	1394.4	1394.2	1392.5	1390.8	1389.1	1387.4
172.5°	1402.2	1403.9	1403.9	1402.1	1400.4	1398.7	1397.0
175°	1412.2	1413.9	1413.9	1412.2	1410.5	1408.8	1407.1
177.5°	1417.4	1418.7	1418.6	1417.0	1415.5	1413.9	1412.4
180°	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9

(END OF REPORT)