

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332921-830

Luminaire Tested: **S124RDIP-S575D1205U830-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332921-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIP-S575D1205U830-4F0-1E-UDD-A4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 575 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6358.3 lumens  
Efficiency: N/A  
Efficacy: 128.7 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 49.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332921-830

CATALOG NUMBER: S124RDIP-S575D1205U830-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P332921-830

CATALOG NUMBER: S124RDIP-S575D1205U830-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	43	43	43	36
1	95	91	87	84	86	83	79	77	67	65	63	52	51	50	39	38	37	31
2	87	80	74	69	78	72	68	63	59	55	52	46	44	42	35	33	32	27
3	79	70	63	58	72	64	58	53	52	48	44	41	38	36	31	29	28	23
4	73	62	55	49	66	57	50	45	46	42	38	37	34	31	28	26	24	20
5	67	56	48	42	60	51	44	39	42	37	33	33	30	27	25	23	21	17
6	61	50	42	37	56	46	39	34	38	32	29	30	26	24	23	20	19	15
7	57	45	37	32	51	41	35	30	34	29	25	27	24	21	21	18	17	14
8	53	41	33	28	48	37	31	26	31	26	22	25	21	19	19	17	15	12
9	49	37	30	25	44	34	28	23	28	23	20	23	19	17	18	15	13	11
10	46	34	27	22	41	31	25	21	26	21	18	21	18	15	17	14	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	7348	7348	7348	7348
5°	8524	7370	6515	7370
10°	10083	7338	5814	7338
15°	11646	7270	4996	7270
20°	12968	7177	4517	7177
25°	13387	7085	4195	7085
30°	11719	6974	3999	6974
35°	9122	6809	3882	6809
40°	6841	6620	3818	6620
45°	5401	6318	3785	6318
50°	4560	5968	3676	5968
55°	3975	5585	3478	5585
60°	3576	5186	3079	5186
65°	3152	4756	2648	4756
70°	2840	4312	2389	4312
75°	2380	3821	2037	3821
80°	2013	3254	1911	3254
85°	1704	2547	1704	2547



TEST NUMBER: P332921-830

CATALOG NUMBER: S124RDIP-S575D1205U830-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	88.2	1.4
10°-20°	266.0	4.2
20°-30°	416.1	6.5
30°-40°	462.6	7.3
40°-50°	410.4	6.5
50°-60°	319.8	5.0
60°-70°	209.4	3.3
70°-80°	103.0	1.6
80°-90°	28.5	0.4
90°-100°	402.7	6.3
100°-110°	838.0	13.2
110°-120°	750.6	11.8
120°-130°	631.4	9.9
130°-140°	526.5	8.3
140°-150°	402.2	6.3
150°-160°	282.7	4.4
160°-170°	166.3	2.6
170°-180°	54.1	0.9
0°-30°	770.3	12.1
0°-40°	1232.9	19.4
0°-60°	1963.1	30.9
0°-90°	2303.9	36.2
90°-120°	1991.3	31.3
90°-150°	3551.4	55.9
90°-180°	4054.0	63.8
0°-180°	6358.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	910	910	910	910	910	
5°	1052	910	804	910	1052	106
15°	1394	870	598	870	1394	396
25°	1503	795	471	795	1503	667
35°	926	691	394	691	926	580
45°	473	553	332	553	473	375
55°	282	397	247	397	282	257
65°	165	249	139	249	165	166
75°	76	122	65	122	76	84
85°	18	28	18	28	18	21
90°	23	1	23	1	23	19
95°	267	36	267	36	267	415
105°	1541	128	1541	128	1541	1524
115°	1480	226	1480	226	1480	1469
125°	1181	314	1181	314	1181	1073
135°	1056	373	1056	373	1056	815
145°	862	430	862	430	862	546
155°	722	490	722	490	722	337
165°	630	533	630	533	630	180
175°	567	556	567	556	567	55
180°	558	558	558	558	558	



TEST NUMBER: P332921-830

CATALOG NUMBER: S124RDIP-S575D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	910.2	910.2	910.2	910.2	910.2	910.2	910.2	910.2	910.2	910.2	910.2
2.5°	960.1	962.7	960.1	959.8	956.9	956.0	954.8	951.0	944.0	939.8	940.8
5°	1051.8	1060.9	1055.8	1055.1	1047.0	1039.0	1033.8	1022.1	1009.6	1001.2	994.2
7.5°	1157.8	1163.1	1159.9	1154.7	1141.7	1134.3	1122.4	1106.9	1084.6	1067.4	1051.9
10°	1230.0	1234.4	1232.9	1223.4	1213.9	1194.4	1183.5	1161.8	1133.5	1111.2	1090.2
12.5°	1301.0	1305.7	1292.8	1293.3	1275.2	1259.8	1242.4	1215.2	1182.5	1153.7	1127.6
15°	1393.5	1387.7	1387.7	1380.4	1360.2	1338.9	1321.0	1292.3	1251.2	1216.8	1180.5
17.5°	1466.0	1468.1	1465.1	1447.7	1431.9	1409.9	1377.0	1343.6	1305.4	1259.1	1222.1
20°	1509.5	1509.5	1506.2	1494.4	1473.9	1450.4	1414.9	1378.6	1330.1	1283.6	1241.7
22.5°	1527.0	1528.2	1524.4	1514.7	1496.2	1473.3	1443.0	1406.1	1356.2	1303.8	1252.0
25°	1502.9	1509.8	1510.5	1508.0	1502.5	1488.6	1462.5	1424.7	1380.0	1323.1	1267.4
27.5°	1379.8	1388.6	1396.3	1408.9	1425.8	1434.6	1435.8	1416.5	1377.5	1322.9	1266.8
30°	1257.2	1264.4	1288.3	1319.5	1343.7	1365.6	1384.8	1389.9	1367.9	1318.7	1259.7
32.5°	1121.0	1131.0	1154.8	1188.4	1228.7	1265.9	1308.8	1330.6	1330.0	1300.5	1245.9
35°	925.6	932.9	955.0	990.1	1038.6	1093.9	1161.8	1214.6	1250.6	1247.9	1214.6
37.5°	746.5	754.8	777.0	806.3	853.2	921.7	987.4	1060.2	1126.6	1163.9	1152.7
40°	649.1	649.5	671.1	701.2	745.2	804.9	876.5	957.2	1031.2	1091.7	1103.4
42.5°	572.2	572.3	586.6	619.1	650.7	707.0	775.2	855.4	942.1	1011.9	1043.0
45°	473.1	476.4	488.1	507.6	532.4	580.1	634.8	709.3	806.4	889.3	941.0
47.5°	400.6	405.5	412.9	428.8	448.7	480.4	525.6	592.5	671.6	762.7	836.3
50°	363.1	363.8	373.3	382.1	399.4	424.7	464.3	520.0	592.7	680.2	762.0
52.5°	330.8	330.6	336.4	347.5	361.6	381.3	413.2	464.0	528.4	606.9	691.4
55°	282.4	284.2	288.6	297.4	308.0	322.0	347.3	385.4	436.0	503.1	579.8
57.5°	245.5	246.5	250.0	253.7	263.4	273.6	292.6	319.1	361.7	416.7	488.1
60°	221.5	221.9	223.0	228.5	236.2	245.7	258.5	280.9	316.9	367.1	423.6
62.5°	198.0	198.7	200.4	204.4	210.4	217.0	230.4	248.4	278.1	321.0	371.9
65°	165.0	165.4	168.0	169.5	174.2	180.0	189.9	202.1	222.6	258.5	297.1
67.5°	137.9	137.9	138.0	140.1	143.4	147.2	153.2	162.9	178.3	200.4	234.3
70°	120.3	120.3	121.0	122.2	123.9	127.2	130.5	137.9	149.3	167.2	193.2
72.5°	103.9	104.2	104.9	105.1	106.0	108.8	111.2	115.8	124.3	137.9	158.9
75°	76.3	77.4	79.2	80.7	82.5	82.2	84.7	87.7	90.2	98.3	110.4
77.5°	56.7	56.2	56.4	57.7	57.9	58.2	60.0	62.3	64.3	68.1	72.4
80°	43.3	43.3	44.4	44.8	44.4	44.8	46.6	47.7	48.4	49.9	53.9
82.5°	32.7	33.3	32.9	33.3	33.6	33.9	35.4	35.6	36.4	36.9	38.6
85°	18.4	18.7	19.0	18.4	18.4	18.4	19.0	19.4	20.2	19.8	20.5
87.5°	11.0	10.7	11.3	11.0	11.1	10.8	10.9	11.3	10.5	11.0	10.6
90°	23.0	23.0	24.1	23.0	21.9	21.9	20.8	19.7	18.7	19.7	17.5
92.5°	84.4	84.4	88.0	94.0	106.9	128.8	161.8	215.1	289.4	347.4	304.1
95°	267.2	281.4	301.2	335.2	388.8	495.0	641.8	811.5	917.8	892.6	673.5
97.5°	714.4	737.1	770.0	835.8	914.5	1028.9	1136.0	1199.1	1153.1	940.2	630.4
100°	1004.4	1013.1	1045.9	1112.8	1208.1	1289.1	1342.7	1320.9	1160.9	880.5	571.7
102.5°	1256.7	1263.7	1298.3	1346.7	1405.1	1438.9	1423.3	1314.8	1095.2	806.1	532.3
105°	1541.0	1547.6	1562.9	1571.7	1569.4	1524.6	1416.2	1226.6	975.8	718.5	498.3
107.5°	1646.6	1643.7	1632.8	1607.8	1553.7	1456.0	1303.3	1101.5	879.5	669.4	492.2
110°	1648.3	1638.5	1618.7	1572.7	1495.0	1374.5	1215.7	1026.2	831.3	652.8	494.0



TEST NUMBER: P332921-830

CATALOG NUMBER: S124RDIP-S575D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1596.7	1580.6	1553.0	1497.4	1409.1	1288.6	1138.6	971.0	804.1	644.9	499.2
115°	1479.7	1470.9	1435.9	1370.2	1283.6	1178.5	1050.4	915.6	778.7	640.7	509.3
117.5°	1361.1	1354.3	1318.9	1263.7	1189.9	1100.7	999.9	888.4	767.3	639.6	520.0
120°	1294.6	1282.5	1254.1	1205.9	1143.4	1065.6	978.1	876.2	761.2	639.6	527.9
122.5°	1242.0	1229.9	1205.9	1164.7	1111.9	1043.8	964.0	865.6	754.2	638.8	535.8
125°	1180.6	1174.1	1153.3	1121.5	1077.7	1017.5	941.9	847.7	742.5	637.4	547.6
127.5°	1144.7	1138.2	1120.7	1092.4	1048.4	991.2	915.9	825.8	727.0	635.0	557.0
130°	1123.7	1117.1	1099.6	1072.2	1027.4	969.3	894.8	808.3	717.4	634.1	564.0
132.5°	1100.0	1093.4	1076.9	1045.9	1001.9	943.9	871.2	789.9	708.6	633.3	570.1
135°	1055.8	1049.2	1031.7	1001.1	957.2	902.5	835.7	764.5	695.5	632.0	579.4
137.5°	1001.1	993.2	978.7	948.5	907.5	858.0	801.7	741.5	684.1	631.7	584.8
140°	961.6	952.8	937.5	913.4	875.1	829.1	779.8	728.3	678.0	630.8	589.3
142.5°	919.5	913.4	899.8	877.5	843.6	803.7	761.4	716.0	672.7	630.8	592.8
145°	862.0	856.5	845.6	826.9	799.6	768.8	736.0	698.8	663.7	628.7	594.7
147.5°	810.9	809.0	800.6	784.7	764.5	740.4	714.1	684.6	655.6	624.7	595.8
150°	782.0	780.9	774.3	760.1	742.5	722.8	701.0	675.8	649.5	622.1	595.8
152.5°	755.7	754.6	750.6	739.0	724.2	707.9	687.8	666.1	642.4	617.7	594.1
155°	721.8	721.8	718.5	709.7	698.8	685.6	669.2	651.7	632.0	611.1	591.4
157.5°	692.0	692.0	690.0	683.4	675.1	664.6	650.8	636.1	621.2	604.4	588.6
160°	673.5	673.5	672.5	665.9	659.3	650.5	638.5	626.5	613.3	599.1	586.0
162.5°	656.0	657.0	655.8	649.2	644.4	636.6	627.2	616.8	606.3	593.8	583.3
165°	629.8	630.8	632.0	627.5	623.2	617.7	610.0	603.5	594.7	586.0	578.2
167.5°	609.0	609.8	610.0	607.2	605.0	601.7	595.6	590.6	584.2	578.1	573.1
170°	595.8	595.8	596.9	595.8	593.6	590.3	586.0	582.7	577.2	572.8	569.5
172.5°	582.7	584.4	585.5	584.4	583.1	580.7	578.1	575.6	571.1	567.5	566.0
175°	567.3	569.5	571.7	569.5	569.5	569.5	567.3	566.3	564.0	561.8	561.8
177.5°	558.4	560.1	561.8	561.0	561.8	561.0	561.0	560.1	559.2	558.4	558.4
180°	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5



TEST NUMBER: P332921-830

CATALOG NUMBER: S124RDIP-S575D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	910.2	910.2	910.2	910.2	910.2	910.2	910.2	910.2	910.2	910.2	910.2
2.5°	937.8	933.7	931.6	926.9	921.3	918.4	915.8	912.0	907.0	901.7	897.9
5°	985.4	976.6	965.5	952.3	940.7	929.3	919.4	909.5	898.1	886.4	874.7
7.5°	1034.3	1016.9	998.2	976.6	955.5	936.4	918.8	901.9	882.9	865.7	850.2
10°	1068.3	1044.8	1018.8	991.3	963.7	939.9	916.4	895.1	871.7	850.8	833.2
12.5°	1095.9	1068.3	1037.0	1002.7	969.6	940.8	913.8	886.1	859.4	836.7	813.2
15°	1141.6	1103.8	1061.7	1020.6	977.7	938.5	902.1	869.9	839.4	807.6	785.1
17.5°	1173.1	1128.2	1077.0	1027.7	976.9	930.7	888.8	850.4	815.2	782.7	756.0
20°	1191.8	1142.4	1085.5	1029.4	972.5	923.0	878.0	835.4	799.1	763.9	736.4
22.5°	1202.4	1147.6	1085.5	1026.7	967.9	914.3	864.8	820.5	780.9	745.7	715.3
25°	1205.8	1147.1	1083.6	1016.2	951.7	894.8	843.5	795.4	751.4	716.2	683.9
27.5°	1201.1	1132.0	1067.1	997.8	931.2	871.3	817.4	766.9	722.8	685.0	652.0
30°	1194.0	1120.0	1050.3	978.5	911.0	853.4	796.5	748.1	702.3	663.1	629.7
32.5°	1178.8	1105.3	1030.4	956.7	888.3	829.1	775.1	726.4	681.5	641.3	605.9
35°	1148.6	1074.1	992.7	917.2	850.1	788.4	737.8	690.9	648.0	605.1	567.7
37.5°	1108.7	1032.7	951.7	869.0	801.8	743.7	697.2	653.2	611.2	572.1	530.7
40°	1071.2	1001.9	918.3	836.1	767.2	711.1	668.2	628.2	586.1	547.1	505.7
42.5°	1025.8	966.7	882.2	799.7	731.7	677.6	637.6	598.6	560.2	522.5	479.3
45°	949.8	905.1	825.9	746.7	678.1	624.5	587.9	553.4	519.6	483.7	443.0
47.5°	862.8	832.5	764.2	683.1	619.6	571.5	536.0	507.8	479.3	443.4	407.6
50°	802.4	783.0	717.0	642.9	582.4	538.0	501.7	475.2	451.5	417.0	385.0
52.5°	737.8	727.5	671.8	600.9	542.4	499.0	468.0	444.2	420.1	391.4	361.6
55°	639.6	645.1	597.8	536.5	481.5	444.9	416.6	396.8	376.3	352.0	328.9
57.5°	539.0	559.2	527.4	473.6	422.1	388.2	366.9	350.2	333.1	312.9	293.2
60°	478.9	495.8	477.9	430.6	385.4	353.9	334.1	321.2	304.0	285.7	270.6
62.5°	420.3	438.3	427.6	389.5	347.6	320.5	303.0	291.1	278.2	262.2	246.6
65°	346.6	358.3	353.2	326.8	297.1	273.9	257.8	249.0	237.2	225.6	211.6
67.5°	265.4	288.1	285.1	271.1	245.4	227.3	216.8	209.1	198.3	189.6	180.1
70°	218.2	239.1	238.7	227.3	213.4	196.5	189.3	182.7	173.1	164.7	156.9
72.5°	178.6	197.7	200.6	191.9	182.4	169.6	162.5	158.0	148.7	143.0	136.7
75°	125.1	139.0	142.7	142.7	138.3	131.7	125.5	122.5	115.8	110.7	107.1
77.5°	82.0	90.8	96.5	97.8	98.5	96.3	91.1	89.1	84.1	82.2	78.7
80°	58.0	63.8	70.4	72.6	74.5	73.7	71.5	70.0	65.3	63.4	62.0
82.5°	40.1	43.3	48.7	53.5	53.1	55.0	53.1	51.8	48.3	47.6	46.1
85°	20.9	21.3	22.0	25.3	27.1	27.9	28.3	27.5	26.4	26.4	23.8
87.5°	10.1	9.8	9.0	9.0	9.1	10.1	10.4	10.2	9.7	9.5	8.9
90°	15.4	15.4	8.8	8.8	7.6	6.6	3.3	1.1	3.3	6.6	7.6
92.5°	221.2	136.3	80.6	57.9	41.8	28.5	18.2	12.4	18.2	28.5	41.8
95°	411.8	232.1	137.0	90.9	64.7	50.4	39.4	36.1	39.4	50.4	64.7
97.5°	370.2	221.9	148.5	110.0	87.4	74.3	64.8	64.8	64.8	74.3	87.4
100°	348.3	224.5	159.9	124.9	104.1	90.9	83.2	83.2	83.2	90.9	104.1
102.5°	342.1	233.3	174.8	141.5	121.6	109.3	102.5	100.8	102.5	109.3	121.6
105°	345.0	254.1	201.5	169.8	150.1	137.0	131.4	128.2	131.4	137.0	150.1
107.5°	361.2	278.4	230.3	198.9	180.0	166.1	160.5	158.3	160.5	166.1	180.0
110°	373.4	296.8	248.6	219.0	199.3	186.2	180.7	178.5	180.7	186.2	199.3





TEST NUMBER: P332921-830

CATALOG NUMBER: S124RDIP-S575D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	386.6	314.3	267.9	238.4	218.6	206.3	200.0	197.8	200.0	206.3	218.6
115°	407.5	341.7	297.9	268.3	247.5	236.6	228.9	225.6	228.9	236.6	247.5
117.5°	428.7	368.3	326.6	296.0	276.4	264.4	257.6	254.5	257.6	264.4	276.4
120°	443.6	386.6	345.0	314.3	295.7	283.7	276.0	273.8	276.0	283.7	295.7
122.5°	457.6	404.2	362.5	332.7	312.4	301.2	293.5	291.3	293.5	301.2	312.4
125°	478.6	428.2	388.8	358.2	337.3	325.3	318.7	314.3	318.7	325.3	337.3
127.5°	496.8	450.5	412.5	381.5	359.9	346.1	338.2	334.7	338.2	346.1	359.9
130°	508.2	465.5	428.2	396.4	375.7	359.2	350.4	346.1	350.4	359.2	375.7
132.5°	519.6	477.8	440.5	410.5	388.0	372.4	361.0	357.5	361.0	372.4	388.0
135°	534.5	495.0	458.9	430.5	407.5	388.8	377.9	373.4	377.9	388.8	407.5
137.5°	545.0	508.2	474.5	447.3	423.4	405.7	393.6	389.5	393.6	405.7	423.4
140°	552.0	517.0	484.1	457.8	434.8	416.2	404.2	400.9	404.2	416.2	434.8
142.5°	557.2	524.8	492.9	467.4	445.4	427.5	416.4	413.1	416.4	427.5	445.4
145°	563.0	533.4	504.9	480.8	460.0	444.7	433.8	430.5	433.8	444.7	460.0
147.5°	568.0	542.2	515.4	493.7	476.5	460.6	451.0	449.9	451.0	460.6	476.5
150°	570.6	546.5	522.5	501.6	485.2	472.0	463.3	462.2	463.3	472.0	485.2
152.5°	572.4	550.1	528.6	509.5	494.8	482.6	473.8	473.5	473.8	482.6	494.8
155°	573.9	555.3	536.7	520.3	508.2	497.2	490.7	489.6	490.7	497.2	508.2
157.5°	573.9	559.0	543.3	530.3	519.8	511.2	505.1	505.1	505.1	511.2	519.8
160°	573.9	560.7	547.6	535.6	526.8	519.2	514.7	514.7	514.7	519.2	526.8
162.5°	573.9	562.5	550.3	540.8	532.9	526.1	522.6	523.5	522.6	526.1	532.9
165°	571.7	563.0	553.1	546.5	541.0	535.6	533.4	533.4	533.4	535.6	541.0
167.5°	569.1	562.7	555.5	550.4	547.4	543.3	542.2	543.3	542.2	543.3	547.4
170°	567.3	561.8	556.4	553.1	550.9	547.6	546.5	547.6	546.5	547.6	550.9
172.5°	565.6	561.0	557.2	554.9	553.6	551.1	550.9	552.0	550.9	551.1	553.6
175°	563.0	559.7	557.5	557.5	556.4	555.3	555.3	556.4	555.3	555.3	556.4
177.5°	560.1	558.4	557.5	557.5	557.5	556.6	557.5	558.4	557.5	556.6	557.5
180°	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5



TEST NUMBER: P332921-830

CATALOG NUMBER: S124RDIP-S575D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	910.2	910.2	910.2	910.2	910.2	910.2	910.2	910.2	910.2	910.2	910.2
2.5°	893.8	890.9	887.0	882.6	877.3	872.7	870.6	872.3	873.3	870.9	870.6
5°	866.6	857.4	850.1	839.1	830.3	822.9	817.7	815.6	816.3	810.5	809.0
7.5°	835.9	825.1	813.1	800.0	787.9	777.1	771.5	768.4	762.1	759.5	755.0
10°	816.3	801.6	789.9	774.5	760.6	747.7	741.5	736.4	730.2	727.2	721.0
12.5°	796.1	779.1	766.2	750.2	735.9	720.5	714.5	705.0	695.2	689.1	681.1
15°	767.5	747.1	731.2	712.2	695.3	677.7	661.9	644.3	637.7	623.8	615.8
17.5°	734.1	713.3	693.8	668.3	642.2	620.4	603.5	586.7	576.6	567.7	563.5
20°	712.2	693.1	666.0	636.3	607.3	583.1	569.5	558.6	547.5	541.3	536.9
22.5°	691.4	667.0	635.5	603.4	574.5	555.5	544.0	532.7	523.8	517.8	512.0
25°	656.5	624.5	591.2	554.5	534.7	518.2	505.7	496.5	491.1	483.3	480.4
27.5°	620.6	581.9	545.1	520.5	499.8	484.7	473.9	467.0	460.1	455.1	451.3
30°	593.0	553.7	520.8	497.3	476.4	463.9	455.1	447.0	441.6	437.5	434.6
32.5°	565.7	526.5	498.7	473.5	457.0	444.9	435.5	429.4	425.1	419.9	418.1
35°	526.2	491.4	467.2	444.5	427.6	416.6	409.3	403.0	399.4	397.9	396.8
37.5°	488.3	459.8	433.8	415.1	400.1	391.4	382.8	379.8	377.2	374.6	375.8
40°	464.3	437.5	414.4	394.6	382.5	373.0	367.8	364.2	361.9	361.9	361.9
42.5°	443.5	417.3	394.7	377.0	364.9	356.8	351.1	348.0	347.3	346.9	348.7
45°	411.1	386.9	364.2	349.5	339.2	331.1	327.8	325.3	325.3	326.8	327.2
47.5°	379.1	356.4	338.1	321.7	312.3	307.3	304.3	303.0	303.2	304.6	306.3
50°	359.4	337.1	319.1	304.3	295.6	290.8	288.2	287.5	288.2	288.2	290.8
52.5°	338.0	317.9	300.3	287.9	278.0	273.5	272.1	271.1	271.5	272.7	273.8
55°	306.6	288.6	271.7	260.0	252.7	249.8	246.5	246.9	246.1	246.9	246.9
57.5°	275.1	259.0	243.3	233.9	227.5	223.3	219.7	220.6	219.6	219.4	218.9
60°	254.9	237.2	224.8	216.4	209.1	205.4	202.1	202.8	201.7	201.0	199.5
62.5°	232.9	218.2	206.3	198.2	192.3	188.0	184.7	184.0	181.4	179.0	175.7
65°	201.0	188.9	178.2	170.5	165.0	161.7	159.2	156.9	151.5	145.6	142.7
67.5°	169.9	161.2	151.3	144.8	140.3	136.0	131.1	127.3	122.2	118.9	117.2
70°	150.0	141.6	133.1	126.9	122.2	118.1	112.5	110.0	106.3	104.9	103.0
72.5°	130.9	123.1	115.2	109.6	104.5	101.3	97.1	94.4	92.8	92.3	90.4
75°	102.0	95.8	89.8	84.7	80.7	78.5	76.6	74.8	74.1	70.8	68.9
77.5°	74.4	70.2	66.6	63.0	60.0	58.6	55.0	53.0	51.7	50.1	49.8
80°	58.0	55.0	51.4	49.1	45.1	43.6	42.1	41.8	41.5	41.1	40.7
82.5°	43.5	40.6	36.9	35.6	34.6	33.6	32.8	32.4	32.0	32.2	32.2
85°	22.0	20.5	20.5	20.2	19.8	19.4	19.0	19.0	18.7	19.0	18.7
87.5°	9.0	8.8	10.1	9.5	10.3	10.7	10.2	10.4	10.9	10.6	10.6
90°	8.8	8.8	15.4	15.4	17.5	19.7	18.7	19.7	20.8	21.9	21.9
92.5°	57.9	80.6	136.3	221.2	304.1	347.4	289.4	215.1	161.8	128.8	106.9
95°	90.9	137.0	232.1	411.8	673.5	892.6	917.8	811.5	641.8	495.0	388.8
97.5°	110.0	148.5	221.9	370.2	630.4	940.2	1153.1	1199.1	1136.0	1028.9	914.5
100°	124.9	159.9	224.5	348.3	571.7	880.5	1160.9	1320.9	1342.7	1289.1	1208.1
102.5°	141.5	174.8	233.3	342.1	532.3	806.1	1095.2	1314.8	1423.3	1438.9	1405.1
105°	169.8	201.5	254.1	345.0	498.3	718.5	975.8	1226.6	1416.2	1524.6	1569.4
107.5°	198.9	230.3	278.4	361.2	492.2	669.4	879.5	1101.5	1303.3	1456.0	1553.7
110°	219.0	248.6	296.8	373.4	494.0	652.8	831.3	1026.2	1215.7	1374.5	1495.0



TEST NUMBER: P332921-830

CATALOG NUMBER: S124RDIP-S575D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	238.4	267.9	314.3	386.6	499.2	644.9	804.1	971.0	1138.6	1288.6	1409.1
115°	268.3	297.9	341.7	407.5	509.3	640.7	778.7	915.6	1050.4	1178.5	1283.6
117.5°	296.0	326.6	368.3	428.7	520.0	639.6	767.3	888.4	999.9	1100.7	1189.9
120°	314.3	345.0	386.6	443.6	527.9	639.6	761.2	876.2	978.1	1065.6	1143.4
122.5°	332.7	362.5	404.2	457.6	535.8	638.8	754.2	865.6	964.0	1043.8	1111.9
125°	358.2	388.8	428.2	478.6	547.6	637.4	742.5	847.7	941.9	1017.5	1077.7
127.5°	381.5	412.5	450.5	496.8	557.0	635.0	727.0	825.8	915.9	991.2	1048.4
130°	396.4	428.2	465.5	508.2	564.0	634.1	717.4	808.3	894.8	969.3	1027.4
132.5°	410.5	440.5	477.8	519.6	570.1	633.3	708.6	789.9	871.2	943.9	1001.9
135°	430.5	458.9	495.0	534.5	579.4	632.0	695.5	764.5	835.7	902.5	957.2
137.5°	447.3	474.5	508.2	545.0	584.8	631.7	684.1	741.5	801.7	858.0	907.5
140°	457.8	484.1	517.0	552.0	589.3	630.8	678.0	728.3	779.8	829.1	875.1
142.5°	467.4	492.9	524.8	557.2	592.8	630.8	672.7	716.0	761.4	803.7	843.6
145°	480.8	504.9	533.4	563.0	594.7	628.7	663.7	698.8	736.0	768.8	799.6
147.5°	493.7	515.4	542.2	568.0	595.8	624.7	655.6	684.6	714.1	740.4	764.5
150°	501.6	522.5	546.5	570.6	595.8	622.1	649.5	675.8	701.0	722.8	742.5
152.5°	509.5	528.6	550.1	572.4	594.1	617.7	642.4	666.1	687.8	707.9	724.2
155°	520.3	536.7	555.3	573.9	591.4	611.1	632.0	651.7	669.2	685.6	698.8
157.5°	530.3	543.3	559.0	573.9	588.6	604.4	621.2	636.1	650.8	664.6	675.1
160°	535.6	547.6	560.7	573.9	586.0	599.1	613.3	626.5	638.5	650.5	659.3
162.5°	540.8	550.3	562.5	573.9	583.3	593.8	606.3	616.8	627.2	636.6	644.4
165°	546.5	553.1	563.0	571.7	578.2	586.0	594.7	603.5	610.0	617.7	623.2
167.5°	550.4	555.5	562.7	569.1	573.1	578.1	584.2	590.6	595.6	601.7	605.0
170°	553.1	556.4	561.8	567.3	569.5	572.8	577.2	582.7	586.0	590.3	593.6
172.5°	554.9	557.2	561.0	565.6	566.0	567.5	571.1	575.6	578.1	580.7	583.1
175°	557.5	557.5	559.7	563.0	561.8	561.8	564.0	566.3	567.3	569.5	569.5
177.5°	557.5	557.5	558.4	560.1	558.4	558.4	559.2	560.1	561.0	561.0	561.8
180°	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5



TEST NUMBER: P332921-830

CATALOG NUMBER: S124RDIP-S575D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	910.2	910.2	910.2	910.2	910.2	910.2	910.2	910.2	910.2	910.2	910.2
2.5°	868.8	869.4	867.4	866.8	867.4	869.4	868.8	870.6	870.9	873.3	872.3
5°	806.1	805.3	803.5	803.9	803.5	805.3	806.1	809.0	810.5	816.3	815.6
7.5°	752.3	749.5	750.4	747.3	750.4	749.5	752.3	755.0	759.5	762.1	768.4
10°	719.5	715.5	712.2	709.3	712.2	715.5	719.5	721.0	727.2	730.2	736.4
12.5°	674.7	671.2	666.7	667.6	666.7	671.2	674.7	681.1	689.1	695.2	705.0
15°	611.0	605.5	596.6	597.8	596.6	605.5	611.0	615.8	623.8	637.7	644.3
17.5°	557.0	557.1	553.1	554.0	553.1	557.1	557.0	563.5	567.7	576.6	586.7
20°	529.1	526.6	527.0	525.8	527.0	526.6	529.1	536.9	541.3	547.5	558.6
22.5°	509.8	506.7	504.1	501.8	504.1	506.7	509.8	512.0	517.8	523.8	532.7
25°	477.1	474.9	471.6	470.9	471.6	474.9	477.1	480.4	483.3	491.1	496.5
27.5°	448.4	447.9	446.6	444.9	446.6	447.9	448.4	451.3	455.1	460.1	467.0
30°	431.6	430.9	430.2	429.0	430.2	430.9	431.6	434.6	437.5	441.6	447.0
32.5°	416.7	416.2	415.5	415.6	415.5	416.2	416.7	418.1	419.9	425.1	429.4
35°	395.3	394.9	394.3	393.9	394.3	394.9	395.3	396.8	397.9	399.4	403.0
37.5°	375.4	376.4	375.9	375.8	375.9	376.4	375.4	375.8	374.6	377.2	379.8
40°	361.6	361.9	362.7	362.3	362.7	361.9	361.6	361.9	361.9	361.9	364.2
42.5°	350.2	350.2	351.3	350.0	351.3	350.2	350.2	348.7	346.9	347.3	348.0
45°	329.7	331.9	331.5	331.5	331.5	331.9	329.7	327.2	326.8	325.3	325.3
47.5°	307.3	309.2	309.7	309.6	309.7	309.2	307.3	306.3	304.6	303.2	303.0
50°	292.7	291.9	293.0	292.7	293.0	291.9	292.7	290.8	288.2	288.2	287.5
52.5°	274.8	274.9	274.8	274.5	274.8	274.9	274.8	273.8	272.7	271.5	271.1
55°	247.1	247.5	246.9	247.1	246.9	247.5	247.1	246.9	246.9	246.1	246.9
57.5°	217.3	215.5	216.2	215.4	216.2	215.5	217.3	218.9	219.4	219.6	220.6
60°	195.9	192.9	192.2	190.7	192.2	192.9	195.9	199.5	201.0	201.7	202.8
62.5°	171.7	169.8	167.2	168.4	167.2	169.8	171.7	175.7	179.0	181.4	184.0
65°	139.7	138.3	137.1	138.6	137.1	138.3	139.7	142.7	145.6	151.5	156.9
67.5°	115.6	114.9	114.9	114.1	114.9	114.9	115.6	117.2	118.9	122.2	127.3
70°	103.0	102.0	102.0	101.2	102.0	102.0	103.0	103.0	104.9	106.3	110.0
72.5°	90.1	89.1	89.4	88.9	89.4	89.1	90.1	90.4	92.3	92.8	94.4
75°	66.7	64.9	64.9	65.3	64.9	64.9	66.7	68.9	70.8	74.1	74.8
77.5°	49.8	49.4	50.0	49.3	50.0	49.4	49.8	49.8	50.1	51.7	53.0
80°	40.7	40.3	40.0	41.1	40.0	40.3	40.7	40.7	41.1	41.5	41.8
82.5°	31.6	31.6	31.5	32.9	31.5	31.6	31.6	32.2	32.2	32.0	32.4
85°	19.0	18.4	19.0	18.4	19.0	18.4	19.0	18.7	19.0	18.7	19.0
87.5°	11.3	11.3	10.7	11.0	10.7	11.3	11.3	10.6	10.6	10.9	10.4
90°	23.0	24.1	23.0	23.0	23.0	24.1	23.0	21.9	21.9	20.8	19.7
92.5°	94.0	88.0	84.4	84.4	84.4	88.0	94.0	106.9	128.8	161.8	215.1
95°	335.2	301.2	281.4	267.2	281.4	301.2	335.2	388.8	495.0	641.8	811.5
97.5°	835.8	770.0	737.1	714.4	737.1	770.0	835.8	914.5	1028.9	1136.0	1199.1
100°	1112.8	1045.9	1013.1	1004.4	1013.1	1045.9	1112.8	1208.1	1289.1	1342.7	1320.9
102.5°	1346.7	1298.3	1263.7	1256.7	1263.7	1298.3	1346.7	1405.1	1438.9	1423.3	1314.8
105°	1571.7	1562.9	1547.6	1541.0	1547.6	1562.9	1571.7	1569.4	1524.6	1416.2	1226.6
107.5°	1607.8	1632.8	1643.7	1646.6	1643.7	1632.8	1607.8	1553.7	1456.0	1303.3	1101.5
110°	1572.7	1618.7	1638.5	1648.3	1638.5	1618.7	1572.7	1495.0	1374.5	1215.7	1026.2



TEST NUMBER: P332921-830

CATALOG NUMBER: S124RDIP-S575D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1497.4	1553.0	1580.6	1596.7	1580.6	1553.0	1497.4	1409.1	1288.6	1138.6	971.0
115°	1370.2	1435.9	1470.9	1479.7	1470.9	1435.9	1370.2	1283.6	1178.5	1050.4	915.6
117.5°	1263.7	1318.9	1354.3	1361.1	1354.3	1318.9	1263.7	1189.9	1100.7	999.9	888.4
120°	1205.9	1254.1	1282.5	1294.6	1282.5	1254.1	1205.9	1143.4	1065.6	978.1	876.2
122.5°	1164.7	1205.9	1229.9	1242.0	1229.9	1205.9	1164.7	1111.9	1043.8	964.0	865.6
125°	1121.5	1153.3	1174.1	1180.6	1174.1	1153.3	1121.5	1077.7	1017.5	941.9	847.7
127.5°	1092.4	1120.7	1138.2	1144.7	1138.2	1120.7	1092.4	1048.4	991.2	915.9	825.8
130°	1072.2	1099.6	1117.1	1123.7	1117.1	1099.6	1072.2	1027.4	969.3	894.8	808.3
132.5°	1045.9	1076.9	1093.4	1100.0	1093.4	1076.9	1045.9	1001.9	943.9	871.2	789.9
135°	1001.1	1031.7	1049.2	1055.8	1049.2	1031.7	1001.1	957.2	902.5	835.7	764.5
137.5°	948.5	978.7	993.2	1001.1	993.2	978.7	948.5	907.5	858.0	801.7	741.5
140°	913.4	937.5	952.8	961.6	952.8	937.5	913.4	875.1	829.1	779.8	728.3
142.5°	877.5	899.8	913.4	919.5	913.4	899.8	877.5	843.6	803.7	761.4	716.0
145°	826.9	845.6	856.5	862.0	856.5	845.6	826.9	799.6	768.8	736.0	698.8
147.5°	784.7	800.6	809.0	810.9	809.0	800.6	784.7	764.5	740.4	714.1	684.6
150°	760.1	774.3	780.9	782.0	780.9	774.3	760.1	742.5	722.8	701.0	675.8
152.5°	739.0	750.6	754.6	755.7	754.6	739.0	724.2	707.9	687.8	666.1	646.1
155°	709.7	718.5	721.8	721.8	721.8	718.5	709.7	698.8	685.6	669.2	651.7
157.5°	683.4	690.0	692.0	692.0	692.0	690.0	683.4	675.1	664.6	650.8	636.1
160°	665.9	672.5	673.5	673.5	673.5	672.5	665.9	659.3	650.5	638.5	626.5
162.5°	649.2	655.8	657.0	656.0	657.0	655.8	649.2	644.4	636.6	627.2	616.8
165°	627.5	632.0	630.8	629.8	630.8	632.0	627.5	623.2	617.7	610.0	603.5
167.5°	607.2	610.0	609.8	609.0	609.8	610.0	607.2	605.0	601.7	595.6	590.6
170°	595.8	596.9	595.8	595.8	595.8	596.9	595.8	593.6	590.3	586.0	582.7
172.5°	584.4	585.5	584.4	582.7	584.4	585.5	584.4	583.1	580.7	578.1	575.6
175°	569.5	571.7	569.5	567.3	569.5	571.7	569.5	569.5	569.5	567.3	566.3
177.5°	561.0	561.8	560.1	558.4	560.1	561.8	561.0	561.8	561.0	561.0	560.1
180°	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5



TEST NUMBER: P332921-830

CATALOG NUMBER: S124RDIP-S575D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	910.2	910.2	910.2	910.2	910.2	910.2	910.2	910.2	910.2	910.2	910.2
2.5°	870.6	872.7	877.3	882.6	887.0	890.9	893.8	897.9	901.7	907.0	912.0
5°	817.7	822.9	830.3	839.1	850.1	857.4	866.6	874.7	886.4	898.1	909.5
7.5°	771.5	777.1	787.9	800.0	813.1	825.1	835.9	850.2	865.7	882.9	901.9
10°	741.5	747.7	760.6	774.5	789.9	801.6	816.3	833.2	850.8	871.7	895.1
12.5°	714.5	720.5	735.9	750.2	766.2	779.1	796.1	813.2	836.7	859.4	886.1
15°	661.9	677.7	695.3	712.2	731.2	747.1	767.5	785.1	807.6	839.4	869.9
17.5°	603.5	620.4	642.2	668.3	693.8	713.3	734.1	756.0	782.7	815.2	850.4
20°	569.5	583.1	607.3	636.3	666.0	693.1	712.2	736.4	763.9	799.1	835.4
22.5°	544.0	555.5	574.5	603.4	635.5	667.0	691.4	715.3	745.7	780.9	820.5
25°	505.7	518.2	534.7	554.5	591.2	624.5	656.5	683.9	716.2	751.4	795.4
27.5°	473.9	484.7	499.8	520.5	545.1	581.9	620.6	652.0	685.0	722.8	766.9
30°	455.1	463.9	476.4	497.3	520.8	553.7	593.0	629.7	663.1	702.3	748.1
32.5°	435.5	444.9	457.0	473.5	498.7	526.5	565.7	605.9	641.3	681.5	726.4
35°	409.3	416.6	427.6	444.5	467.2	491.4	526.2	567.7	605.1	648.0	690.9
37.5°	382.8	391.4	400.1	415.1	433.8	459.8	488.3	530.7	572.1	611.2	653.2
40°	367.8	373.0	382.5	394.6	414.4	437.5	464.3	505.7	547.1	586.1	628.2
42.5°	351.1	356.8	364.9	377.0	394.7	417.3	443.5	479.3	522.5	560.2	598.6
45°	327.8	331.1	339.2	349.5	364.2	386.9	411.1	443.0	483.7	519.6	553.4
47.5°	304.3	307.3	312.3	321.7	338.1	356.4	379.1	407.6	443.4	479.3	507.8
50°	288.2	290.8	295.6	304.3	319.1	337.1	359.4	385.0	417.0	451.5	475.2
52.5°	272.1	273.5	278.0	287.9	300.3	317.9	338.0	361.6	391.4	420.1	444.2
55°	246.5	249.8	252.7	260.0	271.7	288.6	306.6	328.9	352.0	376.3	396.8
57.5°	219.7	223.3	227.5	233.9	243.3	259.0	275.1	293.2	312.9	333.1	350.2
60°	202.1	205.4	209.1	216.4	224.8	237.2	254.9	270.6	285.7	304.0	321.2
62.5°	184.7	188.0	192.3	198.2	206.3	218.2	232.9	246.6	262.2	278.2	291.1
65°	159.2	161.7	165.0	170.5	178.2	188.9	201.0	211.6	225.6	237.2	249.0
67.5°	131.1	136.0	140.3	144.8	151.3	161.2	169.9	180.1	189.6	198.3	209.1
70°	112.5	118.1	122.2	126.9	133.1	141.6	150.0	156.9	164.7	173.1	182.7
72.5°	97.1	101.3	104.5	109.6	115.2	123.1	130.9	136.7	143.0	148.7	158.0
75°	76.6	78.5	80.7	84.7	89.8	95.8	102.0	107.1	110.7	115.8	122.5
77.5°	55.0	58.6	60.0	63.0	66.6	70.2	74.4	78.7	82.2	84.1	89.1
80°	42.1	43.6	45.1	49.1	51.4	55.0	58.0	62.0	63.4	65.3	70.0
82.5°	32.8	33.6	34.6	35.6	36.9	40.6	43.5	46.1	47.6	48.3	51.8
85°	19.0	19.4	19.8	20.2	20.5	20.5	22.0	23.8	26.4	26.4	27.5
87.5°	10.2	10.7	10.3	9.5	10.1	8.8	9.0	8.9	9.5	9.7	10.2
90°	18.7	19.7	17.5	15.4	15.4	8.8	8.8	7.6	6.6	3.3	1.1
92.5°	289.4	347.4	304.1	221.2	136.3	80.6	57.9	41.8	28.5	18.2	12.4
95°	917.8	892.6	673.5	411.8	232.1	137.0	90.9	64.7	50.4	39.4	36.1
97.5°	1153.1	940.2	630.4	370.2	221.9	148.5	110.0	87.4	74.3	64.8	64.8
100°	1160.9	880.5	571.7	348.3	224.5	159.9	124.9	104.1	90.9	83.2	83.2
102.5°	1095.2	806.1	532.3	342.1	233.3	174.8	141.5	121.6	109.3	102.5	100.8
105°	975.8	718.5	498.3	345.0	254.1	201.5	169.8	150.1	137.0	131.4	128.2
107.5°	879.5	669.4	492.2	361.2	278.4	230.3	198.9	180.0	166.1	160.5	158.3
110°	831.3	652.8	494.0	373.4	296.8	248.6	219.0	199.3	186.2	180.7	178.5



TEST NUMBER: P332921-830

CATALOG NUMBER: S124RDIP-S575D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	804.1	644.9	499.2	386.6	314.3	267.9	238.4	218.6	206.3	200.0	197.8
115°	778.7	640.7	509.3	407.5	341.7	297.9	268.3	247.5	236.6	228.9	225.6
117.5°	767.3	639.6	520.0	428.7	368.3	326.6	296.0	276.4	264.4	257.6	254.5
120°	761.2	639.6	527.9	443.6	386.6	345.0	314.3	295.7	283.7	276.0	273.8
122.5°	754.2	638.8	535.8	457.6	404.2	362.5	332.7	312.4	301.2	293.5	291.3
125°	742.5	637.4	547.6	478.6	428.2	388.8	358.2	337.3	325.3	318.7	314.3
127.5°	727.0	635.0	557.0	496.8	450.5	412.5	381.5	359.9	346.1	338.2	334.7
130°	717.4	634.1	564.0	508.2	465.5	428.2	396.4	375.7	359.2	350.4	346.1
132.5°	708.6	633.3	570.1	519.6	477.8	440.5	410.5	388.0	372.4	361.0	357.5
135°	695.5	632.0	579.4	534.5	495.0	458.9	430.5	407.5	388.8	377.9	373.4
137.5°	684.1	631.7	584.8	545.0	508.2	474.5	447.3	423.4	405.7	393.6	389.5
140°	678.0	630.8	589.3	552.0	517.0	484.1	457.8	434.8	416.2	404.2	400.9
142.5°	672.7	630.8	592.8	557.2	524.8	492.9	467.4	445.4	427.5	416.4	413.1
145°	663.7	628.7	594.7	563.0	533.4	504.9	480.8	460.0	444.7	433.8	430.5
147.5°	655.6	624.7	595.8	568.0	542.2	515.4	493.7	476.5	460.6	451.0	449.9
150°	649.5	622.1	595.8	570.6	546.5	522.5	501.6	485.2	472.0	463.3	462.2
152.5°	642.4	617.7	594.1	572.4	550.1	528.6	509.5	494.8	482.6	473.8	473.5
155°	632.0	611.1	591.4	573.9	555.3	536.7	520.3	508.2	497.2	490.7	489.6
157.5°	621.2	604.4	588.6	573.9	559.0	543.3	530.3	519.8	511.2	505.1	505.1
160°	613.3	599.1	586.0	573.9	560.7	547.6	535.6	526.8	519.2	514.7	514.7
162.5°	606.3	593.8	583.3	573.9	562.5	550.3	540.8	532.9	526.1	522.6	523.5
165°	594.7	586.0	578.2	571.7	563.0	553.1	546.5	541.0	535.6	533.4	533.4
167.5°	584.2	578.1	573.1	569.1	562.7	555.5	550.4	547.4	543.3	542.2	543.3
170°	577.2	572.8	569.5	567.3	561.8	556.4	553.1	550.9	547.6	546.5	547.6
172.5°	571.1	567.5	566.0	565.6	561.0	557.2	554.9	553.6	551.1	550.9	552.0
175°	564.0	561.8	561.8	563.0	559.7	557.5	557.5	556.4	555.3	555.3	556.4
177.5°	559.2	558.4	558.4	560.1	558.4	557.5	557.5	557.5	556.6	557.5	558.4
180°	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5



TEST NUMBER: P332921-830

CATALOG NUMBER: S124RDIP-S575D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	910.2	910.2	910.2	910.2	910.2	910.2	910.2	910.2	910.2	910.2	910.2
2.5°	915.8	918.4	921.3	926.9	931.6	933.7	937.8	940.8	939.8	944.0	951.0
5°	919.4	929.3	940.7	952.3	965.5	976.6	985.4	994.2	1001.2	1009.6	1022.1
7.5°	918.8	936.4	955.5	976.6	998.2	1016.9	1034.3	1051.9	1067.4	1084.6	1106.9
10°	916.4	939.9	963.7	991.3	1018.8	1044.8	1068.3	1090.2	1111.2	1133.5	1161.8
12.5°	913.8	940.8	969.6	1002.7	1037.0	1068.3	1095.9	1127.6	1153.7	1182.5	1215.2
15°	902.1	938.5	977.7	1020.6	1061.7	1103.8	1141.6	1180.5	1216.8	1251.2	1292.3
17.5°	888.8	930.7	976.9	1027.7	1077.0	1128.2	1173.1	1222.1	1259.1	1305.4	1343.6
20°	878.0	923.0	972.5	1029.4	1085.5	1142.4	1191.8	1241.7	1283.6	1330.1	1378.6
22.5°	864.8	914.3	967.9	1026.7	1085.5	1147.6	1202.4	1252.0	1303.8	1356.2	1406.1
25°	843.5	894.8	951.7	1016.2	1083.6	1147.1	1205.8	1267.4	1323.1	1380.0	1424.7
27.5°	817.4	871.3	931.2	997.8	1067.1	1132.0	1201.1	1266.8	1322.9	1377.5	1416.5
30°	796.5	853.4	911.0	978.5	1050.3	1120.0	1194.0	1259.7	1318.7	1367.9	1389.9
32.5°	775.1	829.1	888.3	956.7	1030.4	1105.3	1178.8	1245.9	1300.5	1330.0	1330.6
35°	737.8	788.4	850.1	917.2	992.7	1074.1	1148.6	1214.6	1247.9	1250.6	1214.6
37.5°	697.2	743.7	801.8	869.0	951.7	1032.7	1108.7	1152.7	1163.9	1126.6	1060.2
40°	668.2	711.1	767.2	836.1	918.3	1001.9	1071.2	1103.4	1091.7	1031.2	957.2
42.5°	637.6	677.6	731.7	799.7	882.2	966.7	1025.8	1043.0	1011.9	942.1	855.4
45°	587.9	624.5	678.1	746.7	825.9	905.1	949.8	941.0	889.3	806.4	709.3
47.5°	536.0	571.5	619.6	683.1	764.2	832.5	862.8	836.3	762.7	671.6	592.5
50°	501.7	538.0	582.4	642.9	717.0	783.0	802.4	762.0	680.2	592.7	520.0
52.5°	468.0	499.0	542.4	600.9	671.8	727.5	737.8	691.4	606.9	528.4	464.0
55°	416.6	444.9	481.5	536.5	597.8	645.1	639.6	579.8	503.1	436.0	385.4
57.5°	366.9	388.2	422.1	473.6	527.4	559.2	539.0	488.1	416.7	361.7	319.1
60°	334.1	353.9	385.4	430.6	477.9	495.8	478.9	423.6	367.1	316.9	280.9
62.5°	303.0	320.5	347.6	389.5	427.6	438.3	420.3	371.9	321.0	278.1	248.4
65°	257.8	273.9	297.1	326.8	353.2	358.3	346.6	297.1	258.5	222.6	202.1
67.5°	216.8	227.3	245.4	271.1	285.1	288.1	265.4	234.3	200.4	178.3	162.9
70°	189.3	196.5	213.4	227.3	238.7	239.1	218.2	193.2	167.2	149.3	137.9
72.5°	162.5	169.6	182.4	191.9	200.6	197.7	178.6	158.9	137.9	124.3	115.8
75°	125.5	131.7	138.3	142.7	142.7	139.0	125.1	110.4	98.3	90.2	87.7
77.5°	91.1	96.3	98.5	97.8	96.5	90.8	82.0	72.4	68.1	64.3	62.3
80°	71.5	73.7	74.5	72.6	70.4	63.8	58.0	53.9	49.9	48.4	47.7
82.5°	53.1	55.0	53.1	53.5	48.7	43.3	40.1	38.6	36.9	36.4	35.6
85°	28.3	27.9	27.1	25.3	22.0	21.3	20.9	20.5	19.8	20.2	19.4
87.5°	10.4	10.1	9.1	9.0	9.0	9.8	10.1	10.6	11.0	10.5	11.3
90°	3.3	6.6	7.6	8.8	8.8	15.4	15.4	17.5	19.7	18.7	19.7
92.5°	18.2	28.5	41.8	57.9	80.6	136.3	221.2	304.1	347.4	289.4	215.1
95°	39.4	50.4	64.7	90.9	137.0	232.1	411.8	673.5	892.6	917.8	811.5
97.5°	64.8	74.3	87.4	110.0	148.5	221.9	370.2	630.4	940.2	1153.1	1199.1
100°	83.2	90.9	104.1	124.9	159.9	224.5	348.3	571.7	880.5	1160.9	1320.9
102.5°	102.5	109.3	121.6	141.5	174.8	233.3	342.1	532.3	806.1	1095.2	1314.8
105°	131.4	137.0	150.1	169.8	201.5	254.1	345.0	498.3	718.5	975.8	1226.6
107.5°	160.5	166.1	180.0	198.9	230.3	278.4	361.2	492.2	669.4	879.5	1101.5
110°	180.7	186.2	199.3	219.0	248.6	296.8	373.4	494.0	652.8	831.3	1026.2





TEST NUMBER: P332921-830

CATALOG NUMBER: S124RDIP-S575D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	200.0	206.3	218.6	238.4	267.9	314.3	386.6	499.2	644.9	804.1	971.0
115°	228.9	236.6	247.5	268.3	297.9	341.7	407.5	509.3	640.7	778.7	915.6
117.5°	257.6	264.4	276.4	296.0	326.6	368.3	428.7	520.0	639.6	767.3	888.4
120°	276.0	283.7	295.7	314.3	345.0	386.6	443.6	527.9	639.6	761.2	876.2
122.5°	293.5	301.2	312.4	332.7	362.5	404.2	457.6	535.8	638.8	754.2	865.6
125°	318.7	325.3	337.3	358.2	388.8	428.2	478.6	547.6	637.4	742.5	847.7
127.5°	338.2	346.1	359.9	381.5	412.5	450.5	496.8	557.0	635.0	727.0	825.8
130°	350.4	359.2	375.7	396.4	428.2	465.5	508.2	564.0	634.1	717.4	808.3
132.5°	361.0	372.4	388.0	410.5	440.5	477.8	519.6	570.1	633.3	708.6	789.9
135°	377.9	388.8	407.5	430.5	458.9	495.0	534.5	579.4	632.0	695.5	764.5
137.5°	393.6	405.7	423.4	447.3	474.5	508.2	545.0	584.8	631.7	684.1	741.5
140°	404.2	416.2	434.8	457.8	484.1	517.0	552.0	589.3	630.8	678.0	728.3
142.5°	416.4	427.5	445.4	467.4	492.9	524.8	557.2	592.8	630.8	672.7	716.0
145°	433.8	444.7	460.0	480.8	504.9	533.4	563.0	594.7	628.7	663.7	698.8
147.5°	451.0	460.6	476.5	493.7	515.4	542.2	568.0	595.8	624.7	655.6	684.6
150°	463.3	472.0	485.2	501.6	522.5	546.5	570.6	595.8	622.1	649.5	675.8
152.5°	473.8	482.6	494.8	509.5	528.6	550.1	572.4	594.1	617.7	642.4	666.1
155°	490.7	497.2	508.2	520.3	536.7	555.3	573.9	591.4	611.1	632.0	651.7
157.5°	505.1	511.2	519.8	530.3	543.3	559.0	573.9	588.6	604.4	621.2	636.1
160°	514.7	519.2	526.8	535.6	547.6	560.7	573.9	586.0	599.1	613.3	626.5
162.5°	522.6	526.1	532.9	540.8	550.3	562.5	573.9	583.3	593.8	606.3	616.8
165°	533.4	535.6	541.0	546.5	553.1	563.0	571.7	578.2	586.0	594.7	603.5
167.5°	542.2	543.3	547.4	550.4	555.5	562.7	569.1	573.1	578.1	584.2	590.6
170°	546.5	547.6	550.9	553.1	556.4	561.8	567.3	569.5	572.8	577.2	582.7
172.5°	550.9	551.1	553.6	554.9	557.2	561.0	565.6	566.0	567.5	571.1	575.6
175°	555.3	555.3	556.4	557.5	557.5	559.7	563.0	561.8	561.8	564.0	566.3
177.5°	557.5	556.6	557.5	557.5	557.5	558.4	560.1	558.4	558.4	559.2	560.1
180°	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5



TEST NUMBER: P332921-830

CATALOG NUMBER: S124RDIP-S575D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	910.2	910.2	910.2	910.2	910.2	910.2	910.2
2.5°	954.8	956.0	956.9	959.8	960.1	962.7	960.1
5°	1033.8	1039.0	1047.0	1055.1	1055.8	1060.9	1051.8
7.5°	1122.4	1134.3	1141.7	1154.7	1159.9	1163.1	1157.8
10°	1183.5	1194.4	1213.9	1223.4	1232.9	1234.4	1230.0
12.5°	1242.4	1259.8	1275.2	1293.3	1292.8	1305.7	1301.0
15°	1321.0	1338.9	1360.2	1380.4	1387.7	1387.7	1393.5
17.5°	1377.0	1409.9	1431.9	1447.7	1465.1	1468.1	1466.0
20°	1414.9	1450.4	1473.9	1494.4	1506.2	1509.5	1509.5
22.5°	1443.0	1473.3	1496.2	1514.7	1524.4	1528.2	1527.0
25°	1462.5	1488.6	1502.5	1508.0	1510.5	1509.8	1502.9
27.5°	1435.8	1434.6	1425.8	1408.9	1396.3	1388.6	1379.8
30°	1384.8	1365.6	1343.7	1319.5	1288.3	1264.4	1257.2
32.5°	1308.8	1265.9	1228.7	1188.4	1154.8	1131.0	1121.0
35°	1161.8	1093.9	1038.6	990.1	955.0	932.9	925.6
37.5°	987.4	921.7	853.2	806.3	777.0	754.8	746.5
40°	876.5	804.9	745.2	701.2	671.1	649.5	649.1
42.5°	775.2	707.0	650.7	619.1	586.6	572.3	572.2
45°	634.8	580.1	532.4	507.6	488.1	476.4	473.1
47.5°	525.6	480.4	448.7	428.8	412.9	405.5	400.6
50°	464.3	424.7	399.4	382.1	373.3	363.8	363.1
52.5°	413.2	381.3	361.6	347.5	336.4	330.6	330.8
55°	347.3	322.0	308.0	297.4	288.6	284.2	282.4
57.5°	292.6	273.6	263.4	253.7	250.0	246.5	245.5
60°	258.5	245.7	236.2	228.5	223.0	221.9	221.5
62.5°	230.4	217.0	210.4	204.4	200.4	198.7	198.0
65°	189.9	180.0	174.2	169.5	168.0	165.4	165.0
67.5°	153.2	147.2	143.4	140.1	138.0	137.9	137.9
70°	130.5	127.2	123.9	122.2	121.0	120.3	120.3
72.5°	111.2	108.8	106.0	105.1	104.9	104.2	103.9
75°	84.7	82.2	82.5	80.7	79.2	77.4	76.3
77.5°	60.0	58.2	57.9	57.7	56.4	56.2	56.7
80°	46.6	44.8	44.4	44.8	44.4	43.3	43.3
82.5°	35.4	33.9	33.6	33.3	32.9	33.3	32.7
85°	19.0	18.4	18.4	18.4	19.0	18.7	18.4
87.5°	10.9	10.8	11.1	11.0	11.3	10.7	11.0
90°	20.8	21.9	21.9	23.0	24.1	23.0	23.0
92.5°	161.8	128.8	106.9	94.0	88.0	84.4	84.4
95°	641.8	495.0	388.8	335.2	301.2	281.4	267.2
97.5°	1136.0	1028.9	914.5	835.8	770.0	737.1	714.4
100°	1342.7	1289.1	1208.1	1112.8	1045.9	1013.1	1004.4
102.5°	1423.3	1438.9	1405.1	1346.7	1298.3	1263.7	1256.7
105°	1416.2	1524.6	1569.4	1571.7	1562.9	1547.6	1541.0
107.5°	1303.3	1456.0	1553.7	1607.8	1632.8	1643.7	1646.6
110°	1215.7	1374.5	1495.0	1572.7	1618.7	1638.5	1648.3



TEST NUMBER: P332921-830

CATALOG NUMBER: S124RDIP-S575D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	1138.6	1288.6	1409.1	1497.4	1553.0	1580.6	1596.7
115°	1050.4	1178.5	1283.6	1370.2	1435.9	1470.9	1479.7
117.5°	999.9	1100.7	1189.9	1263.7	1318.9	1354.3	1361.1
120°	978.1	1065.6	1143.4	1205.9	1254.1	1282.5	1294.6
122.5°	964.0	1043.8	1111.9	1164.7	1205.9	1229.9	1242.0
125°	941.9	1017.5	1077.7	1121.5	1153.3	1174.1	1180.6
127.5°	915.9	991.2	1048.4	1092.4	1120.7	1138.2	1144.7
130°	894.8	969.3	1027.4	1072.2	1099.6	1117.1	1123.7
132.5°	871.2	943.9	1001.9	1045.9	1076.9	1093.4	1100.0
135°	835.7	902.5	957.2	1001.1	1031.7	1049.2	1055.8
137.5°	801.7	858.0	907.5	948.5	978.7	993.2	1001.1
140°	779.8	829.1	875.1	913.4	937.5	952.8	961.6
142.5°	761.4	803.7	843.6	877.5	899.8	913.4	919.5
145°	736.0	768.8	799.6	826.9	845.6	856.5	862.0
147.5°	714.1	740.4	764.5	784.7	800.6	809.0	810.9
150°	701.0	722.8	742.5	760.1	774.3	780.9	782.0
152.5°	687.8	707.9	724.2	739.0	750.6	754.6	755.7
155°	669.2	685.6	698.8	709.7	718.5	721.8	721.8
157.5°	650.8	664.6	675.1	683.4	690.0	692.0	692.0
160°	638.5	650.5	659.3	665.9	672.5	673.5	673.5
162.5°	627.2	636.6	644.4	649.2	655.8	657.0	656.0
165°	610.0	617.7	623.2	627.5	632.0	630.8	629.8
167.5°	595.6	601.7	605.0	607.2	610.0	609.8	609.0
170°	586.0	590.3	593.6	595.8	596.9	595.8	595.8
172.5°	578.1	580.7	583.1	584.4	585.5	584.4	582.7
175°	567.3	569.5	569.5	569.5	571.7	569.5	567.3
177.5°	561.0	561.0	561.8	561.0	561.8	560.1	558.4
180°	557.5	557.5	557.5	557.5	557.5	557.5	557.5

(END OF REPORT)