

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332510-930

Luminaire Tested: **S124DIP-S350D810U930-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332510-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIP-S350D810U930-4F0-1E-UDD-A4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3646.9 lumens
Efficiency: N/A
Efficacy: 116.9 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332510-930

CATALOG NUMBER: S124DIP-S350D810U930-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332510-930

CATALOG NUMBER: S124DIP-S350D810U930-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43	35
1	95	90	87	83	85	82	79	76	66	64	62	51	50	49	38	37	36	30
2	86	79	73	68	78	72	67	63	58	54	51	45	43	41	33	32	31	25
3	79	70	63	57	71	63	57	52	51	47	43	40	37	35	30	28	26	22
4	72	62	54	48	65	56	50	44	46	41	37	36	32	30	27	25	23	19
5	66	55	47	41	60	50	43	38	41	36	32	32	29	26	24	22	20	16
6	61	49	41	36	55	45	38	33	37	32	28	29	25	23	22	19	18	14
7	56	44	37	31	51	41	34	29	33	28	24	26	23	20	20	18	16	13
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	16	14	12
9	48	37	29	24	44	34	27	23	28	23	19	22	19	16	17	14	13	10
10	45	34	27	22	41	31	25	20	25	21	17	20	17	14	16	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	3760	3760	3760	3760
5°	4428	3770	3327	3770
10°	5302	3754	2995	3754
15°	6273	3716	2751	3716
20°	6985	3677	2533	3677
25°	7098	3619	2382	3619
30°	6040	3566	2335	3566
35°	4644	3476	2335	3476
40°	3620	3371	2380	3371
45°	3017	3214	2419	3214
50°	2656	3022	2501	3022
55°	2434	2792	2601	2792
60°	2280	2585	2722	2585
65°	2122	2355	2823	2355
70°	1940	2127	2887	2127
75°	1734	1871	2854	1871
80°	1450	1534	2762	1534
85°	1074	1112	2640	1112



TEST NUMBER: P332510-930

CATALOG NUMBER: S124DIP-S350D810U930-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.4	1.2
10°-20°	139.9	3.8
20°-30°	221.8	6.1
30°-40°	246.8	6.8
40°-50°	224.7	6.2
50°-60°	183.6	5.0
60°-70°	131.1	3.6
70°-80°	72.2	2.0
80°-90°	21.5	0.6
90°-100°	234.4	6.4
100°-110°	487.8	13.4
110°-120°	436.9	12.0
120°-130°	367.5	10.1
130°-140°	306.4	8.4
140°-150°	234.1	6.4
150°-160°	164.6	4.5
160°-170°	96.8	2.7
170°-180°	31.5	0.9
0°-30°	407.0	11.2
0°-40°	653.9	17.9
0°-60°	1062.2	29.1
0°-90°	1286.9	35.3
90°-120°	1159.1	31.8
90°-150°	2067.1	56.7
90°-180°	2360.0	64.7
0°-180°	3646.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	466	466	466	466	466	
5°	546	465	411	465	546	56
15°	751	445	329	445	751	212
25°	797	406	267	406	797	351
35°	471	353	237	353	471	299
45°	264	282	212	282	264	208
55°	173	198	185	198	173	156
65°	111	123	148	123	111	110
75°	56	60	92	60	56	59
85°	12	12	28	12	12	14
90°	13	1	13	1	13	11
95°	156	21	156	21	156	241
105°	897	75	897	75	897	887
115°	861	131	861	131	861	855
125°	687	183	687	183	687	624
135°	615	217	615	217	615	474
145°	502	250	502	250	502	318
155°	420	285	420	285	420	196
165°	367	310	367	310	367	105
175°	330	324	330	324	330	32
180°	324	324	324	324	324	



TEST NUMBER: P332510-930

CATALOG NUMBER: S124DIP-S350D810U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8
2.5°	495.7	495.6	494.1	493.7	492.7	491.3	491.0	488.4	483.6	481.2	480.6
5°	546.4	550.3	545.3	544.3	543.7	537.4	534.1	530.3	521.4	516.2	512.1
7.5°	607.0	607.4	605.2	603.5	598.5	593.0	584.7	575.8	565.2	554.2	545.9
10°	646.8	648.3	645.8	645.5	635.6	629.4	617.1	606.7	594.7	581.4	569.2
12.5°	688.8	686.6	685.3	677.1	675.2	664.0	649.6	639.0	620.4	605.1	589.0
15°	750.6	746.3	743.6	732.3	726.7	711.0	695.8	684.0	659.9	636.9	619.5
17.5°	786.8	791.1	784.9	780.2	765.7	754.7	739.2	714.4	695.6	667.1	645.1
20°	813.1	813.5	810.0	805.2	793.9	779.9	763.0	736.0	713.4	685.0	654.8
22.5°	820.2	820.3	818.8	814.3	805.7	794.4	777.3	754.7	727.4	696.6	666.4
25°	796.9	796.1	797.9	802.9	799.6	796.1	786.3	769.5	744.0	711.4	679.0
27.5°	710.3	715.7	725.5	737.8	749.7	758.7	761.2	757.8	742.1	715.3	681.3
30°	647.9	654.5	661.9	674.2	698.1	711.8	726.8	738.3	731.9	710.5	678.8
32.5°	579.4	581.1	591.9	605.9	627.9	654.2	678.1	701.2	708.9	697.7	671.2
35°	471.2	473.9	485.7	499.5	526.4	558.6	594.5	626.6	653.0	663.6	650.0
37.5°	384.5	392.2	400.6	415.5	439.1	468.1	505.4	546.9	586.3	612.7	617.2
40°	343.5	348.3	354.2	365.7	385.7	414.3	446.3	493.7	535.7	573.5	585.8
42.5°	311.0	313.9	317.6	327.8	343.1	371.5	400.8	442.5	484.5	529.8	550.5
45°	264.3	267.3	273.5	279.4	291.0	310.6	337.9	372.2	414.5	458.0	496.3
47.5°	230.6	232.4	236.1	242.6	252.4	265.4	287.5	316.2	355.3	397.7	438.4
50°	211.5	213.0	215.9	221.7	229.3	240.8	258.9	285.8	316.4	359.1	399.0
52.5°	196.3	197.0	199.1	203.0	209.0	218.7	233.7	255.8	284.4	322.4	362.2
55°	172.9	173.7	175.6	178.5	183.7	189.9	201.2	217.8	242.7	275.7	310.3
57.5°	153.6	154.2	155.7	156.9	161.2	166.2	175.0	186.8	205.6	233.7	264.5
60°	141.2	140.9	142.8	143.7	146.7	150.9	157.7	169.0	185.4	208.0	236.4
62.5°	129.2	128.7	130.3	131.6	133.2	136.8	142.4	151.2	164.6	185.0	209.5
65°	111.1	110.4	111.4	112.9	114.4	116.3	120.4	128.3	138.9	153.6	172.3
67.5°	93.0	93.8	94.0	94.7	95.6	98.2	101.0	106.6	114.1	125.9	141.7
70°	82.2	82.4	83.2	83.2	83.7	86.1	88.4	91.6	99.0	109.8	122.7
72.5°	71.4	72.2	71.9	72.5	73.0	74.5	76.1	79.3	85.5	93.6	104.5
75°	55.6	56.2	56.2	56.3	56.9	57.5	58.9	61.1	65.6	71.6	79.1
77.5°	40.5	40.6	40.8	41.6	41.6	42.5	43.5	45.3	47.5	51.6	56.3
80°	31.2	31.6	31.5	31.9	31.9	32.6	33.0	35.3	36.3	39.0	42.6
82.5°	22.9	23.3	23.2	23.8	24.1	24.3	24.8	25.8	26.7	29.1	30.6
85°	11.6	12.0	11.6	12.0	12.6	12.7	13.3	13.5	14.3	14.8	16.2
87.5°	6.0	6.5	6.7	6.7	6.8	7.0	7.1	6.8	7.3	7.6	7.9
90°	13.4	13.4	14.0	13.4	12.7	12.7	12.1	11.5	10.8	11.5	10.2
92.5°	49.1	49.1	51.3	54.7	62.2	75.0	94.2	125.2	168.4	202.2	177.0
95°	155.6	163.9	175.3	195.1	226.3	288.1	373.6	472.4	534.3	519.6	392.1
97.5°	415.8	429.0	448.2	486.6	532.3	598.8	661.2	697.9	671.2	547.2	367.0
100°	584.6	589.7	608.8	647.7	703.2	750.3	781.5	768.8	675.7	512.6	332.8
102.5°	731.5	735.6	755.7	783.9	817.9	837.6	828.5	765.2	637.5	469.2	309.8
105°	897.0	900.8	909.7	914.8	913.5	887.4	824.3	714.0	568.0	418.2	290.1
107.5°	958.4	956.8	950.4	935.9	904.3	847.5	758.6	641.2	511.9	389.6	286.5
110°	959.4	953.7	942.2	915.4	870.2	800.1	707.6	597.4	483.9	379.9	287.5



TEST NUMBER: P332510-930

CATALOG NUMBER: S124DIP-S350D810U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	929.4	920.1	904.0	871.6	820.2	750.1	662.8	565.2	468.1	375.4	290.6
115°	861.3	856.1	835.8	797.5	747.1	685.9	611.4	533.0	453.2	372.9	296.4
117.5°	792.3	788.3	767.7	735.6	692.6	640.7	582.0	517.1	446.6	372.3	302.7
120°	753.5	746.5	729.9	701.9	665.5	620.3	569.3	510.0	443.0	372.3	307.3
122.5°	722.9	715.9	701.9	677.9	647.2	607.6	561.1	503.9	439.0	371.8	311.9
125°	687.2	683.4	671.3	652.8	627.3	592.2	548.3	493.4	432.2	371.0	318.8
127.5°	666.3	662.5	652.3	635.9	610.3	576.9	533.0	480.7	423.1	369.7	324.2
130°	654.1	650.3	640.1	624.1	597.9	564.2	520.8	470.5	417.6	369.1	328.3
132.5°	640.3	636.5	626.8	608.8	583.2	549.4	507.0	459.7	412.5	368.6	331.9
135°	614.6	610.7	600.5	582.7	557.2	525.3	486.4	445.0	404.8	367.9	337.2
137.5°	582.7	578.0	569.6	552.0	528.2	499.5	466.7	431.6	398.2	367.7	340.4
140°	559.7	554.6	545.7	531.7	509.4	482.6	453.9	424.0	394.6	367.2	343.0
142.5°	535.2	531.7	523.7	510.8	491.0	467.8	443.2	416.8	391.6	367.2	345.0
145°	501.7	498.6	492.1	481.4	465.4	447.5	428.4	406.8	386.3	365.9	346.2
147.5°	472.0	470.8	466.0	456.7	445.0	431.0	415.6	398.4	381.6	363.6	346.8
150°	455.2	454.5	450.7	442.5	432.2	420.8	408.0	393.3	378.1	362.1	346.8
152.5°	439.9	439.2	436.9	430.2	421.5	412.1	400.3	387.8	374.0	359.5	345.8
155°	420.1	420.1	418.2	413.1	406.8	399.1	389.6	379.3	367.9	355.7	344.2
157.5°	402.8	402.8	401.6	397.8	393.0	386.9	378.8	370.2	361.6	351.8	342.6
160°	392.1	392.1	391.4	387.6	383.8	378.7	371.7	364.7	357.0	348.7	341.0
162.5°	381.9	382.4	381.7	377.9	375.1	370.6	365.0	359.1	352.9	345.7	339.6
165°	366.6	367.2	367.9	365.3	362.7	359.5	355.1	351.2	346.2	341.0	336.6
167.5°	354.4	355.0	355.1	353.4	352.1	350.3	346.7	343.7	340.1	336.5	333.5
170°	346.8	346.8	347.4	346.8	345.5	343.6	341.0	339.2	336.0	333.4	331.5
172.5°	339.2	340.1	340.8	340.1	339.4	338.0	336.5	335.1	332.4	330.4	329.5
175°	330.2	331.5	332.8	331.5	331.5	331.5	330.2	329.6	328.3	327.0	327.0
177.5°	325.0	326.0	327.0	326.5	327.0	326.5	326.5	326.0	325.5	325.0	325.0
180°	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5



TEST NUMBER: P332510-930

CATALOG NUMBER: S124DIP-S350D810U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8
2.5°	480.8	478.6	477.0	475.8	472.5	470.4	468.9	466.8	464.2	461.6	458.4
5°	508.0	501.5	496.7	489.3	482.4	476.6	470.6	465.2	458.7	451.5	446.3
7.5°	536.7	526.9	514.5	503.6	491.4	480.8	471.3	461.6	451.5	441.6	432.7
10°	555.0	542.4	528.5	512.1	496.7	483.0	470.3	457.9	445.9	434.0	423.7
12.5°	574.5	558.9	538.3	519.2	501.9	483.6	468.2	453.1	438.6	426.1	414.2
15°	600.9	578.3	554.6	528.9	506.1	484.7	463.7	444.6	428.4	411.7	400.1
17.5°	617.0	589.1	562.0	535.2	507.6	480.5	457.9	435.9	415.6	399.1	384.5
20°	627.7	599.9	566.1	539.3	506.5	478.7	452.5	428.0	406.8	389.2	374.1
22.5°	636.9	604.9	571.0	535.7	503.1	473.6	444.9	420.3	398.6	380.1	365.7
25°	642.0	605.1	568.4	533.3	496.3	461.4	435.3	406.3	383.2	363.7	348.3
27.5°	642.5	603.1	561.6	522.6	484.4	451.8	419.0	393.1	369.1	348.5	333.6
30°	640.8	599.7	555.1	512.9	474.5	439.2	410.6	382.5	357.9	337.5	322.0
32.5°	635.4	592.6	546.8	502.1	462.3	427.7	398.3	371.5	347.6	327.4	311.2
35°	619.8	577.5	528.7	482.2	441.5	406.6	379.9	352.7	328.8	309.7	294.1
37.5°	595.3	557.2	507.5	459.4	419.4	384.3	357.9	333.4	311.8	292.4	276.4
40°	574.1	540.5	490.6	443.8	400.6	367.2	342.5	319.9	298.5	280.1	264.9
42.5°	549.5	520.2	474.3	424.7	382.9	349.4	325.4	305.1	284.9	268.0	252.7
45°	505.7	486.4	443.2	397.3	353.8	322.2	299.3	281.5	264.6	247.9	235.2
47.5°	455.4	445.8	409.4	365.8	324.7	293.4	273.5	257.1	242.2	228.2	217.0
50°	421.6	416.9	385.6	343.5	304.1	274.8	254.7	240.6	227.9	215.6	204.9
52.5°	388.2	388.1	359.7	321.2	284.8	256.6	236.6	223.5	212.5	202.4	192.9
55°	337.3	342.7	320.5	286.2	253.6	228.0	210.1	198.4	190.6	182.4	175.2
57.5°	290.5	299.5	281.1	250.9	223.6	200.2	184.6	175.8	167.5	162.5	157.3
60°	259.9	268.4	254.1	228.7	203.0	183.0	168.0	160.1	153.0	149.5	145.9
62.5°	232.8	240.3	229.8	206.1	183.8	164.5	152.0	144.4	139.6	135.8	133.4
65°	194.0	200.3	191.2	174.1	154.9	139.5	129.3	123.3	118.7	117.2	114.4
67.5°	156.8	162.6	157.7	143.1	127.8	116.0	108.0	102.3	99.5	98.2	96.3
70°	134.7	140.5	135.3	122.5	110.7	100.9	93.4	90.1	87.2	86.7	84.0
72.5°	116.0	119.9	114.7	104.8	94.7	86.4	80.6	77.1	75.7	74.6	73.1
75°	87.0	90.5	87.0	79.3	72.2	66.4	61.4	60.0	58.3	57.7	56.7
77.5°	61.6	64.6	62.0	57.2	51.8	47.3	44.6	42.9	42.5	41.5	42.0
80°	47.0	49.0	46.5	43.2	39.0	35.9	34.0	33.0	31.9	31.5	32.2
82.5°	33.8	34.7	33.3	31.1	28.0	26.0	24.7	23.6	23.3	23.4	23.4
85°	17.5	17.4	17.2	15.2	14.3	13.0	12.1	12.0	11.7	12.1	12.6
87.5°	7.7	7.8	6.8	6.3	5.7	5.1	4.6	4.2	4.6	5.1	5.4
90°	8.9	8.9	5.1	5.1	4.5	3.8	1.9	0.7	1.9	3.8	4.5
92.5°	128.7	79.3	46.9	33.7	24.4	16.6	10.6	7.3	10.6	16.6	24.4
95°	239.7	135.2	79.7	52.9	37.6	29.4	22.9	21.0	22.9	29.4	37.6
97.5°	215.5	129.1	86.4	64.0	50.9	43.2	37.7	37.7	37.7	43.2	50.9
100°	202.8	130.7	93.1	72.6	60.6	52.9	48.4	48.4	48.4	52.9	60.6
102.5°	199.2	135.7	101.7	82.3	70.8	63.6	59.7	58.6	59.7	63.6	70.8
105°	200.8	147.9	117.3	98.8	87.3	79.7	76.5	74.6	76.5	79.7	87.3
107.5°	210.3	162.1	134.0	115.8	104.8	96.6	93.4	92.2	93.4	96.6	104.8
110°	217.4	172.8	144.7	127.5	116.0	108.4	105.2	104.0	105.2	108.4	116.0



TEST NUMBER: P332510-930

CATALOG NUMBER: S124DIP-S350D810U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	225.0	183.0	156.0	138.7	127.3	120.1	116.4	115.1	116.4	120.1	127.3
115°	237.2	198.9	173.4	156.2	144.1	137.7	133.2	131.3	133.2	137.7	144.1
117.5°	249.5	214.3	190.1	172.3	160.9	153.9	149.9	148.1	149.9	153.9	160.9
120°	258.2	225.0	200.8	183.0	172.1	165.1	160.6	159.4	160.6	165.1	172.1
122.5°	266.4	235.2	211.0	193.6	181.8	175.3	170.9	169.6	170.9	175.3	181.8
125°	278.6	249.2	226.3	208.5	196.3	189.3	185.5	183.0	185.5	189.3	196.3
127.5°	289.2	262.3	240.1	222.1	209.5	201.5	196.9	194.9	196.9	201.5	209.5
130°	295.8	270.9	249.2	230.8	218.7	209.1	204.0	201.5	204.0	209.1	218.7
132.5°	302.4	278.1	256.4	239.0	225.8	216.8	210.1	208.1	210.1	216.8	225.8
135°	311.1	288.1	267.1	250.5	237.2	226.3	220.0	217.4	220.0	226.3	237.2
137.5°	317.2	295.8	276.1	260.3	246.5	236.1	229.1	226.7	229.1	236.1	246.5
140°	321.3	300.9	281.8	266.4	253.1	242.2	235.2	233.3	235.2	242.2	253.1
142.5°	324.3	305.5	286.9	272.1	259.2	248.9	242.4	240.4	242.4	248.9	259.2
145°	327.7	310.5	293.9	279.9	267.7	258.9	252.4	250.5	252.4	258.9	267.7
147.5°	330.6	315.6	300.0	287.4	277.3	268.2	262.5	261.9	262.5	268.2	277.3
150°	332.2	318.1	304.1	292.0	282.4	274.8	269.7	269.0	269.7	274.8	282.4
152.5°	333.1	320.2	307.7	296.6	288.0	280.9	275.8	275.7	275.8	280.9	288.0
155°	334.0	323.2	312.3	302.8	295.8	289.4	285.6	284.9	285.6	289.4	295.8
157.5°	334.0	325.4	316.2	308.7	302.6	297.6	294.0	294.0	294.0	297.6	302.6
160°	334.0	326.4	318.8	311.8	306.6	302.1	299.6	299.6	299.6	302.1	306.6
162.5°	334.0	327.4	320.2	314.8	310.2	306.2	304.2	304.8	304.2	306.2	310.2
165°	332.8	327.7	322.0	318.1	315.0	311.8	310.5	310.5	310.5	311.8	315.0
167.5°	331.3	327.6	323.3	320.4	318.6	316.2	315.6	316.2	315.6	316.2	318.6
170°	330.2	327.0	323.8	322.0	320.7	318.8	318.1	318.8	318.1	318.8	320.7
172.5°	329.2	326.5	324.3	322.9	322.2	320.8	320.7	321.3	320.7	320.8	322.2
175°	327.7	325.8	324.5	324.5	323.8	323.2	323.2	323.8	323.2	323.2	323.8
177.5°	326.0	325.0	324.5	324.5	324.5	324.0	324.5	325.0	324.5	324.0	324.5
180°	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5



TEST NUMBER: P332510-930

CATALOG NUMBER: S124DIP-S350D810U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8
2.5°	456.8	455.4	453.5	450.7	448.3	445.9	445.2	444.3	446.2	444.7	444.2
5°	441.9	437.8	432.6	426.6	423.1	418.2	417.2	415.2	413.3	413.1	411.2
7.5°	426.0	420.0	413.2	407.2	401.5	396.0	392.4	391.7	388.8	387.1	385.2
10°	415.8	408.5	400.6	394.8	388.2	382.5	378.4	376.1	374.1	372.0	370.1
12.5°	403.8	396.0	389.5	383.2	375.4	371.0	364.4	360.4	360.0	360.0	355.0
15°	389.8	382.0	372.0	363.1	358.9	350.4	346.7	342.1	339.2	336.3	334.0
17.5°	373.7	364.1	356.3	346.1	338.0	331.3	326.4	323.7	319.3	315.2	312.3
20°	363.7	353.5	345.2	334.4	325.5	317.2	313.2	309.3	306.1	302.6	299.3
22.5°	353.5	342.8	332.7	322.2	314.0	305.2	301.3	296.0	292.9	291.0	287.7
25°	337.5	325.9	314.3	304.3	295.8	288.0	282.9	278.8	275.3	273.8	271.7
27.5°	320.0	308.5	297.3	285.9	276.3	270.7	266.5	263.5	261.5	259.4	258.4
30°	308.9	296.9	285.0	274.3	265.5	259.9	256.1	254.0	252.4	251.4	250.5
32.5°	297.7	285.8	273.3	263.6	255.6	250.6	247.7	245.6	244.8	244.5	244.1
35°	279.6	267.7	256.1	247.4	239.9	237.9	235.4	234.2	233.8	235.2	235.8
37.5°	262.1	251.0	240.4	232.0	227.0	224.2	223.3	223.4	224.8	225.9	227.3
40°	250.9	240.0	230.0	222.7	218.0	216.3	215.9	216.9	218.4	219.8	221.4
42.5°	239.9	229.3	220.1	213.3	210.0	208.4	208.6	209.6	211.8	213.4	215.7
45°	222.9	214.0	205.1	199.5	196.8	197.2	197.2	198.9	201.1	203.6	206.1
47.5°	206.8	197.9	190.6	185.9	184.5	184.2	185.2	187.5	190.5	193.6	197.1
50°	196.1	187.5	181.2	176.9	175.4	175.9	177.5	179.6	183.3	187.2	190.9
52.5°	185.1	177.3	171.5	167.5	166.4	167.5	169.0	172.4	175.6	179.8	184.2
55°	168.0	161.5	156.9	154.0	153.6	154.2	155.9	159.6	164.2	169.4	173.7
57.5°	151.2	145.6	141.4	139.4	139.6	140.1	143.0	147.3	152.3	157.8	163.3
60°	139.7	134.7	131.2	129.6	129.9	131.0	134.5	138.5	144.7	150.1	155.9
62.5°	128.9	124.5	121.2	119.8	119.5	122.1	125.4	129.6	135.7	141.8	148.1
65°	111.5	108.0	105.3	104.6	105.2	107.1	111.4	116.9	122.1	128.5	135.1
67.5°	94.6	91.7	89.8	90.2	90.9	93.8	97.3	102.1	108.0	114.6	121.1
70°	83.7	81.0	79.5	79.7	80.9	84.3	87.4	92.2	98.6	105.3	110.7
72.5°	72.6	70.8	69.5	70.3	71.4	73.8	77.7	82.5	88.1	94.4	100.1
75°	55.8	55.8	55.0	55.6	57.3	59.6	62.5	67.5	73.1	78.2	82.8
77.5°	41.3	40.9	41.4	42.2	43.1	45.9	49.2	52.8	57.0	62.0	65.9
80°	31.6	31.9	32.8	34.0	34.3	36.4	39.9	43.2	46.5	50.7	54.4
82.5°	23.8	24.0	24.5	25.9	26.3	28.6	30.8	34.1	37.1	39.9	43.0
85°	13.0	13.0	13.9	14.5	15.4	17.0	18.3	20.3	23.0	24.9	27.8
87.5°	6.0	6.0	7.3	7.7	8.4	9.4	9.5	11.4	12.1	13.0	14.4
90°	5.1	5.1	8.9	8.9	10.2	11.5	10.8	11.5	12.1	12.7	12.7
92.5°	33.7	46.9	79.3	128.7	177.0	202.2	168.4	125.2	94.2	75.0	62.2
95°	52.9	79.7	135.2	239.7	392.1	519.6	534.3	472.4	373.6	288.1	226.3
97.5°	64.0	86.4	129.1	215.5	367.0	547.2	671.2	697.9	661.2	598.8	532.3
100°	72.6	93.1	130.7	202.8	332.8	512.6	675.7	768.8	781.5	750.3	703.2
102.5°	82.3	101.7	135.7	199.2	309.8	469.2	637.5	765.2	828.5	837.6	817.9
105°	98.8	117.3	147.9	200.8	290.1	418.2	568.0	714.0	824.3	887.4	913.5
107.5°	115.8	134.0	162.1	210.3	286.5	389.6	511.9	641.2	758.6	847.5	904.3
110°	127.5	144.7	172.8	217.4	287.5	379.9	483.9	597.4	707.6	800.1	870.2



TEST NUMBER: P332510-930

CATALOG NUMBER: S124DIP-S350D810U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	138.7	156.0	183.0	225.0	290.6	375.4	468.1	565.2	662.8	750.1	820.2
115°	156.2	173.4	198.9	237.2	296.4	372.9	453.2	533.0	611.4	685.9	747.1
117.5°	172.3	190.1	214.3	249.5	302.7	372.3	446.6	517.1	582.0	640.7	692.6
120°	183.0	200.8	225.0	258.2	307.3	372.3	443.0	510.0	569.3	620.3	665.5
122.5°	193.6	211.0	235.2	266.4	311.9	371.8	439.0	503.9	561.1	607.6	647.2
125°	208.5	226.3	249.2	278.6	318.8	371.0	432.2	493.4	548.3	592.2	627.3
127.5°	222.1	240.1	262.3	289.2	324.2	369.7	423.1	480.7	533.0	576.9	610.3
130°	230.8	249.2	270.9	295.8	328.3	369.1	417.6	470.5	520.8	564.2	597.9
132.5°	239.0	256.4	278.1	302.4	331.9	368.6	412.5	459.7	507.0	549.4	583.2
135°	250.5	267.1	288.1	311.1	337.2	367.9	404.8	445.0	486.4	525.3	557.2
137.5°	260.3	276.1	295.8	317.2	340.4	367.7	398.2	431.6	466.7	499.5	528.2
140°	266.4	281.8	300.9	321.3	343.0	367.2	394.6	424.0	453.9	482.6	509.4
142.5°	272.1	286.9	305.5	324.3	345.0	367.2	391.6	416.8	443.2	467.8	491.0
145°	279.9	293.9	310.5	327.7	346.2	365.9	386.3	406.8	428.4	447.5	465.4
147.5°	287.4	300.0	315.6	330.6	346.8	363.6	381.6	398.4	415.6	431.0	445.0
150°	292.0	304.1	318.1	332.2	346.8	362.1	378.1	393.3	408.0	420.8	432.2
152.5°	296.6	307.7	320.2	333.1	345.8	359.5	374.0	387.8	400.3	412.1	421.5
155°	302.8	312.3	323.2	334.0	344.2	355.7	367.9	379.3	389.6	399.1	406.8
157.5°	308.7	316.2	325.4	334.0	342.6	351.8	361.6	370.2	378.8	386.9	393.0
160°	311.8	318.8	326.4	334.0	341.0	348.7	357.0	364.7	371.7	378.7	383.8
162.5°	314.8	320.2	327.4	334.0	339.6	345.7	352.9	359.1	365.0	370.6	375.1
165°	318.1	322.0	327.7	332.8	336.6	341.0	346.2	351.2	355.1	359.5	362.7
167.5°	320.4	323.3	327.6	331.3	333.5	336.5	340.1	343.7	346.7	350.3	352.1
170°	322.0	323.8	327.0	330.2	331.5	333.4	336.0	339.2	341.0	343.6	345.5
172.5°	322.9	324.3	326.5	329.2	329.5	330.4	332.4	335.1	336.5	338.0	339.4
175°	324.5	324.5	325.8	327.7	327.0	327.0	328.3	329.6	330.2	331.5	331.5
177.5°	324.5	324.5	325.0	326.0	325.0	325.0	325.5	326.0	326.5	326.5	327.0
180°	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5



TEST NUMBER: P332510-930

CATALOG NUMBER: S124DIP-S350D810U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8
2.5°	443.8	443.6	442.5	442.3	442.5	443.6	443.8	444.2	444.7	446.2	444.3
5°	410.0	409.0	408.5	410.6	408.5	409.0	410.0	411.2	413.1	413.3	415.2
7.5°	384.5	383.8	382.0	381.5	382.0	383.8	384.5	385.2	387.1	388.8	391.7
10°	368.2	367.4	365.8	365.4	365.8	367.4	368.2	370.1	372.0	374.1	376.1
12.5°	352.4	350.9	350.6	351.0	350.6	350.9	352.4	355.0	360.0	360.0	360.4
15°	331.5	330.7	328.6	329.2	328.6	330.7	331.5	334.0	336.3	339.2	342.1
17.5°	310.9	310.0	307.4	309.7	307.4	310.0	310.9	312.3	315.2	319.3	323.7
20°	297.9	296.4	295.1	294.8	295.1	296.4	297.9	299.3	302.6	306.1	309.3
22.5°	285.6	284.2	284.1	282.8	284.1	284.2	285.6	287.7	291.0	292.9	296.0
25°	270.1	268.8	268.4	267.4	268.4	268.8	270.1	271.7	273.8	275.3	278.8
27.5°	258.3	257.6	256.9	257.2	256.9	257.6	258.3	258.4	259.4	261.5	263.5
30°	251.0	250.9	250.5	250.5	250.5	250.9	251.0	250.5	251.4	252.4	254.0
32.5°	245.0	245.0	245.2	245.2	245.2	245.0	245.0	244.1	244.5	244.8	245.6
35°	236.6	237.2	237.5	236.9	237.5	237.2	236.6	235.8	235.2	233.8	234.2
37.5°	228.9	229.5	230.1	230.7	230.1	229.5	228.9	227.3	225.9	224.8	223.4
40°	223.1	224.4	224.8	225.8	224.8	224.4	223.1	221.4	219.8	218.4	216.9
42.5°	217.5	219.0	220.0	220.2	220.0	219.0	217.5	215.7	213.4	211.8	209.6
45°	209.0	210.5	211.9	211.9	211.9	210.5	209.0	206.1	203.6	201.1	198.9
47.5°	200.2	202.4	203.7	204.1	203.7	202.4	200.2	197.1	193.6	190.5	187.5
50°	194.1	196.8	198.2	199.1	198.2	196.8	194.1	190.9	187.2	183.3	179.6
52.5°	188.3	190.9	192.7	193.2	192.7	190.9	188.3	184.2	179.8	175.6	172.4
55°	178.1	182.0	184.1	184.8	184.1	182.0	178.1	173.7	169.4	164.2	159.6
57.5°	168.5	172.1	174.6	175.1	174.6	172.1	168.5	163.3	157.8	152.3	147.3
60°	161.1	165.0	168.0	168.6	168.0	165.0	161.1	155.9	150.1	144.7	138.5
62.5°	153.5	157.6	160.4	161.8	160.4	157.6	153.5	148.1	141.8	135.7	129.6
65°	140.5	144.6	147.2	147.8	147.2	144.6	140.5	135.1	128.5	122.1	116.9
67.5°	126.2	130.3	132.0	133.1	132.0	130.3	126.2	121.1	114.6	108.0	102.1
70°	116.2	119.4	121.4	122.3	121.4	119.4	116.2	110.7	105.3	98.6	92.2
72.5°	104.8	108.2	110.4	110.6	110.4	108.2	104.8	100.1	94.4	88.1	82.5
75°	87.2	90.3	91.5	91.5	91.5	90.3	87.2	82.8	78.2	73.1	67.5
77.5°	69.1	70.6	72.1	72.4	72.1	70.6	69.1	65.9	62.0	57.0	52.8
80°	57.3	58.3	59.4	59.4	59.4	58.3	57.3	54.4	50.7	46.5	43.2
82.5°	45.2	46.1	47.2	47.0	47.2	46.1	45.2	43.0	39.9	37.1	34.1
85°	27.4	29.1	28.9	28.5	28.9	29.1	27.4	27.8	24.9	23.0	20.3
87.5°	15.0	15.3	15.7	16.0	15.7	15.3	15.0	14.4	13.0	12.1	11.4
90°	13.4	14.0	13.4	13.4	13.4	14.0	13.4	12.7	12.7	12.1	11.5
92.5°	54.7	51.3	49.1	49.1	49.1	51.3	54.7	62.2	75.0	94.2	125.2
95°	195.1	175.3	163.9	155.6	163.9	175.3	195.1	226.3	288.1	373.6	472.4
97.5°	486.6	448.2	429.0	415.8	429.0	448.2	486.6	532.3	598.8	661.2	697.9
100°	647.7	608.8	589.7	584.6	589.7	608.8	647.7	703.2	750.3	781.5	768.8
102.5°	783.9	755.7	735.6	731.5	735.6	755.7	783.9	817.9	837.6	828.5	765.2
105°	914.8	909.7	900.8	897.0	900.8	909.7	914.8	913.5	887.4	824.3	714.0
107.5°	935.9	950.4	956.8	958.4	956.8	950.4	935.9	904.3	847.5	758.6	641.2
110°	915.4	942.2	953.7	959.4	953.7	942.2	915.4	870.2	800.1	707.6	597.4



TEST NUMBER: P332510-930

CATALOG NUMBER: S124DIP-S350D810U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	871.6	904.0	920.1	929.4	920.1	904.0	871.6	820.2	750.1	662.8	565.2
115°	797.5	835.8	856.1	861.3	856.1	835.8	797.5	747.1	685.9	611.4	533.0
117.5°	735.6	767.7	788.3	792.3	788.3	767.7	735.6	692.6	640.7	582.0	517.1
120°	701.9	729.9	746.5	753.5	746.5	729.9	701.9	665.5	620.3	569.3	510.0
122.5°	677.9	701.9	715.9	722.9	715.9	701.9	677.9	647.2	607.6	561.1	503.9
125°	652.8	671.3	683.4	687.2	683.4	671.3	652.8	627.3	592.2	548.3	493.4
127.5°	635.9	652.3	662.5	666.3	662.5	652.3	635.9	610.3	576.9	533.0	480.7
130°	624.1	640.1	650.3	654.1	650.3	640.1	624.1	597.9	564.2	520.8	470.5
132.5°	608.8	626.8	636.5	640.3	636.5	626.8	608.8	583.2	549.4	507.0	459.7
135°	582.7	600.5	610.7	614.6	610.7	600.5	582.7	557.2	525.3	486.4	445.0
137.5°	552.0	569.6	578.0	582.7	578.0	569.6	552.0	528.2	499.5	466.7	431.6
140°	531.7	545.7	554.6	559.7	554.6	545.7	531.7	509.4	482.6	453.9	424.0
142.5°	510.8	523.7	531.7	535.2	531.7	523.7	510.8	491.0	467.8	443.2	416.8
145°	481.4	492.1	498.6	501.7	498.6	492.1	481.4	465.4	447.5	428.4	406.8
147.5°	456.7	466.0	470.8	472.0	470.8	466.0	456.7	445.0	431.0	415.6	398.4
150°	442.5	450.7	454.5	455.2	454.5	450.7	442.5	432.2	420.8	408.0	393.3
152.5°	430.2	436.9	439.2	439.9	439.2	436.9	430.2	421.5	412.1	400.3	387.8
155°	413.1	418.2	420.1	420.1	420.1	418.2	413.1	406.8	399.1	389.6	379.3
157.5°	397.8	401.6	402.8	402.8	402.8	401.6	397.8	393.0	386.9	378.8	370.2
160°	387.6	391.4	392.1	392.1	392.1	391.4	387.6	383.8	378.7	371.7	364.7
162.5°	377.9	381.7	382.4	381.9	382.4	381.7	377.9	375.1	370.6	365.0	359.1
165°	365.3	367.9	367.2	366.6	367.2	367.9	365.3	362.7	359.5	355.1	351.2
167.5°	353.4	355.1	355.0	354.4	355.0	355.1	353.4	352.1	350.3	346.7	343.7
170°	346.8	347.4	346.8	346.8	346.8	347.4	346.8	345.5	343.6	341.0	339.2
172.5°	340.1	340.8	340.1	339.2	340.1	340.8	340.1	339.4	338.0	336.5	335.1
175°	331.5	332.8	331.5	330.2	331.5	332.8	331.5	331.5	331.5	330.2	329.6
177.5°	326.5	327.0	326.0	325.0	326.0	327.0	326.5	327.0	326.5	326.5	326.0
180°	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5



TEST NUMBER: P332510-930

CATALOG NUMBER: S124DIP-S350D810U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8
2.5°	445.2	445.9	448.3	450.7	453.5	455.4	456.8	458.4	461.6	464.2	466.8
5°	417.2	418.2	423.1	426.6	432.6	437.8	441.9	446.3	451.5	458.7	465.2
7.5°	392.4	396.0	401.5	407.2	413.2	420.0	426.0	432.7	441.6	451.5	461.6
10°	378.4	382.5	388.2	394.8	400.6	408.5	415.8	423.7	434.0	445.9	457.9
12.5°	364.4	371.0	375.4	383.2	389.5	396.0	403.8	414.2	426.1	438.6	453.1
15°	346.7	350.4	358.9	363.1	372.0	382.0	389.8	400.1	411.7	428.4	444.6
17.5°	326.4	331.3	338.0	346.1	356.3	364.1	373.7	384.5	399.1	415.6	435.9
20°	313.2	317.2	325.5	334.4	345.2	353.5	363.7	374.1	389.2	406.8	428.0
22.5°	301.3	305.2	314.0	322.2	332.7	342.8	353.5	365.7	380.1	398.6	420.3
25°	282.9	288.0	295.8	304.3	314.3	325.9	337.5	348.3	363.7	383.2	406.3
27.5°	266.5	270.7	276.3	285.9	297.3	308.5	320.0	333.6	348.5	369.1	393.1
30°	256.1	259.9	265.5	274.3	285.0	296.9	308.9	322.0	337.5	357.9	382.5
32.5°	247.7	250.6	255.6	263.6	273.3	285.8	297.7	311.2	327.4	347.6	371.5
35°	235.4	237.9	239.9	247.4	256.1	267.7	279.6	294.1	309.7	328.8	352.7
37.5°	223.3	224.2	227.0	232.0	240.4	251.0	262.1	276.4	292.4	311.8	333.4
40°	215.9	216.3	218.0	222.7	230.0	240.0	250.9	264.9	280.1	298.5	319.9
42.5°	208.6	208.4	210.0	213.3	220.1	229.3	239.9	252.7	268.0	284.9	305.1
45°	197.2	197.2	196.8	199.5	205.1	214.0	222.9	235.2	247.9	264.6	281.5
47.5°	185.2	184.2	184.5	185.9	190.6	197.9	206.8	217.0	228.2	242.2	257.1
50°	177.5	175.9	175.4	176.9	181.2	187.5	196.1	204.9	215.6	227.9	240.6
52.5°	169.0	167.5	166.4	167.5	171.5	177.3	185.1	192.9	202.4	212.5	223.5
55°	155.9	154.2	153.6	154.0	156.9	161.5	168.0	175.2	182.4	190.6	198.4
57.5°	143.0	140.1	139.6	139.4	141.4	145.6	151.2	157.3	162.5	167.5	175.8
60°	134.5	131.0	129.9	129.6	131.2	134.7	139.7	145.9	149.5	153.0	160.1
62.5°	125.4	122.1	119.5	119.8	121.2	124.5	128.9	133.4	135.8	139.6	144.4
65°	111.4	107.1	105.2	104.6	105.3	108.0	111.5	114.4	117.2	118.7	123.3
67.5°	97.3	93.8	90.9	90.2	89.8	91.7	94.6	96.3	98.2	99.5	102.3
70°	87.4	84.3	80.9	79.7	79.5	81.0	83.7	84.0	86.7	87.2	90.1
72.5°	77.7	73.8	71.4	70.3	69.5	70.8	72.6	73.1	74.6	75.7	77.1
75°	62.5	59.6	57.3	55.6	55.0	55.8	55.8	56.7	57.7	58.3	60.0
77.5°	49.2	45.9	43.1	42.2	41.4	40.9	41.3	42.0	41.5	42.5	42.9
80°	39.9	36.4	34.3	34.0	32.8	31.9	31.6	32.2	31.5	31.9	33.0
82.5°	30.8	28.6	26.3	25.9	24.5	24.0	23.8	23.4	23.4	23.3	23.6
85°	18.3	17.0	15.4	14.5	13.9	13.0	13.0	12.6	12.1	11.7	12.0
87.5°	9.5	9.4	8.4	7.7	7.3	6.0	6.0	5.4	5.1	4.6	4.2
90°	10.8	11.5	10.2	8.9	8.9	5.1	5.1	4.5	3.8	1.9	0.7
92.5°	168.4	202.2	177.0	128.7	79.3	46.9	33.7	24.4	16.6	10.6	7.3
95°	534.3	519.6	392.1	239.7	135.2	79.7	52.9	37.6	29.4	22.9	21.0
97.5°	671.2	547.2	367.0	215.5	129.1	86.4	64.0	50.9	43.2	37.7	37.7
100°	675.7	512.6	332.8	202.8	130.7	93.1	72.6	60.6	52.9	48.4	48.4
102.5°	637.5	469.2	309.8	199.2	135.7	101.7	82.3	70.8	63.6	59.7	58.6
105°	568.0	418.2	290.1	200.8	147.9	117.3	98.8	87.3	79.7	76.5	74.6
107.5°	511.9	389.6	286.5	210.3	162.1	134.0	115.8	104.8	96.6	93.4	92.2
110°	483.9	379.9	287.5	217.4	172.8	144.7	127.5	116.0	108.4	105.2	104.0



TEST NUMBER: P332510-930

CATALOG NUMBER: S124DIP-S350D810U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	468.1	375.4	290.6	225.0	183.0	156.0	138.7	127.3	120.1	116.4	115.1
115°	453.2	372.9	296.4	237.2	198.9	173.4	156.2	144.1	137.7	133.2	131.3
117.5°	446.6	372.3	302.7	249.5	214.3	190.1	172.3	160.9	153.9	149.9	148.1
120°	443.0	372.3	307.3	258.2	225.0	200.8	183.0	172.1	165.1	160.6	159.4
122.5°	439.0	371.8	311.9	266.4	235.2	211.0	193.6	181.8	175.3	170.9	169.6
125°	432.2	371.0	318.8	278.6	249.2	226.3	208.5	196.3	189.3	185.5	183.0
127.5°	423.1	369.7	324.2	289.2	262.3	240.1	222.1	209.5	201.5	196.9	194.9
130°	417.6	369.1	328.3	295.8	270.9	249.2	230.8	218.7	209.1	204.0	201.5
132.5°	412.5	368.6	331.9	302.4	278.1	256.4	239.0	225.8	216.8	210.1	208.1
135°	404.8	367.9	337.2	311.1	288.1	267.1	250.5	237.2	226.3	220.0	217.4
137.5°	398.2	367.7	340.4	317.2	295.8	276.1	260.3	246.5	236.1	229.1	226.7
140°	394.6	367.2	343.0	321.3	300.9	281.8	266.4	253.1	242.2	235.2	233.3
142.5°	391.6	367.2	345.0	324.3	305.5	286.9	272.1	259.2	248.9	242.4	240.4
145°	386.3	365.9	346.2	327.7	310.5	293.9	279.9	267.7	258.9	252.4	250.5
147.5°	381.6	363.6	346.8	330.6	315.6	300.0	287.4	277.3	268.2	262.5	261.9
150°	378.1	362.1	346.8	332.2	318.1	304.1	292.0	282.4	274.8	269.7	269.0
152.5°	374.0	359.5	345.8	333.1	320.2	307.7	296.6	288.0	280.9	275.8	275.7
155°	367.9	355.7	344.2	334.0	323.2	312.3	302.8	295.8	289.4	285.6	284.9
157.5°	361.6	351.8	342.6	334.0	325.4	316.2	308.7	302.6	297.6	294.0	294.0
160°	357.0	348.7	341.0	334.0	326.4	318.8	311.8	306.6	302.1	299.6	299.6
162.5°	352.9	345.7	339.6	334.0	327.4	320.2	314.8	310.2	306.2	304.2	304.8
165°	346.2	341.0	336.6	332.8	327.7	322.0	318.1	315.0	311.8	310.5	310.5
167.5°	340.1	336.5	333.5	331.3	327.6	323.3	320.4	318.6	316.2	315.6	316.2
170°	336.0	333.4	331.5	330.2	327.0	323.8	322.0	320.7	318.8	318.1	318.8
172.5°	332.4	330.4	329.5	329.2	326.5	324.3	322.9	322.2	320.8	320.7	321.3
175°	328.3	327.0	327.0	327.7	325.8	324.5	324.5	323.8	323.2	323.2	323.8
177.5°	325.5	325.0	325.0	326.0	325.0	324.5	324.5	324.5	324.0	324.5	325.0
180°	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5



TEST NUMBER: P332510-930

CATALOG NUMBER: S124DIP-S350D810U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8
2.5°	468.9	470.4	472.5	475.8	477.0	478.6	480.8	480.6	481.2	483.6	488.4
5°	470.6	476.6	482.4	489.3	496.7	501.5	508.0	512.1	516.2	521.4	530.3
7.5°	471.3	480.8	491.4	503.6	514.5	526.9	536.7	545.9	554.2	565.2	575.8
10°	470.3	483.0	496.7	512.1	528.5	542.4	555.0	569.2	581.4	594.7	606.7
12.5°	468.2	483.6	501.9	519.2	538.3	558.9	574.5	589.0	605.1	620.4	639.0
15°	463.7	484.7	506.1	528.9	554.6	578.3	600.9	619.5	636.9	659.9	684.0
17.5°	457.9	480.5	507.6	535.2	562.0	589.1	617.0	645.1	667.1	695.6	714.4
20°	452.5	478.7	506.5	539.3	566.1	599.9	627.7	654.8	685.0	713.4	736.0
22.5°	444.9	473.6	503.1	535.7	571.0	604.9	636.9	666.4	696.6	727.4	754.7
25°	435.3	461.4	496.3	533.3	568.4	605.1	642.0	679.0	711.4	744.0	769.5
27.5°	419.0	451.8	484.4	522.6	561.6	603.1	642.5	681.3	715.3	742.1	757.8
30°	410.6	439.2	474.5	512.9	555.1	599.7	640.8	678.8	710.5	731.9	738.3
32.5°	398.3	427.7	462.3	502.1	546.8	592.6	635.4	671.2	697.7	708.9	701.2
35°	379.9	406.6	441.5	482.2	528.7	577.5	619.8	650.0	663.6	653.0	626.6
37.5°	357.9	384.3	419.4	459.4	507.5	557.2	595.3	617.2	612.7	586.3	546.9
40°	342.5	367.2	400.6	443.8	490.6	540.5	574.1	585.8	573.5	535.7	493.7
42.5°	325.4	349.4	382.9	424.7	474.3	520.2	549.5	550.5	529.8	484.5	442.5
45°	299.3	322.2	353.8	397.3	443.2	486.4	505.7	496.3	458.0	414.5	372.2
47.5°	273.5	293.4	324.7	365.8	409.4	445.8	455.4	438.4	397.7	355.3	316.2
50°	254.7	274.8	304.1	343.5	385.6	416.9	421.6	399.0	359.1	316.4	285.8
52.5°	236.6	256.6	284.8	321.2	359.7	388.1	388.2	362.2	322.4	284.4	255.8
55°	210.1	228.0	253.6	286.2	320.5	342.7	337.3	310.3	275.7	242.7	217.8
57.5°	184.6	200.2	223.6	250.9	281.1	299.5	290.5	264.5	233.7	205.6	186.8
60°	168.0	183.0	203.0	228.7	254.1	268.4	259.9	236.4	208.0	185.4	169.0
62.5°	152.0	164.5	183.8	206.1	229.8	240.3	232.8	209.5	185.0	164.6	151.2
65°	129.3	139.5	154.9	174.1	191.2	200.3	194.0	172.3	153.6	138.9	128.3
67.5°	108.0	116.0	127.8	143.1	157.7	162.6	156.8	141.7	125.9	114.1	106.6
70°	93.4	100.9	110.7	122.5	135.3	140.5	134.7	122.7	109.8	99.0	91.6
72.5°	80.6	86.4	94.7	104.8	114.7	119.9	116.0	104.5	93.6	85.5	79.3
75°	61.4	66.4	72.2	79.3	87.0	90.5	87.0	79.1	71.6	65.6	61.1
77.5°	44.6	47.3	51.8	57.2	62.0	64.6	61.6	56.3	51.6	47.5	45.3
80°	34.0	35.9	39.0	43.2	46.5	49.0	47.0	42.6	39.0	36.3	35.3
82.5°	24.7	26.0	28.0	31.1	33.3	34.7	33.8	30.6	29.1	26.7	25.8
85°	12.1	13.0	14.3	15.2	17.2	17.4	17.5	16.2	14.8	14.3	13.5
87.5°	4.6	5.1	5.7	6.3	6.8	7.8	7.7	7.9	7.6	7.3	6.8
90°	1.9	3.8	4.5	5.1	5.1	8.9	8.9	10.2	11.5	10.8	11.5
92.5°	10.6	16.6	24.4	33.7	46.9	79.3	128.7	177.0	202.2	168.4	125.2
95°	22.9	29.4	37.6	52.9	79.7	135.2	239.7	392.1	519.6	534.3	472.4
97.5°	37.7	43.2	50.9	64.0	86.4	129.1	215.5	367.0	547.2	671.2	697.9
100°	48.4	52.9	60.6	72.6	93.1	130.7	202.8	332.8	512.6	675.7	768.8
102.5°	59.7	63.6	70.8	82.3	101.7	135.7	199.2	309.8	469.2	637.5	765.2
105°	76.5	79.7	87.3	98.8	117.3	147.9	200.8	290.1	418.2	568.0	714.0
107.5°	93.4	96.6	104.8	115.8	134.0	162.1	210.3	286.5	389.6	511.9	641.2
110°	105.2	108.4	116.0	127.5	144.7	172.8	217.4	287.5	379.9	483.9	597.4



TEST NUMBER: P332510-930

CATALOG NUMBER: S124DIP-S350D810U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	116.4	120.1	127.3	138.7	156.0	183.0	225.0	290.6	375.4	468.1	565.2
115°	133.2	137.7	144.1	156.2	173.4	198.9	237.2	296.4	372.9	453.2	533.0
117.5°	149.9	153.9	160.9	172.3	190.1	214.3	249.5	302.7	372.3	446.6	517.1
120°	160.6	165.1	172.1	183.0	200.8	225.0	258.2	307.3	372.3	443.0	510.0
122.5°	170.9	175.3	181.8	193.6	211.0	235.2	266.4	311.9	371.8	439.0	503.9
125°	185.5	189.3	196.3	208.5	226.3	249.2	278.6	318.8	371.0	432.2	493.4
127.5°	196.9	201.5	209.5	222.1	240.1	262.3	289.2	324.2	369.7	423.1	480.7
130°	204.0	209.1	218.7	230.8	249.2	270.9	295.8	328.3	369.1	417.6	470.5
132.5°	210.1	216.8	225.8	239.0	256.4	278.1	302.4	331.9	368.6	412.5	459.7
135°	220.0	226.3	237.2	250.5	267.1	288.1	311.1	337.2	367.9	404.8	445.0
137.5°	229.1	236.1	246.5	260.3	276.1	295.8	317.2	340.4	367.7	398.2	431.6
140°	235.2	242.2	253.1	266.4	281.8	300.9	321.3	343.0	367.2	394.6	424.0
142.5°	242.4	248.9	259.2	272.1	286.9	305.5	324.3	345.0	367.2	391.6	416.8
145°	252.4	258.9	267.7	279.9	293.9	310.5	327.7	346.2	365.9	386.3	406.8
147.5°	262.5	268.2	277.3	287.4	300.0	315.6	330.6	346.8	363.6	381.6	398.4
150°	269.7	274.8	282.4	292.0	304.1	318.1	332.2	346.8	362.1	378.1	393.3
152.5°	275.8	280.9	288.0	296.6	307.7	320.2	333.1	345.8	359.5	374.0	387.8
155°	285.6	289.4	295.8	302.8	312.3	323.2	334.0	344.2	355.7	367.9	379.3
157.5°	294.0	297.6	302.6	308.7	316.2	325.4	334.0	342.6	351.8	361.6	370.2
160°	299.6	302.1	306.6	311.8	318.8	326.4	334.0	341.0	348.7	357.0	364.7
162.5°	304.2	306.2	310.2	314.8	320.2	327.4	334.0	339.6	345.7	352.9	359.1
165°	310.5	311.8	315.0	318.1	322.0	327.7	332.8	336.6	341.0	346.2	351.2
167.5°	315.6	316.2	318.6	320.4	323.3	327.6	331.3	333.5	336.5	340.1	343.7
170°	318.1	318.8	320.7	322.0	323.8	327.0	330.2	331.5	333.4	336.0	339.2
172.5°	320.7	320.8	322.2	322.9	324.3	326.5	329.2	329.5	330.4	332.4	335.1
175°	323.2	323.2	323.8	324.5	324.5	325.8	327.7	327.0	327.0	328.3	329.6
177.5°	324.5	324.0	324.5	324.5	324.5	325.0	326.0	325.0	325.0	325.5	326.0
180°	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5



TEST NUMBER: P332510-930

CATALOG NUMBER: S124DIP-S350D810U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	465.8	465.8	465.8	465.8	465.8	465.8	465.8
2.5°	491.0	491.3	492.7	493.7	494.1	495.6	495.7
5°	534.1	537.4	543.7	544.3	545.3	550.3	546.4
7.5°	584.7	593.0	598.5	603.5	605.2	607.4	607.0
10°	617.1	629.4	635.6	645.5	645.8	648.3	646.8
12.5°	649.6	664.0	675.2	677.1	685.3	686.6	688.8
15°	695.8	711.0	726.7	732.3	743.6	746.3	750.6
17.5°	739.2	754.7	765.7	780.2	784.9	791.1	786.8
20°	763.0	779.9	793.9	805.2	810.0	813.5	813.1
22.5°	777.3	794.4	805.7	814.3	818.8	820.3	820.2
25°	786.3	796.1	799.6	802.9	797.9	796.1	796.9
27.5°	761.2	758.7	749.7	737.8	725.5	715.7	710.3
30°	726.8	711.8	698.1	674.2	661.9	654.5	647.9
32.5°	678.1	654.2	627.9	605.9	591.9	581.1	579.4
35°	594.5	558.6	526.4	499.5	485.7	473.9	471.2
37.5°	505.4	468.1	439.1	415.5	400.6	392.2	384.5
40°	446.3	414.3	385.7	365.7	354.2	348.3	343.5
42.5°	400.8	371.5	343.1	327.8	317.6	313.9	311.0
45°	337.9	310.6	291.0	279.4	273.5	267.3	264.3
47.5°	287.5	265.4	252.4	242.6	236.1	232.4	230.6
50°	258.9	240.8	229.3	221.7	215.9	213.0	211.5
52.5°	233.7	218.7	209.0	203.0	199.1	197.0	196.3
55°	201.2	189.9	183.7	178.5	175.6	173.7	172.9
57.5°	175.0	166.2	161.2	156.9	155.7	154.2	153.6
60°	157.7	150.9	146.7	143.7	142.8	140.9	141.2
62.5°	142.4	136.8	133.2	131.6	130.3	128.7	129.2
65°	120.4	116.3	114.4	112.9	111.4	110.4	111.1
67.5°	101.0	98.2	95.6	94.7	94.0	93.8	93.0
70°	88.4	86.1	83.7	83.2	83.2	82.4	82.2
72.5°	76.1	74.5	73.0	72.5	71.9	72.2	71.4
75°	58.9	57.5	56.9	56.3	56.2	56.2	55.6
77.5°	43.5	42.5	41.6	41.6	40.8	40.6	40.5
80°	33.0	32.6	31.9	31.9	31.5	31.6	31.2
82.5°	24.8	24.3	24.1	23.8	23.2	23.3	22.9
85°	13.3	12.7	12.6	12.0	11.6	12.0	11.6
87.5°	7.1	7.0	6.8	6.7	6.7	6.5	6.0
90°	12.1	12.7	12.7	13.4	14.0	13.4	13.4
92.5°	94.2	75.0	62.2	54.7	51.3	49.1	49.1
95°	373.6	288.1	226.3	195.1	175.3	163.9	155.6
97.5°	661.2	598.8	532.3	486.6	448.2	429.0	415.8
100°	781.5	750.3	703.2	647.7	608.8	589.7	584.6
102.5°	828.5	837.6	817.9	783.9	755.7	735.6	731.5
105°	824.3	887.4	913.5	914.8	909.7	900.8	897.0
107.5°	758.6	847.5	904.3	935.9	950.4	956.8	958.4
110°	707.6	800.1	870.2	915.4	942.2	953.7	959.4



TEST NUMBER: P332510-930

CATALOG NUMBER: S124DIP-S350D810U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	662.8	750.1	820.2	871.6	904.0	920.1	929.4
115°	611.4	685.9	747.1	797.5	835.8	856.1	861.3
117.5°	582.0	640.7	692.6	735.6	767.7	788.3	792.3
120°	569.3	620.3	665.5	701.9	729.9	746.5	753.5
122.5°	561.1	607.6	647.2	677.9	701.9	715.9	722.9
125°	548.3	592.2	627.3	652.8	671.3	683.4	687.2
127.5°	533.0	576.9	610.3	635.9	652.3	662.5	666.3
130°	520.8	564.2	597.9	624.1	640.1	650.3	654.1
132.5°	507.0	549.4	583.2	608.8	626.8	636.5	640.3
135°	486.4	525.3	557.2	582.7	600.5	610.7	614.6
137.5°	466.7	499.5	528.2	552.0	569.6	578.0	582.7
140°	453.9	482.6	509.4	531.7	545.7	554.6	559.7
142.5°	443.2	467.8	491.0	510.8	523.7	531.7	535.2
145°	428.4	447.5	465.4	481.4	492.1	498.6	501.7
147.5°	415.6	431.0	445.0	456.7	466.0	470.8	472.0
150°	408.0	420.8	432.2	442.5	450.7	454.5	455.2
152.5°	400.3	412.1	421.5	430.2	436.9	439.2	439.9
155°	389.6	399.1	406.8	413.1	418.2	420.1	420.1
157.5°	378.8	386.9	393.0	397.8	401.6	402.8	402.8
160°	371.7	378.7	383.8	387.6	391.4	392.1	392.1
162.5°	365.0	370.6	375.1	377.9	381.7	382.4	381.9
165°	355.1	359.5	362.7	365.3	367.9	367.2	366.6
167.5°	346.7	350.3	352.1	353.4	355.1	355.0	354.4
170°	341.0	343.6	345.5	346.8	347.4	346.8	346.8
172.5°	336.5	338.0	339.4	340.1	340.8	340.1	339.2
175°	330.2	331.5	331.5	331.5	332.8	331.5	330.2
177.5°	326.5	326.5	327.0	326.5	327.0	326.0	325.0
180°	324.5	324.5	324.5	324.5	324.5	324.5	324.5

(END OF REPORT)