

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332537-930

Luminaire Tested: **S124DIP-S575D365U930-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332537-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIP-S575D365U930-4F0-1E-UDD-A4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3180.3 lumens
Efficiency: N/A
Efficacy: 115.6 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 27.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332537-930

CATALOG NUMBER: S124DIP-S575D365U930-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332537-930

CATALOG NUMBER: S124DIP-S575D365U930-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	92	92	92	81	81	81	71	71	71	66
1	102	97	94	90	96	92	89	85	82	79	77	72	70	68	63	62	61	57
2	93	85	79	74	87	81	75	71	72	68	64	64	61	58	56	54	52	48
3	85	75	68	62	80	71	65	59	64	59	54	57	53	49	50	47	44	41
4	78	67	59	53	73	64	56	51	57	51	47	51	46	42	45	41	38	35
5	72	60	52	46	67	57	49	44	51	45	40	46	41	37	41	37	34	31
6	66	54	46	40	62	51	44	38	46	40	35	41	36	33	37	33	30	27
7	61	49	41	35	58	47	39	34	42	36	31	38	33	29	34	30	27	24
8	57	45	37	31	54	42	35	30	38	32	28	35	30	26	31	27	24	22
9	53	41	33	28	50	39	32	27	35	29	25	32	27	23	29	25	22	20
10	50	38	30	25	47	36	29	24	33	27	23	30	25	21	27	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	6181	6181	6181	6181
5°	7280	6198	5471	6198
10°	8716	6171	4925	6171
15°	10313	6108	4523	6108
20°	11485	6045	4164	6045
25°	11670	5951	3917	5951
30°	9930	5862	3838	5862
35°	7634	5714	3840	5714
40°	5951	5542	3911	5542
45°	4962	5284	3976	5284
50°	4366	4968	4111	4968
55°	4000	4590	4277	4590
60°	3749	4251	4477	4251
65°	3490	3872	4642	3872
70°	3189	3496	4747	3496
75°	2851	3079	4688	3079
80°	2390	2520	4542	2520
85°	1760	1815	4353	1815



TEST NUMBER: P332537-930

CATALOG NUMBER: S124DIP-S575D365U930-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.6	2.3
10°-20°	230.0	7.2
20°-30°	364.6	11.5
30°-40°	405.8	12.8
40°-50°	369.4	11.6
50°-60°	301.9	9.5
60°-70°	215.5	6.8
70°-80°	118.7	3.7
80°-90°	33.2	1.0
90°-100°	105.9	3.3
100°-110°	220.5	6.9
110°-120°	197.5	6.2
120°-130°	166.1	5.2
130°-140°	138.5	4.4
140°-150°	105.8	3.3
150°-160°	74.4	2.3
160°-170°	43.7	1.4
170°-180°	14.2	0.4
0°-30°	669.2	21.0
0°-40°	1075.0	33.8
0°-60°	1746.2	54.9
0°-90°	2113.6	66.5
90°-120°	523.9	16.5
90°-150°	934.3	29.4
90°-180°	1067.0	33.6
0°-180°	3180.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	766	766	766	766	766	
5°	898	765	675	765	898	91
15°	1234	731	541	731	1234	349
25°	1310	668	440	668	1310	578
35°	775	580	390	580	775	492
45°	435	463	348	463	435	342
55°	284	326	304	326	284	257
65°	183	203	243	203	183	181
75°	91	99	150	99	91	97
85°	19	20	47	20	19	23
90°	6	0	6	0	6	6
95°	70	10	70	10	70	109
105°	405	34	405	34	405	401
115°	389	59	389	59	389	386
125°	311	83	311	83	311	282
135°	278	98	278	98	278	214
145°	227	113	227	113	227	144
155°	190	129	190	129	190	89
165°	166	140	166	140	166	47
175°	149	146	149	146	149	15
180°	147	147	147	147	147	



TEST NUMBER: P332537-930

CATALOG NUMBER: S124DIP-S575D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7
2.5°	815.0	814.7	812.2	811.7	809.9	807.6	807.1	803.1	794.9	791.2	790.1
5°	898.4	904.7	896.4	894.9	893.9	883.5	878.1	871.7	857.1	848.6	841.9
7.5°	997.8	998.6	995.0	992.1	984.0	974.9	961.2	946.6	929.2	911.1	897.5
10°	1063.3	1065.8	1061.8	1061.1	1044.9	1034.8	1014.5	997.4	977.6	955.8	935.8
12.5°	1132.4	1128.8	1126.7	1113.1	1110.1	1091.6	1068.0	1050.4	1020.0	994.8	968.2
15°	1234.0	1227.0	1222.5	1203.9	1194.7	1169.0	1143.9	1124.5	1084.9	1047.2	1018.6
17.5°	1293.6	1300.6	1290.3	1282.6	1258.8	1240.8	1215.2	1174.6	1143.5	1096.7	1060.6
20°	1336.8	1337.4	1331.7	1323.7	1305.0	1282.2	1254.3	1209.9	1172.7	1126.1	1076.6
22.5°	1348.4	1348.6	1346.1	1338.7	1324.5	1306.0	1277.9	1240.8	1195.9	1145.2	1095.7
25°	1310.1	1308.9	1311.7	1320.0	1314.6	1308.9	1292.7	1265.1	1223.2	1169.5	1116.3
27.5°	1167.8	1176.5	1192.6	1212.9	1232.5	1247.3	1251.6	1245.9	1219.9	1175.8	1120.1
30°	1065.2	1076.0	1088.0	1108.4	1147.7	1170.2	1195.0	1213.7	1203.2	1168.0	1116.0
32.5°	952.5	955.2	973.1	996.2	1032.3	1075.5	1114.8	1152.8	1165.4	1147.0	1103.5
35°	774.6	779.1	798.4	821.3	865.4	918.4	977.4	1030.0	1073.5	1091.0	1068.7
37.5°	632.2	644.9	658.5	683.1	721.9	769.6	831.0	899.0	963.8	1007.2	1014.6
40°	564.7	572.6	582.4	601.1	634.1	681.1	733.7	811.8	880.6	942.8	963.1
42.5°	511.4	516.0	522.0	538.9	564.1	610.7	658.8	727.5	796.6	871.0	905.0
45°	434.6	439.4	449.5	459.3	478.3	510.7	555.5	611.9	681.3	753.1	815.9
47.5°	379.1	382.2	388.2	398.8	414.9	436.3	472.6	519.8	584.2	653.8	720.7
50°	347.6	350.2	355.0	364.5	376.8	395.9	425.7	469.8	520.2	590.4	656.0
52.5°	322.8	323.8	327.3	333.8	343.6	359.6	384.1	420.5	467.5	529.9	595.3
55°	284.2	285.5	288.7	293.4	302.0	312.2	330.8	358.2	399.1	453.3	510.1
57.5°	252.5	253.4	256.1	257.9	265.0	273.2	287.6	307.0	338.1	384.1	434.8
60°	232.2	231.5	234.7	236.4	241.1	248.1	259.2	277.9	304.8	341.9	388.6
62.5°	212.4	211.5	214.2	216.3	219.0	224.9	234.1	248.7	270.6	304.2	344.5
65°	182.7	181.5	183.0	185.6	188.1	191.3	198.0	210.9	228.4	252.5	283.2
67.5°	152.9	154.3	154.5	155.7	157.2	161.5	166.1	175.3	187.6	206.9	232.9
70°	135.1	135.4	136.7	136.7	137.7	141.5	145.3	150.7	162.7	180.5	201.8
72.5°	117.4	118.7	118.2	119.2	119.9	122.5	125.2	130.4	140.6	153.8	171.8
75°	91.4	92.3	92.3	92.6	93.6	94.5	96.8	100.5	107.9	117.6	130.0
77.5°	66.6	66.8	67.2	68.3	68.3	69.9	71.5	74.5	78.2	84.9	92.5
80°	51.4	52.0	51.7	52.3	52.3	53.6	54.2	58.0	59.6	64.1	70.1
82.5°	37.7	38.3	38.2	39.1	39.6	39.9	40.8	42.3	43.9	47.9	50.3
85°	19.0	19.6	19.0	19.6	20.6	21.0	21.9	22.2	23.5	24.5	26.7
87.5°	6.8	7.6	7.6	7.8	8.2	8.5	8.7	8.4	9.4	9.7	10.6
90°	6.0	6.0	6.4	6.0	5.8	5.8	5.5	5.2	4.9	5.2	4.6
92.5°	22.2	22.2	23.2	24.7	28.1	33.9	42.6	56.6	76.1	91.4	80.0
95°	70.3	74.0	79.2	88.1	102.3	130.2	168.8	213.5	241.5	234.8	177.2
97.5°	187.9	194.0	202.6	219.9	240.6	270.7	298.9	315.4	303.4	247.4	165.8
100°	264.2	266.5	275.2	292.8	317.8	339.2	353.3	347.5	305.4	231.7	150.4
102.5°	330.6	332.5	341.6	354.3	369.7	378.5	374.5	345.9	288.1	212.1	140.1
105°	405.4	407.2	411.2	413.5	412.9	401.1	372.6	322.7	256.7	189.0	131.1
107.5°	433.2	432.4	429.6	423.0	408.8	383.0	342.9	289.8	231.4	176.1	129.5
110°	433.7	431.0	425.9	413.8	393.3	361.7	319.8	270.0	218.7	171.7	130.0



TEST NUMBER: P332537-930

CATALOG NUMBER: S124DIP-S575D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	420.0	415.9	408.6	394.0	370.7	339.0	299.5	255.4	211.6	169.7	131.3
115°	389.3	387.0	377.7	360.4	337.7	310.1	276.3	240.9	204.9	168.6	134.0
117.5°	358.1	356.3	347.0	332.5	313.1	289.6	263.1	233.7	201.9	168.3	136.8
120°	340.6	337.5	330.0	317.2	300.8	280.4	257.3	230.5	200.2	168.3	138.9
122.5°	326.8	323.6	317.2	306.4	292.5	274.6	253.6	227.7	198.4	168.0	141.0
125°	310.6	308.9	303.5	295.1	283.6	267.7	247.8	223.1	195.3	167.7	144.1
127.5°	301.2	299.5	294.8	287.4	275.8	260.8	240.9	217.3	191.3	167.1	146.6
130°	295.6	293.9	289.3	282.1	270.3	255.0	235.5	212.6	188.7	166.8	148.4
132.5°	289.4	287.7	283.3	275.2	263.6	248.3	229.2	207.8	186.5	166.6	150.0
135°	277.8	276.1	271.4	263.3	251.8	237.4	219.9	201.1	183.0	166.2	152.5
137.5°	263.3	261.3	257.5	249.6	238.7	225.8	210.9	195.1	180.0	166.2	153.8
140°	253.0	250.7	246.6	240.4	230.2	218.1	205.1	191.6	178.4	166.0	155.0
142.5°	241.9	240.4	236.8	230.9	221.9	211.4	200.3	188.4	177.0	166.0	156.0
145°	226.7	225.3	222.4	217.5	210.3	202.3	193.6	183.8	174.6	165.4	156.5
147.5°	213.4	212.8	210.7	206.4	201.1	194.8	187.8	180.1	172.5	164.4	156.8
150°	205.7	205.5	203.7	200.0	195.3	190.2	184.4	177.8	170.9	163.6	156.8
152.5°	198.9	198.5	197.5	194.4	190.5	186.3	181.0	175.3	169.0	162.5	156.3
155°	189.9	189.9	189.0	186.7	183.8	180.3	176.0	171.5	166.2	160.8	155.6
157.5°	182.1	182.1	181.6	179.8	177.7	174.9	171.2	167.4	163.5	159.0	154.8
160°	177.2	177.2	176.9	175.2	173.5	171.1	168.0	164.9	161.3	157.6	154.2
162.5°	172.6	172.8	172.5	170.8	169.6	167.5	165.0	162.3	159.6	156.2	153.4
165°	165.7	166.0	166.2	165.1	164.0	162.5	160.5	158.7	156.5	154.2	152.1
167.5°	160.2	160.5	160.5	159.7	159.1	158.3	156.7	155.4	153.7	152.1	150.7
170°	156.8	156.8	157.0	156.8	156.2	155.3	154.2	153.3	151.9	150.7	149.9
172.5°	153.3	153.8	154.0	153.8	153.4	152.8	152.1	151.5	150.3	149.3	149.0
175°	149.3	149.9	150.4	149.9	149.9	149.9	149.3	149.0	148.4	147.8	147.8
177.5°	146.9	147.3	147.8	147.6	147.8	147.6	147.6	147.3	147.2	146.9	146.9
180°	146.7	146.7	146.7	146.7	146.7	146.7	146.7	146.7	146.7	146.7	146.7



TEST NUMBER: P332537-930

CATALOG NUMBER: S124DIP-S575D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7
2.5°	790.4	786.8	784.3	782.3	776.7	773.4	770.9	767.3	763.2	758.9	753.6
5°	835.3	824.4	816.5	804.5	793.0	783.5	773.7	764.8	754.0	742.3	733.7
7.5°	882.4	866.3	845.8	827.9	807.9	790.4	774.9	758.9	742.2	726.1	711.3
10°	912.3	891.7	868.9	841.9	816.5	794.0	773.1	752.8	733.1	713.4	696.6
12.5°	944.5	918.8	885.1	853.5	825.2	795.0	769.7	744.9	721.1	700.5	680.9
15°	987.8	950.7	911.7	869.5	832.1	796.9	762.3	730.8	704.3	676.9	657.9
17.5°	1014.4	968.5	923.9	879.8	834.5	790.0	752.8	716.6	683.1	656.1	632.1
20°	1031.9	986.3	930.7	886.6	832.7	787.0	743.9	703.6	668.7	639.8	615.1
22.5°	1047.2	994.3	938.8	880.8	827.1	778.6	731.4	690.9	655.3	624.8	601.1
25°	1055.4	994.8	934.5	876.8	815.9	758.5	715.7	668.1	630.0	597.9	572.6
27.5°	1056.3	991.5	923.3	859.2	796.3	742.8	688.8	646.2	606.7	572.8	548.5
30°	1053.4	985.9	912.6	843.2	780.1	721.9	675.1	628.8	588.4	554.8	529.5
32.5°	1044.6	974.2	898.9	825.4	760.0	703.2	654.8	610.7	571.4	538.3	511.7
35°	1018.9	949.4	869.2	792.7	725.8	668.4	624.6	579.8	540.5	509.2	483.5
37.5°	978.8	915.9	834.4	755.2	689.5	631.9	588.4	548.0	512.6	480.6	454.3
40°	943.7	888.5	806.7	729.6	658.5	603.6	563.0	525.9	490.7	460.6	435.5
42.5°	903.4	855.2	779.8	698.1	629.6	574.5	534.9	501.6	468.4	440.6	415.5
45°	831.4	799.7	728.6	653.1	581.8	529.8	492.0	462.8	434.9	407.6	386.7
47.5°	748.7	733.0	673.1	601.4	533.7	482.4	449.7	422.7	398.3	375.1	356.7
50°	693.1	685.5	633.8	564.7	499.9	451.8	418.7	395.6	374.6	354.3	336.9
52.5°	638.3	638.1	591.4	528.1	468.2	421.8	389.1	367.4	349.3	332.7	317.1
55°	554.5	563.4	526.9	470.4	416.9	375.0	345.4	326.1	313.4	299.8	288.0
57.5°	477.5	492.3	462.2	412.5	367.7	329.1	303.5	288.9	275.4	267.2	258.6
60°	427.3	441.2	417.8	375.9	333.7	300.7	276.3	263.3	251.5	245.8	239.8
62.5°	382.6	395.1	377.6	338.8	302.2	270.5	249.9	237.4	229.5	223.2	219.2
65°	318.8	329.3	314.4	286.2	254.7	229.3	212.5	202.7	195.1	192.6	188.1
67.5°	257.7	267.3	259.2	235.2	210.0	190.8	177.7	168.2	163.7	161.4	158.3
70°	221.4	231.0	222.3	201.5	182.1	165.9	153.5	148.1	143.4	142.4	138.0
72.5°	190.7	197.2	188.6	172.3	155.7	142.0	132.5	126.9	124.3	122.6	120.3
75°	143.1	148.8	143.1	130.4	118.6	109.1	100.9	98.7	95.8	94.8	93.3
77.5°	101.3	106.2	101.8	93.9	85.1	77.8	73.4	70.5	69.9	68.2	69.0
80°	77.4	80.6	76.5	71.1	64.1	59.0	55.8	54.2	52.3	51.7	53.0
82.5°	55.6	57.0	54.9	51.3	46.1	42.7	40.6	38.7	38.4	38.5	38.5
85°	28.9	28.5	28.2	25.0	23.5	21.3	20.0	19.6	19.3	20.0	20.6
87.5°	10.4	10.7	10.1	9.0	8.2	7.4	7.0	6.7	7.0	7.4	7.7
90°	4.0	4.0	2.3	2.3	2.0	1.7	0.9	0.3	0.9	1.7	2.0
92.5°	58.2	35.9	21.2	15.2	11.0	7.5	4.8	3.3	4.8	7.5	11.0
95°	108.4	61.1	36.0	23.9	17.0	13.3	10.4	9.5	10.4	13.3	17.0
97.5°	97.4	58.4	39.1	28.9	23.0	19.6	17.0	17.0	17.0	19.6	23.0
100°	91.6	59.1	42.1	32.9	27.4	23.9	21.9	21.9	21.9	23.9	27.4
102.5°	90.0	61.4	46.0	37.3	32.0	28.8	27.0	26.5	27.0	28.8	32.0
105°	90.7	66.9	53.0	44.7	39.5	36.0	34.6	33.8	34.6	36.0	39.5
107.5°	95.1	73.2	60.6	52.3	47.4	43.7	42.2	41.7	42.2	43.7	47.4
110°	98.2	78.1	65.4	57.6	52.4	49.0	47.5	47.0	47.5	49.0	52.4



TEST NUMBER: P332537-930

CATALOG NUMBER: S124DIP-S575D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	101.7	82.7	70.4	62.7	57.5	54.3	52.6	52.0	52.6	54.3	57.5
115°	107.2	89.9	78.4	70.6	65.1	62.2	60.3	59.4	60.3	62.2	65.1
117.5°	112.8	96.9	85.9	77.9	72.7	69.5	67.8	66.9	67.8	69.5	72.7
120°	116.7	101.7	90.7	82.7	77.8	74.6	72.6	72.1	72.6	74.6	77.8
122.5°	120.4	106.3	95.4	87.6	82.2	79.2	77.2	76.6	77.2	79.2	82.2
125°	125.9	112.7	102.3	94.2	88.8	85.6	83.8	82.7	83.8	85.6	88.8
127.5°	130.7	118.5	108.5	100.4	94.7	91.1	88.9	88.1	88.9	91.1	94.7
130°	133.7	122.5	112.7	104.3	98.8	94.5	92.2	91.1	92.2	94.5	98.8
132.5°	136.7	125.7	115.9	108.0	102.1	98.0	95.0	94.1	95.0	98.0	102.1
135°	140.6	130.2	120.7	113.2	107.2	102.3	99.4	98.2	99.4	102.3	107.2
137.5°	143.4	133.7	124.8	117.6	111.4	106.7	103.5	102.5	103.5	106.7	111.4
140°	145.2	136.0	127.3	120.4	114.4	109.5	106.3	105.5	106.3	109.5	114.4
142.5°	146.6	138.1	129.6	122.9	117.2	112.5	109.6	108.7	109.6	112.5	117.2
145°	148.1	140.3	132.8	126.5	121.0	117.0	114.1	113.2	114.1	117.0	121.0
147.5°	149.4	142.6	135.6	129.9	125.3	121.2	118.6	118.4	118.6	121.2	125.3
150°	150.1	143.8	137.5	132.0	127.7	124.2	121.9	121.6	121.9	124.2	127.7
152.5°	150.6	144.7	139.1	134.0	130.2	126.9	124.7	124.6	124.7	126.9	130.2
155°	151.0	146.1	141.2	136.9	133.7	130.9	129.1	128.8	129.1	130.9	133.7
157.5°	151.0	147.1	142.9	139.5	136.7	134.5	132.9	132.9	132.9	134.5	136.7
160°	151.0	147.6	144.1	140.9	138.6	136.6	135.4	135.4	135.4	136.6	138.6
162.5°	151.0	148.0	144.8	142.3	140.2	138.4	137.5	137.7	137.5	138.4	140.2
165°	150.4	148.1	145.5	143.8	142.4	140.9	140.3	140.3	140.3	140.9	142.4
167.5°	149.7	148.1	146.2	144.8	144.0	142.9	142.6	142.9	142.6	142.9	144.0
170°	149.3	147.8	146.3	145.5	145.0	144.1	143.8	144.1	143.8	144.1	145.0
172.5°	148.8	147.6	146.6	145.9	145.6	145.0	145.0	145.2	145.0	145.0	145.6
175°	148.1	147.2	146.7	146.7	146.3	146.1	146.1	146.3	146.1	146.1	146.3
177.5°	147.3	146.9	146.7	146.7	146.7	146.4	146.7	146.9	146.7	146.4	146.7
180°	146.7	146.7	146.7	146.7	146.7	146.7	146.7	146.7	146.7	146.7	146.7



TEST NUMBER: P332537-930

CATALOG NUMBER: S124DIP-S575D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7
2.5°	751.1	748.8	745.4	740.9	737.1	733.0	732.0	730.5	733.5	731.0	730.3
5°	726.4	719.7	711.2	701.4	695.7	687.4	685.8	682.7	679.5	679.1	676.0
7.5°	700.3	690.6	679.4	669.4	660.1	651.1	645.1	643.9	639.2	636.5	633.3
10°	683.6	671.6	658.5	649.1	638.2	628.8	622.1	618.2	615.1	611.6	608.5
12.5°	663.8	651.0	640.3	630.0	617.2	609.9	599.0	592.4	591.7	591.8	583.6
15°	640.7	628.1	611.6	597.0	590.0	576.1	570.1	562.4	557.7	552.9	549.1
17.5°	614.5	598.7	585.8	569.0	555.7	544.6	536.6	532.1	525.0	518.2	513.3
20°	597.9	581.1	567.5	549.8	535.2	521.5	514.9	508.5	503.1	497.4	492.0
22.5°	581.2	563.6	547.0	529.7	516.1	501.7	495.3	486.7	481.5	478.3	473.0
25°	554.8	535.8	516.7	500.3	486.3	473.6	465.0	458.4	452.7	450.1	446.6
27.5°	526.1	507.2	488.9	470.1	454.3	445.1	438.2	433.2	429.9	426.6	424.9
30°	507.8	488.2	468.6	451.1	436.5	427.3	420.9	417.4	414.9	413.4	411.7
32.5°	489.3	469.9	449.2	433.3	420.3	412.1	407.2	403.7	402.5	401.9	401.4
35°	459.7	440.0	420.9	406.7	394.3	391.1	387.0	385.1	384.5	386.7	387.7
37.5°	430.9	412.6	395.1	381.3	373.2	368.5	367.1	367.2	369.5	371.5	373.7
40°	412.4	394.6	378.1	366.1	358.5	355.6	355.0	356.5	359.1	361.3	363.9
42.5°	394.4	376.8	361.9	350.6	345.3	342.7	343.1	344.6	348.2	350.9	354.7
45°	366.4	351.8	337.2	328.0	323.6	324.2	324.2	327.0	330.5	334.7	338.8
47.5°	340.1	325.3	313.3	305.6	303.3	302.7	304.5	308.3	313.3	318.4	324.2
50°	322.3	308.3	297.8	290.9	288.4	289.3	291.9	295.3	301.3	307.7	313.7
52.5°	304.3	291.6	281.8	275.4	273.6	275.3	277.9	283.4	288.7	295.5	302.8
55°	276.3	265.5	257.9	253.2	252.5	253.5	256.3	262.4	269.9	278.5	285.5
57.5°	248.4	239.5	232.4	229.2	229.5	230.4	235.1	242.2	250.4	259.5	268.5
60°	229.7	221.4	215.7	213.2	213.5	215.4	221.1	227.8	237.9	246.8	256.3
62.5°	211.9	204.6	199.2	196.9	196.5	200.6	206.1	213.0	223.2	233.1	243.4
65°	183.4	177.7	173.2	171.9	172.8	176.0	183.0	192.2	200.8	211.2	222.1
67.5°	155.4	150.7	147.7	148.3	149.4	154.1	160.0	167.9	177.6	188.4	199.1
70°	137.7	133.2	130.7	131.0	132.9	138.6	143.7	151.6	162.1	173.2	182.1
72.5°	119.4	116.5	114.2	115.5	117.4	121.4	127.7	135.7	144.9	155.2	164.6
75°	91.6	91.6	90.4	91.4	94.2	98.0	102.8	111.0	120.3	128.5	136.1
77.5°	68.0	67.3	68.2	69.3	70.9	75.4	80.9	86.8	93.7	102.0	108.3
80°	52.0	52.3	53.9	55.8	56.5	59.9	65.6	71.1	76.5	83.4	89.4
82.5°	39.1	39.4	40.2	42.6	43.3	47.0	50.7	56.1	61.0	65.6	70.7
85°	21.3	21.3	22.8	23.8	25.4	27.9	30.2	33.3	37.7	40.9	45.7
87.5°	8.6	8.6	9.9	10.4	11.3	12.7	13.1	16.0	17.1	18.4	20.7
90°	2.3	2.3	4.0	4.0	4.6	5.2	4.9	5.2	5.5	5.8	5.8
92.5°	15.2	21.2	35.9	58.2	80.0	91.4	76.1	56.6	42.6	33.9	28.1
95°	23.9	36.0	61.1	108.4	177.2	234.8	241.5	213.5	168.8	130.2	102.3
97.5°	28.9	39.1	58.4	97.4	165.8	247.4	303.4	315.4	298.9	270.7	240.6
100°	32.9	42.1	59.1	91.6	150.4	231.7	305.4	347.5	353.3	339.2	317.8
102.5°	37.3	46.0	61.4	90.0	140.1	212.1	288.1	345.9	374.5	378.5	369.7
105°	44.7	53.0	66.9	90.7	131.1	189.0	256.7	322.7	372.6	401.1	412.9
107.5°	52.3	60.6	73.2	95.1	129.5	176.1	231.4	289.8	342.9	383.0	408.8
110°	57.6	65.4	78.1	98.2	130.0	171.7	218.7	270.0	319.8	361.7	393.3



TEST NUMBER: P332537-930

CATALOG NUMBER: S124DIP-S575D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	62.7	70.4	82.7	101.7	131.3	169.7	211.6	255.4	299.5	339.0	370.7
115°	70.6	78.4	89.9	107.2	134.0	168.6	204.9	240.9	276.3	310.1	337.7
117.5°	77.9	85.9	96.9	112.8	136.8	168.3	201.9	233.7	263.1	289.6	313.1
120°	82.7	90.7	101.7	116.7	138.9	168.3	200.2	230.5	257.3	280.4	300.8
122.5°	87.6	95.4	106.3	120.4	141.0	168.0	198.4	227.7	253.6	274.6	292.5
125°	94.2	102.3	112.7	125.9	144.1	167.7	195.3	223.1	247.8	267.7	283.6
127.5°	100.4	108.5	118.5	130.7	146.6	167.1	191.3	217.3	240.9	260.8	275.8
130°	104.3	112.7	122.5	133.7	148.4	166.8	188.7	212.6	235.5	255.0	270.3
132.5°	108.0	115.9	125.7	136.7	150.0	166.6	186.5	207.8	229.2	248.3	263.6
135°	113.2	120.7	130.2	140.6	152.5	166.2	183.0	201.1	219.9	237.4	251.8
137.5°	117.6	124.8	133.7	143.4	153.8	166.2	180.0	195.1	210.9	225.8	238.7
140°	120.4	127.3	136.0	145.2	155.0	166.0	178.4	191.6	205.1	218.1	230.2
142.5°	122.9	129.6	138.1	146.6	156.0	166.0	177.0	188.4	200.3	211.4	221.9
145°	126.5	132.8	140.3	148.1	156.5	165.4	174.6	183.8	193.6	202.3	210.3
147.5°	129.9	135.6	142.6	149.4	156.8	164.4	172.5	180.1	187.8	194.8	201.1
150°	132.0	137.5	143.8	150.1	156.8	163.6	170.9	177.8	184.4	190.2	195.3
152.5°	134.0	139.1	144.7	150.6	156.3	162.5	169.0	175.3	181.0	186.3	190.5
155°	136.9	141.2	146.1	151.0	155.6	160.8	166.2	171.5	176.0	180.3	183.8
157.5°	139.5	142.9	147.1	151.0	154.8	159.0	163.5	167.4	171.2	174.9	177.7
160°	140.9	144.1	147.6	151.0	154.2	157.6	161.3	164.9	168.0	171.1	173.5
162.5°	142.3	144.8	148.0	151.0	153.4	156.2	159.6	162.3	165.0	167.5	169.6
165°	143.8	145.5	148.1	150.4	152.1	154.2	156.5	158.7	160.5	162.5	164.0
167.5°	144.8	146.2	148.1	149.7	150.7	152.1	153.7	155.4	156.7	158.3	159.1
170°	145.5	146.3	147.8	149.3	149.9	150.7	151.9	153.3	154.2	155.3	156.2
172.5°	145.9	146.6	147.6	148.8	149.0	149.3	150.3	151.5	152.1	152.8	153.4
175°	146.7	146.7	147.2	148.1	147.8	147.8	148.4	149.0	149.3	149.9	149.9
177.5°	146.7	146.7	146.9	147.3	146.9	146.9	147.2	147.3	147.6	147.6	147.8
180°	146.7	146.7	146.7	146.7	146.7	146.7	146.7	146.7	146.7	146.7	146.7



TEST NUMBER: P332537-930

CATALOG NUMBER: S124DIP-S575D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7
2.5°	729.7	729.2	727.4	727.2	727.4	729.2	729.7	730.3	731.0	733.5	730.5
5°	674.1	672.5	671.6	675.1	671.6	672.5	674.1	676.0	679.1	679.5	682.7
7.5°	632.2	630.9	628.1	627.2	628.1	630.9	632.2	633.3	636.5	639.2	643.9
10°	605.3	604.0	601.4	600.8	601.4	604.0	605.3	608.5	611.6	615.1	618.2
12.5°	579.4	576.8	576.3	577.0	576.3	576.8	579.4	583.6	591.8	591.7	592.4
15°	544.9	543.7	540.2	541.2	540.2	543.7	544.9	549.1	552.9	557.7	562.4
17.5°	511.1	509.6	505.3	509.1	505.3	509.6	511.1	513.3	518.2	525.0	532.1
20°	489.8	487.2	485.0	484.7	485.0	487.2	489.8	492.0	497.4	503.1	508.5
22.5°	469.4	467.2	467.0	464.9	467.0	467.2	469.4	473.0	478.3	481.5	486.7
25°	444.1	441.9	441.2	439.7	441.2	441.9	444.1	446.6	450.1	452.7	458.4
27.5°	424.6	423.5	422.4	422.9	422.4	423.5	424.6	424.9	426.6	429.9	433.2
30°	412.7	412.4	411.7	411.7	411.7	412.4	412.7	411.7	413.4	414.9	417.4
32.5°	402.8	402.8	403.1	403.1	403.1	402.8	402.8	401.4	401.9	402.5	403.7
35°	388.9	389.9	390.5	389.6	390.5	389.9	388.9	387.7	386.7	384.5	385.1
37.5°	376.3	377.3	378.2	379.3	378.2	377.3	376.3	373.7	371.5	369.5	367.2
40°	366.7	368.9	369.6	371.1	369.6	368.9	366.7	363.9	361.3	359.1	356.5
42.5°	357.6	360.0	361.7	362.0	361.7	360.0	357.6	354.7	350.9	348.2	344.6
45°	343.6	346.1	348.3	348.3	348.3	346.1	343.6	338.8	334.7	330.5	327.0
47.5°	329.1	332.7	334.9	335.5	334.9	332.7	329.1	324.2	318.4	313.3	308.3
50°	319.1	323.6	325.8	327.3	325.8	323.6	319.1	313.7	307.7	301.3	295.3
52.5°	309.5	313.9	316.9	317.7	316.9	313.9	309.5	302.8	295.5	288.7	283.4
55°	292.8	299.1	302.6	303.9	302.6	299.1	292.8	285.5	278.5	269.9	262.4
57.5°	277.0	282.9	287.0	287.9	287.0	282.9	277.0	268.5	259.5	250.4	242.2
60°	264.9	271.3	276.3	277.3	276.3	271.3	264.9	256.3	246.8	237.9	227.8
62.5°	252.4	259.0	263.6	266.1	263.6	259.0	252.4	243.4	233.1	223.2	213.0
65°	231.0	237.6	242.1	243.0	242.1	237.6	231.0	222.1	211.2	200.8	192.2
67.5°	207.5	214.1	217.0	218.9	217.0	214.1	207.5	199.1	188.4	177.6	167.9
70°	190.9	196.3	199.5	201.1	199.5	196.3	190.9	182.1	173.2	162.1	151.6
72.5°	172.2	177.8	181.5	181.8	181.5	177.8	172.2	164.6	155.2	144.9	135.7
75°	143.4	148.5	150.3	150.3	150.3	148.5	143.4	136.1	128.5	120.3	111.0
77.5°	113.5	116.1	118.5	119.0	118.5	116.1	113.5	108.3	102.0	93.7	86.8
80°	94.2	95.8	97.7	97.7	97.7	95.8	94.2	89.4	83.4	76.5	71.1
82.5°	74.4	75.7	77.6	77.4	77.6	75.7	74.4	70.7	65.6	61.0	56.1
85°	45.0	47.9	47.6	47.0	47.6	47.9	45.0	45.7	40.9	37.7	33.3
87.5°	21.5	21.9	22.5	23.1	22.5	21.9	21.5	20.7	18.4	17.1	16.0
90°	6.0	6.4	6.0	6.0	6.0	6.4	6.0	5.8	5.8	5.5	5.2
92.5°	24.7	23.2	22.2	22.2	22.2	23.2	24.7	28.1	33.9	42.6	56.6
95°	88.1	79.2	74.0	70.3	74.0	79.2	88.1	102.3	130.2	168.8	213.5
97.5°	219.9	202.6	194.0	187.9	194.0	202.6	219.9	240.6	270.7	298.9	315.4
100°	292.8	275.2	266.5	264.2	266.5	275.2	292.8	317.8	339.2	353.3	347.5
102.5°	354.3	341.6	332.5	330.6	332.5	341.6	354.3	369.7	378.5	374.5	345.9
105°	413.5	411.2	407.2	405.4	407.2	411.2	413.5	412.9	401.1	372.6	322.7
107.5°	423.0	429.6	432.4	433.2	432.4	429.6	423.0	408.8	383.0	342.9	289.8
110°	413.8	425.9	431.0	433.7	431.0	425.9	413.8	393.3	361.7	319.8	270.0



TEST NUMBER: P332537-930

CATALOG NUMBER: S124DIP-S575D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	394.0	408.6	415.9	420.0	415.9	408.6	394.0	370.7	339.0	299.5	255.4
115°	360.4	377.7	387.0	389.3	387.0	377.7	360.4	337.7	310.1	276.3	240.9
117.5°	332.5	347.0	356.3	358.1	356.3	347.0	332.5	313.1	289.6	263.1	233.7
120°	317.2	330.0	337.5	340.6	337.5	330.0	317.2	300.8	280.4	257.3	230.5
122.5°	306.4	317.2	323.6	326.8	323.6	317.2	306.4	292.5	274.6	253.6	227.7
125°	295.1	303.5	308.9	310.6	308.9	303.5	295.1	283.6	267.7	247.8	223.1
127.5°	287.4	294.8	299.5	301.2	299.5	294.8	287.4	275.8	260.8	240.9	217.3
130°	282.1	289.3	293.9	295.6	293.9	289.3	282.1	270.3	255.0	235.5	212.6
132.5°	275.2	283.3	287.7	289.4	287.7	283.3	275.2	263.6	248.3	229.2	207.8
135°	263.3	271.4	276.1	277.8	276.1	271.4	263.3	251.8	237.4	219.9	201.1
137.5°	249.6	257.5	261.3	263.3	261.3	257.5	249.6	238.7	225.8	210.9	195.1
140°	240.4	246.6	250.7	253.0	250.7	246.6	240.4	230.2	218.1	205.1	191.6
142.5°	230.9	236.8	240.4	241.9	240.4	236.8	230.9	221.9	211.4	200.3	188.4
145°	217.5	222.4	225.3	226.7	225.3	222.4	217.5	210.3	202.3	193.6	183.8
147.5°	206.4	210.7	212.8	213.4	212.8	210.7	206.4	201.1	194.8	187.8	180.1
150°	200.0	203.7	205.5	205.7	205.5	203.7	200.0	195.3	190.2	184.4	177.8
152.5°	194.4	197.5	198.5	198.9	198.5	197.5	194.4	190.5	186.3	181.0	175.3
155°	186.7	189.0	189.9	189.9	189.9	189.0	186.7	183.8	180.3	176.0	171.5
157.5°	179.8	181.6	182.1	182.1	182.1	181.6	179.8	177.7	174.9	171.2	167.4
160°	175.2	176.9	177.2	177.2	177.2	176.9	175.2	173.5	171.1	168.0	164.9
162.5°	170.8	172.5	172.8	172.6	172.8	172.5	170.8	169.6	167.5	165.0	162.3
165°	165.1	166.2	166.0	165.7	166.0	166.2	165.1	164.0	162.5	160.5	158.7
167.5°	159.7	160.5	160.5	160.2	160.5	160.5	159.7	159.1	158.3	156.7	155.4
170°	156.8	157.0	156.8	156.8	156.8	157.0	156.8	156.2	155.3	154.2	153.3
172.5°	153.8	154.0	153.8	153.3	153.8	154.0	153.8	153.4	152.8	152.1	151.5
175°	149.9	150.4	149.9	149.3	149.9	150.4	149.9	149.9	149.9	149.3	149.0
177.5°	147.6	147.8	147.3	146.9	147.3	147.8	147.6	147.8	147.6	147.6	147.3
180°	146.7	146.7	146.7	146.7	146.7	146.7	146.7	146.7	146.7	146.7	146.7



TEST NUMBER: P332537-930

CATALOG NUMBER: S124DIP-S575D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7
2.5°	732.0	733.0	737.1	740.9	745.4	748.8	751.1	753.6	758.9	763.2	767.3
5°	685.8	687.4	695.7	701.4	711.2	719.7	726.4	733.7	742.3	754.0	764.8
7.5°	645.1	651.1	660.1	669.4	679.4	690.6	700.3	711.3	726.1	742.2	758.9
10°	622.1	628.8	638.2	649.1	658.5	671.6	683.6	696.6	713.4	733.1	752.8
12.5°	599.0	609.9	617.2	630.0	640.3	651.0	663.8	680.9	700.5	721.1	744.9
15°	570.1	576.1	590.0	597.0	611.6	628.1	640.7	657.9	676.9	704.3	730.8
17.5°	536.6	544.6	555.7	569.0	585.8	598.7	614.5	632.1	656.1	683.1	716.6
20°	514.9	521.5	535.2	549.8	567.5	581.1	597.9	615.1	639.8	668.7	703.6
22.5°	495.3	501.7	516.1	529.7	547.0	563.6	581.2	601.1	624.8	655.3	690.9
25°	465.0	473.6	486.3	500.3	516.7	535.8	554.8	572.6	597.9	630.0	668.1
27.5°	438.2	445.1	454.3	470.1	488.9	507.2	526.1	548.5	572.8	606.7	646.2
30°	420.9	427.3	436.5	451.1	468.6	488.2	507.8	529.5	554.8	588.4	628.8
32.5°	407.2	412.1	420.3	433.3	449.2	469.9	489.3	511.7	538.3	571.4	610.7
35°	387.0	391.1	394.3	406.7	420.9	440.0	459.7	483.5	509.2	540.5	579.8
37.5°	367.1	368.5	373.2	381.3	395.1	412.6	430.9	454.3	480.6	512.6	548.0
40°	355.0	355.6	358.5	366.1	378.1	394.6	412.4	435.5	460.6	490.7	525.9
42.5°	343.1	342.7	345.3	350.6	361.9	376.8	394.4	415.5	440.6	468.4	501.6
45°	324.2	324.2	323.6	328.0	337.2	351.8	366.4	386.7	407.6	434.9	462.8
47.5°	304.5	302.7	303.3	305.6	313.3	325.3	340.1	356.7	375.1	398.3	422.7
50°	291.9	289.3	288.4	290.9	297.8	308.3	322.3	336.9	354.3	374.6	395.6
52.5°	277.9	275.3	273.6	275.4	281.8	291.6	304.3	317.1	332.7	349.3	367.4
55°	256.3	253.5	252.5	253.2	257.9	265.5	276.3	288.0	299.8	313.4	326.1
57.5°	235.1	230.4	229.5	229.2	232.4	239.5	248.4	258.6	267.2	275.4	288.9
60°	221.1	215.4	213.5	213.2	215.7	221.4	229.7	239.8	245.8	251.5	263.3
62.5°	206.1	200.6	196.5	196.9	199.2	204.6	211.9	219.2	223.2	229.5	237.4
65°	183.0	176.0	172.8	171.9	173.2	177.7	183.4	188.1	192.6	195.1	202.7
67.5°	160.0	154.1	149.4	148.3	147.7	150.7	155.4	158.3	161.4	163.7	168.2
70°	143.7	138.6	132.9	131.0	130.7	133.2	137.7	138.0	142.4	143.4	148.1
72.5°	127.7	121.4	117.4	115.5	114.2	116.5	119.4	120.3	122.6	124.3	126.9
75°	102.8	98.0	94.2	91.4	90.4	91.6	91.6	93.3	94.8	95.8	98.7
77.5°	80.9	75.4	70.9	69.3	68.2	67.3	68.0	69.0	68.2	69.9	70.5
80°	65.6	59.9	56.5	55.8	53.9	52.3	52.0	53.0	51.7	52.3	54.2
82.5°	50.7	47.0	43.3	42.6	40.2	39.4	39.1	38.5	38.5	38.4	38.7
85°	30.2	27.9	25.4	23.8	22.8	21.3	21.3	20.6	20.0	19.3	19.6
87.5°	13.1	12.7	11.3	10.4	9.9	8.6	8.6	7.7	7.4	7.0	6.7
90°	4.9	5.2	4.6	4.0	4.0	2.3	2.3	2.0	1.7	0.9	0.3
92.5°	76.1	91.4	80.0	58.2	35.9	21.2	15.2	11.0	7.5	4.8	3.3
95°	241.5	234.8	177.2	108.4	61.1	36.0	23.9	17.0	13.3	10.4	9.5
97.5°	303.4	247.4	165.8	97.4	58.4	39.1	28.9	23.0	19.6	17.0	17.0
100°	305.4	231.7	150.4	91.6	59.1	42.1	32.9	27.4	23.9	21.9	21.9
102.5°	288.1	212.1	140.1	90.0	61.4	46.0	37.3	32.0	28.8	27.0	26.5
105°	256.7	189.0	131.1	90.7	66.9	53.0	44.7	39.5	36.0	34.6	33.8
107.5°	231.4	176.1	129.5	95.1	73.2	60.6	52.3	47.4	43.7	42.2	41.7
110°	218.7	171.7	130.0	98.2	78.1	65.4	57.6	52.4	49.0	47.5	47.0



TEST NUMBER: P332537-930

CATALOG NUMBER: S124DIP-S575D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	211.6	169.7	131.3	101.7	82.7	70.4	62.7	57.5	54.3	52.6	52.0
115°	204.9	168.6	134.0	107.2	89.9	78.4	70.6	65.1	62.2	60.3	59.4
117.5°	201.9	168.3	136.8	112.8	96.9	85.9	77.9	72.7	69.5	67.8	66.9
120°	200.2	168.3	138.9	116.7	101.7	90.7	82.7	77.8	74.6	72.6	72.1
122.5°	198.4	168.0	141.0	120.4	106.3	95.4	87.6	82.2	79.2	77.2	76.6
125°	195.3	167.7	144.1	125.9	112.7	102.3	94.2	88.8	85.6	83.8	82.7
127.5°	191.3	167.1	146.6	130.7	118.5	108.5	100.4	94.7	91.1	88.9	88.1
130°	188.7	166.8	148.4	133.7	122.5	112.7	104.3	98.8	94.5	92.2	91.1
132.5°	186.5	166.6	150.0	136.7	125.7	115.9	108.0	102.1	98.0	95.0	94.1
135°	183.0	166.2	152.5	140.6	130.2	120.7	113.2	107.2	102.3	99.4	98.2
137.5°	180.0	166.2	153.8	143.4	133.7	124.8	117.6	111.4	106.7	103.5	102.5
140°	178.4	166.0	155.0	145.2	136.0	127.3	120.4	114.4	109.5	106.3	105.5
142.5°	177.0	166.0	156.0	146.6	138.1	129.6	122.9	117.2	112.5	109.6	108.7
145°	174.6	165.4	156.5	148.1	140.3	132.8	126.5	121.0	117.0	114.1	113.2
147.5°	172.5	164.4	156.8	149.4	142.6	135.6	129.9	125.3	121.2	118.6	118.4
150°	170.9	163.6	156.8	150.1	143.8	137.5	132.0	127.7	124.2	121.9	121.6
152.5°	169.0	162.5	156.3	150.6	144.7	139.1	134.0	130.2	126.9	124.7	124.6
155°	166.2	160.8	155.6	151.0	146.1	141.2	136.9	133.7	130.9	129.1	128.8
157.5°	163.5	159.0	154.8	151.0	147.1	142.9	139.5	136.7	134.5	132.9	132.9
160°	161.3	157.6	154.2	151.0	147.6	144.1	140.9	138.6	136.6	135.4	135.4
162.5°	159.6	156.2	153.4	151.0	148.0	144.8	142.3	140.2	138.4	137.5	137.7
165°	156.5	154.2	152.1	150.4	148.1	145.5	143.8	142.4	140.9	140.3	140.3
167.5°	153.7	152.1	150.7	149.7	148.1	146.2	144.8	144.0	142.9	142.6	142.9
170°	151.9	150.7	149.9	149.3	147.8	146.3	145.5	145.0	144.1	143.8	144.1
172.5°	150.3	149.3	149.0	148.8	147.6	146.6	145.9	145.6	145.0	145.0	145.2
175°	148.4	147.8	147.8	148.1	147.2	146.7	146.7	146.3	146.1	146.1	146.3
177.5°	147.2	146.9	146.9	147.3	146.9	146.7	146.7	146.7	146.4	146.7	146.9
180°	146.7	146.7	146.7	146.7	146.7	146.7	146.7	146.7	146.7	146.7	146.7



TEST NUMBER: P332537-930

CATALOG NUMBER: S124DIP-S575D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7
2.5°	770.9	773.4	776.7	782.3	784.3	786.8	790.4	790.1	791.2	794.9	803.1
5°	773.7	783.5	793.0	804.5	816.5	824.4	835.3	841.9	848.6	857.1	871.7
7.5°	774.9	790.4	807.9	827.9	845.8	866.3	882.4	897.5	911.1	929.2	946.6
10°	773.1	794.0	816.5	841.9	868.9	891.7	912.3	935.8	955.8	977.6	997.4
12.5°	769.7	795.0	825.2	853.5	885.1	918.8	944.5	968.2	994.8	1020.0	1050.4
15°	762.3	796.9	832.1	869.5	911.7	950.7	987.8	1018.6	1047.2	1084.9	1124.5
17.5°	752.8	790.0	834.5	879.8	923.9	968.5	1014.4	1060.6	1096.7	1143.5	1174.6
20°	743.9	787.0	832.7	886.6	930.7	986.3	1031.9	1076.6	1126.1	1172.7	1209.9
22.5°	731.4	778.6	827.1	880.8	938.8	994.3	1047.2	1095.7	1145.2	1195.9	1240.8
25°	715.7	758.5	815.9	876.8	934.5	994.8	1055.4	1116.3	1169.5	1223.2	1265.1
27.5°	688.8	742.8	796.3	859.2	923.3	991.5	1056.3	1120.1	1175.8	1219.9	1245.9
30°	675.1	721.9	780.1	843.2	912.6	985.9	1053.4	1116.0	1168.0	1203.2	1213.7
32.5°	654.8	703.2	760.0	825.4	898.9	974.2	1044.6	1103.5	1147.0	1165.4	1152.8
35°	624.6	668.4	725.8	792.7	869.2	949.4	1018.9	1068.7	1091.0	1073.5	1030.0
37.5°	588.4	631.9	689.5	755.2	834.4	915.9	978.8	1014.6	1007.2	963.8	899.0
40°	563.0	603.6	658.5	729.6	806.7	888.5	943.7	963.1	942.8	880.6	811.8
42.5°	534.9	574.5	629.6	698.1	779.8	855.2	903.4	905.0	871.0	796.6	727.5
45°	492.0	529.8	581.8	653.1	728.6	799.7	831.4	815.9	753.1	681.3	611.9
47.5°	449.7	482.4	533.7	601.4	673.1	733.0	748.7	720.7	653.8	584.2	519.8
50°	418.7	451.8	499.9	564.7	633.8	685.5	693.1	656.0	590.4	520.2	469.8
52.5°	389.1	421.8	468.2	528.1	591.4	638.1	638.3	595.3	529.9	467.5	420.5
55°	345.4	375.0	416.9	470.4	526.9	563.4	554.5	510.1	453.3	399.1	358.2
57.5°	303.5	329.1	367.7	412.5	462.2	492.3	477.5	434.8	384.1	338.1	307.0
60°	276.3	300.7	333.7	375.9	417.8	441.2	427.3	388.6	341.9	304.8	277.9
62.5°	249.9	270.5	302.2	338.8	377.6	395.1	382.6	344.5	304.2	270.6	248.7
65°	212.5	229.3	254.7	286.2	314.4	329.3	318.8	283.2	252.5	228.4	210.9
67.5°	177.7	190.8	210.0	235.2	259.2	267.3	257.7	232.9	206.9	187.6	175.3
70°	153.5	165.9	182.1	201.5	222.3	231.0	221.4	201.8	180.5	162.7	150.7
72.5°	132.5	142.0	155.7	172.3	188.6	197.2	190.7	171.8	153.8	140.6	130.4
75°	100.9	109.1	118.6	130.4	143.1	148.8	143.1	130.0	117.6	107.9	100.5
77.5°	73.4	77.8	85.1	93.9	101.8	106.2	101.3	92.5	84.9	78.2	74.5
80°	55.8	59.0	64.1	71.1	76.5	80.6	77.4	70.1	64.1	59.6	58.0
82.5°	40.6	42.7	46.1	51.3	54.9	57.0	55.6	50.3	47.9	43.9	42.3
85°	20.0	21.3	23.5	25.0	28.2	28.5	28.9	26.7	24.5	23.5	22.2
87.5°	7.0	7.4	8.2	9.0	10.1	10.7	10.4	10.6	9.7	9.4	8.4
90°	0.9	1.7	2.0	2.3	2.3	4.0	4.0	4.6	5.2	4.9	5.2
92.5°	4.8	7.5	11.0	15.2	21.2	35.9	58.2	80.0	91.4	76.1	56.6
95°	10.4	13.3	17.0	23.9	36.0	61.1	108.4	177.2	234.8	241.5	213.5
97.5°	17.0	19.6	23.0	28.9	39.1	58.4	97.4	165.8	247.4	303.4	315.4
100°	21.9	23.9	27.4	32.9	42.1	59.1	91.6	150.4	231.7	305.4	347.5
102.5°	27.0	28.8	32.0	37.3	46.0	61.4	90.0	140.1	212.1	288.1	345.9
105°	34.6	36.0	39.5	44.7	53.0	66.9	90.7	131.1	189.0	256.7	322.7
107.5°	42.2	43.7	47.4	52.3	60.6	73.2	95.1	129.5	176.1	231.4	289.8
110°	47.5	49.0	52.4	57.6	65.4	78.1	98.2	130.0	171.7	218.7	270.0



TEST NUMBER: P332537-930

CATALOG NUMBER: S124DIP-S575D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	52.6	54.3	57.5	62.7	70.4	82.7	101.7	131.3	169.7	211.6	255.4
115°	60.3	62.2	65.1	70.6	78.4	89.9	107.2	134.0	168.6	204.9	240.9
117.5°	67.8	69.5	72.7	77.9	85.9	96.9	112.8	136.8	168.3	201.9	233.7
120°	72.6	74.6	77.8	82.7	90.7	101.7	116.7	138.9	168.3	200.2	230.5
122.5°	77.2	79.2	82.2	87.6	95.4	106.3	120.4	141.0	168.0	198.4	227.7
125°	83.8	85.6	88.8	94.2	102.3	112.7	125.9	144.1	167.7	195.3	223.1
127.5°	88.9	91.1	94.7	100.4	108.5	118.5	130.7	146.6	167.1	191.3	217.3
130°	92.2	94.5	98.8	104.3	112.7	122.5	133.7	148.4	166.8	188.7	212.6
132.5°	95.0	98.0	102.1	108.0	115.9	125.7	136.7	150.0	166.6	186.5	207.8
135°	99.4	102.3	107.2	113.2	120.7	130.2	140.6	152.5	166.2	183.0	201.1
137.5°	103.5	106.7	111.4	117.6	124.8	133.7	143.4	153.8	166.2	180.0	195.1
140°	106.3	109.5	114.4	120.4	127.3	136.0	145.2	155.0	166.0	178.4	191.6
142.5°	109.6	112.5	117.2	122.9	129.6	138.1	146.6	156.0	166.0	177.0	188.4
145°	114.1	117.0	121.0	126.5	132.8	140.3	148.1	156.5	165.4	174.6	183.8
147.5°	118.6	121.2	125.3	129.9	135.6	142.6	149.4	156.8	164.4	172.5	180.1
150°	121.9	124.2	127.7	132.0	137.5	143.8	150.1	156.8	163.6	170.9	177.8
152.5°	124.7	126.9	130.2	134.0	139.1	144.7	150.6	156.3	162.5	169.0	175.3
155°	129.1	130.9	133.7	136.9	141.2	146.1	151.0	155.6	160.8	166.2	171.5
157.5°	132.9	134.5	136.7	139.5	142.9	147.1	151.0	154.8	159.0	163.5	167.4
160°	135.4	136.6	138.6	140.9	144.1	147.6	151.0	154.2	157.6	161.3	164.9
162.5°	137.5	138.4	140.2	142.3	144.8	148.0	151.0	153.4	156.2	159.6	162.3
165°	140.3	140.9	142.4	143.8	145.5	148.1	150.4	152.1	154.2	156.5	158.7
167.5°	142.6	142.9	144.0	144.8	146.2	148.1	149.7	150.7	152.1	153.7	155.4
170°	143.8	144.1	145.0	145.5	146.3	147.8	149.3	149.9	150.7	151.9	153.3
172.5°	145.0	145.0	145.6	145.9	146.6	147.6	148.8	149.0	149.3	150.3	151.5
175°	146.1	146.1	146.3	146.7	146.7	147.2	148.1	147.8	147.8	148.4	149.0
177.5°	146.7	146.4	146.7	146.7	146.7	146.9	147.3	146.9	146.9	147.2	147.3
180°	146.7	146.7	146.7	146.7	146.7	146.7	146.7	146.7	146.7	146.7	146.7



TEST NUMBER: P332537-930

CATALOG NUMBER: S124DIP-S575D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	765.7	765.7	765.7	765.7	765.7	765.7	765.7
2.5°	807.1	807.6	809.9	811.7	812.2	814.7	815.0
5°	878.1	883.5	893.9	894.9	896.4	904.7	898.4
7.5°	961.2	974.9	984.0	992.1	995.0	998.6	997.8
10°	1014.5	1034.8	1044.9	1061.1	1061.8	1065.8	1063.3
12.5°	1068.0	1091.6	1110.1	1113.1	1126.7	1128.8	1132.4
15°	1143.9	1169.0	1194.7	1203.9	1222.5	1227.0	1234.0
17.5°	1215.2	1240.8	1258.8	1282.6	1290.3	1300.6	1293.6
20°	1254.3	1282.2	1305.0	1323.7	1331.7	1337.4	1336.8
22.5°	1277.9	1306.0	1324.5	1338.7	1346.1	1348.6	1348.4
25°	1292.7	1308.9	1314.6	1320.0	1311.7	1308.9	1310.1
27.5°	1251.6	1247.3	1232.5	1212.9	1192.6	1176.5	1167.8
30°	1195.0	1170.2	1147.7	1108.4	1088.0	1076.0	1065.2
32.5°	1114.8	1075.5	1032.3	996.2	973.1	955.2	952.5
35°	977.4	918.4	865.4	821.3	798.4	779.1	774.6
37.5°	831.0	769.6	721.9	683.1	658.5	644.9	632.2
40°	733.7	681.1	634.1	601.1	582.4	572.6	564.7
42.5°	658.8	610.7	564.1	538.9	522.0	516.0	511.4
45°	555.5	510.7	478.3	459.3	449.5	439.4	434.6
47.5°	472.6	436.3	414.9	398.8	388.2	382.2	379.1
50°	425.7	395.9	376.8	364.5	355.0	350.2	347.6
52.5°	384.1	359.6	343.6	333.8	327.3	323.8	322.8
55°	330.8	312.2	302.0	293.4	288.7	285.5	284.2
57.5°	287.6	273.2	265.0	257.9	256.1	253.4	252.5
60°	259.2	248.1	241.1	236.4	234.7	231.5	232.2
62.5°	234.1	224.9	219.0	216.3	214.2	211.5	212.4
65°	198.0	191.3	188.1	185.6	183.0	181.5	182.7
67.5°	166.1	161.5	157.2	155.7	154.5	154.3	152.9
70°	145.3	141.5	137.7	136.7	136.7	135.4	135.1
72.5°	125.2	122.5	119.9	119.2	118.2	118.7	117.4
75°	96.8	94.5	93.6	92.6	92.3	92.3	91.4
77.5°	71.5	69.9	68.3	68.3	67.2	66.8	66.6
80°	54.2	53.6	52.3	52.3	51.7	52.0	51.4
82.5°	40.8	39.9	39.6	39.1	38.2	38.3	37.7
85°	21.9	21.0	20.6	19.6	19.0	19.6	19.0
87.5°	8.7	8.5	8.2	7.8	7.6	7.6	6.8
90°	5.5	5.8	5.8	6.0	6.4	6.0	6.0
92.5°	42.6	33.9	28.1	24.7	23.2	22.2	22.2
95°	168.8	130.2	102.3	88.1	79.2	74.0	70.3
97.5°	298.9	270.7	240.6	219.9	202.6	194.0	187.9
100°	353.3	339.2	317.8	292.8	275.2	266.5	264.2
102.5°	374.5	378.5	369.7	354.3	341.6	332.5	330.6
105°	372.6	401.1	412.9	413.5	411.2	407.2	405.4
107.5°	342.9	383.0	408.8	423.0	429.6	432.4	433.2
110°	319.8	361.7	393.3	413.8	425.9	431.0	433.7



TEST NUMBER: P332537-930

CATALOG NUMBER: S124DIP-S575D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	299.5	339.0	370.7	394.0	408.6	415.9	420.0
115°	276.3	310.1	337.7	360.4	377.7	387.0	389.3
117.5°	263.1	289.6	313.1	332.5	347.0	356.3	358.1
120°	257.3	280.4	300.8	317.2	330.0	337.5	340.6
122.5°	253.6	274.6	292.5	306.4	317.2	323.6	326.8
125°	247.8	267.7	283.6	295.1	303.5	308.9	310.6
127.5°	240.9	260.8	275.8	287.4	294.8	299.5	301.2
130°	235.5	255.0	270.3	282.1	289.3	293.9	295.6
132.5°	229.2	248.3	263.6	275.2	283.3	287.7	289.4
135°	219.9	237.4	251.8	263.3	271.4	276.1	277.8
137.5°	210.9	225.8	238.7	249.6	257.5	261.3	263.3
140°	205.1	218.1	230.2	240.4	246.6	250.7	253.0
142.5°	200.3	211.4	221.9	230.9	236.8	240.4	241.9
145°	193.6	202.3	210.3	217.5	222.4	225.3	226.7
147.5°	187.8	194.8	201.1	206.4	210.7	212.8	213.4
150°	184.4	190.2	195.3	200.0	203.7	205.5	205.7
152.5°	181.0	186.3	190.5	194.4	197.5	198.5	198.9
155°	176.0	180.3	183.8	186.7	189.0	189.9	189.9
157.5°	171.2	174.9	177.7	179.8	181.6	182.1	182.1
160°	168.0	171.1	173.5	175.2	176.9	177.2	177.2
162.5°	165.0	167.5	169.6	170.8	172.5	172.8	172.6
165°	160.5	162.5	164.0	165.1	166.2	166.0	165.7
167.5°	156.7	158.3	159.1	159.7	160.5	160.5	160.2
170°	154.2	155.3	156.2	156.8	157.0	156.8	156.8
172.5°	152.1	152.8	153.4	153.8	154.0	153.8	153.3
175°	149.3	149.9	149.9	149.9	150.4	149.9	149.3
177.5°	147.6	147.6	147.8	147.6	147.8	147.3	146.9
180°	146.7	146.7	146.7	146.7	146.7	146.7	146.7

(END OF REPORT)