

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332555-930

Luminaire Tested: **S124DIP-S575D810U930-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332555-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIP-S575D810U930-4F0-1E-UDD-A4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4474.5 lumens
Efficiency: N/A
Efficacy: 116.5 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332555-930

CATALOG NUMBER: S124DIP-S575D810U930-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332555-930

CATALOG NUMBER: S124DIP-S575D810U930-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	54	54	54	47				47
1	97	93	89	86	89	86	83	80	72	70	68	59	58	56	48	47	46				40	
2	89	82	76	71	81	75	70	66	63	60	56	52	50	47	42	40	39				34	
3	81	72	65	59	74	66	60	55	56	51	48	46	43	40	38	35	33				29	
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29				25	
5	68	57	49	43	63	53	46	40	45	39	35	37	33	30	30	28	25				22	
6	63	51	43	37	58	47	40	35	40	35	31	34	30	26	28	25	22				19	
7	58	46	38	33	53	43	36	31	37	31	27	31	27	23	25	22	20				17	
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	23	20	18				15	
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	18	16				14	
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15				13	

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	6181	6181	6181	6181
5°	7280	6198	5471	6198
10°	8716	6171	4925	6171
15°	10313	6108	4523	6108
20°	11485	6045	4164	6045
25°	11670	5951	3917	5951
30°	9930	5862	3838	5862
35°	7634	5714	3840	5714
40°	5951	5542	3911	5542
45°	4962	5284	3976	5284
50°	4366	4968	4111	4968
55°	4000	4590	4277	4590
60°	3749	4251	4477	4251
65°	3490	3872	4642	3872
70°	3189	3496	4747	3496
75°	2851	3079	4688	3079
80°	2390	2520	4542	2520
85°	1760	1815	4353	1815



TEST NUMBER: P332555-930

CATALOG NUMBER: S124DIP-S575D810U930-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.6	1.7
10°-20°	230.0	5.1
20°-30°	364.6	8.1
30°-40°	405.8	9.1
40°-50°	369.4	8.3
50°-60°	301.9	6.7
60°-70°	215.5	4.8
70°-80°	118.7	2.7
80°-90°	34.2	0.8
90°-100°	234.4	5.2
100°-110°	487.8	10.9
110°-120°	436.9	9.8
120°-130°	367.5	8.2
130°-140°	306.4	6.8
140°-150°	234.1	5.2
150°-160°	164.6	3.7
160°-170°	96.8	2.2
170°-180°	31.5	0.7
0°-30°	669.2	15.0
0°-40°	1075.0	24.0
0°-60°	1746.2	39.0
0°-90°	2114.5	47.3
90°-120°	1159.1	25.9
90°-150°	2067.1	46.2
90°-180°	2360.0	52.7
0°-180°	4474.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	766	766	766	766	766	
5°	898	765	675	765	898	91
15°	1234	731	541	731	1234	349
25°	1310	668	440	668	1310	578
35°	775	580	390	580	775	492
45°	435	463	348	463	435	342
55°	284	326	304	326	284	257
65°	183	203	243	203	183	181
75°	91	99	150	99	91	97
85°	19	20	47	20	19	24
90°	13	1	13	1	13	12
95°	156	21	156	21	156	241
105°	897	75	897	75	897	887
115°	861	131	861	131	861	855
125°	687	183	687	183	687	624
135°	615	217	615	217	615	474
145°	502	250	502	250	502	318
155°	420	285	420	285	420	196
165°	367	310	367	310	367	105
175°	330	324	330	324	330	32
180°	324	324	324	324	324	



TEST NUMBER: P332555-930

CATALOG NUMBER: S124DIP-S575D810U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7
2.5°	815.0	814.7	812.2	811.7	809.9	807.6	807.1	803.1	794.9	791.2	790.1
5°	898.4	904.7	896.4	894.9	893.9	883.5	878.1	871.7	857.1	848.6	841.9
7.5°	997.8	998.6	995.0	992.1	984.0	974.9	961.2	946.6	929.2	911.1	897.5
10°	1063.3	1065.8	1061.8	1061.1	1044.9	1034.8	1014.5	997.4	977.6	955.8	935.8
12.5°	1132.4	1128.8	1126.7	1113.1	1110.1	1091.6	1068.0	1050.4	1020.0	994.8	968.2
15°	1234.0	1227.0	1222.5	1203.9	1194.7	1169.0	1143.9	1124.5	1084.9	1047.2	1018.6
17.5°	1293.6	1300.6	1290.3	1282.6	1258.8	1240.8	1215.2	1174.6	1143.5	1096.7	1060.6
20°	1336.8	1337.4	1331.7	1323.7	1305.0	1282.2	1254.3	1209.9	1172.7	1126.1	1076.6
22.5°	1348.4	1348.6	1346.1	1338.7	1324.5	1306.0	1277.9	1240.8	1195.9	1145.2	1095.7
25°	1310.1	1308.9	1311.7	1320.0	1314.6	1308.9	1292.7	1265.1	1223.2	1169.5	1116.3
27.5°	1167.8	1176.5	1192.6	1212.9	1232.5	1247.3	1251.6	1245.9	1219.9	1175.8	1120.1
30°	1065.2	1076.0	1088.0	1108.4	1147.7	1170.2	1195.0	1213.7	1203.2	1168.0	1116.0
32.5°	952.5	955.2	973.1	996.2	1032.3	1075.5	1114.8	1152.8	1165.4	1147.0	1103.5
35°	774.6	779.1	798.4	821.3	865.4	918.4	977.4	1030.0	1073.5	1091.0	1068.7
37.5°	632.2	644.9	658.5	683.1	721.9	769.6	831.0	899.0	963.8	1007.2	1014.6
40°	564.7	572.6	582.4	601.1	634.1	681.1	733.7	811.8	880.6	942.8	963.1
42.5°	511.4	516.0	522.0	538.9	564.1	610.7	658.8	727.5	796.6	871.0	905.0
45°	434.6	439.4	449.5	459.3	478.3	510.7	555.5	611.9	681.3	753.1	815.9
47.5°	379.1	382.2	388.2	398.8	414.9	436.3	472.6	519.8	584.2	653.8	720.7
50°	347.6	350.2	355.0	364.5	376.8	395.9	425.7	469.8	520.2	590.4	656.0
52.5°	322.8	323.8	327.3	333.8	343.6	359.6	384.1	420.5	467.5	529.9	595.3
55°	284.2	285.5	288.7	293.4	302.0	312.2	330.8	358.2	399.1	453.3	510.1
57.5°	252.5	253.4	256.1	257.9	265.0	273.2	287.6	307.0	338.1	384.1	434.8
60°	232.2	231.5	234.7	236.4	241.1	248.1	259.2	277.9	304.8	341.9	388.6
62.5°	212.4	211.5	214.2	216.3	219.0	224.9	234.1	248.7	270.6	304.2	344.5
65°	182.7	181.5	183.0	185.6	188.1	191.3	198.0	210.9	228.4	252.5	283.2
67.5°	152.9	154.3	154.5	155.7	157.2	161.5	166.1	175.3	187.6	206.9	232.9
70°	135.1	135.4	136.7	136.7	137.7	141.5	145.3	150.7	162.7	180.5	201.8
72.5°	117.4	118.7	118.2	119.2	119.9	122.5	125.2	130.4	140.6	153.8	171.8
75°	91.4	92.3	92.3	92.6	93.6	94.5	96.8	100.5	107.9	117.6	130.0
77.5°	66.6	66.8	67.2	68.3	68.3	69.9	71.5	74.5	78.2	84.9	92.5
80°	51.4	52.0	51.7	52.3	52.3	53.6	54.2	58.0	59.6	64.1	70.1
82.5°	37.7	38.3	38.2	39.1	39.6	39.9	40.8	42.3	43.9	47.9	50.3
85°	19.0	19.6	19.0	19.6	20.6	21.0	21.9	22.2	23.5	24.5	26.7
87.5°	8.2	9.0	9.1	9.3	9.6	9.9	10.0	9.6	10.5	10.9	11.7
90°	13.4	13.4	14.0	13.4	12.7	12.7	12.1	11.5	10.8	11.5	10.2
92.5°	49.1	49.1	51.3	54.7	62.2	75.0	94.2	125.2	168.4	202.2	177.0
95°	155.6	163.9	175.3	195.1	226.3	288.1	373.6	472.4	534.3	519.6	392.1
97.5°	415.8	429.0	448.2	486.6	532.3	598.8	661.2	697.9	671.2	547.2	367.0
100°	584.6	589.7	608.8	647.7	703.2	750.3	781.5	768.8	675.7	512.6	332.8
102.5°	731.5	735.6	755.7	783.9	817.9	837.6	828.5	765.2	637.5	469.2	309.8
105°	897.0	900.8	909.7	914.8	913.5	887.4	824.3	714.0	568.0	418.2	290.1
107.5°	958.4	956.8	950.4	935.9	904.3	847.5	758.6	641.2	511.9	389.6	286.5
110°	959.4	953.7	942.2	915.4	870.2	800.1	707.6	597.4	483.9	379.9	287.5



TEST NUMBER: P332555-930

CATALOG NUMBER: S124DIP-S575D810U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	929.4	920.1	904.0	871.6	820.2	750.1	662.8	565.2	468.1	375.4	290.6
115°	861.3	856.1	835.8	797.5	747.1	685.9	611.4	533.0	453.2	372.9	296.4
117.5°	792.3	788.3	767.7	735.6	692.6	640.7	582.0	517.1	446.6	372.3	302.7
120°	753.5	746.5	729.9	701.9	665.5	620.3	569.3	510.0	443.0	372.3	307.3
122.5°	722.9	715.9	701.9	677.9	647.2	607.6	561.1	503.9	439.0	371.8	311.9
125°	687.2	683.4	671.3	652.8	627.3	592.2	548.3	493.4	432.2	371.0	318.8
127.5°	666.3	662.5	652.3	635.9	610.3	576.9	533.0	480.7	423.1	369.7	324.2
130°	654.1	650.3	640.1	624.1	597.9	564.2	520.8	470.5	417.6	369.1	328.3
132.5°	640.3	636.5	626.8	608.8	583.2	549.4	507.0	459.7	412.5	368.6	331.9
135°	614.6	610.7	600.5	582.7	557.2	525.3	486.4	445.0	404.8	367.9	337.2
137.5°	582.7	578.0	569.6	552.0	528.2	499.5	466.7	431.6	398.2	367.7	340.4
140°	559.7	554.6	545.7	531.7	509.4	482.6	453.9	424.0	394.6	367.2	343.0
142.5°	535.2	531.7	523.7	510.8	491.0	467.8	443.2	416.8	391.6	367.2	345.0
145°	501.7	498.6	492.1	481.4	465.4	447.5	428.4	406.8	386.3	365.9	346.2
147.5°	472.0	470.8	466.0	456.7	445.0	431.0	415.6	398.4	381.6	363.6	346.8
150°	455.2	454.5	450.7	442.5	432.2	420.8	408.0	393.3	378.1	362.1	346.8
152.5°	439.9	439.2	436.9	430.2	421.5	412.1	400.3	387.8	374.0	359.5	345.8
155°	420.1	420.1	418.2	413.1	406.8	399.1	389.6	379.3	367.9	355.7	344.2
157.5°	402.8	402.8	401.6	397.8	393.0	386.9	378.8	370.2	361.6	351.8	342.6
160°	392.1	392.1	391.4	387.6	383.8	378.7	371.7	364.7	357.0	348.7	341.0
162.5°	381.9	382.4	381.7	377.9	375.1	370.6	365.0	359.1	352.9	345.7	339.6
165°	366.6	367.2	367.9	365.3	362.7	359.5	355.1	351.2	346.2	341.0	336.6
167.5°	354.4	355.0	355.1	353.4	352.1	350.3	346.7	343.7	340.1	336.5	333.5
170°	346.8	346.8	347.4	346.8	345.5	343.6	341.0	339.2	336.0	333.4	331.5
172.5°	339.2	340.1	340.8	340.1	339.4	338.0	336.5	335.1	332.4	330.4	329.5
175°	330.2	331.5	332.8	331.5	331.5	331.5	330.2	329.6	328.3	327.0	327.0
177.5°	325.0	326.0	327.0	326.5	327.0	326.5	326.5	326.0	325.5	325.0	325.0
180°	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5



TEST NUMBER: P332555-930

CATALOG NUMBER: S124DIP-S575D810U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7
2.5°	790.4	786.8	784.3	782.3	776.7	773.4	770.9	767.3	763.2	758.9	753.6
5°	835.3	824.4	816.5	804.5	793.0	783.5	773.7	764.8	754.0	742.3	733.7
7.5°	882.4	866.3	845.8	827.9	807.9	790.4	774.9	758.9	742.2	726.1	711.3
10°	912.3	891.7	868.9	841.9	816.5	794.0	773.1	752.8	733.1	713.4	696.6
12.5°	944.5	918.8	885.1	853.5	825.2	795.0	769.7	744.9	721.1	700.5	680.9
15°	987.8	950.7	911.7	869.5	832.1	796.9	762.3	730.8	704.3	676.9	657.9
17.5°	1014.4	968.5	923.9	879.8	834.5	790.0	752.8	716.6	683.1	656.1	632.1
20°	1031.9	986.3	930.7	886.6	832.7	787.0	743.9	703.6	668.7	639.8	615.1
22.5°	1047.2	994.3	938.8	880.8	827.1	778.6	731.4	690.9	655.3	624.8	601.1
25°	1055.4	994.8	934.5	876.8	815.9	758.5	715.7	668.1	630.0	597.9	572.6
27.5°	1056.3	991.5	923.3	859.2	796.3	742.8	688.8	646.2	606.7	572.8	548.5
30°	1053.4	985.9	912.6	843.2	780.1	721.9	675.1	628.8	588.4	554.8	529.5
32.5°	1044.6	974.2	898.9	825.4	760.0	703.2	654.8	610.7	571.4	538.3	511.7
35°	1018.9	949.4	869.2	792.7	725.8	668.4	624.6	579.8	540.5	509.2	483.5
37.5°	978.8	915.9	834.4	755.2	689.5	631.9	588.4	548.0	512.6	480.6	454.3
40°	943.7	888.5	806.7	729.6	658.5	603.6	563.0	525.9	490.7	460.6	435.5
42.5°	903.4	855.2	779.8	698.1	629.6	574.5	534.9	501.6	468.4	440.6	415.5
45°	831.4	799.7	728.6	653.1	581.8	529.8	492.0	462.8	434.9	407.6	386.7
47.5°	748.7	733.0	673.1	601.4	533.7	482.4	449.7	422.7	398.3	375.1	356.7
50°	693.1	685.5	633.8	564.7	499.9	451.8	418.7	395.6	374.6	354.3	336.9
52.5°	638.3	638.1	591.4	528.1	468.2	421.8	389.1	367.4	349.3	332.7	317.1
55°	554.5	563.4	526.9	470.4	416.9	375.0	345.4	326.1	313.4	299.8	288.0
57.5°	477.5	492.3	462.2	412.5	367.7	329.1	303.5	288.9	275.4	267.2	258.6
60°	427.3	441.2	417.8	375.9	333.7	300.7	276.3	263.3	251.5	245.8	239.8
62.5°	382.6	395.1	377.6	338.8	302.2	270.5	249.9	237.4	229.5	223.2	219.2
65°	318.8	329.3	314.4	286.2	254.7	229.3	212.5	202.7	195.1	192.6	188.1
67.5°	257.7	267.3	259.2	235.2	210.0	190.8	177.7	168.2	163.7	161.4	158.3
70°	221.4	231.0	222.3	201.5	182.1	165.9	153.5	148.1	143.4	142.4	138.0
72.5°	190.7	197.2	188.6	172.3	155.7	142.0	132.5	126.9	124.3	122.6	120.3
75°	143.1	148.8	143.1	130.4	118.6	109.1	100.9	98.7	95.8	94.8	93.3
77.5°	101.3	106.2	101.8	93.9	85.1	77.8	73.4	70.5	69.9	68.2	69.0
80°	77.4	80.6	76.5	71.1	64.1	59.0	55.8	54.2	52.3	51.7	53.0
82.5°	55.6	57.0	54.9	51.3	46.1	42.7	40.6	38.7	38.4	38.5	38.5
85°	28.9	28.5	28.2	25.0	23.5	21.3	20.0	19.6	19.3	20.0	20.6
87.5°	11.4	11.7	10.7	9.6	8.7	7.9	7.3	6.7	7.3	7.9	8.2
90°	8.9	8.9	5.1	5.1	4.5	3.8	1.9	0.7	1.9	3.8	4.5
92.5°	128.7	79.3	46.9	33.7	24.4	16.6	10.6	7.3	10.6	16.6	24.4
95°	239.7	135.2	79.7	52.9	37.6	29.4	22.9	21.0	22.9	29.4	37.6
97.5°	215.5	129.1	86.4	64.0	50.9	43.2	37.7	37.7	37.7	43.2	50.9
100°	202.8	130.7	93.1	72.6	60.6	52.9	48.4	48.4	48.4	52.9	60.6
102.5°	199.2	135.7	101.7	82.3	70.8	63.6	59.7	58.6	59.7	63.6	70.8
105°	200.8	147.9	117.3	98.8	87.3	79.7	76.5	74.6	76.5	79.7	87.3
107.5°	210.3	162.1	134.0	115.8	104.8	96.6	93.4	92.2	93.4	96.6	104.8
110°	217.4	172.8	144.7	127.5	116.0	108.4	105.2	104.0	105.2	108.4	116.0



TEST NUMBER: P332555-930

CATALOG NUMBER: S124DIP-S575D810U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	225.0	183.0	156.0	138.7	127.3	120.1	116.4	115.1	116.4	120.1	127.3
115°	237.2	198.9	173.4	156.2	144.1	137.7	133.2	131.3	133.2	137.7	144.1
117.5°	249.5	214.3	190.1	172.3	160.9	153.9	149.9	148.1	149.9	153.9	160.9
120°	258.2	225.0	200.8	183.0	172.1	165.1	160.6	159.4	160.6	165.1	172.1
122.5°	266.4	235.2	211.0	193.6	181.8	175.3	170.9	169.6	170.9	175.3	181.8
125°	278.6	249.2	226.3	208.5	196.3	189.3	185.5	183.0	185.5	189.3	196.3
127.5°	289.2	262.3	240.1	222.1	209.5	201.5	196.9	194.9	196.9	201.5	209.5
130°	295.8	270.9	249.2	230.8	218.7	209.1	204.0	201.5	204.0	209.1	218.7
132.5°	302.4	278.1	256.4	239.0	225.8	216.8	210.1	208.1	210.1	216.8	225.8
135°	311.1	288.1	267.1	250.5	237.2	226.3	220.0	217.4	220.0	226.3	237.2
137.5°	317.2	295.8	276.1	260.3	246.5	236.1	229.1	226.7	229.1	236.1	246.5
140°	321.3	300.9	281.8	266.4	253.1	242.2	235.2	233.3	235.2	242.2	253.1
142.5°	324.3	305.5	286.9	272.1	259.2	248.9	242.4	240.4	242.4	248.9	259.2
145°	327.7	310.5	293.9	279.9	267.7	258.9	252.4	250.5	252.4	258.9	267.7
147.5°	330.6	315.6	300.0	287.4	277.3	268.2	262.5	261.9	262.5	268.2	277.3
150°	332.2	318.1	304.1	292.0	282.4	274.8	269.7	269.0	269.7	274.8	282.4
152.5°	333.1	320.2	307.7	296.6	288.0	280.9	275.8	275.7	275.8	280.9	288.0
155°	334.0	323.2	312.3	302.8	295.8	289.4	285.6	284.9	285.6	289.4	295.8
157.5°	334.0	325.4	316.2	308.7	302.6	297.6	294.0	294.0	294.0	297.6	302.6
160°	334.0	326.4	318.8	311.8	306.6	302.1	299.6	299.6	299.6	302.1	306.6
162.5°	334.0	327.4	320.2	314.8	310.2	306.2	304.2	304.8	304.2	306.2	310.2
165°	332.8	327.7	322.0	318.1	315.0	311.8	310.5	310.5	310.5	311.8	315.0
167.5°	331.3	327.6	323.3	320.4	318.6	316.2	315.6	316.2	315.6	316.2	318.6
170°	330.2	327.0	323.8	322.0	320.7	318.8	318.1	318.8	318.1	318.8	320.7
172.5°	329.2	326.5	324.3	322.9	322.2	320.8	320.7	321.3	320.7	320.8	322.2
175°	327.7	325.8	324.5	324.5	323.8	323.2	323.2	323.8	323.2	323.2	323.8
177.5°	326.0	325.0	324.5	324.5	324.5	324.0	324.5	325.0	324.5	324.0	324.5
180°	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5



TEST NUMBER: P332555-930

CATALOG NUMBER: S124DIP-S575D810U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7
2.5°	751.1	748.8	745.4	740.9	737.1	733.0	732.0	730.5	733.5	731.0	730.3
5°	726.4	719.7	711.2	701.4	695.7	687.4	685.8	682.7	679.5	679.1	676.0
7.5°	700.3	690.6	679.4	669.4	660.1	651.1	645.1	643.9	639.2	636.5	633.3
10°	683.6	671.6	658.5	649.1	638.2	628.8	622.1	618.2	615.1	611.6	608.5
12.5°	663.8	651.0	640.3	630.0	617.2	609.9	599.0	592.4	591.7	591.8	583.6
15°	640.7	628.1	611.6	597.0	590.0	576.1	570.1	562.4	557.7	552.9	549.1
17.5°	614.5	598.7	585.8	569.0	555.7	544.6	536.6	532.1	525.0	518.2	513.3
20°	597.9	581.1	567.5	549.8	535.2	521.5	514.9	508.5	503.1	497.4	492.0
22.5°	581.2	563.6	547.0	529.7	516.1	501.7	495.3	486.7	481.5	478.3	473.0
25°	554.8	535.8	516.7	500.3	486.3	473.6	465.0	458.4	452.7	450.1	446.6
27.5°	526.1	507.2	488.9	470.1	454.3	445.1	438.2	433.2	429.9	426.6	424.9
30°	507.8	488.2	468.6	451.1	436.5	427.3	420.9	417.4	414.9	413.4	411.7
32.5°	489.3	469.9	449.2	433.3	420.3	412.1	407.2	403.7	402.5	401.9	401.4
35°	459.7	440.0	420.9	406.7	394.3	391.1	387.0	385.1	384.5	386.7	387.7
37.5°	430.9	412.6	395.1	381.3	373.2	368.5	367.1	367.2	369.5	371.5	373.7
40°	412.4	394.6	378.1	366.1	358.5	355.6	355.0	356.5	359.1	361.3	363.9
42.5°	394.4	376.8	361.9	350.6	345.3	342.7	343.1	344.6	348.2	350.9	354.7
45°	366.4	351.8	337.2	328.0	323.6	324.2	324.2	327.0	330.5	334.7	338.8
47.5°	340.1	325.3	313.3	305.6	303.3	302.7	304.5	308.3	313.3	318.4	324.2
50°	322.3	308.3	297.8	290.9	288.4	289.3	291.9	295.3	301.3	307.7	313.7
52.5°	304.3	291.6	281.8	275.4	273.6	275.3	277.9	283.4	288.7	295.5	302.8
55°	276.3	265.5	257.9	253.2	252.5	253.5	256.3	262.4	269.9	278.5	285.5
57.5°	248.4	239.5	232.4	229.2	229.5	230.4	235.1	242.2	250.4	259.5	268.5
60°	229.7	221.4	215.7	213.2	213.5	215.4	221.1	227.8	237.9	246.8	256.3
62.5°	211.9	204.6	199.2	196.9	196.5	200.6	206.1	213.0	223.2	233.1	243.4
65°	183.4	177.7	173.2	171.9	172.8	176.0	183.0	192.2	200.8	211.2	222.1
67.5°	155.4	150.7	147.7	148.3	149.4	154.1	160.0	167.9	177.6	188.4	199.1
70°	137.7	133.2	130.7	131.0	132.9	138.6	143.7	151.6	162.1	173.2	182.1
72.5°	119.4	116.5	114.2	115.5	117.4	121.4	127.7	135.7	144.9	155.2	164.6
75°	91.6	91.6	90.4	91.4	94.2	98.0	102.8	111.0	120.3	128.5	136.1
77.5°	68.0	67.3	68.2	69.3	70.9	75.4	80.9	86.8	93.7	102.0	108.3
80°	52.0	52.3	53.9	55.8	56.5	59.9	65.6	71.1	76.5	83.4	89.4
82.5°	39.1	39.4	40.2	42.6	43.3	47.0	50.7	56.1	61.0	65.6	70.7
85°	21.3	21.3	22.8	23.8	25.4	27.9	30.2	33.3	37.7	40.9	45.7
87.5°	9.1	9.1	10.9	11.4	12.5	13.9	14.3	17.3	18.4	19.8	22.1
90°	5.1	5.1	8.9	8.9	10.2	11.5	10.8	11.5	12.1	12.7	12.7
92.5°	33.7	46.9	79.3	128.7	177.0	202.2	168.4	125.2	94.2	75.0	62.2
95°	52.9	79.7	135.2	239.7	392.1	519.6	534.3	472.4	373.6	288.1	226.3
97.5°	64.0	86.4	129.1	215.5	367.0	547.2	671.2	697.9	661.2	598.8	532.3
100°	72.6	93.1	130.7	202.8	332.8	512.6	675.7	768.8	781.5	750.3	703.2
102.5°	82.3	101.7	135.7	199.2	309.8	469.2	637.5	765.2	828.5	837.6	817.9
105°	98.8	117.3	147.9	200.8	290.1	418.2	568.0	714.0	824.3	887.4	913.5
107.5°	115.8	134.0	162.1	210.3	286.5	389.6	511.9	641.2	758.6	847.5	904.3
110°	127.5	144.7	172.8	217.4	287.5	379.9	483.9	597.4	707.6	800.1	870.2



TEST NUMBER: P332555-930

CATALOG NUMBER: S124DIP-S575D810U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	138.7	156.0	183.0	225.0	290.6	375.4	468.1	565.2	662.8	750.1	820.2
115°	156.2	173.4	198.9	237.2	296.4	372.9	453.2	533.0	611.4	685.9	747.1
117.5°	172.3	190.1	214.3	249.5	302.7	372.3	446.6	517.1	582.0	640.7	692.6
120°	183.0	200.8	225.0	258.2	307.3	372.3	443.0	510.0	569.3	620.3	665.5
122.5°	193.6	211.0	235.2	266.4	311.9	371.8	439.0	503.9	561.1	607.6	647.2
125°	208.5	226.3	249.2	278.6	318.8	371.0	432.2	493.4	548.3	592.2	627.3
127.5°	222.1	240.1	262.3	289.2	324.2	369.7	423.1	480.7	533.0	576.9	610.3
130°	230.8	249.2	270.9	295.8	328.3	369.1	417.6	470.5	520.8	564.2	597.9
132.5°	239.0	256.4	278.1	302.4	331.9	368.6	412.5	459.7	507.0	549.4	583.2
135°	250.5	267.1	288.1	311.1	337.2	367.9	404.8	445.0	486.4	525.3	557.2
137.5°	260.3	276.1	295.8	317.2	340.4	367.7	398.2	431.6	466.7	499.5	528.2
140°	266.4	281.8	300.9	321.3	343.0	367.2	394.6	424.0	453.9	482.6	509.4
142.5°	272.1	286.9	305.5	324.3	345.0	367.2	391.6	416.8	443.2	467.8	491.0
145°	279.9	293.9	310.5	327.7	346.2	365.9	386.3	406.8	428.4	447.5	465.4
147.5°	287.4	300.0	315.6	330.6	346.8	363.6	381.6	398.4	415.6	431.0	445.0
150°	292.0	304.1	318.1	332.2	346.8	362.1	378.1	393.3	408.0	420.8	432.2
152.5°	296.6	307.7	320.2	333.1	345.8	359.5	374.0	387.8	400.3	412.1	421.5
155°	302.8	312.3	323.2	334.0	344.2	355.7	367.9	379.3	389.6	399.1	406.8
157.5°	308.7	316.2	325.4	334.0	342.6	351.8	361.6	370.2	378.8	386.9	393.0
160°	311.8	318.8	326.4	334.0	341.0	348.7	357.0	364.7	371.7	378.7	383.8
162.5°	314.8	320.2	327.4	334.0	339.6	345.7	352.9	359.1	365.0	370.6	375.1
165°	318.1	322.0	327.7	332.8	336.6	341.0	346.2	351.2	355.1	359.5	362.7
167.5°	320.4	323.3	327.6	331.3	333.5	336.5	340.1	343.7	346.7	350.3	352.1
170°	322.0	323.8	327.0	330.2	331.5	333.4	336.0	339.2	341.0	343.6	345.5
172.5°	322.9	324.3	326.5	329.2	329.5	330.4	332.4	335.1	336.5	338.0	339.4
175°	324.5	324.5	325.8	327.7	327.0	327.0	328.3	329.6	330.2	331.5	331.5
177.5°	324.5	324.5	325.0	326.0	325.0	325.0	325.5	326.0	326.5	326.5	327.0
180°	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5



TEST NUMBER: P332555-930

CATALOG NUMBER: S124DIP-S575D810U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7
2.5°	729.7	729.2	727.4	727.2	727.4	729.2	729.7	730.3	731.0	733.5	730.5
5°	674.1	672.5	671.6	675.1	671.6	672.5	674.1	676.0	679.1	679.5	682.7
7.5°	632.2	630.9	628.1	627.2	628.1	630.9	632.2	633.3	636.5	639.2	643.9
10°	605.3	604.0	601.4	600.8	601.4	604.0	605.3	608.5	611.6	615.1	618.2
12.5°	579.4	576.8	576.3	577.0	576.3	576.8	579.4	583.6	591.8	591.7	592.4
15°	544.9	543.7	540.2	541.2	540.2	543.7	544.9	549.1	552.9	557.7	562.4
17.5°	511.1	509.6	505.3	509.1	505.3	509.6	511.1	513.3	518.2	525.0	532.1
20°	489.8	487.2	485.0	484.7	485.0	487.2	489.8	492.0	497.4	503.1	508.5
22.5°	469.4	467.2	467.0	464.9	467.0	467.2	469.4	473.0	478.3	481.5	486.7
25°	444.1	441.9	441.2	439.7	441.2	441.9	444.1	446.6	450.1	452.7	458.4
27.5°	424.6	423.5	422.4	422.9	422.4	423.5	424.6	424.9	426.6	429.9	433.2
30°	412.7	412.4	411.7	411.7	411.7	412.4	412.7	411.7	413.4	414.9	417.4
32.5°	402.8	402.8	403.1	403.1	403.1	402.8	402.8	401.4	401.9	402.5	403.7
35°	388.9	389.9	390.5	389.6	390.5	389.9	388.9	387.7	386.7	384.5	385.1
37.5°	376.3	377.3	378.2	379.3	378.2	377.3	376.3	373.7	371.5	369.5	367.2
40°	366.7	368.9	369.6	371.1	369.6	368.9	366.7	363.9	361.3	359.1	356.5
42.5°	357.6	360.0	361.7	362.0	361.7	360.0	357.6	354.7	350.9	348.2	344.6
45°	343.6	346.1	348.3	348.3	348.3	346.1	343.6	338.8	334.7	330.5	327.0
47.5°	329.1	332.7	334.9	335.5	334.9	332.7	329.1	324.2	318.4	313.3	308.3
50°	319.1	323.6	325.8	327.3	325.8	323.6	319.1	313.7	307.7	301.3	295.3
52.5°	309.5	313.9	316.9	317.7	316.9	313.9	309.5	302.8	295.5	288.7	283.4
55°	292.8	299.1	302.6	303.9	302.6	299.1	292.8	285.5	278.5	269.9	262.4
57.5°	277.0	282.9	287.0	287.9	287.0	282.9	277.0	268.5	259.5	250.4	242.2
60°	264.9	271.3	276.3	277.3	276.3	271.3	264.9	256.3	246.8	237.9	227.8
62.5°	252.4	259.0	263.6	266.1	263.6	259.0	252.4	243.4	233.1	223.2	213.0
65°	231.0	237.6	242.1	243.0	242.1	237.6	231.0	222.1	211.2	200.8	192.2
67.5°	207.5	214.1	217.0	218.9	217.0	214.1	207.5	199.1	188.4	177.6	167.9
70°	190.9	196.3	199.5	201.1	199.5	196.3	190.9	182.1	173.2	162.1	151.6
72.5°	172.2	177.8	181.5	181.8	181.5	177.8	172.2	164.6	155.2	144.9	135.7
75°	143.4	148.5	150.3	150.3	150.3	148.5	143.4	136.1	128.5	120.3	111.0
77.5°	113.5	116.1	118.5	119.0	118.5	116.1	113.5	108.3	102.0	93.7	86.8
80°	94.2	95.8	97.7	97.7	97.7	95.8	94.2	89.4	83.4	76.5	71.1
82.5°	74.4	75.7	77.6	77.4	77.6	75.7	74.4	70.7	65.6	61.0	56.1
85°	45.0	47.9	47.6	47.0	47.6	47.9	45.0	45.7	40.9	37.7	33.3
87.5°	23.0	23.4	24.0	24.5	24.0	23.4	23.0	22.1	19.8	18.4	17.3
90°	13.4	14.0	13.4	13.4	13.4	14.0	13.4	12.7	12.7	12.1	11.5
92.5°	54.7	51.3	49.1	49.1	49.1	51.3	54.7	62.2	75.0	94.2	125.2
95°	195.1	175.3	163.9	155.6	163.9	175.3	195.1	226.3	288.1	373.6	472.4
97.5°	486.6	448.2	429.0	415.8	429.0	448.2	486.6	532.3	598.8	661.2	697.9
100°	647.7	608.8	589.7	584.6	589.7	608.8	647.7	703.2	750.3	781.5	768.8
102.5°	783.9	755.7	735.6	731.5	735.6	755.7	783.9	817.9	837.6	828.5	765.2
105°	914.8	909.7	900.8	897.0	900.8	909.7	914.8	913.5	887.4	824.3	714.0
107.5°	935.9	950.4	956.8	958.4	956.8	950.4	935.9	904.3	847.5	758.6	641.2
110°	915.4	942.2	953.7	959.4	953.7	942.2	915.4	870.2	800.1	707.6	597.4



TEST NUMBER: P332555-930

CATALOG NUMBER: S124DIP-S575D810U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	871.6	904.0	920.1	929.4	920.1	904.0	871.6	820.2	750.1	662.8	565.2
115°	797.5	835.8	856.1	861.3	856.1	835.8	797.5	747.1	685.9	611.4	533.0
117.5°	735.6	767.7	788.3	792.3	788.3	767.7	735.6	692.6	640.7	582.0	517.1
120°	701.9	729.9	746.5	753.5	746.5	729.9	701.9	665.5	620.3	569.3	510.0
122.5°	677.9	701.9	715.9	722.9	715.9	701.9	677.9	647.2	607.6	561.1	503.9
125°	652.8	671.3	683.4	687.2	683.4	671.3	652.8	627.3	592.2	548.3	493.4
127.5°	635.9	652.3	662.5	666.3	662.5	652.3	635.9	610.3	576.9	533.0	480.7
130°	624.1	640.1	650.3	654.1	650.3	640.1	624.1	597.9	564.2	520.8	470.5
132.5°	608.8	626.8	636.5	640.3	636.5	626.8	608.8	583.2	549.4	507.0	459.7
135°	582.7	600.5	610.7	614.6	610.7	600.5	582.7	557.2	525.3	486.4	445.0
137.5°	552.0	569.6	578.0	582.7	578.0	569.6	552.0	528.2	499.5	466.7	431.6
140°	531.7	545.7	554.6	559.7	554.6	545.7	531.7	509.4	482.6	453.9	424.0
142.5°	510.8	523.7	531.7	535.2	531.7	523.7	510.8	491.0	467.8	443.2	416.8
145°	481.4	492.1	498.6	501.7	498.6	492.1	481.4	465.4	447.5	428.4	406.8
147.5°	456.7	466.0	470.8	472.0	470.8	466.0	456.7	445.0	431.0	415.6	398.4
150°	442.5	450.7	454.5	455.2	454.5	450.7	442.5	432.2	420.8	408.0	393.3
152.5°	430.2	436.9	439.2	439.9	439.2	436.9	430.2	421.5	412.1	400.3	387.8
155°	413.1	418.2	420.1	420.1	420.1	418.2	413.1	406.8	399.1	389.6	379.3
157.5°	397.8	401.6	402.8	402.8	402.8	401.6	397.8	393.0	386.9	378.8	370.2
160°	387.6	391.4	392.1	392.1	392.1	391.4	387.6	383.8	378.7	371.7	364.7
162.5°	377.9	381.7	382.4	381.9	382.4	381.7	377.9	375.1	370.6	365.0	359.1
165°	365.3	367.9	367.2	366.6	367.2	367.9	365.3	362.7	359.5	355.1	351.2
167.5°	353.4	355.1	355.0	354.4	355.0	355.1	353.4	352.1	350.3	346.7	343.7
170°	346.8	347.4	346.8	346.8	346.8	347.4	346.8	345.5	343.6	341.0	339.2
172.5°	340.1	340.8	340.1	339.2	340.1	340.8	340.1	339.4	338.0	336.5	335.1
175°	331.5	332.8	331.5	330.2	331.5	332.8	331.5	331.5	331.5	330.2	329.6
177.5°	326.5	327.0	326.0	325.0	326.0	327.0	326.5	327.0	326.5	326.5	326.0
180°	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5



TEST NUMBER: P332555-930

CATALOG NUMBER: S124DIP-S575D810U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7
2.5°	732.0	733.0	737.1	740.9	745.4	748.8	751.1	753.6	758.9	763.2	767.3
5°	685.8	687.4	695.7	701.4	711.2	719.7	726.4	733.7	742.3	754.0	764.8
7.5°	645.1	651.1	660.1	669.4	679.4	690.6	700.3	711.3	726.1	742.2	758.9
10°	622.1	628.8	638.2	649.1	658.5	671.6	683.6	696.6	713.4	733.1	752.8
12.5°	599.0	609.9	617.2	630.0	640.3	651.0	663.8	680.9	700.5	721.1	744.9
15°	570.1	576.1	590.0	597.0	611.6	628.1	640.7	657.9	676.9	704.3	730.8
17.5°	536.6	544.6	555.7	569.0	585.8	598.7	614.5	632.1	656.1	683.1	716.6
20°	514.9	521.5	535.2	549.8	567.5	581.1	597.9	615.1	639.8	668.7	703.6
22.5°	495.3	501.7	516.1	529.7	547.0	563.6	581.2	601.1	624.8	655.3	690.9
25°	465.0	473.6	486.3	500.3	516.7	535.8	554.8	572.6	597.9	630.0	668.1
27.5°	438.2	445.1	454.3	470.1	488.9	507.2	526.1	548.5	572.8	606.7	646.2
30°	420.9	427.3	436.5	451.1	468.6	488.2	507.8	529.5	554.8	588.4	628.8
32.5°	407.2	412.1	420.3	433.3	449.2	469.9	489.3	511.7	538.3	571.4	610.7
35°	387.0	391.1	394.3	406.7	420.9	440.0	459.7	483.5	509.2	540.5	579.8
37.5°	367.1	368.5	373.2	381.3	395.1	412.6	430.9	454.3	480.6	512.6	548.0
40°	355.0	355.6	358.5	366.1	378.1	394.6	412.4	435.5	460.6	490.7	525.9
42.5°	343.1	342.7	345.3	350.6	361.9	376.8	394.4	415.5	440.6	468.4	501.6
45°	324.2	324.2	323.6	328.0	337.2	351.8	366.4	386.7	407.6	434.9	462.8
47.5°	304.5	302.7	303.3	305.6	313.3	325.3	340.1	356.7	375.1	398.3	422.7
50°	291.9	289.3	288.4	290.9	297.8	308.3	322.3	336.9	354.3	374.6	395.6
52.5°	277.9	275.3	273.6	275.4	281.8	291.6	304.3	317.1	332.7	349.3	367.4
55°	256.3	253.5	252.5	253.2	257.9	265.5	276.3	288.0	299.8	313.4	326.1
57.5°	235.1	230.4	229.5	229.2	232.4	239.5	248.4	258.6	267.2	275.4	288.9
60°	221.1	215.4	213.5	213.2	215.7	221.4	229.7	239.8	245.8	251.5	263.3
62.5°	206.1	200.6	196.5	196.9	199.2	204.6	211.9	219.2	223.2	229.5	237.4
65°	183.0	176.0	172.8	171.9	173.2	177.7	183.4	188.1	192.6	195.1	202.7
67.5°	160.0	154.1	149.4	148.3	147.7	150.7	155.4	158.3	161.4	163.7	168.2
70°	143.7	138.6	132.9	131.0	130.7	133.2	137.7	138.0	142.4	143.4	148.1
72.5°	127.7	121.4	117.4	115.5	114.2	116.5	119.4	120.3	122.6	124.3	126.9
75°	102.8	98.0	94.2	91.4	90.4	91.6	91.6	93.3	94.8	95.8	98.7
77.5°	80.9	75.4	70.9	69.3	68.2	67.3	68.0	69.0	68.2	69.9	70.5
80°	65.6	59.9	56.5	55.8	53.9	52.3	52.0	53.0	51.7	52.3	54.2
82.5°	50.7	47.0	43.3	42.6	40.2	39.4	39.1	38.5	38.5	38.4	38.7
85°	30.2	27.9	25.4	23.8	22.8	21.3	21.3	20.6	20.0	19.3	19.6
87.5°	14.3	13.9	12.5	11.4	10.9	9.1	9.1	8.2	7.9	7.3	6.7
90°	10.8	11.5	10.2	8.9	8.9	5.1	5.1	4.5	3.8	1.9	0.7
92.5°	168.4	202.2	177.0	128.7	79.3	46.9	33.7	24.4	16.6	10.6	7.3
95°	534.3	519.6	392.1	239.7	135.2	79.7	52.9	37.6	29.4	22.9	21.0
97.5°	671.2	547.2	367.0	215.5	129.1	86.4	64.0	50.9	43.2	37.7	37.7
100°	675.7	512.6	332.8	202.8	130.7	93.1	72.6	60.6	52.9	48.4	48.4
102.5°	637.5	469.2	309.8	199.2	135.7	101.7	82.3	70.8	63.6	59.7	58.6
105°	568.0	418.2	290.1	200.8	147.9	117.3	98.8	87.3	79.7	76.5	74.6
107.5°	511.9	389.6	286.5	210.3	162.1	134.0	115.8	104.8	96.6	93.4	92.2
110°	483.9	379.9	287.5	217.4	172.8	144.7	127.5	116.0	108.4	105.2	104.0



TEST NUMBER: P332555-930

CATALOG NUMBER: S124DIP-S575D810U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	468.1	375.4	290.6	225.0	183.0	156.0	138.7	127.3	120.1	116.4	115.1
115°	453.2	372.9	296.4	237.2	198.9	173.4	156.2	144.1	137.7	133.2	131.3
117.5°	446.6	372.3	302.7	249.5	214.3	190.1	172.3	160.9	153.9	149.9	148.1
120°	443.0	372.3	307.3	258.2	225.0	200.8	183.0	172.1	165.1	160.6	159.4
122.5°	439.0	371.8	311.9	266.4	235.2	211.0	193.6	181.8	175.3	170.9	169.6
125°	432.2	371.0	318.8	278.6	249.2	226.3	208.5	196.3	189.3	185.5	183.0
127.5°	423.1	369.7	324.2	289.2	262.3	240.1	222.1	209.5	201.5	196.9	194.9
130°	417.6	369.1	328.3	295.8	270.9	249.2	230.8	218.7	209.1	204.0	201.5
132.5°	412.5	368.6	331.9	302.4	278.1	256.4	239.0	225.8	216.8	210.1	208.1
135°	404.8	367.9	337.2	311.1	288.1	267.1	250.5	237.2	226.3	220.0	217.4
137.5°	398.2	367.7	340.4	317.2	295.8	276.1	260.3	246.5	236.1	229.1	226.7
140°	394.6	367.2	343.0	321.3	300.9	281.8	266.4	253.1	242.2	235.2	233.3
142.5°	391.6	367.2	345.0	324.3	305.5	286.9	272.1	259.2	248.9	242.4	240.4
145°	386.3	365.9	346.2	327.7	310.5	293.9	279.9	267.7	258.9	252.4	250.5
147.5°	381.6	363.6	346.8	330.6	315.6	300.0	287.4	277.3	268.2	262.5	261.9
150°	378.1	362.1	346.8	332.2	318.1	304.1	292.0	282.4	274.8	269.7	269.0
152.5°	374.0	359.5	345.8	333.1	320.2	307.7	296.6	288.0	280.9	275.8	275.7
155°	367.9	355.7	344.2	334.0	323.2	312.3	302.8	295.8	289.4	285.6	284.9
157.5°	361.6	351.8	342.6	334.0	325.4	316.2	308.7	302.6	297.6	294.0	294.0
160°	357.0	348.7	341.0	334.0	326.4	318.8	311.8	306.6	302.1	299.6	299.6
162.5°	352.9	345.7	339.6	334.0	327.4	320.2	314.8	310.2	306.2	304.2	304.8
165°	346.2	341.0	336.6	332.8	327.7	322.0	318.1	315.0	311.8	310.5	310.5
167.5°	340.1	336.5	333.5	331.3	327.6	323.3	320.4	318.6	316.2	315.6	316.2
170°	336.0	333.4	331.5	330.2	327.0	323.8	322.0	320.7	318.8	318.1	318.8
172.5°	332.4	330.4	329.5	329.2	326.5	324.3	322.9	322.2	320.8	320.7	321.3
175°	328.3	327.0	327.0	327.7	325.8	324.5	324.5	323.8	323.2	323.2	323.8
177.5°	325.5	325.0	325.0	326.0	325.0	324.5	324.5	324.5	324.0	324.5	325.0
180°	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5



TEST NUMBER: P332555-930

CATALOG NUMBER: S124DIP-S575D810U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7
2.5°	770.9	773.4	776.7	782.3	784.3	786.8	790.4	790.1	791.2	794.9	803.1
5°	773.7	783.5	793.0	804.5	816.5	824.4	835.3	841.9	848.6	857.1	871.7
7.5°	774.9	790.4	807.9	827.9	845.8	866.3	882.4	897.5	911.1	929.2	946.6
10°	773.1	794.0	816.5	841.9	868.9	891.7	912.3	935.8	955.8	977.6	997.4
12.5°	769.7	795.0	825.2	853.5	885.1	918.8	944.5	968.2	994.8	1020.0	1050.4
15°	762.3	796.9	832.1	869.5	911.7	950.7	987.8	1018.6	1047.2	1084.9	1124.5
17.5°	752.8	790.0	834.5	879.8	923.9	968.5	1014.4	1060.6	1096.7	1143.5	1174.6
20°	743.9	787.0	832.7	886.6	930.7	986.3	1031.9	1076.6	1126.1	1172.7	1209.9
22.5°	731.4	778.6	827.1	880.8	938.8	994.3	1047.2	1095.7	1145.2	1195.9	1240.8
25°	715.7	758.5	815.9	876.8	934.5	994.8	1055.4	1116.3	1169.5	1223.2	1265.1
27.5°	688.8	742.8	796.3	859.2	923.3	991.5	1056.3	1120.1	1175.8	1219.9	1245.9
30°	675.1	721.9	780.1	843.2	912.6	985.9	1053.4	1116.0	1168.0	1203.2	1213.7
32.5°	654.8	703.2	760.0	825.4	898.9	974.2	1044.6	1103.5	1147.0	1165.4	1152.8
35°	624.6	668.4	725.8	792.7	869.2	949.4	1018.9	1068.7	1091.0	1073.5	1030.0
37.5°	588.4	631.9	689.5	755.2	834.4	915.9	978.8	1014.6	1007.2	963.8	899.0
40°	563.0	603.6	658.5	729.6	806.7	888.5	943.7	963.1	942.8	880.6	811.8
42.5°	534.9	574.5	629.6	698.1	779.8	855.2	903.4	905.0	871.0	796.6	727.5
45°	492.0	529.8	581.8	653.1	728.6	799.7	831.4	815.9	753.1	681.3	611.9
47.5°	449.7	482.4	533.7	601.4	673.1	733.0	748.7	720.7	653.8	584.2	519.8
50°	418.7	451.8	499.9	564.7	633.8	685.5	693.1	656.0	590.4	520.2	469.8
52.5°	389.1	421.8	468.2	528.1	591.4	638.1	638.3	595.3	529.9	467.5	420.5
55°	345.4	375.0	416.9	470.4	526.9	563.4	554.5	510.1	453.3	399.1	358.2
57.5°	303.5	329.1	367.7	412.5	462.2	492.3	477.5	434.8	384.1	338.1	307.0
60°	276.3	300.7	333.7	375.9	417.8	441.2	427.3	388.6	341.9	304.8	277.9
62.5°	249.9	270.5	302.2	338.8	377.6	395.1	382.6	344.5	304.2	270.6	248.7
65°	212.5	229.3	254.7	286.2	314.4	329.3	318.8	283.2	252.5	228.4	210.9
67.5°	177.7	190.8	210.0	235.2	259.2	267.3	257.7	232.9	206.9	187.6	175.3
70°	153.5	165.9	182.1	201.5	222.3	231.0	221.4	201.8	180.5	162.7	150.7
72.5°	132.5	142.0	155.7	172.3	188.6	197.2	190.7	171.8	153.8	140.6	130.4
75°	100.9	109.1	118.6	130.4	143.1	148.8	143.1	130.0	117.6	107.9	100.5
77.5°	73.4	77.8	85.1	93.9	101.8	106.2	101.3	92.5	84.9	78.2	74.5
80°	55.8	59.0	64.1	71.1	76.5	80.6	77.4	70.1	64.1	59.6	58.0
82.5°	40.6	42.7	46.1	51.3	54.9	57.0	55.6	50.3	47.9	43.9	42.3
85°	20.0	21.3	23.5	25.0	28.2	28.5	28.9	26.7	24.5	23.5	22.2
87.5°	7.3	7.9	8.7	9.6	10.7	11.7	11.4	11.7	10.9	10.5	9.6
90°	1.9	3.8	4.5	5.1	5.1	8.9	8.9	10.2	11.5	10.8	11.5
92.5°	10.6	16.6	24.4	33.7	46.9	79.3	128.7	177.0	202.2	168.4	125.2
95°	22.9	29.4	37.6	52.9	79.7	135.2	239.7	392.1	519.6	534.3	472.4
97.5°	37.7	43.2	50.9	64.0	86.4	129.1	215.5	367.0	547.2	671.2	697.9
100°	48.4	52.9	60.6	72.6	93.1	130.7	202.8	332.8	512.6	675.7	768.8
102.5°	59.7	63.6	70.8	82.3	101.7	135.7	199.2	309.8	469.2	637.5	765.2
105°	76.5	79.7	87.3	98.8	117.3	147.9	200.8	290.1	418.2	568.0	714.0
107.5°	93.4	96.6	104.8	115.8	134.0	162.1	210.3	286.5	389.6	511.9	641.2
110°	105.2	108.4	116.0	127.5	144.7	172.8	217.4	287.5	379.9	483.9	597.4



TEST NUMBER: P332555-930

CATALOG NUMBER: S124DIP-S575D810U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	116.4	120.1	127.3	138.7	156.0	183.0	225.0	290.6	375.4	468.1	565.2
115°	133.2	137.7	144.1	156.2	173.4	198.9	237.2	296.4	372.9	453.2	533.0
117.5°	149.9	153.9	160.9	172.3	190.1	214.3	249.5	302.7	372.3	446.6	517.1
120°	160.6	165.1	172.1	183.0	200.8	225.0	258.2	307.3	372.3	443.0	510.0
122.5°	170.9	175.3	181.8	193.6	211.0	235.2	266.4	311.9	371.8	439.0	503.9
125°	185.5	189.3	196.3	208.5	226.3	249.2	278.6	318.8	371.0	432.2	493.4
127.5°	196.9	201.5	209.5	222.1	240.1	262.3	289.2	324.2	369.7	423.1	480.7
130°	204.0	209.1	218.7	230.8	249.2	270.9	295.8	328.3	369.1	417.6	470.5
132.5°	210.1	216.8	225.8	239.0	256.4	278.1	302.4	331.9	368.6	412.5	459.7
135°	220.0	226.3	237.2	250.5	267.1	288.1	311.1	337.2	367.9	404.8	445.0
137.5°	229.1	236.1	246.5	260.3	276.1	295.8	317.2	340.4	367.7	398.2	431.6
140°	235.2	242.2	253.1	266.4	281.8	300.9	321.3	343.0	367.2	394.6	424.0
142.5°	242.4	248.9	259.2	272.1	286.9	305.5	324.3	345.0	367.2	391.6	416.8
145°	252.4	258.9	267.7	279.9	293.9	310.5	327.7	346.2	365.9	386.3	406.8
147.5°	262.5	268.2	277.3	287.4	300.0	315.6	330.6	346.8	363.6	381.6	398.4
150°	269.7	274.8	282.4	292.0	304.1	318.1	332.2	346.8	362.1	378.1	393.3
152.5°	275.8	280.9	288.0	296.6	307.7	320.2	333.1	345.8	359.5	374.0	387.8
155°	285.6	289.4	295.8	302.8	312.3	323.2	334.0	344.2	355.7	367.9	379.3
157.5°	294.0	297.6	302.6	308.7	316.2	325.4	334.0	342.6	351.8	361.6	370.2
160°	299.6	302.1	306.6	311.8	318.8	326.4	334.0	341.0	348.7	357.0	364.7
162.5°	304.2	306.2	310.2	314.8	320.2	327.4	334.0	339.6	345.7	352.9	359.1
165°	310.5	311.8	315.0	318.1	322.0	327.7	332.8	336.6	341.0	346.2	351.2
167.5°	315.6	316.2	318.6	320.4	323.3	327.6	331.3	333.5	336.5	340.1	343.7
170°	318.1	318.8	320.7	322.0	323.8	327.0	330.2	331.5	333.4	336.0	339.2
172.5°	320.7	320.8	322.2	322.9	324.3	326.5	329.2	329.5	330.4	332.4	335.1
175°	323.2	323.2	323.8	324.5	324.5	325.8	327.7	327.0	327.0	328.3	329.6
177.5°	324.5	324.0	324.5	324.5	324.5	325.0	326.0	325.0	325.0	325.5	326.0
180°	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5



TEST NUMBER: P332555-930

CATALOG NUMBER: S124DIP-S575D810U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	765.7	765.7	765.7	765.7	765.7	765.7	765.7
2.5°	807.1	807.6	809.9	811.7	812.2	814.7	815.0
5°	878.1	883.5	893.9	894.9	896.4	904.7	898.4
7.5°	961.2	974.9	984.0	992.1	995.0	998.6	997.8
10°	1014.5	1034.8	1044.9	1061.1	1061.8	1065.8	1063.3
12.5°	1068.0	1091.6	1110.1	1113.1	1126.7	1128.8	1132.4
15°	1143.9	1169.0	1194.7	1203.9	1222.5	1227.0	1234.0
17.5°	1215.2	1240.8	1258.8	1282.6	1290.3	1300.6	1293.6
20°	1254.3	1282.2	1305.0	1323.7	1331.7	1337.4	1336.8
22.5°	1277.9	1306.0	1324.5	1338.7	1346.1	1348.6	1348.4
25°	1292.7	1308.9	1314.6	1320.0	1311.7	1308.9	1310.1
27.5°	1251.6	1247.3	1232.5	1212.9	1192.6	1176.5	1167.8
30°	1195.0	1170.2	1147.7	1108.4	1088.0	1076.0	1065.2
32.5°	1114.8	1075.5	1032.3	996.2	973.1	955.2	952.5
35°	977.4	918.4	865.4	821.3	798.4	779.1	774.6
37.5°	831.0	769.6	721.9	683.1	658.5	644.9	632.2
40°	733.7	681.1	634.1	601.1	582.4	572.6	564.7
42.5°	658.8	610.7	564.1	538.9	522.0	516.0	511.4
45°	555.5	510.7	478.3	459.3	449.5	439.4	434.6
47.5°	472.6	436.3	414.9	398.8	388.2	382.2	379.1
50°	425.7	395.9	376.8	364.5	355.0	350.2	347.6
52.5°	384.1	359.6	343.6	333.8	327.3	323.8	322.8
55°	330.8	312.2	302.0	293.4	288.7	285.5	284.2
57.5°	287.6	273.2	265.0	257.9	256.1	253.4	252.5
60°	259.2	248.1	241.1	236.4	234.7	231.5	232.2
62.5°	234.1	224.9	219.0	216.3	214.2	211.5	212.4
65°	198.0	191.3	188.1	185.6	183.0	181.5	182.7
67.5°	166.1	161.5	157.2	155.7	154.5	154.3	152.9
70°	145.3	141.5	137.7	136.7	136.7	135.4	135.1
72.5°	125.2	122.5	119.9	119.2	118.2	118.7	117.4
75°	96.8	94.5	93.6	92.6	92.3	92.3	91.4
77.5°	71.5	69.9	68.3	68.3	67.2	66.8	66.6
80°	54.2	53.6	52.3	52.3	51.7	52.0	51.4
82.5°	40.8	39.9	39.6	39.1	38.2	38.3	37.7
85°	21.9	21.0	20.6	19.6	19.0	19.6	19.0
87.5°	10.0	9.9	9.6	9.3	9.1	9.0	8.2
90°	12.1	12.7	12.7	13.4	14.0	13.4	13.4
92.5°	94.2	75.0	62.2	54.7	51.3	49.1	49.1
95°	373.6	288.1	226.3	195.1	175.3	163.9	155.6
97.5°	661.2	598.8	532.3	486.6	448.2	429.0	415.8
100°	781.5	750.3	703.2	647.7	608.8	589.7	584.6
102.5°	828.5	837.6	817.9	783.9	755.7	735.6	731.5
105°	824.3	887.4	913.5	914.8	909.7	900.8	897.0
107.5°	758.6	847.5	904.3	935.9	950.4	956.8	958.4
110°	707.6	800.1	870.2	915.4	942.2	953.7	959.4



TEST NUMBER: P332555-930

CATALOG NUMBER: S124DIP-S575D810U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	662.8	750.1	820.2	871.6	904.0	920.1	929.4
115°	611.4	685.9	747.1	797.5	835.8	856.1	861.3
117.5°	582.0	640.7	692.6	735.6	767.7	788.3	792.3
120°	569.3	620.3	665.5	701.9	729.9	746.5	753.5
122.5°	561.1	607.6	647.2	677.9	701.9	715.9	722.9
125°	548.3	592.2	627.3	652.8	671.3	683.4	687.2
127.5°	533.0	576.9	610.3	635.9	652.3	662.5	666.3
130°	520.8	564.2	597.9	624.1	640.1	650.3	654.1
132.5°	507.0	549.4	583.2	608.8	626.8	636.5	640.3
135°	486.4	525.3	557.2	582.7	600.5	610.7	614.6
137.5°	466.7	499.5	528.2	552.0	569.6	578.0	582.7
140°	453.9	482.6	509.4	531.7	545.7	554.6	559.7
142.5°	443.2	467.8	491.0	510.8	523.7	531.7	535.2
145°	428.4	447.5	465.4	481.4	492.1	498.6	501.7
147.5°	415.6	431.0	445.0	456.7	466.0	470.8	472.0
150°	408.0	420.8	432.2	442.5	450.7	454.5	455.2
152.5°	400.3	412.1	421.5	430.2	436.9	439.2	439.9
155°	389.6	399.1	406.8	413.1	418.2	420.1	420.1
157.5°	378.8	386.9	393.0	397.8	401.6	402.8	402.8
160°	371.7	378.7	383.8	387.6	391.4	392.1	392.1
162.5°	365.0	370.6	375.1	377.9	381.7	382.4	381.9
165°	355.1	359.5	362.7	365.3	367.9	367.2	366.6
167.5°	346.7	350.3	352.1	353.4	355.1	355.0	354.4
170°	341.0	343.6	345.5	346.8	347.4	346.8	346.8
172.5°	336.5	338.0	339.4	340.1	340.8	340.1	339.2
175°	330.2	331.5	331.5	331.5	332.8	331.5	330.2
177.5°	326.5	326.5	327.0	326.5	327.0	326.0	325.0
180°	324.5	324.5	324.5	324.5	324.5	324.5	324.5

(END OF REPORT)