

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332977-930

Luminaire Tested: **S124RDIP-S1020D1035U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332977-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIP-S1020D1035U930-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1035 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6323.8 lumens
Efficiency: N/A
Efficacy: 104.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 60.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332977-930

CATALOG NUMBER: S124RDIP-S1020D1035U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332977-930

CATALOG NUMBER: S124RDIP-S1020D1035U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	60	60	60	54
1	99	95	91	87	92	88	85	82	75	73	71	64	62	61	53	52	51	46
2	90	83	77	72	84	77	72	68	66	62	59	56	54	51	47	45	43	39
3	83	73	66	60	76	68	62	57	59	54	50	50	46	43	42	39	37	33
4	76	65	57	51	70	61	54	48	52	47	43	45	41	37	38	35	32	29
5	70	58	50	44	64	54	47	42	47	41	37	40	36	33	34	31	28	25
6	64	52	44	38	59	49	42	36	42	37	33	37	32	29	31	28	25	22
7	59	47	39	34	55	44	37	32	39	33	29	33	29	26	28	25	22	20
8	55	43	35	30	51	40	33	28	35	30	26	31	26	23	26	23	20	18
9	51	39	32	27	48	37	30	26	32	27	23	28	24	21	24	21	18	16
10	48	36	29	24	45	34	27	23	30	25	21	26	22	19	22	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11885	11885	11885
5°	11912	11766	11839
10°	11837	11625	11625
15°	11701	11381	11295
20°	11515	11059	10856
25°	11276	10684	10413
30°	11044	10288	9857
35°	10787	9876	9298
40°	10478	9409	8696
45°	10193	8944	8082
50°	9868	8410	7433
55°	9520	7854	6726
60°	9137	7245	6006
65°	8785	6481	5297
70°	8275	5641	4497
75°	7629	4676	3656
80°	6657	3561	3357
85°	5641	3242	3029



TEST NUMBER: P332977-930

CATALOG NUMBER: S124RDIP-S1020D1035U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.3	2.2
10°-20°	385.6	6.1
20°-30°	556.9	8.8
30°-40°	631.2	10.0
40°-50°	609.5	9.6
50°-60°	506.9	8.0
60°-70°	350.0	5.5
70°-80°	177.4	2.8
80°-90°	48.7	0.8
90°-100°	69.4	1.1
100°-110°	205.6	3.3
110°-120°	348.9	5.5
120°-130°	460.1	7.3
130°-140°	516.7	8.2
140°-150°	507.8	8.0
150°-160°	427.1	6.8
160°-170°	284.1	4.5
170°-180°	99.5	1.6
0°-30°	1080.8	17.1
0°-40°	1712.0	27.1
0°-60°	2828.4	44.7
0°-90°	3404.5	53.8
90°-120°	623.9	9.9
90°-150°	2108.6	33.3
90°-180°	2919.0	46.2
0°-180°	6323.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1472	1472	1472	1472	1472	
5°	1470	1465	1452	1462	1461	139
15°	1400	1389	1362	1359	1352	394
25°	1266	1244	1199	1181	1169	583
35°	1094	1057	1002	965	944	684
45°	893	850	783	730	708	688
55°	676	630	558	501	478	605
65°	460	410	339	293	277	454
75°	245	202	150	125	117	258
85°	61	39	35	33	33	69
90°	2	11	18	23	24	6
95°	49	56	62	64	64	54
105°	190	191	194	196	198	201
115°	355	355	353	352	352	350
125°	517	517	516	514	513	460
135°	666	671	671	670	667	515
145°	810	813	814	813	810	507
155°	928	928	927	930	927	427
165°	1010	1008	1006	1010	1008	285
175°	1051	1047	1046	1051	1046	100
180°	1052	1052	1052	1052	1052	



TEST NUMBER: P332977-930

CATALOG NUMBER: S124RDIP-S1020D1035U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2
2.5°	1475.8	1475.0	1474.1	1473.4	1472.6	1471.0	1468.8	1466.6	1464.4	1462.2	1464.4
5°	1469.9	1468.9	1467.9	1466.9	1465.9	1463.9	1460.9	1457.9	1454.9	1451.9	1454.4
7.5°	1456.6	1455.6	1454.5	1453.4	1452.4	1449.9	1446.0	1442.1	1438.2	1434.3	1435.9
10°	1444.0	1442.8	1441.4	1440.2	1439.0	1436.1	1431.6	1427.1	1422.5	1418.1	1419.0
12.5°	1427.8	1426.3	1424.8	1423.4	1422.0	1418.5	1413.2	1407.9	1402.6	1397.3	1397.9
15°	1400.0	1397.7	1395.5	1393.3	1391.0	1386.7	1380.5	1374.2	1368.0	1361.7	1361.2
17.5°	1366.4	1363.2	1359.9	1356.7	1353.4	1348.0	1340.5	1333.0	1325.5	1317.9	1316.5
20°	1340.3	1337.0	1333.7	1330.5	1327.2	1321.4	1312.9	1304.3	1295.8	1287.3	1285.3
22.5°	1311.4	1307.7	1304.1	1300.5	1296.8	1290.4	1281.3	1272.2	1263.1	1253.9	1250.9
25°	1265.9	1261.3	1256.9	1252.4	1247.8	1240.5	1230.2	1219.9	1209.7	1199.4	1195.1
27.5°	1218.1	1212.4	1206.8	1201.1	1195.5	1187.2	1176.2	1165.2	1154.2	1143.2	1138.0
30°	1184.7	1178.4	1172.2	1166.0	1159.7	1150.6	1138.9	1127.1	1115.3	1103.6	1097.3
32.5°	1149.6	1142.5	1135.4	1128.4	1121.3	1111.7	1099.5	1087.4	1075.1	1063.0	1055.7
35°	1094.5	1086.5	1078.5	1070.5	1062.5	1052.2	1039.7	1027.2	1014.6	1002.1	993.6
37.5°	1035.7	1027.4	1019.2	1010.9	1002.7	991.6	977.7	963.8	949.9	936.0	926.5
40°	994.3	985.9	977.7	969.4	961.2	949.9	935.6	921.3	907.0	892.8	882.2
42.5°	954.6	945.9	937.2	928.5	919.9	908.1	893.2	878.3	863.5	848.6	837.9
45°	892.8	883.5	874.2	865.0	855.7	843.5	828.5	813.5	798.4	783.4	771.2
47.5°	829.0	819.4	809.8	800.3	790.7	778.1	762.5	746.8	731.2	715.6	702.9
50°	785.7	775.9	766.1	756.4	746.6	733.7	717.7	701.6	685.6	669.6	657.0
52.5°	741.5	731.9	722.4	712.8	703.2	690.2	673.8	657.4	640.9	624.5	611.8
55°	676.4	666.3	656.3	646.3	636.3	623.1	606.8	590.5	574.3	558.0	544.9
57.5°	611.9	601.4	591.0	580.6	570.2	556.9	541.0	524.9	508.8	492.8	479.6
60°	565.9	555.9	545.8	535.8	525.8	512.7	496.8	480.7	464.6	448.7	435.6
62.5°	524.4	514.0	503.5	493.1	482.7	469.3	452.8	436.4	420.0	403.6	391.5
65°	459.9	449.1	438.4	427.6	416.9	403.4	387.4	371.4	355.3	339.3	328.6
67.5°	393.0	382.6	372.3	362.0	351.6	339.1	324.2	309.3	294.4	279.6	270.3
70°	350.6	340.1	329.5	319.0	308.5	296.1	281.8	267.5	253.2	239.0	230.7
72.5°	305.5	296.0	286.4	277.0	267.4	255.9	242.5	228.9	215.5	202.0	194.9
75°	244.6	235.4	226.1	216.8	207.6	197.0	185.2	173.5	161.7	149.9	144.1
77.5°	182.9	175.0	167.1	159.2	151.4	142.7	133.1	123.7	114.1	104.6	101.3
80°	143.2	135.9	128.7	121.4	114.1	106.7	99.2	91.7	84.1	76.6	75.9
82.5°	108.9	102.2	95.6	88.9	82.3	76.7	72.5	68.2	63.8	59.5	58.9
85°	60.9	55.8	50.9	45.8	40.8	37.9	37.2	36.4	35.7	35.0	34.4
87.5°	21.2	20.1	18.8	17.6	16.4	15.8	15.9	16.1	16.1	16.2	16.2
90°	2.4	4.4	6.4	8.4	10.4	12.1	13.5	15.0	16.5	17.9	19.0
92.5°	17.4	19.7	21.9	24.2	26.5	28.2	29.2	30.2	31.2	32.2	32.9
95°	48.8	50.5	52.1	53.7	55.4	56.7	58.0	59.4	60.6	61.9	62.4
97.5°	85.3	86.6	87.9	89.2	90.5	91.9	93.4	94.8	96.4	97.8	98.5
100°	113.9	114.6	115.4	116.1	116.8	118.0	119.6	121.2	122.9	124.5	124.9
102.5°	143.9	144.1	144.5	144.7	145.0	145.9	147.4	148.9	150.3	151.9	152.4
105°	189.6	189.8	190.0	190.1	190.4	190.8	191.5	192.2	193.0	193.7	194.2
107.5°	237.7	237.8	238.1	238.3	238.5	238.6	238.8	238.9	239.0	239.1	239.6
110°	270.2	270.5	270.9	271.3	271.7	271.7	271.5	271.3	271.2	271.0	270.6



TEST NUMBER: P332977-930

CATALOG NUMBER: S124RDIP-S1020D1035U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	304.0	304.1	304.2	304.3	304.4	304.2	303.9	303.5	303.2	302.9	302.8
115°	354.8	354.8	354.8	354.8	354.8	354.7	354.2	353.9	353.5	353.2	353.0
117.5°	402.7	402.8	402.9	403.1	403.2	403.2	402.9	402.7	402.4	402.2	401.5
120°	434.6	435.3	436.0	436.8	437.5	437.6	437.0	436.4	435.9	435.4	434.5
122.5°	467.7	468.1	468.3	468.6	468.9	469.0	468.7	468.4	468.1	467.9	467.3
125°	516.7	516.7	516.7	516.7	516.7	516.7	516.5	516.3	516.1	515.9	515.6
127.5°	561.2	561.7	562.2	562.8	563.4	563.5	563.2	562.9	562.6	562.3	562.0
130°	592.4	593.0	593.5	594.0	594.6	594.8	594.8	594.8	594.8	594.8	594.5
132.5°	624.4	624.8	625.1	625.5	625.9	626.1	625.9	625.7	625.6	625.5	625.1
135°	666.5	667.6	668.6	669.8	670.8	671.4	671.4	671.4	671.4	671.4	671.0
137.5°	712.4	712.9	713.4	713.9	714.4	714.8	715.1	715.4	715.7	716.0	715.5
140°	743.0	743.3	743.7	744.0	744.4	744.6	744.6	744.6	744.6	744.6	744.4
142.5°	770.9	771.4	771.7	772.1	772.4	772.5	772.4	772.3	772.1	771.9	771.9
145°	809.7	810.4	811.1	811.9	812.6	813.0	813.3	813.4	813.6	813.8	813.6
147.5°	848.2	849.0	849.9	850.8	851.6	852.0	851.8	851.7	851.5	851.4	851.3
150°	871.6	872.3	873.0	873.8	874.5	874.8	874.8	874.8	874.8	874.8	874.8
152.5°	893.7	894.1	894.5	895.0	895.4	895.7	895.9	896.0	896.2	896.3	896.7
155°	927.7	927.7	927.7	927.7	927.7	927.6	927.4	927.2	927.1	926.9	927.6
157.5°	956.3	956.0	955.7	955.4	955.0	954.9	954.8	954.8	954.8	954.7	955.3
160°	973.3	973.1	972.9	972.7	972.6	972.4	972.2	972.0	971.8	971.7	972.2
162.5°	988.9	988.5	988.0	987.5	987.0	986.7	986.5	986.3	986.2	985.9	986.9
165°	1009.9	1009.3	1008.9	1008.3	1007.7	1007.3	1006.9	1006.6	1006.2	1005.8	1006.9
167.5°	1026.1	1025.2	1024.5	1023.8	1023.0	1022.6	1022.6	1022.7	1022.7	1022.8	1023.9
170°	1035.1	1034.2	1033.3	1032.4	1031.5	1031.1	1031.4	1031.5	1031.7	1031.8	1033.0
172.5°	1041.6	1040.9	1040.2	1039.3	1038.6	1038.2	1038.3	1038.3	1038.4	1038.4	1039.6
175°	1050.6	1049.7	1048.8	1047.9	1047.0	1046.4	1046.3	1046.0	1045.9	1045.7	1047.0
177.5°	1053.5	1052.8	1052.1	1051.3	1050.6	1050.3	1050.3	1050.3	1050.3	1050.3	1051.2
180°	1052.2	1052.2	1052.2	1052.2	1052.2	1052.2	1052.2	1052.2	1052.2	1052.2	1052.2



TEST NUMBER: P332977-930

CATALOG NUMBER: S124RDIP-S1020D1035U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2
2.5°	1466.6	1468.8	1471.0	1472.1	1471.9	1471.7	1471.5	1471.3
5°	1456.9	1459.4	1461.9	1462.9	1462.4	1461.9	1461.4	1460.9
7.5°	1437.5	1439.1	1440.7	1441.1	1440.3	1439.5	1438.7	1437.9
10°	1420.1	1421.1	1422.0	1422.0	1421.1	1420.1	1419.0	1418.1
12.5°	1398.5	1399.1	1399.7	1399.3	1397.9	1396.5	1395.1	1393.8
15°	1360.7	1360.2	1359.7	1358.5	1356.8	1355.0	1353.3	1351.5
17.5°	1315.2	1313.8	1312.4	1310.3	1307.7	1305.0	1302.4	1299.7
20°	1283.3	1281.3	1279.3	1276.7	1273.4	1270.2	1266.9	1263.6
22.5°	1247.9	1244.9	1241.9	1239.1	1236.4	1233.8	1231.1	1228.5
25°	1190.8	1186.6	1182.3	1178.9	1176.5	1173.9	1171.4	1169.0
27.5°	1132.7	1127.5	1122.2	1117.8	1114.2	1110.5	1106.9	1103.3
30°	1091.0	1084.8	1078.5	1073.3	1069.3	1065.4	1061.4	1057.4
32.5°	1048.5	1041.2	1034.0	1028.4	1024.6	1020.8	1017.0	1013.2
35°	985.0	976.6	968.0	961.6	957.0	952.5	948.0	943.5
37.5°	917.0	907.5	898.0	891.0	886.5	881.9	877.4	872.9
40°	871.7	861.2	850.7	843.2	838.7	834.1	829.6	825.2
42.5°	827.1	816.4	805.7	798.0	793.3	788.6	783.8	779.2
45°	758.9	746.6	734.3	725.9	721.5	716.9	712.4	707.9
47.5°	690.2	677.4	664.6	655.8	650.9	645.9	640.9	636.0
50°	644.5	632.0	619.5	610.8	606.1	601.3	596.6	591.8
52.5°	599.0	586.3	573.6	564.8	559.8	554.8	549.8	544.9
55°	531.9	518.9	505.9	497.0	492.2	487.5	482.7	477.9
57.5°	466.4	453.1	439.9	431.5	427.9	424.3	420.7	417.1
60°	422.6	409.5	396.6	388.0	384.0	380.0	376.0	372.0
62.5°	379.5	367.5	355.5	347.8	344.6	341.4	338.2	335.0
65°	317.7	307.0	296.2	289.3	286.3	283.3	280.3	277.3
67.5°	261.0	251.8	242.5	236.2	232.8	229.6	226.2	223.0
70°	222.4	214.2	205.9	200.5	198.0	195.5	193.0	190.5
72.5°	187.8	180.8	173.7	169.1	166.7	164.4	162.2	159.9
75°	138.4	132.6	126.9	123.3	121.7	120.3	118.7	117.2
77.5°	97.9	94.6	91.2	89.3	88.8	88.4	87.9	87.5
80°	75.2	74.4	73.6	73.1	72.9	72.6	72.4	72.2
82.5°	58.4	57.9	57.3	56.9	56.7	56.4	56.2	55.9
85°	33.9	33.4	32.9	32.7	32.7	32.7	32.7	32.7
87.5°	16.2	16.2	16.3	16.4	16.7	17.0	17.2	17.5
90°	20.1	21.2	22.3	23.0	23.3	23.7	24.1	24.4
92.5°	33.5	34.2	34.8	35.3	35.5	35.7	36.0	36.1
95°	62.9	63.5	64.0	64.3	64.3	64.3	64.3	64.3
97.5°	99.1	99.8	100.4	100.8	100.8	100.8	100.8	100.8
100°	125.2	125.6	126.0	126.1	126.1	126.1	126.1	126.1
102.5°	152.9	153.4	153.8	154.2	154.3	154.5	154.7	154.7
105°	194.8	195.3	195.8	196.4	196.9	197.5	198.0	198.5
107.5°	240.1	240.6	241.1	241.3	241.3	241.2	241.2	241.2
110°	270.3	269.9	269.5	269.6	270.2	270.7	271.3	271.8



TEST NUMBER: P332977-930

CATALOG NUMBER: S124RDIP-S1020D1035U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	302.7	302.6	302.6	302.6	302.7	302.8	303.0	303.0
115°	352.8	352.6	352.5	352.3	352.1	351.9	351.7	351.6
117.5°	401.0	400.3	399.7	399.3	398.8	398.5	398.1	397.8
120°	433.6	432.7	431.8	431.5	431.9	432.2	432.6	432.9
122.5°	466.7	466.1	465.5	464.8	464.1	463.5	462.8	462.2
125°	515.2	514.9	514.5	514.1	513.8	513.4	513.1	512.7
127.5°	561.6	561.3	560.8	560.5	560.3	559.9	559.7	559.4
130°	594.2	593.8	593.5	592.9	592.2	591.4	590.7	590.0
132.5°	624.8	624.4	624.0	623.7	623.4	623.1	622.8	622.6
135°	670.7	670.3	669.9	669.4	669.0	668.4	667.8	667.3
137.5°	715.0	714.5	714.1	713.9	714.0	714.1	714.2	714.4
140°	744.3	744.0	743.9	743.7	743.6	743.3	743.1	743.0
142.5°	771.8	771.8	771.8	771.8	771.8	771.7	771.7	771.6
145°	813.4	813.3	813.0	812.7	812.1	811.6	811.1	810.5
147.5°	851.1	850.9	850.8	850.6	850.4	850.3	850.1	849.9
150°	874.8	874.8	874.8	874.7	874.6	874.3	874.2	874.0
152.5°	897.2	897.6	898.1	898.1	897.6	897.1	896.6	896.1
155°	928.4	929.0	929.8	929.8	929.0	928.4	927.6	926.9
157.5°	955.8	956.3	956.9	956.8	956.3	955.6	955.0	954.4
160°	972.7	973.3	973.8	973.6	972.7	971.8	970.9	970.0
162.5°	987.9	988.9	989.9	989.9	989.0	988.1	987.2	986.3
165°	1008.0	1009.1	1010.2	1010.3	1009.7	1008.9	1008.2	1007.5
167.5°	1024.9	1026.1	1027.1	1027.1	1026.0	1024.8	1023.7	1022.6
170°	1034.0	1035.1	1036.2	1036.1	1034.9	1033.6	1032.3	1031.0
172.5°	1040.8	1042.0	1043.3	1043.3	1042.0	1040.7	1039.5	1038.2
175°	1048.2	1049.5	1050.8	1050.8	1049.5	1048.2	1047.0	1045.7
177.5°	1052.3	1053.3	1054.3	1054.3	1053.1	1051.9	1050.8	1049.6
180°	1052.2	1052.2	1052.2	1052.2	1052.2	1052.2	1052.2	1052.2

(END OF REPORT)