

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332983-930

Luminaire Tested: **S124RDIP-S1020D1205U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332983-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIP-S1020D1205U930-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1205 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6802.9 lumens
Efficiency: N/A
Efficacy: 104.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 65.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332983-930

CATALOG NUMBER: S124RDIP-S1020D1205U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332983-930

CATALOG NUMBER: S124RDIP-S1020D1205U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50				
1	98	94	90	87	90	87	84	81	73	71	69	61	60	58	50	49	48	43				
2	90	82	76	71	82	76	71	67	65	61	58	54	51	49	44	42	41	36				
3	82	73	65	60	75	67	61	56	57	53	49	48	45	42	40	37	35	31				
4	75	64	57	51	69	60	53	48	51	46	42	43	39	36	35	33	30	27				
5	69	57	49	43	63	53	46	41	46	40	36	39	35	31	32	29	27	23				
6	64	52	44	38	58	48	41	36	41	36	32	35	31	28	29	26	24	21				
7	59	47	39	33	54	43	36	31	38	32	28	32	28	24	27	23	21	18				
8	55	42	35	29	50	40	33	28	34	29	25	29	25	22	25	21	19	17				
9	51	39	31	26	47	36	30	25	31	26	22	27	23	20	23	19	17	15				
10	48	36	28	24	44	33	27	22	29	24	20	25	21	18	21	18	16	14				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11885	11885	11885
5°	11912	11766	11839
10°	11837	11625	11625
15°	11701	11381	11295
20°	11515	11059	10856
25°	11276	10684	10413
30°	11044	10288	9857
35°	10787	9876	9298
40°	10478	9409	8696
45°	10193	8944	8082
50°	9868	8410	7433
55°	9520	7854	6726
60°	9137	7245	6006
65°	8785	6481	5297
70°	8275	5641	4497
75°	7629	4676	3656
80°	6657	3561	3357
85°	5641	3242	3029



TEST NUMBER: P332983-930

CATALOG NUMBER: S124RDIP-S1020D1205U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.3	2.0
10°-20°	385.6	5.7
20°-30°	556.9	8.2
30°-40°	631.2	9.3
40°-50°	609.5	9.0
50°-60°	506.9	7.5
60°-70°	350.0	5.1
70°-80°	177.4	2.6
80°-90°	49.2	0.7
90°-100°	80.8	1.2
100°-110°	239.3	3.5
110°-120°	406.2	6.0
120°-130°	535.6	7.9
130°-140°	601.5	8.8
140°-150°	591.0	8.7
150°-160°	497.1	7.3
160°-170°	330.7	4.9
170°-180°	115.8	1.7
0°-30°	1080.8	15.9
0°-40°	1712.0	25.2
0°-60°	2828.4	41.6
0°-90°	3405.0	50.1
90°-120°	726.2	10.7
90°-150°	2454.3	36.1
90°-180°	3398.0	49.9
0°-180°	6802.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1472	1472	1472	1472	1472	
5°	1470	1465	1452	1462	1461	139
15°	1400	1389	1362	1359	1352	394
25°	1266	1244	1199	1181	1169	583
35°	1094	1057	1002	965	944	684
45°	893	850	783	730	708	688
55°	676	630	558	501	478	605
65°	460	410	339	293	277	454
75°	245	202	150	125	117	258
85°	61	39	35	33	33	69
90°	3	13	21	26	28	6
95°	57	65	72	75	75	63
105°	221	222	225	228	231	234
115°	413	413	411	410	409	407
125°	601	601	600	599	597	536
135°	776	781	782	780	777	600
145°	942	946	947	946	944	590
155°	1080	1080	1079	1082	1079	497
165°	1176	1173	1171	1176	1173	331
175°	1223	1218	1217	1223	1217	116
180°	1225	1225	1225	1225	1225	



TEST NUMBER: P332983-930

CATALOG NUMBER: S124RDIP-S1020D1205U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2
2.5°	1475.8	1475.0	1474.1	1473.4	1472.6	1471.0	1468.8	1466.6	1464.4	1462.2	1464.4
5°	1469.9	1468.9	1467.9	1466.9	1465.9	1463.9	1460.9	1457.9	1454.9	1451.9	1454.4
7.5°	1456.6	1455.6	1454.5	1453.4	1452.4	1449.9	1446.0	1442.1	1438.2	1434.3	1435.9
10°	1444.0	1442.8	1441.4	1440.2	1439.0	1436.1	1431.6	1427.1	1422.5	1418.1	1419.0
12.5°	1427.8	1426.3	1424.8	1423.4	1422.0	1418.5	1413.2	1407.9	1402.6	1397.3	1397.9
15°	1400.0	1397.7	1395.5	1393.3	1391.0	1386.7	1380.5	1374.2	1368.0	1361.7	1361.2
17.5°	1366.4	1363.2	1359.9	1356.7	1353.4	1348.0	1340.5	1333.0	1325.5	1317.9	1316.5
20°	1340.3	1337.0	1333.7	1330.5	1327.2	1321.4	1312.9	1304.3	1295.8	1287.3	1285.3
22.5°	1311.4	1307.7	1304.1	1300.5	1296.8	1290.4	1281.3	1272.2	1263.1	1253.9	1250.9
25°	1265.9	1261.3	1256.9	1252.4	1247.8	1240.5	1230.2	1219.9	1209.7	1199.4	1195.1
27.5°	1218.1	1212.4	1206.8	1201.1	1195.5	1187.2	1176.2	1165.2	1154.2	1143.2	1138.0
30°	1184.7	1178.4	1172.2	1166.0	1159.7	1150.6	1138.9	1127.1	1115.3	1103.6	1097.3
32.5°	1149.6	1142.5	1135.4	1128.4	1121.3	1111.7	1099.5	1087.4	1075.1	1063.0	1055.7
35°	1094.5	1086.5	1078.5	1070.5	1062.5	1052.2	1039.7	1027.2	1014.6	1002.1	993.6
37.5°	1035.7	1027.4	1019.2	1010.9	1002.7	991.6	977.7	963.8	949.9	936.0	926.5
40°	994.3	985.9	977.7	969.4	961.2	949.9	935.6	921.3	907.0	892.8	882.2
42.5°	954.6	945.9	937.2	928.5	919.9	908.1	893.2	878.3	863.5	848.6	837.9
45°	892.8	883.5	874.2	865.0	855.7	843.5	828.5	813.5	798.4	783.4	771.2
47.5°	829.0	819.4	809.8	800.3	790.7	778.1	762.5	746.8	731.2	715.6	702.9
50°	785.7	775.9	766.1	756.4	746.6	733.7	717.7	701.6	685.6	669.6	657.0
52.5°	741.5	731.9	722.4	712.8	703.2	690.2	673.8	657.4	640.9	624.5	611.8
55°	676.4	666.3	656.3	646.3	636.3	623.1	606.8	590.5	574.3	558.0	544.9
57.5°	611.9	601.4	591.0	580.6	570.2	556.9	541.0	524.9	508.8	492.8	479.6
60°	565.9	555.9	545.8	535.8	525.8	512.7	496.8	480.7	464.6	448.7	435.6
62.5°	524.4	514.0	503.5	493.1	482.7	469.3	452.8	436.4	420.0	403.6	391.5
65°	459.9	449.1	438.4	427.6	416.9	403.4	387.4	371.4	355.3	339.3	328.6
67.5°	393.0	382.6	372.3	362.0	351.6	339.1	324.2	309.3	294.4	279.6	270.3
70°	350.6	340.1	329.5	319.0	308.5	296.1	281.8	267.5	253.2	239.0	230.7
72.5°	305.5	296.0	286.4	277.0	267.4	255.9	242.5	228.9	215.5	202.0	194.9
75°	244.6	235.4	226.1	216.8	207.6	197.0	185.2	173.5	161.7	149.9	144.1
77.5°	182.9	175.0	167.1	159.2	151.4	142.7	133.1	123.7	114.1	104.6	101.3
80°	143.2	135.9	128.7	121.4	114.1	106.7	99.2	91.7	84.1	76.6	75.9
82.5°	108.9	102.2	95.6	88.9	82.3	76.7	72.5	68.2	63.8	59.5	58.9
85°	60.9	55.8	50.9	45.8	40.8	37.9	37.2	36.4	35.7	35.0	34.4
87.5°	21.3	20.1	19.0	17.9	16.7	16.2	16.4	16.6	16.6	16.8	16.9
90°	2.9	5.1	7.5	9.8	12.1	14.1	15.8	17.4	19.2	20.9	22.1
92.5°	20.3	22.9	25.6	28.2	30.9	32.8	34.0	35.1	36.4	37.5	38.2
95°	56.8	58.7	60.7	62.5	64.4	66.1	67.6	69.1	70.5	72.0	72.6
97.5°	99.3	100.8	102.3	103.8	105.3	107.0	108.7	110.4	112.1	113.8	114.6
100°	132.6	133.5	134.3	135.1	136.0	137.4	139.3	141.1	143.0	145.0	145.4
102.5°	167.5	167.8	168.1	168.4	168.8	169.8	171.5	173.3	175.0	176.8	177.3
105°	220.7	220.9	221.1	221.4	221.5	222.1	222.9	223.7	224.6	225.4	226.1
107.5°	276.5	276.9	277.1	277.4	277.6	277.8	277.9	278.0	278.2	278.3	278.9
110°	314.5	314.9	315.3	315.8	316.2	316.3	316.1	315.8	315.6	315.4	315.0



TEST NUMBER: P332983-930

CATALOG NUMBER: S124RDIP-S1020D1205U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	353.8	354.0	354.1	354.2	354.2	354.1	353.7	353.4	352.9	352.5	352.5
115°	412.9	412.9	412.9	412.9	412.9	412.8	412.4	412.0	411.5	411.1	410.9
117.5°	468.7	468.9	469.0	469.2	469.4	469.3	469.0	468.7	468.4	468.1	467.4
120°	505.8	506.6	507.5	508.3	509.2	509.3	508.7	508.0	507.4	506.8	505.7
122.5°	544.5	544.8	545.1	545.4	545.8	545.8	545.5	545.3	544.9	544.6	544.0
125°	601.4	601.4	601.4	601.4	601.4	601.4	601.2	601.0	600.7	600.5	600.1
127.5°	653.2	653.9	654.4	655.1	655.7	655.9	655.5	655.2	654.8	654.5	654.1
130°	689.6	690.2	690.8	691.5	692.1	692.4	692.4	692.4	692.4	692.4	692.0
132.5°	726.7	727.2	727.7	728.1	728.6	728.7	728.6	728.4	728.2	728.1	727.6
135°	775.8	777.1	778.3	779.6	780.8	781.5	781.5	781.5	781.5	781.5	781.1
137.5°	829.2	829.8	830.4	831.0	831.5	832.0	832.3	832.7	833.0	833.3	832.8
140°	864.8	865.2	865.7	866.1	866.5	866.7	866.7	866.7	866.7	866.7	866.5
142.5°	897.4	897.8	898.2	898.6	899.1	899.2	899.0	898.9	898.7	898.5	898.5
145°	942.5	943.3	944.2	945.0	945.8	946.4	946.6	946.8	947.0	947.2	947.0
147.5°	987.2	988.2	989.2	990.2	991.2	991.6	991.5	991.3	991.2	991.0	990.8
150°	1014.5	1015.3	1016.2	1017.0	1017.8	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2
152.5°	1040.2	1040.7	1041.2	1041.7	1042.3	1042.6	1042.8	1042.9	1043.1	1043.3	1043.7
155°	1079.8	1079.8	1079.8	1079.8	1079.8	1079.7	1079.5	1079.3	1079.0	1078.9	1079.7
157.5°	1113.1	1112.8	1112.4	1112.1	1111.7	1111.4	1111.4	1111.3	1111.3	1111.3	1111.9
160°	1132.9	1132.7	1132.5	1132.2	1132.0	1131.8	1131.6	1131.4	1131.1	1131.0	1131.6
162.5°	1151.0	1150.5	1150.0	1149.4	1148.8	1148.5	1148.3	1148.1	1147.9	1147.6	1148.8
165°	1175.5	1174.8	1174.2	1173.6	1173.0	1172.4	1172.0	1171.6	1171.2	1170.8	1172.0
167.5°	1194.3	1193.4	1192.5	1191.6	1190.7	1190.3	1190.3	1190.3	1190.4	1190.4	1191.7
170°	1204.8	1203.8	1202.7	1201.7	1200.6	1200.2	1200.4	1200.6	1200.9	1201.1	1202.3
172.5°	1212.4	1211.5	1210.6	1209.7	1208.9	1208.4	1208.5	1208.6	1208.6	1208.7	1210.1
175°	1222.9	1221.8	1220.7	1219.7	1218.6	1218.0	1217.8	1217.6	1217.4	1217.2	1218.6
177.5°	1226.3	1225.4	1224.6	1223.8	1222.9	1222.5	1222.5	1222.5	1222.5	1222.5	1223.7
180°	1224.7	1224.7	1224.7	1224.7	1224.7	1224.7	1224.7	1224.7	1224.7	1224.7	1224.7



TEST NUMBER: P332983-930

CATALOG NUMBER: S124RDIP-S1020D1205U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2
2.5°	1466.6	1468.8	1471.0	1472.1	1471.9	1471.7	1471.5	1471.3
5°	1456.9	1459.4	1461.9	1462.9	1462.4	1461.9	1461.4	1460.9
7.5°	1437.5	1439.1	1440.7	1441.1	1440.3	1439.5	1438.7	1437.9
10°	1420.1	1421.1	1422.0	1422.0	1421.1	1420.1	1419.0	1418.1
12.5°	1398.5	1399.1	1399.7	1399.3	1397.9	1396.5	1395.1	1393.8
15°	1360.7	1360.2	1359.7	1358.5	1356.8	1355.0	1353.3	1351.5
17.5°	1315.2	1313.8	1312.4	1310.3	1307.7	1305.0	1302.4	1299.7
20°	1283.3	1281.3	1279.3	1276.7	1273.4	1270.2	1266.9	1263.6
22.5°	1247.9	1244.9	1241.9	1239.1	1236.4	1233.8	1231.1	1228.5
25°	1190.8	1186.6	1182.3	1178.9	1176.5	1173.9	1171.4	1169.0
27.5°	1132.7	1127.5	1122.2	1117.8	1114.2	1110.5	1106.9	1103.3
30°	1091.0	1084.8	1078.5	1073.3	1069.3	1065.4	1061.4	1057.4
32.5°	1048.5	1041.2	1034.0	1028.4	1024.6	1020.8	1017.0	1013.2
35°	985.0	976.6	968.0	961.6	957.0	952.5	948.0	943.5
37.5°	917.0	907.5	898.0	891.0	886.5	881.9	877.4	872.9
40°	871.7	861.2	850.7	843.2	838.7	834.1	829.6	825.2
42.5°	827.1	816.4	805.7	798.0	793.3	788.6	783.8	779.2
45°	758.9	746.6	734.3	725.9	721.5	716.9	712.4	707.9
47.5°	690.2	677.4	664.6	655.8	650.9	645.9	640.9	636.0
50°	644.5	632.0	619.5	610.8	606.1	601.3	596.6	591.8
52.5°	599.0	586.3	573.6	564.8	559.8	554.8	549.8	544.9
55°	531.9	518.9	505.9	497.0	492.2	487.5	482.7	477.9
57.5°	466.4	453.1	439.9	431.5	427.9	424.3	420.7	417.1
60°	422.6	409.5	396.6	388.0	384.0	380.0	376.0	372.0
62.5°	379.5	367.5	355.5	347.8	344.6	341.4	338.2	335.0
65°	317.7	307.0	296.2	289.3	286.3	283.3	280.3	277.3
67.5°	261.0	251.8	242.5	236.2	232.8	229.6	226.2	223.0
70°	222.4	214.2	205.9	200.5	198.0	195.5	193.0	190.5
72.5°	187.8	180.8	173.7	169.1	166.7	164.4	162.2	159.9
75°	138.4	132.6	126.9	123.3	121.7	120.3	118.7	117.2
77.5°	97.9	94.6	91.2	89.3	88.8	88.4	87.9	87.5
80°	75.2	74.4	73.6	73.1	72.9	72.6	72.4	72.2
82.5°	58.4	57.9	57.3	56.9	56.7	56.4	56.2	55.9
85°	33.9	33.4	32.9	32.7	32.7	32.7	32.7	32.7
87.5°	16.9	17.0	17.0	17.2	17.4	17.8	18.0	18.3
90°	23.4	24.6	25.9	26.7	27.1	27.6	28.0	28.5
92.5°	39.1	39.8	40.5	41.0	41.3	41.6	41.8	42.1
95°	73.2	73.9	74.5	74.8	74.8	74.8	74.8	74.8
97.5°	115.4	116.1	116.9	117.2	117.2	117.2	117.2	117.2
100°	145.8	146.2	146.6	146.8	146.8	146.8	146.8	146.8
102.5°	177.9	178.6	179.1	179.4	179.7	179.9	180.0	180.2
105°	226.7	227.3	228.0	228.6	229.3	229.8	230.5	231.1
107.5°	279.5	280.1	280.6	281.0	280.9	280.9	280.8	280.8
110°	314.5	314.1	313.7	313.8	314.5	315.1	315.8	316.3



TEST NUMBER: P332983-930

CATALOG NUMBER: S124RDIP-S1020D1205U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	352.4	352.3	352.2	352.2	352.4	352.5	352.6	352.8
115°	410.7	410.4	410.3	410.0	409.9	409.6	409.4	409.2
117.5°	466.7	465.9	465.2	464.7	464.2	463.8	463.4	463.0
120°	504.7	503.6	502.6	502.2	502.6	503.0	503.5	503.9
122.5°	543.2	542.5	541.8	541.0	540.3	539.6	538.7	538.0
125°	599.7	599.2	598.8	598.4	598.0	597.6	597.1	596.7
127.5°	653.7	653.3	652.8	652.5	652.2	651.8	651.4	651.1
130°	691.5	691.1	690.7	690.1	689.3	688.4	687.5	686.7
132.5°	727.2	726.8	726.4	725.9	725.6	725.3	725.0	724.6
135°	780.6	780.2	779.8	779.3	778.6	778.0	777.3	776.7
137.5°	832.3	831.7	831.2	831.0	831.1	831.2	831.4	831.4
140°	866.3	866.1	865.8	865.7	865.4	865.2	865.0	864.8
142.5°	898.5	898.4	898.4	898.3	898.3	898.2	898.2	898.1
145°	946.8	946.6	946.4	945.9	945.3	944.7	944.0	943.5
147.5°	990.7	990.5	990.3	990.1	989.9	989.7	989.4	989.3
150°	1018.2	1018.2	1018.2	1018.1	1017.9	1017.7	1017.5	1017.3
152.5°	1044.2	1044.8	1045.3	1045.3	1044.7	1044.2	1043.6	1043.1
155°	1080.6	1081.4	1082.2	1082.2	1081.4	1080.6	1079.7	1078.9
157.5°	1112.6	1113.1	1113.8	1113.8	1113.0	1112.3	1111.6	1110.9
160°	1132.2	1132.9	1133.5	1133.3	1132.2	1131.1	1130.2	1129.1
162.5°	1149.9	1151.0	1152.2	1152.3	1151.2	1150.1	1149.1	1148.0
165°	1173.3	1174.5	1175.8	1176.0	1175.2	1174.4	1173.5	1172.6
167.5°	1192.9	1194.3	1195.5	1195.5	1194.2	1192.9	1191.6	1190.3
170°	1203.6	1204.8	1206.2	1206.0	1204.5	1203.1	1201.6	1200.1
172.5°	1211.5	1212.9	1214.4	1214.4	1212.8	1211.4	1209.9	1208.4
175°	1220.1	1221.6	1223.0	1223.0	1221.6	1220.1	1218.6	1217.2
177.5°	1224.8	1226.0	1227.2	1227.1	1225.7	1224.4	1223.0	1221.7
180°	1224.7	1224.7	1224.7	1224.7	1224.7	1224.7	1224.7	1224.7

(END OF REPORT)