

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332959-930

Luminaire Tested: **S124RDIP-S1020D365U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332959-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIP-S1020D365U930-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4435.9 lumens
Efficiency: N/A
Efficacy: 102.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 43.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332959-930

CATALOG NUMBER: S124RDIP-S1020D365U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332959-930

CATALOG NUMBER: S124RDIP-S1020D365U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	114	114	114	114	108	108	108	108	98	98	98	89	89	89	81	81	81	77				77
1	104	100	96	92	99	95	92	89	87	84	82	79	77	75	72	70	69	65				65
2	95	88	81	76	91	84	78	74	77	72	68	70	67	63	64	61	59	55				55
3	87	78	70	64	83	74	67	62	68	63	58	62	58	54	57	53	50	47				47
4	80	69	61	55	76	66	59	53	61	55	50	56	51	47	51	47	44	41				41
5	74	62	53	47	70	59	52	46	55	48	43	50	45	41	46	42	38	36				36
6	68	56	47	41	65	54	46	40	50	43	38	46	40	36	42	38	34	32				32
7	63	51	42	37	60	49	41	36	45	39	34	42	36	32	39	34	30	28				28
8	59	46	38	33	56	45	37	32	41	35	30	38	33	29	36	31	27	25				25
9	55	42	35	29	52	41	34	29	38	32	27	35	30	26	33	28	25	23				23
10	52	39	32	27	49	38	31	26	35	29	25	33	28	24	31	26	23	21				21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11885	11885	11885
5°	11912	11766	11839
10°	11837	11625	11625
15°	11701	11381	11295
20°	11515	11059	10856
25°	11276	10684	10413
30°	11044	10288	9857
35°	10787	9876	9298
40°	10478	9409	8696
45°	10193	8944	8082
50°	9868	8410	7433
55°	9520	7854	6726
60°	9137	7245	6006
65°	8785	6481	5297
70°	8275	5641	4497
75°	7629	4676	3656
80°	6657	3561	3357
85°	5641	3242	3029



TEST NUMBER: P332959-930

CATALOG NUMBER: S124RDIP-S1020D365U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.3	3.1
10°-20°	385.6	8.7
20°-30°	556.9	12.6
30°-40°	631.2	14.2
40°-50°	609.5	13.7
50°-60°	506.9	11.4
60°-70°	350.0	7.9
70°-80°	177.4	4.0
80°-90°	46.6	1.1
90°-100°	24.6	0.6
100°-110°	72.8	1.6
110°-120°	123.5	2.8
120°-130°	162.9	3.7
130°-140°	182.9	4.1
140°-150°	179.8	4.1
150°-160°	151.2	3.4
160°-170°	100.6	2.3
170°-180°	35.2	0.8
0°-30°	1080.8	24.4
0°-40°	1712.0	38.6
0°-60°	2828.4	63.8
0°-90°	3402.4	76.7
90°-120°	220.9	5.0
90°-150°	746.5	16.8
90°-180°	1034.0	23.3
0°-180°	4435.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1472	1472	1472	1472	1472	
5°	1470	1465	1452	1462	1461	139
15°	1400	1389	1362	1359	1352	394
25°	1266	1244	1199	1181	1169	583
35°	1094	1057	1002	965	944	684
45°	893	850	783	730	708	688
55°	676	630	558	501	478	605
65°	460	410	339	293	277	454
75°	245	202	150	125	117	258
85°	61	39	35	33	33	68
90°	1	4	6	8	9	4
95°	17	20	22	23	23	19
105°	67	67	69	69	70	71
115°	126	126	125	125	124	124
125°	183	183	183	182	182	163
135°	236	238	238	237	236	182
145°	287	288	288	288	287	179
155°	328	328	328	329	328	151
165°	358	357	356	358	357	101
175°	372	371	370	372	370	35
180°	372	372	372	372	372	



TEST NUMBER: P332959-930

CATALOG NUMBER: S124RDIP-S1020D365U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2
2.5°	1475.8	1475.0	1474.1	1473.4	1472.6	1471.0	1468.8	1466.6	1464.4	1462.2	1464.4
5°	1469.9	1468.9	1467.9	1466.9	1465.9	1463.9	1460.9	1457.9	1454.9	1451.9	1454.4
7.5°	1456.6	1455.6	1454.5	1453.4	1452.4	1449.9	1446.0	1442.1	1438.2	1434.3	1435.9
10°	1444.0	1442.8	1441.4	1440.2	1439.0	1436.1	1431.6	1427.1	1422.5	1418.1	1419.0
12.5°	1427.8	1426.3	1424.8	1423.4	1422.0	1418.5	1413.2	1407.9	1402.6	1397.3	1397.9
15°	1400.0	1397.7	1395.5	1393.3	1391.0	1386.7	1380.5	1374.2	1368.0	1361.7	1361.2
17.5°	1366.4	1363.2	1359.9	1356.7	1353.4	1348.0	1340.5	1333.0	1325.5	1317.9	1316.5
20°	1340.3	1337.0	1333.7	1330.5	1327.2	1321.4	1312.9	1304.3	1295.8	1287.3	1285.3
22.5°	1311.4	1307.7	1304.1	1300.5	1296.8	1290.4	1281.3	1272.2	1263.1	1253.9	1250.9
25°	1265.9	1261.3	1256.9	1252.4	1247.8	1240.5	1230.2	1219.9	1209.7	1199.4	1195.1
27.5°	1218.1	1212.4	1206.8	1201.1	1195.5	1187.2	1176.2	1165.2	1154.2	1143.2	1138.0
30°	1184.7	1178.4	1172.2	1166.0	1159.7	1150.6	1138.9	1127.1	1115.3	1103.6	1097.3
32.5°	1149.6	1142.5	1135.4	1128.4	1121.3	1111.7	1099.5	1087.4	1075.1	1063.0	1055.7
35°	1094.5	1086.5	1078.5	1070.5	1062.5	1052.2	1039.7	1027.2	1014.6	1002.1	993.6
37.5°	1035.7	1027.4	1019.2	1010.9	1002.7	991.6	977.7	963.8	949.9	936.0	926.5
40°	994.3	985.9	977.7	969.4	961.2	949.9	935.6	921.3	907.0	892.8	882.2
42.5°	954.6	945.9	937.2	928.5	919.9	908.1	893.2	878.3	863.5	848.6	837.9
45°	892.8	883.5	874.2	865.0	855.7	843.5	828.5	813.5	798.4	783.4	771.2
47.5°	829.0	819.4	809.8	800.3	790.7	778.1	762.5	746.8	731.2	715.6	702.9
50°	785.7	775.9	766.1	756.4	746.6	733.7	717.7	701.6	685.6	669.6	657.0
52.5°	741.5	731.9	722.4	712.8	703.2	690.2	673.8	657.4	640.9	624.5	611.8
55°	676.4	666.3	656.3	646.3	636.3	623.1	606.8	590.5	574.3	558.0	544.9
57.5°	611.9	601.4	591.0	580.6	570.2	556.9	541.0	524.9	508.8	492.8	479.6
60°	565.9	555.9	545.8	535.8	525.8	512.7	496.8	480.7	464.6	448.7	435.6
62.5°	524.4	514.0	503.5	493.1	482.7	469.3	452.8	436.4	420.0	403.6	391.5
65°	459.9	449.1	438.4	427.6	416.9	403.4	387.4	371.4	355.3	339.3	328.6
67.5°	393.0	382.6	372.3	362.0	351.6	339.1	324.2	309.3	294.4	279.6	270.3
70°	350.6	340.1	329.5	319.0	308.5	296.1	281.8	267.5	253.2	239.0	230.7
72.5°	305.5	296.0	286.4	277.0	267.4	255.9	242.5	228.9	215.5	202.0	194.9
75°	244.6	235.4	226.1	216.8	207.6	197.0	185.2	173.5	161.7	149.9	144.1
77.5°	182.9	175.0	167.1	159.2	151.4	142.7	133.1	123.7	114.1	104.6	101.3
80°	143.2	135.9	128.7	121.4	114.1	106.7	99.2	91.7	84.1	76.6	75.9
82.5°	108.9	102.2	95.6	88.9	82.3	76.7	72.5	68.2	63.8	59.5	58.9
85°	60.9	55.8	50.9	45.8	40.8	37.9	37.2	36.4	35.7	35.0	34.4
87.5°	21.0	19.5	18.0	16.6	15.1	14.3	14.2	14.1	14.0	13.9	13.8
90°	0.9	1.5	2.3	3.0	3.7	4.3	4.8	5.3	5.8	6.4	6.7
92.5°	6.2	7.0	7.7	8.6	9.4	9.9	10.4	10.7	11.1	11.4	11.7
95°	17.3	17.9	18.4	19.0	19.6	20.1	20.5	21.0	21.4	21.9	22.1
97.5°	30.2	30.7	31.1	31.6	32.0	32.5	33.0	33.6	34.1	34.7	34.9
100°	40.4	40.6	40.8	41.1	41.3	41.7	42.3	43.0	43.5	44.1	44.2
102.5°	51.0	51.0	51.1	51.3	51.4	51.7	52.2	52.7	53.2	53.7	54.0
105°	67.1	67.2	67.3	67.3	67.3	67.5	67.8	68.1	68.3	68.6	68.7
107.5°	84.1	84.2	84.3	84.4	84.5	84.5	84.5	84.5	84.6	84.6	84.8
110°	95.6	95.8	95.9	96.0	96.1	96.2	96.1	96.0	96.0	96.0	95.8



TEST NUMBER: P332959-930

CATALOG NUMBER: S124RDIP-S1020D365U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	107.6	107.6	107.7	107.7	107.7	107.7	107.5	107.5	107.4	107.2	107.2
115°	125.6	125.6	125.6	125.6	125.6	125.6	125.4	125.3	125.1	125.1	125.0
117.5°	142.5	142.6	142.7	142.7	142.8	142.8	142.7	142.6	142.4	142.4	142.2
120°	153.8	154.1	154.3	154.6	154.9	154.9	154.7	154.5	154.3	154.2	153.8
122.5°	165.6	165.7	165.8	165.9	166.0	166.0	165.9	165.8	165.8	165.7	165.4
125°	183.0	183.0	183.0	183.0	183.0	182.9	182.9	182.8	182.7	182.6	182.5
127.5°	198.7	198.9	199.1	199.3	199.4	199.5	199.4	199.3	199.2	199.1	198.9
130°	209.8	209.9	210.1	210.3	210.5	210.6	210.6	210.6	210.6	210.6	210.5
132.5°	221.0	221.2	221.3	221.4	221.6	221.6	221.6	221.5	221.5	221.4	221.3
135°	235.9	236.4	236.7	237.1	237.5	237.7	237.7	237.7	237.7	237.7	237.6
137.5°	252.2	252.4	252.6	252.7	252.9	253.1	253.2	253.2	253.4	253.5	253.3
140°	263.0	263.2	263.3	263.4	263.6	263.6	263.6	263.6	263.6	263.6	263.6
142.5°	273.0	273.0	273.2	273.3	273.5	273.5	273.5	273.4	273.4	273.3	273.3
145°	286.7	286.9	287.1	287.4	287.7	287.9	287.9	288.0	288.0	288.1	288.0
147.5°	300.3	300.6	300.8	301.2	301.5	301.6	301.6	301.5	301.5	301.4	301.3
150°	308.6	308.8	309.1	309.3	309.6	309.7	309.7	309.7	309.7	309.7	309.7
152.5°	316.4	316.6	316.7	316.8	317.0	317.1	317.2	317.2	317.2	317.3	317.5
155°	328.4	328.4	328.4	328.4	328.4	328.4	328.3	328.2	328.2	328.2	328.4
157.5°	338.6	338.4	338.3	338.3	338.1	338.0	338.0	338.0	338.0	338.0	338.2
160°	344.5	344.5	344.5	344.4	344.3	344.2	344.2	344.1	344.1	344.0	344.2
162.5°	350.1	349.9	349.8	349.6	349.4	349.4	349.3	349.2	349.1	349.0	349.4
165°	357.5	357.3	357.2	356.9	356.8	356.6	356.4	356.4	356.2	356.1	356.4
167.5°	363.2	363.0	362.7	362.4	362.2	362.0	362.1	362.1	362.1	362.1	362.5
170°	366.5	366.2	365.8	365.5	365.2	365.1	365.1	365.2	365.3	365.3	365.7
172.5°	368.8	368.5	368.2	367.9	367.7	367.5	367.5	367.6	367.6	367.6	368.0
175°	371.9	371.6	371.3	371.0	370.6	370.5	370.4	370.3	370.3	370.2	370.6
177.5°	373.0	372.8	372.4	372.2	371.9	371.9	371.9	371.9	371.9	371.9	372.2
180°	372.5	372.5	372.5	372.5	372.5	372.5	372.5	372.5	372.5	372.5	372.5



TEST NUMBER: P332959-930

CATALOG NUMBER: S124RDIP-S1020D365U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2
2.5°	1466.6	1468.8	1471.0	1472.1	1471.9	1471.7	1471.5	1471.3
5°	1456.9	1459.4	1461.9	1462.9	1462.4	1461.9	1461.4	1460.9
7.5°	1437.5	1439.1	1440.7	1441.1	1440.3	1439.5	1438.7	1437.9
10°	1420.1	1421.1	1422.0	1422.0	1421.1	1420.1	1419.0	1418.1
12.5°	1398.5	1399.1	1399.7	1399.3	1397.9	1396.5	1395.1	1393.8
15°	1360.7	1360.2	1359.7	1358.5	1356.8	1355.0	1353.3	1351.5
17.5°	1315.2	1313.8	1312.4	1310.3	1307.7	1305.0	1302.4	1299.7
20°	1283.3	1281.3	1279.3	1276.7	1273.4	1270.2	1266.9	1263.6
22.5°	1247.9	1244.9	1241.9	1239.1	1236.4	1233.8	1231.1	1228.5
25°	1190.8	1186.6	1182.3	1178.9	1176.5	1173.9	1171.4	1169.0
27.5°	1132.7	1127.5	1122.2	1117.8	1114.2	1110.5	1106.9	1103.3
30°	1091.0	1084.8	1078.5	1073.3	1069.3	1065.4	1061.4	1057.4
32.5°	1048.5	1041.2	1034.0	1028.4	1024.6	1020.8	1017.0	1013.2
35°	985.0	976.6	968.0	961.6	957.0	952.5	948.0	943.5
37.5°	917.0	907.5	898.0	891.0	886.5	881.9	877.4	872.9
40°	871.7	861.2	850.7	843.2	838.7	834.1	829.6	825.2
42.5°	827.1	816.4	805.7	798.0	793.3	788.6	783.8	779.2
45°	758.9	746.6	734.3	725.9	721.5	716.9	712.4	707.9
47.5°	690.2	677.4	664.6	655.8	650.9	645.9	640.9	636.0
50°	644.5	632.0	619.5	610.8	606.1	601.3	596.6	591.8
52.5°	599.0	586.3	573.6	564.8	559.8	554.8	549.8	544.9
55°	531.9	518.9	505.9	497.0	492.2	487.5	482.7	477.9
57.5°	466.4	453.1	439.9	431.5	427.9	424.3	420.7	417.1
60°	422.6	409.5	396.6	388.0	384.0	380.0	376.0	372.0
62.5°	379.5	367.5	355.5	347.8	344.6	341.4	338.2	335.0
65°	317.7	307.0	296.2	289.3	286.3	283.3	280.3	277.3
67.5°	261.0	251.8	242.5	236.2	232.8	229.6	226.2	223.0
70°	222.4	214.2	205.9	200.5	198.0	195.5	193.0	190.5
72.5°	187.8	180.8	173.7	169.1	166.7	164.4	162.2	159.9
75°	138.4	132.6	126.9	123.3	121.7	120.3	118.7	117.2
77.5°	97.9	94.6	91.2	89.3	88.8	88.4	87.9	87.5
80°	75.2	74.4	73.6	73.1	72.9	72.6	72.4	72.2
82.5°	58.4	57.9	57.3	56.9	56.7	56.4	56.2	55.9
85°	33.9	33.4	32.9	32.7	32.7	32.7	32.7	32.7
87.5°	13.6	13.5	13.4	13.5	13.7	13.9	14.1	14.3
90°	7.1	7.5	7.9	8.2	8.2	8.4	8.5	8.6
92.5°	11.9	12.1	12.3	12.5	12.6	12.6	12.7	12.8
95°	22.3	22.5	22.7	22.7	22.7	22.7	22.7	22.7
97.5°	35.1	35.3	35.5	35.6	35.6	35.6	35.6	35.6
100°	44.4	44.4	44.6	44.7	44.7	44.7	44.7	44.7
102.5°	54.1	54.3	54.5	54.6	54.6	54.7	54.7	54.8
105°	69.0	69.1	69.3	69.5	69.7	70.0	70.1	70.3
107.5°	85.0	85.2	85.4	85.4	85.4	85.4	85.4	85.4
110°	95.7	95.6	95.4	95.5	95.6	95.9	96.0	96.2



TEST NUMBER: P332959-930

CATALOG NUMBER: S124RDIP-S1020D365U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	107.2	107.1	107.1	107.1	107.2	107.2	107.2	107.3
115°	124.9	124.8	124.7	124.7	124.7	124.6	124.5	124.5
117.5°	141.9	141.7	141.5	141.4	141.2	141.0	141.0	140.8
120°	153.5	153.2	152.9	152.8	152.9	153.0	153.1	153.3
122.5°	165.3	165.0	164.8	164.5	164.4	164.1	163.9	163.6
125°	182.4	182.3	182.1	182.0	181.9	181.7	181.6	181.5
127.5°	198.9	198.7	198.5	198.4	198.4	198.3	198.1	198.0
130°	210.3	210.2	210.1	209.9	209.6	209.4	209.1	208.9
132.5°	221.2	221.0	220.9	220.8	220.7	220.6	220.5	220.4
135°	237.4	237.3	237.2	237.0	236.8	236.6	236.4	236.3
137.5°	253.2	253.0	252.8	252.7	252.7	252.8	252.8	252.9
140°	263.5	263.4	263.3	263.3	263.3	263.2	263.1	263.0
142.5°	273.3	273.3	273.2	273.2	273.2	273.2	273.2	273.2
145°	288.0	287.9	287.9	287.7	287.6	287.3	287.1	287.0
147.5°	301.3	301.3	301.2	301.2	301.1	301.0	300.9	300.9
150°	309.7	309.7	309.7	309.7	309.7	309.6	309.5	309.4
152.5°	317.6	317.8	318.0	317.9	317.7	317.6	317.4	317.2
155°	328.6	328.9	329.1	329.1	328.9	328.6	328.4	328.2
157.5°	338.3	338.6	338.8	338.8	338.5	338.3	338.1	337.9
160°	344.4	344.5	344.8	344.7	344.4	344.1	343.7	343.4
162.5°	349.8	350.1	350.4	350.4	350.2	349.8	349.5	349.2
165°	356.9	357.3	357.6	357.7	357.4	357.2	356.9	356.7
167.5°	362.9	363.2	363.6	363.6	363.2	362.8	362.4	362.0
170°	366.1	366.5	366.9	366.8	366.4	365.9	365.5	365.0
172.5°	368.5	368.9	369.3	369.3	368.9	368.4	368.0	367.5
175°	371.1	371.5	372.0	372.0	371.5	371.1	370.6	370.2
177.5°	372.5	372.9	373.2	373.2	372.8	372.4	372.0	371.6
180°	372.5	372.5	372.5	372.5	372.5	372.5	372.5	372.5

(END OF REPORT)