

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332995-930

Luminaire Tested: **S124RDIP-S1195D590U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332995-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIP-S1195D590U930-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 590 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5598.2 lumens
Efficiency: N/A
Efficacy: 101.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 55.1
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332995-930

CATALOG NUMBER: S124RDIP-S1195D590U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332995-930

CATALOG NUMBER: S124RDIP-S1195D590U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	95	95	95	84	84	84	75	75	75	70
1	103	98	95	91	97	93	90	87	84	81	79	75	73	71	67	65	64	60
2	94	86	80	75	89	82	77	72	74	69	66	66	63	60	59	57	54	51
3	86	76	69	63	81	73	66	61	65	60	56	59	55	51	53	49	47	43
4	79	68	60	54	74	65	57	52	58	53	48	53	48	44	47	44	41	38
5	73	61	52	46	68	58	50	45	52	46	42	47	42	39	43	39	36	33
6	67	55	46	41	63	52	45	39	48	41	37	43	38	34	39	35	31	29
7	62	50	42	36	59	47	40	35	43	37	32	39	34	30	36	31	28	26
8	58	45	37	32	55	43	36	31	40	33	29	36	31	27	33	29	25	23
9	54	42	34	29	51	40	33	28	36	30	26	33	28	25	30	26	23	21
10	51	38	31	26	48	37	30	25	34	28	24	31	26	22	28	24	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13726	13726	13726
5°	13757	13588	13674
10°	13671	13426	13426
15°	13514	13143	13046
20°	13298	12773	12538
25°	13023	12339	12026
30°	12755	11882	11384
35°	12458	11406	10738
40°	12101	10866	10043
45°	11772	10330	9334
50°	11396	9712	8584
55°	10994	9070	7769
60°	10551	8365	6936
65°	10147	7484	6117
70°	9557	6515	5193
75°	8812	5402	4223
80°	7685	4114	3873
85°	6512	3742	3492



TEST NUMBER: P332995-930

CATALOG NUMBER: S124RDIP-S1195D590U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.7	2.9
10°-20°	445.4	8.0
20°-30°	643.1	11.5
30°-40°	729.0	13.0
40°-50°	704.0	12.6
50°-60°	585.4	10.5
60°-70°	404.2	7.2
70°-80°	204.9	3.7
80°-90°	54.4	1.0
90°-100°	39.7	0.7
100°-110°	117.5	2.1
110°-120°	199.4	3.6
120°-130°	262.9	4.7
130°-140°	295.3	5.3
140°-150°	290.2	5.2
150°-160°	244.0	4.4
160°-170°	162.4	2.9
170°-180°	56.9	1.0
0°-30°	1248.2	22.3
0°-40°	1977.3	35.3
0°-60°	3266.6	58.4
0°-90°	3930.1	70.2
90°-120°	356.5	6.4
90°-150°	1204.9	21.5
90°-180°	1668.0	29.8
0°-180°	5598.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1700	1700	1700	1700	1700	
5°	1698	1692	1677	1689	1687	161
15°	1617	1604	1573	1570	1561	455
25°	1462	1437	1385	1364	1350	673
35°	1264	1221	1157	1114	1090	790
45°	1031	981	905	843	818	795
55°	781	727	644	579	552	698
65°	531	474	392	338	320	524
75°	282	234	173	144	135	298
85°	70	46	40	38	38	79
90°	1	6	10	13	14	5
95°	28	32	35	37	37	31
105°	108	109	111	112	114	115
115°	203	203	202	201	201	200
125°	295	295	295	294	293	263
135°	381	384	384	383	381	295
145°	463	464	465	464	463	289
155°	530	530	530	531	530	244
165°	577	576	575	577	576	163
175°	600	598	598	600	598	57
180°	601	601	601	601	601	



TEST NUMBER: P332995-930

CATALOG NUMBER: S124RDIP-S1195D590U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2
2.5°	1704.4	1703.5	1702.6	1701.6	1700.7	1699.0	1696.5	1693.9	1691.3	1688.8	1691.3
5°	1697.6	1696.5	1695.3	1694.2	1693.1	1690.7	1687.3	1683.8	1680.3	1676.8	1679.7
7.5°	1682.3	1681.1	1679.8	1678.6	1677.4	1674.5	1670.1	1665.6	1661.0	1656.5	1658.4
10°	1667.7	1666.2	1664.8	1663.4	1661.9	1658.6	1653.4	1648.2	1643.0	1637.8	1638.9
12.5°	1648.9	1647.3	1645.6	1643.9	1642.3	1638.3	1632.2	1626.1	1619.9	1613.8	1614.5
15°	1616.9	1614.3	1611.8	1609.2	1606.5	1601.6	1594.4	1587.1	1579.9	1572.6	1572.1
17.5°	1578.2	1574.3	1570.6	1566.8	1563.1	1556.9	1548.2	1539.5	1530.8	1522.2	1520.5
20°	1547.9	1544.2	1540.4	1536.7	1532.9	1526.1	1516.3	1506.4	1496.6	1486.8	1484.4
22.5°	1514.6	1510.4	1506.2	1501.9	1497.7	1490.4	1479.8	1469.3	1458.7	1448.2	1444.7
25°	1462.0	1456.8	1451.6	1446.4	1441.2	1432.6	1420.8	1408.9	1397.1	1385.2	1380.3
27.5°	1406.8	1400.3	1393.8	1387.2	1380.6	1371.1	1358.4	1345.7	1333.0	1320.4	1314.3
30°	1368.3	1361.1	1353.8	1346.5	1339.4	1328.9	1315.3	1301.7	1288.2	1274.6	1267.3
32.5°	1327.6	1319.5	1311.3	1303.2	1295.0	1283.9	1269.8	1255.8	1241.7	1227.7	1219.3
35°	1264.1	1254.8	1245.6	1236.3	1227.1	1215.2	1200.8	1186.3	1171.8	1157.4	1147.5
37.5°	1196.2	1186.6	1177.0	1167.5	1158.0	1145.2	1129.2	1113.1	1097.1	1081.1	1070.1
40°	1148.3	1138.7	1129.2	1119.7	1110.0	1097.1	1080.6	1064.0	1047.6	1031.1	1019.0
42.5°	1102.4	1092.4	1082.4	1072.4	1062.4	1048.8	1031.6	1014.4	997.3	980.1	967.7
45°	1031.1	1020.3	1009.7	999.0	988.3	974.2	956.9	939.6	922.2	904.8	890.6
47.5°	957.4	946.3	935.3	924.2	913.2	898.6	880.6	862.5	844.5	826.5	811.7
50°	907.4	896.1	884.8	873.6	862.3	847.3	828.8	810.3	791.8	773.3	758.9
52.5°	856.4	845.3	834.3	823.2	812.2	797.1	778.2	759.2	740.2	721.2	706.5
55°	781.1	769.6	758.0	746.4	734.8	719.7	700.8	682.1	663.2	644.4	629.4
57.5°	706.6	694.6	682.6	670.6	658.5	643.3	624.8	606.2	587.7	569.2	553.9
60°	653.5	642.0	630.4	618.8	607.2	592.2	573.7	555.2	536.6	518.1	503.1
62.5°	605.6	593.6	581.6	569.6	557.5	542.0	523.0	504.0	485.0	466.1	452.2
65°	531.2	518.7	506.3	493.8	481.4	465.9	447.4	428.9	410.4	391.8	379.4
67.5°	453.8	441.9	430.0	418.1	406.2	391.6	374.4	357.3	340.1	322.9	312.2
70°	404.9	392.7	380.6	368.4	356.3	341.9	325.5	309.0	292.5	276.0	266.4
72.5°	352.8	341.9	330.8	319.8	308.8	295.5	280.0	264.4	248.8	233.3	225.1
75°	282.5	271.8	261.1	250.4	239.7	227.6	213.9	200.3	186.8	173.2	166.5
77.5°	211.2	202.1	193.0	183.9	174.8	164.8	153.8	142.8	131.8	120.8	116.9
80°	165.3	156.9	148.5	140.1	131.8	123.3	114.5	105.9	97.2	88.5	87.6
82.5°	125.8	118.1	110.4	102.6	95.0	88.6	83.6	78.7	73.7	68.7	68.1
85°	70.3	64.5	58.7	52.9	47.1	43.9	43.0	42.1	41.3	40.4	39.8
87.5°	24.2	22.6	21.0	19.3	17.8	16.9	16.8	16.8	16.7	16.6	16.6
90°	1.4	2.5	3.7	4.8	6.0	6.9	7.7	8.6	9.4	10.2	10.8
92.5°	9.9	11.3	12.6	13.9	15.2	16.1	16.7	17.3	17.9	18.4	18.8
95°	27.9	28.9	29.8	30.7	31.6	32.4	33.2	33.9	34.7	35.3	35.6
97.5°	48.8	49.5	50.2	51.0	51.7	52.5	53.3	54.2	55.0	55.9	56.3
100°	65.1	65.6	66.0	66.4	66.8	67.4	68.3	69.3	70.2	71.2	71.3
102.5°	82.2	82.3	82.5	82.7	82.8	83.4	84.2	85.0	85.9	86.7	87.1
105°	108.4	108.4	108.5	108.7	108.8	109.0	109.4	109.8	110.2	110.6	111.0
107.5°	135.7	135.9	136.0	136.2	136.3	136.4	136.4	136.5	136.6	136.6	136.9
110°	154.4	154.6	154.8	155.0	155.2	155.2	155.2	155.1	155.0	154.8	154.7



TEST NUMBER: P332995-930

CATALOG NUMBER: S124RDIP-S1195D590U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	173.7	173.7	173.8	173.8	173.9	173.8	173.7	173.4	173.3	173.1	173.0
115°	202.8	202.8	202.8	202.8	202.8	202.6	202.4	202.2	202.0	201.8	201.7
117.5°	230.1	230.2	230.2	230.3	230.4	230.4	230.2	230.1	229.9	229.8	229.4
120°	248.3	248.7	249.2	249.6	250.0	250.1	249.7	249.4	249.1	248.7	248.3
122.5°	267.3	267.4	267.6	267.7	267.9	268.0	267.8	267.7	267.5	267.4	267.0
125°	295.3	295.3	295.3	295.3	295.3	295.2	295.1	295.1	294.9	294.8	294.6
127.5°	320.7	321.0	321.3	321.6	321.9	322.0	321.8	321.6	321.5	321.3	321.1
130°	338.5	338.8	339.2	339.5	339.7	339.9	339.9	339.9	339.9	339.9	339.7
132.5°	356.8	357.0	357.2	357.4	357.7	357.8	357.7	357.6	357.5	357.4	357.2
135°	380.8	381.5	382.0	382.7	383.4	383.6	383.6	383.6	383.6	383.6	383.4
137.5°	407.1	407.3	407.6	407.9	408.2	408.5	408.6	408.8	409.0	409.1	408.9
140°	424.5	424.8	424.9	425.2	425.3	425.5	425.5	425.5	425.5	425.5	425.3
142.5°	440.5	440.8	441.0	441.2	441.4	441.4	441.3	441.2	441.2	441.1	441.1
145°	462.7	463.1	463.5	463.9	464.3	464.6	464.7	464.8	464.9	465.0	464.9
147.5°	484.6	485.1	485.6	486.1	486.7	486.8	486.7	486.7	486.6	486.5	486.4
150°	498.0	498.5	498.9	499.3	499.7	499.9	499.9	499.9	499.9	499.9	499.9
152.5°	510.7	510.9	511.2	511.4	511.7	511.8	511.9	512.0	512.1	512.2	512.4
155°	530.1	530.1	530.1	530.1	530.1	530.0	529.9	529.9	529.8	529.6	530.0
157.5°	546.5	546.3	546.1	545.9	545.8	545.6	545.6	545.6	545.6	545.5	545.8
160°	556.1	556.0	556.0	555.9	555.7	555.6	555.5	555.5	555.3	555.2	555.5
162.5°	565.1	564.8	564.5	564.3	564.0	563.8	563.7	563.6	563.5	563.4	563.9
165°	577.1	576.7	576.4	576.2	575.8	575.6	575.4	575.2	574.9	574.8	575.4
167.5°	586.3	585.9	585.4	585.0	584.6	584.3	584.3	584.4	584.4	584.4	585.1
170°	591.5	591.0	590.4	590.0	589.4	589.2	589.3	589.4	589.5	589.6	590.3
172.5°	595.2	594.8	594.4	593.9	593.5	593.3	593.3	593.3	593.3	593.4	594.0
175°	600.3	599.8	599.3	598.8	598.3	597.9	597.9	597.8	597.6	597.5	598.3
177.5°	602.0	601.6	601.2	600.8	600.3	600.1	600.1	600.1	600.1	600.1	600.7
180°	601.3	601.3	601.3	601.3	601.3	601.3	601.3	601.3	601.3	601.3	601.3



TEST NUMBER: P332995-930

CATALOG NUMBER: S124RDIP-S1195D590U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2
2.5°	1693.9	1696.5	1699.0	1700.1	1699.9	1699.7	1699.4	1699.2
5°	1682.6	1685.5	1688.4	1689.5	1689.0	1688.4	1687.8	1687.3
7.5°	1660.2	1662.1	1663.9	1664.4	1663.5	1662.6	1661.6	1660.7
10°	1640.1	1641.2	1642.4	1642.4	1641.2	1640.1	1638.9	1637.8
12.5°	1615.2	1615.9	1616.6	1616.1	1614.5	1612.9	1611.3	1609.6
15°	1571.5	1570.9	1570.3	1569.0	1567.0	1565.0	1563.0	1561.0
17.5°	1518.9	1517.3	1515.6	1513.4	1510.3	1507.2	1504.1	1501.0
20°	1482.1	1479.8	1477.5	1474.5	1470.7	1467.0	1463.1	1459.4
22.5°	1441.3	1437.8	1434.4	1431.1	1428.0	1424.9	1421.9	1418.8
25°	1375.3	1370.4	1365.5	1361.6	1358.7	1355.8	1352.9	1350.1
27.5°	1308.2	1302.1	1296.1	1290.9	1286.8	1282.6	1278.5	1274.3
30°	1260.0	1252.9	1245.6	1239.7	1235.0	1230.4	1225.8	1221.2
32.5°	1210.9	1202.5	1194.1	1187.7	1183.3	1178.9	1174.5	1170.1
35°	1137.7	1127.9	1118.0	1110.5	1105.3	1100.1	1094.9	1089.6
37.5°	1059.1	1048.1	1037.1	1029.0	1023.8	1018.6	1013.4	1008.2
40°	1006.8	994.7	982.5	973.8	968.6	963.4	958.2	953.0
42.5°	955.3	942.9	930.5	921.6	916.2	910.8	905.3	899.8
45°	876.4	862.3	848.1	838.4	833.2	828.0	822.8	817.6
47.5°	797.0	782.4	767.7	757.4	751.7	746.0	740.2	734.5
50°	744.4	729.9	715.4	705.5	700.0	694.5	689.0	683.5
52.5°	691.9	677.2	662.4	652.2	646.5	640.8	635.0	629.3
55°	614.3	599.3	584.2	574.0	568.5	563.0	557.5	552.0
57.5°	538.7	523.3	508.1	498.4	494.2	490.0	485.8	481.7
60°	488.0	473.0	458.0	448.2	443.5	438.9	434.2	429.6
62.5°	438.3	424.4	410.5	401.7	398.0	394.4	390.6	386.9
65°	367.0	354.6	342.1	334.1	330.7	327.2	323.8	320.2
67.5°	301.5	290.7	280.1	272.8	269.0	265.1	261.3	257.5
70°	256.9	247.4	237.8	231.6	228.7	225.8	222.9	220.0
72.5°	217.0	208.8	200.6	195.3	192.6	190.0	187.3	184.6
75°	159.9	153.2	146.5	142.4	140.6	138.8	137.1	135.4
77.5°	113.1	109.2	105.3	103.1	102.6	102.1	101.6	101.0
80°	86.8	85.9	85.0	84.5	84.2	83.9	83.6	83.3
82.5°	67.5	66.9	66.2	65.7	65.5	65.1	64.9	64.6
85°	39.2	38.6	38.1	37.7	37.7	37.7	37.7	37.7
87.5°	16.4	16.3	16.2	16.3	16.6	16.8	17.1	17.4
90°	11.5	12.1	12.7	13.1	13.4	13.5	13.8	13.9
92.5°	19.2	19.6	19.9	20.1	20.3	20.4	20.5	20.6
95°	36.0	36.3	36.6	36.8	36.8	36.8	36.8	36.8
97.5°	56.7	57.0	57.4	57.6	57.6	57.6	57.6	57.6
100°	71.6	71.7	72.0	72.1	72.1	72.1	72.1	72.1
102.5°	87.3	87.6	87.9	88.1	88.2	88.3	88.4	88.5
105°	111.3	111.6	111.9	112.2	112.5	112.8	113.2	113.5
107.5°	137.2	137.5	137.8	137.9	137.9	137.9	137.9	137.9
110°	154.4	154.3	154.0	154.1	154.4	154.7	155.0	155.3



TEST NUMBER: P332995-930

CATALOG NUMBER: S124RDIP-S1195D590U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	173.0	172.9	172.9	172.9	173.0	173.0	173.1	173.2
115°	201.6	201.5	201.4	201.3	201.2	201.1	201.0	200.9
117.5°	229.1	228.8	228.4	228.1	227.9	227.7	227.5	227.3
120°	247.8	247.2	246.7	246.5	246.8	247.0	247.2	247.4
122.5°	266.7	266.4	266.0	265.6	265.2	264.9	264.5	264.2
125°	294.4	294.2	294.0	293.8	293.6	293.3	293.2	292.9
127.5°	320.9	320.7	320.5	320.3	320.2	320.0	319.8	319.7
130°	339.5	339.3	339.1	338.8	338.3	337.9	337.5	337.1
132.5°	357.0	356.8	356.6	356.4	356.2	356.0	355.9	355.7
135°	383.2	383.0	382.8	382.5	382.2	381.9	381.6	381.3
137.5°	408.5	408.3	408.1	407.9	408.0	408.1	408.1	408.2
140°	425.3	425.2	425.1	424.9	424.9	424.8	424.7	424.5
142.5°	441.1	441.1	441.0	441.0	441.0	441.0	440.9	440.9
145°	464.8	464.7	464.6	464.4	464.1	463.7	463.4	463.2
147.5°	486.3	486.2	486.2	486.1	486.0	485.8	485.8	485.7
150°	499.9	499.9	499.9	499.9	499.7	499.6	499.5	499.5
152.5°	512.7	512.9	513.1	513.1	512.9	512.6	512.3	512.1
155°	530.4	530.8	531.3	531.3	530.8	530.4	530.0	529.6
157.5°	546.2	546.5	546.8	546.7	546.4	546.1	545.7	545.4
160°	555.9	556.1	556.4	556.4	555.9	555.3	554.8	554.3
162.5°	564.5	565.1	565.7	565.7	565.2	564.6	564.1	563.6
165°	576.0	576.6	577.2	577.3	576.9	576.5	576.1	575.7
167.5°	585.6	586.3	586.9	586.9	586.3	585.6	585.0	584.3
170°	590.8	591.5	592.1	592.1	591.3	590.6	589.9	589.1
172.5°	594.8	595.5	596.1	596.1	595.4	594.7	593.9	593.3
175°	599.0	599.7	600.4	600.4	599.7	599.0	598.3	597.5
177.5°	601.3	601.9	602.4	602.4	601.8	601.1	600.4	599.7
180°	601.3	601.3	601.3	601.3	601.3	601.3	601.3	601.3

(END OF REPORT)