

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333000-930

Luminaire Tested: **S124RDIP-S1195D810U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333000-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIP-S1195D810U930-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 810 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6567.2 lumens
Efficiency: N/A
Efficacy: 108.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 60.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333000-930

CATALOG NUMBER: S124RDIP-S1195D810U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333000-930

CATALOG NUMBER: S124RDIP-S1195D810U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	89	89	89	76	76	76	65	65	65	60
1	100	96	92	89	94	90	87	84	78	76	74	68	66	64	58	57	56	51
2	92	84	78	73	85	79	74	69	69	65	62	60	57	54	52	49	47	43
3	84	74	67	61	78	70	63	58	61	56	52	53	49	46	46	43	41	37
4	77	66	58	52	72	62	55	50	55	49	45	48	43	40	41	38	35	32
5	71	59	51	45	66	56	48	43	49	43	39	43	38	35	37	34	31	28
6	65	53	45	39	61	50	43	37	44	38	34	39	34	31	34	30	27	25
7	60	48	40	35	56	45	38	33	40	34	30	36	31	27	31	27	24	22
8	56	44	36	31	52	41	34	29	37	31	27	33	28	24	29	25	22	20
9	52	40	33	27	49	38	31	26	34	28	24	30	25	22	26	23	20	18
10	49	37	30	25	46	35	28	24	31	26	22	28	23	20	25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13726	13726	13726
5°	13757	13588	13674
10°	13671	13426	13426
15°	13514	13143	13046
20°	13298	12773	12538
25°	13023	12339	12026
30°	12755	11882	11384
35°	12458	11406	10738
40°	12101	10866	10043
45°	11772	10330	9334
50°	11396	9712	8584
55°	10994	9070	7769
60°	10551	8365	6936
65°	10147	7484	6117
70°	9557	6515	5193
75°	8812	5402	4223
80°	7685	4114	3873
85°	6512	3742	3492



TEST NUMBER: P333000-930

CATALOG NUMBER: S124RDIP-S1195D810U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.7	2.4
10°-20°	445.4	6.8
20°-30°	643.1	9.8
30°-40°	729.0	11.1
40°-50°	704.0	10.7
50°-60°	585.4	8.9
60°-70°	404.2	6.2
70°-80°	204.9	3.1
80°-90°	55.0	0.8
90°-100°	29.1	0.4
100°-110°	185.9	2.8
110°-120°	355.6	5.4
120°-130°	451.4	6.9
130°-140°	482.9	7.4
140°-150°	451.6	6.9
150°-160°	364.2	5.5
160°-170°	234.9	3.6
170°-180°	81.0	1.2
0°-30°	1248.2	19.0
0°-40°	1977.3	30.1
0°-60°	3266.6	49.7
0°-90°	3930.8	59.9
90°-120°	570.6	8.7
90°-150°	1956.4	29.8
90°-180°	2636.0	40.1
0°-180°	6567.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1700	1700	1700	1700	1700	
5°	1698	1692	1677	1689	1687	161
15°	1617	1604	1573	1570	1561	455
25°	1462	1437	1385	1364	1350	673
35°	1264	1221	1157	1114	1090	790
45°	1031	981	905	843	818	795
55°	781	727	644	579	552	698
65°	531	474	392	338	320	524
75°	282	234	173	144	135	298
85°	70	46	40	38	38	79
90°	2	9	14	18	19	5
95°	35	15	14	18	18	45
105°	192	196	199	203	182	201
115°	358	360	360	361	361	352
125°	504	506	505	507	507	449
135°	625	624	627	628	629	481
145°	720	722	722	723	724	450
155°	790	790	789	791	789	364
165°	833	830	830	834	829	235
175°	852	849	849	854	847	81
180°	852	852	852	852	852	



TEST NUMBER: P333000-930

CATALOG NUMBER: S124RDIP-S1195D810U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2
2.5°	1704.4	1703.5	1702.6	1701.6	1700.7	1699.0	1696.5	1693.9	1691.3	1688.8	1691.3
5°	1697.6	1696.5	1695.3	1694.2	1693.1	1690.7	1687.3	1683.8	1680.3	1676.8	1679.7
7.5°	1682.3	1681.1	1679.8	1678.6	1677.4	1674.5	1670.1	1665.6	1661.0	1656.5	1658.4
10°	1667.7	1666.2	1664.8	1663.4	1661.9	1658.6	1653.4	1648.2	1643.0	1637.8	1638.9
12.5°	1648.9	1647.3	1645.6	1643.9	1642.3	1638.3	1632.2	1626.1	1619.9	1613.8	1614.5
15°	1616.9	1614.3	1611.8	1609.2	1606.5	1601.6	1594.4	1587.1	1579.9	1572.6	1572.1
17.5°	1578.2	1574.3	1570.6	1566.8	1563.1	1556.9	1548.2	1539.5	1530.8	1522.2	1520.5
20°	1547.9	1544.2	1540.4	1536.7	1532.9	1526.1	1516.3	1506.4	1496.6	1486.8	1484.4
22.5°	1514.6	1510.4	1506.2	1501.9	1497.7	1490.4	1479.8	1469.3	1458.7	1448.2	1444.7
25°	1462.0	1456.8	1451.6	1446.4	1441.2	1432.6	1420.8	1408.9	1397.1	1385.2	1380.3
27.5°	1406.8	1400.3	1393.8	1387.2	1380.6	1371.1	1358.4	1345.7	1333.0	1320.4	1314.3
30°	1368.3	1361.1	1353.8	1346.5	1339.4	1328.9	1315.3	1301.7	1288.2	1274.6	1267.3
32.5°	1327.6	1319.5	1311.3	1303.2	1295.0	1283.9	1269.8	1255.8	1241.7	1227.7	1219.3
35°	1264.1	1254.8	1245.6	1236.3	1227.1	1215.2	1200.8	1186.3	1171.8	1157.4	1147.5
37.5°	1196.2	1186.6	1177.0	1167.5	1158.0	1145.2	1129.2	1113.1	1097.1	1081.1	1070.1
40°	1148.3	1138.7	1129.2	1119.7	1110.0	1097.1	1080.6	1064.0	1047.6	1031.1	1019.0
42.5°	1102.4	1092.4	1082.4	1072.4	1062.4	1048.8	1031.6	1014.4	997.3	980.1	967.7
45°	1031.1	1020.3	1009.7	999.0	988.3	974.2	956.9	939.6	922.2	904.8	890.6
47.5°	957.4	946.3	935.3	924.2	913.2	898.6	880.6	862.5	844.5	826.5	811.7
50°	907.4	896.1	884.8	873.6	862.3	847.3	828.8	810.3	791.8	773.3	758.9
52.5°	856.4	845.3	834.3	823.2	812.2	797.1	778.2	759.2	740.2	721.2	706.5
55°	781.1	769.6	758.0	746.4	734.8	719.7	700.8	682.1	663.2	644.4	629.4
57.5°	706.6	694.6	682.6	670.6	658.5	643.3	624.8	606.2	587.7	569.2	553.9
60°	653.5	642.0	630.4	618.8	607.2	592.2	573.7	555.2	536.6	518.1	503.1
62.5°	605.6	593.6	581.6	569.6	557.5	542.0	523.0	504.0	485.0	466.1	452.2
65°	531.2	518.7	506.3	493.8	481.4	465.9	447.4	428.9	410.4	391.8	379.4
67.5°	453.8	441.9	430.0	418.1	406.2	391.6	374.4	357.3	340.1	322.9	312.2
70°	404.9	392.7	380.6	368.4	356.3	341.9	325.5	309.0	292.5	276.0	266.4
72.5°	352.8	341.9	330.8	319.8	308.8	295.5	280.0	264.4	248.8	233.3	225.1
75°	282.5	271.8	261.1	250.4	239.7	227.6	213.9	200.3	186.8	173.2	166.5
77.5°	211.2	202.1	193.0	183.9	174.8	164.8	153.8	142.8	131.8	120.8	116.9
80°	165.3	156.9	148.5	140.1	131.8	123.3	114.5	105.9	97.2	88.5	87.6
82.5°	125.8	118.1	110.4	102.6	95.0	88.6	83.6	78.7	73.7	68.7	68.1
85°	70.3	64.5	58.7	52.9	47.1	43.9	43.0	42.1	41.3	40.4	39.8
87.5°	24.4	22.8	21.3	19.7	18.2	17.4	17.4	17.4	17.4	17.4	17.3
90°	1.9	3.5	5.1	6.6	8.2	9.5	10.6	11.7	12.9	14.0	14.8
92.5°	8.1	8.2	8.2	8.3	8.4	9.0	10.1	11.3	12.4	13.5	14.3
95°	35.1	30.2	25.4	20.6	15.8	13.5	13.6	13.8	13.9	14.0	14.8
97.5°	74.4	77.5	80.5	83.5	86.5	80.1	64.2	48.4	32.6	16.8	16.9
100°	104.5	107.1	109.7	112.2	114.7	106.2	86.7	67.2	47.6	28.0	25.6
102.5°	138.2	140.1	141.9	143.8	145.7	145.4	142.8	140.2	137.7	135.2	109.2
105°	191.8	192.7	193.6	194.4	195.3	196.1	196.7	197.5	198.2	198.9	200.2
107.5°	241.7	242.1	242.6	243.0	243.4	244.1	245.1	246.1	247.0	248.0	248.6
110°	275.4	275.8	276.2	276.6	277.1	277.7	278.6	279.4	280.3	281.1	281.4



TEST NUMBER: P333000-930

CATALOG NUMBER: S124RDIP-S1195D810U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	308.0	308.8	309.6	310.3	311.1	311.7	312.1	312.4	312.8	313.2	313.2
115°	358.2	358.7	359.1	359.5	360.0	360.1	360.0	359.8	359.7	359.5	359.8
117.5°	403.5	404.1	404.6	405.2	405.8	406.3	406.5	406.8	407.2	407.5	407.4
120°	434.1	434.7	435.3	435.9	436.3	436.6	436.4	436.3	436.2	436.0	436.3
122.5°	462.7	463.0	463.3	463.7	464.1	464.3	464.5	464.7	464.9	465.1	465.3
125°	503.6	504.2	504.8	505.3	505.9	506.0	505.7	505.5	505.2	504.9	505.3
127.5°	542.3	542.5	542.7	542.8	542.9	543.3	544.0	544.6	545.3	545.9	545.8
130°	567.4	567.5	567.6	567.8	567.9	568.2	568.6	569.1	569.5	569.9	570.1
132.5°	590.3	590.5	590.8	591.1	591.3	591.7	592.2	592.8	593.3	593.9	594.0
135°	624.8	624.6	624.4	624.3	624.2	624.4	624.9	625.5	626.1	626.6	626.9
137.5°	655.2	655.3	655.3	655.3	655.4	655.7	656.4	657.0	657.6	658.3	658.6
140°	675.1	675.4	675.6	676.0	676.2	676.5	676.8	677.1	677.4	677.6	678.1
142.5°	692.9	693.4	694.0	694.5	695.0	695.3	695.5	695.7	695.9	696.0	696.3
145°	720.3	720.8	721.2	721.6	722.0	722.3	722.3	722.3	722.3	722.3	722.4
147.5°	742.2	743.0	743.7	744.5	745.3	745.7	745.5	745.3	745.2	745.1	745.2
150°	758.0	758.6	759.1	759.7	760.2	760.4	760.3	760.2	760.0	759.9	759.9
152.5°	771.2	771.7	772.1	772.6	773.1	773.1	772.9	772.7	772.3	772.1	772.3
155°	789.9	789.9	790.1	790.3	790.4	790.3	789.9	789.4	789.0	788.6	789.1
157.5°	805.5	805.4	805.4	805.3	805.2	804.9	804.4	804.0	803.5	803.0	803.7
160°	814.7	814.2	813.8	813.4	813.0	812.7	812.6	812.4	812.3	812.1	813.0
162.5°	822.9	822.3	821.7	821.3	820.7	820.4	820.2	820.1	819.9	819.8	820.7
165°	833.2	832.5	831.8	831.0	830.4	830.0	830.0	830.0	830.0	830.0	831.1
167.5°	841.3	840.6	839.8	839.1	838.4	838.0	837.9	837.8	837.7	837.6	838.9
170°	846.0	845.1	844.2	843.3	842.5	842.2	842.3	842.4	842.6	842.8	843.8
172.5°	849.0	848.2	847.3	846.4	845.6	845.2	845.4	845.5	845.6	845.8	846.9
175°	852.3	851.4	850.6	849.8	848.9	848.6	848.7	848.8	849.0	849.1	850.4
177.5°	853.9	853.0	852.2	851.4	850.7	850.4	850.6	850.8	851.1	851.3	852.2
180°	852.3	852.3	852.3	852.3	852.3	852.3	852.3	852.3	852.3	852.3	852.3



TEST NUMBER: P333000-930

CATALOG NUMBER: S124RDIP-S1195D810U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2
2.5°	1693.9	1696.5	1699.0	1700.1	1699.9	1699.7	1699.4	1699.2
5°	1682.6	1685.5	1688.4	1689.5	1689.0	1688.4	1687.8	1687.3
7.5°	1660.2	1662.1	1663.9	1664.4	1663.5	1662.6	1661.6	1660.7
10°	1640.1	1641.2	1642.4	1642.4	1641.2	1640.1	1638.9	1637.8
12.5°	1615.2	1615.9	1616.6	1616.1	1614.5	1612.9	1611.3	1609.6
15°	1571.5	1570.9	1570.3	1569.0	1567.0	1565.0	1563.0	1561.0
17.5°	1518.9	1517.3	1515.6	1513.4	1510.3	1507.2	1504.1	1501.0
20°	1482.1	1479.8	1477.5	1474.5	1470.7	1467.0	1463.1	1459.4
22.5°	1441.3	1437.8	1434.4	1431.1	1428.0	1424.9	1421.9	1418.8
25°	1375.3	1370.4	1365.5	1361.6	1358.7	1355.8	1352.9	1350.1
27.5°	1308.2	1302.1	1296.1	1290.9	1286.8	1282.6	1278.5	1274.3
30°	1260.0	1252.9	1245.6	1239.7	1235.0	1230.4	1225.8	1221.2
32.5°	1210.9	1202.5	1194.1	1187.7	1183.3	1178.9	1174.5	1170.1
35°	1137.7	1127.9	1118.0	1110.5	1105.3	1100.1	1094.9	1089.6
37.5°	1059.1	1048.1	1037.1	1029.0	1023.8	1018.6	1013.4	1008.2
40°	1006.8	994.7	982.5	973.8	968.6	963.4	958.2	953.0
42.5°	955.3	942.9	930.5	921.6	916.2	910.8	905.3	899.8
45°	876.4	862.3	848.1	838.4	833.2	828.0	822.8	817.6
47.5°	797.0	782.4	767.7	757.4	751.7	746.0	740.2	734.5
50°	744.4	729.9	715.4	705.5	700.0	694.5	689.0	683.5
52.5°	691.9	677.2	662.4	652.2	646.5	640.8	635.0	629.3
55°	614.3	599.3	584.2	574.0	568.5	563.0	557.5	552.0
57.5°	538.7	523.3	508.1	498.4	494.2	490.0	485.8	481.7
60°	488.0	473.0	458.0	448.2	443.5	438.9	434.2	429.6
62.5°	438.3	424.4	410.5	401.7	398.0	394.4	390.6	386.9
65°	367.0	354.6	342.1	334.1	330.7	327.2	323.8	320.2
67.5°	301.5	290.7	280.1	272.8	269.0	265.1	261.3	257.5
70°	256.9	247.4	237.8	231.6	228.7	225.8	222.9	220.0
72.5°	217.0	208.8	200.6	195.3	192.6	190.0	187.3	184.6
75°	159.9	153.2	146.5	142.4	140.6	138.8	137.1	135.4
77.5°	113.1	109.2	105.3	103.1	102.6	102.1	101.6	101.0
80°	86.8	85.9	85.0	84.5	84.2	83.9	83.6	83.3
82.5°	67.5	66.9	66.2	65.7	65.5	65.1	64.9	64.6
85°	39.2	38.6	38.1	37.7	37.7	37.7	37.7	37.7
87.5°	17.3	17.2	17.1	17.3	17.5	17.9	18.1	18.4
90°	15.7	16.6	17.4	18.0	18.3	18.6	18.8	19.2
92.5°	15.2	16.1	16.9	17.4	17.4	17.4	17.5	17.6
95°	15.7	16.6	17.4	17.9	18.1	18.2	18.3	18.5
97.5°	17.0	17.1	17.2	17.3	17.4	17.5	17.7	17.9
100°	23.2	20.8	18.4	17.3	17.4	17.5	17.7	17.9
102.5°	83.2	57.2	31.2	18.3	18.3	18.3	18.3	18.3
105°	201.5	202.7	204.0	202.1	197.0	191.8	186.8	181.6
107.5°	249.2	249.8	250.5	251.0	251.6	252.1	252.7	253.2
110°	281.7	282.0	282.3	282.6	283.1	283.5	283.9	284.3



TEST NUMBER: P333000-930

CATALOG NUMBER: S124RDIP-S1195D810U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	313.2	313.1	313.0	313.2	313.8	314.4	314.9	315.4
115°	360.1	360.4	360.7	360.9	360.9	360.9	360.9	360.9
117.5°	407.3	407.3	407.2	407.2	407.2	407.1	407.0	407.0
120°	436.6	436.9	437.2	437.2	436.9	436.6	436.3	436.0
122.5°	465.5	465.6	465.8	465.7	465.5	465.1	464.9	464.6
125°	505.7	506.1	506.5	506.9	507.0	507.1	507.3	507.4
127.5°	545.8	545.7	545.6	545.5	545.4	545.3	545.2	545.0
130°	570.2	570.3	570.5	570.5	570.5	570.5	570.5	570.5
132.5°	594.2	594.3	594.4	594.4	594.4	594.2	594.1	594.0
135°	627.2	627.5	627.8	628.0	628.4	628.6	628.9	629.2
137.5°	658.8	659.2	659.5	659.6	659.5	659.4	659.3	659.3
140°	678.5	678.9	679.3	679.6	679.8	679.9	680.0	680.2
142.5°	696.6	696.9	697.2	697.4	697.4	697.5	697.5	697.5
145°	722.5	722.7	722.8	723.0	723.3	723.6	723.9	724.1
147.5°	745.3	745.4	745.5	745.7	745.8	745.9	746.1	746.2
150°	759.9	759.9	759.9	759.9	760.1	760.2	760.3	760.5
152.5°	772.6	772.8	773.0	773.1	773.0	772.9	772.8	772.7
155°	789.7	790.3	790.8	790.9	790.4	790.0	789.6	789.2
157.5°	804.5	805.2	805.9	805.9	805.2	804.5	803.7	803.0
160°	813.8	814.7	815.5	815.5	814.7	813.8	813.0	812.1
162.5°	821.5	822.3	823.2	823.1	822.1	821.2	820.3	819.3
165°	832.3	833.4	834.5	834.5	833.2	831.9	830.6	829.3
167.5°	840.2	841.4	842.6	842.5	841.1	839.7	838.3	836.9
170°	845.0	846.1	847.3	847.1	845.7	844.3	842.9	841.5
172.5°	848.1	849.2	850.4	850.1	848.6	847.1	845.5	844.0
175°	851.7	853.0	854.2	854.0	852.3	850.6	848.9	847.2
177.5°	853.1	854.0	854.9	854.7	853.3	852.0	850.6	849.2
180°	852.3	852.3	852.3	852.3	852.3	852.3	852.3	852.3

(END OF REPORT)