

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332867-930

Luminaire Tested: **S124RDIP-S350D365U930-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332867-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIP-S350D365U930-4F0-1E-UDD-A4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2278.1 lumens
Efficiency: N/A
Efficacy: 112.2 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 20.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332867-930

CATALOG NUMBER: S124RDIP-S350D365U930-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332867-930

CATALOG NUMBER: S124RDIP-S350D365U930-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	53
1	99	95	91	88	92	88	85	82	75	73	71	64	62	61	53	52	51	46
2	91	83	77	72	84	78	72	68	67	63	60	57	54	51	47	45	44	39
3	83	74	67	61	77	69	62	57	59	54	51	50	47	44	42	40	38	34
4	76	66	58	52	70	61	54	49	53	48	43	45	41	38	38	35	33	29
5	70	59	51	45	65	55	48	42	47	42	38	41	37	33	34	31	29	26
6	65	53	45	39	60	49	42	37	43	37	33	37	33	29	31	28	26	23
7	60	48	40	34	55	45	38	33	39	33	29	34	29	26	29	25	23	20
8	56	43	36	31	51	41	34	29	36	30	26	31	27	23	26	23	21	18
9	52	40	32	27	48	37	31	26	33	27	24	28	24	21	24	21	19	17
10	48	36	29	25	45	34	28	23	30	25	21	26	22	19	23	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	3866	3866	3866	3866
5°	4485	3878	3428	3878
10°	5305	3861	3059	3861
15°	6128	3825	2629	3825
20°	6823	3776	2377	3776
25°	7044	3728	2207	3728
30°	6166	3669	2105	3669
35°	4800	3582	2042	3582
40°	3599	3483	2009	3483
45°	2842	3323	1991	3323
50°	2399	3141	1934	3141
55°	2090	2939	1830	2939
60°	1881	2729	1621	2729
65°	1658	2502	1394	2502
70°	1494	2268	1256	2268
75°	1251	2009	1070	2009
80°	1055	1715	1004	1715
85°	889	1343	889	1343



TEST NUMBER: P332867-930

CATALOG NUMBER: S124RDIP-S350D365U930-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.4	2.0
10°-20°	140.0	6.1
20°-30°	218.9	9.6
30°-40°	243.4	10.7
40°-50°	215.9	9.5
50°-60°	168.3	7.4
60°-70°	110.2	4.8
70°-80°	54.2	2.4
80°-90°	14.2	0.6
90°-100°	105.9	4.7
100°-110°	220.5	9.7
110°-120°	197.5	8.7
120°-130°	166.1	7.3
130°-140°	138.5	6.1
140°-150°	105.8	4.6
150°-160°	74.4	3.3
160°-170°	43.7	1.9
170°-180°	14.2	0.6
0°-30°	405.3	17.8
0°-40°	648.7	28.5
0°-60°	1032.9	45.3
0°-90°	1211.4	53.2
90°-120°	523.9	23.0
90°-150°	934.3	41.0
90°-180°	1067.0	46.8
0°-180°	2278.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	479	479	479	479	479	
5°	553	478	423	478	553	56
15°	733	458	314	458	733	208
25°	791	418	248	418	791	351
35°	487	364	207	364	487	305
45°	249	291	174	291	249	197
55°	148	209	130	209	148	135
65°	87	131	73	131	87	87
75°	40	64	34	64	40	44
85°	10	14	10	14	10	11
90°	6	0	6	0	6	5
95°	70	10	70	10	70	109
105°	405	34	405	34	405	401
115°	389	59	389	59	389	386
125°	311	83	311	83	311	282
135°	278	98	278	98	278	214
145°	227	113	227	113	227	144
155°	190	129	190	129	190	89
165°	166	140	166	140	166	47
175°	149	146	149	146	149	15
180°	147	147	147	147	147	



TEST NUMBER: P332867-930

CATALOG NUMBER: S124RDIP-S350D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9
2.5°	505.2	506.5	505.2	505.0	503.4	503.0	502.4	500.3	496.7	494.5	495.0
5°	553.4	558.2	555.5	555.1	550.9	546.7	544.0	537.8	531.2	526.8	523.1
7.5°	609.2	612.0	610.3	607.6	600.7	596.8	590.5	582.4	570.6	561.7	553.4
10°	647.2	649.5	648.7	643.7	638.7	628.4	622.6	611.3	596.4	584.7	573.6
12.5°	684.5	687.0	680.2	680.4	670.9	662.8	653.7	639.4	622.2	607.1	593.3
15°	733.2	730.1	730.1	726.3	715.7	704.5	695.0	680.0	658.4	640.3	621.1
17.5°	771.4	772.4	770.9	761.7	753.4	741.8	724.5	706.9	686.9	662.5	643.0
20°	794.2	794.2	792.5	786.3	775.5	763.1	744.4	725.3	699.9	675.3	653.4
22.5°	803.5	804.0	802.0	797.0	787.3	775.2	759.2	739.8	713.5	686.0	658.8
25°	790.8	794.4	794.8	793.4	790.5	783.2	769.5	749.7	726.1	696.2	666.8
27.5°	725.9	730.6	734.7	741.4	750.2	754.8	755.5	745.3	724.8	696.0	666.5
30°	661.5	665.3	677.8	694.2	706.9	718.5	728.6	731.3	719.7	693.9	662.8
32.5°	589.8	595.1	607.6	625.3	646.5	666.1	688.6	700.1	699.8	684.3	655.6
35°	487.0	490.9	502.5	521.0	546.4	575.6	611.3	639.0	657.9	656.6	639.0
37.5°	392.8	397.1	408.8	424.2	448.9	484.9	519.5	557.8	592.7	612.4	606.5
40°	341.5	341.7	353.1	368.9	392.1	423.5	461.1	503.6	542.6	574.5	580.6
42.5°	301.1	301.1	308.7	325.7	342.3	371.9	407.9	450.0	495.7	532.5	548.8
45°	248.9	250.6	256.8	267.0	280.1	305.2	334.0	373.2	424.3	467.9	495.1
47.5°	210.8	213.4	217.3	225.6	236.0	252.7	276.5	311.8	353.4	401.3	440.0
50°	191.0	191.4	196.4	201.1	210.1	223.5	244.3	273.6	311.9	357.9	401.0
52.5°	174.1	174.0	177.0	182.9	190.2	200.6	217.4	244.1	278.0	319.4	363.8
55°	148.5	149.5	151.9	156.5	162.1	169.4	182.7	202.8	229.4	264.7	305.1
57.5°	129.2	129.7	131.5	133.5	138.6	144.0	153.9	167.9	190.3	219.2	256.8
60°	116.5	116.8	117.3	120.2	124.3	129.3	136.1	147.8	166.7	193.1	222.9
62.5°	104.2	104.5	105.4	107.5	110.7	114.1	121.2	130.7	146.3	168.9	195.7
65°	86.8	87.0	88.4	89.1	91.6	94.7	100.0	106.3	117.2	136.1	156.3
67.5°	72.6	72.6	72.6	73.7	75.4	77.5	80.6	85.7	93.8	105.4	123.3
70°	63.3	63.3	63.7	64.2	65.2	66.9	68.7	72.6	78.5	88.0	101.7
72.5°	54.6	54.8	55.2	55.3	55.8	57.2	58.5	61.0	65.4	72.6	83.6
75°	40.1	40.7	41.7	42.5	43.5	43.2	44.6	46.1	47.5	51.7	58.0
77.5°	29.8	29.6	29.7	30.3	30.4	30.7	31.6	32.8	33.8	35.8	38.1
80°	22.7	22.7	23.3	23.6	23.3	23.6	24.5	25.1	25.4	26.3	28.4
82.5°	17.2	17.5	17.4	17.5	17.6	17.9	18.7	18.8	19.2	19.5	20.3
85°	9.6	9.9	10.0	9.6	9.6	9.6	10.0	10.2	10.6	10.4	10.8
87.5°	4.6	4.5	4.6	4.6	4.7	4.6	4.6	4.9	4.6	4.7	4.6
90°	6.0	6.0	6.4	6.0	5.8	5.8	5.5	5.2	4.9	5.2	4.6
92.5°	22.2	22.2	23.2	24.7	28.1	33.9	42.6	56.6	76.1	91.4	80.0
95°	70.3	74.0	79.2	88.1	102.3	130.2	168.8	213.5	241.5	234.8	177.2
97.5°	187.9	194.0	202.6	219.9	240.6	270.7	298.9	315.4	303.4	247.4	165.8
100°	264.2	266.5	275.2	292.8	317.8	339.2	353.3	347.5	305.4	231.7	150.4
102.5°	330.6	332.5	341.6	354.3	369.7	378.5	374.5	345.9	288.1	212.1	140.1
105°	405.4	407.2	411.2	413.5	412.9	401.1	372.6	322.7	256.7	189.0	131.1
107.5°	433.2	432.4	429.6	423.0	408.8	383.0	342.9	289.8	231.4	176.1	129.5
110°	433.7	431.0	425.9	413.8	393.3	361.7	319.8	270.0	218.7	171.7	130.0



TEST NUMBER: P332867-930

CATALOG NUMBER: S124RDIP-S350D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	420.0	415.9	408.6	394.0	370.7	339.0	299.5	255.4	211.6	169.7	131.3
115°	389.3	387.0	377.7	360.4	337.7	310.1	276.3	240.9	204.9	168.6	134.0
117.5°	358.1	356.3	347.0	332.5	313.1	289.6	263.1	233.7	201.9	168.3	136.8
120°	340.6	337.5	330.0	317.2	300.8	280.4	257.3	230.5	200.2	168.3	138.9
122.5°	326.8	323.6	317.2	306.4	292.5	274.6	253.6	227.7	198.4	168.0	141.0
125°	310.6	308.9	303.5	295.1	283.6	267.7	247.8	223.1	195.3	167.7	144.1
127.5°	301.2	299.5	294.8	287.4	275.8	260.8	240.9	217.3	191.3	167.1	146.6
130°	295.6	293.9	289.3	282.1	270.3	255.0	235.5	212.6	188.7	166.8	148.4
132.5°	289.4	287.7	283.3	275.2	263.6	248.3	229.2	207.8	186.5	166.6	150.0
135°	277.8	276.1	271.4	263.3	251.8	237.4	219.9	201.1	183.0	166.2	152.5
137.5°	263.3	261.3	257.5	249.6	238.7	225.8	210.9	195.1	180.0	166.2	153.8
140°	253.0	250.7	246.6	240.4	230.2	218.1	205.1	191.6	178.4	166.0	155.0
142.5°	241.9	240.4	236.8	230.9	221.9	211.4	200.3	188.4	177.0	166.0	156.0
145°	226.7	225.3	222.4	217.5	210.3	202.3	193.6	183.8	174.6	165.4	156.5
147.5°	213.4	212.8	210.7	206.4	201.1	194.8	187.8	180.1	172.5	164.4	156.8
150°	205.7	205.5	203.7	200.0	195.3	190.2	184.4	177.8	170.9	163.6	156.8
152.5°	198.9	198.5	197.5	194.4	190.5	186.3	181.0	175.3	169.0	162.5	156.3
155°	189.9	189.9	189.0	186.7	183.8	180.3	176.0	171.5	166.2	160.8	155.6
157.5°	182.1	182.1	181.6	179.8	177.7	174.9	171.2	167.4	163.5	159.0	154.8
160°	177.2	177.2	176.9	175.2	173.5	171.1	168.0	164.9	161.3	157.6	154.2
162.5°	172.6	172.8	172.5	170.8	169.6	167.5	165.0	162.3	159.6	156.2	153.4
165°	165.7	166.0	166.2	165.1	164.0	162.5	160.5	158.7	156.5	154.2	152.1
167.5°	160.2	160.5	160.5	159.7	159.1	158.3	156.7	155.4	153.7	152.1	150.7
170°	156.8	156.8	157.0	156.8	156.2	155.3	154.2	153.3	151.9	150.7	149.9
172.5°	153.3	153.8	154.0	153.8	153.4	152.8	152.1	151.5	150.3	149.3	149.0
175°	149.3	149.9	150.4	149.9	149.9	149.9	149.3	149.0	148.4	147.8	147.8
177.5°	146.9	147.3	147.8	147.6	147.8	147.6	147.6	147.3	147.2	146.9	146.9
180°	146.7	146.7	146.7	146.7	146.7	146.7	146.7	146.7	146.7	146.7	146.7



TEST NUMBER: P332867-930

CATALOG NUMBER: S124RDIP-S350D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9
2.5°	493.4	491.3	490.2	487.7	484.8	483.2	481.8	479.8	477.2	474.4	472.5
5°	518.4	513.8	508.0	501.1	495.0	488.9	483.7	478.5	472.5	466.4	460.2
7.5°	544.1	535.1	525.2	513.8	502.8	492.7	483.4	474.6	464.6	455.5	447.4
10°	562.1	549.8	536.1	521.5	507.1	494.6	482.2	471.0	458.7	447.7	438.4
12.5°	576.6	562.1	545.6	527.6	510.1	495.0	480.8	466.2	452.2	440.3	427.9
15°	600.6	580.8	558.6	537.0	514.5	493.7	474.7	457.7	441.6	424.9	413.1
17.5°	617.3	593.6	566.6	540.7	514.0	489.7	467.7	447.4	428.9	411.8	397.8
20°	627.1	601.0	571.1	541.6	511.7	485.7	461.9	439.5	420.4	401.9	387.4
22.5°	632.7	603.8	571.1	540.2	509.2	481.0	455.0	431.7	410.9	392.3	376.3
25°	634.5	603.6	570.2	534.7	500.8	470.8	443.8	418.5	395.3	376.8	359.9
27.5°	631.9	595.6	561.4	525.0	489.9	458.4	430.1	403.5	380.3	360.4	343.0
30°	628.3	589.3	552.6	514.8	479.3	449.0	419.1	393.6	369.5	348.9	331.3
32.5°	620.2	581.6	542.1	503.4	467.4	436.2	407.8	382.2	358.6	337.5	318.8
35°	604.3	565.2	522.4	482.6	447.3	414.8	388.2	363.5	341.0	318.4	298.7
37.5°	583.3	543.4	500.8	457.2	421.8	391.3	366.9	343.6	321.6	301.0	279.2
40°	563.6	527.2	483.1	439.9	403.7	374.1	351.6	330.5	308.3	287.9	266.1
42.5°	539.7	508.7	464.1	420.8	385.0	356.5	335.5	315.0	294.7	274.9	252.2
45°	499.8	476.2	434.6	392.9	356.8	328.6	309.3	291.1	273.5	254.5	233.1
47.5°	454.0	438.1	402.1	359.4	326.0	300.7	282.0	267.2	252.2	233.3	214.5
50°	422.2	412.0	377.2	338.3	306.4	283.1	264.0	250.1	237.5	219.4	202.6
52.5°	388.2	382.8	353.4	316.2	285.4	262.5	246.2	233.7	221.0	205.9	190.3
55°	336.5	339.4	314.5	282.3	253.3	234.1	219.2	208.8	198.0	185.2	173.1
57.5°	283.6	294.2	277.5	249.2	222.1	204.2	193.1	184.3	175.2	164.7	154.3
60°	252.0	260.9	251.4	226.5	202.8	186.2	175.8	169.0	160.0	150.3	142.4
62.5°	221.1	230.6	225.0	204.9	182.9	168.6	159.4	153.1	146.3	137.9	129.7
65°	182.4	188.5	185.8	171.9	156.3	144.1	135.7	131.0	124.8	118.7	111.4
67.5°	139.7	151.6	150.0	142.6	129.1	119.6	114.1	110.0	104.4	99.8	94.8
70°	114.8	125.8	125.6	119.6	112.3	103.5	99.5	96.1	91.1	86.7	82.6
72.5°	94.0	104.0	105.6	100.9	96.0	89.2	85.5	83.2	78.3	75.3	71.9
75°	65.8	73.1	75.1	75.1	72.7	69.3	66.0	64.4	61.0	58.3	56.3
77.5°	43.1	47.8	50.8	51.4	51.9	50.6	47.9	46.9	44.2	43.3	41.4
80°	30.5	33.6	37.0	38.2	39.1	38.8	37.7	36.9	34.3	33.3	32.6
82.5°	21.0	22.7	25.6	28.2	27.9	28.9	27.9	27.3	25.4	25.0	24.3
85°	11.0	11.2	11.6	13.3	14.3	14.7	14.8	14.5	13.9	13.9	12.6
87.5°	4.5	4.3	4.3	4.3	4.4	5.0	5.3	5.3	5.0	4.6	4.2
90°	4.0	4.0	2.3	2.3	2.0	1.7	0.9	0.3	0.9	1.7	2.0
92.5°	58.2	35.9	21.2	15.2	11.0	7.5	4.8	3.3	4.8	7.5	11.0
95°	108.4	61.1	36.0	23.9	17.0	13.3	10.4	9.5	10.4	13.3	17.0
97.5°	97.4	58.4	39.1	28.9	23.0	19.6	17.0	17.0	17.0	19.6	23.0
100°	91.6	59.1	42.1	32.9	27.4	23.9	21.9	21.9	21.9	23.9	27.4
102.5°	90.0	61.4	46.0	37.3	32.0	28.8	27.0	26.5	27.0	28.8	32.0
105°	90.7	66.9	53.0	44.7	39.5	36.0	34.6	33.8	34.6	36.0	39.5
107.5°	95.1	73.2	60.6	52.3	47.4	43.7	42.2	41.7	42.2	43.7	47.4
110°	98.2	78.1	65.4	57.6	52.4	49.0	47.5	47.0	47.5	49.0	52.4



TEST NUMBER: P332867-930

CATALOG NUMBER: S124RDIP-S350D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	101.7	82.7	70.4	62.7	57.5	54.3	52.6	52.0	52.6	54.3	57.5
115°	107.2	89.9	78.4	70.6	65.1	62.2	60.3	59.4	60.3	62.2	65.1
117.5°	112.8	96.9	85.9	77.9	72.7	69.5	67.8	66.9	67.8	69.5	72.7
120°	116.7	101.7	90.7	82.7	77.8	74.6	72.6	72.1	72.6	74.6	77.8
122.5°	120.4	106.3	95.4	87.6	82.2	79.2	77.2	76.6	77.2	79.2	82.2
125°	125.9	112.7	102.3	94.2	88.8	85.6	83.8	82.7	83.8	85.6	88.8
127.5°	130.7	118.5	108.5	100.4	94.7	91.1	88.9	88.1	88.9	91.1	94.7
130°	133.7	122.5	112.7	104.3	98.8	94.5	92.2	91.1	92.2	94.5	98.8
132.5°	136.7	125.7	115.9	108.0	102.1	98.0	95.0	94.1	95.0	98.0	102.1
135°	140.6	130.2	120.7	113.2	107.2	102.3	99.4	98.2	99.4	102.3	107.2
137.5°	143.4	133.7	124.8	117.6	111.4	106.7	103.5	102.5	103.5	106.7	111.4
140°	145.2	136.0	127.3	120.4	114.4	109.5	106.3	105.5	106.3	109.5	114.4
142.5°	146.6	138.1	129.6	122.9	117.2	112.5	109.6	108.7	109.6	112.5	117.2
145°	148.1	140.3	132.8	126.5	121.0	117.0	114.1	113.2	114.1	117.0	121.0
147.5°	149.4	142.6	135.6	129.9	125.3	121.2	118.6	118.4	118.6	121.2	125.3
150°	150.1	143.8	137.5	132.0	127.7	124.2	121.9	121.6	121.9	124.2	127.7
152.5°	150.6	144.7	139.1	134.0	130.2	126.9	124.7	124.6	124.7	126.9	130.2
155°	151.0	146.1	141.2	136.9	133.7	130.9	129.1	128.8	129.1	130.9	133.7
157.5°	151.0	147.1	142.9	139.5	136.7	134.5	132.9	132.9	132.9	134.5	136.7
160°	151.0	147.6	144.1	140.9	138.6	136.6	135.4	135.4	135.4	136.6	138.6
162.5°	151.0	148.0	144.8	142.3	140.2	138.4	137.5	137.7	137.5	138.4	140.2
165°	150.4	148.1	145.5	143.8	142.4	140.9	140.3	140.3	140.3	140.9	142.4
167.5°	149.7	148.1	146.2	144.8	144.0	142.9	142.6	142.9	142.6	142.9	144.0
170°	149.3	147.8	146.3	145.5	145.0	144.1	143.8	144.1	143.8	144.1	145.0
172.5°	148.8	147.6	146.6	145.9	145.6	145.0	145.0	145.2	145.0	145.0	145.6
175°	148.1	147.2	146.7	146.7	146.3	146.1	146.1	146.3	146.1	146.1	146.3
177.5°	147.3	146.9	146.7	146.7	146.7	146.4	146.7	146.9	146.7	146.4	146.7
180°	146.7	146.7	146.7	146.7	146.7	146.7	146.7	146.7	146.7	146.7	146.7



TEST NUMBER: P332867-930

CATALOG NUMBER: S124RDIP-S350D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9
2.5°	470.3	468.7	466.8	464.4	461.6	459.2	458.0	459.0	459.5	458.2	458.0
5°	455.9	451.1	447.3	441.5	436.8	433.0	430.3	429.1	429.5	426.4	425.7
7.5°	439.9	434.1	427.8	420.9	414.6	408.9	405.9	404.3	401.0	399.6	397.2
10°	429.5	421.8	415.6	407.5	400.1	393.5	390.1	387.4	384.2	382.6	379.4
12.5°	418.9	409.9	403.1	394.7	387.2	379.1	375.9	371.0	365.8	362.6	358.3
15°	403.8	393.1	384.7	374.7	365.8	356.6	348.3	339.0	335.6	328.2	324.0
17.5°	386.3	375.4	365.1	351.6	337.9	326.4	317.6	308.7	303.4	298.7	296.5
20°	374.7	364.7	350.4	334.8	319.5	306.8	299.6	293.8	288.0	284.8	282.5
22.5°	363.8	350.9	334.4	317.5	302.2	292.3	286.3	280.3	275.6	272.5	269.4
25°	345.4	328.6	311.0	291.7	281.4	272.6	266.1	261.2	258.4	254.3	252.7
27.5°	326.5	306.1	286.8	273.9	263.0	255.0	249.3	245.7	242.1	239.5	237.4
30°	312.0	291.4	274.0	261.6	250.6	244.1	239.5	235.2	232.3	230.2	228.7
32.5°	297.7	277.0	262.4	249.2	240.4	234.1	229.1	225.9	223.6	220.9	220.0
35°	276.9	258.5	245.8	233.8	225.0	219.2	215.3	212.1	210.1	209.4	208.8
37.5°	256.9	241.9	228.2	218.4	210.5	205.9	201.4	199.7	198.4	197.1	197.7
40°	244.3	230.2	218.0	207.7	201.2	196.2	193.6	191.6	190.5	190.5	190.5
42.5°	233.3	219.6	207.7	198.4	192.0	187.8	184.7	183.1	182.7	182.5	183.5
45°	216.3	203.6	191.6	183.8	178.5	174.2	172.5	171.1	171.1	171.9	172.1
47.5°	199.4	187.5	177.9	169.3	164.3	161.7	160.1	159.5	159.6	160.3	161.2
50°	189.1	177.3	167.9	160.1	155.6	153.0	151.6	151.2	151.6	151.6	153.0
52.5°	177.8	167.3	158.0	151.5	146.3	143.9	143.2	142.6	142.8	143.5	144.1
55°	161.3	151.9	143.0	136.8	133.0	131.4	129.6	129.9	129.5	129.9	129.9
57.5°	144.7	136.2	128.0	123.1	119.7	117.5	115.6	116.1	115.5	115.4	115.1
60°	134.1	124.8	118.3	113.8	110.0	108.0	106.3	106.7	106.2	105.7	104.9
62.5°	122.5	114.8	108.5	104.3	101.2	99.0	97.2	96.9	95.5	94.2	92.5
65°	105.7	99.4	93.8	89.8	86.8	85.1	83.7	82.6	79.7	76.6	75.1
67.5°	89.4	84.8	79.6	76.1	73.8	71.6	69.0	67.0	64.3	62.6	61.6
70°	78.9	74.5	70.0	66.8	64.2	62.1	59.3	57.9	55.9	55.2	54.2
72.5°	68.9	64.7	60.7	57.6	55.0	53.3	51.0	49.7	48.8	48.5	47.6
75°	53.6	50.4	47.3	44.6	42.5	41.3	40.4	39.4	39.0	37.3	36.3
77.5°	39.1	36.9	35.1	33.1	31.6	30.8	28.9	27.9	27.2	26.4	26.2
80°	30.5	28.9	27.0	25.8	23.7	23.0	22.2	22.0	21.8	21.6	21.4
82.5°	22.9	21.4	19.5	18.8	18.2	17.7	17.3	17.0	16.9	17.0	17.0
85°	11.6	10.8	10.8	10.6	10.4	10.2	10.0	10.0	9.9	10.0	9.9
87.5°	4.3	4.2	4.5	4.2	4.5	4.6	4.4	4.4	4.6	4.4	4.4
90°	2.3	2.3	4.0	4.0	4.6	5.2	4.9	5.2	5.5	5.8	5.8
92.5°	15.2	21.2	35.9	58.2	80.0	91.4	76.1	56.6	42.6	33.9	28.1
95°	23.9	36.0	61.1	108.4	177.2	234.8	241.5	213.5	168.8	130.2	102.3
97.5°	28.9	39.1	58.4	97.4	165.8	247.4	303.4	315.4	298.9	270.7	240.6
100°	32.9	42.1	59.1	91.6	150.4	231.7	305.4	347.5	353.3	339.2	317.8
102.5°	37.3	46.0	61.4	90.0	140.1	212.1	288.1	345.9	374.5	378.5	369.7
105°	44.7	53.0	66.9	90.7	131.1	189.0	256.7	322.7	372.6	401.1	412.9
107.5°	52.3	60.6	73.2	95.1	129.5	176.1	231.4	289.8	342.9	383.0	408.8
110°	57.6	65.4	78.1	98.2	130.0	171.7	218.7	270.0	319.8	361.7	393.3



TEST NUMBER: P332867-930

CATALOG NUMBER: S124RDIP-S350D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	62.7	70.4	82.7	101.7	131.3	169.7	211.6	255.4	299.5	339.0	370.7
115°	70.6	78.4	89.9	107.2	134.0	168.6	204.9	240.9	276.3	310.1	337.7
117.5°	77.9	85.9	96.9	112.8	136.8	168.3	201.9	233.7	263.1	289.6	313.1
120°	82.7	90.7	101.7	116.7	138.9	168.3	200.2	230.5	257.3	280.4	300.8
122.5°	87.6	95.4	106.3	120.4	141.0	168.0	198.4	227.7	253.6	274.6	292.5
125°	94.2	102.3	112.7	125.9	144.1	167.7	195.3	223.1	247.8	267.7	283.6
127.5°	100.4	108.5	118.5	130.7	146.6	167.1	191.3	217.3	240.9	260.8	275.8
130°	104.3	112.7	122.5	133.7	148.4	166.8	188.7	212.6	235.5	255.0	270.3
132.5°	108.0	115.9	125.7	136.7	150.0	166.6	186.5	207.8	229.2	248.3	263.6
135°	113.2	120.7	130.2	140.6	152.5	166.2	183.0	201.1	219.9	237.4	251.8
137.5°	117.6	124.8	133.7	143.4	153.8	166.2	180.0	195.1	210.9	225.8	238.7
140°	120.4	127.3	136.0	145.2	155.0	166.0	178.4	191.6	205.1	218.1	230.2
142.5°	122.9	129.6	138.1	146.6	156.0	166.0	177.0	188.4	200.3	211.4	221.9
145°	126.5	132.8	140.3	148.1	156.5	165.4	174.6	183.8	193.6	202.3	210.3
147.5°	129.9	135.6	142.6	149.4	156.8	164.4	172.5	180.1	187.8	194.8	201.1
150°	132.0	137.5	143.8	150.1	156.8	163.6	170.9	177.8	184.4	190.2	195.3
152.5°	134.0	139.1	144.7	150.6	156.3	162.5	169.0	175.3	181.0	186.3	190.5
155°	136.9	141.2	146.1	151.0	155.6	160.8	166.2	171.5	176.0	180.3	183.8
157.5°	139.5	142.9	147.1	151.0	154.8	159.0	163.5	167.4	171.2	174.9	177.7
160°	140.9	144.1	147.6	151.0	154.2	157.6	161.3	164.9	168.0	171.1	173.5
162.5°	142.3	144.8	148.0	151.0	153.4	156.2	159.6	162.3	165.0	167.5	169.6
165°	143.8	145.5	148.1	150.4	152.1	154.2	156.5	158.7	160.5	162.5	164.0
167.5°	144.8	146.2	148.1	149.7	150.7	152.1	153.7	155.4	156.7	158.3	159.1
170°	145.5	146.3	147.8	149.3	149.9	150.7	151.9	153.3	154.2	155.3	156.2
172.5°	145.9	146.6	147.6	148.8	149.0	149.3	150.3	151.5	152.1	152.8	153.4
175°	146.7	146.7	147.2	148.1	147.8	147.8	148.4	149.0	149.3	149.9	149.9
177.5°	146.7	146.7	146.9	147.3	146.9	146.9	147.2	147.3	147.6	147.6	147.8
180°	146.7	146.7	146.7	146.7	146.7	146.7	146.7	146.7	146.7	146.7	146.7



TEST NUMBER: P332867-930

CATALOG NUMBER: S124RDIP-S350D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9
2.5°	457.1	457.5	456.4	456.1	456.4	457.5	457.1	458.0	458.2	459.5	459.0
5°	424.1	423.7	422.7	423.0	422.7	423.7	424.1	425.7	426.4	429.5	429.1
7.5°	395.8	394.4	394.8	393.2	394.8	394.4	395.8	397.2	399.6	401.0	404.3
10°	378.5	376.4	374.7	373.2	374.7	376.4	378.5	379.4	382.6	384.2	387.4
12.5°	355.0	353.1	350.8	351.2	350.8	353.1	355.0	358.3	362.6	365.8	371.0
15°	321.5	318.5	314.0	314.5	314.0	318.5	321.5	324.0	328.2	335.6	339.0
17.5°	293.1	293.1	291.0	291.6	291.0	293.1	293.1	296.5	298.7	303.4	308.7
20°	278.4	277.1	277.3	276.7	277.3	277.1	278.4	282.5	284.8	288.0	293.8
22.5°	268.2	266.6	265.2	264.1	265.2	266.6	268.2	269.4	272.5	275.6	280.3
25°	251.0	249.9	248.2	247.8	248.2	249.9	251.0	252.7	254.3	258.4	261.2
27.5°	235.9	235.7	235.0	234.1	235.0	235.7	235.9	237.4	239.5	242.1	245.7
30°	227.1	226.7	226.3	225.8	226.3	226.7	227.1	228.7	230.2	232.3	235.2
32.5°	219.2	219.0	218.6	218.7	218.6	219.0	219.2	220.0	220.9	223.6	225.9
35°	208.0	207.8	207.4	207.2	207.4	207.8	208.0	208.8	209.4	210.1	212.1
37.5°	197.5	198.0	197.8	197.7	197.8	198.0	197.5	197.7	197.1	198.4	199.7
40°	190.3	190.5	190.9	190.6	190.9	190.5	190.3	190.5	190.5	190.5	191.6
42.5°	184.3	184.3	184.8	184.2	184.8	184.3	184.3	183.5	182.5	182.7	183.1
45°	173.5	174.6	174.4	174.4	174.4	174.6	173.5	172.1	171.9	171.1	171.1
47.5°	161.7	162.7	163.0	162.9	163.0	162.7	161.7	161.2	160.3	159.6	159.5
50°	154.0	153.6	154.2	154.0	154.2	153.6	154.0	153.0	151.6	151.6	151.2
52.5°	144.6	144.6	144.6	144.4	144.6	144.6	144.6	144.1	143.5	142.8	142.6
55°	130.0	130.3	129.9	130.0	129.9	130.3	130.0	129.9	129.9	129.5	129.9
57.5°	114.3	113.4	113.7	113.3	113.7	113.4	114.3	115.1	115.4	115.5	116.1
60°	103.1	101.5	101.1	100.4	101.1	101.5	103.1	104.9	105.7	106.2	106.7
62.5°	90.4	89.3	88.0	88.6	88.0	89.3	90.4	92.5	94.2	95.5	96.9
65°	73.5	72.7	72.2	73.0	72.2	72.7	73.5	75.1	76.6	79.7	82.6
67.5°	60.8	60.4	60.4	60.1	60.4	60.4	60.8	61.6	62.6	64.3	67.0
70°	54.2	53.6	53.6	53.2	53.6	53.6	54.2	54.2	55.2	55.9	57.9
72.5°	47.5	46.9	47.0	46.8	47.0	46.9	47.5	47.6	48.5	48.8	49.7
75°	35.1	34.2	34.2	34.3	34.2	34.2	35.1	36.3	37.3	39.0	39.4
77.5°	26.2	26.0	26.3	25.9	26.3	26.0	26.2	26.2	26.4	27.2	27.9
80°	21.4	21.2	21.0	21.6	21.0	21.2	21.4	21.4	21.6	21.8	22.0
82.5°	16.6	16.6	16.6	17.3	16.6	16.6	16.6	17.0	17.0	16.9	17.0
85°	10.0	9.6	10.0	9.6	10.0	9.6	10.0	9.9	10.0	9.9	10.0
87.5°	4.7	4.6	4.5	4.6	4.5	4.6	4.7	4.4	4.4	4.6	4.4
90°	6.0	6.4	6.0	6.0	6.0	6.4	6.0	5.8	5.8	5.5	5.2
92.5°	24.7	23.2	22.2	22.2	22.2	23.2	24.7	28.1	33.9	42.6	56.6
95°	88.1	79.2	74.0	70.3	74.0	79.2	88.1	102.3	130.2	168.8	213.5
97.5°	219.9	202.6	194.0	187.9	194.0	202.6	219.9	240.6	270.7	298.9	315.4
100°	292.8	275.2	266.5	264.2	266.5	275.2	292.8	317.8	339.2	353.3	347.5
102.5°	354.3	341.6	332.5	330.6	332.5	341.6	354.3	369.7	378.5	374.5	345.9
105°	413.5	411.2	407.2	405.4	407.2	411.2	413.5	412.9	401.1	372.6	322.7
107.5°	423.0	429.6	432.4	433.2	432.4	429.6	423.0	408.8	383.0	342.9	289.8
110°	413.8	425.9	431.0	433.7	431.0	425.9	413.8	393.3	361.7	319.8	270.0



TEST NUMBER: P332867-930

CATALOG NUMBER: S124RDIP-S350D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	394.0	408.6	415.9	420.0	415.9	408.6	394.0	370.7	339.0	299.5	255.4
115°	360.4	377.7	387.0	389.3	387.0	377.7	360.4	337.7	310.1	276.3	240.9
117.5°	332.5	347.0	356.3	358.1	356.3	347.0	332.5	313.1	289.6	263.1	233.7
120°	317.2	330.0	337.5	340.6	337.5	330.0	317.2	300.8	280.4	257.3	230.5
122.5°	306.4	317.2	323.6	326.8	323.6	317.2	306.4	292.5	274.6	253.6	227.7
125°	295.1	303.5	308.9	310.6	308.9	303.5	295.1	283.6	267.7	247.8	223.1
127.5°	287.4	294.8	299.5	301.2	299.5	294.8	287.4	275.8	260.8	240.9	217.3
130°	282.1	289.3	293.9	295.6	293.9	289.3	282.1	270.3	255.0	235.5	212.6
132.5°	275.2	283.3	287.7	289.4	287.7	283.3	275.2	263.6	248.3	229.2	207.8
135°	263.3	271.4	276.1	277.8	276.1	271.4	263.3	251.8	237.4	219.9	201.1
137.5°	249.6	257.5	261.3	263.3	261.3	257.5	249.6	238.7	225.8	210.9	195.1
140°	240.4	246.6	250.7	253.0	250.7	246.6	240.4	230.2	218.1	205.1	191.6
142.5°	230.9	236.8	240.4	241.9	240.4	236.8	230.9	221.9	211.4	200.3	188.4
145°	217.5	222.4	225.3	226.7	225.3	222.4	217.5	210.3	202.3	193.6	183.8
147.5°	206.4	210.7	212.8	213.4	212.8	210.7	206.4	201.1	194.8	187.8	180.1
150°	200.0	203.7	205.5	205.7	205.5	203.7	200.0	195.3	190.2	184.4	177.8
152.5°	194.4	197.5	198.5	198.9	198.5	197.5	194.4	190.5	186.3	181.0	175.3
155°	186.7	189.0	189.9	189.9	189.9	189.0	186.7	183.8	180.3	176.0	171.5
157.5°	179.8	181.6	182.1	182.1	182.1	181.6	179.8	177.7	174.9	171.2	167.4
160°	175.2	176.9	177.2	177.2	177.2	176.9	175.2	173.5	171.1	168.0	164.9
162.5°	170.8	172.5	172.8	172.6	172.8	172.5	170.8	169.6	167.5	165.0	162.3
165°	165.1	166.2	166.0	165.7	166.0	166.2	165.1	164.0	162.5	160.5	158.7
167.5°	159.7	160.5	160.5	160.2	160.5	160.5	159.7	159.1	158.3	156.7	155.4
170°	156.8	157.0	156.8	156.8	156.8	157.0	156.8	156.2	155.3	154.2	153.3
172.5°	153.8	154.0	153.8	153.3	153.8	154.0	153.8	153.4	152.8	152.1	151.5
175°	149.9	150.4	149.9	149.3	149.9	150.4	149.9	149.9	149.9	149.3	149.0
177.5°	147.6	147.8	147.3	146.9	147.3	147.8	147.6	147.8	147.6	147.6	147.3
180°	146.7	146.7	146.7	146.7	146.7	146.7	146.7	146.7	146.7	146.7	146.7



TEST NUMBER: P332867-930

CATALOG NUMBER: S124RDIP-S350D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9
2.5°	458.0	459.2	461.6	464.4	466.8	468.7	470.3	472.5	474.4	477.2	479.8
5°	430.3	433.0	436.8	441.5	447.3	451.1	455.9	460.2	466.4	472.5	478.5
7.5°	405.9	408.9	414.6	420.9	427.8	434.1	439.9	447.4	455.5	464.6	474.6
10°	390.1	393.5	400.1	407.5	415.6	421.8	429.5	438.4	447.7	458.7	471.0
12.5°	375.9	379.1	387.2	394.7	403.1	409.9	418.9	427.9	440.3	452.2	466.2
15°	348.3	356.6	365.8	374.7	384.7	393.1	403.8	413.1	424.9	441.6	457.7
17.5°	317.6	326.4	337.9	351.6	365.1	375.4	386.3	397.8	411.8	428.9	447.4
20°	299.6	306.8	319.5	334.8	350.4	364.7	374.7	387.4	401.9	420.4	439.5
22.5°	286.3	292.3	302.2	317.5	334.4	350.9	363.8	376.3	392.3	410.9	431.7
25°	266.1	272.6	281.4	291.7	311.0	328.6	345.4	359.9	376.8	395.3	418.5
27.5°	249.3	255.0	263.0	273.9	286.8	306.1	326.5	343.0	360.4	380.3	403.5
30°	239.5	244.1	250.6	261.6	274.0	291.4	312.0	331.3	348.9	369.5	393.6
32.5°	229.1	234.1	240.4	249.2	262.4	277.0	297.7	318.8	337.5	358.6	382.2
35°	215.3	219.2	225.0	233.8	245.8	258.5	276.9	298.7	318.4	341.0	363.5
37.5°	201.4	205.9	210.5	218.4	228.2	241.9	256.9	279.2	301.0	321.6	343.6
40°	193.6	196.2	201.2	207.7	218.0	230.2	244.3	266.1	287.9	308.3	330.5
42.5°	184.7	187.8	192.0	198.4	207.7	219.6	233.3	252.2	274.9	294.7	315.0
45°	172.5	174.2	178.5	183.8	191.6	203.6	216.3	233.1	254.5	273.5	291.1
47.5°	160.1	161.7	164.3	169.3	177.9	187.5	199.4	214.5	233.3	252.2	267.2
50°	151.6	153.0	155.6	160.1	167.9	177.3	189.1	202.6	219.4	237.5	250.1
52.5°	143.2	143.9	146.3	151.5	158.0	167.3	177.8	190.3	205.9	221.0	233.7
55°	129.6	131.4	133.0	136.8	143.0	151.9	161.3	173.1	185.2	198.0	208.8
57.5°	115.6	117.5	119.7	123.1	128.0	136.2	144.7	154.3	164.7	175.2	184.3
60°	106.3	108.0	110.0	113.8	118.3	124.8	134.1	142.4	150.3	160.0	169.0
62.5°	97.2	99.0	101.2	104.3	108.5	114.8	122.5	129.7	137.9	146.3	153.1
65°	83.7	85.1	86.8	89.8	93.8	99.4	105.7	111.4	118.7	124.8	131.0
67.5°	69.0	71.6	73.8	76.1	79.6	84.8	89.4	94.8	99.8	104.4	110.0
70°	59.3	62.1	64.2	66.8	70.0	74.5	78.9	82.6	86.7	91.1	96.1
72.5°	51.0	53.3	55.0	57.6	60.7	64.7	68.9	71.9	75.3	78.3	83.2
75°	40.4	41.3	42.5	44.6	47.3	50.4	53.6	56.3	58.3	61.0	64.4
77.5°	28.9	30.8	31.6	33.1	35.1	36.9	39.1	41.4	43.3	44.2	46.9
80°	22.2	23.0	23.7	25.8	27.0	28.9	30.5	32.6	33.3	34.3	36.9
82.5°	17.3	17.7	18.2	18.8	19.5	21.4	22.9	24.3	25.0	25.4	27.3
85°	10.0	10.2	10.4	10.6	10.8	10.8	11.6	12.6	13.9	13.9	14.5
87.5°	4.4	4.6	4.5	4.2	4.5	4.2	4.3	4.2	4.6	5.0	5.3
90°	4.9	5.2	4.6	4.0	4.0	2.3	2.3	2.0	1.7	0.9	0.3
92.5°	76.1	91.4	80.0	58.2	35.9	21.2	15.2	11.0	7.5	4.8	3.3
95°	241.5	234.8	177.2	108.4	61.1	36.0	23.9	17.0	13.3	10.4	9.5
97.5°	303.4	247.4	165.8	97.4	58.4	39.1	28.9	23.0	19.6	17.0	17.0
100°	305.4	231.7	150.4	91.6	59.1	42.1	32.9	27.4	23.9	21.9	21.9
102.5°	288.1	212.1	140.1	90.0	61.4	46.0	37.3	32.0	28.8	27.0	26.5
105°	256.7	189.0	131.1	90.7	66.9	53.0	44.7	39.5	36.0	34.6	33.8
107.5°	231.4	176.1	129.5	95.1	73.2	60.6	52.3	47.4	43.7	42.2	41.7
110°	218.7	171.7	130.0	98.2	78.1	65.4	57.6	52.4	49.0	47.5	47.0



TEST NUMBER: P332867-930

CATALOG NUMBER: S124RDIP-S350D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	211.6	169.7	131.3	101.7	82.7	70.4	62.7	57.5	54.3	52.6	52.0
115°	204.9	168.6	134.0	107.2	89.9	78.4	70.6	65.1	62.2	60.3	59.4
117.5°	201.9	168.3	136.8	112.8	96.9	85.9	77.9	72.7	69.5	67.8	66.9
120°	200.2	168.3	138.9	116.7	101.7	90.7	82.7	77.8	74.6	72.6	72.1
122.5°	198.4	168.0	141.0	120.4	106.3	95.4	87.6	82.2	79.2	77.2	76.6
125°	195.3	167.7	144.1	125.9	112.7	102.3	94.2	88.8	85.6	83.8	82.7
127.5°	191.3	167.1	146.6	130.7	118.5	108.5	100.4	94.7	91.1	88.9	88.1
130°	188.7	166.8	148.4	133.7	122.5	112.7	104.3	98.8	94.5	92.2	91.1
132.5°	186.5	166.6	150.0	136.7	125.7	115.9	108.0	102.1	98.0	95.0	94.1
135°	183.0	166.2	152.5	140.6	130.2	120.7	113.2	107.2	102.3	99.4	98.2
137.5°	180.0	166.2	153.8	143.4	133.7	124.8	117.6	111.4	106.7	103.5	102.5
140°	178.4	166.0	155.0	145.2	136.0	127.3	120.4	114.4	109.5	106.3	105.5
142.5°	177.0	166.0	156.0	146.6	138.1	129.6	122.9	117.2	112.5	109.6	108.7
145°	174.6	165.4	156.5	148.1	140.3	132.8	126.5	121.0	117.0	114.1	113.2
147.5°	172.5	164.4	156.8	149.4	142.6	135.6	129.9	125.3	121.2	118.6	118.4
150°	170.9	163.6	156.8	150.1	143.8	137.5	132.0	127.7	124.2	121.9	121.6
152.5°	169.0	162.5	156.3	150.6	144.7	139.1	134.0	130.2	126.9	124.7	124.6
155°	166.2	160.8	155.6	151.0	146.1	141.2	136.9	133.7	130.9	129.1	128.8
157.5°	163.5	159.0	154.8	151.0	147.1	142.9	139.5	136.7	134.5	132.9	132.9
160°	161.3	157.6	154.2	151.0	147.6	144.1	140.9	138.6	136.6	135.4	135.4
162.5°	159.6	156.2	153.4	151.0	148.0	144.8	142.3	140.2	138.4	137.5	137.7
165°	156.5	154.2	152.1	150.4	148.1	145.5	143.8	142.4	140.9	140.3	140.3
167.5°	153.7	152.1	150.7	149.7	148.1	146.2	144.8	144.0	142.9	142.6	142.9
170°	151.9	150.7	149.9	149.3	147.8	146.3	145.5	145.0	144.1	143.8	144.1
172.5°	150.3	149.3	149.0	148.8	147.6	146.6	145.9	145.6	145.0	145.0	145.2
175°	148.4	147.8	147.8	148.1	147.2	146.7	146.7	146.3	146.1	146.1	146.3
177.5°	147.2	146.9	146.9	147.3	146.9	146.7	146.7	146.7	146.4	146.7	146.9
180°	146.7	146.7	146.7	146.7	146.7	146.7	146.7	146.7	146.7	146.7	146.7



TEST NUMBER: P332867-930

CATALOG NUMBER: S124RDIP-S350D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9
2.5°	481.8	483.2	484.8	487.7	490.2	491.3	493.4	495.0	494.5	496.7	500.3
5°	483.7	488.9	495.0	501.1	508.0	513.8	518.4	523.1	526.8	531.2	537.8
7.5°	483.4	492.7	502.8	513.8	525.2	535.1	544.1	553.4	561.7	570.6	582.4
10°	482.2	494.6	507.1	521.5	536.1	549.8	562.1	573.6	584.7	596.4	611.3
12.5°	480.8	495.0	510.1	527.6	545.6	562.1	576.6	593.3	607.1	622.2	639.4
15°	474.7	493.7	514.5	537.0	558.6	580.8	600.6	621.1	640.3	658.4	680.0
17.5°	467.7	489.7	514.0	540.7	566.6	593.6	617.3	643.0	662.5	686.9	706.9
20°	461.9	485.7	511.7	541.6	571.1	601.0	627.1	653.4	675.3	699.9	725.3
22.5°	455.0	481.0	509.2	540.2	571.1	603.8	632.7	658.8	686.0	713.5	739.8
25°	443.8	470.8	500.8	534.7	570.2	603.6	634.5	666.8	696.2	726.1	749.7
27.5°	430.1	458.4	489.9	525.0	561.4	595.6	631.9	666.5	696.0	724.8	745.3
30°	419.1	449.0	479.3	514.8	552.6	589.3	628.3	662.8	693.9	719.7	731.3
32.5°	407.8	436.2	467.4	503.4	542.1	581.6	620.2	655.6	684.3	699.8	700.1
35°	388.2	414.8	447.3	482.6	522.4	565.2	604.3	639.0	656.6	657.9	639.0
37.5°	366.9	391.3	421.8	457.2	500.8	543.4	583.3	606.5	612.4	592.7	557.8
40°	351.6	374.1	403.7	439.9	483.1	527.2	563.6	580.6	574.5	542.6	503.6
42.5°	335.5	356.5	385.0	420.8	464.1	508.7	539.7	548.8	532.5	495.7	450.0
45°	309.3	328.6	356.8	392.9	434.6	476.2	499.8	495.1	467.9	424.3	373.2
47.5°	282.0	300.7	326.0	359.4	402.1	438.1	454.0	440.0	401.3	353.4	311.8
50°	264.0	283.1	306.4	338.3	377.2	412.0	422.2	401.0	357.9	311.9	273.6
52.5°	246.2	262.5	285.4	316.2	353.4	382.8	388.2	363.8	319.4	278.0	244.1
55°	219.2	234.1	253.3	282.3	314.5	339.4	336.5	305.1	264.7	229.4	202.8
57.5°	193.1	204.2	222.1	249.2	277.5	294.2	283.6	256.8	219.2	190.3	167.9
60°	175.8	186.2	202.8	226.5	251.4	260.9	252.0	222.9	193.1	166.7	147.8
62.5°	159.4	168.6	182.9	204.9	225.0	230.6	221.1	195.7	168.9	146.3	130.7
65°	135.7	144.1	156.3	171.9	185.8	188.5	182.4	156.3	136.1	117.2	106.3
67.5°	114.1	119.6	129.1	142.6	150.0	151.6	139.7	123.3	105.4	93.8	85.7
70°	99.5	103.5	112.3	119.6	125.6	125.8	114.8	101.7	88.0	78.5	72.6
72.5°	85.5	89.2	96.0	100.9	105.6	104.0	94.0	83.6	72.6	65.4	61.0
75°	66.0	69.3	72.7	75.1	75.1	73.1	65.8	58.0	51.7	47.5	46.1
77.5°	47.9	50.6	51.9	51.4	50.8	47.8	43.1	38.1	35.8	33.8	32.8
80°	37.7	38.8	39.1	38.2	37.0	33.6	30.5	28.4	26.3	25.4	25.1
82.5°	27.9	28.9	27.9	28.2	25.6	22.7	21.0	20.3	19.5	19.2	18.8
85°	14.8	14.7	14.3	13.3	11.6	11.2	11.0	10.8	10.4	10.6	10.2
87.5°	5.3	5.0	4.4	4.3	4.3	4.3	4.5	4.6	4.7	4.6	4.9
90°	0.9	1.7	2.0	2.3	2.3	4.0	4.0	4.6	5.2	4.9	5.2
92.5°	4.8	7.5	11.0	15.2	21.2	35.9	58.2	80.0	91.4	76.1	56.6
95°	10.4	13.3	17.0	23.9	36.0	61.1	108.4	177.2	234.8	241.5	213.5
97.5°	17.0	19.6	23.0	28.9	39.1	58.4	97.4	165.8	247.4	303.4	315.4
100°	21.9	23.9	27.4	32.9	42.1	59.1	91.6	150.4	231.7	305.4	347.5
102.5°	27.0	28.8	32.0	37.3	46.0	61.4	90.0	140.1	212.1	288.1	345.9
105°	34.6	36.0	39.5	44.7	53.0	66.9	90.7	131.1	189.0	256.7	322.7
107.5°	42.2	43.7	47.4	52.3	60.6	73.2	95.1	129.5	176.1	231.4	289.8
110°	47.5	49.0	52.4	57.6	65.4	78.1	98.2	130.0	171.7	218.7	270.0



TEST NUMBER: P332867-930

CATALOG NUMBER: S124RDIP-S350D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	52.6	54.3	57.5	62.7	70.4	82.7	101.7	131.3	169.7	211.6	255.4
115°	60.3	62.2	65.1	70.6	78.4	89.9	107.2	134.0	168.6	204.9	240.9
117.5°	67.8	69.5	72.7	77.9	85.9	96.9	112.8	136.8	168.3	201.9	233.7
120°	72.6	74.6	77.8	82.7	90.7	101.7	116.7	138.9	168.3	200.2	230.5
122.5°	77.2	79.2	82.2	87.6	95.4	106.3	120.4	141.0	168.0	198.4	227.7
125°	83.8	85.6	88.8	94.2	102.3	112.7	125.9	144.1	167.7	195.3	223.1
127.5°	88.9	91.1	94.7	100.4	108.5	118.5	130.7	146.6	167.1	191.3	217.3
130°	92.2	94.5	98.8	104.3	112.7	122.5	133.7	148.4	166.8	188.7	212.6
132.5°	95.0	98.0	102.1	108.0	115.9	125.7	136.7	150.0	166.6	186.5	207.8
135°	99.4	102.3	107.2	113.2	120.7	130.2	140.6	152.5	166.2	183.0	201.1
137.5°	103.5	106.7	111.4	117.6	124.8	133.7	143.4	153.8	166.2	180.0	195.1
140°	106.3	109.5	114.4	120.4	127.3	136.0	145.2	155.0	166.0	178.4	191.6
142.5°	109.6	112.5	117.2	122.9	129.6	138.1	146.6	156.0	166.0	177.0	188.4
145°	114.1	117.0	121.0	126.5	132.8	140.3	148.1	156.5	165.4	174.6	183.8
147.5°	118.6	121.2	125.3	129.9	135.6	142.6	149.4	156.8	164.4	172.5	180.1
150°	121.9	124.2	127.7	132.0	137.5	143.8	150.1	156.8	163.6	170.9	177.8
152.5°	124.7	126.9	130.2	134.0	139.1	144.7	150.6	156.3	162.5	169.0	175.3
155°	129.1	130.9	133.7	136.9	141.2	146.1	151.0	155.6	160.8	166.2	171.5
157.5°	132.9	134.5	136.7	139.5	142.9	147.1	151.0	154.8	159.0	163.5	167.4
160°	135.4	136.6	138.6	140.9	144.1	147.6	151.0	154.2	157.6	161.3	164.9
162.5°	137.5	138.4	140.2	142.3	144.8	148.0	151.0	153.4	156.2	159.6	162.3
165°	140.3	140.9	142.4	143.8	145.5	148.1	150.4	152.1	154.2	156.5	158.7
167.5°	142.6	142.9	144.0	144.8	146.2	148.1	149.7	150.7	152.1	153.7	155.4
170°	143.8	144.1	145.0	145.5	146.3	147.8	149.3	149.9	150.7	151.9	153.3
172.5°	145.0	145.0	145.6	145.9	146.6	147.6	148.8	149.0	149.3	150.3	151.5
175°	146.1	146.1	146.3	146.7	146.7	147.2	148.1	147.8	147.8	148.4	149.0
177.5°	146.7	146.4	146.7	146.7	146.7	146.9	147.3	146.9	146.9	147.2	147.3
180°	146.7	146.7	146.7	146.7	146.7	146.7	146.7	146.7	146.7	146.7	146.7



TEST NUMBER: P332867-930

CATALOG NUMBER: S124RDIP-S350D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	478.9	478.9	478.9	478.9	478.9	478.9	478.9
2.5°	502.4	503.0	503.4	505.0	505.2	506.5	505.2
5°	544.0	546.7	550.9	555.1	555.5	558.2	553.4
7.5°	590.5	596.8	600.7	607.6	610.3	612.0	609.2
10°	622.6	628.4	638.7	643.7	648.7	649.5	647.2
12.5°	653.7	662.8	670.9	680.4	680.2	687.0	684.5
15°	695.0	704.5	715.7	726.3	730.1	730.1	733.2
17.5°	724.5	741.8	753.4	761.7	770.9	772.4	771.4
20°	744.4	763.1	775.5	786.3	792.5	794.2	794.2
22.5°	759.2	775.2	787.3	797.0	802.0	804.0	803.5
25°	769.5	783.2	790.5	793.4	794.8	794.4	790.8
27.5°	755.5	754.8	750.2	741.4	734.7	730.6	725.9
30°	728.6	718.5	706.9	694.2	677.8	665.3	661.5
32.5°	688.6	666.1	646.5	625.3	607.6	595.1	589.8
35°	611.3	575.6	546.4	521.0	502.5	490.9	487.0
37.5°	519.5	484.9	448.9	424.2	408.8	397.1	392.8
40°	461.1	423.5	392.1	368.9	353.1	341.7	341.5
42.5°	407.9	371.9	342.3	325.7	308.7	301.1	301.1
45°	334.0	305.2	280.1	267.0	256.8	250.6	248.9
47.5°	276.5	252.7	236.0	225.6	217.3	213.4	210.8
50°	244.3	223.5	210.1	201.1	196.4	191.4	191.0
52.5°	217.4	200.6	190.2	182.9	177.0	174.0	174.1
55°	182.7	169.4	162.1	156.5	151.9	149.5	148.5
57.5°	153.9	144.0	138.6	133.5	131.5	129.7	129.2
60°	136.1	129.3	124.3	120.2	117.3	116.8	116.5
62.5°	121.2	114.1	110.7	107.5	105.4	104.5	104.2
65°	100.0	94.7	91.6	89.1	88.4	87.0	86.8
67.5°	80.6	77.5	75.4	73.7	72.6	72.6	72.6
70°	68.7	66.9	65.2	64.2	63.7	63.3	63.3
72.5°	58.5	57.2	55.8	55.3	55.2	54.8	54.6
75°	44.6	43.2	43.5	42.5	41.7	40.7	40.1
77.5°	31.6	30.7	30.4	30.3	29.7	29.6	29.8
80°	24.5	23.6	23.3	23.6	23.3	22.7	22.7
82.5°	18.7	17.9	17.6	17.5	17.4	17.5	17.2
85°	10.0	9.6	9.6	9.6	10.0	9.9	9.6
87.5°	4.6	4.6	4.7	4.6	4.6	4.5	4.6
90°	5.5	5.8	5.8	6.0	6.4	6.0	6.0
92.5°	42.6	33.9	28.1	24.7	23.2	22.2	22.2
95°	168.8	130.2	102.3	88.1	79.2	74.0	70.3
97.5°	298.9	270.7	240.6	219.9	202.6	194.0	187.9
100°	353.3	339.2	317.8	292.8	275.2	266.5	264.2
102.5°	374.5	378.5	369.7	354.3	341.6	332.5	330.6
105°	372.6	401.1	412.9	413.5	411.2	407.2	405.4
107.5°	342.9	383.0	408.8	423.0	429.6	432.4	433.2
110°	319.8	361.7	393.3	413.8	425.9	431.0	433.7



TEST NUMBER: P332867-930

CATALOG NUMBER: S124RDIP-S350D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	299.5	339.0	370.7	394.0	408.6	415.9	420.0
115°	276.3	310.1	337.7	360.4	377.7	387.0	389.3
117.5°	263.1	289.6	313.1	332.5	347.0	356.3	358.1
120°	257.3	280.4	300.8	317.2	330.0	337.5	340.6
122.5°	253.6	274.6	292.5	306.4	317.2	323.6	326.8
125°	247.8	267.7	283.6	295.1	303.5	308.9	310.6
127.5°	240.9	260.8	275.8	287.4	294.8	299.5	301.2
130°	235.5	255.0	270.3	282.1	289.3	293.9	295.6
132.5°	229.2	248.3	263.6	275.2	283.3	287.7	289.4
135°	219.9	237.4	251.8	263.3	271.4	276.1	277.8
137.5°	210.9	225.8	238.7	249.6	257.5	261.3	263.3
140°	205.1	218.1	230.2	240.4	246.6	250.7	253.0
142.5°	200.3	211.4	221.9	230.9	236.8	240.4	241.9
145°	193.6	202.3	210.3	217.5	222.4	225.3	226.7
147.5°	187.8	194.8	201.1	206.4	210.7	212.8	213.4
150°	184.4	190.2	195.3	200.0	203.7	205.5	205.7
152.5°	181.0	186.3	190.5	194.4	197.5	198.5	198.9
155°	176.0	180.3	183.8	186.7	189.0	189.9	189.9
157.5°	171.2	174.9	177.7	179.8	181.6	182.1	182.1
160°	168.0	171.1	173.5	175.2	176.9	177.2	177.2
162.5°	165.0	167.5	169.6	170.8	172.5	172.8	172.6
165°	160.5	162.5	164.0	165.1	166.2	166.0	165.7
167.5°	156.7	158.3	159.1	159.7	160.5	160.5	160.2
170°	154.2	155.3	156.2	156.8	157.0	156.8	156.8
172.5°	152.1	152.8	153.4	153.8	154.0	153.8	153.3
175°	149.3	149.9	149.9	149.9	150.4	149.9	149.3
177.5°	147.6	147.6	147.8	147.6	147.8	147.3	146.9
180°	146.7	146.7	146.7	146.7	146.7	146.7	146.7

(END OF REPORT)