

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332877-930

Luminaire Tested: **S124RDIP-S350D810U930-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332877-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIP-S350D810U930-4F0-1E-UDD-A  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 350 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 810 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3849.5 lumens  
Efficiency: N/A  
Efficacy: 123.4 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 31.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332877-930

CATALOG NUMBER: S124RDIP-S350D810U930-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P332877-930

CATALOG NUMBER: S124RDIP-S350D810U930-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	32
1	94	90	86	83	84	81	78	75	64	62	60	49	48	47	35	34	34	27
2	86	79	73	68	77	71	66	62	57	53	50	43	41	39	31	30	29	23
3	78	69	62	57	70	63	57	52	50	46	43	39	36	34	28	26	25	20
4	72	61	54	48	64	56	49	44	45	40	36	34	31	29	25	23	21	17
5	66	55	47	41	59	50	43	38	40	35	31	31	28	25	23	21	19	15
6	61	49	41	36	54	45	38	33	36	31	27	28	25	22	21	18	17	13
7	56	44	37	31	50	40	34	29	33	28	24	25	22	19	19	17	15	12
8	52	40	33	28	47	37	30	26	30	25	21	23	20	17	17	15	13	11
9	48	37	29	24	43	33	27	23	27	22	19	21	18	16	16	14	12	10
10	45	33	26	22	41	31	24	20	25	20	17	20	16	14	15	13	11	9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	3866	3866	3866	3866
5°	4485	3878	3428	3878
10°	5305	3861	3059	3861
15°	6128	3825	2629	3825
20°	6823	3776	2377	3776
25°	7044	3728	2207	3728
30°	6166	3669	2105	3669
35°	4800	3582	2042	3582
40°	3599	3483	2009	3483
45°	2842	3323	1991	3323
50°	2399	3141	1934	3141
55°	2090	2939	1830	2939
60°	1881	2729	1621	2729
65°	1658	2502	1394	2502
70°	1494	2268	1256	2268
75°	1251	2009	1070	2009
80°	1055	1715	1004	1715
85°	889	1343	889	1343



TEST NUMBER: P332877-930

CATALOG NUMBER: S124RDIP-S350D810U930-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	46.4	1.2
10°-20°	140.0	3.6
20°-30°	218.9	5.7
30°-40°	243.4	6.3
40°-50°	215.9	5.6
50°-60°	168.3	4.4
60°-70°	110.2	2.9
70°-80°	54.2	1.4
80°-90°	15.8	0.4
90°-100°	29.1	0.8
100°-110°	185.9	4.8
110°-120°	355.6	9.2
120°-130°	451.4	11.7
130°-140°	482.9	12.5
140°-150°	451.6	11.7
150°-160°	364.2	9.5
160°-170°	234.9	6.1
170°-180°	81.0	2.1
0°-30°	405.3	10.5
0°-40°	648.7	16.9
0°-60°	1032.9	26.8
0°-90°	1213.0	31.5
90°-120°	570.6	14.8
90°-150°	1956.4	50.8
90°-180°	2636.0	68.5
0°-180°	3849.5	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	479	479	479	479	479	
5°	553	478	423	478	553	56
15°	733	458	314	458	733	208
25°	791	418	248	418	791	351
35°	487	364	207	364	487	305
45°	249	291	174	291	249	197
55°	148	209	130	209	148	135
65°	87	131	73	131	87	87
75°	40	64	34	64	40	44
85°	10	14	10	14	10	11
90°	19	2	19	2	19	9
95°	18	35	18	35	18	15
105°	182	192	182	192	182	158
115°	361	358	361	358	361	357
125°	507	504	507	504	507	452
135°	629	625	629	625	629	484
145°	724	720	724	720	724	453
155°	789	790	789	790	789	364
165°	829	833	829	833	829	234
175°	847	852	847	852	847	81
180°	852	852	852	852	852	



TEST NUMBER: P332877-930

CATALOG NUMBER: S124RDIP-S350D810U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9
2.5°	505.2	506.5	505.2	505.0	503.4	503.0	502.4	500.3	496.7	494.5	495.0
5°	553.4	558.2	555.5	555.1	550.9	546.7	544.0	537.8	531.2	526.8	523.1
7.5°	609.2	612.0	610.3	607.6	600.7	596.8	590.5	582.4	570.6	561.7	553.4
10°	647.2	649.5	648.7	643.7	638.7	628.4	622.6	611.3	596.4	584.7	573.6
12.5°	684.5	687.0	680.2	680.4	670.9	662.8	653.7	639.4	622.2	607.1	593.3
15°	733.2	730.1	730.1	726.3	715.7	704.5	695.0	680.0	658.4	640.3	621.1
17.5°	771.4	772.4	770.9	761.7	753.4	741.8	724.5	706.9	686.9	662.5	643.0
20°	794.2	794.2	792.5	786.3	775.5	763.1	744.4	725.3	699.9	675.3	653.4
22.5°	803.5	804.0	802.0	797.0	787.3	775.2	759.2	739.8	713.5	686.0	658.8
25°	790.8	794.4	794.8	793.4	790.5	783.2	769.5	749.7	726.1	696.2	666.8
27.5°	725.9	730.6	734.7	741.4	750.2	754.8	755.5	745.3	724.8	696.0	666.5
30°	661.5	665.3	677.8	694.2	706.9	718.5	728.6	731.3	719.7	693.9	662.8
32.5°	589.8	595.1	607.6	625.3	646.5	666.1	688.6	700.1	699.8	684.3	655.6
35°	487.0	490.9	502.5	521.0	546.4	575.6	611.3	639.0	657.9	656.6	639.0
37.5°	392.8	397.1	408.8	424.2	448.9	484.9	519.5	557.8	592.7	612.4	606.5
40°	341.5	341.7	353.1	368.9	392.1	423.5	461.1	503.6	542.6	574.5	580.6
42.5°	301.1	301.1	308.7	325.7	342.3	371.9	407.9	450.0	495.7	532.5	548.8
45°	248.9	250.6	256.8	267.0	280.1	305.2	334.0	373.2	424.3	467.9	495.1
47.5°	210.8	213.4	217.3	225.6	236.0	252.7	276.5	311.8	353.4	401.3	440.0
50°	191.0	191.4	196.4	201.1	210.1	223.5	244.3	273.6	311.9	357.9	401.0
52.5°	174.1	174.0	177.0	182.9	190.2	200.6	217.4	244.1	278.0	319.4	363.8
55°	148.5	149.5	151.9	156.5	162.1	169.4	182.7	202.8	229.4	264.7	305.1
57.5°	129.2	129.7	131.5	133.5	138.6	144.0	153.9	167.9	190.3	219.2	256.8
60°	116.5	116.8	117.3	120.2	124.3	129.3	136.1	147.8	166.7	193.1	222.9
62.5°	104.2	104.5	105.4	107.5	110.7	114.1	121.2	130.7	146.3	168.9	195.7
65°	86.8	87.0	88.4	89.1	91.6	94.7	100.0	106.3	117.2	136.1	156.3
67.5°	72.6	72.6	72.6	73.7	75.4	77.5	80.6	85.7	93.8	105.4	123.3
70°	63.3	63.3	63.7	64.2	65.2	66.9	68.7	72.6	78.5	88.0	101.7
72.5°	54.6	54.8	55.2	55.3	55.8	57.2	58.5	61.0	65.4	72.6	83.6
75°	40.1	40.7	41.7	42.5	43.5	43.2	44.6	46.1	47.5	51.7	58.0
77.5°	29.8	29.6	29.7	30.3	30.4	30.7	31.6	32.8	33.8	35.8	38.1
80°	22.7	22.7	23.3	23.6	23.3	23.6	24.5	25.1	25.4	26.3	28.4
82.5°	17.2	17.5	17.4	17.5	17.6	17.9	18.7	18.8	19.2	19.5	20.3
85°	9.6	9.9	10.0	9.6	9.6	9.6	10.0	10.2	10.6	10.4	10.8
87.5°	7.3	7.0	7.1	7.0	7.2	6.8	6.8	7.0	6.5	6.5	6.3
90°	19.2	18.8	18.6	18.3	18.0	17.4	16.6	15.7	14.8	14.0	12.9
92.5°	17.6	17.5	17.4	17.4	17.4	16.9	16.1	15.2	14.3	13.5	12.4
95°	18.5	18.3	18.2	18.1	17.9	17.4	16.6	15.7	14.8	14.0	13.9
97.5°	17.9	17.7	17.5	17.4	17.3	17.2	17.1	17.0	16.9	16.8	32.6
100°	17.9	17.7	17.5	17.4	17.3	18.4	20.8	23.2	25.6	28.0	47.6
102.5°	18.3	18.3	18.3	18.3	18.3	31.2	57.2	83.2	109.2	135.2	137.7
105°	181.6	186.8	191.8	197.0	202.1	204.0	202.7	201.5	200.2	198.9	198.2
107.5°	253.2	252.7	252.1	251.6	251.0	250.5	249.8	249.2	248.6	248.0	247.0
110°	284.3	283.9	283.5	283.1	282.6	282.3	282.0	281.7	281.4	281.1	280.3



TEST NUMBER: P332877-930

CATALOG NUMBER: S124RDIP-S350D810U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	315.4	314.9	314.4	313.8	313.2	313.0	313.1	313.2	313.2	313.2	312.8
115°	360.9	360.9	360.9	360.9	360.9	360.7	360.4	360.1	359.8	359.5	359.7
117.5°	407.0	407.0	407.1	407.2	407.2	407.2	407.3	407.3	407.4	407.5	407.2
120°	436.0	436.3	436.6	436.9	437.2	437.2	436.9	436.6	436.3	436.0	436.2
122.5°	464.6	464.9	465.1	465.5	465.7	465.8	465.6	465.5	465.3	465.1	464.9
125°	507.4	507.3	507.1	507.0	506.9	506.5	506.1	505.7	505.3	504.9	505.2
127.5°	545.0	545.2	545.3	545.4	545.5	545.6	545.7	545.8	545.8	545.9	545.3
130°	570.5	570.5	570.5	570.5	570.5	570.5	570.3	570.2	570.1	569.9	569.5
132.5°	594.0	594.1	594.2	594.4	594.4	594.4	594.3	594.2	594.0	593.9	593.3
135°	629.2	628.9	628.6	628.4	628.0	627.8	627.5	627.2	626.9	626.6	626.1
137.5°	659.3	659.3	659.4	659.5	659.6	659.5	659.2	658.8	658.6	658.3	657.6
140°	680.2	680.0	679.9	679.8	679.6	679.3	678.9	678.5	678.1	677.6	677.4
142.5°	697.5	697.5	697.5	697.4	697.4	697.2	696.9	696.6	696.3	696.0	695.9
145°	724.1	723.9	723.6	723.3	723.0	722.8	722.7	722.5	722.4	722.3	722.3
147.5°	746.2	746.1	745.9	745.8	745.7	745.5	745.4	745.3	745.2	745.1	745.2
150°	760.5	760.3	760.2	760.1	759.9	759.9	759.9	759.9	759.9	759.9	760.0
152.5°	772.7	772.8	772.9	773.0	773.1	773.0	772.8	772.6	772.3	772.1	772.3
155°	789.2	789.6	790.0	790.4	790.9	790.8	790.3	789.7	789.1	788.6	789.0
157.5°	803.0	803.7	804.5	805.2	805.9	805.9	805.2	804.5	803.7	803.0	803.5
160°	812.1	813.0	813.8	814.7	815.5	815.5	814.7	813.8	813.0	812.1	812.3
162.5°	819.3	820.3	821.2	822.1	823.1	823.2	822.3	821.5	820.7	819.8	819.9
165°	829.3	830.6	831.9	833.2	834.5	834.5	833.4	832.3	831.1	830.0	830.0
167.5°	836.9	838.3	839.7	841.1	842.5	842.6	841.4	840.2	838.9	837.6	837.7
170°	841.5	842.9	844.3	845.7	847.1	847.3	846.1	845.0	843.8	842.8	842.6
172.5°	844.0	845.5	847.1	848.6	850.1	850.4	849.2	848.1	846.9	845.8	845.6
175°	847.2	848.9	850.6	852.3	854.0	854.2	853.0	851.7	850.4	849.1	849.0
177.5°	849.2	850.6	852.0	853.3	854.7	854.9	854.0	853.1	852.2	851.3	851.1
180°	852.3	852.3	852.3	852.3	852.3	852.3	852.3	852.3	852.3	852.3	852.3



TEST NUMBER: P332877-930

CATALOG NUMBER: S124RDIP-S350D810U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9
2.5°	493.4	491.3	490.2	487.7	484.8	483.2	481.8	479.8	477.2	474.4	472.5
5°	518.4	513.8	508.0	501.1	495.0	488.9	483.7	478.5	472.5	466.4	460.2
7.5°	544.1	535.1	525.2	513.8	502.8	492.7	483.4	474.6	464.6	455.5	447.4
10°	562.1	549.8	536.1	521.5	507.1	494.6	482.2	471.0	458.7	447.7	438.4
12.5°	576.6	562.1	545.6	527.6	510.1	495.0	480.8	466.2	452.2	440.3	427.9
15°	600.6	580.8	558.6	537.0	514.5	493.7	474.7	457.7	441.6	424.9	413.1
17.5°	617.3	593.6	566.6	540.7	514.0	489.7	467.7	447.4	428.9	411.8	397.8
20°	627.1	601.0	571.1	541.6	511.7	485.7	461.9	439.5	420.4	401.9	387.4
22.5°	632.7	603.8	571.1	540.2	509.2	481.0	455.0	431.7	410.9	392.3	376.3
25°	634.5	603.6	570.2	534.7	500.8	470.8	443.8	418.5	395.3	376.8	359.9
27.5°	631.9	595.6	561.4	525.0	489.9	458.4	430.1	403.5	380.3	360.4	343.0
30°	628.3	589.3	552.6	514.8	479.3	449.0	419.1	393.6	369.5	348.9	331.3
32.5°	620.2	581.6	542.1	503.4	467.4	436.2	407.8	382.2	358.6	337.5	318.8
35°	604.3	565.2	522.4	482.6	447.3	414.8	388.2	363.5	341.0	318.4	298.7
37.5°	583.3	543.4	500.8	457.2	421.8	391.3	366.9	343.6	321.6	301.0	279.2
40°	563.6	527.2	483.1	439.9	403.7	374.1	351.6	330.5	308.3	287.9	266.1
42.5°	539.7	508.7	464.1	420.8	385.0	356.5	335.5	315.0	294.7	274.9	252.2
45°	499.8	476.2	434.6	392.9	356.8	328.6	309.3	291.1	273.5	254.5	233.1
47.5°	454.0	438.1	402.1	359.4	326.0	300.7	282.0	267.2	252.2	233.3	214.5
50°	422.2	412.0	377.2	338.3	306.4	283.1	264.0	250.1	237.5	219.4	202.6
52.5°	388.2	382.8	353.4	316.2	285.4	262.5	246.2	233.7	221.0	205.9	190.3
55°	336.5	339.4	314.5	282.3	253.3	234.1	219.2	208.8	198.0	185.2	173.1
57.5°	283.6	294.2	277.5	249.2	222.1	204.2	193.1	184.3	175.2	164.7	154.3
60°	252.0	260.9	251.4	226.5	202.8	186.2	175.8	169.0	160.0	150.3	142.4
62.5°	221.1	230.6	225.0	204.9	182.9	168.6	159.4	153.1	146.3	137.9	129.7
65°	182.4	188.5	185.8	171.9	156.3	144.1	135.7	131.0	124.8	118.7	111.4
67.5°	139.7	151.6	150.0	142.6	129.1	119.6	114.1	110.0	104.4	99.8	94.8
70°	114.8	125.8	125.6	119.6	112.3	103.5	99.5	96.1	91.1	86.7	82.6
72.5°	94.0	104.0	105.6	100.9	96.0	89.2	85.5	83.2	78.3	75.3	71.9
75°	65.8	73.1	75.1	75.1	72.7	69.3	66.0	64.4	61.0	58.3	56.3
77.5°	43.1	47.8	50.8	51.4	51.9	50.6	47.9	46.9	44.2	43.3	41.4
80°	30.5	33.6	37.0	38.2	39.1	38.8	37.7	36.9	34.3	33.3	32.6
82.5°	21.0	22.7	25.6	28.2	27.9	28.9	27.9	27.3	25.4	25.0	24.3
85°	11.0	11.2	11.6	13.3	14.3	14.7	14.8	14.5	13.9	13.9	12.6
87.5°	6.0	5.7	5.8	5.5	5.3	5.6	5.8	5.6	5.5	5.3	5.1
90°	11.7	10.6	9.5	8.2	6.6	5.1	3.5	1.9	3.5	5.1	6.6
92.5°	11.3	10.1	9.0	8.4	8.3	8.2	8.2	8.1	8.2	8.2	8.3
95°	13.8	13.6	13.5	15.8	20.6	25.4	30.2	35.1	30.2	25.4	20.6
97.5°	48.4	64.2	80.1	86.5	83.5	80.5	77.5	74.4	77.5	80.5	83.5
100°	67.2	86.7	106.2	114.7	112.2	109.7	107.1	104.5	107.1	109.7	112.2
102.5°	140.2	142.8	145.4	145.7	143.8	141.9	140.1	138.2	140.1	141.9	143.8
105°	197.5	196.7	196.1	195.3	194.4	193.6	192.7	191.8	192.7	193.6	194.4
107.5°	246.1	245.1	244.1	243.4	243.0	242.6	242.1	241.7	242.1	242.6	243.0
110°	279.4	278.6	277.7	277.1	276.6	276.2	275.8	275.4	275.8	276.2	276.6





TEST NUMBER: P332877-930

CATALOG NUMBER: S124RDIP-S350D810U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	312.4	312.1	311.7	311.1	310.3	309.6	308.8	308.0	308.8	309.6	310.3
115°	359.8	360.0	360.1	360.0	359.5	359.1	358.7	358.2	358.7	359.1	359.5
117.5°	406.8	406.5	406.3	405.8	405.2	404.6	404.1	403.5	404.1	404.6	405.2
120°	436.3	436.4	436.6	436.3	435.9	435.3	434.7	434.1	434.7	435.3	435.9
122.5°	464.7	464.5	464.3	464.1	463.7	463.3	463.0	462.7	463.0	463.3	463.7
125°	505.5	505.7	506.0	505.9	505.3	504.8	504.2	503.6	504.2	504.8	505.3
127.5°	544.6	544.0	543.3	542.9	542.8	542.7	542.5	542.3	542.5	542.7	542.8
130°	569.1	568.6	568.2	567.9	567.8	567.6	567.5	567.4	567.5	567.6	567.8
132.5°	592.8	592.2	591.7	591.3	591.1	590.8	590.5	590.3	590.5	590.8	591.1
135°	625.5	624.9	624.4	624.2	624.3	624.4	624.6	624.8	624.6	624.4	624.3
137.5°	657.0	656.4	655.7	655.4	655.3	655.3	655.3	655.2	655.3	655.3	655.3
140°	677.1	676.8	676.5	676.2	676.0	675.6	675.4	675.1	675.4	675.6	676.0
142.5°	695.7	695.5	695.3	695.0	694.5	694.0	693.4	692.9	693.4	694.0	694.5
145°	722.3	722.3	722.3	722.0	721.6	721.2	720.8	720.3	720.8	721.2	721.6
147.5°	745.3	745.5	745.7	745.3	744.5	743.7	743.0	742.2	743.0	743.7	744.5
150°	760.2	760.3	760.4	760.2	759.7	759.1	758.6	758.0	758.6	759.1	759.7
152.5°	772.7	772.9	773.1	773.1	772.6	772.1	771.7	771.2	771.7	772.1	772.6
155°	789.4	789.9	790.3	790.4	790.3	790.1	789.9	789.9	789.9	790.1	790.3
157.5°	804.0	804.4	804.9	805.2	805.3	805.4	805.4	805.5	805.4	805.4	805.3
160°	812.4	812.6	812.7	813.0	813.4	813.8	814.2	814.7	814.2	813.8	813.4
162.5°	820.1	820.2	820.4	820.7	821.3	821.7	822.3	822.9	822.3	821.7	821.3
165°	830.0	830.0	830.0	830.4	831.0	831.8	832.5	833.2	832.5	831.8	831.0
167.5°	837.8	837.9	838.0	838.4	839.1	839.8	840.6	841.3	840.6	839.8	839.1
170°	842.4	842.3	842.2	842.5	843.3	844.2	845.1	846.0	845.1	844.2	843.3
172.5°	845.5	845.4	845.2	845.6	846.4	847.3	848.2	849.0	848.2	847.3	846.4
175°	848.8	848.7	848.6	848.9	849.8	850.6	851.4	852.3	851.4	850.6	849.8
177.5°	850.8	850.6	850.4	850.7	851.4	852.2	853.0	853.9	853.0	852.2	851.4
180°	852.3	852.3	852.3	852.3	852.3	852.3	852.3	852.3	852.3	852.3	852.3



TEST NUMBER: P332877-930

CATALOG NUMBER: S124RDIP-S350D810U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9
2.5°	470.3	468.7	466.8	464.4	461.6	459.2	458.0	459.0	459.5	458.2	458.0
5°	455.9	451.1	447.3	441.5	436.8	433.0	430.3	429.1	429.5	426.4	425.7
7.5°	439.9	434.1	427.8	420.9	414.6	408.9	405.9	404.3	401.0	399.6	397.2
10°	429.5	421.8	415.6	407.5	400.1	393.5	390.1	387.4	384.2	382.6	379.4
12.5°	418.9	409.9	403.1	394.7	387.2	379.1	375.9	371.0	365.8	362.6	358.3
15°	403.8	393.1	384.7	374.7	365.8	356.6	348.3	339.0	335.6	328.2	324.0
17.5°	386.3	375.4	365.1	351.6	337.9	326.4	317.6	308.7	303.4	298.7	296.5
20°	374.7	364.7	350.4	334.8	319.5	306.8	299.6	293.8	288.0	284.8	282.5
22.5°	363.8	350.9	334.4	317.5	302.2	292.3	286.3	280.3	275.6	272.5	269.4
25°	345.4	328.6	311.0	291.7	281.4	272.6	266.1	261.2	258.4	254.3	252.7
27.5°	326.5	306.1	286.8	273.9	263.0	255.0	249.3	245.7	242.1	239.5	237.4
30°	312.0	291.4	274.0	261.6	250.6	244.1	239.5	235.2	232.3	230.2	228.7
32.5°	297.7	277.0	262.4	249.2	240.4	234.1	229.1	225.9	223.6	220.9	220.0
35°	276.9	258.5	245.8	233.8	225.0	219.2	215.3	212.1	210.1	209.4	208.8
37.5°	256.9	241.9	228.2	218.4	210.5	205.9	201.4	199.7	198.4	197.1	197.7
40°	244.3	230.2	218.0	207.7	201.2	196.2	193.6	191.6	190.5	190.5	190.5
42.5°	233.3	219.6	207.7	198.4	192.0	187.8	184.7	183.1	182.7	182.5	183.5
45°	216.3	203.6	191.6	183.8	178.5	174.2	172.5	171.1	171.1	171.9	172.1
47.5°	199.4	187.5	177.9	169.3	164.3	161.7	160.1	159.5	159.6	160.3	161.2
50°	189.1	177.3	167.9	160.1	155.6	153.0	151.6	151.2	151.6	151.6	153.0
52.5°	177.8	167.3	158.0	151.5	146.3	143.9	143.2	142.6	142.8	143.5	144.1
55°	161.3	151.9	143.0	136.8	133.0	131.4	129.6	129.9	129.5	129.9	129.9
57.5°	144.7	136.2	128.0	123.1	119.7	117.5	115.6	116.1	115.5	115.4	115.1
60°	134.1	124.8	118.3	113.8	110.0	108.0	106.3	106.7	106.2	105.7	104.9
62.5°	122.5	114.8	108.5	104.3	101.2	99.0	97.2	96.9	95.5	94.2	92.5
65°	105.7	99.4	93.8	89.8	86.8	85.1	83.7	82.6	79.7	76.6	75.1
67.5°	89.4	84.8	79.6	76.1	73.8	71.6	69.0	67.0	64.3	62.6	61.6
70°	78.9	74.5	70.0	66.8	64.2	62.1	59.3	57.9	55.9	55.2	54.2
72.5°	68.9	64.7	60.7	57.6	55.0	53.3	51.0	49.7	48.8	48.5	47.6
75°	53.6	50.4	47.3	44.6	42.5	41.3	40.4	39.4	39.0	37.3	36.3
77.5°	39.1	36.9	35.1	33.1	31.6	30.8	28.9	27.9	27.2	26.4	26.2
80°	30.5	28.9	27.0	25.8	23.7	23.0	22.2	22.0	21.8	21.6	21.4
82.5°	22.9	21.4	19.5	18.8	18.2	17.7	17.3	17.0	16.9	17.0	17.0
85°	11.6	10.8	10.8	10.6	10.4	10.2	10.0	10.0	9.9	10.0	9.9
87.5°	5.5	5.6	5.9	5.7	6.1	6.4	6.4	6.5	6.8	6.8	6.8
90°	8.2	9.5	10.6	11.7	12.9	14.0	14.8	15.7	16.6	17.4	18.0
92.5°	8.4	9.0	10.1	11.3	12.4	13.5	14.3	15.2	16.1	16.9	17.4
95°	15.8	13.5	13.6	13.8	13.9	14.0	14.8	15.7	16.6	17.4	17.9
97.5°	86.5	80.1	64.2	48.4	32.6	16.8	16.9	17.0	17.1	17.2	17.3
100°	114.7	106.2	86.7	67.2	47.6	28.0	25.6	23.2	20.8	18.4	17.3
102.5°	145.7	145.4	142.8	140.2	137.7	135.2	109.2	83.2	57.2	31.2	18.3
105°	195.3	196.1	196.7	197.5	198.2	198.9	200.2	201.5	202.7	204.0	202.1
107.5°	243.4	244.1	245.1	246.1	247.0	248.0	248.6	249.2	249.8	250.5	251.0
110°	277.1	277.7	278.6	279.4	280.3	281.1	281.4	281.7	282.0	282.3	282.6



TEST NUMBER: P332877-930

CATALOG NUMBER: S124RDIP-S350D810U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	311.1	311.7	312.1	312.4	312.8	313.2	313.2	313.2	313.1	313.0	313.2
115°	360.0	360.1	360.0	359.8	359.7	359.5	359.8	360.1	360.4	360.7	360.9
117.5°	405.8	406.3	406.5	406.8	407.2	407.5	407.4	407.3	407.3	407.2	407.2
120°	436.3	436.6	436.4	436.3	436.2	436.0	436.3	436.6	436.9	437.2	437.2
122.5°	464.1	464.3	464.5	464.7	464.9	465.1	465.3	465.5	465.6	465.8	465.7
125°	505.9	506.0	505.7	505.5	505.2	504.9	505.3	505.7	506.1	506.5	506.9
127.5°	542.9	543.3	544.0	544.6	545.3	545.9	545.8	545.8	545.7	545.6	545.5
130°	567.9	568.2	568.6	569.1	569.5	569.9	570.1	570.2	570.3	570.5	570.5
132.5°	591.3	591.7	592.2	592.8	593.3	593.9	594.0	594.2	594.3	594.4	594.4
135°	624.2	624.4	624.9	625.5	626.1	626.6	626.9	627.2	627.5	627.8	628.0
137.5°	655.4	655.7	656.4	657.0	657.6	658.3	658.6	658.8	659.2	659.5	659.6
140°	676.2	676.5	676.8	677.1	677.4	677.6	678.1	678.5	678.9	679.3	679.6
142.5°	695.0	695.3	695.5	695.7	695.9	696.0	696.3	696.6	696.9	697.2	697.4
145°	722.0	722.3	722.3	722.3	722.3	722.3	722.4	722.5	722.7	722.8	723.0
147.5°	745.3	745.7	745.5	745.3	745.2	745.1	745.2	745.3	745.4	745.5	745.7
150°	760.2	760.4	760.3	760.2	760.0	759.9	759.9	759.9	759.9	759.9	759.9
152.5°	773.1	773.1	772.9	772.7	772.3	772.1	772.3	772.6	772.8	773.0	773.1
155°	790.4	790.3	789.9	789.4	789.0	788.6	789.1	789.7	790.3	790.8	790.9
157.5°	805.2	804.9	804.4	804.0	803.5	803.0	803.7	804.5	805.2	805.9	805.9
160°	813.0	812.7	812.6	812.4	812.3	812.1	813.0	813.8	814.7	815.5	815.5
162.5°	820.7	820.4	820.2	820.1	819.9	819.8	820.7	821.5	822.3	823.2	823.1
165°	830.4	830.0	830.0	830.0	830.0	830.0	831.1	832.3	833.4	834.5	834.5
167.5°	838.4	838.0	837.9	837.8	837.7	837.6	838.9	840.2	841.4	842.6	842.5
170°	842.5	842.2	842.3	842.4	842.6	842.8	843.8	845.0	846.1	847.3	847.1
172.5°	845.6	845.2	845.4	845.5	845.6	845.8	846.9	848.1	849.2	850.4	850.1
175°	848.9	848.6	848.7	848.8	849.0	849.1	850.4	851.7	853.0	854.2	854.0
177.5°	850.7	850.4	850.6	850.8	851.1	851.3	852.2	853.1	854.0	854.9	854.7
180°	852.3	852.3	852.3	852.3	852.3	852.3	852.3	852.3	852.3	852.3	852.3



TEST NUMBER: P332877-930

CATALOG NUMBER: S124RDIP-S350D810U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9
2.5°	457.1	457.5	456.4	456.1	456.4	457.5	457.1	458.0	458.2	459.5	459.0
5°	424.1	423.7	422.7	423.0	422.7	423.7	424.1	425.7	426.4	429.5	429.1
7.5°	395.8	394.4	394.8	393.2	394.8	394.4	395.8	397.2	399.6	401.0	404.3
10°	378.5	376.4	374.7	373.2	374.7	376.4	378.5	379.4	382.6	384.2	387.4
12.5°	355.0	353.1	350.8	351.2	350.8	353.1	355.0	358.3	362.6	365.8	371.0
15°	321.5	318.5	314.0	314.5	314.0	318.5	321.5	324.0	328.2	335.6	339.0
17.5°	293.1	293.1	291.0	291.6	291.0	293.1	293.1	296.5	298.7	303.4	308.7
20°	278.4	277.1	277.3	276.7	277.3	277.1	278.4	282.5	284.8	288.0	293.8
22.5°	268.2	266.6	265.2	264.1	265.2	266.6	268.2	269.4	272.5	275.6	280.3
25°	251.0	249.9	248.2	247.8	248.2	249.9	251.0	252.7	254.3	258.4	261.2
27.5°	235.9	235.7	235.0	234.1	235.0	235.7	235.9	237.4	239.5	242.1	245.7
30°	227.1	226.7	226.3	225.8	226.3	226.7	227.1	228.7	230.2	232.3	235.2
32.5°	219.2	219.0	218.6	218.7	218.6	219.0	219.2	220.0	220.9	223.6	225.9
35°	208.0	207.8	207.4	207.2	207.4	207.8	208.0	208.8	209.4	210.1	212.1
37.5°	197.5	198.0	197.8	197.7	197.8	198.0	197.5	197.7	197.1	198.4	199.7
40°	190.3	190.5	190.9	190.6	190.9	190.5	190.3	190.5	190.5	190.5	191.6
42.5°	184.3	184.3	184.8	184.2	184.8	184.3	184.3	183.5	182.5	182.7	183.1
45°	173.5	174.6	174.4	174.4	174.4	174.6	173.5	172.1	171.9	171.1	171.1
47.5°	161.7	162.7	163.0	162.9	163.0	162.7	161.7	161.2	160.3	159.6	159.5
50°	154.0	153.6	154.2	154.0	154.2	153.6	154.0	153.0	151.6	151.6	151.2
52.5°	144.6	144.6	144.6	144.4	144.6	144.6	144.6	144.1	143.5	142.8	142.6
55°	130.0	130.3	129.9	130.0	129.9	130.3	130.0	129.9	129.9	129.5	129.9
57.5°	114.3	113.4	113.7	113.3	113.7	113.4	114.3	115.1	115.4	115.5	116.1
60°	103.1	101.5	101.1	100.4	101.1	101.5	103.1	104.9	105.7	106.2	106.7
62.5°	90.4	89.3	88.0	88.6	88.0	89.3	90.4	92.5	94.2	95.5	96.9
65°	73.5	72.7	72.2	73.0	72.2	72.7	73.5	75.1	76.6	79.7	82.6
67.5°	60.8	60.4	60.4	60.1	60.4	60.4	60.8	61.6	62.6	64.3	67.0
70°	54.2	53.6	53.6	53.2	53.6	53.6	54.2	54.2	55.2	55.9	57.9
72.5°	47.5	46.9	47.0	46.8	47.0	46.9	47.5	47.6	48.5	48.8	49.7
75°	35.1	34.2	34.2	34.3	34.2	34.2	35.1	36.3	37.3	39.0	39.4
77.5°	26.2	26.0	26.3	25.9	26.3	26.0	26.2	26.2	26.4	27.2	27.9
80°	21.4	21.2	21.0	21.6	21.0	21.2	21.4	21.4	21.6	21.8	22.0
82.5°	16.6	16.6	16.6	17.3	16.6	16.6	16.6	17.0	17.0	16.9	17.0
85°	10.0	9.6	10.0	9.6	10.0	9.6	10.0	9.9	10.0	9.9	10.0
87.5°	7.2	7.1	7.0	7.3	7.0	7.1	7.2	6.8	6.8	6.8	6.5
90°	18.3	18.6	18.8	19.2	18.8	18.6	18.3	18.0	17.4	16.6	15.7
92.5°	17.4	17.4	17.5	17.6	17.5	17.4	17.4	17.4	16.9	16.1	15.2
95°	18.1	18.2	18.3	18.5	18.3	18.2	18.1	17.9	17.4	16.6	15.7
97.5°	17.4	17.5	17.7	17.9	17.7	17.5	17.4	17.3	17.2	17.1	17.0
100°	17.4	17.5	17.7	17.9	17.7	17.5	17.4	17.3	18.4	20.8	23.2
102.5°	18.3	18.3	18.3	18.3	18.3	18.3	18.3	18.3	31.2	57.2	83.2
105°	197.0	191.8	186.8	181.6	186.8	191.8	197.0	202.1	204.0	202.7	201.5
107.5°	251.6	252.1	252.7	253.2	252.7	252.1	251.6	251.0	250.5	249.8	249.2
110°	283.1	283.5	283.9	284.3	283.9	283.5	283.1	282.6	282.3	282.0	281.7



TEST NUMBER: P332877-930

CATALOG NUMBER: S124RDIP-S350D810U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	313.8	314.4	314.9	315.4	314.9	314.4	313.8	313.2	313.0	313.1	313.2
115°	360.9	360.9	360.9	360.9	360.9	360.9	360.9	360.9	360.7	360.4	360.1
117.5°	407.2	407.1	407.0	407.0	407.0	407.1	407.2	407.2	407.2	407.3	407.3
120°	436.9	436.6	436.3	436.0	436.3	436.6	436.9	437.2	437.2	436.9	436.6
122.5°	465.5	465.1	464.9	464.6	464.9	465.1	465.5	465.7	465.8	465.6	465.5
125°	507.0	507.1	507.3	507.4	507.3	507.1	507.0	506.9	506.5	506.1	505.7
127.5°	545.4	545.3	545.2	545.0	545.2	545.3	545.4	545.5	545.6	545.7	545.8
130°	570.5	570.5	570.5	570.5	570.5	570.5	570.5	570.5	570.5	570.3	570.2
132.5°	594.4	594.2	594.1	594.0	594.1	594.2	594.4	594.4	594.4	594.3	594.2
135°	628.4	628.6	628.9	629.2	628.9	628.6	628.4	628.0	627.8	627.5	627.2
137.5°	659.5	659.4	659.3	659.3	659.3	659.4	659.5	659.6	659.5	659.2	658.8
140°	679.8	679.9	680.0	680.2	680.0	679.9	679.8	679.6	679.3	678.9	678.5
142.5°	697.4	697.5	697.5	697.5	697.5	697.5	697.4	697.4	697.2	696.9	696.6
145°	723.3	723.6	723.9	724.1	723.9	723.6	723.3	723.0	722.8	722.7	722.5
147.5°	745.8	745.9	746.1	746.2	746.1	745.9	745.8	745.7	745.5	745.4	745.3
150°	760.1	760.2	760.3	760.5	760.3	760.2	760.1	759.9	759.9	759.9	759.9
152.5°	773.0	772.9	772.8	772.7	772.8	772.9	773.0	773.1	773.0	772.8	772.6
155°	790.4	790.0	789.6	789.2	789.6	790.0	790.4	790.9	790.8	790.3	789.7
157.5°	805.2	804.5	803.7	803.0	803.7	804.5	805.2	805.9	805.9	805.2	804.5
160°	814.7	813.8	813.0	812.1	813.0	813.8	814.7	815.5	815.5	814.7	813.8
162.5°	822.1	821.2	820.3	819.3	820.3	821.2	822.1	823.1	823.2	822.3	821.5
165°	833.2	831.9	830.6	829.3	830.6	831.9	833.2	834.5	834.5	833.4	832.3
167.5°	841.1	839.7	838.3	836.9	838.3	839.7	841.1	842.5	842.6	841.4	840.2
170°	845.7	844.3	842.9	841.5	842.9	844.3	845.7	847.1	847.3	846.1	845.0
172.5°	848.6	847.1	845.5	844.0	845.5	847.1	848.6	850.1	850.4	849.2	848.1
175°	852.3	850.6	848.9	847.2	848.9	850.6	852.3	854.0	854.2	853.0	851.7
177.5°	853.3	852.0	850.6	849.2	850.6	852.0	853.3	854.7	854.9	854.0	853.1
180°	852.3	852.3	852.3	852.3	852.3	852.3	852.3	852.3	852.3	852.3	852.3



TEST NUMBER: P332877-930

CATALOG NUMBER: S124RDIP-S350D810U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9
2.5°	458.0	459.2	461.6	464.4	466.8	468.7	470.3	472.5	474.4	477.2	479.8
5°	430.3	433.0	436.8	441.5	447.3	451.1	455.9	460.2	466.4	472.5	478.5
7.5°	405.9	408.9	414.6	420.9	427.8	434.1	439.9	447.4	455.5	464.6	474.6
10°	390.1	393.5	400.1	407.5	415.6	421.8	429.5	438.4	447.7	458.7	471.0
12.5°	375.9	379.1	387.2	394.7	403.1	409.9	418.9	427.9	440.3	452.2	466.2
15°	348.3	356.6	365.8	374.7	384.7	393.1	403.8	413.1	424.9	441.6	457.7
17.5°	317.6	326.4	337.9	351.6	365.1	375.4	386.3	397.8	411.8	428.9	447.4
20°	299.6	306.8	319.5	334.8	350.4	364.7	374.7	387.4	401.9	420.4	439.5
22.5°	286.3	292.3	302.2	317.5	334.4	350.9	363.8	376.3	392.3	410.9	431.7
25°	266.1	272.6	281.4	291.7	311.0	328.6	345.4	359.9	376.8	395.3	418.5
27.5°	249.3	255.0	263.0	273.9	286.8	306.1	326.5	343.0	360.4	380.3	403.5
30°	239.5	244.1	250.6	261.6	274.0	291.4	312.0	331.3	348.9	369.5	393.6
32.5°	229.1	234.1	240.4	249.2	262.4	277.0	297.7	318.8	337.5	358.6	382.2
35°	215.3	219.2	225.0	233.8	245.8	258.5	276.9	298.7	318.4	341.0	363.5
37.5°	201.4	205.9	210.5	218.4	228.2	241.9	256.9	279.2	301.0	321.6	343.6
40°	193.6	196.2	201.2	207.7	218.0	230.2	244.3	266.1	287.9	308.3	330.5
42.5°	184.7	187.8	192.0	198.4	207.7	219.6	233.3	252.2	274.9	294.7	315.0
45°	172.5	174.2	178.5	183.8	191.6	203.6	216.3	233.1	254.5	273.5	291.1
47.5°	160.1	161.7	164.3	169.3	177.9	187.5	199.4	214.5	233.3	252.2	267.2
50°	151.6	153.0	155.6	160.1	167.9	177.3	189.1	202.6	219.4	237.5	250.1
52.5°	143.2	143.9	146.3	151.5	158.0	167.3	177.8	190.3	205.9	221.0	233.7
55°	129.6	131.4	133.0	136.8	143.0	151.9	161.3	173.1	185.2	198.0	208.8
57.5°	115.6	117.5	119.7	123.1	128.0	136.2	144.7	154.3	164.7	175.2	184.3
60°	106.3	108.0	110.0	113.8	118.3	124.8	134.1	142.4	150.3	160.0	169.0
62.5°	97.2	99.0	101.2	104.3	108.5	114.8	122.5	129.7	137.9	146.3	153.1
65°	83.7	85.1	86.8	89.8	93.8	99.4	105.7	111.4	118.7	124.8	131.0
67.5°	69.0	71.6	73.8	76.1	79.6	84.8	89.4	94.8	99.8	104.4	110.0
70°	59.3	62.1	64.2	66.8	70.0	74.5	78.9	82.6	86.7	91.1	96.1
72.5°	51.0	53.3	55.0	57.6	60.7	64.7	68.9	71.9	75.3	78.3	83.2
75°	40.4	41.3	42.5	44.6	47.3	50.4	53.6	56.3	58.3	61.0	64.4
77.5°	28.9	30.8	31.6	33.1	35.1	36.9	39.1	41.4	43.3	44.2	46.9
80°	22.2	23.0	23.7	25.8	27.0	28.9	30.5	32.6	33.3	34.3	36.9
82.5°	17.3	17.7	18.2	18.8	19.5	21.4	22.9	24.3	25.0	25.4	27.3
85°	10.0	10.2	10.4	10.6	10.8	10.8	11.6	12.6	13.9	13.9	14.5
87.5°	6.4	6.4	6.1	5.7	5.9	5.6	5.5	5.1	5.3	5.5	5.6
90°	14.8	14.0	12.9	11.7	10.6	9.5	8.2	6.6	5.1	3.5	1.9
92.5°	14.3	13.5	12.4	11.3	10.1	9.0	8.4	8.3	8.2	8.2	8.1
95°	14.8	14.0	13.9	13.8	13.6	13.5	15.8	20.6	25.4	30.2	35.1
97.5°	16.9	16.8	32.6	48.4	64.2	80.1	86.5	83.5	80.5	77.5	74.4
100°	25.6	28.0	47.6	67.2	86.7	106.2	114.7	112.2	109.7	107.1	104.5
102.5°	109.2	135.2	137.7	140.2	142.8	145.4	145.7	143.8	141.9	140.1	138.2
105°	200.2	198.9	198.2	197.5	196.7	196.1	195.3	194.4	193.6	192.7	191.8
107.5°	248.6	248.0	247.0	246.1	245.1	244.1	243.4	243.0	242.6	242.1	241.7
110°	281.4	281.1	280.3	279.4	278.6	277.7	277.1	276.6	276.2	275.8	275.4



TEST NUMBER: P332877-930

CATALOG NUMBER: S124RDIP-S350D810U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	313.2	313.2	312.8	312.4	312.1	311.7	311.1	310.3	309.6	308.8	308.0
115°	359.8	359.5	359.7	359.8	360.0	360.1	360.0	359.5	359.1	358.7	358.2
117.5°	407.4	407.5	407.2	406.8	406.5	406.3	405.8	405.2	404.6	404.1	403.5
120°	436.3	436.0	436.2	436.3	436.4	436.6	436.3	435.9	435.3	434.7	434.1
122.5°	465.3	465.1	464.9	464.7	464.5	464.3	464.1	463.7	463.3	463.0	462.7
125°	505.3	504.9	505.2	505.5	505.7	506.0	505.9	505.3	504.8	504.2	503.6
127.5°	545.8	545.9	545.3	544.6	544.0	543.3	542.9	542.8	542.7	542.5	542.3
130°	570.1	569.9	569.5	569.1	568.6	568.2	567.9	567.8	567.6	567.5	567.4
132.5°	594.0	593.9	593.3	592.8	592.2	591.7	591.3	591.1	590.8	590.5	590.3
135°	626.9	626.6	626.1	625.5	624.9	624.4	624.2	624.3	624.4	624.6	624.8
137.5°	658.6	658.3	657.6	657.0	656.4	655.7	655.4	655.3	655.3	655.3	655.2
140°	678.1	677.6	677.4	677.1	676.8	676.5	676.2	676.0	675.6	675.4	675.1
142.5°	696.3	696.0	695.9	695.7	695.5	695.3	695.0	694.5	694.0	693.4	692.9
145°	722.4	722.3	722.3	722.3	722.3	722.3	722.0	721.6	721.2	720.8	720.3
147.5°	745.2	745.1	745.2	745.3	745.5	745.7	745.3	744.5	743.7	743.0	742.2
150°	759.9	759.9	760.0	760.2	760.3	760.4	760.2	759.7	759.1	758.6	758.0
152.5°	772.3	772.1	772.3	772.7	772.9	773.1	773.1	772.6	772.1	771.7	771.2
155°	789.1	788.6	789.0	789.4	789.9	790.3	790.4	790.3	790.1	789.9	789.9
157.5°	803.7	803.0	803.5	804.0	804.4	804.9	805.2	805.3	805.4	805.4	805.5
160°	813.0	812.1	812.3	812.4	812.6	812.7	813.0	813.4	813.8	814.2	814.7
162.5°	820.7	819.8	819.9	820.1	820.2	820.4	820.7	821.3	821.7	822.3	822.9
165°	831.1	830.0	830.0	830.0	830.0	830.0	830.4	831.0	831.8	832.5	833.2
167.5°	838.9	837.6	837.7	837.8	837.9	838.0	838.4	839.1	839.8	840.6	841.3
170°	843.8	842.8	842.6	842.4	842.3	842.2	842.5	843.3	844.2	845.1	846.0
172.5°	846.9	845.8	845.6	845.5	845.4	845.2	845.6	846.4	847.3	848.2	849.0
175°	850.4	849.1	849.0	848.8	848.7	848.6	848.9	849.8	850.6	851.4	852.3
177.5°	852.2	851.3	851.1	850.8	850.6	850.4	850.7	851.4	852.2	853.0	853.9
180°	852.3	852.3	852.3	852.3	852.3	852.3	852.3	852.3	852.3	852.3	852.3



TEST NUMBER: P332877-930

CATALOG NUMBER: S124RDIP-S350D810U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9
2.5°	481.8	483.2	484.8	487.7	490.2	491.3	493.4	495.0	494.5	496.7	500.3
5°	483.7	488.9	495.0	501.1	508.0	513.8	518.4	523.1	526.8	531.2	537.8
7.5°	483.4	492.7	502.8	513.8	525.2	535.1	544.1	553.4	561.7	570.6	582.4
10°	482.2	494.6	507.1	521.5	536.1	549.8	562.1	573.6	584.7	596.4	611.3
12.5°	480.8	495.0	510.1	527.6	545.6	562.1	576.6	593.3	607.1	622.2	639.4
15°	474.7	493.7	514.5	537.0	558.6	580.8	600.6	621.1	640.3	658.4	680.0
17.5°	467.7	489.7	514.0	540.7	566.6	593.6	617.3	643.0	662.5	686.9	706.9
20°	461.9	485.7	511.7	541.6	571.1	601.0	627.1	653.4	675.3	699.9	725.3
22.5°	455.0	481.0	509.2	540.2	571.1	603.8	632.7	658.8	686.0	713.5	739.8
25°	443.8	470.8	500.8	534.7	570.2	603.6	634.5	666.8	696.2	726.1	749.7
27.5°	430.1	458.4	489.9	525.0	561.4	595.6	631.9	666.5	696.0	724.8	745.3
30°	419.1	449.0	479.3	514.8	552.6	589.3	628.3	662.8	693.9	719.7	731.3
32.5°	407.8	436.2	467.4	503.4	542.1	581.6	620.2	655.6	684.3	699.8	700.1
35°	388.2	414.8	447.3	482.6	522.4	565.2	604.3	639.0	656.6	657.9	639.0
37.5°	366.9	391.3	421.8	457.2	500.8	543.4	583.3	606.5	612.4	592.7	557.8
40°	351.6	374.1	403.7	439.9	483.1	527.2	563.6	580.6	574.5	542.6	503.6
42.5°	335.5	356.5	385.0	420.8	464.1	508.7	539.7	548.8	532.5	495.7	450.0
45°	309.3	328.6	356.8	392.9	434.6	476.2	499.8	495.1	467.9	424.3	373.2
47.5°	282.0	300.7	326.0	359.4	402.1	438.1	454.0	440.0	401.3	353.4	311.8
50°	264.0	283.1	306.4	338.3	377.2	412.0	422.2	401.0	357.9	311.9	273.6
52.5°	246.2	262.5	285.4	316.2	353.4	382.8	388.2	363.8	319.4	278.0	244.1
55°	219.2	234.1	253.3	282.3	314.5	339.4	336.5	305.1	264.7	229.4	202.8
57.5°	193.1	204.2	222.1	249.2	277.5	294.2	283.6	256.8	219.2	190.3	167.9
60°	175.8	186.2	202.8	226.5	251.4	260.9	252.0	222.9	193.1	166.7	147.8
62.5°	159.4	168.6	182.9	204.9	225.0	230.6	221.1	195.7	168.9	146.3	130.7
65°	135.7	144.1	156.3	171.9	185.8	188.5	182.4	156.3	136.1	117.2	106.3
67.5°	114.1	119.6	129.1	142.6	150.0	151.6	139.7	123.3	105.4	93.8	85.7
70°	99.5	103.5	112.3	119.6	125.6	125.8	114.8	101.7	88.0	78.5	72.6
72.5°	85.5	89.2	96.0	100.9	105.6	104.0	94.0	83.6	72.6	65.4	61.0
75°	66.0	69.3	72.7	75.1	75.1	73.1	65.8	58.0	51.7	47.5	46.1
77.5°	47.9	50.6	51.9	51.4	50.8	47.8	43.1	38.1	35.8	33.8	32.8
80°	37.7	38.8	39.1	38.2	37.0	33.6	30.5	28.4	26.3	25.4	25.1
82.5°	27.9	28.9	27.9	28.2	25.6	22.7	21.0	20.3	19.5	19.2	18.8
85°	14.8	14.7	14.3	13.3	11.6	11.2	11.0	10.8	10.4	10.6	10.2
87.5°	5.8	5.6	5.3	5.5	5.8	5.7	6.0	6.3	6.5	6.5	7.0
90°	3.5	5.1	6.6	8.2	9.5	10.6	11.7	12.9	14.0	14.8	15.7
92.5°	8.2	8.2	8.3	8.4	9.0	10.1	11.3	12.4	13.5	14.3	15.2
95°	30.2	25.4	20.6	15.8	13.5	13.6	13.8	13.9	14.0	14.8	15.7
97.5°	77.5	80.5	83.5	86.5	80.1	64.2	48.4	32.6	16.8	16.9	17.0
100°	107.1	109.7	112.2	114.7	106.2	86.7	67.2	47.6	28.0	25.6	23.2
102.5°	140.1	141.9	143.8	145.7	145.4	142.8	140.2	137.7	135.2	109.2	83.2
105°	192.7	193.6	194.4	195.3	196.1	196.7	197.5	198.2	198.9	200.2	201.5
107.5°	242.1	242.6	243.0	243.4	244.1	245.1	246.1	247.0	248.0	248.6	249.2
110°	275.8	276.2	276.6	277.1	277.7	278.6	279.4	280.3	281.1	281.4	281.7





TEST NUMBER: P332877-930

CATALOG NUMBER: S124RDIP-S350D810U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	308.8	309.6	310.3	311.1	311.7	312.1	312.4	312.8	313.2	313.2	313.2
115°	358.7	359.1	359.5	360.0	360.1	360.0	359.8	359.7	359.5	359.8	360.1
117.5°	404.1	404.6	405.2	405.8	406.3	406.5	406.8	407.2	407.5	407.4	407.3
120°	434.7	435.3	435.9	436.3	436.6	436.4	436.3	436.2	436.0	436.3	436.6
122.5°	463.0	463.3	463.7	464.1	464.3	464.5	464.7	464.9	465.1	465.3	465.5
125°	504.2	504.8	505.3	505.9	506.0	505.7	505.5	505.2	504.9	505.3	505.7
127.5°	542.5	542.7	542.8	542.9	543.3	544.0	544.6	545.3	545.9	545.8	545.8
130°	567.5	567.6	567.8	567.9	568.2	568.6	569.1	569.5	569.9	570.1	570.2
132.5°	590.5	590.8	591.1	591.3	591.7	592.2	592.8	593.3	593.9	594.0	594.2
135°	624.6	624.4	624.3	624.2	624.4	624.9	625.5	626.1	626.6	626.9	627.2
137.5°	655.3	655.3	655.3	655.4	655.7	656.4	657.0	657.6	658.3	658.6	658.8
140°	675.4	675.6	676.0	676.2	676.5	676.8	677.1	677.4	677.6	678.1	678.5
142.5°	693.4	694.0	694.5	695.0	695.3	695.5	695.7	695.9	696.0	696.3	696.6
145°	720.8	721.2	721.6	722.0	722.3	722.3	722.3	722.3	722.3	722.4	722.5
147.5°	743.0	743.7	744.5	745.3	745.7	745.5	745.3	745.2	745.1	745.2	745.3
150°	758.6	759.1	759.7	760.2	760.4	760.3	760.2	760.0	759.9	759.9	759.9
152.5°	771.7	772.1	772.6	773.1	773.1	772.9	772.7	772.3	772.1	772.3	772.6
155°	789.9	790.1	790.3	790.4	790.3	789.9	789.4	789.0	788.6	789.1	789.7
157.5°	805.4	805.4	805.3	805.2	804.9	804.4	804.0	803.5	803.0	803.7	804.5
160°	814.2	813.8	813.4	813.0	812.7	812.6	812.4	812.3	812.1	813.0	813.8
162.5°	822.3	821.7	821.3	820.7	820.4	820.2	820.1	819.9	819.8	820.7	821.5
165°	832.5	831.8	831.0	830.4	830.0	830.0	830.0	830.0	830.0	831.1	832.3
167.5°	840.6	839.8	839.1	838.4	838.0	837.9	837.8	837.7	837.6	838.9	840.2
170°	845.1	844.2	843.3	842.5	842.2	842.3	842.4	842.6	842.8	843.8	845.0
172.5°	848.2	847.3	846.4	845.6	845.2	845.4	845.5	845.6	845.8	846.9	848.1
175°	851.4	850.6	849.8	848.9	848.6	848.7	848.8	849.0	849.1	850.4	851.7
177.5°	853.0	852.2	851.4	850.7	850.4	850.6	850.8	851.1	851.3	852.2	853.1
180°	852.3	852.3	852.3	852.3	852.3	852.3	852.3	852.3	852.3	852.3	852.3



TEST NUMBER: P332877-930

CATALOG NUMBER: S124RDIP-S350D810U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	478.9	478.9	478.9	478.9	478.9	478.9	478.9
2.5°	502.4	503.0	503.4	505.0	505.2	506.5	505.2
5°	544.0	546.7	550.9	555.1	555.5	558.2	553.4
7.5°	590.5	596.8	600.7	607.6	610.3	612.0	609.2
10°	622.6	628.4	638.7	643.7	648.7	649.5	647.2
12.5°	653.7	662.8	670.9	680.4	680.2	687.0	684.5
15°	695.0	704.5	715.7	726.3	730.1	730.1	733.2
17.5°	724.5	741.8	753.4	761.7	770.9	772.4	771.4
20°	744.4	763.1	775.5	786.3	792.5	794.2	794.2
22.5°	759.2	775.2	787.3	797.0	802.0	804.0	803.5
25°	769.5	783.2	790.5	793.4	794.8	794.4	790.8
27.5°	755.5	754.8	750.2	741.4	734.7	730.6	725.9
30°	728.6	718.5	706.9	694.2	677.8	665.3	661.5
32.5°	688.6	666.1	646.5	625.3	607.6	595.1	589.8
35°	611.3	575.6	546.4	521.0	502.5	490.9	487.0
37.5°	519.5	484.9	448.9	424.2	408.8	397.1	392.8
40°	461.1	423.5	392.1	368.9	353.1	341.7	341.5
42.5°	407.9	371.9	342.3	325.7	308.7	301.1	301.1
45°	334.0	305.2	280.1	267.0	256.8	250.6	248.9
47.5°	276.5	252.7	236.0	225.6	217.3	213.4	210.8
50°	244.3	223.5	210.1	201.1	196.4	191.4	191.0
52.5°	217.4	200.6	190.2	182.9	177.0	174.0	174.1
55°	182.7	169.4	162.1	156.5	151.9	149.5	148.5
57.5°	153.9	144.0	138.6	133.5	131.5	129.7	129.2
60°	136.1	129.3	124.3	120.2	117.3	116.8	116.5
62.5°	121.2	114.1	110.7	107.5	105.4	104.5	104.2
65°	100.0	94.7	91.6	89.1	88.4	87.0	86.8
67.5°	80.6	77.5	75.4	73.7	72.6	72.6	72.6
70°	68.7	66.9	65.2	64.2	63.7	63.3	63.3
72.5°	58.5	57.2	55.8	55.3	55.2	54.8	54.6
75°	44.6	43.2	43.5	42.5	41.7	40.7	40.1
77.5°	31.6	30.7	30.4	30.3	29.7	29.6	29.8
80°	24.5	23.6	23.3	23.6	23.3	22.7	22.7
82.5°	18.7	17.9	17.6	17.5	17.4	17.5	17.2
85°	10.0	9.6	9.6	9.6	10.0	9.9	9.6
87.5°	6.8	6.8	7.2	7.0	7.1	7.0	7.3
90°	16.6	17.4	18.0	18.3	18.6	18.8	19.2
92.5°	16.1	16.9	17.4	17.4	17.4	17.5	17.6
95°	16.6	17.4	17.9	18.1	18.2	18.3	18.5
97.5°	17.1	17.2	17.3	17.4	17.5	17.7	17.9
100°	20.8	18.4	17.3	17.4	17.5	17.7	17.9
102.5°	57.2	31.2	18.3	18.3	18.3	18.3	18.3
105°	202.7	204.0	202.1	197.0	191.8	186.8	181.6
107.5°	249.8	250.5	251.0	251.6	252.1	252.7	253.2
110°	282.0	282.3	282.6	283.1	283.5	283.9	284.3



TEST NUMBER: P332877-930

CATALOG NUMBER: S124RDIP-S350D810U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	313.1	313.0	313.2	313.8	314.4	314.9	315.4
115°	360.4	360.7	360.9	360.9	360.9	360.9	360.9
117.5°	407.3	407.2	407.2	407.2	407.1	407.0	407.0
120°	436.9	437.2	437.2	436.9	436.6	436.3	436.0
122.5°	465.6	465.8	465.7	465.5	465.1	464.9	464.6
125°	506.1	506.5	506.9	507.0	507.1	507.3	507.4
127.5°	545.7	545.6	545.5	545.4	545.3	545.2	545.0
130°	570.3	570.5	570.5	570.5	570.5	570.5	570.5
132.5°	594.3	594.4	594.4	594.4	594.2	594.1	594.0
135°	627.5	627.8	628.0	628.4	628.6	628.9	629.2
137.5°	659.2	659.5	659.6	659.5	659.4	659.3	659.3
140°	678.9	679.3	679.6	679.8	679.9	680.0	680.2
142.5°	696.9	697.2	697.4	697.4	697.5	697.5	697.5
145°	722.7	722.8	723.0	723.3	723.6	723.9	724.1
147.5°	745.4	745.5	745.7	745.8	745.9	746.1	746.2
150°	759.9	759.9	759.9	760.1	760.2	760.3	760.5
152.5°	772.8	773.0	773.1	773.0	772.9	772.8	772.7
155°	790.3	790.8	790.9	790.4	790.0	789.6	789.2
157.5°	805.2	805.9	805.9	805.2	804.5	803.7	803.0
160°	814.7	815.5	815.5	814.7	813.8	813.0	812.1
162.5°	822.3	823.2	823.1	822.1	821.2	820.3	819.3
165°	833.4	834.5	834.5	833.2	831.9	830.6	829.3
167.5°	841.4	842.6	842.5	841.1	839.7	838.3	836.9
170°	846.1	847.3	847.1	845.7	844.3	842.9	841.5
172.5°	849.2	850.4	850.1	848.6	847.1	845.5	844.0
175°	853.0	854.2	854.0	852.3	850.6	848.9	847.2
177.5°	854.0	854.9	854.7	853.3	852.0	850.6	849.2
180°	852.3	852.3	852.3	852.3	852.3	852.3	852.3

(END OF REPORT)