

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332921-930

Luminaire Tested: **S124RDIP-S575D1205U930-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332921-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIP-S575D1205U930-4F0-1E-UDD-A4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 575 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5499.9 lumens  
Efficiency: N/A  
Efficacy: 111.3 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 49.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332921-930

CATALOG NUMBER: S124RDIP-S575D1205U930-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P332921-930

CATALOG NUMBER: S124RDIP-S575D1205U930-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	43	43	43	36
1	95	91	87	84	86	83	79	77	67	65	63	52	51	50	39	38	37	31
2	87	80	74	69	78	72	68	63	59	55	52	46	44	42	35	33	32	27
3	79	70	63	58	72	64	58	53	52	48	44	41	38	36	31	29	28	23
4	73	62	55	49	66	57	50	45	46	42	38	37	34	31	28	26	24	20
5	67	56	48	42	60	51	44	39	42	37	33	33	30	27	25	23	21	17
6	61	50	42	37	56	46	39	34	38	32	29	30	26	24	23	20	19	15
7	57	45	37	32	51	41	35	30	34	29	25	27	24	21	21	18	17	14
8	53	41	33	28	48	37	31	26	31	26	22	25	21	19	19	17	15	12
9	49	37	30	25	44	34	28	23	28	23	20	23	19	17	18	15	13	11
10	46	34	27	22	41	31	25	21	26	21	18	21	18	15	17	14	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	6356	6356	6356	6356
5°	7373	6375	5635	6375
10°	8722	6347	5029	6347
15°	10074	6288	4322	6288
20°	11217	6208	3908	6208
25°	11580	6128	3628	6128
30°	10137	6032	3459	6032
35°	7890	5889	3358	5889
40°	5917	5727	3303	5727
45°	4672	5465	3273	5465
50°	3945	5163	3180	5163
55°	3438	4830	3009	4830
60°	3094	4487	2662	4487
65°	2728	4115	2290	4115
70°	2455	3729	2068	3729
75°	2059	3306	1762	3306
80°	1739	2817	1650	2817
85°	1473	2205	1473	2205



TEST NUMBER: P332921-930

CATALOG NUMBER: S124RDIP-S575D1205U930-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	76.3	1.4
10°-20°	230.1	4.2
20°-30°	359.9	6.5
30°-40°	400.1	7.3
40°-50°	355.0	6.5
50°-60°	276.6	5.0
60°-70°	181.1	3.3
70°-80°	89.1	1.6
80°-90°	24.6	0.4
90°-100°	348.3	6.3
100°-110°	724.9	13.2
110°-120°	649.3	11.8
120°-130°	546.2	9.9
130°-140°	455.4	8.3
140°-150°	347.9	6.3
150°-160°	244.5	4.4
160°-170°	143.8	2.6
170°-180°	46.8	0.9
0°-30°	666.3	12.1
0°-40°	1066.4	19.4
0°-60°	1698.1	30.9
0°-90°	1992.8	36.2
90°-120°	1722.5	31.3
90°-150°	3071.9	55.9
90°-180°	3507.0	63.8
0°-180°	5499.9	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	787	787	787	787	787	
5°	910	787	695	787	910	92
15°	1205	752	517	752	1205	343
25°	1300	688	407	688	1300	577
35°	801	598	341	598	801	502
45°	409	479	287	479	409	324
55°	244	343	214	343	244	222
65°	143	215	120	215	143	144
75°	66	106	56	106	66	73
85°	16	24	16	24	16	18
90°	20	1	20	1	20	17
95°	231	31	231	31	231	359
105°	1333	111	1333	111	1333	1318
115°	1280	195	1280	195	1280	1271
125°	1021	272	1021	272	1021	928
135°	913	323	913	323	913	705
145°	746	372	746	372	746	473
155°	624	424	624	424	624	291
165°	545	461	545	461	545	156
175°	491	481	491	481	491	48
180°	482	482	482	482	482	



TEST NUMBER: P332921-930

CATALOG NUMBER: S124RDIP-S575D1205U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3
2.5°	830.5	832.7	830.5	830.2	827.7	827.0	825.9	822.6	816.5	812.9	813.8
5°	909.8	917.7	913.3	912.6	905.6	898.7	894.2	884.1	873.3	866.0	860.0
7.5°	1001.5	1006.1	1003.3	998.8	987.6	981.1	970.9	957.5	938.2	923.3	909.9
10°	1064.0	1067.7	1066.5	1058.3	1050.0	1033.1	1023.7	1004.9	980.5	961.2	943.1
12.5°	1125.4	1129.4	1118.3	1118.7	1103.0	1089.7	1074.6	1051.2	1022.9	997.9	975.3
15°	1205.4	1200.4	1200.4	1194.0	1176.6	1158.1	1142.6	1117.9	1082.3	1052.6	1021.2
17.5°	1268.1	1269.9	1267.3	1252.3	1238.6	1219.6	1191.1	1162.2	1129.2	1089.2	1057.1
20°	1305.7	1305.7	1302.8	1292.7	1274.9	1254.6	1223.8	1192.5	1150.6	1110.3	1074.1
22.5°	1320.9	1321.9	1318.6	1310.2	1294.2	1274.4	1248.2	1216.3	1173.1	1127.8	1083.0
25°	1300.0	1305.9	1306.6	1304.4	1299.7	1287.6	1265.1	1232.4	1193.7	1144.5	1096.3
27.5°	1193.5	1201.1	1207.8	1218.7	1233.3	1241.0	1241.9	1225.3	1191.6	1144.3	1095.8
30°	1087.4	1093.7	1114.4	1141.3	1162.3	1181.3	1197.8	1202.2	1183.2	1140.7	1089.6
32.5°	969.6	978.3	998.9	1027.9	1062.8	1095.0	1132.1	1151.0	1150.5	1124.9	1077.7
35°	800.6	807.0	826.1	856.5	898.4	946.2	1004.9	1050.6	1081.7	1079.5	1050.6
37.5°	645.7	652.9	672.1	697.4	738.0	797.3	854.1	917.0	974.5	1006.8	997.1
40°	561.5	561.8	580.5	606.5	644.6	696.3	758.1	827.9	892.0	944.4	954.5
42.5°	495.0	495.0	507.4	535.5	562.9	611.6	670.6	739.9	814.9	875.3	902.2
45°	409.2	412.1	422.2	439.0	460.6	501.8	549.1	613.5	697.6	769.2	814.0
47.5°	346.5	350.7	357.2	370.9	388.1	415.6	454.6	512.5	580.9	659.7	723.4
50°	314.1	314.7	322.9	330.5	345.4	367.4	401.6	449.8	512.7	588.4	659.2
52.5°	286.2	286.0	291.0	300.6	312.7	329.8	357.4	401.4	457.1	525.0	598.0
55°	244.3	245.8	249.6	257.2	266.4	278.5	300.4	333.4	377.2	435.2	501.5
57.5°	212.4	213.2	216.2	219.5	227.9	236.7	253.1	276.0	312.9	360.4	422.2
60°	191.6	191.9	192.9	197.6	204.3	212.5	223.6	243.0	274.1	317.6	366.4
62.5°	171.3	171.9	173.3	176.8	182.0	187.7	199.3	214.8	240.6	277.7	321.7
65°	142.8	143.1	145.3	146.6	150.7	155.7	164.3	174.8	192.6	223.6	257.0
67.5°	119.3	119.3	119.4	121.2	124.0	127.3	132.5	140.9	154.3	173.3	202.7
70°	104.0	104.0	104.7	105.7	107.2	110.1	112.9	119.3	129.1	144.6	167.1
72.5°	89.8	90.1	90.7	90.9	91.7	94.1	96.2	100.2	107.5	119.3	137.5
75°	66.0	66.9	68.5	69.8	71.3	71.1	73.3	75.8	78.0	85.0	95.5
77.5°	49.1	48.6	48.8	49.9	50.1	50.4	51.9	53.9	55.6	58.9	62.6
80°	37.4	37.4	38.4	38.7	38.4	38.7	40.3	41.3	41.9	43.1	46.6
82.5°	28.3	28.8	28.5	28.8	29.0	29.4	30.7	30.8	31.5	32.0	33.4
85°	15.9	16.1	16.5	15.9	15.9	15.9	16.5	16.8	17.4	17.1	17.8
87.5°	9.5	9.3	9.8	9.5	9.6	9.4	9.5	9.8	9.0	9.5	9.1
90°	19.9	19.9	20.9	19.9	18.9	18.9	18.0	17.0	16.1	17.0	15.2
92.5°	73.0	73.0	76.1	81.3	92.5	111.5	140.0	186.1	250.3	300.5	263.0
95°	231.1	243.4	260.6	289.9	336.3	428.2	555.1	702.0	793.9	772.1	582.6
97.5°	617.9	637.6	666.0	723.0	791.1	890.0	982.6	1037.2	997.4	813.3	545.3
100°	868.8	876.4	904.7	962.5	1045.0	1115.1	1161.5	1142.6	1004.2	761.7	494.6
102.5°	1087.0	1093.1	1123.0	1164.9	1215.4	1244.6	1231.2	1137.3	947.4	697.2	460.4
105°	1332.9	1338.6	1351.9	1359.5	1357.6	1318.7	1225.0	1061.0	844.1	621.5	431.0
107.5°	1424.3	1421.8	1412.3	1390.7	1343.9	1259.5	1127.4	952.8	760.8	579.0	425.7
110°	1425.8	1417.3	1400.2	1360.4	1293.1	1189.0	1051.6	887.7	719.1	564.7	427.3



TEST NUMBER: P332921-930

CATALOG NUMBER: S124RDIP-S575D1205U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1381.1	1367.3	1343.4	1295.3	1218.9	1114.7	984.9	839.9	695.5	557.8	431.8
115°	1279.9	1272.4	1242.0	1185.2	1110.4	1019.4	908.6	792.0	673.6	554.2	440.5
117.5°	1177.4	1171.5	1140.8	1093.1	1029.2	952.1	865.0	768.5	663.7	553.3	449.8
120°	1119.8	1109.4	1084.8	1043.1	989.0	921.8	846.0	757.9	658.4	553.3	456.6
122.5°	1074.3	1063.9	1043.1	1007.5	961.8	902.9	833.9	748.8	652.4	552.5	463.5
125°	1021.2	1015.6	997.6	970.1	932.2	880.1	814.7	733.3	642.3	551.4	473.7
127.5°	990.2	984.6	969.4	944.9	906.9	857.4	792.2	714.3	628.8	549.3	481.8
130°	972.0	966.3	951.1	927.5	888.7	838.5	774.0	699.2	620.5	548.5	487.9
132.5°	951.5	945.8	931.5	904.7	866.7	816.4	753.6	683.2	612.9	547.8	493.2
135°	913.3	907.6	892.4	865.9	828.0	780.6	722.8	661.3	601.6	546.7	501.2
137.5°	865.9	859.1	846.6	820.4	785.0	742.2	693.5	641.4	591.7	546.4	505.9
140°	831.8	824.2	811.0	790.1	756.9	717.1	674.5	630.0	586.4	545.7	509.7
142.5°	795.4	790.1	778.4	759.0	729.7	695.2	658.6	619.4	581.9	545.7	512.7
145°	745.6	740.9	731.4	715.3	691.6	665.0	636.7	604.5	574.1	543.8	514.5
147.5°	701.4	699.8	692.5	678.7	661.3	640.4	617.7	592.2	567.1	540.4	515.4
150°	676.5	675.5	669.8	657.5	642.3	625.3	606.3	584.6	561.8	538.1	515.4
152.5°	653.7	652.7	649.3	639.3	626.4	612.4	594.9	576.2	555.7	534.3	513.9
155°	624.4	624.4	621.5	613.9	604.5	593.0	578.9	563.7	546.7	528.6	511.6
157.5°	598.6	598.6	596.9	591.2	584.0	574.9	563.0	550.2	537.4	522.8	509.2
160°	582.6	582.6	581.7	576.0	570.3	562.7	552.3	541.9	530.5	518.2	506.9
162.5°	567.4	568.3	567.3	561.6	557.4	550.7	542.5	533.5	524.5	513.6	504.6
165°	544.8	545.7	546.7	542.8	539.1	534.3	527.7	522.0	514.5	506.9	500.2
167.5°	526.8	527.5	527.7	525.2	523.3	520.5	515.2	510.9	505.3	500.0	495.7
170°	515.4	515.4	516.3	515.4	513.5	510.6	506.9	504.0	499.3	495.5	492.6
172.5°	504.0	505.5	506.5	505.5	504.3	502.3	500.0	497.9	494.0	490.9	489.6
175°	490.7	492.6	494.6	492.6	492.6	492.6	490.7	489.8	487.9	486.0	486.0
177.5°	483.0	484.5	486.0	485.3	486.0	485.3	485.3	484.5	483.7	483.0	483.0
180°	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2



TEST NUMBER: P332921-930

CATALOG NUMBER: S124RDIP-S575D1205U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3
2.5°	811.2	807.6	805.8	801.8	797.0	794.4	792.1	788.9	784.6	780.0	776.7
5°	852.4	844.7	835.2	823.8	813.7	803.8	795.2	786.7	776.9	766.7	756.6
7.5°	894.6	879.6	863.5	844.7	826.6	810.0	794.8	780.2	763.7	748.9	735.4
10°	924.1	903.8	881.3	857.5	833.6	813.0	792.7	774.3	754.0	736.0	720.7
12.5°	947.9	924.1	897.0	867.3	838.7	813.8	790.4	766.5	743.4	723.7	703.4
15°	987.5	954.8	918.4	882.8	845.7	811.8	780.3	752.4	726.1	698.5	679.1
17.5°	1014.7	975.9	931.6	888.9	845.1	805.0	768.8	735.6	705.2	677.0	654.0
20°	1030.9	988.1	939.0	890.4	841.2	798.4	759.5	722.6	691.2	660.8	637.0
22.5°	1040.1	992.7	939.0	888.1	837.2	790.8	748.0	709.7	675.5	645.1	618.7
25°	1043.0	992.2	937.3	879.0	823.2	774.0	729.6	688.0	650.0	619.5	591.6
27.5°	1038.9	979.2	923.0	863.1	805.5	753.7	707.0	663.3	625.3	592.6	563.9
30°	1032.8	968.8	908.5	846.4	788.0	738.2	689.0	647.1	607.5	573.6	544.7
32.5°	1019.7	956.1	891.3	827.5	768.4	717.1	670.5	628.4	589.5	554.7	524.1
35°	993.5	929.1	858.7	793.4	735.3	682.0	638.2	597.6	560.5	523.4	491.1
37.5°	959.0	893.3	823.2	751.7	693.6	643.3	603.1	565.0	528.7	494.9	459.0
40°	926.6	866.7	794.3	723.3	663.7	615.1	578.0	543.4	507.0	473.3	437.4
42.5°	887.3	836.2	763.1	691.8	632.9	586.1	551.5	517.8	484.6	452.0	414.6
45°	821.6	782.9	714.4	645.9	586.5	540.2	508.5	478.7	449.5	418.4	383.2
47.5°	746.3	720.2	661.0	590.8	536.0	494.3	463.7	439.3	414.6	383.5	352.6
50°	694.1	677.3	620.2	556.1	503.8	465.4	434.0	411.1	390.5	360.7	333.0
52.5°	638.2	629.3	581.1	519.8	469.2	431.6	404.8	384.3	363.4	338.6	312.7
55°	553.3	558.0	517.1	464.1	416.5	384.8	360.4	343.2	325.5	304.5	284.5
57.5°	466.3	483.7	456.2	409.7	365.1	335.8	317.4	303.0	288.1	270.7	253.6
60°	414.3	428.8	413.4	372.4	333.4	306.1	289.0	277.9	262.9	247.1	234.1
62.5°	363.5	379.1	369.9	336.9	300.7	277.2	262.1	251.8	240.7	226.8	213.3
65°	299.8	309.9	305.5	282.7	257.0	236.9	223.0	215.4	205.2	195.1	183.0
67.5°	229.6	249.2	246.6	234.5	212.3	196.7	187.5	180.8	171.5	164.0	155.8
70°	188.7	206.8	206.5	196.7	184.6	170.0	163.7	158.0	149.7	142.4	135.7
72.5°	154.5	171.0	173.5	166.0	157.8	146.7	140.6	136.6	128.7	123.7	118.2
75°	108.2	120.3	123.4	123.4	119.6	113.9	108.5	106.0	100.2	95.8	92.6
77.5°	70.9	78.5	83.5	84.6	85.2	83.3	78.8	77.0	72.7	71.1	68.1
80°	50.1	55.2	60.9	62.8	64.4	63.8	61.9	60.6	56.5	54.9	53.6
82.5°	34.7	37.4	42.2	46.3	45.9	47.5	45.9	44.8	41.7	41.2	39.9
85°	18.1	18.4	19.0	21.9	23.5	24.1	24.5	23.8	22.8	22.8	20.6
87.5°	8.7	8.5	7.8	7.8	7.9	8.7	9.0	8.8	8.4	8.2	7.7
90°	13.3	13.3	7.6	7.6	6.6	5.7	2.9	1.0	2.9	5.7	6.6
92.5°	191.4	117.9	69.7	50.1	36.2	24.6	15.7	10.8	15.7	24.6	36.2
95°	356.2	200.8	118.5	78.6	55.9	43.6	34.1	31.2	34.1	43.6	55.9
97.5°	320.2	191.9	128.5	95.1	75.6	64.2	56.1	56.1	56.1	64.2	75.6
100°	301.3	194.2	138.4	108.0	90.0	78.6	72.0	72.0	72.0	78.6	90.0
102.5°	296.0	201.8	151.2	122.4	105.2	94.6	88.7	87.2	88.7	94.6	105.2
105°	298.4	219.8	174.3	146.8	129.8	118.5	113.7	110.9	113.7	118.5	129.8
107.5°	312.4	240.8	199.2	172.0	155.7	143.7	138.8	137.0	138.8	143.7	155.7
110°	323.0	256.7	215.1	189.5	172.4	161.0	156.3	154.4	156.3	161.0	172.4





TEST NUMBER: P332921-930

CATALOG NUMBER: S124RDIP-S575D1205U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	334.4	271.9	231.7	206.2	189.1	178.5	173.0	171.1	173.0	178.5	189.1
115°	352.5	295.5	257.7	232.1	214.1	204.6	198.0	195.2	198.0	204.6	214.1
117.5°	370.8	318.5	282.5	256.0	239.1	228.7	222.8	220.1	222.8	228.7	239.1
120°	383.7	334.4	298.4	271.9	255.8	245.4	238.7	236.8	238.7	245.4	255.8
122.5°	395.8	349.6	313.6	287.8	270.2	260.6	253.9	252.0	253.9	260.6	270.2
125°	414.0	370.4	336.3	309.8	291.8	281.4	275.7	271.9	275.7	281.4	291.8
127.5°	429.7	389.7	356.8	330.0	311.3	299.4	292.5	289.5	292.5	299.4	311.3
130°	439.6	402.7	370.4	342.9	325.0	310.7	303.1	299.4	303.1	310.7	325.0
132.5°	449.5	413.3	381.1	355.1	335.6	322.1	312.3	309.2	312.3	322.1	335.6
135°	462.4	428.2	397.0	372.3	352.5	336.3	326.9	323.0	326.9	336.3	352.5
137.5°	471.4	439.6	410.4	386.9	366.2	350.9	340.5	336.9	340.5	350.9	366.2
140°	477.4	447.2	418.7	396.0	376.1	360.0	349.6	346.7	349.6	360.0	376.1
142.5°	482.0	454.0	426.3	404.3	385.2	369.8	360.2	357.3	360.2	369.8	385.2
145°	487.0	461.4	436.8	415.9	397.9	384.7	375.2	372.3	375.2	384.7	397.9
147.5°	491.3	469.0	445.8	427.1	412.1	398.4	390.1	389.1	390.1	398.4	412.1
150°	493.6	472.7	451.9	433.9	419.7	408.3	400.7	399.8	400.7	408.3	419.7
152.5°	495.1	475.8	457.2	440.8	428.0	417.4	409.9	409.6	409.9	417.4	428.0
155°	496.4	480.3	464.2	450.0	439.6	430.1	424.4	423.5	424.4	430.1	439.6
157.5°	496.4	483.6	469.9	458.7	449.6	442.2	436.9	436.9	436.9	442.2	449.6
160°	496.4	485.0	473.7	463.3	455.7	449.1	445.2	445.2	445.2	449.1	455.7
162.5°	496.4	486.6	476.0	467.8	461.0	455.1	452.1	452.8	452.1	455.1	461.0
165°	494.6	487.0	478.4	472.7	468.0	463.3	461.4	461.4	461.4	463.3	468.0
167.5°	492.3	486.7	480.5	476.1	473.5	469.9	469.0	469.9	469.0	469.9	473.5
170°	490.7	486.0	481.3	478.4	476.5	473.7	472.7	473.7	472.7	473.7	476.5
172.5°	489.3	485.3	482.0	480.0	478.8	476.7	476.5	477.4	476.5	476.7	478.8
175°	487.0	484.1	482.2	482.2	481.3	480.3	480.3	481.3	480.3	480.3	481.3
177.5°	484.5	483.0	482.2	482.2	482.2	481.4	482.2	483.0	482.2	481.4	482.2
180°	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2



TEST NUMBER: P332921-930

CATALOG NUMBER: S124RDIP-S575D1205U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3
2.5°	773.1	770.6	767.3	763.4	758.9	754.9	753.1	754.6	755.4	753.3	753.1
5°	749.6	741.7	735.3	725.8	718.2	711.8	707.4	705.5	706.1	701.1	699.8
7.5°	723.1	713.7	703.4	692.0	681.5	672.2	667.3	664.6	659.3	657.0	653.1
10°	706.1	693.4	683.3	669.9	657.9	646.8	641.4	637.0	631.6	629.0	623.6
12.5°	688.6	673.9	662.8	648.9	636.6	623.2	618.1	609.8	601.4	596.1	589.1
15°	663.9	646.2	632.5	616.0	601.4	586.2	572.6	557.3	551.6	539.6	532.6
17.5°	635.0	617.0	600.1	578.0	555.5	536.6	522.0	507.5	498.7	491.1	487.5
20°	616.0	599.6	576.1	550.4	525.3	504.3	492.6	483.1	473.6	468.2	464.4
22.5°	598.0	577.0	549.7	522.0	496.9	480.5	470.6	460.8	453.1	447.9	442.9
25°	567.9	540.2	511.4	479.6	462.5	448.3	437.4	429.5	424.8	418.1	415.6
27.5°	536.8	503.4	471.5	450.2	432.4	419.3	409.9	404.0	397.9	393.6	390.4
30°	512.9	479.0	450.5	430.2	412.1	401.3	393.6	386.7	382.0	378.5	375.9
32.5°	489.3	455.4	431.4	409.6	395.3	384.8	376.7	371.5	367.7	363.2	361.7
35°	455.2	425.1	404.1	384.5	369.9	360.4	354.0	348.6	345.4	344.2	343.2
37.5°	422.4	397.7	375.2	359.1	346.1	338.6	331.1	328.5	326.3	324.0	325.1
40°	401.6	378.5	358.5	341.4	330.8	322.6	318.1	315.0	313.1	313.1	313.1
42.5°	383.6	360.9	341.4	326.1	315.6	308.7	303.7	301.0	300.4	300.1	301.7
45°	355.6	334.7	315.0	302.3	293.4	286.4	283.6	281.4	281.4	282.7	283.0
47.5°	327.9	308.3	292.4	278.3	270.1	265.8	263.3	262.1	262.3	263.5	265.0
50°	310.9	291.6	276.0	263.3	255.7	251.5	249.3	248.7	249.3	249.3	251.5
52.5°	292.4	275.0	259.8	249.1	240.4	236.6	235.4	234.5	234.9	235.9	236.8
55°	265.2	249.6	235.1	224.9	218.6	216.1	213.2	213.5	212.9	213.5	213.5
57.5°	238.0	224.0	210.4	202.4	196.8	193.1	190.0	190.9	190.0	189.8	189.3
60°	220.5	205.2	194.4	187.2	180.8	177.7	174.8	175.5	174.5	173.8	172.6
62.5°	201.5	188.7	178.5	171.5	166.3	162.7	159.8	159.1	156.9	154.8	152.0
65°	173.8	163.4	154.2	147.5	142.8	139.9	137.7	135.7	131.0	126.0	123.4
67.5°	147.0	139.4	130.9	125.2	121.4	117.6	113.4	110.1	105.7	102.9	101.3
70°	129.7	122.5	115.1	109.7	105.7	102.2	97.3	95.1	92.0	90.7	89.1
72.5°	113.2	106.5	99.6	94.8	90.4	87.6	84.0	81.7	80.3	79.8	78.2
75°	88.2	82.8	77.7	73.3	69.8	67.9	66.3	64.7	64.1	61.2	59.6
77.5°	64.3	60.7	57.6	54.5	51.9	50.7	47.6	45.8	44.8	43.4	43.0
80°	50.1	47.6	44.4	42.5	39.1	37.7	36.4	36.2	35.9	35.5	35.2
82.5°	37.7	35.1	32.0	30.8	29.9	29.1	28.4	28.0	27.7	27.9	27.9
85°	19.0	17.8	17.8	17.4	17.1	16.8	16.5	16.5	16.1	16.5	16.1
87.5°	7.8	7.6	8.7	8.2	8.9	9.2	8.8	9.0	9.5	9.1	9.1
90°	7.6	7.6	13.3	13.3	15.2	17.0	16.1	17.0	18.0	18.9	18.9
92.5°	50.1	69.7	117.9	191.4	263.0	300.5	250.3	186.1	140.0	111.5	92.5
95°	78.6	118.5	200.8	356.2	582.6	772.1	793.9	702.0	555.1	428.2	336.3
97.5°	95.1	128.5	191.9	320.2	545.3	813.3	997.4	1037.2	982.6	890.0	791.1
100°	108.0	138.4	194.2	301.3	494.6	761.7	1004.2	1142.6	1161.5	1115.1	1045.0
102.5°	122.4	151.2	201.8	296.0	460.4	697.2	947.4	1137.3	1231.2	1244.6	1215.4
105°	146.8	174.3	219.8	298.4	431.0	621.5	844.1	1061.0	1225.0	1318.7	1357.6
107.5°	172.0	199.2	240.8	312.4	425.7	579.0	760.8	952.8	1127.4	1259.5	1343.9
110°	189.5	215.1	256.7	323.0	427.3	564.7	719.1	887.7	1051.6	1189.0	1293.1



TEST NUMBER: P332921-930

CATALOG NUMBER: S124RDIP-S575D1205U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	206.2	231.7	271.9	334.4	431.8	557.8	695.5	839.9	984.9	1114.7	1218.9
115°	232.1	257.7	295.5	352.5	440.5	554.2	673.6	792.0	908.6	1019.4	1110.4
117.5°	256.0	282.5	318.5	370.8	449.8	553.3	663.7	768.5	865.0	952.1	1029.2
120°	271.9	298.4	334.4	383.7	456.6	553.3	658.4	757.9	846.0	921.8	989.0
122.5°	287.8	313.6	349.6	395.8	463.5	552.5	652.4	748.8	833.9	902.9	961.8
125°	309.8	336.3	370.4	414.0	473.7	551.4	642.3	733.3	814.7	880.1	932.2
127.5°	330.0	356.8	389.7	429.7	481.8	549.3	628.8	714.3	792.2	857.4	906.9
130°	342.9	370.4	402.7	439.6	487.9	548.5	620.5	699.2	774.0	838.5	888.7
132.5°	355.1	381.1	413.3	449.5	493.2	547.8	612.9	683.2	753.6	816.4	866.7
135°	372.3	397.0	428.2	462.4	501.2	546.7	601.6	661.3	722.8	780.6	828.0
137.5°	386.9	410.4	439.6	471.4	505.9	546.4	591.7	641.4	693.5	742.2	785.0
140°	396.0	418.7	447.2	477.4	509.7	545.7	586.4	630.0	674.5	717.1	756.9
142.5°	404.3	426.3	454.0	482.0	512.7	545.7	581.9	619.4	658.6	695.2	729.7
145°	415.9	436.8	461.4	487.0	514.5	543.8	574.1	604.5	636.7	665.0	691.6
147.5°	427.1	445.8	469.0	491.3	515.4	540.4	567.1	592.2	617.7	640.4	661.3
150°	433.9	451.9	472.7	493.6	515.4	538.1	561.8	584.6	606.3	625.3	642.3
152.5°	440.8	457.2	475.8	495.1	513.9	534.3	555.7	576.2	594.9	612.4	626.4
155°	450.0	464.2	480.3	496.4	511.6	528.6	546.7	563.7	578.9	593.0	604.5
157.5°	458.7	469.9	483.6	496.4	509.2	522.8	537.4	550.2	563.0	574.9	584.0
160°	463.3	473.7	485.0	496.4	506.9	518.2	530.5	541.9	552.3	562.7	570.3
162.5°	467.8	476.0	486.6	496.4	504.6	513.6	524.5	533.5	542.5	550.7	557.4
165°	472.7	478.4	487.0	494.6	500.2	506.9	514.5	522.0	527.7	534.3	539.1
167.5°	476.1	480.5	486.7	492.3	495.7	500.0	505.3	510.9	515.2	520.5	523.3
170°	478.4	481.3	486.0	490.7	492.6	495.5	499.3	504.0	506.9	510.6	513.5
172.5°	480.0	482.0	485.3	489.3	489.6	490.9	494.0	497.9	500.0	502.3	504.3
175°	482.2	482.2	484.1	487.0	486.0	486.0	487.9	489.8	490.7	492.6	492.6
177.5°	482.2	482.2	483.0	484.5	483.0	483.0	483.7	484.5	485.3	485.3	486.0
180°	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2



TEST NUMBER: P332921-930

CATALOG NUMBER: S124RDIP-S575D1205U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3
2.5°	751.5	752.0	750.3	749.7	750.3	752.0	751.5	753.1	753.3	755.4	754.6
5°	697.2	696.6	695.0	695.4	695.0	696.6	697.2	699.8	701.1	706.1	705.5
7.5°	650.8	648.3	649.1	646.5	649.1	648.3	650.8	653.1	657.0	659.3	664.6
10°	622.4	618.9	616.0	613.5	616.0	618.9	622.4	623.6	629.0	631.6	637.0
12.5°	583.6	580.6	576.7	577.5	576.7	580.6	583.6	589.1	596.1	601.4	609.8
15°	528.5	523.7	516.1	517.1	516.1	523.7	528.5	532.6	539.6	551.6	557.3
17.5°	481.8	481.9	478.4	479.2	478.4	481.9	481.8	487.5	491.1	498.7	507.5
20°	457.7	455.5	455.8	454.9	455.8	455.5	457.7	464.4	468.2	473.6	483.1
22.5°	441.0	438.3	436.0	434.1	436.0	438.3	441.0	442.9	447.9	453.1	460.8
25°	412.7	410.8	408.0	407.3	408.0	410.8	412.7	415.6	418.1	424.8	429.5
27.5°	387.8	387.4	386.3	384.8	386.3	387.4	387.8	390.4	393.6	397.9	404.0
30°	373.3	372.8	372.1	371.1	372.1	372.8	373.3	375.9	378.5	382.0	386.7
32.5°	360.4	360.0	359.4	359.5	359.4	360.0	360.4	361.7	363.2	367.7	371.5
35°	341.9	341.6	341.0	340.7	341.0	341.6	341.9	343.2	344.2	345.4	348.6
37.5°	324.7	325.5	325.1	325.1	325.1	325.5	324.7	325.1	324.0	326.3	328.5
40°	312.7	313.1	313.7	313.4	313.7	313.1	312.7	313.1	313.1	313.1	315.0
42.5°	302.9	303.0	303.9	302.7	303.9	303.0	302.9	301.7	300.1	300.4	301.0
45°	285.2	287.1	286.7	286.7	286.7	287.1	285.2	283.0	282.7	281.4	281.4
47.5°	265.8	267.5	267.9	267.8	267.9	267.5	265.8	265.0	263.5	262.3	262.1
50°	253.2	252.5	253.5	253.2	253.5	252.5	253.2	251.5	249.3	249.3	248.7
52.5°	237.7	237.8	237.7	237.4	237.7	237.8	237.7	236.8	235.9	234.9	234.5
55°	213.8	214.1	213.5	213.8	213.5	214.1	213.8	213.5	213.5	212.9	213.5
57.5°	187.9	186.4	187.0	186.3	187.0	186.4	187.9	189.3	189.8	190.0	190.9
60°	169.4	166.9	166.2	164.9	166.2	166.9	169.4	172.6	173.8	174.5	175.5
62.5°	148.5	146.8	144.6	145.7	144.6	146.8	148.5	152.0	154.8	156.9	159.1
65°	120.8	119.6	118.6	119.9	118.6	119.6	120.8	123.4	126.0	131.0	135.7
67.5°	100.0	99.4	99.4	98.7	99.4	99.4	100.0	101.3	102.9	105.7	110.1
70°	89.1	88.2	88.2	87.6	88.2	88.2	89.1	89.1	90.7	92.0	95.1
72.5°	77.9	77.0	77.3	76.9	77.3	77.0	77.9	78.2	79.8	80.3	81.7
75°	57.7	56.2	56.2	56.5	56.2	56.2	57.7	59.6	61.2	64.1	64.7
77.5°	43.0	42.7	43.2	42.6	43.2	42.7	43.0	43.0	43.4	44.8	45.8
80°	35.2	34.9	34.6	35.5	34.6	34.9	35.2	35.2	35.5	35.9	36.2
82.5°	27.3	27.3	27.2	28.5	27.2	27.3	27.3	27.9	27.9	27.7	28.0
85°	16.5	15.9	16.5	15.9	16.5	15.9	16.5	16.1	16.5	16.1	16.5
87.5°	9.8	9.8	9.3	9.5	9.3	9.8	9.8	9.1	9.1	9.5	9.0
90°	19.9	20.9	19.9	19.9	19.9	20.9	19.9	18.9	18.9	18.0	17.0
92.5°	81.3	76.1	73.0	73.0	73.0	76.1	81.3	92.5	111.5	140.0	186.1
95°	289.9	260.6	243.4	231.1	243.4	260.6	289.9	336.3	428.2	555.1	702.0
97.5°	723.0	666.0	637.6	617.9	637.6	666.0	723.0	791.1	890.0	982.6	1037.2
100°	962.5	904.7	876.4	868.8	876.4	904.7	962.5	1045.0	1115.1	1161.5	1142.6
102.5°	1164.9	1123.0	1093.1	1087.0	1093.1	1123.0	1164.9	1215.4	1244.6	1231.2	1137.3
105°	1359.5	1351.9	1338.6	1332.9	1338.6	1351.9	1359.5	1357.6	1318.7	1225.0	1061.0
107.5°	1390.7	1412.3	1421.8	1424.3	1421.8	1412.3	1390.7	1343.9	1259.5	1127.4	952.8
110°	1360.4	1400.2	1417.3	1425.8	1417.3	1400.2	1360.4	1293.1	1189.0	1051.6	887.7



TEST NUMBER: P332921-930

CATALOG NUMBER: S124RDIP-S575D1205U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1295.3	1343.4	1367.3	1381.1	1367.3	1343.4	1295.3	1218.9	1114.7	984.9	839.9
115°	1185.2	1242.0	1272.4	1279.9	1272.4	1242.0	1185.2	1110.4	1019.4	908.6	792.0
117.5°	1093.1	1140.8	1171.5	1177.4	1171.5	1140.8	1093.1	1029.2	952.1	865.0	768.5
120°	1043.1	1084.8	1109.4	1119.8	1109.4	1084.8	1043.1	989.0	921.8	846.0	757.9
122.5°	1007.5	1043.1	1063.9	1074.3	1063.9	1043.1	1007.5	961.8	902.9	833.9	748.8
125°	970.1	997.6	1015.6	1021.2	1015.6	997.6	970.1	932.2	880.1	814.7	733.3
127.5°	944.9	969.4	984.6	990.2	984.6	969.4	944.9	906.9	857.4	792.2	714.3
130°	927.5	951.1	966.3	972.0	966.3	951.1	927.5	888.7	838.5	774.0	699.2
132.5°	904.7	931.5	945.8	951.5	945.8	931.5	904.7	866.7	816.4	753.6	683.2
135°	865.9	892.4	907.6	913.3	907.6	892.4	865.9	828.0	780.6	722.8	661.3
137.5°	820.4	846.6	859.1	865.9	859.1	846.6	820.4	785.0	742.2	693.5	641.4
140°	790.1	811.0	824.2	831.8	824.2	811.0	790.1	756.9	717.1	674.5	630.0
142.5°	759.0	778.4	790.1	795.4	790.1	778.4	759.0	729.7	695.2	658.6	619.4
145°	715.3	731.4	740.9	745.6	740.9	731.4	715.3	691.6	665.0	636.7	604.5
147.5°	678.7	692.5	699.8	701.4	699.8	692.5	678.7	661.3	640.4	617.7	592.2
150°	657.5	669.8	675.5	676.5	675.5	669.8	657.5	642.3	625.3	606.3	584.6
152.5°	639.3	649.3	652.7	653.7	652.7	649.3	639.3	626.4	612.4	594.9	576.2
155°	613.9	621.5	624.4	624.4	624.4	621.5	613.9	604.5	593.0	578.9	563.7
157.5°	591.2	596.9	598.6	598.6	598.6	596.9	591.2	584.0	574.9	563.0	550.2
160°	576.0	581.7	582.6	582.6	582.6	581.7	576.0	570.3	562.7	552.3	541.9
162.5°	561.6	567.3	568.3	567.4	568.3	567.3	561.6	557.4	550.7	542.5	533.5
165°	542.8	546.7	545.7	544.8	545.7	546.7	542.8	539.1	534.3	527.7	522.0
167.5°	525.2	527.7	527.5	526.8	527.5	527.7	525.2	523.3	520.5	515.2	510.9
170°	515.4	516.3	515.4	515.4	515.4	516.3	515.4	513.5	510.6	506.9	504.0
172.5°	505.5	506.5	505.5	504.0	505.5	506.5	505.5	504.3	502.3	500.0	497.9
175°	492.6	494.6	492.6	490.7	492.6	494.6	492.6	492.6	492.6	490.7	489.8
177.5°	485.3	486.0	484.5	483.0	484.5	486.0	485.3	486.0	485.3	485.3	484.5
180°	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2



TEST NUMBER: P332921-930

CATALOG NUMBER: S124RDIP-S575D1205U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3
2.5°	753.1	754.9	758.9	763.4	767.3	770.6	773.1	776.7	780.0	784.6	788.9
5°	707.4	711.8	718.2	725.8	735.3	741.7	749.6	756.6	766.7	776.9	786.7
7.5°	667.3	672.2	681.5	692.0	703.4	713.7	723.1	735.4	748.9	763.7	780.2
10°	641.4	646.8	657.9	669.9	683.3	693.4	706.1	720.7	736.0	754.0	774.3
12.5°	618.1	623.2	636.6	648.9	662.8	673.9	688.6	703.4	723.7	743.4	766.5
15°	572.6	586.2	601.4	616.0	632.5	646.2	663.9	679.1	698.5	726.1	752.4
17.5°	522.0	536.6	555.5	578.0	600.1	617.0	635.0	654.0	677.0	705.2	735.6
20°	492.6	504.3	525.3	550.4	576.1	599.6	616.0	637.0	660.8	691.2	722.6
22.5°	470.6	480.5	496.9	522.0	549.7	577.0	598.0	618.7	645.1	675.5	709.7
25°	437.4	448.3	462.5	479.6	511.4	540.2	567.9	591.6	619.5	650.0	688.0
27.5°	409.9	419.3	432.4	450.2	471.5	503.4	536.8	563.9	592.6	625.3	663.3
30°	393.6	401.3	412.1	430.2	450.5	479.0	512.9	544.7	573.6	607.5	647.1
32.5°	376.7	384.8	395.3	409.6	431.4	455.4	489.3	524.1	554.7	589.5	628.4
35°	354.0	360.4	369.9	384.5	404.1	425.1	455.2	491.1	523.4	560.5	597.6
37.5°	331.1	338.6	346.1	359.1	375.2	397.7	422.4	459.0	494.9	528.7	565.0
40°	318.1	322.6	330.8	341.4	358.5	378.5	401.6	437.4	473.3	507.0	543.4
42.5°	303.7	308.7	315.6	326.1	341.4	360.9	383.6	414.6	452.0	484.6	517.8
45°	283.6	286.4	293.4	302.3	315.0	334.7	355.6	383.2	418.4	449.5	478.7
47.5°	263.3	265.8	270.1	278.3	292.4	308.3	327.9	352.6	383.5	414.6	439.3
50°	249.3	251.5	255.7	263.3	276.0	291.6	310.9	333.0	360.7	390.5	411.1
52.5°	235.4	236.6	240.4	249.1	259.8	275.0	292.4	312.7	338.6	363.4	384.3
55°	213.2	216.1	218.6	224.9	235.1	249.6	265.2	284.5	304.5	325.5	343.2
57.5°	190.0	193.1	196.8	202.4	210.4	224.0	238.0	253.6	270.7	288.1	303.0
60°	174.8	177.7	180.8	187.2	194.4	205.2	220.5	234.1	247.1	262.9	277.9
62.5°	159.8	162.7	166.3	171.5	178.5	188.7	201.5	213.3	226.8	240.7	251.8
65°	137.7	139.9	142.8	147.5	154.2	163.4	173.8	183.0	195.1	205.2	215.4
67.5°	113.4	117.6	121.4	125.2	130.9	139.4	147.0	155.8	164.0	171.5	180.8
70°	97.3	102.2	105.7	109.7	115.1	122.5	129.7	135.7	142.4	149.7	158.0
72.5°	84.0	87.6	90.4	94.8	99.6	106.5	113.2	118.2	123.7	128.7	136.6
75°	66.3	67.9	69.8	73.3	77.7	82.8	88.2	92.6	95.8	100.2	106.0
77.5°	47.6	50.7	51.9	54.5	57.6	60.7	64.3	68.1	71.1	72.7	77.0
80°	36.4	37.7	39.1	42.5	44.4	47.6	50.1	53.6	54.9	56.5	60.6
82.5°	28.4	29.1	29.9	30.8	32.0	35.1	37.7	39.9	41.2	41.7	44.8
85°	16.5	16.8	17.1	17.4	17.8	17.8	19.0	20.6	22.8	22.8	23.8
87.5°	8.8	9.2	8.9	8.2	8.7	7.6	7.8	7.7	8.2	8.4	8.8
90°	16.1	17.0	15.2	13.3	13.3	7.6	7.6	6.6	5.7	2.9	1.0
92.5°	250.3	300.5	263.0	191.4	117.9	69.7	50.1	36.2	24.6	15.7	10.8
95°	793.9	772.1	582.6	356.2	200.8	118.5	78.6	55.9	43.6	34.1	31.2
97.5°	997.4	813.3	545.3	320.2	191.9	128.5	95.1	75.6	64.2	56.1	56.1
100°	1004.2	761.7	494.6	301.3	194.2	138.4	108.0	90.0	78.6	72.0	72.0
102.5°	947.4	697.2	460.4	296.0	201.8	151.2	122.4	105.2	94.6	88.7	87.2
105°	844.1	621.5	431.0	298.4	219.8	174.3	146.8	129.8	118.5	113.7	110.9
107.5°	760.8	579.0	425.7	312.4	240.8	199.2	172.0	155.7	143.7	138.8	137.0
110°	719.1	564.7	427.3	323.0	256.7	215.1	189.5	172.4	161.0	156.3	154.4



TEST NUMBER: P332921-930

CATALOG NUMBER: S124RDIP-S575D1205U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	695.5	557.8	431.8	334.4	271.9	231.7	206.2	189.1	178.5	173.0	171.1
115°	673.6	554.2	440.5	352.5	295.5	257.7	232.1	214.1	204.6	198.0	195.2
117.5°	663.7	553.3	449.8	370.8	318.5	282.5	256.0	239.1	228.7	222.8	220.1
120°	658.4	553.3	456.6	383.7	334.4	298.4	271.9	255.8	245.4	238.7	236.8
122.5°	652.4	552.5	463.5	395.8	349.6	313.6	287.8	270.2	260.6	253.9	252.0
125°	642.3	551.4	473.7	414.0	370.4	336.3	309.8	291.8	281.4	275.7	271.9
127.5°	628.8	549.3	481.8	429.7	389.7	356.8	330.0	311.3	299.4	292.5	289.5
130°	620.5	548.5	487.9	439.6	402.7	370.4	342.9	325.0	310.7	303.1	299.4
132.5°	612.9	547.8	493.2	449.5	413.3	381.1	355.1	335.6	322.1	312.3	309.2
135°	601.6	546.7	501.2	462.4	428.2	397.0	372.3	352.5	336.3	326.9	323.0
137.5°	591.7	546.4	505.9	471.4	439.6	410.4	386.9	366.2	350.9	340.5	336.9
140°	586.4	545.7	509.7	477.4	447.2	418.7	396.0	376.1	360.0	349.6	346.7
142.5°	581.9	545.7	512.7	482.0	454.0	426.3	404.3	385.2	369.8	360.2	357.3
145°	574.1	543.8	514.5	487.0	461.4	436.8	415.9	397.9	384.7	375.2	372.3
147.5°	567.1	540.4	515.4	491.3	469.0	445.8	427.1	412.1	398.4	390.1	389.1
150°	561.8	538.1	515.4	493.6	472.7	451.9	433.9	419.7	408.3	400.7	399.8
152.5°	555.7	534.3	513.9	495.1	475.8	457.2	440.8	428.0	417.4	409.9	409.6
155°	546.7	528.6	511.6	496.4	480.3	464.2	450.0	439.6	430.1	424.4	423.5
157.5°	537.4	522.8	509.2	496.4	483.6	469.9	458.7	449.6	442.2	436.9	436.9
160°	530.5	518.2	506.9	496.4	485.0	473.7	463.3	455.7	449.1	445.2	445.2
162.5°	524.5	513.6	504.6	496.4	486.6	476.0	467.8	461.0	455.1	452.1	452.8
165°	514.5	506.9	500.2	494.6	487.0	478.4	472.7	468.0	463.3	461.4	461.4
167.5°	505.3	500.0	495.7	492.3	486.7	480.5	476.1	473.5	469.9	469.0	469.9
170°	499.3	495.5	492.6	490.7	486.0	481.3	478.4	476.5	473.7	472.7	473.7
172.5°	494.0	490.9	489.6	489.3	485.3	482.0	480.0	478.8	476.7	476.5	477.4
175°	487.9	486.0	486.0	487.0	484.1	482.2	482.2	481.3	480.3	480.3	481.3
177.5°	483.7	483.0	483.0	484.5	483.0	482.2	482.2	482.2	481.4	482.2	483.0
180°	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2



TEST NUMBER: P332921-930

CATALOG NUMBER: S124RDIP-S575D1205U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3
2.5°	792.1	794.4	797.0	801.8	805.8	807.6	811.2	813.8	812.9	816.5	822.6
5°	795.2	803.8	813.7	823.8	835.2	844.7	852.4	860.0	866.0	873.3	884.1
7.5°	794.8	810.0	826.6	844.7	863.5	879.6	894.6	909.9	923.3	938.2	957.5
10°	792.7	813.0	833.6	857.5	881.3	903.8	924.1	943.1	961.2	980.5	1004.9
12.5°	790.4	813.8	838.7	867.3	897.0	924.1	947.9	975.3	997.9	1022.9	1051.2
15°	780.3	811.8	845.7	882.8	918.4	954.8	987.5	1021.2	1052.6	1082.3	1117.9
17.5°	768.8	805.0	845.1	888.9	931.6	975.9	1014.7	1057.1	1089.2	1129.2	1162.2
20°	759.5	798.4	841.2	890.4	939.0	988.1	1030.9	1074.1	1110.3	1150.6	1192.5
22.5°	748.0	790.8	837.2	888.1	939.0	992.7	1040.1	1083.0	1127.8	1173.1	1216.3
25°	729.6	774.0	823.2	879.0	937.3	992.2	1043.0	1096.3	1144.5	1193.7	1232.4
27.5°	707.0	753.7	805.5	863.1	923.0	979.2	1038.9	1095.8	1144.3	1191.6	1225.3
30°	689.0	738.2	788.0	846.4	908.5	968.8	1032.8	1089.6	1140.7	1183.2	1202.2
32.5°	670.5	717.1	768.4	827.5	891.3	956.1	1019.7	1077.7	1124.9	1150.5	1151.0
35°	638.2	682.0	735.3	793.4	858.7	929.1	993.5	1050.6	1079.5	1081.7	1050.6
37.5°	603.1	643.3	693.6	751.7	823.2	893.3	959.0	997.1	1006.8	974.5	917.0
40°	578.0	615.1	663.7	723.3	794.3	866.7	926.6	954.5	944.4	892.0	827.9
42.5°	551.5	586.1	632.9	691.8	763.1	836.2	887.3	902.2	875.3	814.9	739.9
45°	508.5	540.2	586.5	645.9	714.4	782.9	821.6	814.0	769.2	697.6	613.5
47.5°	463.7	494.3	536.0	590.8	661.0	720.2	746.3	723.4	659.7	580.9	512.5
50°	434.0	465.4	503.8	556.1	620.2	677.3	694.1	659.2	588.4	512.7	449.8
52.5°	404.8	431.6	469.2	519.8	581.1	629.3	638.2	598.0	525.0	457.1	401.4
55°	360.4	384.8	416.5	464.1	517.1	558.0	553.3	501.5	435.2	377.2	333.4
57.5°	317.4	335.8	365.1	409.7	456.2	483.7	466.3	422.2	360.4	312.9	276.0
60°	289.0	306.1	333.4	372.4	413.4	428.8	414.3	366.4	317.6	274.1	243.0
62.5°	262.1	277.2	300.7	336.9	369.9	379.1	363.5	321.7	277.7	240.6	214.8
65°	223.0	236.9	257.0	282.7	305.5	309.9	299.8	257.0	223.6	192.6	174.8
67.5°	187.5	196.7	212.3	234.5	246.6	249.2	229.6	202.7	173.3	154.3	140.9
70°	163.7	170.0	184.6	196.7	206.5	206.8	188.7	167.1	144.6	129.1	119.3
72.5°	140.6	146.7	157.8	166.0	173.5	171.0	154.5	137.5	119.3	107.5	100.2
75°	108.5	113.9	119.6	123.4	123.4	120.3	108.2	95.5	85.0	78.0	75.8
77.5°	78.8	83.3	85.2	84.6	83.5	78.5	70.9	62.6	58.9	55.6	53.9
80°	61.9	63.8	64.4	62.8	60.9	55.2	50.1	46.6	43.1	41.9	41.3
82.5°	45.9	47.5	45.9	46.3	42.2	37.4	34.7	33.4	32.0	31.5	30.8
85°	24.5	24.1	23.5	21.9	19.0	18.4	18.1	17.8	17.1	17.4	16.8
87.5°	9.0	8.7	7.9	7.8	7.8	8.5	8.7	9.1	9.5	9.0	9.8
90°	2.9	5.7	6.6	7.6	7.6	13.3	13.3	15.2	17.0	16.1	17.0
92.5°	15.7	24.6	36.2	50.1	69.7	117.9	191.4	263.0	300.5	250.3	186.1
95°	34.1	43.6	55.9	78.6	118.5	200.8	356.2	582.6	772.1	793.9	702.0
97.5°	56.1	64.2	75.6	95.1	128.5	191.9	320.2	545.3	813.3	997.4	1037.2
100°	72.0	78.6	90.0	108.0	138.4	194.2	301.3	494.6	761.7	1004.2	1142.6
102.5°	88.7	94.6	105.2	122.4	151.2	201.8	296.0	460.4	697.2	947.4	1137.3
105°	113.7	118.5	129.8	146.8	174.3	219.8	298.4	431.0	621.5	844.1	1061.0
107.5°	138.8	143.7	155.7	172.0	199.2	240.8	312.4	425.7	579.0	760.8	952.8
110°	156.3	161.0	172.4	189.5	215.1	256.7	323.0	427.3	564.7	719.1	887.7





TEST NUMBER: P332921-930

CATALOG NUMBER: S124RDIP-S575D1205U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	173.0	178.5	189.1	206.2	231.7	271.9	334.4	431.8	557.8	695.5	839.9
115°	198.0	204.6	214.1	232.1	257.7	295.5	352.5	440.5	554.2	673.6	792.0
117.5°	222.8	228.7	239.1	256.0	282.5	318.5	370.8	449.8	553.3	663.7	768.5
120°	238.7	245.4	255.8	271.9	298.4	334.4	383.7	456.6	553.3	658.4	757.9
122.5°	253.9	260.6	270.2	287.8	313.6	349.6	395.8	463.5	552.5	652.4	748.8
125°	275.7	281.4	291.8	309.8	336.3	370.4	414.0	473.7	551.4	642.3	733.3
127.5°	292.5	299.4	311.3	330.0	356.8	389.7	429.7	481.8	549.3	628.8	714.3
130°	303.1	310.7	325.0	342.9	370.4	402.7	439.6	487.9	548.5	620.5	699.2
132.5°	312.3	322.1	335.6	355.1	381.1	413.3	449.5	493.2	547.8	612.9	683.2
135°	326.9	336.3	352.5	372.3	397.0	428.2	462.4	501.2	546.7	601.6	661.3
137.5°	340.5	350.9	366.2	386.9	410.4	439.6	471.4	505.9	546.4	591.7	641.4
140°	349.6	360.0	376.1	396.0	418.7	447.2	477.4	509.7	545.7	586.4	630.0
142.5°	360.2	369.8	385.2	404.3	426.3	454.0	482.0	512.7	545.7	581.9	619.4
145°	375.2	384.7	397.9	415.9	436.8	461.4	487.0	514.5	543.8	574.1	604.5
147.5°	390.1	398.4	412.1	427.1	445.8	469.0	491.3	515.4	540.4	567.1	592.2
150°	400.7	408.3	419.7	433.9	451.9	472.7	493.6	515.4	538.1	561.8	584.6
152.5°	409.9	417.4	428.0	440.8	457.2	475.8	495.1	513.9	534.3	555.7	576.2
155°	424.4	430.1	439.6	450.0	464.2	480.3	496.4	511.6	528.6	546.7	563.7
157.5°	436.9	442.2	449.6	458.7	469.9	483.6	496.4	509.2	522.8	537.4	550.2
160°	445.2	449.1	455.7	463.3	473.7	485.0	496.4	506.9	518.2	530.5	541.9
162.5°	452.1	455.1	461.0	467.8	476.0	486.6	496.4	504.6	513.6	524.5	533.5
165°	461.4	463.3	468.0	472.7	478.4	487.0	494.6	500.2	506.9	514.5	522.0
167.5°	469.0	469.9	473.5	476.1	480.5	486.7	492.3	495.7	500.0	505.3	510.9
170°	472.7	473.7	476.5	478.4	481.3	486.0	490.7	492.6	495.5	499.3	504.0
172.5°	476.5	476.7	478.8	480.0	482.0	485.3	489.3	489.6	490.9	494.0	497.9
175°	480.3	480.3	481.3	482.2	482.2	484.1	487.0	486.0	486.0	487.9	489.8
177.5°	482.2	481.4	482.2	482.2	482.2	483.0	484.5	483.0	483.0	483.7	484.5
180°	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2



TEST NUMBER: P332921-930

CATALOG NUMBER: S124RDIP-S575D1205U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	787.3	787.3	787.3	787.3	787.3	787.3	787.3
2.5°	825.9	827.0	827.7	830.2	830.5	832.7	830.5
5°	894.2	898.7	905.6	912.6	913.3	917.7	909.8
7.5°	970.9	981.1	987.6	998.8	1003.3	1006.1	1001.5
10°	1023.7	1033.1	1050.0	1058.3	1066.5	1067.7	1064.0
12.5°	1074.6	1089.7	1103.0	1118.7	1118.3	1129.4	1125.4
15°	1142.6	1158.1	1176.6	1194.0	1200.4	1200.4	1205.4
17.5°	1191.1	1219.6	1238.6	1252.3	1267.3	1269.9	1268.1
20°	1223.8	1254.6	1274.9	1292.7	1302.8	1305.7	1305.7
22.5°	1248.2	1274.4	1294.2	1310.2	1318.6	1321.9	1320.9
25°	1265.1	1287.6	1299.7	1304.4	1306.6	1305.9	1300.0
27.5°	1241.9	1241.0	1233.3	1218.7	1207.8	1201.1	1193.5
30°	1197.8	1181.3	1162.3	1141.3	1114.4	1093.7	1087.4
32.5°	1132.1	1095.0	1062.8	1027.9	998.9	978.3	969.6
35°	1004.9	946.2	898.4	856.5	826.1	807.0	800.6
37.5°	854.1	797.3	738.0	697.4	672.1	652.9	645.7
40°	758.1	696.3	644.6	606.5	580.5	561.8	561.5
42.5°	670.6	611.6	562.9	535.5	507.4	495.0	495.0
45°	549.1	501.8	460.6	439.0	422.2	412.1	409.2
47.5°	454.6	415.6	388.1	370.9	357.2	350.7	346.5
50°	401.6	367.4	345.4	330.5	322.9	314.7	314.1
52.5°	357.4	329.8	312.7	300.6	291.0	286.0	286.2
55°	300.4	278.5	266.4	257.2	249.6	245.8	244.3
57.5°	253.1	236.7	227.9	219.5	216.2	213.2	212.4
60°	223.6	212.5	204.3	197.6	192.9	191.9	191.6
62.5°	199.3	187.7	182.0	176.8	173.3	171.9	171.3
65°	164.3	155.7	150.7	146.6	145.3	143.1	142.8
67.5°	132.5	127.3	124.0	121.2	119.4	119.3	119.3
70°	112.9	110.1	107.2	105.7	104.7	104.0	104.0
72.5°	96.2	94.1	91.7	90.9	90.7	90.1	89.8
75°	73.3	71.1	71.3	69.8	68.5	66.9	66.0
77.5°	51.9	50.4	50.1	49.9	48.8	48.6	49.1
80°	40.3	38.7	38.4	38.7	38.4	37.4	37.4
82.5°	30.7	29.4	29.0	28.8	28.5	28.8	28.3
85°	16.5	15.9	15.9	15.9	16.5	16.1	15.9
87.5°	9.5	9.4	9.6	9.5	9.8	9.3	9.5
90°	18.0	18.9	18.9	19.9	20.9	19.9	19.9
92.5°	140.0	111.5	92.5	81.3	76.1	73.0	73.0
95°	555.1	428.2	336.3	289.9	260.6	243.4	231.1
97.5°	982.6	890.0	791.1	723.0	666.0	637.6	617.9
100°	1161.5	1115.1	1045.0	962.5	904.7	876.4	868.8
102.5°	1231.2	1244.6	1215.4	1164.9	1123.0	1093.1	1087.0
105°	1225.0	1318.7	1357.6	1359.5	1351.9	1338.6	1332.9
107.5°	1127.4	1259.5	1343.9	1390.7	1412.3	1421.8	1424.3
110°	1051.6	1189.0	1293.1	1360.4	1400.2	1417.3	1425.8



TEST NUMBER: P332921-930

CATALOG NUMBER: S124RDIP-S575D1205U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	984.9	1114.7	1218.9	1295.3	1343.4	1367.3	1381.1
115°	908.6	1019.4	1110.4	1185.2	1242.0	1272.4	1279.9
117.5°	865.0	952.1	1029.2	1093.1	1140.8	1171.5	1177.4
120°	846.0	921.8	989.0	1043.1	1084.8	1109.4	1119.8
122.5°	833.9	902.9	961.8	1007.5	1043.1	1063.9	1074.3
125°	814.7	880.1	932.2	970.1	997.6	1015.6	1021.2
127.5°	792.2	857.4	906.9	944.9	969.4	984.6	990.2
130°	774.0	838.5	888.7	927.5	951.1	966.3	972.0
132.5°	753.6	816.4	866.7	904.7	931.5	945.8	951.5
135°	722.8	780.6	828.0	865.9	892.4	907.6	913.3
137.5°	693.5	742.2	785.0	820.4	846.6	859.1	865.9
140°	674.5	717.1	756.9	790.1	811.0	824.2	831.8
142.5°	658.6	695.2	729.7	759.0	778.4	790.1	795.4
145°	636.7	665.0	691.6	715.3	731.4	740.9	745.6
147.5°	617.7	640.4	661.3	678.7	692.5	699.8	701.4
150°	606.3	625.3	642.3	657.5	669.8	675.5	676.5
152.5°	594.9	612.4	626.4	639.3	649.3	652.7	653.7
155°	578.9	593.0	604.5	613.9	621.5	624.4	624.4
157.5°	563.0	574.9	584.0	591.2	596.9	598.6	598.6
160°	552.3	562.7	570.3	576.0	581.7	582.6	582.6
162.5°	542.5	550.7	557.4	561.6	567.3	568.3	567.4
165°	527.7	534.3	539.1	542.8	546.7	545.7	544.8
167.5°	515.2	520.5	523.3	525.2	527.7	527.5	526.8
170°	506.9	510.6	513.5	515.4	516.3	515.4	515.4
172.5°	500.0	502.3	504.3	505.5	506.5	505.5	504.0
175°	490.7	492.6	492.6	492.6	494.6	492.6	490.7
177.5°	485.3	485.3	486.0	485.3	486.0	484.5	483.0
180°	482.2	482.2	482.2	482.2	482.2	482.2	482.2

(END OF REPORT)