

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332903-930

Luminaire Tested: **S124RDIP-S575D590U930-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332903-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIP-S575D590U930-4F0-1E-UDD-A4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 575 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3713.2 lumens  
Efficiency: N/A  
Efficacy: 113.2 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 32.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332903-930

CATALOG NUMBER: S124RDIP-S575D590U930-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P332903-930

CATALOG NUMBER: S124RDIP-S575D590U930-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	54
1	99	95	91	88	92	88	85	82	76	73	71	64	62	61	53	52	51	46
2	91	83	78	73	84	78	73	68	67	63	60	57	54	52	48	46	44	39
3	83	74	67	61	77	69	63	58	59	55	51	51	47	44	43	40	38	34
4	76	66	58	52	70	61	54	49	53	48	44	45	41	38	38	35	33	30
5	70	59	51	45	65	55	48	43	48	42	38	41	37	33	35	32	29	26
6	65	53	45	39	60	49	42	37	43	37	33	37	33	29	32	28	26	23
7	60	48	40	34	55	45	38	33	39	34	29	34	29	26	29	26	23	20
8	56	43	36	31	52	41	34	29	36	30	26	31	27	23	27	23	21	18
9	52	40	32	27	48	37	31	26	33	27	24	29	24	21	25	21	19	17
10	48	37	29	25	45	34	28	24	30	25	21	26	22	19	23	20	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	6356	6356	6356	6356
5°	7373	6375	5635	6375
10°	8722	6347	5029	6347
15°	10074	6288	4322	6288
20°	11217	6208	3908	6208
25°	11580	6128	3628	6128
30°	10137	6032	3459	6032
35°	7890	5889	3358	5889
40°	5917	5727	3303	5727
45°	4672	5465	3273	5465
50°	3945	5163	3180	5163
55°	3438	4830	3009	4830
60°	3094	4487	2662	4487
65°	2728	4115	2290	4115
70°	2455	3729	2068	3729
75°	2059	3306	1762	3306
80°	1739	2817	1650	2817
85°	1473	2205	1473	2205



TEST NUMBER: P332903-930

CATALOG NUMBER: S124RDIP-S575D590U930-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	76.3	2.1
10°-20°	230.1	6.2
20°-30°	359.9	9.7
30°-40°	400.1	10.8
40°-50°	355.0	9.6
50°-60°	276.6	7.4
60°-70°	181.1	4.9
70°-80°	89.1	2.4
80°-90°	23.3	0.6
90°-100°	171.0	4.6
100°-110°	355.9	9.6
110°-120°	318.7	8.6
120°-130°	268.1	7.2
130°-140°	223.6	6.0
140°-150°	170.8	4.6
150°-160°	120.0	3.2
160°-170°	70.6	1.9
170°-180°	23.0	0.6
0°-30°	666.3	17.9
0°-40°	1066.4	28.7
0°-60°	1698.1	45.7
0°-90°	1991.5	53.6
90°-120°	845.6	22.8
90°-150°	1508.1	40.6
90°-180°	1722.0	46.4
0°-180°	3713.2	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	787	787	787	787	787	
5°	910	787	695	787	910	92
15°	1205	752	517	752	1205	343
25°	1300	688	407	688	1300	577
35°	801	598	341	598	801	502
45°	409	479	287	479	409	324
55°	244	343	214	343	244	222
65°	143	215	120	215	143	144
75°	66	106	56	106	66	73
85°	16	24	16	24	16	18
90°	10	0	10	0	10	9
95°	114	15	114	15	114	176
105°	654	54	654	54	654	647
115°	628	96	628	96	628	624
125°	501	134	501	134	501	456
135°	448	159	448	159	448	346
145°	366	183	366	183	366	232
155°	306	208	306	208	306	143
165°	267	226	267	226	267	77
175°	241	236	241	236	241	23
180°	237	237	237	237	237	



TEST NUMBER: P332903-930

CATALOG NUMBER: S124RDIP-S575D590U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3
2.5°	830.5	832.7	830.5	830.2	827.7	827.0	825.9	822.6	816.5	812.9	813.8
5°	909.8	917.7	913.3	912.6	905.6	898.7	894.2	884.1	873.3	866.0	860.0
7.5°	1001.5	1006.1	1003.3	998.8	987.6	981.1	970.9	957.5	938.2	923.3	909.9
10°	1064.0	1067.7	1066.5	1058.3	1050.0	1033.1	1023.7	1004.9	980.5	961.2	943.1
12.5°	1125.4	1129.4	1118.3	1118.7	1103.0	1089.7	1074.6	1051.2	1022.9	997.9	975.3
15°	1205.4	1200.4	1200.4	1194.0	1176.6	1158.1	1142.6	1117.9	1082.3	1052.6	1021.2
17.5°	1268.1	1269.9	1267.3	1252.3	1238.6	1219.6	1191.1	1162.2	1129.2	1089.2	1057.1
20°	1305.7	1305.7	1302.8	1292.7	1274.9	1254.6	1223.8	1192.5	1150.6	1110.3	1074.1
22.5°	1320.9	1321.9	1318.6	1310.2	1294.2	1274.4	1248.2	1216.3	1173.1	1127.8	1083.0
25°	1300.0	1305.9	1306.6	1304.4	1299.7	1287.6	1265.1	1232.4	1193.7	1144.5	1096.3
27.5°	1193.5	1201.1	1207.8	1218.7	1233.3	1241.0	1241.9	1225.3	1191.6	1144.3	1095.8
30°	1087.4	1093.7	1114.4	1141.3	1162.3	1181.3	1197.8	1202.2	1183.2	1140.7	1089.6
32.5°	969.6	978.3	998.9	1027.9	1062.8	1095.0	1132.1	1151.0	1150.5	1124.9	1077.7
35°	800.6	807.0	826.1	856.5	898.4	946.2	1004.9	1050.6	1081.7	1079.5	1050.6
37.5°	645.7	652.9	672.1	697.4	738.0	797.3	854.1	917.0	974.5	1006.8	997.1
40°	561.5	561.8	580.5	606.5	644.6	696.3	758.1	827.9	892.0	944.4	954.5
42.5°	495.0	495.0	507.4	535.5	562.9	611.6	670.6	739.9	814.9	875.3	902.2
45°	409.2	412.1	422.2	439.0	460.6	501.8	549.1	613.5	697.6	769.2	814.0
47.5°	346.5	350.7	357.2	370.9	388.1	415.6	454.6	512.5	580.9	659.7	723.4
50°	314.1	314.7	322.9	330.5	345.4	367.4	401.6	449.8	512.7	588.4	659.2
52.5°	286.2	286.0	291.0	300.6	312.7	329.8	357.4	401.4	457.1	525.0	598.0
55°	244.3	245.8	249.6	257.2	266.4	278.5	300.4	333.4	377.2	435.2	501.5
57.5°	212.4	213.2	216.2	219.5	227.9	236.7	253.1	276.0	312.9	360.4	422.2
60°	191.6	191.9	192.9	197.6	204.3	212.5	223.6	243.0	274.1	317.6	366.4
62.5°	171.3	171.9	173.3	176.8	182.0	187.7	199.3	214.8	240.6	277.7	321.7
65°	142.8	143.1	145.3	146.6	150.7	155.7	164.3	174.8	192.6	223.6	257.0
67.5°	119.3	119.3	119.4	121.2	124.0	127.3	132.5	140.9	154.3	173.3	202.7
70°	104.0	104.0	104.7	105.7	107.2	110.1	112.9	119.3	129.1	144.6	167.1
72.5°	89.8	90.1	90.7	90.9	91.7	94.1	96.2	100.2	107.5	119.3	137.5
75°	66.0	66.9	68.5	69.8	71.3	71.1	73.3	75.8	78.0	85.0	95.5
77.5°	49.1	48.6	48.8	49.9	50.1	50.4	51.9	53.9	55.6	58.9	62.6
80°	37.4	37.4	38.4	38.7	38.4	38.7	40.3	41.3	41.9	43.1	46.6
82.5°	28.3	28.8	28.5	28.8	29.0	29.4	30.7	30.8	31.5	32.0	33.4
85°	15.9	16.1	16.5	15.9	15.9	15.9	16.5	16.8	17.4	17.1	17.8
87.5°	7.5	7.3	7.7	7.5	7.7	7.4	7.6	8.0	7.4	7.7	7.6
90°	9.8	9.8	10.2	9.8	9.3	9.3	8.8	8.4	7.9	8.4	7.4
92.5°	35.8	35.8	37.4	39.9	45.4	54.7	68.7	91.3	122.9	147.5	129.1
95°	113.5	119.5	127.9	142.4	165.1	210.2	272.6	344.6	389.7	379.0	286.0
97.5°	303.3	313.0	326.9	355.0	388.3	436.9	482.4	509.2	489.7	399.3	267.7
100°	426.5	430.2	444.2	472.5	513.0	547.4	570.2	560.9	493.0	373.9	242.8
102.5°	533.6	536.6	551.3	571.9	596.7	611.1	604.5	558.3	465.0	342.3	226.0
105°	654.4	657.1	663.7	667.4	666.5	647.4	601.4	520.9	414.4	305.1	211.7
107.5°	699.2	698.0	693.3	682.7	659.7	618.3	553.4	467.8	373.5	284.3	209.0
110°	699.9	695.8	687.4	667.9	634.9	583.7	516.2	435.8	353.0	277.2	209.8



TEST NUMBER: P332903-930

CATALOG NUMBER: S124RDIP-S575D590U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	678.0	671.2	659.5	635.9	598.3	547.2	483.5	412.4	341.4	273.9	212.0
115°	628.4	624.6	609.8	581.8	545.1	500.4	446.1	388.8	330.7	272.1	216.3
117.5°	578.0	575.1	560.0	536.6	505.2	467.4	424.6	377.2	325.9	271.6	220.8
120°	549.8	544.6	532.6	512.1	485.5	452.5	415.3	372.1	323.3	271.6	224.2
122.5°	527.4	522.3	512.1	494.6	472.1	443.2	409.4	367.6	320.2	271.3	227.6
125°	501.3	498.6	489.8	476.2	457.6	432.0	400.0	360.0	315.4	270.7	232.5
127.5°	486.1	483.3	475.9	463.9	445.2	420.9	388.9	350.7	308.8	269.6	236.5
130°	477.2	474.4	466.9	455.3	436.3	411.6	380.0	343.2	304.6	269.3	239.5
132.5°	467.2	464.3	457.3	444.2	425.4	400.8	369.9	335.4	300.9	268.9	242.1
135°	448.3	445.6	438.1	425.1	406.5	383.2	354.9	324.7	295.3	268.3	246.1
137.5°	425.1	421.8	415.6	402.8	385.4	364.4	340.5	314.9	290.5	268.2	248.3
140°	408.4	404.6	398.1	387.9	371.6	352.0	331.2	309.2	287.9	267.9	250.2
142.5°	390.4	387.9	382.1	372.6	358.2	341.3	323.3	304.1	285.7	267.9	251.7
145°	366.0	363.7	359.1	351.1	339.5	326.5	312.5	296.7	281.8	266.9	252.6
147.5°	344.4	343.5	340.0	333.2	324.7	314.4	303.2	290.7	278.4	265.3	253.0
150°	332.1	331.6	328.8	322.8	315.4	307.0	297.7	287.0	275.8	264.2	253.0
152.5°	320.9	320.4	318.8	313.8	307.5	300.6	292.0	282.8	272.8	262.3	252.3
155°	306.5	306.5	305.1	301.4	296.7	291.1	284.1	276.7	268.3	259.5	251.1
157.5°	293.8	293.8	293.0	290.2	286.7	282.2	276.4	270.1	263.8	256.7	250.0
160°	286.0	286.0	285.6	282.7	280.0	276.2	271.2	266.0	260.5	254.4	248.8
162.5°	278.6	279.0	278.5	275.7	273.7	270.3	266.3	262.0	257.5	252.2	247.7
165°	267.4	267.9	268.3	266.5	264.6	262.3	259.0	256.2	252.6	248.8	245.6
167.5°	258.6	258.9	259.0	257.9	256.9	255.5	252.9	250.8	248.1	245.5	243.4
170°	253.0	253.0	253.5	253.0	252.1	250.7	248.8	247.4	245.1	243.2	241.8
172.5°	247.4	248.2	248.7	248.2	247.6	246.6	245.5	244.4	242.5	241.0	240.4
175°	240.9	241.8	242.8	241.8	241.8	241.8	240.9	240.4	239.5	238.6	238.6
177.5°	237.1	237.8	238.6	238.2	238.6	238.2	238.2	237.8	237.5	237.1	237.1
180°	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8



TEST NUMBER: P332903-930

CATALOG NUMBER: S124RDIP-S575D590U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3
2.5°	811.2	807.6	805.8	801.8	797.0	794.4	792.1	788.9	784.6	780.0	776.7
5°	852.4	844.7	835.2	823.8	813.7	803.8	795.2	786.7	776.9	766.7	756.6
7.5°	894.6	879.6	863.5	844.7	826.6	810.0	794.8	780.2	763.7	748.9	735.4
10°	924.1	903.8	881.3	857.5	833.6	813.0	792.7	774.3	754.0	736.0	720.7
12.5°	947.9	924.1	897.0	867.3	838.7	813.8	790.4	766.5	743.4	723.7	703.4
15°	987.5	954.8	918.4	882.8	845.7	811.8	780.3	752.4	726.1	698.5	679.1
17.5°	1014.7	975.9	931.6	888.9	845.1	805.0	768.8	735.6	705.2	677.0	654.0
20°	1030.9	988.1	939.0	890.4	841.2	798.4	759.5	722.6	691.2	660.8	637.0
22.5°	1040.1	992.7	939.0	888.1	837.2	790.8	748.0	709.7	675.5	645.1	618.7
25°	1043.0	992.2	937.3	879.0	823.2	774.0	729.6	688.0	650.0	619.5	591.6
27.5°	1038.9	979.2	923.0	863.1	805.5	753.7	707.0	663.3	625.3	592.6	563.9
30°	1032.8	968.8	908.5	846.4	788.0	738.2	689.0	647.1	607.5	573.6	544.7
32.5°	1019.7	956.1	891.3	827.5	768.4	717.1	670.5	628.4	589.5	554.7	524.1
35°	993.5	929.1	858.7	793.4	735.3	682.0	638.2	597.6	560.5	523.4	491.1
37.5°	959.0	893.3	823.2	751.7	693.6	643.3	603.1	565.0	528.7	494.9	459.0
40°	926.6	866.7	794.3	723.3	663.7	615.1	578.0	543.4	507.0	473.3	437.4
42.5°	887.3	836.2	763.1	691.8	632.9	586.1	551.5	517.8	484.6	452.0	414.6
45°	821.6	782.9	714.4	645.9	586.5	540.2	508.5	478.7	449.5	418.4	383.2
47.5°	746.3	720.2	661.0	590.8	536.0	494.3	463.7	439.3	414.6	383.5	352.6
50°	694.1	677.3	620.2	556.1	503.8	465.4	434.0	411.1	390.5	360.7	333.0
52.5°	638.2	629.3	581.1	519.8	469.2	431.6	404.8	384.3	363.4	338.6	312.7
55°	553.3	558.0	517.1	464.1	416.5	384.8	360.4	343.2	325.5	304.5	284.5
57.5°	466.3	483.7	456.2	409.7	365.1	335.8	317.4	303.0	288.1	270.7	253.6
60°	414.3	428.8	413.4	372.4	333.4	306.1	289.0	277.9	262.9	247.1	234.1
62.5°	363.5	379.1	369.9	336.9	300.7	277.2	262.1	251.8	240.7	226.8	213.3
65°	299.8	309.9	305.5	282.7	257.0	236.9	223.0	215.4	205.2	195.1	183.0
67.5°	229.6	249.2	246.6	234.5	212.3	196.7	187.5	180.8	171.5	164.0	155.8
70°	188.7	206.8	206.5	196.7	184.6	170.0	163.7	158.0	149.7	142.4	135.7
72.5°	154.5	171.0	173.5	166.0	157.8	146.7	140.6	136.6	128.7	123.7	118.2
75°	108.2	120.3	123.4	123.4	119.6	113.9	108.5	106.0	100.2	95.8	92.6
77.5°	70.9	78.5	83.5	84.6	85.2	83.3	78.8	77.0	72.7	71.1	68.1
80°	50.1	55.2	60.9	62.8	64.4	63.8	61.9	60.6	56.5	54.9	53.6
82.5°	34.7	37.4	42.2	46.3	45.9	47.5	45.9	44.8	41.7	41.2	39.9
85°	18.1	18.4	19.0	21.9	23.5	24.1	24.5	23.8	22.8	22.8	20.6
87.5°	7.4	7.2	7.1	7.1	7.3	8.2	8.6	8.7	8.2	7.7	7.0
90°	6.5	6.5	3.8	3.8	3.3	2.8	1.4	0.5	1.4	2.8	3.3
92.5°	93.9	57.9	34.2	24.5	17.8	12.1	7.7	5.3	7.7	12.1	17.8
95°	174.9	98.6	58.1	38.6	27.5	21.4	16.7	15.3	16.7	21.4	27.5
97.5°	157.2	94.2	63.1	46.7	37.1	31.6	27.6	27.6	27.6	31.6	37.1
100°	147.9	95.3	67.9	53.0	44.2	38.6	35.4	35.4	35.4	38.6	44.2
102.5°	145.3	99.1	74.2	60.1	51.6	46.4	43.5	42.8	43.5	46.4	51.6
105°	146.5	107.9	85.6	72.1	63.8	58.1	55.8	54.4	55.8	58.1	63.8
107.5°	153.4	118.2	97.8	84.5	76.5	70.5	68.2	67.3	68.2	70.5	76.5
110°	158.6	126.0	105.6	93.0	84.6	79.1	76.7	75.8	76.7	79.1	84.6





TEST NUMBER: P332903-930

CATALOG NUMBER: S124RDIP-S575D590U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	164.2	133.5	113.7	101.2	92.9	87.6	85.0	84.0	85.0	87.6	92.9
115°	173.0	145.1	126.5	114.0	105.1	100.4	97.2	95.8	97.2	100.4	105.1
117.5°	182.1	156.4	138.7	125.6	117.4	112.3	109.4	108.1	109.4	112.3	117.4
120°	188.3	164.2	146.5	133.5	125.6	120.4	117.2	116.3	117.2	120.4	125.6
122.5°	194.3	171.6	153.9	141.3	132.6	127.9	124.7	123.7	124.7	127.9	132.6
125°	203.3	181.8	165.1	152.1	143.2	138.1	135.3	133.5	135.3	138.1	143.2
127.5°	211.0	191.4	175.1	162.0	152.8	147.0	143.7	142.1	143.7	147.0	152.8
130°	215.8	197.6	181.8	168.4	159.6	152.5	148.8	147.0	148.8	152.5	159.6
132.5°	220.6	202.8	187.0	174.3	164.8	158.2	153.3	151.8	153.3	158.2	164.8
135°	227.0	210.2	194.9	182.8	173.0	165.1	160.5	158.6	160.5	165.1	173.0
137.5°	231.5	215.8	201.5	190.0	179.8	172.3	167.1	165.4	167.1	172.3	179.8
140°	234.4	219.6	205.5	194.4	184.7	176.8	171.6	170.2	171.6	176.8	184.7
142.5°	236.6	222.9	209.3	198.5	189.1	181.6	176.8	175.5	176.8	181.6	189.1
145°	239.0	226.5	214.4	204.2	195.3	188.8	184.2	182.8	184.2	188.8	195.3
147.5°	241.2	230.2	218.9	209.7	202.3	195.6	191.5	191.0	191.5	195.6	202.3
150°	242.3	232.1	221.8	213.0	206.0	200.5	196.7	196.2	196.7	200.5	206.0
152.5°	243.0	233.6	224.5	216.4	210.1	204.9	201.2	201.1	201.2	204.9	210.1
155°	243.7	235.8	227.9	220.9	215.8	211.2	208.4	207.9	208.4	211.2	215.8
157.5°	243.7	237.4	230.6	225.2	220.7	217.1	214.5	214.5	214.5	217.1	220.7
160°	243.7	238.1	232.5	227.4	223.7	220.5	218.6	218.6	218.6	220.5	223.7
162.5°	243.7	238.9	233.7	229.7	226.3	223.4	221.9	222.3	221.9	223.4	226.3
165°	242.8	239.0	234.9	232.1	229.8	227.4	226.5	226.5	226.5	227.4	229.8
167.5°	241.7	239.0	235.9	233.7	232.4	230.6	230.2	230.6	230.2	230.6	232.4
170°	240.9	238.6	236.3	234.9	233.9	232.5	232.1	232.5	232.1	232.5	233.9
172.5°	240.2	238.2	236.6	235.6	235.1	234.0	233.9	234.4	233.9	234.0	235.1
175°	239.0	237.7	236.8	236.8	236.3	235.8	235.8	236.3	235.8	235.8	236.3
177.5°	237.8	237.1	236.8	236.8	236.8	236.4	236.8	237.1	236.8	236.4	236.8
180°	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8



TEST NUMBER: P332903-930

CATALOG NUMBER: S124RDIP-S575D590U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3
2.5°	773.1	770.6	767.3	763.4	758.9	754.9	753.1	754.6	755.4	753.3	753.1
5°	749.6	741.7	735.3	725.8	718.2	711.8	707.4	705.5	706.1	701.1	699.8
7.5°	723.1	713.7	703.4	692.0	681.5	672.2	667.3	664.6	659.3	657.0	653.1
10°	706.1	693.4	683.3	669.9	657.9	646.8	641.4	637.0	631.6	629.0	623.6
12.5°	688.6	673.9	662.8	648.9	636.6	623.2	618.1	609.8	601.4	596.1	589.1
15°	663.9	646.2	632.5	616.0	601.4	586.2	572.6	557.3	551.6	539.6	532.6
17.5°	635.0	617.0	600.1	578.0	555.5	536.6	522.0	507.5	498.7	491.1	487.5
20°	616.0	599.6	576.1	550.4	525.3	504.3	492.6	483.1	473.6	468.2	464.4
22.5°	598.0	577.0	549.7	522.0	496.9	480.5	470.6	460.8	453.1	447.9	442.9
25°	567.9	540.2	511.4	479.6	462.5	448.3	437.4	429.5	424.8	418.1	415.6
27.5°	536.8	503.4	471.5	450.2	432.4	419.3	409.9	404.0	397.9	393.6	390.4
30°	512.9	479.0	450.5	430.2	412.1	401.3	393.6	386.7	382.0	378.5	375.9
32.5°	489.3	455.4	431.4	409.6	395.3	384.8	376.7	371.5	367.7	363.2	361.7
35°	455.2	425.1	404.1	384.5	369.9	360.4	354.0	348.6	345.4	344.2	343.2
37.5°	422.4	397.7	375.2	359.1	346.1	338.6	331.1	328.5	326.3	324.0	325.1
40°	401.6	378.5	358.5	341.4	330.8	322.6	318.1	315.0	313.1	313.1	313.1
42.5°	383.6	360.9	341.4	326.1	315.6	308.7	303.7	301.0	300.4	300.1	301.7
45°	355.6	334.7	315.0	302.3	293.4	286.4	283.6	281.4	281.4	282.7	283.0
47.5°	327.9	308.3	292.4	278.3	270.1	265.8	263.3	262.1	262.3	263.5	265.0
50°	310.9	291.6	276.0	263.3	255.7	251.5	249.3	248.7	249.3	249.3	251.5
52.5°	292.4	275.0	259.8	249.1	240.4	236.6	235.4	234.5	234.9	235.9	236.8
55°	265.2	249.6	235.1	224.9	218.6	216.1	213.2	213.5	212.9	213.5	213.5
57.5°	238.0	224.0	210.4	202.4	196.8	193.1	190.0	190.9	190.0	189.8	189.3
60°	220.5	205.2	194.4	187.2	180.8	177.7	174.8	175.5	174.5	173.8	172.6
62.5°	201.5	188.7	178.5	171.5	166.3	162.7	159.8	159.1	156.9	154.8	152.0
65°	173.8	163.4	154.2	147.5	142.8	139.9	137.7	135.7	131.0	126.0	123.4
67.5°	147.0	139.4	130.9	125.2	121.4	117.6	113.4	110.1	105.7	102.9	101.3
70°	129.7	122.5	115.1	109.7	105.7	102.2	97.3	95.1	92.0	90.7	89.1
72.5°	113.2	106.5	99.6	94.8	90.4	87.6	84.0	81.7	80.3	79.8	78.2
75°	88.2	82.8	77.7	73.3	69.8	67.9	66.3	64.7	64.1	61.2	59.6
77.5°	64.3	60.7	57.6	54.5	51.9	50.7	47.6	45.8	44.8	43.4	43.0
80°	50.1	47.6	44.4	42.5	39.1	37.7	36.4	36.2	35.9	35.5	35.2
82.5°	37.7	35.1	32.0	30.8	29.9	29.1	28.4	28.0	27.7	27.9	27.9
85°	19.0	17.8	17.8	17.4	17.1	16.8	16.5	16.5	16.1	16.5	16.1
87.5°	7.1	6.8	7.4	6.8	7.3	7.5	7.2	7.3	7.6	7.2	7.2
90°	3.8	3.8	6.5	6.5	7.4	8.4	7.9	8.4	8.8	9.3	9.3
92.5°	24.5	34.2	57.9	93.9	129.1	147.5	122.9	91.3	68.7	54.7	45.4
95°	38.6	58.1	98.6	174.9	286.0	379.0	389.7	344.6	272.6	210.2	165.1
97.5°	46.7	63.1	94.2	157.2	267.7	399.3	489.7	509.2	482.4	436.9	388.3
100°	53.0	67.9	95.3	147.9	242.8	373.9	493.0	560.9	570.2	547.4	513.0
102.5°	60.1	74.2	99.1	145.3	226.0	342.3	465.0	558.3	604.5	611.1	596.7
105°	72.1	85.6	107.9	146.5	211.7	305.1	414.4	520.9	601.4	647.4	666.5
107.5°	84.5	97.8	118.2	153.4	209.0	284.3	373.5	467.8	553.4	618.3	659.7
110°	93.0	105.6	126.0	158.6	209.8	277.2	353.0	435.8	516.2	583.7	634.9



TEST NUMBER: P332903-930

CATALOG NUMBER: S124RDIP-S575D590U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	101.2	113.7	133.5	164.2	212.0	273.9	341.4	412.4	483.5	547.2	598.3
115°	114.0	126.5	145.1	173.0	216.3	272.1	330.7	388.8	446.1	500.4	545.1
117.5°	125.6	138.7	156.4	182.1	220.8	271.6	325.9	377.2	424.6	467.4	505.2
120°	133.5	146.5	164.2	188.3	224.2	271.6	323.3	372.1	415.3	452.5	485.5
122.5°	141.3	153.9	171.6	194.3	227.6	271.3	320.2	367.6	409.4	443.2	472.1
125°	152.1	165.1	181.8	203.3	232.5	270.7	315.4	360.0	400.0	432.0	457.6
127.5°	162.0	175.1	191.4	211.0	236.5	269.6	308.8	350.7	388.9	420.9	445.2
130°	168.4	181.8	197.6	215.8	239.5	269.3	304.6	343.2	380.0	411.6	436.3
132.5°	174.3	187.0	202.8	220.6	242.1	268.9	300.9	335.4	369.9	400.8	425.4
135°	182.8	194.9	210.2	227.0	246.1	268.3	295.3	324.7	354.9	383.2	406.5
137.5°	190.0	201.5	215.8	231.5	248.3	268.2	290.5	314.9	340.5	364.4	385.4
140°	194.4	205.5	219.6	234.4	250.2	267.9	287.9	309.2	331.2	352.0	371.6
142.5°	198.5	209.3	222.9	236.6	251.7	267.9	285.7	304.1	323.3	341.3	358.2
145°	204.2	214.4	226.5	239.0	252.6	266.9	281.8	296.7	312.5	326.5	339.5
147.5°	209.7	218.9	230.2	241.2	253.0	265.3	278.4	290.7	303.2	314.4	324.7
150°	213.0	221.8	232.1	242.3	253.0	264.2	275.8	287.0	297.7	307.0	315.4
152.5°	216.4	224.5	233.6	243.0	252.3	262.3	272.8	282.8	292.0	300.6	307.5
155°	220.9	227.9	235.8	243.7	251.1	259.5	268.3	276.7	284.1	291.1	296.7
157.5°	225.2	230.6	237.4	243.7	250.0	256.7	263.8	270.1	276.4	282.2	286.7
160°	227.4	232.5	238.1	243.7	248.8	254.4	260.5	266.0	271.2	276.2	280.0
162.5°	229.7	233.7	238.9	243.7	247.7	252.2	257.5	262.0	266.3	270.3	273.7
165°	232.1	234.9	239.0	242.8	245.6	248.8	252.6	256.2	259.0	262.3	264.6
167.5°	233.7	235.9	239.0	241.7	243.4	245.5	248.1	250.8	252.9	255.5	256.9
170°	234.9	236.3	238.6	240.9	241.8	243.2	245.1	247.4	248.8	250.7	252.1
172.5°	235.6	236.6	238.2	240.2	240.4	241.0	242.5	244.4	245.5	246.6	247.6
175°	236.8	236.8	237.7	239.0	238.6	238.6	239.5	240.4	240.9	241.8	241.8
177.5°	236.8	236.8	237.1	237.8	237.1	237.1	237.5	237.8	238.2	238.2	238.6
180°	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8



TEST NUMBER: P332903-930

CATALOG NUMBER: S124RDIP-S575D590U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3
2.5°	751.5	752.0	750.3	749.7	750.3	752.0	751.5	753.1	753.3	755.4	754.6
5°	697.2	696.6	695.0	695.4	695.0	696.6	697.2	699.8	701.1	706.1	705.5
7.5°	650.8	648.3	649.1	646.5	649.1	648.3	650.8	653.1	657.0	659.3	664.6
10°	622.4	618.9	616.0	613.5	616.0	618.9	622.4	623.6	629.0	631.6	637.0
12.5°	583.6	580.6	576.7	577.5	576.7	580.6	583.6	589.1	596.1	601.4	609.8
15°	528.5	523.7	516.1	517.1	516.1	523.7	528.5	532.6	539.6	551.6	557.3
17.5°	481.8	481.9	478.4	479.2	478.4	481.9	481.8	487.5	491.1	498.7	507.5
20°	457.7	455.5	455.8	454.9	455.8	455.5	457.7	464.4	468.2	473.6	483.1
22.5°	441.0	438.3	436.0	434.1	436.0	438.3	441.0	442.9	447.9	453.1	460.8
25°	412.7	410.8	408.0	407.3	408.0	410.8	412.7	415.6	418.1	424.8	429.5
27.5°	387.8	387.4	386.3	384.8	386.3	387.4	387.8	390.4	393.6	397.9	404.0
30°	373.3	372.8	372.1	371.1	372.1	372.8	373.3	375.9	378.5	382.0	386.7
32.5°	360.4	360.0	359.4	359.5	359.4	360.0	360.4	361.7	363.2	367.7	371.5
35°	341.9	341.6	341.0	340.7	341.0	341.6	341.9	343.2	344.2	345.4	348.6
37.5°	324.7	325.5	325.1	325.1	325.1	325.5	324.7	325.1	324.0	326.3	328.5
40°	312.7	313.1	313.7	313.4	313.7	313.1	312.7	313.1	313.1	313.1	315.0
42.5°	302.9	303.0	303.9	302.7	303.9	303.0	302.9	301.7	300.1	300.4	301.0
45°	285.2	287.1	286.7	286.7	286.7	287.1	285.2	283.0	282.7	281.4	281.4
47.5°	265.8	267.5	267.9	267.8	267.9	267.5	265.8	265.0	263.5	262.3	262.1
50°	253.2	252.5	253.5	253.2	253.5	252.5	253.2	251.5	249.3	249.3	248.7
52.5°	237.7	237.8	237.7	237.4	237.7	237.8	237.7	236.8	235.9	234.9	234.5
55°	213.8	214.1	213.5	213.8	213.5	214.1	213.8	213.5	213.5	212.9	213.5
57.5°	187.9	186.4	187.0	186.3	187.0	186.4	187.9	189.3	189.8	190.0	190.9
60°	169.4	166.9	166.2	164.9	166.2	166.9	169.4	172.6	173.8	174.5	175.5
62.5°	148.5	146.8	144.6	145.7	144.6	146.8	148.5	152.0	154.8	156.9	159.1
65°	120.8	119.6	118.6	119.9	118.6	119.6	120.8	123.4	126.0	131.0	135.7
67.5°	100.0	99.4	99.4	98.7	99.4	99.4	100.0	101.3	102.9	105.7	110.1
70°	89.1	88.2	88.2	87.6	88.2	88.2	89.1	89.1	90.7	92.0	95.1
72.5°	77.9	77.0	77.3	76.9	77.3	77.0	77.9	78.2	79.8	80.3	81.7
75°	57.7	56.2	56.2	56.5	56.2	56.2	57.7	59.6	61.2	64.1	64.7
77.5°	43.0	42.7	43.2	42.6	43.2	42.7	43.0	43.0	43.4	44.8	45.8
80°	35.2	34.9	34.6	35.5	34.6	34.9	35.2	35.2	35.5	35.9	36.2
82.5°	27.3	27.3	27.2	28.5	27.2	27.3	27.3	27.9	27.9	27.7	28.0
85°	16.5	15.9	16.5	15.9	16.5	15.9	16.5	16.1	16.5	16.1	16.5
87.5°	7.8	7.7	7.3	7.5	7.3	7.7	7.8	7.2	7.2	7.6	7.3
90°	9.8	10.2	9.8	9.8	9.8	10.2	9.8	9.3	9.3	8.8	8.4
92.5°	39.9	37.4	35.8	35.8	35.8	37.4	39.9	45.4	54.7	68.7	91.3
95°	142.4	127.9	119.5	113.5	119.5	127.9	142.4	165.1	210.2	272.6	344.6
97.5°	355.0	326.9	313.0	303.3	313.0	326.9	355.0	388.3	436.9	482.4	509.2
100°	472.5	444.2	430.2	426.5	430.2	444.2	472.5	513.0	547.4	570.2	560.9
102.5°	571.9	551.3	536.6	533.6	536.6	551.3	571.9	596.7	611.1	604.5	558.3
105°	667.4	663.7	657.1	654.4	657.1	663.7	667.4	666.5	647.4	601.4	520.9
107.5°	682.7	693.3	698.0	699.2	698.0	693.3	682.7	659.7	618.3	553.4	467.8
110°	667.9	687.4	695.8	699.9	695.8	687.4	667.9	634.9	583.7	516.2	435.8



TEST NUMBER: P332903-930

CATALOG NUMBER: S124RDIP-S575D590U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	635.9	659.5	671.2	678.0	671.2	659.5	635.9	598.3	547.2	483.5	412.4
115°	581.8	609.8	624.6	628.4	624.6	609.8	581.8	545.1	500.4	446.1	388.8
117.5°	536.6	560.0	575.1	578.0	575.1	560.0	536.6	505.2	467.4	424.6	377.2
120°	512.1	532.6	544.6	549.8	544.6	532.6	512.1	485.5	452.5	415.3	372.1
122.5°	494.6	512.1	522.3	527.4	522.3	512.1	494.6	472.1	443.2	409.4	367.6
125°	476.2	489.8	498.6	501.3	498.6	489.8	476.2	457.6	432.0	400.0	360.0
127.5°	463.9	475.9	483.3	486.1	483.3	475.9	463.9	445.2	420.9	388.9	350.7
130°	455.3	466.9	474.4	477.2	474.4	466.9	455.3	436.3	411.6	380.0	343.2
132.5°	444.2	457.3	464.3	467.2	464.3	457.3	444.2	425.4	400.8	369.9	335.4
135°	425.1	438.1	445.6	448.3	445.6	438.1	425.1	406.5	383.2	354.9	324.7
137.5°	402.8	415.6	421.8	425.1	421.8	415.6	402.8	385.4	364.4	340.5	314.9
140°	387.9	398.1	404.6	408.4	404.6	398.1	387.9	371.6	352.0	331.2	309.2
142.5°	372.6	382.1	387.9	390.4	387.9	382.1	372.6	358.2	341.3	323.3	304.1
145°	351.1	359.1	363.7	366.0	363.7	359.1	351.1	339.5	326.5	312.5	296.7
147.5°	333.2	340.0	343.5	344.4	343.5	340.0	333.2	324.7	314.4	303.2	290.7
150°	322.8	328.8	331.6	332.1	331.6	328.8	322.8	315.4	307.0	297.7	287.0
152.5°	313.8	318.8	320.4	320.9	320.4	318.8	313.8	307.5	300.6	292.0	282.8
155°	301.4	305.1	306.5	306.5	306.5	305.1	301.4	296.7	291.1	284.1	276.7
157.5°	290.2	293.0	293.8	293.8	293.8	293.0	290.2	286.7	282.2	276.4	270.1
160°	282.7	285.6	286.0	286.0	286.0	285.6	282.7	280.0	276.2	271.2	266.0
162.5°	275.7	278.5	279.0	278.6	279.0	278.5	275.7	273.7	270.3	266.3	262.0
165°	266.5	268.3	267.9	267.4	267.9	268.3	266.5	264.6	262.3	259.0	256.2
167.5°	257.9	259.0	258.9	258.6	258.9	259.0	257.9	256.9	255.5	252.9	250.8
170°	253.0	253.5	253.0	253.0	253.0	253.5	253.0	252.1	250.7	248.8	247.4
172.5°	248.2	248.7	248.2	247.4	248.2	248.7	248.2	247.6	246.6	245.5	244.4
175°	241.8	242.8	241.8	240.9	241.8	242.8	241.8	241.8	241.8	240.9	240.4
177.5°	238.2	238.6	237.8	237.1	237.8	238.6	238.2	238.6	238.2	238.2	237.8
180°	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8



TEST NUMBER: P332903-930

CATALOG NUMBER: S124RDIP-S575D590U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3
2.5°	753.1	754.9	758.9	763.4	767.3	770.6	773.1	776.7	780.0	784.6	788.9
5°	707.4	711.8	718.2	725.8	735.3	741.7	749.6	756.6	766.7	776.9	786.7
7.5°	667.3	672.2	681.5	692.0	703.4	713.7	723.1	735.4	748.9	763.7	780.2
10°	641.4	646.8	657.9	669.9	683.3	693.4	706.1	720.7	736.0	754.0	774.3
12.5°	618.1	623.2	636.6	648.9	662.8	673.9	688.6	703.4	723.7	743.4	766.5
15°	572.6	586.2	601.4	616.0	632.5	646.2	663.9	679.1	698.5	726.1	752.4
17.5°	522.0	536.6	555.5	578.0	600.1	617.0	635.0	654.0	677.0	705.2	735.6
20°	492.6	504.3	525.3	550.4	576.1	599.6	616.0	637.0	660.8	691.2	722.6
22.5°	470.6	480.5	496.9	522.0	549.7	577.0	598.0	618.7	645.1	675.5	709.7
25°	437.4	448.3	462.5	479.6	511.4	540.2	567.9	591.6	619.5	650.0	688.0
27.5°	409.9	419.3	432.4	450.2	471.5	503.4	536.8	563.9	592.6	625.3	663.3
30°	393.6	401.3	412.1	430.2	450.5	479.0	512.9	544.7	573.6	607.5	647.1
32.5°	376.7	384.8	395.3	409.6	431.4	455.4	489.3	524.1	554.7	589.5	628.4
35°	354.0	360.4	369.9	384.5	404.1	425.1	455.2	491.1	523.4	560.5	597.6
37.5°	331.1	338.6	346.1	359.1	375.2	397.7	422.4	459.0	494.9	528.7	565.0
40°	318.1	322.6	330.8	341.4	358.5	378.5	401.6	437.4	473.3	507.0	543.4
42.5°	303.7	308.7	315.6	326.1	341.4	360.9	383.6	414.6	452.0	484.6	517.8
45°	283.6	286.4	293.4	302.3	315.0	334.7	355.6	383.2	418.4	449.5	478.7
47.5°	263.3	265.8	270.1	278.3	292.4	308.3	327.9	352.6	383.5	414.6	439.3
50°	249.3	251.5	255.7	263.3	276.0	291.6	310.9	333.0	360.7	390.5	411.1
52.5°	235.4	236.6	240.4	249.1	259.8	275.0	292.4	312.7	338.6	363.4	384.3
55°	213.2	216.1	218.6	224.9	235.1	249.6	265.2	284.5	304.5	325.5	343.2
57.5°	190.0	193.1	196.8	202.4	210.4	224.0	238.0	253.6	270.7	288.1	303.0
60°	174.8	177.7	180.8	187.2	194.4	205.2	220.5	234.1	247.1	262.9	277.9
62.5°	159.8	162.7	166.3	171.5	178.5	188.7	201.5	213.3	226.8	240.7	251.8
65°	137.7	139.9	142.8	147.5	154.2	163.4	173.8	183.0	195.1	205.2	215.4
67.5°	113.4	117.6	121.4	125.2	130.9	139.4	147.0	155.8	164.0	171.5	180.8
70°	97.3	102.2	105.7	109.7	115.1	122.5	129.7	135.7	142.4	149.7	158.0
72.5°	84.0	87.6	90.4	94.8	99.6	106.5	113.2	118.2	123.7	128.7	136.6
75°	66.3	67.9	69.8	73.3	77.7	82.8	88.2	92.6	95.8	100.2	106.0
77.5°	47.6	50.7	51.9	54.5	57.6	60.7	64.3	68.1	71.1	72.7	77.0
80°	36.4	37.7	39.1	42.5	44.4	47.6	50.1	53.6	54.9	56.5	60.6
82.5°	28.4	29.1	29.9	30.8	32.0	35.1	37.7	39.9	41.2	41.7	44.8
85°	16.5	16.8	17.1	17.4	17.8	17.8	19.0	20.6	22.8	22.8	23.8
87.5°	7.2	7.5	7.3	6.8	7.4	6.8	7.1	7.0	7.7	8.2	8.7
90°	7.9	8.4	7.4	6.5	6.5	3.8	3.8	3.3	2.8	1.4	0.5
92.5°	122.9	147.5	129.1	93.9	57.9	34.2	24.5	17.8	12.1	7.7	5.3
95°	389.7	379.0	286.0	174.9	98.6	58.1	38.6	27.5	21.4	16.7	15.3
97.5°	489.7	399.3	267.7	157.2	94.2	63.1	46.7	37.1	31.6	27.6	27.6
100°	493.0	373.9	242.8	147.9	95.3	67.9	53.0	44.2	38.6	35.4	35.4
102.5°	465.0	342.3	226.0	145.3	99.1	74.2	60.1	51.6	46.4	43.5	42.8
105°	414.4	305.1	211.7	146.5	107.9	85.6	72.1	63.8	58.1	55.8	54.4
107.5°	373.5	284.3	209.0	153.4	118.2	97.8	84.5	76.5	70.5	68.2	67.3
110°	353.0	277.2	209.8	158.6	126.0	105.6	93.0	84.6	79.1	76.7	75.8



TEST NUMBER: P332903-930

CATALOG NUMBER: S124RDIP-S575D590U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	341.4	273.9	212.0	164.2	133.5	113.7	101.2	92.9	87.6	85.0	84.0
115°	330.7	272.1	216.3	173.0	145.1	126.5	114.0	105.1	100.4	97.2	95.8
117.5°	325.9	271.6	220.8	182.1	156.4	138.7	125.6	117.4	112.3	109.4	108.1
120°	323.3	271.6	224.2	188.3	164.2	146.5	133.5	125.6	120.4	117.2	116.3
122.5°	320.2	271.3	227.6	194.3	171.6	153.9	141.3	132.6	127.9	124.7	123.7
125°	315.4	270.7	232.5	203.3	181.8	165.1	152.1	143.2	138.1	135.3	133.5
127.5°	308.8	269.6	236.5	211.0	191.4	175.1	162.0	152.8	147.0	143.7	142.1
130°	304.6	269.3	239.5	215.8	197.6	181.8	168.4	159.6	152.5	148.8	147.0
132.5°	300.9	268.9	242.1	220.6	202.8	187.0	174.3	164.8	158.2	153.3	151.8
135°	295.3	268.3	246.1	227.0	210.2	194.9	182.8	173.0	165.1	160.5	158.6
137.5°	290.5	268.2	248.3	231.5	215.8	201.5	190.0	179.8	172.3	167.1	165.4
140°	287.9	267.9	250.2	234.4	219.6	205.5	194.4	184.7	176.8	171.6	170.2
142.5°	285.7	267.9	251.7	236.6	222.9	209.3	198.5	189.1	181.6	176.8	175.5
145°	281.8	266.9	252.6	239.0	226.5	214.4	204.2	195.3	188.8	184.2	182.8
147.5°	278.4	265.3	253.0	241.2	230.2	218.9	209.7	202.3	195.6	191.5	191.0
150°	275.8	264.2	253.0	242.3	232.1	221.8	213.0	206.0	200.5	196.7	196.2
152.5°	272.8	262.3	252.3	243.0	233.6	224.5	216.4	210.1	204.9	201.2	201.1
155°	268.3	259.5	251.1	243.7	235.8	227.9	220.9	215.8	211.2	208.4	207.9
157.5°	263.8	256.7	250.0	243.7	237.4	230.6	225.2	220.7	217.1	214.5	214.5
160°	260.5	254.4	248.8	243.7	238.1	232.5	227.4	223.7	220.5	218.6	218.6
162.5°	257.5	252.2	247.7	243.7	238.9	233.7	229.7	226.3	223.4	221.9	222.3
165°	252.6	248.8	245.6	242.8	239.0	234.9	232.1	229.8	227.4	226.5	226.5
167.5°	248.1	245.5	243.4	241.7	239.0	235.9	233.7	232.4	230.6	230.2	230.6
170°	245.1	243.2	241.8	240.9	238.6	236.3	234.9	233.9	232.5	232.1	232.5
172.5°	242.5	241.0	240.4	240.2	238.2	236.6	235.6	235.1	234.0	233.9	234.4
175°	239.5	238.6	238.6	239.0	237.7	236.8	236.8	236.3	235.8	235.8	236.3
177.5°	237.5	237.1	237.1	237.8	237.1	236.8	236.8	236.8	236.4	236.8	237.1
180°	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8



TEST NUMBER: P332903-930

CATALOG NUMBER: S124RDIP-S575D590U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3
2.5°	792.1	794.4	797.0	801.8	805.8	807.6	811.2	813.8	812.9	816.5	822.6
5°	795.2	803.8	813.7	823.8	835.2	844.7	852.4	860.0	866.0	873.3	884.1
7.5°	794.8	810.0	826.6	844.7	863.5	879.6	894.6	909.9	923.3	938.2	957.5
10°	792.7	813.0	833.6	857.5	881.3	903.8	924.1	943.1	961.2	980.5	1004.9
12.5°	790.4	813.8	838.7	867.3	897.0	924.1	947.9	975.3	997.9	1022.9	1051.2
15°	780.3	811.8	845.7	882.8	918.4	954.8	987.5	1021.2	1052.6	1082.3	1117.9
17.5°	768.8	805.0	845.1	888.9	931.6	975.9	1014.7	1057.1	1089.2	1129.2	1162.2
20°	759.5	798.4	841.2	890.4	939.0	988.1	1030.9	1074.1	1110.3	1150.6	1192.5
22.5°	748.0	790.8	837.2	888.1	939.0	992.7	1040.1	1083.0	1127.8	1173.1	1216.3
25°	729.6	774.0	823.2	879.0	937.3	992.2	1043.0	1096.3	1144.5	1193.7	1232.4
27.5°	707.0	753.7	805.5	863.1	923.0	979.2	1038.9	1095.8	1144.3	1191.6	1225.3
30°	689.0	738.2	788.0	846.4	908.5	968.8	1032.8	1089.6	1140.7	1183.2	1202.2
32.5°	670.5	717.1	768.4	827.5	891.3	956.1	1019.7	1077.7	1124.9	1150.5	1151.0
35°	638.2	682.0	735.3	793.4	858.7	929.1	993.5	1050.6	1079.5	1081.7	1050.6
37.5°	603.1	643.3	693.6	751.7	823.2	893.3	959.0	997.1	1006.8	974.5	917.0
40°	578.0	615.1	663.7	723.3	794.3	866.7	926.6	954.5	944.4	892.0	827.9
42.5°	551.5	586.1	632.9	691.8	763.1	836.2	887.3	902.2	875.3	814.9	739.9
45°	508.5	540.2	586.5	645.9	714.4	782.9	821.6	814.0	769.2	697.6	613.5
47.5°	463.7	494.3	536.0	590.8	661.0	720.2	746.3	723.4	659.7	580.9	512.5
50°	434.0	465.4	503.8	556.1	620.2	677.3	694.1	659.2	588.4	512.7	449.8
52.5°	404.8	431.6	469.2	519.8	581.1	629.3	638.2	598.0	525.0	457.1	401.4
55°	360.4	384.8	416.5	464.1	517.1	558.0	553.3	501.5	435.2	377.2	333.4
57.5°	317.4	335.8	365.1	409.7	456.2	483.7	466.3	422.2	360.4	312.9	276.0
60°	289.0	306.1	333.4	372.4	413.4	428.8	414.3	366.4	317.6	274.1	243.0
62.5°	262.1	277.2	300.7	336.9	369.9	379.1	363.5	321.7	277.7	240.6	214.8
65°	223.0	236.9	257.0	282.7	305.5	309.9	299.8	257.0	223.6	192.6	174.8
67.5°	187.5	196.7	212.3	234.5	246.6	249.2	229.6	202.7	173.3	154.3	140.9
70°	163.7	170.0	184.6	196.7	206.5	206.8	188.7	167.1	144.6	129.1	119.3
72.5°	140.6	146.7	157.8	166.0	173.5	171.0	154.5	137.5	119.3	107.5	100.2
75°	108.5	113.9	119.6	123.4	123.4	120.3	108.2	95.5	85.0	78.0	75.8
77.5°	78.8	83.3	85.2	84.6	83.5	78.5	70.9	62.6	58.9	55.6	53.9
80°	61.9	63.8	64.4	62.8	60.9	55.2	50.1	46.6	43.1	41.9	41.3
82.5°	45.9	47.5	45.9	46.3	42.2	37.4	34.7	33.4	32.0	31.5	30.8
85°	24.5	24.1	23.5	21.9	19.0	18.4	18.1	17.8	17.1	17.4	16.8
87.5°	8.6	8.2	7.3	7.1	7.1	7.2	7.4	7.6	7.7	7.4	8.0
90°	1.4	2.8	3.3	3.8	3.8	6.5	6.5	7.4	8.4	7.9	8.4
92.5°	7.7	12.1	17.8	24.5	34.2	57.9	93.9	129.1	147.5	122.9	91.3
95°	16.7	21.4	27.5	38.6	58.1	98.6	174.9	286.0	379.0	389.7	344.6
97.5°	27.6	31.6	37.1	46.7	63.1	94.2	157.2	267.7	399.3	489.7	509.2
100°	35.4	38.6	44.2	53.0	67.9	95.3	147.9	242.8	373.9	493.0	560.9
102.5°	43.5	46.4	51.6	60.1	74.2	99.1	145.3	226.0	342.3	465.0	558.3
105°	55.8	58.1	63.8	72.1	85.6	107.9	146.5	211.7	305.1	414.4	520.9
107.5°	68.2	70.5	76.5	84.5	97.8	118.2	153.4	209.0	284.3	373.5	467.8
110°	76.7	79.1	84.6	93.0	105.6	126.0	158.6	209.8	277.2	353.0	435.8





TEST NUMBER: P332903-930

CATALOG NUMBER: S124RDIP-S575D590U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	85.0	87.6	92.9	101.2	113.7	133.5	164.2	212.0	273.9	341.4	412.4
115°	97.2	100.4	105.1	114.0	126.5	145.1	173.0	216.3	272.1	330.7	388.8
117.5°	109.4	112.3	117.4	125.6	138.7	156.4	182.1	220.8	271.6	325.9	377.2
120°	117.2	120.4	125.6	133.5	146.5	164.2	188.3	224.2	271.6	323.3	372.1
122.5°	124.7	127.9	132.6	141.3	153.9	171.6	194.3	227.6	271.3	320.2	367.6
125°	135.3	138.1	143.2	152.1	165.1	181.8	203.3	232.5	270.7	315.4	360.0
127.5°	143.7	147.0	152.8	162.0	175.1	191.4	211.0	236.5	269.6	308.8	350.7
130°	148.8	152.5	159.6	168.4	181.8	197.6	215.8	239.5	269.3	304.6	343.2
132.5°	153.3	158.2	164.8	174.3	187.0	202.8	220.6	242.1	268.9	300.9	335.4
135°	160.5	165.1	173.0	182.8	194.9	210.2	227.0	246.1	268.3	295.3	324.7
137.5°	167.1	172.3	179.8	190.0	201.5	215.8	231.5	248.3	268.2	290.5	314.9
140°	171.6	176.8	184.7	194.4	205.5	219.6	234.4	250.2	267.9	287.9	309.2
142.5°	176.8	181.6	189.1	198.5	209.3	222.9	236.6	251.7	267.9	285.7	304.1
145°	184.2	188.8	195.3	204.2	214.4	226.5	239.0	252.6	266.9	281.8	296.7
147.5°	191.5	195.6	202.3	209.7	218.9	230.2	241.2	253.0	265.3	278.4	290.7
150°	196.7	200.5	206.0	213.0	221.8	232.1	242.3	253.0	264.2	275.8	287.0
152.5°	201.2	204.9	210.1	216.4	224.5	233.6	243.0	252.3	262.3	272.8	282.8
155°	208.4	211.2	215.8	220.9	227.9	235.8	243.7	251.1	259.5	268.3	276.7
157.5°	214.5	217.1	220.7	225.2	230.6	237.4	243.7	250.0	256.7	263.8	270.1
160°	218.6	220.5	223.7	227.4	232.5	238.1	243.7	248.8	254.4	260.5	266.0
162.5°	221.9	223.4	226.3	229.7	233.7	238.9	243.7	247.7	252.2	257.5	262.0
165°	226.5	227.4	229.8	232.1	234.9	239.0	242.8	245.6	248.8	252.6	256.2
167.5°	230.2	230.6	232.4	233.7	235.9	239.0	241.7	243.4	245.5	248.1	250.8
170°	232.1	232.5	233.9	234.9	236.3	238.6	240.9	241.8	243.2	245.1	247.4
172.5°	233.9	234.0	235.1	235.6	236.6	238.2	240.2	240.4	241.0	242.5	244.4
175°	235.8	235.8	236.3	236.8	236.8	237.7	239.0	238.6	238.6	239.5	240.4
177.5°	236.8	236.4	236.8	236.8	236.8	237.1	237.8	237.1	237.1	237.5	237.8
180°	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8



TEST NUMBER: P332903-930

CATALOG NUMBER: S124RDIP-S575D590U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	787.3	787.3	787.3	787.3	787.3	787.3	787.3
2.5°	825.9	827.0	827.7	830.2	830.5	832.7	830.5
5°	894.2	898.7	905.6	912.6	913.3	917.7	909.8
7.5°	970.9	981.1	987.6	998.8	1003.3	1006.1	1001.5
10°	1023.7	1033.1	1050.0	1058.3	1066.5	1067.7	1064.0
12.5°	1074.6	1089.7	1103.0	1118.7	1118.3	1129.4	1125.4
15°	1142.6	1158.1	1176.6	1194.0	1200.4	1200.4	1205.4
17.5°	1191.1	1219.6	1238.6	1252.3	1267.3	1269.9	1268.1
20°	1223.8	1254.6	1274.9	1292.7	1302.8	1305.7	1305.7
22.5°	1248.2	1274.4	1294.2	1310.2	1318.6	1321.9	1320.9
25°	1265.1	1287.6	1299.7	1304.4	1306.6	1305.9	1300.0
27.5°	1241.9	1241.0	1233.3	1218.7	1207.8	1201.1	1193.5
30°	1197.8	1181.3	1162.3	1141.3	1114.4	1093.7	1087.4
32.5°	1132.1	1095.0	1062.8	1027.9	998.9	978.3	969.6
35°	1004.9	946.2	898.4	856.5	826.1	807.0	800.6
37.5°	854.1	797.3	738.0	697.4	672.1	652.9	645.7
40°	758.1	696.3	644.6	606.5	580.5	561.8	561.5
42.5°	670.6	611.6	562.9	535.5	507.4	495.0	495.0
45°	549.1	501.8	460.6	439.0	422.2	412.1	409.2
47.5°	454.6	415.6	388.1	370.9	357.2	350.7	346.5
50°	401.6	367.4	345.4	330.5	322.9	314.7	314.1
52.5°	357.4	329.8	312.7	300.6	291.0	286.0	286.2
55°	300.4	278.5	266.4	257.2	249.6	245.8	244.3
57.5°	253.1	236.7	227.9	219.5	216.2	213.2	212.4
60°	223.6	212.5	204.3	197.6	192.9	191.9	191.6
62.5°	199.3	187.7	182.0	176.8	173.3	171.9	171.3
65°	164.3	155.7	150.7	146.6	145.3	143.1	142.8
67.5°	132.5	127.3	124.0	121.2	119.4	119.3	119.3
70°	112.9	110.1	107.2	105.7	104.7	104.0	104.0
72.5°	96.2	94.1	91.7	90.9	90.7	90.1	89.8
75°	73.3	71.1	71.3	69.8	68.5	66.9	66.0
77.5°	51.9	50.4	50.1	49.9	48.8	48.6	49.1
80°	40.3	38.7	38.4	38.7	38.4	37.4	37.4
82.5°	30.7	29.4	29.0	28.8	28.5	28.8	28.3
85°	16.5	15.9	15.9	15.9	16.5	16.1	15.9
87.5°	7.6	7.4	7.7	7.5	7.7	7.3	7.5
90°	8.8	9.3	9.3	9.8	10.2	9.8	9.8
92.5°	68.7	54.7	45.4	39.9	37.4	35.8	35.8
95°	272.6	210.2	165.1	142.4	127.9	119.5	113.5
97.5°	482.4	436.9	388.3	355.0	326.9	313.0	303.3
100°	570.2	547.4	513.0	472.5	444.2	430.2	426.5
102.5°	604.5	611.1	596.7	571.9	551.3	536.6	533.6
105°	601.4	647.4	666.5	667.4	663.7	657.1	654.4
107.5°	553.4	618.3	659.7	682.7	693.3	698.0	699.2
110°	516.2	583.7	634.9	667.9	687.4	695.8	699.9



TEST NUMBER: P332903-930

CATALOG NUMBER: S124RDIP-S575D590U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	483.5	547.2	598.3	635.9	659.5	671.2	678.0
115°	446.1	500.4	545.1	581.8	609.8	624.6	628.4
117.5°	424.6	467.4	505.2	536.6	560.0	575.1	578.0
120°	415.3	452.5	485.5	512.1	532.6	544.6	549.8
122.5°	409.4	443.2	472.1	494.6	512.1	522.3	527.4
125°	400.0	432.0	457.6	476.2	489.8	498.6	501.3
127.5°	388.9	420.9	445.2	463.9	475.9	483.3	486.1
130°	380.0	411.6	436.3	455.3	466.9	474.4	477.2
132.5°	369.9	400.8	425.4	444.2	457.3	464.3	467.2
135°	354.9	383.2	406.5	425.1	438.1	445.6	448.3
137.5°	340.5	364.4	385.4	402.8	415.6	421.8	425.1
140°	331.2	352.0	371.6	387.9	398.1	404.6	408.4
142.5°	323.3	341.3	358.2	372.6	382.1	387.9	390.4
145°	312.5	326.5	339.5	351.1	359.1	363.7	366.0
147.5°	303.2	314.4	324.7	333.2	340.0	343.5	344.4
150°	297.7	307.0	315.4	322.8	328.8	331.6	332.1
152.5°	292.0	300.6	307.5	313.8	318.8	320.4	320.9
155°	284.1	291.1	296.7	301.4	305.1	306.5	306.5
157.5°	276.4	282.2	286.7	290.2	293.0	293.8	293.8
160°	271.2	276.2	280.0	282.7	285.6	286.0	286.0
162.5°	266.3	270.3	273.7	275.7	278.5	279.0	278.6
165°	259.0	262.3	264.6	266.5	268.3	267.9	267.4
167.5°	252.9	255.5	256.9	257.9	259.0	258.9	258.6
170°	248.8	250.7	252.1	253.0	253.5	253.0	253.0
172.5°	245.5	246.6	247.6	248.2	248.7	248.2	247.4
175°	240.9	241.8	241.8	241.8	242.8	241.8	240.9
177.5°	238.2	238.2	238.6	238.2	238.6	237.8	237.1
180°	236.8	236.8	236.8	236.8	236.8	236.8	236.8

(END OF REPORT)