

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332933-930

Luminaire Tested: **S124RDIP-S795D590U930-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332933-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIP-S795D590U930-4F0-1E-UDD-A4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4443.4 lumens
Efficiency: N/A
Efficacy: 110.3 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 40.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332933-930

CATALOG NUMBER: S124RDIP-S795D590U930-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332933-930

CATALOG NUMBER: S124RDIP-S795D590U930-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	66	66	66	61
1	101	97	93	90	94	91	87	85	79	77	75	69	67	66	60	58	57	53
2	92	85	79	74	86	80	75	70	70	66	63	61	58	56	53	51	49	45
3	85	75	68	62	79	71	65	59	63	58	54	55	51	48	48	45	42	39
4	78	67	59	53	72	63	56	51	56	50	46	49	45	41	43	40	37	34
5	71	60	52	46	67	57	49	44	50	45	40	44	40	36	39	35	33	30
6	66	54	46	40	62	51	44	39	46	40	35	40	36	32	35	32	29	26
7	61	49	41	36	57	46	39	34	41	36	31	37	32	29	32	29	26	23
8	57	45	37	32	53	42	35	30	38	32	28	34	29	26	30	26	23	21
9	53	41	33	28	50	39	32	27	35	29	25	31	26	23	28	24	21	19
10	50	38	30	26	47	36	29	25	32	27	23	29	24	21	26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8688	8688	8688	8688
5°	10078	8715	7703	8715
10°	11922	8676	6874	8676
15°	13771	8596	5907	8596
20°	15332	8485	5342	8485
25°	15828	8378	4960	8378
30°	13856	8245	4729	8245
35°	10787	8051	4590	8051
40°	8088	7827	4515	7827
45°	6387	7470	4475	7470
50°	5392	7058	4346	7058
55°	4700	6602	4114	6602
60°	4229	6132	3641	6132
65°	3727	5624	3131	5624
70°	3356	5098	2825	5098
75°	2813	4517	2408	4517
80°	2380	3849	2259	3849
85°	2010	3010	2010	3010



TEST NUMBER: P332933-930

CATALOG NUMBER: S124RDIP-S795D590U930-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	104.3	2.3
10°-20°	314.5	7.1
20°-30°	492.0	11.1
30°-40°	546.9	12.3
40°-50°	485.2	10.9
50°-60°	378.1	8.5
60°-70°	247.6	5.6
70°-80°	121.7	2.7
80°-90°	31.4	0.7
90°-100°	171.0	3.8
100°-110°	355.9	8.0
110°-120°	318.7	7.2
120°-130°	268.1	6.0
130°-140°	223.6	5.0
140°-150°	170.8	3.8
150°-160°	120.0	2.7
160°-170°	70.6	1.6
170°-180°	23.0	0.5
0°-30°	910.8	20.5
0°-40°	1457.7	32.8
0°-60°	2321.1	52.2
0°-90°	2721.7	61.3
90°-120°	845.6	19.0
90°-150°	1508.1	33.9
90°-180°	1722.0	38.8
0°-180°	4443.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1076	1076	1076	1076	1076	
5°	1244	1075	950	1075	1244	126
15°	1648	1028	707	1028	1648	469
25°	1777	940	557	940	1777	788
35°	1094	817	466	817	1094	686
45°	559	654	392	654	559	443
55°	334	469	292	469	334	304
65°	195	294	164	294	195	196
75°	90	145	77	145	90	99
85°	22	32	22	32	22	25
90°	10	0	10	0	10	9
95°	114	15	114	15	114	176
105°	654	54	654	54	654	647
115°	628	96	628	96	628	624
125°	501	134	501	134	501	456
135°	448	159	448	159	448	346
145°	366	183	366	183	366	232
155°	306	208	306	208	306	143
165°	267	226	267	226	267	77
175°	241	236	241	236	241	23
180°	237	237	237	237	237	



TEST NUMBER: P332933-930

CATALOG NUMBER: S124RDIP-S795D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2
2.5°	1135.1	1138.3	1135.1	1134.8	1131.4	1130.3	1128.9	1124.5	1116.1	1111.3	1112.3
5°	1243.6	1254.4	1248.4	1247.5	1238.0	1228.4	1222.3	1208.4	1193.7	1183.7	1175.5
7.5°	1369.0	1375.2	1371.4	1365.3	1349.9	1341.2	1327.1	1308.8	1282.4	1262.2	1243.7
10°	1454.3	1459.5	1457.8	1446.5	1435.3	1412.3	1399.2	1373.7	1340.3	1313.9	1289.2
12.5°	1538.2	1543.9	1528.5	1529.1	1507.7	1489.6	1469.0	1436.8	1398.2	1364.2	1333.2
15°	1647.7	1640.8	1640.8	1632.1	1608.3	1583.1	1561.9	1528.0	1479.4	1438.7	1395.8
17.5°	1733.4	1735.8	1732.3	1711.8	1693.1	1667.0	1628.1	1588.6	1543.5	1488.8	1445.0
20°	1784.7	1784.7	1780.9	1766.9	1742.7	1714.9	1672.8	1629.9	1572.7	1517.6	1468.2
22.5°	1805.6	1806.9	1802.3	1790.9	1769.0	1742.0	1706.2	1662.6	1603.5	1541.6	1480.3
25°	1776.9	1785.2	1786.0	1783.0	1776.5	1760.0	1729.2	1684.6	1631.7	1564.5	1498.5
27.5°	1631.4	1641.8	1650.9	1665.9	1685.9	1696.2	1697.6	1675.0	1628.8	1564.1	1497.8
30°	1486.4	1495.1	1523.2	1560.1	1588.8	1614.8	1637.3	1643.4	1617.4	1559.3	1489.5
32.5°	1325.4	1337.3	1365.5	1405.1	1452.8	1496.8	1547.4	1573.3	1572.6	1537.7	1473.2
35°	1094.5	1103.1	1129.1	1170.8	1228.0	1293.5	1373.7	1436.1	1478.6	1475.5	1436.1
37.5°	882.6	892.4	918.8	953.2	1008.8	1089.8	1167.4	1253.4	1332.0	1376.1	1363.0
40°	767.5	767.9	793.5	829.1	881.1	951.8	1036.3	1131.7	1219.3	1290.9	1304.7
42.5°	676.6	676.7	693.6	731.9	769.4	835.9	916.6	1011.4	1113.9	1196.5	1233.3
45°	559.4	563.3	577.2	600.1	629.6	686.0	750.6	838.6	953.5	1051.5	1112.6
47.5°	473.7	479.4	488.2	507.0	530.4	568.0	621.4	700.5	794.0	901.8	988.8
50°	429.3	430.2	441.4	451.8	472.2	502.1	548.9	614.8	700.7	804.4	901.1
52.5°	391.1	390.9	397.7	410.9	427.5	450.8	488.6	548.6	624.8	717.6	817.4
55°	333.9	336.1	341.3	351.6	364.2	380.7	410.6	455.8	515.6	594.9	685.5
57.5°	290.3	291.5	295.5	299.9	311.5	323.5	345.9	377.2	427.7	492.7	577.2
60°	261.9	262.4	263.7	270.1	279.2	290.5	305.7	332.2	374.6	434.1	500.8
62.5°	234.2	234.9	236.9	241.7	248.7	256.5	272.4	293.7	328.8	379.6	439.8
65°	195.1	195.6	198.6	200.3	205.9	212.9	224.6	238.9	263.2	305.7	351.2
67.5°	163.1	163.1	163.2	165.6	169.4	174.1	181.1	192.5	210.8	236.9	277.0
70°	142.2	142.2	143.1	144.4	146.6	150.4	154.3	163.1	176.5	197.7	228.5
72.5°	122.8	123.1	124.0	124.3	125.4	128.6	131.5	137.1	147.0	163.1	187.9
75°	90.2	91.5	93.7	95.4	97.6	97.1	100.2	103.6	106.6	116.2	130.5
77.5°	67.1	66.4	66.7	68.2	68.4	68.9	71.0	73.7	76.0	80.5	85.6
80°	51.2	51.2	52.5	52.9	52.5	52.9	55.0	56.3	57.2	58.9	63.8
82.5°	38.6	39.4	39.0	39.4	39.6	40.0	41.9	42.2	43.0	43.7	45.7
85°	21.7	22.1	22.6	21.7	21.7	21.7	22.6	23.0	23.9	23.4	24.3
87.5°	9.6	9.2	9.7	9.6	9.9	9.5	9.8	10.4	9.5	10.0	9.8
90°	9.8	9.8	10.2	9.8	9.3	9.3	8.8	8.4	7.9	8.4	7.4
92.5°	35.8	35.8	37.4	39.9	45.4	54.7	68.7	91.3	122.9	147.5	129.1
95°	113.5	119.5	127.9	142.4	165.1	210.2	272.6	344.6	389.7	379.0	286.0
97.5°	303.3	313.0	326.9	355.0	388.3	436.9	482.4	509.2	489.7	399.3	267.7
100°	426.5	430.2	444.2	472.5	513.0	547.4	570.2	560.9	493.0	373.9	242.8
102.5°	533.6	536.6	551.3	571.9	596.7	611.1	604.5	558.3	465.0	342.3	226.0
105°	654.4	657.1	663.7	667.4	666.5	647.4	601.4	520.9	414.4	305.1	211.7
107.5°	699.2	698.0	693.3	682.7	659.7	618.3	553.4	467.8	373.5	284.3	209.0
110°	699.9	695.8	687.4	667.9	634.9	583.7	516.2	435.8	353.0	277.2	209.8



TEST NUMBER: P332933-930

CATALOG NUMBER: S124RDIP-S795D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	678.0	671.2	659.5	635.9	598.3	547.2	483.5	412.4	341.4	273.9	212.0
115°	628.4	624.6	609.8	581.8	545.1	500.4	446.1	388.8	330.7	272.1	216.3
117.5°	578.0	575.1	560.0	536.6	505.2	467.4	424.6	377.2	325.9	271.6	220.8
120°	549.8	544.6	532.6	512.1	485.5	452.5	415.3	372.1	323.3	271.6	224.2
122.5°	527.4	522.3	512.1	494.6	472.1	443.2	409.4	367.6	320.2	271.3	227.6
125°	501.3	498.6	489.8	476.2	457.6	432.0	400.0	360.0	315.4	270.7	232.5
127.5°	486.1	483.3	475.9	463.9	445.2	420.9	388.9	350.7	308.8	269.6	236.5
130°	477.2	474.4	466.9	455.3	436.3	411.6	380.0	343.2	304.6	269.3	239.5
132.5°	467.2	464.3	457.3	444.2	425.4	400.8	369.9	335.4	300.9	268.9	242.1
135°	448.3	445.6	438.1	425.1	406.5	383.2	354.9	324.7	295.3	268.3	246.1
137.5°	425.1	421.8	415.6	402.8	385.4	364.4	340.5	314.9	290.5	268.2	248.3
140°	408.4	404.6	398.1	387.9	371.6	352.0	331.2	309.2	287.9	267.9	250.2
142.5°	390.4	387.9	382.1	372.6	358.2	341.3	323.3	304.1	285.7	267.9	251.7
145°	366.0	363.7	359.1	351.1	339.5	326.5	312.5	296.7	281.8	266.9	252.6
147.5°	344.4	343.5	340.0	333.2	324.7	314.4	303.2	290.7	278.4	265.3	253.0
150°	332.1	331.6	328.8	322.8	315.4	307.0	297.7	287.0	275.8	264.2	253.0
152.5°	320.9	320.4	318.8	313.8	307.5	300.6	292.0	282.8	272.8	262.3	252.3
155°	306.5	306.5	305.1	301.4	296.7	291.1	284.1	276.7	268.3	259.5	251.1
157.5°	293.8	293.8	293.0	290.2	286.7	282.2	276.4	270.1	263.8	256.7	250.0
160°	286.0	286.0	285.6	282.7	280.0	276.2	271.2	266.0	260.5	254.4	248.8
162.5°	278.6	279.0	278.5	275.7	273.7	270.3	266.3	262.0	257.5	252.2	247.7
165°	267.4	267.9	268.3	266.5	264.6	262.3	259.0	256.2	252.6	248.8	245.6
167.5°	258.6	258.9	259.0	257.9	256.9	255.5	252.9	250.8	248.1	245.5	243.4
170°	253.0	253.0	253.5	253.0	252.1	250.7	248.8	247.4	245.1	243.2	241.8
172.5°	247.4	248.2	248.7	248.2	247.6	246.6	245.5	244.4	242.5	241.0	240.4
175°	240.9	241.8	242.8	241.8	241.8	241.8	240.9	240.4	239.5	238.6	238.6
177.5°	237.1	237.8	238.6	238.2	238.6	238.2	238.2	237.8	237.5	237.1	237.1
180°	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8



TEST NUMBER: P332933-930

CATALOG NUMBER: S124RDIP-S795D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2
2.5°	1108.8	1104.0	1101.6	1096.0	1089.4	1085.9	1082.8	1078.3	1072.4	1066.2	1061.6
5°	1165.1	1154.7	1141.7	1126.1	1112.2	1098.8	1087.0	1075.4	1061.9	1048.0	1034.1
7.5°	1222.9	1202.4	1180.3	1154.7	1129.8	1107.2	1086.4	1066.4	1043.8	1023.7	1005.3
10°	1263.1	1235.3	1204.5	1172.1	1139.5	1111.3	1083.6	1058.4	1030.7	1006.0	985.1
12.5°	1295.7	1263.1	1226.0	1185.5	1146.5	1112.4	1080.4	1047.7	1016.1	989.3	961.6
15°	1349.8	1305.1	1255.3	1206.7	1156.0	1109.6	1066.7	1028.5	992.5	954.8	928.4
17.5°	1387.0	1334.0	1273.4	1215.0	1155.1	1100.4	1050.9	1005.4	963.9	925.4	893.9
20°	1409.2	1350.7	1283.4	1217.2	1149.9	1091.4	1038.0	987.7	944.9	903.2	870.7
22.5°	1421.7	1356.9	1283.4	1214.0	1144.4	1081.0	1022.5	970.0	923.3	881.7	845.7
25°	1425.7	1356.3	1281.3	1201.5	1125.2	1058.0	997.3	940.5	888.4	846.9	808.7
27.5°	1420.2	1338.5	1261.6	1179.7	1101.0	1030.1	966.5	906.8	854.7	810.0	770.9
30°	1411.9	1324.2	1241.9	1156.8	1077.1	1009.0	941.8	884.5	830.4	784.0	744.5
32.5°	1393.8	1306.9	1218.2	1131.2	1050.4	980.2	916.5	858.9	805.8	758.3	716.4
35°	1358.0	1270.1	1173.8	1084.4	1005.1	932.2	872.5	816.9	766.2	715.4	671.2
37.5°	1311.0	1221.1	1125.3	1027.4	948.0	879.3	824.3	772.3	722.8	676.5	627.5
40°	1266.6	1184.6	1085.7	988.6	907.1	840.7	790.0	742.7	692.9	646.9	597.9
42.5°	1212.8	1143.0	1043.1	945.6	865.1	801.2	754.0	707.8	662.3	617.8	566.7
45°	1123.1	1070.2	976.5	882.8	801.8	738.4	695.0	654.3	614.4	571.9	523.8
47.5°	1020.2	984.4	903.5	807.6	732.6	675.6	633.7	600.5	566.7	524.2	482.0
50°	948.8	925.8	847.7	760.1	688.6	636.1	593.2	562.0	533.8	493.0	455.3
52.5°	872.5	860.2	794.3	710.5	641.4	590.0	553.3	525.2	496.7	462.8	427.5
55°	756.2	762.7	706.8	634.4	569.3	525.9	492.6	469.1	444.9	416.3	389.0
57.5°	637.4	661.1	623.6	560.0	499.0	459.0	433.9	414.2	393.8	370.1	346.7
60°	566.3	586.2	565.0	509.1	455.8	418.4	395.0	379.8	359.5	337.8	320.0
62.5°	496.9	518.3	505.6	460.5	411.0	378.9	358.2	344.1	329.0	310.1	291.6
65°	409.8	423.6	417.6	386.4	351.2	323.9	304.8	294.4	280.5	266.7	250.2
67.5°	313.8	340.6	337.1	320.5	290.2	268.8	256.3	247.1	234.5	224.2	213.0
70°	258.0	282.7	282.3	268.8	252.3	232.4	223.7	216.0	204.6	194.7	185.6
72.5°	211.2	233.8	237.2	226.9	215.6	200.5	192.2	186.8	175.9	169.0	161.7
75°	147.9	164.4	168.7	168.7	163.5	155.6	148.3	144.8	137.1	130.9	126.6
77.5°	96.9	107.4	114.1	115.7	116.5	113.9	107.8	105.3	99.4	97.2	93.0
80°	68.5	75.4	83.2	85.9	88.1	87.2	84.5	82.8	77.2	75.0	73.3
82.5°	47.4	51.2	57.6	63.3	62.7	65.0	62.7	61.3	57.1	56.3	54.5
85°	24.7	25.1	26.0	29.9	32.1	32.9	33.4	32.5	31.2	31.2	28.2
87.5°	9.6	9.3	9.4	9.4	9.7	10.9	11.7	11.9	11.0	10.3	9.3
90°	6.5	6.5	3.8	3.8	3.3	2.8	1.4	0.5	1.4	2.8	3.3
92.5°	93.9	57.9	34.2	24.5	17.8	12.1	7.7	5.3	7.7	12.1	17.8
95°	174.9	98.6	58.1	38.6	27.5	21.4	16.7	15.3	16.7	21.4	27.5
97.5°	157.2	94.2	63.1	46.7	37.1	31.6	27.6	27.6	27.6	31.6	37.1
100°	147.9	95.3	67.9	53.0	44.2	38.6	35.4	35.4	35.4	38.6	44.2
102.5°	145.3	99.1	74.2	60.1	51.6	46.4	43.5	42.8	43.5	46.4	51.6
105°	146.5	107.9	85.6	72.1	63.8	58.1	55.8	54.4	55.8	58.1	63.8
107.5°	153.4	118.2	97.8	84.5	76.5	70.5	68.2	67.3	68.2	70.5	76.5
110°	158.6	126.0	105.6	93.0	84.6	79.1	76.7	75.8	76.7	79.1	84.6



TEST NUMBER: P332933-930

CATALOG NUMBER: S124RDIP-S795D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	164.2	133.5	113.7	101.2	92.9	87.6	85.0	84.0	85.0	87.6	92.9
115°	173.0	145.1	126.5	114.0	105.1	100.4	97.2	95.8	97.2	100.4	105.1
117.5°	182.1	156.4	138.7	125.6	117.4	112.3	109.4	108.1	109.4	112.3	117.4
120°	188.3	164.2	146.5	133.5	125.6	120.4	117.2	116.3	117.2	120.4	125.6
122.5°	194.3	171.6	153.9	141.3	132.6	127.9	124.7	123.7	124.7	127.9	132.6
125°	203.3	181.8	165.1	152.1	143.2	138.1	135.3	133.5	135.3	138.1	143.2
127.5°	211.0	191.4	175.1	162.0	152.8	147.0	143.7	142.1	143.7	147.0	152.8
130°	215.8	197.6	181.8	168.4	159.6	152.5	148.8	147.0	148.8	152.5	159.6
132.5°	220.6	202.8	187.0	174.3	164.8	158.2	153.3	151.8	153.3	158.2	164.8
135°	227.0	210.2	194.9	182.8	173.0	165.1	160.5	158.6	160.5	165.1	173.0
137.5°	231.5	215.8	201.5	190.0	179.8	172.3	167.1	165.4	167.1	172.3	179.8
140°	234.4	219.6	205.5	194.4	184.7	176.8	171.6	170.2	171.6	176.8	184.7
142.5°	236.6	222.9	209.3	198.5	189.1	181.6	176.8	175.5	176.8	181.6	189.1
145°	239.0	226.5	214.4	204.2	195.3	188.8	184.2	182.8	184.2	188.8	195.3
147.5°	241.2	230.2	218.9	209.7	202.3	195.6	191.5	191.0	191.5	195.6	202.3
150°	242.3	232.1	221.8	213.0	206.0	200.5	196.7	196.2	196.7	200.5	206.0
152.5°	243.0	233.6	224.5	216.4	210.1	204.9	201.2	201.1	201.2	204.9	210.1
155°	243.7	235.8	227.9	220.9	215.8	211.2	208.4	207.9	208.4	211.2	215.8
157.5°	243.7	237.4	230.6	225.2	220.7	217.1	214.5	214.5	214.5	217.1	220.7
160°	243.7	238.1	232.5	227.4	223.7	220.5	218.6	218.6	218.6	220.5	223.7
162.5°	243.7	238.9	233.7	229.7	226.3	223.4	221.9	222.3	221.9	223.4	226.3
165°	242.8	239.0	234.9	232.1	229.8	227.4	226.5	226.5	226.5	227.4	229.8
167.5°	241.7	239.0	235.9	233.7	232.4	230.6	230.2	230.6	230.2	230.6	232.4
170°	240.9	238.6	236.3	234.9	233.9	232.5	232.1	232.5	232.1	232.5	233.9
172.5°	240.2	238.2	236.6	235.6	235.1	234.0	233.9	234.4	233.9	234.0	235.1
175°	239.0	237.7	236.8	236.8	236.3	235.8	235.8	236.3	235.8	235.8	236.3
177.5°	237.8	237.1	236.8	236.8	236.8	236.4	236.8	237.1	236.8	236.4	236.8
180°	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8



TEST NUMBER: P332933-930

CATALOG NUMBER: S124RDIP-S795D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2
2.5°	1056.8	1053.3	1048.8	1043.6	1037.4	1031.8	1029.4	1031.4	1032.5	1029.7	1029.4
5°	1024.6	1013.7	1005.1	992.1	981.7	973.0	966.9	964.3	965.2	958.3	956.5
7.5°	988.5	975.6	961.4	946.0	931.6	918.8	912.2	908.5	901.2	898.0	892.7
10°	965.2	947.9	934.0	915.7	899.3	884.1	876.8	870.7	863.3	859.8	852.5
12.5°	941.3	921.1	905.9	887.0	870.2	851.8	844.8	833.6	822.1	814.7	805.3
15°	907.5	883.3	864.6	842.0	822.1	801.3	782.7	761.8	754.1	737.6	728.1
17.5°	868.0	843.4	820.4	790.1	759.4	733.5	713.6	693.7	681.8	671.2	666.3
20°	842.0	819.5	787.4	752.3	718.0	689.4	673.4	660.4	647.3	640.0	634.8
22.5°	817.4	788.6	751.4	713.5	679.2	656.8	643.2	629.8	619.3	612.3	605.3
25°	776.2	738.4	699.0	655.6	632.2	612.7	597.9	587.1	580.6	571.5	568.0
27.5°	733.8	688.0	644.5	615.4	591.0	573.2	560.3	552.1	543.9	538.1	533.6
30°	701.2	654.8	615.7	588.0	563.3	548.5	538.1	528.6	522.0	517.3	513.8
32.5°	668.9	622.5	589.7	559.9	540.4	525.9	514.9	507.8	502.6	496.5	494.4
35°	622.2	581.1	552.4	525.5	505.6	492.6	483.9	476.5	472.2	470.4	469.1
37.5°	577.4	543.6	512.9	490.8	473.0	462.8	452.6	449.0	446.0	442.9	444.3
40°	548.9	517.3	490.0	466.6	452.2	441.0	434.9	430.6	428.0	428.0	428.0
42.5°	524.3	493.3	466.8	445.7	431.5	421.9	415.2	411.5	410.6	410.3	412.4
45°	486.1	457.5	430.6	413.2	401.0	391.5	387.7	384.6	384.6	386.4	386.8
47.5°	448.2	421.3	399.8	380.3	369.2	363.3	359.9	358.3	358.5	360.3	362.2
50°	424.9	398.5	377.2	359.9	349.5	343.8	340.8	340.0	340.8	340.8	343.8
52.5°	399.6	375.9	355.1	340.5	328.6	323.3	321.7	320.5	321.1	322.5	323.8
55°	362.5	341.3	321.3	307.4	298.7	295.3	291.4	291.8	291.0	291.8	291.8
57.5°	325.3	306.2	287.6	276.6	269.0	264.0	259.8	261.0	259.7	259.5	258.8
60°	301.3	280.5	265.8	255.8	247.1	242.8	238.9	239.8	238.5	237.6	235.9
62.5°	275.3	258.0	243.9	234.3	227.4	222.3	218.4	217.6	214.6	211.6	207.8
65°	237.6	223.3	210.8	201.6	195.1	191.2	188.2	185.6	179.0	172.1	168.7
67.5°	201.0	190.6	178.9	171.2	165.9	160.8	155.0	150.6	144.5	140.6	138.5
70°	177.3	167.4	157.4	150.0	144.4	139.7	133.1	130.1	125.7	124.0	121.8
72.5°	154.8	145.5	136.2	129.6	123.6	119.8	114.7	111.7	109.8	109.1	107.0
75°	120.6	113.2	106.2	100.2	95.4	92.8	90.7	88.5	87.6	83.6	81.5
77.5°	88.0	83.1	78.8	74.4	71.0	69.3	65.1	62.6	61.1	59.4	58.9
80°	68.5	65.1	60.7	58.1	53.3	51.6	49.9	49.4	49.0	48.6	48.1
82.5°	51.5	48.0	43.7	42.2	40.8	39.8	38.7	38.3	37.9	38.2	38.1
85°	26.0	24.3	24.3	23.9	23.4	23.0	22.6	22.6	22.1	22.6	22.1
87.5°	9.4	9.0	9.6	9.0	9.5	9.6	9.2	9.3	9.8	9.1	9.1
90°	3.8	3.8	6.5	6.5	7.4	8.4	7.9	8.4	8.8	9.3	9.3
92.5°	24.5	34.2	57.9	93.9	129.1	147.5	122.9	91.3	68.7	54.7	45.4
95°	38.6	58.1	98.6	174.9	286.0	379.0	389.7	344.6	272.6	210.2	165.1
97.5°	46.7	63.1	94.2	157.2	267.7	399.3	489.7	509.2	482.4	436.9	388.3
100°	53.0	67.9	95.3	147.9	242.8	373.9	493.0	560.9	570.2	547.4	513.0
102.5°	60.1	74.2	99.1	145.3	226.0	342.3	465.0	558.3	604.5	611.1	596.7
105°	72.1	85.6	107.9	146.5	211.7	305.1	414.4	520.9	601.4	647.4	666.5
107.5°	84.5	97.8	118.2	153.4	209.0	284.3	373.5	467.8	553.4	618.3	659.7
110°	93.0	105.6	126.0	158.6	209.8	277.2	353.0	435.8	516.2	583.7	634.9



TEST NUMBER: P332933-930

CATALOG NUMBER: S124RDIP-S795D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	101.2	113.7	133.5	164.2	212.0	273.9	341.4	412.4	483.5	547.2	598.3
115°	114.0	126.5	145.1	173.0	216.3	272.1	330.7	388.8	446.1	500.4	545.1
117.5°	125.6	138.7	156.4	182.1	220.8	271.6	325.9	377.2	424.6	467.4	505.2
120°	133.5	146.5	164.2	188.3	224.2	271.6	323.3	372.1	415.3	452.5	485.5
122.5°	141.3	153.9	171.6	194.3	227.6	271.3	320.2	367.6	409.4	443.2	472.1
125°	152.1	165.1	181.8	203.3	232.5	270.7	315.4	360.0	400.0	432.0	457.6
127.5°	162.0	175.1	191.4	211.0	236.5	269.6	308.8	350.7	388.9	420.9	445.2
130°	168.4	181.8	197.6	215.8	239.5	269.3	304.6	343.2	380.0	411.6	436.3
132.5°	174.3	187.0	202.8	220.6	242.1	268.9	300.9	335.4	369.9	400.8	425.4
135°	182.8	194.9	210.2	227.0	246.1	268.3	295.3	324.7	354.9	383.2	406.5
137.5°	190.0	201.5	215.8	231.5	248.3	268.2	290.5	314.9	340.5	364.4	385.4
140°	194.4	205.5	219.6	234.4	250.2	267.9	287.9	309.2	331.2	352.0	371.6
142.5°	198.5	209.3	222.9	236.6	251.7	267.9	285.7	304.1	323.3	341.3	358.2
145°	204.2	214.4	226.5	239.0	252.6	266.9	281.8	296.7	312.5	326.5	339.5
147.5°	209.7	218.9	230.2	241.2	253.0	265.3	278.4	290.7	303.2	314.4	324.7
150°	213.0	221.8	232.1	242.3	253.0	264.2	275.8	287.0	297.7	307.0	315.4
152.5°	216.4	224.5	233.6	243.0	252.3	262.3	272.8	282.8	292.0	300.6	307.5
155°	220.9	227.9	235.8	243.7	251.1	259.5	268.3	276.7	284.1	291.1	296.7
157.5°	225.2	230.6	237.4	243.7	250.0	256.7	263.8	270.1	276.4	282.2	286.7
160°	227.4	232.5	238.1	243.7	248.8	254.4	260.5	266.0	271.2	276.2	280.0
162.5°	229.7	233.7	238.9	243.7	247.7	252.2	257.5	262.0	266.3	270.3	273.7
165°	232.1	234.9	239.0	242.8	245.6	248.8	252.6	256.2	259.0	262.3	264.6
167.5°	233.7	235.9	239.0	241.7	243.4	245.5	248.1	250.8	252.9	255.5	256.9
170°	234.9	236.3	238.6	240.9	241.8	243.2	245.1	247.4	248.8	250.7	252.1
172.5°	235.6	236.6	238.2	240.2	240.4	241.0	242.5	244.4	245.5	246.6	247.6
175°	236.8	236.8	237.7	239.0	238.6	238.6	239.5	240.4	240.9	241.8	241.8
177.5°	236.8	236.8	237.1	237.8	237.1	237.1	237.5	237.8	238.2	238.2	238.6
180°	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8



TEST NUMBER: P332933-930

CATALOG NUMBER: S124RDIP-S795D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2
2.5°	1027.3	1028.0	1025.6	1024.8	1025.6	1028.0	1027.3	1029.4	1029.7	1032.5	1031.4
5°	953.1	952.2	950.1	950.5	950.1	952.2	953.1	956.5	958.3	965.2	964.3
7.5°	889.6	886.2	887.1	883.7	887.1	886.2	889.6	892.7	898.0	901.2	908.5
10°	850.8	846.0	842.0	838.6	842.0	846.0	850.8	852.5	859.8	863.3	870.7
12.5°	797.7	793.6	788.3	789.4	788.3	793.6	797.7	805.3	814.7	822.1	833.6
15°	722.4	715.9	705.5	706.8	705.5	715.9	722.4	728.1	737.6	754.1	761.8
17.5°	658.7	658.8	654.0	655.1	654.0	658.8	658.7	666.3	671.2	681.8	693.7
20°	625.7	622.6	623.1	621.8	623.1	622.6	625.7	634.8	640.0	647.3	660.4
22.5°	602.8	599.1	596.1	593.4	596.1	599.1	602.8	605.3	612.3	619.3	629.8
25°	564.1	561.5	557.6	556.8	557.6	561.5	564.1	568.0	571.5	580.6	587.1
27.5°	530.1	529.6	528.1	526.0	528.1	529.6	530.1	533.6	538.1	543.9	552.1
30°	510.4	509.5	508.6	507.3	508.6	509.5	510.4	513.8	517.3	522.0	528.6
32.5°	492.7	492.1	491.3	491.4	491.3	492.1	492.7	494.4	496.5	502.6	507.8
35°	467.4	467.0	466.1	465.7	466.1	467.0	467.4	469.1	470.4	472.2	476.5
37.5°	443.8	445.0	444.4	444.3	444.4	445.0	443.8	444.3	442.9	446.0	449.0
40°	427.5	428.0	428.8	428.4	428.8	428.0	427.5	428.0	428.0	428.0	430.6
42.5°	414.0	414.1	415.3	413.8	415.3	414.1	414.0	412.4	410.3	410.6	411.5
45°	389.8	392.4	392.0	392.0	392.0	392.4	389.8	386.8	386.4	384.6	384.6
47.5°	363.4	365.6	366.2	366.2	366.2	365.6	363.4	362.2	360.3	358.5	358.3
50°	346.0	345.1	346.4	346.0	346.4	345.1	346.0	343.8	340.8	340.8	340.0
52.5°	324.9	325.1	325.0	324.5	325.0	325.1	324.9	323.8	322.5	321.1	320.5
55°	292.3	292.7	291.8	292.3	291.8	292.7	292.3	291.8	291.8	291.0	291.8
57.5°	256.9	254.8	255.7	254.6	255.7	254.8	256.9	258.8	259.5	259.7	261.0
60°	231.5	228.0	227.2	225.5	227.2	228.0	231.5	235.9	237.6	238.5	239.8
62.5°	203.1	200.6	197.7	199.1	197.7	200.6	203.1	207.8	211.6	214.6	217.6
65°	165.2	163.5	162.2	163.9	162.2	163.5	165.2	168.7	172.1	179.0	185.6
67.5°	136.7	135.8	135.8	134.9	135.8	135.8	136.7	138.5	140.6	144.5	150.6
70°	121.8	120.6	120.6	119.7	120.6	120.6	121.8	121.8	124.0	125.7	130.1
72.5°	106.6	105.3	105.7	105.1	105.7	105.3	106.6	107.0	109.1	109.8	111.7
75°	78.9	76.7	76.7	77.2	76.7	76.7	78.9	81.5	83.6	87.6	88.5
77.5°	58.9	58.5	59.0	58.3	59.0	58.5	58.9	58.9	59.4	61.1	62.6
80°	48.1	47.7	47.3	48.6	47.3	47.7	48.1	48.1	48.6	49.0	49.4
82.5°	37.3	37.3	37.2	38.9	37.2	37.3	37.3	38.1	38.2	37.9	38.3
85°	22.6	21.7	22.6	21.7	22.6	21.7	22.6	22.1	22.6	22.1	22.6
87.5°	9.9	9.7	9.2	9.6	9.2	9.7	9.9	9.1	9.1	9.8	9.3
90°	9.8	10.2	9.8	9.8	9.8	10.2	9.8	9.3	9.3	8.8	8.4
92.5°	39.9	37.4	35.8	35.8	35.8	37.4	39.9	45.4	54.7	68.7	91.3
95°	142.4	127.9	119.5	113.5	119.5	127.9	142.4	165.1	210.2	272.6	344.6
97.5°	355.0	326.9	313.0	303.3	313.0	326.9	355.0	388.3	436.9	482.4	509.2
100°	472.5	444.2	430.2	426.5	430.2	444.2	472.5	513.0	547.4	570.2	560.9
102.5°	571.9	551.3	536.6	533.6	536.6	551.3	571.9	596.7	611.1	604.5	558.3
105°	667.4	663.7	657.1	654.4	657.1	663.7	667.4	666.5	647.4	601.4	520.9
107.5°	682.7	693.3	698.0	699.2	698.0	693.3	682.7	659.7	618.3	553.4	467.8
110°	667.9	687.4	695.8	699.9	695.8	687.4	667.9	634.9	583.7	516.2	435.8



TEST NUMBER: P332933-930

CATALOG NUMBER: S124RDIP-S795D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	635.9	659.5	671.2	678.0	671.2	659.5	635.9	598.3	547.2	483.5	412.4
115°	581.8	609.8	624.6	628.4	624.6	609.8	581.8	545.1	500.4	446.1	388.8
117.5°	536.6	560.0	575.1	578.0	575.1	560.0	536.6	505.2	467.4	424.6	377.2
120°	512.1	532.6	544.6	549.8	544.6	532.6	512.1	485.5	452.5	415.3	372.1
122.5°	494.6	512.1	522.3	527.4	522.3	512.1	494.6	472.1	443.2	409.4	367.6
125°	476.2	489.8	498.6	501.3	498.6	489.8	476.2	457.6	432.0	400.0	360.0
127.5°	463.9	475.9	483.3	486.1	483.3	475.9	463.9	445.2	420.9	388.9	350.7
130°	455.3	466.9	474.4	477.2	474.4	466.9	455.3	436.3	411.6	380.0	343.2
132.5°	444.2	457.3	464.3	467.2	464.3	457.3	444.2	425.4	400.8	369.9	335.4
135°	425.1	438.1	445.6	448.3	445.6	438.1	425.1	406.5	383.2	354.9	324.7
137.5°	402.8	415.6	421.8	425.1	421.8	415.6	402.8	385.4	364.4	340.5	314.9
140°	387.9	398.1	404.6	408.4	404.6	398.1	387.9	371.6	352.0	331.2	309.2
142.5°	372.6	382.1	387.9	390.4	387.9	382.1	372.6	358.2	341.3	323.3	304.1
145°	351.1	359.1	363.7	366.0	363.7	359.1	351.1	339.5	326.5	312.5	296.7
147.5°	333.2	340.0	343.5	344.4	343.5	340.0	333.2	324.7	314.4	303.2	290.7
150°	322.8	328.8	331.6	332.1	331.6	328.8	322.8	315.4	307.0	297.7	287.0
152.5°	313.8	318.8	320.4	320.9	320.4	318.8	313.8	307.5	300.6	292.0	282.8
155°	301.4	305.1	306.5	306.5	306.5	305.1	301.4	296.7	291.1	284.1	276.7
157.5°	290.2	293.0	293.8	293.8	293.8	293.0	290.2	286.7	282.2	276.4	270.1
160°	282.7	285.6	286.0	286.0	286.0	285.6	282.7	280.0	276.2	271.2	266.0
162.5°	275.7	278.5	279.0	278.6	279.0	278.5	275.7	273.7	270.3	266.3	262.0
165°	266.5	268.3	267.9	267.4	267.9	268.3	266.5	264.6	262.3	259.0	256.2
167.5°	257.9	259.0	258.9	258.6	258.9	259.0	257.9	256.9	255.5	252.9	250.8
170°	253.0	253.5	253.0	253.0	253.0	253.5	253.0	252.1	250.7	248.8	247.4
172.5°	248.2	248.7	248.2	247.4	248.2	248.7	248.2	247.6	246.6	245.5	244.4
175°	241.8	242.8	241.8	240.9	241.8	242.8	241.8	241.8	241.8	240.9	240.4
177.5°	238.2	238.6	237.8	237.1	237.8	238.6	238.2	238.6	238.2	238.2	237.8
180°	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8



TEST NUMBER: P332933-930

CATALOG NUMBER: S124RDIP-S795D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2
2.5°	1029.4	1031.8	1037.4	1043.6	1048.8	1053.3	1056.8	1061.6	1066.2	1072.4	1078.3
5°	966.9	973.0	981.7	992.1	1005.1	1013.7	1024.6	1034.1	1048.0	1061.9	1075.4
7.5°	912.2	918.8	931.6	946.0	961.4	975.6	988.5	1005.3	1023.7	1043.8	1066.4
10°	876.8	884.1	899.3	915.7	934.0	947.9	965.2	985.1	1006.0	1030.7	1058.4
12.5°	844.8	851.8	870.2	887.0	905.9	921.1	941.3	961.6	989.3	1016.1	1047.7
15°	782.7	801.3	822.1	842.0	864.6	883.3	907.5	928.4	954.8	992.5	1028.5
17.5°	713.6	733.5	759.4	790.1	820.4	843.4	868.0	893.9	925.4	963.9	1005.4
20°	673.4	689.4	718.0	752.3	787.4	819.5	842.0	870.7	903.2	944.9	987.7
22.5°	643.2	656.8	679.2	713.5	751.4	788.6	817.4	845.7	881.7	923.3	970.0
25°	597.9	612.7	632.2	655.6	699.0	738.4	776.2	808.7	846.9	888.4	940.5
27.5°	560.3	573.2	591.0	615.4	644.5	688.0	733.8	770.9	810.0	854.7	906.8
30°	538.1	548.5	563.3	588.0	615.7	654.8	701.2	744.5	784.0	830.4	884.5
32.5°	514.9	525.9	540.4	559.9	589.7	622.5	668.9	716.4	758.3	805.8	858.9
35°	483.9	492.6	505.6	525.5	552.4	581.1	622.2	671.2	715.4	766.2	816.9
37.5°	452.6	462.8	473.0	490.8	512.9	543.6	577.4	627.5	676.5	722.8	772.3
40°	434.9	441.0	452.2	466.6	490.0	517.3	548.9	597.9	646.9	692.9	742.7
42.5°	415.2	421.9	431.5	445.7	466.8	493.3	524.3	566.7	617.8	662.3	707.8
45°	387.7	391.5	401.0	413.2	430.6	457.5	486.1	523.8	571.9	614.4	654.3
47.5°	359.9	363.3	369.2	380.3	399.8	421.3	448.2	482.0	524.2	566.7	600.5
50°	340.8	343.8	349.5	359.9	377.2	398.5	424.9	455.3	493.0	533.8	562.0
52.5°	321.7	323.3	328.6	340.5	355.1	375.9	399.6	427.5	462.8	496.7	525.2
55°	291.4	295.3	298.7	307.4	321.3	341.3	362.5	389.0	416.3	444.9	469.1
57.5°	259.8	264.0	269.0	276.6	287.6	306.2	325.3	346.7	370.1	393.8	414.2
60°	238.9	242.8	247.1	255.8	265.8	280.5	301.3	320.0	337.8	359.5	379.8
62.5°	218.4	222.3	227.4	234.3	243.9	258.0	275.3	291.6	310.1	329.0	344.1
65°	188.2	191.2	195.1	201.6	210.8	223.3	237.6	250.2	266.7	280.5	294.4
67.5°	155.0	160.8	165.9	171.2	178.9	190.6	201.0	213.0	224.2	234.5	247.1
70°	133.1	139.7	144.4	150.0	157.4	167.4	177.3	185.6	194.7	204.6	216.0
72.5°	114.7	119.8	123.6	129.6	136.2	145.5	154.8	161.7	169.0	175.9	186.8
75°	90.7	92.8	95.4	100.2	106.2	113.2	120.6	126.6	130.9	137.1	144.8
77.5°	65.1	69.3	71.0	74.4	78.8	83.1	88.0	93.0	97.2	99.4	105.3
80°	49.9	51.6	53.3	58.1	60.7	65.1	68.5	73.3	75.0	77.2	82.8
82.5°	38.7	39.8	40.8	42.2	43.7	48.0	51.5	54.5	56.3	57.1	61.3
85°	22.6	23.0	23.4	23.9	24.3	24.3	26.0	28.2	31.2	31.2	32.5
87.5°	9.2	9.6	9.5	9.0	9.6	9.0	9.4	9.3	10.3	11.0	11.9
90°	7.9	8.4	7.4	6.5	6.5	3.8	3.8	3.3	2.8	1.4	0.5
92.5°	122.9	147.5	129.1	93.9	57.9	34.2	24.5	17.8	12.1	7.7	5.3
95°	389.7	379.0	286.0	174.9	98.6	58.1	38.6	27.5	21.4	16.7	15.3
97.5°	489.7	399.3	267.7	157.2	94.2	63.1	46.7	37.1	31.6	27.6	27.6
100°	493.0	373.9	242.8	147.9	95.3	67.9	53.0	44.2	38.6	35.4	35.4
102.5°	465.0	342.3	226.0	145.3	99.1	74.2	60.1	51.6	46.4	43.5	42.8
105°	414.4	305.1	211.7	146.5	107.9	85.6	72.1	63.8	58.1	55.8	54.4
107.5°	373.5	284.3	209.0	153.4	118.2	97.8	84.5	76.5	70.5	68.2	67.3
110°	353.0	277.2	209.8	158.6	126.0	105.6	93.0	84.6	79.1	76.7	75.8



TEST NUMBER: P332933-930

CATALOG NUMBER: S124RDIP-S795D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	341.4	273.9	212.0	164.2	133.5	113.7	101.2	92.9	87.6	85.0	84.0
115°	330.7	272.1	216.3	173.0	145.1	126.5	114.0	105.1	100.4	97.2	95.8
117.5°	325.9	271.6	220.8	182.1	156.4	138.7	125.6	117.4	112.3	109.4	108.1
120°	323.3	271.6	224.2	188.3	164.2	146.5	133.5	125.6	120.4	117.2	116.3
122.5°	320.2	271.3	227.6	194.3	171.6	153.9	141.3	132.6	127.9	124.7	123.7
125°	315.4	270.7	232.5	203.3	181.8	165.1	152.1	143.2	138.1	135.3	133.5
127.5°	308.8	269.6	236.5	211.0	191.4	175.1	162.0	152.8	147.0	143.7	142.1
130°	304.6	269.3	239.5	215.8	197.6	181.8	168.4	159.6	152.5	148.8	147.0
132.5°	300.9	268.9	242.1	220.6	202.8	187.0	174.3	164.8	158.2	153.3	151.8
135°	295.3	268.3	246.1	227.0	210.2	194.9	182.8	173.0	165.1	160.5	158.6
137.5°	290.5	268.2	248.3	231.5	215.8	201.5	190.0	179.8	172.3	167.1	165.4
140°	287.9	267.9	250.2	234.4	219.6	205.5	194.4	184.7	176.8	171.6	170.2
142.5°	285.7	267.9	251.7	236.6	222.9	209.3	198.5	189.1	181.6	176.8	175.5
145°	281.8	266.9	252.6	239.0	226.5	214.4	204.2	195.3	188.8	184.2	182.8
147.5°	278.4	265.3	253.0	241.2	230.2	218.9	209.7	202.3	195.6	191.5	191.0
150°	275.8	264.2	253.0	242.3	232.1	221.8	213.0	206.0	200.5	196.7	196.2
152.5°	272.8	262.3	252.3	243.0	233.6	224.5	216.4	210.1	204.9	201.2	201.1
155°	268.3	259.5	251.1	243.7	235.8	227.9	220.9	215.8	211.2	208.4	207.9
157.5°	263.8	256.7	250.0	243.7	237.4	230.6	225.2	220.7	217.1	214.5	214.5
160°	260.5	254.4	248.8	243.7	238.1	232.5	227.4	223.7	220.5	218.6	218.6
162.5°	257.5	252.2	247.7	243.7	238.9	233.7	229.7	226.3	223.4	221.9	222.3
165°	252.6	248.8	245.6	242.8	239.0	234.9	232.1	229.8	227.4	226.5	226.5
167.5°	248.1	245.5	243.4	241.7	239.0	235.9	233.7	232.4	230.6	230.2	230.6
170°	245.1	243.2	241.8	240.9	238.6	236.3	234.9	233.9	232.5	232.1	232.5
172.5°	242.5	241.0	240.4	240.2	238.2	236.6	235.6	235.1	234.0	233.9	234.4
175°	239.5	238.6	238.6	239.0	237.7	236.8	236.8	236.3	235.8	235.8	236.3
177.5°	237.5	237.1	237.1	237.8	237.1	236.8	236.8	236.8	236.4	236.8	237.1
180°	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8



TEST NUMBER: P332933-930

CATALOG NUMBER: S124RDIP-S795D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2
2.5°	1082.8	1085.9	1089.4	1096.0	1101.6	1104.0	1108.8	1112.3	1111.3	1116.1	1124.5
5°	1087.0	1098.8	1112.2	1126.1	1141.7	1154.7	1165.1	1175.5	1183.7	1193.7	1208.4
7.5°	1086.4	1107.2	1129.8	1154.7	1180.3	1202.4	1222.9	1243.7	1262.2	1282.4	1308.8
10°	1083.6	1111.3	1139.5	1172.1	1204.5	1235.3	1263.1	1289.2	1313.9	1340.3	1373.7
12.5°	1080.4	1112.4	1146.5	1185.5	1226.0	1263.1	1295.7	1333.2	1364.2	1398.2	1436.8
15°	1066.7	1109.6	1156.0	1206.7	1255.3	1305.1	1349.8	1395.8	1438.7	1479.4	1528.0
17.5°	1050.9	1100.4	1155.1	1215.0	1273.4	1334.0	1387.0	1445.0	1488.8	1543.5	1588.6
20°	1038.0	1091.4	1149.9	1217.2	1283.4	1350.7	1409.2	1468.2	1517.6	1572.7	1629.9
22.5°	1022.5	1081.0	1144.4	1214.0	1283.4	1356.9	1421.7	1480.3	1541.6	1603.5	1662.6
25°	997.3	1058.0	1125.2	1201.5	1281.3	1356.3	1425.7	1498.5	1564.5	1631.7	1684.6
27.5°	966.5	1030.1	1101.0	1179.7	1261.6	1338.5	1420.2	1497.8	1564.1	1628.8	1675.0
30°	941.8	1009.0	1077.1	1156.8	1241.9	1324.2	1411.9	1489.5	1559.3	1617.4	1643.4
32.5°	916.5	980.2	1050.4	1131.2	1218.2	1306.9	1393.8	1473.2	1537.7	1572.6	1573.3
35°	872.5	932.2	1005.1	1084.4	1173.8	1270.1	1358.0	1436.1	1475.5	1478.6	1436.1
37.5°	824.3	879.3	948.0	1027.4	1125.3	1221.1	1311.0	1363.0	1376.1	1332.0	1253.4
40°	790.0	840.7	907.1	988.6	1085.7	1184.6	1266.6	1304.7	1290.9	1219.3	1131.7
42.5°	754.0	801.2	865.1	945.6	1043.1	1143.0	1212.8	1233.3	1196.5	1113.9	1011.4
45°	695.0	738.4	801.8	882.8	976.5	1070.2	1123.1	1112.6	1051.5	953.5	838.6
47.5°	633.7	675.6	732.6	807.6	903.5	984.4	1020.2	988.8	901.8	794.0	700.5
50°	593.2	636.1	688.6	760.1	847.7	925.8	948.8	901.1	804.4	700.7	614.8
52.5°	553.3	590.0	641.4	710.5	794.3	860.2	872.5	817.4	717.6	624.8	548.6
55°	492.6	525.9	569.3	634.4	706.8	762.7	756.2	685.5	594.9	515.6	455.8
57.5°	433.9	459.0	499.0	560.0	623.6	661.1	637.4	577.2	492.7	427.7	377.2
60°	395.0	418.4	455.8	509.1	565.0	586.2	566.3	500.8	434.1	374.6	332.2
62.5°	358.2	378.9	411.0	460.5	505.6	518.3	496.9	439.8	379.6	328.8	293.7
65°	304.8	323.9	351.2	386.4	417.6	423.6	409.8	351.2	305.7	263.2	238.9
67.5°	256.3	268.8	290.2	320.5	337.1	340.6	313.8	277.0	236.9	210.8	192.5
70°	223.7	232.4	252.3	268.8	282.3	282.7	258.0	228.5	197.7	176.5	163.1
72.5°	192.2	200.5	215.6	226.9	237.2	233.8	211.2	187.9	163.1	147.0	137.1
75°	148.3	155.6	163.5	168.7	168.7	164.4	147.9	130.5	116.2	106.6	103.6
77.5°	107.8	113.9	116.5	115.7	114.1	107.4	96.9	85.6	80.5	76.0	73.7
80°	84.5	87.2	88.1	85.9	83.2	75.4	68.5	63.8	58.9	57.2	56.3
82.5°	62.7	65.0	62.7	63.3	57.6	51.2	47.4	45.7	43.7	43.0	42.2
85°	33.4	32.9	32.1	29.9	26.0	25.1	24.7	24.3	23.4	23.9	23.0
87.5°	11.7	10.9	9.7	9.4	9.4	9.3	9.6	9.8	10.0	9.5	10.4
90°	1.4	2.8	3.3	3.8	3.8	6.5	6.5	7.4	8.4	7.9	8.4
92.5°	7.7	12.1	17.8	24.5	34.2	57.9	93.9	129.1	147.5	122.9	91.3
95°	16.7	21.4	27.5	38.6	58.1	98.6	174.9	286.0	379.0	389.7	344.6
97.5°	27.6	31.6	37.1	46.7	63.1	94.2	157.2	267.7	399.3	489.7	509.2
100°	35.4	38.6	44.2	53.0	67.9	95.3	147.9	242.8	373.9	493.0	560.9
102.5°	43.5	46.4	51.6	60.1	74.2	99.1	145.3	226.0	342.3	465.0	558.3
105°	55.8	58.1	63.8	72.1	85.6	107.9	146.5	211.7	305.1	414.4	520.9
107.5°	68.2	70.5	76.5	84.5	97.8	118.2	153.4	209.0	284.3	373.5	467.8
110°	76.7	79.1	84.6	93.0	105.6	126.0	158.6	209.8	277.2	353.0	435.8



TEST NUMBER: P332933-930

CATALOG NUMBER: S124RDIP-S795D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	85.0	87.6	92.9	101.2	113.7	133.5	164.2	212.0	273.9	341.4	412.4
115°	97.2	100.4	105.1	114.0	126.5	145.1	173.0	216.3	272.1	330.7	388.8
117.5°	109.4	112.3	117.4	125.6	138.7	156.4	182.1	220.8	271.6	325.9	377.2
120°	117.2	120.4	125.6	133.5	146.5	164.2	188.3	224.2	271.6	323.3	372.1
122.5°	124.7	127.9	132.6	141.3	153.9	171.6	194.3	227.6	271.3	320.2	367.6
125°	135.3	138.1	143.2	152.1	165.1	181.8	203.3	232.5	270.7	315.4	360.0
127.5°	143.7	147.0	152.8	162.0	175.1	191.4	211.0	236.5	269.6	308.8	350.7
130°	148.8	152.5	159.6	168.4	181.8	197.6	215.8	239.5	269.3	304.6	343.2
132.5°	153.3	158.2	164.8	174.3	187.0	202.8	220.6	242.1	268.9	300.9	335.4
135°	160.5	165.1	173.0	182.8	194.9	210.2	227.0	246.1	268.3	295.3	324.7
137.5°	167.1	172.3	179.8	190.0	201.5	215.8	231.5	248.3	268.2	290.5	314.9
140°	171.6	176.8	184.7	194.4	205.5	219.6	234.4	250.2	267.9	287.9	309.2
142.5°	176.8	181.6	189.1	198.5	209.3	222.9	236.6	251.7	267.9	285.7	304.1
145°	184.2	188.8	195.3	204.2	214.4	226.5	239.0	252.6	266.9	281.8	296.7
147.5°	191.5	195.6	202.3	209.7	218.9	230.2	241.2	253.0	265.3	278.4	290.7
150°	196.7	200.5	206.0	213.0	221.8	232.1	242.3	253.0	264.2	275.8	287.0
152.5°	201.2	204.9	210.1	216.4	224.5	233.6	243.0	252.3	262.3	272.8	282.8
155°	208.4	211.2	215.8	220.9	227.9	235.8	243.7	251.1	259.5	268.3	276.7
157.5°	214.5	217.1	220.7	225.2	230.6	237.4	243.7	250.0	256.7	263.8	270.1
160°	218.6	220.5	223.7	227.4	232.5	238.1	243.7	248.8	254.4	260.5	266.0
162.5°	221.9	223.4	226.3	229.7	233.7	238.9	243.7	247.7	252.2	257.5	262.0
165°	226.5	227.4	229.8	232.1	234.9	239.0	242.8	245.6	248.8	252.6	256.2
167.5°	230.2	230.6	232.4	233.7	235.9	239.0	241.7	243.4	245.5	248.1	250.8
170°	232.1	232.5	233.9	234.9	236.3	238.6	240.9	241.8	243.2	245.1	247.4
172.5°	233.9	234.0	235.1	235.6	236.6	238.2	240.2	240.4	241.0	242.5	244.4
175°	235.8	235.8	236.3	236.8	236.8	237.7	239.0	238.6	238.6	239.5	240.4
177.5°	236.8	236.4	236.8	236.8	236.8	237.1	237.8	237.1	237.1	237.5	237.8
180°	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8



TEST NUMBER: P332933-930

CATALOG NUMBER: S124RDIP-S795D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2
2.5°	1128.9	1130.3	1131.4	1134.8	1135.1	1138.3	1135.1
5°	1222.3	1228.4	1238.0	1247.5	1248.4	1254.4	1243.6
7.5°	1327.1	1341.2	1349.9	1365.3	1371.4	1375.2	1369.0
10°	1399.2	1412.3	1435.3	1446.5	1457.8	1459.5	1454.3
12.5°	1469.0	1489.6	1507.7	1529.1	1528.5	1543.9	1538.2
15°	1561.9	1583.1	1608.3	1632.1	1640.8	1640.8	1647.7
17.5°	1628.1	1667.0	1693.1	1711.8	1732.3	1735.8	1733.4
20°	1672.8	1714.9	1742.7	1766.9	1780.9	1784.7	1784.7
22.5°	1706.2	1742.0	1769.0	1790.9	1802.3	1806.9	1805.6
25°	1729.2	1760.0	1776.5	1783.0	1786.0	1785.2	1776.9
27.5°	1697.6	1696.2	1685.9	1665.9	1650.9	1641.8	1631.4
30°	1637.3	1614.8	1588.8	1560.1	1523.2	1495.1	1486.4
32.5°	1547.4	1496.8	1452.8	1405.1	1365.5	1337.3	1325.4
35°	1373.7	1293.5	1228.0	1170.8	1129.1	1103.1	1094.5
37.5°	1167.4	1089.8	1008.8	953.2	918.8	892.4	882.6
40°	1036.3	951.8	881.1	829.1	793.5	767.9	767.5
42.5°	916.6	835.9	769.4	731.9	693.6	676.7	676.6
45°	750.6	686.0	629.6	600.1	577.2	563.3	559.4
47.5°	621.4	568.0	530.4	507.0	488.2	479.4	473.7
50°	548.9	502.1	472.2	451.8	441.4	430.2	429.3
52.5°	488.6	450.8	427.5	410.9	397.7	390.9	391.1
55°	410.6	380.7	364.2	351.6	341.3	336.1	333.9
57.5°	345.9	323.5	311.5	299.9	295.5	291.5	290.3
60°	305.7	290.5	279.2	270.1	263.7	262.4	261.9
62.5°	272.4	256.5	248.7	241.7	236.9	234.9	234.2
65°	224.6	212.9	205.9	200.3	198.6	195.6	195.1
67.5°	181.1	174.1	169.4	165.6	163.2	163.1	163.1
70°	154.3	150.4	146.6	144.4	143.1	142.2	142.2
72.5°	131.5	128.6	125.4	124.3	124.0	123.1	122.8
75°	100.2	97.1	97.6	95.4	93.7	91.5	90.2
77.5°	71.0	68.9	68.4	68.2	66.7	66.4	67.1
80°	55.0	52.9	52.5	52.9	52.5	51.2	51.2
82.5°	41.9	40.0	39.6	39.4	39.0	39.4	38.6
85°	22.6	21.7	21.7	21.7	22.6	22.1	21.7
87.5°	9.8	9.5	9.9	9.6	9.7	9.2	9.6
90°	8.8	9.3	9.3	9.8	10.2	9.8	9.8
92.5°	68.7	54.7	45.4	39.9	37.4	35.8	35.8
95°	272.6	210.2	165.1	142.4	127.9	119.5	113.5
97.5°	482.4	436.9	388.3	355.0	326.9	313.0	303.3
100°	570.2	547.4	513.0	472.5	444.2	430.2	426.5
102.5°	604.5	611.1	596.7	571.9	551.3	536.6	533.6
105°	601.4	647.4	666.5	667.4	663.7	657.1	654.4
107.5°	553.4	618.3	659.7	682.7	693.3	698.0	699.2
110°	516.2	583.7	634.9	667.9	687.4	695.8	699.9



TEST NUMBER: P332933-930

CATALOG NUMBER: S124RDIP-S795D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	483.5	547.2	598.3	635.9	659.5	671.2	678.0
115°	446.1	500.4	545.1	581.8	609.8	624.6	628.4
117.5°	424.6	467.4	505.2	536.6	560.0	575.1	578.0
120°	415.3	452.5	485.5	512.1	532.6	544.6	549.8
122.5°	409.4	443.2	472.1	494.6	512.1	522.3	527.4
125°	400.0	432.0	457.6	476.2	489.8	498.6	501.3
127.5°	388.9	420.9	445.2	463.9	475.9	483.3	486.1
130°	380.0	411.6	436.3	455.3	466.9	474.4	477.2
132.5°	369.9	400.8	425.4	444.2	457.3	464.3	467.2
135°	354.9	383.2	406.5	425.1	438.1	445.6	448.3
137.5°	340.5	364.4	385.4	402.8	415.6	421.8	425.1
140°	331.2	352.0	371.6	387.9	398.1	404.6	408.4
142.5°	323.3	341.3	358.2	372.6	382.1	387.9	390.4
145°	312.5	326.5	339.5	351.1	359.1	363.7	366.0
147.5°	303.2	314.4	324.7	333.2	340.0	343.5	344.4
150°	297.7	307.0	315.4	322.8	328.8	331.6	332.1
152.5°	292.0	300.6	307.5	313.8	318.8	320.4	320.9
155°	284.1	291.1	296.7	301.4	305.1	306.5	306.5
157.5°	276.4	282.2	286.7	290.2	293.0	293.8	293.8
160°	271.2	276.2	280.0	282.7	285.6	286.0	286.0
162.5°	266.3	270.3	273.7	275.7	278.5	279.0	278.6
165°	259.0	262.3	264.6	266.5	268.3	267.9	267.4
167.5°	252.9	255.5	256.9	257.9	259.0	258.9	258.6
170°	248.8	250.7	252.1	253.0	253.5	253.0	253.0
172.5°	245.5	246.6	247.6	248.2	248.7	248.2	247.4
175°	240.9	241.8	241.8	241.8	242.8	241.8	240.9
177.5°	238.2	238.2	238.6	238.2	238.6	237.8	237.1
180°	236.8	236.8	236.8	236.8	236.8	236.8	236.8

(END OF REPORT)