

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: NEO-RAY

Report Number: P332519

Luminaire Tested: **S124DIP-S350D1035U835-4F0-1E-UDD-A4**

Issue Date: 3/3/2020


**Test Information**

Test Method: LM-79-08  
Report Number: P332519  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIP-S350D1035U835-4F0-1E-UDD-A4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 350 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5274.7 lumens  
Efficiency: N/A  
Efficacy: 141.4 lumens/watt  
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 37.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332519

CATALOG NUMBER: S124DIP-S350D1035U835-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P332519

CATALOG NUMBER: S124DIP-S350D1035U835-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	38	38	38	30				
1	93	89	86	82	84	80	77	74	63	61	59	48	46	45	33	33	32	25				
2	85	78	72	67	76	70	65	61	56	52	49	42	40	38	30	28	27	22				
3	78	69	62	56	69	62	56	51	49	45	42	37	35	32	26	25	23	18				
4	71	61	53	47	64	55	48	43	44	39	35	33	30	28	24	22	20	16				
5	65	54	46	41	58	49	42	37	39	34	30	30	27	24	21	19	18	14				
6	60	48	41	35	54	44	37	32	35	30	27	27	24	21	19	17	15	12				
7	55	44	36	31	50	39	33	28	32	27	23	24	21	18	18	15	14	11				
8	51	39	32	27	46	36	29	25	29	24	21	22	19	16	16	14	12	10				
9	48	36	29	24	43	33	26	22	26	22	18	20	17	15	15	13	11	9				
10	44	33	26	21	40	30	24	20	24	20	16	19	16	13	14	12	10	8				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	4612	4612	4612	4612
5°	5431	4624	4081	4624
10°	6503	4604	3674	4604
15°	7694	4557	3375	4557
20°	8568	4509	3107	4509
25°	8706	4440	2922	4440
30°	7408	4373	2864	4373
35°	5695	4263	2864	4263
40°	4440	4135	2918	4135
45°	3701	3942	2967	3942
50°	3258	3706	3067	3706
55°	2985	3424	3191	3424
60°	2796	3171	3339	3171
65°	2604	2888	3463	2888
70°	2379	2608	3541	2608
75°	2127	2296	3500	2296
80°	1781	1883	3389	1883
85°	1315	1362	3242	1362



TEST NUMBER: P332519

CATALOG NUMBER: S124DIP-S350D1035U835-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	55.7	1.1
10°-20°	171.6	3.3
20°-30°	272.0	5.2
30°-40°	302.8	5.7
40°-50°	275.6	5.2
50°-60°	225.2	4.3
60°-70°	160.8	3.0
70°-80°	88.5	1.7
80°-90°	27.0	0.5
90°-100°	367.0	7.0
100°-110°	763.9	14.5
110°-120°	684.2	13.0
120°-130°	575.5	10.9
130°-140°	479.9	9.1
140°-150°	366.6	7.0
150°-160°	257.7	4.9
160°-170°	151.6	2.9
170°-180°	49.3	0.9
0°-30°	499.3	9.5
0°-40°	802.0	15.2
0°-60°	1302.8	24.7
0°-90°	1579.1	29.9
90°-120°	1815.1	34.4
90°-150°	3237.1	61.4
90°-180°	3696.0	70.1
0°-180°	5274.7	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	571	571	571	571	571	
5°	670	571	504	571	670	68
15°	921	545	404	545	921	260
25°	977	498	328	498	977	431
35°	578	433	291	433	578	367
45°	324	345	260	345	324	255
55°	212	243	227	243	212	192
65°	136	151	181	151	136	135
75°	68	74	112	74	68	72
85°	14	15	35	15	14	18
90°	21	1	21	1	21	17
95°	244	33	244	33	244	378
105°	1405	117	1405	117	1405	1389
115°	1349	206	1349	206	1349	1339
125°	1076	286	1076	286	1076	978
135°	962	340	962	340	962	743
145°	786	392	786	392	786	498
155°	658	446	658	446	658	307
165°	574	486	574	486	574	165
175°	517	507	517	507	517	50
180°	508	508	508	508	508	



TEST NUMBER: P332519

CATALOG NUMBER: S124DIP-S350D1035U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3
2.5°	608.0	607.9	606.0	605.6	604.3	602.6	602.2	599.1	593.1	590.2	589.5
5°	670.2	675.0	668.8	667.6	666.9	659.1	655.1	650.4	639.5	633.1	628.1
7.5°	744.5	745.0	742.3	740.2	734.1	727.3	717.1	706.2	693.2	679.8	669.6
10°	793.3	795.2	792.1	791.7	779.6	772.0	756.9	744.1	729.4	713.1	698.2
12.5°	844.8	842.2	840.6	830.5	828.2	814.4	796.8	783.7	761.0	742.2	722.4
15°	920.6	915.4	912.1	898.2	891.3	872.1	853.4	839.0	809.4	781.2	759.9
17.5°	965.1	970.3	962.7	956.9	939.2	925.7	906.6	876.3	853.2	818.2	791.3
20°	997.3	997.8	993.5	987.6	973.7	956.6	935.8	902.7	875.0	840.2	803.2
22.5°	1006.0	1006.1	1004.3	998.8	988.2	974.4	953.4	925.7	892.2	854.4	817.4
25°	977.4	976.5	978.6	984.8	980.8	976.5	964.4	943.8	912.6	872.6	832.8
27.5°	871.2	877.8	889.8	904.9	919.5	930.6	933.7	929.5	910.2	877.3	835.6
30°	794.7	802.8	811.8	826.9	856.3	873.1	891.5	905.5	897.7	871.4	832.6
32.5°	710.7	712.7	726.0	743.2	770.1	802.4	831.7	860.1	869.5	855.7	823.3
35°	577.9	581.3	595.7	612.7	645.6	685.2	729.2	768.5	800.9	813.9	797.3
37.5°	471.6	481.1	491.3	509.6	538.6	574.2	619.9	670.8	719.1	751.5	757.0
40°	421.3	427.2	434.5	448.5	473.1	508.1	547.4	605.6	657.0	703.4	718.5
42.5°	381.5	385.0	389.5	402.1	420.8	455.7	491.6	542.8	594.3	649.8	675.2
45°	324.2	327.8	335.4	342.7	356.9	381.0	414.4	456.5	508.4	561.8	608.7
47.5°	282.9	285.1	289.6	297.5	309.6	325.5	352.6	387.8	435.8	487.8	537.7
50°	259.4	261.3	264.8	271.9	281.2	295.4	317.6	350.5	388.1	440.4	489.4
52.5°	240.8	241.6	244.2	249.0	256.4	268.3	286.6	313.8	348.8	395.4	444.2
55°	212.1	213.0	215.4	218.9	225.3	232.9	246.8	267.2	297.7	338.2	380.6
57.5°	188.4	189.1	191.0	192.4	197.7	203.8	214.6	229.1	252.2	286.6	324.4
60°	173.2	172.8	175.1	176.3	179.9	185.1	193.4	207.3	227.4	255.1	289.9
62.5°	158.5	157.8	159.8	161.4	163.4	167.8	174.6	185.5	201.9	226.9	257.0
65°	136.3	135.4	136.6	138.5	140.3	142.7	147.7	157.4	170.4	188.4	211.3
67.5°	114.1	115.1	115.3	116.2	117.3	120.5	123.9	130.8	140.0	154.4	173.8
70°	100.8	101.1	102.0	102.0	102.7	105.6	108.4	112.4	121.4	134.7	150.5
72.5°	87.6	88.6	88.2	88.9	89.5	91.4	93.4	97.3	104.9	114.8	128.2
75°	68.2	68.9	68.9	69.1	69.8	70.5	72.2	75.0	80.5	87.8	97.0
77.5°	49.7	49.8	50.1	51.0	51.0	52.1	53.3	55.6	58.3	63.3	69.0
80°	38.3	38.8	38.6	39.1	39.1	40.0	40.5	43.3	44.5	47.8	52.3
82.5°	28.1	28.6	28.5	29.2	29.6	29.8	30.4	31.6	32.8	35.7	37.5
85°	14.2	14.7	14.2	14.7	15.4	15.6	16.3	16.6	17.5	18.2	19.9
87.5°	8.4	8.9	9.1	9.1	9.3	9.5	9.5	9.1	9.6	10.0	10.4
90°	21.0	21.0	22.0	21.0	20.0	20.0	19.0	18.0	17.0	18.0	16.0
92.5°	76.9	76.9	80.3	85.7	97.4	117.4	147.6	196.1	263.8	316.7	277.1
95°	243.6	256.6	274.5	305.5	354.4	451.2	585.0	739.7	836.6	813.6	614.0
97.5°	651.1	671.9	701.8	761.9	833.6	937.8	1035.4	1093.0	1051.0	856.9	574.6
100°	915.5	923.4	953.4	1014.3	1101.1	1175.0	1223.9	1204.0	1058.2	802.6	521.1
102.5°	1145.5	1151.9	1183.4	1227.5	1280.8	1311.6	1297.4	1198.4	998.3	734.8	485.2
105°	1404.6	1410.6	1424.6	1432.6	1430.6	1389.6	1290.8	1118.1	889.5	654.9	454.2
107.5°	1500.9	1498.3	1488.3	1465.5	1416.2	1327.2	1188.0	1004.1	801.6	610.2	448.6
110°	1502.5	1493.5	1475.5	1433.6	1362.7	1252.9	1108.1	935.4	757.7	595.0	450.2



TEST NUMBER: P332519

CATALOG NUMBER: S124DIP-S350D1035U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1455.3	1440.8	1415.6	1364.9	1284.4	1174.6	1037.8	885.1	733.0	587.8	455.0
115°	1348.7	1340.7	1308.8	1248.9	1170.0	1074.2	957.4	834.6	709.8	584.0	464.2
117.5°	1240.7	1234.5	1202.2	1151.9	1084.6	1003.3	911.5	809.8	699.4	583.0	474.0
120°	1180.0	1169.0	1143.1	1099.1	1042.2	971.4	891.5	798.6	693.8	583.0	481.2
122.5°	1132.1	1121.1	1099.1	1061.6	1013.5	951.4	878.7	789.1	687.4	582.2	488.4
125°	1076.2	1070.2	1051.2	1022.3	982.3	927.4	858.5	772.7	676.9	581.0	499.2
127.5°	1043.4	1037.4	1021.5	995.7	955.6	903.5	834.8	752.7	662.7	578.8	507.7
130°	1024.3	1018.3	1002.3	977.3	936.4	883.5	815.6	736.8	653.9	578.0	514.1
132.5°	1002.7	996.7	981.5	953.4	913.3	860.3	794.1	720.0	645.9	577.2	519.7
135°	962.4	956.4	940.4	912.5	872.5	822.6	761.7	696.8	633.9	576.0	528.1
137.5°	912.5	905.3	892.1	864.5	827.2	782.1	730.8	675.9	623.5	575.8	533.1
140°	876.5	868.5	854.6	832.6	797.6	755.7	710.8	663.9	618.0	575.0	537.1
142.5°	838.2	832.6	820.2	799.8	768.9	732.6	694.0	652.7	613.2	575.0	540.3
145°	785.7	780.7	770.7	753.7	728.8	700.8	670.9	636.9	605.0	573.0	542.1
147.5°	739.1	737.4	729.8	715.2	696.8	674.9	650.9	623.9	597.6	569.4	543.1
150°	712.8	711.8	705.8	692.8	676.9	658.9	638.9	616.0	592.0	567.0	543.1
152.5°	688.8	687.8	684.2	673.7	660.1	645.3	626.9	607.2	585.6	563.0	541.5
155°	657.9	657.9	654.9	646.9	636.9	624.9	610.0	594.0	576.0	557.1	539.1
157.5°	630.7	630.7	628.9	622.9	615.4	605.8	593.2	579.8	566.2	550.9	536.5
160°	614.0	614.0	613.0	607.0	601.0	593.0	582.0	571.0	559.1	546.1	534.1
162.5°	598.0	598.8	597.8	591.8	587.4	580.2	571.6	562.2	552.7	541.3	531.7
165°	574.0	575.0	576.0	572.0	568.0	563.0	556.1	550.1	542.1	534.1	527.1
167.5°	555.1	555.9	556.1	553.5	551.5	548.5	542.9	538.3	532.5	526.9	522.3
170°	543.1	543.1	544.1	543.1	541.1	538.1	534.1	531.1	526.1	522.1	519.1
172.5°	531.1	532.7	533.7	532.7	531.5	529.3	526.9	524.7	520.5	517.3	515.9
175°	517.1	519.1	521.1	519.1	519.1	519.1	517.1	516.1	514.1	512.1	512.1
177.5°	508.9	510.5	512.1	511.3	512.1	511.3	511.3	510.5	509.7	508.9	508.9
180°	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1



TEST NUMBER: P332519

CATALOG NUMBER: S124DIP-S350D1035U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3
2.5°	589.7	587.0	585.1	583.6	579.5	577.0	575.1	572.5	569.4	566.2	562.2
5°	623.1	615.1	609.2	600.2	591.7	584.6	577.2	570.6	562.6	553.8	547.4
7.5°	658.3	646.3	631.0	617.7	602.7	589.7	578.1	566.2	553.8	541.7	530.7
10°	680.7	665.3	648.2	628.1	609.2	592.4	576.8	561.6	546.9	532.3	519.7
12.5°	704.7	685.5	660.3	636.8	615.6	593.1	574.3	555.7	538.0	522.6	508.0
15°	737.0	709.3	680.2	648.7	620.8	594.5	568.7	545.3	525.4	505.0	490.8
17.5°	756.8	722.5	689.3	656.4	622.6	589.4	561.6	534.6	509.7	489.5	471.6
20°	769.9	735.8	694.4	661.5	621.3	587.2	555.0	524.9	498.9	477.4	458.9
22.5°	781.2	741.9	700.4	657.1	617.1	580.9	545.7	515.5	488.9	466.2	448.5
25°	787.4	742.2	697.2	654.1	608.7	565.9	533.9	498.4	470.0	446.1	427.2
27.5°	788.1	739.7	688.8	641.0	594.1	554.2	513.9	482.1	452.7	427.4	409.2
30°	786.0	735.6	680.9	629.1	582.0	538.7	503.6	469.1	439.0	413.9	395.0
32.5°	779.3	726.9	670.7	615.8	567.0	524.6	488.5	455.6	426.3	401.6	381.7
35°	760.2	708.3	648.5	591.4	541.5	498.7	466.0	432.6	403.3	379.9	360.7
37.5°	730.2	683.4	622.5	563.5	514.4	471.4	439.0	408.9	382.4	358.6	339.0
40°	704.1	662.9	601.8	544.3	491.3	450.4	420.1	392.4	366.1	343.6	324.9
42.5°	674.0	638.1	581.8	520.9	469.7	428.6	399.1	374.2	349.5	328.7	310.0
45°	620.3	596.6	543.6	487.3	434.0	395.2	367.1	345.3	324.5	304.1	288.5
47.5°	558.6	546.8	502.2	448.7	398.2	359.9	335.5	315.4	297.1	279.9	266.1
50°	517.1	511.4	472.9	421.3	373.0	337.0	312.4	295.1	279.5	264.4	251.3
52.5°	476.2	476.0	441.2	394.0	349.3	314.7	290.2	274.1	260.6	248.3	236.6
55°	413.7	420.3	393.1	351.0	311.0	279.7	257.7	243.3	233.8	223.7	214.9
57.5°	356.3	367.3	344.8	307.7	274.3	245.6	226.4	215.6	205.5	199.3	192.9
60°	318.8	329.2	311.7	280.5	249.0	224.4	206.1	196.4	187.7	183.4	178.9
62.5°	285.5	294.7	281.8	252.8	225.5	201.8	186.4	177.1	171.2	166.6	163.6
65°	237.9	245.7	234.5	213.5	190.0	171.1	158.6	151.2	145.6	143.7	140.3
67.5°	192.3	199.4	193.4	175.5	156.7	142.3	132.5	125.5	122.1	120.5	118.1
70°	165.2	172.3	165.9	150.3	135.8	123.8	114.5	110.5	107.0	106.3	103.0
72.5°	142.3	147.1	140.7	128.5	116.2	106.0	98.8	94.6	92.8	91.5	89.7
75°	106.7	111.0	106.7	97.3	88.5	81.4	75.3	73.6	71.5	70.8	69.6
77.5°	75.5	79.2	76.0	70.1	63.5	58.0	54.7	52.6	52.1	50.9	51.5
80°	57.7	60.1	57.0	53.0	47.8	44.0	41.7	40.5	39.1	38.6	39.5
82.5°	41.5	42.5	40.9	38.2	34.4	31.9	30.3	28.9	28.6	28.7	28.7
85°	21.5	21.3	21.1	18.7	17.5	15.9	14.9	14.7	14.4	14.9	15.4
87.5°	10.0	10.2	8.8	8.0	7.3	6.5	5.7	5.1	5.7	6.5	6.9
90°	14.0	14.0	8.0	8.0	7.0	6.0	3.0	1.0	3.0	6.0	7.0
92.5°	201.7	124.2	73.5	52.7	38.1	26.0	16.6	11.4	16.6	26.0	38.1
95°	375.4	211.6	124.8	82.9	58.9	45.9	35.9	32.9	35.9	45.9	58.9
97.5°	337.4	202.3	135.4	100.2	79.7	67.7	59.1	59.1	59.1	67.7	79.7
100°	317.5	204.7	145.8	113.8	94.8	82.9	75.9	75.9	75.9	82.9	94.8
102.5°	311.9	212.6	159.3	129.0	110.8	99.6	93.4	91.8	93.4	99.6	110.8
105°	314.5	231.6	183.7	154.7	136.8	124.8	119.8	116.8	119.8	124.8	136.8
107.5°	329.2	253.8	209.8	181.3	164.1	151.3	146.4	144.4	146.4	151.3	164.1
110°	340.4	270.5	226.6	199.7	181.7	169.7	164.7	162.7	164.7	169.7	181.7





TEST NUMBER: P332519

CATALOG NUMBER: S124DIP-S350D1035U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	352.4	286.5	244.2	217.2	199.3	188.1	182.3	180.3	182.3	188.1	199.3
115°	371.4	311.5	271.5	244.6	225.6	215.6	208.6	205.7	208.6	215.6	225.6
117.5°	390.7	335.6	297.7	269.7	252.0	241.0	234.8	232.0	234.8	241.0	252.0
120°	404.3	352.4	314.5	286.5	269.5	258.6	251.6	249.6	251.6	258.6	269.5
122.5°	417.1	368.4	330.4	303.3	284.7	274.5	267.5	265.6	267.5	274.5	284.7
125°	436.3	390.3	354.4	326.4	307.5	296.5	290.5	286.5	290.5	296.5	307.5
127.5°	452.8	410.7	376.0	347.8	328.0	315.5	308.3	305.1	308.3	315.5	328.0
130°	463.2	424.3	390.3	361.4	342.4	327.4	319.5	315.5	319.5	327.4	342.4
132.5°	473.6	435.5	401.5	374.2	353.6	339.4	329.0	325.8	329.0	339.4	353.6
135°	487.2	451.2	418.3	392.3	371.4	354.4	344.4	340.4	344.4	354.4	371.4
137.5°	496.8	463.2	432.5	407.7	385.9	369.8	358.8	355.0	358.8	369.8	385.9
140°	503.1	471.2	441.3	417.3	396.3	379.4	368.4	365.4	368.4	379.4	396.3
142.5°	507.9	478.4	449.2	426.1	405.9	389.7	379.6	376.6	379.6	389.7	405.9
145°	513.1	486.2	460.2	438.3	419.3	405.3	395.3	392.3	395.3	405.3	419.3
147.5°	517.7	494.2	469.8	450.0	434.3	419.9	411.1	410.1	411.1	419.9	434.3
150°	520.1	498.2	476.2	457.2	442.3	430.3	422.3	421.3	422.3	430.3	442.3
152.5°	521.7	501.4	481.8	464.4	451.0	439.9	431.9	431.7	431.9	439.9	451.0
155°	523.1	506.1	489.2	474.2	463.2	453.2	447.2	446.2	447.2	453.2	463.2
157.5°	523.1	509.5	495.2	483.4	473.8	466.0	460.4	460.4	460.4	466.0	473.8
160°	523.1	511.1	499.2	488.2	480.2	473.2	469.2	469.2	469.2	473.2	480.2
162.5°	523.1	512.7	501.6	493.0	485.8	479.6	476.4	477.2	476.4	479.6	485.8
165°	521.1	513.1	504.1	498.2	493.2	488.2	486.2	486.2	486.2	488.2	493.2
167.5°	518.7	512.9	506.3	501.8	499.0	495.2	494.2	495.2	494.2	495.2	499.0
170°	517.1	512.1	507.1	504.1	502.2	499.2	498.2	499.2	498.2	499.2	502.2
172.5°	515.5	511.3	507.9	505.7	504.5	502.3	502.2	503.1	502.2	502.3	504.5
175°	513.1	510.1	508.1	508.1	507.1	506.1	506.1	507.1	506.1	506.1	507.1
177.5°	510.5	508.9	508.1	508.1	508.1	507.3	508.1	508.9	508.1	507.3	508.1
180°	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1



TEST NUMBER: P332519

CATALOG NUMBER: S124DIP-S350D1035U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3
2.5°	560.3	558.6	556.2	552.8	549.9	546.9	546.1	545.0	547.3	545.4	544.8
5°	542.0	537.0	530.6	523.3	519.0	512.9	511.7	509.3	506.9	506.7	504.3
7.5°	522.5	515.2	506.8	499.4	492.5	485.7	481.3	480.4	476.9	474.8	472.5
10°	510.0	501.0	491.3	484.2	476.2	469.1	464.1	461.3	458.9	456.3	453.9
12.5°	495.3	485.7	477.7	470.0	460.5	455.1	446.9	442.0	441.5	441.5	435.4
15°	478.1	468.6	456.3	445.4	440.2	429.8	425.3	419.6	416.1	412.5	409.7
17.5°	458.4	446.6	437.0	424.5	414.6	406.3	400.4	397.0	391.6	386.6	383.0
20°	446.1	433.6	423.4	410.1	399.3	389.1	384.1	379.4	375.4	371.1	367.1
22.5°	433.6	420.5	408.1	395.2	385.1	374.3	369.5	363.1	359.3	356.9	352.9
25°	413.9	399.7	385.5	373.2	362.8	353.3	347.0	342.0	337.7	335.8	333.2
27.5°	392.5	378.4	364.7	350.7	338.9	332.0	326.9	323.2	320.7	318.2	317.0
30°	378.9	364.2	349.6	336.5	325.7	318.8	314.1	311.5	309.6	308.4	307.2
32.5°	365.1	350.6	335.2	323.3	313.5	307.4	303.8	301.2	300.3	299.9	299.4
35°	342.9	328.3	314.1	303.4	294.2	291.8	288.7	287.3	286.8	288.5	289.2
37.5°	321.5	307.9	294.8	284.5	278.4	275.0	273.9	274.0	275.7	277.1	278.8
40°	307.7	294.4	282.1	273.1	267.4	265.3	264.8	266.0	267.9	269.6	271.5
42.5°	294.2	281.2	270.0	261.6	257.6	255.6	255.9	257.1	259.8	261.8	264.6
45°	273.4	262.5	251.6	244.7	241.4	241.9	241.9	244.0	246.6	249.7	252.8
47.5°	253.7	242.7	233.8	228.0	226.3	225.9	227.2	230.0	233.7	237.5	241.8
50°	240.5	230.0	222.2	217.0	215.1	215.8	217.7	220.3	224.8	229.6	234.1
52.5°	227.0	217.5	210.3	205.5	204.1	205.4	207.3	211.4	215.4	220.5	225.9
55°	206.1	198.1	192.4	188.9	188.4	189.1	191.2	195.7	201.4	207.8	213.0
57.5°	185.4	178.6	173.4	171.0	171.2	171.9	175.4	180.7	186.8	193.6	200.3
60°	171.3	165.2	160.9	159.0	159.3	160.7	165.0	169.9	177.5	184.1	191.2
62.5°	158.1	152.7	148.6	146.9	146.6	149.7	153.8	158.9	166.5	173.9	181.6
65°	136.8	132.5	129.2	128.3	129.0	131.4	136.6	143.4	149.8	157.6	165.7
67.5°	116.0	112.5	110.2	110.6	111.5	115.0	119.3	125.2	132.5	140.6	148.5
70°	102.7	99.4	97.5	97.7	99.2	103.4	107.2	113.1	120.9	129.2	135.8
72.5°	89.1	86.9	85.2	86.2	87.6	90.5	95.3	101.2	108.1	115.8	122.8
75°	68.4	68.4	67.5	68.2	70.3	73.1	76.7	82.8	89.7	95.9	101.5
77.5°	50.7	50.2	50.8	51.7	52.9	56.3	60.4	64.8	69.9	76.1	80.8
80°	38.8	39.1	40.2	41.7	42.1	44.7	49.0	53.0	57.0	62.2	66.7
82.5°	29.2	29.4	30.0	31.8	32.3	35.1	37.8	41.8	45.5	49.0	52.7
85°	15.9	15.9	17.0	17.8	18.9	20.8	22.5	24.9	28.2	30.5	34.1
87.5°	7.7	7.7	9.6	10.0	11.0	12.3	12.5	14.8	15.7	16.9	18.6
90°	8.0	8.0	14.0	14.0	16.0	18.0	17.0	18.0	19.0	20.0	20.0
92.5°	52.7	73.5	124.2	201.7	277.1	316.7	263.8	196.1	147.6	117.4	97.4
95°	82.9	124.8	211.6	375.4	614.0	813.6	836.6	739.7	585.0	451.2	354.4
97.5°	100.2	135.4	202.3	337.4	574.6	856.9	1051.0	1093.0	1035.4	937.8	833.6
100°	113.8	145.8	204.7	317.5	521.1	802.6	1058.2	1204.0	1223.9	1175.0	1101.1
102.5°	129.0	159.3	212.6	311.9	485.2	734.8	998.3	1198.4	1297.4	1311.6	1280.8
105°	154.7	183.7	231.6	314.5	454.2	654.9	889.5	1118.1	1290.8	1389.6	1430.6
107.5°	181.3	209.8	253.8	329.2	448.6	610.2	801.6	1004.1	1188.0	1327.2	1416.2
110°	199.7	226.6	270.5	340.4	450.2	595.0	757.7	935.4	1108.1	1252.9	1362.7



TEST NUMBER: P332519

CATALOG NUMBER: S124DIP-S350D1035U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	217.2	244.2	286.5	352.4	455.0	587.8	733.0	885.1	1037.8	1174.6	1284.4
115°	244.6	271.5	311.5	371.4	464.2	584.0	709.8	834.6	957.4	1074.2	1170.0
117.5°	269.7	297.7	335.6	390.7	474.0	583.0	699.4	809.8	911.5	1003.3	1084.6
120°	286.5	314.5	352.4	404.3	481.2	583.0	693.8	798.6	891.5	971.4	1042.2
122.5°	303.3	330.4	368.4	417.1	488.4	582.2	687.4	789.1	878.7	951.4	1013.5
125°	326.4	354.4	390.3	436.3	499.2	581.0	676.9	772.7	858.5	927.4	982.3
127.5°	347.8	376.0	410.7	452.8	507.7	578.8	662.7	752.7	834.8	903.5	955.6
130°	361.4	390.3	424.3	463.2	514.1	578.0	653.9	736.8	815.6	883.5	936.4
132.5°	374.2	401.5	435.5	473.6	519.7	577.2	645.9	720.0	794.1	860.3	913.3
135°	392.3	418.3	451.2	487.2	528.1	576.0	633.9	696.8	761.7	822.6	872.5
137.5°	407.7	432.5	463.2	496.8	533.1	575.8	623.5	675.9	730.8	782.1	827.2
140°	417.3	441.3	471.2	503.1	537.1	575.0	618.0	663.9	710.8	755.7	797.6
142.5°	426.1	449.2	478.4	507.9	540.3	575.0	613.2	652.7	694.0	732.6	768.9
145°	438.3	460.2	486.2	513.1	542.1	573.0	605.0	636.9	670.9	700.8	728.8
147.5°	450.0	469.8	494.2	517.7	543.1	569.4	597.6	623.9	650.9	674.9	696.8
150°	457.2	476.2	498.2	520.1	543.1	567.0	592.0	616.0	638.9	658.9	676.9
152.5°	464.4	481.8	501.4	521.7	541.5	563.0	585.6	607.2	626.9	645.3	660.1
155°	474.2	489.2	506.1	523.1	539.1	557.1	576.0	594.0	610.0	624.9	636.9
157.5°	483.4	495.2	509.5	523.1	536.5	550.9	566.2	579.8	593.2	605.8	615.4
160°	488.2	499.2	511.1	523.1	534.1	546.1	559.1	571.0	582.0	593.0	601.0
162.5°	493.0	501.6	512.7	523.1	531.7	541.3	552.7	562.2	571.6	580.2	587.4
165°	498.2	504.1	513.1	521.1	527.1	534.1	542.1	550.1	556.1	563.0	568.0
167.5°	501.8	506.3	512.9	518.7	522.3	526.9	532.5	538.3	542.9	548.5	551.5
170°	504.1	507.1	512.1	517.1	519.1	522.1	526.1	531.1	534.1	538.1	541.1
172.5°	505.7	507.9	511.3	515.5	515.9	517.3	520.5	524.7	526.9	529.3	531.5
175°	508.1	508.1	510.1	513.1	512.1	512.1	514.1	516.1	517.1	519.1	519.1
177.5°	508.1	508.1	508.9	510.5	508.9	508.9	509.7	510.5	511.3	511.3	512.1
180°	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1



TEST NUMBER: P332519

CATALOG NUMBER: S124DIP-S350D1035U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3
2.5°	544.4	544.1	542.7	542.5	542.7	544.1	544.4	544.8	545.4	547.3	545.0
5°	502.9	501.7	501.0	503.6	501.0	501.7	502.9	504.3	506.7	506.9	509.3
7.5°	471.6	470.7	468.6	467.9	468.6	470.7	471.6	472.5	474.8	476.9	480.4
10°	451.6	450.6	448.7	448.2	448.7	450.6	451.6	453.9	456.3	458.9	461.3
12.5°	432.2	430.4	430.0	430.5	430.0	430.4	432.2	435.4	441.5	441.5	442.0
15°	406.6	405.6	403.0	403.8	403.0	405.6	406.6	409.7	412.5	416.1	419.6
17.5°	381.3	380.2	377.0	379.8	377.0	380.2	381.3	383.0	386.6	391.6	397.0
20°	365.4	363.5	361.9	361.6	361.9	363.5	365.4	367.1	371.1	375.4	379.4
22.5°	350.3	348.6	348.4	346.9	348.4	348.6	350.3	352.9	356.9	359.3	363.1
25°	331.3	329.7	329.2	328.0	329.2	329.7	331.3	333.2	335.8	337.7	342.0
27.5°	316.8	316.0	315.1	315.5	315.1	316.0	316.8	317.0	318.2	320.7	323.2
30°	307.9	307.7	307.2	307.2	307.2	307.7	307.9	307.2	308.4	309.6	311.5
32.5°	300.5	300.5	300.8	300.8	300.8	300.5	300.5	299.4	299.9	300.3	301.2
35°	290.2	290.9	291.3	290.6	291.3	290.9	290.2	289.2	288.5	286.8	287.3
37.5°	280.8	281.5	282.2	283.0	282.2	281.5	280.8	278.8	277.1	275.7	274.0
40°	273.6	275.2	275.7	276.9	275.7	275.2	273.6	271.5	269.6	267.9	266.0
42.5°	266.8	268.6	269.8	270.1	269.8	268.6	266.8	264.6	261.8	259.8	257.1
45°	256.3	258.2	259.9	259.9	259.9	258.2	256.3	252.8	249.7	246.6	244.0
47.5°	245.5	248.2	249.9	250.3	249.9	248.2	245.5	241.8	237.5	233.7	230.0
50°	238.1	241.4	243.1	244.2	243.1	241.4	238.1	234.1	229.6	224.8	220.3
52.5°	230.9	234.2	236.4	237.0	236.4	234.2	230.9	225.9	220.5	215.4	211.4
55°	218.4	223.2	225.8	226.7	225.8	223.2	218.4	213.0	207.8	201.4	195.7
57.5°	206.7	211.1	214.1	214.8	214.1	211.1	206.7	200.3	193.6	186.8	180.7
60°	197.6	202.4	206.1	206.8	206.1	202.4	197.6	191.2	184.1	177.5	169.9
62.5°	188.3	193.3	196.7	198.5	196.7	193.3	188.3	181.6	173.9	166.5	158.9
65°	172.3	177.3	180.6	181.3	180.6	177.3	172.3	165.7	157.6	149.8	143.4
67.5°	154.8	159.8	161.9	163.3	161.9	159.8	154.8	148.5	140.6	132.5	125.2
70°	142.5	146.5	148.9	150.0	148.9	146.5	142.5	135.8	129.2	120.9	113.1
72.5°	128.5	132.7	135.4	135.7	135.4	132.7	128.5	122.8	115.8	108.1	101.2
75°	107.0	110.8	112.2	112.2	112.2	110.8	107.0	101.5	95.9	89.7	82.8
77.5°	84.7	86.6	88.4	88.8	88.4	86.6	84.7	80.8	76.1	69.9	64.8
80°	70.3	71.5	72.9	72.9	72.9	71.5	70.3	66.7	62.2	57.0	53.0
82.5°	55.5	56.5	57.9	57.7	57.9	56.5	55.5	52.7	49.0	45.5	41.8
85°	33.6	35.7	35.5	35.0	35.5	35.7	33.6	34.1	30.5	28.2	24.9
87.5°	19.3	19.7	20.1	20.5	20.1	19.7	19.3	18.6	16.9	15.7	14.8
90°	21.0	22.0	21.0	21.0	21.0	22.0	21.0	20.0	20.0	19.0	18.0
92.5°	85.7	80.3	76.9	76.9	76.9	80.3	85.7	97.4	117.4	147.6	196.1
95°	305.5	274.5	256.6	243.6	256.6	274.5	305.5	354.4	451.2	585.0	739.7
97.5°	761.9	701.8	671.9	651.1	671.9	701.8	761.9	833.6	937.8	1035.4	1093.0
100°	1014.3	953.4	923.4	915.5	923.4	953.4	1014.3	1101.1	1175.0	1223.9	1204.0
102.5°	1227.5	1183.4	1151.9	1145.5	1151.9	1183.4	1227.5	1280.8	1311.6	1297.4	1198.4
105°	1432.6	1424.6	1410.6	1404.6	1410.6	1424.6	1432.6	1430.6	1389.6	1290.8	1118.1
107.5°	1465.5	1488.3	1498.3	1500.9	1498.3	1488.3	1465.5	1416.2	1327.2	1188.0	1004.1
110°	1433.6	1475.5	1493.5	1502.5	1493.5	1475.5	1433.6	1362.7	1252.9	1108.1	935.4



TEST NUMBER: P332519

CATALOG NUMBER: S124DIP-S350D1035U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1364.9	1415.6	1440.8	1455.3	1440.8	1415.6	1364.9	1284.4	1174.6	1037.8	885.1
115°	1248.9	1308.8	1340.7	1348.7	1340.7	1308.8	1248.9	1170.0	1074.2	957.4	834.6
117.5°	1151.9	1202.2	1234.5	1240.7	1234.5	1202.2	1151.9	1084.6	1003.3	911.5	809.8
120°	1099.1	1143.1	1169.0	1180.0	1169.0	1143.1	1099.1	1042.2	971.4	891.5	798.6
122.5°	1061.6	1099.1	1121.1	1132.1	1121.1	1099.1	1061.6	1013.5	951.4	878.7	789.1
125°	1022.3	1051.2	1070.2	1076.2	1070.2	1051.2	1022.3	982.3	927.4	858.5	772.7
127.5°	995.7	1021.5	1037.4	1043.4	1037.4	1021.5	995.7	955.6	903.5	834.8	752.7
130°	977.3	1002.3	1018.3	1024.3	1018.3	1002.3	977.3	936.4	883.5	815.6	736.8
132.5°	953.4	981.5	996.7	1002.7	996.7	981.5	953.4	913.3	860.3	794.1	720.0
135°	912.5	940.4	956.4	962.4	956.4	940.4	912.5	872.5	822.6	761.7	696.8
137.5°	864.5	892.1	905.3	912.5	905.3	892.1	864.5	827.2	782.1	730.8	675.9
140°	832.6	854.6	868.5	876.5	868.5	854.6	832.6	797.6	755.7	710.8	663.9
142.5°	799.8	820.2	832.6	838.2	832.6	820.2	799.8	768.9	732.6	694.0	652.7
145°	753.7	770.7	780.7	785.7	780.7	770.7	753.7	728.8	700.8	670.9	636.9
147.5°	715.2	729.8	737.4	739.1	737.4	729.8	715.2	696.8	674.9	650.9	623.9
150°	692.8	705.8	711.8	712.8	711.8	705.8	692.8	676.9	658.9	638.9	616.0
152.5°	673.7	684.2	687.8	688.8	687.8	684.2	673.7	660.1	645.3	626.9	607.2
155°	646.9	654.9	657.9	657.9	657.9	654.9	646.9	636.9	624.9	610.0	594.0
157.5°	622.9	628.9	630.7	630.7	630.7	628.9	622.9	615.4	605.8	593.2	579.8
160°	607.0	613.0	614.0	614.0	614.0	613.0	607.0	601.0	593.0	582.0	571.0
162.5°	591.8	597.8	598.8	598.0	598.8	597.8	591.8	587.4	580.2	571.6	562.2
165°	572.0	576.0	575.0	574.0	575.0	576.0	572.0	568.0	563.0	556.1	550.1
167.5°	553.5	556.1	555.9	555.1	555.9	556.1	553.5	551.5	548.5	542.9	538.3
170°	543.1	544.1	543.1	543.1	543.1	544.1	543.1	541.1	538.1	534.1	531.1
172.5°	532.7	533.7	532.7	531.1	532.7	533.7	532.7	531.5	529.3	526.9	524.7
175°	519.1	521.1	519.1	517.1	519.1	521.1	519.1	519.1	519.1	517.1	516.1
177.5°	511.3	512.1	510.5	508.9	510.5	512.1	511.3	512.1	511.3	511.3	510.5
180°	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1



TEST NUMBER: P332519

CATALOG NUMBER: S124DIP-S350D1035U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3
2.5°	546.1	546.9	549.9	552.8	556.2	558.6	560.3	562.2	566.2	569.4	572.5
5°	511.7	512.9	519.0	523.3	530.6	537.0	542.0	547.4	553.8	562.6	570.6
7.5°	481.3	485.7	492.5	499.4	506.8	515.2	522.5	530.7	541.7	553.8	566.2
10°	464.1	469.1	476.2	484.2	491.3	501.0	510.0	519.7	532.3	546.9	561.6
12.5°	446.9	455.1	460.5	470.0	477.7	485.7	495.3	508.0	522.6	538.0	555.7
15°	425.3	429.8	440.2	445.4	456.3	468.6	478.1	490.8	505.0	525.4	545.3
17.5°	400.4	406.3	414.6	424.5	437.0	446.6	458.4	471.6	489.5	509.7	534.6
20°	384.1	389.1	399.3	410.1	423.4	433.6	446.1	458.9	477.4	498.9	524.9
22.5°	369.5	374.3	385.1	395.2	408.1	420.5	433.6	448.5	466.2	488.9	515.5
25°	347.0	353.3	362.8	373.2	385.5	399.7	413.9	427.2	446.1	470.0	498.4
27.5°	326.9	332.0	338.9	350.7	364.7	378.4	392.5	409.2	427.4	452.7	482.1
30°	314.1	318.8	325.7	336.5	349.6	364.2	378.9	395.0	413.9	439.0	469.1
32.5°	303.8	307.4	313.5	323.3	335.2	350.6	365.1	381.7	401.6	426.3	455.6
35°	288.7	291.8	294.2	303.4	314.1	328.3	342.9	360.7	379.9	403.3	432.6
37.5°	273.9	275.0	278.4	284.5	294.8	307.9	321.5	339.0	358.6	382.4	408.9
40°	264.8	265.3	267.4	273.1	282.1	294.4	307.7	324.9	343.6	366.1	392.4
42.5°	255.9	255.6	257.6	261.6	270.0	281.2	294.2	310.0	328.7	349.5	374.2
45°	241.9	241.9	241.4	244.7	251.6	262.5	273.4	288.5	304.1	324.5	345.3
47.5°	227.2	225.9	226.3	228.0	233.8	242.7	253.7	266.1	279.9	297.1	315.4
50°	217.7	215.8	215.1	217.0	222.2	230.0	240.5	251.3	264.4	279.5	295.1
52.5°	207.3	205.4	204.1	205.5	210.3	217.5	227.0	236.6	248.3	260.6	274.1
55°	191.2	189.1	188.4	188.9	192.4	198.1	206.1	214.9	223.7	233.8	243.3
57.5°	175.4	171.9	171.2	171.0	173.4	178.6	185.4	192.9	199.3	205.5	215.6
60°	165.0	160.7	159.3	159.0	160.9	165.2	171.3	178.9	183.4	187.7	196.4
62.5°	153.8	149.7	146.6	146.9	148.6	152.7	158.1	163.6	166.6	171.2	177.1
65°	136.6	131.4	129.0	128.3	129.2	132.5	136.8	140.3	143.7	145.6	151.2
67.5°	119.3	115.0	111.5	110.6	110.2	112.5	116.0	118.1	120.5	122.1	125.5
70°	107.2	103.4	99.2	97.7	97.5	99.4	102.7	103.0	106.3	107.0	110.5
72.5°	95.3	90.5	87.6	86.2	85.2	86.9	89.1	89.7	91.5	92.8	94.6
75°	76.7	73.1	70.3	68.2	67.5	68.4	68.4	69.6	70.8	71.5	73.6
77.5°	60.4	56.3	52.9	51.7	50.8	50.2	50.7	51.5	50.9	52.1	52.6
80°	49.0	44.7	42.1	41.7	40.2	39.1	38.8	39.5	38.6	39.1	40.5
82.5°	37.8	35.1	32.3	31.8	30.0	29.4	29.2	28.7	28.7	28.6	28.9
85°	22.5	20.8	18.9	17.8	17.0	15.9	15.9	15.4	14.9	14.4	14.7
87.5°	12.5	12.3	11.0	10.0	9.6	7.7	7.7	6.9	6.5	5.7	5.1
90°	17.0	18.0	16.0	14.0	14.0	8.0	8.0	7.0	6.0	3.0	1.0
92.5°	263.8	316.7	277.1	201.7	124.2	73.5	52.7	38.1	26.0	16.6	11.4
95°	836.6	813.6	614.0	375.4	211.6	124.8	82.9	58.9	45.9	35.9	32.9
97.5°	1051.0	856.9	574.6	337.4	202.3	135.4	100.2	79.7	67.7	59.1	59.1
100°	1058.2	802.6	521.1	317.5	204.7	145.8	113.8	94.8	82.9	75.9	75.9
102.5°	998.3	734.8	485.2	311.9	212.6	159.3	129.0	110.8	99.6	93.4	91.8
105°	889.5	654.9	454.2	314.5	231.6	183.7	154.7	136.8	124.8	119.8	116.8
107.5°	801.6	610.2	448.6	329.2	253.8	209.8	181.3	164.1	151.3	146.4	144.4
110°	757.7	595.0	450.2	340.4	270.5	226.6	199.7	181.7	169.7	164.7	162.7



TEST NUMBER: P332519

CATALOG NUMBER: S124DIP-S350D1035U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	733.0	587.8	455.0	352.4	286.5	244.2	217.2	199.3	188.1	182.3	180.3
115°	709.8	584.0	464.2	371.4	311.5	271.5	244.6	225.6	215.6	208.6	205.7
117.5°	699.4	583.0	474.0	390.7	335.6	297.7	269.7	252.0	241.0	234.8	232.0
120°	693.8	583.0	481.2	404.3	352.4	314.5	286.5	269.5	258.6	251.6	249.6
122.5°	687.4	582.2	488.4	417.1	368.4	330.4	303.3	284.7	274.5	267.5	265.6
125°	676.9	581.0	499.2	436.3	390.3	354.4	326.4	307.5	296.5	290.5	286.5
127.5°	662.7	578.8	507.7	452.8	410.7	376.0	347.8	328.0	315.5	308.3	305.1
130°	653.9	578.0	514.1	463.2	424.3	390.3	361.4	342.4	327.4	319.5	315.5
132.5°	645.9	577.2	519.7	473.6	435.5	401.5	374.2	353.6	339.4	329.0	325.8
135°	633.9	576.0	528.1	487.2	451.2	418.3	392.3	371.4	354.4	344.4	340.4
137.5°	623.5	575.8	533.1	496.8	463.2	432.5	407.7	385.9	369.8	358.8	355.0
140°	618.0	575.0	537.1	503.1	471.2	441.3	417.3	396.3	379.4	368.4	365.4
142.5°	613.2	575.0	540.3	507.9	478.4	449.2	426.1	405.9	389.7	379.6	376.6
145°	605.0	573.0	542.1	513.1	486.2	460.2	438.3	419.3	405.3	395.3	392.3
147.5°	597.6	569.4	543.1	517.7	494.2	469.8	450.0	434.3	419.9	411.1	410.1
150°	592.0	567.0	543.1	520.1	498.2	476.2	457.2	442.3	430.3	422.3	421.3
152.5°	585.6	563.0	541.5	521.7	501.4	481.8	464.4	451.0	439.9	431.9	431.7
155°	576.0	557.1	539.1	523.1	506.1	489.2	474.2	463.2	453.2	447.2	446.2
157.5°	566.2	550.9	536.5	523.1	509.5	495.2	483.4	473.8	466.0	460.4	460.4
160°	559.1	546.1	534.1	523.1	511.1	499.2	488.2	480.2	473.2	469.2	469.2
162.5°	552.7	541.3	531.7	523.1	512.7	501.6	493.0	485.8	479.6	476.4	477.2
165°	542.1	534.1	527.1	521.1	513.1	504.1	498.2	493.2	488.2	486.2	486.2
167.5°	532.5	526.9	522.3	518.7	512.9	506.3	501.8	499.0	495.2	494.2	495.2
170°	526.1	522.1	519.1	517.1	512.1	507.1	504.1	502.2	499.2	498.2	499.2
172.5°	520.5	517.3	515.9	515.5	511.3	507.9	505.7	504.5	502.3	502.2	503.1
175°	514.1	512.1	512.1	513.1	510.1	508.1	508.1	507.1	506.1	506.1	507.1
177.5°	509.7	508.9	508.9	510.5	508.9	508.1	508.1	508.1	507.3	508.1	508.9
180°	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1



TEST NUMBER: P332519

CATALOG NUMBER: S124DIP-S350D1035U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3
2.5°	575.1	577.0	579.5	583.6	585.1	587.0	589.7	589.5	590.2	593.1	599.1
5°	577.2	584.6	591.7	600.2	609.2	615.1	623.1	628.1	633.1	639.5	650.4
7.5°	578.1	589.7	602.7	617.7	631.0	646.3	658.3	669.6	679.8	693.2	706.2
10°	576.8	592.4	609.2	628.1	648.2	665.3	680.7	698.2	713.1	729.4	744.1
12.5°	574.3	593.1	615.6	636.8	660.3	685.5	704.7	722.4	742.2	761.0	783.7
15°	568.7	594.5	620.8	648.7	680.2	709.3	737.0	759.9	781.2	809.4	839.0
17.5°	561.6	589.4	622.6	656.4	689.3	722.5	756.8	791.3	818.2	853.2	876.3
20°	555.0	587.2	621.3	661.5	694.4	735.8	769.9	803.2	840.2	875.0	902.7
22.5°	545.7	580.9	617.1	657.1	700.4	741.9	781.2	817.4	854.4	892.2	925.7
25°	533.9	565.9	608.7	654.1	697.2	742.2	787.4	832.8	872.6	912.6	943.8
27.5°	513.9	554.2	594.1	641.0	688.8	739.7	788.1	835.6	877.3	910.2	929.5
30°	503.6	538.7	582.0	629.1	680.9	735.6	786.0	832.6	871.4	897.7	905.5
32.5°	488.5	524.6	567.0	615.8	670.7	726.9	779.3	823.3	855.7	869.5	860.1
35°	466.0	498.7	541.5	591.4	648.5	708.3	760.2	797.3	813.9	800.9	768.5
37.5°	439.0	471.4	514.4	563.5	622.5	683.4	730.2	757.0	751.5	719.1	670.8
40°	420.1	450.4	491.3	544.3	601.8	662.9	704.1	718.5	703.4	657.0	605.6
42.5°	399.1	428.6	469.7	520.9	581.8	638.1	674.0	675.2	649.8	594.3	542.8
45°	367.1	395.2	434.0	487.3	543.6	596.6	620.3	608.7	561.8	508.4	456.5
47.5°	335.5	359.9	398.2	448.7	502.2	546.8	558.6	537.7	487.8	435.8	387.8
50°	312.4	337.0	373.0	421.3	472.9	511.4	517.1	489.4	440.4	388.1	350.5
52.5°	290.2	314.7	349.3	394.0	441.2	476.0	476.2	444.2	395.4	348.8	313.8
55°	257.7	279.7	311.0	351.0	393.1	420.3	413.7	380.6	338.2	297.7	267.2
57.5°	226.4	245.6	274.3	307.7	344.8	367.3	356.3	324.4	286.6	252.2	229.1
60°	206.1	224.4	249.0	280.5	311.7	329.2	318.8	289.9	255.1	227.4	207.3
62.5°	186.4	201.8	225.5	252.8	281.8	294.7	285.5	257.0	226.9	201.9	185.5
65°	158.6	171.1	190.0	213.5	234.5	245.7	237.9	211.3	188.4	170.4	157.4
67.5°	132.5	142.3	156.7	175.5	193.4	199.4	192.3	173.8	154.4	140.0	130.8
70°	114.5	123.8	135.8	150.3	165.9	172.3	165.2	150.5	134.7	121.4	112.4
72.5°	98.8	106.0	116.2	128.5	140.7	147.1	142.3	128.2	114.8	104.9	97.3
75°	75.3	81.4	88.5	97.3	106.7	111.0	106.7	97.0	87.8	80.5	75.0
77.5°	54.7	58.0	63.5	70.1	76.0	79.2	75.5	69.0	63.3	58.3	55.6
80°	41.7	44.0	47.8	53.0	57.0	60.1	57.7	52.3	47.8	44.5	43.3
82.5°	30.3	31.9	34.4	38.2	40.9	42.5	41.5	37.5	35.7	32.8	31.6
85°	14.9	15.9	17.5	18.7	21.1	21.3	21.5	19.9	18.2	17.5	16.6
87.5°	5.7	6.5	7.3	8.0	8.8	10.2	10.0	10.4	10.0	9.6	9.1
90°	3.0	6.0	7.0	8.0	8.0	14.0	14.0	16.0	18.0	17.0	18.0
92.5°	16.6	26.0	38.1	52.7	73.5	124.2	201.7	277.1	316.7	263.8	196.1
95°	35.9	45.9	58.9	82.9	124.8	211.6	375.4	614.0	813.6	836.6	739.7
97.5°	59.1	67.7	79.7	100.2	135.4	202.3	337.4	574.6	856.9	1051.0	1093.0
100°	75.9	82.9	94.8	113.8	145.8	204.7	317.5	521.1	802.6	1058.2	1204.0
102.5°	93.4	99.6	110.8	129.0	159.3	212.6	311.9	485.2	734.8	998.3	1198.4
105°	119.8	124.8	136.8	154.7	183.7	231.6	314.5	454.2	654.9	889.5	1118.1
107.5°	146.4	151.3	164.1	181.3	209.8	253.8	329.2	448.6	610.2	801.6	1004.1
110°	164.7	169.7	181.7	199.7	226.6	270.5	340.4	450.2	595.0	757.7	935.4





TEST NUMBER: P332519

CATALOG NUMBER: S124DIP-S350D1035U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	182.3	188.1	199.3	217.2	244.2	286.5	352.4	455.0	587.8	733.0	885.1
115°	208.6	215.6	225.6	244.6	271.5	311.5	371.4	464.2	584.0	709.8	834.6
117.5°	234.8	241.0	252.0	269.7	297.7	335.6	390.7	474.0	583.0	699.4	809.8
120°	251.6	258.6	269.5	286.5	314.5	352.4	404.3	481.2	583.0	693.8	798.6
122.5°	267.5	274.5	284.7	303.3	330.4	368.4	417.1	488.4	582.2	687.4	789.1
125°	290.5	296.5	307.5	326.4	354.4	390.3	436.3	499.2	581.0	676.9	772.7
127.5°	308.3	315.5	328.0	347.8	376.0	410.7	452.8	507.7	578.8	662.7	752.7
130°	319.5	327.4	342.4	361.4	390.3	424.3	463.2	514.1	578.0	653.9	736.8
132.5°	329.0	339.4	353.6	374.2	401.5	435.5	473.6	519.7	577.2	645.9	720.0
135°	344.4	354.4	371.4	392.3	418.3	451.2	487.2	528.1	576.0	633.9	696.8
137.5°	358.8	369.8	385.9	407.7	432.5	463.2	496.8	533.1	575.8	623.5	675.9
140°	368.4	379.4	396.3	417.3	441.3	471.2	503.1	537.1	575.0	618.0	663.9
142.5°	379.6	389.7	405.9	426.1	449.2	478.4	507.9	540.3	575.0	613.2	652.7
145°	395.3	405.3	419.3	438.3	460.2	486.2	513.1	542.1	573.0	605.0	636.9
147.5°	411.1	419.9	434.3	450.0	469.8	494.2	517.7	543.1	569.4	597.6	623.9
150°	422.3	430.3	442.3	457.2	476.2	498.2	520.1	543.1	567.0	592.0	616.0
152.5°	431.9	439.9	451.0	464.4	481.8	501.4	521.7	541.5	563.0	585.6	607.2
155°	447.2	453.2	463.2	474.2	489.2	506.1	523.1	539.1	557.1	576.0	594.0
157.5°	460.4	466.0	473.8	483.4	495.2	509.5	523.1	536.5	550.9	566.2	579.8
160°	469.2	473.2	480.2	488.2	499.2	511.1	523.1	534.1	546.1	559.1	571.0
162.5°	476.4	479.6	485.8	493.0	501.6	512.7	523.1	531.7	541.3	552.7	562.2
165°	486.2	488.2	493.2	498.2	504.1	513.1	521.1	527.1	534.1	542.1	550.1
167.5°	494.2	495.2	499.0	501.8	506.3	512.9	518.7	522.3	526.9	532.5	538.3
170°	498.2	499.2	502.2	504.1	507.1	512.1	517.1	519.1	522.1	526.1	531.1
172.5°	502.2	502.3	504.5	505.7	507.9	511.3	515.5	515.9	517.3	520.5	524.7
175°	506.1	506.1	507.1	508.1	508.1	510.1	513.1	512.1	512.1	514.1	516.1
177.5°	508.1	507.3	508.1	508.1	508.1	508.9	510.5	508.9	508.9	509.7	510.5
180°	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1



TEST NUMBER: P332519

CATALOG NUMBER: S124DIP-S350D1035U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	571.3	571.3	571.3	571.3	571.3	571.3	571.3
2.5°	602.2	602.6	604.3	605.6	606.0	607.9	608.0
5°	655.1	659.1	666.9	667.6	668.8	675.0	670.2
7.5°	717.1	727.3	734.1	740.2	742.3	745.0	744.5
10°	756.9	772.0	779.6	791.7	792.1	795.2	793.3
12.5°	796.8	814.4	828.2	830.5	840.6	842.2	844.8
15°	853.4	872.1	891.3	898.2	912.1	915.4	920.6
17.5°	906.6	925.7	939.2	956.9	962.7	970.3	965.1
20°	935.8	956.6	973.7	987.6	993.5	997.8	997.3
22.5°	953.4	974.4	988.2	998.8	1004.3	1006.1	1006.0
25°	964.4	976.5	980.8	984.8	978.6	976.5	977.4
27.5°	933.7	930.6	919.5	904.9	889.8	877.8	871.2
30°	891.5	873.1	856.3	826.9	811.8	802.8	794.7
32.5°	831.7	802.4	770.1	743.2	726.0	712.7	710.7
35°	729.2	685.2	645.6	612.7	595.7	581.3	577.9
37.5°	619.9	574.2	538.6	509.6	491.3	481.1	471.6
40°	547.4	508.1	473.1	448.5	434.5	427.2	421.3
42.5°	491.6	455.7	420.8	402.1	389.5	385.0	381.5
45°	414.4	381.0	356.9	342.7	335.4	327.8	324.2
47.5°	352.6	325.5	309.6	297.5	289.6	285.1	282.9
50°	317.6	295.4	281.2	271.9	264.8	261.3	259.4
52.5°	286.6	268.3	256.4	249.0	244.2	241.6	240.8
55°	246.8	232.9	225.3	218.9	215.4	213.0	212.1
57.5°	214.6	203.8	197.7	192.4	191.0	189.1	188.4
60°	193.4	185.1	179.9	176.3	175.1	172.8	173.2
62.5°	174.6	167.8	163.4	161.4	159.8	157.8	158.5
65°	147.7	142.7	140.3	138.5	136.6	135.4	136.3
67.5°	123.9	120.5	117.3	116.2	115.3	115.1	114.1
70°	108.4	105.6	102.7	102.0	102.0	101.1	100.8
72.5°	93.4	91.4	89.5	88.9	88.2	88.6	87.6
75°	72.2	70.5	69.8	69.1	68.9	68.9	68.2
77.5°	53.3	52.1	51.0	51.0	50.1	49.8	49.7
80°	40.5	40.0	39.1	39.1	38.6	38.8	38.3
82.5°	30.4	29.8	29.6	29.2	28.5	28.6	28.1
85°	16.3	15.6	15.4	14.7	14.2	14.7	14.2
87.5°	9.5	9.5	9.3	9.1	9.1	8.9	8.4
90°	19.0	20.0	20.0	21.0	22.0	21.0	21.0
92.5°	147.6	117.4	97.4	85.7	80.3	76.9	76.9
95°	585.0	451.2	354.4	305.5	274.5	256.6	243.6
97.5°	1035.4	937.8	833.6	761.9	701.8	671.9	651.1
100°	1223.9	1175.0	1101.1	1014.3	953.4	923.4	915.5
102.5°	1297.4	1311.6	1280.8	1227.5	1183.4	1151.9	1145.5
105°	1290.8	1389.6	1430.6	1432.6	1424.6	1410.6	1404.6
107.5°	1188.0	1327.2	1416.2	1465.5	1488.3	1498.3	1500.9
110°	1108.1	1252.9	1362.7	1433.6	1475.5	1493.5	1502.5



TEST NUMBER: P332519

CATALOG NUMBER: S124DIP-S350D1035U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	1037.8	1174.6	1284.4	1364.9	1415.6	1440.8	1455.3
115°	957.4	1074.2	1170.0	1248.9	1308.8	1340.7	1348.7
117.5°	911.5	1003.3	1084.6	1151.9	1202.2	1234.5	1240.7
120°	891.5	971.4	1042.2	1099.1	1143.1	1169.0	1180.0
122.5°	878.7	951.4	1013.5	1061.6	1099.1	1121.1	1132.1
125°	858.5	927.4	982.3	1022.3	1051.2	1070.2	1076.2
127.5°	834.8	903.5	955.6	995.7	1021.5	1037.4	1043.4
130°	815.6	883.5	936.4	977.3	1002.3	1018.3	1024.3
132.5°	794.1	860.3	913.3	953.4	981.5	996.7	1002.7
135°	761.7	822.6	872.5	912.5	940.4	956.4	962.4
137.5°	730.8	782.1	827.2	864.5	892.1	905.3	912.5
140°	710.8	755.7	797.6	832.6	854.6	868.5	876.5
142.5°	694.0	732.6	768.9	799.8	820.2	832.6	838.2
145°	670.9	700.8	728.8	753.7	770.7	780.7	785.7
147.5°	650.9	674.9	696.8	715.2	729.8	737.4	739.1
150°	638.9	658.9	676.9	692.8	705.8	711.8	712.8
152.5°	626.9	645.3	660.1	673.7	684.2	687.8	688.8
155°	610.0	624.9	636.9	646.9	654.9	657.9	657.9
157.5°	593.2	605.8	615.4	622.9	628.9	630.7	630.7
160°	582.0	593.0	601.0	607.0	613.0	614.0	614.0
162.5°	571.6	580.2	587.4	591.8	597.8	598.8	598.0
165°	556.1	563.0	568.0	572.0	576.0	575.0	574.0
167.5°	542.9	548.5	551.5	553.5	556.1	555.9	555.1
170°	534.1	538.1	541.1	543.1	544.1	543.1	543.1
172.5°	526.9	529.3	531.5	532.7	533.7	532.7	531.1
175°	517.1	519.1	519.1	519.1	521.1	519.1	517.1
177.5°	511.3	511.3	512.1	511.3	512.1	510.5	508.9
180°	508.1	508.1	508.1	508.1	508.1	508.1	508.1

(END OF REPORT)