

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332964

Luminaire Tested: **S124RDIP-S1020D590U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332964  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIP-S1020D590U835-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 590 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6533.2 lumens  
Efficiency: N/A  
Efficacy: 133.9 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 48.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332964

CATALOG NUMBER: S124RDIP-S1020D590U835-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332964

CATALOG NUMBER: S124RDIP-S1020D590U835-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	104	104	104	104	91	91	91	79	79	79	69	69	69	64
1	101	97	93	90	95	91	88	85	80	78	76	71	69	67	61	60	59	55
2	92	85	79	74	87	80	75	70	71	67	63	62	59	57	54	52	50	46
3	85	75	68	62	79	71	64	59	63	58	54	55	51	48	49	46	43	40
4	78	67	59	53	73	63	56	50	56	50	46	50	45	42	44	40	37	34
5	71	60	52	45	67	56	49	44	50	44	40	45	40	36	39	36	33	30
6	66	54	46	40	62	51	44	38	46	40	35	41	36	32	36	32	29	26
7	61	49	41	35	57	46	39	34	41	35	31	37	32	28	33	29	26	23
8	57	44	37	31	53	42	35	30	38	32	28	34	29	26	30	26	23	21
9	53	41	33	28	50	39	32	27	35	29	25	31	27	23	28	24	21	19
10	50	37	30	25	47	36	29	24	32	27	23	29	24	21	26	22	19	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	14577	14577	14577
5°	14610	14431	14521
10°	14519	14258	14258
15°	14352	13959	13855
20°	14123	13564	13315
25°	13831	13104	12772
30°	13546	12618	12089
35°	13231	12113	11404
40°	12852	11540	10666
45°	12501	10970	9913
50°	12103	10315	9117
55°	11676	9633	8251
60°	11207	8885	7367
65°	10776	7950	6497
70°	10150	6918	5516
75°	9357	5736	4485
80°	8164	4370	4114
85°	6919	3974	3714



TEST NUMBER: P332964

CATALOG NUMBER: S124RDIP-S1020D590U835-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	169.6	2.6
10°-20°	473.0	7.2
20°-30°	683.0	10.5
30°-40°	774.2	11.9
40°-50°	747.6	11.4
50°-60°	621.7	9.5
60°-70°	429.3	6.6
70°-80°	217.6	3.3
80°-90°	58.0	0.9
90°-100°	26.1	0.4
100°-110°	166.3	2.5
110°-120°	318.2	4.9
120°-130°	403.9	6.2
130°-140°	432.1	6.6
140°-150°	404.1	6.2
150°-160°	325.9	5.0
160°-170°	210.2	3.2
170°-180°	72.4	1.1
0°-30°	1325.6	20.3
0°-40°	2099.9	32.1
0°-60°	3469.2	53.1
0°-90°	4174.1	63.9
90°-120°	510.6	7.8
90°-150°	1750.6	26.8
90°-180°	2359.0	36.1
0°-180°	6533.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1806	1806	1806	1806	1806	
5°	1803	1797	1781	1794	1792	171
15°	1717	1704	1670	1667	1658	484
25°	1553	1526	1471	1448	1434	715
35°	1342	1297	1229	1183	1157	839
45°	1095	1042	961	896	868	844
55°	830	772	684	615	586	742
65°	564	503	416	359	340	557
75°	300	248	184	153	144	317
85°	75	48	43	40	40	84
90°	2	8	12	16	17	5
95°	31	13	12	16	16	40
105°	172	175	178	182	163	180
115°	321	322	322	323	323	315
125°	451	453	452	453	454	402
135°	559	559	561	562	563	431
145°	645	646	646	647	648	403
155°	707	707	706	708	706	326
165°	746	743	743	747	742	211
175°	763	759	760	764	758	73
180°	763	763	763	763	763	



TEST NUMBER: P332964

CATALOG NUMBER: S124RDIP-S1020D590U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7
2.5°	1810.1	1809.1	1808.1	1807.2	1806.2	1804.3	1801.6	1798.9	1796.2	1793.5	1796.2
5°	1802.9	1801.7	1800.5	1799.2	1798.0	1795.5	1791.9	1788.2	1784.5	1780.8	1783.9
7.5°	1786.6	1785.3	1784.0	1782.7	1781.4	1778.4	1773.6	1768.8	1764.0	1759.2	1761.2
10°	1771.1	1769.6	1768.0	1766.5	1765.0	1761.4	1755.9	1750.4	1744.8	1739.3	1740.5
12.5°	1751.2	1749.4	1747.6	1745.9	1744.1	1739.9	1733.4	1726.9	1720.4	1713.9	1714.6
15°	1717.2	1714.4	1711.7	1708.9	1706.1	1700.9	1693.2	1685.5	1677.9	1670.2	1669.6
17.5°	1676.0	1672.0	1668.0	1664.0	1660.0	1653.4	1644.2	1635.0	1625.8	1616.5	1614.8
20°	1643.9	1639.9	1635.9	1631.9	1627.9	1620.7	1610.3	1599.8	1589.4	1578.9	1576.5
22.5°	1608.5	1604.0	1599.5	1595.1	1590.6	1582.7	1571.6	1560.4	1549.2	1538.0	1534.3
25°	1552.7	1547.1	1541.6	1536.1	1530.5	1521.5	1508.9	1496.3	1483.7	1471.1	1465.9
27.5°	1494.0	1487.1	1480.2	1473.2	1466.3	1456.1	1442.6	1429.2	1415.7	1402.2	1395.8
30°	1453.1	1445.4	1437.8	1430.1	1422.4	1411.3	1396.9	1382.4	1368.0	1353.6	1345.9
32.5°	1410.0	1401.3	1392.6	1384.0	1375.3	1363.5	1348.6	1333.7	1318.7	1303.8	1294.9
35°	1342.5	1332.7	1322.8	1313.0	1303.2	1290.6	1275.2	1259.9	1244.5	1229.1	1218.7
37.5°	1270.3	1260.2	1250.1	1239.9	1229.8	1216.2	1199.2	1182.2	1165.1	1148.1	1136.4
40°	1219.5	1209.3	1199.2	1189.0	1178.9	1165.1	1147.6	1130.0	1112.5	1095.0	1082.1
42.5°	1170.8	1160.2	1149.5	1138.9	1128.3	1113.8	1095.6	1077.3	1059.1	1040.8	1027.7
45°	1095.0	1083.7	1072.3	1060.9	1049.5	1034.6	1016.2	997.8	979.3	960.9	945.9
47.5°	1016.8	1005.0	993.3	981.6	969.8	954.4	935.2	916.0	896.8	877.7	862.1
50°	963.7	951.7	939.7	927.7	915.7	899.9	880.3	860.6	840.9	821.3	805.9
52.5°	909.5	897.7	886.0	874.3	862.5	846.6	826.4	806.3	786.1	766.0	750.4
55°	829.6	817.3	805.0	792.7	780.4	764.3	744.3	724.3	704.4	684.4	668.4
57.5°	750.5	737.7	724.9	712.1	699.4	683.1	663.5	643.8	624.1	604.5	588.3
60°	694.1	681.8	669.5	657.2	644.9	628.9	609.3	589.6	569.9	550.3	534.3
62.5°	643.2	630.4	617.6	604.8	592.1	575.6	555.4	535.3	515.1	495.0	480.2
65°	564.1	550.9	537.7	524.5	511.3	494.8	475.2	455.5	435.8	416.2	403.0
67.5°	482.0	469.3	456.7	444.0	431.3	415.9	397.6	379.4	361.1	342.9	331.5
70°	430.0	417.1	404.2	391.3	378.4	363.2	345.7	328.1	310.6	293.1	283.0
72.5°	374.7	363.0	351.3	339.7	328.0	313.9	297.4	280.8	264.3	247.8	239.1
75°	300.0	288.7	277.3	265.9	254.6	241.6	227.2	212.8	198.3	183.9	176.8
77.5°	224.3	214.6	205.0	195.3	185.7	175.0	163.3	151.7	140.0	128.3	124.2
80°	175.6	166.7	157.8	148.9	140.0	130.9	121.7	112.5	103.2	94.0	93.1
82.5°	133.6	125.4	117.2	109.0	100.9	94.1	88.9	83.6	78.3	73.0	72.3
85°	74.7	68.5	62.4	56.2	50.1	46.5	45.6	44.7	43.8	42.9	42.2
87.5°	25.8	24.1	22.4	20.7	19.0	18.2	18.1	18.1	18.0	18.0	17.9
90°	1.7	3.1	4.5	5.9	7.3	8.5	9.5	10.5	11.5	12.5	13.3
92.5°	7.2	7.3	7.3	7.4	7.5	8.0	9.1	10.1	11.1	12.1	12.9
95°	31.4	27.1	22.8	18.4	14.1	12.0	12.2	12.3	12.4	12.5	13.3
97.5°	66.6	69.3	72.0	74.7	77.4	71.6	57.5	43.4	29.2	15.1	15.1
100°	93.5	95.8	98.1	100.4	102.7	95.1	77.6	60.1	42.6	25.1	22.9
102.5°	123.7	125.3	127.0	128.7	130.4	130.1	127.8	125.5	123.2	120.9	97.7
105°	171.7	172.5	173.2	174.0	174.7	175.4	176.1	176.7	177.3	178.0	179.1
107.5°	216.3	216.7	217.1	217.4	217.8	218.4	219.3	220.2	221.0	221.9	222.5
110°	246.4	246.8	247.2	247.6	247.9	248.5	249.3	250.0	250.8	251.6	251.8



TEST NUMBER: P332964

CATALOG NUMBER: S124RDIP-S1020D590U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	275.6	276.3	277.0	277.7	278.4	278.9	279.2	279.6	280.0	280.3	280.3
115°	320.6	321.0	321.3	321.7	322.1	322.2	322.1	322.0	321.8	321.7	322.0
117.5°	361.1	361.6	362.1	362.6	363.1	363.5	363.8	364.1	364.3	364.6	364.6
120°	388.5	389.0	389.5	390.0	390.5	390.7	390.6	390.4	390.3	390.2	390.4
122.5°	414.0	414.3	414.6	414.9	415.2	415.5	415.7	415.8	416.0	416.2	416.3
125°	450.6	451.1	451.7	452.2	452.7	452.8	452.5	452.3	452.0	451.8	452.2
127.5°	485.3	485.4	485.6	485.7	485.8	486.2	486.8	487.3	487.9	488.5	488.4
130°	507.7	507.8	507.9	508.1	508.2	508.4	508.8	509.2	509.6	510.0	510.1
132.5°	528.2	528.4	528.7	528.9	529.1	529.5	530.0	530.4	530.9	531.4	531.5
135°	559.0	558.9	558.8	558.6	558.5	558.7	559.2	559.7	560.2	560.7	561.0
137.5°	586.3	586.3	586.4	586.4	586.5	586.8	587.3	587.9	588.5	589.0	589.3
140°	604.1	604.3	604.6	604.8	605.1	605.3	605.6	605.9	606.1	606.4	606.7
142.5°	620.1	620.5	621.0	621.4	621.9	622.2	622.3	622.5	622.6	622.8	623.1
145°	644.6	645.0	645.3	645.7	646.1	646.3	646.3	646.3	646.3	646.3	646.4
147.5°	664.1	664.8	665.5	666.2	666.9	667.2	667.1	667.0	666.8	666.7	666.8
150°	678.2	678.7	679.3	679.8	680.3	680.5	680.3	680.2	680.1	679.9	679.9
152.5°	690.1	690.5	690.9	691.3	691.7	691.8	691.6	691.4	691.1	690.9	691.1
155°	706.8	706.9	707.0	707.1	707.3	707.1	706.8	706.4	706.0	705.6	706.1
157.5°	720.8	720.7	720.6	720.6	720.5	720.2	719.8	719.4	718.9	718.5	719.2
160°	729.0	728.6	728.2	727.9	727.5	727.2	727.1	727.0	726.8	726.7	727.5
162.5°	736.3	735.8	735.3	734.9	734.4	734.1	733.9	733.8	733.7	733.6	734.3
165°	745.5	744.9	744.3	743.6	743.0	742.7	742.7	742.7	742.7	742.7	743.7
167.5°	752.8	752.2	751.5	750.9	750.2	749.8	749.8	749.7	749.6	749.5	750.7
170°	757.0	756.2	755.4	754.7	753.9	753.6	753.7	753.8	754.0	754.1	755.1
172.5°	759.7	758.9	758.2	757.4	756.7	756.3	756.5	756.6	756.7	756.8	757.9
175°	762.7	761.9	761.1	760.4	759.6	759.3	759.4	759.6	759.7	759.8	760.9
177.5°	764.0	763.3	762.6	761.9	761.2	760.9	761.1	761.3	761.5	761.7	762.6
180°	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7



TEST NUMBER: P332964

CATALOG NUMBER: S124RDIP-S1020D590U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7
2.5°	1798.9	1801.6	1804.3	1805.6	1805.3	1805.1	1804.8	1804.6
5°	1786.9	1790.0	1793.1	1794.3	1793.7	1793.1	1792.5	1791.9
7.5°	1763.2	1765.1	1767.1	1767.6	1766.6	1765.6	1764.6	1763.6
10°	1741.8	1743.0	1744.2	1744.2	1743.0	1741.8	1740.5	1739.3
12.5°	1715.3	1716.1	1716.8	1716.3	1714.6	1712.9	1711.2	1709.5
15°	1669.0	1668.3	1667.7	1666.3	1664.2	1662.0	1659.9	1657.7
17.5°	1613.1	1611.4	1609.7	1607.2	1603.9	1600.7	1597.4	1594.1
20°	1574.0	1571.6	1569.1	1565.9	1561.9	1557.9	1553.9	1549.9
22.5°	1530.6	1526.9	1523.3	1519.8	1516.5	1513.3	1510.0	1506.8
25°	1460.6	1455.4	1450.2	1446.0	1443.0	1439.9	1436.8	1433.8
27.5°	1389.3	1382.9	1376.4	1371.0	1366.6	1362.1	1357.7	1353.3
30°	1338.2	1330.5	1322.8	1316.5	1311.6	1306.7	1301.8	1296.9
32.5°	1286.0	1277.1	1268.2	1261.4	1256.7	1252.0	1247.4	1242.7
35°	1208.2	1197.8	1187.3	1179.4	1173.8	1168.3	1162.8	1157.2
37.5°	1124.8	1113.1	1101.4	1092.8	1087.3	1081.7	1076.2	1070.7
40°	1069.2	1056.3	1043.4	1034.2	1028.7	1023.1	1017.6	1012.1
42.5°	1014.5	1001.4	988.2	978.8	973.0	967.2	961.4	955.7
45°	930.8	915.7	900.7	890.4	884.9	879.3	873.8	868.3
47.5°	846.5	830.9	815.2	804.4	798.3	792.2	786.1	780.1
50°	790.5	775.2	759.8	749.2	743.4	737.5	731.7	725.9
52.5°	734.7	719.1	703.5	692.7	686.6	680.5	674.4	668.4
55°	652.4	636.5	620.5	609.6	603.7	597.9	592.1	586.2
57.5°	572.0	555.8	539.6	529.3	524.8	520.4	516.0	511.6
60°	518.3	502.3	486.4	475.9	471.0	466.1	461.2	456.3
62.5°	465.5	450.7	436.0	426.6	422.7	418.8	414.8	410.9
65°	389.7	376.5	363.3	354.9	351.2	347.5	343.8	340.1
67.5°	320.1	308.8	297.4	289.7	285.6	281.6	277.5	273.5
70°	272.8	262.7	252.6	245.9	242.9	239.8	236.7	233.7
72.5°	230.4	221.8	213.1	207.4	204.5	201.7	198.9	196.1
75°	169.8	162.7	155.6	151.2	149.3	147.5	145.6	143.8
77.5°	120.1	116.0	111.8	109.5	108.9	108.4	107.8	107.3
80°	92.2	91.3	90.3	89.7	89.4	89.1	88.8	88.5
82.5°	71.6	71.0	70.3	69.8	69.5	69.2	68.9	68.6
85°	41.6	41.0	40.4	40.1	40.1	40.1	40.1	40.1
87.5°	17.8	17.7	17.6	17.7	18.0	18.3	18.6	18.9
90°	14.1	14.8	15.6	16.1	16.4	16.6	16.9	17.1
92.5°	13.6	14.4	15.1	15.5	15.6	15.6	15.7	15.7
95°	14.1	14.8	15.6	16.0	16.2	16.3	16.4	16.5
97.5°	15.2	15.3	15.4	15.5	15.6	15.7	15.8	16.0
100°	20.8	18.6	16.5	15.5	15.6	15.7	15.8	16.0
102.5°	74.4	51.2	27.9	16.3	16.4	16.4	16.4	16.4
105°	180.3	181.4	182.5	180.8	176.3	171.7	167.1	162.6
107.5°	223.0	223.6	224.1	224.6	225.1	225.6	226.1	226.6
110°	252.1	252.3	252.6	252.9	253.3	253.6	254.0	254.4





TEST NUMBER: P332964

CATALOG NUMBER: S124RDIP-S1020D590U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	280.2	280.2	280.1	280.3	280.8	281.3	281.8	282.2
115°	322.2	322.5	322.7	322.9	322.9	322.9	322.9	322.9
117.5°	364.5	364.5	364.4	364.4	364.3	364.3	364.2	364.2
120°	390.7	390.9	391.2	391.2	390.9	390.7	390.4	390.2
122.5°	416.5	416.6	416.8	416.7	416.5	416.2	416.0	415.7
125°	452.5	452.9	453.3	453.6	453.7	453.8	453.9	454.1
127.5°	488.4	488.3	488.2	488.1	488.0	487.9	487.8	487.7
130°	510.2	510.3	510.5	510.5	510.5	510.5	510.5	510.5
132.5°	531.7	531.8	531.9	531.9	531.8	531.7	531.6	531.5
135°	561.2	561.5	561.7	562.0	562.2	562.5	562.8	563.0
137.5°	589.6	589.9	590.1	590.2	590.2	590.1	590.0	589.9
140°	607.1	607.5	607.9	608.1	608.3	608.4	608.5	608.6
142.5°	623.3	623.6	623.9	624.1	624.1	624.1	624.1	624.2
145°	646.5	646.7	646.8	647.0	647.2	647.5	647.8	648.0
147.5°	666.9	667.0	667.1	667.2	667.4	667.5	667.6	667.7
150°	679.9	679.9	679.9	680.0	680.1	680.3	680.4	680.5
152.5°	691.3	691.5	691.7	691.8	691.7	691.6	691.5	691.5
155°	706.6	707.1	707.6	707.7	707.3	706.9	706.6	706.2
157.5°	719.8	720.5	721.1	721.1	720.5	719.8	719.2	718.5
160°	728.2	729.0	729.8	729.8	729.0	728.2	727.5	726.7
162.5°	735.1	735.8	736.6	736.6	735.7	734.8	734.0	733.1
165°	744.7	745.7	746.8	746.7	745.5	744.4	743.3	742.1
167.5°	751.8	752.9	754.0	753.9	752.7	751.4	750.1	748.9
170°	756.1	757.1	758.2	758.0	756.8	755.5	754.2	753.0
172.5°	758.9	759.9	760.9	760.7	759.4	758.0	756.6	755.2
175°	762.1	763.2	764.4	764.2	762.7	761.1	759.6	758.1
177.5°	763.4	764.2	765.0	764.8	763.6	762.4	761.1	759.9
180°	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7

(END OF REPORT)