

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332885

Luminaire Tested: **S124RDIP-S350D1035U835-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332885
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIP-S350D1035U835-4F0-1E-UDD-A4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5183.3 lumens
Efficiency: N/A
Efficacy: 139.0 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 37.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332885

CATALOG NUMBER: S124RDIP-S350D1035U835-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332885

CATALOG NUMBER: S124RDIP-S350D1035U835-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	91	91	91	91	72	72	72	53	53	53	37	37	37	29				
1	93	89	86	82	83	80	77	74	63	61	59	47	46	45	33	32	31	25				
2	85	78	72	68	76	70	65	61	55	52	49	42	40	38	29	28	27	21				
3	78	69	62	56	69	62	56	51	49	45	42	37	34	32	26	24	23	18				
4	71	61	53	48	64	55	49	44	44	39	36	33	30	28	23	22	20	16				
5	65	54	47	41	58	49	42	37	39	34	31	30	27	24	21	19	18	14				
6	60	49	41	35	54	44	37	32	35	30	27	27	24	21	19	17	15	12				
7	55	44	36	31	50	40	33	28	32	27	23	24	21	19	18	15	14	11				
8	51	40	32	27	46	36	30	25	29	24	21	22	19	17	16	14	12	10				
9	48	36	29	24	43	33	27	22	26	22	19	20	17	15	15	13	11	9				
10	45	33	26	22	40	30	24	20	24	20	17	19	16	13	14	12	10	8				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4742	4742	4742	4742
5°	5501	4756	4204	4756
10°	6507	4736	3752	4736
15°	7516	4692	3224	4692
20°	8369	4631	2916	4631
25°	8639	4572	2707	4572
30°	7563	4501	2581	4501
35°	5887	4394	2505	4394
40°	4415	4272	2464	4272
45°	3486	4077	2442	4077
50°	2943	3852	2372	3852
55°	2564	3605	2245	3605
60°	2307	3347	1988	3347
65°	2034	3070	1710	3070
70°	1832	2783	1541	2783
75°	1535	2464	1313	2464
80°	1297	2101	1232	2101
85°	1093	1649	1093	1649



TEST NUMBER: P332885

CATALOG NUMBER: S124RDIP-S350D1035U835-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.9	1.1
10°-20°	171.7	3.3
20°-30°	268.5	5.2
30°-40°	298.5	5.8
40°-50°	264.9	5.1
50°-60°	206.4	4.0
60°-70°	135.1	2.6
70°-80°	66.4	1.3
80°-90°	19.2	0.4
90°-100°	367.0	7.1
100°-110°	763.9	14.7
110°-120°	684.2	13.2
120°-130°	575.5	11.1
130°-140°	479.9	9.3
140°-150°	366.6	7.1
150°-160°	257.7	5.0
160°-170°	151.6	2.9
170°-180°	49.3	1.0
0°-30°	497.1	9.6
0°-40°	795.6	15.4
0°-60°	1266.9	24.4
0°-90°	1487.6	28.7
90°-120°	1815.1	35.0
90°-150°	3237.1	62.5
90°-180°	3696.0	71.3
0°-180°	5183.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	587	587	587	587	587	
5°	679	587	519	587	679	69
15°	899	561	386	561	899	256
25°	970	513	304	513	970	430
35°	597	446	254	446	597	374
45°	305	357	214	357	305	242
55°	182	256	160	256	182	166
65°	106	161	90	161	106	107
75°	49	79	42	79	49	54
85°	12	18	12	18	12	14
90°	21	1	21	1	21	17
95°	244	33	244	33	244	378
105°	1405	117	1405	117	1405	1389
115°	1349	206	1349	206	1349	1339
125°	1076	286	1076	286	1076	978
135°	962	340	962	340	962	743
145°	786	392	786	392	786	498
155°	658	446	658	446	658	307
165°	574	486	574	486	574	165
175°	517	507	517	507	517	50
180°	508	508	508	508	508	



TEST NUMBER: P332885

CATALOG NUMBER: S124RDIP-S350D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	619.6	621.3	619.6	619.4	617.5	616.9	616.2	613.7	609.2	606.5	607.1
5°	678.8	684.7	681.4	680.9	675.7	670.5	667.2	659.6	651.5	646.1	641.6
7.5°	747.2	750.6	748.5	745.2	736.8	732.0	724.3	714.4	699.9	688.9	678.8
10°	793.8	796.6	795.7	789.5	783.4	770.8	763.7	749.8	731.5	717.1	703.6
12.5°	839.6	842.6	834.3	834.6	822.9	813.0	801.8	784.2	763.2	744.6	727.7
15°	899.3	895.5	895.5	890.8	877.8	864.1	852.5	834.0	807.5	785.3	761.8
17.5°	946.1	947.4	945.5	934.3	924.1	909.9	888.6	867.1	842.5	812.6	788.7
20°	974.1	974.1	972.0	964.4	951.2	936.0	913.1	889.6	858.4	828.3	801.4
22.5°	985.5	986.2	983.7	977.5	965.6	950.8	931.2	907.4	875.2	841.4	808.0
25°	969.9	974.4	974.8	973.2	969.6	960.6	943.8	919.5	890.6	853.9	817.9
27.5°	890.4	896.1	901.1	909.3	920.2	925.8	926.6	914.2	889.0	853.7	817.5
30°	811.3	816.0	831.4	851.5	867.1	881.3	893.7	897.0	882.8	851.1	813.0
32.5°	723.4	729.9	745.3	766.9	792.9	817.0	844.6	858.7	858.3	839.3	804.1
35°	597.3	602.1	616.3	639.0	670.2	706.0	749.8	783.8	807.0	805.4	783.8
37.5°	481.8	487.1	501.4	520.3	550.6	594.8	637.2	684.2	727.0	751.1	743.9
40°	418.9	419.1	433.1	452.5	480.9	519.5	565.6	617.7	665.5	704.6	712.1
42.5°	369.3	369.3	378.6	399.5	419.9	456.2	500.3	552.0	608.0	653.1	673.1
45°	305.3	307.4	315.0	327.5	343.6	374.4	409.7	457.7	520.4	573.9	607.3
47.5°	258.5	261.7	266.5	276.7	289.5	310.0	339.2	382.4	433.4	492.2	539.7
50°	234.3	234.8	240.9	246.6	257.7	274.1	299.6	335.6	382.5	439.0	491.8
52.5°	213.5	213.4	217.1	224.3	233.3	246.0	266.7	299.4	341.0	391.7	446.2
55°	182.2	183.4	186.3	191.9	198.8	207.8	224.1	248.7	281.4	324.7	374.2
57.5°	158.5	159.1	161.3	163.7	170.0	176.6	188.8	205.9	233.4	268.9	315.0
60°	142.9	143.2	143.9	147.4	152.4	158.6	166.9	181.3	204.5	236.9	273.4
62.5°	127.8	128.2	129.3	131.9	135.8	140.0	148.7	160.3	179.5	207.2	240.0
65°	106.5	106.7	108.4	109.3	112.4	116.2	122.6	130.4	143.7	166.9	191.7
67.5°	89.0	89.0	89.1	90.4	92.5	95.0	98.8	105.1	115.1	129.3	151.2
70°	77.6	77.6	78.1	78.8	80.0	82.1	84.3	89.0	96.3	107.9	124.7
72.5°	67.0	67.2	67.7	67.8	68.4	70.2	71.8	74.8	80.2	89.0	102.6
75°	49.2	49.9	51.1	52.1	53.3	53.0	54.7	56.6	58.2	63.4	71.2
77.5°	36.6	36.3	36.4	37.2	37.3	37.6	38.8	40.2	41.5	43.9	46.7
80°	27.9	27.9	28.6	28.9	28.6	28.9	30.1	30.8	31.2	32.2	34.8
82.5°	21.1	21.5	21.3	21.5	21.6	21.9	22.9	23.0	23.5	23.9	24.9
85°	11.8	12.1	12.3	11.8	11.8	11.8	12.3	12.5	13.0	12.8	13.3
87.5°	8.4	8.2	8.6	8.4	8.3	8.2	8.1	8.3	7.7	8.1	7.7
90°	21.0	21.0	22.0	21.0	20.0	20.0	19.0	18.0	17.0	18.0	16.0
92.5°	76.9	76.9	80.3	85.7	97.4	117.4	147.6	196.1	263.8	316.7	277.1
95°	243.6	256.6	274.5	305.5	354.4	451.2	585.0	739.7	836.6	813.6	614.0
97.5°	651.1	671.9	701.8	761.9	833.6	937.8	1035.4	1093.0	1051.0	856.9	574.6
100°	915.5	923.4	953.4	1014.3	1101.1	1175.0	1223.9	1204.0	1058.2	802.6	521.1
102.5°	1145.5	1151.9	1183.4	1227.5	1280.8	1311.6	1297.4	1198.4	998.3	734.8	485.2
105°	1404.6	1410.6	1424.6	1432.6	1430.6	1389.6	1290.8	1118.1	889.5	654.9	454.2
107.5°	1500.9	1498.3	1488.3	1465.5	1416.2	1327.2	1188.0	1004.1	801.6	610.2	448.6
110°	1502.5	1493.5	1475.5	1433.6	1362.7	1252.9	1108.1	935.4	757.7	595.0	450.2



TEST NUMBER: P332885

CATALOG NUMBER: S124RDIP-S350D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1455.3	1440.8	1415.6	1364.9	1284.4	1174.6	1037.8	885.1	733.0	587.8	455.0
115°	1348.7	1340.7	1308.8	1248.9	1170.0	1074.2	957.4	834.6	709.8	584.0	464.2
117.5°	1240.7	1234.5	1202.2	1151.9	1084.6	1003.3	911.5	809.8	699.4	583.0	474.0
120°	1180.0	1169.0	1143.1	1099.1	1042.2	971.4	891.5	798.6	693.8	583.0	481.2
122.5°	1132.1	1121.1	1099.1	1061.6	1013.5	951.4	878.7	789.1	687.4	582.2	488.4
125°	1076.2	1070.2	1051.2	1022.3	982.3	927.4	858.5	772.7	676.9	581.0	499.2
127.5°	1043.4	1037.4	1021.5	995.7	955.6	903.5	834.8	752.7	662.7	578.8	507.7
130°	1024.3	1018.3	1002.3	977.3	936.4	883.5	815.6	736.8	653.9	578.0	514.1
132.5°	1002.7	996.7	981.5	953.4	913.3	860.3	794.1	720.0	645.9	577.2	519.7
135°	962.4	956.4	940.4	912.5	872.5	822.6	761.7	696.8	633.9	576.0	528.1
137.5°	912.5	905.3	892.1	864.5	827.2	782.1	730.8	675.9	623.5	575.8	533.1
140°	876.5	868.5	854.6	832.6	797.6	755.7	710.8	663.9	618.0	575.0	537.1
142.5°	838.2	832.6	820.2	799.8	768.9	732.6	694.0	652.7	613.2	575.0	540.3
145°	785.7	780.7	770.7	753.7	728.8	700.8	670.9	636.9	605.0	573.0	542.1
147.5°	739.1	737.4	729.8	715.2	696.8	674.9	650.9	623.9	597.6	569.4	543.1
150°	712.8	711.8	705.8	692.8	676.9	658.9	638.9	616.0	592.0	567.0	543.1
152.5°	688.8	687.8	684.2	673.7	660.1	645.3	626.9	607.2	585.6	563.0	541.5
155°	657.9	657.9	654.9	646.9	636.9	624.9	610.0	594.0	576.0	557.1	539.1
157.5°	630.7	630.7	628.9	622.9	615.4	605.8	593.2	579.8	566.2	550.9	536.5
160°	614.0	614.0	613.0	607.0	601.0	593.0	582.0	571.0	559.1	546.1	534.1
162.5°	598.0	598.8	597.8	591.8	587.4	580.2	571.6	562.2	552.7	541.3	531.7
165°	574.0	575.0	576.0	572.0	568.0	563.0	556.1	550.1	542.1	534.1	527.1
167.5°	555.1	555.9	556.1	553.5	551.5	548.5	542.9	538.3	532.5	526.9	522.3
170°	543.1	543.1	544.1	543.1	541.1	538.1	534.1	531.1	526.1	522.1	519.1
172.5°	531.1	532.7	533.7	532.7	531.5	529.3	526.9	524.7	520.5	517.3	515.9
175°	517.1	519.1	521.1	519.1	519.1	519.1	517.1	516.1	514.1	512.1	512.1
177.5°	508.9	510.5	512.1	511.3	512.1	511.3	511.3	510.5	509.7	508.9	508.9
180°	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1



TEST NUMBER: P332885

CATALOG NUMBER: S124RDIP-S350D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	605.2	602.6	601.2	598.2	594.6	592.7	591.0	588.5	585.3	581.9	579.5
5°	635.9	630.2	623.1	614.6	607.1	599.7	593.3	586.9	579.6	572.0	564.5
7.5°	667.4	656.3	644.2	630.2	616.7	604.3	592.9	582.1	569.8	558.7	548.7
10°	689.4	674.3	657.5	639.7	622.0	606.6	591.4	577.7	562.6	549.1	537.7
12.5°	707.2	689.4	669.2	647.1	625.7	607.1	589.7	571.8	554.6	540.0	524.8
15°	736.7	712.4	685.2	658.6	631.0	605.6	582.2	561.4	541.7	521.1	506.7
17.5°	757.1	728.1	695.0	663.2	630.5	600.6	573.6	548.8	526.1	505.1	487.9
20°	769.2	737.2	700.5	664.3	627.6	595.7	566.6	539.1	515.7	493.0	475.2
22.5°	776.0	740.6	700.5	662.6	624.6	590.0	558.1	529.5	504.0	481.2	461.6
25°	778.2	740.3	699.4	655.8	614.2	577.5	544.3	513.3	484.9	462.2	441.4
27.5°	775.1	730.5	688.6	643.9	600.9	562.3	527.5	494.9	466.5	442.1	420.7
30°	770.6	722.8	677.8	631.4	587.9	550.7	514.0	482.8	453.2	427.9	406.4
32.5°	760.7	713.3	664.9	617.4	573.3	535.0	500.2	468.8	439.8	413.9	391.0
35°	741.2	693.2	640.7	591.9	548.6	508.8	476.2	445.9	418.2	390.5	366.4
37.5°	715.5	666.5	614.2	560.8	517.4	479.9	450.0	421.5	394.5	369.2	342.5
40°	691.3	646.6	592.6	539.6	495.1	458.9	431.2	405.4	378.2	353.1	326.4
42.5°	662.0	623.9	569.3	516.1	472.2	437.3	411.5	386.3	361.5	337.2	309.3
45°	613.0	584.1	533.0	481.9	437.6	403.0	379.4	357.1	335.4	312.2	285.9
47.5°	556.8	537.3	493.2	440.8	399.9	368.8	345.9	327.7	309.3	286.1	263.1
50°	517.8	505.3	462.7	414.9	375.8	347.2	323.8	306.7	291.3	269.1	248.5
52.5°	476.2	469.5	433.5	387.8	350.1	322.0	302.0	286.7	271.1	252.6	233.4
55°	412.7	416.3	385.8	346.2	310.7	287.1	268.9	256.1	242.8	227.2	212.3
57.5°	347.9	360.9	340.4	305.7	272.4	250.5	236.8	226.1	214.9	202.0	189.2
60°	309.1	320.0	308.4	277.8	248.7	228.4	215.6	207.3	196.2	184.4	174.7
62.5°	271.2	282.9	276.0	251.3	224.3	206.8	195.5	187.8	179.5	169.2	159.1
65°	223.7	231.2	227.9	210.9	191.7	176.8	166.4	160.7	153.1	145.6	136.6
67.5°	171.3	185.9	184.0	174.9	158.4	146.7	139.9	134.9	128.0	122.4	116.3
70°	140.8	154.3	154.1	146.7	137.7	126.9	122.1	117.9	111.7	106.3	101.3
72.5°	115.3	127.6	129.5	123.8	117.7	109.4	104.9	102.0	96.0	92.3	88.2
75°	80.7	89.7	92.1	92.1	89.2	85.0	80.9	79.0	74.8	71.5	69.1
77.5°	52.9	58.6	62.3	63.1	63.6	62.1	58.8	57.5	54.2	53.1	50.8
80°	37.4	41.2	45.4	46.9	48.0	47.6	46.2	45.2	42.1	40.9	40.0
82.5°	25.8	27.9	31.4	34.6	34.2	35.5	34.2	33.5	31.1	30.7	29.8
85°	13.5	13.7	14.2	16.3	17.5	18.0	18.2	17.8	17.0	17.0	15.4
87.5°	7.3	7.1	6.3	6.3	6.3	6.9	6.8	6.6	6.5	6.5	6.1
90°	14.0	14.0	8.0	8.0	7.0	6.0	3.0	1.0	3.0	6.0	7.0
92.5°	201.7	124.2	73.5	52.7	38.1	26.0	16.6	11.4	16.6	26.0	38.1
95°	375.4	211.6	124.8	82.9	58.9	45.9	35.9	32.9	35.9	45.9	58.9
97.5°	337.4	202.3	135.4	100.2	79.7	67.7	59.1	59.1	59.1	67.7	79.7
100°	317.5	204.7	145.8	113.8	94.8	82.9	75.9	75.9	75.9	82.9	94.8
102.5°	311.9	212.6	159.3	129.0	110.8	99.6	93.4	91.8	93.4	99.6	110.8
105°	314.5	231.6	183.7	154.7	136.8	124.8	119.8	116.8	119.8	124.8	136.8
107.5°	329.2	253.8	209.8	181.3	164.1	151.3	146.4	144.4	146.4	151.3	164.1
110°	340.4	270.5	226.6	199.7	181.7	169.7	164.7	162.7	164.7	169.7	181.7



TEST NUMBER: P332885

CATALOG NUMBER: S124RDIP-S350D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	352.4	286.5	244.2	217.2	199.3	188.1	182.3	180.3	182.3	188.1	199.3
115°	371.4	311.5	271.5	244.6	225.6	215.6	208.6	205.7	208.6	215.6	225.6
117.5°	390.7	335.6	297.7	269.7	252.0	241.0	234.8	232.0	234.8	241.0	252.0
120°	404.3	352.4	314.5	286.5	269.5	258.6	251.6	249.6	251.6	258.6	269.5
122.5°	417.1	368.4	330.4	303.3	284.7	274.5	267.5	265.6	267.5	274.5	284.7
125°	436.3	390.3	354.4	326.4	307.5	296.5	290.5	286.5	290.5	296.5	307.5
127.5°	452.8	410.7	376.0	347.8	328.0	315.5	308.3	305.1	308.3	315.5	328.0
130°	463.2	424.3	390.3	361.4	342.4	327.4	319.5	315.5	319.5	327.4	342.4
132.5°	473.6	435.5	401.5	374.2	353.6	339.4	329.0	325.8	329.0	339.4	353.6
135°	487.2	451.2	418.3	392.3	371.4	354.4	344.4	340.4	344.4	354.4	371.4
137.5°	496.8	463.2	432.5	407.7	385.9	369.8	358.8	355.0	358.8	369.8	385.9
140°	503.1	471.2	441.3	417.3	396.3	379.4	368.4	365.4	368.4	379.4	396.3
142.5°	507.9	478.4	449.2	426.1	405.9	389.7	379.6	376.6	379.6	389.7	405.9
145°	513.1	486.2	460.2	438.3	419.3	405.3	395.3	392.3	395.3	405.3	419.3
147.5°	517.7	494.2	469.8	450.0	434.3	419.9	411.1	410.1	411.1	419.9	434.3
150°	520.1	498.2	476.2	457.2	442.3	430.3	422.3	421.3	422.3	430.3	442.3
152.5°	521.7	501.4	481.8	464.4	451.0	439.9	431.9	431.7	431.9	439.9	451.0
155°	523.1	506.1	489.2	474.2	463.2	453.2	447.2	446.2	447.2	453.2	463.2
157.5°	523.1	509.5	495.2	483.4	473.8	466.0	460.4	460.4	460.4	466.0	473.8
160°	523.1	511.1	499.2	488.2	480.2	473.2	469.2	469.2	469.2	473.2	480.2
162.5°	523.1	512.7	501.6	493.0	485.8	479.6	476.4	477.2	476.4	479.6	485.8
165°	521.1	513.1	504.1	498.2	493.2	488.2	486.2	486.2	486.2	488.2	493.2
167.5°	518.7	512.9	506.3	501.8	499.0	495.2	494.2	495.2	494.2	495.2	499.0
170°	517.1	512.1	507.1	504.1	502.2	499.2	498.2	499.2	498.2	499.2	502.2
172.5°	515.5	511.3	507.9	505.7	504.5	502.3	502.2	503.1	502.2	502.3	504.5
175°	513.1	510.1	508.1	508.1	507.1	506.1	506.1	507.1	506.1	506.1	507.1
177.5°	510.5	508.9	508.1	508.1	508.1	507.3	508.1	508.9	508.1	507.3	508.1
180°	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1



TEST NUMBER: P332885

CATALOG NUMBER: S124RDIP-S350D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	576.8	574.9	572.5	569.6	566.2	563.2	561.8	563.0	563.6	562.0	561.8
5°	559.2	553.3	548.6	541.5	535.8	531.1	527.8	526.3	526.8	523.0	522.1
7.5°	539.5	532.5	524.7	516.3	508.5	501.5	497.9	495.9	491.8	490.1	487.2
10°	526.8	517.4	509.8	499.8	490.8	482.6	478.5	475.2	471.2	469.3	465.3
12.5°	513.8	502.8	494.4	484.1	474.9	465.0	461.1	455.0	448.7	444.7	439.5
15°	495.3	482.1	471.9	459.6	448.7	437.4	427.2	415.8	411.6	402.6	397.4
17.5°	473.8	460.4	447.8	431.3	414.5	400.3	389.5	378.6	372.1	366.4	363.7
20°	459.6	447.3	429.8	410.6	391.9	376.3	367.5	360.4	353.3	349.3	346.5
22.5°	446.2	430.4	410.1	389.4	370.7	358.5	351.1	343.8	338.0	334.2	330.4
25°	423.6	403.0	381.5	357.8	345.1	334.4	326.4	320.4	316.9	311.9	310.0
27.5°	400.5	375.5	351.8	335.9	322.6	312.8	305.8	301.4	296.9	293.7	291.2
30°	382.7	357.4	336.1	320.9	307.4	299.4	293.7	288.5	284.9	282.3	280.5
32.5°	365.1	339.8	321.9	305.6	294.9	287.1	281.0	277.1	274.3	271.0	269.8
35°	339.6	317.1	301.5	286.8	276.0	268.9	264.1	260.1	257.7	256.8	256.1
37.5°	315.1	296.7	279.9	267.9	258.2	252.6	247.0	245.0	243.4	241.7	242.5
40°	299.6	282.3	267.4	254.7	246.8	240.7	237.4	235.0	233.6	233.6	233.6
42.5°	286.2	269.3	254.7	243.3	235.5	230.3	226.6	224.6	224.1	223.9	225.1
45°	265.3	249.7	235.0	225.5	218.9	213.7	211.6	209.9	209.9	210.9	211.1
47.5°	244.6	230.0	218.2	207.6	201.5	198.3	196.4	195.6	195.7	196.6	197.7
50°	231.9	217.5	205.9	196.4	190.8	187.7	186.0	185.5	186.0	186.0	187.7
52.5°	218.1	205.2	193.8	185.8	179.4	176.5	175.6	174.9	175.2	176.0	176.7
55°	197.9	186.3	175.4	167.8	163.1	161.2	159.0	159.3	158.8	159.3	159.3
57.5°	177.5	167.1	157.0	151.0	146.8	144.1	141.8	142.4	141.7	141.6	141.2
60°	164.5	153.1	145.1	139.6	134.9	132.5	130.4	130.9	130.2	129.7	128.7
62.5°	150.3	140.8	133.1	127.9	124.1	121.4	119.2	118.8	117.1	115.5	113.4
65°	129.7	121.9	115.0	110.1	106.5	104.4	102.7	101.3	97.7	94.0	92.1
67.5°	109.7	104.0	97.6	93.4	90.5	87.8	84.6	82.2	78.9	76.8	75.6
70°	96.8	91.4	85.9	81.9	78.8	76.2	72.7	71.0	68.6	67.7	66.5
72.5°	84.5	79.4	74.4	70.7	67.5	65.4	62.6	61.0	59.9	59.5	58.4
75°	65.8	61.8	58.0	54.7	52.1	50.6	49.5	48.3	47.8	45.7	44.5
77.5°	48.0	45.3	43.0	40.6	38.8	37.8	35.5	34.2	33.4	32.4	32.1
80°	37.4	35.5	33.1	31.7	29.1	28.2	27.2	27.0	26.7	26.5	26.3
82.5°	28.1	26.2	23.9	23.0	22.3	21.7	21.2	20.9	20.7	20.8	20.8
85°	14.2	13.3	13.3	13.0	12.8	12.5	12.3	12.3	12.1	12.3	12.1
87.5°	6.3	6.1	7.3	7.0	7.5	7.9	7.6	7.8	8.1	8.0	8.0
90°	8.0	8.0	14.0	14.0	16.0	18.0	17.0	18.0	19.0	20.0	20.0
92.5°	52.7	73.5	124.2	201.7	277.1	316.7	263.8	196.1	147.6	117.4	97.4
95°	82.9	124.8	211.6	375.4	614.0	813.6	836.6	739.7	585.0	451.2	354.4
97.5°	100.2	135.4	202.3	337.4	574.6	856.9	1051.0	1093.0	1035.4	937.8	833.6
100°	113.8	145.8	204.7	317.5	521.1	802.6	1058.2	1204.0	1223.9	1175.0	1101.1
102.5°	129.0	159.3	212.6	311.9	485.2	734.8	998.3	1198.4	1297.4	1311.6	1280.8
105°	154.7	183.7	231.6	314.5	454.2	654.9	889.5	1118.1	1290.8	1389.6	1430.6
107.5°	181.3	209.8	253.8	329.2	448.6	610.2	801.6	1004.1	1188.0	1327.2	1416.2
110°	199.7	226.6	270.5	340.4	450.2	595.0	757.7	935.4	1108.1	1252.9	1362.7



TEST NUMBER: P332885

CATALOG NUMBER: S124RDIP-S350D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	217.2	244.2	286.5	352.4	455.0	587.8	733.0	885.1	1037.8	1174.6	1284.4
115°	244.6	271.5	311.5	371.4	464.2	584.0	709.8	834.6	957.4	1074.2	1170.0
117.5°	269.7	297.7	335.6	390.7	474.0	583.0	699.4	809.8	911.5	1003.3	1084.6
120°	286.5	314.5	352.4	404.3	481.2	583.0	693.8	798.6	891.5	971.4	1042.2
122.5°	303.3	330.4	368.4	417.1	488.4	582.2	687.4	789.1	878.7	951.4	1013.5
125°	326.4	354.4	390.3	436.3	499.2	581.0	676.9	772.7	858.5	927.4	982.3
127.5°	347.8	376.0	410.7	452.8	507.7	578.8	662.7	752.7	834.8	903.5	955.6
130°	361.4	390.3	424.3	463.2	514.1	578.0	653.9	736.8	815.6	883.5	936.4
132.5°	374.2	401.5	435.5	473.6	519.7	577.2	645.9	720.0	794.1	860.3	913.3
135°	392.3	418.3	451.2	487.2	528.1	576.0	633.9	696.8	761.7	822.6	872.5
137.5°	407.7	432.5	463.2	496.8	533.1	575.8	623.5	675.9	730.8	782.1	827.2
140°	417.3	441.3	471.2	503.1	537.1	575.0	618.0	663.9	710.8	755.7	797.6
142.5°	426.1	449.2	478.4	507.9	540.3	575.0	613.2	652.7	694.0	732.6	768.9
145°	438.3	460.2	486.2	513.1	542.1	573.0	605.0	636.9	670.9	700.8	728.8
147.5°	450.0	469.8	494.2	517.7	543.1	569.4	597.6	623.9	650.9	674.9	696.8
150°	457.2	476.2	498.2	520.1	543.1	567.0	592.0	616.0	638.9	658.9	676.9
152.5°	464.4	481.8	501.4	521.7	541.5	563.0	585.6	607.2	626.9	645.3	660.1
155°	474.2	489.2	506.1	523.1	539.1	557.1	576.0	594.0	610.0	624.9	636.9
157.5°	483.4	495.2	509.5	523.1	536.5	550.9	566.2	579.8	593.2	605.8	615.4
160°	488.2	499.2	511.1	523.1	534.1	546.1	559.1	571.0	582.0	593.0	601.0
162.5°	493.0	501.6	512.7	523.1	531.7	541.3	552.7	562.2	571.6	580.2	587.4
165°	498.2	504.1	513.1	521.1	527.1	534.1	542.1	550.1	556.1	563.0	568.0
167.5°	501.8	506.3	512.9	518.7	522.3	526.9	532.5	538.3	542.9	548.5	551.5
170°	504.1	507.1	512.1	517.1	519.1	522.1	526.1	531.1	534.1	538.1	541.1
172.5°	505.7	507.9	511.3	515.5	515.9	517.3	520.5	524.7	526.9	529.3	531.5
175°	508.1	508.1	510.1	513.1	512.1	512.1	514.1	516.1	517.1	519.1	519.1
177.5°	508.1	508.1	508.9	510.5	508.9	508.9	509.7	510.5	511.3	511.3	512.1
180°	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1



TEST NUMBER: P332885

CATALOG NUMBER: S124RDIP-S350D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	560.7	561.1	559.8	559.4	559.8	561.1	560.7	561.8	562.0	563.6	563.0
5°	520.2	519.7	518.5	518.8	518.5	519.7	520.2	522.1	523.0	526.8	526.3
7.5°	485.5	483.7	484.2	482.3	484.2	483.7	485.5	487.2	490.1	491.8	495.9
10°	464.3	461.7	459.6	457.7	459.6	461.7	464.3	465.3	469.3	471.2	475.2
12.5°	435.4	433.1	430.3	430.8	430.3	433.1	435.4	439.5	444.7	448.7	455.0
15°	394.3	390.7	385.1	385.8	385.1	390.7	394.3	397.4	402.6	411.6	415.8
17.5°	359.5	359.5	356.9	357.6	356.9	359.5	359.5	363.7	366.4	372.1	378.6
20°	341.5	339.9	340.1	339.4	340.1	339.9	341.5	346.5	349.3	353.3	360.4
22.5°	329.0	327.0	325.3	323.9	325.3	327.0	329.0	330.4	334.2	338.0	343.8
25°	307.9	306.5	304.4	303.9	304.4	306.5	307.9	310.0	311.9	316.9	320.4
27.5°	289.3	289.1	288.2	287.1	288.2	289.1	289.3	291.2	293.7	296.9	301.4
30°	278.6	278.1	277.6	276.9	277.6	278.1	278.6	280.5	282.3	284.9	288.5
32.5°	268.9	268.6	268.1	268.2	268.1	268.6	268.9	269.8	271.0	274.3	277.1
35°	255.1	254.9	254.4	254.2	254.4	254.9	255.1	256.1	256.8	257.7	260.1
37.5°	242.3	242.9	242.6	242.5	242.6	242.9	242.3	242.5	241.7	243.4	245.0
40°	233.4	233.6	234.1	233.8	234.1	233.6	233.4	233.6	233.6	233.6	235.0
42.5°	226.0	226.0	226.7	225.9	226.7	226.0	226.0	225.1	223.9	224.1	224.6
45°	212.8	214.2	213.9	213.9	213.9	214.2	212.8	211.1	210.9	209.9	209.9
47.5°	198.3	199.6	199.9	199.8	199.9	199.6	198.3	197.7	196.6	195.7	195.6
50°	188.9	188.4	189.1	188.9	189.1	188.4	188.9	187.7	186.0	186.0	185.5
52.5°	177.3	177.4	177.4	177.1	177.4	177.4	177.3	176.7	176.0	175.2	174.9
55°	159.5	159.8	159.3	159.5	159.3	159.8	159.5	159.3	159.3	158.8	159.3
57.5°	140.2	139.1	139.5	139.0	139.5	139.1	140.2	141.2	141.6	141.7	142.4
60°	126.4	124.5	124.0	123.1	124.0	124.5	126.4	128.7	129.7	130.2	130.9
62.5°	110.9	109.5	107.9	108.7	107.9	109.5	110.9	113.4	115.5	117.1	118.8
65°	90.2	89.2	88.5	89.5	88.5	89.2	90.2	92.1	94.0	97.7	101.3
67.5°	74.6	74.1	74.1	73.7	74.1	74.1	74.6	75.6	76.8	78.9	82.2
70°	66.5	65.8	65.8	65.3	65.8	65.8	66.5	66.5	67.7	68.6	71.0
72.5°	58.2	57.5	57.7	57.4	57.7	57.5	58.2	58.4	59.5	59.9	61.0
75°	43.1	41.9	41.9	42.1	41.9	41.9	43.1	44.5	45.7	47.8	48.3
77.5°	32.1	31.9	32.2	31.8	32.2	31.9	32.1	32.1	32.4	33.4	34.2
80°	26.3	26.0	25.8	26.5	25.8	26.0	26.3	26.3	26.5	26.7	27.0
82.5°	20.4	20.4	20.3	21.2	20.3	20.4	20.4	20.8	20.8	20.7	20.9
85°	12.3	11.8	12.3	11.8	12.3	11.8	12.3	12.1	12.3	12.1	12.3
87.5°	8.5	8.6	8.2	8.4	8.2	8.6	8.5	8.0	8.0	8.1	7.8
90°	21.0	22.0	21.0	21.0	21.0	22.0	21.0	20.0	20.0	19.0	18.0
92.5°	85.7	80.3	76.9	76.9	76.9	80.3	85.7	97.4	117.4	147.6	196.1
95°	305.5	274.5	256.6	243.6	256.6	274.5	305.5	354.4	451.2	585.0	739.7
97.5°	761.9	701.8	671.9	651.1	671.9	701.8	761.9	833.6	937.8	1035.4	1093.0
100°	1014.3	953.4	923.4	915.5	923.4	953.4	1014.3	1101.1	1175.0	1223.9	1204.0
102.5°	1227.5	1183.4	1151.9	1145.5	1151.9	1183.4	1227.5	1280.8	1311.6	1297.4	1198.4
105°	1432.6	1424.6	1410.6	1404.6	1410.6	1424.6	1432.6	1430.6	1389.6	1290.8	1118.1
107.5°	1465.5	1488.3	1498.3	1500.9	1498.3	1488.3	1465.5	1416.2	1327.2	1188.0	1004.1
110°	1433.6	1475.5	1493.5	1502.5	1493.5	1475.5	1433.6	1362.7	1252.9	1108.1	935.4



TEST NUMBER: P332885

CATALOG NUMBER: S124RDIP-S350D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1364.9	1415.6	1440.8	1455.3	1440.8	1415.6	1364.9	1284.4	1174.6	1037.8	885.1
115°	1248.9	1308.8	1340.7	1348.7	1340.7	1308.8	1248.9	1170.0	1074.2	957.4	834.6
117.5°	1151.9	1202.2	1234.5	1240.7	1234.5	1202.2	1151.9	1084.6	1003.3	911.5	809.8
120°	1099.1	1143.1	1169.0	1180.0	1169.0	1143.1	1099.1	1042.2	971.4	891.5	798.6
122.5°	1061.6	1099.1	1121.1	1132.1	1121.1	1099.1	1061.6	1013.5	951.4	878.7	789.1
125°	1022.3	1051.2	1070.2	1076.2	1070.2	1051.2	1022.3	982.3	927.4	858.5	772.7
127.5°	995.7	1021.5	1037.4	1043.4	1037.4	1021.5	995.7	955.6	903.5	834.8	752.7
130°	977.3	1002.3	1018.3	1024.3	1018.3	1002.3	977.3	936.4	883.5	815.6	736.8
132.5°	953.4	981.5	996.7	1002.7	996.7	981.5	953.4	913.3	860.3	794.1	720.0
135°	912.5	940.4	956.4	962.4	956.4	940.4	912.5	872.5	822.6	761.7	696.8
137.5°	864.5	892.1	905.3	912.5	905.3	892.1	864.5	827.2	782.1	730.8	675.9
140°	832.6	854.6	868.5	876.5	868.5	854.6	832.6	797.6	755.7	710.8	663.9
142.5°	799.8	820.2	832.6	838.2	832.6	820.2	799.8	768.9	732.6	694.0	652.7
145°	753.7	770.7	780.7	785.7	780.7	770.7	753.7	728.8	700.8	670.9	636.9
147.5°	715.2	729.8	737.4	739.1	737.4	729.8	715.2	696.8	674.9	650.9	623.9
150°	692.8	705.8	711.8	712.8	711.8	705.8	692.8	676.9	658.9	638.9	616.0
152.5°	673.7	684.2	687.8	688.8	687.8	684.2	673.7	660.1	645.3	626.9	607.2
155°	646.9	654.9	657.9	657.9	657.9	654.9	646.9	636.9	624.9	610.0	594.0
157.5°	622.9	628.9	630.7	630.7	630.7	628.9	622.9	615.4	605.8	593.2	579.8
160°	607.0	613.0	614.0	614.0	614.0	613.0	607.0	601.0	593.0	582.0	571.0
162.5°	591.8	597.8	598.8	598.0	598.8	597.8	591.8	587.4	580.2	571.6	562.2
165°	572.0	576.0	575.0	574.0	575.0	576.0	572.0	568.0	563.0	556.1	550.1
167.5°	553.5	556.1	555.9	555.1	555.9	556.1	553.5	551.5	548.5	542.9	538.3
170°	543.1	544.1	543.1	543.1	543.1	544.1	543.1	541.1	538.1	534.1	531.1
172.5°	532.7	533.7	532.7	531.1	532.7	533.7	532.7	531.5	529.3	526.9	524.7
175°	519.1	521.1	519.1	517.1	519.1	521.1	519.1	519.1	519.1	517.1	516.1
177.5°	511.3	512.1	510.5	508.9	510.5	512.1	511.3	512.1	511.3	511.3	510.5
180°	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1



TEST NUMBER: P332885

CATALOG NUMBER: S124RDIP-S350D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	561.8	563.2	566.2	569.6	572.5	574.9	576.8	579.5	581.9	585.3	588.5
5°	527.8	531.1	535.8	541.5	548.6	553.3	559.2	564.5	572.0	579.6	586.9
7.5°	497.9	501.5	508.5	516.3	524.7	532.5	539.5	548.7	558.7	569.8	582.1
10°	478.5	482.6	490.8	499.8	509.8	517.4	526.8	537.7	549.1	562.6	577.7
12.5°	461.1	465.0	474.9	484.1	494.4	502.8	513.8	524.8	540.0	554.6	571.8
15°	427.2	437.4	448.7	459.6	471.9	482.1	495.3	506.7	521.1	541.7	561.4
17.5°	389.5	400.3	414.5	431.3	447.8	460.4	473.8	487.9	505.1	526.1	548.8
20°	367.5	376.3	391.9	410.6	429.8	447.3	459.6	475.2	493.0	515.7	539.1
22.5°	351.1	358.5	370.7	389.4	410.1	430.4	446.2	461.6	481.2	504.0	529.5
25°	326.4	334.4	345.1	357.8	381.5	403.0	423.6	441.4	462.2	484.9	513.3
27.5°	305.8	312.8	322.6	335.9	351.8	375.5	400.5	420.7	442.1	466.5	494.9
30°	293.7	299.4	307.4	320.9	336.1	357.4	382.7	406.4	427.9	453.2	482.8
32.5°	281.0	287.1	294.9	305.6	321.9	339.8	365.1	391.0	413.9	439.8	468.8
35°	264.1	268.9	276.0	286.8	301.5	317.1	339.6	366.4	390.5	418.2	445.9
37.5°	247.0	252.6	258.2	267.9	279.9	296.7	315.1	342.5	369.2	394.5	421.5
40°	237.4	240.7	246.8	254.7	267.4	282.3	299.6	326.4	353.1	378.2	405.4
42.5°	226.6	230.3	235.5	243.3	254.7	269.3	286.2	309.3	337.2	361.5	386.3
45°	211.6	213.7	218.9	225.5	235.0	249.7	265.3	285.9	312.2	335.4	357.1
47.5°	196.4	198.3	201.5	207.6	218.2	230.0	244.6	263.1	286.1	309.3	327.7
50°	186.0	187.7	190.8	196.4	205.9	217.5	231.9	248.5	269.1	291.3	306.7
52.5°	175.6	176.5	179.4	185.8	193.8	205.2	218.1	233.4	252.6	271.1	286.7
55°	159.0	161.2	163.1	167.8	175.4	186.3	197.9	212.3	227.2	242.8	256.1
57.5°	141.8	144.1	146.8	151.0	157.0	167.1	177.5	189.2	202.0	214.9	226.1
60°	130.4	132.5	134.9	139.6	145.1	153.1	164.5	174.7	184.4	196.2	207.3
62.5°	119.2	121.4	124.1	127.9	133.1	140.8	150.3	159.1	169.2	179.5	187.8
65°	102.7	104.4	106.5	110.1	115.0	121.9	129.7	136.6	145.6	153.1	160.7
67.5°	84.6	87.8	90.5	93.4	97.6	104.0	109.7	116.3	122.4	128.0	134.9
70°	72.7	76.2	78.8	81.9	85.9	91.4	96.8	101.3	106.3	111.7	117.9
72.5°	62.6	65.4	67.5	70.7	74.4	79.4	84.5	88.2	92.3	96.0	102.0
75°	49.5	50.6	52.1	54.7	58.0	61.8	65.8	69.1	71.5	74.8	79.0
77.5°	35.5	37.8	38.8	40.6	43.0	45.3	48.0	50.8	53.1	54.2	57.5
80°	27.2	28.2	29.1	31.7	33.1	35.5	37.4	40.0	40.9	42.1	45.2
82.5°	21.2	21.7	22.3	23.0	23.9	26.2	28.1	29.8	30.7	31.1	33.5
85°	12.3	12.5	12.8	13.0	13.3	13.3	14.2	15.4	17.0	17.0	17.8
87.5°	7.6	7.9	7.5	7.0	7.3	6.1	6.3	6.1	6.5	6.5	6.6
90°	17.0	18.0	16.0	14.0	14.0	8.0	8.0	7.0	6.0	3.0	1.0
92.5°	263.8	316.7	277.1	201.7	124.2	73.5	52.7	38.1	26.0	16.6	11.4
95°	836.6	813.6	614.0	375.4	211.6	124.8	82.9	58.9	45.9	35.9	32.9
97.5°	1051.0	856.9	574.6	337.4	202.3	135.4	100.2	79.7	67.7	59.1	59.1
100°	1058.2	802.6	521.1	317.5	204.7	145.8	113.8	94.8	82.9	75.9	75.9
102.5°	998.3	734.8	485.2	311.9	212.6	159.3	129.0	110.8	99.6	93.4	91.8
105°	889.5	654.9	454.2	314.5	231.6	183.7	154.7	136.8	124.8	119.8	116.8
107.5°	801.6	610.2	448.6	329.2	253.8	209.8	181.3	164.1	151.3	146.4	144.4
110°	757.7	595.0	450.2	340.4	270.5	226.6	199.7	181.7	169.7	164.7	162.7



TEST NUMBER: P332885

CATALOG NUMBER: S124RDIP-S350D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	733.0	587.8	455.0	352.4	286.5	244.2	217.2	199.3	188.1	182.3	180.3
115°	709.8	584.0	464.2	371.4	311.5	271.5	244.6	225.6	215.6	208.6	205.7
117.5°	699.4	583.0	474.0	390.7	335.6	297.7	269.7	252.0	241.0	234.8	232.0
120°	693.8	583.0	481.2	404.3	352.4	314.5	286.5	269.5	258.6	251.6	249.6
122.5°	687.4	582.2	488.4	417.1	368.4	330.4	303.3	284.7	274.5	267.5	265.6
125°	676.9	581.0	499.2	436.3	390.3	354.4	326.4	307.5	296.5	290.5	286.5
127.5°	662.7	578.8	507.7	452.8	410.7	376.0	347.8	328.0	315.5	308.3	305.1
130°	653.9	578.0	514.1	463.2	424.3	390.3	361.4	342.4	327.4	319.5	315.5
132.5°	645.9	577.2	519.7	473.6	435.5	401.5	374.2	353.6	339.4	329.0	325.8
135°	633.9	576.0	528.1	487.2	451.2	418.3	392.3	371.4	354.4	344.4	340.4
137.5°	623.5	575.8	533.1	496.8	463.2	432.5	407.7	385.9	369.8	358.8	355.0
140°	618.0	575.0	537.1	503.1	471.2	441.3	417.3	396.3	379.4	368.4	365.4
142.5°	613.2	575.0	540.3	507.9	478.4	449.2	426.1	405.9	389.7	379.6	376.6
145°	605.0	573.0	542.1	513.1	486.2	460.2	438.3	419.3	405.3	395.3	392.3
147.5°	597.6	569.4	543.1	517.7	494.2	469.8	450.0	434.3	419.9	411.1	410.1
150°	592.0	567.0	543.1	520.1	498.2	476.2	457.2	442.3	430.3	422.3	421.3
152.5°	585.6	563.0	541.5	521.7	501.4	481.8	464.4	451.0	439.9	431.9	431.7
155°	576.0	557.1	539.1	523.1	506.1	489.2	474.2	463.2	453.2	447.2	446.2
157.5°	566.2	550.9	536.5	523.1	509.5	495.2	483.4	473.8	466.0	460.4	460.4
160°	559.1	546.1	534.1	523.1	511.1	499.2	488.2	480.2	473.2	469.2	469.2
162.5°	552.7	541.3	531.7	523.1	512.7	501.6	493.0	485.8	479.6	476.4	477.2
165°	542.1	534.1	527.1	521.1	513.1	504.1	498.2	493.2	488.2	486.2	486.2
167.5°	532.5	526.9	522.3	518.7	512.9	506.3	501.8	499.0	495.2	494.2	495.2
170°	526.1	522.1	519.1	517.1	512.1	507.1	504.1	502.2	499.2	498.2	499.2
172.5°	520.5	517.3	515.9	515.5	511.3	507.9	505.7	504.5	502.3	502.2	503.1
175°	514.1	512.1	512.1	513.1	510.1	508.1	508.1	507.1	506.1	506.1	507.1
177.5°	509.7	508.9	508.9	510.5	508.9	508.1	508.1	508.1	507.3	508.1	508.9
180°	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1



TEST NUMBER: P332885

CATALOG NUMBER: S124RDIP-S350D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	591.0	592.7	594.6	598.2	601.2	602.6	605.2	607.1	606.5	609.2	613.7
5°	593.3	599.7	607.1	614.6	623.1	630.2	635.9	641.6	646.1	651.5	659.6
7.5°	592.9	604.3	616.7	630.2	644.2	656.3	667.4	678.8	688.9	699.9	714.4
10°	591.4	606.6	622.0	639.7	657.5	674.3	689.4	703.6	717.1	731.5	749.8
12.5°	589.7	607.1	625.7	647.1	669.2	689.4	707.2	727.7	744.6	763.2	784.2
15°	582.2	605.6	631.0	658.6	685.2	712.4	736.7	761.8	785.3	807.5	834.0
17.5°	573.6	600.6	630.5	663.2	695.0	728.1	757.1	788.7	812.6	842.5	867.1
20°	566.6	595.7	627.6	664.3	700.5	737.2	769.2	801.4	828.3	858.4	889.6
22.5°	558.1	590.0	624.6	662.6	700.5	740.6	776.0	808.0	841.4	875.2	907.4
25°	544.3	577.5	614.2	655.8	699.4	740.3	778.2	817.9	853.9	890.6	919.5
27.5°	527.5	562.3	600.9	643.9	688.6	730.5	775.1	817.5	853.7	889.0	914.2
30°	514.0	550.7	587.9	631.4	677.8	722.8	770.6	813.0	851.1	882.8	897.0
32.5°	500.2	535.0	573.3	617.4	664.9	713.3	760.7	804.1	839.3	858.3	858.7
35°	476.2	508.8	548.6	591.9	640.7	693.2	741.2	783.8	805.4	807.0	783.8
37.5°	450.0	479.9	517.4	560.8	614.2	666.5	715.5	743.9	751.1	727.0	684.2
40°	431.2	458.9	495.1	539.6	592.6	646.6	691.3	712.1	704.6	665.5	617.7
42.5°	411.5	437.3	472.2	516.1	569.3	623.9	662.0	673.1	653.1	608.0	552.0
45°	379.4	403.0	437.6	481.9	533.0	584.1	613.0	607.3	573.9	520.4	457.7
47.5°	345.9	368.8	399.9	440.8	493.2	537.3	556.8	539.7	492.2	433.4	382.4
50°	323.8	347.2	375.8	414.9	462.7	505.3	517.8	491.8	439.0	382.5	335.6
52.5°	302.0	322.0	350.1	387.8	433.5	469.5	476.2	446.2	391.7	341.0	299.4
55°	268.9	287.1	310.7	346.2	385.8	416.3	412.7	374.2	324.7	281.4	248.7
57.5°	236.8	250.5	272.4	305.7	340.4	360.9	347.9	315.0	268.9	233.4	205.9
60°	215.6	228.4	248.7	277.8	308.4	320.0	309.1	273.4	236.9	204.5	181.3
62.5°	195.5	206.8	224.3	251.3	276.0	282.9	271.2	240.0	207.2	179.5	160.3
65°	166.4	176.8	191.7	210.9	227.9	231.2	223.7	191.7	166.9	143.7	130.4
67.5°	139.9	146.7	158.4	174.9	184.0	185.9	171.3	151.2	129.3	115.1	105.1
70°	122.1	126.9	137.7	146.7	154.1	154.3	140.8	124.7	107.9	96.3	89.0
72.5°	104.9	109.4	117.7	123.8	129.5	127.6	115.3	102.6	89.0	80.2	74.8
75°	80.9	85.0	89.2	92.1	92.1	89.7	80.7	71.2	63.4	58.2	56.6
77.5°	58.8	62.1	63.6	63.1	62.3	58.6	52.9	46.7	43.9	41.5	40.2
80°	46.2	47.6	48.0	46.9	45.4	41.2	37.4	34.8	32.2	31.2	30.8
82.5°	34.2	35.5	34.2	34.6	31.4	27.9	25.8	24.9	23.9	23.5	23.0
85°	18.2	18.0	17.5	16.3	14.2	13.7	13.5	13.3	12.8	13.0	12.5
87.5°	6.8	6.9	6.3	6.3	6.3	7.1	7.3	7.7	8.1	7.7	8.3
90°	3.0	6.0	7.0	8.0	8.0	14.0	14.0	16.0	18.0	17.0	18.0
92.5°	16.6	26.0	38.1	52.7	73.5	124.2	201.7	277.1	316.7	263.8	196.1
95°	35.9	45.9	58.9	82.9	124.8	211.6	375.4	614.0	813.6	836.6	739.7
97.5°	59.1	67.7	79.7	100.2	135.4	202.3	337.4	574.6	856.9	1051.0	1093.0
100°	75.9	82.9	94.8	113.8	145.8	204.7	317.5	521.1	802.6	1058.2	1204.0
102.5°	93.4	99.6	110.8	129.0	159.3	212.6	311.9	485.2	734.8	998.3	1198.4
105°	119.8	124.8	136.8	154.7	183.7	231.6	314.5	454.2	654.9	889.5	1118.1
107.5°	146.4	151.3	164.1	181.3	209.8	253.8	329.2	448.6	610.2	801.6	1004.1
110°	164.7	169.7	181.7	199.7	226.6	270.5	340.4	450.2	595.0	757.7	935.4



TEST NUMBER: P332885

CATALOG NUMBER: S124RDIP-S350D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	182.3	188.1	199.3	217.2	244.2	286.5	352.4	455.0	587.8	733.0	885.1
115°	208.6	215.6	225.6	244.6	271.5	311.5	371.4	464.2	584.0	709.8	834.6
117.5°	234.8	241.0	252.0	269.7	297.7	335.6	390.7	474.0	583.0	699.4	809.8
120°	251.6	258.6	269.5	286.5	314.5	352.4	404.3	481.2	583.0	693.8	798.6
122.5°	267.5	274.5	284.7	303.3	330.4	368.4	417.1	488.4	582.2	687.4	789.1
125°	290.5	296.5	307.5	326.4	354.4	390.3	436.3	499.2	581.0	676.9	772.7
127.5°	308.3	315.5	328.0	347.8	376.0	410.7	452.8	507.7	578.8	662.7	752.7
130°	319.5	327.4	342.4	361.4	390.3	424.3	463.2	514.1	578.0	653.9	736.8
132.5°	329.0	339.4	353.6	374.2	401.5	435.5	473.6	519.7	577.2	645.9	720.0
135°	344.4	354.4	371.4	392.3	418.3	451.2	487.2	528.1	576.0	633.9	696.8
137.5°	358.8	369.8	385.9	407.7	432.5	463.2	496.8	533.1	575.8	623.5	675.9
140°	368.4	379.4	396.3	417.3	441.3	471.2	503.1	537.1	575.0	618.0	663.9
142.5°	379.6	389.7	405.9	426.1	449.2	478.4	507.9	540.3	575.0	613.2	652.7
145°	395.3	405.3	419.3	438.3	460.2	486.2	513.1	542.1	573.0	605.0	636.9
147.5°	411.1	419.9	434.3	450.0	469.8	494.2	517.7	543.1	569.4	597.6	623.9
150°	422.3	430.3	442.3	457.2	476.2	498.2	520.1	543.1	567.0	592.0	616.0
152.5°	431.9	439.9	451.0	464.4	481.8	501.4	521.7	541.5	563.0	585.6	607.2
155°	447.2	453.2	463.2	474.2	489.2	506.1	523.1	539.1	557.1	576.0	594.0
157.5°	460.4	466.0	473.8	483.4	495.2	509.5	523.1	536.5	550.9	566.2	579.8
160°	469.2	473.2	480.2	488.2	499.2	511.1	523.1	534.1	546.1	559.1	571.0
162.5°	476.4	479.6	485.8	493.0	501.6	512.7	523.1	531.7	541.3	552.7	562.2
165°	486.2	488.2	493.2	498.2	504.1	513.1	521.1	527.1	534.1	542.1	550.1
167.5°	494.2	495.2	499.0	501.8	506.3	512.9	518.7	522.3	526.9	532.5	538.3
170°	498.2	499.2	502.2	504.1	507.1	512.1	517.1	519.1	522.1	526.1	531.1
172.5°	502.2	502.3	504.5	505.7	507.9	511.3	515.5	515.9	517.3	520.5	524.7
175°	506.1	506.1	507.1	508.1	508.1	510.1	513.1	512.1	512.1	514.1	516.1
177.5°	508.1	507.3	508.1	508.1	508.1	508.9	510.5	508.9	508.9	509.7	510.5
180°	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1



TEST NUMBER: P332885

CATALOG NUMBER: S124RDIP-S350D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	616.2	616.9	617.5	619.4	619.6	621.3	619.6
5°	667.2	670.5	675.7	680.9	681.4	684.7	678.8
7.5°	724.3	732.0	736.8	745.2	748.5	750.6	747.2
10°	763.7	770.8	783.4	789.5	795.7	796.6	793.8
12.5°	801.8	813.0	822.9	834.6	834.3	842.6	839.6
15°	852.5	864.1	877.8	890.8	895.5	895.5	899.3
17.5°	888.6	909.9	924.1	934.3	945.5	947.4	946.1
20°	913.1	936.0	951.2	964.4	972.0	974.1	974.1
22.5°	931.2	950.8	965.6	977.5	983.7	986.2	985.5
25°	943.8	960.6	969.6	973.2	974.8	974.4	969.9
27.5°	926.6	925.8	920.2	909.3	901.1	896.1	890.4
30°	893.7	881.3	867.1	851.5	831.4	816.0	811.3
32.5°	844.6	817.0	792.9	766.9	745.3	729.9	723.4
35°	749.8	706.0	670.2	639.0	616.3	602.1	597.3
37.5°	637.2	594.8	550.6	520.3	501.4	487.1	481.8
40°	565.6	519.5	480.9	452.5	433.1	419.1	418.9
42.5°	500.3	456.2	419.9	399.5	378.6	369.3	369.3
45°	409.7	374.4	343.6	327.5	315.0	307.4	305.3
47.5°	339.2	310.0	289.5	276.7	266.5	261.7	258.5
50°	299.6	274.1	257.7	246.6	240.9	234.8	234.3
52.5°	266.7	246.0	233.3	224.3	217.1	213.4	213.5
55°	224.1	207.8	198.8	191.9	186.3	183.4	182.2
57.5°	188.8	176.6	170.0	163.7	161.3	159.1	158.5
60°	166.9	158.6	152.4	147.4	143.9	143.2	142.9
62.5°	148.7	140.0	135.8	131.9	129.3	128.2	127.8
65°	122.6	116.2	112.4	109.3	108.4	106.7	106.5
67.5°	98.8	95.0	92.5	90.4	89.1	89.0	89.0
70°	84.3	82.1	80.0	78.8	78.1	77.6	77.6
72.5°	71.8	70.2	68.4	67.8	67.7	67.2	67.0
75°	54.7	53.0	53.3	52.1	51.1	49.9	49.2
77.5°	38.8	37.6	37.3	37.2	36.4	36.3	36.6
80°	30.1	28.9	28.6	28.9	28.6	27.9	27.9
82.5°	22.9	21.9	21.6	21.5	21.3	21.5	21.1
85°	12.3	11.8	11.8	11.8	12.3	12.1	11.8
87.5°	8.1	8.2	8.3	8.4	8.6	8.2	8.4
90°	19.0	20.0	20.0	21.0	22.0	21.0	21.0
92.5°	147.6	117.4	97.4	85.7	80.3	76.9	76.9
95°	585.0	451.2	354.4	305.5	274.5	256.6	243.6
97.5°	1035.4	937.8	833.6	761.9	701.8	671.9	651.1
100°	1223.9	1175.0	1101.1	1014.3	953.4	923.4	915.5
102.5°	1297.4	1311.6	1280.8	1227.5	1183.4	1151.9	1145.5
105°	1290.8	1389.6	1430.6	1432.6	1424.6	1410.6	1404.6
107.5°	1188.0	1327.2	1416.2	1465.5	1488.3	1498.3	1500.9
110°	1108.1	1252.9	1362.7	1433.6	1475.5	1493.5	1502.5



TEST NUMBER: P332885

CATALOG NUMBER: S124RDIP-S350D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1037.8	1174.6	1284.4	1364.9	1415.6	1440.8	1455.3
115°	957.4	1074.2	1170.0	1248.9	1308.8	1340.7	1348.7
117.5°	911.5	1003.3	1084.6	1151.9	1202.2	1234.5	1240.7
120°	891.5	971.4	1042.2	1099.1	1143.1	1169.0	1180.0
122.5°	878.7	951.4	1013.5	1061.6	1099.1	1121.1	1132.1
125°	858.5	927.4	982.3	1022.3	1051.2	1070.2	1076.2
127.5°	834.8	903.5	955.6	995.7	1021.5	1037.4	1043.4
130°	815.6	883.5	936.4	977.3	1002.3	1018.3	1024.3
132.5°	794.1	860.3	913.3	953.4	981.5	996.7	1002.7
135°	761.7	822.6	872.5	912.5	940.4	956.4	962.4
137.5°	730.8	782.1	827.2	864.5	892.1	905.3	912.5
140°	710.8	755.7	797.6	832.6	854.6	868.5	876.5
142.5°	694.0	732.6	768.9	799.8	820.2	832.6	838.2
145°	670.9	700.8	728.8	753.7	770.7	780.7	785.7
147.5°	650.9	674.9	696.8	715.2	729.8	737.4	739.1
150°	638.9	658.9	676.9	692.8	705.8	711.8	712.8
152.5°	626.9	645.3	660.1	673.7	684.2	687.8	688.8
155°	610.0	624.9	636.9	646.9	654.9	657.9	657.9
157.5°	593.2	605.8	615.4	622.9	628.9	630.7	630.7
160°	582.0	593.0	601.0	607.0	613.0	614.0	614.0
162.5°	571.6	580.2	587.4	591.8	597.8	598.8	598.0
165°	556.1	563.0	568.0	572.0	576.0	575.0	574.0
167.5°	542.9	548.5	551.5	553.5	556.1	555.9	555.1
170°	534.1	538.1	541.1	543.1	544.1	543.1	543.1
172.5°	526.9	529.3	531.5	532.7	533.7	532.7	531.1
175°	517.1	519.1	519.1	519.1	521.1	519.1	517.1
177.5°	511.3	511.3	512.1	511.3	512.1	510.5	508.9
180°	508.1	508.1	508.1	508.1	508.1	508.1	508.1

(END OF REPORT)