

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332866

Luminaire Tested: **S124RDIP-S350D365U835-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332866  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIP-S350D365U835-4F0-1E-UDD-A1  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 350 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2753.8 lumens  
Efficiency: N/A  
Efficacy: 135.7 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 20.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332866

CATALOG NUMBER: S124RDIP-S350D365U835-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P332866

CATALOG NUMBER: S124RDIP-S350D365U835-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60	54
1	99	95	91	88	92	88	85	82	76	73	71	64	63	61	54	53	51	46
2	91	84	78	73	84	78	73	68	67	63	60	57	54	52	48	46	44	40
3	83	74	67	61	77	69	63	58	59	55	51	51	47	44	43	40	38	34
4	76	66	58	52	70	61	55	49	53	48	44	46	42	38	38	36	33	30
5	70	59	51	45	65	55	48	43	48	42	38	41	37	34	35	32	29	26
6	65	53	45	39	60	50	42	37	43	38	33	37	33	30	32	28	26	23
7	60	48	40	35	56	45	38	33	39	34	30	34	30	26	29	26	23	21
8	56	44	36	31	52	41	34	29	36	30	26	31	27	24	27	23	21	19
9	52	40	32	27	48	37	31	26	33	28	24	29	24	21	25	21	19	17
10	49	37	29	25	45	34	28	24	30	25	21	27	22	19	23	20	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	4742	4742	4742	4742
5°	5501	4756	4204	4756
10°	6507	4736	3752	4736
15°	7516	4692	3224	4692
20°	8369	4631	2916	4631
25°	8639	4572	2707	4572
30°	7563	4501	2581	4501
35°	5887	4394	2505	4394
40°	4415	4272	2464	4272
45°	3486	4077	2442	4077
50°	2943	3852	2372	3852
55°	2564	3605	2245	3605
60°	2307	3347	1988	3347
65°	2034	3070	1710	3070
70°	1832	2783	1541	2783
75°	1535	2464	1313	2464
80°	1297	2101	1232	2101
85°	1093	1649	1093	1649



TEST NUMBER: P332866

CATALOG NUMBER: S124RDIP-S350D365U835-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	56.9	2.1
10°-20°	171.7	6.2
20°-30°	268.5	9.8
30°-40°	298.5	10.8
40°-50°	264.9	9.6
50°-60°	206.4	7.5
60°-70°	135.1	4.9
70°-80°	66.4	2.4
80°-90°	17.8	0.6
90°-100°	30.1	1.1
100°-110°	89.3	3.2
110°-120°	151.5	5.5
120°-130°	199.8	7.3
130°-140°	224.4	8.1
140°-150°	220.5	8.0
150°-160°	185.4	6.7
160°-170°	123.4	4.5
170°-180°	43.2	1.6
0°-30°	497.1	18.1
0°-40°	795.6	28.9
0°-60°	1266.9	46.0
0°-90°	1486.2	54.0
90°-120°	270.9	9.8
90°-150°	915.6	33.2
90°-180°	1268.0	46.0
0°-180°	2753.8	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	587	587	587	587	587	
5°	679	587	519	587	679	69
15°	899	561	386	561	899	256
25°	970	513	304	513	970	430
35°	597	446	254	446	597	374
45°	305	357	214	357	305	242
55°	182	256	160	256	182	166
65°	106	161	90	161	106	107
75°	49	79	42	79	49	54
85°	12	18	12	18	12	14
90°	11	1	11	1	11	6
95°	28	21	28	21	28	29
105°	86	82	86	82	86	91
115°	153	154	153	154	153	151
125°	223	224	223	224	223	199
135°	290	289	290	289	290	224
145°	352	352	352	352	352	220
155°	402	403	402	403	402	185
165°	438	438	438	438	438	123
175°	454	456	454	456	454	43
180°	457	457	457	457	457	



TEST NUMBER: P332866

CATALOG NUMBER: S124RDIP-S350D365U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	619.6	621.3	619.6	619.4	617.5	616.9	616.2	613.7	609.2	606.5	607.1
5°	678.8	684.7	681.4	680.9	675.7	670.5	667.2	659.6	651.5	646.1	641.6
7.5°	747.2	750.6	748.5	745.2	736.8	732.0	724.3	714.4	699.9	688.9	678.8
10°	793.8	796.6	795.7	789.5	783.4	770.8	763.7	749.8	731.5	717.1	703.6
12.5°	839.6	842.6	834.3	834.6	822.9	813.0	801.8	784.2	763.2	744.6	727.7
15°	899.3	895.5	895.5	890.8	877.8	864.1	852.5	834.0	807.5	785.3	761.8
17.5°	946.1	947.4	945.5	934.3	924.1	909.9	888.6	867.1	842.5	812.6	788.7
20°	974.1	974.1	972.0	964.4	951.2	936.0	913.1	889.6	858.4	828.3	801.4
22.5°	985.5	986.2	983.7	977.5	965.6	950.8	931.2	907.4	875.2	841.4	808.0
25°	969.9	974.4	974.8	973.2	969.6	960.6	943.8	919.5	890.6	853.9	817.9
27.5°	890.4	896.1	901.1	909.3	920.2	925.8	926.6	914.2	889.0	853.7	817.5
30°	811.3	816.0	831.4	851.5	867.1	881.3	893.7	897.0	882.8	851.1	813.0
32.5°	723.4	729.9	745.3	766.9	792.9	817.0	844.6	858.7	858.3	839.3	804.1
35°	597.3	602.1	616.3	639.0	670.2	706.0	749.8	783.8	807.0	805.4	783.8
37.5°	481.8	487.1	501.4	520.3	550.6	594.8	637.2	684.2	727.0	751.1	743.9
40°	418.9	419.1	433.1	452.5	480.9	519.5	565.6	617.7	665.5	704.6	712.1
42.5°	369.3	369.3	378.6	399.5	419.9	456.2	500.3	552.0	608.0	653.1	673.1
45°	305.3	307.4	315.0	327.5	343.6	374.4	409.7	457.7	520.4	573.9	607.3
47.5°	258.5	261.7	266.5	276.7	289.5	310.0	339.2	382.4	433.4	492.2	539.7
50°	234.3	234.8	240.9	246.6	257.7	274.1	299.6	335.6	382.5	439.0	491.8
52.5°	213.5	213.4	217.1	224.3	233.3	246.0	266.7	299.4	341.0	391.7	446.2
55°	182.2	183.4	186.3	191.9	198.8	207.8	224.1	248.7	281.4	324.7	374.2
57.5°	158.5	159.1	161.3	163.7	170.0	176.6	188.8	205.9	233.4	268.9	315.0
60°	142.9	143.2	143.9	147.4	152.4	158.6	166.9	181.3	204.5	236.9	273.4
62.5°	127.8	128.2	129.3	131.9	135.8	140.0	148.7	160.3	179.5	207.2	240.0
65°	106.5	106.7	108.4	109.3	112.4	116.2	122.6	130.4	143.7	166.9	191.7
67.5°	89.0	89.0	89.1	90.4	92.5	95.0	98.8	105.1	115.1	129.3	151.2
70°	77.6	77.6	78.1	78.8	80.0	82.1	84.3	89.0	96.3	107.9	124.7
72.5°	67.0	67.2	67.7	67.8	68.4	70.2	71.8	74.8	80.2	89.0	102.6
75°	49.2	49.9	51.1	52.1	53.3	53.0	54.7	56.6	58.2	63.4	71.2
77.5°	36.6	36.3	36.4	37.2	37.3	37.6	38.8	40.2	41.5	43.9	46.7
80°	27.9	27.9	28.6	28.9	28.6	28.9	30.1	30.8	31.2	32.2	34.8
82.5°	21.1	21.5	21.3	21.5	21.6	21.9	22.9	23.0	23.5	23.9	24.9
85°	11.8	12.1	12.3	11.8	11.8	11.8	12.3	12.5	13.0	12.8	13.3
87.5°	6.3	6.1	6.2	6.2	6.3	6.1	6.2	6.5	6.0	6.1	6.0
90°	10.6	10.4	10.3	10.1	10.0	9.7	9.2	8.7	8.2	7.8	7.1
92.5°	15.7	15.6	15.5	15.4	15.3	15.1	14.8	14.6	14.3	14.0	13.6
95°	27.9	27.9	27.9	27.9	27.9	27.8	27.6	27.3	27.1	26.9	26.3
97.5°	43.7	43.7	43.7	43.7	43.7	43.6	43.3	43.0	42.8	42.5	41.8
100°	54.8	54.8	54.8	54.8	54.8	54.7	54.5	54.4	54.2	54.1	53.4
102.5°	67.2	67.1	67.1	67.0	67.0	66.8	66.6	66.4	66.2	65.9	65.3
105°	86.2	86.0	85.8	85.5	85.3	85.0	84.8	84.6	84.3	84.1	83.8
107.5°	104.7	104.8	104.8	104.8	104.8	104.7	104.5	104.3	104.0	103.8	103.8
110°	118.0	117.8	117.6	117.3	117.1	117.0	117.2	117.4	117.5	117.7	117.7



TEST NUMBER: P332866

CATALOG NUMBER: S124RDIP-S350D365U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	131.6	131.5	131.5	131.5	131.4	131.4	131.4	131.5	131.5	131.5	131.7
115°	152.7	152.7	152.8	152.9	153.0	153.0	153.1	153.2	153.3	153.4	153.5
117.5°	172.7	172.9	173.0	173.2	173.4	173.6	173.8	174.1	174.4	174.6	174.7
120°	188.0	187.8	187.7	187.5	187.4	187.5	187.9	188.3	188.7	189.1	189.3
122.5°	200.7	201.0	201.3	201.6	201.8	202.1	202.4	202.7	202.9	203.2	203.3
125°	222.6	222.8	222.9	223.1	223.2	223.4	223.6	223.7	223.9	224.0	224.1
127.5°	242.9	243.0	243.2	243.3	243.4	243.5	243.7	243.9	244.0	244.2	244.3
130°	256.2	256.5	256.8	257.1	257.4	257.7	257.8	258.0	258.2	258.3	258.3
132.5°	270.3	270.5	270.6	270.7	270.8	271.0	271.1	271.3	271.4	271.6	271.7
135°	289.8	290.0	290.2	290.5	290.7	290.9	291.1	291.2	291.4	291.5	291.5
137.5°	310.2	310.1	310.1	310.0	310.0	310.1	310.3	310.5	310.7	310.9	310.8
140°	322.6	322.7	322.8	322.9	322.9	323.0	323.1	323.2	323.3	323.3	323.3
142.5°	335.1	335.1	335.1	335.1	335.1	335.1	335.2	335.2	335.2	335.2	335.3
145°	352.0	352.2	352.4	352.7	352.9	353.1	353.1	353.2	353.3	353.4	353.3
147.5°	369.1	369.1	369.2	369.3	369.4	369.4	369.5	369.6	369.6	369.7	369.8
150°	379.5	379.6	379.7	379.8	379.8	379.9	379.9	379.9	379.9	379.9	379.9
152.5°	389.1	389.3	389.5	389.7	389.9	390.0	389.8	389.6	389.4	389.2	389.1
155°	402.5	402.8	403.1	403.4	403.7	403.7	403.4	403.1	402.8	402.5	402.6
157.5°	414.4	414.7	415.0	415.2	415.5	415.5	415.3	415.0	414.8	414.6	414.6
160°	421.2	421.6	422.0	422.4	422.8	422.9	422.6	422.4	422.2	421.9	422.0
162.5°	428.3	428.7	429.1	429.5	429.8	429.8	429.4	429.0	428.6	428.1	428.2
165°	437.5	437.8	438.1	438.4	438.7	438.6	438.2	437.7	437.2	436.8	436.9
167.5°	444.0	444.5	445.0	445.5	446.0	446.0	445.5	445.1	444.6	444.1	444.1
170°	447.7	448.3	448.8	449.4	449.9	450.0	449.5	449.0	448.5	448.1	448.0
172.5°	450.8	451.4	451.9	452.5	453.0	453.0	452.5	452.0	451.4	450.9	450.9
175°	454.1	454.6	455.2	455.7	456.3	456.3	455.7	455.2	454.6	454.1	454.2
177.5°	455.8	456.3	456.8	457.3	457.8	457.8	457.4	456.9	456.5	456.1	456.1
180°	456.9	456.9	456.9	456.9	456.9	456.9	456.9	456.9	456.9	456.9	456.9



TEST NUMBER: P332866

CATALOG NUMBER: S124RDIP-S350D365U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	605.2	602.6	601.2	598.2	594.6	592.7	591.0	588.5	585.3	581.9	579.5
5°	635.9	630.2	623.1	614.6	607.1	599.7	593.3	586.9	579.6	572.0	564.5
7.5°	667.4	656.3	644.2	630.2	616.7	604.3	592.9	582.1	569.8	558.7	548.7
10°	689.4	674.3	657.5	639.7	622.0	606.6	591.4	577.7	562.6	549.1	537.7
12.5°	707.2	689.4	669.2	647.1	625.7	607.1	589.7	571.8	554.6	540.0	524.8
15°	736.7	712.4	685.2	658.6	631.0	605.6	582.2	561.4	541.7	521.1	506.7
17.5°	757.1	728.1	695.0	663.2	630.5	600.6	573.6	548.8	526.1	505.1	487.9
20°	769.2	737.2	700.5	664.3	627.6	595.7	566.6	539.1	515.7	493.0	475.2
22.5°	776.0	740.6	700.5	662.6	624.6	590.0	558.1	529.5	504.0	481.2	461.6
25°	778.2	740.3	699.4	655.8	614.2	577.5	544.3	513.3	484.9	462.2	441.4
27.5°	775.1	730.5	688.6	643.9	600.9	562.3	527.5	494.9	466.5	442.1	420.7
30°	770.6	722.8	677.8	631.4	587.9	550.7	514.0	482.8	453.2	427.9	406.4
32.5°	760.7	713.3	664.9	617.4	573.3	535.0	500.2	468.8	439.8	413.9	391.0
35°	741.2	693.2	640.7	591.9	548.6	508.8	476.2	445.9	418.2	390.5	366.4
37.5°	715.5	666.5	614.2	560.8	517.4	479.9	450.0	421.5	394.5	369.2	342.5
40°	691.3	646.6	592.6	539.6	495.1	458.9	431.2	405.4	378.2	353.1	326.4
42.5°	662.0	623.9	569.3	516.1	472.2	437.3	411.5	386.3	361.5	337.2	309.3
45°	613.0	584.1	533.0	481.9	437.6	403.0	379.4	357.1	335.4	312.2	285.9
47.5°	556.8	537.3	493.2	440.8	399.9	368.8	345.9	327.7	309.3	286.1	263.1
50°	517.8	505.3	462.7	414.9	375.8	347.2	323.8	306.7	291.3	269.1	248.5
52.5°	476.2	469.5	433.5	387.8	350.1	322.0	302.0	286.7	271.1	252.6	233.4
55°	412.7	416.3	385.8	346.2	310.7	287.1	268.9	256.1	242.8	227.2	212.3
57.5°	347.9	360.9	340.4	305.7	272.4	250.5	236.8	226.1	214.9	202.0	189.2
60°	309.1	320.0	308.4	277.8	248.7	228.4	215.6	207.3	196.2	184.4	174.7
62.5°	271.2	282.9	276.0	251.3	224.3	206.8	195.5	187.8	179.5	169.2	159.1
65°	223.7	231.2	227.9	210.9	191.7	176.8	166.4	160.7	153.1	145.6	136.6
67.5°	171.3	185.9	184.0	174.9	158.4	146.7	139.9	134.9	128.0	122.4	116.3
70°	140.8	154.3	154.1	146.7	137.7	126.9	122.1	117.9	111.7	106.3	101.3
72.5°	115.3	127.6	129.5	123.8	117.7	109.4	104.9	102.0	96.0	92.3	88.2
75°	80.7	89.7	92.1	92.1	89.2	85.0	80.9	79.0	74.8	71.5	69.1
77.5°	52.9	58.6	62.3	63.1	63.6	62.1	58.8	57.5	54.2	53.1	50.8
80°	37.4	41.2	45.4	46.9	48.0	47.6	46.2	45.2	42.1	40.9	40.0
82.5°	25.8	27.9	31.4	34.6	34.2	35.5	34.2	33.5	31.1	30.7	29.8
85°	13.5	13.7	14.2	16.3	17.5	18.0	18.2	17.8	17.0	17.0	15.4
87.5°	5.8	5.5	5.8	5.6	5.7	6.2	6.6	6.6	6.3	5.9	5.5
90°	6.5	5.9	5.3	4.5	3.7	2.8	1.9	1.1	1.9	2.8	3.7
92.5°	13.1	12.7	12.2	11.5	10.5	9.5	8.6	7.6	8.6	9.5	10.5
95°	25.8	25.2	24.7	24.0	23.3	22.6	21.9	21.2	21.9	22.6	23.3
97.5°	41.2	40.5	39.9	39.3	38.7	38.2	37.6	37.0	37.6	38.2	38.7
100°	52.7	51.9	51.2	50.7	50.4	50.1	49.8	49.5	49.8	50.1	50.4
102.5°	64.7	64.0	63.4	63.0	62.9	62.7	62.6	62.5	62.6	62.7	62.9
105°	83.5	83.2	82.8	82.6	82.6	82.5	82.4	82.3	82.4	82.5	82.6
107.5°	103.7	103.7	103.6	103.6	103.5	103.4	103.3	103.2	103.3	103.4	103.5
110°	117.8	117.9	118.0	117.9	117.8	117.6	117.5	117.3	117.5	117.6	117.8





TEST NUMBER: P332866

CATALOG NUMBER: S124RDIP-S350D365U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	131.8	131.9	132.1	132.1	132.1	132.1	132.0	132.0	132.0	132.1	132.1
115°	153.7	153.8	154.0	154.1	154.1	154.1	154.1	154.1	154.1	154.1	154.1
117.5°	174.9	175.0	175.1	175.1	175.0	175.0	174.9	174.8	174.9	175.0	175.0
120°	189.5	189.8	190.0	190.0	189.6	189.3	189.0	188.7	189.0	189.3	189.6
122.5°	203.4	203.5	203.6	203.6	203.5	203.4	203.2	203.1	203.2	203.4	203.5
125°	224.2	224.3	224.3	224.4	224.4	224.4	224.4	224.4	224.4	224.4	224.4
127.5°	244.4	244.6	244.7	244.6	244.4	244.2	243.9	243.7	243.9	244.2	244.4
130°	258.3	258.3	258.3	258.2	258.0	257.7	257.5	257.3	257.5	257.7	258.0
132.5°	271.7	271.8	271.8	271.8	271.6	271.4	271.3	271.1	271.3	271.4	271.6
135°	291.5	291.5	291.5	291.3	290.8	290.3	289.9	289.4	289.9	290.3	290.8
137.5°	310.6	310.5	310.4	310.2	310.0	309.8	309.6	309.3	309.6	309.8	310.0
140°	323.3	323.3	323.3	323.3	323.1	322.9	322.8	322.6	322.8	322.9	323.1
142.5°	335.3	335.4	335.5	335.4	335.2	335.1	334.9	334.8	334.9	335.1	335.2
145°	353.2	353.1	353.1	352.9	352.5	352.2	351.9	351.6	351.9	352.2	352.5
147.5°	369.8	369.9	369.9	369.8	369.4	369.0	368.7	368.3	368.7	369.0	369.4
150°	379.9	379.9	379.9	379.7	379.4	379.1	378.8	378.5	378.8	379.1	379.4
152.5°	389.1	389.0	388.9	388.8	388.6	388.4	388.3	388.1	388.3	388.4	388.6
155°	402.6	402.7	402.8	402.8	402.8	402.8	402.8	402.8	402.8	402.8	402.8
157.5°	414.6	414.6	414.6	414.7	414.9	415.0	415.1	415.3	415.1	415.0	414.9
160°	422.1	422.2	422.2	422.3	422.4	422.5	422.5	422.6	422.5	422.5	422.4
162.5°	428.3	428.4	428.5	428.6	428.8	429.0	429.2	429.4	429.2	429.0	428.8
165°	437.1	437.2	437.4	437.6	437.8	438.1	438.3	438.5	438.3	438.1	437.8
167.5°	444.1	444.1	444.0	444.2	444.5	444.9	445.2	445.5	445.2	444.9	444.5
170°	447.9	447.8	447.8	447.9	448.3	448.7	449.1	449.5	449.1	448.7	448.3
172.5°	450.9	450.8	450.8	451.0	451.3	451.6	452.0	452.3	452.0	451.6	451.3
175°	454.2	454.3	454.4	454.6	455.0	455.4	455.8	456.2	455.8	455.4	455.0
177.5°	456.1	456.1	456.1	456.2	456.5	456.8	457.2	457.5	457.2	456.8	456.5
180°	456.9	456.9	456.9	456.9	456.9	456.9	456.9	456.9	456.9	456.9	456.9



TEST NUMBER: P332866

CATALOG NUMBER: S124RDIP-S350D365U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	576.8	574.9	572.5	569.6	566.2	563.2	561.8	563.0	563.6	562.0	561.8
5°	559.2	553.3	548.6	541.5	535.8	531.1	527.8	526.3	526.8	523.0	522.1
7.5°	539.5	532.5	524.7	516.3	508.5	501.5	497.9	495.9	491.8	490.1	487.2
10°	526.8	517.4	509.8	499.8	490.8	482.6	478.5	475.2	471.2	469.3	465.3
12.5°	513.8	502.8	494.4	484.1	474.9	465.0	461.1	455.0	448.7	444.7	439.5
15°	495.3	482.1	471.9	459.6	448.7	437.4	427.2	415.8	411.6	402.6	397.4
17.5°	473.8	460.4	447.8	431.3	414.5	400.3	389.5	378.6	372.1	366.4	363.7
20°	459.6	447.3	429.8	410.6	391.9	376.3	367.5	360.4	353.3	349.3	346.5
22.5°	446.2	430.4	410.1	389.4	370.7	358.5	351.1	343.8	338.0	334.2	330.4
25°	423.6	403.0	381.5	357.8	345.1	334.4	326.4	320.4	316.9	311.9	310.0
27.5°	400.5	375.5	351.8	335.9	322.6	312.8	305.8	301.4	296.9	293.7	291.2
30°	382.7	357.4	336.1	320.9	307.4	299.4	293.7	288.5	284.9	282.3	280.5
32.5°	365.1	339.8	321.9	305.6	294.9	287.1	281.0	277.1	274.3	271.0	269.8
35°	339.6	317.1	301.5	286.8	276.0	268.9	264.1	260.1	257.7	256.8	256.1
37.5°	315.1	296.7	279.9	267.9	258.2	252.6	247.0	245.0	243.4	241.7	242.5
40°	299.6	282.3	267.4	254.7	246.8	240.7	237.4	235.0	233.6	233.6	233.6
42.5°	286.2	269.3	254.7	243.3	235.5	230.3	226.6	224.6	224.1	223.9	225.1
45°	265.3	249.7	235.0	225.5	218.9	213.7	211.6	209.9	209.9	210.9	211.1
47.5°	244.6	230.0	218.2	207.6	201.5	198.3	196.4	195.6	195.7	196.6	197.7
50°	231.9	217.5	205.9	196.4	190.8	187.7	186.0	185.5	186.0	186.0	187.7
52.5°	218.1	205.2	193.8	185.8	179.4	176.5	175.6	174.9	175.2	176.0	176.7
55°	197.9	186.3	175.4	167.8	163.1	161.2	159.0	159.3	158.8	159.3	159.3
57.5°	177.5	167.1	157.0	151.0	146.8	144.1	141.8	142.4	141.7	141.6	141.2
60°	164.5	153.1	145.1	139.6	134.9	132.5	130.4	130.9	130.2	129.7	128.7
62.5°	150.3	140.8	133.1	127.9	124.1	121.4	119.2	118.8	117.1	115.5	113.4
65°	129.7	121.9	115.0	110.1	106.5	104.4	102.7	101.3	97.7	94.0	92.1
67.5°	109.7	104.0	97.6	93.4	90.5	87.8	84.6	82.2	78.9	76.8	75.6
70°	96.8	91.4	85.9	81.9	78.8	76.2	72.7	71.0	68.6	67.7	66.5
72.5°	84.5	79.4	74.4	70.7	67.5	65.4	62.6	61.0	59.9	59.5	58.4
75°	65.8	61.8	58.0	54.7	52.1	50.6	49.5	48.3	47.8	45.7	44.5
77.5°	48.0	45.3	43.0	40.6	38.8	37.8	35.5	34.2	33.4	32.4	32.1
80°	37.4	35.5	33.1	31.7	29.1	28.2	27.2	27.0	26.7	26.5	26.3
82.5°	28.1	26.2	23.9	23.0	22.3	21.7	21.2	20.9	20.7	20.8	20.8
85°	14.2	13.3	13.3	13.0	12.8	12.5	12.3	12.3	12.1	12.3	12.1
87.5°	5.6	5.6	5.7	5.5	5.8	5.9	5.8	5.9	6.2	5.9	6.0
90°	4.5	5.3	5.9	6.5	7.1	7.8	8.2	8.7	9.2	9.7	10.0
92.5°	11.5	12.2	12.7	13.1	13.6	14.0	14.3	14.6	14.8	15.1	15.3
95°	24.0	24.7	25.2	25.8	26.3	26.9	27.1	27.3	27.6	27.8	27.9
97.5°	39.3	39.9	40.5	41.2	41.8	42.5	42.8	43.0	43.3	43.6	43.7
100°	50.7	51.2	51.9	52.7	53.4	54.1	54.2	54.4	54.5	54.7	54.8
102.5°	63.0	63.4	64.0	64.7	65.3	65.9	66.2	66.4	66.6	66.8	67.0
105°	82.6	82.8	83.2	83.5	83.8	84.1	84.3	84.6	84.8	85.0	85.3
107.5°	103.6	103.6	103.7	103.7	103.8	103.8	104.0	104.3	104.5	104.7	104.8
110°	117.9	118.0	117.9	117.8	117.7	117.7	117.5	117.4	117.2	117.0	117.1



TEST NUMBER: P332866

CATALOG NUMBER: S124RDIP-S350D365U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	132.1	132.1	131.9	131.8	131.7	131.5	131.5	131.5	131.4	131.4	131.4
115°	154.1	154.0	153.8	153.7	153.5	153.4	153.3	153.2	153.1	153.0	153.0
117.5°	175.1	175.1	175.0	174.9	174.7	174.6	174.4	174.1	173.8	173.6	173.4
120°	190.0	190.0	189.8	189.5	189.3	189.1	188.7	188.3	187.9	187.5	187.4
122.5°	203.6	203.6	203.5	203.4	203.3	203.2	202.9	202.7	202.4	202.1	201.8
125°	224.4	224.3	224.3	224.2	224.1	224.0	223.9	223.7	223.6	223.4	223.2
127.5°	244.6	244.7	244.6	244.4	244.3	244.2	244.0	243.9	243.7	243.5	243.4
130°	258.2	258.3	258.3	258.3	258.3	258.3	258.2	258.0	257.8	257.7	257.4
132.5°	271.8	271.8	271.8	271.7	271.7	271.6	271.4	271.3	271.1	271.0	270.8
135°	291.3	291.5	291.5	291.5	291.5	291.5	291.4	291.2	291.1	290.9	290.7
137.5°	310.2	310.4	310.5	310.6	310.8	310.9	310.7	310.5	310.3	310.1	310.0
140°	323.3	323.3	323.3	323.3	323.3	323.3	323.3	323.2	323.1	323.0	322.9
142.5°	335.4	335.5	335.4	335.3	335.3	335.2	335.2	335.2	335.2	335.1	335.1
145°	352.9	353.1	353.1	353.2	353.3	353.4	353.3	353.2	353.1	353.1	352.9
147.5°	369.8	369.9	369.9	369.8	369.8	369.7	369.6	369.6	369.5	369.4	369.4
150°	379.7	379.9	379.9	379.9	379.9	379.9	379.9	379.9	379.9	379.9	379.8
152.5°	388.8	388.9	389.0	389.1	389.1	389.2	389.4	389.6	389.8	390.0	389.9
155°	402.8	402.8	402.7	402.6	402.6	402.5	402.8	403.1	403.4	403.7	403.7
157.5°	414.7	414.6	414.6	414.6	414.6	414.6	414.8	415.0	415.3	415.5	415.5
160°	422.3	422.2	422.2	422.1	422.0	421.9	422.2	422.4	422.6	422.9	422.8
162.5°	428.6	428.5	428.4	428.3	428.2	428.1	428.6	429.0	429.4	429.8	429.8
165°	437.6	437.4	437.2	437.1	436.9	436.8	437.2	437.7	438.2	438.6	438.7
167.5°	444.2	444.0	444.1	444.1	444.1	444.1	444.6	445.1	445.5	446.0	446.0
170°	447.9	447.8	447.8	447.9	448.0	448.1	448.5	449.0	449.5	450.0	449.9
172.5°	451.0	450.8	450.8	450.9	450.9	450.9	451.4	452.0	452.5	453.0	453.0
175°	454.6	454.4	454.3	454.2	454.2	454.1	454.6	455.2	455.7	456.3	456.3
177.5°	456.2	456.1	456.1	456.1	456.1	456.1	456.5	456.9	457.4	457.8	457.8
180°	456.9	456.9	456.9	456.9	456.9	456.9	456.9	456.9	456.9	456.9	456.9



TEST NUMBER: P332866

CATALOG NUMBER: S124RDIP-S350D365U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	560.7	561.1	559.8	559.4	559.8	561.1	560.7	561.8	562.0	563.6	563.0
5°	520.2	519.7	518.5	518.8	518.5	519.7	520.2	522.1	523.0	526.8	526.3
7.5°	485.5	483.7	484.2	482.3	484.2	483.7	485.5	487.2	490.1	491.8	495.9
10°	464.3	461.7	459.6	457.7	459.6	461.7	464.3	465.3	469.3	471.2	475.2
12.5°	435.4	433.1	430.3	430.8	430.3	433.1	435.4	439.5	444.7	448.7	455.0
15°	394.3	390.7	385.1	385.8	385.1	390.7	394.3	397.4	402.6	411.6	415.8
17.5°	359.5	359.5	356.9	357.6	356.9	359.5	359.5	363.7	366.4	372.1	378.6
20°	341.5	339.9	340.1	339.4	340.1	339.9	341.5	346.5	349.3	353.3	360.4
22.5°	329.0	327.0	325.3	323.9	325.3	327.0	329.0	330.4	334.2	338.0	343.8
25°	307.9	306.5	304.4	303.9	304.4	306.5	307.9	310.0	311.9	316.9	320.4
27.5°	289.3	289.1	288.2	287.1	288.2	289.1	289.3	291.2	293.7	296.9	301.4
30°	278.6	278.1	277.6	276.9	277.6	278.1	278.6	280.5	282.3	284.9	288.5
32.5°	268.9	268.6	268.1	268.2	268.1	268.6	268.9	269.8	271.0	274.3	277.1
35°	255.1	254.9	254.4	254.2	254.4	254.9	255.1	256.1	256.8	257.7	260.1
37.5°	242.3	242.9	242.6	242.5	242.6	242.9	242.3	242.5	241.7	243.4	245.0
40°	233.4	233.6	234.1	233.8	234.1	233.6	233.4	233.6	233.6	233.6	235.0
42.5°	226.0	226.0	226.7	225.9	226.7	226.0	226.0	225.1	223.9	224.1	224.6
45°	212.8	214.2	213.9	213.9	213.9	214.2	212.8	211.1	210.9	209.9	209.9
47.5°	198.3	199.6	199.9	199.8	199.9	199.6	198.3	197.7	196.6	195.7	195.6
50°	188.9	188.4	189.1	188.9	189.1	188.4	188.9	187.7	186.0	186.0	185.5
52.5°	177.3	177.4	177.4	177.1	177.4	177.4	177.3	176.7	176.0	175.2	174.9
55°	159.5	159.8	159.3	159.5	159.3	159.8	159.5	159.3	159.3	158.8	159.3
57.5°	140.2	139.1	139.5	139.0	139.5	139.1	140.2	141.2	141.6	141.7	142.4
60°	126.4	124.5	124.0	123.1	124.0	124.5	126.4	128.7	129.7	130.2	130.9
62.5°	110.9	109.5	107.9	108.7	107.9	109.5	110.9	113.4	115.5	117.1	118.8
65°	90.2	89.2	88.5	89.5	88.5	89.2	90.2	92.1	94.0	97.7	101.3
67.5°	74.6	74.1	74.1	73.7	74.1	74.1	74.6	75.6	76.8	78.9	82.2
70°	66.5	65.8	65.8	65.3	65.8	65.8	66.5	66.5	67.7	68.6	71.0
72.5°	58.2	57.5	57.7	57.4	57.7	57.5	58.2	58.4	59.5	59.9	61.0
75°	43.1	41.9	41.9	42.1	41.9	41.9	43.1	44.5	45.7	47.8	48.3
77.5°	32.1	31.9	32.2	31.8	32.2	31.9	32.1	32.1	32.4	33.4	34.2
80°	26.3	26.0	25.8	26.5	25.8	26.0	26.3	26.3	26.5	26.7	27.0
82.5°	20.4	20.4	20.3	21.2	20.3	20.4	20.4	20.8	20.8	20.7	20.9
85°	12.3	11.8	12.3	11.8	12.3	11.8	12.3	12.1	12.3	12.1	12.3
87.5°	6.4	6.2	6.1	6.3	6.1	6.2	6.4	6.0	5.9	6.2	5.9
90°	10.1	10.3	10.4	10.6	10.4	10.3	10.1	10.0	9.7	9.2	8.7
92.5°	15.4	15.5	15.6	15.7	15.6	15.5	15.4	15.3	15.1	14.8	14.6
95°	27.9	27.9	27.9	27.9	27.9	27.9	27.9	27.9	27.8	27.6	27.3
97.5°	43.7	43.7	43.7	43.7	43.7	43.7	43.7	43.7	43.6	43.3	43.0
100°	54.8	54.8	54.8	54.8	54.8	54.8	54.8	54.8	54.7	54.5	54.4
102.5°	67.0	67.1	67.1	67.2	67.1	67.1	67.0	67.0	66.8	66.6	66.4
105°	85.5	85.8	86.0	86.2	86.0	85.8	85.5	85.3	85.0	84.8	84.6
107.5°	104.8	104.8	104.8	104.7	104.8	104.8	104.8	104.8	104.7	104.5	104.3
110°	117.3	117.6	117.8	118.0	117.8	117.6	117.3	117.1	117.0	117.2	117.4



TEST NUMBER: P332866

CATALOG NUMBER: S124RDIP-S350D365U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	131.5	131.5	131.5	131.6	131.5	131.5	131.5	131.4	131.4	131.4	131.5
115°	152.9	152.8	152.7	152.7	152.7	152.8	152.9	153.0	153.0	153.1	153.2
117.5°	173.2	173.0	172.9	172.7	172.9	173.0	173.2	173.4	173.6	173.8	174.1
120°	187.5	187.7	187.8	188.0	187.8	187.7	187.5	187.4	187.5	187.9	188.3
122.5°	201.6	201.3	201.0	200.7	201.0	201.3	201.6	201.8	202.1	202.4	202.7
125°	223.1	222.9	222.8	222.6	222.8	222.9	223.1	223.2	223.4	223.6	223.7
127.5°	243.3	243.2	243.0	242.9	243.0	243.2	243.3	243.4	243.5	243.7	243.9
130°	257.1	256.8	256.5	256.2	256.5	256.8	257.1	257.4	257.7	257.8	258.0
132.5°	270.7	270.6	270.5	270.3	270.5	270.6	270.7	270.8	271.0	271.1	271.3
135°	290.5	290.2	290.0	289.8	290.0	290.2	290.5	290.7	290.9	291.1	291.2
137.5°	310.0	310.1	310.1	310.2	310.1	310.1	310.0	310.0	310.1	310.3	310.5
140°	322.9	322.8	322.7	322.6	322.7	322.8	322.9	322.9	323.0	323.1	323.2
142.5°	335.1	335.1	335.1	335.1	335.1	335.1	335.1	335.1	335.1	335.2	335.2
145°	352.7	352.4	352.2	352.0	352.2	352.4	352.7	352.9	353.1	353.1	353.2
147.5°	369.3	369.2	369.1	369.1	369.1	369.2	369.3	369.4	369.4	369.5	369.6
150°	379.8	379.7	379.6	379.5	379.6	379.7	379.8	379.8	379.9	379.9	379.9
152.5°	389.7	389.5	389.3	389.1	389.3	389.5	389.7	389.9	390.0	389.8	389.6
155°	403.4	403.1	402.8	402.5	402.8	403.1	403.4	403.7	403.7	403.4	403.1
157.5°	415.2	415.0	414.7	414.4	414.7	415.0	415.2	415.5	415.5	415.3	415.0
160°	422.4	422.0	421.6	421.2	421.6	422.0	422.4	422.8	422.9	422.6	422.4
162.5°	429.5	429.1	428.7	428.3	428.7	429.1	429.5	429.8	429.8	429.4	429.0
165°	438.4	438.1	437.8	437.5	437.8	438.1	438.4	438.7	438.6	438.2	437.7
167.5°	445.5	445.0	444.5	444.0	444.5	445.0	445.5	446.0	446.0	445.5	445.1
170°	449.4	448.8	448.3	447.7	448.3	448.8	449.4	449.9	450.0	449.5	449.0
172.5°	452.5	451.9	451.4	450.8	451.4	451.9	452.5	453.0	453.0	452.5	452.0
175°	455.7	455.2	454.6	454.1	454.6	455.2	455.7	456.3	456.3	455.7	455.2
177.5°	457.3	456.8	456.3	455.8	456.3	456.8	457.3	457.8	457.8	457.4	456.9
180°	456.9	456.9	456.9	456.9	456.9	456.9	456.9	456.9	456.9	456.9	456.9



TEST NUMBER: P332866

CATALOG NUMBER: S124RDIP-S350D365U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	561.8	563.2	566.2	569.6	572.5	574.9	576.8	579.5	581.9	585.3	588.5
5°	527.8	531.1	535.8	541.5	548.6	553.3	559.2	564.5	572.0	579.6	586.9
7.5°	497.9	501.5	508.5	516.3	524.7	532.5	539.5	548.7	558.7	569.8	582.1
10°	478.5	482.6	490.8	499.8	509.8	517.4	526.8	537.7	549.1	562.6	577.7
12.5°	461.1	465.0	474.9	484.1	494.4	502.8	513.8	524.8	540.0	554.6	571.8
15°	427.2	437.4	448.7	459.6	471.9	482.1	495.3	506.7	521.1	541.7	561.4
17.5°	389.5	400.3	414.5	431.3	447.8	460.4	473.8	487.9	505.1	526.1	548.8
20°	367.5	376.3	391.9	410.6	429.8	447.3	459.6	475.2	493.0	515.7	539.1
22.5°	351.1	358.5	370.7	389.4	410.1	430.4	446.2	461.6	481.2	504.0	529.5
25°	326.4	334.4	345.1	357.8	381.5	403.0	423.6	441.4	462.2	484.9	513.3
27.5°	305.8	312.8	322.6	335.9	351.8	375.5	400.5	420.7	442.1	466.5	494.9
30°	293.7	299.4	307.4	320.9	336.1	357.4	382.7	406.4	427.9	453.2	482.8
32.5°	281.0	287.1	294.9	305.6	321.9	339.8	365.1	391.0	413.9	439.8	468.8
35°	264.1	268.9	276.0	286.8	301.5	317.1	339.6	366.4	390.5	418.2	445.9
37.5°	247.0	252.6	258.2	267.9	279.9	296.7	315.1	342.5	369.2	394.5	421.5
40°	237.4	240.7	246.8	254.7	267.4	282.3	299.6	326.4	353.1	378.2	405.4
42.5°	226.6	230.3	235.5	243.3	254.7	269.3	286.2	309.3	337.2	361.5	386.3
45°	211.6	213.7	218.9	225.5	235.0	249.7	265.3	285.9	312.2	335.4	357.1
47.5°	196.4	198.3	201.5	207.6	218.2	230.0	244.6	263.1	286.1	309.3	327.7
50°	186.0	187.7	190.8	196.4	205.9	217.5	231.9	248.5	269.1	291.3	306.7
52.5°	175.6	176.5	179.4	185.8	193.8	205.2	218.1	233.4	252.6	271.1	286.7
55°	159.0	161.2	163.1	167.8	175.4	186.3	197.9	212.3	227.2	242.8	256.1
57.5°	141.8	144.1	146.8	151.0	157.0	167.1	177.5	189.2	202.0	214.9	226.1
60°	130.4	132.5	134.9	139.6	145.1	153.1	164.5	174.7	184.4	196.2	207.3
62.5°	119.2	121.4	124.1	127.9	133.1	140.8	150.3	159.1	169.2	179.5	187.8
65°	102.7	104.4	106.5	110.1	115.0	121.9	129.7	136.6	145.6	153.1	160.7
67.5°	84.6	87.8	90.5	93.4	97.6	104.0	109.7	116.3	122.4	128.0	134.9
70°	72.7	76.2	78.8	81.9	85.9	91.4	96.8	101.3	106.3	111.7	117.9
72.5°	62.6	65.4	67.5	70.7	74.4	79.4	84.5	88.2	92.3	96.0	102.0
75°	49.5	50.6	52.1	54.7	58.0	61.8	65.8	69.1	71.5	74.8	79.0
77.5°	35.5	37.8	38.8	40.6	43.0	45.3	48.0	50.8	53.1	54.2	57.5
80°	27.2	28.2	29.1	31.7	33.1	35.5	37.4	40.0	40.9	42.1	45.2
82.5°	21.2	21.7	22.3	23.0	23.9	26.2	28.1	29.8	30.7	31.1	33.5
85°	12.3	12.5	12.8	13.0	13.3	13.3	14.2	15.4	17.0	17.0	17.8
87.5°	5.8	5.9	5.8	5.5	5.7	5.6	5.6	5.5	5.9	6.3	6.6
90°	8.2	7.8	7.1	6.5	5.9	5.3	4.5	3.7	2.8	1.9	1.1
92.5°	14.3	14.0	13.6	13.1	12.7	12.2	11.5	10.5	9.5	8.6	7.6
95°	27.1	26.9	26.3	25.8	25.2	24.7	24.0	23.3	22.6	21.9	21.2
97.5°	42.8	42.5	41.8	41.2	40.5	39.9	39.3	38.7	38.2	37.6	37.0
100°	54.2	54.1	53.4	52.7	51.9	51.2	50.7	50.4	50.1	49.8	49.5
102.5°	66.2	65.9	65.3	64.7	64.0	63.4	63.0	62.9	62.7	62.6	62.5
105°	84.3	84.1	83.8	83.5	83.2	82.8	82.6	82.6	82.5	82.4	82.3
107.5°	104.0	103.8	103.8	103.7	103.7	103.6	103.6	103.5	103.4	103.3	103.2
110°	117.5	117.7	117.7	117.8	117.9	118.0	117.9	117.8	117.6	117.5	117.3



TEST NUMBER: P332866

CATALOG NUMBER: S124RDIP-S350D365U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	131.5	131.5	131.7	131.8	131.9	132.1	132.1	132.1	132.1	132.0	132.0
115°	153.3	153.4	153.5	153.7	153.8	154.0	154.1	154.1	154.1	154.1	154.1
117.5°	174.4	174.6	174.7	174.9	175.0	175.1	175.1	175.0	175.0	174.9	174.8
120°	188.7	189.1	189.3	189.5	189.8	190.0	190.0	189.6	189.3	189.0	188.7
122.5°	202.9	203.2	203.3	203.4	203.5	203.6	203.6	203.5	203.4	203.2	203.1
125°	223.9	224.0	224.1	224.2	224.3	224.3	224.4	224.4	224.4	224.4	224.4
127.5°	244.0	244.2	244.3	244.4	244.6	244.7	244.6	244.4	244.2	243.9	243.7
130°	258.2	258.3	258.3	258.3	258.3	258.3	258.2	258.0	257.7	257.5	257.3
132.5°	271.4	271.6	271.7	271.7	271.8	271.8	271.8	271.6	271.4	271.3	271.1
135°	291.4	291.5	291.5	291.5	291.5	291.5	291.3	290.8	290.3	289.9	289.4
137.5°	310.7	310.9	310.8	310.6	310.5	310.4	310.2	310.0	309.8	309.6	309.3
140°	323.3	323.3	323.3	323.3	323.3	323.3	323.3	323.1	322.9	322.8	322.6
142.5°	335.2	335.2	335.3	335.3	335.4	335.5	335.4	335.2	335.1	334.9	334.8
145°	353.3	353.4	353.3	353.2	353.1	353.1	352.9	352.5	352.2	351.9	351.6
147.5°	369.6	369.7	369.8	369.8	369.9	369.9	369.8	369.4	369.0	368.7	368.3
150°	379.9	379.9	379.9	379.9	379.9	379.9	379.7	379.4	379.1	378.8	378.5
152.5°	389.4	389.2	389.1	389.1	389.0	388.9	388.8	388.6	388.4	388.3	388.1
155°	402.8	402.5	402.6	402.6	402.7	402.8	402.8	402.8	402.8	402.8	402.8
157.5°	414.8	414.6	414.6	414.6	414.6	414.6	414.7	414.9	415.0	415.1	415.3
160°	422.2	421.9	422.0	422.1	422.2	422.2	422.3	422.4	422.5	422.5	422.6
162.5°	428.6	428.1	428.2	428.3	428.4	428.5	428.6	428.8	429.0	429.2	429.4
165°	437.2	436.8	436.9	437.1	437.2	437.4	437.6	437.8	438.1	438.3	438.5
167.5°	444.6	444.1	444.1	444.1	444.1	444.0	444.2	444.5	444.9	445.2	445.5
170°	448.5	448.1	448.0	447.9	447.8	447.8	447.9	448.3	448.7	449.1	449.5
172.5°	451.4	450.9	450.9	450.9	450.8	450.8	451.0	451.3	451.6	452.0	452.3
175°	454.6	454.1	454.2	454.2	454.3	454.4	454.6	455.0	455.4	455.8	456.2
177.5°	456.5	456.1	456.1	456.1	456.1	456.1	456.2	456.5	456.8	457.2	457.5
180°	456.9	456.9	456.9	456.9	456.9	456.9	456.9	456.9	456.9	456.9	456.9



TEST NUMBER: P332866

CATALOG NUMBER: S124RDIP-S350D365U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	591.0	592.7	594.6	598.2	601.2	602.6	605.2	607.1	606.5	609.2	613.7
5°	593.3	599.7	607.1	614.6	623.1	630.2	635.9	641.6	646.1	651.5	659.6
7.5°	592.9	604.3	616.7	630.2	644.2	656.3	667.4	678.8	688.9	699.9	714.4
10°	591.4	606.6	622.0	639.7	657.5	674.3	689.4	703.6	717.1	731.5	749.8
12.5°	589.7	607.1	625.7	647.1	669.2	689.4	707.2	727.7	744.6	763.2	784.2
15°	582.2	605.6	631.0	658.6	685.2	712.4	736.7	761.8	785.3	807.5	834.0
17.5°	573.6	600.6	630.5	663.2	695.0	728.1	757.1	788.7	812.6	842.5	867.1
20°	566.6	595.7	627.6	664.3	700.5	737.2	769.2	801.4	828.3	858.4	889.6
22.5°	558.1	590.0	624.6	662.6	700.5	740.6	776.0	808.0	841.4	875.2	907.4
25°	544.3	577.5	614.2	655.8	699.4	740.3	778.2	817.9	853.9	890.6	919.5
27.5°	527.5	562.3	600.9	643.9	688.6	730.5	775.1	817.5	853.7	889.0	914.2
30°	514.0	550.7	587.9	631.4	677.8	722.8	770.6	813.0	851.1	882.8	897.0
32.5°	500.2	535.0	573.3	617.4	664.9	713.3	760.7	804.1	839.3	858.3	858.7
35°	476.2	508.8	548.6	591.9	640.7	693.2	741.2	783.8	805.4	807.0	783.8
37.5°	450.0	479.9	517.4	560.8	614.2	666.5	715.5	743.9	751.1	727.0	684.2
40°	431.2	458.9	495.1	539.6	592.6	646.6	691.3	712.1	704.6	665.5	617.7
42.5°	411.5	437.3	472.2	516.1	569.3	623.9	662.0	673.1	653.1	608.0	552.0
45°	379.4	403.0	437.6	481.9	533.0	584.1	613.0	607.3	573.9	520.4	457.7
47.5°	345.9	368.8	399.9	440.8	493.2	537.3	556.8	539.7	492.2	433.4	382.4
50°	323.8	347.2	375.8	414.9	462.7	505.3	517.8	491.8	439.0	382.5	335.6
52.5°	302.0	322.0	350.1	387.8	433.5	469.5	476.2	446.2	391.7	341.0	299.4
55°	268.9	287.1	310.7	346.2	385.8	416.3	412.7	374.2	324.7	281.4	248.7
57.5°	236.8	250.5	272.4	305.7	340.4	360.9	347.9	315.0	268.9	233.4	205.9
60°	215.6	228.4	248.7	277.8	308.4	320.0	309.1	273.4	236.9	204.5	181.3
62.5°	195.5	206.8	224.3	251.3	276.0	282.9	271.2	240.0	207.2	179.5	160.3
65°	166.4	176.8	191.7	210.9	227.9	231.2	223.7	191.7	166.9	143.7	130.4
67.5°	139.9	146.7	158.4	174.9	184.0	185.9	171.3	151.2	129.3	115.1	105.1
70°	122.1	126.9	137.7	146.7	154.1	154.3	140.8	124.7	107.9	96.3	89.0
72.5°	104.9	109.4	117.7	123.8	129.5	127.6	115.3	102.6	89.0	80.2	74.8
75°	80.9	85.0	89.2	92.1	92.1	89.7	80.7	71.2	63.4	58.2	56.6
77.5°	58.8	62.1	63.6	63.1	62.3	58.6	52.9	46.7	43.9	41.5	40.2
80°	46.2	47.6	48.0	46.9	45.4	41.2	37.4	34.8	32.2	31.2	30.8
82.5°	34.2	35.5	34.2	34.6	31.4	27.9	25.8	24.9	23.9	23.5	23.0
85°	18.2	18.0	17.5	16.3	14.2	13.7	13.5	13.3	12.8	13.0	12.5
87.5°	6.6	6.2	5.7	5.6	5.8	5.5	5.8	6.0	6.1	6.0	6.5
90°	1.9	2.8	3.7	4.5	5.3	5.9	6.5	7.1	7.8	8.2	8.7
92.5°	8.6	9.5	10.5	11.5	12.2	12.7	13.1	13.6	14.0	14.3	14.6
95°	21.9	22.6	23.3	24.0	24.7	25.2	25.8	26.3	26.9	27.1	27.3
97.5°	37.6	38.2	38.7	39.3	39.9	40.5	41.2	41.8	42.5	42.8	43.0
100°	49.8	50.1	50.4	50.7	51.2	51.9	52.7	53.4	54.1	54.2	54.4
102.5°	62.6	62.7	62.9	63.0	63.4	64.0	64.7	65.3	65.9	66.2	66.4
105°	82.4	82.5	82.6	82.6	82.8	83.2	83.5	83.8	84.1	84.3	84.6
107.5°	103.3	103.4	103.5	103.6	103.6	103.7	103.7	103.8	103.8	104.0	104.3
110°	117.5	117.6	117.8	117.9	118.0	117.9	117.8	117.7	117.7	117.5	117.4





TEST NUMBER: P332866

CATALOG NUMBER: S124RDIP-S350D365U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	132.0	132.1	132.1	132.1	132.1	131.9	131.8	131.7	131.5	131.5	131.5
115°	154.1	154.1	154.1	154.1	154.0	153.8	153.7	153.5	153.4	153.3	153.2
117.5°	174.9	175.0	175.0	175.1	175.1	175.0	174.9	174.7	174.6	174.4	174.1
120°	189.0	189.3	189.6	190.0	190.0	189.8	189.5	189.3	189.1	188.7	188.3
122.5°	203.2	203.4	203.5	203.6	203.6	203.5	203.4	203.3	203.2	202.9	202.7
125°	224.4	224.4	224.4	224.4	224.3	224.3	224.2	224.1	224.0	223.9	223.7
127.5°	243.9	244.2	244.4	244.6	244.7	244.6	244.4	244.3	244.2	244.0	243.9
130°	257.5	257.7	258.0	258.2	258.3	258.3	258.3	258.3	258.3	258.2	258.0
132.5°	271.3	271.4	271.6	271.8	271.8	271.8	271.7	271.7	271.6	271.4	271.3
135°	289.9	290.3	290.8	291.3	291.5	291.5	291.5	291.5	291.5	291.4	291.2
137.5°	309.6	309.8	310.0	310.2	310.4	310.5	310.6	310.8	310.9	310.7	310.5
140°	322.8	322.9	323.1	323.3	323.3	323.3	323.3	323.3	323.3	323.3	323.2
142.5°	334.9	335.1	335.2	335.4	335.5	335.4	335.3	335.3	335.2	335.2	335.2
145°	351.9	352.2	352.5	352.9	353.1	353.1	353.2	353.3	353.4	353.3	353.2
147.5°	368.7	369.0	369.4	369.8	369.9	369.9	369.8	369.8	369.7	369.6	369.6
150°	378.8	379.1	379.4	379.7	379.9	379.9	379.9	379.9	379.9	379.9	379.9
152.5°	388.3	388.4	388.6	388.8	388.9	389.0	389.1	389.1	389.2	389.4	389.6
155°	402.8	402.8	402.8	402.8	402.8	402.7	402.6	402.6	402.5	402.8	403.1
157.5°	415.1	415.0	414.9	414.7	414.6	414.6	414.6	414.6	414.6	414.8	415.0
160°	422.5	422.5	422.4	422.3	422.2	422.2	422.1	422.0	421.9	422.2	422.4
162.5°	429.2	429.0	428.8	428.6	428.5	428.4	428.3	428.2	428.1	428.6	429.0
165°	438.3	438.1	437.8	437.6	437.4	437.2	437.1	436.9	436.8	437.2	437.7
167.5°	445.2	444.9	444.5	444.2	444.0	444.1	444.1	444.1	444.1	444.6	445.1
170°	449.1	448.7	448.3	447.9	447.8	447.8	447.9	448.0	448.1	448.5	449.0
172.5°	452.0	451.6	451.3	451.0	450.8	450.8	450.9	450.9	450.9	451.4	452.0
175°	455.8	455.4	455.0	454.6	454.4	454.3	454.2	454.2	454.1	454.6	455.2
177.5°	457.2	456.8	456.5	456.2	456.1	456.1	456.1	456.1	456.1	456.5	456.9
180°	456.9	456.9	456.9	456.9	456.9	456.9	456.9	456.9	456.9	456.9	456.9



TEST NUMBER: P332866

CATALOG NUMBER: S124RDIP-S350D365U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	616.2	616.9	617.5	619.4	619.6	621.3	619.6
5°	667.2	670.5	675.7	680.9	681.4	684.7	678.8
7.5°	724.3	732.0	736.8	745.2	748.5	750.6	747.2
10°	763.7	770.8	783.4	789.5	795.7	796.6	793.8
12.5°	801.8	813.0	822.9	834.6	834.3	842.6	839.6
15°	852.5	864.1	877.8	890.8	895.5	895.5	899.3
17.5°	888.6	909.9	924.1	934.3	945.5	947.4	946.1
20°	913.1	936.0	951.2	964.4	972.0	974.1	974.1
22.5°	931.2	950.8	965.6	977.5	983.7	986.2	985.5
25°	943.8	960.6	969.6	973.2	974.8	974.4	969.9
27.5°	926.6	925.8	920.2	909.3	901.1	896.1	890.4
30°	893.7	881.3	867.1	851.5	831.4	816.0	811.3
32.5°	844.6	817.0	792.9	766.9	745.3	729.9	723.4
35°	749.8	706.0	670.2	639.0	616.3	602.1	597.3
37.5°	637.2	594.8	550.6	520.3	501.4	487.1	481.8
40°	565.6	519.5	480.9	452.5	433.1	419.1	418.9
42.5°	500.3	456.2	419.9	399.5	378.6	369.3	369.3
45°	409.7	374.4	343.6	327.5	315.0	307.4	305.3
47.5°	339.2	310.0	289.5	276.7	266.5	261.7	258.5
50°	299.6	274.1	257.7	246.6	240.9	234.8	234.3
52.5°	266.7	246.0	233.3	224.3	217.1	213.4	213.5
55°	224.1	207.8	198.8	191.9	186.3	183.4	182.2
57.5°	188.8	176.6	170.0	163.7	161.3	159.1	158.5
60°	166.9	158.6	152.4	147.4	143.9	143.2	142.9
62.5°	148.7	140.0	135.8	131.9	129.3	128.2	127.8
65°	122.6	116.2	112.4	109.3	108.4	106.7	106.5
67.5°	98.8	95.0	92.5	90.4	89.1	89.0	89.0
70°	84.3	82.1	80.0	78.8	78.1	77.6	77.6
72.5°	71.8	70.2	68.4	67.8	67.7	67.2	67.0
75°	54.7	53.0	53.3	52.1	51.1	49.9	49.2
77.5°	38.8	37.6	37.3	37.2	36.4	36.3	36.6
80°	30.1	28.9	28.6	28.9	28.6	27.9	27.9
82.5°	22.9	21.9	21.6	21.5	21.3	21.5	21.1
85°	12.3	11.8	11.8	11.8	12.3	12.1	11.8
87.5°	6.2	6.1	6.3	6.2	6.2	6.1	6.3
90°	9.2	9.7	10.0	10.1	10.3	10.4	10.6
92.5°	14.8	15.1	15.3	15.4	15.5	15.6	15.7
95°	27.6	27.8	27.9	27.9	27.9	27.9	27.9
97.5°	43.3	43.6	43.7	43.7	43.7	43.7	43.7
100°	54.5	54.7	54.8	54.8	54.8	54.8	54.8
102.5°	66.6	66.8	67.0	67.0	67.1	67.1	67.2
105°	84.8	85.0	85.3	85.5	85.8	86.0	86.2
107.5°	104.5	104.7	104.8	104.8	104.8	104.8	104.7
110°	117.2	117.0	117.1	117.3	117.6	117.8	118.0



TEST NUMBER: P332866

CATALOG NUMBER: S124RDIP-S350D365U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	131.4	131.4	131.4	131.5	131.5	131.5	131.6
115°	153.1	153.0	153.0	152.9	152.8	152.7	152.7
117.5°	173.8	173.6	173.4	173.2	173.0	172.9	172.7
120°	187.9	187.5	187.4	187.5	187.7	187.8	188.0
122.5°	202.4	202.1	201.8	201.6	201.3	201.0	200.7
125°	223.6	223.4	223.2	223.1	222.9	222.8	222.6
127.5°	243.7	243.5	243.4	243.3	243.2	243.0	242.9
130°	257.8	257.7	257.4	257.1	256.8	256.5	256.2
132.5°	271.1	271.0	270.8	270.7	270.6	270.5	270.3
135°	291.1	290.9	290.7	290.5	290.2	290.0	289.8
137.5°	310.3	310.1	310.0	310.0	310.1	310.1	310.2
140°	323.1	323.0	322.9	322.9	322.8	322.7	322.6
142.5°	335.2	335.1	335.1	335.1	335.1	335.1	335.1
145°	353.1	353.1	352.9	352.7	352.4	352.2	352.0
147.5°	369.5	369.4	369.4	369.3	369.2	369.1	369.1
150°	379.9	379.9	379.8	379.8	379.7	379.6	379.5
152.5°	389.8	390.0	389.9	389.7	389.5	389.3	389.1
155°	403.4	403.7	403.7	403.4	403.1	402.8	402.5
157.5°	415.3	415.5	415.5	415.2	415.0	414.7	414.4
160°	422.6	422.9	422.8	422.4	422.0	421.6	421.2
162.5°	429.4	429.8	429.8	429.5	429.1	428.7	428.3
165°	438.2	438.6	438.7	438.4	438.1	437.8	437.5
167.5°	445.5	446.0	446.0	445.5	445.0	444.5	444.0
170°	449.5	450.0	449.9	449.4	448.8	448.3	447.7
172.5°	452.5	453.0	453.0	452.5	451.9	451.4	450.8
175°	455.7	456.3	456.3	455.7	455.2	454.6	454.1
177.5°	457.4	457.8	457.8	457.3	456.8	456.3	455.8
180°	456.9	456.9	456.9	456.9	456.9	456.9	456.9

(END OF REPORT)