

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332873

Luminaire Tested: **S124RDIP-S350D590U835-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332873
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIP-S350D590U835-4F0-1E-UDD-A4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3598.2 lumens
Efficiency: N/A
Efficacy: 140.6 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332873

CATALOG NUMBER: S124RDIP-S350D590U835-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332873

CATALOG NUMBER: S124RDIP-S350D590U835-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48	41																												
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	41	36																												
2	88	81	75	70	80	74	69	65	61	58	55	49	47	45	38	37	35	30																												
3	80	71	64	59	73	65	59	54	54	50	46	44	41	38	34	32	31	26																												
4	74	63	56	50	67	58	52	46	48	43	40	39	36	33	31	29	27	23																												
5	68	56	49	43	62	52	45	40	43	38	34	35	32	29	28	25	23	20																												
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	25	23	21	18																												
7	58	46	38	33	53	42	35	31	36	30	27	29	25	22	23	21	18	16																												
8	54	42	34	29	49	38	32	27	32	27	24	27	23	20	21	19	17	14																												
9	50	38	31	26	45	35	29	24	30	25	21	25	21	18	20	17	15	13																												
10	47	35	28	23	43	32	26	22	27	22	19	23	19	16	18	16	14	12																												

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4742	4742	4742	4742
5°	5501	4756	4204	4756
10°	6507	4736	3752	4736
15°	7516	4692	3224	4692
20°	8369	4631	2916	4631
25°	8639	4572	2707	4572
30°	7563	4501	2581	4501
35°	5887	4394	2505	4394
40°	4415	4272	2464	4272
45°	3486	4077	2442	4077
50°	2943	3852	2372	3852
55°	2564	3605	2245	3605
60°	2307	3347	1988	3347
65°	2034	3070	1710	3070
70°	1832	2783	1541	2783
75°	1535	2464	1313	2464
80°	1297	2101	1232	2101
85°	1093	1649	1093	1649



TEST NUMBER: P332873

CATALOG NUMBER: S124RDIP-S350D590U835-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.9	1.6
10°-20°	171.7	4.8
20°-30°	268.5	7.5
30°-40°	298.5	8.3
40°-50°	264.9	7.4
50°-60°	206.4	5.7
60°-70°	135.1	3.8
70°-80°	66.4	1.8
80°-90°	18.0	0.5
90°-100°	209.7	5.8
100°-110°	436.5	12.1
110°-120°	391.0	10.9
120°-130°	328.9	9.1
130°-140°	274.2	7.6
140°-150°	209.5	5.8
150°-160°	147.2	4.1
160°-170°	86.6	2.4
170°-180°	28.2	0.8
0°-30°	497.1	13.8
0°-40°	795.6	22.1
0°-60°	1266.9	35.2
0°-90°	1486.4	41.3
90°-120°	1037.2	28.8
90°-150°	1849.7	51.4
90°-180°	2112.0	58.7
0°-180°	3598.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	587	587	587	587	587	
5°	679	587	519	587	679	69
15°	899	561	386	561	899	256
25°	970	513	304	513	970	430
35°	597	446	254	446	597	374
45°	305	357	214	357	305	242
55°	182	256	160	256	182	166
65°	106	161	90	161	106	107
75°	49	79	42	79	49	54
85°	12	18	12	18	12	14
90°	12	1	12	1	12	10
95°	139	19	139	19	139	216
105°	803	67	803	67	803	794
115°	771	118	771	118	771	765
125°	615	164	615	164	615	559
135°	550	194	550	194	550	424
145°	449	224	449	224	449	285
155°	376	255	376	255	376	175
165°	328	278	328	278	328	94
175°	296	290	296	290	296	29
180°	290	290	290	290	290	



TEST NUMBER: P332873

CATALOG NUMBER: S124RDIP-S350D590U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	619.6	621.3	619.6	619.4	617.5	616.9	616.2	613.7	609.2	606.5	607.1
5°	678.8	684.7	681.4	680.9	675.7	670.5	667.2	659.6	651.5	646.1	641.6
7.5°	747.2	750.6	748.5	745.2	736.8	732.0	724.3	714.4	699.9	688.9	678.8
10°	793.8	796.6	795.7	789.5	783.4	770.8	763.7	749.8	731.5	717.1	703.6
12.5°	839.6	842.6	834.3	834.6	822.9	813.0	801.8	784.2	763.2	744.6	727.7
15°	899.3	895.5	895.5	890.8	877.8	864.1	852.5	834.0	807.5	785.3	761.8
17.5°	946.1	947.4	945.5	934.3	924.1	909.9	888.6	867.1	842.5	812.6	788.7
20°	974.1	974.1	972.0	964.4	951.2	936.0	913.1	889.6	858.4	828.3	801.4
22.5°	985.5	986.2	983.7	977.5	965.6	950.8	931.2	907.4	875.2	841.4	808.0
25°	969.9	974.4	974.8	973.2	969.6	960.6	943.8	919.5	890.6	853.9	817.9
27.5°	890.4	896.1	901.1	909.3	920.2	925.8	926.6	914.2	889.0	853.7	817.5
30°	811.3	816.0	831.4	851.5	867.1	881.3	893.7	897.0	882.8	851.1	813.0
32.5°	723.4	729.9	745.3	766.9	792.9	817.0	844.6	858.7	858.3	839.3	804.1
35°	597.3	602.1	616.3	639.0	670.2	706.0	749.8	783.8	807.0	805.4	783.8
37.5°	481.8	487.1	501.4	520.3	550.6	594.8	637.2	684.2	727.0	751.1	743.9
40°	418.9	419.1	433.1	452.5	480.9	519.5	565.6	617.7	665.5	704.6	712.1
42.5°	369.3	369.3	378.6	399.5	419.9	456.2	500.3	552.0	608.0	653.1	673.1
45°	305.3	307.4	315.0	327.5	343.6	374.4	409.7	457.7	520.4	573.9	607.3
47.5°	258.5	261.7	266.5	276.7	289.5	310.0	339.2	382.4	433.4	492.2	539.7
50°	234.3	234.8	240.9	246.6	257.7	274.1	299.6	335.6	382.5	439.0	491.8
52.5°	213.5	213.4	217.1	224.3	233.3	246.0	266.7	299.4	341.0	391.7	446.2
55°	182.2	183.4	186.3	191.9	198.8	207.8	224.1	248.7	281.4	324.7	374.2
57.5°	158.5	159.1	161.3	163.7	170.0	176.6	188.8	205.9	233.4	268.9	315.0
60°	142.9	143.2	143.9	147.4	152.4	158.6	166.9	181.3	204.5	236.9	273.4
62.5°	127.8	128.2	129.3	131.9	135.8	140.0	148.7	160.3	179.5	207.2	240.0
65°	106.5	106.7	108.4	109.3	112.4	116.2	122.6	130.4	143.7	166.9	191.7
67.5°	89.0	89.0	89.1	90.4	92.5	95.0	98.8	105.1	115.1	129.3	151.2
70°	77.6	77.6	78.1	78.8	80.0	82.1	84.3	89.0	96.3	107.9	124.7
72.5°	67.0	67.2	67.7	67.8	68.4	70.2	71.8	74.8	80.2	89.0	102.6
75°	49.2	49.9	51.1	52.1	53.3	53.0	54.7	56.6	58.2	63.4	71.2
77.5°	36.6	36.3	36.4	37.2	37.3	37.6	38.8	40.2	41.5	43.9	46.7
80°	27.9	27.9	28.6	28.9	28.6	28.9	30.1	30.8	31.2	32.2	34.8
82.5°	21.1	21.5	21.3	21.5	21.6	21.9	22.9	23.0	23.5	23.9	24.9
85°	11.8	12.1	12.3	11.8	11.8	11.8	12.3	12.5	13.0	12.8	13.3
87.5°	6.6	6.4	6.7	6.6	6.6	6.4	6.5	6.8	6.3	6.6	6.4
90°	12.0	12.0	12.5	12.0	11.4	11.4	10.8	10.3	9.7	10.3	9.1
92.5°	43.9	43.9	45.9	48.9	55.7	67.1	84.3	112.0	150.7	180.9	158.4
95°	139.2	146.6	156.9	174.6	202.5	257.8	334.3	422.7	478.0	464.9	350.8
97.5°	372.0	383.9	401.0	435.4	476.3	535.9	591.7	624.5	600.6	489.7	328.4
100°	523.1	527.7	544.8	579.6	629.2	671.4	699.4	688.0	604.7	458.6	297.8
102.5°	654.5	658.2	676.2	701.4	731.9	749.5	741.4	684.8	570.4	419.9	277.2
105°	802.6	806.0	814.0	818.6	817.5	794.1	737.6	638.9	508.3	374.2	259.6
107.5°	857.6	856.1	850.4	837.4	809.2	758.4	678.8	573.8	458.1	348.7	256.4
110°	858.5	853.4	843.1	819.2	778.7	715.9	633.2	534.5	433.0	340.0	257.3



TEST NUMBER: P332873

CATALOG NUMBER: S124RDIP-S350D590U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	831.6	823.3	808.9	779.9	733.9	671.2	593.0	505.8	418.8	335.9	260.0
115°	770.7	766.1	747.9	713.6	668.6	613.8	547.1	476.9	405.6	333.7	265.3
117.5°	709.0	705.4	686.9	658.2	619.7	573.3	520.8	462.7	399.7	333.1	270.8
120°	674.3	668.0	653.2	628.1	595.5	555.0	509.4	456.4	396.5	333.1	275.0
122.5°	646.9	640.6	628.1	606.6	579.1	543.6	502.1	450.9	392.8	332.7	279.1
125°	614.9	611.5	600.7	584.1	561.3	529.9	490.6	441.5	386.8	332.0	285.2
127.5°	596.2	592.8	583.7	569.0	546.0	516.3	477.0	430.1	378.7	330.7	290.1
130°	585.3	581.9	572.7	558.5	535.1	504.8	466.1	421.0	373.6	330.3	293.8
132.5°	573.0	569.5	560.9	544.8	521.8	491.6	453.7	411.4	369.1	329.8	297.0
135°	549.9	546.5	537.4	521.4	498.6	470.0	435.3	398.2	362.2	329.1	301.8
137.5°	521.4	517.3	509.8	494.0	472.7	446.9	417.6	386.2	356.3	329.0	304.6
140°	500.9	496.3	488.3	475.8	455.8	431.8	406.2	379.3	353.1	328.6	306.9
142.5°	478.9	475.8	468.7	457.0	439.4	418.6	396.6	373.0	350.4	328.6	308.7
145°	448.9	446.1	440.4	430.7	416.4	400.5	383.3	363.9	345.7	327.4	309.8
147.5°	422.4	421.3	417.0	408.7	398.2	385.6	371.9	356.5	341.5	325.4	310.3
150°	407.3	406.7	403.3	395.9	386.8	376.5	365.1	352.0	338.3	324.0	310.3
152.5°	393.6	393.0	391.0	384.9	377.2	368.7	358.2	346.9	334.6	321.7	309.4
155°	375.9	375.9	374.2	369.7	363.9	357.1	348.5	339.4	329.1	318.3	308.0
157.5°	360.4	360.4	359.4	356.0	351.6	346.1	339.0	331.3	323.6	314.8	306.6
160°	350.8	350.8	350.3	346.8	343.4	338.8	332.6	326.3	319.5	312.0	305.2
162.5°	341.7	342.2	341.6	338.2	335.7	331.5	326.6	321.3	315.8	309.3	303.8
165°	328.0	328.6	329.1	326.9	324.6	321.7	317.7	314.3	309.8	305.2	301.2
167.5°	317.2	317.6	317.7	316.3	315.1	313.4	310.2	307.6	304.3	301.1	298.5
170°	310.3	310.3	310.9	310.3	309.2	307.5	305.2	303.5	300.6	298.3	296.6
172.5°	303.5	304.4	305.0	304.4	303.7	302.5	301.1	299.8	297.4	295.6	294.8
175°	295.5	296.6	297.8	296.6	296.6	296.6	295.5	294.9	293.8	292.6	292.6
177.5°	290.8	291.7	292.6	292.2	292.6	292.2	292.2	291.7	291.3	290.8	290.8
180°	290.4	290.4	290.4	290.4	290.4	290.4	290.4	290.4	290.4	290.4	290.4



TEST NUMBER: P332873

CATALOG NUMBER: S124RDIP-S350D590U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	605.2	602.6	601.2	598.2	594.6	592.7	591.0	588.5	585.3	581.9	579.5
5°	635.9	630.2	623.1	614.6	607.1	599.7	593.3	586.9	579.6	572.0	564.5
7.5°	667.4	656.3	644.2	630.2	616.7	604.3	592.9	582.1	569.8	558.7	548.7
10°	689.4	674.3	657.5	639.7	622.0	606.6	591.4	577.7	562.6	549.1	537.7
12.5°	707.2	689.4	669.2	647.1	625.7	607.1	589.7	571.8	554.6	540.0	524.8
15°	736.7	712.4	685.2	658.6	631.0	605.6	582.2	561.4	541.7	521.1	506.7
17.5°	757.1	728.1	695.0	663.2	630.5	600.6	573.6	548.8	526.1	505.1	487.9
20°	769.2	737.2	700.5	664.3	627.6	595.7	566.6	539.1	515.7	493.0	475.2
22.5°	776.0	740.6	700.5	662.6	624.6	590.0	558.1	529.5	504.0	481.2	461.6
25°	778.2	740.3	699.4	655.8	614.2	577.5	544.3	513.3	484.9	462.2	441.4
27.5°	775.1	730.5	688.6	643.9	600.9	562.3	527.5	494.9	466.5	442.1	420.7
30°	770.6	722.8	677.8	631.4	587.9	550.7	514.0	482.8	453.2	427.9	406.4
32.5°	760.7	713.3	664.9	617.4	573.3	535.0	500.2	468.8	439.8	413.9	391.0
35°	741.2	693.2	640.7	591.9	548.6	508.8	476.2	445.9	418.2	390.5	366.4
37.5°	715.5	666.5	614.2	560.8	517.4	479.9	450.0	421.5	394.5	369.2	342.5
40°	691.3	646.6	592.6	539.6	495.1	458.9	431.2	405.4	378.2	353.1	326.4
42.5°	662.0	623.9	569.3	516.1	472.2	437.3	411.5	386.3	361.5	337.2	309.3
45°	613.0	584.1	533.0	481.9	437.6	403.0	379.4	357.1	335.4	312.2	285.9
47.5°	556.8	537.3	493.2	440.8	399.9	368.8	345.9	327.7	309.3	286.1	263.1
50°	517.8	505.3	462.7	414.9	375.8	347.2	323.8	306.7	291.3	269.1	248.5
52.5°	476.2	469.5	433.5	387.8	350.1	322.0	302.0	286.7	271.1	252.6	233.4
55°	412.7	416.3	385.8	346.2	310.7	287.1	268.9	256.1	242.8	227.2	212.3
57.5°	347.9	360.9	340.4	305.7	272.4	250.5	236.8	226.1	214.9	202.0	189.2
60°	309.1	320.0	308.4	277.8	248.7	228.4	215.6	207.3	196.2	184.4	174.7
62.5°	271.2	282.9	276.0	251.3	224.3	206.8	195.5	187.8	179.5	169.2	159.1
65°	223.7	231.2	227.9	210.9	191.7	176.8	166.4	160.7	153.1	145.6	136.6
67.5°	171.3	185.9	184.0	174.9	158.4	146.7	139.9	134.9	128.0	122.4	116.3
70°	140.8	154.3	154.1	146.7	137.7	126.9	122.1	117.9	111.7	106.3	101.3
72.5°	115.3	127.6	129.5	123.8	117.7	109.4	104.9	102.0	96.0	92.3	88.2
75°	80.7	89.7	92.1	92.1	89.2	85.0	80.9	79.0	74.8	71.5	69.1
77.5°	52.9	58.6	62.3	63.1	63.6	62.1	58.8	57.5	54.2	53.1	50.8
80°	37.4	41.2	45.4	46.9	48.0	47.6	46.2	45.2	42.1	40.9	40.0
82.5°	25.8	27.9	31.4	34.6	34.2	35.5	34.2	33.5	31.1	30.7	29.8
85°	13.5	13.7	14.2	16.3	17.5	18.0	18.2	17.8	17.0	17.0	15.4
87.5°	6.1	6.0	5.6	5.6	5.7	6.4	6.6	6.6	6.2	6.0	5.5
90°	8.0	8.0	4.6	4.6	4.0	3.4	1.7	0.6	1.7	3.4	4.0
92.5°	115.2	71.0	42.0	30.1	21.8	14.8	9.5	6.5	9.5	14.8	21.8
95°	214.5	120.9	71.3	47.3	33.7	26.2	20.5	18.8	20.5	26.2	33.7
97.5°	192.8	115.6	77.4	57.3	45.5	38.7	33.8	33.8	33.8	38.7	45.5
100°	181.4	116.9	83.3	65.0	54.2	47.3	43.4	43.4	43.4	47.3	54.2
102.5°	178.2	121.5	91.0	73.7	63.3	56.9	53.4	52.5	53.4	56.9	63.3
105°	179.7	132.3	105.0	88.4	78.2	71.3	68.5	66.7	68.5	71.3	78.2
107.5°	188.1	145.0	119.9	103.6	93.8	86.5	83.6	82.5	83.6	86.5	93.8
110°	194.5	154.6	129.5	114.1	103.8	97.0	94.1	93.0	94.1	97.0	103.8



TEST NUMBER: P332873

CATALOG NUMBER: S124RDIP-S350D590U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	201.4	163.7	139.5	124.1	113.9	107.5	104.2	103.0	104.2	107.5	113.9
115°	212.2	178.0	155.2	139.8	128.9	123.2	119.2	117.5	119.2	123.2	128.9
117.5°	223.3	191.8	170.1	154.1	144.0	137.7	134.2	132.6	134.2	137.7	144.0
120°	231.0	201.4	179.7	163.7	154.0	147.7	143.8	142.6	143.8	147.7	154.0
122.5°	238.3	210.5	188.8	173.3	162.7	156.9	152.9	151.7	152.9	156.9	162.7
125°	249.3	223.0	202.5	186.5	175.7	169.4	166.0	163.7	166.0	169.4	175.7
127.5°	258.8	234.7	214.8	198.7	187.4	180.3	176.2	174.3	176.2	180.3	187.4
130°	264.7	242.4	223.0	206.5	195.7	187.1	182.5	180.3	182.5	187.1	195.7
132.5°	270.6	248.8	229.4	213.8	202.1	194.0	188.0	186.2	188.0	194.0	202.1
135°	278.4	257.8	239.0	224.2	212.2	202.5	196.8	194.5	196.8	202.5	212.2
137.5°	283.9	264.7	247.1	233.0	220.5	211.3	205.0	202.9	205.0	211.3	220.5
140°	287.5	269.3	252.1	238.4	226.5	216.8	210.5	208.8	210.5	216.8	226.5
142.5°	290.2	273.4	256.7	243.5	231.9	222.7	216.9	215.2	216.9	222.7	231.9
145°	293.2	277.8	263.0	250.4	239.6	231.6	225.9	224.2	225.9	231.6	239.6
147.5°	295.8	282.4	268.5	257.2	248.1	239.9	234.9	234.3	234.9	239.9	248.1
150°	297.2	284.7	272.1	261.3	252.7	245.9	241.3	240.7	241.3	245.9	252.7
152.5°	298.1	286.5	275.3	265.4	257.7	251.3	246.8	246.7	246.8	251.3	257.7
155°	298.9	289.2	279.5	271.0	264.7	259.0	255.6	255.0	255.6	259.0	264.7
157.5°	298.9	291.2	282.9	276.2	270.7	266.3	263.1	263.1	263.1	266.3	270.7
160°	298.9	292.1	285.2	278.9	274.4	270.4	268.1	268.1	268.1	270.4	274.4
162.5°	298.9	293.0	286.6	281.7	277.6	274.0	272.2	272.7	272.2	274.0	277.6
165°	297.8	293.2	288.1	284.7	281.8	278.9	277.8	277.8	277.8	278.9	281.8
167.5°	296.4	293.1	289.3	286.7	285.1	282.9	282.4	282.9	282.4	282.9	285.1
170°	295.5	292.6	289.8	288.1	286.9	285.2	284.7	285.2	284.7	285.2	286.9
172.5°	294.6	292.2	290.2	289.0	288.3	287.0	286.9	287.5	286.9	287.0	288.3
175°	293.2	291.5	290.4	290.4	289.8	289.2	289.2	289.8	289.2	289.2	289.8
177.5°	291.7	290.8	290.4	290.4	290.4	289.9	290.4	290.8	290.4	289.9	290.4
180°	290.4	290.4	290.4	290.4	290.4	290.4	290.4	290.4	290.4	290.4	290.4



TEST NUMBER: P332873

CATALOG NUMBER: S124RDIP-S350D590U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	576.8	574.9	572.5	569.6	566.2	563.2	561.8	563.0	563.6	562.0	561.8
5°	559.2	553.3	548.6	541.5	535.8	531.1	527.8	526.3	526.8	523.0	522.1
7.5°	539.5	532.5	524.7	516.3	508.5	501.5	497.9	495.9	491.8	490.1	487.2
10°	526.8	517.4	509.8	499.8	490.8	482.6	478.5	475.2	471.2	469.3	465.3
12.5°	513.8	502.8	494.4	484.1	474.9	465.0	461.1	455.0	448.7	444.7	439.5
15°	495.3	482.1	471.9	459.6	448.7	437.4	427.2	415.8	411.6	402.6	397.4
17.5°	473.8	460.4	447.8	431.3	414.5	400.3	389.5	378.6	372.1	366.4	363.7
20°	459.6	447.3	429.8	410.6	391.9	376.3	367.5	360.4	353.3	349.3	346.5
22.5°	446.2	430.4	410.1	389.4	370.7	358.5	351.1	343.8	338.0	334.2	330.4
25°	423.6	403.0	381.5	357.8	345.1	334.4	326.4	320.4	316.9	311.9	310.0
27.5°	400.5	375.5	351.8	335.9	322.6	312.8	305.8	301.4	296.9	293.7	291.2
30°	382.7	357.4	336.1	320.9	307.4	299.4	293.7	288.5	284.9	282.3	280.5
32.5°	365.1	339.8	321.9	305.6	294.9	287.1	281.0	277.1	274.3	271.0	269.8
35°	339.6	317.1	301.5	286.8	276.0	268.9	264.1	260.1	257.7	256.8	256.1
37.5°	315.1	296.7	279.9	267.9	258.2	252.6	247.0	245.0	243.4	241.7	242.5
40°	299.6	282.3	267.4	254.7	246.8	240.7	237.4	235.0	233.6	233.6	233.6
42.5°	286.2	269.3	254.7	243.3	235.5	230.3	226.6	224.6	224.1	223.9	225.1
45°	265.3	249.7	235.0	225.5	218.9	213.7	211.6	209.9	209.9	210.9	211.1
47.5°	244.6	230.0	218.2	207.6	201.5	198.3	196.4	195.6	195.7	196.6	197.7
50°	231.9	217.5	205.9	196.4	190.8	187.7	186.0	185.5	186.0	186.0	187.7
52.5°	218.1	205.2	193.8	185.8	179.4	176.5	175.6	174.9	175.2	176.0	176.7
55°	197.9	186.3	175.4	167.8	163.1	161.2	159.0	159.3	158.8	159.3	159.3
57.5°	177.5	167.1	157.0	151.0	146.8	144.1	141.8	142.4	141.7	141.6	141.2
60°	164.5	153.1	145.1	139.6	134.9	132.5	130.4	130.9	130.2	129.7	128.7
62.5°	150.3	140.8	133.1	127.9	124.1	121.4	119.2	118.8	117.1	115.5	113.4
65°	129.7	121.9	115.0	110.1	106.5	104.4	102.7	101.3	97.7	94.0	92.1
67.5°	109.7	104.0	97.6	93.4	90.5	87.8	84.6	82.2	78.9	76.8	75.6
70°	96.8	91.4	85.9	81.9	78.8	76.2	72.7	71.0	68.6	67.7	66.5
72.5°	84.5	79.4	74.4	70.7	67.5	65.4	62.6	61.0	59.9	59.5	58.4
75°	65.8	61.8	58.0	54.7	52.1	50.6	49.5	48.3	47.8	45.7	44.5
77.5°	48.0	45.3	43.0	40.6	38.8	37.8	35.5	34.2	33.4	32.4	32.1
80°	37.4	35.5	33.1	31.7	29.1	28.2	27.2	27.0	26.7	26.5	26.3
82.5°	28.1	26.2	23.9	23.0	22.3	21.7	21.2	20.9	20.7	20.8	20.8
85°	14.2	13.3	13.3	13.0	12.8	12.5	12.3	12.3	12.1	12.3	12.1
87.5°	5.6	5.5	6.1	5.8	6.2	6.4	6.1	6.2	6.5	6.3	6.3
90°	4.6	4.6	8.0	8.0	9.1	10.3	9.7	10.3	10.8	11.4	11.4
92.5°	30.1	42.0	71.0	115.2	158.4	180.9	150.7	112.0	84.3	67.1	55.7
95°	47.3	71.3	120.9	214.5	350.8	464.9	478.0	422.7	334.3	257.8	202.5
97.5°	57.3	77.4	115.6	192.8	328.4	489.7	600.6	624.5	591.7	535.9	476.3
100°	65.0	83.3	116.9	181.4	297.8	458.6	604.7	688.0	699.4	671.4	629.2
102.5°	73.7	91.0	121.5	178.2	277.2	419.9	570.4	684.8	741.4	749.5	731.9
105°	88.4	105.0	132.3	179.7	259.6	374.2	508.3	638.9	737.6	794.1	817.5
107.5°	103.6	119.9	145.0	188.1	256.4	348.7	458.1	573.8	678.8	758.4	809.2
110°	114.1	129.5	154.6	194.5	257.3	340.0	433.0	534.5	633.2	715.9	778.7



TEST NUMBER: P332873

CATALOG NUMBER: S124RDIP-S350D590U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	124.1	139.5	163.7	201.4	260.0	335.9	418.8	505.8	593.0	671.2	733.9
115°	139.8	155.2	178.0	212.2	265.3	333.7	405.6	476.9	547.1	613.8	668.6
117.5°	154.1	170.1	191.8	223.3	270.8	333.1	399.7	462.7	520.8	573.3	619.7
120°	163.7	179.7	201.4	231.0	275.0	333.1	396.5	456.4	509.4	555.0	595.5
122.5°	173.3	188.8	210.5	238.3	279.1	332.7	392.8	450.9	502.1	543.6	579.1
125°	186.5	202.5	223.0	249.3	285.2	332.0	386.8	441.5	490.6	529.9	561.3
127.5°	198.7	214.8	234.7	258.8	290.1	330.7	378.7	430.1	477.0	516.3	546.0
130°	206.5	223.0	242.4	264.7	293.8	330.3	373.6	421.0	466.1	504.8	535.1
132.5°	213.8	229.4	248.8	270.6	297.0	329.8	369.1	411.4	453.7	491.6	521.8
135°	224.2	239.0	257.8	278.4	301.8	329.1	362.2	398.2	435.3	470.0	498.6
137.5°	233.0	247.1	264.7	283.9	304.6	329.0	356.3	386.2	417.6	446.9	472.7
140°	238.4	252.1	269.3	287.5	306.9	328.6	353.1	379.3	406.2	431.8	455.8
142.5°	243.5	256.7	273.4	290.2	308.7	328.6	350.4	373.0	396.6	418.6	439.4
145°	250.4	263.0	277.8	293.2	309.8	327.4	345.7	363.9	383.3	400.5	416.4
147.5°	257.2	268.5	282.4	295.8	310.3	325.4	341.5	356.5	371.9	385.6	398.2
150°	261.3	272.1	284.7	297.2	310.3	324.0	338.3	352.0	365.1	376.5	386.8
152.5°	265.4	275.3	286.5	298.1	309.4	321.7	334.6	346.9	358.2	368.7	377.2
155°	271.0	279.5	289.2	298.9	308.0	318.3	329.1	339.4	348.5	357.1	363.9
157.5°	276.2	282.9	291.2	298.9	306.6	314.8	323.6	331.3	339.0	346.1	351.6
160°	278.9	285.2	292.1	298.9	305.2	312.0	319.5	326.3	332.6	338.8	343.4
162.5°	281.7	286.6	293.0	298.9	303.8	309.3	315.8	321.3	326.6	331.5	335.7
165°	284.7	288.1	293.2	297.8	301.2	305.2	309.8	314.3	317.7	321.7	324.6
167.5°	286.7	289.3	293.1	296.4	298.5	301.1	304.3	307.6	310.2	313.4	315.1
170°	288.1	289.8	292.6	295.5	296.6	298.3	300.6	303.5	305.2	307.5	309.2
172.5°	289.0	290.2	292.2	294.6	294.8	295.6	297.4	299.8	301.1	302.5	303.7
175°	290.4	290.4	291.5	293.2	292.6	292.6	293.8	294.9	295.5	296.6	296.6
177.5°	290.4	290.4	290.8	291.7	290.8	290.8	291.3	291.7	292.2	292.2	292.6
180°	290.4	290.4	290.4	290.4	290.4	290.4	290.4	290.4	290.4	290.4	290.4



TEST NUMBER: P332873

CATALOG NUMBER: S124RDIP-S350D590U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	560.7	561.1	559.8	559.4	559.8	561.1	560.7	561.8	562.0	563.6	563.0
5°	520.2	519.7	518.5	518.8	518.5	519.7	520.2	522.1	523.0	526.8	526.3
7.5°	485.5	483.7	484.2	482.3	484.2	483.7	485.5	487.2	490.1	491.8	495.9
10°	464.3	461.7	459.6	457.7	459.6	461.7	464.3	465.3	469.3	471.2	475.2
12.5°	435.4	433.1	430.3	430.8	430.3	433.1	435.4	439.5	444.7	448.7	455.0
15°	394.3	390.7	385.1	385.8	385.1	390.7	394.3	397.4	402.6	411.6	415.8
17.5°	359.5	359.5	356.9	357.6	356.9	359.5	359.5	363.7	366.4	372.1	378.6
20°	341.5	339.9	340.1	339.4	340.1	339.9	341.5	346.5	349.3	353.3	360.4
22.5°	329.0	327.0	325.3	323.9	325.3	327.0	329.0	330.4	334.2	338.0	343.8
25°	307.9	306.5	304.4	303.9	304.4	306.5	307.9	310.0	311.9	316.9	320.4
27.5°	289.3	289.1	288.2	287.1	288.2	289.1	289.3	291.2	293.7	296.9	301.4
30°	278.6	278.1	277.6	276.9	277.6	278.1	278.6	280.5	282.3	284.9	288.5
32.5°	268.9	268.6	268.1	268.2	268.1	268.6	268.9	269.8	271.0	274.3	277.1
35°	255.1	254.9	254.4	254.2	254.4	254.9	255.1	256.1	256.8	257.7	260.1
37.5°	242.3	242.9	242.6	242.5	242.6	242.9	242.3	242.5	241.7	243.4	245.0
40°	233.4	233.6	234.1	233.8	234.1	233.6	233.4	233.6	233.6	233.6	235.0
42.5°	226.0	226.0	226.7	225.9	226.7	226.0	226.0	225.1	223.9	224.1	224.6
45°	212.8	214.2	213.9	213.9	213.9	214.2	212.8	211.1	210.9	209.9	209.9
47.5°	198.3	199.6	199.9	199.8	199.9	199.6	198.3	197.7	196.6	195.7	195.6
50°	188.9	188.4	189.1	188.9	189.1	188.4	188.9	187.7	186.0	186.0	185.5
52.5°	177.3	177.4	177.4	177.1	177.4	177.4	177.3	176.7	176.0	175.2	174.9
55°	159.5	159.8	159.3	159.5	159.3	159.8	159.5	159.3	159.3	158.8	159.3
57.5°	140.2	139.1	139.5	139.0	139.5	139.1	140.2	141.2	141.6	141.7	142.4
60°	126.4	124.5	124.0	123.1	124.0	124.5	126.4	128.7	129.7	130.2	130.9
62.5°	110.9	109.5	107.9	108.7	107.9	109.5	110.9	113.4	115.5	117.1	118.8
65°	90.2	89.2	88.5	89.5	88.5	89.2	90.2	92.1	94.0	97.7	101.3
67.5°	74.6	74.1	74.1	73.7	74.1	74.1	74.6	75.6	76.8	78.9	82.2
70°	66.5	65.8	65.8	65.3	65.8	65.8	66.5	66.5	67.7	68.6	71.0
72.5°	58.2	57.5	57.7	57.4	57.7	57.5	58.2	58.4	59.5	59.9	61.0
75°	43.1	41.9	41.9	42.1	41.9	41.9	43.1	44.5	45.7	47.8	48.3
77.5°	32.1	31.9	32.2	31.8	32.2	31.9	32.1	32.1	32.4	33.4	34.2
80°	26.3	26.0	25.8	26.5	25.8	26.0	26.3	26.3	26.5	26.7	27.0
82.5°	20.4	20.4	20.3	21.2	20.3	20.4	20.4	20.8	20.8	20.7	20.9
85°	12.3	11.8	12.3	11.8	12.3	11.8	12.3	12.1	12.3	12.1	12.3
87.5°	6.8	6.7	6.4	6.6	6.4	6.7	6.8	6.3	6.3	6.5	6.2
90°	12.0	12.5	12.0	12.0	12.0	12.5	12.0	11.4	11.4	10.8	10.3
92.5°	48.9	45.9	43.9	43.9	43.9	45.9	48.9	55.7	67.1	84.3	112.0
95°	174.6	156.9	146.6	139.2	146.6	156.9	174.6	202.5	257.8	334.3	422.7
97.5°	435.4	401.0	383.9	372.0	383.9	401.0	435.4	476.3	535.9	591.7	624.5
100°	579.6	544.8	527.7	523.1	527.7	544.8	579.6	629.2	671.4	699.4	688.0
102.5°	701.4	676.2	658.2	654.5	658.2	676.2	701.4	731.9	749.5	741.4	684.8
105°	818.6	814.0	806.0	802.6	806.0	814.0	818.6	817.5	794.1	737.6	638.9
107.5°	837.4	850.4	856.1	857.6	856.1	850.4	837.4	809.2	758.4	678.8	573.8
110°	819.2	843.1	853.4	858.5	853.4	843.1	819.2	778.7	715.9	633.2	534.5



TEST NUMBER: P332873

CATALOG NUMBER: S124RDIP-S350D590U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	779.9	808.9	823.3	831.6	823.3	808.9	779.9	733.9	671.2	593.0	505.8
115°	713.6	747.9	766.1	770.7	766.1	747.9	713.6	668.6	613.8	547.1	476.9
117.5°	658.2	686.9	705.4	709.0	705.4	686.9	658.2	619.7	573.3	520.8	462.7
120°	628.1	653.2	668.0	674.3	668.0	653.2	628.1	595.5	555.0	509.4	456.4
122.5°	606.6	628.1	640.6	646.9	640.6	628.1	606.6	579.1	543.6	502.1	450.9
125°	584.1	600.7	611.5	614.9	611.5	600.7	584.1	561.3	529.9	490.6	441.5
127.5°	569.0	583.7	592.8	596.2	592.8	583.7	569.0	546.0	516.3	477.0	430.1
130°	558.5	572.7	581.9	585.3	581.9	572.7	558.5	535.1	504.8	466.1	421.0
132.5°	544.8	560.9	569.5	573.0	569.5	560.9	544.8	521.8	491.6	453.7	411.4
135°	521.4	537.4	546.5	549.9	546.5	537.4	521.4	498.6	470.0	435.3	398.2
137.5°	494.0	509.8	517.3	521.4	517.3	509.8	494.0	472.7	446.9	417.6	386.2
140°	475.8	488.3	496.3	500.9	496.3	488.3	475.8	455.8	431.8	406.2	379.3
142.5°	457.0	468.7	475.8	478.9	475.8	468.7	457.0	439.4	418.6	396.6	373.0
145°	430.7	440.4	446.1	448.9	446.1	440.4	430.7	416.4	400.5	383.3	363.9
147.5°	408.7	417.0	421.3	422.4	421.3	417.0	408.7	398.2	385.6	371.9	356.5
150°	395.9	403.3	406.7	407.3	406.7	403.3	395.9	386.8	376.5	365.1	352.0
152.5°	384.9	391.0	393.0	393.6	393.0	391.0	384.9	377.2	368.7	358.2	346.9
155°	369.7	374.2	375.9	375.9	375.9	374.2	369.7	363.9	357.1	348.5	339.4
157.5°	356.0	359.4	360.4	360.4	360.4	359.4	356.0	351.6	346.1	339.0	331.3
160°	346.8	350.3	350.8	350.8	350.8	350.3	346.8	343.4	338.8	332.6	326.3
162.5°	338.2	341.6	342.2	341.7	342.2	341.6	338.2	335.7	331.5	326.6	321.3
165°	326.9	329.1	328.6	328.0	328.6	329.1	326.9	324.6	321.7	317.7	314.3
167.5°	316.3	317.7	317.6	317.2	317.6	317.7	316.3	315.1	313.4	310.2	307.6
170°	310.3	310.9	310.3	310.3	310.3	310.9	310.3	309.2	307.5	305.2	303.5
172.5°	304.4	305.0	304.4	303.5	304.4	305.0	304.4	303.7	302.5	301.1	299.8
175°	296.6	297.8	296.6	295.5	296.6	297.8	296.6	296.6	296.6	295.5	294.9
177.5°	292.2	292.6	291.7	290.8	291.7	292.6	292.2	292.6	292.2	292.2	291.7
180°	290.4	290.4	290.4	290.4	290.4	290.4	290.4	290.4	290.4	290.4	290.4



TEST NUMBER: P332873

CATALOG NUMBER: S124RDIP-S350D590U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	561.8	563.2	566.2	569.6	572.5	574.9	576.8	579.5	581.9	585.3	588.5
5°	527.8	531.1	535.8	541.5	548.6	553.3	559.2	564.5	572.0	579.6	586.9
7.5°	497.9	501.5	508.5	516.3	524.7	532.5	539.5	548.7	558.7	569.8	582.1
10°	478.5	482.6	490.8	499.8	509.8	517.4	526.8	537.7	549.1	562.6	577.7
12.5°	461.1	465.0	474.9	484.1	494.4	502.8	513.8	524.8	540.0	554.6	571.8
15°	427.2	437.4	448.7	459.6	471.9	482.1	495.3	506.7	521.1	541.7	561.4
17.5°	389.5	400.3	414.5	431.3	447.8	460.4	473.8	487.9	505.1	526.1	548.8
20°	367.5	376.3	391.9	410.6	429.8	447.3	459.6	475.2	493.0	515.7	539.1
22.5°	351.1	358.5	370.7	389.4	410.1	430.4	446.2	461.6	481.2	504.0	529.5
25°	326.4	334.4	345.1	357.8	381.5	403.0	423.6	441.4	462.2	484.9	513.3
27.5°	305.8	312.8	322.6	335.9	351.8	375.5	400.5	420.7	442.1	466.5	494.9
30°	293.7	299.4	307.4	320.9	336.1	357.4	382.7	406.4	427.9	453.2	482.8
32.5°	281.0	287.1	294.9	305.6	321.9	339.8	365.1	391.0	413.9	439.8	468.8
35°	264.1	268.9	276.0	286.8	301.5	317.1	339.6	366.4	390.5	418.2	445.9
37.5°	247.0	252.6	258.2	267.9	279.9	296.7	315.1	342.5	369.2	394.5	421.5
40°	237.4	240.7	246.8	254.7	267.4	282.3	299.6	326.4	353.1	378.2	405.4
42.5°	226.6	230.3	235.5	243.3	254.7	269.3	286.2	309.3	337.2	361.5	386.3
45°	211.6	213.7	218.9	225.5	235.0	249.7	265.3	285.9	312.2	335.4	357.1
47.5°	196.4	198.3	201.5	207.6	218.2	230.0	244.6	263.1	286.1	309.3	327.7
50°	186.0	187.7	190.8	196.4	205.9	217.5	231.9	248.5	269.1	291.3	306.7
52.5°	175.6	176.5	179.4	185.8	193.8	205.2	218.1	233.4	252.6	271.1	286.7
55°	159.0	161.2	163.1	167.8	175.4	186.3	197.9	212.3	227.2	242.8	256.1
57.5°	141.8	144.1	146.8	151.0	157.0	167.1	177.5	189.2	202.0	214.9	226.1
60°	130.4	132.5	134.9	139.6	145.1	153.1	164.5	174.7	184.4	196.2	207.3
62.5°	119.2	121.4	124.1	127.9	133.1	140.8	150.3	159.1	169.2	179.5	187.8
65°	102.7	104.4	106.5	110.1	115.0	121.9	129.7	136.6	145.6	153.1	160.7
67.5°	84.6	87.8	90.5	93.4	97.6	104.0	109.7	116.3	122.4	128.0	134.9
70°	72.7	76.2	78.8	81.9	85.9	91.4	96.8	101.3	106.3	111.7	117.9
72.5°	62.6	65.4	67.5	70.7	74.4	79.4	84.5	88.2	92.3	96.0	102.0
75°	49.5	50.6	52.1	54.7	58.0	61.8	65.8	69.1	71.5	74.8	79.0
77.5°	35.5	37.8	38.8	40.6	43.0	45.3	48.0	50.8	53.1	54.2	57.5
80°	27.2	28.2	29.1	31.7	33.1	35.5	37.4	40.0	40.9	42.1	45.2
82.5°	21.2	21.7	22.3	23.0	23.9	26.2	28.1	29.8	30.7	31.1	33.5
85°	12.3	12.5	12.8	13.0	13.3	13.3	14.2	15.4	17.0	17.0	17.8
87.5°	6.1	6.4	6.2	5.8	6.1	5.5	5.6	5.5	6.0	6.2	6.6
90°	9.7	10.3	9.1	8.0	8.0	4.6	4.6	4.0	3.4	1.7	0.6
92.5°	150.7	180.9	158.4	115.2	71.0	42.0	30.1	21.8	14.8	9.5	6.5
95°	478.0	464.9	350.8	214.5	120.9	71.3	47.3	33.7	26.2	20.5	18.8
97.5°	600.6	489.7	328.4	192.8	115.6	77.4	57.3	45.5	38.7	33.8	33.8
100°	604.7	458.6	297.8	181.4	116.9	83.3	65.0	54.2	47.3	43.4	43.4
102.5°	570.4	419.9	277.2	178.2	121.5	91.0	73.7	63.3	56.9	53.4	52.5
105°	508.3	374.2	259.6	179.7	132.3	105.0	88.4	78.2	71.3	68.5	66.7
107.5°	458.1	348.7	256.4	188.1	145.0	119.9	103.6	93.8	86.5	83.6	82.5
110°	433.0	340.0	257.3	194.5	154.6	129.5	114.1	103.8	97.0	94.1	93.0



TEST NUMBER: P332873

CATALOG NUMBER: S124RDIP-S350D590U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	418.8	335.9	260.0	201.4	163.7	139.5	124.1	113.9	107.5	104.2	103.0
115°	405.6	333.7	265.3	212.2	178.0	155.2	139.8	128.9	123.2	119.2	117.5
117.5°	399.7	333.1	270.8	223.3	191.8	170.1	154.1	144.0	137.7	134.2	132.6
120°	396.5	333.1	275.0	231.0	201.4	179.7	163.7	154.0	147.7	143.8	142.6
122.5°	392.8	332.7	279.1	238.3	210.5	188.8	173.3	162.7	156.9	152.9	151.7
125°	386.8	332.0	285.2	249.3	223.0	202.5	186.5	175.7	169.4	166.0	163.7
127.5°	378.7	330.7	290.1	258.8	234.7	214.8	198.7	187.4	180.3	176.2	174.3
130°	373.6	330.3	293.8	264.7	242.4	223.0	206.5	195.7	187.1	182.5	180.3
132.5°	369.1	329.8	297.0	270.6	248.8	229.4	213.8	202.1	194.0	188.0	186.2
135°	362.2	329.1	301.8	278.4	257.8	239.0	224.2	212.2	202.5	196.8	194.5
137.5°	356.3	329.0	304.6	283.9	264.7	247.1	233.0	220.5	211.3	205.0	202.9
140°	353.1	328.6	306.9	287.5	269.3	252.1	238.4	226.5	216.8	210.5	208.8
142.5°	350.4	328.6	308.7	290.2	273.4	256.7	243.5	231.9	222.7	216.9	215.2
145°	345.7	327.4	309.8	293.2	277.8	263.0	250.4	239.6	231.6	225.9	224.2
147.5°	341.5	325.4	310.3	295.8	282.4	268.5	257.2	248.1	239.9	234.9	234.3
150°	338.3	324.0	310.3	297.2	284.7	272.1	261.3	252.7	245.9	241.3	240.7
152.5°	334.6	321.7	309.4	298.1	286.5	275.3	265.4	257.7	251.3	246.8	246.7
155°	329.1	318.3	308.0	298.9	289.2	279.5	271.0	264.7	259.0	255.6	255.0
157.5°	323.6	314.8	306.6	298.9	291.2	282.9	276.2	270.7	266.3	263.1	263.1
160°	319.5	312.0	305.2	298.9	292.1	285.2	278.9	274.4	270.4	268.1	268.1
162.5°	315.8	309.3	303.8	298.9	293.0	286.6	281.7	277.6	274.0	272.2	272.7
165°	309.8	305.2	301.2	297.8	293.2	288.1	284.7	281.8	278.9	277.8	277.8
167.5°	304.3	301.1	298.5	296.4	293.1	289.3	286.7	285.1	282.9	282.4	282.9
170°	300.6	298.3	296.6	295.5	292.6	289.8	288.1	286.9	285.2	284.7	285.2
172.5°	297.4	295.6	294.8	294.6	292.2	290.2	289.0	288.3	287.0	286.9	287.5
175°	293.8	292.6	292.6	293.2	291.5	290.4	290.4	289.8	289.2	289.2	289.8
177.5°	291.3	290.8	290.8	291.7	290.8	290.4	290.4	290.4	289.9	290.4	290.8
180°	290.4	290.4	290.4	290.4	290.4	290.4	290.4	290.4	290.4	290.4	290.4



TEST NUMBER: P332873

CATALOG NUMBER: S124RDIP-S350D590U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	591.0	592.7	594.6	598.2	601.2	602.6	605.2	607.1	606.5	609.2	613.7
5°	593.3	599.7	607.1	614.6	623.1	630.2	635.9	641.6	646.1	651.5	659.6
7.5°	592.9	604.3	616.7	630.2	644.2	656.3	667.4	678.8	688.9	699.9	714.4
10°	591.4	606.6	622.0	639.7	657.5	674.3	689.4	703.6	717.1	731.5	749.8
12.5°	589.7	607.1	625.7	647.1	669.2	689.4	707.2	727.7	744.6	763.2	784.2
15°	582.2	605.6	631.0	658.6	685.2	712.4	736.7	761.8	785.3	807.5	834.0
17.5°	573.6	600.6	630.5	663.2	695.0	728.1	757.1	788.7	812.6	842.5	867.1
20°	566.6	595.7	627.6	664.3	700.5	737.2	769.2	801.4	828.3	858.4	889.6
22.5°	558.1	590.0	624.6	662.6	700.5	740.6	776.0	808.0	841.4	875.2	907.4
25°	544.3	577.5	614.2	655.8	699.4	740.3	778.2	817.9	853.9	890.6	919.5
27.5°	527.5	562.3	600.9	643.9	688.6	730.5	775.1	817.5	853.7	889.0	914.2
30°	514.0	550.7	587.9	631.4	677.8	722.8	770.6	813.0	851.1	882.8	897.0
32.5°	500.2	535.0	573.3	617.4	664.9	713.3	760.7	804.1	839.3	858.3	858.7
35°	476.2	508.8	548.6	591.9	640.7	693.2	741.2	783.8	805.4	807.0	783.8
37.5°	450.0	479.9	517.4	560.8	614.2	666.5	715.5	743.9	751.1	727.0	684.2
40°	431.2	458.9	495.1	539.6	592.6	646.6	691.3	712.1	704.6	665.5	617.7
42.5°	411.5	437.3	472.2	516.1	569.3	623.9	662.0	673.1	653.1	608.0	552.0
45°	379.4	403.0	437.6	481.9	533.0	584.1	613.0	607.3	573.9	520.4	457.7
47.5°	345.9	368.8	399.9	440.8	493.2	537.3	556.8	539.7	492.2	433.4	382.4
50°	323.8	347.2	375.8	414.9	462.7	505.3	517.8	491.8	439.0	382.5	335.6
52.5°	302.0	322.0	350.1	387.8	433.5	469.5	476.2	446.2	391.7	341.0	299.4
55°	268.9	287.1	310.7	346.2	385.8	416.3	412.7	374.2	324.7	281.4	248.7
57.5°	236.8	250.5	272.4	305.7	340.4	360.9	347.9	315.0	268.9	233.4	205.9
60°	215.6	228.4	248.7	277.8	308.4	320.0	309.1	273.4	236.9	204.5	181.3
62.5°	195.5	206.8	224.3	251.3	276.0	282.9	271.2	240.0	207.2	179.5	160.3
65°	166.4	176.8	191.7	210.9	227.9	231.2	223.7	191.7	166.9	143.7	130.4
67.5°	139.9	146.7	158.4	174.9	184.0	185.9	171.3	151.2	129.3	115.1	105.1
70°	122.1	126.9	137.7	146.7	154.1	154.3	140.8	124.7	107.9	96.3	89.0
72.5°	104.9	109.4	117.7	123.8	129.5	127.6	115.3	102.6	89.0	80.2	74.8
75°	80.9	85.0	89.2	92.1	92.1	89.7	80.7	71.2	63.4	58.2	56.6
77.5°	58.8	62.1	63.6	63.1	62.3	58.6	52.9	46.7	43.9	41.5	40.2
80°	46.2	47.6	48.0	46.9	45.4	41.2	37.4	34.8	32.2	31.2	30.8
82.5°	34.2	35.5	34.2	34.6	31.4	27.9	25.8	24.9	23.9	23.5	23.0
85°	18.2	18.0	17.5	16.3	14.2	13.7	13.5	13.3	12.8	13.0	12.5
87.5°	6.6	6.4	5.7	5.6	5.6	6.0	6.1	6.4	6.6	6.3	6.8
90°	1.7	3.4	4.0	4.6	4.6	8.0	8.0	9.1	10.3	9.7	10.3
92.5°	9.5	14.8	21.8	30.1	42.0	71.0	115.2	158.4	180.9	150.7	112.0
95°	20.5	26.2	33.7	47.3	71.3	120.9	214.5	350.8	464.9	478.0	422.7
97.5°	33.8	38.7	45.5	57.3	77.4	115.6	192.8	328.4	489.7	600.6	624.5
100°	43.4	47.3	54.2	65.0	83.3	116.9	181.4	297.8	458.6	604.7	688.0
102.5°	53.4	56.9	63.3	73.7	91.0	121.5	178.2	277.2	419.9	570.4	684.8
105°	68.5	71.3	78.2	88.4	105.0	132.3	179.7	259.6	374.2	508.3	638.9
107.5°	83.6	86.5	93.8	103.6	119.9	145.0	188.1	256.4	348.7	458.1	573.8
110°	94.1	97.0	103.8	114.1	129.5	154.6	194.5	257.3	340.0	433.0	534.5



TEST NUMBER: P332873

CATALOG NUMBER: S124RDIP-S350D590U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	104.2	107.5	113.9	124.1	139.5	163.7	201.4	260.0	335.9	418.8	505.8
115°	119.2	123.2	128.9	139.8	155.2	178.0	212.2	265.3	333.7	405.6	476.9
117.5°	134.2	137.7	144.0	154.1	170.1	191.8	223.3	270.8	333.1	399.7	462.7
120°	143.8	147.7	154.0	163.7	179.7	201.4	231.0	275.0	333.1	396.5	456.4
122.5°	152.9	156.9	162.7	173.3	188.8	210.5	238.3	279.1	332.7	392.8	450.9
125°	166.0	169.4	175.7	186.5	202.5	223.0	249.3	285.2	332.0	386.8	441.5
127.5°	176.2	180.3	187.4	198.7	214.8	234.7	258.8	290.1	330.7	378.7	430.1
130°	182.5	187.1	195.7	206.5	223.0	242.4	264.7	293.8	330.3	373.6	421.0
132.5°	188.0	194.0	202.1	213.8	229.4	248.8	270.6	297.0	329.8	369.1	411.4
135°	196.8	202.5	212.2	224.2	239.0	257.8	278.4	301.8	329.1	362.2	398.2
137.5°	205.0	211.3	220.5	233.0	247.1	264.7	283.9	304.6	329.0	356.3	386.2
140°	210.5	216.8	226.5	238.4	252.1	269.3	287.5	306.9	328.6	353.1	379.3
142.5°	216.9	222.7	231.9	243.5	256.7	273.4	290.2	308.7	328.6	350.4	373.0
145°	225.9	231.6	239.6	250.4	263.0	277.8	293.2	309.8	327.4	345.7	363.9
147.5°	234.9	239.9	248.1	257.2	268.5	282.4	295.8	310.3	325.4	341.5	356.5
150°	241.3	245.9	252.7	261.3	272.1	284.7	297.2	310.3	324.0	338.3	352.0
152.5°	246.8	251.3	257.7	265.4	275.3	286.5	298.1	309.4	321.7	334.6	346.9
155°	255.6	259.0	264.7	271.0	279.5	289.2	298.9	308.0	318.3	329.1	339.4
157.5°	263.1	266.3	270.7	276.2	282.9	291.2	298.9	306.6	314.8	323.6	331.3
160°	268.1	270.4	274.4	278.9	285.2	292.1	298.9	305.2	312.0	319.5	326.3
162.5°	272.2	274.0	277.6	281.7	286.6	293.0	298.9	303.8	309.3	315.8	321.3
165°	277.8	278.9	281.8	284.7	288.1	293.2	297.8	301.2	305.2	309.8	314.3
167.5°	282.4	282.9	285.1	286.7	289.3	293.1	296.4	298.5	301.1	304.3	307.6
170°	284.7	285.2	286.9	288.1	289.8	292.6	295.5	296.6	298.3	300.6	303.5
172.5°	286.9	287.0	288.3	289.0	290.2	292.2	294.6	294.8	295.6	297.4	299.8
175°	289.2	289.2	289.8	290.4	290.4	291.5	293.2	292.6	292.6	293.8	294.9
177.5°	290.4	289.9	290.4	290.4	290.4	290.8	291.7	290.8	290.8	291.3	291.7
180°	290.4	290.4	290.4	290.4	290.4	290.4	290.4	290.4	290.4	290.4	290.4



TEST NUMBER: P332873

CATALOG NUMBER: S124RDIP-S350D590U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	616.2	616.9	617.5	619.4	619.6	621.3	619.6
5°	667.2	670.5	675.7	680.9	681.4	684.7	678.8
7.5°	724.3	732.0	736.8	745.2	748.5	750.6	747.2
10°	763.7	770.8	783.4	789.5	795.7	796.6	793.8
12.5°	801.8	813.0	822.9	834.6	834.3	842.6	839.6
15°	852.5	864.1	877.8	890.8	895.5	895.5	899.3
17.5°	888.6	909.9	924.1	934.3	945.5	947.4	946.1
20°	913.1	936.0	951.2	964.4	972.0	974.1	974.1
22.5°	931.2	950.8	965.6	977.5	983.7	986.2	985.5
25°	943.8	960.6	969.6	973.2	974.8	974.4	969.9
27.5°	926.6	925.8	920.2	909.3	901.1	896.1	890.4
30°	893.7	881.3	867.1	851.5	831.4	816.0	811.3
32.5°	844.6	817.0	792.9	766.9	745.3	729.9	723.4
35°	749.8	706.0	670.2	639.0	616.3	602.1	597.3
37.5°	637.2	594.8	550.6	520.3	501.4	487.1	481.8
40°	565.6	519.5	480.9	452.5	433.1	419.1	418.9
42.5°	500.3	456.2	419.9	399.5	378.6	369.3	369.3
45°	409.7	374.4	343.6	327.5	315.0	307.4	305.3
47.5°	339.2	310.0	289.5	276.7	266.5	261.7	258.5
50°	299.6	274.1	257.7	246.6	240.9	234.8	234.3
52.5°	266.7	246.0	233.3	224.3	217.1	213.4	213.5
55°	224.1	207.8	198.8	191.9	186.3	183.4	182.2
57.5°	188.8	176.6	170.0	163.7	161.3	159.1	158.5
60°	166.9	158.6	152.4	147.4	143.9	143.2	142.9
62.5°	148.7	140.0	135.8	131.9	129.3	128.2	127.8
65°	122.6	116.2	112.4	109.3	108.4	106.7	106.5
67.5°	98.8	95.0	92.5	90.4	89.1	89.0	89.0
70°	84.3	82.1	80.0	78.8	78.1	77.6	77.6
72.5°	71.8	70.2	68.4	67.8	67.7	67.2	67.0
75°	54.7	53.0	53.3	52.1	51.1	49.9	49.2
77.5°	38.8	37.6	37.3	37.2	36.4	36.3	36.6
80°	30.1	28.9	28.6	28.9	28.6	27.9	27.9
82.5°	22.9	21.9	21.6	21.5	21.3	21.5	21.1
85°	12.3	11.8	11.8	11.8	12.3	12.1	11.8
87.5°	6.5	6.4	6.6	6.6	6.7	6.4	6.6
90°	10.8	11.4	11.4	12.0	12.5	12.0	12.0
92.5°	84.3	67.1	55.7	48.9	45.9	43.9	43.9
95°	334.3	257.8	202.5	174.6	156.9	146.6	139.2
97.5°	591.7	535.9	476.3	435.4	401.0	383.9	372.0
100°	699.4	671.4	629.2	579.6	544.8	527.7	523.1
102.5°	741.4	749.5	731.9	701.4	676.2	658.2	654.5
105°	737.6	794.1	817.5	818.6	814.0	806.0	802.6
107.5°	678.8	758.4	809.2	837.4	850.4	856.1	857.6
110°	633.2	715.9	778.7	819.2	843.1	853.4	858.5



TEST NUMBER: P332873

CATALOG NUMBER: S124RDIP-S350D590U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	593.0	671.2	733.9	779.9	808.9	823.3	831.6
115°	547.1	613.8	668.6	713.6	747.9	766.1	770.7
117.5°	520.8	573.3	619.7	658.2	686.9	705.4	709.0
120°	509.4	555.0	595.5	628.1	653.2	668.0	674.3
122.5°	502.1	543.6	579.1	606.6	628.1	640.6	646.9
125°	490.6	529.9	561.3	584.1	600.7	611.5	614.9
127.5°	477.0	516.3	546.0	569.0	583.7	592.8	596.2
130°	466.1	504.8	535.1	558.5	572.7	581.9	585.3
132.5°	453.7	491.6	521.8	544.8	560.9	569.5	573.0
135°	435.3	470.0	498.6	521.4	537.4	546.5	549.9
137.5°	417.6	446.9	472.7	494.0	509.8	517.3	521.4
140°	406.2	431.8	455.8	475.8	488.3	496.3	500.9
142.5°	396.6	418.6	439.4	457.0	468.7	475.8	478.9
145°	383.3	400.5	416.4	430.7	440.4	446.1	448.9
147.5°	371.9	385.6	398.2	408.7	417.0	421.3	422.4
150°	365.1	376.5	386.8	395.9	403.3	406.7	407.3
152.5°	358.2	368.7	377.2	384.9	391.0	393.0	393.6
155°	348.5	357.1	363.9	369.7	374.2	375.9	375.9
157.5°	339.0	346.1	351.6	356.0	359.4	360.4	360.4
160°	332.6	338.8	343.4	346.8	350.3	350.8	350.8
162.5°	326.6	331.5	335.7	338.2	341.6	342.2	341.7
165°	317.7	321.7	324.6	326.9	329.1	328.6	328.0
167.5°	310.2	313.4	315.1	316.3	317.7	317.6	317.2
170°	305.2	307.5	309.2	310.3	310.9	310.3	310.3
172.5°	301.1	302.5	303.7	304.4	305.0	304.4	303.5
175°	295.5	296.6	296.6	296.6	297.8	296.6	295.5
177.5°	292.2	292.2	292.6	292.2	292.6	291.7	290.8
180°	290.4	290.4	290.4	290.4	290.4	290.4	290.4

(END OF REPORT)