

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332879

Luminaire Tested: **S124RDIP-S350D810U835-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332879  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIP-S350D810U835-4F0-1E-UDD-A4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 350 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4381.6 lumens  
Efficiency: N/A  
Efficacy: 140.4 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 31.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332879

CATALOG NUMBER: S124RDIP-S350D810U835-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P332879

CATALOG NUMBER: S124RDIP-S350D810U835-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	34																												
1	95	90	87	83	85	82	79	76	66	63	62	51	49	48	37	36	36	29																												
2	86	79	73	69	78	72	67	63	58	54	51	45	43	41	33	32	30	25																												
3	79	70	63	57	71	63	57	53	51	47	44	40	37	35	29	28	26	21																												
4	72	62	54	49	65	56	50	45	46	41	37	36	32	30	26	24	23	19																												
5	66	55	47	42	60	50	44	39	41	36	32	32	29	26	24	22	20	16																												
6	61	49	42	36	55	45	38	33	37	32	28	29	26	23	22	19	18	14																												
7	56	45	37	32	51	41	34	29	33	28	25	26	23	20	20	18	16	13																												
8	52	40	33	28	47	37	30	26	30	25	22	24	21	18	18	16	14	12																												
9	49	37	30	25	44	34	27	23	28	23	20	22	19	16	17	15	13	11																												
10	45	34	27	22	41	31	25	21	26	21	18	20	17	15	16	13	12	10																												

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	4742	4742	4742	4742
5°	5501	4756	4204	4756
10°	6507	4736	3752	4736
15°	7516	4692	3224	4692
20°	8369	4631	2916	4631
25°	8639	4572	2707	4572
30°	7563	4501	2581	4501
35°	5887	4394	2505	4394
40°	4415	4272	2464	4272
45°	3486	4077	2442	4077
50°	2943	3852	2372	3852
55°	2564	3605	2245	3605
60°	2307	3347	1988	3347
65°	2034	3070	1710	3070
70°	1832	2783	1541	2783
75°	1535	2464	1313	2464
80°	1297	2101	1232	2101
85°	1093	1649	1093	1649



TEST NUMBER: P332879

CATALOG NUMBER: S124RDIP-S350D810U835-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	56.9	1.3
10°-20°	171.7	3.9
20°-30°	268.5	6.1
30°-40°	298.5	6.8
40°-50°	264.9	6.0
50°-60°	206.4	4.7
60°-70°	135.1	3.1
70°-80°	66.4	1.5
80°-90°	18.6	0.4
90°-100°	287.5	6.6
100°-110°	598.3	13.7
110°-120°	535.9	12.2
120°-130°	450.8	10.3
130°-140°	375.9	8.6
140°-150°	287.1	6.6
150°-160°	201.8	4.6
160°-170°	118.7	2.7
170°-180°	38.6	0.9
0°-30°	497.1	11.3
0°-40°	795.6	18.2
0°-60°	1266.9	28.9
0°-90°	1487.0	33.9
90°-120°	1421.6	32.4
90°-150°	2535.4	57.9
90°-180°	2895.0	66.1
0°-180°	4381.6	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	587	587	587	587	587	
5°	679	587	519	587	679	69
15°	899	561	386	561	899	256
25°	970	513	304	513	970	430
35°	597	446	254	446	597	374
45°	305	357	214	357	305	242
55°	182	256	160	256	182	166
65°	106	161	90	161	106	107
75°	49	79	42	79	49	54
85°	12	18	12	18	12	14
90°	16	1	16	1	16	14
95°	191	26	191	26	191	296
105°	1100	92	1100	92	1100	1088
115°	1056	161	1056	161	1056	1049
125°	843	224	843	224	843	766
135°	754	267	754	267	754	582
145°	615	307	615	307	615	390
155°	515	350	515	350	515	240
165°	450	381	450	381	450	129
175°	405	397	405	397	405	39
180°	398	398	398	398	398	



TEST NUMBER: P332879

CATALOG NUMBER: S124RDIP-S350D810U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	619.6	621.3	619.6	619.4	617.5	616.9	616.2	613.7	609.2	606.5	607.1
5°	678.8	684.7	681.4	680.9	675.7	670.5	667.2	659.6	651.5	646.1	641.6
7.5°	747.2	750.6	748.5	745.2	736.8	732.0	724.3	714.4	699.9	688.9	678.8
10°	793.8	796.6	795.7	789.5	783.4	770.8	763.7	749.8	731.5	717.1	703.6
12.5°	839.6	842.6	834.3	834.6	822.9	813.0	801.8	784.2	763.2	744.6	727.7
15°	899.3	895.5	895.5	890.8	877.8	864.1	852.5	834.0	807.5	785.3	761.8
17.5°	946.1	947.4	945.5	934.3	924.1	909.9	888.6	867.1	842.5	812.6	788.7
20°	974.1	974.1	972.0	964.4	951.2	936.0	913.1	889.6	858.4	828.3	801.4
22.5°	985.5	986.2	983.7	977.5	965.6	950.8	931.2	907.4	875.2	841.4	808.0
25°	969.9	974.4	974.8	973.2	969.6	960.6	943.8	919.5	890.6	853.9	817.9
27.5°	890.4	896.1	901.1	909.3	920.2	925.8	926.6	914.2	889.0	853.7	817.5
30°	811.3	816.0	831.4	851.5	867.1	881.3	893.7	897.0	882.8	851.1	813.0
32.5°	723.4	729.9	745.3	766.9	792.9	817.0	844.6	858.7	858.3	839.3	804.1
35°	597.3	602.1	616.3	639.0	670.2	706.0	749.8	783.8	807.0	805.4	783.8
37.5°	481.8	487.1	501.4	520.3	550.6	594.8	637.2	684.2	727.0	751.1	743.9
40°	418.9	419.1	433.1	452.5	480.9	519.5	565.6	617.7	665.5	704.6	712.1
42.5°	369.3	369.3	378.6	399.5	419.9	456.2	500.3	552.0	608.0	653.1	673.1
45°	305.3	307.4	315.0	327.5	343.6	374.4	409.7	457.7	520.4	573.9	607.3
47.5°	258.5	261.7	266.5	276.7	289.5	310.0	339.2	382.4	433.4	492.2	539.7
50°	234.3	234.8	240.9	246.6	257.7	274.1	299.6	335.6	382.5	439.0	491.8
52.5°	213.5	213.4	217.1	224.3	233.3	246.0	266.7	299.4	341.0	391.7	446.2
55°	182.2	183.4	186.3	191.9	198.8	207.8	224.1	248.7	281.4	324.7	374.2
57.5°	158.5	159.1	161.3	163.7	170.0	176.6	188.8	205.9	233.4	268.9	315.0
60°	142.9	143.2	143.9	147.4	152.4	158.6	166.9	181.3	204.5	236.9	273.4
62.5°	127.8	128.2	129.3	131.9	135.8	140.0	148.7	160.3	179.5	207.2	240.0
65°	106.5	106.7	108.4	109.3	112.4	116.2	122.6	130.4	143.7	166.9	191.7
67.5°	89.0	89.0	89.1	90.4	92.5	95.0	98.8	105.1	115.1	129.3	151.2
70°	77.6	77.6	78.1	78.8	80.0	82.1	84.3	89.0	96.3	107.9	124.7
72.5°	67.0	67.2	67.7	67.8	68.4	70.2	71.8	74.8	80.2	89.0	102.6
75°	49.2	49.9	51.1	52.1	53.3	53.0	54.7	56.6	58.2	63.4	71.2
77.5°	36.6	36.3	36.4	37.2	37.3	37.6	38.8	40.2	41.5	43.9	46.7
80°	27.9	27.9	28.6	28.9	28.6	28.9	30.1	30.8	31.2	32.2	34.8
82.5°	21.1	21.5	21.3	21.5	21.6	21.9	22.9	23.0	23.5	23.9	24.9
85°	11.8	12.1	12.3	11.8	11.8	11.8	12.3	12.5	13.0	12.8	13.3
87.5°	7.4	7.3	7.6	7.4	7.5	7.3	7.3	7.5	7.0	7.4	7.0
90°	16.4	16.4	17.2	16.4	15.6	15.6	14.9	14.1	13.3	14.1	12.5
92.5°	60.2	60.2	62.9	67.1	76.3	92.0	115.6	153.6	206.6	248.0	217.1
95°	190.8	201.0	215.0	239.3	277.6	353.4	458.2	579.4	655.3	637.3	480.9
97.5°	510.0	526.2	549.7	596.8	652.9	734.5	811.0	856.0	823.2	671.2	450.1
100°	717.0	723.3	746.7	794.4	862.5	920.3	958.6	943.0	828.8	628.7	408.2
102.5°	897.2	902.2	926.9	961.5	1003.2	1027.3	1016.2	938.6	781.9	575.5	380.0
105°	1100.2	1104.9	1115.8	1122.1	1120.5	1088.4	1011.0	875.8	696.7	512.9	355.8
107.5°	1175.5	1173.5	1165.7	1147.9	1109.2	1039.5	930.5	786.5	627.9	477.9	351.4
110°	1176.8	1169.8	1155.7	1122.8	1067.3	981.3	867.9	732.7	593.5	466.0	352.6



TEST NUMBER: P332879

CATALOG NUMBER: S124RDIP-S350D810U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1139.9	1128.5	1108.8	1069.0	1006.0	920.0	812.9	693.3	574.1	460.4	356.4
115°	1056.4	1050.1	1025.1	978.2	916.4	841.3	749.9	653.7	555.9	457.4	363.6
117.5°	971.8	966.9	941.6	902.2	849.5	785.8	713.9	634.3	547.8	456.6	371.3
120°	924.2	915.6	895.3	860.9	816.3	760.8	698.3	625.5	543.4	456.6	376.9
122.5°	886.7	878.1	860.9	831.5	793.8	745.2	688.2	618.0	538.4	456.0	382.5
125°	842.9	838.2	823.4	800.7	769.4	726.4	672.5	605.2	530.1	455.1	391.0
127.5°	817.3	812.6	800.1	779.9	748.5	707.6	653.8	589.6	519.0	453.4	397.7
130°	802.3	797.6	785.1	765.5	733.4	692.0	638.8	577.1	512.2	452.7	402.7
132.5°	785.4	780.7	768.8	746.7	715.3	673.9	621.9	563.9	505.9	452.1	407.1
135°	753.8	749.1	736.6	714.7	683.4	644.3	596.6	545.8	496.5	451.2	413.6
137.5°	714.7	709.0	698.7	677.1	647.9	612.6	572.4	529.4	488.4	451.0	417.5
140°	686.5	680.3	669.3	652.1	624.8	591.9	556.7	520.0	484.0	450.4	420.7
142.5°	656.5	652.1	642.4	626.5	602.2	573.8	543.6	511.2	480.3	450.4	423.2
145°	615.4	611.5	603.6	590.4	570.8	548.9	525.5	498.9	473.8	448.8	424.6
147.5°	578.9	577.5	571.6	560.2	545.8	528.6	509.8	488.7	468.1	446.0	425.4
150°	558.3	557.5	552.8	542.7	530.1	516.1	500.4	482.4	463.7	444.1	425.4
152.5°	539.5	538.7	535.9	527.6	517.0	505.4	491.0	475.6	458.7	441.0	424.1
155°	515.3	515.3	512.9	506.7	498.9	489.5	477.8	465.2	451.2	436.3	422.2
157.5°	494.0	494.0	492.6	487.9	482.0	474.5	464.6	454.1	443.5	431.5	420.2
160°	480.9	480.9	480.1	475.4	470.7	464.5	455.9	447.3	437.9	427.7	418.3
162.5°	468.4	469.0	468.2	463.5	460.1	454.5	447.7	440.4	432.9	424.0	416.5
165°	449.6	450.4	451.2	448.0	444.9	441.0	435.5	430.8	424.6	418.3	412.9
167.5°	434.7	435.4	435.5	433.5	431.9	429.6	425.2	421.6	417.1	412.7	409.1
170°	425.4	425.4	426.1	425.4	423.8	421.5	418.3	416.0	412.1	408.9	406.6
172.5°	416.0	417.2	418.0	417.2	416.3	414.6	412.7	411.0	407.7	405.2	404.1
175°	405.0	406.6	408.2	406.6	406.6	406.6	405.0	404.3	402.7	401.1	401.1
177.5°	398.6	399.9	401.1	400.5	401.1	400.5	400.5	399.9	399.2	398.6	398.6
180°	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0



TEST NUMBER: P332879

CATALOG NUMBER: S124RDIP-S350D810U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	605.2	602.6	601.2	598.2	594.6	592.7	591.0	588.5	585.3	581.9	579.5
5°	635.9	630.2	623.1	614.6	607.1	599.7	593.3	586.9	579.6	572.0	564.5
7.5°	667.4	656.3	644.2	630.2	616.7	604.3	592.9	582.1	569.8	558.7	548.7
10°	689.4	674.3	657.5	639.7	622.0	606.6	591.4	577.7	562.6	549.1	537.7
12.5°	707.2	689.4	669.2	647.1	625.7	607.1	589.7	571.8	554.6	540.0	524.8
15°	736.7	712.4	685.2	658.6	631.0	605.6	582.2	561.4	541.7	521.1	506.7
17.5°	757.1	728.1	695.0	663.2	630.5	600.6	573.6	548.8	526.1	505.1	487.9
20°	769.2	737.2	700.5	664.3	627.6	595.7	566.6	539.1	515.7	493.0	475.2
22.5°	776.0	740.6	700.5	662.6	624.6	590.0	558.1	529.5	504.0	481.2	461.6
25°	778.2	740.3	699.4	655.8	614.2	577.5	544.3	513.3	484.9	462.2	441.4
27.5°	775.1	730.5	688.6	643.9	600.9	562.3	527.5	494.9	466.5	442.1	420.7
30°	770.6	722.8	677.8	631.4	587.9	550.7	514.0	482.8	453.2	427.9	406.4
32.5°	760.7	713.3	664.9	617.4	573.3	535.0	500.2	468.8	439.8	413.9	391.0
35°	741.2	693.2	640.7	591.9	548.6	508.8	476.2	445.9	418.2	390.5	366.4
37.5°	715.5	666.5	614.2	560.8	517.4	479.9	450.0	421.5	394.5	369.2	342.5
40°	691.3	646.6	592.6	539.6	495.1	458.9	431.2	405.4	378.2	353.1	326.4
42.5°	662.0	623.9	569.3	516.1	472.2	437.3	411.5	386.3	361.5	337.2	309.3
45°	613.0	584.1	533.0	481.9	437.6	403.0	379.4	357.1	335.4	312.2	285.9
47.5°	556.8	537.3	493.2	440.8	399.9	368.8	345.9	327.7	309.3	286.1	263.1
50°	517.8	505.3	462.7	414.9	375.8	347.2	323.8	306.7	291.3	269.1	248.5
52.5°	476.2	469.5	433.5	387.8	350.1	322.0	302.0	286.7	271.1	252.6	233.4
55°	412.7	416.3	385.8	346.2	310.7	287.1	268.9	256.1	242.8	227.2	212.3
57.5°	347.9	360.9	340.4	305.7	272.4	250.5	236.8	226.1	214.9	202.0	189.2
60°	309.1	320.0	308.4	277.8	248.7	228.4	215.6	207.3	196.2	184.4	174.7
62.5°	271.2	282.9	276.0	251.3	224.3	206.8	195.5	187.8	179.5	169.2	159.1
65°	223.7	231.2	227.9	210.9	191.7	176.8	166.4	160.7	153.1	145.6	136.6
67.5°	171.3	185.9	184.0	174.9	158.4	146.7	139.9	134.9	128.0	122.4	116.3
70°	140.8	154.3	154.1	146.7	137.7	126.9	122.1	117.9	111.7	106.3	101.3
72.5°	115.3	127.6	129.5	123.8	117.7	109.4	104.9	102.0	96.0	92.3	88.2
75°	80.7	89.7	92.1	92.1	89.2	85.0	80.9	79.0	74.8	71.5	69.1
77.5°	52.9	58.6	62.3	63.1	63.6	62.1	58.8	57.5	54.2	53.1	50.8
80°	37.4	41.2	45.4	46.9	48.0	47.6	46.2	45.2	42.1	40.9	40.0
82.5°	25.8	27.9	31.4	34.6	34.2	35.5	34.2	33.5	31.1	30.7	29.8
85°	13.5	13.7	14.2	16.3	17.5	18.0	18.2	17.8	17.0	17.0	15.4
87.5°	6.7	6.5	6.0	6.0	6.0	6.6	6.7	6.6	6.3	6.2	5.8
90°	10.9	10.9	6.3	6.3	5.5	4.7	2.3	0.8	2.3	4.7	5.5
92.5°	157.9	97.3	57.5	41.3	29.9	20.3	13.0	8.9	13.0	20.3	29.9
95°	294.0	165.8	97.7	64.9	46.1	36.0	28.1	25.8	28.1	36.0	46.1
97.5°	264.3	158.4	106.0	78.5	62.4	53.0	46.3	46.3	46.3	53.0	62.4
100°	248.7	160.3	114.2	89.1	74.3	64.9	59.4	59.4	59.4	64.9	74.3
102.5°	244.3	166.5	124.8	101.0	86.8	78.0	73.2	71.9	73.2	78.0	86.8
105°	246.3	181.4	143.9	121.2	107.1	97.7	93.8	91.5	93.8	97.7	107.1
107.5°	257.9	198.8	164.4	142.0	128.5	118.5	114.6	113.1	114.6	118.5	128.5
110°	266.6	211.9	177.5	156.4	142.3	132.9	129.0	127.5	129.0	132.9	142.3





TEST NUMBER: P332879

CATALOG NUMBER: S124RDIP-S350D810U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	276.0	224.4	191.3	170.1	156.1	147.3	142.8	141.2	142.8	147.3	156.1
115°	290.9	244.0	212.7	191.6	176.7	168.9	163.4	161.1	163.4	168.9	176.7
117.5°	306.0	262.9	233.2	211.3	197.4	188.8	183.9	181.7	183.9	188.8	197.4
120°	316.7	276.0	246.3	224.4	211.1	202.5	197.0	195.5	197.0	202.5	211.1
122.5°	326.7	288.5	258.8	237.5	223.0	215.0	209.6	208.0	209.6	215.0	223.0
125°	341.7	305.7	277.6	255.7	240.8	232.2	227.5	224.4	227.5	232.2	240.8
127.5°	354.7	321.7	294.5	272.4	256.9	247.1	241.5	239.0	241.5	247.1	256.9
130°	362.8	332.3	305.7	283.1	268.2	256.5	250.2	247.1	250.2	256.5	268.2
132.5°	370.9	341.1	314.5	293.1	277.0	265.9	257.7	255.2	257.7	265.9	277.0
135°	381.6	353.4	327.6	307.3	290.9	277.6	269.8	266.6	269.8	277.6	290.9
137.5°	389.1	362.8	338.7	319.3	302.3	289.6	281.0	278.1	281.0	289.6	302.3
140°	394.1	369.1	345.6	326.8	310.4	297.1	288.5	286.2	288.5	297.1	310.4
142.5°	397.8	374.7	351.9	333.7	317.9	305.3	297.3	294.9	297.3	305.3	317.9
145°	401.9	380.8	360.5	343.3	328.4	317.5	309.6	307.3	309.6	317.5	328.4
147.5°	405.5	387.1	368.0	352.5	340.1	328.9	322.0	321.2	322.0	328.9	340.1
150°	407.4	390.2	373.0	358.1	346.4	337.0	330.8	330.0	330.8	337.0	346.4
152.5°	408.6	392.7	377.4	363.8	353.3	344.5	338.3	338.1	338.3	344.5	353.3
155°	409.7	396.4	383.1	371.4	362.8	355.0	350.3	349.5	350.3	355.0	362.8
157.5°	409.7	399.1	387.8	378.6	371.1	365.0	360.6	360.6	360.6	365.0	371.1
160°	409.7	400.3	391.0	382.4	376.1	370.6	367.5	367.5	367.5	370.6	376.1
162.5°	409.7	401.6	392.8	386.1	380.5	375.6	373.1	373.8	373.1	375.6	380.5
165°	408.2	401.9	394.9	390.2	386.3	382.4	380.8	380.8	380.8	382.4	386.3
167.5°	406.3	401.8	396.6	393.0	390.8	387.8	387.1	387.8	387.1	387.8	390.8
170°	405.0	401.1	397.2	394.9	393.3	391.0	390.2	391.0	390.2	391.0	393.3
172.5°	403.8	400.5	397.8	396.1	395.2	393.5	393.3	394.1	393.3	393.5	395.2
175°	401.9	399.6	398.0	398.0	397.2	396.4	396.4	397.2	396.4	396.4	397.2
177.5°	399.9	398.6	398.0	398.0	398.0	397.4	398.0	398.6	398.0	397.4	398.0
180°	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0



TEST NUMBER: P332879

CATALOG NUMBER: S124RDIP-S350D810U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	576.8	574.9	572.5	569.6	566.2	563.2	561.8	563.0	563.6	562.0	561.8
5°	559.2	553.3	548.6	541.5	535.8	531.1	527.8	526.3	526.8	523.0	522.1
7.5°	539.5	532.5	524.7	516.3	508.5	501.5	497.9	495.9	491.8	490.1	487.2
10°	526.8	517.4	509.8	499.8	490.8	482.6	478.5	475.2	471.2	469.3	465.3
12.5°	513.8	502.8	494.4	484.1	474.9	465.0	461.1	455.0	448.7	444.7	439.5
15°	495.3	482.1	471.9	459.6	448.7	437.4	427.2	415.8	411.6	402.6	397.4
17.5°	473.8	460.4	447.8	431.3	414.5	400.3	389.5	378.6	372.1	366.4	363.7
20°	459.6	447.3	429.8	410.6	391.9	376.3	367.5	360.4	353.3	349.3	346.5
22.5°	446.2	430.4	410.1	389.4	370.7	358.5	351.1	343.8	338.0	334.2	330.4
25°	423.6	403.0	381.5	357.8	345.1	334.4	326.4	320.4	316.9	311.9	310.0
27.5°	400.5	375.5	351.8	335.9	322.6	312.8	305.8	301.4	296.9	293.7	291.2
30°	382.7	357.4	336.1	320.9	307.4	299.4	293.7	288.5	284.9	282.3	280.5
32.5°	365.1	339.8	321.9	305.6	294.9	287.1	281.0	277.1	274.3	271.0	269.8
35°	339.6	317.1	301.5	286.8	276.0	268.9	264.1	260.1	257.7	256.8	256.1
37.5°	315.1	296.7	279.9	267.9	258.2	252.6	247.0	245.0	243.4	241.7	242.5
40°	299.6	282.3	267.4	254.7	246.8	240.7	237.4	235.0	233.6	233.6	233.6
42.5°	286.2	269.3	254.7	243.3	235.5	230.3	226.6	224.6	224.1	223.9	225.1
45°	265.3	249.7	235.0	225.5	218.9	213.7	211.6	209.9	209.9	210.9	211.1
47.5°	244.6	230.0	218.2	207.6	201.5	198.3	196.4	195.6	195.7	196.6	197.7
50°	231.9	217.5	205.9	196.4	190.8	187.7	186.0	185.5	186.0	186.0	187.7
52.5°	218.1	205.2	193.8	185.8	179.4	176.5	175.6	174.9	175.2	176.0	176.7
55°	197.9	186.3	175.4	167.8	163.1	161.2	159.0	159.3	158.8	159.3	159.3
57.5°	177.5	167.1	157.0	151.0	146.8	144.1	141.8	142.4	141.7	141.6	141.2
60°	164.5	153.1	145.1	139.6	134.9	132.5	130.4	130.9	130.2	129.7	128.7
62.5°	150.3	140.8	133.1	127.9	124.1	121.4	119.2	118.8	117.1	115.5	113.4
65°	129.7	121.9	115.0	110.1	106.5	104.4	102.7	101.3	97.7	94.0	92.1
67.5°	109.7	104.0	97.6	93.4	90.5	87.8	84.6	82.2	78.9	76.8	75.6
70°	96.8	91.4	85.9	81.9	78.8	76.2	72.7	71.0	68.6	67.7	66.5
72.5°	84.5	79.4	74.4	70.7	67.5	65.4	62.6	61.0	59.9	59.5	58.4
75°	65.8	61.8	58.0	54.7	52.1	50.6	49.5	48.3	47.8	45.7	44.5
77.5°	48.0	45.3	43.0	40.6	38.8	37.8	35.5	34.2	33.4	32.4	32.1
80°	37.4	35.5	33.1	31.7	29.1	28.2	27.2	27.0	26.7	26.5	26.3
82.5°	28.1	26.2	23.9	23.0	22.3	21.7	21.2	20.9	20.7	20.8	20.8
85°	14.2	13.3	13.3	13.0	12.8	12.5	12.3	12.3	12.1	12.3	12.1
87.5°	6.0	5.8	6.7	6.4	6.9	7.2	6.8	7.0	7.3	7.1	7.1
90°	6.3	6.3	10.9	10.9	12.5	14.1	13.3	14.1	14.9	15.6	15.6
92.5°	41.3	57.5	97.3	157.9	217.1	248.0	206.6	153.6	115.6	92.0	76.3
95°	64.9	97.7	165.8	294.0	480.9	637.3	655.3	579.4	458.2	353.4	277.6
97.5°	78.5	106.0	158.4	264.3	450.1	671.2	823.2	856.0	811.0	734.5	652.9
100°	89.1	114.2	160.3	248.7	408.2	628.7	828.8	943.0	958.6	920.3	862.5
102.5°	101.0	124.8	166.5	244.3	380.0	575.5	781.9	938.6	1016.2	1027.3	1003.2
105°	121.2	143.9	181.4	246.3	355.8	512.9	696.7	875.8	1011.0	1088.4	1120.5
107.5°	142.0	164.4	198.8	257.9	351.4	477.9	627.9	786.5	930.5	1039.5	1109.2
110°	156.4	177.5	211.9	266.6	352.6	466.0	593.5	732.7	867.9	981.3	1067.3



TEST NUMBER: P332879

CATALOG NUMBER: S124RDIP-S350D810U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	170.1	191.3	224.4	276.0	356.4	460.4	574.1	693.3	812.9	920.0	1006.0
115°	191.6	212.7	244.0	290.9	363.6	457.4	555.9	653.7	749.9	841.3	916.4
117.5°	211.3	233.2	262.9	306.0	371.3	456.6	547.8	634.3	713.9	785.8	849.5
120°	224.4	246.3	276.0	316.7	376.9	456.6	543.4	625.5	698.3	760.8	816.3
122.5°	237.5	258.8	288.5	326.7	382.5	456.0	538.4	618.0	688.2	745.2	793.8
125°	255.7	277.6	305.7	341.7	391.0	455.1	530.1	605.2	672.5	726.4	769.4
127.5°	272.4	294.5	321.7	354.7	397.7	453.4	519.0	589.6	653.8	707.6	748.5
130°	283.1	305.7	332.3	362.8	402.7	452.7	512.2	577.1	638.8	692.0	733.4
132.5°	293.1	314.5	341.1	370.9	407.1	452.1	505.9	563.9	621.9	673.9	715.3
135°	307.3	327.6	353.4	381.6	413.6	451.2	496.5	545.8	596.6	644.3	683.4
137.5°	319.3	338.7	362.8	389.1	417.5	451.0	488.4	529.4	572.4	612.6	647.9
140°	326.8	345.6	369.1	394.1	420.7	450.4	484.0	520.0	556.7	591.9	624.8
142.5°	333.7	351.9	374.7	397.8	423.2	450.4	480.3	511.2	543.6	573.8	602.2
145°	343.3	360.5	380.8	401.9	424.6	448.8	473.8	498.9	525.5	548.9	570.8
147.5°	352.5	368.0	387.1	405.5	425.4	446.0	468.1	488.7	509.8	528.6	545.8
150°	358.1	373.0	390.2	407.4	425.4	444.1	463.7	482.4	500.4	516.1	530.1
152.5°	363.8	377.4	392.7	408.6	424.1	441.0	458.7	475.6	491.0	505.4	517.0
155°	371.4	383.1	396.4	409.7	422.2	436.3	451.2	465.2	477.8	489.5	498.9
157.5°	378.6	387.8	399.1	409.7	420.2	431.5	443.5	454.1	464.6	474.5	482.0
160°	382.4	391.0	400.3	409.7	418.3	427.7	437.9	447.3	455.9	464.5	470.7
162.5°	386.1	392.8	401.6	409.7	416.5	424.0	432.9	440.4	447.7	454.5	460.1
165°	390.2	394.9	401.9	408.2	412.9	418.3	424.6	430.8	435.5	441.0	444.9
167.5°	393.0	396.6	401.8	406.3	409.1	412.7	417.1	421.6	425.2	429.6	431.9
170°	394.9	397.2	401.1	405.0	406.6	408.9	412.1	416.0	418.3	421.5	423.8
172.5°	396.1	397.8	400.5	403.8	404.1	405.2	407.7	411.0	412.7	414.6	416.3
175°	398.0	398.0	399.6	401.9	401.1	401.1	402.7	404.3	405.0	406.6	406.6
177.5°	398.0	398.0	398.6	399.9	398.6	398.6	399.2	399.9	400.5	400.5	401.1
180°	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0



TEST NUMBER: P332879

CATALOG NUMBER: S124RDIP-S350D810U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	560.7	561.1	559.8	559.4	559.8	561.1	560.7	561.8	562.0	563.6	563.0
5°	520.2	519.7	518.5	518.8	518.5	519.7	520.2	522.1	523.0	526.8	526.3
7.5°	485.5	483.7	484.2	482.3	484.2	483.7	485.5	487.2	490.1	491.8	495.9
10°	464.3	461.7	459.6	457.7	459.6	461.7	464.3	465.3	469.3	471.2	475.2
12.5°	435.4	433.1	430.3	430.8	430.3	433.1	435.4	439.5	444.7	448.7	455.0
15°	394.3	390.7	385.1	385.8	385.1	390.7	394.3	397.4	402.6	411.6	415.8
17.5°	359.5	359.5	356.9	357.6	356.9	359.5	359.5	363.7	366.4	372.1	378.6
20°	341.5	339.9	340.1	339.4	340.1	339.9	341.5	346.5	349.3	353.3	360.4
22.5°	329.0	327.0	325.3	323.9	325.3	327.0	329.0	330.4	334.2	338.0	343.8
25°	307.9	306.5	304.4	303.9	304.4	306.5	307.9	310.0	311.9	316.9	320.4
27.5°	289.3	289.1	288.2	287.1	288.2	289.1	289.3	291.2	293.7	296.9	301.4
30°	278.6	278.1	277.6	276.9	277.6	278.1	278.6	280.5	282.3	284.9	288.5
32.5°	268.9	268.6	268.1	268.2	268.1	268.6	268.9	269.8	271.0	274.3	277.1
35°	255.1	254.9	254.4	254.2	254.4	254.9	255.1	256.1	256.8	257.7	260.1
37.5°	242.3	242.9	242.6	242.5	242.6	242.9	242.3	242.5	241.7	243.4	245.0
40°	233.4	233.6	234.1	233.8	234.1	233.6	233.4	233.6	233.6	233.6	235.0
42.5°	226.0	226.0	226.7	225.9	226.7	226.0	226.0	225.1	223.9	224.1	224.6
45°	212.8	214.2	213.9	213.9	213.9	214.2	212.8	211.1	210.9	209.9	209.9
47.5°	198.3	199.6	199.9	199.8	199.9	199.6	198.3	197.7	196.6	195.7	195.6
50°	188.9	188.4	189.1	188.9	189.1	188.4	188.9	187.7	186.0	186.0	185.5
52.5°	177.3	177.4	177.4	177.1	177.4	177.4	177.3	176.7	176.0	175.2	174.9
55°	159.5	159.8	159.3	159.5	159.3	159.8	159.5	159.3	159.3	158.8	159.3
57.5°	140.2	139.1	139.5	139.0	139.5	139.1	140.2	141.2	141.6	141.7	142.4
60°	126.4	124.5	124.0	123.1	124.0	124.5	126.4	128.7	129.7	130.2	130.9
62.5°	110.9	109.5	107.9	108.7	107.9	109.5	110.9	113.4	115.5	117.1	118.8
65°	90.2	89.2	88.5	89.5	88.5	89.2	90.2	92.1	94.0	97.7	101.3
67.5°	74.6	74.1	74.1	73.7	74.1	74.1	74.6	75.6	76.8	78.9	82.2
70°	66.5	65.8	65.8	65.3	65.8	65.8	66.5	66.5	67.7	68.6	71.0
72.5°	58.2	57.5	57.7	57.4	57.7	57.5	58.2	58.4	59.5	59.9	61.0
75°	43.1	41.9	41.9	42.1	41.9	41.9	43.1	44.5	45.7	47.8	48.3
77.5°	32.1	31.9	32.2	31.8	32.2	31.9	32.1	32.1	32.4	33.4	34.2
80°	26.3	26.0	25.8	26.5	25.8	26.0	26.3	26.3	26.5	26.7	27.0
82.5°	20.4	20.4	20.3	21.2	20.3	20.4	20.4	20.8	20.8	20.7	20.9
85°	12.3	11.8	12.3	11.8	12.3	11.8	12.3	12.1	12.3	12.1	12.3
87.5°	7.6	7.6	7.3	7.4	7.3	7.6	7.6	7.1	7.1	7.3	7.0
90°	16.4	17.2	16.4	16.4	16.4	17.2	16.4	15.6	15.6	14.9	14.1
92.5°	67.1	62.9	60.2	60.2	60.2	62.9	67.1	76.3	92.0	115.6	153.6
95°	239.3	215.0	201.0	190.8	201.0	215.0	239.3	277.6	353.4	458.2	579.4
97.5°	596.8	549.7	526.2	510.0	526.2	549.7	596.8	652.9	734.5	811.0	856.0
100°	794.4	746.7	723.3	717.0	723.3	746.7	794.4	862.5	920.3	958.6	943.0
102.5°	961.5	926.9	902.2	897.2	902.2	926.9	961.5	1003.2	1027.3	1016.2	938.6
105°	1122.1	1115.8	1104.9	1100.2	1104.9	1115.8	1122.1	1120.5	1088.4	1011.0	875.8
107.5°	1147.9	1165.7	1173.5	1175.5	1173.5	1165.7	1147.9	1109.2	1039.5	930.5	786.5
110°	1122.8	1155.7	1169.8	1176.8	1169.8	1155.7	1122.8	1067.3	981.3	867.9	732.7



TEST NUMBER: P332879

CATALOG NUMBER: S124RDIP-S350D810U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1069.0	1108.8	1128.5	1139.9	1128.5	1108.8	1069.0	1006.0	920.0	812.9	693.3
115°	978.2	1025.1	1050.1	1056.4	1050.1	1025.1	978.2	916.4	841.3	749.9	653.7
117.5°	902.2	941.6	966.9	971.8	966.9	941.6	902.2	849.5	785.8	713.9	634.3
120°	860.9	895.3	915.6	924.2	915.6	895.3	860.9	816.3	760.8	698.3	625.5
122.5°	831.5	860.9	878.1	886.7	878.1	860.9	831.5	793.8	745.2	688.2	618.0
125°	800.7	823.4	838.2	842.9	838.2	823.4	800.7	769.4	726.4	672.5	605.2
127.5°	779.9	800.1	812.6	817.3	812.6	800.1	779.9	748.5	707.6	653.8	589.6
130°	765.5	785.1	797.6	802.3	797.6	785.1	765.5	733.4	692.0	638.8	577.1
132.5°	746.7	768.8	780.7	785.4	780.7	768.8	746.7	715.3	673.9	621.9	563.9
135°	714.7	736.6	749.1	753.8	749.1	736.6	714.7	683.4	644.3	596.6	545.8
137.5°	677.1	698.7	709.0	714.7	709.0	698.7	677.1	647.9	612.6	572.4	529.4
140°	652.1	669.3	680.3	686.5	680.3	669.3	652.1	624.8	591.9	556.7	520.0
142.5°	626.5	642.4	652.1	656.5	652.1	642.4	626.5	602.2	573.8	543.6	511.2
145°	590.4	603.6	611.5	615.4	611.5	603.6	590.4	570.8	548.9	525.5	498.9
147.5°	560.2	571.6	577.5	578.9	577.5	571.6	560.2	545.8	528.6	509.8	488.7
150°	542.7	552.8	557.5	558.3	557.5	552.8	542.7	530.1	516.1	500.4	482.4
152.5°	527.6	535.9	538.7	539.5	538.7	535.9	527.6	517.0	505.4	491.0	475.6
155°	506.7	512.9	515.3	515.3	515.3	512.9	506.7	498.9	489.5	477.8	465.2
157.5°	487.9	492.6	494.0	494.0	494.0	492.6	487.9	482.0	474.5	464.6	454.1
160°	475.4	480.1	480.9	480.9	480.9	480.1	475.4	470.7	464.5	455.9	447.3
162.5°	463.5	468.2	469.0	468.4	469.0	468.2	463.5	460.1	454.5	447.7	440.4
165°	448.0	451.2	450.4	449.6	450.4	451.2	448.0	444.9	441.0	435.5	430.8
167.5°	433.5	435.5	435.4	434.7	435.4	435.5	433.5	431.9	429.6	425.2	421.6
170°	425.4	426.1	425.4	425.4	425.4	426.1	425.4	423.8	421.5	418.3	416.0
172.5°	417.2	418.0	417.2	416.0	417.2	418.0	417.2	416.3	414.6	412.7	411.0
175°	406.6	408.2	406.6	405.0	406.6	408.2	406.6	406.6	406.6	405.0	404.3
177.5°	400.5	401.1	399.9	398.6	399.9	401.1	400.5	401.1	400.5	400.5	399.9
180°	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0



TEST NUMBER: P332879

CATALOG NUMBER: S124RDIP-S350D810U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	561.8	563.2	566.2	569.6	572.5	574.9	576.8	579.5	581.9	585.3	588.5
5°	527.8	531.1	535.8	541.5	548.6	553.3	559.2	564.5	572.0	579.6	586.9
7.5°	497.9	501.5	508.5	516.3	524.7	532.5	539.5	548.7	558.7	569.8	582.1
10°	478.5	482.6	490.8	499.8	509.8	517.4	526.8	537.7	549.1	562.6	577.7
12.5°	461.1	465.0	474.9	484.1	494.4	502.8	513.8	524.8	540.0	554.6	571.8
15°	427.2	437.4	448.7	459.6	471.9	482.1	495.3	506.7	521.1	541.7	561.4
17.5°	389.5	400.3	414.5	431.3	447.8	460.4	473.8	487.9	505.1	526.1	548.8
20°	367.5	376.3	391.9	410.6	429.8	447.3	459.6	475.2	493.0	515.7	539.1
22.5°	351.1	358.5	370.7	389.4	410.1	430.4	446.2	461.6	481.2	504.0	529.5
25°	326.4	334.4	345.1	357.8	381.5	403.0	423.6	441.4	462.2	484.9	513.3
27.5°	305.8	312.8	322.6	335.9	351.8	375.5	400.5	420.7	442.1	466.5	494.9
30°	293.7	299.4	307.4	320.9	336.1	357.4	382.7	406.4	427.9	453.2	482.8
32.5°	281.0	287.1	294.9	305.6	321.9	339.8	365.1	391.0	413.9	439.8	468.8
35°	264.1	268.9	276.0	286.8	301.5	317.1	339.6	366.4	390.5	418.2	445.9
37.5°	247.0	252.6	258.2	267.9	279.9	296.7	315.1	342.5	369.2	394.5	421.5
40°	237.4	240.7	246.8	254.7	267.4	282.3	299.6	326.4	353.1	378.2	405.4
42.5°	226.6	230.3	235.5	243.3	254.7	269.3	286.2	309.3	337.2	361.5	386.3
45°	211.6	213.7	218.9	225.5	235.0	249.7	265.3	285.9	312.2	335.4	357.1
47.5°	196.4	198.3	201.5	207.6	218.2	230.0	244.6	263.1	286.1	309.3	327.7
50°	186.0	187.7	190.8	196.4	205.9	217.5	231.9	248.5	269.1	291.3	306.7
52.5°	175.6	176.5	179.4	185.8	193.8	205.2	218.1	233.4	252.6	271.1	286.7
55°	159.0	161.2	163.1	167.8	175.4	186.3	197.9	212.3	227.2	242.8	256.1
57.5°	141.8	144.1	146.8	151.0	157.0	167.1	177.5	189.2	202.0	214.9	226.1
60°	130.4	132.5	134.9	139.6	145.1	153.1	164.5	174.7	184.4	196.2	207.3
62.5°	119.2	121.4	124.1	127.9	133.1	140.8	150.3	159.1	169.2	179.5	187.8
65°	102.7	104.4	106.5	110.1	115.0	121.9	129.7	136.6	145.6	153.1	160.7
67.5°	84.6	87.8	90.5	93.4	97.6	104.0	109.7	116.3	122.4	128.0	134.9
70°	72.7	76.2	78.8	81.9	85.9	91.4	96.8	101.3	106.3	111.7	117.9
72.5°	62.6	65.4	67.5	70.7	74.4	79.4	84.5	88.2	92.3	96.0	102.0
75°	49.5	50.6	52.1	54.7	58.0	61.8	65.8	69.1	71.5	74.8	79.0
77.5°	35.5	37.8	38.8	40.6	43.0	45.3	48.0	50.8	53.1	54.2	57.5
80°	27.2	28.2	29.1	31.7	33.1	35.5	37.4	40.0	40.9	42.1	45.2
82.5°	21.2	21.7	22.3	23.0	23.9	26.2	28.1	29.8	30.7	31.1	33.5
85°	12.3	12.5	12.8	13.0	13.3	13.3	14.2	15.4	17.0	17.0	17.8
87.5°	6.8	7.2	6.9	6.4	6.7	5.8	6.0	5.8	6.2	6.3	6.6
90°	13.3	14.1	12.5	10.9	10.9	6.3	6.3	5.5	4.7	2.3	0.8
92.5°	206.6	248.0	217.1	157.9	97.3	57.5	41.3	29.9	20.3	13.0	8.9
95°	655.3	637.3	480.9	294.0	165.8	97.7	64.9	46.1	36.0	28.1	25.8
97.5°	823.2	671.2	450.1	264.3	158.4	106.0	78.5	62.4	53.0	46.3	46.3
100°	828.8	628.7	408.2	248.7	160.3	114.2	89.1	74.3	64.9	59.4	59.4
102.5°	781.9	575.5	380.0	244.3	166.5	124.8	101.0	86.8	78.0	73.2	71.9
105°	696.7	512.9	355.8	246.3	181.4	143.9	121.2	107.1	97.7	93.8	91.5
107.5°	627.9	477.9	351.4	257.9	198.8	164.4	142.0	128.5	118.5	114.6	113.1
110°	593.5	466.0	352.6	266.6	211.9	177.5	156.4	142.3	132.9	129.0	127.5



TEST NUMBER: P332879

CATALOG NUMBER: S124RDIP-S350D810U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	574.1	460.4	356.4	276.0	224.4	191.3	170.1	156.1	147.3	142.8	141.2
115°	555.9	457.4	363.6	290.9	244.0	212.7	191.6	176.7	168.9	163.4	161.1
117.5°	547.8	456.6	371.3	306.0	262.9	233.2	211.3	197.4	188.8	183.9	181.7
120°	543.4	456.6	376.9	316.7	276.0	246.3	224.4	211.1	202.5	197.0	195.5
122.5°	538.4	456.0	382.5	326.7	288.5	258.8	237.5	223.0	215.0	209.6	208.0
125°	530.1	455.1	391.0	341.7	305.7	277.6	255.7	240.8	232.2	227.5	224.4
127.5°	519.0	453.4	397.7	354.7	321.7	294.5	272.4	256.9	247.1	241.5	239.0
130°	512.2	452.7	402.7	362.8	332.3	305.7	283.1	268.2	256.5	250.2	247.1
132.5°	505.9	452.1	407.1	370.9	341.1	314.5	293.1	277.0	265.9	257.7	255.2
135°	496.5	451.2	413.6	381.6	353.4	327.6	307.3	290.9	277.6	269.8	266.6
137.5°	488.4	451.0	417.5	389.1	362.8	338.7	319.3	302.3	289.6	281.0	278.1
140°	484.0	450.4	420.7	394.1	369.1	345.6	326.8	310.4	297.1	288.5	286.2
142.5°	480.3	450.4	423.2	397.8	374.7	351.9	333.7	317.9	305.3	297.3	294.9
145°	473.8	448.8	424.6	401.9	380.8	360.5	343.3	328.4	317.5	309.6	307.3
147.5°	468.1	446.0	425.4	405.5	387.1	368.0	352.5	340.1	328.9	322.0	321.2
150°	463.7	444.1	425.4	407.4	390.2	373.0	358.1	346.4	337.0	330.8	330.0
152.5°	458.7	441.0	424.1	408.6	392.7	377.4	363.8	353.3	344.5	338.3	338.1
155°	451.2	436.3	422.2	409.7	396.4	383.1	371.4	362.8	355.0	350.3	349.5
157.5°	443.5	431.5	420.2	409.7	399.1	387.8	378.6	371.1	365.0	360.6	360.6
160°	437.9	427.7	418.3	409.7	400.3	391.0	382.4	376.1	370.6	367.5	367.5
162.5°	432.9	424.0	416.5	409.7	401.6	392.8	386.1	380.5	375.6	373.1	373.8
165°	424.6	418.3	412.9	408.2	401.9	394.9	390.2	386.3	382.4	380.8	380.8
167.5°	417.1	412.7	409.1	406.3	401.8	396.6	393.0	390.8	387.8	387.1	387.8
170°	412.1	408.9	406.6	405.0	401.1	397.2	394.9	393.3	391.0	390.2	391.0
172.5°	407.7	405.2	404.1	403.8	400.5	397.8	396.1	395.2	393.5	393.3	394.1
175°	402.7	401.1	401.1	401.9	399.6	398.0	398.0	397.2	396.4	396.4	397.2
177.5°	399.2	398.6	398.6	399.9	398.6	398.0	398.0	398.0	397.4	398.0	398.6
180°	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0



TEST NUMBER: P332879

CATALOG NUMBER: S124RDIP-S350D810U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	591.0	592.7	594.6	598.2	601.2	602.6	605.2	607.1	606.5	609.2	613.7
5°	593.3	599.7	607.1	614.6	623.1	630.2	635.9	641.6	646.1	651.5	659.6
7.5°	592.9	604.3	616.7	630.2	644.2	656.3	667.4	678.8	688.9	699.9	714.4
10°	591.4	606.6	622.0	639.7	657.5	674.3	689.4	703.6	717.1	731.5	749.8
12.5°	589.7	607.1	625.7	647.1	669.2	689.4	707.2	727.7	744.6	763.2	784.2
15°	582.2	605.6	631.0	658.6	685.2	712.4	736.7	761.8	785.3	807.5	834.0
17.5°	573.6	600.6	630.5	663.2	695.0	728.1	757.1	788.7	812.6	842.5	867.1
20°	566.6	595.7	627.6	664.3	700.5	737.2	769.2	801.4	828.3	858.4	889.6
22.5°	558.1	590.0	624.6	662.6	700.5	740.6	776.0	808.0	841.4	875.2	907.4
25°	544.3	577.5	614.2	655.8	699.4	740.3	778.2	817.9	853.9	890.6	919.5
27.5°	527.5	562.3	600.9	643.9	688.6	730.5	775.1	817.5	853.7	889.0	914.2
30°	514.0	550.7	587.9	631.4	677.8	722.8	770.6	813.0	851.1	882.8	897.0
32.5°	500.2	535.0	573.3	617.4	664.9	713.3	760.7	804.1	839.3	858.3	858.7
35°	476.2	508.8	548.6	591.9	640.7	693.2	741.2	783.8	805.4	807.0	783.8
37.5°	450.0	479.9	517.4	560.8	614.2	666.5	715.5	743.9	751.1	727.0	684.2
40°	431.2	458.9	495.1	539.6	592.6	646.6	691.3	712.1	704.6	665.5	617.7
42.5°	411.5	437.3	472.2	516.1	569.3	623.9	662.0	673.1	653.1	608.0	552.0
45°	379.4	403.0	437.6	481.9	533.0	584.1	613.0	607.3	573.9	520.4	457.7
47.5°	345.9	368.8	399.9	440.8	493.2	537.3	556.8	539.7	492.2	433.4	382.4
50°	323.8	347.2	375.8	414.9	462.7	505.3	517.8	491.8	439.0	382.5	335.6
52.5°	302.0	322.0	350.1	387.8	433.5	469.5	476.2	446.2	391.7	341.0	299.4
55°	268.9	287.1	310.7	346.2	385.8	416.3	412.7	374.2	324.7	281.4	248.7
57.5°	236.8	250.5	272.4	305.7	340.4	360.9	347.9	315.0	268.9	233.4	205.9
60°	215.6	228.4	248.7	277.8	308.4	320.0	309.1	273.4	236.9	204.5	181.3
62.5°	195.5	206.8	224.3	251.3	276.0	282.9	271.2	240.0	207.2	179.5	160.3
65°	166.4	176.8	191.7	210.9	227.9	231.2	223.7	191.7	166.9	143.7	130.4
67.5°	139.9	146.7	158.4	174.9	184.0	185.9	171.3	151.2	129.3	115.1	105.1
70°	122.1	126.9	137.7	146.7	154.1	154.3	140.8	124.7	107.9	96.3	89.0
72.5°	104.9	109.4	117.7	123.8	129.5	127.6	115.3	102.6	89.0	80.2	74.8
75°	80.9	85.0	89.2	92.1	92.1	89.7	80.7	71.2	63.4	58.2	56.6
77.5°	58.8	62.1	63.6	63.1	62.3	58.6	52.9	46.7	43.9	41.5	40.2
80°	46.2	47.6	48.0	46.9	45.4	41.2	37.4	34.8	32.2	31.2	30.8
82.5°	34.2	35.5	34.2	34.6	31.4	27.9	25.8	24.9	23.9	23.5	23.0
85°	18.2	18.0	17.5	16.3	14.2	13.7	13.5	13.3	12.8	13.0	12.5
87.5°	6.7	6.6	6.0	6.0	6.0	6.5	6.7	7.0	7.4	7.0	7.5
90°	2.3	4.7	5.5	6.3	6.3	10.9	10.9	12.5	14.1	13.3	14.1
92.5°	13.0	20.3	29.9	41.3	57.5	97.3	157.9	217.1	248.0	206.6	153.6
95°	28.1	36.0	46.1	64.9	97.7	165.8	294.0	480.9	637.3	655.3	579.4
97.5°	46.3	53.0	62.4	78.5	106.0	158.4	264.3	450.1	671.2	823.2	856.0
100°	59.4	64.9	74.3	89.1	114.2	160.3	248.7	408.2	628.7	828.8	943.0
102.5°	73.2	78.0	86.8	101.0	124.8	166.5	244.3	380.0	575.5	781.9	938.6
105°	93.8	97.7	107.1	121.2	143.9	181.4	246.3	355.8	512.9	696.7	875.8
107.5°	114.6	118.5	128.5	142.0	164.4	198.8	257.9	351.4	477.9	627.9	786.5
110°	129.0	132.9	142.3	156.4	177.5	211.9	266.6	352.6	466.0	593.5	732.7





TEST NUMBER: P332879

CATALOG NUMBER: S124RDIP-S350D810U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	142.8	147.3	156.1	170.1	191.3	224.4	276.0	356.4	460.4	574.1	693.3
115°	163.4	168.9	176.7	191.6	212.7	244.0	290.9	363.6	457.4	555.9	653.7
117.5°	183.9	188.8	197.4	211.3	233.2	262.9	306.0	371.3	456.6	547.8	634.3
120°	197.0	202.5	211.1	224.4	246.3	276.0	316.7	376.9	456.6	543.4	625.5
122.5°	209.6	215.0	223.0	237.5	258.8	288.5	326.7	382.5	456.0	538.4	618.0
125°	227.5	232.2	240.8	255.7	277.6	305.7	341.7	391.0	455.1	530.1	605.2
127.5°	241.5	247.1	256.9	272.4	294.5	321.7	354.7	397.7	453.4	519.0	589.6
130°	250.2	256.5	268.2	283.1	305.7	332.3	362.8	402.7	452.7	512.2	577.1
132.5°	257.7	265.9	277.0	293.1	314.5	341.1	370.9	407.1	452.1	505.9	563.9
135°	269.8	277.6	290.9	307.3	327.6	353.4	381.6	413.6	451.2	496.5	545.8
137.5°	281.0	289.6	302.3	319.3	338.7	362.8	389.1	417.5	451.0	488.4	529.4
140°	288.5	297.1	310.4	326.8	345.6	369.1	394.1	420.7	450.4	484.0	520.0
142.5°	297.3	305.3	317.9	333.7	351.9	374.7	397.8	423.2	450.4	480.3	511.2
145°	309.6	317.5	328.4	343.3	360.5	380.8	401.9	424.6	448.8	473.8	498.9
147.5°	322.0	328.9	340.1	352.5	368.0	387.1	405.5	425.4	446.0	468.1	488.7
150°	330.8	337.0	346.4	358.1	373.0	390.2	407.4	425.4	444.1	463.7	482.4
152.5°	338.3	344.5	353.3	363.8	377.4	392.7	408.6	424.1	441.0	458.7	475.6
155°	350.3	355.0	362.8	371.4	383.1	396.4	409.7	422.2	436.3	451.2	465.2
157.5°	360.6	365.0	371.1	378.6	387.8	399.1	409.7	420.2	431.5	443.5	454.1
160°	367.5	370.6	376.1	382.4	391.0	400.3	409.7	418.3	427.7	437.9	447.3
162.5°	373.1	375.6	380.5	386.1	392.8	401.6	409.7	416.5	424.0	432.9	440.4
165°	380.8	382.4	386.3	390.2	394.9	401.9	408.2	412.9	418.3	424.6	430.8
167.5°	387.1	387.8	390.8	393.0	396.6	401.8	406.3	409.1	412.7	417.1	421.6
170°	390.2	391.0	393.3	394.9	397.2	401.1	405.0	406.6	408.9	412.1	416.0
172.5°	393.3	393.5	395.2	396.1	397.8	400.5	403.8	404.1	405.2	407.7	411.0
175°	396.4	396.4	397.2	398.0	398.0	399.6	401.9	401.1	401.1	402.7	404.3
177.5°	398.0	397.4	398.0	398.0	398.0	398.6	399.9	398.6	398.6	399.2	399.9
180°	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0



TEST NUMBER: P332879

CATALOG NUMBER: S124RDIP-S350D810U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	616.2	616.9	617.5	619.4	619.6	621.3	619.6
5°	667.2	670.5	675.7	680.9	681.4	684.7	678.8
7.5°	724.3	732.0	736.8	745.2	748.5	750.6	747.2
10°	763.7	770.8	783.4	789.5	795.7	796.6	793.8
12.5°	801.8	813.0	822.9	834.6	834.3	842.6	839.6
15°	852.5	864.1	877.8	890.8	895.5	895.5	899.3
17.5°	888.6	909.9	924.1	934.3	945.5	947.4	946.1
20°	913.1	936.0	951.2	964.4	972.0	974.1	974.1
22.5°	931.2	950.8	965.6	977.5	983.7	986.2	985.5
25°	943.8	960.6	969.6	973.2	974.8	974.4	969.9
27.5°	926.6	925.8	920.2	909.3	901.1	896.1	890.4
30°	893.7	881.3	867.1	851.5	831.4	816.0	811.3
32.5°	844.6	817.0	792.9	766.9	745.3	729.9	723.4
35°	749.8	706.0	670.2	639.0	616.3	602.1	597.3
37.5°	637.2	594.8	550.6	520.3	501.4	487.1	481.8
40°	565.6	519.5	480.9	452.5	433.1	419.1	418.9
42.5°	500.3	456.2	419.9	399.5	378.6	369.3	369.3
45°	409.7	374.4	343.6	327.5	315.0	307.4	305.3
47.5°	339.2	310.0	289.5	276.7	266.5	261.7	258.5
50°	299.6	274.1	257.7	246.6	240.9	234.8	234.3
52.5°	266.7	246.0	233.3	224.3	217.1	213.4	213.5
55°	224.1	207.8	198.8	191.9	186.3	183.4	182.2
57.5°	188.8	176.6	170.0	163.7	161.3	159.1	158.5
60°	166.9	158.6	152.4	147.4	143.9	143.2	142.9
62.5°	148.7	140.0	135.8	131.9	129.3	128.2	127.8
65°	122.6	116.2	112.4	109.3	108.4	106.7	106.5
67.5°	98.8	95.0	92.5	90.4	89.1	89.0	89.0
70°	84.3	82.1	80.0	78.8	78.1	77.6	77.6
72.5°	71.8	70.2	68.4	67.8	67.7	67.2	67.0
75°	54.7	53.0	53.3	52.1	51.1	49.9	49.2
77.5°	38.8	37.6	37.3	37.2	36.4	36.3	36.6
80°	30.1	28.9	28.6	28.9	28.6	27.9	27.9
82.5°	22.9	21.9	21.6	21.5	21.3	21.5	21.1
85°	12.3	11.8	11.8	11.8	12.3	12.1	11.8
87.5°	7.3	7.3	7.5	7.4	7.6	7.3	7.4
90°	14.9	15.6	15.6	16.4	17.2	16.4	16.4
92.5°	115.6	92.0	76.3	67.1	62.9	60.2	60.2
95°	458.2	353.4	277.6	239.3	215.0	201.0	190.8
97.5°	811.0	734.5	652.9	596.8	549.7	526.2	510.0
100°	958.6	920.3	862.5	794.4	746.7	723.3	717.0
102.5°	1016.2	1027.3	1003.2	961.5	926.9	902.2	897.2
105°	1011.0	1088.4	1120.5	1122.1	1115.8	1104.9	1100.2
107.5°	930.5	1039.5	1109.2	1147.9	1165.7	1173.5	1175.5
110°	867.9	981.3	1067.3	1122.8	1155.7	1169.8	1176.8



TEST NUMBER: P332879

CATALOG NUMBER: S124RDIP-S350D810U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	812.9	920.0	1006.0	1069.0	1108.8	1128.5	1139.9
115°	749.9	841.3	916.4	978.2	1025.1	1050.1	1056.4
117.5°	713.9	785.8	849.5	902.2	941.6	966.9	971.8
120°	698.3	760.8	816.3	860.9	895.3	915.6	924.2
122.5°	688.2	745.2	793.8	831.5	860.9	878.1	886.7
125°	672.5	726.4	769.4	800.7	823.4	838.2	842.9
127.5°	653.8	707.6	748.5	779.9	800.1	812.6	817.3
130°	638.8	692.0	733.4	765.5	785.1	797.6	802.3
132.5°	621.9	673.9	715.3	746.7	768.8	780.7	785.4
135°	596.6	644.3	683.4	714.7	736.6	749.1	753.8
137.5°	572.4	612.6	647.9	677.1	698.7	709.0	714.7
140°	556.7	591.9	624.8	652.1	669.3	680.3	686.5
142.5°	543.6	573.8	602.2	626.5	642.4	652.1	656.5
145°	525.5	548.9	570.8	590.4	603.6	611.5	615.4
147.5°	509.8	528.6	545.8	560.2	571.6	577.5	578.9
150°	500.4	516.1	530.1	542.7	552.8	557.5	558.3
152.5°	491.0	505.4	517.0	527.6	535.9	538.7	539.5
155°	477.8	489.5	498.9	506.7	512.9	515.3	515.3
157.5°	464.6	474.5	482.0	487.9	492.6	494.0	494.0
160°	455.9	464.5	470.7	475.4	480.1	480.9	480.9
162.5°	447.7	454.5	460.1	463.5	468.2	469.0	468.4
165°	435.5	441.0	444.9	448.0	451.2	450.4	449.6
167.5°	425.2	429.6	431.9	433.5	435.5	435.4	434.7
170°	418.3	421.5	423.8	425.4	426.1	425.4	425.4
172.5°	412.7	414.6	416.3	417.2	418.0	417.2	416.0
175°	405.0	406.6	406.6	406.6	408.2	406.6	405.0
177.5°	400.5	400.5	401.1	400.5	401.1	399.9	398.6
180°	398.0	398.0	398.0	398.0	398.0	398.0	398.0

(END OF REPORT)