

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332921

Luminaire Tested: **S124RDIP-S575D1205U835-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332921  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIP-S575D1205U835-4F0-1E-UDD-A4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 575 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6745.9 lumens  
Efficiency: N/A  
Efficacy: 136.6 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: Semi-Indirect  
  
Input Watts (W): 49.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332921

CATALOG NUMBER: S124RDIP-S575D1205U835-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P332921

CATALOG NUMBER: S124RDIP-S575D1205U835-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	43	43	43	36
1	95	91	87	84	86	83	79	77	67	65	63	52	51	50	39	38	37	31
2	87	80	74	69	78	72	68	63	59	55	52	46	44	42	35	33	32	27
3	79	70	63	58	72	64	58	53	52	48	44	41	38	36	31	29	28	23
4	73	62	55	49	66	57	50	45	46	42	38	37	34	31	28	26	24	20
5	67	56	48	42	60	51	44	39	42	37	33	33	30	27	25	23	21	17
6	61	50	42	37	56	46	39	34	38	32	29	30	26	24	23	20	19	15
7	57	45	37	32	51	41	35	30	34	29	25	27	24	21	21	18	17	14
8	53	41	33	28	48	37	31	26	31	26	22	25	21	19	19	17	15	12
9	49	37	30	25	44	34	28	23	28	23	20	23	19	17	18	15	13	11
10	46	34	27	22	41	31	25	21	26	21	18	21	18	15	17	14	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	7796	7796	7796	7796
5°	9043	7819	6912	7819
10°	10698	7785	6169	7785
15°	12357	7713	5300	7713
20°	13759	7614	4793	7614
25°	14203	7517	4450	7517
30°	12433	7399	4243	7399
35°	9678	7224	4119	7224
40°	7258	7024	4051	7024
45°	5730	6703	4015	6703
50°	4838	6332	3900	6332
55°	4217	5925	3690	5925
60°	3794	5503	3266	5503
65°	3345	5047	2810	5047
70°	3012	4574	2535	4574
75°	2523	4055	2162	4055
80°	2134	3454	2027	3454
85°	1806	2705	1806	2705



TEST NUMBER: P332921

CATALOG NUMBER: S124RDIP-S575D1205U835-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	93.6	1.4
10°-20°	282.2	4.2
20°-30°	441.5	6.5
30°-40°	490.8	7.3
40°-50°	435.4	6.5
50°-60°	339.3	5.0
60°-70°	222.1	3.3
70°-80°	109.2	1.6
80°-90°	30.2	0.4
90°-100°	427.2	6.3
100°-110°	889.1	13.2
110°-120°	796.4	11.8
120°-130°	669.9	9.9
130°-140°	558.5	8.3
140°-150°	426.7	6.3
150°-160°	299.9	4.4
160°-170°	176.4	2.6
170°-180°	57.4	0.9
0°-30°	817.3	12.1
0°-40°	1308.0	19.4
0°-60°	2082.7	30.9
0°-90°	2444.3	36.2
90°-120°	2112.7	31.3
90°-150°	3767.8	55.9
90°-180°	4302.0	63.8
0°-180°	6745.9	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	966	966	966	966	966	
5°	1116	965	853	965	1116	113
15°	1478	923	634	923	1478	420
25°	1594	844	500	844	1594	707
35°	982	733	418	733	982	616
45°	502	587	352	587	502	397
55°	300	421	262	421	300	273
65°	175	264	147	264	175	176
75°	81	130	69	130	81	89
85°	20	29	20	29	20	23
90°	24	1	24	1	24	21
95°	284	38	284	38	284	440
105°	1635	136	1635	136	1635	1616
115°	1570	239	1570	239	1570	1558
125°	1253	334	1253	334	1253	1138
135°	1120	396	1120	396	1120	865
145°	914	457	914	457	914	580
155°	766	519	766	519	766	357
165°	668	566	668	566	668	191
175°	602	590	602	590	602	59
180°	592	592	592	592	592	



TEST NUMBER: P332921

CATALOG NUMBER: S124RDIP-S575D1205U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7
2.5°	1018.6	1021.4	1018.6	1018.3	1015.2	1014.3	1013.0	1009.0	1001.5	997.1	998.1
5°	1115.9	1125.6	1120.2	1119.4	1110.8	1102.3	1096.8	1084.4	1071.1	1062.2	1054.8
7.5°	1228.4	1234.0	1230.6	1225.1	1211.3	1203.4	1190.8	1174.4	1150.7	1132.5	1116.0
10°	1305.0	1309.6	1308.1	1298.0	1287.9	1267.2	1255.6	1232.6	1202.6	1178.9	1156.7
12.5°	1380.3	1385.3	1371.6	1372.1	1352.9	1336.6	1318.1	1289.3	1254.6	1224.0	1196.3
15°	1478.5	1472.3	1472.3	1464.5	1443.1	1420.5	1401.5	1371.1	1327.5	1291.0	1252.5
17.5°	1555.4	1557.6	1554.4	1536.0	1519.2	1495.9	1460.9	1425.5	1385.0	1335.9	1296.6
20°	1601.5	1601.5	1598.0	1585.5	1563.7	1538.8	1501.1	1462.6	1411.2	1361.8	1317.4
22.5°	1620.1	1621.4	1617.3	1607.0	1587.4	1563.1	1531.0	1491.8	1438.9	1383.3	1328.3
25°	1594.5	1601.8	1602.6	1599.9	1594.1	1579.3	1551.7	1511.6	1464.1	1403.8	1344.7
27.5°	1463.9	1473.2	1481.4	1494.8	1512.7	1522.1	1523.3	1502.9	1461.5	1403.5	1344.0
30°	1333.8	1341.5	1366.8	1399.9	1425.6	1448.9	1469.2	1474.6	1451.3	1399.1	1336.5
32.5°	1189.3	1199.9	1225.2	1260.8	1303.6	1343.1	1388.6	1411.7	1411.1	1379.8	1321.9
35°	982.0	989.8	1013.2	1050.5	1101.9	1160.6	1232.6	1288.6	1326.8	1324.0	1288.6
37.5°	792.0	800.8	824.4	855.4	905.2	977.9	1047.6	1124.8	1195.3	1234.9	1223.0
40°	688.7	689.1	712.0	743.9	790.6	854.0	929.9	1015.5	1094.1	1158.3	1170.7
42.5°	607.1	607.2	622.4	656.8	690.4	750.1	822.5	907.5	999.5	1073.6	1106.6
45°	501.9	505.4	517.9	538.5	564.9	615.5	673.5	752.5	855.6	943.5	998.4
47.5°	425.0	430.2	438.1	454.9	476.0	509.7	557.6	628.6	712.5	809.2	887.3
50°	385.2	386.0	396.1	405.4	423.7	450.6	492.6	551.7	628.8	721.7	808.5
52.5°	351.0	350.8	356.9	368.7	383.6	404.5	438.4	492.3	560.6	643.9	733.5
55°	299.6	301.5	306.2	315.5	326.8	341.6	368.5	408.9	462.6	533.8	615.1
57.5°	260.5	261.5	265.2	269.2	279.5	290.3	310.4	338.5	383.8	442.1	517.9
60°	235.0	235.4	236.6	242.4	250.6	260.7	274.3	298.0	336.2	389.5	449.4
62.5°	210.1	210.8	212.6	216.9	223.2	230.2	244.4	263.5	295.1	340.6	394.6
65°	175.1	175.5	178.2	179.8	184.8	191.0	201.5	214.4	236.2	274.3	315.2
67.5°	146.3	146.3	146.4	148.6	152.1	156.2	162.5	172.8	189.2	212.6	248.6
70°	127.6	127.6	128.4	129.6	131.5	135.0	138.5	146.3	158.4	177.4	205.0
72.5°	110.2	110.5	111.3	111.5	112.5	115.4	118.0	122.9	131.9	146.3	168.6
75°	80.9	82.1	84.0	85.6	87.5	87.2	89.9	93.0	95.7	104.3	117.1
77.5°	60.2	59.6	59.8	61.2	61.4	61.8	63.7	66.1	68.2	72.2	76.8
80°	45.9	45.9	47.1	47.5	47.1	47.5	49.4	50.6	51.4	52.9	57.2
82.5°	34.7	35.3	34.9	35.3	35.6	36.0	37.6	37.8	38.6	39.2	41.0
85°	19.5	19.8	20.2	19.5	19.5	19.5	20.2	20.6	21.4	21.0	21.8
87.5°	11.7	11.4	12.0	11.7	11.8	11.5	11.6	12.0	11.1	11.7	11.2
90°	24.4	24.4	25.6	24.4	23.2	23.2	22.1	20.9	19.8	20.9	18.6
92.5°	89.5	89.5	93.4	99.7	113.4	136.7	171.7	228.2	307.0	368.6	322.6
95°	283.5	298.6	319.6	355.6	412.5	525.2	680.9	861.0	973.8	947.0	714.6
97.5°	757.9	782.0	816.9	886.8	970.3	1091.6	1205.2	1272.2	1223.4	997.5	668.8
100°	1065.6	1074.9	1109.7	1180.6	1281.7	1367.7	1424.6	1401.4	1231.7	934.2	606.6
102.5°	1333.3	1340.7	1377.4	1428.8	1490.8	1526.6	1510.1	1394.9	1162.0	855.2	564.7
105°	1634.9	1641.9	1658.2	1667.5	1665.1	1617.5	1502.5	1301.4	1035.3	762.3	528.7
107.5°	1747.0	1743.9	1732.3	1705.8	1648.4	1544.8	1382.8	1168.7	933.1	710.2	522.2
110°	1748.8	1738.4	1717.4	1668.6	1586.1	1458.3	1289.8	1088.8	882.0	692.6	524.1



TEST NUMBER: P332921

CATALOG NUMBER: S124RDIP-S575D1205U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1694.0	1677.0	1647.7	1588.7	1495.0	1367.2	1208.0	1030.2	853.1	684.2	529.6
115°	1569.9	1560.6	1523.4	1453.7	1361.9	1250.3	1114.4	971.4	826.2	679.8	540.3
117.5°	1444.1	1436.9	1399.3	1340.7	1262.4	1167.8	1060.9	942.6	814.1	678.6	551.7
120°	1373.5	1360.7	1330.5	1279.4	1213.1	1130.6	1037.7	929.6	807.6	678.6	560.1
122.5°	1317.7	1304.9	1279.4	1235.7	1179.7	1107.4	1022.8	918.4	800.2	677.7	568.5
125°	1252.6	1245.7	1223.6	1189.9	1143.4	1079.5	999.3	899.4	787.8	676.3	581.0
127.5°	1214.5	1207.6	1189.0	1159.0	1112.3	1051.6	971.7	876.1	771.3	673.7	591.0
130°	1192.2	1185.2	1166.6	1137.6	1090.0	1028.4	949.4	857.6	761.1	672.8	598.4
132.5°	1167.1	1160.1	1142.5	1109.7	1063.0	1001.4	924.3	838.0	751.8	671.9	604.9
135°	1120.2	1113.2	1094.6	1062.1	1015.6	957.5	886.6	811.1	737.9	670.5	614.7
137.5°	1062.1	1053.7	1038.4	1006.3	962.8	910.3	850.6	786.7	725.8	670.2	620.5
140°	1020.2	1010.9	994.7	969.1	928.4	879.6	827.3	772.7	719.3	669.3	625.2
142.5°	975.6	969.1	954.7	931.0	895.0	852.7	807.8	759.7	713.7	669.3	628.9
145°	914.5	908.7	897.1	877.3	848.3	815.7	780.9	741.4	704.2	667.0	631.0
147.5°	860.3	858.3	849.4	832.5	811.1	785.5	757.6	726.3	695.6	662.8	632.1
150°	829.7	828.5	821.5	806.4	787.8	766.9	743.7	717.0	689.1	660.0	632.1
152.5°	801.8	800.6	796.4	784.1	768.3	751.1	729.7	706.7	681.6	655.4	630.3
155°	765.8	765.8	762.3	753.0	741.4	727.4	710.0	691.4	670.5	648.4	627.5
157.5°	734.2	734.2	732.1	725.1	716.3	705.1	690.5	674.9	659.1	641.2	624.5
160°	714.6	714.6	713.5	706.5	699.5	690.2	677.4	664.7	650.7	635.6	621.7
162.5°	696.0	697.0	695.8	688.8	683.7	675.4	665.4	654.4	643.3	630.0	618.9
165°	668.2	669.3	670.5	665.8	661.2	655.4	647.2	640.3	631.0	621.7	613.5
167.5°	646.1	647.0	647.2	644.2	641.9	638.4	631.9	626.6	619.8	613.3	608.0
170°	632.1	632.1	633.3	632.1	629.8	626.3	621.7	618.2	612.4	607.7	604.2
172.5°	618.2	620.0	621.2	620.0	618.6	616.1	613.3	610.7	605.9	602.1	600.5
175°	601.9	604.2	606.6	604.2	604.2	604.2	601.9	600.8	598.4	596.1	596.1
177.5°	592.4	594.2	596.1	595.2	596.1	595.2	595.2	594.2	593.3	592.4	592.4
180°	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5



TEST NUMBER: P332921

CATALOG NUMBER: S124RDIP-S575D1205U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7
2.5°	995.0	990.6	988.4	983.4	977.5	974.4	971.6	967.6	962.3	956.7	952.6
5°	1045.5	1036.1	1024.4	1010.4	998.0	985.9	975.4	964.9	952.9	940.4	928.0
7.5°	1097.3	1078.9	1059.1	1036.1	1013.8	993.5	974.8	956.9	936.7	918.5	902.0
10°	1133.4	1108.5	1080.9	1051.7	1022.5	997.2	972.3	949.7	924.8	902.7	884.0
12.5°	1162.7	1133.4	1100.2	1063.8	1028.7	998.1	969.5	940.1	911.8	887.7	862.8
15°	1211.2	1171.1	1126.4	1082.8	1037.3	995.7	957.1	922.9	890.6	856.8	833.0
17.5°	1244.6	1197.0	1142.7	1090.3	1036.5	987.4	943.0	902.2	864.9	830.4	802.1
20°	1264.5	1212.0	1151.7	1092.1	1031.8	979.3	931.5	886.3	847.8	810.5	781.3
22.5°	1275.7	1217.6	1151.7	1089.3	1026.9	970.0	917.5	870.5	828.5	791.2	758.9
25°	1279.3	1217.0	1149.7	1078.1	1009.7	949.4	894.9	843.9	797.2	759.9	725.6
27.5°	1274.3	1201.0	1132.1	1058.6	988.0	924.4	867.2	813.6	766.9	726.8	691.7
30°	1266.8	1188.3	1114.3	1038.1	966.5	905.4	845.1	793.7	745.1	703.5	668.1
32.5°	1250.7	1172.7	1093.2	1015.0	942.5	879.6	822.4	770.7	723.0	680.4	642.8
35°	1218.6	1139.6	1053.2	973.1	901.9	836.5	782.8	733.0	687.5	642.0	602.3
37.5°	1176.3	1095.7	1009.7	922.0	850.7	789.0	739.7	693.0	648.5	607.0	563.0
40°	1136.5	1063.0	974.3	887.1	814.0	754.4	708.9	666.5	621.8	580.5	536.5
42.5°	1088.3	1025.6	936.0	848.5	776.3	718.9	676.5	635.1	594.4	554.4	508.5
45°	1007.7	960.3	876.2	792.2	719.4	662.6	623.7	587.1	551.3	513.2	470.0
47.5°	915.4	883.3	810.8	724.7	657.4	606.3	568.7	538.8	508.5	470.4	432.5
50°	851.3	830.7	760.7	682.1	617.9	570.8	532.3	504.2	479.0	442.4	408.5
52.5°	782.8	771.9	712.7	637.5	575.5	529.4	496.5	471.3	445.7	415.3	383.6
55°	678.6	684.4	634.2	569.2	510.9	472.0	442.0	421.0	399.2	373.5	349.0
57.5°	571.9	593.3	559.6	502.5	447.8	411.9	389.3	371.6	353.4	332.0	311.1
60°	508.1	526.0	507.0	456.8	408.9	375.5	354.5	340.8	322.5	303.1	287.1
62.5°	445.9	465.0	453.7	413.2	368.8	340.0	321.5	308.8	295.2	278.2	261.6
65°	367.7	380.1	374.7	346.7	315.2	290.6	273.5	264.2	251.7	239.3	224.5
67.5°	281.6	305.7	302.5	287.6	260.4	241.2	230.0	221.8	210.4	201.2	191.1
70°	231.5	253.7	253.3	241.2	226.4	208.5	200.8	193.8	183.6	174.7	166.5
72.5°	189.5	209.8	212.8	203.6	193.5	179.9	172.4	167.6	157.8	151.7	145.0
75°	132.7	147.5	151.4	151.4	146.7	139.7	133.1	130.0	122.9	117.5	113.6
77.5°	87.0	96.3	102.4	103.8	104.5	102.2	96.7	94.5	89.2	87.2	83.5
80°	61.5	67.7	74.7	77.0	79.0	78.2	75.9	74.3	69.3	67.3	65.8
82.5°	42.5	45.9	51.7	56.8	56.3	58.3	56.3	55.0	51.2	50.5	48.9
85°	22.2	22.6	23.3	26.8	28.8	29.6	30.0	29.2	28.0	28.0	25.3
87.5°	10.7	10.4	9.6	9.6	9.7	10.7	11.0	10.8	10.3	10.1	9.4
90°	16.3	16.3	9.3	9.3	8.1	7.0	3.5	1.2	3.5	7.0	8.1
92.5°	234.7	144.6	85.5	61.4	44.4	30.2	19.3	13.2	19.3	30.2	44.4
95°	436.9	246.3	145.3	96.4	68.6	53.5	41.8	38.3	41.8	53.5	68.6
97.5°	392.8	235.4	157.6	116.7	92.7	78.8	68.8	68.8	68.8	78.8	92.7
100°	369.5	238.2	169.7	132.5	110.4	96.4	88.3	88.3	88.3	96.4	110.4
102.5°	363.0	247.5	185.5	150.1	129.0	116.0	108.8	106.9	108.8	116.0	129.0
105°	366.0	269.6	213.8	180.1	159.2	145.3	139.4	136.0	139.4	145.3	159.2
107.5°	383.2	295.4	244.3	211.0	191.0	176.2	170.3	168.0	170.3	176.2	191.0
110°	396.2	314.9	263.8	232.4	211.5	197.5	191.7	189.4	191.7	197.5	211.5





TEST NUMBER: P332921

CATALOG NUMBER: S124RDIP-S575D1205U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	410.2	333.5	284.2	252.9	231.9	218.9	212.2	209.9	212.2	218.9	231.9
115°	432.3	362.5	316.1	284.7	262.6	251.0	242.9	239.4	242.9	251.0	262.6
117.5°	454.8	390.7	346.5	314.0	293.3	280.5	273.3	270.0	273.3	280.5	293.3
120°	470.6	410.2	366.0	333.5	313.7	301.0	292.8	290.5	292.8	301.0	313.7
122.5°	485.5	428.8	384.6	353.0	331.4	319.6	311.4	309.1	311.4	319.6	331.4
125°	507.8	454.3	412.5	380.0	357.9	345.1	338.1	333.5	338.1	345.1	357.9
127.5°	527.1	478.0	437.6	404.8	381.8	367.2	358.8	355.1	358.8	367.2	381.8
130°	539.2	493.9	454.3	420.6	398.6	381.1	371.8	367.2	371.8	381.1	398.6
132.5°	551.3	506.9	467.4	435.5	411.6	395.1	383.0	379.3	383.0	395.1	411.6
135°	567.1	525.2	486.9	456.7	432.3	412.5	400.9	396.2	400.9	412.5	432.3
137.5°	578.2	539.2	503.4	474.6	449.2	430.4	417.6	413.2	417.6	430.4	449.2
140°	585.6	548.5	513.6	485.7	461.3	441.6	428.8	425.3	428.8	441.6	461.3
142.5°	591.2	556.8	522.9	495.9	472.5	453.6	441.8	438.3	441.8	453.6	472.5
145°	597.3	565.9	535.7	510.1	488.0	471.8	460.2	456.7	460.2	471.8	488.0
147.5°	602.6	575.2	546.8	523.8	505.5	488.7	478.5	477.3	478.5	488.7	505.5
150°	605.4	579.8	554.3	532.2	514.8	500.8	491.5	490.4	491.5	500.8	514.8
152.5°	607.3	583.6	560.8	540.6	525.0	512.0	502.7	502.4	502.7	512.0	525.0
155°	608.9	589.1	569.4	552.0	539.2	527.5	520.6	519.4	520.6	527.5	539.2
157.5°	608.9	593.1	576.4	562.6	551.5	542.4	535.9	535.9	535.9	542.4	551.5
160°	608.9	594.9	581.0	568.2	558.9	550.8	546.1	546.1	546.1	550.8	558.9
162.5°	608.9	596.8	583.8	573.8	565.4	558.2	554.5	555.4	554.5	558.2	565.4
165°	606.6	597.3	586.8	579.8	574.0	568.2	565.9	565.9	565.9	568.2	574.0
167.5°	603.8	597.0	589.4	584.0	580.8	576.4	575.2	576.4	575.2	576.4	580.8
170°	601.9	596.1	590.3	586.8	584.5	581.0	579.8	581.0	579.8	581.0	584.5
172.5°	600.1	595.2	591.2	588.7	587.3	584.7	584.5	585.6	584.5	584.7	587.3
175°	597.3	593.8	591.5	591.5	590.3	589.1	589.1	590.3	589.1	589.1	590.3
177.5°	594.2	592.4	591.5	591.5	591.5	590.5	591.5	592.4	591.5	590.5	591.5
180°	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5



TEST NUMBER: P332921

CATALOG NUMBER: S124RDIP-S575D1205U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7
2.5°	948.3	945.2	941.1	936.4	930.8	925.9	923.7	925.5	926.5	924.0	923.7
5°	919.4	909.7	901.9	890.2	880.9	873.1	867.6	865.3	866.1	859.9	858.3
7.5°	886.9	875.4	862.7	848.8	835.9	824.5	818.5	815.2	808.6	805.8	801.0
10°	866.1	850.5	838.1	821.7	807.0	793.3	786.7	781.3	774.7	771.5	764.9
12.5°	844.6	826.6	812.9	795.9	780.8	764.4	758.1	748.0	737.6	731.1	722.6
15°	814.3	792.6	775.8	755.6	737.7	719.0	702.3	683.6	676.6	661.8	653.3
17.5°	778.9	756.8	736.1	709.0	681.4	658.2	640.3	622.5	611.7	602.3	597.9
20°	755.6	735.4	706.6	675.1	644.3	618.6	604.2	592.6	580.9	574.3	569.6
22.5°	733.5	707.7	674.2	640.2	609.5	589.4	577.2	565.2	555.7	549.4	543.2
25°	696.5	662.6	627.2	588.3	567.3	549.8	536.5	526.8	521.0	512.8	509.7
27.5°	658.4	617.4	578.3	552.2	530.3	514.3	502.8	495.5	488.1	482.8	478.8
30°	629.1	587.5	552.5	527.6	505.4	492.2	482.8	474.3	468.5	464.2	461.1
32.5°	600.2	558.6	529.1	502.4	484.9	472.0	462.0	455.6	451.0	445.5	443.6
35°	558.3	521.4	495.7	471.6	453.7	442.0	434.2	427.6	423.7	422.2	421.0
37.5°	518.1	487.8	460.2	440.4	424.5	415.3	406.1	402.9	400.2	397.4	398.7
40°	492.6	464.2	439.7	418.7	405.8	395.7	390.2	386.4	384.0	384.0	384.0
42.5°	470.5	442.7	418.8	400.0	387.1	378.6	372.5	369.2	368.5	368.1	370.0
45°	436.2	410.5	386.4	370.8	359.9	351.3	347.8	345.1	345.1	346.7	347.1
47.5°	402.2	378.1	358.7	341.3	331.3	326.0	322.9	321.5	321.7	323.2	325.0
50°	381.3	357.6	338.5	322.9	313.6	308.5	305.8	305.0	305.8	305.8	308.5
52.5°	358.6	337.3	318.6	305.5	294.9	290.2	288.7	287.6	288.1	289.3	290.5
55°	325.3	306.2	288.3	275.9	268.1	265.0	261.5	261.9	261.1	261.9	261.9
57.5°	291.9	274.8	258.1	248.2	241.4	236.9	233.1	234.1	233.0	232.8	232.2
60°	270.4	251.7	238.5	229.6	221.8	217.9	214.4	215.2	214.0	213.2	211.7
62.5°	247.1	231.5	218.9	210.3	204.0	199.5	196.0	195.2	192.5	189.9	186.4
65°	213.2	200.4	189.1	180.9	175.1	171.6	168.9	166.5	160.7	154.5	151.4
67.5°	180.3	171.0	160.5	153.6	148.9	144.3	139.1	135.1	129.6	126.2	124.3
70°	159.1	150.2	141.2	134.6	129.6	125.3	119.4	116.7	112.8	111.3	109.3
72.5°	138.9	130.6	122.2	116.3	110.9	107.5	103.0	100.2	98.5	97.9	95.9
75°	108.2	101.6	95.3	89.9	85.6	83.3	81.3	79.4	78.6	75.1	73.1
77.5°	78.9	74.5	70.7	66.8	63.7	62.2	58.4	56.2	54.9	53.2	52.8
80°	61.5	58.4	54.5	52.1	47.9	46.3	44.7	44.4	44.0	43.6	43.2
82.5°	46.2	43.1	39.2	37.8	36.7	35.7	34.8	34.4	34.0	34.2	34.2
85°	23.3	21.8	21.8	21.4	21.0	20.6	20.2	20.2	19.8	20.2	19.8
87.5°	9.6	9.3	10.7	10.1	10.9	11.3	10.8	11.0	11.6	11.2	11.2
90°	9.3	9.3	16.3	16.3	18.6	20.9	19.8	20.9	22.1	23.2	23.2
92.5°	61.4	85.5	144.6	234.7	322.6	368.6	307.0	228.2	171.7	136.7	113.4
95°	96.4	145.3	246.3	436.9	714.6	947.0	973.8	861.0	680.9	525.2	412.5
97.5°	116.7	157.6	235.4	392.8	668.8	997.5	1223.4	1272.2	1205.2	1091.6	970.3
100°	132.5	169.7	238.2	369.5	606.6	934.2	1231.7	1401.4	1424.6	1367.7	1281.7
102.5°	150.1	185.5	247.5	363.0	564.7	855.2	1162.0	1394.9	1510.1	1526.6	1490.8
105°	180.1	213.8	269.6	366.0	528.7	762.3	1035.3	1301.4	1502.5	1617.5	1665.1
107.5°	211.0	244.3	295.4	383.2	522.2	710.2	933.1	1168.7	1382.8	1544.8	1648.4
110°	232.4	263.8	314.9	396.2	524.1	692.6	882.0	1088.8	1289.8	1458.3	1586.1



TEST NUMBER: P332921

CATALOG NUMBER: S124RDIP-S575D1205U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	252.9	284.2	333.5	410.2	529.6	684.2	853.1	1030.2	1208.0	1367.2	1495.0
115°	284.7	316.1	362.5	432.3	540.3	679.8	826.2	971.4	1114.4	1250.3	1361.9
117.5°	314.0	346.5	390.7	454.8	551.7	678.6	814.1	942.6	1060.9	1167.8	1262.4
120°	333.5	366.0	410.2	470.6	560.1	678.6	807.6	929.6	1037.7	1130.6	1213.1
122.5°	353.0	384.6	428.8	485.5	568.5	677.7	800.2	918.4	1022.8	1107.4	1179.7
125°	380.0	412.5	454.3	507.8	581.0	676.3	787.8	899.4	999.3	1079.5	1143.4
127.5°	404.8	437.6	478.0	527.1	591.0	673.7	771.3	876.1	971.7	1051.6	1112.3
130°	420.6	454.3	493.9	539.2	598.4	672.8	761.1	857.6	949.4	1028.4	1090.0
132.5°	435.5	467.4	506.9	551.3	604.9	671.9	751.8	838.0	924.3	1001.4	1063.0
135°	456.7	486.9	525.2	567.1	614.7	670.5	737.9	811.1	886.6	957.5	1015.6
137.5°	474.6	503.4	539.2	578.2	620.5	670.2	725.8	786.7	850.6	910.3	962.8
140°	485.7	513.6	548.5	585.6	625.2	669.3	719.3	772.7	827.3	879.6	928.4
142.5°	495.9	522.9	556.8	591.2	628.9	669.3	713.7	759.7	807.8	852.7	895.0
145°	510.1	535.7	565.9	597.3	631.0	667.0	704.2	741.4	780.9	815.7	848.3
147.5°	523.8	546.8	575.2	602.6	632.1	662.8	695.6	726.3	757.6	785.5	811.1
150°	532.2	554.3	579.8	605.4	632.1	660.0	689.1	717.0	743.7	766.9	787.8
152.5°	540.6	560.8	583.6	607.3	630.3	655.4	681.6	706.7	729.7	751.1	768.3
155°	552.0	569.4	589.1	608.9	627.5	648.4	670.5	691.4	710.0	727.4	741.4
157.5°	562.6	576.4	593.1	608.9	624.5	641.2	659.1	674.9	690.5	705.1	716.3
160°	568.2	581.0	594.9	608.9	621.7	635.6	650.7	664.7	677.4	690.2	699.5
162.5°	573.8	583.8	596.8	608.9	618.9	630.0	643.3	654.4	665.4	675.4	683.7
165°	579.8	586.8	597.3	606.6	613.5	621.7	631.0	640.3	647.2	655.4	661.2
167.5°	584.0	589.4	597.0	603.8	608.0	613.3	619.8	626.6	631.9	638.4	641.9
170°	586.8	590.3	596.1	601.9	604.2	607.7	612.4	618.2	621.7	626.3	629.8
172.5°	588.7	591.2	595.2	600.1	600.5	602.1	605.9	610.7	613.3	616.1	618.6
175°	591.5	591.5	593.8	597.3	596.1	596.1	598.4	600.8	601.9	604.2	604.2
177.5°	591.5	591.5	592.4	594.2	592.4	592.4	593.3	594.2	595.2	595.2	596.1
180°	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5



TEST NUMBER: P332921

CATALOG NUMBER: S124RDIP-S575D1205U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7
2.5°	921.8	922.4	920.3	919.6	920.3	922.4	921.8	923.7	924.0	926.5	925.5
5°	855.2	854.4	852.5	852.9	852.5	854.4	855.2	858.3	859.9	866.1	865.3
7.5°	798.2	795.2	796.1	792.9	796.1	795.2	798.2	801.0	805.8	808.6	815.2
10°	763.4	759.1	755.6	752.5	755.6	759.1	763.4	764.9	771.5	774.7	781.3
12.5°	715.8	712.1	707.3	708.3	707.3	712.1	715.8	722.6	731.1	737.6	748.0
15°	648.2	642.4	633.0	634.2	633.0	642.4	648.2	653.3	661.8	676.6	683.6
17.5°	591.0	591.1	586.8	587.8	586.8	591.1	591.0	597.9	602.3	611.7	622.5
20°	561.4	558.7	559.1	557.9	559.1	558.7	561.4	569.6	574.3	580.9	592.6
22.5°	540.9	537.6	534.8	532.4	534.8	537.6	540.9	543.2	549.4	555.7	565.2
25°	506.2	503.9	500.4	499.6	500.4	503.9	506.2	509.7	512.8	521.0	526.8
27.5°	475.7	475.2	473.8	472.0	473.8	475.2	475.7	478.8	482.8	488.1	495.5
30°	457.9	457.2	456.4	455.2	456.4	457.2	457.9	461.1	464.2	468.5	474.3
32.5°	442.1	441.6	440.8	440.9	440.8	441.6	442.1	443.6	445.5	451.0	455.6
35°	419.4	419.0	418.3	417.9	418.3	419.0	419.4	421.0	422.2	423.7	427.6
37.5°	398.3	399.3	398.8	398.7	398.8	399.3	398.3	398.7	397.4	400.2	402.9
40°	383.6	384.0	384.8	384.4	384.8	384.0	383.6	384.0	384.0	384.0	386.4
42.5°	371.5	371.6	372.7	371.3	372.7	371.6	371.5	370.0	368.1	368.5	369.2
45°	349.8	352.1	351.7	351.7	351.7	352.1	349.8	347.1	346.7	345.1	345.1
47.5°	326.0	328.1	328.6	328.5	328.6	328.1	326.0	325.0	323.2	321.7	321.5
50°	310.5	309.7	310.9	310.5	310.9	309.7	310.5	308.5	305.8	305.8	305.0
52.5°	291.5	291.7	291.6	291.2	291.6	291.7	291.5	290.5	289.3	288.1	287.6
55°	262.2	262.6	261.9	262.2	261.9	262.6	262.2	261.9	261.9	261.1	261.9
57.5°	230.5	228.6	229.4	228.5	229.4	228.6	230.5	232.2	232.8	233.0	234.1
60°	207.8	204.7	203.9	202.3	203.9	204.7	207.8	211.7	213.2	214.0	215.2
62.5°	182.2	180.1	177.4	178.7	177.4	180.1	182.2	186.4	189.9	192.5	195.2
65°	148.2	146.7	145.5	147.1	145.5	146.7	148.2	151.4	154.5	160.7	166.5
67.5°	122.7	121.9	121.9	121.1	121.9	121.9	122.7	124.3	126.2	129.6	135.1
70°	109.3	108.2	108.2	107.4	108.2	108.2	109.3	109.3	111.3	112.8	116.7
72.5°	95.6	94.5	94.8	94.3	94.8	94.5	95.6	95.9	97.9	98.5	100.2
75°	70.8	68.9	68.9	69.3	68.9	68.9	70.8	73.1	75.1	78.6	79.4
77.5°	52.8	52.4	53.0	52.3	53.0	52.4	52.8	52.8	53.2	54.9	56.2
80°	43.2	42.8	42.4	43.6	42.4	42.8	43.2	43.2	43.6	44.0	44.4
82.5°	33.5	33.5	33.4	34.9	33.4	33.5	33.5	34.2	34.2	34.0	34.4
85°	20.2	19.5	20.2	19.5	20.2	19.5	20.2	19.8	20.2	19.8	20.2
87.5°	12.0	12.0	11.4	11.7	11.4	12.0	12.0	11.2	11.2	11.6	11.0
90°	24.4	25.6	24.4	24.4	24.4	25.6	24.4	23.2	23.2	22.1	20.9
92.5°	99.7	93.4	89.5	89.5	89.5	93.4	99.7	113.4	136.7	171.7	228.2
95°	355.6	319.6	298.6	283.5	298.6	319.6	355.6	412.5	525.2	680.9	861.0
97.5°	886.8	816.9	782.0	757.9	782.0	816.9	886.8	970.3	1091.6	1205.2	1272.2
100°	1180.6	1109.7	1074.9	1065.6	1074.9	1109.7	1180.6	1281.7	1367.7	1424.6	1401.4
102.5°	1428.8	1377.4	1340.7	1333.3	1340.7	1377.4	1428.8	1490.8	1526.6	1510.1	1394.9
105°	1667.5	1658.2	1641.9	1634.9	1641.9	1658.2	1667.5	1665.1	1617.5	1502.5	1301.4
107.5°	1705.8	1732.3	1743.9	1747.0	1743.9	1732.3	1705.8	1648.4	1544.8	1382.8	1168.7
110°	1668.6	1717.4	1738.4	1748.8	1738.4	1717.4	1668.6	1586.1	1458.3	1289.8	1088.8



TEST NUMBER: P332921

CATALOG NUMBER: S124RDIP-S575D1205U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1588.7	1647.7	1677.0	1694.0	1677.0	1647.7	1588.7	1495.0	1367.2	1208.0	1030.2
115°	1453.7	1523.4	1560.6	1569.9	1560.6	1523.4	1453.7	1361.9	1250.3	1114.4	971.4
117.5°	1340.7	1399.3	1436.9	1444.1	1436.9	1399.3	1340.7	1262.4	1167.8	1060.9	942.6
120°	1279.4	1330.5	1360.7	1373.5	1360.7	1330.5	1279.4	1213.1	1130.6	1037.7	929.6
122.5°	1235.7	1279.4	1304.9	1317.7	1304.9	1279.4	1235.7	1179.7	1107.4	1022.8	918.4
125°	1189.9	1223.6	1245.7	1252.6	1245.7	1223.6	1189.9	1143.4	1079.5	999.3	899.4
127.5°	1159.0	1189.0	1207.6	1214.5	1207.6	1189.0	1159.0	1112.3	1051.6	971.7	876.1
130°	1137.6	1166.6	1185.2	1192.2	1185.2	1166.6	1137.6	1090.0	1028.4	949.4	857.6
132.5°	1109.7	1142.5	1160.1	1167.1	1160.1	1142.5	1109.7	1063.0	1001.4	924.3	838.0
135°	1062.1	1094.6	1113.2	1120.2	1113.2	1094.6	1062.1	1015.6	957.5	886.6	811.1
137.5°	1006.3	1038.4	1053.7	1062.1	1053.7	1038.4	1006.3	962.8	910.3	850.6	786.7
140°	969.1	994.7	1010.9	1020.2	1010.9	994.7	969.1	928.4	879.6	827.3	772.7
142.5°	931.0	954.7	969.1	975.6	969.1	954.7	931.0	895.0	852.7	807.8	759.7
145°	877.3	897.1	908.7	914.5	908.7	897.1	877.3	848.3	815.7	780.9	741.4
147.5°	832.5	849.4	858.3	860.3	858.3	849.4	832.5	811.1	785.5	757.6	726.3
150°	806.4	821.5	828.5	829.7	828.5	821.5	806.4	787.8	766.9	743.7	717.0
152.5°	784.1	796.4	800.6	801.8	800.6	796.4	784.1	768.3	751.1	729.7	706.7
155°	753.0	762.3	765.8	765.8	765.8	762.3	753.0	741.4	727.4	710.0	691.4
157.5°	725.1	732.1	734.2	734.2	734.2	732.1	725.1	716.3	705.1	690.5	674.9
160°	706.5	713.5	714.6	714.6	714.6	713.5	706.5	699.5	690.2	677.4	664.7
162.5°	688.8	695.8	697.0	696.0	697.0	695.8	688.8	683.7	675.4	665.4	654.4
165°	665.8	670.5	669.3	668.2	669.3	670.5	665.8	661.2	655.4	647.2	640.3
167.5°	644.2	647.2	647.0	646.1	647.0	647.2	644.2	641.9	638.4	631.9	626.6
170°	632.1	633.3	632.1	632.1	632.1	633.3	632.1	629.8	626.3	621.7	618.2
172.5°	620.0	621.2	620.0	618.2	620.0	621.2	620.0	618.6	616.1	613.3	610.7
175°	604.2	606.6	604.2	601.9	604.2	606.6	604.2	604.2	604.2	601.9	600.8
177.5°	595.2	596.1	594.2	592.4	594.2	596.1	595.2	596.1	595.2	595.2	594.2
180°	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5



TEST NUMBER: P332921

CATALOG NUMBER: S124RDIP-S575D1205U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7
2.5°	923.7	925.9	930.8	936.4	941.1	945.2	948.3	952.6	956.7	962.3	967.6
5°	867.6	873.1	880.9	890.2	901.9	909.7	919.4	928.0	940.4	952.9	964.9
7.5°	818.5	824.5	835.9	848.8	862.7	875.4	886.9	902.0	918.5	936.7	956.9
10°	786.7	793.3	807.0	821.7	838.1	850.5	866.1	884.0	902.7	924.8	949.7
12.5°	758.1	764.4	780.8	795.9	812.9	826.6	844.6	862.8	887.7	911.8	940.1
15°	702.3	719.0	737.7	755.6	775.8	792.6	814.3	833.0	856.8	890.6	922.9
17.5°	640.3	658.2	681.4	709.0	736.1	756.8	778.9	802.1	830.4	864.9	902.2
20°	604.2	618.6	644.3	675.1	706.6	735.4	755.6	781.3	810.5	847.8	886.3
22.5°	577.2	589.4	609.5	640.2	674.2	707.7	733.5	758.9	791.2	828.5	870.5
25°	536.5	549.8	567.3	588.3	627.2	662.6	696.5	725.6	759.9	797.2	843.9
27.5°	502.8	514.3	530.3	552.2	578.3	617.4	658.4	691.7	726.8	766.9	813.6
30°	482.8	492.2	505.4	527.6	552.5	587.5	629.1	668.1	703.5	745.1	793.7
32.5°	462.0	472.0	484.9	502.4	529.1	558.6	600.2	642.8	680.4	723.0	770.7
35°	434.2	442.0	453.7	471.6	495.7	521.4	558.3	602.3	642.0	687.5	733.0
37.5°	406.1	415.3	424.5	440.4	460.2	487.8	518.1	563.0	607.0	648.5	693.0
40°	390.2	395.7	405.8	418.7	439.7	464.2	492.6	536.5	580.5	621.8	666.5
42.5°	372.5	378.6	387.1	400.0	418.8	442.7	470.5	508.5	554.4	594.4	635.1
45°	347.8	351.3	359.9	370.8	386.4	410.5	436.2	470.0	513.2	551.3	587.1
47.5°	322.9	326.0	331.3	341.3	358.7	378.1	402.2	432.5	470.4	508.5	538.8
50°	305.8	308.5	313.6	322.9	338.5	357.6	381.3	408.5	442.4	479.0	504.2
52.5°	288.7	290.2	294.9	305.5	318.6	337.3	358.6	383.6	415.3	445.7	471.3
55°	261.5	265.0	268.1	275.9	288.3	306.2	325.3	349.0	373.5	399.2	421.0
57.5°	233.1	236.9	241.4	248.2	258.1	274.8	291.9	311.1	332.0	353.4	371.6
60°	214.4	217.9	221.8	229.6	238.5	251.7	270.4	287.1	303.1	322.5	340.8
62.5°	196.0	199.5	204.0	210.3	218.9	231.5	247.1	261.6	278.2	295.2	308.8
65°	168.9	171.6	175.1	180.9	189.1	200.4	213.2	224.5	239.3	251.7	264.2
67.5°	139.1	144.3	148.9	153.6	160.5	171.0	180.3	191.1	201.2	210.4	221.8
70°	119.4	125.3	129.6	134.6	141.2	150.2	159.1	166.5	174.7	183.6	193.8
72.5°	103.0	107.5	110.9	116.3	122.2	130.6	138.9	145.0	151.7	157.8	167.6
75°	81.3	83.3	85.6	89.9	95.3	101.6	108.2	113.6	117.5	122.9	130.0
77.5°	58.4	62.2	63.7	66.8	70.7	74.5	78.9	83.5	87.2	89.2	94.5
80°	44.7	46.3	47.9	52.1	54.5	58.4	61.5	65.8	67.3	69.3	74.3
82.5°	34.8	35.7	36.7	37.8	39.2	43.1	46.2	48.9	50.5	51.2	55.0
85°	20.2	20.6	21.0	21.4	21.8	21.8	23.3	25.3	28.0	28.0	29.2
87.5°	10.8	11.3	10.9	10.1	10.7	9.3	9.6	9.4	10.1	10.3	10.8
90°	19.8	20.9	18.6	16.3	16.3	9.3	9.3	8.1	7.0	3.5	1.2
92.5°	307.0	368.6	322.6	234.7	144.6	85.5	61.4	44.4	30.2	19.3	13.2
95°	973.8	947.0	714.6	436.9	246.3	145.3	96.4	68.6	53.5	41.8	38.3
97.5°	1223.4	997.5	668.8	392.8	235.4	157.6	116.7	92.7	78.8	68.8	68.8
100°	1231.7	934.2	606.6	369.5	238.2	169.7	132.5	110.4	96.4	88.3	88.3
102.5°	1162.0	855.2	564.7	363.0	247.5	185.5	150.1	129.0	116.0	108.8	106.9
105°	1035.3	762.3	528.7	366.0	269.6	213.8	180.1	159.2	145.3	139.4	136.0
107.5°	933.1	710.2	522.2	383.2	295.4	244.3	211.0	191.0	176.2	170.3	168.0
110°	882.0	692.6	524.1	396.2	314.9	263.8	232.4	211.5	197.5	191.7	189.4



TEST NUMBER: P332921

CATALOG NUMBER: S124RDIP-S575D1205U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	853.1	684.2	529.6	410.2	333.5	284.2	252.9	231.9	218.9	212.2	209.9
115°	826.2	679.8	540.3	432.3	362.5	316.1	284.7	262.6	251.0	242.9	239.4
117.5°	814.1	678.6	551.7	454.8	390.7	346.5	314.0	293.3	280.5	273.3	270.0
120°	807.6	678.6	560.1	470.6	410.2	366.0	333.5	313.7	301.0	292.8	290.5
122.5°	800.2	677.7	568.5	485.5	428.8	384.6	353.0	331.4	319.6	311.4	309.1
125°	787.8	676.3	581.0	507.8	454.3	412.5	380.0	357.9	345.1	338.1	333.5
127.5°	771.3	673.7	591.0	527.1	478.0	437.6	404.8	381.8	367.2	358.8	355.1
130°	761.1	672.8	598.4	539.2	493.9	454.3	420.6	398.6	381.1	371.8	367.2
132.5°	751.8	671.9	604.9	551.3	506.9	467.4	435.5	411.6	395.1	383.0	379.3
135°	737.9	670.5	614.7	567.1	525.2	486.9	456.7	432.3	412.5	400.9	396.2
137.5°	725.8	670.2	620.5	578.2	539.2	503.4	474.6	449.2	430.4	417.6	413.2
140°	719.3	669.3	625.2	585.6	548.5	513.6	485.7	461.3	441.6	428.8	425.3
142.5°	713.7	669.3	628.9	591.2	556.8	522.9	495.9	472.5	453.6	441.8	438.3
145°	704.2	667.0	631.0	597.3	565.9	535.7	510.1	488.0	471.8	460.2	456.7
147.5°	695.6	662.8	632.1	602.6	575.2	546.8	523.8	505.5	488.7	478.5	477.3
150°	689.1	660.0	632.1	605.4	579.8	554.3	532.2	514.8	500.8	491.5	490.4
152.5°	681.6	655.4	630.3	607.3	583.6	560.8	540.6	525.0	512.0	502.7	502.4
155°	670.5	648.4	627.5	608.9	589.1	569.4	552.0	539.2	527.5	520.6	519.4
157.5°	659.1	641.2	624.5	608.9	593.1	576.4	562.6	551.5	542.4	535.9	535.9
160°	650.7	635.6	621.7	608.9	594.9	581.0	568.2	558.9	550.8	546.1	546.1
162.5°	643.3	630.0	618.9	608.9	596.8	583.8	573.8	565.4	558.2	554.5	555.4
165°	631.0	621.7	613.5	606.6	597.3	586.8	579.8	574.0	568.2	565.9	565.9
167.5°	619.8	613.3	608.0	603.8	597.0	589.4	584.0	580.8	576.4	575.2	576.4
170°	612.4	607.7	604.2	601.9	596.1	590.3	586.8	584.5	581.0	579.8	581.0
172.5°	605.9	602.1	600.5	600.1	595.2	591.2	588.7	587.3	584.7	584.5	585.6
175°	598.4	596.1	596.1	597.3	593.8	591.5	591.5	590.3	589.1	589.1	590.3
177.5°	593.3	592.4	592.4	594.2	592.4	591.5	591.5	591.5	590.5	591.5	592.4
180°	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5



TEST NUMBER: P332921

CATALOG NUMBER: S124RDIP-S575D1205U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7
2.5°	971.6	974.4	977.5	983.4	988.4	990.6	995.0	998.1	997.1	1001.5	1009.0
5°	975.4	985.9	998.0	1010.4	1024.4	1036.1	1045.5	1054.8	1062.2	1071.1	1084.4
7.5°	974.8	993.5	1013.8	1036.1	1059.1	1078.9	1097.3	1116.0	1132.5	1150.7	1174.4
10°	972.3	997.2	1022.5	1051.7	1080.9	1108.5	1133.4	1156.7	1178.9	1202.6	1232.6
12.5°	969.5	998.1	1028.7	1063.8	1100.2	1133.4	1162.7	1196.3	1224.0	1254.6	1289.3
15°	957.1	995.7	1037.3	1082.8	1126.4	1171.1	1211.2	1252.5	1291.0	1327.5	1371.1
17.5°	943.0	987.4	1036.5	1090.3	1142.7	1197.0	1244.6	1296.6	1335.9	1385.0	1425.5
20°	931.5	979.3	1031.8	1092.1	1151.7	1212.0	1264.5	1317.4	1361.8	1411.2	1462.6
22.5°	917.5	970.0	1026.9	1089.3	1151.7	1217.6	1275.7	1328.3	1383.3	1438.9	1491.8
25°	894.9	949.4	1009.7	1078.1	1149.7	1217.0	1279.3	1344.7	1403.8	1464.1	1511.6
27.5°	867.2	924.4	988.0	1058.6	1132.1	1201.0	1274.3	1344.0	1403.5	1461.5	1502.9
30°	845.1	905.4	966.5	1038.1	1114.3	1188.3	1266.8	1336.5	1399.1	1451.3	1474.6
32.5°	822.4	879.6	942.5	1015.0	1093.2	1172.7	1250.7	1321.9	1379.8	1411.1	1411.7
35°	782.8	836.5	901.9	973.1	1053.2	1139.6	1218.6	1288.6	1324.0	1326.8	1288.6
37.5°	739.7	789.0	850.7	922.0	1009.7	1095.7	1176.3	1223.0	1234.9	1195.3	1124.8
40°	708.9	754.4	814.0	887.1	974.3	1063.0	1136.5	1170.7	1158.3	1094.1	1015.5
42.5°	676.5	718.9	776.3	848.5	936.0	1025.6	1088.3	1106.6	1073.6	999.5	907.5
45°	623.7	662.6	719.4	792.2	876.2	960.3	1007.7	998.4	943.5	855.6	752.5
47.5°	568.7	606.3	657.4	724.7	810.8	883.3	915.4	887.3	809.2	712.5	628.6
50°	532.3	570.8	617.9	682.1	760.7	830.7	851.3	808.5	721.7	628.8	551.7
52.5°	496.5	529.4	575.5	637.5	712.7	771.9	782.8	733.5	643.9	560.6	492.3
55°	442.0	472.0	510.9	569.2	634.2	684.4	678.6	615.1	533.8	462.6	408.9
57.5°	389.3	411.9	447.8	502.5	559.6	593.3	571.9	517.9	442.1	383.8	338.5
60°	354.5	375.5	408.9	456.8	507.0	526.0	508.1	449.4	389.5	336.2	298.0
62.5°	321.5	340.0	368.8	413.2	453.7	465.0	445.9	394.6	340.6	295.1	263.5
65°	273.5	290.6	315.2	346.7	374.7	380.1	367.7	315.2	274.3	236.2	214.4
67.5°	230.0	241.2	260.4	287.6	302.5	305.7	281.6	248.6	212.6	189.2	172.8
70°	200.8	208.5	226.4	241.2	253.3	253.7	231.5	205.0	177.4	158.4	146.3
72.5°	172.4	179.9	193.5	203.6	212.8	209.8	189.5	168.6	146.3	131.9	122.9
75°	133.1	139.7	146.7	151.4	151.4	147.5	132.7	117.1	104.3	95.7	93.0
77.5°	96.7	102.2	104.5	103.8	102.4	96.3	87.0	76.8	72.2	68.2	66.1
80°	75.9	78.2	79.0	77.0	74.7	67.7	61.5	57.2	52.9	51.4	50.6
82.5°	56.3	58.3	56.3	56.8	51.7	45.9	42.5	41.0	39.2	38.6	37.8
85°	30.0	29.6	28.8	26.8	23.3	22.6	22.2	21.8	21.0	21.4	20.6
87.5°	11.0	10.7	9.7	9.6	9.6	10.4	10.7	11.2	11.7	11.1	12.0
90°	3.5	7.0	8.1	9.3	9.3	16.3	16.3	18.6	20.9	19.8	20.9
92.5°	19.3	30.2	44.4	61.4	85.5	144.6	234.7	322.6	368.6	307.0	228.2
95°	41.8	53.5	68.6	96.4	145.3	246.3	436.9	714.6	947.0	973.8	861.0
97.5°	68.8	78.8	92.7	116.7	157.6	235.4	392.8	668.8	997.5	1223.4	1272.2
100°	88.3	96.4	110.4	132.5	169.7	238.2	369.5	606.6	934.2	1231.7	1401.4
102.5°	108.8	116.0	129.0	150.1	185.5	247.5	363.0	564.7	855.2	1162.0	1394.9
105°	139.4	145.3	159.2	180.1	213.8	269.6	366.0	528.7	762.3	1035.3	1301.4
107.5°	170.3	176.2	191.0	211.0	244.3	295.4	383.2	522.2	710.2	933.1	1168.7
110°	191.7	197.5	211.5	232.4	263.8	314.9	396.2	524.1	692.6	882.0	1088.8





TEST NUMBER: P332921

CATALOG NUMBER: S124RDIP-S575D1205U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	212.2	218.9	231.9	252.9	284.2	333.5	410.2	529.6	684.2	853.1	1030.2
115°	242.9	251.0	262.6	284.7	316.1	362.5	432.3	540.3	679.8	826.2	971.4
117.5°	273.3	280.5	293.3	314.0	346.5	390.7	454.8	551.7	678.6	814.1	942.6
120°	292.8	301.0	313.7	333.5	366.0	410.2	470.6	560.1	678.6	807.6	929.6
122.5°	311.4	319.6	331.4	353.0	384.6	428.8	485.5	568.5	677.7	800.2	918.4
125°	338.1	345.1	357.9	380.0	412.5	454.3	507.8	581.0	676.3	787.8	899.4
127.5°	358.8	367.2	381.8	404.8	437.6	478.0	527.1	591.0	673.7	771.3	876.1
130°	371.8	381.1	398.6	420.6	454.3	493.9	539.2	598.4	672.8	761.1	857.6
132.5°	383.0	395.1	411.6	435.5	467.4	506.9	551.3	604.9	671.9	751.8	838.0
135°	400.9	412.5	432.3	456.7	486.9	525.2	567.1	614.7	670.5	737.9	811.1
137.5°	417.6	430.4	449.2	474.6	503.4	539.2	578.2	620.5	670.2	725.8	786.7
140°	428.8	441.6	461.3	485.7	513.6	548.5	585.6	625.2	669.3	719.3	772.7
142.5°	441.8	453.6	472.5	495.9	522.9	556.8	591.2	628.9	669.3	713.7	759.7
145°	460.2	471.8	488.0	510.1	535.7	565.9	597.3	631.0	667.0	704.2	741.4
147.5°	478.5	488.7	505.5	523.8	546.8	575.2	602.6	632.1	662.8	695.6	726.3
150°	491.5	500.8	514.8	532.2	554.3	579.8	605.4	632.1	660.0	689.1	717.0
152.5°	502.7	512.0	525.0	540.6	560.8	583.6	607.3	630.3	655.4	681.6	706.7
155°	520.6	527.5	539.2	552.0	569.4	589.1	608.9	627.5	648.4	670.5	691.4
157.5°	535.9	542.4	551.5	562.6	576.4	593.1	608.9	624.5	641.2	659.1	674.9
160°	546.1	550.8	558.9	568.2	581.0	594.9	608.9	621.7	635.6	650.7	664.7
162.5°	554.5	558.2	565.4	573.8	583.8	596.8	608.9	618.9	630.0	643.3	654.4
165°	565.9	568.2	574.0	579.8	586.8	597.3	606.6	613.5	621.7	631.0	640.3
167.5°	575.2	576.4	580.8	584.0	589.4	597.0	603.8	608.0	613.3	619.8	626.6
170°	579.8	581.0	584.5	586.8	590.3	596.1	601.9	604.2	607.7	612.4	618.2
172.5°	584.5	584.7	587.3	588.7	591.2	595.2	600.1	600.5	602.1	605.9	610.7
175°	589.1	589.1	590.3	591.5	591.5	593.8	597.3	596.1	596.1	598.4	600.8
177.5°	591.5	590.5	591.5	591.5	591.5	592.4	594.2	592.4	592.4	593.3	594.2
180°	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5



TEST NUMBER: P332921

CATALOG NUMBER: S124RDIP-S575D1205U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	965.7	965.7	965.7	965.7	965.7	965.7	965.7
2.5°	1013.0	1014.3	1015.2	1018.3	1018.6	1021.4	1018.6
5°	1096.8	1102.3	1110.8	1119.4	1120.2	1125.6	1115.9
7.5°	1190.8	1203.4	1211.3	1225.1	1230.6	1234.0	1228.4
10°	1255.6	1267.2	1287.9	1298.0	1308.1	1309.6	1305.0
12.5°	1318.1	1336.6	1352.9	1372.1	1371.6	1385.3	1380.3
15°	1401.5	1420.5	1443.1	1464.5	1472.3	1472.3	1478.5
17.5°	1460.9	1495.9	1519.2	1536.0	1554.4	1557.6	1555.4
20°	1501.1	1538.8	1563.7	1585.5	1598.0	1601.5	1601.5
22.5°	1531.0	1563.1	1587.4	1607.0	1617.3	1621.4	1620.1
25°	1551.7	1579.3	1594.1	1599.9	1602.6	1601.8	1594.5
27.5°	1523.3	1522.1	1512.7	1494.8	1481.4	1473.2	1463.9
30°	1469.2	1448.9	1425.6	1399.9	1366.8	1341.5	1333.8
32.5°	1388.6	1343.1	1303.6	1260.8	1225.2	1199.9	1189.3
35°	1232.6	1160.6	1101.9	1050.5	1013.2	989.8	982.0
37.5°	1047.6	977.9	905.2	855.4	824.4	800.8	792.0
40°	929.9	854.0	790.6	743.9	712.0	689.1	688.7
42.5°	822.5	750.1	690.4	656.8	622.4	607.2	607.1
45°	673.5	615.5	564.9	538.5	517.9	505.4	501.9
47.5°	557.6	509.7	476.0	454.9	438.1	430.2	425.0
50°	492.6	450.6	423.7	405.4	396.1	386.0	385.2
52.5°	438.4	404.5	383.6	368.7	356.9	350.8	351.0
55°	368.5	341.6	326.8	315.5	306.2	301.5	299.6
57.5°	310.4	290.3	279.5	269.2	265.2	261.5	260.5
60°	274.3	260.7	250.6	242.4	236.6	235.4	235.0
62.5°	244.4	230.2	223.2	216.9	212.6	210.8	210.1
65°	201.5	191.0	184.8	179.8	178.2	175.5	175.1
67.5°	162.5	156.2	152.1	148.6	146.4	146.3	146.3
70°	138.5	135.0	131.5	129.6	128.4	127.6	127.6
72.5°	118.0	115.4	112.5	111.5	111.3	110.5	110.2
75°	89.9	87.2	87.5	85.6	84.0	82.1	80.9
77.5°	63.7	61.8	61.4	61.2	59.8	59.6	60.2
80°	49.4	47.5	47.1	47.5	47.1	45.9	45.9
82.5°	37.6	36.0	35.6	35.3	34.9	35.3	34.7
85°	20.2	19.5	19.5	19.5	20.2	19.8	19.5
87.5°	11.6	11.5	11.8	11.7	12.0	11.4	11.7
90°	22.1	23.2	23.2	24.4	25.6	24.4	24.4
92.5°	171.7	136.7	113.4	99.7	93.4	89.5	89.5
95°	680.9	525.2	412.5	355.6	319.6	298.6	283.5
97.5°	1205.2	1091.6	970.3	886.8	816.9	782.0	757.9
100°	1424.6	1367.7	1281.7	1180.6	1109.7	1074.9	1065.6
102.5°	1510.1	1526.6	1490.8	1428.8	1377.4	1340.7	1333.3
105°	1502.5	1617.5	1665.1	1667.5	1658.2	1641.9	1634.9
107.5°	1382.8	1544.8	1648.4	1705.8	1732.3	1743.9	1747.0
110°	1289.8	1458.3	1586.1	1668.6	1717.4	1738.4	1748.8



TEST NUMBER: P332921

CATALOG NUMBER: S124RDIP-S575D1205U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	1208.0	1367.2	1495.0	1588.7	1647.7	1677.0	1694.0
115°	1114.4	1250.3	1361.9	1453.7	1523.4	1560.6	1569.9
117.5°	1060.9	1167.8	1262.4	1340.7	1399.3	1436.9	1444.1
120°	1037.7	1130.6	1213.1	1279.4	1330.5	1360.7	1373.5
122.5°	1022.8	1107.4	1179.7	1235.7	1279.4	1304.9	1317.7
125°	999.3	1079.5	1143.4	1189.9	1223.6	1245.7	1252.6
127.5°	971.7	1051.6	1112.3	1159.0	1189.0	1207.6	1214.5
130°	949.4	1028.4	1090.0	1137.6	1166.6	1185.2	1192.2
132.5°	924.3	1001.4	1063.0	1109.7	1142.5	1160.1	1167.1
135°	886.6	957.5	1015.6	1062.1	1094.6	1113.2	1120.2
137.5°	850.6	910.3	962.8	1006.3	1038.4	1053.7	1062.1
140°	827.3	879.6	928.4	969.1	994.7	1010.9	1020.2
142.5°	807.8	852.7	895.0	931.0	954.7	969.1	975.6
145°	780.9	815.7	848.3	877.3	897.1	908.7	914.5
147.5°	757.6	785.5	811.1	832.5	849.4	858.3	860.3
150°	743.7	766.9	787.8	806.4	821.5	828.5	829.7
152.5°	729.7	751.1	768.3	784.1	796.4	800.6	801.8
155°	710.0	727.4	741.4	753.0	762.3	765.8	765.8
157.5°	690.5	705.1	716.3	725.1	732.1	734.2	734.2
160°	677.4	690.2	699.5	706.5	713.5	714.6	714.6
162.5°	665.4	675.4	683.7	688.8	695.8	697.0	696.0
165°	647.2	655.4	661.2	665.8	670.5	669.3	668.2
167.5°	631.9	638.4	641.9	644.2	647.2	647.0	646.1
170°	621.7	626.3	629.8	632.1	633.3	632.1	632.1
172.5°	613.3	616.1	618.6	620.0	621.2	620.0	618.2
175°	601.9	604.2	604.2	604.2	606.6	604.2	601.9
177.5°	595.2	595.2	596.1	595.2	596.1	594.2	592.4
180°	591.5	591.5	591.5	591.5	591.5	591.5	591.5

(END OF REPORT)